

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P1046636

Luminaire Tested: FMNL1515FS5--950

Issue Date: 07/03/2025

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P1046636
Test Lab: Cooper lighting solutions
Issue Date: 07/03/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: FMNL1515FS5--950
Description: HALO 15 inch 90 CRI COLOR SELECTABLE flush mount White Trim FIXTURE with night light
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1510.4 lumens
Efficiency: N/A
Efficacy: 89.4 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.41
Luminous Opening: Circular (Dia: 1.2' x H: 0')
CIE Type: Direct

Input Watts (W): 16.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P1046636
CATALOG NUMBER: FMNL1515FS5--950

Luminous Intensity Polar Plot



TEST NUMBER: P1046636
CATALOG NUMBER: FMNL1515FS5--950

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.0	2.8
10°-20°	123.8	8.2
20°-30°	189.8	12.6
30°-40°	233.0	15.4
40°-50°	247.7	16.4
50°-60°	232.2	15.4
60°-70°	188.0	12.4
70°-80°	124.3	8.2
80°-90°	63.8	4.2
90°-100°	28.4	1.9
100°-110°	15.6	1.0
110°-120°	10.2	0.7
120°-130°	5.9	0.4
130°-140°	3.1	0.2
140°-150°	1.3	0.1
150°-160°	0.4	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	356.6	23.6
0°-40°	589.5	39.0
0°-60°	1069.4	70.8
0°-90°	1445.4	95.7
90°-120°	54.2	3.6
90°-150°	64.5	4.3
90°-180°	65.0	4.3
0°-180°	1510.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	454	
5°	452	43
15°	438	124
25°	411	190
35°	372	233
45°	321	248
55°	260	232
65°	190	188
75°	118	124
85°	57	52
90°	37	21
95°	25	19
105°	15	16
115°	10	10
125°	6	6
135°	4	3
145°	2	1
155°	1	0
165°	0	0
175°	0	0
180°	0	

TEST NUMBER: P1046636
CATALOG NUMBER: FMNL1515FS5--950

CANDELA DISTRIBUTION (FULL):

0°	
0°	454.2
2.5°	453.3
5°	452.3
7.5°	450.5
10°	446.8
12.5°	443.0
15°	438.4
17.5°	432.8
20°	426.2
22.5°	419.7
25°	411.3
27.5°	402.9
30°	393.6
32.5°	383.3
35°	372.1
37.5°	360.9
40°	347.9
42.5°	334.8
45°	320.8
47.5°	306.8
50°	291.9
52.5°	276.1
55°	260.2
57.5°	242.5
60°	225.7
62.5°	208.0
65°	190.3
67.5°	171.6
70°	153.0
72.5°	135.2
75°	117.5
77.5°	99.8
80°	83.9
82.5°	70.0
85°	56.9
87.5°	46.6
90°	37.3
92.5°	30.8
95°	25.2
97.5°	20.5
100°	17.7
102.5°	15.9
105°	14.9
107.5°	13.1
110°	12.1

TEST NUMBER: P1046636
CATALOG NUMBER: FMNL1515FS5--950

CANDELA DISTRIBUTION (continued):

	0°
112.5°	11.2
115°	10.3
117.5°	9.3
120°	8.4
122.5°	7.5
125°	6.5
127.5°	5.6
130°	4.7
132.5°	4.7
135°	3.7
137.5°	3.7
140°	2.8
142.5°	2.8
145°	1.9
147.5°	1.9
150°	0.9
152.5°	0.9
155°	0.9
157.5°	0.9
160°	0.9
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

TEST NUMBER: P1046636
CATALOG NUMBER: FMNL1515FS5--950

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.9	18.5	17.4	18.9	19.3	16.9	18.5	17.4	18.9	19.3
	3H	19.0	20.4	19.4	20.9	21.3	19.0	20.4	19.4	20.9	21.3
	4H	19.9	21.2	20.3	21.7	22.1	19.9	21.2	20.3	21.7	22.1
	6H	20.6	21.9	21.1	22.4	22.9	20.6	21.9	21.1	22.4	22.9
	8H	21.0	22.2	21.5	22.7	23.2	21.0	22.2	21.5	22.7	23.2
	12H	21.4	22.5	21.9	23.0	23.5	21.4	22.5	21.9	23.0	23.5
4H	2H	17.6	19.0	18.1	19.4	19.9	17.6	19.0	18.1	19.4	19.9
	3H	19.9	21.1	20.4	21.6	22.1	19.9	21.1	20.4	21.6	22.1
	4H	20.9	22.0	21.4	22.5	23.0	20.9	22.0	21.4	22.5	23.0
	6H	21.9	22.8	22.4	23.3	23.9	21.9	22.8	22.4	23.3	23.9
	8H	22.3	23.2	22.9	23.7	24.3	22.3	23.2	22.9	23.7	24.3
	12H	22.8	23.6	23.3	24.1	24.7	22.8	23.6	23.3	24.1	24.7
8H	4H	21.4	22.2	21.9	22.8	23.3	21.4	22.2	21.9	22.8	23.3
	6H	22.5	23.2	23.0	23.8	24.4	22.5	23.2	23.0	23.8	24.4
	8H	23.1	23.7	23.6	24.3	24.9	23.1	23.7	23.6	24.3	24.9
	12H	23.7	24.3	24.3	24.9	25.5	23.7	24.3	24.3	24.9	25.5
12H	4H	21.4	22.2	22.0	22.8	23.3	21.4	22.2	22.0	22.8	23.3
	6H	22.6	23.3	23.2	23.8	24.5	22.6	23.3	23.2	23.8	24.5
	8H	23.3	23.9	23.9	24.4	25.1	23.3	23.9	23.9	24.4	25.1

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Halo Home

Report Number: SP1-2506-468-17

Test Date: 07/09/2025

Luminaire Tested: FMNL1515FS5-5000K

Data in this report applies to families of products including FMNL1515FS5-5000K

The results of this test have not been influenced by sources from within Eaton or from external interests.

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-468-17
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 07/10/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Halo Home
 Catalog Number: **FMNL1515FS5-5000K**
 Description: HALO FLUSH MOUNT NIGHT LIGHT 15 INCH

Spectral Parameters

CCT (K): 5247
 CIE u' : 0.2072
 CIE v' : 0.4837
 Duv: 0.0025
 CIE x: 0.3388
 CIE y: 0.3514
 CIE z: 0.3098
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 565
 Purity: 7.10182
 R_f: 91.8
 R_g: 101.9

CRI (Ra): 94.5
 R1: 97.3
 R2: 94.6
 R3: 90.4
 R4: 94.4
 R5: 96.0
 R6: 92.1
 R7: 95.5
 R8: 95.6
 R9: 84.6
 R10: 85.5
 R11: 92.9
 R12: 73.9
 R13: 96.3
 R14: 94.0
 R15: 96.7



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 24.0


REPORT NUMBER: SP1-2506-468-17

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025


Sample Number	Condition	Description
P2506-468-LM.3	Good	HALO FLUSH MOUNT NIGHT LIGHT 15 INCH

REPORT NUMBER: SP1-2506-468-17

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-468-17

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	172	NR	620	216	NR	750	4	NR	880	0	NR
365	0	NR	495	200	NR	625	222	NR	755	3	NR	885	0	NR
370	0	NR	500	230	NR	630	1000	NR	760	3	NR	890	0	NR
375	0	NR	505	255	NR	635	624	NR	765	2	NR	895	0	NR
380	0	NR	510	273	NR	640	120	NR	770	2	NR	900	0	NR
385	1	NR	515	285	NR	645	120	NR	775	2	NR	905	0	NR
390	2	NR	520	292	NR	650	102	NR	780	2	NR	910	0	NR
395	3	NR	525	295	NR	655	81	NR	785	1	NR	915	0	NR
400	4	NR	530	296	NR	660	66	NR	790	1	NR	920	0	NR
405	5	NR	535	296	NR	665	52	NR	795	1	NR	925	0	NR
410	8	NR	540	295	NR	670	52	NR	800	1	NR	930	0	NR
415	14	NR	545	293	NR	675	39	NR	805	1	NR	935	0	NR
420	25	NR	550	291	NR	680	33	NR	810	1	NR	940	0	NR
425	46	NR	555	289	NR	685	28	NR	815	1	NR	945	0	NR
430	81	NR	560	286	NR	690	24	NR	820	1	NR	950	0	NR
435	139	NR	565	282	NR	695	21	NR	825	0	NR	955	0	NR
440	235	NR	570	276	NR	700	18	NR	830	0	NR	960	0	NR
445	404	NR	575	269	NR	705	15	NR	835	0	NR	965	0	NR
450	534	NR	580	262	NR	710	13	NR	840	0	NR	970	0	NR
455	425	NR	585	253	NR	715	11	NR	845	0	NR	975	0	NR
460	293	NR	590	243	NR	720	9	NR	850	0	NR	980	0	NR
465	243	NR	595	231	NR	725	8	NR	855	0	NR	985	0	NR
470	187	NR	600	223	NR	730	7	NR	860	0	NR	990	0	NR
475	147	NR	605	217	NR	735	6	NR	865	0	NR	995	0	NR
480	142	NR	610	246	NR	740	5	NR	870	0	NR	1000	0	NR
485	153	NR	615	270	NR	745	4	NR	875	0	NR			

REPORT NUMBER: SP1-2506-468-17

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 2.11

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	172	NR	620	216	NR	750	4	NR	880	0	NR
365	0	NR	495	200	NR	625	222	NR	755	3	NR	885	0	NR
370	0	NR	500	230	NR	630	1000	NR	760	3	NR	890	0	NR
375	0	NR	505	255	NR	635	624	NR	765	2	NR	895	0	NR
380	0	NR	510	273	NR	640	120	NR	770	2	NR	900	0	NR
385	1	NR	515	285	NR	645	120	NR	775	2	NR	905	0	NR
390	2	NR	520	292	NR	650	102	NR	780	2	NR	910	0	NR
395	3	NR	525	295	NR	655	81	NR	785	1	NR	915	0	NR
400	4	NR	530	296	NR	660	66	NR	790	1	NR	920	0	NR
405	5	NR	535	296	NR	665	52	NR	795	1	NR	925	0	NR
410	8	NR	540	295	NR	670	52	NR	800	1	NR	930	0	NR
415	14	NR	545	293	NR	675	39	NR	805	1	NR	935	0	NR
420	25	NR	550	291	NR	680	33	NR	810	1	NR	940	0	NR
425	46	NR	555	289	NR	685	28	NR	815	1	NR	945	0	NR
430	81	NR	560	286	NR	690	24	NR	820	1	NR	950	0	NR
435	139	NR	565	282	NR	695	21	NR	825	0	NR	955	0	NR
440	235	NR	570	276	NR	700	18	NR	830	0	NR	960	0	NR
445	404	NR	575	269	NR	705	15	NR	835	0	NR	965	0	NR
450	534	NR	580	262	NR	710	13	NR	840	0	NR	970	0	NR
455	425	NR	585	253	NR	715	11	NR	845	0	NR	975	0	NR
460	293	NR	590	243	NR	720	9	NR	850	0	NR	980	0	NR
465	243	NR	595	231	NR	725	8	NR	855	0	NR	985	0	NR
470	187	NR	600	223	NR	730	7	NR	860	0	NR	990	0	NR
475	147	NR	605	217	NR	735	6	NR	865	0	NR	995	0	NR
480	142	NR	610	246	NR	740	5	NR	870	0	NR	1000	0	NR
485	153	NR	615	270	NR	745	4	NR	875	0	NR			

REPORT NUMBER: SP1-2506-468-17

Melanopic Flux vs. Wavelength








Melanopic Lumens: NR

M/P: 4.54


λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	172	NR	620	216	NR	750	4	NR	880	0	NR
365	0	NR	495	200	NR	625	222	NR	755	3	NR	885	0	NR
370	0	NR	500	230	NR	630	1000	NR	760	3	NR	890	0	NR
375	0	NR	505	255	NR	635	624	NR	765	2	NR	895	0	NR
380	0	NR	510	273	NR	640	120	NR	770	2	NR	900	0	NR
385	1	NR	515	285	NR	645	120	NR	775	2	NR	905	0	NR
390	2	NR	520	292	NR	650	102	NR	780	2	NR	910	0	NR
395	3	NR	525	295	NR	655	81	NR	785	1	NR	915	0	NR
400	4	NR	530	296	NR	660	66	NR	790	1	NR	920	0	NR
405	5	NR	535	296	NR	665	52	NR	795	1	NR	925	0	NR
410	8	NR	540	295	NR	670	52	NR	800	1	NR	930	0	NR
415	14	NR	545	293	NR	675	39	NR	805	1	NR	935	0	NR
420	25	NR	550	291	NR	680	33	NR	810	1	NR	940	0	NR
425	46	NR	555	289	NR	685	28	NR	815	1	NR	945	0	NR
430	81	NR	560	286	NR	690	24	NR	820	1	NR	950	0	NR
435	139	NR	565	282	NR	695	21	NR	825	0	NR	955	0	NR
440	235	NR	570	276	NR	700	18	NR	830	0	NR	960	0	NR
445	404	NR	575	269	NR	705	15	NR	835	0	NR	965	0	NR
450	534	NR	580	262	NR	710	13	NR	840	0	NR	970	0	NR
455	425	NR	585	253	NR	715	11	NR	845	0	NR	975	0	NR
460	293	NR	590	243	NR	720	9	NR	850	0	NR	980	0	NR
465	243	NR	595	231	NR	725	8	NR	855	0	NR	985	0	NR
470	187	NR	600	223	NR	730	7	NR	860	0	NR	990	0	NR
475	147	NR	605	217	NR	735	6	NR	865	0	NR	995	0	NR
480	142	NR	610	246	NR	740	5	NR	870	0	NR	1000	0	NR
485	153	NR	615	270	NR	745	4	NR	875	0	NR			

REPORT NUMBER: SP1-2506-468-17




TM-30-18
Summary
 $R_f = 91.8$
 $R_g = 101.9$
 CIE $R_a = 94.5$
 $R_9 = 84.6$

Color Vector Graphics


Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 85	CES26 = 91	CES51 = 99	CES76 = 82
CES02 = 60	CES27 = 93	CES52 = 96	CES77 = 87
CES03 = 31	CES28 = 93	CES53 = 95	CES78 = 79
CES04 = 68	CES29 = 93	CES54 = 96	CES79 = 95
CES05 = 48	CES30 = 97	CES55 = 95	CES80 = 91
CES06 = 50	CES31 = 93	CES56 = 96	CES81 = 86
CES07 = 41	CES32 = 85	CES57 = 95	CES82 = 96
CES08 = 40	CES33 = 96	CES58 = 96	CES83 = 96
CES09 = 29	CES34 = 89	CES59 = 99	CES84 = 93
CES10 = 73	CES35 = 93	CES60 = 94	CES85 = 85
CES11 = 55	CES36 = 83	CES61 = 94	CES86 = 91
CES12 = 61	CES37 = 91	CES62 = 89	CES87 = 90
CES13 = 42	CES38 = 92	CES63 = 93	CES88 = 96
CES14 = 74	CES39 = 98	CES64 = 92	CES89 = 88
CES15 = 71	CES40 = 95	CES65 = 90	CES90 = 98
CES16 = 46	CES41 = 98	CES66 = 88	CES91 = 74
CES17 = 48	CES42 = 87	CES67 = 87	CES92 = 83
CES18 = 56	CES43 = 89	CES68 = 88	CES93 = 89
CES19 = 70	CES44 = 99	CES69 = 89	CES94 = 81
CES20 = 65	CES45 = 92	CES70 = 85	CES95 = 84
CES21 = 84	CES46 = 95	CES71 = 79	CES96 = 92
CES22 = 77	CES47 = 94	CES72 = 93	CES97 = 92
CES23 = 91	CES48 = 97	CES73 = 78	CES98 = 94
CES24 = 89	CES49 = 93	CES74 = 93	CES99 = 99
CES25 = 70	CES50 = 98	CES75 = 79	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)