

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P990979

Luminaire Tested: **ML4ALSFLD2W1E-TIR4D40FL-TL4RDMW-600LM-3000K**

Issue Date: 5/13/2025

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
Report Number: P990979
Test Lab: Cooper Lighting Solutions
Issue Date: 5/13/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: ML4ALSFLD2W1E-TIR4D40FL-TL4RDMW-600LM-3000K
Description: 4IN ROUND ML FLEX ADJUSTABLE, SELECTABLE CCT, WITH 40D TIR, MATTE WHITE TRIM
Light Source: (1) D2W LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 607.7 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.64
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 8.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P990979

CATALOG NUMBER: ML4ALSFLD2W1E-TIR4D40FL-TL4RDMW-600LM-3000K

Luminous Intensity Polar Plot



TEST NUMBER: P990979

CATALOG NUMBER: ML4ALSFLD2W1E-TIR4D40FL-TL4RDMW-600LM-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	98		98	97	96	94
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	89	101	96	91	88	93	90	87		91	88	85		89	86	84	82
4	99	91	86	82	97	90	86	82	88	84	81		86	83	80		84	81	79	78
5	94	86	81	77	93	85	80	76	84	79	76		82	78	75		81	77	74	73
6	90	82	76	72	89	81	76	72	79	75	71		78	74	71		77	73	70	69
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		73	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	61	59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	140922
5°	135493
10°	121328
15°	99450
20°	73402
25°	48491
30°	29155
35°	16865
40°	9967
45°	6262
50°	4279
55°	3333
60°	2738
65°	2714
70°	2452
75°	1763
80°	426
85°	0

TEST NUMBER: P990979

CATALOG NUMBER: ML4ALSFLD2W1E-TIR4D40FL-TL4RDMW-600LM-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.4	16.5
10°-20°	213.1	35.1
20°-30°	164.4	27.1
30°-40°	73.7	12.1
40°-50°	29.1	4.8
50°-60°	14.1	2.3
60°-70°	8.9	1.5
70°-80°	3.7	0.6
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	478.0	78.6
0°-40°	551.7	90.8
0°-60°	594.8	97.9
0°-90°	607.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	607.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1142	
5°	1094	100
15°	779	213
25°	356	164
35°	112	74
45°	36	29
55°	16	14
65°	9	9
75°	4	4
85°	0	0
90°	0	

TEST NUMBER: P990979
CATALOG NUMBER: ML4ALSFLD2W1E-TIR4D40FL-TL4RDMW-600LM-3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1142.5
1°	1139.4
2°	1133.8
3°	1124.6
4°	1111.0
5°	1094.3
6°	1075.7
7°	1052.2
8°	1026.2
9°	997.8
10°	968.7
11°	933.4
12°	897.5
13°	861.7
14°	821.5
15°	778.8
16°	736.7
17°	693.4
18°	650.1
19°	603.7
20°	559.2
22.5°	452.8
25°	356.3
27.5°	271.6
30°	204.7
32.5°	152.2
35°	112.0
37.5°	82.9
40°	61.9
42.5°	46.4
45°	35.9
47.5°	27.8
50°	22.3
52.5°	17.9
55°	15.5
57.5°	13.0
60°	11.1
62.5°	9.9
65°	9.3
67.5°	8.0
70°	6.8
72.5°	4.9
75°	3.7
77.5°	1.9
80°	0.6

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



TEST NUMBER: P990979
CATALOG NUMBER: ML4ALSFLD2W1E-TIR4D40FL-TL4RDMW-600LM-3000K

CANDELA DISTRIBUTION (continued):

	0°
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)