

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P997168

Luminaire Tested: **SMX4SLSFSD2W-1000LM-3500K**

Issue Date: 3/11/2025



Test Information

Test Method: LM-41-14
Report Number: P997168
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A2410456A001)
Test Lab:
Issue Date: 3/11/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: SMX4SLSFSD2W-1000LM-3500K
Description: 4IN SQAURE, 90CRI, DIMMING TO 10%, DAMP LOCATION
Light Source: SELECTABLE CCT 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1109.2 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.37
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 11.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P997168

CATALOG NUMBER: SMX4SLSFSD2W-1000LM-3500K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997168

CATALOG NUMBER: SMX4SLSFSD2W-1000LM-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84		
2	99	91	84	78	96	89	83	77	85	80	76	82	78	74	79	76	72	70		
3	90	80	72	65	88	78	71	65	75	69	63	72	67	62	70	65	61	59		
4	83	71	62	55	80	69	61	55	67	60	54	64	58	53	62	57	53	50		
5	76	63	54	48	74	62	54	47	60	52	47	58	51	46	56	50	46	44		
6	70	57	48	41	68	56	47	41	54	47	41	52	46	41	51	45	40	38		
7	65	52	43	37	63	51	42	36	49	42	36	48	41	36	46	40	36	34		
8	61	47	38	33	59	46	38	33	45	38	32	44	37	32	43	36	32	30		
9	57	43	35	29	55	43	35	29	41	34	29	40	34	29	39	33	29	27		
10	53	40	32	27	52	39	32	27	38	31	26	37	31	26	36	30	26	24		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	39201	39201	39201	39201
5°	39231	39152	39192	39142
10°	39133	39023	39063	39013
15°	38977	38854	38865	38844
20°	38771	38624	38603	38624
25°	38476	38302	38269	38313
30°	38120	37938	37881	37949
35°	37708	37514	37442	37514
40°	37238	37031	36928	37006
45°	36693	36456	36358	36442
50°	36029	35767	35644	35736
55°	35155	34913	34775	34862
60°	34041	33764	33646	33705
65°	32486	32229	32065	32135
70°	30229	29998	29795	29824
75°	26809	26656	26465	26427
80°	21516	21459	21232	21118
85°	13722	13496	13722	13155



TEST NUMBER: P997168
CATALOG NUMBER: SMX4SLSFSD2W-1000LM-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.5	3.4
10°-20°	107.2	9.7
20°-30°	162.0	14.6
30°-40°	194.7	17.6
40°-50°	201.3	18.1
50°-60°	181.0	16.3
60°-70°	136.1	12.3
70°-80°	73.7	6.6
80°-90°	15.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	306.7	27.7
0°-40°	501.4	45.2
0°-60°	883.7	79.7
0°-90°	1109.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1109.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	397	397	397	397	397	
5°	395	395	395	394	395	38
15°	381	380	380	380	381	108
25°	353	351	351	351	353	163
35°	312	311	310	311	312	196
45°	262	261	260	261	262	202
55°	204	203	202	202	204	182
65°	139	138	137	137	139	137
75°	70	70	69	69	70	74
85°	12	12	12	12	12	16
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997168

CATALOG NUMBER: SMX4SLSFSD2W-1000LM-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	396.6	396.6	396.6	396.6	396.6	396.6	396.6	396.6	396.6	396.6	396.6
0.5°	397.4	396.9	396.7	396.4	396.1	396.3	396.7	396.7	396.9	397.0	396.8
1°	397.0	397.1	396.4	396.5	396.3	396.2	396.4	396.8	396.8	397.0	396.4
1.5°	397.0	396.6	396.7	396.3	396.1	396.1	396.6	396.4	397.1	396.6	396.4
2°	396.9	396.9	396.3	396.3	395.6	396.1	396.2	396.3	396.6	396.7	396.3
2.5°	396.7	396.4	396.1	395.5	395.8	395.7	396.1	396.0	396.7	396.5	395.8
3°	396.7	396.4	396.0	396.0	395.6	395.7	395.7	395.9	396.1	396.4	395.8
3.5°	396.6	396.4	395.6	395.5	395.3	395.3	395.6	395.7	396.2	396.1	395.6
4°	395.9	396.0	395.5	395.1	395.2	395.1	395.1	395.2	395.5	395.6	395.3
4.5°	395.7	395.6	395.2	394.8	394.5	394.8	395.1	395.0	395.5	395.4	395.0
5°	395.4	395.2	394.8	394.5	394.6	394.6	394.3	394.7	395.0	395.0	394.6
5.5°	395.2	395.0	394.4	394.2	393.8	393.9	394.4	393.9	394.5	394.7	394.1
6°	394.7	394.7	394.1	393.9	393.4	393.6	393.6	393.9	394.1	394.3	393.9
6.5°	394.3	393.9	393.4	393.2	392.9	393.0	393.5	393.1	393.8	393.8	393.3
7°	393.5	393.5	393.0	392.6	392.8	392.6	392.5	392.9	393.1	393.2	393.0
7.5°	393.5	393.1	392.4	392.0	392.1	391.8	392.3	392.2	392.6	392.5	392.4
8°	392.6	392.5	392.2	391.7	391.4	391.7	391.7	391.6	391.9	392.2	391.7
8.5°	392.3	391.8	391.1	390.7	391.0	390.4	390.8	390.9	391.4	391.2	391.2
9°	391.2	391.2	390.7	390.5	390.1	390.3	390.2	390.3	390.5	391.1	390.3
9.5°	390.9	390.6	389.9	389.4	389.7	389.4	389.7	389.4	390.1	389.9	389.8
10°	389.9	389.9	389.3	388.8	388.8	388.6	388.5	388.7	389.2	389.3	389.0
10.5°	389.4	388.9	388.5	387.9	388.0	387.8	388.3	387.8	388.5	388.7	388.5
11°	388.5	388.4	387.7	387.4	387.2	387.3	386.7	387.3	387.5	387.6	387.3
11.5°	387.9	387.4	386.9	386.5	386.4	386.2	386.5	386.3	386.9	387.0	386.8
12°	386.9	386.5	385.7	385.5	385.5	385.5	385.4	385.4	385.8	385.8	385.6
12.5°	385.8	385.7	385.2	384.7	384.5	384.5	384.5	384.5	385.0	385.0	384.9
13°	385.1	384.7	384.3	383.6	383.8	383.6	383.6	383.5	383.9	384.0	384.0
13.5°	384.3	383.7	383.2	382.6	382.8	382.5	382.8	382.5	383.1	383.3	383.1
14°	382.9	382.8	382.2	381.9	381.8	381.7	381.3	381.5	381.9	382.1	381.9
14.5°	382.4	381.6	381.4	380.4	380.7	380.4	380.8	380.4	380.8	380.9	380.8
15°	380.9	380.9	380.2	379.7	379.7	379.6	379.3	379.4	379.8	380.1	380.1
15.5°	379.8	379.4	379.0	378.3	378.3	378.3	378.5	378.4	378.6	378.7	378.7
16°	378.9	378.8	377.9	377.5	377.6	377.4	377.0	377.0	377.3	377.8	377.6
16.5°	377.7	377.2	376.6	376.0	376.0	375.9	376.0	375.9	376.4	376.6	376.4
17°	376.4	376.2	375.5	375.1	375.2	374.9	375.0	374.7	375.0	375.2	375.2
17.5°	375.2	375.0	374.3	373.4	373.8	373.4	373.6	373.1	373.8	374.0	374.0
18°	373.7	373.7	373.1	372.6	372.5	372.2	372.2	372.2	372.5	372.7	372.7
18.5°	372.8	372.2	371.5	370.8	371.1	370.9	371.1	370.6	371.1	371.5	371.3
19°	371.2	371.2	370.3	369.8	369.7	369.6	369.3	369.7	369.9	370.2	370.1
19.5°	370.0	369.4	368.9	368.2	368.5	368.3	368.4	367.9	368.3	368.5	368.8
20°	368.6	368.4	367.5	367.2	367.2	366.8	366.8	366.7	367.0	367.3	367.4
20.5°	367.3	366.8	366.0	365.4	365.3	365.3	365.1	365.0	365.6	365.9	365.9
21°	365.8	365.4	364.6	363.9	364.1	363.9	363.8	363.6	364.0	364.3	364.4

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997168

CATALOG NUMBER: SMX4SLSFSD2W-1000LM-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	361.3	360.6	360.0	359.4	359.3	359.3	359.0	358.9	359.4	359.6	359.7
23°	359.6	359.1	358.6	357.7	358.0	357.7	357.3	357.4	357.8	358.1	358.4
23.5°	357.9	357.5	356.8	356.1	356.1	355.8	355.9	355.8	356.1	356.4	356.5
24°	356.3	355.9	355.2	354.6	354.7	354.3	354.1	353.9	354.3	354.7	355.0
24.5°	354.6	354.3	353.6	352.5	352.9	352.3	352.5	352.5	352.9	353.0	353.3
25°	352.8	352.4	351.8	351.3	351.2	350.9	350.6	350.6	350.9	351.2	351.5
25.5°	351.3	350.6	350.1	349.0	349.3	348.9	349.2	348.9	349.1	349.6	349.7
26°	349.2	349.0	348.3	347.6	347.9	347.2	347.1	347.2	347.3	347.6	348.1
26.5°	347.7	347.2	346.4	345.5	345.7	345.5	345.5	345.3	345.5	345.8	346.2
27°	345.6	345.4	344.6	343.8	344.0	343.8	343.5	343.3	343.7	344.1	344.2
27.5°	343.9	343.3	342.6	342.1	342.0	341.5	341.8	341.5	341.8	342.1	342.6
28°	341.8	341.6	340.7	339.9	340.2	340.1	339.5	339.4	339.9	340.1	340.6
28.5°	340.1	339.6	338.7	338.1	338.3	337.8	337.9	337.7	338.0	338.3	338.6
29°	338.2	337.8	336.9	336.1	336.2	335.9	335.8	335.8	336.0	336.3	336.5
29.5°	336.3	335.6	335.0	334.1	334.3	334.0	333.9	333.7	334.0	334.4	335.0
30°	334.0	333.6	333.0	332.1	332.4	332.1	331.9	331.7	331.9	332.4	332.6
30.5°	332.3	331.6	330.9	330.1	330.3	329.7	330.0	329.4	329.9	330.2	330.6
31°	329.9	329.6	328.9	328.0	328.3	328.0	327.8	327.4	327.9	328.4	328.5
31.5°	328.3	327.4	326.8	325.9	326.1	325.7	325.7	325.6	325.6	326.1	326.5
32°	325.7	325.4	324.6	323.7	324.1	323.5	323.3	323.3	323.7	324.3	324.4
32.5°	323.8	323.3	322.5	321.7	321.8	321.5	321.5	321.3	321.4	321.8	322.2
33°	321.6	320.9	320.4	319.4	319.9	319.3	319.1	318.9	319.3	319.7	320.1
33.5°	319.5	319.0	318.1	317.2	317.6	317.1	317.0	316.9	317.1	317.5	317.8
34°	317.1	316.7	315.8	314.9	315.4	314.8	314.8	314.6	314.8	315.1	315.6
34.5°	315.1	314.4	313.8	312.7	312.9	312.7	312.4	312.3	312.6	313.1	313.4
35°	312.5	312.4	311.3	310.6	310.9	310.4	310.3	310.2	310.3	310.8	311.0
35.5°	310.6	309.9	309.2	308.1	308.6	307.9	308.0	307.7	307.9	308.2	309.0
36°	308.0	307.7	306.8	306.0	306.4	306.0	305.6	305.5	305.8	306.3	306.4
36.5°	305.9	305.2	304.4	303.4	303.8	303.3	303.4	303.0	303.4	303.7	304.3
37°	303.3	303.0	302.1	301.2	301.7	301.1	300.9	300.7	301.1	301.6	301.8
37.5°	301.0	300.4	299.7	298.8	299.0	298.6	298.5	298.3	298.5	298.9	299.4
38°	298.6	298.3	297.2	296.4	297.0	296.4	296.3	295.9	296.2	296.7	297.1
38.5°	296.2	295.7	294.8	293.9	294.3	293.8	293.5	293.5	293.6	294.1	294.5
39°	293.5	293.4	292.3	291.6	292.0	291.4	291.2	291.2	291.3	291.8	292.3
39.5°	291.5	290.7	290.0	289.0	289.4	288.8	288.8	288.5	288.8	289.2	289.6
40°	288.6	288.4	287.2	286.5	287.0	286.4	286.0	286.0	286.2	286.7	287.2
40.5°	286.2	285.6	284.9	284.0	284.2	283.8	283.6	283.4	283.8	284.2	284.7
41°	283.7	283.3	282.2	281.5	282.0	281.3	281.2	281.0	281.2	281.6	282.1
41.5°	281.2	280.5	279.7	278.6	279.1	278.6	278.4	278.4	278.6	279.0	279.6
42°	278.5	278.3	277.1	276.3	276.8	276.2	276.1	275.8	276.0	276.4	277.0
42.5°	276.0	275.4	274.4	273.5	274.1	273.4	273.2	273.1	273.5	273.8	274.2
43°	273.1	272.8	272.0	271.1	271.5	271.0	270.8	270.6	270.9	271.3	271.9
43.5°	270.8	270.2	269.1	268.2	268.8	268.3	268.0	267.8	268.0	268.6	269.1

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997168

CATALOG NUMBER: SMX4SLSFSD2W-1000LM-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	262.5	262.2	261.0	260.1	260.8	260.2	259.8	259.8	260.1	260.5	260.9
45.5°	259.9	259.1	258.3	257.4	258.0	257.3	257.1	257.2	257.1	257.8	258.3
46°	257.1	256.8	255.6	254.8	255.4	254.6	254.5	254.3	254.7	254.9	255.5
46.5°	254.3	253.7	252.8	251.8	252.4	251.9	251.6	251.5	251.7	252.3	252.7
47°	251.5	251.1	249.9	249.2	249.8	249.0	248.9	248.8	249.0	249.3	250.0
47.5°	248.8	248.1	247.4	246.2	247.0	246.2	245.9	245.9	246.1	246.6	247.0
48°	245.8	245.3	244.3	243.5	244.1	243.5	243.3	243.0	243.4	243.8	244.3
48.5°	243.0	242.5	241.6	240.6	241.2	240.5	240.3	240.3	240.4	240.8	241.3
49°	240.2	239.7	238.8	237.8	238.6	237.8	237.6	237.3	237.5	238.1	238.6
49.5°	237.2	236.7	235.7	234.9	235.3	234.8	234.7	234.6	234.6	235.0	235.6
50°	234.3	233.7	232.9	231.9	232.6	232.1	231.8	231.5	231.8	232.2	232.7
50.5°	231.4	231.0	229.9	228.9	229.5	228.9	228.7	228.7	228.8	229.3	229.9
51°	228.3	227.9	227.1	226.1	226.8	226.0	225.9	225.7	226.1	226.2	226.8
51.5°	225.5	224.9	223.9	222.9	223.6	223.2	222.8	222.9	222.9	223.4	224.0
52°	222.5	222.0	221.3	220.2	221.0	220.2	219.9	219.8	220.1	220.4	221.0
52.5°	219.5	218.9	218.0	217.0	217.6	217.2	216.7	216.9	216.9	217.5	218.0
53°	216.4	215.9	215.0	214.1	214.8	214.2	214.0	213.8	213.9	214.4	215.0
53.5°	213.3	212.9	211.9	210.8	211.7	211.1	210.7	210.8	210.8	211.3	211.9
54°	210.2	209.8	209.0	208.0	208.7	208.1	208.0	207.8	207.9	208.3	208.9
54.5°	207.2	206.7	205.7	204.6	205.5	204.9	204.7	204.6	204.7	205.1	205.8
55°	204.0	203.6	202.8	202.0	202.6	201.9	201.7	201.6	201.8	202.3	202.7
55.5°	201.1	200.5	199.6	198.5	199.3	198.8	198.7	198.4	198.5	199.2	199.6
56°	197.8	197.5	196.5	195.7	196.4	195.7	195.4	195.5	195.7	195.8	196.4
56.5°	194.7	194.2	193.3	192.3	193.1	192.7	192.3	192.2	192.3	192.9	193.5
57°	191.5	191.1	190.1	189.3	190.1	189.4	189.2	189.1	189.1	189.6	190.3
57.5°	188.3	187.9	187.0	186.0	186.9	186.3	185.9	185.9	186.1	186.6	187.1
58°	185.2	184.8	183.8	183.0	183.7	183.1	182.9	182.7	182.9	183.2	183.9
58.5°	181.9	181.4	180.6	179.7	180.4	179.9	179.7	179.6	179.7	180.1	180.8
59°	178.7	178.3	177.4	176.5	177.4	176.7	176.5	176.4	176.6	177.0	177.5
59.5°	175.4	175.0	174.1	173.2	174.0	173.5	173.2	173.1	173.0	173.8	174.4
60°	172.2	171.7	170.9	170.0	170.8	170.1	170.1	169.8	170.2	170.4	170.9
60.5°	168.8	168.5	167.6	166.7	167.6	167.0	166.8	166.7	166.7	167.3	167.8
61°	165.7	165.2	164.3	163.4	164.3	163.7	163.6	163.4	163.5	163.9	164.5
61.5°	162.3	162.0	161.0	160.1	160.9	160.6	160.3	160.1	160.3	160.8	161.3
62°	159.1	158.5	157.8	156.9	157.8	157.2	157.0	157.0	157.1	157.3	157.8
62.5°	155.7	155.2	154.4	153.5	154.4	153.9	153.6	153.5	153.6	154.2	154.8
63°	152.3	151.9	151.0	150.2	151.1	150.5	150.4	150.3	150.4	150.8	151.3
63.5°	149.0	148.6	147.7	146.8	147.7	147.3	147.0	146.7	146.9	147.4	148.0
64°	145.6	145.1	144.3	143.5	144.5	143.9	143.8	143.7	143.8	144.1	144.6
64.5°	142.2	141.9	140.9	140.1	141.1	140.5	140.3	140.1	140.3	140.8	141.4
65°	138.9	138.4	137.6	136.8	137.8	137.3	137.0	137.0	137.1	137.4	137.9
65.5°	135.5	135.1	134.2	133.5	134.4	133.9	133.6	133.5	133.6	134.1	134.7
66°	132.0	131.5	130.7	130.0	131.0	130.5	130.3	130.2	130.3	130.6	131.2

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997168

CATALOG NUMBER: SMX4SLSFSD2W-1000LM-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	121.8	121.4	120.5	119.8	120.8	120.4	120.1	120.0	120.1	120.5	121.1
68°	118.4	118.0	117.1	116.5	117.4	116.9	116.8	116.6	116.8	117.1	117.6
68.5°	114.9	114.5	113.8	112.9	114.0	113.5	113.3	113.2	113.2	113.7	114.3
69°	111.4	111.1	110.2	109.6	110.5	110.1	110.0	109.9	109.9	110.2	110.8
69.5°	107.9	107.6	106.8	106.1	107.2	106.7	106.6	106.3	106.5	107.0	107.4
70°	104.6	104.1	103.3	102.8	103.8	103.3	103.1	103.0	103.1	103.3	103.9
70.5°	101.1	100.8	100.0	99.2	100.3	99.8	99.6	99.5	99.7	100.1	100.6
71°	97.7	97.3	96.6	95.8	97.0	96.4	96.4	96.3	96.2	96.6	97.2
71.5°	94.2	93.9	93.1	92.3	93.6	93.0	92.9	92.7	92.8	93.3	93.8
72°	90.7	90.4	89.7	89.1	90.2	89.7	89.7	89.6	89.5	89.9	90.4
72.5°	87.3	87.0	86.2	85.5	86.7	86.3	86.3	86.2	86.2	86.5	86.9
73°	83.9	83.5	82.8	82.2	83.3	82.9	82.9	82.8	82.8	83.1	83.5
73.5°	80.4	80.1	79.4	78.7	79.9	79.6	79.5	79.4	79.4	79.7	80.0
74°	77.0	76.7	76.0	75.4	76.4	76.2	76.1	75.9	76.0	76.3	76.6
74.5°	73.6	73.4	72.7	71.9	73.2	72.8	72.7	72.5	72.6	73.0	73.5
75°	70.2	69.9	69.3	68.7	69.8	69.5	69.4	69.1	69.3	69.6	70.0
75.5°	66.9	66.6	65.9	65.2	66.5	66.0	66.0	65.8	65.9	66.3	66.9
76°	63.5	63.2	62.5	61.9	63.1	62.7	62.7	62.5	62.5	62.9	63.4
76.5°	60.2	59.9	59.3	58.6	59.8	59.4	59.4	59.1	59.3	59.6	60.1
77°	56.8	56.5	56.0	55.5	56.6	56.2	56.1	56.0	56.1	56.4	56.7
77.5°	53.7	53.3	52.8	52.1	53.3	53.0	52.9	52.7	52.8	53.2	53.6
78°	50.4	50.1	49.6	49.0	50.2	49.8	49.7	49.6	49.7	49.9	50.4
78.5°	47.2	47.0	46.4	45.8	46.9	46.6	46.5	46.4	46.4	46.8	47.2
79°	44.1	43.7	43.2	42.8	43.8	43.5	43.5	43.4	43.4	43.6	44.1
79.5°	40.9	40.7	40.2	39.6	40.7	40.4	40.3	40.2	40.3	40.7	41.0
80°	37.8	37.6	37.2	36.7	37.7	37.5	37.4	37.3	37.3	37.6	37.9
80.5°	35.0	34.8	34.4	33.9	34.7	34.4	34.4	34.3	34.3	34.6	35.1
81°	32.2	32.0	31.6	31.1	31.9	31.6	31.5	31.4	31.5	31.7	32.1
81.5°	29.4	29.2	28.8	28.4	29.0	28.8	28.7	28.5	28.7	28.9	29.3
82°	26.6	26.4	26.0	25.6	26.3	26.0	26.0	25.9	25.9	26.2	26.5
82.5°	23.8	23.6	23.2	22.8	23.6	23.4	23.3	23.2	23.3	23.5	23.9
83°	21.3	21.0	20.6	20.2	21.0	20.8	20.8	20.7	20.7	20.9	21.2
83.5°	18.7	18.6	18.2	17.8	18.6	18.4	18.3	18.2	18.3	18.6	18.8
84°	16.4	16.2	15.9	15.5	16.3	16.0	16.0	16.0	16.0	16.2	16.5
84.5°	14.1	14.0	13.7	13.3	14.0	13.9	13.8	13.7	13.8	14.0	14.2
85°	12.1	11.9	11.6	11.3	11.9	12.2	12.0	12.0	12.1	11.9	12.1
85.5°	10.1	10.0	9.7	9.4	10.3	10.5	10.3	10.2	10.5	10.3	10.5
86°	8.3	8.2	7.9	7.7	8.7	8.9	8.5	8.5	8.8	8.8	8.9
86.5°	6.6	6.6	6.4	6.1	7.1	7.2	6.8	6.7	7.2	7.2	7.3
87°	5.2	5.1	5.0	4.8	5.5	5.5	5.0	5.0	5.5	5.6	5.7
87.5°	4.0	3.9	3.8	3.6	4.0	3.9	3.9	3.9	3.9	4.0	4.1
88°	3.1	3.1	3.0	2.9	2.9	2.9	2.9	2.9	2.9	3.1	3.1
88.5°	2.4	2.3	2.3	2.2	2.1	2.0	2.1	2.1	2.2	2.2	2.3

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P997168
CATALOG NUMBER: SMX4SLSFSD2W-1000LM-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997168

CATALOG NUMBER: SMX4SLSFSD2W-1000LM-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	396.6	396.6	396.6	396.6	396.6	396.6
0.5°	396.4	396.0	396.2	396.6	396.7	397.4
1°	396.5	396.1	396.5	396.6	396.7	397.0
1.5°	396.3	395.9	396.0	396.6	396.7	397.0
2°	396.2	395.9	396.1	396.0	396.7	396.9
2.5°	396.0	395.6	395.8	396.4	396.4	396.7
3°	396.0	395.7	395.9	395.7	396.4	396.7
3.5°	395.6	395.0	395.4	395.8	395.8	396.6
4°	395.4	395.1	395.4	395.5	395.8	395.9
4.5°	394.8	394.4	394.8	395.2	395.5	395.7
5°	394.8	394.5	394.7	394.7	395.4	395.4
5.5°	394.3	394.0	393.8	394.6	394.6	395.2
6°	393.8	393.4	393.9	393.8	394.5	394.7
6.5°	393.5	393.2	393.3	393.7	393.9	394.3
7°	393.0	392.5	392.8	393.1	393.5	393.5
7.5°	392.2	391.9	392.3	392.6	392.8	393.5
8°	392.0	391.5	392.0	391.9	392.4	392.6
8.5°	391.3	390.9	390.9	391.8	391.5	392.3
9°	390.7	390.2	390.6	390.6	391.5	391.2
9.5°	389.8	389.4	389.6	390.2	390.3	390.9
10°	389.4	388.7	389.4	389.3	389.8	389.9
10.5°	388.5	387.7	388.1	388.9	389.0	389.4
11°	387.5	387.5	387.7	387.6	388.1	388.5
11.5°	387.0	386.1	386.7	387.1	387.6	387.9
12°	386.1	385.5	385.9	386.0	386.4	386.9
12.5°	385.2	384.5	384.8	385.5	385.8	385.8
13°	384.2	383.8	384.2	384.5	384.8	385.1
13.5°	383.3	382.7	382.9	383.4	383.9	384.3
14°	382.3	381.8	382.1	382.6	383.0	382.9
14.5°	381.3	380.6	380.9	381.4	381.7	382.4
15°	380.4	379.6	379.9	380.2	380.9	380.9
15.5°	379.0	378.5	378.8	379.4	379.7	379.8
16°	377.9	377.3	377.7	377.9	378.8	378.9
16.5°	376.6	376.3	376.4	377.3	377.3	377.7
17°	375.6	375.0	375.4	375.7	376.3	376.4
17.5°	374.4	373.7	374.0	374.6	374.9	375.2
18°	372.8	372.4	373.0	373.5	373.6	373.7
18.5°	371.9	371.3	371.6	372.1	372.6	372.8
19°	370.2	370.0	370.3	370.5	371.2	371.2
19.5°	369.1	368.4	368.8	369.4	369.9	370.0
20°	367.6	367.2	367.7	367.9	368.4	368.6
20.5°	366.0	365.6	365.7	366.7	367.0	367.3
21°	364.8	364.2	364.8	364.9	365.4	365.8

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997168

CATALOG NUMBER: SMX4SLSFSD2W-1000LM-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	360.2	359.3	359.7	360.8	360.9	361.3
23°	358.4	358.0	358.7	358.8	359.6	359.6
23.5°	357.1	356.4	356.7	357.5	357.8	357.9
24°	355.3	354.7	355.1	355.7	356.2	356.3
24.5°	353.6	352.8	353.4	354.2	354.4	354.6
25°	351.9	351.3	351.7	352.3	352.9	352.8
25.5°	350.0	349.3	350.0	350.7	351.0	351.3
26°	348.3	347.8	348.4	348.7	349.4	349.2
26.5°	346.5	345.7	346.3	347.2	347.4	347.7
27°	344.7	344.1	344.6	345.1	345.7	345.6
27.5°	342.8	342.0	342.7	343.3	343.8	343.9
28°	340.9	340.2	340.7	341.3	341.8	341.8
28.5°	338.9	338.4	338.8	339.5	340.0	340.1
29°	337.2	336.4	337.0	337.5	338.3	338.2
29.5°	335.0	334.5	334.9	335.7	336.0	336.3
30°	333.1	332.5	333.0	333.4	334.4	334.0
30.5°	330.9	330.4	330.9	331.8	331.7	332.3
31°	329.2	328.5	329.0	329.4	330.4	329.9
31.5°	326.6	326.3	326.8	327.7	327.7	328.3
32°	325.1	323.9	324.8	325.4	325.7	325.7
32.5°	322.4	322.1	322.6	323.2	323.7	323.8
33°	320.7	319.8	320.4	321.1	321.6	321.6
33.5°	317.9	317.5	318.3	318.9	319.5	319.5
34°	316.4	315.5	316.1	316.7	317.2	317.1
34.5°	313.6	313.0	313.7	314.3	315.1	315.1
35°	311.6	310.9	311.6	312.1	312.8	312.5
35.5°	309.2	308.6	309.2	310.0	310.5	310.6
36°	307.2	306.4	306.8	307.5	308.2	308.0
36.5°	304.7	303.8	304.6	305.4	305.7	305.9
37°	302.4	301.6	302.3	302.9	303.4	303.3
37.5°	299.9	299.1	299.7	300.7	300.9	301.0
38°	297.6	296.9	297.5	298.0	298.8	298.6
38.5°	295.1	294.4	295.0	295.8	296.2	296.2
39°	292.8	291.7	292.6	293.2	294.0	293.5
39.5°	290.1	289.4	290.1	290.7	291.3	291.5
40°	287.8	286.8	287.6	288.3	288.9	288.6
40.5°	285.1	284.4	285.0	285.8	286.1	286.2
41°	282.8	281.8	282.6	283.1	283.8	283.7
41.5°	280.1	279.3	279.9	280.6	281.1	281.2
42°	277.5	276.7	277.3	278.0	278.6	278.5
42.5°	274.8	274.1	274.8	275.4	275.8	276.0
43°	272.4	271.6	272.3	272.8	273.4	273.1
43.5°	269.6	268.8	269.5	270.2	270.7	270.8

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997168

CATALOG NUMBER: SMX4SLSFSD2W-1000LM-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	261.6	260.7	261.4	262.1	262.6	262.5
45.5°	258.8	258.0	258.7	259.2	259.8	259.9
46°	256.0	255.3	255.8	256.6	257.2	257.1
46.5°	253.2	252.3	253.1	253.6	254.3	254.3
47°	250.7	249.7	250.3	251.0	251.5	251.5
47.5°	247.6	247.0	247.6	248.2	248.7	248.8
48°	245.0	243.9	244.7	245.3	245.9	245.8
48.5°	241.9	241.1	241.7	242.6	243.0	243.0
49°	239.2	238.3	239.0	239.6	240.1	240.2
49.5°	236.0	235.5	236.1	236.7	237.1	237.2
50°	233.6	232.4	233.2	233.8	234.4	234.3
50.5°	230.4	229.6	230.2	230.7	231.3	231.4
51°	227.4	226.5	227.2	227.9	228.3	228.3
51.5°	224.6	223.6	224.4	224.8	225.4	225.5
52°	221.6	220.7	221.4	222.0	222.5	222.5
52.5°	218.7	217.7	218.3	218.9	219.5	219.5
53°	215.5	214.5	215.4	215.9	216.4	216.4
53.5°	212.6	211.6	212.2	212.8	213.5	213.3
54°	209.4	208.5	209.1	209.8	210.2	210.2
54.5°	206.4	205.4	206.2	206.7	207.3	207.2
55°	203.4	202.3	203.0	203.7	204.1	204.0
55.5°	200.3	199.4	200.0	200.4	200.9	201.1
56°	197.1	196.1	196.7	197.4	198.0	197.8
56.5°	194.0	193.0	193.7	194.2	194.7	194.7
57°	190.9	189.9	190.5	191.1	191.6	191.5
57.5°	187.7	186.7	187.2	187.8	188.2	188.3
58°	184.5	183.3	184.0	184.7	185.3	185.2
58.5°	181.3	180.3	180.9	181.5	181.9	181.9
59°	178.2	177.0	177.6	178.3	178.7	178.7
59.5°	174.7	173.8	174.5	174.9	175.5	175.4
60°	171.7	170.5	171.2	171.8	172.3	172.2
60.5°	168.4	167.4	168.0	168.4	169.0	168.8
61°	165.1	163.9	164.6	165.2	165.5	165.7
61.5°	161.7	160.7	161.5	161.9	162.4	162.3
62°	158.6	157.3	158.0	158.6	159.0	159.1
62.5°	155.2	154.2	154.8	155.2	155.7	155.7
63°	152.0	150.8	151.3	152.0	152.4	152.3
63.5°	148.5	147.5	148.2	148.5	149.0	149.0
64°	145.3	144.1	144.6	145.2	145.7	145.6
64.5°	141.8	140.7	141.5	141.8	142.3	142.2
65°	138.6	137.4	137.9	138.4	139.0	138.9
65.5°	135.2	134.1	134.6	135.0	135.5	135.5
66°	131.8	130.6	131.2	131.5	132.1	132.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997168

CATALOG NUMBER: SMX4SLSFSD2W-1000LM-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	121.7	120.4	121.0	121.4	121.9	121.8
68°	118.2	117.0	117.6	118.0	118.3	118.4
68.5°	114.7	113.5	114.1	114.5	115.0	114.9
69°	111.4	110.0	110.7	111.0	111.4	111.4
69.5°	107.9	106.7	107.2	107.7	108.0	107.9
70°	104.5	103.2	103.8	104.2	104.5	104.6
70.5°	101.1	99.8	100.4	100.7	101.2	101.1
71°	97.8	96.5	96.9	97.2	97.6	97.7
71.5°	94.3	92.9	93.6	93.8	94.2	94.2
72°	90.9	89.5	90.0	90.5	90.7	90.7
72.5°	87.5	86.1	86.6	86.9	87.4	87.3
73°	84.2	82.7	83.2	83.6	83.8	83.9
73.5°	80.8	79.3	79.8	80.1	80.5	80.4
74°	77.4	75.9	76.4	76.7	76.9	77.0
74.5°	74.0	72.5	73.0	73.3	73.7	73.6
75°	70.6	69.2	69.6	69.9	70.3	70.2
75.5°	67.2	65.9	66.3	66.6	66.9	66.9
76°	63.9	62.5	62.9	63.2	63.5	63.5
76.5°	60.4	59.2	59.7	59.9	60.2	60.2
77°	57.2	55.9	56.3	56.7	56.9	56.8
77.5°	54.0	52.7	53.1	53.3	53.7	53.7
78°	50.8	49.6	49.9	50.1	50.5	50.4
78.5°	47.6	46.3	46.8	46.9	47.3	47.2
79°	44.5	43.2	43.6	43.8	44.1	44.1
79.5°	41.3	40.1	40.5	40.7	41.0	40.9
80°	38.3	37.1	37.4	37.6	37.9	37.8
80.5°	35.4	34.3	34.6	34.8	35.1	35.0
81°	32.5	31.6	31.8	32.0	32.3	32.2
81.5°	29.5	28.8	29.0	29.2	29.5	29.4
82°	26.8	26.0	26.2	26.4	26.7	26.6
82.5°	24.1	23.2	23.4	23.6	23.9	23.8
83°	21.6	20.6	20.9	21.0	21.2	21.3
83.5°	19.1	18.1	18.4	18.5	18.7	18.7
84°	16.7	15.8	16.1	16.1	16.4	16.4
84.5°	14.4	13.6	13.8	13.9	14.2	14.1
85°	12.3	11.6	11.7	11.8	12.1	12.1
85.5°	10.7	9.7	9.8	9.9	10.1	10.1
86°	9.1	7.9	8.1	8.1	8.3	8.3
86.5°	7.5	6.3	6.4	6.5	6.7	6.6
87°	5.8	4.9	5.0	5.1	5.3	5.2
87.5°	4.2	3.7	3.8	3.9	4.0	4.0
88°	3.1	3.0	3.1	3.1	3.2	3.1
88.5°	2.2	2.3	2.3	2.4	2.4	2.4

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P997168
CATALOG NUMBER: SMX4SLSFSD2W-1000LM-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270° - · - 135°-315°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





21.5°	364.3	363.8	362.9	362.4	362.4	362.1	362.3	362.1	362.4	362.8	363.1
22°	362.6	362.4	361.6	360.9	361.4	360.8	360.8	360.6	360.9	361.4	361.5



44°	267.7	267.7	266.6	265.7	266.2	265.7	265.2	265.3	265.4	265.9	266.2
44.5°	265.3	264.7	263.8	262.9	263.4	262.7	262.7	262.4	262.7	263.2	263.8



66.5°	128.6	128.3	127.4	126.6	127.6	127.1	126.8	126.7	126.8	127.2	127.8
67°	125.2	124.8	124.0	123.2	124.2	123.7	123.6	123.4	123.5	123.9	124.4



89°	1.6	1.5	1.5	1.5	1.4	1.4	1.5	1.5	1.5	1.6	1.6
89.5°	0.8	0.8	0.8	0.8	1.0	0.9	1.0	1.0	1.1	1.1	1.1

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



21.5°	363.2	362.3	362.9	363.6	364.0	364.3
22°	361.7	361.3	361.8	361.9	362.7	362.6

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



44°	267.2	265.9	266.7	267.4	268.0	267.7
44.5°	264.2	263.4	264.1	264.7	265.3	265.3

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



66.5°	128.4	127.2	127.9	128.2	128.7	128.6
67°	125.0	123.7	124.3	124.7	125.2	125.2

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



89°	1.6	1.5	1.6	1.6	1.6	1.6
89.5°	1.0	0.8	0.8	0.8	0.8	0.8

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)