

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P184305

Luminaire Tested: **L80808SP9030AH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P184305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27054)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L80808SP9030AH
Description: HALO TRACK L LED 08, 850 LM, SPOT, ALUMINIUM HAZE

Light Source: EATON LED 3000K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 909.0 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.27
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 11.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P184305

CATALOG NUMBER: L80808SP9030AH

Luminous Intensity Polar Plot





TEST NUMBER: P184305

CATALOG NUMBER: L80808SP9030AH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96								
2	111	107	104	102	109	106	103	100	102	100	98	100	98	96	97	96	94	93								
3	108	103	99	96	106	102	98	96	99	96	94	97	95	93	95	93	91	90								
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87								
5	102	96	92	89	100	95	91	88	93	90	88	92	89	87	91	88	86	85								
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	83								
7	97	90	86	84	95	90	86	83	89	85	83	88	85	83	87	84	82	81								
8	94	88	84	81	93	87	84	81	87	83	81	86	83	81	85	82	80	79								
9	92	86	82	79	91	85	82	79	85	81	79	84	81	79	83	81	79	78								
10	90	84	80	78	89	83	80	77	83	80	77	82	79	77	82	79	77	76								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1692518
5°	1196629
10°	510389
15°	276823
20°	150256
25°	46019
30°	11293
35°	7415
40°	4265
45°	2450
50°	4401
55°	3785
60°	3903
65°	3061
70°	3206
75°	4999
80°	11239
85°	17360



TEST NUMBER: P184305

CATALOG NUMBER: L80808SP9030AH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	406.2	44.7
10°-20°	341.2	37.5
20°-30°	106.1	11.7
30°-40°	17.1	1.9
40°-50°	9.4	1.0
50°-60°	8.6	1.0
60°-70°	6.4	0.7
70°-80°	6.8	0.7
80°-90°	7.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	853.5	93.9
0°-40°	870.6	95.8
0°-60°	888.7	97.8
0°-90°	909.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	909.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7718	
5°	5436	406
15°	1219	341
25°	190	106
35°	28	17
45°	8	9
55°	10	9
65°	6	6
75°	6	7
85°	7	7
90°	0	



TEST NUMBER: P184305

CATALOG NUMBER: L80808SP9030AH

CANDELA DISTRIBUTION (FULL):

0°	
0°	7718.5
1°	7608.6
2°	7301.5
3°	6843.9
4°	6199.0
5°	5436.3
6°	4620.0
7°	3861.3
8°	3249.1
9°	2706.2
10°	2292.2
11°	1976.2
12°	1731.5
13°	1531.4
14°	1371.0
15°	1219.4
16°	1047.0
17°	933.1
18°	835.1
19°	758.8
20°	643.9
21°	531.9
22°	428.9
23°	337.8
24°	260.5
25°	190.2
26°	138.7
27°	100.0
28°	88.2
29°	55.5
30°	44.6
32.5°	24.8
35°	27.7
37.5°	27.7
40°	14.9
42.5°	21.8
45°	7.9
47.5°	5.9
50°	12.9
52.5°	8.9
55°	9.9
57.5°	8.9
60°	8.9
62.5°	5.0
65°	5.9



TEST NUMBER: P184305

CATALOG NUMBER: L80808SP9030AH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	7.9
70°	5.0
72.5°	6.9
75°	5.9
77.5°	5.9
80°	8.9
82.5°	5.0
85°	6.9
87.5°	9.9
90°	0.0

(END OF REPORT)