

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P991372

Luminaire Tested: **SMD4R07FS5-950**

Issue Date: 05/20/2025



Test Information

Test Method: LM-79-08
Report Number: P991372
Test Lab: THIRD PARTY NVLAP
Issue Date: 05/20/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: SMD4R07FS5-950
Description: HALO SURFACE MOUNT 4 inch 90 CRI COLOR SELECTABLE Round FIXTURE
Light Source: 5000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 759.9 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.36
Luminous Opening: Circular (Dia: 0.3' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P991372
CATALOG NUMBER: SMD4R07FS5-950

Luminous Intensity Polar Plot



TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86
2	99	91	84	78	96	89	82	77	85	80	75	82	77	73	79	75	72
3	90	79	71	65	88	78	70	64	75	68	63	72	67	62	70	65	61
4	82	70	62	55	80	69	61	54	67	59	54	64	58	53	62	57	52
5	76	63	54	47	74	62	53	47	60	52	46	58	51	46	56	50	45
6	70	57	48	41	68	56	47	41	54	46	41	52	45	40	51	45	40
7	65	51	43	36	63	51	42	36	49	41	36	47	41	36	46	40	35
8	60	47	38	32	59	46	38	32	45	37	32	44	37	32	42	36	32
9	56	43	35	29	55	42	34	29	41	34	29	40	34	29	39	33	29
10	53	40	32	26	52	39	32	26	38	31	26	37	31	26	36	30	26

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	41191	41191	41191	41191
5°	41226	41104	41104	41165
10°	41162	40945	40930	41084
15°	41005	40705	40658	40910
20°	40788	40383	40335	40691
25°	40493	40006	39938	40375
30°	40126	39545	39475	40038
35°	39689	39001	38946	39596
40°	39161	38385	38346	39081
45°	38570	37665	37622	38505
50°	37833	36791	36815	37833
55°	36983	35761	35814	36983
60°	35877	34415	34567	35938
65°	34519	32753	33041	34663
70°	32680	30632	31077	33036
75°	30418	27770	28535	30948
80°	27448	23677	24993	28413
85°	22539	16074	18695	24810



TEST NUMBER: P991372
 CATALOG NUMBER: SMD4R07FS5-950

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.6	3.4
10°-20°	73.1	9.6
20°-30°	110.3	14.5
30°-40°	132.3	17.4
40°-50°	136.5	18.0
50°-60°	122.4	16.1
60°-70°	92.7	12.2
70°-80°	53.0	7.0
80°-90°	13.7	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.1	0.0
120°-130°	0.1	0.0
130°-140°	0.1	0.0
140°-150°	0.1	0.0
150°-160°	0.1	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-30°	208.9	27.5
0°-40°	341.2	44.9
0°-60°	600.1	79.0
0°-90°	759.4	99.9
90°-120°	0.1	0.0
90°-150°	0.3	0.0
90°-180°	1.0	0.1
0°-180°	759.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	270	270	270	270	270	
5°	270	269	269	269	270	26
15°	260	258	258	260	260	73
25°	241	238	238	240	241	111
35°	214	210	210	213	214	134
45°	179	175	175	179	179	138
55°	139	135	135	139	139	124
65°	96	91	92	96	96	95
75°	52	47	48	53	52	55
85°	13	9	11	14	13	14
90°	0	0	0	1	0	1
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	



TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	270.5	270.5	270.5	270.5	270.5	270.5	270.5	270.5	270.5	270.5	270.5
0.5°	270.6	270.7	270.7	270.7	270.5	270.4	270.4	270.4	270.6	270.7	270.7
1°	270.6	270.8	270.6	270.6	270.3	270.3	270.3	270.3	270.5	270.7	270.6
1.5°	270.6	270.6	270.6	270.6	270.3	270.2	270.2	270.2	270.4	270.5	270.6
2°	270.5	270.6	270.5	270.5	270.1	270.1	270.0	270.0	270.2	270.5	270.4
2.5°	270.4	270.4	270.4	270.4	270.0	269.9	269.8	269.9	270.1	270.3	270.3
3°	270.4	270.3	270.2	270.1	269.9	269.8	269.7	269.7	269.9	270.2	270.2
3.5°	270.3	270.1	270.1	270.0	269.8	269.6	269.5	269.6	269.7	270.0	270.0
4°	270.1	270.0	269.9	269.7	269.5	269.4	269.2	269.3	269.5	269.9	269.8
4.5°	269.9	269.7	269.7	269.5	269.2	269.1	268.9	269.0	269.1	269.5	269.6
5°	269.7	269.5	269.4	269.2	268.9	268.8	268.6	268.6	268.9	269.3	269.3
5.5°	269.4	269.2	269.1	269.0	268.7	268.4	268.3	268.3	268.6	269.0	269.1
6°	269.2	269.0	268.8	268.6	268.4	268.2	268.0	268.0	268.3	268.7	268.7
6.5°	268.9	268.6	268.5	268.3	268.0	267.7	267.6	267.7	267.9	268.4	268.4
7°	268.6	268.3	268.2	267.9	267.6	267.4	267.2	267.3	267.5	268.0	268.1
7.5°	268.3	268.0	267.8	267.5	267.2	266.9	266.8	266.9	267.1	267.5	267.7
8°	267.8	267.6	267.4	267.0	266.7	266.5	266.4	266.5	266.7	267.2	267.3
8.5°	267.5	267.1	266.9	266.6	266.4	266.0	266.0	266.0	266.2	266.7	266.9
9°	267.0	266.7	266.5	266.1	265.9	265.6	265.4	265.4	265.7	266.3	266.3
9.5°	266.6	266.2	266.0	265.6	265.3	265.0	264.9	265.0	265.1	265.8	265.9
10°	266.2	265.8	265.6	265.1	264.8	264.5	264.3	264.4	264.7	265.2	265.4
10.5°	265.7	265.2	264.9	264.5	264.3	263.9	263.7	263.8	264.1	264.6	264.9
11°	265.2	264.8	264.5	263.9	263.7	263.4	263.2	263.2	263.5	264.1	264.3
11.5°	264.6	264.1	263.9	263.4	263.1	262.7	262.5	262.6	262.9	263.5	263.8
12°	264.0	263.6	263.2	262.7	262.4	262.1	261.9	261.9	262.3	262.9	263.1
12.5°	263.5	262.9	262.6	262.1	261.8	261.4	261.2	261.3	261.6	262.2	262.5
13°	262.8	262.4	262.0	261.3	261.2	260.8	260.5	260.6	260.9	261.7	261.8
13.5°	262.2	261.7	261.3	260.7	260.4	260.1	259.8	259.9	260.1	260.9	261.2
14°	261.5	261.1	260.6	260.0	259.7	259.4	259.1	259.1	259.4	260.2	260.4
14.5°	260.8	260.3	259.9	259.2	258.9	258.6	258.3	258.4	258.6	259.4	259.8
15°	260.1	259.6	259.2	258.4	258.2	257.8	257.5	257.6	257.9	258.7	258.9
15.5°	259.4	258.8	258.4	257.6	257.4	257.0	256.7	256.9	257.1	257.8	258.3
16°	258.6	258.0	257.7	256.8	256.6	256.3	255.9	256.0	256.3	257.1	257.4
16.5°	257.8	257.2	256.7	256.0	255.7	255.3	255.0	255.2	255.4	256.2	256.6
17°	257.0	256.4	255.9	255.1	254.9	254.5	254.2	254.2	254.6	255.4	255.7
17.5°	256.2	255.5	255.1	254.2	254.1	253.6	253.3	253.4	253.6	254.5	255.0
18°	255.4	254.7	254.3	253.3	253.1	252.8	252.4	252.4	252.8	253.6	253.9
18.5°	254.5	253.8	253.2	252.4	252.2	251.8	251.4	251.5	251.8	252.6	253.1
19°	253.6	252.9	252.4	251.4	251.2	250.9	250.4	250.4	250.9	251.7	252.1
19.5°	252.7	252.0	251.4	250.4	250.2	249.8	249.4	249.6	249.9	250.7	251.3
20°	251.7	251.1	250.5	249.5	249.2	248.9	248.4	248.5	248.9	249.8	250.2
20.5°	250.8	250.0	249.4	248.5	248.2	247.8	247.4	247.5	247.9	248.8	249.3
21°	249.7	249.0	248.4	247.5	247.2	246.8	246.4	246.4	246.9	247.8	248.2
21.5°	248.7	248.0	247.3	246.4	246.1	245.7	245.3	245.4	245.7	246.6	247.2
22°	247.7	247.0	246.4	245.3	245.1	244.6	244.2	244.3	244.7	245.6	246.1

TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	246.7	246.0	245.2	244.3	244.0	243.5	243.1	243.2	243.5	244.5	245.1
23°	245.5	244.9	244.2	243.2	242.8	242.4	242.0	242.0	242.5	243.4	243.9
23.5°	244.5	243.7	243.0	242.0	241.7	241.2	240.8	241.0	241.2	242.2	242.9
24°	243.3	242.6	241.9	240.8	240.5	240.1	239.6	239.7	240.1	241.1	241.7
24.5°	242.2	241.4	240.7	239.6	239.3	238.9	238.4	238.6	238.9	239.9	240.6
25°	241.0	240.2	239.6	238.4	238.1	237.7	237.2	237.3	237.7	238.7	239.3
25.5°	239.9	239.0	238.4	237.2	236.8	236.4	236.0	236.2	236.4	237.5	238.3
26°	238.6	237.8	237.1	235.9	235.6	235.2	234.7	234.8	235.2	236.2	237.0
26.5°	237.5	236.6	235.7	234.6	234.3	233.9	233.4	233.6	233.9	234.9	235.7
27°	236.2	235.3	234.6	233.3	233.1	232.6	232.1	232.2	232.7	233.7	234.4
27.5°	234.9	234.1	233.3	232.0	231.8	231.3	230.8	230.9	231.3	232.4	233.2
28°	233.5	232.8	231.9	230.7	230.4	230.0	229.4	229.5	230.1	231.1	231.9
28.5°	232.3	231.4	230.6	229.4	229.1	228.6	228.1	228.3	228.6	229.7	230.6
29°	230.9	230.1	229.3	228.0	227.7	227.2	226.7	226.9	227.4	228.4	229.2
29.5°	229.7	228.8	227.9	226.6	226.4	225.8	225.3	225.5	225.9	227.0	227.9
30°	228.2	227.4	226.6	225.3	224.9	224.4	223.9	224.0	224.5	225.6	226.5
30.5°	226.9	226.0	225.1	223.8	223.5	223.0	222.4	222.6	223.0	224.1	225.1
31°	225.4	224.6	223.7	222.4	222.1	221.5	221.0	221.2	221.7	222.7	223.6
31.5°	224.0	223.2	222.2	220.9	220.6	220.0	219.5	219.8	220.2	221.2	222.3
32°	222.5	221.8	220.7	219.4	219.1	218.6	218.1	218.2	218.7	219.8	220.8
32.5°	221.1	220.3	219.3	218.0	217.7	217.0	216.5	216.8	217.2	218.3	219.4
33°	219.7	218.8	217.8	216.4	216.1	215.6	215.0	215.2	215.8	216.8	217.8
33.5°	218.2	217.3	216.2	214.9	214.6	214.0	213.4	213.7	214.2	215.2	216.4
34°	216.6	215.7	214.7	213.4	213.0	212.5	211.9	212.2	212.7	213.8	214.8
34.5°	215.2	214.3	213.1	211.8	211.4	210.8	210.3	210.6	211.0	212.1	213.3
35°	213.5	212.6	211.6	210.2	209.8	209.3	208.7	209.0	209.5	210.6	211.7
35.5°	212.0	211.1	210.0	208.6	208.2	207.7	207.1	207.4	207.9	209.0	210.2
36°	210.4	209.5	208.4	207.0	206.7	206.1	205.5	205.7	206.3	207.4	208.6
36.5°	208.8	208.0	206.7	205.3	205.1	204.4	203.8	204.2	204.7	205.8	207.0
37°	207.1	206.3	205.1	203.7	203.4	202.8	202.2	202.5	203.0	204.2	205.3
37.5°	205.6	204.7	203.4	202.0	201.8	201.1	200.6	200.8	201.3	202.5	203.8
38°	203.8	203.0	201.8	200.4	200.1	199.4	198.9	199.1	199.7	200.8	202.1
38.5°	202.3	201.4	200.1	198.8	198.4	197.7	197.2	197.5	198.0	199.1	200.5
39°	200.5	199.7	198.4	197.0	196.7	196.1	195.4	195.7	196.3	197.5	198.8
39.5°	198.8	198.0	196.7	195.3	195.0	194.3	193.7	194.0	194.6	195.7	197.1
40°	197.0	196.2	195.0	193.6	193.1	192.5	192.0	192.2	192.9	194.0	195.4
40.5°	195.4	194.5	193.1	191.8	191.4	190.7	190.2	190.5	191.1	192.2	193.7
41°	193.6	192.7	191.4	190.1	189.5	189.0	188.4	188.7	189.4	190.5	191.9
41.5°	191.9	191.0	189.6	188.2	187.8	187.1	186.6	187.0	187.6	188.7	190.1
42°	190.0	189.1	187.8	186.4	186.0	185.4	184.8	185.0	185.8	187.0	188.3
42.5°	188.4	187.4	186.0	184.5	184.3	183.5	183.0	183.3	184.0	185.2	186.7
43°	186.5	185.6	184.2	182.7	182.4	181.7	181.2	181.5	182.2	183.4	184.8
43.5°	184.7	183.8	182.3	180.8	180.6	179.8	179.3	179.7	180.3	181.5	183.1
44°	182.8	181.9	180.5	179.1	178.6	178.0	177.4	177.8	178.5	179.7	181.1
44.5°	181.0	180.1	178.6	177.2	176.9	176.1	175.5	175.9	176.6	177.8	179.3

TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	179.1	178.2	176.8	175.3	174.9	174.2	173.7	174.0	174.7	175.9	177.4
45.5°	177.3	176.4	174.8	173.4	173.1	172.3	171.8	172.2	172.9	174.0	175.6
46°	175.3	174.4	172.9	171.6	171.1	170.4	169.8	170.3	171.0	172.2	173.7
46.5°	173.4	172.5	170.9	169.6	169.2	168.4	168.0	168.4	169.0	170.2	171.8
47°	171.5	170.5	169.1	167.7	167.2	166.5	166.0	166.4	167.1	168.3	169.9
47.5°	169.6	168.7	167.0	165.7	165.3	164.5	164.1	164.5	165.2	166.3	168.0
48°	167.6	166.7	165.2	163.7	163.2	162.6	162.1	162.5	163.3	164.5	166.0
48.5°	165.7	164.7	163.1	161.7	161.3	160.6	160.1	160.5	161.3	162.5	164.1
49°	163.7	162.8	161.2	159.8	159.3	158.7	158.1	158.5	159.3	160.5	162.1
49.5°	161.8	160.7	159.1	157.8	157.4	156.6	156.2	156.6	157.3	158.5	160.2
50°	159.7	158.7	157.2	155.8	155.3	154.7	154.1	154.5	155.4	156.6	158.1
50.5°	157.8	156.8	155.1	153.7	153.3	152.6	152.1	152.5	153.3	154.5	156.1
51°	155.8	154.7	153.1	151.7	151.3	150.6	150.1	150.5	151.3	152.5	154.1
51.5°	153.7	152.7	151.0	149.6	149.3	148.5	148.1	148.5	149.3	150.5	152.2
52°	151.7	150.7	149.0	147.6	147.2	146.5	146.0	146.4	147.3	148.5	150.2
52.5°	149.7	148.6	146.9	145.5	145.1	144.4	144.0	144.5	145.2	146.4	148.1
53°	147.6	146.5	144.9	143.5	143.0	142.3	141.8	142.3	143.2	144.4	146.1
53.5°	145.6	144.5	142.7	141.3	141.0	140.2	139.8	140.2	141.1	142.3	144.1
54°	143.4	142.3	140.7	139.2	138.9	138.2	137.7	138.1	139.0	140.2	142.0
54.5°	141.4	140.3	138.5	137.1	136.8	136.0	135.7	136.1	136.9	138.1	139.9
55°	139.3	138.1	136.5	135.1	134.7	133.9	133.5	133.9	134.9	136.1	137.8
55.5°	137.2	136.1	134.3	132.8	132.5	131.8	131.4	131.9	132.8	134.0	135.7
56°	135.1	133.9	132.2	130.8	130.4	129.7	129.2	129.7	130.6	131.8	133.6
56.5°	132.9	131.8	130.0	128.6	128.3	127.5	127.1	127.6	128.5	129.7	131.5
57°	130.8	129.6	127.9	126.5	126.1	125.4	125.0	125.4	126.4	127.6	129.4
57.5°	128.7	127.4	125.7	124.3	123.9	123.2	122.9	123.3	124.2	125.5	127.3
58°	126.5	125.2	123.6	122.2	121.7	121.1	120.6	121.1	122.1	123.4	125.1
58.5°	124.4	123.1	121.3	119.9	119.6	118.9	118.5	119.1	120.0	121.2	123.0
59°	122.2	120.9	119.2	117.8	117.4	116.7	116.3	116.8	117.8	119.1	120.8
59.5°	120.0	118.8	117.0	115.5	115.2	114.5	114.1	114.6	115.6	116.9	118.7
60°	117.8	116.6	114.9	113.5	113.0	112.4	112.0	112.5	113.5	114.8	116.5
60.5°	115.7	114.4	112.6	111.2	110.8	110.1	109.8	110.3	111.3	112.6	114.4
61°	113.5	112.1	110.4	109.0	108.6	107.9	107.6	108.1	109.1	110.4	112.2
61.5°	111.3	110.0	108.2	106.8	106.4	105.7	105.4	106.0	106.9	108.3	110.1
62°	109.0	107.7	106.0	104.6	104.2	103.5	103.3	103.8	104.8	106.1	107.9
62.5°	106.9	105.5	103.7	102.3	102.0	101.3	101.0	101.6	102.6	103.9	105.7
63°	104.6	103.3	101.5	100.2	99.7	99.1	98.8	99.3	100.4	101.7	103.5
63.5°	102.4	101.1	99.3	97.9	97.5	96.9	96.6	97.1	98.2	99.5	101.3
64°	100.2	98.9	97.1	95.7	95.3	94.6	94.5	94.9	96.0	97.3	99.1
64.5°	98.0	96.7	94.9	93.4	93.1	92.4	92.2	92.8	93.8	95.2	96.9
65°	95.8	94.4	92.7	91.3	90.9	90.3	90.1	90.6	91.7	93.0	94.7
65.5°	93.5	92.2	90.4	89.0	88.7	88.1	87.8	88.4	89.4	90.8	92.5
66°	91.3	89.9	88.2	86.7	86.4	85.9	85.7	86.2	87.3	88.6	90.3
66.5°	89.0	87.7	85.9	84.5	84.2	83.7	83.5	84.0	85.1	86.4	88.2
67°	86.8	85.4	83.7	82.3	82.0	81.5	81.3	81.8	82.9	84.2	86.0



TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	84.6	83.2	81.5	80.0	79.8	79.3	79.1	79.6	80.7	82.1	83.8
68°	82.4	81.0	79.2	77.8	77.6	77.1	76.9	77.4	78.5	79.9	81.6
68.5°	80.2	78.7	77.0	75.6	75.4	74.9	74.6	75.3	76.3	77.7	79.4
69°	77.9	76.5	74.8	73.4	73.3	72.7	72.5	73.1	74.2	75.6	77.2
69.5°	75.7	74.3	72.6	71.1	71.0	70.4	70.3	70.9	72.0	73.4	75.1
70°	73.4	72.0	70.3	69.0	68.8	68.2	68.1	68.7	69.8	71.2	72.9
70.5°	71.3	69.8	68.1	66.7	66.6	66.0	65.9	66.5	67.6	69.0	70.7
71°	69.1	67.6	65.9	64.5	64.4	63.8	63.8	64.3	65.5	66.9	68.5
71.5°	66.8	65.5	63.8	62.3	62.2	61.6	61.5	62.2	63.3	64.7	66.3
72°	64.7	63.2	61.6	60.2	60.1	59.5	59.4	60.0	61.2	62.5	64.2
72.5°	62.5	61.0	59.4	58.0	57.9	57.3	57.2	57.9	59.0	60.4	62.0
73°	60.3	58.8	57.2	55.8	55.7	55.2	55.1	55.7	56.9	58.3	59.9
73.5°	58.1	56.7	55.0	53.6	53.5	53.0	52.9	53.6	54.7	56.1	57.7
74°	56.0	54.5	52.9	51.5	51.4	50.9	50.8	51.5	52.7	54.0	55.6
74.5°	53.8	52.4	50.8	49.4	49.3	48.8	48.7	49.4	50.5	51.9	53.5
75°	51.7	50.2	48.7	47.3	47.2	46.7	46.7	47.3	48.5	49.8	51.4
75.5°	49.6	48.2	46.5	45.2	45.0	44.6	44.5	45.2	46.4	47.8	49.3
76°	47.5	46.0	44.4	43.1	43.0	42.5	42.5	43.2	44.3	45.6	47.2
76.5°	45.3	44.0	42.4	41.0	40.9	40.4	40.4	41.1	42.2	43.6	45.2
77°	43.3	41.9	40.3	38.9	38.9	38.5	38.4	39.1	40.2	41.6	43.1
77.5°	41.2	39.8	38.2	37.0	36.9	36.4	36.4	37.1	38.2	39.6	41.1
78°	39.2	37.8	36.3	35.0	34.9	34.4	34.5	35.2	36.3	37.6	39.1
78.5°	37.2	35.6	34.3	33.0	32.8	32.4	32.5	33.1	34.2	35.6	37.1
79°	35.2	33.7	32.4	31.1	30.9	30.5	30.5	31.2	32.3	33.7	35.1
79.5°	33.3	31.8	30.4	29.1	28.9	28.5	28.6	29.3	30.4	31.7	33.2
80°	31.3	30.0	28.5	27.2	27.0	26.7	26.7	27.4	28.5	29.8	31.2
80.5°	29.4	28.1	26.5	25.3	25.1	24.8	24.8	25.5	26.6	27.9	29.3
81°	27.4	26.1	24.6	23.5	23.3	22.9	22.9	23.6	24.8	26.0	27.5
81.5°	25.5	24.2	22.7	21.5	21.4	21.1	21.1	21.8	22.9	24.2	25.6
82°	23.7	22.3	20.9	19.7	19.5	19.3	19.3	19.9	21.1	22.4	23.7
82.5°	21.8	20.5	19.0	17.9	17.7	17.4	17.5	18.2	19.3	20.5	21.9
83°	20.0	18.6	17.2	16.1	15.9	15.7	15.7	16.4	17.5	18.7	20.1
83.5°	18.1	16.8	15.4	14.3	14.2	13.9	14.0	14.7	15.8	17.0	18.4
84°	16.4	15.1	13.7	12.5	12.4	12.2	12.3	13.0	14.0	15.3	16.6
84.5°	14.6	13.3	12.0	10.8	10.8	10.6	10.7	11.4	12.3	13.6	14.9
85°	12.9	11.6	10.2	9.2	9.2	9.0	9.1	9.8	10.7	11.8	13.2
85.5°	11.1	9.9	8.6	7.5	7.5	7.3	7.5	8.2	9.1	10.2	11.5
86°	9.5	8.3	6.9	5.9	5.9	5.7	5.8	6.6	7.5	8.6	9.9
86.5°	7.8	6.6	5.3	4.4	4.3	4.1	4.2	4.9	5.9	7.0	8.3
87°	6.2	5.0	3.9	3.5	2.9	2.7	2.8	3.3	4.2	5.4	6.7
87.5°	4.6	3.6	2.9	2.6	1.6	1.5	1.6	2.0	2.8	3.8	5.1
88°	3.2	2.7	2.0	1.8	0.8	0.7	0.8	1.0	1.5	2.4	3.5
88.5°	2.4	1.8	1.0	0.9	0.3	0.2	0.2	0.4	0.7	1.2	2.1
89°	1.6	0.9	0.1	0.1	0.0	0.0	0.0	0.1	0.2	0.6	1.0
89.5°	0.8	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.5

TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1
90.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.0	0.0	0.0
114°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0
114.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0
115.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0
116°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
116.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
118°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
118.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
119°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
119.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
121°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
121.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
123°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
123.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
124°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
124.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
125°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
125.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
126°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
126.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
127°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
127.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
128°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
128.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
129°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
129.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
130°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
130.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
131°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
131.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
133°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
133.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
134°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
134.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1

TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
136°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
136.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
138°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
138.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
139°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
139.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.1	0.1
140.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.1	0.1
141°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.1	0.1
141.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.1	0.1
142°	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.1
142.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.1
143°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.1
143.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.1
144°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
144.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.1	0.2	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145.5°	0.1	0.2	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
146°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
146.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
147°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
147.5°	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
148°	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
148.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
149°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
149.5°	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
150°	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
150.5°	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
151°	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
151.5°	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
152°	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
152.5°	0.2	0.1	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
153°	0.2	0.1	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
153.5°	0.2	0.1	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
154°	0.2	0.1	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
154.5°	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
155°	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.2	0.2
155.5°	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2
156°	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2
156.5°	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2
157°	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2

TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2
158°	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2
158.5°	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2
159°	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2
159.5°	0.2	0.1	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.2	0.2
160°	0.2	0.1	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.2	0.2
160.5°	0.2	0.1	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.2	0.2
161°	0.2	0.1	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.2	0.2
161.5°	0.2	0.1	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.2	0.2
162°	0.2	0.1	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.2
162.5°	0.2	0.1	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.2
163°	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.2
163.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.3	0.3	0.3	0.2
164°	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.3	0.3	0.3	0.2
164.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.3	0.3	0.3	0.2
165°	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.3	0.2	0.2
165.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.3	0.2	0.2
166°	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.3	0.2	0.2
166.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.2	0.2
167°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.2	0.2
167.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.2	0.2
168°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.2	0.2
168.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.2	0.2
169°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.2	0.3
169.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.2	0.3
170°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.2	0.2
170.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.2	0.2
171°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.2	0.2	0.2
171.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.2	0.2	0.2
172°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.2	0.2	0.2
172.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.2	0.2	0.2
173°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.2	0.2	0.2	0.2
173.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.2	0.2	0.2	0.2
174°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
174.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
175°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
175.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
176°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
176.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
177°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
177.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
178°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
178.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
179°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
179.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: P991372
CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	270.5	270.5	270.5	270.5	270.5	270.5
0.5°	270.7	270.5	270.5	270.4	270.5	270.6
1°	270.6	270.4	270.5	270.4	270.5	270.6
1.5°	270.6	270.5	270.4	270.4	270.5	270.6
2°	270.5	270.3	270.4	270.3	270.4	270.5
2.5°	270.6	270.3	270.3	270.3	270.3	270.4
3°	270.4	270.1	270.2	270.2	270.2	270.4
3.5°	270.3	270.0	270.0	270.1	270.1	270.3
4°	270.0	269.7	270.0	269.9	269.9	270.1
4.5°	269.9	269.6	269.7	269.8	269.8	269.9
5°	269.6	269.3	269.5	269.5	269.5	269.7
5.5°	269.4	269.2	269.2	269.3	269.3	269.4
6°	269.0	268.8	269.0	269.1	269.0	269.2
6.5°	268.8	268.6	268.6	268.8	268.8	268.9
7°	268.3	268.1	268.3	268.5	268.5	268.6
7.5°	268.1	267.8	268.0	268.2	268.1	268.3
8°	267.6	267.4	267.6	267.8	267.8	267.8
8.5°	267.3	267.1	267.2	267.4	267.4	267.5
9°	266.7	266.6	266.8	266.9	267.0	267.0
9.5°	266.3	266.2	266.3	266.6	266.5	266.6
10°	265.7	265.7	265.9	266.1	266.1	266.2
10.5°	265.3	265.2	265.4	265.6	265.6	265.7
11°	264.7	264.6	264.9	265.1	265.1	265.2
11.5°	264.2	264.1	264.2	264.5	264.5	264.6
12°	263.6	263.5	263.8	264.0	263.9	264.0
12.5°	263.1	262.9	263.1	263.4	263.4	263.5
13°	262.4	262.3	262.6	262.7	262.8	262.8
13.5°	261.9	261.6	261.9	262.2	262.2	262.2
14°	261.0	260.9	261.3	261.4	261.5	261.5
14.5°	260.4	260.2	260.6	260.8	260.8	260.8
15°	259.6	259.5	259.8	260.1	260.1	260.1
15.5°	258.9	258.7	259.1	259.4	259.4	259.4
16°	258.1	258.0	258.4	258.6	258.7	258.6
16.5°	257.3	257.3	257.6	257.9	257.9	257.8
17°	256.5	256.4	256.8	257.0	257.1	257.0
17.5°	255.7	255.6	255.9	256.3	256.3	256.2
18°	254.7	254.7	255.1	255.4	255.4	255.4
18.5°	253.9	253.8	254.2	254.6	254.6	254.5
19°	252.9	252.9	253.3	253.6	253.7	253.6
19.5°	252.0	252.0	252.4	252.9	252.8	252.7
20°	251.1	251.1	251.5	251.8	251.8	251.7
20.5°	250.1	250.1	250.5	250.9	250.8	250.8
21°	249.1	249.1	249.6	249.8	249.9	249.7
21.5°	248.1	248.1	248.5	249.0	248.9	248.7
22°	247.0	247.0	247.5	247.8	247.9	247.7



TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	245.9	246.0	246.4	246.9	246.8	246.7
23°	244.9	244.9	245.5	245.7	245.7	245.5
23.5°	243.8	243.8	244.3	244.7	244.6	244.5
24°	242.6	242.6	243.2	243.5	243.5	243.3
24.5°	241.5	241.5	242.0	242.5	242.4	242.2
25°	240.2	240.3	240.9	241.3	241.3	241.0
25.5°	239.1	239.2	239.7	240.2	240.1	239.9
26°	237.9	237.9	238.6	238.9	238.9	238.6
26.5°	236.7	236.7	237.3	237.8	237.7	237.5
27°	235.4	235.5	236.1	236.5	236.5	236.2
27.5°	234.1	234.2	234.8	235.3	235.2	234.9
28°	232.8	232.9	233.6	233.9	233.9	233.5
28.5°	231.5	231.6	232.2	232.7	232.6	232.3
29°	230.2	230.3	231.0	231.4	231.4	230.9
29.5°	228.8	229.0	229.6	230.1	230.0	229.7
30°	227.4	227.7	228.2	228.7	228.7	228.2
30.5°	226.0	226.3	226.8	227.4	227.3	226.9
31°	224.6	224.9	225.5	225.9	225.9	225.4
31.5°	223.3	223.5	224.1	224.6	224.5	224.0
32°	221.8	222.0	222.7	223.1	223.1	222.5
32.5°	220.3	220.6	221.2	221.7	221.6	221.1
33°	218.9	219.1	219.8	220.2	220.2	219.7
33.5°	217.4	217.6	218.3	218.8	218.6	218.2
34°	215.9	216.1	216.8	217.2	217.2	216.6
34.5°	214.3	214.6	215.2	215.7	215.6	215.2
35°	212.8	213.0	213.7	214.2	214.1	213.5
35.5°	211.2	211.4	212.2	212.6	212.6	212.0
36°	209.7	209.8	210.7	211.0	211.0	210.4
36.5°	208.1	208.2	209.0	209.5	209.4	208.8
37°	206.4	206.7	207.4	207.8	207.8	207.1
37.5°	204.8	205.0	205.8	206.2	206.1	205.6
38°	203.2	203.3	204.2	204.5	204.5	203.8
38.5°	201.6	201.7	202.5	202.9	202.8	202.3
39°	199.9	200.0	200.9	201.3	201.2	200.5
39.5°	198.2	198.4	199.1	199.6	199.5	198.8
40°	196.5	196.6	197.5	197.8	197.8	197.0
40.5°	194.8	195.0	195.7	196.2	196.0	195.4
41°	193.0	193.2	194.0	194.4	194.4	193.6
41.5°	191.2	191.4	192.2	192.7	192.6	191.9
42°	189.4	189.6	190.5	190.9	190.9	190.0
42.5°	187.7	187.9	188.7	189.2	189.0	188.4
43°	185.9	186.1	187.0	187.4	187.3	186.5
43.5°	184.1	184.4	185.1	185.5	185.4	184.7
44°	182.3	182.5	183.3	183.7	183.7	182.8
44.5°	180.4	180.7	181.5	181.9	181.7	181.0



TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	178.7	178.8	179.6	180.0	180.0	179.1
45.5°	176.7	177.0	177.8	178.2	178.0	177.3
46°	174.9	175.1	175.9	176.3	176.2	175.3
46.5°	173.0	173.2	174.0	174.4	174.2	173.4
47°	171.2	171.3	172.1	172.5	172.4	171.5
47.5°	169.2	169.4	170.2	170.7	170.4	169.6
48°	167.2	167.5	168.4	168.7	168.6	167.6
48.5°	165.3	165.6	166.4	166.8	166.6	165.7
49°	163.4	163.6	164.4	164.8	164.6	163.7
49.5°	161.5	161.7	162.5	162.9	162.6	161.8
50°	159.5	159.7	160.5	160.8	160.7	159.7
50.5°	157.5	157.7	158.5	158.9	158.7	157.8
51°	155.5	155.7	156.5	156.8	156.7	155.8
51.5°	153.5	153.7	154.5	154.8	154.7	153.7
52°	151.6	151.7	152.5	152.8	152.6	151.7
52.5°	149.5	149.7	150.5	150.8	150.6	149.7
53°	147.5	147.6	148.5	148.7	148.6	147.6
53.5°	145.4	145.6	146.4	146.7	146.4	145.6
54°	143.4	143.5	144.3	144.6	144.4	143.4
54.5°	141.3	141.4	142.3	142.5	142.3	141.4
55°	139.2	139.3	140.2	140.5	140.3	139.3
55.5°	137.1	137.3	138.1	138.4	138.1	137.2
56°	135.0	135.2	136.0	136.3	136.0	135.1
56.5°	132.9	133.1	133.9	134.1	133.9	132.9
57°	130.9	130.9	131.7	132.0	131.8	130.8
57.5°	128.7	128.8	129.6	129.9	129.7	128.7
58°	126.6	126.7	127.5	127.7	127.5	126.5
58.5°	124.4	124.5	125.4	125.6	125.3	124.4
59°	122.3	122.4	123.2	123.4	123.2	122.2
59.5°	120.1	120.3	121.1	121.3	121.0	120.0
60°	118.1	118.0	118.9	119.2	118.9	117.8
60.5°	115.8	115.9	116.7	116.9	116.6	115.7
61°	113.7	113.8	114.6	114.7	114.5	113.5
61.5°	111.5	111.6	112.4	112.6	112.3	111.3
62°	109.4	109.4	110.2	110.4	110.1	109.0
62.5°	107.2	107.2	108.0	108.2	107.9	106.9
63°	105.1	105.0	105.8	106.0	105.6	104.6
63.5°	102.8	102.8	103.6	103.8	103.4	102.4
64°	100.6	100.6	101.4	101.6	101.2	100.2
64.5°	98.4	98.5	99.2	99.4	99.0	98.0
65°	96.3	96.2	97.0	97.1	96.9	95.8
65.5°	94.0	94.0	94.8	94.9	94.6	93.5
66°	91.9	91.8	92.6	92.7	92.3	91.3
66.5°	89.6	89.6	90.3	90.5	90.1	89.0
67°	87.5	87.4	88.1	88.2	87.8	86.8



TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	85.3	85.2	85.9	86.1	85.7	84.6
68°	83.1	83.0	83.7	83.8	83.4	82.4
68.5°	80.9	80.8	81.5	81.6	81.2	80.2
69°	78.7	78.6	79.3	79.4	78.9	77.9
69.5°	76.5	76.4	77.0	77.2	76.7	75.7
70°	74.3	74.2	74.9	75.0	74.5	73.4
70.5°	72.1	72.0	72.7	72.8	72.3	71.3
71°	70.0	69.8	70.5	70.6	70.1	69.1
71.5°	67.8	67.7	68.3	68.4	67.9	66.8
72°	65.7	65.4	66.1	66.2	65.7	64.7
72.5°	63.4	63.3	63.9	64.0	63.5	62.5
73°	61.3	61.1	61.8	61.8	61.3	60.3
73.5°	59.1	59.0	59.6	59.7	59.1	58.1
74°	57.0	56.7	57.4	57.5	57.0	56.0
74.5°	54.9	54.7	55.3	55.4	54.9	53.8
75°	52.8	52.6	53.2	53.2	52.8	51.7
75.5°	50.7	50.5	51.1	51.1	50.6	49.6
76°	48.6	48.4	49.0	49.0	48.5	47.5
76.5°	46.5	46.3	46.9	46.9	46.4	45.3
77°	44.4	44.3	44.8	44.8	44.3	43.3
77.5°	42.4	42.2	42.8	42.8	42.3	41.2
78°	40.4	40.2	40.8	40.8	40.2	39.2
78.5°	38.4	38.2	38.7	38.7	38.2	37.2
79°	36.3	36.3	36.7	36.7	36.1	35.2
79.5°	34.4	34.4	34.8	34.8	34.2	33.3
80°	32.4	32.4	32.9	32.9	32.3	31.3
80.5°	30.5	30.5	31.0	30.9	30.4	29.4
81°	28.6	28.6	29.1	29.0	28.4	27.4
81.5°	26.8	26.7	27.1	27.1	26.5	25.5
82°	24.8	24.9	25.3	25.3	24.7	23.7
82.5°	23.0	23.1	23.4	23.4	22.8	21.8
83°	21.2	21.3	21.6	21.5	20.9	20.0
83.5°	19.4	19.4	19.8	19.7	19.1	18.1
84°	17.7	17.7	18.1	18.0	17.3	16.4
84.5°	16.0	16.0	16.3	16.2	15.5	14.6
85°	14.2	14.2	14.6	14.4	13.8	12.9
85.5°	12.5	12.5	12.8	12.7	12.1	11.1
86°	10.9	10.9	11.1	11.1	10.4	9.5
86.5°	9.3	9.2	9.5	9.3	8.8	7.8
87°	7.6	7.6	7.8	7.7	7.1	6.2
87.5°	6.0	6.0	6.2	6.1	5.5	4.6
88°	4.4	4.4	4.7	4.5	4.0	3.2
88.5°	2.9	3.5	3.1	2.9	3.0	2.4
89°	1.6	2.6	2.3	2.2	2.0	1.6
89.5°	0.8	1.8	1.6	1.5	1.1	0.8



TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.3	0.9	0.8	0.7	0.1	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.1
111.5°	0.0	0.0	0.0	0.0	0.1	0.1
112°	0.0	0.0	0.0	0.0	0.1	0.1



TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.0	0.1	0.0	0.1	0.1	0.1
113°	0.0	0.1	0.1	0.1	0.1	0.1
113.5°	0.0	0.1	0.1	0.1	0.1	0.1
114°	0.0	0.1	0.1	0.1	0.1	0.1
114.5°	0.0	0.1	0.1	0.1	0.1	0.1
115°	0.0	0.1	0.1	0.1	0.1	0.1
115.5°	0.0	0.1	0.1	0.1	0.1	0.1
116°	0.1	0.1	0.1	0.1	0.1	0.1
116.5°	0.1	0.1	0.1	0.1	0.1	0.1
117°	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1
118°	0.1	0.1	0.1	0.1	0.1	0.1
118.5°	0.1	0.1	0.1	0.1	0.1	0.1
119°	0.1	0.1	0.1	0.1	0.1	0.1
119.5°	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1
120.5°	0.1	0.1	0.1	0.1	0.1	0.1
121°	0.1	0.1	0.1	0.1	0.1	0.1
121.5°	0.1	0.1	0.1	0.1	0.1	0.1
122°	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.1	0.1	0.1	0.1	0.1	0.1
123°	0.1	0.1	0.1	0.1	0.1	0.1
123.5°	0.1	0.1	0.1	0.1	0.1	0.1
124°	0.1	0.1	0.1	0.1	0.1	0.1
124.5°	0.1	0.1	0.1	0.1	0.1	0.1
125°	0.1	0.1	0.1	0.1	0.1	0.1
125.5°	0.1	0.1	0.1	0.1	0.1	0.1
126°	0.1	0.1	0.1	0.1	0.1	0.1
126.5°	0.1	0.1	0.1	0.1	0.1	0.1
127°	0.1	0.1	0.1	0.1	0.1	0.1
127.5°	0.1	0.1	0.1	0.1	0.1	0.1
128°	0.1	0.1	0.1	0.1	0.1	0.1
128.5°	0.1	0.1	0.1	0.1	0.1	0.1
129°	0.1	0.1	0.1	0.1	0.1	0.1
129.5°	0.1	0.1	0.1	0.1	0.1	0.1
130°	0.1	0.1	0.1	0.1	0.1	0.1
130.5°	0.1	0.1	0.1	0.1	0.1	0.1
131°	0.1	0.1	0.1	0.1	0.1	0.1
131.5°	0.1	0.1	0.1	0.1	0.1	0.1
132°	0.1	0.1	0.1	0.1	0.1	0.1
132.5°	0.1	0.1	0.1	0.1	0.1	0.1
133°	0.1	0.1	0.1	0.1	0.1	0.1
133.5°	0.1	0.1	0.1	0.1	0.1	0.1
134°	0.1	0.1	0.1	0.1	0.1	0.1
134.5°	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.1	0.1	0.1	0.1	0.1	0.1
135.5°	0.1	0.1	0.1	0.1	0.1	0.1
136°	0.1	0.1	0.1	0.1	0.1	0.1
136.5°	0.1	0.1	0.1	0.1	0.1	0.1
137°	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1
138°	0.1	0.1	0.1	0.1	0.1	0.1
138.5°	0.1	0.1	0.1	0.1	0.1	0.1
139°	0.1	0.1	0.1	0.1	0.1	0.1
139.5°	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1
140.5°	0.1	0.1	0.1	0.1	0.1	0.1
141°	0.1	0.1	0.1	0.1	0.1	0.1
141.5°	0.1	0.1	0.1	0.1	0.1	0.1
142°	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.1	0.1	0.1	0.1	0.1	0.1
143°	0.2	0.1	0.1	0.1	0.1	0.1
143.5°	0.2	0.1	0.1	0.1	0.1	0.1
144°	0.2	0.1	0.1	0.1	0.1	0.1
144.5°	0.2	0.1	0.1	0.1	0.1	0.1
145°	0.2	0.1	0.1	0.1	0.1	0.1
145.5°	0.2	0.1	0.1	0.1	0.1	0.1
146°	0.2	0.1	0.1	0.1	0.1	0.1
146.5°	0.2	0.1	0.1	0.1	0.1	0.1
147°	0.2	0.1	0.1	0.1	0.1	0.1
147.5°	0.2	0.1	0.1	0.1	0.1	0.2
148°	0.2	0.1	0.1	0.1	0.1	0.2
148.5°	0.2	0.1	0.1	0.1	0.1	0.1
149°	0.2	0.1	0.1	0.1	0.2	0.1
149.5°	0.2	0.1	0.1	0.1	0.2	0.2
150°	0.2	0.1	0.1	0.1	0.2	0.2
150.5°	0.2	0.1	0.1	0.1	0.2	0.2
151°	0.2	0.1	0.1	0.1	0.2	0.2
151.5°	0.2	0.1	0.1	0.1	0.2	0.2
152°	0.2	0.1	0.1	0.1	0.2	0.2
152.5°	0.2	0.1	0.1	0.1	0.2	0.2
153°	0.2	0.1	0.1	0.1	0.2	0.2
153.5°	0.2	0.1	0.1	0.1	0.2	0.2
154°	0.2	0.1	0.1	0.1	0.2	0.2
154.5°	0.2	0.1	0.1	0.1	0.2	0.2
155°	0.2	0.1	0.1	0.1	0.2	0.2
155.5°	0.2	0.1	0.1	0.1	0.2	0.2
156°	0.2	0.1	0.1	0.1	0.2	0.1
156.5°	0.2	0.1	0.1	0.1	0.2	0.1
157°	0.2	0.1	0.1	0.1	0.2	0.1



TEST NUMBER: P991372

CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.2	0.1	0.1	0.2	0.2	0.1
158°	0.2	0.1	0.1	0.2	0.2	0.1
158.5°	0.2	0.1	0.1	0.2	0.2	0.2
159°	0.2	0.1	0.1	0.2	0.2	0.2
159.5°	0.2	0.1	0.1	0.2	0.2	0.2
160°	0.2	0.1	0.1	0.2	0.2	0.2
160.5°	0.2	0.1	0.2	0.2	0.2	0.2
161°	0.2	0.2	0.2	0.2	0.2	0.2
161.5°	0.2	0.2	0.2	0.2	0.2	0.2
162°	0.2	0.2	0.2	0.2	0.2	0.2
162.5°	0.2	0.2	0.2	0.2	0.2	0.2
163°	0.2	0.2	0.2	0.2	0.2	0.2
163.5°	0.2	0.2	0.2	0.2	0.2	0.2
164°	0.2	0.2	0.2	0.2	0.2	0.2
164.5°	0.2	0.2	0.2	0.2	0.2	0.2
165°	0.2	0.2	0.2	0.2	0.2	0.2
165.5°	0.2	0.2	0.2	0.2	0.2	0.2
166°	0.2	0.2	0.2	0.2	0.2	0.2
166.5°	0.2	0.2	0.2	0.2	0.2	0.2
167°	0.2	0.2	0.2	0.2	0.2	0.2
167.5°	0.3	0.2	0.2	0.2	0.2	0.2
168°	0.3	0.2	0.2	0.2	0.2	0.2
168.5°	0.2	0.2	0.2	0.2	0.2	0.2
169°	0.2	0.2	0.2	0.2	0.2	0.2
169.5°	0.2	0.2	0.2	0.2	0.2	0.2
170°	0.2	0.2	0.2	0.2	0.2	0.2
170.5°	0.2	0.2	0.2	0.2	0.2	0.2
171°	0.2	0.2	0.2	0.2	0.2	0.2
171.5°	0.2	0.2	0.2	0.2	0.2	0.2
172°	0.2	0.2	0.2	0.2	0.2	0.2
172.5°	0.2	0.2	0.2	0.2	0.2	0.2
173°	0.2	0.2	0.2	0.2	0.2	0.2
173.5°	0.2	0.2	0.2	0.2	0.2	0.2
174°	0.2	0.2	0.2	0.2	0.2	0.2
174.5°	0.2	0.2	0.2	0.2	0.2	0.2
175°	0.2	0.2	0.2	0.2	0.2	0.2
175.5°	0.2	0.2	0.2	0.2	0.2	0.2
176°	0.2	0.2	0.2	0.2	0.2	0.2
176.5°	0.2	0.2	0.2	0.2	0.2	0.2
177°	0.2	0.2	0.2	0.2	0.2	0.2
177.5°	0.2	0.2	0.2	0.2	0.2	0.2
178°	0.2	0.2	0.2	0.2	0.2	0.2
178.5°	0.2	0.2	0.2	0.2	0.2	0.2
179°	0.2	0.2	0.2	0.2	0.2	0.2
179.5°	0.2	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: P991372
CATALOG NUMBER: SMD4R07FS5-950

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.2	0.2	0.2	0.2	0.2	0.2

(END OF REPORT)