

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: E395202

Luminaire Tested: **H7-1410**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: E395202
Test Lab:
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: H7-1410
Description: HALO RECESSED INC - LV ADJ, 8" SPOT
Light Source: 50MR16NFL, 900 LUMENS
Ballast/Driver: -

Summary


Lumens per Lamp: 900 (1 lamp)
Luminaire Lumens: 991.1 lumens
Efficiency: 110.1%
Efficacy: 16.5 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.46
Luminous Opening: (L: 0 ' x W: -0.15 ' x H: 0 '
CIE Type: Direct

Input Watts (W): 60
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: E395202
CATALOG NUMBER: H7-1410

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	131	131	131	131	128	128	128	128	122	122	122	117	117	117	112	112	112	110
1	120	115	111	107	117	113	109	105	108	105	102	104	101	98	100	98	95	93
2	112	104	97	92	109	102	96	91	98	93	89	94	90	87	91	88	85	82
3	105	95	88	82	103	94	87	81	91	85	80	88	83	79	85	81	77	75
4	100	89	81	75	97	88	81	75	85	79	74	83	77	73	81	76	72	70
5	95	84	76	71	93	83	76	70	81	75	70	79	73	69	77	72	68	67
6	91	80	72	67	89	79	72	67	77	71	66	76	70	66	74	69	65	64
7	88	76	69	64	86	76	69	64	74	68	63	73	67	63	71	67	63	61
8	84	73	66	61	83	73	66	61	71	65	61	70	65	61	69	64	61	59
9	81	71	64	59	80	70	64	59	69	63	59	68	63	59	67	62	59	57
10	79	68	62	57	78	68	61	57	67	61	57	66	61	57	65	60	57	55

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	Luminous shape not found, reference photometric report, or contact the photometric lab for calculations.			
5°				
10°				
15°				
20°				
25°				
30°				
35°				
40°				
45°				
50°				
55°				
60°				
65°				
70°				
75°				
80°				
85°				



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

ZONAL LUMENS:

Zone	Lumens	% Fixture	% Lamp
0°-10°	217.4	21.9	24.2
10°-20°	326.1	32.9	36.2
20°-30°	108.8	11.0	12.1
30°-40°	30.2	3.1	3.4
40°-50°	6.3	0.6	0.7
50°-60°	36.7	3.7	4.1
60°-70°	110.6	11.2	12.3
70°-80°	109.2	11.0	12.1
80°-90°	45.8	4.6	5.1
90°-100°	0.0	0.0	0.0
100°-110°	0.0	0.0	0.0
110°-120°	0.0	0.0	0.0
120°-130°	0.0	0.0	0.0
130°-140°	0.0	0.0	0.0
140°-150°	0.0	0.0	0.0
150°-160°	0.0	0.0	0.0
160°-170°	0.0	0.0	0.0
170°-180°	0.0	0.0	0.0
0°-30°	652.3	65.8	72.5
0°-40°	682.5	68.9	75.8
0°-60°	725.5	73.2	80.6
0°-90°	991.1	100.0	110.1
90°-120°	0.0	0.0	0.0
90°-150°	0.0	0.0	0.0
90°-180°	0.0	0.0	0.0
0°-180°	991.1	100.0	110.1

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2575	2575	2575	2575	2575	
5°	2387	2386	2387	2387	2387	219
15°	1215	1215	1215	1215	1215	335
25°	212	212	212	212	212	110
35°	42	42	42	42	42	30
45°	6	6	6	6	6	6
55°	3	3	3	3	3	3
65°	2	2	2	2	2	2
75°	1	1	1	1	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575
2.5°	2510	2509	2508	2507	2506	2506	2506	2506	2506	2507	2508
5°	2387	2384	2383	2382	2381	2381	2381	2382	2383	2384	2384
7.5°	2254	2250	2248	2246	2245	2245	2246	2241	2235	2231	2229
10°	2115	2109	2104	2100	2097	2089	2072	2057	2044	2033	2025
12.5°	1643	1636	1633	1635	1635	1624	1618	1616	1619	1627	1639
15°	1215	1206	1201	1200	1183	1166	1152	1140	1131	1131	1145
17.5°	851	845	844	840	827	818	811	807	806	802	802
20°	552	548	549	544	538	534	532	531	523	513	502
22.5°	306	304	304	300	297	296	305	314	321	325	327
25°	212	211	211	210	210	211	212	212	212	212	212
27.5°	148	148	147	146	145	145	144	142	142	144	147
30°	105	105	105	106	107	108	108	108	108	107	106
32.5°	71	70	70	69	70	70	72	73	74	74	73
35°	42	42	41	39	38	37	37	39	41	43	45
37.5°	23	23	23	24	25	25	25	26	25	25	25
40°	16	16	16	16	17	17	17	17	17	17	17
42.5°	12	12	12	12	12	12	12	12	12	11	11
45°	6	6	6	6	6	6	6	7	7	7	6
47.5°	4	4	3	3	3	2	2	2	2	2	2
50°	4	4	3	3	2	2	2	2	1	0	0
52.5°	3	3	3	3	2	2	2	2	1	0	0
55°	3	3	3	2	2	2	2	2	1	0	0
57.5°	3	3	3	2	2	2	2	1	0	0	0
60°	3	3	2	2	2	1	1	1	0	0	0
62.5°	3	2	2	2	1	1	1	1	0	0	0
65°	2	2	2	2	1	1	1	1	0	0	0
67.5°	2	2	2	1	1	1	1	0	0	0	0
70°	2	2	2	1	1	1	1	0	0	0	0
72.5°	2	2	1	1	1	1	1	0	0	0	0
75°	1	1	1	1	1	1	1	0	0	0	0
77.5°	1	1	1	1	1	1	0	0	0	0	0
80°	1	1	1	1	0	0	0	0	0	0	0
82.5°	1	1	1	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575
2.5°	2509	2510	2512	2516	2515	2515	2514	2514	2514	2515	2515
5°	2381	2378	2376	2375	2374	2373	2372	2372	2372	2373	2373
7.5°	2228	2229	2232	2236	2241	2240	2240	2240	2240	2240	2241
10°	2019	2016	2016	2019	2028	2009	2001	1999	2001	2008	2019
12.5°	1656	1666	1663	1659	1654	1635	1623	1619	1621	1632	1649
15°	1159	1172	1182	1191	1196	1198	1204	1194	1195	1196	1195
17.5°	806	812	822	836	837	827	824	823	822	824	826
20°	495	504	516	524	527	524	516	501	505	517	524
22.5°	326	325	322	317	310	313	322	327	326	319	308
25°	210	207	211	212	214	214	213	209	207	211	213
27.5°	150	150	150	149	147	146	147	149	149	148	147
30°	107	107	106	107	107	106	106	106	106	106	106
32.5°	72	72	72	73	73	72	72	73	73	73	72
35°	45	44	43	42	43	44	45	44	44	44	44
37.5°	24	24	25	26	25	24	25	25	25	26	26
40°	17	17	16	16	16	17	16	16	17	17	17
42.5°	12	12	12	12	11	12	12	12	12	12	12
45°	6	7	7	7	7	7	7	7	7	7	7
47.5°	2	3	3	2	2	3	2	3	3	3	3
50°	0	0	0	0	0	0	0	1	2	1	0
52.5°	0	0	0	0	0	0	0	3	19	21	74
55°	0	0	0	0	0	0	0	91	139	179	280
57.5°	0	0	0	0	0	0	52	190	351	512	598
60°	0	0	0	0	0	0	119	256	458	679	868
62.5°	0	0	0	0	0	45	172	332	539	735	909
65°	0	0	0	0	0	89	210	393	594	756	928
67.5°	0	0	0	0	11	120	251	431	601	756	828
70°	0	0	0	0	38	139	278	447	589	733	728
72.5°	0	0	0	0	56	148	288	435	559	635	631
75°	0	0	0	0	65	153	281	402	513	540	536
77.5°	0	0	0	0	67	148	258	356	451	446	443
80°	0	0	0	8	62	133	223	299	358	355	352
82.5°	0	0	0	10	51	108	176	232	268	265	262
85°	0	0	0	9	36	76	121	159	178	176	174
87.5°	0	0	0	5	19	39	62	81	89	88	87
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575
2.5°	2516	2512	2510	2509	2508	2507	2506	2506	2506	2506	2506
5°	2375	2376	2378	2381	2383	2385	2383	2382	2381	2381	2381
7.5°	2237	2232	2229	2228	2229	2231	2235	2240	2246	2245	2245
10°	2021	2018	2017	2020	2025	2033	2043	2056	2071	2088	2097
12.5°	1659	1663	1666	1661	1643	1629	1620	1617	1618	1624	1634
15°	1191	1183	1173	1160	1146	1131	1136	1136	1149	1164	1181
17.5°	832	825	814	806	802	802	806	808	812	818	828
20°	524	519	510	499	499	509	521	531	534	535	538
22.5°	308	316	321	324	324	324	321	315	307	296	295
25°	213	212	210	206	208	209	209	209	210	210	209
27.5°	147	148	149	148	147	145	142	140	142	144	145
30°	106	106	105	104	105	105	106	106	107	107	107
32.5°	72	73	74	74	74	75	74	73	72	71	70
35°	44	44	44	45	46	45	42	40	37	36	38
37.5°	24	24	26	26	25	22	22	23	24	24	24
40°	17	17	16	16	17	17	17	16	16	16	16
42.5°	12	12	11	12	12	12	12	11	12	12	12
45°	7	6	7	7	7	7	6	8	9	9	8
47.5°	2	3	4	3	2	13	16	14	11	7	5
50°	24	37	21	32	49	50	39	25	14	9	6
52.5°	129	135	145	149	143	91	57	32	18	11	6
55°	336	341	339	282	198	130	74	45	24	13	7
57.5°	602	606	511	384	265	179	111	61	31	16	8
60°	932	830	659	503	366	243	154	90	46	22	10
62.5°	1034	1025	832	645	484	339	215	124	65	30	13
65°	928	927	929	821	622	454	304	182	97	44	18
67.5°	825	824	824	826	797	593	415	262	145	68	25
70°	725	723	723	724	726	731	553	368	214	104	39
72.5°	627	625	624	624	625	629	634	504	314	161	66
75°	532	530	528	527	528	530	533	539	447	254	110
77.5°	440	437	435	434	434	434	436	439	445	383	186
80°	349	347	345	343	342	342	343	344	347	353	313
82.5°	260	258	257	255	254	253	253	253	254	257	262
85°	173	171	170	169	168	167	167	166	166	167	168
87.5°	86	85	85	84	84	83	83	82	82	82	82
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575
2.5°	2507	2508	2509	2510	2509	2508	2507	2506	2506	2506	2506
5°	2382	2383	2384	2386	2384	2383	2382	2381	2381	2381	2382
7.5°	2246	2248	2250	2254	2250	2248	2246	2245	2245	2245	2240
10°	2100	2104	2109	2115	2109	2104	2100	2097	2088	2071	2056
12.5°	1636	1634	1636	1643	1636	1634	1636	1634	1624	1618	1617
15°	1203	1202	1206	1215	1206	1202	1202	1181	1164	1149	1136
17.5°	840	845	846	851	846	845	840	828	818	812	808
20°	544	550	548	552	548	550	544	538	535	534	531
22.5°	298	304	304	306	304	303	298	295	296	307	315
25°	209	211	211	212	211	211	209	209	210	210	209
27.5°	146	147	148	148	148	147	146	145	144	142	140
30°	106	105	105	105	105	105	106	107	107	107	106
32.5°	70	70	70	71	70	70	70	70	71	72	73
35°	39	41	42	42	42	41	39	38	36	37	40
37.5°	24	23	23	23	23	23	24	24	24	24	23
40°	16	16	16	16	16	16	16	16	16	16	16
42.5°	12	12	12	12	12	12	12	12	12	12	11
45°	7	7	6	6	6	7	7	7	7	7	6
47.5°	4	4	4	4	4	4	3	3	3	3	3
50°	4	4	4	4	4	4	3	3	3	2	2
52.5°	4	4	3	3	3	3	3	3	2	2	1
55°	4	3	3	3	3	3	2	2	2	1	1
57.5°	5	3	3	3	3	3	2	2	1	1	1
60°	5	3	3	3	3	2	2	2	1	1	1
62.5°	5	3	3	3	3	2	2	1	1	1	1
65°	7	3	2	2	2	2	2	1	1	1	1
67.5°	9	3	2	2	2	2	1	1	1	1	1
70°	12	4	2	2	2	1	1	1	1	1	0
72.5°	18	5	2	2	1	1	0	0	0	0	0
75°	31	6	2	1	1	1	0	0	0	0	0
77.5°	61	10	2	1	1	0	0	0	0	0	0
80°	124	22	2	1	1	0	0	0	0	0	0
82.5°	239	59	3	1	0	0	0	0	0	0	0
85°	172	161	12	0	0	0	0	0	0	0	0
87.5°	82	84	81	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575
2.5°	2506	2507	2508	2509	2510	2512	2516	2515	2515	2514	2514
5°	2383	2384	2383	2381	2378	2376	2375	2373	2373	2372	2372
7.5°	2235	2231	2229	2228	2229	2232	2237	2241	2240	2240	2240
10°	2043	2033	2025	2020	2017	2018	2021	2019	2008	2001	1999
12.5°	1620	1629	1643	1661	1666	1663	1659	1649	1632	1621	1619
15°	1136	1131	1146	1160	1173	1183	1191	1195	1196	1195	1194
17.5°	806	802	802	806	814	825	832	826	824	822	823
20°	521	509	499	499	510	519	524	524	517	505	501
22.5°	321	324	322	324	321	316	308	308	319	326	327
25°	209	209	208	206	210	211	213	213	211	207	209
27.5°	142	145	147	148	149	148	147	147	148	149	149
30°	106	105	105	104	105	106	106	106	106	106	106
32.5°	74	75	74	74	74	73	72	72	73	73	73
35°	42	45	46	45	44	44	44	44	44	44	44
37.5°	22	22	25	26	26	24	24	26	26	25	25
40°	17	17	17	16	16	17	17	17	17	17	16
42.5°	12	12	12	12	11	12	12	12	12	12	12
45°	6	7	7	7	7	6	7	7	7	7	7
47.5°	3	3	2	2	2	2	2	3	3	3	3
50°	1	1	1	0	0	0	0	0	1	1	1
52.5°	1	1	1	1	0	0	0	0	0	0	0
55°	1	1	1	1	1	0	0	0	0	0	0
57.5°	1	1	1	1	1	0	0	0	0	0	0
60°	1	1	1	1	0	0	0	0	0	0	0
62.5°	1	1	1	0	0	0	0	0	0	0	0
65°	1	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575
2.5°	2514	2513	2514	2513	2512	2510	2509	2508	2507	2506	2506
5°	2372	2373	2374	2375	2376	2378	2381	2384	2384	2383	2382
7.5°	2240	2240	2239	2236	2232	2229	2228	2229	2231	2235	2241
10°	2001	2009	2028	2019	2016	2016	2019	2025	2033	2044	2057
12.5°	1623	1635	1651	1659	1663	1666	1656	1639	1627	1619	1616
15°	1204	1198	1196	1191	1182	1172	1159	1145	1113	1131	1140
17.5°	824	827	832	836	822	812	806	802	802	806	807
20°	516	524	527	524	516	504	495	502	513	523	531
22.5°	322	313	310	317	322	325	326	327	325	321	314
25°	213	214	214	212	211	207	210	212	212	212	212
27.5°	147	146	147	149	150	150	150	147	144	141	142
30°	106	106	107	107	106	107	107	106	107	108	108
32.5°	72	72	73	73	72	72	72	73	74	74	73
35°	45	44	43	42	43	44	45	45	43	41	39
37.5°	25	24	25	26	25	24	24	25	25	25	26
40°	16	17	16	16	16	17	17	17	17	17	17
42.5°	12	12	11	12	12	12	12	11	11	12	12
45°	7	7	7	7	7	7	6	6	7	7	7
47.5°	2	3	2	2	3	3	2	2	2	2	2
50°	0	0	0	0	0	0	0	0	0	1	2
52.5°	0	0	0	0	0	0	0	0	0	1	2
55°	0	0	0	0	0	0	0	0	0	1	2
57.5°	0	0	0	0	0	0	0	0	0	0	1
60°	0	0	0	0	0	0	0	0	0	0	1
62.5°	0	0	0	0	0	0	0	0	0	0	1
65°	0	0	0	0	0	0	0	0	0	0	1
67.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575
2.5°	2506	2506	2506	2507	2508	2509	2510	2509	2508	2507	2506
5°	2381	2381	2381	2382	2383	2384	2387	2384	2383	2382	2381
7.5°	2246	2245	2245	2246	2248	2250	2254	2250	2248	2246	2245
10°	2072	2089	2097	2095	2102	2108	2115	2108	2102	2095	2097
12.5°	1618	1624	1635	1635	1633	1636	1643	1636	1633	1635	1635
15°	1152	1166	1183	1200	1201	1206	1215	1206	1201	1200	1183
17.5°	811	818	827	840	844	845	851	845	844	840	827
20°	532	534	538	544	549	548	552	548	549	544	538
22.5°	305	296	297	300	304	304	306	304	304	300	297
25°	212	211	210	210	211	211	212	211	211	210	210
27.5°	144	145	145	146	147	148	148	148	147	146	145
30°	108	108	107	106	104	104	105	104	104	106	107
32.5°	72	70	70	69	70	70	71	70	70	69	70
35°	37	37	38	39	41	42	42	42	41	39	38
37.5°	25	25	25	24	23	23	23	23	23	24	25
40°	17	17	17	16	16	16	16	16	16	16	17
42.5°	12	12	12	12	12	12	12	12	12	12	12
45°	6	6	6	6	6	6	6	6	6	6	6
47.5°	2	2	3	3	3	4	4	4	3	3	3
50°	2	2	2	3	3	4	4	4	3	3	2
52.5°	2	2	2	3	3	3	3	3	3	3	2
55°	2	2	2	2	3	3	3	3	3	2	2
57.5°	2	2	2	2	3	3	3	3	3	2	2
60°	1	1	2	2	2	3	3	3	2	2	2
62.5°	1	1	1	2	2	2	3	2	2	2	1
65°	1	1	1	2	2	2	2	2	2	2	1
67.5°	1	1	1	1	2	2	2	2	2	1	1
70°	1	1	1	1	2	2	2	2	2	1	1
72.5°	1	1	1	1	1	2	2	2	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	0	1	1	1	1	1	1	1	1	1	1
80°	0	0	0	1	1	1	1	1	1	1	0
82.5°	0	0	0	0	1	1	1	1	1	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575
2.5°	2506	2506	2506	2506	2507	2508	2509	2510	2512	2513	2514
5°	2381	2381	2382	2383	2384	2384	2381	2378	2376	2375	2374
7.5°	2245	2246	2241	2235	2231	2229	2228	2229	2232	2236	2239
10°	2089	2072	2057	2044	2033	2025	2019	2016	2016	2019	2028
12.5°	1624	1618	1616	1619	1627	1639	1656	1666	1663	1659	1651
15°	1166	1152	1140	1131	1113	1145	1159	1172	1182	1191	1196
17.5°	818	811	807	806	802	802	806	812	822	836	832
20°	534	532	531	523	513	502	495	504	516	524	527
22.5°	296	305	314	321	325	327	326	325	322	317	310
25°	211	212	212	212	212	212	210	207	211	212	214
27.5°	145	144	142	141	144	147	150	150	150	149	147
30°	108	108	108	108	107	106	107	107	106	107	107
32.5°	70	72	73	74	74	73	72	72	72	73	73
35°	37	37	39	41	43	45	45	44	43	42	43
37.5°	25	25	26	25	25	25	24	24	25	26	25
40°	17	17	17	17	17	17	17	17	16	16	16
42.5°	12	12	12	12	11	11	12	12	12	12	11
45°	6	6	7	7	7	6	6	7	7	7	7
47.5°	2	2	2	2	2	2	2	3	3	2	2
50°	2	2	2	1	0	0	0	0	0	0	0
52.5°	2	2	2	1	0	0	0	0	0	0	0
55°	2	2	2	1	0	0	0	0	0	0	0
57.5°	2	2	1	0	0	0	0	0	0	0	0
60°	1	1	1	0	0	0	0	0	0	0	0
62.5°	1	1	1	0	0	0	0	0	0	0	0
65°	1	1	1	0	0	0	0	0	0	0	0
67.5°	1	1	0	0	0	0	0	0	0	0	0
70°	1	1	0	0	0	0	0	0	0	0	0
72.5°	1	1	0	0	0	0	0	0	0	0	0
75°	1	1	0	0	0	0	0	0	0	0	0
77.5°	1	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575
2.5°	2513	2514	2514	2514	2515	2515	2516	2512	2510	2509	2508
5°	2373	2372	2372	2372	2373	2373	2375	2376	2378	2381	2383
7.5°	2240	2240	2240	2240	2240	2241	2237	2232	2229	2228	2229
10°	2009	2001	1999	2001	2008	2019	2021	2018	2017	2020	2025
12.5°	1635	1623	1619	1621	1632	1649	1659	1663	1666	1661	1643
15°	1198	1204	1194	1195	1196	1195	1191	1183	1173	1160	1146
17.5°	827	824	823	822	824	826	832	825	814	806	802
20°	524	516	501	505	517	524	524	519	510	499	499
22.5°	313	322	327	326	319	308	308	316	321	324	322
25°	214	213	209	207	211	213	213	211	210	206	208
27.5°	146	147	149	149	148	147	147	148	149	148	147
30°	106	106	106	106	106	106	106	106	105	104	105
32.5°	72	72	73	73	73	72	72	73	74	74	74
35°	44	45	44	44	44	44	44	44	44	45	46
37.5°	24	25	25	25	26	26	24	24	26	26	25
40°	17	16	16	17	17	17	17	17	16	16	17
42.5°	12	12	12	12	12	12	12	12	11	12	12
45°	7	7	7	7	7	7	7	6	7	7	7
47.5°	3	2	3	3	3	3	2	2	2	2	2
50°	0	0	1	1	1	0	0	0	0	0	1
52.5°	0	0	0	0	0	0	0	0	0	1	1
55°	0	0	0	0	0	0	0	0	1	1	1
57.5°	0	0	0	0	0	0	0	0	1	1	1
60°	0	0	0	0	0	0	0	0	0	1	1
62.5°	0	0	0	0	0	0	0	0	0	0	1
65°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575
2.5°	2507	2506	2506	2506	2506	2506	2507	2508	2509	2510	2509
5°	2384	2383	2382	2381	2381	2381	2382	2383	2384	2387	2384
7.5°	2231	2235	2240	2245	2245	2245	2246	2248	2250	2254	2250
10°	2033	2043	2056	2071	2088	2097	2100	2104	2109	2115	2109
12.5°	1629	1620	1617	1618	1624	1634	1636	1634	1636	1643	1636
15°	1131	1136	1136	1149	1164	1181	1202	1202	1206	1215	1206
17.5°	802	806	808	812	818	828	840	845	846	851	846
20°	509	521	531	534	535	538	544	550	548	552	548
22.5°	324	321	315	307	296	295	298	303	304	306	304
25°	209	209	209	210	210	209	209	211	211	212	211
27.5°	145	142	140	142	144	145	146	147	148	148	148
30°	105	106	106	107	107	107	106	105	105	105	105
32.5°	75	74	73	72	71	70	70	70	70	71	70
35°	45	42	40	37	36	38	39	41	42	42	42
37.5°	22	22	23	24	24	24	24	23	23	23	23
40°	17	17	16	16	16	16	16	16	16	16	16
42.5°	12	12	11	12	12	12	12	12	12	12	12
45°	7	6	6	7	7	7	7	7	6	6	6
47.5°	3	3	3	3	3	3	3	4	4	4	4
50°	1	1	2	2	3	3	3	4	4	4	4
52.5°	1	1	1	2	2	3	3	3	3	3	3
55°	1	1	1	1	2	2	2	3	3	3	3
57.5°	1	1	1	1	1	2	2	3	3	3	3
60°	1	1	1	1	1	2	2	2	3	3	3
62.5°	1	1	1	1	1	1	2	2	3	3	3
65°	0	1	1	1	1	1	2	2	2	2	2
67.5°	0	0	1	1	1	1	1	2	2	2	2
70°	0	0	0	1	1	1	1	1	2	2	2
72.5°	0	0	0	0	0	0	0	1	1	2	2
75°	0	0	0	0	0	0	0	1	1	1	2
77.5°	0	0	0	0	0	0	0	0	1	1	2
80°	0	0	0	0	0	0	0	0	1	1	2
82.5°	0	0	0	0	0	0	0	0	0	1	3
85°	0	0	0	0	0	0	0	0	0	0	12
87.5°	0	0	0	0	0	0	0	0	0	0	81
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575
2.5°	2508	2507	2506	2506	2506	2506	2506	2507	2508	2509	2510
5°	2383	2382	2381	2381	2381	2382	2383	2385	2383	2381	2378
7.5°	2248	2246	2245	2245	2246	2240	2235	2231	2229	2228	2229
10°	2104	2100	2097	2088	2071	2056	2043	2033	2025	2020	2017
12.5°	1634	1636	1634	1624	1618	1617	1620	1629	1643	1661	1666
15°	1202	1203	1181	1164	1149	1136	1136	1131	1146	1160	1173
17.5°	845	840	828	818	812	808	806	802	802	806	814
20°	550	544	538	535	534	531	521	509	499	499	510
22.5°	304	298	295	296	307	315	321	324	324	324	321
25°	211	209	209	210	210	209	209	209	208	206	210
27.5°	147	146	145	144	142	140	142	145	147	148	149
30°	105	106	107	107	107	106	106	105	105	104	105
32.5°	70	70	70	71	72	73	74	75	74	74	74
35°	41	39	38	36	37	40	42	45	46	45	44
37.5°	23	24	24	24	24	23	22	22	25	26	26
40°	16	16	16	16	16	16	17	17	17	16	16
42.5°	12	12	12	12	12	11	12	12	12	12	11
45°	7	7	8	9	9	8	6	7	7	7	7
47.5°	4	4	5	7	11	14	16	13	2	3	4
50°	4	4	6	9	14	25	39	50	49	32	21
52.5°	4	4	6	11	18	32	57	91	143	149	145
55°	3	4	7	13	24	45	74	130	198	282	339
57.5°	3	5	8	16	31	61	111	179	265	384	511
60°	3	5	10	22	46	90	154	243	366	503	659
62.5°	3	5	13	30	65	124	215	339	484	645	832
65°	3	7	18	44	97	182	304	454	622	821	929
67.5°	3	9	25	68	145	262	415	593	797	826	824
70°	4	12	39	104	214	368	553	731	726	724	723
72.5°	5	18	66	161	314	504	634	629	625	624	624
75°	6	31	110	254	447	539	533	530	528	527	528
77.5°	10	61	186	383	445	439	436	434	434	434	435
80°	22	124	313	353	347	344	343	342	342	343	345
82.5°	59	239	262	257	254	253	253	253	254	255	257
85°	161	172	168	167	166	166	167	167	168	169	170
87.5°	84	82	82	82	82	82	83	83	84	84	85
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575
2.5°	2512	2516	2515	2515	2514	2514	2514	2515	2515	2516	2512
5°	2376	2375	2373	2373	2372	2372	2372	2373	2374	2375	2376
7.5°	2232	2237	2241	2240	2240	2240	2240	2240	2241	2236	2232
10°	2018	2021	2019	2008	2001	1999	2001	2009	2028	2019	2016
12.5°	1663	1659	1649	1632	1621	1619	1623	1635	1654	1659	1663
15°	1183	1191	1195	1196	1195	1194	1204	1198	1196	1191	1182
17.5°	825	832	826	824	822	823	824	827	837	836	822
20°	519	524	524	517	505	501	516	524	527	524	516
22.5°	316	308	308	319	326	327	322	313	310	317	322
25°	212	213	213	211	207	209	213	214	214	212	211
27.5°	148	147	147	148	149	149	147	146	147	149	150
30°	106	106	106	106	106	106	106	106	107	107	106
32.5°	73	72	72	73	73	73	72	72	73	73	72
35°	44	44	44	44	44	44	45	44	43	42	43
37.5°	24	24	26	26	25	25	25	24	25	26	25
40°	17	17	17	17	17	16	16	17	16	16	16
42.5°	12	12	12	12	12	12	12	12	11	12	12
45°	6	7	7	7	7	7	7	7	7	7	7
47.5°	3	2	3	3	3	3	2	3	2	2	3
50°	37	24	0	1	2	1	0	0	0	0	0
52.5°	135	129	74	21	19	3	0	0	0	0	0
55°	341	336	280	179	139	91	0	0	0	0	0
57.5°	606	602	598	512	351	190	52	0	0	0	0
60°	830	932	868	679	458	256	119	0	0	0	0
62.5°	1025	1034	909	735	539	332	172	45	0	0	0
65°	927	928	928	756	594	393	210	89	0	0	0
67.5°	824	825	828	756	601	431	251	120	11	0	0
70°	723	725	728	733	589	447	278	139	38	0	0
72.5°	625	627	631	635	559	435	288	148	56	0	0
75°	530	532	536	540	513	402	281	153	65	0	0
77.5°	437	440	443	446	451	356	258	148	67	0	0
80°	347	349	352	355	358	299	223	133	62	8	0
82.5°	258	260	262	265	268	232	176	108	51	10	0
85°	171	173	174	176	178	159	121	76	36	9	0
87.5°	85	86	87	88	89	81	62	39	19	5	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575	2575
2.5°	2510	2509	2508	2507	2506	2506	2506	2506	2506	2507	2508
5°	2378	2381	2384	2384	2383	2382	2381	2381	2381	2382	2383
7.5°	2229	2228	2229	2231	2235	2241	2246	2245	2245	2246	2248
10°	2016	2019	2025	2033	2044	2057	2072	2089	2097	2100	2104
12.5°	1666	1656	1639	1627	1619	1616	1618	1624	1635	1635	1633
15°	1172	1159	1145	1131	1131	1140	1152	1166	1183	1200	1201
17.5°	812	806	802	802	806	807	811	818	827	840	844
20°	504	495	502	513	523	531	532	534	538	544	549
22.5°	325	326	327	325	321	314	305	296	297	300	304
25°	207	210	212	212	212	212	212	211	210	210	211
27.5°	150	150	147	144	142	142	144	145	145	146	147
30°	107	107	106	107	108	108	108	108	107	106	105
32.5°	72	72	73	74	74	73	72	70	70	69	70
35°	44	45	45	43	41	39	37	37	38	39	41
37.5°	24	24	25	25	25	26	25	25	25	24	23
40°	17	17	17	17	17	17	17	17	17	16	16
42.5°	12	12	11	11	12	12	12	12	12	12	12
45°	7	6	6	7	7	7	6	6	6	6	6
47.5°	3	2	2	2	2	2	2	2	3	3	3
50°	0	0	0	0	1	2	2	2	2	3	3
52.5°	0	0	0	0	1	2	2	2	2	3	3
55°	0	0	0	0	1	2	2	2	2	2	3
57.5°	0	0	0	0	0	1	2	2	2	2	3
60°	0	0	0	0	0	1	1	1	2	2	2
62.5°	0	0	0	0	0	1	1	1	1	2	2
65°	0	0	0	0	0	1	1	1	1	2	2
67.5°	0	0	0	0	0	0	1	1	1	1	2
70°	0	0	0	0	0	0	1	1	1	1	2
72.5°	0	0	0	0	0	0	1	1	1	1	1
75°	0	0	0	0	0	0	1	1	1	1	1
77.5°	0	0	0	0	0	0	0	1	1	1	1
80°	0	0	0	0	0	0	0	0	0	1	1
82.5°	0	0	0	0	0	0	0	0	0	0	1
85°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
90°	0	0	0	0	0	0	0	0	0	0	0
92.5°	0	0	0	0	0	0	0	0	0	0	0
95°	0	0	0	0	0	0	0	0	0	0	0
97.5°	0	0	0	0	0	0	0	0	0	0	0
100°	0	0	0	0	0	0	0	0	0	0	0
102.5°	0	0	0	0	0	0	0	0	0	0	0
105°	0	0	0	0	0	0	0	0	0	0	0
107.5°	0	0	0	0	0	0	0	0	0	0	0
110°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0	0	0	0	0	0	0	0	0	0	0
115°	0	0	0	0	0	0	0	0	0	0	0
117.5°	0	0	0	0	0	0	0	0	0	0	0
120°	0	0	0	0	0	0	0	0	0	0	0
122.5°	0	0	0	0	0	0	0	0	0	0	0
125°	0	0	0	0	0	0	0	0	0	0	0
127.5°	0	0	0	0	0	0	0	0	0	0	0
130°	0	0	0	0	0	0	0	0	0	0	0
132.5°	0	0	0	0	0	0	0	0	0	0	0
135°	0	0	0	0	0	0	0	0	0	0	0
137.5°	0	0	0	0	0	0	0	0	0	0	0
140°	0	0	0	0	0	0	0	0	0	0	0
142.5°	0	0	0	0	0	0	0	0	0	0	0
145°	0	0	0	0	0	0	0	0	0	0	0
147.5°	0	0	0	0	0	0	0	0	0	0	0
150°	0	0	0	0	0	0	0	0	0	0	0
152.5°	0	0	0	0	0	0	0	0	0	0	0
155°	0	0	0	0	0	0	0	0	0	0	0
157.5°	0	0	0	0	0	0	0	0	0	0	0
160°	0	0	0	0	0	0	0	0	0	0	0
162.5°	0	0	0	0	0	0	0	0	0	0	0
165°	0	0	0	0	0	0	0	0	0	0	0
167.5°	0	0	0	0	0	0	0	0	0	0	0
170°	0	0	0	0	0	0	0	0	0	0	0
172.5°	0	0	0	0	0	0	0	0	0	0	0
175°	0	0	0	0	0	0	0	0	0	0	0
177.5°	0	0	0	0	0	0	0	0	0	0	0
180°	0	0	0	0	0	0	0	0	0	0	0



TEST NUMBER: E395202
 CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	2575	2575
2.5°	2509	2510
5°	2384	2387
7.5°	2250	2254
10°	2109	2115
12.5°	1636	1643
15°	1206	1215
17.5°	845	851
20°	548	552
22.5°	304	306
25°	211	212
27.5°	148	148
30°	105	105
32.5°	70	71
35°	42	42
37.5°	23	23
40°	16	16
42.5°	12	12
45°	6	6
47.5°	4	4
50°	4	4
52.5°	3	3
55°	3	3
57.5°	3	3
60°	3	3
62.5°	2	3
65°	2	2
67.5°	2	2
70°	2	2
72.5°	2	2
75°	1	1
77.5°	1	1
80°	1	1
82.5°	1	1
85°	0	0
87.5°	0	0
90°	0	0
92.5°	0	0
95°	0	0
97.5°	0	0
100°	0	0
102.5°	0	0
105°	0	0
107.5°	0	0
110°	0	0



TEST NUMBER: E395202
CATALOG NUMBER: H7-1410

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0	0
115°	0	0
117.5°	0	0
120°	0	0
122.5°	0	0
125°	0	0
127.5°	0	0
130°	0	0
132.5°	0	0
135°	0	0
137.5°	0	0
140°	0	0
142.5°	0	0
145°	0	0
147.5°	0	0
150°	0	0
152.5°	0	0
155°	0	0
157.5°	0	0
160°	0	0
162.5°	0	0
165°	0	0
167.5°	0	0
170°	0	0
172.5°	0	0
175°	0	0
177.5°	0	0
180°	0	0

(END OF REPORT)