

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P997232

Luminaire Tested: **SMX8RLSFS010-1500LM-3000K**

Issue Date: 3/11/2025

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P997232
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A2410770A001)
Test Lab:
Issue Date: 3/11/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: SMX8RLSFS010-1500LM-3000K
Description: 8IN ROUND, 90CRI, 0-10V DIMMING, DAMP LOCATION
Light Source: SELECTABLE CCT 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1516.9 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.39
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 15.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P997232

CATALOG NUMBER: SMX8RLSFS010-1500LM-3000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997232

CATALOG NUMBER: SMX8RLSFS010-1500LM-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	104	99	96	106	102	98	94	97	94	91	93	91	88	90	88	86	83		
2	99	90	83	78	96	88	82	77	85	79	75	82	77	73	78	75	71	69		
3	90	79	71	64	87	78	70	64	75	68	63	72	66	61	69	64	60	58		
4	82	70	61	54	80	69	60	54	66	59	53	64	57	52	62	56	52	49		
5	75	62	53	47	73	61	53	46	59	52	46	57	51	45	55	49	45	43		
6	70	56	47	41	68	55	47	40	53	46	40	52	45	40	50	44	39	37		
7	65	51	42	36	63	50	42	36	48	41	35	47	40	35	46	40	35	33		
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29		
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26		
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15915	15915	15915	15915
5°	15906	15915	15906	15915
10°	15888	15885	15888	15885
15°	15854	15854	15854	15854
20°	15803	15806	15803	15806
25°	15718	15728	15718	15728
30°	15638	15642	15638	15642
35°	15542	15534	15542	15534
40°	15436	15416	15436	15416
45°	15254	15271	15254	15271
50°	15075	15080	15075	15080
55°	14829	14840	14829	14840
60°	14496	14514	14496	14514
65°	13993	14044	13993	14044
70°	13265	13283	13265	13283
75°	12114	12150	12114	12150
80°	10338	10426	10338	10426
85°	7777	8197	7777	8197



TEST NUMBER: P997232
CATALOG NUMBER: SMX8RLSFS010-1500LM-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.3	3.3
10°-20°	141.5	9.3
20°-30°	215.1	14.2
30°-40°	260.8	17.2
40°-50°	272.7	18.0
50°-60°	249.0	16.4
60°-70°	191.7	12.6
70°-80°	108.8	7.2
80°-90°	28.0	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	406.0	26.8
0°-40°	666.8	44.0
0°-60°	1188.5	78.4
0°-90°	1516.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1516.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	521	521	521	521	521	
5°	519	519	519	519	519	49
15°	502	502	502	502	502	142
25°	467	467	467	467	467	215
35°	417	417	417	417	417	261
45°	353	354	353	354	353	273
55°	279	279	279	279	279	249
65°	194	194	194	194	194	192
75°	103	103	103	103	103	109
85°	22	23	22	23	22	27
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997232

CATALOG NUMBER: SMX8RLSFS010-1500LM-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	521.3	521.3	521.3	521.3	521.3	521.3	521.3	521.3	521.3	521.3	521.3
0.5°	521.3	521.7	521.2	521.3	521.2	521.3	521.2	521.7	521.3	521.7	521.2
1°	521.4	521.4	521.1	521.2	521.3	521.2	521.1	521.4	521.4	521.4	521.1
1.5°	521.4	521.3	521.1	520.9	521.1	520.9	521.1	521.3	521.4	521.3	521.1
2°	521.1	521.3	520.9	520.7	521.0	520.7	520.9	521.3	521.1	521.3	520.9
2.5°	520.8	521.0	520.9	520.6	520.9	520.6	520.9	521.0	520.8	521.0	520.9
3°	520.6	520.4	520.4	520.6	520.6	520.6	520.4	520.4	520.6	520.4	520.4
3.5°	520.2	520.3	520.2	520.2	520.6	520.2	520.2	520.3	520.2	520.3	520.2
4°	519.6	519.9	519.6	520.1	520.2	520.1	519.6	519.9	519.6	519.9	519.6
4.5°	519.4	519.6	519.2	519.4	519.9	519.4	519.2	519.6	519.4	519.6	519.2
5°	519.0	519.1	518.8	519.2	519.3	519.2	518.8	519.1	519.0	519.1	518.8
5.5°	518.9	518.7	518.4	518.6	519.1	518.6	518.4	518.7	518.9	518.7	518.4
6°	518.5	518.1	517.9	518.2	518.4	518.2	517.9	518.1	518.5	518.1	517.9
6.5°	517.6	517.4	517.5	517.5	517.9	517.5	517.5	517.4	517.6	517.4	517.5
7°	516.8	516.9	516.8	517.1	517.2	517.1	516.8	516.9	516.8	516.9	516.8
7.5°	516.3	516.4	516.4	516.4	516.4	516.4	516.4	516.4	516.3	516.4	516.4
8°	515.8	515.6	515.8	515.6	515.5	515.6	515.8	515.6	515.8	515.6	515.8
8.5°	514.8	515.0	514.8	514.7	515.0	514.7	514.8	515.0	514.8	515.0	514.8
9°	514.0	514.2	514.1	514.0	514.2	514.0	514.1	514.2	514.0	514.2	514.1
9.5°	513.1	513.5	513.1	513.2	513.4	513.2	513.1	513.5	513.1	513.5	513.1
10°	512.5	512.4	512.4	512.4	512.4	512.4	512.4	512.4	512.5	512.4	512.4
10.5°	511.3	511.6	511.6	511.3	511.7	511.3	511.6	511.6	511.3	511.6	511.6
11°	510.3	510.6	510.6	510.5	510.7	510.5	510.6	510.6	510.3	510.6	510.6
11.5°	509.2	509.7	509.5	509.4	509.7	509.4	509.5	509.7	509.2	509.7	509.5
12°	508.5	508.4	508.3	508.6	508.6	508.6	508.3	508.4	508.5	508.4	508.3
12.5°	507.4	507.6	507.3	507.6	507.6	507.6	507.3	507.6	507.4	507.6	507.3
13°	506.3	506.4	506.2	506.5	506.4	506.5	506.2	506.4	506.3	506.4	506.2
13.5°	505.2	505.2	505.3	505.4	505.4	505.4	505.3	505.2	505.2	505.2	505.3
14°	504.0	504.2	503.9	504.2	504.0	504.2	503.9	504.2	504.0	504.2	503.9
14.5°	502.9	502.9	502.8	502.8	503.1	502.8	502.8	502.9	502.9	502.9	502.8
15°	501.6	501.4	501.2	501.6	501.6	501.6	501.2	501.4	501.6	501.4	501.2
15.5°	499.9	500.2	499.7	500.3	500.4	500.3	499.7	500.2	499.9	500.2	499.7
16°	498.3	498.5	498.4	498.9	499.0	498.9	498.4	498.5	498.3	498.5	498.4
16.5°	497.2	497.3	497.2	497.3	497.5	497.3	497.2	497.3	497.2	497.3	497.2
17°	495.8	495.6	495.8	495.8	496.1	495.8	495.8	495.6	495.8	495.6	495.8
17.5°	494.3	494.1	494.2	494.2	494.6	494.2	494.2	494.1	494.3	494.1	494.2
18°	492.7	492.5	492.6	492.8	493.0	492.8	492.6	492.5	492.7	492.5	492.6
18.5°	491.1	491.0	491.2	491.1	491.2	491.1	491.2	491.0	491.1	491.0	491.2
19°	489.7	489.4	489.6	489.5	489.5	489.5	489.6	489.4	489.7	489.4	489.6
19.5°	488.0	487.9	488.0	487.8	487.9	487.8	488.0	487.9	488.0	487.9	488.0
20°	486.4	486.1	486.2	486.2	486.5	486.2	486.2	486.1	486.4	486.1	486.2
20.5°	484.6	484.3	484.4	484.5	484.7	484.5	484.4	484.3	484.6	484.3	484.4
21°	482.6	482.3	482.5	483.0	482.8	483.0	482.5	482.3	482.6	482.3	482.5

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997232

CATALOG NUMBER: SMX8RLSFS010-1500LM-3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	476.9	476.9	476.9	476.9	477.1	476.9	476.9	476.9	476.9	476.9	476.9
23°	475.2	474.7	475.1	475.0	475.1	475.0	475.1	474.7	475.2	474.7	475.1
23.5°	473.2	472.9	473.1	473.1	473.0	473.1	473.1	472.9	473.2	472.9	473.1
24°	470.9	470.7	471.1	471.1	471.0	471.1	471.1	470.7	470.9	470.7	471.1
24.5°	468.7	468.8	468.9	469.0	468.9	469.0	468.9	468.8	468.7	468.8	468.9
25°	466.6	466.5	466.8	466.9	466.9	466.9	466.8	466.5	466.6	466.5	466.8
25.5°	464.7	464.5	464.7	464.7	464.6	464.7	464.7	464.5	464.7	464.5	464.7
26°	462.5	462.3	462.6	462.5	462.5	462.5	462.6	462.3	462.5	462.3	462.6
26.5°	460.2	460.1	460.4	460.3	460.4	460.3	460.4	460.1	460.2	460.1	460.4
27°	457.9	457.8	458.1	458.0	458.0	458.0	458.1	457.8	457.9	457.8	458.1
27.5°	455.8	455.5	455.8	455.7	455.6	455.7	455.8	455.5	455.8	455.5	455.8
28°	453.5	452.9	453.5	453.3	453.2	453.3	453.5	452.9	453.5	452.9	453.5
28.5°	451.0	450.6	451.2	450.8	450.8	450.8	451.2	450.6	451.0	450.6	451.2
29°	448.6	448.4	448.6	448.6	448.7	448.6	448.6	448.4	448.6	448.4	448.6
29.5°	446.2	446.0	446.1	446.0	446.1	446.0	446.1	446.0	446.2	446.0	446.1
30°	443.6	443.5	443.7	443.6	443.7	443.6	443.7	443.5	443.6	443.5	443.7
30.5°	441.3	440.9	441.1	441.1	441.2	441.1	441.1	440.9	441.3	440.9	441.1
31°	438.7	438.3	438.6	438.7	438.6	438.7	438.6	438.3	438.7	438.3	438.6
31.5°	436.3	435.6	435.9	436.1	436.0	436.1	435.9	435.6	436.3	435.6	435.9
32°	433.6	433.1	433.4	433.6	433.3	433.6	433.4	433.1	433.6	433.1	433.4
32.5°	430.7	430.6	430.7	430.8	430.8	430.8	430.7	430.6	430.7	430.6	430.7
33°	428.3	427.9	428.1	428.2	428.2	428.2	428.1	427.9	428.3	427.9	428.1
33.5°	425.3	425.2	425.3	425.3	425.3	425.3	425.3	425.2	425.3	425.2	425.3
34°	422.5	422.6	422.7	422.7	422.3	422.7	422.7	422.6	422.5	422.6	422.7
34.5°	419.9	419.7	419.7	419.7	419.6	419.7	419.7	419.7	419.9	419.7	419.7
35°	417.0	416.9	416.9	417.0	416.8	417.0	416.9	416.9	417.0	416.9	416.9
35.5°	414.0	414.1	414.2	414.1	414.0	414.1	414.2	414.1	414.0	414.1	414.2
36°	411.2	411.2	411.4	411.3	411.1	411.3	411.4	411.2	411.2	411.2	411.4
36.5°	408.4	408.3	408.4	408.1	408.2	408.1	408.4	408.3	408.4	408.3	408.4
37°	405.3	405.3	405.4	405.2	405.1	405.2	405.4	405.3	405.3	405.3	405.4
37.5°	402.4	402.3	402.3	402.1	402.3	402.1	402.3	402.3	402.4	402.3	402.3
38°	399.4	399.0	399.3	399.2	399.3	399.2	399.3	399.0	399.4	399.0	399.3
38.5°	396.6	396.0	396.3	396.2	396.3	396.2	396.3	396.0	396.6	396.0	396.3
39°	393.3	393.0	393.3	393.2	393.3	393.2	393.3	393.0	393.3	393.0	393.3
39.5°	390.6	390.0	390.1	389.9	390.1	389.9	390.1	390.0	390.6	390.0	390.1
40°	387.3	386.8	387.1	386.8	386.8	386.8	387.1	386.8	387.3	386.8	387.1
40.5°	383.8	383.6	383.6	383.6	383.4	383.6	383.6	383.6	383.8	383.6	383.6
41°	380.5	380.4	380.4	380.5	380.1	380.5	380.4	380.4	380.5	380.4	380.4
41.5°	377.1	377.1	377.1	377.1	376.9	377.1	377.1	377.1	377.1	377.1	377.1
42°	373.8	373.9	373.9	374.0	373.9	374.0	373.9	373.9	373.8	373.9	373.9
42.5°	370.6	370.4	370.7	370.7	370.8	370.7	370.7	370.4	370.6	370.4	370.7
43°	367.2	367.0	367.1	367.4	367.4	367.4	367.1	367.0	367.2	367.0	367.1
43.5°	363.7	363.6	363.8	364.0	363.9	364.0	363.8	363.6	363.7	363.6	363.8

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997232

CATALOG NUMBER: SMX8RLSFS010-1500LM-3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	353.3	353.4	353.6	353.6	353.7	353.6	353.6	353.4	353.3	353.4	353.6
45.5°	350.2	349.8	350.1	350.0	350.1	350.0	350.1	349.8	350.2	349.8	350.1
46°	346.6	346.3	346.4	346.6	346.6	346.6	346.4	346.3	346.6	346.3	346.4
46.5°	343.0	342.9	342.9	342.9	343.1	342.9	342.9	342.9	343.0	342.9	342.9
47°	339.4	339.4	339.3	339.3	339.5	339.3	339.3	339.4	339.4	339.4	339.3
47.5°	335.8	335.8	335.9	336.0	335.9	336.0	335.9	335.8	335.8	335.8	335.9
48°	332.1	332.2	332.3	332.3	332.1	332.3	332.3	332.2	332.1	332.2	332.3
48.5°	328.4	328.5	328.7	328.7	328.7	328.7	328.7	328.5	328.4	328.5	328.7
49°	324.9	324.8	325.1	325.1	324.9	325.1	325.1	324.8	324.9	324.8	325.1
49.5°	321.2	321.0	321.4	321.3	321.3	321.3	321.4	321.0	321.2	321.0	321.4
50°	317.4	317.3	317.5	317.7	317.5	317.7	317.5	317.3	317.4	317.3	317.5
50.5°	313.6	313.7	313.7	313.9	313.9	313.9	313.7	313.7	313.6	313.7	313.7
51°	310.2	309.9	309.8	310.3	310.0	310.3	309.8	309.9	310.2	309.9	309.8
51.5°	306.4	306.1	306.0	306.3	306.2	306.3	306.0	306.1	306.4	306.1	306.0
52°	302.5	302.2	302.3	302.3	302.4	302.3	302.3	302.2	302.5	302.2	302.3
52.5°	298.6	298.4	298.5	298.4	298.5	298.4	298.5	298.4	298.6	298.4	298.5
53°	294.6	294.5	294.6	294.5	294.6	294.5	294.6	294.5	294.6	294.5	294.6
53.5°	290.6	290.6	290.7	290.6	290.7	290.6	290.7	290.6	290.6	290.6	290.7
54°	286.6	286.5	286.7	286.7	286.6	286.7	286.7	286.5	286.6	286.5	286.7
54.5°	282.6	282.6	282.7	282.7	282.9	282.7	282.7	282.6	282.6	282.6	282.7
55°	278.6	278.6	278.8	278.8	278.8	278.8	278.8	278.6	278.6	278.6	278.8
55.5°	274.5	274.6	274.8	274.7	274.7	274.7	274.8	274.6	274.5	274.6	274.8
56°	270.7	270.7	270.5	270.7	270.5	270.7	270.5	270.7	270.7	270.7	270.5
56.5°	266.8	266.8	266.5	266.8	266.7	266.8	266.5	266.8	266.8	266.8	266.5
57°	262.6	262.6	262.5	262.6	262.5	262.6	262.5	262.6	262.6	262.6	262.5
57.5°	258.3	258.5	258.4	258.5	258.3	258.5	258.4	258.5	258.3	258.5	258.4
58°	254.4	254.3	254.4	254.3	254.2	254.3	254.4	254.3	254.4	254.3	254.4
58.5°	250.2	250.2	250.2	250.2	250.3	250.2	250.2	250.2	250.2	250.2	250.2
59°	245.9	246.0	246.1	246.0	246.0	246.0	246.1	246.0	245.9	246.0	246.1
59.5°	241.8	241.7	241.9	241.9	241.9	241.9	241.9	241.7	241.8	241.7	241.9
60°	237.4	237.5	237.6	237.8	237.7	237.8	237.6	237.5	237.4	237.5	237.6
60.5°	233.3	233.3	233.2	233.5	233.5	233.5	233.2	233.3	233.3	233.3	233.2
61°	229.0	229.0	228.8	229.2	229.1	229.2	228.8	229.0	229.0	229.0	228.8
61.5°	224.8	224.6	224.7	224.9	224.9	224.9	224.7	224.6	224.8	224.6	224.7
62°	220.4	220.3	220.4	220.5	220.5	220.5	220.4	220.3	220.4	220.3	220.4
62.5°	215.9	216.0	216.0	216.0	216.2	216.0	216.0	216.0	215.9	216.0	216.0
63°	211.6	211.6	211.7	211.6	211.8	211.6	211.7	211.6	211.6	211.6	211.7
63.5°	207.1	207.3	207.3	207.2	207.3	207.2	207.3	207.3	207.1	207.3	207.3
64°	202.7	202.7	202.9	202.7	203.0	202.7	202.9	202.7	202.7	202.7	202.9
64.5°	198.2	198.4	198.4	198.3	198.7	198.3	198.4	198.4	198.2	198.4	198.4
65°	193.7	193.9	194.1	194.1	194.4	194.1	194.1	193.9	193.7	193.9	194.1
65.5°	189.4	189.5	189.5	189.5	189.8	189.5	189.5	189.5	189.4	189.5	189.5
66°	184.9	184.9	185.0	185.0	185.1	185.0	185.0	184.9	184.9	184.9	185.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997232

CATALOG NUMBER: SMX8RLSFS010-1500LM-3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	171.4	171.4	171.4	171.5	171.7	171.5	171.4	171.4	171.4	171.4	171.4
68°	166.8	167.0	166.8	167.0	167.2	167.0	166.8	167.0	166.8	167.0	166.8
68.5°	162.4	162.4	162.3	162.5	162.7	162.5	162.3	162.4	162.4	162.4	162.3
69°	157.7	157.8	157.8	158.0	158.0	158.0	157.8	157.8	157.7	157.8	157.8
69.5°	153.1	153.3	153.3	153.1	153.3	153.1	153.3	153.3	153.1	153.3	153.3
70°	148.6	148.6	148.8	148.6	148.8	148.6	148.8	148.6	148.6	148.6	148.8
70.5°	144.1	144.2	144.0	144.2	144.1	144.2	144.0	144.2	144.1	144.2	144.0
71°	139.4	139.7	139.6	139.6	139.5	139.6	139.6	139.7	139.4	139.7	139.6
71.5°	134.8	135.0	134.9	135.0	134.9	135.0	134.9	135.0	134.8	135.0	134.9
72°	130.2	130.3	130.2	130.5	130.3	130.5	130.2	130.3	130.2	130.3	130.2
72.5°	125.6	125.6	125.6	125.7	125.8	125.7	125.6	125.6	125.6	125.6	125.6
73°	121.0	121.0	121.2	121.3	121.2	121.3	121.2	121.0	121.0	121.0	121.2
73.5°	116.3	116.4	116.5	116.7	116.5	116.7	116.5	116.4	116.3	116.4	116.5
74°	111.8	112.0	111.9	112.1	112.1	112.1	111.9	112.0	111.8	112.0	111.9
74.5°	107.2	107.2	107.3	107.5	107.6	107.5	107.3	107.2	107.2	107.2	107.3
75°	102.7	102.7	102.8	103.0	103.0	103.0	102.8	102.7	102.7	102.7	102.8
75.5°	98.2	98.1	98.3	98.4	98.6	98.4	98.3	98.1	98.2	98.1	98.3
76°	93.6	93.7	93.8	93.9	94.0	93.9	93.8	93.7	93.6	93.7	93.8
76.5°	89.0	89.1	89.2	89.5	89.6	89.5	89.2	89.1	89.0	89.1	89.2
77°	84.6	84.7	84.8	85.1	85.3	85.1	84.8	84.7	84.6	84.7	84.8
77.5°	80.1	80.2	80.4	80.7	80.9	80.7	80.4	80.2	80.1	80.2	80.4
78°	75.7	75.8	76.1	76.2	76.6	76.2	76.1	75.8	75.7	75.8	76.1
78.5°	71.4	71.5	71.7	71.8	72.1	71.8	71.7	71.5	71.4	71.5	71.7
79°	67.2	67.3	67.4	67.6	68.0	67.6	67.4	67.3	67.2	67.3	67.4
79.5°	63.0	63.0	63.2	63.4	63.6	63.4	63.2	63.0	63.0	63.0	63.2
80°	58.8	58.9	59.0	59.3	59.3	59.3	59.0	58.9	58.8	58.9	59.0
80.5°	54.8	54.8	55.1	55.3	55.3	55.3	55.1	54.8	54.8	54.8	55.1
81°	50.9	50.9	51.1	51.3	51.2	51.3	51.1	50.9	50.9	50.9	51.1
81.5°	46.9	46.9	47.1	47.3	47.2	47.3	47.1	46.9	46.9	46.9	47.1
82°	43.0	43.0	43.2	43.5	43.5	43.5	43.2	43.0	43.0	43.0	43.2
82.5°	39.2	39.2	39.4	39.9	40.0	39.9	39.4	39.2	39.2	39.2	39.4
83°	35.5	35.6	36.0	36.4	36.5	36.4	36.0	35.6	35.5	35.6	36.0
83.5°	31.7	31.9	32.4	32.8	33.1	32.8	32.4	31.9	31.7	31.9	32.4
84°	28.3	28.6	29.1	29.5	29.8	29.5	29.1	28.6	28.3	28.6	29.1
84.5°	25.2	25.4	25.8	26.3	26.9	26.3	25.8	25.4	25.2	25.4	25.8
85°	22.2	22.4	22.8	23.3	23.4	23.3	22.8	22.4	22.2	22.4	22.8
85.5°	19.4	19.5	19.9	20.4	21.0	20.4	19.9	19.5	19.4	19.5	19.9
86°	16.7	16.9	17.4	17.8	18.3	17.8	17.4	16.9	16.7	16.9	17.4
86.5°	14.2	14.3	14.9	15.5	16.1	15.5	14.9	14.3	14.2	14.3	14.9
87°	11.9	12.1	12.8	13.3	13.9	13.3	12.8	12.1	11.9	12.1	12.8
87.5°	9.7	10.1	10.7	11.2	11.9	11.2	10.7	10.1	9.7	10.1	10.7
88°	7.9	8.4	8.8	9.4	10.0	9.4	8.8	8.4	7.9	8.4	8.8
88.5°	6.4	6.6	7.2	7.7	8.4	7.7	7.2	6.6	6.4	6.6	7.2

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P997232
CATALOG NUMBER: SMX8RLSFS010-1500LM-3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997232

CATALOG NUMBER: SMX8RLSFS010-1500LM-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	521.3	521.3	521.3	521.3	521.3	521.3
0.5°	521.3	521.2	521.3	521.2	521.7	521.3
1°	521.2	521.3	521.2	521.1	521.4	521.4
1.5°	520.9	521.1	520.9	521.1	521.3	521.4
2°	520.7	521.0	520.7	520.9	521.3	521.1
2.5°	520.6	520.9	520.6	520.9	521.0	520.8
3°	520.6	520.6	520.6	520.4	520.4	520.6
3.5°	520.2	520.6	520.2	520.2	520.3	520.2
4°	520.1	520.2	520.1	519.6	519.9	519.6
4.5°	519.4	519.9	519.4	519.2	519.6	519.4
5°	519.2	519.3	519.2	518.8	519.1	519.0
5.5°	518.6	519.1	518.6	518.4	518.7	518.9
6°	518.2	518.4	518.2	517.9	518.1	518.5
6.5°	517.5	517.9	517.5	517.5	517.4	517.6
7°	517.1	517.2	517.1	516.8	516.9	516.8
7.5°	516.4	516.4	516.4	516.4	516.4	516.3
8°	515.6	515.5	515.6	515.8	515.6	515.8
8.5°	514.7	515.0	514.7	514.8	515.0	514.8
9°	514.0	514.2	514.0	514.1	514.2	514.0
9.5°	513.2	513.4	513.2	513.1	513.5	513.1
10°	512.4	512.4	512.4	512.4	512.4	512.5
10.5°	511.3	511.7	511.3	511.6	511.6	511.3
11°	510.5	510.7	510.5	510.6	510.6	510.3
11.5°	509.4	509.7	509.4	509.5	509.7	509.2
12°	508.6	508.6	508.6	508.3	508.4	508.5
12.5°	507.6	507.6	507.6	507.3	507.6	507.4
13°	506.5	506.4	506.5	506.2	506.4	506.3
13.5°	505.4	505.4	505.4	505.3	505.2	505.2
14°	504.2	504.0	504.2	503.9	504.2	504.0
14.5°	502.8	503.1	502.8	502.8	502.9	502.9
15°	501.6	501.6	501.6	501.2	501.4	501.6
15.5°	500.3	500.4	500.3	499.7	500.2	499.9
16°	498.9	499.0	498.9	498.4	498.5	498.3
16.5°	497.3	497.5	497.3	497.2	497.3	497.2
17°	495.8	496.1	495.8	495.8	495.6	495.8
17.5°	494.2	494.6	494.2	494.2	494.1	494.3
18°	492.8	493.0	492.8	492.6	492.5	492.7
18.5°	491.1	491.2	491.1	491.2	491.0	491.1
19°	489.5	489.5	489.5	489.6	489.4	489.7
19.5°	487.8	487.9	487.8	488.0	487.9	488.0
20°	486.2	486.5	486.2	486.2	486.1	486.4
20.5°	484.5	484.7	484.5	484.4	484.3	484.6
21°	483.0	482.8	483.0	482.5	482.3	482.6

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997232

CATALOG NUMBER: SMX8RLSFS010-1500LM-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	476.9	477.1	476.9	476.9	476.9	476.9
23°	475.0	475.1	475.0	475.1	474.7	475.2
23.5°	473.1	473.0	473.1	473.1	472.9	473.2
24°	471.1	471.0	471.1	471.1	470.7	470.9
24.5°	469.0	468.9	469.0	468.9	468.8	468.7
25°	466.9	466.9	466.9	466.8	466.5	466.6
25.5°	464.7	464.6	464.7	464.7	464.5	464.7
26°	462.5	462.5	462.5	462.6	462.3	462.5
26.5°	460.3	460.4	460.3	460.4	460.1	460.2
27°	458.0	458.0	458.0	458.1	457.8	457.9
27.5°	455.7	455.6	455.7	455.8	455.5	455.8
28°	453.3	453.2	453.3	453.5	452.9	453.5
28.5°	450.8	450.8	450.8	451.2	450.6	451.0
29°	448.6	448.7	448.6	448.6	448.4	448.6
29.5°	446.0	446.1	446.0	446.1	446.0	446.2
30°	443.6	443.7	443.6	443.7	443.5	443.6
30.5°	441.1	441.2	441.1	441.1	440.9	441.3
31°	438.7	438.6	438.7	438.6	438.3	438.7
31.5°	436.1	436.0	436.1	435.9	435.6	436.3
32°	433.6	433.3	433.6	433.4	433.1	433.6
32.5°	430.8	430.8	430.8	430.7	430.6	430.7
33°	428.2	428.2	428.2	428.1	427.9	428.3
33.5°	425.3	425.3	425.3	425.3	425.2	425.3
34°	422.7	422.3	422.7	422.7	422.6	422.5
34.5°	419.7	419.6	419.7	419.7	419.7	419.9
35°	417.0	416.8	417.0	416.9	416.9	417.0
35.5°	414.1	414.0	414.1	414.2	414.1	414.0
36°	411.3	411.1	411.3	411.4	411.2	411.2
36.5°	408.1	408.2	408.1	408.4	408.3	408.4
37°	405.2	405.1	405.2	405.4	405.3	405.3
37.5°	402.1	402.3	402.1	402.3	402.3	402.4
38°	399.2	399.3	399.2	399.3	399.0	399.4
38.5°	396.2	396.3	396.2	396.3	396.0	396.6
39°	393.2	393.3	393.2	393.3	393.0	393.3
39.5°	389.9	390.1	389.9	390.1	390.0	390.6
40°	386.8	386.8	386.8	387.1	386.8	387.3
40.5°	383.6	383.4	383.6	383.6	383.6	383.8
41°	380.5	380.1	380.5	380.4	380.4	380.5
41.5°	377.1	376.9	377.1	377.1	377.1	377.1
42°	374.0	373.9	374.0	373.9	373.9	373.8
42.5°	370.7	370.8	370.7	370.7	370.4	370.6
43°	367.4	367.4	367.4	367.1	367.0	367.2
43.5°	364.0	363.9	364.0	363.8	363.6	363.7

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997232

CATALOG NUMBER: SMX8RLSFS010-1500LM-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	353.6	353.7	353.6	353.6	353.4	353.3
45.5°	350.0	350.1	350.0	350.1	349.8	350.2
46°	346.6	346.6	346.6	346.4	346.3	346.6
46.5°	342.9	343.1	342.9	342.9	342.9	343.0
47°	339.3	339.5	339.3	339.3	339.4	339.4
47.5°	336.0	335.9	336.0	335.9	335.8	335.8
48°	332.3	332.1	332.3	332.3	332.2	332.1
48.5°	328.7	328.7	328.7	328.7	328.5	328.4
49°	325.1	324.9	325.1	325.1	324.8	324.9
49.5°	321.3	321.3	321.3	321.4	321.0	321.2
50°	317.7	317.5	317.7	317.5	317.3	317.4
50.5°	313.9	313.9	313.9	313.7	313.7	313.6
51°	310.3	310.0	310.3	309.8	309.9	310.2
51.5°	306.3	306.2	306.3	306.0	306.1	306.4
52°	302.3	302.4	302.3	302.3	302.2	302.5
52.5°	298.4	298.5	298.4	298.5	298.4	298.6
53°	294.5	294.6	294.5	294.6	294.5	294.6
53.5°	290.6	290.7	290.6	290.7	290.6	290.6
54°	286.7	286.6	286.7	286.7	286.5	286.6
54.5°	282.7	282.9	282.7	282.7	282.6	282.6
55°	278.8	278.8	278.8	278.8	278.6	278.6
55.5°	274.7	274.7	274.7	274.8	274.6	274.5
56°	270.7	270.5	270.7	270.5	270.7	270.7
56.5°	266.8	266.7	266.8	266.5	266.8	266.8
57°	262.6	262.5	262.6	262.5	262.6	262.6
57.5°	258.5	258.3	258.5	258.4	258.5	258.3
58°	254.3	254.2	254.3	254.4	254.3	254.4
58.5°	250.2	250.3	250.2	250.2	250.2	250.2
59°	246.0	246.0	246.0	246.1	246.0	245.9
59.5°	241.9	241.9	241.9	241.9	241.7	241.8
60°	237.8	237.7	237.8	237.6	237.5	237.4
60.5°	233.5	233.5	233.5	233.2	233.3	233.3
61°	229.2	229.1	229.2	228.8	229.0	229.0
61.5°	224.9	224.9	224.9	224.7	224.6	224.8
62°	220.5	220.5	220.5	220.4	220.3	220.4
62.5°	216.0	216.2	216.0	216.0	216.0	215.9
63°	211.6	211.8	211.6	211.7	211.6	211.6
63.5°	207.2	207.3	207.2	207.3	207.3	207.1
64°	202.7	203.0	202.7	202.9	202.7	202.7
64.5°	198.3	198.7	198.3	198.4	198.4	198.2
65°	194.1	194.4	194.1	194.1	193.9	193.7
65.5°	189.5	189.8	189.5	189.5	189.5	189.4
66°	185.0	185.1	185.0	185.0	184.9	184.9

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997232

CATALOG NUMBER: SMX8RLSFS010-1500LM-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	171.5	171.7	171.5	171.4	171.4	171.4
68°	167.0	167.2	167.0	166.8	167.0	166.8
68.5°	162.5	162.7	162.5	162.3	162.4	162.4
69°	158.0	158.0	158.0	157.8	157.8	157.7
69.5°	153.1	153.3	153.1	153.3	153.3	153.1
70°	148.6	148.8	148.6	148.8	148.6	148.6
70.5°	144.2	144.1	144.2	144.0	144.2	144.1
71°	139.6	139.5	139.6	139.6	139.7	139.4
71.5°	135.0	134.9	135.0	134.9	135.0	134.8
72°	130.5	130.3	130.5	130.2	130.3	130.2
72.5°	125.7	125.8	125.7	125.6	125.6	125.6
73°	121.3	121.2	121.3	121.2	121.0	121.0
73.5°	116.7	116.5	116.7	116.5	116.4	116.3
74°	112.1	112.1	112.1	111.9	112.0	111.8
74.5°	107.5	107.6	107.5	107.3	107.2	107.2
75°	103.0	103.0	103.0	102.8	102.7	102.7
75.5°	98.4	98.6	98.4	98.3	98.1	98.2
76°	93.9	94.0	93.9	93.8	93.7	93.6
76.5°	89.5	89.6	89.5	89.2	89.1	89.0
77°	85.1	85.3	85.1	84.8	84.7	84.6
77.5°	80.7	80.9	80.7	80.4	80.2	80.1
78°	76.2	76.6	76.2	76.1	75.8	75.7
78.5°	71.8	72.1	71.8	71.7	71.5	71.4
79°	67.6	68.0	67.6	67.4	67.3	67.2
79.5°	63.4	63.6	63.4	63.2	63.0	63.0
80°	59.3	59.3	59.3	59.0	58.9	58.8
80.5°	55.3	55.3	55.3	55.1	54.8	54.8
81°	51.3	51.2	51.3	51.1	50.9	50.9
81.5°	47.3	47.2	47.3	47.1	46.9	46.9
82°	43.5	43.5	43.5	43.2	43.0	43.0
82.5°	39.9	40.0	39.9	39.4	39.2	39.2
83°	36.4	36.5	36.4	36.0	35.6	35.5
83.5°	32.8	33.1	32.8	32.4	31.9	31.7
84°	29.5	29.8	29.5	29.1	28.6	28.3
84.5°	26.3	26.9	26.3	25.8	25.4	25.2
85°	23.3	23.4	23.3	22.8	22.4	22.2
85.5°	20.4	21.0	20.4	19.9	19.5	19.4
86°	17.8	18.3	17.8	17.4	16.9	16.7
86.5°	15.5	16.1	15.5	14.9	14.3	14.2
87°	13.3	13.9	13.3	12.8	12.1	11.9
87.5°	11.2	11.9	11.2	10.7	10.1	9.7
88°	9.4	10.0	9.4	8.8	8.4	7.9
88.5°	7.7	8.4	7.7	7.2	6.6	6.4

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P997232
CATALOG NUMBER: SMX8RLSFS010-1500LM-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270° - · - 135°-315°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





21.5°	480.8	480.6	480.7	480.8	481.0	480.8	480.7	480.6	480.8	480.6	480.7
22°	479.1	478.8	478.8	478.9	478.9	478.9	478.8	478.8	479.1	478.8	478.8



44°	360.3	360.3	360.4	360.7	360.5	360.7	360.4	360.3	360.3	360.3	360.4
44.5°	356.8	356.9	357.1	357.2	357.1	357.2	357.1	356.9	356.8	356.9	357.1

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



66.5°	180.4	180.4	180.4	180.4	180.7	180.4	180.4	180.4	180.4	180.4	180.4	180.4
67°	176.0	175.9	175.9	176.0	176.2	176.0	175.9	175.9	176.0	175.9	175.9	175.9



89°	5.1	5.3	5.8	6.3	6.9	6.3	5.8	5.3	5.1	5.3	5.8
89.5°	3.9	4.1	4.5	5.1	5.7	5.1	4.5	4.1	3.9	4.1	4.5

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



21.5°	480.8	481.0	480.8	480.7	480.6	480.8
22°	478.9	478.9	478.9	478.8	478.8	479.1

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



44°	360.7	360.5	360.7	360.4	360.3	360.3
44.5°	357.2	357.1	357.2	357.1	356.9	356.8

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



66.5°	180.4	180.7	180.4	180.4	180.4	180.4
67°	176.0	176.2	176.0	175.9	175.9	176.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



89°	6.3	6.9	6.3	5.8	5.3	5.1
89.5°	5.1	5.7	5.1	4.5	4.1	3.9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)