

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P997248

Luminaire Tested: **SMX8SLSFS010-1500LM-3500K**

Issue Date: 3/11/2025

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P997248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A2411376A001)
Test Lab:
Issue Date: 3/11/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: SMX8SLSFS010-1500LM-3500K
Description: 8IN SQAURE, 90CRI, 0-10V DIMMING, DAMP LOCATION
Light Source: SELECTABLE CCT 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1535.9 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.39
Luminous Opening: Rectangular (W 0.67' x L: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P997248

CATALOG NUMBER: SMX8SLSFS010-1500LM-3500K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997248

CATALOG NUMBER: SMX8SLSFS010-1500LM-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	104	99	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84		
2	99	90	83	78	96	88	82	77	85	79	75	82	77	73	78	75	71	69		
3	90	79	71	64	87	78	70	64	75	68	63	72	66	61	69	64	60	58		
4	82	70	61	54	80	69	60	54	66	59	53	64	57	52	62	56	52	49		
5	75	62	53	47	73	61	53	46	59	52	46	57	51	45	55	50	45	43		
6	70	56	47	41	68	55	47	40	53	46	40	52	45	40	50	44	39	37		
7	65	51	42	36	63	50	42	36	48	41	35	47	40	35	46	40	35	33		
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29		
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26		
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12646	12646	12646	12646
5°	12630	12651	12620	12637
10°	12622	12639	12608	12615
15°	12598	12613	12574	12588
20°	12567	12572	12526	12552
25°	12514	12522	12472	12483
30°	12451	12473	12407	12412
35°	12373	12394	12329	12332
40°	12286	12311	12230	12223
45°	12164	12201	12113	12089
50°	12012	12079	11960	11926
55°	11818	11902	11785	11710
60°	11543	11668	11524	11419
65°	11138	11314	11138	10984
70°	10551	10776	10565	10341
75°	9635	9932	9663	9348
80°	8189	8603	8244	7829
85°	6025	6768	6245	5475

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997248

CATALOG NUMBER: SMX8SLSFS010-1500LM-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.9	3.2
10°-20°	143.3	9.3
20°-30°	217.9	14.2
30°-40°	264.2	17.2
40°-50°	276.4	18.0
50°-60°	252.4	16.4
60°-70°	194.2	12.6
70°-80°	110.1	7.2
80°-90°	27.6	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	411.1	26.8
0°-40°	675.3	44.0
0°-60°	1204.0	78.4
0°-90°	1535.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1535.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	525	526	524	525	525	50
15°	508	508	506	507	508	143
25°	473	473	471	472	473	218
35°	423	423	421	421	423	264
45°	359	360	357	356	359	277
55°	283	285	282	280	283	252
65°	196	199	196	194	196	194
75°	104	107	104	101	104	110
85°	22	25	23	20	22	27
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997248

CATALOG NUMBER: SMX8SLSFS010-1500LM-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4
0.5°	526.7	527.4	527.5	527.5	527.7	527.1	527.5	527.4	526.6	527.4	527.3
1°	526.7	527.6	527.4	527.6	527.8	527.1	527.6	527.4	526.4	527.5	527.1
1.5°	526.5	527.3	527.3	527.6	527.8	527.0	527.6	527.1	526.4	527.4	527.0
2°	526.3	527.1	527.0	527.6	527.7	526.8	527.4	527.2	526.5	527.2	526.9
2.5°	526.1	526.8	526.8	527.1	527.3	526.8	527.2	526.9	526.2	526.8	526.8
3°	526.1	526.6	526.5	526.8	526.9	526.4	527.0	526.8	526.0	526.6	526.6
3.5°	525.8	526.5	526.5	526.6	526.5	526.3	526.6	526.1	525.5	526.2	526.3
4°	525.8	526.2	526.1	526.3	526.3	526.0	526.3	525.9	525.4	526.0	526.0
4.5°	525.4	525.5	525.7	526.1	525.8	525.7	526.0	525.4	524.8	525.7	525.4
5°	524.7	525.3	525.2	525.8	525.6	525.1	525.4	525.2	524.3	524.9	525.0
5.5°	524.3	524.7	524.7	525.0	525.0	524.7	525.3	524.6	523.9	524.4	524.2
6°	523.7	524.4	524.2	524.8	524.7	524.2	524.7	524.1	523.4	523.9	523.8
6.5°	523.3	523.8	523.7	524.2	524.1	523.7	524.2	523.7	522.8	523.1	523.1
7°	522.7	523.3	523.2	523.9	523.7	523.1	523.4	523.2	522.0	522.7	522.7
7.5°	522.3	522.4	522.5	523.1	523.0	522.6	522.8	522.3	521.4	522.0	521.9
8°	521.2	521.9	521.9	522.4	522.3	521.8	521.8	521.6	520.7	521.2	521.3
8.5°	520.7	521.2	521.2	521.4	521.4	521.3	521.4	520.8	520.0	520.4	520.4
9°	519.7	520.5	520.4	520.8	521.0	520.4	520.4	520.3	519.4	519.4	519.7
9.5°	519.2	519.7	519.7	519.9	519.9	519.5	519.8	519.4	518.6	518.6	518.8
10°	518.4	519.0	519.1	519.2	519.1	518.5	518.6	518.6	517.8	518.1	517.9
10.5°	517.4	518.0	518.1	518.3	518.3	517.8	518.1	517.5	516.9	517.0	517.0
11°	516.3	517.2	517.1	517.5	517.2	516.8	517.3	516.8	515.9	516.0	516.2
11.5°	515.6	516.3	515.9	516.4	516.2	516.1	516.5	515.7	514.8	515.2	515.1
12°	514.6	515.4	515.2	515.2	515.4	514.8	515.2	514.4	513.8	514.2	514.3
12.5°	513.6	514.3	514.1	514.2	514.0	513.8	514.3	513.5	512.8	513.2	513.0
13°	512.3	513.4	512.9	513.3	513.2	512.5	512.8	512.4	511.6	511.7	512.0
13.5°	511.2	512.1	511.7	512.0	511.9	511.5	511.8	511.4	510.4	510.8	510.7
14°	509.8	511.0	510.3	510.9	510.7	510.5	510.4	510.2	509.0	509.4	509.6
14.5°	508.8	509.7	509.3	509.5	509.3	509.0	509.3	508.9	507.8	508.2	508.1
15°	507.5	508.6	508.1	508.3	508.1	507.7	508.0	507.7	506.5	506.9	507.1
15.5°	506.3	507.1	506.8	506.7	506.8	506.4	506.7	506.1	505.2	505.6	505.4
16°	505.0	505.8	505.4	505.4	505.5	505.1	505.2	504.8	504.0	503.8	504.2
16.5°	503.6	504.6	504.1	504.0	503.8	503.5	503.9	503.3	502.4	502.8	502.5
17°	501.9	503.1	502.6	502.5	502.6	502.1	502.4	501.9	500.9	501.1	501.1
17.5°	500.6	501.4	501.2	501.1	500.8	500.7	501.0	500.5	499.2	499.7	499.6
18°	499.1	499.9	499.6	499.6	499.7	499.1	499.3	498.8	497.7	497.9	498.3
18.5°	497.7	498.2	498.2	497.9	497.8	497.4	497.8	497.2	496.1	496.3	496.3
19°	495.8	496.9	496.5	496.3	496.1	495.7	495.9	495.3	494.3	494.5	494.8
19.5°	494.2	495.2	495.0	494.5	494.3	494.2	494.3	493.5	492.7	492.9	493.1
20°	492.5	493.6	493.1	493.0	492.7	492.6	492.5	491.8	490.9	491.0	491.5
20.5°	490.8	491.6	491.5	491.0	491.0	490.9	490.9	490.3	489.1	489.4	489.6
21°	489.0	490.1	489.6	489.4	489.3	489.1	489.1	488.1	487.3	487.7	488.1

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997248

CATALOG NUMBER: SMX8SLSFS010-1500LM-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	483.5	484.0	483.9	483.7	483.6	483.4	483.4	482.4	481.5	482.1	482.2
23°	481.4	482.2	481.9	481.6	481.8	481.4	481.5	480.7	479.5	480.2	480.4
23.5°	479.6	480.3	480.0	479.6	479.9	479.3	479.5	478.7	477.7	478.0	478.0
24°	477.5	478.5	478.0	477.5	477.8	477.3	477.5	476.5	475.9	475.9	476.3
24.5°	475.5	476.4	476.0	475.7	475.6	475.3	475.3	474.6	473.6	473.9	474.2
25°	473.0	474.3	474.0	473.7	473.3	473.1	473.1	472.3	471.4	472.0	472.3
25.5°	471.2	471.9	471.9	471.4	471.2	470.9	471.1	470.2	469.1	469.8	470.0
26°	468.6	469.8	469.7	469.3	469.0	468.7	468.8	467.9	467.0	467.5	468.0
26.5°	466.5	467.5	467.4	466.9	467.0	466.3	466.6	465.8	464.9	465.2	465.5
27°	464.0	465.3	465.3	464.8	464.7	464.1	464.2	463.3	462.7	463.0	463.3
27.5°	462.0	462.9	463.0	462.5	462.4	462.0	462.0	461.3	460.3	460.7	460.7
28°	459.3	460.5	460.7	460.2	460.1	459.6	459.6	458.7	457.8	458.1	458.5
28.5°	457.0	458.0	458.3	457.7	457.8	457.4	457.2	456.6	455.1	455.8	455.9
29°	454.5	455.7	455.8	455.3	455.4	454.7	454.6	454.0	453.0	453.5	453.7
29.5°	452.3	453.2	453.4	452.9	453.0	452.3	452.3	451.5	450.6	451.0	451.2
30°	449.7	450.5	450.8	450.3	450.5	449.6	449.8	449.0	448.1	448.4	448.7
30.5°	447.2	448.1	448.4	447.7	447.9	447.3	447.1	446.3	445.4	445.8	446.0
31°	444.5	445.4	445.6	445.2	445.5	444.7	444.7	443.7	442.9	443.1	443.6
31.5°	441.9	442.6	443.1	442.5	442.5	442.2	442.0	441.1	440.3	440.4	440.8
32°	439.1	439.8	440.1	439.8	439.9	439.6	439.4	438.4	437.8	437.7	438.3
32.5°	436.8	437.3	437.8	437.5	437.3	437.0	436.7	436.0	435.1	435.4	435.7
33°	434.2	434.7	435.1	434.8	434.8	434.3	434.3	433.2	432.4	432.6	433.0
33.5°	431.1	431.9	432.5	432.0	431.8	431.7	431.2	430.5	429.3	429.9	430.1
34°	428.2	429.1	429.7	429.2	429.1	428.8	428.4	427.8	426.8	427.0	427.5
34.5°	425.6	426.4	426.8	426.4	426.1	426.1	425.7	424.9	423.8	424.4	424.7
35°	422.7	423.5	423.8	423.5	423.4	423.2	422.8	421.8	421.2	421.3	421.6
35.5°	420.0	420.7	421.0	420.6	420.6	420.3	419.8	419.0	418.0	418.9	418.8
36°	416.9	417.8	418.1	417.7	417.9	417.3	416.9	416.3	415.4	415.8	415.9
36.5°	414.0	414.6	415.2	414.7	414.9	414.6	413.8	413.3	412.2	412.8	412.7
37°	411.0	411.5	411.9	411.8	411.8	411.4	411.1	410.4	409.3	409.7	409.8
37.5°	408.1	408.5	409.0	408.8	408.7	408.4	408.0	407.1	406.2	406.9	406.4
38°	405.0	405.5	405.9	405.7	405.6	405.1	404.8	404.0	403.3	403.9	403.6
38.5°	401.9	402.5	402.7	402.8	402.6	402.4	401.7	400.9	400.0	401.0	400.4
39°	398.7	399.4	399.5	399.6	399.5	399.2	398.7	397.8	397.0	397.6	397.2
39.5°	395.6	396.3	396.4	396.4	396.5	396.3	395.7	395.0	393.8	394.6	394.3
40°	392.5	393.1	393.3	393.3	393.3	393.1	392.5	391.6	390.7	391.3	391.0
40.5°	389.1	389.9	390.1	390.1	389.9	389.9	389.2	388.3	387.4	388.1	387.6
41°	385.9	386.7	387.0	386.7	386.7	386.6	386.1	385.1	384.2	384.7	384.4
41.5°	382.6	383.2	383.8	383.5	383.7	383.3	382.7	381.7	380.9	381.2	381.0
42°	379.3	379.9	380.2	380.3	380.4	379.8	379.5	378.3	377.6	377.7	377.8
42.5°	375.9	376.7	377.1	377.0	377.0	376.4	376.0	375.0	374.4	374.6	374.5
43°	372.5	373.4	373.6	373.6	373.7	373.1	372.6	371.7	371.0	371.3	371.1
43.5°	369.1	369.9	370.1	370.1	370.2	369.6	369.2	368.3	367.5	368.0	367.5

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997248

CATALOG NUMBER: SMX8SLSFS010-1500LM-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	358.7	359.6	359.8	360.0	359.8	359.4	358.8	357.9	357.2	357.5	357.2
45.5°	355.2	356.0	356.3	356.4	356.3	355.9	355.4	354.6	353.8	354.2	353.7
46°	351.6	352.5	353.0	353.1	352.9	352.6	352.1	351.1	350.3	350.6	350.2
46.5°	348.2	348.7	349.3	349.5	349.4	349.3	348.6	347.7	346.6	347.0	346.7
47°	344.4	345.2	345.7	345.9	345.8	345.4	345.0	344.1	343.0	343.4	343.1
47.5°	340.9	341.5	341.9	342.2	342.1	341.9	341.0	340.3	339.3	339.8	339.4
48°	337.0	338.0	338.3	338.5	338.7	338.0	337.5	336.6	335.7	335.9	335.7
48.5°	333.4	334.1	334.7	334.8	335.1	334.5	333.9	333.1	332.1	332.3	331.9
49°	329.4	330.4	330.9	331.1	331.2	330.8	330.4	329.2	328.2	328.6	328.2
49.5°	325.7	326.6	327.1	327.4	327.5	327.0	326.6	325.5	324.4	324.9	324.3
50°	322.0	322.8	323.4	323.7	323.8	323.1	322.8	321.3	320.6	321.0	320.6
50.5°	318.1	318.9	319.5	319.6	319.9	319.4	318.7	317.4	316.8	317.1	316.8
51°	314.4	315.1	315.7	315.8	316.1	315.5	315.0	313.7	313.1	313.3	312.9
51.5°	310.4	311.5	311.9	312.0	312.5	311.9	311.2	310.2	309.4	309.6	309.3
52°	306.7	307.6	308.2	308.3	308.7	308.0	307.6	306.5	305.6	305.7	305.2
52.5°	302.7	303.6	304.1	304.3	304.6	304.3	303.6	302.5	301.8	301.8	301.2
53°	298.8	299.6	300.3	300.5	300.9	300.2	299.9	298.5	297.7	297.8	297.3
53.5°	294.8	295.6	296.2	296.4	297.0	296.4	295.6	294.7	293.7	293.9	293.3
54°	290.9	291.7	292.1	292.4	292.7	292.4	291.8	290.6	289.7	289.7	289.2
54.5°	286.6	287.6	288.2	288.1	288.8	288.3	287.7	286.6	285.7	285.8	285.1
55°	282.7	283.5	284.2	284.3	284.7	284.4	283.8	282.8	281.9	281.7	281.2
55.5°	278.4	279.4	280.2	280.2	280.8	280.3	279.7	278.6	277.7	277.6	277.1
56°	274.5	275.3	275.9	276.2	276.7	276.3	275.5	274.5	273.5	273.6	273.1
56.5°	270.5	271.5	271.9	272.2	272.6	272.4	271.6	270.5	269.6	269.5	269.1
57°	266.4	267.3	267.8	268.1	268.6	268.2	267.5	266.3	265.5	265.3	264.9
57.5°	261.7	263.1	263.6	263.8	264.4	264.1	263.4	262.1	261.4	261.1	260.7
58°	257.9	258.8	259.4	259.5	260.2	259.7	259.2	258.0	257.2	256.9	256.5
58.5°	253.7	254.6	255.2	255.2	256.2	255.7	254.9	253.8	252.8	252.8	252.3
59°	249.2	250.3	250.9	251.1	251.8	251.2	250.7	249.6	248.6	248.4	247.8
59.5°	244.8	246.0	246.6	246.6	247.6	247.1	246.5	245.5	244.4	244.3	243.5
60°	240.7	241.7	242.3	242.3	243.3	242.7	242.2	241.3	240.3	239.9	239.3
60.5°	236.3	237.3	237.9	237.9	239.1	238.6	237.9	236.9	236.1	235.6	234.9
61°	232.0	233.1	233.4	233.7	234.8	234.2	233.6	232.7	231.6	231.2	230.6
61.5°	227.7	228.8	229.3	229.3	230.5	229.8	229.2	228.4	227.2	226.8	226.3
62°	223.2	224.4	224.8	225.0	226.0	225.5	225.0	223.9	223.0	222.5	221.9
62.5°	218.9	219.9	220.5	220.3	221.8	221.2	220.5	219.6	218.5	218.2	217.4
63°	214.3	215.5	215.9	216.0	217.2	216.7	216.2	215.3	214.2	213.8	213.0
63.5°	210.0	210.9	211.4	211.5	212.8	212.2	211.6	210.8	209.8	209.3	208.5
64°	205.1	206.5	206.9	207.0	208.4	207.8	207.3	206.5	205.2	204.8	204.1
64.5°	200.7	202.0	202.4	202.4	203.9	203.3	202.7	202.1	200.6	200.1	199.6
65°	196.3	197.4	197.8	198.1	199.4	199.0	198.5	197.5	196.3	195.8	195.2
65.5°	192.0	192.9	193.3	193.4	194.9	194.5	193.9	193.1	191.8	191.3	190.7
66°	187.3	188.5	189.0	189.1	190.4	189.9	189.5	188.5	187.5	186.9	186.2

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997248

CATALOG NUMBER: SMX8SLSFS010-1500LM-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	173.4	174.8	175.4	175.4	177.0	176.5	175.9	175.0	173.8	173.1	172.4
68°	168.7	170.1	170.5	170.8	172.3	171.6	171.4	170.2	169.2	168.4	167.9
68.5°	164.5	165.5	165.9	166.2	167.5	167.0	166.7	165.5	164.5	163.8	163.3
69°	159.7	160.8	161.2	161.7	163.0	162.6	162.2	160.9	159.8	159.2	158.7
69.5°	154.9	156.1	156.7	157.0	158.5	158.0	157.6	156.3	155.2	154.4	153.9
70°	150.5	151.5	151.9	152.6	153.7	153.2	152.9	151.5	150.7	149.8	149.2
70.5°	145.8	147.1	147.6	147.9	149.2	148.7	148.3	147.0	146.0	145.3	144.6
71°	141.1	142.4	142.8	143.4	144.4	144.1	143.8	142.4	141.5	140.7	139.9
71.5°	136.4	137.7	138.2	138.7	139.9	139.5	138.9	137.5	136.7	136.0	135.3
72°	131.9	132.9	133.5	134.1	135.1	134.8	134.3	133.0	131.9	131.2	130.6
72.5°	127.0	128.3	128.9	129.5	130.5	129.9	129.4	128.4	127.3	126.6	125.8
73°	122.3	123.7	124.2	124.6	125.7	125.4	124.8	123.6	122.7	121.8	121.2
73.5°	117.5	119.0	119.5	119.9	121.0	120.6	120.1	119.0	117.8	117.1	116.4
74°	112.9	114.3	114.8	115.3	116.2	116.2	115.7	114.3	113.4	112.4	111.7
74.5°	108.5	109.8	110.3	110.5	111.6	111.5	111.0	109.5	108.7	107.9	107.5
75°	104.0	105.3	105.8	105.9	107.2	106.8	106.4	105.2	104.3	103.3	102.9
75.5°	99.3	100.7	101.1	101.2	102.7	102.2	101.9	100.7	99.5	98.8	98.3
76°	94.6	95.9	96.3	96.5	97.9	97.7	97.3	96.1	95.2	94.2	93.8
76.5°	90.0	91.3	91.9	91.9	93.5	93.1	92.8	91.5	90.3	89.5	89.1
77°	85.5	86.8	87.3	87.3	88.8	88.5	88.3	87.0	85.8	85.0	84.5
77.5°	80.9	82.3	82.8	82.7	84.4	83.9	83.8	82.4	81.3	80.5	80.2
78°	76.5	77.9	78.2	78.3	79.8	79.5	79.3	77.8	76.7	76.0	75.6
78.5°	72.1	73.4	73.8	73.9	75.3	74.9	74.6	73.4	72.4	71.7	71.3
79°	67.9	69.0	69.4	69.5	70.8	70.7	70.5	69.0	68.2	67.4	67.3
79.5°	63.6	64.7	65.2	65.3	66.5	66.4	66.1	64.8	63.9	63.0	62.8
80°	59.3	60.4	60.9	61.0	62.3	62.2	61.8	60.6	59.7	58.9	58.5
80.5°	55.0	56.2	56.7	56.8	58.2	58.0	57.6	56.4	55.7	54.9	54.6
81°	51.2	52.0	52.6	52.7	54.2	54.1	53.7	52.5	51.7	51.0	50.7
81.5°	47.2	48.0	48.6	48.7	50.3	50.0	49.6	48.5	47.7	46.9	46.6
82°	43.0	44.0	44.5	44.6	46.2	46.1	45.6	44.5	43.8	43.0	42.7
82.5°	38.9	40.0	40.5	40.7	42.2	42.2	41.8	40.8	40.1	39.4	39.0
83°	35.2	36.0	36.4	36.7	38.5	38.4	38.0	36.9	36.3	35.5	35.3
83.5°	31.5	32.3	32.6	32.8	34.7	34.6	34.2	33.3	32.6	32.0	31.7
84°	28.1	28.8	29.2	29.2	31.0	31.0	30.6	29.7	29.0	28.5	28.2
84.5°	24.9	25.7	26.0	26.0	27.6	27.6	27.3	26.5	25.9	25.4	25.2
85°	21.9	22.6	22.8	22.9	24.6	24.5	24.2	23.4	22.7	22.1	22.1
85.5°	18.9	19.6	19.8	19.9	21.4	21.4	21.1	20.3	19.6	19.3	19.1
86°	16.2	16.9	17.0	17.0	18.4	18.5	18.1	17.4	16.8	16.4	16.3
86.5°	13.7	14.5	14.5	14.4	15.6	15.6	15.4	14.7	14.1	13.8	13.8
87°	11.5	12.1	12.2	12.1	13.0	13.1	12.9	12.2	11.7	11.5	11.5
87.5°	9.5	10.1	10.2	10.0	10.8	10.8	10.7	10.0	9.6	9.4	9.4
88°	7.9	8.3	8.3	8.1	8.6	8.7	8.5	8.1	7.6	7.6	7.6
88.5°	6.6	6.8	6.8	6.6	6.7	6.9	6.8	6.2	5.8	5.9	6.1

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P997248
CATALOG NUMBER: SMX8SLSFS010-1500LM-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997248

CATALOG NUMBER: SMX8SLSFS010-1500LM-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	527.4	527.4	527.4	527.4	527.4	527.4
0.5°	527.6	527.5	527.1	527.8	527.4	526.7
1°	527.6	527.5	526.8	527.3	527.7	526.7
1.5°	527.1	527.4	526.9	527.4	527.3	526.5
2°	527.2	527.1	526.8	527.1	527.2	526.3
2.5°	526.7	526.9	526.8	527.0	526.7	526.1
3°	526.7	526.5	526.4	526.5	526.8	526.1
3.5°	526.1	526.1	526.2	526.5	526.4	525.8
4°	526.0	525.8	525.5	525.8	526.2	525.8
4.5°	525.4	525.4	525.2	525.5	525.5	525.4
5°	525.1	525.0	524.8	524.9	525.2	524.7
5.5°	524.4	524.3	524.3	524.6	524.6	524.3
6°	524.0	524.0	523.6	523.7	524.2	523.7
6.5°	523.3	523.4	523.1	523.3	523.5	523.3
7°	522.8	522.6	522.4	522.8	523.1	522.7
7.5°	522.0	521.9	521.7	522.0	522.3	522.3
8°	521.6	521.1	520.9	521.1	521.8	521.2
8.5°	520.8	520.5	520.4	520.9	520.8	520.7
9°	520.0	519.9	519.5	520.0	520.3	519.7
9.5°	519.1	519.0	518.8	519.3	519.4	519.2
10°	518.4	518.1	517.7	518.4	518.7	518.4
10.5°	517.3	517.3	516.8	517.5	517.8	517.4
11°	516.5	516.3	516.1	516.6	517.0	516.3
11.5°	515.2	515.3	515.2	515.6	515.8	515.6
12°	514.2	514.1	513.9	514.6	514.8	514.6
12.5°	513.0	513.2	513.1	513.6	513.7	513.6
13°	512.1	512.3	511.6	512.4	512.7	512.3
13.5°	510.6	511.0	510.6	511.1	511.4	511.2
14°	509.6	509.7	509.1	509.8	510.3	509.8
14.5°	508.4	508.4	508.0	508.7	508.9	508.8
15°	507.0	507.1	506.5	507.6	507.9	507.5
15.5°	505.6	505.9	505.4	506.3	506.5	506.3
16°	504.2	504.4	504.2	504.8	505.2	505.0
16.5°	502.6	503.3	502.8	503.4	503.6	503.6
17°	501.2	501.9	501.0	501.9	502.2	501.9
17.5°	499.6	500.2	499.5	500.2	500.6	500.6
18°	498.2	498.6	497.9	499.0	499.3	499.1
18.5°	496.6	496.8	496.4	497.3	497.5	497.7
19°	495.1	495.2	494.7	495.7	496.0	495.8
19.5°	493.5	493.3	493.2	494.1	494.2	494.2
20°	491.8	491.9	491.3	492.6	492.8	492.5
20.5°	489.9	490.2	489.9	490.3	490.7	490.8
21°	488.0	488.1	487.6	488.7	489.1	489.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997248

CATALOG NUMBER: SMX8SLSFS010-1500LM-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	482.1	482.6	482.2	483.3	483.1	483.5
23°	480.3	480.5	480.2	481.4	481.3	481.4
23.5°	478.2	478.3	478.5	479.4	479.1	479.6
24°	476.2	476.1	476.3	477.6	477.4	477.5
24.5°	474.1	474.1	474.2	475.6	475.1	475.5
25°	471.9	471.8	472.0	473.7	473.5	473.0
25.5°	469.8	469.7	469.9	471.6	471.0	471.2
26°	467.6	467.7	467.7	469.1	468.8	468.6
26.5°	465.3	465.3	465.3	466.7	466.2	466.5
27°	463.0	462.8	462.8	464.4	464.1	464.0
27.5°	460.5	460.5	460.5	462.0	461.6	462.0
28°	458.3	458.3	458.1	459.7	459.5	459.3
28.5°	455.6	455.7	455.7	457.1	456.8	457.0
29°	453.3	453.0	453.3	454.9	454.6	454.5
29.5°	450.7	450.6	451.1	452.4	451.9	452.3
30°	448.3	448.3	448.6	449.9	449.4	449.7
30.5°	445.7	445.6	445.9	447.2	446.8	447.2
31°	443.3	442.8	443.3	444.7	444.5	444.5
31.5°	440.5	440.2	440.6	442.0	441.7	441.9
32°	437.9	437.8	438.0	439.2	439.0	439.1
32.5°	435.2	435.3	435.7	436.7	436.3	436.8
33°	432.6	432.6	432.8	433.9	433.6	434.2
33.5°	429.9	429.7	430.1	431.3	431.1	431.1
34°	427.1	426.9	427.4	428.4	428.3	428.2
34.5°	424.1	424.1	424.5	425.3	425.5	425.6
35°	421.3	421.3	421.7	422.5	422.6	422.7
35.5°	418.3	418.1	418.8	419.6	419.8	420.0
36°	415.5	415.1	415.9	416.8	417.0	416.9
36.5°	412.4	412.4	412.6	413.7	413.8	414.0
37°	409.3	409.4	409.7	410.8	410.8	411.0
37.5°	406.1	406.4	406.8	407.4	407.8	408.1
38°	403.0	403.3	403.6	404.2	404.8	405.0
38.5°	399.8	399.9	400.4	401.1	401.6	401.9
39°	396.7	396.9	397.3	398.0	398.6	398.7
39.5°	393.8	393.7	394.3	395.0	395.5	395.6
40°	390.5	390.5	391.1	391.9	392.3	392.5
40.5°	387.2	387.2	387.7	388.6	389.0	389.1
41°	383.9	384.0	384.3	385.1	385.8	385.9
41.5°	380.6	380.6	381.0	381.8	382.3	382.6
42°	377.1	377.3	377.7	378.6	379.0	379.3
42.5°	373.8	373.9	374.5	375.1	375.8	375.9
43°	370.4	370.7	371.1	371.7	372.4	372.5
43.5°	366.8	367.0	367.8	368.2	369.0	369.1

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997248

CATALOG NUMBER: SMX8SLSFS010-1500LM-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	356.6	356.5	357.0	357.9	358.8	358.7
45.5°	353.3	353.1	353.7	354.3	355.4	355.2
46°	349.7	349.7	350.0	351.0	351.8	351.6
46.5°	346.1	346.2	346.5	347.4	348.0	348.2
47°	342.5	342.3	342.7	343.8	344.5	344.4
47.5°	338.8	338.6	339.1	340.0	340.8	340.9
48°	335.2	335.1	335.4	336.3	337.1	337.0
48.5°	331.5	331.4	331.6	332.6	333.4	333.4
49°	327.7	327.4	327.7	329.0	329.6	329.4
49.5°	324.0	323.6	324.2	324.9	325.8	325.7
50°	320.1	319.7	320.2	321.3	321.8	322.0
50.5°	316.3	315.9	316.4	317.4	318.2	318.1
51°	312.6	312.3	312.7	313.5	314.5	314.4
51.5°	308.9	308.4	308.9	309.8	310.8	310.4
52°	304.9	304.5	304.8	305.7	306.6	306.7
52.5°	301.0	300.5	300.9	301.7	302.9	302.7
53°	297.1	296.5	297.0	297.7	298.7	298.8
53.5°	293.2	292.6	293.0	293.8	294.8	294.8
54°	289.0	288.3	288.7	289.7	290.5	290.9
54.5°	284.9	284.3	284.8	285.6	286.6	286.6
55°	280.9	280.1	280.6	281.6	282.4	282.7
55.5°	276.8	276.1	276.6	277.3	278.3	278.4
56°	272.6	272.1	272.4	273.4	274.2	274.5
56.5°	268.7	268.0	268.6	269.3	270.1	270.5
57°	264.5	263.7	264.3	265.2	265.9	266.4
57.5°	260.3	259.7	260.1	260.6	261.8	261.7
58°	256.1	255.3	255.6	256.5	257.2	257.9
58.5°	252.0	251.2	251.7	252.2	253.2	253.7
59°	247.7	246.9	247.0	248.0	248.8	249.2
59.5°	243.3	242.6	242.8	243.5	244.5	244.8
60°	239.0	238.1	238.5	239.4	240.0	240.7
60.5°	234.7	233.7	234.1	234.8	235.8	236.3
61°	230.4	229.3	229.8	230.6	231.6	232.0
61.5°	226.0	224.9	225.7	226.1	227.3	227.7
62°	221.5	220.6	221.0	221.8	222.9	223.2
62.5°	217.0	216.2	216.5	217.2	218.3	218.9
63°	212.6	211.7	212.1	212.7	213.7	214.3
63.5°	208.1	207.2	207.6	208.2	209.3	210.0
64°	203.6	202.6	203.2	203.8	204.8	205.1
64.5°	199.1	198.2	198.5	199.1	200.4	200.7
65°	194.8	193.6	193.9	194.7	195.7	196.3
65.5°	190.3	188.9	189.7	190.2	191.3	192.0
66°	185.9	184.5	185.1	185.6	186.7	187.3

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997248

CATALOG NUMBER: SMX8SLSFS010-1500LM-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	172.0	170.8	171.2	172.0	173.1	173.4
68°	167.4	166.1	166.6	167.3	168.5	168.7
68.5°	162.9	161.6	161.9	162.4	163.9	164.5
69°	158.3	156.8	157.2	157.9	159.1	159.7
69.5°	153.5	152.2	152.5	153.1	154.4	154.9
70°	149.0	147.5	148.0	148.6	149.9	150.5
70.5°	144.2	142.9	143.3	144.0	145.2	145.8
71°	139.5	138.2	138.7	139.4	140.5	141.1
71.5°	134.8	133.5	133.9	134.7	136.0	136.4
72°	130.1	128.8	129.1	130.0	131.2	131.9
72.5°	125.4	124.1	124.6	125.3	126.5	127.0
73°	120.7	119.3	119.9	120.5	121.7	122.3
73.5°	116.2	114.8	115.0	115.9	117.3	117.5
74°	111.5	110.2	110.7	111.2	112.5	112.9
74.5°	107.0	105.6	106.1	106.8	108.1	108.5
75°	102.5	100.9	101.4	102.2	103.4	104.0
75.5°	97.8	96.5	96.8	97.4	98.6	99.3
76°	93.2	91.9	92.3	93.0	94.0	94.6
76.5°	88.5	87.2	87.6	88.3	89.4	90.0
77°	84.0	82.7	83.2	83.9	84.8	85.5
77.5°	79.5	78.1	78.6	79.3	80.4	80.9
78°	75.0	73.8	74.2	75.0	75.8	76.5
78.5°	70.8	69.4	69.8	70.5	71.5	72.1
79°	66.6	65.2	65.6	66.3	67.2	67.9
79.5°	62.2	60.7	61.2	62.0	63.0	63.6
80°	58.2	56.7	56.9	57.8	58.7	59.3
80.5°	54.3	52.6	52.8	53.7	54.6	55.0
81°	50.2	48.5	48.9	49.7	50.4	51.2
81.5°	46.1	44.6	44.9	45.7	46.4	47.2
82°	42.3	40.5	41.0	41.7	42.4	43.0
82.5°	38.5	36.6	37.0	37.7	38.4	38.9
83°	34.9	32.7	33.1	33.7	34.6	35.2
83.5°	31.4	29.1	29.7	30.1	30.9	31.5
84°	27.8	26.1	26.5	27.0	27.7	28.1
84.5°	24.9	23.0	23.3	23.9	24.5	24.9
85°	21.7	19.9	20.3	20.9	21.5	21.9
85.5°	18.8	17.2	17.6	18.1	18.6	18.9
86°	16.1	14.7	15.1	15.6	16.0	16.2
86.5°	13.6	12.4	12.8	13.3	13.6	13.7
87°	11.3	10.3	10.7	11.2	11.5	11.5
87.5°	9.5	8.5	9.1	9.5	9.6	9.5
88°	7.5	7.0	7.5	7.9	7.9	7.9
88.5°	6.0	5.7	6.4	6.6	6.5	6.6

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P997248
CATALOG NUMBER: SMX8SLSFS010-1500LM-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270° - · - 135°-315°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





21.5°	487.3	488.1	487.6	487.5	487.4	487.2	487.3	486.4	485.4	485.9	486.0
22°	485.2	486.0	485.9	485.7	485.8	485.2	485.2	484.4	483.4	484.0	484.3



44°	365.5	366.5	366.6	366.7	366.9	366.1	365.8	364.8	364.1	364.7	364.1
44.5°	362.2	363.0	363.3	363.3	363.2	362.8	362.1	361.6	360.5	361.3	360.6



66.5°	182.7	183.9	184.5	184.5	186.0	185.4	185.0	184.1	182.8	182.3	181.6
67°	178.1	179.3	179.8	180.1	181.4	180.9	180.6	179.4	178.3	177.8	177.1



89°	5.2	5.5	5.4	5.1	5.2	5.3	5.2	4.7	4.5	4.5	4.7
89.5°	4.0	4.3	4.3	4.0	3.8	3.9	3.8	3.5	3.2	3.4	3.6

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



21.5°	486.1	486.3	485.9	487.0	487.2	487.3
22°	484.4	484.6	483.9	485.2	485.4	485.2

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



44°	363.5	363.4	364.1	364.9	365.6	365.5
44.5°	360.0	360.0	360.6	361.2	362.2	362.2

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



66.5°	181.3	180.0	180.6	181.2	182.3	182.7
67°	176.9	175.5	175.8	176.5	177.5	178.1

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



89°	4.7	4.5	5.1	5.4	5.3	5.2
89.5°	3.5	3.7	4.2	4.4	4.3	4.0

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)