

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P1046634

Luminaire Tested: FMNL1515FS5--935

Issue Date: 07/03/2025

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
Report Number: P1046634
Test Lab: Cooper lighting solutions
Issue Date: 07/03/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: FMNL1515FS5--935
Description: HALO 15 inch 90 CRI COLOR SELECTABLE flush mount White Trim FIXTURE with night light
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1560.4 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.41
Luminous Opening: Circular (Dia: 1.2' x H: 0')
CIE Type: Direct

Input Watts (W): 16.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P1046634
CATALOG NUMBER: FMNL1515FS5--935

Luminous Intensity Polar Plot



TEST NUMBER: P1046634

CATALOG NUMBER: FMNL1515FS5--935

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	118	118	118	118	115	115	115	115	109	109	109	103	103	103	98	98	98	96		
1	106	101	96	92	103	98	94	90	93	90	86	89	86	83	84	82	80	77		
2	96	87	80	74	93	85	78	73	81	75	70	77	72	68	73	69	66	63		
3	87	76	68	61	84	74	66	60	71	64	58	67	62	57	64	59	55	53		
4	80	67	58	51	77	66	57	50	63	55	49	60	53	48	57	52	47	45		
5	73	60	51	44	71	59	50	43	56	48	42	53	47	42	51	45	41	38		
6	68	54	45	38	65	53	44	38	50	43	37	48	41	36	46	40	36	33		
7	63	49	40	33	61	48	39	33	46	38	33	44	37	32	42	36	31	29		
8	58	44	36	30	56	43	35	29	42	34	29	40	33	29	39	33	28	26		
9	54	41	32	27	53	40	32	26	38	31	26	37	30	26	36	30	25	23		
10	51	37	29	24	49	37	29	24	35	28	24	34	28	23	33	27	23	21		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4467
5°	4464
10°	4460
15°	4462
20°	4459
25°	4462
30°	4468
35°	4467
40°	4465
45°	4462
50°	4466
55°	4460
60°	4439
65°	4427
70°	4397
75°	4464
80°	4752
85°	6421

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 87.5°

Luminance: 10517 cd/sqm

TEST NUMBER: P1046634
CATALOG NUMBER: FMNL1515FS5--935

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.4	2.8
10°-20°	127.9	8.2
20°-30°	196.1	12.6
30°-40°	240.7	15.4
40°-50°	255.9	16.4
50°-60°	239.8	15.4
60°-70°	194.2	12.4
70°-80°	128.4	8.2
80°-90°	65.9	4.2
90°-100°	29.3	1.9
100°-110°	16.1	1.0
110°-120°	10.5	0.7
120°-130°	6.1	0.4
130°-140°	3.2	0.2
140°-150°	1.4	0.1
150°-160°	0.5	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	368.4	23.6
0°-40°	609.1	39.0
0°-60°	1104.8	70.8
0°-90°	1493.3	95.7
90°-120°	55.9	3.6
90°-150°	66.6	4.3
90°-180°	67.0	4.3
0°-180°	1560.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	469	
5°	467	44
15°	453	128
25°	425	196
35°	384	241
45°	332	256
55°	269	240
65°	197	194
75°	121	128
85°	59	54
90°	38	22
95°	26	20
105°	15	16
115°	11	11
125°	7	6
135°	4	3
145°	2	1
155°	1	0
165°	0	0
175°	0	0
180°	0	0

TEST NUMBER: P1046634
CATALOG NUMBER: FMNL1515FS5--935

CANDELA DISTRIBUTION (FULL):

0°	
0°	469.3
2.5°	468.3
5°	467.3
7.5°	465.4
10°	461.5
12.5°	457.7
15°	452.9
17.5°	447.1
20°	440.3
22.5°	433.6
25°	424.9
27.5°	416.3
30°	406.6
32.5°	396.0
35°	384.5
37.5°	372.9
40°	359.4
42.5°	345.9
45°	331.5
47.5°	317.0
50°	301.6
52.5°	285.2
55°	268.8
57.5°	250.5
60°	233.2
62.5°	214.9
65°	196.6
67.5°	177.3
70°	158.0
72.5°	139.7
75°	121.4
77.5°	103.1
80°	86.7
82.5°	72.3
85°	58.8
87.5°	48.2
90°	38.5
92.5°	31.8
95°	26.0
97.5°	21.2
100°	18.3
102.5°	16.4
105°	15.4
107.5°	13.5
110°	12.5

TEST NUMBER: P1046634
CATALOG NUMBER: FMNL1515FS5--935

CANDELA DISTRIBUTION (continued):

	0°
112.5°	11.6
115°	10.6
117.5°	9.6
120°	8.7
122.5°	7.7
125°	6.7
127.5°	5.8
130°	4.8
132.5°	4.8
135°	3.9
137.5°	3.9
140°	2.9
142.5°	2.9
145°	1.9
147.5°	1.9
150°	1.0
152.5°	1.0
155°	1.0
157.5°	1.0
160°	1.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

TEST NUMBER: P1046634
CATALOG NUMBER: FMNL1515FS5--935

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.0	18.6	17.5	19.0	19.5	17.0	18.6	17.5	19.0	19.5
	3H	19.1	20.5	19.5	21.0	21.4	19.1	20.5	19.5	21.0	21.4
	4H	20.0	21.3	20.4	21.8	22.3	20.0	21.3	20.4	21.8	22.3
	6H	20.7	22.0	21.2	22.5	23.0	20.7	22.0	21.2	22.5	23.0
	8H	21.1	22.3	21.6	22.8	23.3	21.1	22.3	21.6	22.8	23.3
	12H	21.5	22.6	22.0	23.1	23.6	21.5	22.6	22.0	23.1	23.6
4H	2H	17.7	19.1	18.2	19.5	20.0	17.7	19.1	18.2	19.5	20.0
	3H	20.0	21.2	20.5	21.7	22.2	20.0	21.2	20.5	21.7	22.2
	4H	21.1	22.1	21.6	22.6	23.1	21.1	22.1	21.6	22.6	23.1
	6H	22.0	22.9	22.5	23.5	24.0	22.0	22.9	22.5	23.5	24.0
	8H	22.4	23.3	23.0	23.8	24.4	22.4	23.3	23.0	23.8	24.4
	12H	22.9	23.7	23.5	24.3	24.8	22.9	23.7	23.5	24.3	24.8
8H	4H	21.5	22.4	22.0	22.9	23.4	21.5	22.4	22.0	22.9	23.4
	6H	22.6	23.3	23.2	23.9	24.5	22.6	23.3	23.2	23.9	24.5
	8H	23.2	23.8	23.8	24.4	25.0	23.2	23.8	23.8	24.4	25.0
	12H	23.8	24.4	24.4	25.0	25.6	23.8	24.4	24.4	25.0	25.6
12H	4H	21.5	22.3	22.1	22.9	23.5	21.5	22.3	22.1	22.9	23.5
	6H	22.7	23.4	23.3	24.0	24.6	22.7	23.4	23.3	24.0	24.6
	8H	23.4	24.0	24.0	24.6	25.2	23.4	24.0	24.0	24.6	25.2

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Halo Home

Report Number: SP1-2506-468-15

Test Date: 07/09/2025

Luminaire Tested: FMNL1515FS5-3500K

Data in this report applies to families of products including FMNL1515FS5-3500K

The results of this test have not been influenced by sources from within Eaton or from external interests.

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-468-15
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 07/10/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Halo Home
 Catalog Number: **FMNL1515FS5-3500K**
 Description: HALO FLUSH MOUNT NIGHT LIGHT 15 INCH

Spectral Parameters

CCT (K): 3517
 CIE u' : 0.2364
 CIE v' : 0.5080
 Duv: -0.0022
 CIE x: 0.4021
 CIE y: 0.3841
 CIE z: 0.2139
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 581
 Purity: 35.93442
 R_f: 92.8
 R_g: 103.1

CRI (Ra): 96.4
 R1: 98.7
 R2: 98.1
 R3: 93.5
 R4: 94.4
 R5: 99.1
 R6: 96.2
 R7: 96.0
 R8: 95.4
 R9: 86.0
 R10: 93.7
 R11: 91.5
 R12: 84.8
 R13: 99.5
 R14: 95.0
 R15: 99.1



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 24.0


REPORT NUMBER: SP1-2506-468-15

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025


Sample Number	Condition	Description
P2506-468-LM.3	Good	HALO FLUSH MOUNT NIGHT LIGHT 15 INCH

REPORT NUMBER: SP1-2506-468-15

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-468-15

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	91	NR	620	201	NR	750	3	NR	880	0	NR
365	0	NR	495	111	NR	625	209	NR	755	3	NR	885	0	NR
370	0	NR	500	131	NR	630	1000	NR	760	2	NR	890	0	NR
375	0	NR	505	147	NR	635	616	NR	765	2	NR	895	0	NR
380	0	NR	510	159	NR	640	111	NR	770	2	NR	900	0	NR
385	0	NR	515	168	NR	645	112	NR	775	1	NR	905	0	NR
390	1	NR	520	173	NR	650	95	NR	780	1	NR	910	0	NR
395	1	NR	525	176	NR	655	74	NR	785	1	NR	915	0	NR
400	2	NR	530	178	NR	660	60	NR	790	1	NR	920	0	NR
405	2	NR	535	180	NR	665	47	NR	795	1	NR	925	0	NR
410	3	NR	540	182	NR	670	47	NR	800	1	NR	930	0	NR
415	7	NR	545	184	NR	675	35	NR	805	1	NR	935	0	NR
420	13	NR	550	187	NR	680	29	NR	810	1	NR	940	0	NR
425	22	NR	555	190	NR	685	25	NR	815	0	NR	945	0	NR
430	38	NR	560	194	NR	690	21	NR	820	0	NR	950	0	NR
435	65	NR	565	198	NR	695	18	NR	825	0	NR	955	0	NR
440	113	NR	570	200	NR	700	15	NR	830	0	NR	960	0	NR
445	189	NR	575	202	NR	705	13	NR	835	0	NR	965	0	NR
450	226	NR	580	204	NR	710	11	NR	840	0	NR	970	0	NR
455	169	NR	585	204	NR	715	9	NR	845	0	NR	975	0	NR
460	122	NR	590	201	NR	720	8	NR	850	0	NR	980	0	NR
465	102	NR	595	195	NR	725	7	NR	855	0	NR	985	0	NR
470	79	NR	600	193	NR	730	6	NR	860	0	NR	990	0	NR
475	66	NR	605	192	NR	735	5	NR	865	0	NR	995	0	NR
480	67	NR	610	224	NR	740	4	NR	870	0	NR	1000	0	NR
485	76	NR	615	249	NR	745	3	NR	875	0	NR			

REPORT NUMBER: SP1-2506-468-15

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.65

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	91	NR	620	201	NR	750	3	NR	880	0	NR
365	0	NR	495	111	NR	625	209	NR	755	3	NR	885	0	NR
370	0	NR	500	131	NR	630	1000	NR	760	2	NR	890	0	NR
375	0	NR	505	147	NR	635	616	NR	765	2	NR	895	0	NR
380	0	NR	510	159	NR	640	111	NR	770	2	NR	900	0	NR
385	0	NR	515	168	NR	645	112	NR	775	1	NR	905	0	NR
390	1	NR	520	173	NR	650	95	NR	780	1	NR	910	0	NR
395	1	NR	525	176	NR	655	74	NR	785	1	NR	915	0	NR
400	2	NR	530	178	NR	660	60	NR	790	1	NR	920	0	NR
405	2	NR	535	180	NR	665	47	NR	795	1	NR	925	0	NR
410	3	NR	540	182	NR	670	47	NR	800	1	NR	930	0	NR
415	7	NR	545	184	NR	675	35	NR	805	1	NR	935	0	NR
420	13	NR	550	187	NR	680	29	NR	810	1	NR	940	0	NR
425	22	NR	555	190	NR	685	25	NR	815	0	NR	945	0	NR
430	38	NR	560	194	NR	690	21	NR	820	0	NR	950	0	NR
435	65	NR	565	198	NR	695	18	NR	825	0	NR	955	0	NR
440	113	NR	570	200	NR	700	15	NR	830	0	NR	960	0	NR
445	189	NR	575	202	NR	705	13	NR	835	0	NR	965	0	NR
450	226	NR	580	204	NR	710	11	NR	840	0	NR	970	0	NR
455	169	NR	585	204	NR	715	9	NR	845	0	NR	975	0	NR
460	122	NR	590	201	NR	720	8	NR	850	0	NR	980	0	NR
465	102	NR	595	195	NR	725	7	NR	855	0	NR	985	0	NR
470	79	NR	600	193	NR	730	6	NR	860	0	NR	990	0	NR
475	66	NR	605	192	NR	735	5	NR	865	0	NR	995	0	NR
480	67	NR	610	224	NR	740	4	NR	870	0	NR	1000	0	NR
485	76	NR	615	249	NR	745	3	NR	875	0	NR			

REPORT NUMBER: SP1-2506-468-15

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.35


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	91	NR	620	201	NR	750	3	NR	880	0	NR
365	0	NR	495	111	NR	625	209	NR	755	3	NR	885	0	NR
370	0	NR	500	131	NR	630	1000	NR	760	2	NR	890	0	NR
375	0	NR	505	147	NR	635	616	NR	765	2	NR	895	0	NR
380	0	NR	510	159	NR	640	111	NR	770	2	NR	900	0	NR
385	0	NR	515	168	NR	645	112	NR	775	1	NR	905	0	NR
390	1	NR	520	173	NR	650	95	NR	780	1	NR	910	0	NR
395	1	NR	525	176	NR	655	74	NR	785	1	NR	915	0	NR
400	2	NR	530	178	NR	660	60	NR	790	1	NR	920	0	NR
405	2	NR	535	180	NR	665	47	NR	795	1	NR	925	0	NR
410	3	NR	540	182	NR	670	47	NR	800	1	NR	930	0	NR
415	7	NR	545	184	NR	675	35	NR	805	1	NR	935	0	NR
420	13	NR	550	187	NR	680	29	NR	810	1	NR	940	0	NR
425	22	NR	555	190	NR	685	25	NR	815	0	NR	945	0	NR
430	38	NR	560	194	NR	690	21	NR	820	0	NR	950	0	NR
435	65	NR	565	198	NR	695	18	NR	825	0	NR	955	0	NR
440	113	NR	570	200	NR	700	15	NR	830	0	NR	960	0	NR
445	189	NR	575	202	NR	705	13	NR	835	0	NR	965	0	NR
450	226	NR	580	204	NR	710	11	NR	840	0	NR	970	0	NR
455	169	NR	585	204	NR	715	9	NR	845	0	NR	975	0	NR
460	122	NR	590	201	NR	720	8	NR	850	0	NR	980	0	NR
465	102	NR	595	195	NR	725	7	NR	855	0	NR	985	0	NR
470	79	NR	600	193	NR	730	6	NR	860	0	NR	990	0	NR
475	66	NR	605	192	NR	735	5	NR	865	0	NR	995	0	NR
480	67	NR	610	224	NR	740	4	NR	870	0	NR	1000	0	NR
485	76	NR	615	249	NR	745	3	NR	875	0	NR			

REPORT NUMBER: SP1-2506-468-15





TM-30-18

Summary

$R_f = 92.8$
 $R_g = 103.1$
 $CIE R_a = 96.4$
 $R_g = 86.0$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 93	CES51 = 96	CES76 = 88
CES02 = 62	CES27 = 94	CES52 = 94	CES77 = 88
CES03 = 32	CES28 = 96	CES53 = 93	CES78 = 84
CES04 = 69	CES29 = 92	CES54 = 96	CES79 = 92
CES05 = 50	CES30 = 99	CES55 = 97	CES80 = 93
CES06 = 51	CES31 = 93	CES56 = 95	CES81 = 77
CES07 = 43	CES32 = 85	CES57 = 95	CES82 = 96
CES08 = 42	CES33 = 93	CES58 = 95	CES83 = 94
CES09 = 29	CES34 = 92	CES59 = 99	CES84 = 95
CES10 = 75	CES35 = 95	CES60 = 96	CES85 = 83
CES11 = 57	CES36 = 87	CES61 = 96	CES86 = 85
CES12 = 64	CES37 = 92	CES62 = 94	CES87 = 92
CES13 = 44	CES38 = 96	CES63 = 96	CES88 = 97
CES14 = 74	CES39 = 97	CES64 = 98	CES89 = 86
CES15 = 72	CES40 = 94	CES65 = 94	CES90 = 98
CES16 = 48	CES41 = 96	CES66 = 95	CES91 = 79
CES17 = 49	CES42 = 88	CES67 = 94	CES92 = 83
CES18 = 56	CES43 = 89	CES68 = 93	CES93 = 90
CES19 = 71	CES44 = 99	CES69 = 93	CES94 = 79
CES20 = 67	CES45 = 91	CES70 = 90	CES95 = 87
CES21 = 86	CES46 = 93	CES71 = 88	CES96 = 93
CES22 = 78	CES47 = 87	CES72 = 96	CES97 = 91
CES23 = 91	CES48 = 99	CES73 = 85	CES98 = 94
CES24 = 90	CES49 = 91	CES74 = 91	CES99 = 99
CES25 = 71	CES50 = 95	CES75 = 88	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)