

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P152179

Luminaire Tested: **VXS-E05-LED-E1-SL4-7030**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P152179
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-E05-LED-E1-SL4-7030
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL
Light Source: (105) 3000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13490.7 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type IV - Short - Full Cutoff
BUG Rating: B2 - U0 - G3

Input Watts (W): 127.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P152179

CATALOG NUMBER: VXS-E05-LED-E1-SL4-7030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 7.2 fc
 Type IV - Short - Full Cutoff

REPORT NUMBER: P152179

CATALOG NUMBER: VXS-E05-LED-E1-SL4-7030

Luminous Intensity Polar Plot



REPORT NUMBER: P152179

CATALOG NUMBER: VXS-E05-LED-E1-SL4-7030

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	2800.5	0.0	2800.5
	% Fixture	20.8	0.0	20.8
Street Side	Lumens	10690.2	0.0	10690.2
	% Fixture	79.2	0.0	79.2
Total	Lumens	13490.7	0.0	13490.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.9	2.0
10°-20°	736.2	5.5
20°-30°	1089.8	8.1
30°-40°	1377.3	10.2
40°-50°	1557.6	11.5
50°-60°	2216.5	16.4
60°-70°	4128.0	30.6
70°-80°	1891.9	14.0
80°-90°	224.6	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	13490.7	100.0
0°-180°	13490.7	100.0

Coefficient of Utilization



REPORT NUMBER: P152179


CATALOG NUMBER: VXS-E05-LED-E1-SL4-7030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1228.4	9.1			
FM	(30°-60°)	3952.3	29.3			
FH	(60°-80°)	5342.8	39.6			G3/7500
FVH	(80°-90°)	166.6	1.2			G2/225
BL	(0°-30°)	866.5	6.4	B2/1000		
BM	(30°-60°)	1199.0	8.9	B2/2500		
BH	(60°-80°)	677.0	5.0	B2/1000		G2/1000
BVH	(80°-90°)	58.0	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short



REPORT NUMBER: P152179

CATALOG NUMBER: VXS-E05-LED-E1-SL4-7030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5
2.5°	2922.7	2930.4	2921.2	2919.7	2919.7	2918.1	2909.0	2907.5	2895.3	2896.9	2899.9
5°	2944.0	2947.0	2941.0	2939.5	2936.4	2930.4	2922.7	2913.6	2904.5	2895.3	2887.7
7.5°	2965.4	2962.3	2957.7	2957.7	2953.2	2944.0	2928.8	2916.6	2896.9	2886.2	2872.4
10°	2995.8	2991.2	2985.2	2982.1	2974.5	2960.8	2939.5	2922.7	2898.3	2877.1	2854.2
12.5°	3024.7	3023.2	3014.1	3009.5	2997.3	2983.6	2957.7	2931.8	2899.9	2866.4	2836.0
15°	3076.5	3070.4	3061.2	3052.1	3032.3	3014.1	2974.5	2944.0	2898.3	2854.2	2807.0
17.5°	3166.3	3155.6	3146.5	3126.7	3102.4	3070.4	3012.5	2960.8	2898.3	2834.4	2781.1
20°	3330.7	3307.9	3295.6	3269.8	3227.2	3169.3	3079.5	2995.8	2902.9	2820.7	2749.2
22.5°	3516.4	3501.1	3484.5	3467.7	3400.7	3317.0	3195.2	3070.4	2930.4	2814.6	2723.3
25°	3725.0	3705.2	3696.1	3667.2	3604.7	3508.8	3342.9	3169.3	2992.7	2839.0	2723.3
27.5°	3910.7	3904.6	3903.0	3869.5	3810.2	3697.5	3501.1	3292.6	3078.0	2889.2	2746.1
30°	4079.6	4073.6	4070.5	4052.2	3983.7	3849.7	3636.7	3402.3	3170.9	2959.3	2788.8
32.5°	4259.3	4239.5	4230.4	4195.3	4117.7	3960.9	3717.3	3473.8	3243.9	3027.8	2836.0
35°	4405.4	4388.6	4370.4	4320.1	4210.6	4024.9	3752.3	3498.1	3272.8	3065.8	2860.3
37.5°	4511.9	4495.2	4469.3	4405.4	4269.9	4046.1	3750.8	3490.6	3262.2	3059.7	2864.9
40°	4559.2	4542.4	4515.0	4434.3	4280.5	4034.0	3721.9	3455.5	3230.3	3027.8	2846.6
42.5°	4540.8	4528.7	4493.7	4416.1	4247.0	3979.2	3664.0	3390.1	3169.3	2976.0	2805.5
45°	4470.9	4461.8	4428.2	4346.0	4171.0	3890.9	3578.9	3307.9	3096.3	2912.0	2750.7
47.5°	4365.8	4362.8	4329.3	4248.6	4075.0	3802.6	3490.6	3227.2	3023.2	2849.6	2705.1
50°	4250.2	4234.9	4218.1	4143.5	3985.3	3726.4	3426.6	3176.9	2982.1	2826.8	2685.3
52.5°	4177.1	4172.5	4157.3	4090.3	3938.0	3682.3	3397.6	3158.7	2979.1	2822.3	2674.6
55°	4825.5	4836.2	4696.2	4405.4	4149.6	3804.1	3484.5	3251.5	3053.7	2895.3	2787.3
57.5°	7137.8	7090.7	6850.2	6273.2	5621.7	4761.6	4142.1	3766.0	3520.9	3548.4	3603.2
60°	8316.1	8306.9	8262.8	8039.0	7605.2	6950.6	6224.5	5391.8	5126.9	5155.9	5177.2
62.5°	8842.8	8856.5	8889.9	8806.2	8692.0	8501.8	8139.5	7804.6	7449.8	7317.4	6962.8
65°	9086.3	9110.7	9186.7	9234.0	9278.1	9311.6	9454.7	9847.5	10106.2	9622.2	8495.6
67.5°	8582.5	8699.7	8950.9	9196.0	9415.1	9727.2	10211.3	11123.1	11757.8	11162.7	9529.3
70°	6256.5	6416.3	6704.0	7462.1	8271.9	8979.8	9917.5	11305.8	12263.2	11803.5	9785.1
72.5°	3922.8	3966.9	4094.8	4373.5	4974.7	5883.5	7523.0	9605.4	10710.6	10343.7	8270.4
75°	2488.9	2504.1	2499.6	2563.4	2665.5	2863.3	3511.8	5673.5	7337.2	6764.9	4609.3
77.5°	1482.7	1505.5	1514.6	1534.4	1583.1	1653.2	1706.4	1930.3	3076.5	2986.6	1673.0
80°	1242.2	1260.4	1245.2	1240.6	1210.2	1188.9	1214.7	1188.9	1103.6	1062.5	978.8
82.5°	657.6	656.1	651.5	695.6	785.5	855.5	908.8	896.6	811.4	691.1	586.1
85°	360.7	373.0	373.0	388.2	374.5	376.0	388.2	409.5	379.1	316.6	258.8
87.5°	30.5	47.2	38.0	47.2	63.9	45.7	44.1	44.1	38.0	27.4	24.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152179

CATALOG NUMBER: VXS-E05-LED-E1-SL4-7030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5
2.5°	2892.2	2889.2	2883.1	2878.5	2878.5	2871.0	2866.4	2863.3	2861.9	2855.8	2855.8
5°	2883.1	2872.4	2861.9	2854.2	2849.6	2842.1	2829.8	2823.7	2816.2	2810.1	2807.0
7.5°	2863.3	2843.5	2826.8	2814.6	2799.4	2787.3	2772.0	2758.3	2744.7	2738.5	2735.4
10°	2833.0	2807.0	2781.1	2758.3	2737.0	2715.6	2695.9	2676.2	2659.4	2647.2	2635.0
12.5°	2803.9	2764.5	2730.9	2697.4	2663.9	2638.0	2610.7	2581.8	2557.4	2534.5	2528.5
15°	2764.5	2718.8	2676.2	2635.0	2593.9	2551.3	2517.8	2485.8	2446.2	2420.4	2400.6
17.5°	2727.9	2673.1	2621.3	2572.6	2522.4	2478.2	2428.0	2385.4	2345.8	2306.2	2277.3
20°	2688.3	2628.9	2574.1	2519.3	2464.6	2408.2	2350.4	2295.5	2246.8	2199.7	2152.4
22.5°	2653.3	2592.4	2539.1	2479.8	2418.9	2354.9	2288.0	2219.5	2163.1	2102.3	2047.5
25°	2632.0	2565.0	2510.2	2452.3	2385.4	2315.3	2239.3	2158.5	2090.1	2020.0	1954.6
27.5°	2632.0	2545.2	2488.9	2431.0	2362.5	2288.0	2204.2	2116.0	2038.3	1960.6	1880.0
30°	2654.8	2548.3	2472.1	2411.3	2341.2	2260.5	2167.7	2074.8	1989.5	1898.2	1820.6
32.5°	2676.2	2554.3	2460.0	2382.3	2301.7	2222.5	2128.1	2029.1	1934.8	1848.0	1765.8
35°	2689.8	2554.3	2437.1	2338.1	2246.8	2169.2	2076.4	1977.4	1881.5	1796.3	1720.1
37.5°	2691.3	2542.2	2400.6	2288.0	2192.0	2111.4	2023.1	1930.3	1838.9	1759.7	1695.8
40°	2676.2	2517.8	2364.0	2234.7	2134.2	2052.0	1971.3	1887.6	1805.4	1739.9	1685.2
42.5°	2648.7	2491.9	2329.0	2192.0	2087.0	2001.8	1927.2	1855.6	1784.0	1727.8	1682.1
45°	2607.6	2456.9	2297.1	2166.1	2062.7	1972.8	1899.8	1840.4	1779.5	1732.3	1686.6
47.5°	2571.1	2444.8	2307.8	2182.9	2074.8	1982.0	1907.4	1857.1	1809.9	1778.0	1715.5
50°	2563.4	2438.7	2312.3	2196.6	2087.0	1992.6	1927.2	1901.2	1887.6	1867.8	1771.9
52.5°	2542.2	2437.1	2345.8	2281.9	2211.8	2167.7	2099.2	2123.5	2108.3	2038.3	1864.8
55°	2765.9	2796.4	2881.7	3003.4	3116.1	3142.0	3134.3	3105.4	2951.6	2539.1	2088.5
57.5°	3802.6	3974.6	4136.0	4207.5	4198.3	4117.7	4059.8	3942.6	3720.4	3218.0	2529.9
60°	5242.6	5270.1	5184.8	5058.4	4845.3	4667.3	4476.9	4257.7	3935.0	3443.3	2800.9
62.5°	6568.5	6200.1	5821.0	5464.9	5140.6	4857.5	4592.6	4286.6	3866.5	3353.5	2765.9
65°	7504.7	6725.3	6127.0	5615.5	5157.4	4761.6	4431.3	4034.0	3560.5	3097.8	2563.4
67.5°	7987.3	6792.3	5874.4	5162.0	4511.9	3963.9	3524.0	3137.4	2785.7	2583.2	2243.8
70°	7448.4	5764.8	4486.1	3680.8	2902.9	2327.6	1838.9	1543.5	1441.6	1633.4	1698.9
72.5°	5550.2	3752.3	2668.5	2064.1	1581.7	1260.4	966.6	759.6	618.0	648.5	841.8
75°	2624.4	1619.7	1144.8	870.8	692.6	573.9	468.8	429.3	359.3	298.3	280.1
77.5°	1021.5	744.4	615.0	450.6	319.7	257.3	219.2	211.6	216.2	210.1	207.0
80°	777.8	526.7	330.4	242.1	208.5	184.1	162.9	156.8	159.8	167.5	175.0
82.5°	433.9	271.0	200.9	175.0	156.8	134.0	121.8	112.6	114.2	123.3	140.0
85°	167.5	130.9	120.2	115.6	108.1	86.7	74.6	76.1	86.7	103.5	103.5
87.5°	18.2	18.2	24.4	18.2	18.2	18.2	16.8	19.8	21.3	27.4	31.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152179

CATALOG NUMBER: VXS-E05-LED-E1-SL4-7030

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5	2878.5
2.5°	2852.7	2852.7	2852.7	2849.6	2851.2	2845.1	2845.1	2840.5	2848.1	2843.5	2842.1
5°	2808.6	2807.0	2800.9	2800.9	2800.9	2800.9	2805.5	2793.4	2802.5	2802.5	2797.9
7.5°	2734.0	2734.0	2717.2	2726.3	2723.3	2727.9	2734.0	2727.9	2737.0	2743.1	2738.5
10°	2630.5	2630.5	2616.8	2627.4	2622.8	2633.5	2644.1	2638.0	2644.1	2653.3	2656.4
12.5°	2516.3	2510.2	2498.0	2502.6	2502.6	2508.7	2513.3	2520.8	2528.5	2540.6	2546.7
15°	2383.8	2374.7	2359.5	2359.5	2350.4	2353.4	2362.5	2365.6	2380.8	2397.5	2417.3
17.5°	2248.4	2225.5	2208.8	2189.0	2173.8	2185.9	2196.6	2204.2	2216.4	2242.3	2256.0
20°	2120.5	2074.8	2042.9	2017.0	2000.2	2007.9	2021.6	2030.7	2041.3	2047.5	2052.0
22.5°	1994.2	1942.4	1898.2	1866.3	1838.9	1846.5	1840.4	1835.9	1843.4	1823.6	1822.2
25°	1884.6	1823.6	1764.2	1726.2	1692.7	1682.1	1650.2	1642.5	1621.2	1604.5	1592.2
27.5°	1805.4	1726.2	1660.7	1616.6	1563.3	1523.7	1482.7	1441.6	1418.8	1391.3	1377.6
30°	1743.0	1659.3	1581.7	1507.0	1437.0	1376.2	1321.3	1268.1	1231.5	1191.9	1166.0
32.5°	1685.2	1607.5	1513.2	1411.1	1316.8	1248.3	1176.7	1115.9	1057.9	1006.2	968.2
35°	1645.6	1558.8	1438.5	1313.7	1207.2	1126.4	1050.4	963.6	893.6	826.6	785.5
37.5°	1624.2	1517.7	1370.1	1231.5	1112.7	1021.5	927.0	826.6	741.3	679.0	616.5
40°	1607.5	1476.6	1309.1	1158.4	1033.6	924.0	814.4	695.6	601.2	535.9	487.2
42.5°	1589.2	1430.9	1255.9	1100.6	962.1	834.2	701.8	575.4	485.6	439.9	418.7
45°	1569.4	1391.3	1205.6	1045.8	892.0	736.8	584.6	467.4	414.1	398.9	398.9
47.5°	1564.9	1365.5	1169.1	992.5	812.8	624.1	476.5	403.4	388.2	391.2	397.3
50°	1583.1	1357.8	1137.1	930.1	707.9	505.4	403.4	379.1	382.1	391.2	400.3
52.5°	1627.3	1363.9	1103.6	843.3	583.0	417.1	373.0	371.4	380.5	394.3	403.4
55°	1701.9	1363.9	1039.7	713.9	465.8	374.5	362.3	368.4	380.5	392.7	400.3
57.5°	1861.8	1350.3	927.0	570.9	389.7	359.3	359.3	366.8	377.5	389.7	395.8
60°	2052.0	1332.0	768.7	441.5	351.6	347.0	357.7	366.8	376.0	386.6	392.7
62.5°	2064.1	1284.8	608.9	365.4	331.8	339.5	356.2	368.4	371.4	379.1	386.6
65°	1896.7	1120.4	484.0	327.3	322.7	334.9	351.6	360.7	362.3	365.4	373.0
67.5°	1660.7	913.4	391.2	309.0	313.6	327.3	336.4	344.0	348.6	356.2	357.7
70°	1363.9	733.7	334.9	290.8	295.3	310.6	318.1	325.8	334.9	344.0	339.5
72.5°	966.6	570.9	293.8	271.0	277.1	290.8	299.9	306.0	313.6	322.7	316.6
75°	411.0	398.9	254.2	245.1	254.2	263.3	272.4	281.7	289.2	293.8	293.8
77.5°	210.1	234.4	219.2	219.2	225.3	234.4	242.1	251.2	255.8	260.3	266.4
80°	178.1	181.1	184.1	190.3	196.4	205.5	213.2	220.7	222.3	223.7	226.8
82.5°	147.7	153.8	156.8	165.9	170.5	173.6	178.1	178.1	181.1	181.1	176.6
85°	106.5	114.2	118.8	120.2	118.8	120.2	121.8	124.9	132.4	132.4	126.3
87.5°	30.5	28.9	36.6	38.0	41.1	47.2	53.3	63.9	66.9	70.1	70.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P152179

CATALOG NUMBER: VXS-E05-LED-E1-SL4-7030

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	2878.5	2878.5	2878.5	2878.5
2.5°	2840.5	2843.5	2837.5	2839.0
5°	2797.9	2803.9	2796.4	2805.5
7.5°	2743.1	2752.2	2750.7	2749.2
10°	2663.9	2676.2	2676.2	2680.7
12.5°	2563.4	2571.1	2577.2	2580.2
15°	2428.0	2441.7	2449.3	2449.3
17.5°	2265.1	2274.2	2278.9	2272.7
20°	2058.0	2055.0	2056.6	2041.3
22.5°	1819.1	1823.6	1809.9	1813.0
25°	1584.7	1577.1	1583.1	1574.0
27.5°	1357.8	1359.4	1342.6	1350.3
30°	1141.7	1134.1	1112.7	1123.4
32.5°	933.2	913.4	890.5	876.8
35°	736.8	706.3	695.6	691.1
37.5°	578.4	545.0	534.3	522.2
40°	459.7	447.6	443.0	446.0
42.5°	412.5	412.5	415.5	417.1
45°	400.3	404.9	409.5	411.0
47.5°	401.9	406.4	412.5	414.1
50°	404.9	409.5	414.1	415.5
52.5°	406.4	406.4	409.5	411.0
55°	403.4	401.9	403.4	404.9
57.5°	397.3	394.3	395.8	400.3
60°	394.3	389.7	392.7	395.8
62.5°	386.6	385.1	388.2	389.7
65°	369.9	371.4	376.0	376.0
67.5°	354.7	356.2	357.7	359.3
70°	336.4	337.9	340.9	342.5
72.5°	315.1	321.2	325.8	331.8
75°	298.3	304.5	313.6	319.7
77.5°	269.4	274.0	284.7	292.2
80°	228.3	226.8	228.3	233.0
82.5°	175.0	175.0	173.6	172.0
85°	123.3	121.8	117.2	117.2
87.5°	66.9	65.5	63.9	60.9
90°	0.0	0.0	0.0	0.0

(END OF REPORT)