

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P147726

Luminaire Tested: **VXS-F05-LED-E1-5WQ-7050**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P147726
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F05-LED-E1-5WQ-7050
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE
Light Source: (35) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13484.6 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B4 - U0 - G2


Input Watts (W): 133.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P147726
 CATALOG NUMBER: VXS-F05-LED-E1-5WQ-7050

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 2 fc
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P147726
CATALOG NUMBER: VXS-F05-LED-E1-5WQ-7050

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P147726

CATALOG NUMBER: VXS-F05-LED-E1-5WQ-7050


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6742.3	0.0	6742.3
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	6742.3	0.0	6742.3
	% Fixture	50.0	0.0	50.0
Total	Lumens	13484.6	0.0	13484.6
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.3	0.5
10°-20°	248.3	1.8
20°-30°	502.8	3.7
30°-40°	842.9	6.3
40°-50°	1486.8	11.0
50°-60°	2622.0	19.4
60°-70°	4003.0	29.7
70°-80°	3345.0	24.8
80°-90°	363.5	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	13484.6	100.0
0°-180°	13484.6	100.0



REPORT NUMBER: P147726


CATALOG NUMBER: VXS-F05-LED-E1-5WQ-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	410.7	3.0			
FM (30°-60°)	2475.9	18.4			
FH (60°-80°)	3674.0	27.2			G2/5000
FVH (80°-90°)	181.7	1.3			G2/225
BL (0°-30°)	410.7	3.0	B1/500		
BM (30°-60°)	2475.9	18.4	B2/2500		
BH (60°-80°)	3674.0	27.2	B4/5000		G2/5000
BVH (80°-90°)	181.7	1.3			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G2

Type V Short





REPORT NUMBER: P147726

CATALOG NUMBER: VXS-F05-LED-E1-5WQ-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	700.2	700.2	700.2	700.2	700.2	700.2	700.2	700.2	700.2	700.2	700.2
2.5°	705.9	707.4	705.9	705.9	705.9	705.9	705.9	704.5	704.5	704.5	705.9
5°	720.0	721.5	720.0	721.5	721.5	721.5	721.5	720.0	720.0	720.0	720.0
7.5°	742.6	742.6	742.6	744.0	742.6	742.6	744.0	742.6	742.6	742.6	742.6
10°	775.0	773.7	773.7	773.7	773.7	773.7	775.0	775.0	775.0	773.7	773.7
12.5°	814.6	813.2	814.6	814.6	816.1	816.1	816.1	816.1	816.1	816.1	814.6
15°	862.6	862.6	862.6	864.0	866.8	866.8	865.4	866.8	866.8	866.8	866.8
17.5°	916.3	919.1	916.3	917.6	919.1	917.6	920.5	921.9	923.3	921.9	917.6
20°	971.3	972.7	972.7	972.7	972.7	975.5	977.0	977.0	981.2	979.8	978.3
22.5°	1023.5	1026.4	1026.4	1027.8	1027.8	1032.0	1032.0	1032.0	1034.8	1037.6	1034.8
25°	1078.7	1077.2	1077.2	1080.0	1081.5	1087.0	1087.0	1089.9	1094.1	1095.5	1092.7
27.5°	1128.0	1126.6	1126.6	1130.9	1132.2	1139.3	1139.3	1145.0	1147.8	1149.2	1146.4
30°	1180.2	1180.2	1178.9	1183.1	1187.4	1193.0	1195.8	1201.5	1205.7	1207.0	1204.2
32.5°	1242.4	1239.6	1240.9	1243.8	1246.6	1252.2	1256.5	1263.5	1269.2	1270.6	1267.8
35°	1313.0	1308.7	1310.2	1313.0	1317.2	1325.7	1332.7	1337.0	1345.4	1348.3	1342.6
37.5°	1390.6	1392.0	1390.6	1397.7	1404.8	1414.6	1423.1	1428.7	1437.2	1441.5	1437.2
40°	1500.7	1496.5	1500.7	1507.8	1519.1	1531.8	1548.7	1553.0	1561.5	1569.9	1560.0
42.5°	1643.3	1640.5	1650.4	1656.1	1668.7	1682.9	1704.0	1715.3	1728.1	1733.7	1725.2
45°	1829.6	1829.6	1840.9	1842.4	1862.2	1880.5	1910.2	1924.2	1948.3	1948.3	1948.3
47.5°	2035.9	2044.2	2051.3	2065.5	2079.6	2113.5	2143.1	2174.2	2196.8	2199.6	2195.3
50°	2249.0	2257.4	2278.7	2298.4	2329.4	2371.8	2404.2	2445.2	2465.0	2482.0	2476.3
52.5°	2484.8	2486.2	2511.6	2537.0	2582.2	2628.8	2681.0	2723.3	2758.7	2774.2	2761.5
55°	2743.1	2745.9	2768.5	2795.3	2846.2	2899.8	2964.8	3008.5	3053.7	3082.0	3060.7
57.5°	3022.7	3024.0	3046.6	3079.2	3139.8	3193.5	3255.5	3317.7	3360.1	3385.5	3371.4
60°	3331.8	3338.9	3355.9	3396.8	3454.6	3511.1	3573.3	3628.3	3677.7	3704.6	3690.5
62.5°	3662.2	3669.2	3693.3	3725.7	3776.6	3838.7	3897.9	3968.6	4009.5	4039.2	4017.9
65°	3883.8	3896.6	3934.7	3978.4	4053.3	4133.7	4202.9	4298.9	4348.3	4383.6	4363.8
67.5°	3897.9	3905.0	3951.6	4017.9	4118.2	4239.6	4380.8	4530.5	4627.9	4674.4	4640.5
69°	3802.0	3811.8	3857.0	3931.8	4043.4	4184.6	4352.5	4539.0	4688.6	4757.7	4725.3
70°	3693.3	3714.4	3763.8	3845.7	3954.4	4102.7	4276.3	4475.3	4650.5	4745.1	4721.0
72.5°	3464.6	3470.2	3502.7	3567.6	3650.9	3773.7	3937.5	4125.3	4291.8	4427.4	4447.2
75°	3074.9	3093.3	3117.2	3161.0	3203.3	3292.3	3402.4	3530.9	3628.3	3732.7	3737.0
77.5°	2323.8	2378.9	2397.2	2407.2	2425.5	2496.1	2592.0	2703.6	2784.0	2801.0	2798.1
80°	1043.3	1116.7	1133.7	1214.1	1263.5	1380.7	1527.6	1698.3	1812.7	1825.5	1794.4
82.5°	204.7	218.9	255.5	319.1	434.8	504.0	600.0	720.0	830.2	893.7	855.5
85°	67.8	72.0	83.3	91.8	105.9	120.0	145.4	180.7	224.5	248.5	221.7
87.5°	26.8	26.8	31.1	33.9	36.7	36.7	36.7	33.9	32.4	26.8	24.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P147726

CATALOG NUMBER: VXS-F05-LED-E1-5WQ-7050

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	700.2	700.2	700.2	700.2	700.2	700.2	700.2	700.2
2.5°	704.5	704.5	704.5	704.5	704.5	704.5	704.5	704.5
5°	720.0	718.7	718.7	717.2	717.2	717.2	717.2	717.2
7.5°	741.1	739.8	738.3	739.8	738.3	738.3	738.3	738.3
10°	773.7	770.9	769.4	768.0	768.0	768.0	766.6	766.6
12.5°	811.8	811.8	810.4	808.9	806.1	807.6	806.1	803.3
15°	864.0	861.2	859.8	858.3	855.5	855.5	855.5	854.1
17.5°	916.3	913.5	913.5	909.2	907.8	907.8	907.8	909.2
20°	974.1	969.9	967.0	964.2	961.5	962.8	960.0	962.8
22.5°	1032.0	1026.4	1023.5	1019.3	1015.1	1015.1	1013.7	1010.9
25°	1088.5	1081.5	1078.7	1074.4	1068.7	1068.7	1065.9	1063.1
27.5°	1142.2	1135.1	1132.2	1123.8	1118.1	1116.7	1113.9	1112.5
30°	1201.5	1193.0	1188.7	1180.2	1171.8	1170.4	1166.1	1166.1
32.5°	1263.5	1255.1	1252.2	1239.6	1232.5	1232.5	1229.6	1226.8
35°	1341.2	1328.5	1325.7	1313.0	1303.1	1303.1	1300.3	1301.7
37.5°	1433.0	1423.1	1413.2	1403.3	1392.0	1390.6	1387.8	1385.0
40°	1555.8	1544.5	1533.2	1519.1	1509.2	1506.4	1502.2	1500.7
42.5°	1719.6	1708.3	1685.7	1674.4	1664.5	1656.1	1654.6	1653.2
45°	1928.5	1914.4	1898.9	1877.7	1865.0	1846.6	1843.8	1836.8
47.5°	2179.8	2153.0	2126.1	2107.8	2088.1	2066.8	2062.6	2051.3
50°	2446.6	2425.5	2380.3	2350.7	2319.6	2298.4	2284.2	2280.0
52.5°	2733.3	2693.7	2648.5	2609.0	2563.8	2535.5	2510.2	2503.1
55°	3032.5	2976.1	2919.6	2873.0	2827.8	2793.9	2769.9	2758.7
57.5°	3331.8	3269.7	3207.6	3156.8	3118.7	3074.9	3050.9	3045.3
60°	3643.8	3584.6	3521.0	3470.2	3423.6	3385.5	3371.4	3344.6
62.5°	3974.2	3912.1	3852.7	3803.4	3744.0	3717.2	3693.3	3677.7
65°	4298.9	4226.9	4152.1	4099.9	4040.5	4002.4	3972.7	3951.6
67.5°	4550.3	4441.5	4341.2	4253.8	4173.3	4114.0	4075.9	4056.1
69°	4620.8	4485.3	4356.8	4242.5	4147.9	4081.5	4039.2	4019.4
70°	4612.3	4462.7	4321.5	4195.9	4092.7	4022.2	3981.2	3944.6
72.5°	4351.2	4214.2	4057.5	3920.5	3827.4	3759.6	3718.7	3698.9
75°	3713.1	3621.2	3508.3	3402.4	3334.6	3295.1	3244.2	3245.7
77.5°	2703.6	2706.4	2630.2	2521.5	2445.2	2431.1	2408.5	2385.9
80°	1677.2	1543.1	1455.5	1338.3	1252.2	1177.4	1145.0	1074.4
82.5°	773.7	604.2	468.7	354.4	272.4	213.2	186.3	152.4
85°	172.2	131.3	108.7	87.6	74.8	69.2	56.5	52.2
87.5°	24.0	21.1	19.8	18.3	15.5	11.3	8.5	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)