

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P149912

Luminaire Tested: **VXS-E06-LED-E1-SL2-7060**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P149912
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33678)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-E06-LED-E1-SL2-7060
Description: VISION SITE SMALL LED LUMINAIRE
(6) LIGHTBARS WITH AccuLED OPTICS - TYPE 2 W/ SPILL LIGHT CONTROL
Light Source: (126) 5700K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 18809.1 lumens
Efficiency: N/A
Efficacy: 125.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type II - Short - Non-Cutoff
BUG Rating: B3 - U0 - G3

Input Watts (W): 150.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P149912

CATALOG NUMBER: VXS-E06-LED-E1-SL2-7060

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 4.1 fc
 Type II - Short - Non-Cutoff

REPORT NUMBER: P149912

CATALOG NUMBER: VXS-E06-LED-E1-SL2-7060

Luminous Intensity Polar Plot



REPORT NUMBER: P149912

CATALOG NUMBER: VXS-E06-LED-E1-SL2-7060


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4446.4	0.0	4446.4
	% Fixture	23.6	0.0	23.6
Street Side	Lumens	14362.7	0.0	14362.7
	% Fixture	76.4	0.0	76.4
Total	Lumens	18809.1	0.0	18809.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.6	1.0
10°-20°	636.4	3.4
20°-30°	1099.1	5.8
30°-40°	1819.4	9.7
40°-50°	3085.7	16.4
50°-60°	4099.9	21.8
60°-70°	5296.0	28.2
70°-80°	2221.2	11.8
80°-90°	356.8	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	18809.1	100.0
0°-180°	18809.1	100.0

Coefficient of Utilization



REPORT NUMBER: P149912


CATALOG NUMBER: VXS-E06-LED-E1-SL2-7060

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1037.8	5.5			
FM	(30°-60°)	6946.8	36.9			
FH	(60°-80°)	6099.1	32.4			G3/7500
FVH	(80°-90°)	279.0	1.5			G3/500
BL	(0°-30°)	892.3	4.7	B2/1000		
BM	(30°-60°)	2058.2	10.9	B2/2500		
BH	(60°-80°)	1418.1	7.5	B3/2500		G3/2500
BVH	(80°-90°)	77.8	0.4			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type II Short



REPORT NUMBER: P149912

CATALOG NUMBER: VXS-E06-LED-E1-SL2-7060

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	60°	61°	62°	64°
0°	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8
2.5°	1951.6	1957.8	1953.7	1957.8	1961.9	1963.9	1968.1	1966.0	1966.0	1968.1	1963.9
5°	1951.6	1951.6	1957.8	1968.1	1972.1	1984.5	1998.9	1996.8	1998.9	1996.8	2000.9
7.5°	1992.7	1990.7	1996.8	2009.1	2013.3	2031.7	2056.3	2060.4	2064.6	2064.6	2070.7
10°	2064.6	2062.5	2068.6	2074.8	2080.9	2095.3	2130.2	2144.6	2146.6	2148.7	2156.9
12.5°	2154.8	2152.7	2144.6	2144.6	2142.5	2169.2	2216.4	2243.1	2247.2	2255.3	2261.6
15°	2218.4	2212.3	2200.0	2191.7	2202.1	2245.1	2314.9	2345.7	2349.7	2356.0	2372.3
17.5°	2280.0	2273.9	2247.2	2226.6	2241.0	2310.8	2405.2	2438.0	2446.2	2452.4	2470.9
20°	2366.2	2362.1	2323.1	2273.9	2269.7	2360.0	2474.9	2518.0	2524.2	2532.4	2550.9
22.5°	2497.5	2479.1	2433.9	2341.6	2296.4	2388.8	2524.2	2583.7	2591.9	2600.1	2624.8
25°	2661.8	2653.5	2575.5	2433.9	2339.5	2417.5	2577.6	2651.5	2663.7	2674.0	2706.8
27.5°	2832.0	2819.7	2735.6	2550.9	2415.4	2474.9	2661.8	2745.9	2762.3	2778.7	2809.4
30°	2983.9	2979.8	2910.1	2708.9	2538.5	2583.7	2797.2	2899.8	2918.2	2938.8	2967.5
32.5°	3341.0	3343.0	3271.2	3066.0	2836.2	2780.7	2992.1	3146.0	3154.2	3178.9	3230.2
35°	4024.4	4032.6	4005.9	3843.8	3585.2	3357.4	3377.9	3529.8	3538.0	3558.5	3607.8
37.5°	4482.1	4498.4	4580.5	4631.8	4500.5	4395.9	4135.2	4075.6	4081.9	4069.5	4059.3
40°	4734.4	4759.1	4974.5	5241.3	5385.0	5387.0	5274.2	5011.5	4911.0	4882.2	4759.1
42.5°	4878.1	4919.2	5225.0	5680.5	6093.1	6376.3	6446.0	6154.6	6080.7	5949.3	5713.4
45°	4972.5	5021.8	5382.9	6006.8	6614.3	7096.6	7459.8	7330.5	7281.2	7201.2	6983.6
47.5°	4956.1	4995.1	5370.7	6117.6	6887.3	7572.6	8217.1	8350.5	8290.9	8270.4	8122.7
50°	4656.5	4691.4	5073.1	5842.7	6737.4	7753.3	8697.3	9074.9	9074.9	9113.9	9068.7
52.5°	4336.4	4365.1	4711.9	5403.4	6253.1	7576.8	8964.0	9589.9	9672.0	9739.8	9846.5
55°	4215.2	4250.2	4512.8	5103.8	5840.6	7071.9	9054.4	9975.8	10127.7	10242.6	10484.8
57.5°	4272.7	4307.6	4494.3	4941.8	5598.4	6556.8	9058.4	10495.0	10788.5	11024.5	11514.9
60°	4521.0	4553.9	4709.8	5091.5	5534.8	6259.3	8884.0	11322.1	11789.9	12233.3	13050.1
62.5°	4406.1	4447.2	4674.9	5339.9	6008.9	6033.5	8254.0	11962.4	12715.5	13370.2	14669.2
65°	3903.3	3946.4	4125.0	4746.7	6037.6	6132.0	7320.2	11974.6	12910.5	13794.9	15196.6
67.5°	2963.4	2979.8	3121.5	3620.1	4828.8	6240.7	6359.8	10556.6	11447.3	12434.3	13881.1
70°	1514.5	1543.2	1584.4	1998.9	3109.1	5157.2	5465.1	7779.9	8914.8	9934.7	11673.0
72.5°	525.4	535.6	576.7	763.4	1514.5	3384.1	4783.7	5331.6	6017.1	6971.4	8984.6
75°	316.1	316.1	330.4	385.8	691.6	1762.8	4256.3	4354.8	4447.2	4767.3	6084.8
77.5°	250.4	254.5	254.5	264.8	383.7	905.0	3232.2	4049.0	4061.3	4092.1	4313.8
80°	178.5	186.7	203.2	211.4	248.3	496.7	1814.2	3554.4	3796.6	3913.6	4075.6
82.5°	133.4	141.6	172.4	182.7	193.0	277.1	814.7	2452.4	2893.6	3127.6	3698.1
85°	59.5	69.7	117.0	129.3	135.4	147.8	381.8	697.7	802.4	900.9	1188.2
87.5°	10.3	10.3	18.4	26.6	39.0	36.9	84.1	119.1	121.0	141.6	158.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P149912

CATALOG NUMBER: VXS-E06-LED-E1-SL2-7060

CANDELA DISTRIBUTION (continued):

	65°	66°	67°	68°	69°	70°	71°	72°	73°	74°	75°
0°	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8
2.5°	1963.9	1963.9	1963.9	1961.9	1963.9	1963.9	1963.9	1963.9	1966.0	1966.0	1966.0
5°	2007.0	2003.0	2005.0	2005.0	2005.0	2003.0	2007.0	2005.0	2007.0	2013.3	2011.2
7.5°	2070.7	2074.8	2076.8	2078.9	2078.9	2078.9	2080.9	2085.1	2085.1	2091.2	2089.1
10°	2165.1	2163.0	2165.1	2171.2	2177.4	2179.5	2185.6	2183.5	2187.7	2195.9	2204.0
12.5°	2265.6	2269.7	2275.9	2282.1	2292.3	2294.4	2300.5	2302.6	2314.9	2314.9	2323.1
15°	2378.5	2380.5	2392.8	2394.9	2407.3	2411.4	2421.7	2425.7	2440.1	2442.2	2450.4
17.5°	2481.1	2485.2	2491.4	2497.5	2511.9	2518.0	2526.3	2534.5	2546.8	2550.9	2565.3
20°	2563.2	2571.4	2573.5	2585.8	2598.1	2606.3	2614.5	2622.7	2635.0	2641.2	2655.5
22.5°	2637.1	2645.3	2651.5	2661.8	2669.9	2682.3	2686.3	2700.7	2713.1	2723.3	2735.6
25°	2717.1	2729.4	2735.6	2754.1	2760.2	2772.5	2782.8	2797.2	2813.6	2825.9	2842.3
27.5°	2829.9	2848.5	2856.7	2877.2	2891.6	2897.7	2914.1	2934.6	2949.0	2963.4	2979.8
30°	2986.0	3020.8	3027.0	3041.3	3068.1	3072.1	3092.6	3109.1	3131.7	3146.0	3160.4
32.5°	3228.1	3271.2	3275.3	3291.7	3314.3	3322.5	3339.0	3357.4	3392.3	3398.4	3421.0
35°	3599.6	3618.0	3634.5	3640.6	3659.1	3669.3	3681.7	3702.2	3737.1	3733.0	3757.6
37.5°	4044.9	4051.1	4053.2	4032.6	4036.7	4018.2	4040.8	4044.9	4057.2	4067.5	4092.1
40°	4681.1	4617.5	4609.2	4560.0	4510.8	4484.0	4473.8	4432.7	4443.0	4447.2	4467.7
42.5°	5610.8	5487.6	5385.0	5315.2	5194.2	5134.6	5054.6	4991.0	4941.8	4960.2	4968.4
45°	6788.7	6612.2	6448.1	6234.6	6076.6	5963.7	5822.1	5694.9	5637.4	5610.8	5643.6
47.5°	7964.7	7808.7	7615.8	7396.2	7145.8	6959.1	6723.0	6515.8	6372.1	6318.8	6347.5
50°	8980.5	8836.8	8691.1	8561.9	8270.4	8067.3	7745.1	7476.2	7250.5	7135.5	7104.8
52.5°	9823.9	9748.0	9670.1	9561.2	9327.3	9124.1	8867.6	8602.9	8303.2	8069.3	7989.2
55°	10577.1	10622.3	10583.2	10585.3	10493.0	10363.6	10146.1	9949.1	9739.8	9475.0	9364.2
57.5°	11675.0	11941.9	11995.1	12128.6	12194.2	12264.0	12325.6	12208.6	12155.2	11958.2	11960.3
60°	13405.1	13794.9	14133.6	14441.5	14693.8	14940.1	15198.7	15313.6	15440.8	15500.3	15703.5
62.5°	15245.9	15617.3	16122.2	16534.6	16766.5	17086.7	17367.9	17550.5	17774.2	18012.2	18322.2
65°	15701.5	16148.8	16466.9	16742.0	16971.8	17142.1	17296.1	17513.6	17700.3	18077.9	18443.2
67.5°	14533.8	14890.9	15182.3	15453.2	15631.7	15775.3	15912.8	16056.5	16376.7	16719.4	17086.7
70°	12475.4	12906.3	13388.6	13739.6	13827.8	13950.9	14082.3	14269.0	14429.1	14788.2	15067.4
72.5°	10023.0	10642.8	11051.2	11537.5	11642.2	11828.9	11902.8	12048.5	12077.3	12272.2	12346.1
75°	6985.7	7695.8	8106.2	8463.3	8533.1	8430.5	8471.5	7956.4	7825.1	7718.3	7632.1
77.5°	4611.3	4802.2	4867.9	4810.4	4535.3	4319.9	4090.1	3864.4	3888.9	3706.3	3386.1
80°	4100.3	4143.4	4083.9	4026.4	3868.4	3642.7	3435.4	3224.0	3119.4	3008.5	2844.4
82.5°	3989.5	4155.8	4174.2	4104.5	3979.3	3733.0	3482.6	3168.6	2901.9	2655.5	2405.2
85°	1333.9	1623.3	1752.5	1873.7	1910.6	1953.7	1805.9	1604.9	1362.7	1200.5	939.9
87.5°	170.4	211.4	244.2	209.3	244.2	287.4	207.3	231.9	234.0	145.7	108.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P149912

CATALOG NUMBER: VXS-E06-LED-E1-SL2-7060

CANDELA DISTRIBUTION (continued):

	76°	77°	78°	79°	80°	81°	82°	83°	84°	85°	86°
0°	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8
2.5°	1968.1	1966.0	1966.0	1966.0	1963.9	1966.0	1966.0	1966.0	1966.0	1966.0	1963.9
5°	2013.3	2013.3	2019.4	2021.5	2017.3	2015.2	2017.3	2019.4	2019.4	2017.3	2019.4
7.5°	2097.4	2099.4	2103.5	2109.6	2105.6	2107.7	2109.6	2107.7	2113.8	2115.9	2113.8
10°	2204.0	2208.2	2218.4	2220.5	2218.4	2226.6	2228.7	2224.6	2228.7	2228.7	2236.9
12.5°	2327.3	2331.3	2343.6	2347.8	2351.8	2353.9	2360.0	2362.1	2368.3	2372.3	2378.5
15°	2460.6	2464.7	2473.0	2487.3	2491.4	2495.4	2499.6	2511.9	2514.0	2522.2	2528.3
17.5°	2573.5	2579.6	2591.9	2602.2	2608.4	2618.7	2622.7	2637.1	2641.2	2653.5	2663.7
20°	2663.7	2674.0	2684.2	2696.6	2706.8	2719.2	2723.3	2737.6	2745.9	2752.0	2764.4
22.5°	2745.9	2758.1	2772.5	2786.9	2795.1	2811.5	2817.7	2823.8	2842.3	2850.6	2862.8
25°	2852.5	2864.9	2881.3	2899.8	2908.0	2928.5	2934.6	2945.0	2965.5	2973.7	2992.1
27.5°	2998.2	3014.7	3027.0	3045.5	3055.8	3070.2	3084.5	3096.8	3115.2	3127.6	3148.1
30°	3180.9	3193.3	3213.8	3228.1	3244.6	3265.1	3281.5	3293.8	3304.0	3322.5	3345.1
32.5°	3449.7	3451.8	3457.9	3492.8	3509.3	3525.7	3548.3	3558.5	3574.9	3593.5	3618.0
35°	3784.2	3802.8	3817.1	3833.6	3852.0	3870.5	3878.7	3909.4	3923.8	3948.5	3973.1
37.5°	4116.7	4118.8	4151.6	4161.9	4178.3	4196.8	4225.5	4256.3	4293.3	4317.8	4356.9
40°	4473.8	4490.3	4531.3	4551.8	4572.3	4617.5	4640.0	4689.3	4750.9	4785.8	4851.4
42.5°	4991.0	5015.6	5089.5	5122.3	5171.6	5245.5	5292.6	5360.4	5385.0	5469.1	5499.9
45°	5668.2	5744.1	5850.9	5920.6	6008.9	6088.9	6129.9	6160.7	6197.7	6263.3	6255.1
47.5°	6400.8	6499.4	6618.3	6762.1	6819.5	6913.9	6967.3	7026.7	6993.9	6977.5	6961.1
50°	7151.9	7266.8	7424.9	7554.2	7642.4	7699.9	7745.1	7736.8	7667.0	7630.2	7527.5
52.5°	7987.3	8054.9	8204.8	8315.5	8368.9	8381.2	8371.0	8309.4	8243.7	8126.7	8005.7
55°	9267.8	9237.0	9296.5	9347.8	9331.4	9388.9	9241.1	9183.6	9021.6	8869.6	8707.6
57.5°	11869.9	11911.0	11578.5	11428.8	11402.1	11455.4	11194.8	11162.0	10770.1	10720.7	10447.8
60°	15674.8	15875.9	15615.2	15469.5	15075.5	14946.2	14654.8	14533.8	14158.2	13854.5	13470.7
62.5°	18535.5	18718.2	18826.9	18619.7	18389.8	18051.3	17610.1	17121.6	16723.4	16257.6	15851.3
65°	18794.2	19163.5	19413.9	19510.4	19348.3	18976.8	18433.0	17817.3	17207.8	16622.9	16109.8
67.5°	17585.4	17915.8	18303.6	18650.5	18671.0	18428.8	17965.1	17339.2	16635.2	15912.8	15311.5
70°	15508.6	15923.1	16261.8	16627.0	16881.5	16742.0	16510.1	15935.4	15204.9	14642.5	13950.9
72.5°	12612.8	12787.4	12869.4	13228.6	13232.6	12978.1	12814.0	12496.0	11906.9	11508.8	10981.3
75°	7365.4	6981.7	6573.3	6218.2	5928.8	5807.8	5270.1	5179.8	4818.5	4594.9	4266.5
77.5°	3037.3	2694.5	2253.4	1886.0	1522.7	1358.5	1120.5	1015.9	880.4	820.9	781.9
80°	2604.2	2280.0	1947.6	1629.4	1346.2	1063.0	827.0	642.4	504.9	428.9	398.1
82.5°	2126.1	1931.1	1699.3	1526.8	1305.2	1093.8	923.5	716.3	535.6	394.0	301.7
85°	767.6	630.1	506.9	465.8	371.4	305.8	256.5	219.6	180.6	143.6	127.3
87.5°	86.2	82.1	47.2	45.2	51.3	36.9	43.1	39.0	32.8	28.7	30.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P149912

CATALOG NUMBER: VXS-E06-LED-E1-SL2-7060

CANDELA DISTRIBUTION (continued):

	87°	88°	89°	90°	95°	105°	115°	125°	135°	145°	155°
0°	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8	1957.8
2.5°	1963.9	1963.9	1966.0	1966.0	1968.1	1970.2	1974.2	1972.1	1972.1	1974.2	1974.2
5°	2019.4	2025.5	2023.5	2023.5	2023.5	2025.5	2027.6	2019.4	2011.2	2003.0	1998.9
7.5°	2115.9	2119.9	2124.0	2119.9	2124.0	2122.0	2117.9	2095.3	2068.6	2035.8	2013.3
10°	2241.0	2241.0	2245.1	2243.1	2251.3	2245.1	2232.8	2181.5	2124.0	2054.3	2003.0
12.5°	2376.5	2390.8	2384.7	2386.7	2403.1	2386.7	2358.0	2282.1	2179.5	2066.5	1976.3
15°	2536.6	2542.7	2546.8	2540.6	2550.9	2536.6	2485.2	2364.1	2214.3	2056.3	1922.9
17.5°	2667.9	2669.9	2672.0	2676.1	2690.5	2674.0	2585.8	2421.7	2222.6	2009.1	1832.6
20°	2770.5	2780.7	2788.9	2788.9	2809.4	2784.9	2667.9	2450.4	2195.9	1931.1	1717.7
22.5°	2877.2	2885.4	2895.6	2897.7	2924.4	2899.8	2735.6	2444.1	2126.1	1820.3	1584.4
25°	3008.5	3016.8	3025.0	3035.2	3072.1	3037.3	2803.3	2419.6	2029.6	1689.0	1440.6
27.5°	3160.4	3178.9	3185.1	3201.5	3244.6	3191.2	2860.8	2382.6	1922.9	1537.1	1288.8
30°	3363.5	3386.1	3394.4	3416.9	3476.5	3359.5	2893.6	2319.0	1787.5	1383.2	1126.6
32.5°	3636.5	3667.3	3691.9	3716.6	3784.2	3527.8	2897.7	2226.6	1629.4	1210.8	970.7
35°	3993.6	4040.8	4059.3	4075.6	4139.3	3710.4	2879.3	2089.1	1436.6	1034.3	847.6
37.5°	4393.8	4440.9	4453.3	4461.6	4473.8	3866.3	2834.1	1879.8	1219.0	880.4	749.0
40°	4886.3	4927.4	4943.7	4931.5	4865.8	3987.5	2733.6	1635.6	1007.7	775.8	687.5
42.5°	5487.6	5549.2	5555.3	5499.9	5282.4	4055.1	2532.4	1348.3	841.5	699.8	640.3
45°	6232.5	6228.5	6193.6	6154.6	5736.0	4028.5	2251.3	1097.9	736.8	640.3	597.2
47.5°	6901.6	6831.8	6778.4	6663.5	6136.1	3872.5	1888.1	909.1	673.2	595.1	560.2
50°	7449.5	7322.3	7209.4	7084.2	6433.7	3595.4	1526.8	771.6	613.6	556.2	525.4
52.5°	7882.6	7728.6	7597.3	7474.2	6721.0	3287.7	1251.8	671.1	556.2	517.2	486.4
55°	8559.8	8405.9	8196.6	8061.0	7160.2	3004.5	1073.3	591.1	500.7	476.1	445.3
57.5°	10273.4	10137.9	9887.6	9536.6	8288.9	2897.7	972.7	529.4	455.5	441.2	416.6
60°	13265.5	13045.9	12719.6	12362.5	10583.2	2969.5	892.7	486.4	424.8	412.5	394.0
62.5°	15522.9	15137.1	14767.7	14437.3	12417.9	2967.5	788.1	453.6	402.3	396.1	377.6
65°	15615.2	15223.3	14851.8	14505.1	12459.0	2641.2	664.9	424.8	398.1	396.1	365.3
67.5°	14786.2	14361.3	14002.3	13565.1	11533.5	2064.6	533.6	406.3	414.5	410.5	361.1
70°	13431.7	12877.6	12582.1	12151.2	10150.3	1444.8	439.2	412.5	449.4	437.1	367.4
72.5°	10542.2	10123.5	9674.1	9374.5	7946.1	913.3	369.4	416.6	463.8	443.3	383.7
75°	3923.8	4036.7	3852.0	3786.3	4036.7	535.6	328.4	387.9	414.5	383.7	348.9
77.5°	792.1	757.3	718.2	710.1	917.3	330.4	301.7	336.6	318.1	281.1	283.2
80°	379.7	369.4	357.1	355.0	340.6	275.0	279.1	287.4	240.1	217.5	231.9
82.5°	252.4	238.0	234.0	225.7	229.8	246.2	264.8	246.2	184.7	172.4	209.3
85°	117.0	112.8	110.8	110.8	123.1	221.7	219.6	180.6	127.3	123.1	209.3
87.5°	28.7	28.7	30.8	28.7	32.8	65.7	57.5	55.4	47.2	53.4	98.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P149912

CATALOG NUMBER: VXS-E06-LED-E1-SL2-7060

CANDELA DISTRIBUTION (continued):

	165°	175°	180°
0°	1957.8	1957.8	1957.8
2.5°	1972.1	1974.2	1972.1
5°	1990.7	1990.7	1990.7
7.5°	1990.7	1984.5	1982.5
10°	1961.9	1943.4	1943.4
12.5°	1912.6	1881.9	1877.8
15°	1820.3	1779.3	1773.2
17.5°	1703.3	1647.9	1637.6
20°	1572.0	1502.2	1489.9
22.5°	1428.3	1348.3	1342.2
25°	1286.7	1204.7	1188.2
27.5°	1128.7	1048.7	1040.5
30°	970.7	900.9	896.8
32.5°	837.3	794.2	786.0
35°	742.9	718.2	708.0
37.5°	681.3	662.9	660.8
40°	634.1	617.7	615.6
42.5°	595.1	580.7	578.8
45°	556.2	543.8	539.7
47.5°	517.2	504.9	502.8
50°	482.3	465.8	463.8
52.5°	449.4	433.1	428.9
55°	418.7	402.3	402.3
57.5°	392.0	375.5	373.5
60°	367.4	350.9	348.9
62.5°	348.9	328.4	326.3
65°	334.5	314.0	309.8
67.5°	326.3	301.7	295.5
70°	340.6	295.5	285.3
72.5°	342.7	289.3	275.0
75°	330.4	273.0	262.7
77.5°	289.3	244.2	234.0
80°	250.4	188.8	174.4
82.5°	238.0	153.9	133.4
85°	184.7	100.5	94.4
87.5°	104.7	55.4	45.2
90°	0.0	0.0	0.0

(END OF REPORT)