

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P147733

Luminaire Tested: **VXS-F06-LED-E1-5WQ-8030**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P147733
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33675)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F06-LED-E1-5WQ-8030
Description: VISION SITE SMALL LED LUMINAIRE
(6) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE WIDE
Light Source: (42) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13309.6 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type V - Short - Semi-Cutoff
BUG Rating: B4 - U0 - G2


Input Watts (W): 156.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P147733
 CATALOG NUMBER: VXS-F06-LED-E1-5WQ-8030

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 2 fc
 Type V - Short - Semi-Cutoff

REPORT NUMBER: P147733
CATALOG NUMBER: VXS-F06-LED-E1-5WQ-8030

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 69-Deg Vertical

REPORT NUMBER: P147733

CATALOG NUMBER: VXS-F06-LED-E1-5WQ-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6654.8	0.0	6654.8
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	6654.8	0.0	6654.8
	% Fixture	50.0	0.0	50.0
Total	Lumens	13309.6	0.0	13309.6
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.4	0.5
10°-20°	245.1	1.8
20°-30°	496.2	3.7
30°-40°	832.0	6.3
40°-50°	1467.5	11.0
50°-60°	2588.0	19.4
60°-70°	3951.1	29.7
70°-80°	3301.6	24.8
80°-90°	358.8	2.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	13309.6	100.0
0°-180°	13309.6	100.0



REPORT NUMBER: P147733


CATALOG NUMBER: VXS-F06-LED-E1-5WQ-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	405.4	3.0			
FM	(30°-60°)	2443.7	18.4			
FH	(60°-80°)	3626.3	27.2			G2/5000
FVH	(80°-90°)	179.4	1.3			G2/225
BL	(0°-30°)	405.4	3.0	B1/500		
BM	(30°-60°)	2443.7	18.4	B2/2500		
BH	(60°-80°)	3626.3	27.2	B4/5000		G2/5000
BVH	(80°-90°)	179.4	1.3			G2/225
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G2

Type V Short





REPORT NUMBER: P147733

CATALOG NUMBER: VXS-F06-LED-E1-5WQ-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	691.2	691.2	691.2	691.2	691.2	691.2	691.2	691.2	691.2	691.2	691.2
2.5°	696.7	698.1	696.7	696.7	696.7	696.7	696.7	695.3	695.3	695.3	696.7
5°	710.7	712.0	710.7	712.0	712.0	712.0	712.0	710.7	710.7	710.7	710.7
7.5°	733.0	733.0	733.0	734.4	733.0	733.0	734.4	733.0	733.0	733.0	733.0
10°	765.0	763.6	763.6	763.6	763.6	763.6	765.0	765.0	765.0	763.6	763.6
12.5°	804.0	802.6	804.0	804.0	805.4	805.4	805.4	805.4	805.4	805.4	804.0
15°	851.4	851.4	851.4	852.8	855.5	855.5	854.2	855.5	855.5	855.5	855.5
17.5°	904.4	907.2	904.4	905.8	907.2	905.8	908.5	909.9	911.3	909.9	905.8
20°	958.8	960.1	960.1	960.1	960.1	962.9	964.2	964.2	968.5	967.0	965.7
22.5°	1010.3	1013.1	1013.1	1014.4	1014.4	1018.7	1018.7	1018.7	1021.5	1024.2	1021.5
25°	1064.7	1063.2	1063.2	1066.0	1067.4	1073.0	1073.0	1075.8	1079.9	1081.3	1078.5
27.5°	1113.4	1112.0	1112.0	1116.2	1117.5	1124.6	1124.6	1130.2	1132.8	1134.3	1131.5
30°	1165.0	1165.0	1163.5	1167.8	1171.9	1177.5	1180.3	1185.8	1190.1	1191.4	1188.6
32.5°	1226.2	1223.4	1224.9	1227.7	1230.5	1236.0	1240.2	1247.2	1252.7	1254.1	1251.3
35°	1296.0	1291.7	1293.2	1296.0	1300.1	1308.5	1315.4	1319.6	1328.0	1330.8	1325.2
37.5°	1372.5	1374.0	1372.5	1379.6	1386.5	1396.3	1404.7	1410.2	1418.5	1422.7	1418.5
40°	1481.2	1477.1	1481.2	1488.2	1499.4	1511.9	1528.6	1532.8	1541.1	1549.5	1539.8
42.5°	1622.0	1619.2	1629.0	1634.5	1647.0	1661.0	1682.0	1693.1	1705.6	1711.2	1702.8
45°	1805.9	1805.9	1817.1	1818.4	1838.0	1856.1	1885.4	1899.3	1923.0	1923.0	1923.0
47.5°	2009.4	2017.7	2024.7	2038.7	2052.5	2086.0	2115.3	2145.9	2168.3	2171.0	2166.8
50°	2219.8	2228.2	2249.0	2268.6	2299.3	2341.0	2373.1	2413.5	2433.0	2449.7	2444.1
52.5°	2452.5	2453.9	2479.0	2504.0	2548.7	2594.6	2646.2	2688.0	2722.8	2738.1	2725.6
55°	2707.6	2710.3	2732.6	2759.1	2809.2	2862.2	2926.3	2969.5	3014.1	3042.0	3021.0
57.5°	2983.4	2984.8	3007.2	3039.2	3099.1	3152.0	3213.4	3274.6	3316.5	3341.6	3327.6
60°	3288.6	3295.5	3312.3	3352.6	3409.8	3465.6	3526.8	3581.2	3629.9	3656.5	3642.5
62.5°	3614.7	3621.7	3645.3	3677.4	3727.6	3788.8	3847.4	3917.1	3957.4	3986.7	3965.8
65°	3833.5	3846.0	3883.6	3926.8	4000.6	4080.1	4148.4	4243.1	4291.9	4326.7	4307.3
67.5°	3847.4	3854.3	3900.3	3965.8	4064.8	4184.6	4323.9	4471.6	4567.8	4613.8	4580.3
69°	3752.6	3762.4	3806.9	3880.8	3990.9	4130.3	4296.1	4480.0	4627.7	4696.0	4663.9
70°	3645.3	3666.2	3715.0	3795.9	3903.1	4049.4	4220.8	4417.3	4590.1	4683.4	4659.8
72.5°	3419.6	3425.2	3457.2	3521.3	3603.5	3724.8	3886.4	4071.7	4236.2	4369.9	4389.4
75°	3035.0	3053.1	3076.8	3120.0	3161.8	3249.5	3358.2	3485.1	3581.2	3684.4	3688.5
77.5°	2293.7	2348.0	2366.1	2375.9	2394.0	2463.6	2558.4	2668.5	2747.9	2764.7	2761.9
80°	1029.7	1102.3	1119.0	1198.3	1247.2	1362.8	1507.8	1676.4	1789.2	1801.8	1771.1
82.5°	202.1	216.0	252.2	314.9	429.2	497.5	592.2	710.7	819.4	882.1	844.5
85°	66.8	71.1	82.2	90.6	104.6	118.4	143.5	178.3	221.6	245.3	218.8
87.5°	26.4	26.4	30.7	33.5	36.3	36.3	36.3	33.5	32.0	26.4	23.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P147733

CATALOG NUMBER: VXS-F06-LED-E1-5WQ-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	691.2	691.2	691.2	691.2	691.2	691.2	691.2	691.2
2.5°	695.3	695.3	695.3	695.3	695.3	695.3	695.3	695.3
5°	710.7	709.3	709.3	707.9	707.9	707.9	707.9	707.9
7.5°	731.6	730.2	728.8	730.2	728.8	728.8	728.8	728.8
10°	763.6	760.8	759.5	758.0	758.0	758.0	756.7	756.7
12.5°	801.2	801.2	799.9	798.4	795.6	797.1	795.6	792.8
15°	852.8	850.1	848.6	847.3	844.5	844.5	844.5	843.0
17.5°	904.4	901.6	901.6	897.4	896.0	896.0	896.0	897.4
20°	961.5	957.3	954.5	951.7	948.9	950.4	947.6	950.4
22.5°	1018.7	1013.1	1010.3	1006.1	1001.9	1001.9	1000.5	997.7
25°	1074.4	1067.4	1064.7	1060.4	1054.8	1054.8	1052.0	1049.3
27.5°	1127.4	1120.3	1117.5	1109.2	1103.6	1102.3	1099.5	1098.0
30°	1185.8	1177.5	1173.3	1165.0	1156.6	1155.2	1151.0	1151.0
32.5°	1247.2	1238.8	1236.0	1223.4	1216.5	1216.5	1213.7	1210.9
35°	1323.8	1311.3	1308.5	1296.0	1286.2	1286.2	1283.4	1284.8
37.5°	1414.4	1404.7	1394.8	1385.1	1374.0	1372.5	1369.7	1367.0
40°	1535.6	1524.5	1513.3	1499.4	1489.6	1486.8	1482.7	1481.2
42.5°	1697.2	1686.1	1663.8	1652.6	1642.9	1634.5	1633.2	1631.7
45°	1903.5	1889.5	1874.2	1853.4	1840.7	1822.7	1819.9	1813.0
47.5°	2151.5	2125.1	2098.5	2080.4	2060.9	2040.0	2035.9	2024.7
50°	2414.9	2394.0	2349.4	2320.1	2289.4	2268.6	2254.6	2250.5
52.5°	2697.7	2658.8	2614.2	2575.1	2530.6	2502.7	2477.6	2470.7
55°	2993.2	2937.4	2881.7	2835.8	2791.1	2757.7	2734.0	2722.8
57.5°	3288.6	3227.3	3166.0	3115.8	3078.1	3035.0	3011.3	3005.7
60°	3596.6	3538.0	3475.3	3425.2	3379.2	3341.6	3327.6	3301.1
62.5°	3922.6	3861.3	3802.8	3754.0	3695.4	3669.0	3645.3	3629.9
65°	4243.1	4172.0	4098.2	4046.6	3988.1	3950.5	3921.2	3900.3
67.5°	4491.2	4383.8	4285.0	4198.5	4119.1	4060.6	4022.9	4003.4
69°	4560.8	4427.0	4300.2	4187.4	4094.0	4028.5	3986.7	3967.3
70°	4552.4	4404.8	4265.4	4141.3	4039.7	3969.9	3929.6	3893.4
72.5°	4294.7	4159.5	4004.9	3869.6	3777.7	3710.8	3670.4	3650.9
75°	3664.9	3574.3	3462.8	3358.2	3291.4	3252.3	3202.2	3203.6
77.5°	2668.5	2671.3	2596.1	2488.7	2413.5	2399.6	2377.3	2354.9
80°	1655.4	1523.1	1436.7	1321.0	1236.0	1162.2	1130.2	1060.4
82.5°	763.6	596.4	462.6	349.7	268.9	210.4	183.9	150.5
85°	170.1	129.6	107.3	86.4	73.9	68.3	55.8	51.6
87.5°	23.7	20.9	19.5	18.1	15.3	11.2	8.4	6.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)