

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P148240

Luminaire Tested: **VXS-E05-LED-E1-5XQ**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P148240
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33676)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-E05-LED-E1-5XQ
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE EXTRA WIDE
Light Source: (105) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15901.9 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type V - Short - Non-Cutoff
BUG Rating: B4 - U0 - G3


Input Watts (W): 127.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



CATALOG NUMBER: VXS-E05-LED-E1-5XQ

Iso-Footcandle Lines of Horizontal Illumination

--- 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 2.4 fc
Type V - Short - Non-Cutoff

REPORT NUMBER: P148240

CATALOG NUMBER: VXS-E05-LED-E1-5XQ

Luminous Intensity Polar Plot



REPORT NUMBER: P148240

CATALOG NUMBER: VXS-E05-LED-E1-5XQ

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	7950.9	0.0	7950.9
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	7950.9	0.0	7950.9
	% Fixture	50.0	0.0	50.0
Total	Lumens	15901.9	0.0	15901.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.6	0.9
10°-20°	424.8	2.7
20°-30°	711.3	4.5
30°-40°	1084.3	6.8
40°-50°	1731.4	10.9
50°-60°	2662.2	16.7
60°-70°	3876.2	24.4
70°-80°	4366.6	27.5
80°-90°	901.4	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	15901.9	100.0
0°-180°	15901.9	100.0

Coefficient of Utilization



REPORT NUMBER: P148240


CATALOG NUMBER: VXS-E05-LED-E1-5XQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	639.8	4.0			
FM	(30°-60°)	2739.0	17.2			
FH	(60°-80°)	4121.4	25.9			G2/5000
FVH	(80°-90°)	450.7	2.8			G3/500
BL	(0°-30°)	639.8	4.0	B2/1000		
BM	(30°-60°)	2739.0	17.2	B3/5000		
BH	(60°-80°)	4121.4	25.9	B4/5000		G2/5000
BVH	(80°-90°)	450.7	2.8			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G3

Type V Short



REPORT NUMBER: P148240

CATALOG NUMBER: VXS-E05-LED-E1-5XQ

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1506.6	1506.6	1506.6	1506.6	1506.6	1506.6	1506.6	1506.6	1506.6	1506.6	1506.6
2.5°	1509.2	1510.1	1509.6	1508.8	1509.2	1508.7	1508.0	1507.6	1504.6	1506.2	1508.7
5°	1509.2	1508.4	1508.0	1507.5	1507.6	1508.8	1507.6	1506.2	1505.9	1506.6	1505.4
7.5°	1508.4	1506.7	1505.9	1505.5	1505.9	1506.3	1505.1	1503.3	1504.6	1503.3	1501.7
10°	1505.8	1504.6	1505.1	1503.3	1503.7	1503.3	1501.7	1500.4	1501.2	1500.0	1497.9
12.5°	1506.7	1504.6	1504.2	1503.3	1502.9	1502.5	1500.4	1498.3	1498.8	1497.9	1495.9
15°	1506.7	1505.5	1505.1	1503.3	1502.9	1502.1	1499.6	1498.8	1498.8	1497.5	1495.0
17.5°	1507.6	1506.6	1506.6	1504.6	1503.7	1503.3	1500.4	1499.2	1500.4	1497.9	1496.3
20°	1510.1	1509.2	1509.5	1508.4	1506.7	1506.6	1504.6	1503.7	1504.1	1503.7	1499.2
22.5°	1515.0	1514.9	1515.9	1515.4	1515.0	1515.4	1513.8	1513.7	1514.2	1514.2	1510.5
25°	1529.1	1528.7	1529.6	1529.6	1529.9	1533.0	1531.7	1531.2	1533.4	1533.4	1529.5
27.5°	1555.9	1555.0	1555.9	1556.7	1558.8	1562.5	1561.7	1562.9	1566.2	1565.4	1562.1
30°	1586.7	1585.8	1587.9	1590.4	1592.1	1597.9	1595.4	1601.7	1604.6	1607.0	1604.6
32.5°	1631.7	1631.7	1635.4	1637.1	1640.8	1646.6	1647.5	1652.4	1656.3	1660.4	1657.5
35°	1691.7	1690.8	1693.7	1696.7	1701.2	1706.6	1708.8	1715.4	1721.2	1724.1	1718.8
37.5°	1783.4	1778.8	1784.1	1785.8	1789.5	1790.9	1796.7	1805.0	1811.2	1810.4	1806.6
40°	1907.6	1906.6	1904.6	1902.1	1907.9	1910.1	1909.9	1921.2	1931.2	1929.5	1929.1
42.5°	2052.4	2048.7	2046.2	2046.2	2049.5	2050.5	2063.3	2071.7	2078.8	2080.4	2078.8
45°	2208.3	2204.6	2205.4	2203.7	2205.0	2210.4	2217.9	2233.4	2246.6	2247.0	2240.0
47.5°	2375.9	2364.1	2373.4	2360.4	2368.3	2372.4	2391.3	2413.7	2437.1	2441.2	2435.0
50°	2545.9	2544.6	2543.7	2541.2	2545.0	2554.2	2577.1	2612.4	2635.0	2650.1	2640.0
52.5°	2731.6	2725.4	2722.5	2718.3	2722.1	2740.0	2772.1	2802.9	2843.3	2860.4	2846.6
55°	2912.5	2910.4	2899.6	2899.2	2907.2	2934.9	2969.9	3007.9	3051.7	3070.9	3065.8
57.5°	3098.3	3086.2	3082.9	3077.9	3093.8	3120.0	3162.9	3231.3	3276.7	3298.3	3285.8
60°	3280.0	3270.9	3263.7	3262.1	3273.0	3309.6	3371.3	3453.3	3509.5	3537.9	3517.9
62.5°	3475.0	3469.2	3460.8	3451.2	3474.2	3521.2	3597.9	3688.7	3771.6	3806.6	3776.3
65°	3717.5	3705.4	3696.3	3684.1	3702.9	3762.1	3858.3	3986.2	4097.5	4138.3	4116.7
67.5°	3973.3	3962.1	3962.9	3955.4	3988.8	4070.8	4195.0	4368.7	4517.9	4587.5	4546.6
70°	4196.7	4202.9	4204.6	4235.0	4292.5	4417.5	4624.2	4896.3	5122.5	5228.8	5185.0
71°	4130.8	4144.6	4165.8	4197.5	4296.7	4444.6	4726.6	5056.3	5326.2	5506.2	5445.8
72.5°	3944.2	3952.5	3963.3	4011.6	4123.7	4319.6	4609.9	4986.6	5333.8	5566.6	5496.7
75°	3674.2	3682.1	3685.8	3719.6	3821.7	3992.5	4258.3	4592.5	4898.8	5097.1	5077.5
77.5°	3266.7	3268.0	3297.1	3349.2	3463.7	3659.2	3939.2	4285.8	4573.8	4727.9	4630.1
80°	2345.8	2329.9	2360.0	2427.2	2568.7	2793.0	3079.6	3475.4	3795.0	3939.2	3787.6
82.5°	892.5	940.8	1017.1	1127.9	1175.9	1425.0	1692.5	1925.0	2194.2	2495.0	2419.6
85°	95.8	108.0	135.4	167.9	212.0	293.4	405.4	553.3	682.1	801.7	711.6
87.5°	35.9	36.7	40.8	47.0	47.9	49.9	53.4	62.1	57.9	49.9	40.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P148240

CATALOG NUMBER: VXS-E05-LED-E1-5XQ

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1506.6	1506.6	1506.6	1506.6	1506.6	1506.6	1506.6	1506.6
2.5°	1506.6	1507.0	1506.6	1507.0	1507.0	1505.4	1505.8	1505.0
5°	1506.3	1505.0	1505.5	1505.9	1505.5	1506.3	1505.0	1505.9
7.5°	1504.2	1501.7	1502.6	1502.6	1501.7	1502.9	1502.1	1501.7
10°	1500.0	1496.7	1498.3	1497.5	1497.0	1497.5	1497.5	1497.5
12.5°	1496.3	1494.1	1494.5	1494.2	1493.7	1494.9	1494.5	1494.9
15°	1495.4	1492.1	1491.6	1490.8	1491.2	1492.1	1492.1	1493.4
17.5°	1494.6	1490.4	1489.9	1489.2	1489.5	1491.2	1491.6	1490.8
20°	1497.1	1493.8	1492.8	1492.1	1491.6	1493.7	1493.3	1493.4
22.5°	1508.7	1504.6	1504.1	1500.8	1499.6	1500.8	1500.0	1500.1
25°	1527.5	1522.5	1520.8	1516.3	1513.0	1513.0	1511.7	1510.9
27.5°	1561.2	1553.8	1552.1	1548.3	1543.7	1544.6	1542.1	1541.7
30°	1600.4	1593.8	1588.0	1582.5	1577.1	1575.0	1572.1	1571.6
32.5°	1651.6	1644.1	1637.1	1630.5	1622.9	1620.0	1615.0	1612.4
35°	1714.6	1704.6	1696.3	1691.6	1684.1	1680.4	1677.1	1680.8
37.5°	1802.5	1790.5	1786.2	1780.8	1775.9	1770.1	1771.2	1770.1
40°	1924.1	1913.4	1909.2	1899.6	1898.3	1891.7	1895.9	1891.7
42.5°	2074.6	2054.6	2051.6	2044.1	2041.7	2037.9	2039.6	2036.7
45°	2238.3	2220.4	2217.1	2205.0	2205.4	2196.7	2200.0	2200.0
47.5°	2422.5	2403.7	2388.3	2379.6	2376.3	2370.9	2373.8	2373.4
50°	2612.5	2587.0	2569.9	2553.0	2545.4	2547.5	2541.7	2551.7
52.5°	2816.7	2778.8	2754.6	2738.3	2724.1	2727.0	2727.9	2730.8
55°	3027.9	2979.6	2944.6	2923.3	2910.5	2911.3	2915.0	2918.3
57.5°	3240.4	3180.0	3132.5	3100.8	3092.4	3096.3	3096.3	3095.8
60°	3460.8	3388.4	3327.0	3291.2	3283.7	3281.7	3297.9	3292.4
62.5°	3697.5	3610.4	3547.2	3501.2	3490.4	3497.9	3512.5	3509.2
65°	4011.2	3890.8	3809.1	3763.7	3745.4	3753.0	3772.5	3771.6
67.5°	4415.9	4247.5	4139.6	4081.2	4067.9	4077.1	4087.9	4098.2
70°	5020.8	4780.4	4626.3	4500.0	4445.8	4435.4	4446.2	4446.6
71°	5233.8	4957.5	4712.1	4557.9	4469.2	4431.7	4434.6	4415.8
72.5°	5225.0	4884.6	4597.5	4436.3	4313.0	4282.9	4268.3	4245.8
75°	4872.8	4566.2	4317.1	4141.2	4022.5	3987.0	3961.2	3960.0
77.5°	4419.2	4193.0	3918.3	3732.0	3587.5	3528.7	3502.5	3501.8
80°	3552.5	3213.7	3012.8	2900.8	2726.2	2675.9	2622.5	2602.5
82.5°	2148.4	1678.8	1365.0	1213.0	1128.7	929.5	834.2	789.2
85°	500.4	355.4	245.0	160.8	115.9	92.1	70.9	62.5
87.5°	33.8	26.6	23.7	19.2	14.6	14.2	8.7	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)