

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P672693

Luminaire Tested: **CCP-SA-2B-740-U-5NQ**

Issue Date: 04/16/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P672693  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-2B-740-U-5NQ  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @450mA w/ 5NQ  
distribution lens  
Light Source: (32) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7186.7 lumens  
Efficiency: N/A  
Efficacy: 156.2 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B2 - U0 - G1

Input Watts (W): 46  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT


REPORT NUMBER: P672693

CATALOG NUMBER: CCP-SA-2B-740-U-5NQ

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 3.8 fc

Type V - Short - N/A

REPORT NUMBER: P672693  
CATALOG NUMBER: CCP-SA-2B-740-U-5NQ

## Luminous Intensity Polar Plot



REPORT NUMBER: P672693

CATALOG NUMBER: CCP-SA-2B-740-U-5NQ


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 3593.4   | 0.0    | 3593.4 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 3593.4   | 0.0    | 3593.4 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 7186.7   | 0.0    | 7186.7 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 81.8   | 1.1       |
| 10°-20°   | 267.2  | 3.7       |
| 20°-30°   | 506.7  | 7.1       |
| 30°-40°   | 849.8  | 11.8      |
| 40°-50°   | 1344.8 | 18.7      |
| 50°-60°   | 2112.6 | 29.4      |
| 60°-70°   | 1785.0 | 24.8      |
| 70°-80°   | 207.8  | 2.9       |
| 80°-90°   | 31.0   | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 7186.7 | 100.0     |
| 0°-180°   | 7186.7 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P672693


CATALOG NUMBER: CCP-SA-2B-740-U-5NQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 427.9  | 6.0       |                         |      |         |
| FM   | (30°-60°)   | 2153.6 | 30.0      |                         |      |         |
| FH   | (60°-80°)   | 996.4  | 13.9      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 15.5   | 0.2       |                         |      | G1/100  |
| BL   | (0°-30°)    | 427.9  | 6.0       | B1/500                  |      |         |
| BM   | (30°-60°)   | 2153.6 | 30.0      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 996.4  | 13.9      | B2/1000                 |      | G1/1800 |
| BVH  | (80°-90°)   | 15.5   | 0.2       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G1**

Type V Short





REPORT NUMBER: P672693

CATALOG NUMBER: CCP-SA-2B-740-U-5NQ

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 826.3  | 826.3  | 826.3  | 826.3  | 826.3  | 826.3  | 826.3  | 826.3  | 826.3  | 826.3  | 826.3  |
| 2.5°  | 830.9  | 828.4  | 830.9  | 830.9  | 829.4  | 829.9  | 827.9  | 827.4  | 829.9  | 827.9  | 827.4  |
| 5°    | 848.1  | 846.0  | 848.1  | 846.6  | 844.0  | 844.5  | 841.5  | 840.5  | 843.5  | 840.5  | 841.0  |
| 7.5°  | 867.8  | 864.2  | 865.2  | 866.8  | 864.2  | 864.2  | 861.7  | 860.2  | 861.7  | 858.7  | 860.7  |
| 10°   | 884.4  | 881.4  | 882.9  | 884.9  | 884.4  | 886.0  | 883.4  | 882.4  | 880.9  | 877.4  | 880.4  |
| 12.5° | 906.2  | 905.1  | 907.2  | 909.7  | 908.7  | 910.7  | 905.1  | 903.6  | 903.1  | 899.1  | 902.6  |
| 15°   | 934.4  | 931.9  | 935.5  | 938.5  | 937.0  | 940.5  | 936.0  | 933.9  | 931.4  | 926.4  | 929.4  |
| 17.5° | 962.7  | 960.7  | 965.8  | 967.3  | 967.8  | 970.8  | 967.3  | 964.2  | 963.2  | 959.7  | 957.7  |
| 20°   | 996.6  | 994.0  | 998.1  | 1001.1 | 998.6  | 1002.1 | 1000.6 | 998.6  | 997.6  | 992.0  | 991.5  |
| 22.5° | 1034.5 | 1030.9 | 1037.0 | 1040.5 | 1037.0 | 1040.5 | 1037.5 | 1037.0 | 1037.5 | 1029.4 | 1030.4 |
| 25°   | 1076.9 | 1077.4 | 1083.4 | 1086.0 | 1084.0 | 1086.0 | 1081.4 | 1084.5 | 1082.9 | 1074.4 | 1071.3 |
| 27.5° | 1131.4 | 1129.4 | 1136.0 | 1143.6 | 1138.5 | 1138.5 | 1136.5 | 1139.5 | 1139.0 | 1130.9 | 1128.9 |
| 30°   | 1195.1 | 1194.6 | 1204.2 | 1208.7 | 1201.6 | 1198.6 | 1198.1 | 1205.7 | 1206.2 | 1197.6 | 1194.1 |
| 32.5° | 1261.7 | 1261.7 | 1273.4 | 1278.9 | 1268.8 | 1266.8 | 1264.8 | 1274.9 | 1273.4 | 1261.7 | 1254.2 |
| 35°   | 1335.0 | 1332.0 | 1347.6 | 1355.7 | 1345.6 | 1339.5 | 1338.5 | 1347.6 | 1345.6 | 1329.4 | 1320.3 |
| 37.5° | 1407.2 | 1409.2 | 1427.4 | 1436.5 | 1424.4 | 1416.8 | 1419.3 | 1425.4 | 1425.9 | 1408.2 | 1398.6 |
| 40°   | 1495.6 | 1496.1 | 1518.8 | 1525.9 | 1510.3 | 1498.6 | 1502.2 | 1515.8 | 1514.8 | 1493.1 | 1481.0 |
| 42.5° | 1594.6 | 1592.6 | 1620.9 | 1626.9 | 1605.7 | 1583.5 | 1594.1 | 1615.3 | 1620.4 | 1596.1 | 1583.5 |
| 45°   | 1700.7 | 1703.7 | 1733.0 | 1739.6 | 1706.2 | 1678.0 | 1700.7 | 1732.5 | 1739.1 | 1712.8 | 1697.1 |
| 47.5° | 1829.5 | 1833.0 | 1868.4 | 1870.9 | 1833.0 | 1796.1 | 1826.5 | 1867.9 | 1870.4 | 1834.0 | 1815.8 |
| 50°   | 1976.5 | 1988.6 | 2028.0 | 2033.0 | 1995.7 | 1948.2 | 1991.6 | 2028.5 | 2018.9 | 1970.4 | 1953.7 |
| 52.5° | 2143.2 | 2152.7 | 2214.4 | 2235.6 | 2202.8 | 2151.7 | 2186.6 | 2209.3 | 2178.5 | 2114.9 | 2089.1 |
| 55°   | 2285.1 | 2301.2 | 2383.1 | 2447.7 | 2472.5 | 2434.1 | 2430.1 | 2396.7 | 2310.8 | 2213.9 | 2187.1 |
| 57.5° | 2325.0 | 2340.6 | 2467.4 | 2634.1 | 2781.1 | 2800.3 | 2711.4 | 2544.2 | 2359.3 | 2209.8 | 2182.5 |
| 60°   | 2162.9 | 2184.1 | 2369.4 | 2685.1 | 3106.9 | 3280.6 | 2959.4 | 2556.8 | 2233.6 | 2033.0 | 1998.7 |
| 62.5° | 1698.7 | 1738.1 | 1977.5 | 2472.5 | 3238.2 | 3718.1 | 3061.4 | 2339.1 | 1854.2 | 1617.3 | 1571.9 |
| 65°   | 923.8  | 957.7  | 1221.8 | 1842.6 | 2972.0 | 3811.5 | 2811.4 | 1781.0 | 1212.8 | 974.8  | 950.1  |
| 67.5° | 346.5  | 371.3  | 492.5  | 910.7  | 2101.2 | 3258.4 | 2134.1 | 1019.8 | 550.6  | 395.0  | 360.1  |
| 70°   | 147.5  | 150.5  | 178.3  | 317.2  | 955.1  | 2119.9 | 1092.5 | 346.5  | 183.9  | 148.5  | 144.5  |
| 72.5° | 106.1  | 106.6  | 114.2  | 140.4  | 290.9  | 929.9  | 330.3  | 145.5  | 112.1  | 101.0  | 101.0  |
| 75°   | 84.9   | 85.4   | 89.9   | 101.5  | 137.4  | 273.8  | 142.4  | 102.0  | 86.9   | 79.3   | 78.3   |
| 77.5° | 66.7   | 67.7   | 72.2   | 79.3   | 91.9   | 125.3  | 96.5   | 80.3   | 69.7   | 62.6   | 61.6   |
| 80°   | 49.5   | 51.0   | 57.1   | 60.6   | 64.7   | 83.3   | 70.2   | 62.6   | 55.6   | 48.0   | 46.5   |
| 82.5° | 32.8   | 34.3   | 42.4   | 45.0   | 44.4   | 52.5   | 48.5   | 48.0   | 42.4   | 31.8   | 30.3   |
| 85°   | 19.7   | 20.7   | 27.3   | 29.3   | 27.3   | 25.8   | 30.8   | 33.3   | 29.8   | 20.7   | 19.2   |
| 87.5° | 8.6    | 8.6    | 12.1   | 12.6   | 12.1   | 9.6    | 14.6   | 17.2   | 17.7   | 10.6   | 9.6    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

INVUE

Report Number: SP1-2104-224-3

Luminaire Tested: CCW-SA-2A-740-U-SL4

Test Date: 04/26/2021

### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2104-224-3  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 04/26/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: INVUE  
 Catalog Number: **CCW-SA-2A-740-U-SL4**  
 Description: INVUE WALL PACK ClearCurve Light Square

### Spectral Parameters

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 3829   | CRI (Ra): | 69.8 |      |       |
| CIE u':                   | 0.2271 | R1:       | 67.2 | R9:  | -35.1 |
| CIE v':                   | 0.5076 | R2:       | 75.2 | R10: | 43.1  |
| Duv:                      | 0.0022 | R3:       | 83.2 | R11: | 69.0  |
| CIE x:                    | 0.3900 | R4:       | 71.0 | R12: | 44.3  |
| CIE y:                    | 0.3873 | R5:       | 67.4 | R13: | 67.6  |
| CIE z:                    | 0.2227 | R6:       | 66.8 | R14: | 90.3  |
| Peak Wavelength (nm):     | 440    | R7:       | 77.6 |      |       |
| Dominant Wavelength (nm): | 578    | R8:       | 50.3 |      |       |
| Purity:                   | 33.4   |           |      |      |       |
| Rf:                       | 70.6   |           |      |      |       |
| Rg:                       | 96.7   |           |      |      |       |



### Test Conditions

Stabilization Time: 62M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.8/39%  
 Sphere Temperature (°C): 24.2

REPORT NUMBER: SP1-2104-224-3

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2104-224-3

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



REPORT NUMBER: SP1-2104-224-3

### Photopic Flux vs. Wavelength



#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 1901             | 0.0              | 490       | 14057            | 2.0              | 620       | 73853            | 19.2             | 750       | 3678             | 0.0              | 880       | 2528             | 0.0              |
| 365       | 1585             | 0.0              | 495       | 20304            | 3.7              | 625       | 68653            | 15.1             | 755       | 3385             | 0.0              | 885       | 2638             | 0.0              |
| 370       | 1604             | 0.0              | 500       | 28346            | 6.3              | 630       | 62254            | 11.3             | 760       | 2963             | 0.0              | 890       | 2417             | 0.0              |
| 375       | 1905             | 0.0              | 505       | 37228            | 10.4             | 635       | 56177            | 8.4              | 765       | 2782             | 0.0              | 895       | 1902             | 0.0              |
| 380       | 1882             | 0.0              | 510       | 46037            | 15.8             | 640       | 50521            | 6.0              | 770       | 2657             | 0.0              | 900       | 2330             | 0.0              |
| 385       | 1693             | 0.0              | 515       | 53619            | 22.2             | 645       | 45727            | 4.4              | 775       | 2259             | 0.0              | 905       | 2456             | 0.0              |
| 390       | 1640             | 0.0              | 520       | 59890            | 29.0             | 650       | 40814            | 3.0              | 780       | 2169             | 0.0              | 910       | 2205             | 0.0              |
| 395       | 1513             | 0.0              | 525       | 64946            | 34.9             | 655       | 35925            | 2.1              | 785       | 2065             | 0.0              | 915       | 2002             | 0.0              |
| 400       | 1481             | 0.0              | 530       | 69048            | 40.7             | 660       | 31824            | 1.3              | 790       | 2054             | 0.0              | 920       | 2125             | 0.0              |
| 405       | 2044             | 0.0              | 535       | 72246            | 44.8             | 665       | 27860            | 0.9              | 795       | 1908             | 0.0              | 925       | 2266             | 0.0              |
| 410       | 3966             | 0.0              | 540       | 74621            | 48.6             | 670       | 24069            | 0.5              | 800       | 2026             | 0.0              | 930       | 2159             | 0.0              |
| 415       | 8943             | 0.0              | 545       | 77288            | 51.4             | 675       | 20926            | 0.4              | 805       | 1766             | 0.0              | 935       | 2581             | 0.0              |
| 420       | 19566            | 0.1              | 550       | 80334            | 54.6             | 680       | 18170            | 0.2              | 810       | 1913             | 0.0              | 940       | 2052             | 0.0              |
| 425       | 39243            | 0.2              | 555       | 83561            | 57.1             | 685       | 15785            | 0.1              | 815       | 2019             | 0.0              | 945       | 1631             | 0.0              |
| 430       | 66113            | 0.5              | 560       | 86964            | 59.1             | 690       | 13770            | 0.1              | 820       | 1876             | 0.0              | 950       | 2301             | 0.0              |
| 435       | 92550            | 1.1              | 565       | 90264            | 60.0             | 695       | 11953            | 0.1              | 825       | 1869             | 0.0              | 955       | 3077             | 0.0              |
| 440       | 106034           | 1.7              | 570       | 93519            | 60.8             | 700       | 10452            | 0.0              | 830       | 1862             | 0.0              | 960       | 2911             | 0.0              |
| 445       | 86383            | 1.8              | 575       | 95920            | 59.7             | 705       | 9162             | 0.0              | 835       | 1663             | 0.0              | 965       | 3163             | 0.0              |
| 450       | 49216            | 1.3              | 580       | 97650            | 58.0             | 710       | 8266             | 0.0              | 840       | 1843             | 0.0              | 970       | 1995             | 0.0              |
| 455       | 27376            | 0.9              | 585       | 98486            | 54.7             | 715       | 7583             | 0.0              | 845       | 1921             | 0.0              | 975       | 2418             | 0.0              |
| 460       | 17830            | 0.7              | 590       | 98332            | 50.8             | 720       | 6750             | 0.0              | 850       | 2105             | 0.0              | 980       | 2674             | 0.0              |
| 465       | 11374            | 0.6              | 595       | 96023            | 45.5             | 725       | 5965             | 0.0              | 855       | 2096             | 0.0              | 985       | 2850             | 0.0              |
| 470       | 8344             | 0.5              | 600       | 93650            | 40.4             | 730       | 5310             | 0.0              | 860       | 2601             | 0.0              | 990       | 1972             | 0.0              |
| 475       | 7639             | 0.6              | 605       | 90313            | 35.0             | 735       | 4838             | 0.0              | 865       | 2199             | 0.0              | 995       | 2443             | 0.0              |
| 480       | 7991             | 0.8              | 610       | 85305            | 29.3             | 740       | 4280             | 0.0              | 870       | 2491             | 0.0              | 1000      | 1979             | 0.0              |
| 485       | 9994             | 1.2              | 615       | 79870            | 24.1             | 745       | 3928             | 0.0              | 875       | 2370             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-224-3

### Scotopic Flux vs. Wavelength




Scotopic Lumens: 7682.8

S/P: 1.42

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 1901             | 0.0              | 490       | 14057            | 21.6             | 620       | 73853            | 0.9              | 750       | 3678             | 0.0              | 880       | 2528             | 0.0              |
| 365       | 1585             | 0.0              | 495       | 20304            | 32.8             | 625       | 68653            | 0.6              | 755       | 3385             | 0.0              | 885       | 2638             | 0.0              |
| 370       | 1604             | 0.0              | 500       | 28346            | 47.4             | 630       | 62254            | 0.4              | 760       | 2963             | 0.0              | 890       | 2417             | 0.0              |
| 375       | 1905             | 0.0              | 505       | 37228            | 63.3             | 635       | 56177            | 0.2              | 765       | 2782             | 0.0              | 895       | 1902             | 0.0              |
| 380       | 1882             | 0.0              | 510       | 46037            | 78.0             | 640       | 50521            | 0.1              | 770       | 2657             | 0.0              | 900       | 2330             | 0.0              |
| 385       | 1693             | 0.0              | 515       | 53619            | 88.9             | 645       | 45727            | 0.1              | 775       | 2259             | 0.0              | 905       | 2456             | 0.0              |
| 390       | 1640             | 0.0              | 520       | 59890            | 95.2             | 650       | 40814            | 0.0              | 780       | 2169             | 0.0              | 910       | 2205             | 0.0              |
| 395       | 1513             | 0.0              | 525       | 64946            | 97.2             | 655       | 35925            | 0.0              | 785       | 2065             | 0.0              | 915       | 2002             | 0.0              |
| 400       | 1481             | 0.0              | 530       | 69048            | 95.2             | 660       | 31824            | 0.0              | 790       | 2054             | 0.0              | 920       | 2125             | 0.0              |
| 405       | 2044             | 0.1              | 535       | 72246            | 90.0             | 665       | 27860            | 0.0              | 795       | 1908             | 0.0              | 925       | 2266             | 0.0              |
| 410       | 3966             | 0.2              | 540       | 74621            | 82.5             | 670       | 24069            | 0.0              | 800       | 2026             | 0.0              | 930       | 2159             | 0.0              |
| 415       | 8943             | 0.9              | 545       | 77288            | 74.1             | 675       | 20926            | 0.0              | 805       | 1766             | 0.0              | 935       | 2581             | 0.0              |
| 420       | 19566            | 3.2              | 550       | 80334            | 65.7             | 680       | 18170            | 0.0              | 810       | 1913             | 0.0              | 940       | 2052             | 0.0              |
| 425       | 39243            | 9.6              | 555       | 83561            | 57.1             | 685       | 15785            | 0.0              | 815       | 2019             | 0.0              | 945       | 1631             | 0.0              |
| 430       | 66113            | 22.5             | 560       | 86964            | 48.6             | 690       | 13770            | 0.0              | 820       | 1876             | 0.0              | 950       | 2301             | 0.0              |
| 435       | 92550            | 41.4             | 565       | 90264            | 40.5             | 695       | 11953            | 0.0              | 825       | 1869             | 0.0              | 955       | 3077             | 0.0              |
| 440       | 106034           | 59.3             | 570       | 93519            | 33.0             | 700       | 10452            | 0.0              | 830       | 1862             | 0.0              | 960       | 2911             | 0.0              |
| 445       | 86383            | 57.8             | 575       | 95920            | 26.1             | 705       | 9162             | 0.0              | 835       | 1663             | 0.0              | 965       | 3163             | 0.0              |
| 450       | 49216            | 38.1             | 580       | 97650            | 20.1             | 710       | 8266             | 0.0              | 840       | 1843             | 0.0              | 970       | 1995             | 0.0              |
| 455       | 27376            | 23.9             | 585       | 98486            | 15.1             | 715       | 7583             | 0.0              | 845       | 1921             | 0.0              | 975       | 2418             | 0.0              |
| 460       | 17830            | 17.2             | 590       | 98332            | 10.9             | 720       | 6750             | 0.0              | 850       | 2105             | 0.0              | 980       | 2674             | 0.0              |
| 465       | 11374            | 12.0             | 595       | 96023            | 7.7              | 725       | 5965             | 0.0              | 855       | 2096             | 0.0              | 985       | 2850             | 0.0              |
| 470       | 8344             | 9.6              | 600       | 93650            | 5.3              | 730       | 5310             | 0.0              | 860       | 2601             | 0.0              | 990       | 1972             | 0.0              |
| 475       | 7639             | 9.6              | 605       | 90313            | 3.5              | 735       | 4838             | 0.0              | 865       | 2199             | 0.0              | 995       | 2443             | 0.0              |
| 480       | 7991             | 10.8             | 610       | 85305            | 2.3              | 740       | 4280             | 0.0              | 870       | 2491             | 0.0              | 1000      | 1979             | 0.0              |
| 485       | 9994             | 14.5             | 615       | 79870            | 1.5              | 745       | 3928             | 0.0              | 875       | 2370             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-224-3

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: 2823**
**M/P: 0.52**


| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 1901             | 0.0              | 490       | 14057            | 11.7             | 620       | 73853            | 0.1              | 750       | 3678             | 0.0              | 880       | 2528             | 0.0              |
| 365       | 1585             | 0.0              | 495       | 20304            | 16.8             | 625       | 68653            | 0.0              | 755       | 3385             | 0.0              | 885       | 2638             | 0.0              |
| 370       | 1604             | 0.0              | 500       | 28346            | 22.8             | 630       | 62254            | 0.0              | 760       | 2963             | 0.0              | 890       | 2417             | 0.0              |
| 375       | 1905             | 0.0              | 505       | 37228            | 28.6             | 635       | 56177            | 0.0              | 765       | 2782             | 0.0              | 895       | 1902             | 0.0              |
| 380       | 1882             | 0.0              | 510       | 46037            | 33.1             | 640       | 50521            | 0.0              | 770       | 2657             | 0.0              | 900       | 2330             | 0.0              |
| 385       | 1693             | 0.0              | 515       | 53619            | 35.0             | 645       | 45727            | 0.0              | 775       | 2259             | 0.0              | 905       | 2456             | 0.0              |
| 390       | 1640             | 0.0              | 520       | 59890            | 34.9             | 650       | 40814            | 0.0              | 780       | 2169             | 0.0              | 910       | 2205             | 0.0              |
| 395       | 1513             | 0.0              | 525       | 64946            | 32.9             | 655       | 35925            | 0.0              | 785       | 2065             | 0.0              | 915       | 2002             | 0.0              |
| 400       | 1481             | 0.0              | 530       | 69048            | 29.8             | 660       | 31824            | 0.0              | 790       | 2054             | 0.0              | 920       | 2125             | 0.0              |
| 405       | 2044             | 0.0              | 535       | 72246            | 26.0             | 665       | 27860            | 0.0              | 795       | 1908             | 0.0              | 925       | 2266             | 0.0              |
| 410       | 3966             | 0.2              | 540       | 74621            | 21.8             | 670       | 24069            | 0.0              | 800       | 2026             | 0.0              | 930       | 2159             | 0.0              |
| 415       | 8943             | 0.6              | 545       | 77288            | 18.0             | 675       | 20926            | 0.0              | 805       | 1766             | 0.0              | 935       | 2581             | 0.0              |
| 420       | 19566            | 2.2              | 550       | 80334            | 14.4             | 680       | 18170            | 0.0              | 810       | 1913             | 0.0              | 940       | 2052             | 0.0              |
| 425       | 39243            | 6.1              | 555       | 83561            | 11.3             | 685       | 15785            | 0.0              | 815       | 2019             | 0.0              | 945       | 1631             | 0.0              |
| 430       | 66113            | 14.0             | 560       | 86964            | 8.6              | 690       | 13770            | 0.0              | 820       | 1876             | 0.0              | 950       | 2301             | 0.0              |
| 435       | 92550            | 24.7             | 565       | 90264            | 6.3              | 695       | 11953            | 0.0              | 825       | 1869             | 0.0              | 955       | 3077             | 0.0              |
| 440       | 106034           | 35.4             | 570       | 93519            | 4.6              | 700       | 10452            | 0.0              | 830       | 1862             | 0.0              | 960       | 2911             | 0.0              |
| 445       | 86383            | 34.1             | 575       | 95920            | 3.2              | 705       | 9162             | 0.0              | 835       | 1663             | 0.0              | 965       | 3163             | 0.0              |
| 450       | 49216            | 22.7             | 580       | 97650            | 2.2              | 710       | 8266             | 0.0              | 840       | 1843             | 0.0              | 970       | 1995             | 0.0              |
| 455       | 27376            | 14.3             | 585       | 98486            | 1.5              | 715       | 7583             | 0.0              | 845       | 1921             | 0.0              | 975       | 2418             | 0.0              |
| 460       | 17830            | 10.5             | 590       | 98332            | 1.0              | 720       | 6750             | 0.0              | 850       | 2105             | 0.0              | 980       | 2674             | 0.0              |
| 465       | 11374            | 7.4              | 595       | 96023            | 0.6              | 725       | 5965             | 0.0              | 855       | 2096             | 0.0              | 985       | 2850             | 0.0              |
| 470       | 8344             | 6.0              | 600       | 93650            | 0.4              | 730       | 5310             | 0.0              | 860       | 2601             | 0.0              | 990       | 1972             | 0.0              |
| 475       | 7639             | 5.8              | 605       | 90313            | 0.2              | 735       | 4838             | 0.0              | 865       | 2199             | 0.0              | 995       | 2443             | 0.0              |
| 480       | 7991             | 6.4              | 610       | 85305            | 0.2              | 740       | 4280             | 0.0              | 870       | 2491             | 0.0              | 1000      | 1979             | 0.0              |
| 485       | 9994             | 8.2              | 615       | 79870            | 0.1              | 745       | 3928             | 0.0              | 875       | 2370             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-224-3

TM-30-18

### Summary

$R_f = 70.6$   
 $R_g = 96.7$   
 $CIE R_a = 69.8$   
 $R_g = -35.1$




### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 54 | CES51 = 84 | CES76 = 46 |
| CES02 = 61 | CES27 = 76 | CES52 = 86 | CES77 = 70 |
| CES03 = 30 | CES28 = 78 | CES53 = 71 | CES78 = 50 |
| CES04 = 70 | CES29 = 46 | CES54 = 77 | CES79 = 77 |
| CES05 = 47 | CES30 = 49 | CES55 = 76 | CES80 = 75 |
| CES06 = 50 | CES31 = 52 | CES56 = 65 | CES81 = 74 |
| CES07 = 40 | CES32 = 51 | CES57 = 62 | CES82 = 90 |
| CES08 = 39 | CES33 = 57 | CES58 = 65 | CES83 = 84 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 89 |
| CES10 = 74 | CES35 = 81 | CES60 = 90 | CES85 = 87 |
| CES11 = 57 | CES36 = 82 | CES61 = 87 | CES86 = 71 |
| CES12 = 63 | CES37 = 74 | CES62 = 73 | CES87 = 77 |
| CES13 = 42 | CES38 = 58 | CES63 = 72 | CES88 = 75 |
| CES14 = 74 | CES39 = 91 | CES64 = 70 | CES89 = 72 |
| CES15 = 71 | CES40 = 84 | CES65 = 63 | CES90 = 71 |
| CES16 = 46 | CES41 = 79 | CES66 = 65 | CES91 = 95 |
| CES17 = 49 | CES42 = 74 | CES67 = 63 | CES92 = 68 |
| CES18 = 56 | CES43 = 69 | CES68 = 70 | CES93 = 82 |
| CES19 = 72 | CES44 = 98 | CES69 = 81 | CES94 = 56 |
| CES20 = 65 | CES45 = 79 | CES70 = 59 | CES95 = 74 |
| CES21 = 86 | CES46 = 75 | CES71 = 57 | CES96 = 78 |
| CES22 = 78 | CES47 = 69 | CES72 = 85 | CES97 = 82 |
| CES23 = 92 | CES48 = 58 | CES73 = 50 | CES98 = 71 |
| CES24 = 91 | CES49 = 74 | CES74 = 91 | CES99 = 59 |
| CES25 = 72 | CES50 = 83 | CES75 = 54 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)