

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P672424

Luminaire Tested: **CCP-SA-1E-760-U-5WQ**

Issue Date: 04/16/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P672424  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-1E-760-U-5WQ  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/ 5WQ  
distribution lens  
Light Source: (16) 5700K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7330 lumens  
Efficiency: N/A  
Efficacy: 130.7 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G2


Input Watts (W): 56.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P672424

CATALOG NUMBER: CCP-SA-1E-760-U-5WQ

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 2.5 fc  
 Type V - Short - N/A

REPORT NUMBER: P672424

CATALOG NUMBER: CCP-SA-1E-760-U-5WQ

## Luminous Intensity Polar Plot



REPORT NUMBER: P672424

CATALOG NUMBER: CCP-SA-1E-760-U-5WQ

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 3665.0   | 0.0    | 3665.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 3665.0   | 0.0    | 3665.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 7330.0   | 0.0    | 7330.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 53.6   | 0.7       |
| 10°-20°   | 159.2  | 2.2       |
| 20°-30°   | 279.7  | 3.8       |
| 30°-40°   | 446.2  | 6.1       |
| 40°-50°   | 746.1  | 10.2      |
| 50°-60°   | 1276.7 | 17.4      |
| 60°-70°   | 2107.6 | 28.8      |
| 70°-80°   | 2020.1 | 27.6      |
| 80°-90°   | 240.9  | 3.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 7330.0 | 100.0     |
| 0°-180°   | 7330.0 | 100.0     |



REPORT NUMBER: P672424


CATALOG NUMBER: CCP-SA-1E-760-U-5WQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 246.2  | 3.4       |                         |      |         |
| FM   | (30°-60°)   | 1234.5 | 16.8      |                         |      |         |
| FH   | (60°-80°)   | 2063.9 | 28.2      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 120.5  | 1.6       |                         |      | G2/225  |
| BL   | (0°-30°)    | 246.2  | 3.4       | B1/500                  |      |         |
| BM   | (30°-60°)   | 1234.5 | 16.8      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 2063.9 | 28.2      | B3/2500                 |      | G2/5000 |
| BVH  | (80°-90°)   | 120.5  | 1.6       |                         |      | G2/225  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G2**

Type V Short





REPORT NUMBER: P672424

CATALOG NUMBER: CCP-SA-1E-760-U-5WQ

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 570.8  | 570.8  | 570.8  | 570.8  | 570.8  | 570.8  | 570.8  | 570.8  | 570.8  | 570.8  | 570.8  |
| 2.5°  | 567.2  | 567.2  | 568.8  | 569.3  | 568.8  | 568.2  | 567.7  | 567.2  | 568.8  | 568.2  | 568.8  |
| 5°    | 565.7  | 565.7  | 566.2  | 566.7  | 565.7  | 565.2  | 564.2  | 563.6  | 564.7  | 564.7  | 565.7  |
| 7.5°  | 561.6  | 561.1  | 561.6  | 562.1  | 560.6  | 560.1  | 558.5  | 558.5  | 558.5  | 558.0  | 559.0  |
| 10°   | 558.0  | 557.0  | 557.0  | 556.0  | 553.4  | 553.9  | 551.9  | 553.4  | 556.0  | 556.5  | 557.0  |
| 12.5° | 559.5  | 558.5  | 557.5  | 554.9  | 551.4  | 551.9  | 551.4  | 552.9  | 556.5  | 558.5  | 560.1  |
| 15°   | 566.7  | 565.7  | 563.1  | 558.5  | 556.5  | 556.5  | 555.5  | 556.0  | 561.1  | 564.2  | 565.7  |
| 17.5° | 574.4  | 572.3  | 567.7  | 564.7  | 562.6  | 564.2  | 560.6  | 560.1  | 564.2  | 568.8  | 570.3  |
| 20°   | 580.5  | 579.0  | 573.4  | 569.8  | 569.8  | 571.3  | 567.7  | 565.7  | 570.3  | 575.9  | 577.4  |
| 22.5° | 591.3  | 590.2  | 584.6  | 581.0  | 581.0  | 581.5  | 579.5  | 578.0  | 583.1  | 588.7  | 590.2  |
| 25°   | 606.6  | 606.6  | 601.0  | 599.4  | 598.9  | 600.0  | 597.4  | 595.9  | 600.5  | 604.6  | 606.1  |
| 27.5° | 624.5  | 623.0  | 618.4  | 617.3  | 619.4  | 623.0  | 618.4  | 614.3  | 617.9  | 621.4  | 621.9  |
| 30°   | 643.4  | 643.4  | 639.3  | 639.3  | 640.9  | 642.4  | 638.3  | 634.2  | 637.8  | 641.9  | 642.4  |
| 32.5° | 670.0  | 668.5  | 667.0  | 667.5  | 667.0  | 664.9  | 662.9  | 662.4  | 665.4  | 668.0  | 669.0  |
| 35°   | 702.8  | 702.2  | 700.2  | 701.2  | 701.2  | 701.2  | 695.1  | 693.0  | 698.2  | 700.2  | 699.2  |
| 37.5° | 753.4  | 752.9  | 747.8  | 744.7  | 741.1  | 739.6  | 731.9  | 731.4  | 743.7  | 749.8  | 748.8  |
| 40°   | 815.3  | 813.2  | 808.6  | 803.5  | 798.9  | 795.8  | 788.2  | 793.8  | 806.6  | 811.2  | 811.2  |
| 42.5° | 882.8  | 880.2  | 875.1  | 872.6  | 869.5  | 866.4  | 856.2  | 858.8  | 874.1  | 878.7  | 873.6  |
| 45°   | 965.7  | 962.1  | 956.4  | 950.8  | 946.2  | 940.1  | 935.0  | 937.5  | 953.9  | 959.5  | 955.4  |
| 47.5° | 1053.6 | 1052.6 | 1048.0 | 1043.4 | 1039.3 | 1035.2 | 1028.6 | 1033.2 | 1047.5 | 1046.5 | 1038.3 |
| 50°   | 1146.7 | 1148.8 | 1149.3 | 1153.9 | 1150.8 | 1151.3 | 1139.0 | 1136.5 | 1147.7 | 1141.1 | 1130.9 |
| 52.5° | 1247.0 | 1250.0 | 1260.8 | 1270.0 | 1286.9 | 1288.9 | 1273.6 | 1257.2 | 1255.1 | 1237.8 | 1227.0 |
| 55°   | 1363.1 | 1362.6 | 1386.1 | 1411.7 | 1449.0 | 1460.8 | 1426.5 | 1395.8 | 1378.9 | 1345.2 | 1333.9 |
| 57.5° | 1494.5 | 1493.0 | 1528.8 | 1573.8 | 1641.3 | 1670.5 | 1607.5 | 1549.2 | 1508.3 | 1467.9 | 1456.2 |
| 60°   | 1637.2 | 1640.8 | 1684.3 | 1757.4 | 1874.0 | 1914.4 | 1819.3 | 1722.6 | 1660.2 | 1607.5 | 1602.9 |
| 62.5° | 1804.0 | 1804.5 | 1855.6 | 1954.8 | 2106.2 | 2171.2 | 2040.3 | 1909.3 | 1830.0 | 1772.2 | 1760.0 |
| 65°   | 2000.9 | 2004.4 | 2059.2 | 2159.4 | 2333.3 | 2413.6 | 2262.7 | 2103.2 | 2009.6 | 1931.3 | 1929.8 |
| 67.5° | 2202.9 | 2200.9 | 2251.0 | 2357.4 | 2525.1 | 2599.3 | 2441.2 | 2263.3 | 2141.5 | 2043.8 | 2031.0 |
| 70°   | 2332.3 | 2343.6 | 2397.8 | 2499.6 | 2660.2 | 2732.3 | 2540.0 | 2325.1 | 2197.8 | 2108.3 | 2102.1 |
| 72.5° | 2223.4 | 2244.3 | 2314.4 | 2483.2 | 2710.8 | 2796.2 | 2516.4 | 2261.2 | 2100.6 | 2010.6 | 2010.6 |
| 75°   | 1805.0 | 1839.8 | 1937.4 | 2197.3 | 2535.9 | 2683.7 | 2329.7 | 1978.9 | 1745.1 | 1649.0 | 1649.0 |
| 77.5° | 1099.7 | 1132.9 | 1264.9 | 1582.0 | 2047.9 | 2237.2 | 1899.1 | 1490.4 | 1219.9 | 1102.2 | 1086.9 |
| 80°   | 365.7  | 387.2  | 516.6  | 804.0  | 1257.2 | 1488.9 | 1272.5 | 846.5  | 546.2  | 416.3  | 414.3  |
| 82.5° | 97.2   | 105.9  | 147.3  | 233.2  | 545.7  | 806.6  | 582.1  | 279.3  | 160.1  | 124.3  | 114.6  |
| 85°   | 33.8   | 36.3   | 62.4   | 77.7   | 138.6  | 267.0  | 162.1  | 101.3  | 77.7   | 47.1   | 44.0   |
| 87.5° | 9.7    | 10.7   | 25.1   | 27.1   | 39.9   | 31.2   | 44.0   | 40.4   | 36.8   | 15.3   | 13.8   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

INVUE

Report Number: SP1-2012-088-5-R3

Luminaire Tested: CCW-SA1A-760-U-SL2-HSS

Test Date: 01/19/2021

### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2012-088-5-R3  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 01/19/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: INVUE  
 Catalog Number: **CCW-SA1A-760-U-SL2-HSS**  
 Description: INVUE WALL PACK

\*\*\*THIS IS A REVISION OF SP1-2012-088-5-R2. TO UPDATE THE CATALOG  
 INFORMATION.\*\*\*TESTED IN SITU. INVUE WALL PACK LIGHT SQUARE T2 OPTICS 1-SQUARE WITH  
 HOUSE SIDE SHIELD

### Spectral Parameters

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 5447   | CRI (Ra): | 71.9 |      |       |
| CIE u':                   | 0.2053 | R1:       | 70.7 | R9:  | -27.5 |
| CIE v':                   | 0.4809 | R2:       | 74.8 | R10: | 41.5  |
| Duv:                      | 0.0027 | R3:       | 78.7 | R11: | 74.9  |
| CIE x:                    | 0.3337 | R4:       | 74.0 | R12: | 49.9  |
| CIE y:                    | 0.3473 | R5:       | 72.5 | R13: | 70.2  |
| CIE z:                    | 0.3190 | R6:       | 67.7 | R14: | 88.1  |
| Peak Wavelength (nm):     | 443    | R7:       | 77.7 |      |       |
| Dominant Wavelength (nm): | 556    | R8:       | 58.8 |      |       |
| Purity:                   | 4.5    |           |      |      |       |
| Rf:                       | 72.3   |           |      |      |       |
| Rg:                       | 97.2   |           |      |      |       |



### Test Conditions


Stabilization Time: 75M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.4/18%  
 Sphere Temperature (°C): 25.3

REPORT NUMBER: SP1-2012-088-5-R3

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 7/29/2020        | 1/29/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2012-088-5-R3

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-2012-088-5-R3

### Photopic Flux vs. Wavelength



#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 828              | 0.0              | 490       | 9471             | 1.3              | 620       | 23317            | 6.1              | 750       | 1157             | 0.0              | 880       | 1136             | 0.0              |
| 365       | 696              | 0.0              | 495       | 12752            | 2.3              | 625       | 21413            | 4.7              | 755       | 1067             | 0.0              | 885       | 773              | 0.0              |
| 370       | 807              | 0.0              | 500       | 16685            | 3.7              | 630       | 19344            | 3.5              | 760       | 1059             | 0.0              | 890       | 872              | 0.0              |
| 375       | 837              | 0.0              | 505       | 20565            | 5.8              | 635       | 17464            | 2.6              | 765       | 1009             | 0.0              | 895       | 891              | 0.0              |
| 380       | 757              | 0.0              | 510       | 24119            | 8.3              | 640       | 15745            | 1.9              | 770       | 774              | 0.0              | 900       | 807              | 0.0              |
| 385       | 706              | 0.0              | 515       | 27181            | 11.3             | 645       | 14060            | 1.4              | 775       | 761              | 0.0              | 905       | 899              | 0.0              |
| 390       | 746              | 0.0              | 520       | 29555            | 14.3             | 650       | 12579            | 0.9              | 780       | 653              | 0.0              | 910       | 506              | 0.0              |
| 395       | 660              | 0.0              | 525       | 31307            | 16.8             | 655       | 11181            | 0.6              | 785       | 704              | 0.0              | 915       | 598              | 0.0              |
| 400       | 671              | 0.0              | 530       | 32558            | 19.2             | 660       | 9847             | 0.4              | 790       | 663              | 0.0              | 920       | 510              | 0.0              |
| 405       | 848              | 0.0              | 535       | 33301            | 20.7             | 665       | 8641             | 0.3              | 795       | 493              | 0.0              | 925       | 874              | 0.0              |
| 410       | 1490             | 0.0              | 540       | 33727            | 22.0             | 670       | 7535             | 0.2              | 800       | 584              | 0.0              | 930       | 549              | 0.0              |
| 415       | 3203             | 0.0              | 545       | 34356            | 22.9             | 675       | 6542             | 0.1              | 805       | 739              | 0.0              | 935       | 720              | 0.0              |
| 420       | 7298             | 0.0              | 550       | 34589            | 23.5             | 680       | 5664             | 0.1              | 810       | 601              | 0.0              | 940       | 754              | 0.0              |
| 425       | 15315            | 0.1              | 555       | 34855            | 23.8             | 685       | 4962             | 0.0              | 815       | 677              | 0.0              | 945       | 931              | 0.0              |
| 430       | 27886            | 0.2              | 560       | 35083            | 23.8             | 690       | 4369             | 0.0              | 820       | 726              | 0.0              | 950       | 811              | 0.0              |
| 435       | 45485            | 0.5              | 565       | 35553            | 23.6             | 695       | 3785             | 0.0              | 825       | 693              | 0.0              | 955       | 955              | 0.0              |
| 440       | 61965            | 1.0              | 570       | 35511            | 23.1             | 700       | 3318             | 0.0              | 830       | 619              | 0.0              | 960       | 1025             | 0.0              |
| 445       | 62721            | 1.3              | 575       | 35515            | 22.1             | 705       | 2962             | 0.0              | 835       | 738              | 0.0              | 965       | 916              | 0.0              |
| 450       | 44754            | 1.2              | 580       | 35114            | 20.9             | 710       | 2689             | 0.0              | 840       | 681              | 0.0              | 970       | 695              | 0.0              |
| 455       | 26152            | 0.9              | 585       | 34546            | 19.2             | 715       | 2476             | 0.0              | 845       | 691              | 0.0              | 975       | 568              | 0.0              |
| 460       | 17101            | 0.7              | 590       | 33522            | 17.3             | 720       | 2192             | 0.0              | 850       | 710              | 0.0              | 980       | 643              | 0.0              |
| 465       | 11400            | 0.6              | 595       | 32326            | 15.3             | 725       | 1939             | 0.0              | 855       | 1025             | 0.0              | 985       | 804              | 0.0              |
| 470       | 7763             | 0.5              | 600       | 30973            | 13.3             | 730       | 1698             | 0.0              | 860       | 889              | 0.0              | 990       | 812              | 0.0              |
| 475       | 6419             | 0.5              | 605       | 29160            | 11.3             | 735       | 1533             | 0.0              | 865       | 885              | 0.0              | 995       | 496              | 0.0              |
| 480       | 6330             | 0.6              | 610       | 27373            | 9.4              | 740       | 1375             | 0.0              | 870       | 905              | 0.0              | 1000      | 659              | 0.0              |
| 485       | 7299             | 0.9              | 615       | 25423            | 7.7              | 745       | 1254             | 0.0              | 875       | 739              | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2012-088-5-R3

### Scotopic Flux vs. Wavelength



Scotopic Lumens: 1610.2

S/P: 0.74

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 828              | 0.0              | 490       | 9471             | 14.6             | 620       | 23317            | 0.3              | 750       | 1157             | 0.0              | 880       | 1136             | 0.0              |
| 365       | 696              | 0.0              | 495       | 12752            | 20.6             | 625       | 21413            | 0.2              | 755       | 1067             | 0.0              | 885       | 773              | 0.0              |
| 370       | 807              | 0.0              | 500       | 16685            | 27.9             | 630       | 19344            | 0.1              | 760       | 1059             | 0.0              | 890       | 872              | 0.0              |
| 375       | 837              | 0.0              | 505       | 20565            | 35.0             | 635       | 17464            | 0.1              | 765       | 1009             | 0.0              | 895       | 891              | 0.0              |
| 380       | 757              | 0.0              | 510       | 24119            | 40.9             | 640       | 15745            | 0.0              | 770       | 774              | 0.0              | 900       | 807              | 0.0              |
| 385       | 706              | 0.0              | 515       | 27181            | 45.1             | 645       | 14060            | 0.0              | 775       | 761              | 0.0              | 905       | 899              | 0.0              |
| 390       | 746              | 0.0              | 520       | 29555            | 47.0             | 650       | 12579            | 0.0              | 780       | 653              | 0.0              | 910       | 506              | 0.0              |
| 395       | 660              | 0.0              | 525       | 31307            | 46.8             | 655       | 11181            | 0.0              | 785       | 704              | 0.0              | 915       | 598              | 0.0              |
| 400       | 671              | 0.0              | 530       | 32558            | 44.9             | 660       | 9847             | 0.0              | 790       | 663              | 0.0              | 920       | 510              | 0.0              |
| 405       | 848              | 0.0              | 535       | 33301            | 41.5             | 665       | 8641             | 0.0              | 795       | 493              | 0.0              | 925       | 874              | 0.0              |
| 410       | 1490             | 0.1              | 540       | 33727            | 37.3             | 670       | 7535             | 0.0              | 800       | 584              | 0.0              | 930       | 549              | 0.0              |
| 415       | 3203             | 0.3              | 545       | 34356            | 32.9             | 675       | 6542             | 0.0              | 805       | 739              | 0.0              | 935       | 720              | 0.0              |
| 420       | 7298             | 1.2              | 550       | 34589            | 28.3             | 680       | 5664             | 0.0              | 810       | 601              | 0.0              | 940       | 754              | 0.0              |
| 425       | 15315            | 3.7              | 555       | 34855            | 23.8             | 685       | 4962             | 0.0              | 815       | 677              | 0.0              | 945       | 931              | 0.0              |
| 430       | 27886            | 9.5              | 560       | 35083            | 19.6             | 690       | 4369             | 0.0              | 820       | 726              | 0.0              | 950       | 811              | 0.0              |
| 435       | 45485            | 20.3             | 565       | 35553            | 16.0             | 695       | 3785             | 0.0              | 825       | 693              | 0.0              | 955       | 955              | 0.0              |
| 440       | 61965            | 34.6             | 570       | 35511            | 12.5             | 700       | 3318             | 0.0              | 830       | 619              | 0.0              | 960       | 1025             | 0.0              |
| 445       | 62721            | 42.0             | 575       | 35515            | 9.7              | 705       | 2962             | 0.0              | 835       | 738              | 0.0              | 965       | 916              | 0.0              |
| 450       | 44754            | 34.7             | 580       | 35114            | 7.2              | 710       | 2689             | 0.0              | 840       | 681              | 0.0              | 970       | 695              | 0.0              |
| 455       | 26152            | 22.9             | 585       | 34546            | 5.3              | 715       | 2476             | 0.0              | 845       | 691              | 0.0              | 975       | 568              | 0.0              |
| 460       | 17101            | 16.5             | 590       | 33522            | 3.7              | 720       | 2192             | 0.0              | 850       | 710              | 0.0              | 980       | 643              | 0.0              |
| 465       | 11400            | 12.0             | 595       | 32326            | 2.6              | 725       | 1939             | 0.0              | 855       | 1025             | 0.0              | 985       | 804              | 0.0              |
| 470       | 7763             | 8.9              | 600       | 30973            | 1.7              | 730       | 1698             | 0.0              | 860       | 889              | 0.0              | 990       | 812              | 0.0              |
| 475       | 6419             | 8.0              | 605       | 29160            | 1.1              | 735       | 1533             | 0.0              | 865       | 885              | 0.0              | 995       | 496              | 0.0              |
| 480       | 6330             | 8.5              | 610       | 27373            | 0.7              | 740       | 1375             | 0.0              | 870       | 905              | 0.0              | 1000      | 659              | 0.0              |
| 485       | 7299             | 10.6             | 615       | 25423            | 0.5              | 745       | 1254             | 0.0              | 875       | 739              | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2012-088-5-R3

### Melanopic Flux vs. Wavelength




**Melanopic Lumens: 4010.3**      **S/P: 1.85**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 828              | 0.0              | 490       | 9471             | 7.9              | 620       | 23317            | 0.0              | 750       | 1157             | 0.0              | 880       | 1136             | 0.0              |
| 365       | 696              | 0.0              | 495       | 12752            | 10.5             | 625       | 21413            | 0.0              | 755       | 1067             | 0.0              | 885       | 773              | 0.0              |
| 370       | 807              | 0.0              | 500       | 16685            | 13.4             | 630       | 19344            | 0.0              | 760       | 1059             | 0.0              | 890       | 872              | 0.0              |
| 375       | 837              | 0.0              | 505       | 20565            | 15.8             | 635       | 17464            | 0.0              | 765       | 1009             | 0.0              | 895       | 891              | 0.0              |
| 380       | 757              | 0.0              | 510       | 24119            | 17.3             | 640       | 15745            | 0.0              | 770       | 774              | 0.0              | 900       | 807              | 0.0              |
| 385       | 706              | 0.0              | 515       | 27181            | 17.8             | 645       | 14060            | 0.0              | 775       | 761              | 0.0              | 905       | 899              | 0.0              |
| 390       | 746              | 0.0              | 520       | 29555            | 17.2             | 650       | 12579            | 0.0              | 780       | 653              | 0.0              | 910       | 506              | 0.0              |
| 395       | 660              | 0.0              | 525       | 31307            | 15.9             | 655       | 11181            | 0.0              | 785       | 704              | 0.0              | 915       | 598              | 0.0              |
| 400       | 671              | 0.0              | 530       | 32558            | 14.1             | 660       | 9847             | 0.0              | 790       | 663              | 0.0              | 920       | 510              | 0.0              |
| 405       | 848              | 0.0              | 535       | 33301            | 12.0             | 665       | 8641             | 0.0              | 795       | 493              | 0.0              | 925       | 874              | 0.0              |
| 410       | 1490             | 0.1              | 540       | 33727            | 9.9              | 670       | 7535             | 0.0              | 800       | 584              | 0.0              | 930       | 549              | 0.0              |
| 415       | 3203             | 0.2              | 545       | 34356            | 8.0              | 675       | 6542             | 0.0              | 805       | 739              | 0.0              | 935       | 720              | 0.0              |
| 420       | 7298             | 0.8              | 550       | 34589            | 6.2              | 680       | 5664             | 0.0              | 810       | 601              | 0.0              | 940       | 754              | 0.0              |
| 425       | 15315            | 2.4              | 555       | 34855            | 4.7              | 685       | 4962             | 0.0              | 815       | 677              | 0.0              | 945       | 931              | 0.0              |
| 430       | 27886            | 5.9              | 560       | 35083            | 3.5              | 690       | 4369             | 0.0              | 820       | 726              | 0.0              | 950       | 811              | 0.0              |
| 435       | 45485            | 12.1             | 565       | 35553            | 2.5              | 695       | 3785             | 0.0              | 825       | 693              | 0.0              | 955       | 955              | 0.0              |
| 440       | 61965            | 20.7             | 570       | 35511            | 1.7              | 700       | 3318             | 0.0              | 830       | 619              | 0.0              | 960       | 1025             | 0.0              |
| 445       | 62721            | 24.7             | 575       | 35515            | 1.2              | 705       | 2962             | 0.0              | 835       | 738              | 0.0              | 965       | 916              | 0.0              |
| 450       | 44754            | 20.6             | 580       | 35114            | 0.8              | 710       | 2689             | 0.0              | 840       | 681              | 0.0              | 970       | 695              | 0.0              |
| 455       | 26152            | 13.7             | 585       | 34546            | 0.5              | 715       | 2476             | 0.0              | 845       | 691              | 0.0              | 975       | 568              | 0.0              |
| 460       | 17101            | 10.1             | 590       | 33522            | 0.3              | 720       | 2192             | 0.0              | 850       | 710              | 0.0              | 980       | 643              | 0.0              |
| 465       | 11400            | 7.4              | 595       | 32326            | 0.2              | 725       | 1939             | 0.0              | 855       | 1025             | 0.0              | 985       | 804              | 0.0              |
| 470       | 7763             | 5.6              | 600       | 30973            | 0.1              | 730       | 1698             | 0.0              | 860       | 889              | 0.0              | 990       | 812              | 0.0              |
| 475       | 6419             | 4.9              | 605       | 29160            | 0.1              | 735       | 1533             | 0.0              | 865       | 885              | 0.0              | 995       | 496              | 0.0              |
| 480       | 6330             | 5.1              | 610       | 27373            | 0.0              | 740       | 1375             | 0.0              | 870       | 905              | 0.0              | 1000      | 659              | 0.0              |
| 485       | 7299             | 6.0              | 615       | 25423            | 0.0              | 745       | 1254             | 0.0              | 875       | 739              | 0.0              |           |                  |                  |




### Summary

$R_f = 72.3$   
 $R_g = 97.2$   
 CIE  $R_a = 71.9$   
 $R_g = -27.5$

### Spectral Power Distribution Comparison



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 89 | CES76 = 43 |
| CES02 = 59 | CES27 = 80 | CES52 = 90 | CES77 = 64 |
| CES03 = 30 | CES28 = 77 | CES53 = 77 | CES78 = 46 |
| CES04 = 69 | CES29 = 51 | CES54 = 82 | CES79 = 74 |
| CES05 = 46 | CES30 = 61 | CES55 = 81 | CES80 = 70 |
| CES06 = 50 | CES31 = 56 | CES56 = 71 | CES81 = 72 |
| CES07 = 38 | CES32 = 52 | CES57 = 69 | CES82 = 88 |
| CES08 = 38 | CES33 = 63 | CES58 = 70 | CES83 = 83 |
| CES09 = 29 | CES34 = 63 | CES59 = 88 | CES84 = 87 |
| CES10 = 72 | CES35 = 79 | CES60 = 92 | CES85 = 83 |
| CES11 = 55 | CES36 = 93 | CES61 = 88 | CES86 = 76 |
| CES12 = 61 | CES37 = 73 | CES62 = 82 | CES87 = 75 |
| CES13 = 41 | CES38 = 70 | CES63 = 75 | CES88 = 78 |
| CES14 = 74 | CES39 = 91 | CES64 = 72 | CES89 = 76 |
| CES15 = 70 | CES40 = 83 | CES65 = 65 | CES90 = 76 |
| CES16 = 46 | CES41 = 85 | CES66 = 66 | CES91 = 89 |
| CES17 = 48 | CES42 = 71 | CES67 = 64 | CES92 = 69 |
| CES18 = 55 | CES43 = 69 | CES68 = 70 | CES93 = 82 |
| CES19 = 71 | CES44 = 98 | CES69 = 80 | CES94 = 60 |
| CES20 = 64 | CES45 = 79 | CES70 = 58 | CES95 = 72 |
| CES21 = 85 | CES46 = 79 | CES71 = 54 | CES96 = 79 |
| CES22 = 77 | CES47 = 76 | CES72 = 84 | CES97 = 84 |
| CES23 = 91 | CES48 = 69 | CES73 = 47 | CES98 = 73 |
| CES24 = 90 | CES49 = 79 | CES74 = 94 | CES99 = 62 |
| CES25 = 71 | CES50 = 87 | CES75 = 50 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)