

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: INVUE

Report Number: P869113

Luminaire Tested: EMM2-HSN-SA2B-722-U-5MQ

Issue Date: 08/22/2024

Test Information

Test Method: LM-79-2024
Report Number: P869113
Test Lab: INNOVATION CENTER(G3)
Issue Date: 5/19/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: INVUE
Catalog Number: EMM2-HSN-SA2B-722-U-5MQ
Description: EPIC MODERN SHORT HOUSING DISCRETE LED ARRAYS 100W 70CRI 2200K FIXTURE w/
TYPE V SQUARE MEDIUM DISTRIBUTION OPTIC
Light Source: (20) 2200K CCT, 70 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11467.2 lumens
Efficiency: N/A
Efficacy: 127.4 lumens/watt
Luminous Opening: Rectangular (W 0.67' x L: 0.33' x H: 0')
IES Classification: Type V - Short
BUG Rating: B3 - U0 - G2

Input Watts (W): 90
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.99
Total Harmonic Distortion (THDi): 6.20%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P869113

CATALOG NUMBER: EMM2-HSN-SA2B-722-U-5MQ

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 14.2 fc
 Type V - Short - N/A

REPORT NUMBER: P869113

CATALOG NUMBER: EMM2-HSN-SA2B-722-U-5MQ

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P869113

CATALOG NUMBER: EMM2-HSN-SA2B-722-U-5MQ

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 5733.6 | 0.0 | 5733.6 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 5733.6 | 0.0 | 5733.6 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 11467.2 | 0.0 | 11467.2 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

Coefficient of Utilization

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 137.0 | 1.2 |
| 10°-20° | 417.0 | 3.6 |
| 20°-30° | 733.6 | 6.4 |
| 30°-40° | 1186.3 | 10.3 |
| 40°-50° | 1847.9 | 16.1 |
| 50°-60° | 2702.1 | 23.6 |
| 60°-70° | 3111.6 | 27.1 |
| 70°-80° | 1270.8 | 11.1 |
| 80°-90° | 60.8 | 0.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 11467.2 | 100.0 |
| 0°-180° | 11467.2 | 100.0 |



REPORT NUMBER: P869113


CATALOG NUMBER: EMM2-HSN-SA2B-722-U-5MQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 643.8 | 5.6 | | | |
| FM (30°-60°) | 2868.2 | 25.0 | | | |
| FH (60°-80°) | 2191.2 | 19.1 | | | G2/5000 |
| FVH (80°-90°) | 30.4 | 0.3 | | | G1/100 |
| BL (0°-30°) | 643.8 | 5.6 | B2/1000 | | |
| BM (30°-60°) | 2868.2 | 25.0 | B3/5000 | | |
| BH (60°-80°) | 2191.2 | 19.1 | B3/2500 | | G2/5000 |
| BVH (80°-90°) | 30.4 | 0.3 | | | G1/100 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G2

Type V Short





REPORT NUMBER: P869113

CATALOG NUMBER: EMM2-HSN-SA2B-722-U-5MQ

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 1424.9 | 1424.9 | 1424.9 | 1424.9 | 1424.9 | 1424.9 | 1424.9 | 1424.9 | 1424.9 | 1424.9 | 1424.9 |
| 2.5° | 1429.3 | 1429.3 | 1427.1 | 1427.1 | 1422.7 | 1427.1 | 1424.9 | 1427.1 | 1424.9 | 1424.9 | 1427.1 |
| 5° | 1433.7 | 1433.7 | 1429.3 | 1431.5 | 1427.1 | 1429.3 | 1427.1 | 1431.5 | 1429.3 | 1427.1 | 1431.5 |
| 7.5° | 1440.3 | 1440.3 | 1435.9 | 1438.1 | 1433.7 | 1435.9 | 1433.7 | 1438.1 | 1435.9 | 1435.9 | 1438.1 |
| 10° | 1446.9 | 1449.1 | 1444.7 | 1442.5 | 1442.5 | 1444.7 | 1446.9 | 1449.1 | 1446.9 | 1446.9 | 1451.3 |
| 12.5° | 1457.9 | 1460.1 | 1455.7 | 1453.5 | 1453.5 | 1455.7 | 1457.9 | 1462.3 | 1455.7 | 1455.7 | 1455.7 |
| 15° | 1468.9 | 1468.9 | 1466.7 | 1464.5 | 1466.7 | 1468.9 | 1468.9 | 1473.3 | 1468.9 | 1464.5 | 1464.5 |
| 17.5° | 1473.3 | 1475.5 | 1473.3 | 1477.7 | 1479.9 | 1482.1 | 1484.3 | 1484.3 | 1477.7 | 1475.5 | 1475.5 |
| 20° | 1488.7 | 1490.9 | 1486.5 | 1488.7 | 1495.3 | 1504.1 | 1504.1 | 1504.1 | 1504.1 | 1497.5 | 1497.5 |
| 22.5° | 1515.2 | 1517.4 | 1515.2 | 1515.2 | 1524.0 | 1532.8 | 1532.8 | 1539.4 | 1530.6 | 1526.2 | 1526.2 |
| 25° | 1559.2 | 1559.2 | 1557.0 | 1559.2 | 1563.6 | 1568.0 | 1576.8 | 1581.2 | 1581.2 | 1579.0 | 1581.2 |
| 27.5° | 1612.1 | 1614.3 | 1612.1 | 1612.1 | 1609.9 | 1618.7 | 1631.9 | 1638.5 | 1640.7 | 1642.9 | 1642.9 |
| 30° | 1682.5 | 1686.9 | 1684.7 | 1686.9 | 1691.3 | 1697.9 | 1702.4 | 1704.6 | 1704.6 | 1700.2 | 1700.2 |
| 32.5° | 1759.6 | 1764.0 | 1759.6 | 1770.6 | 1786.0 | 1786.0 | 1781.6 | 1790.4 | 1783.8 | 1779.4 | 1775.0 |
| 35° | 1849.9 | 1849.9 | 1854.3 | 1858.7 | 1880.7 | 1891.7 | 1891.7 | 1887.3 | 1874.1 | 1867.5 | 1871.9 |
| 37.5° | 1953.4 | 1955.6 | 1960.0 | 1962.2 | 1982.0 | 2001.9 | 1999.7 | 1988.6 | 1973.2 | 1955.6 | 1955.6 |
| 40° | 2076.7 | 2072.3 | 2074.5 | 2090.0 | 2105.4 | 2129.6 | 2131.8 | 2116.4 | 2090.0 | 2072.3 | 2072.3 |
| 42.5° | 2189.1 | 2191.3 | 2200.1 | 2219.9 | 2255.1 | 2274.9 | 2263.9 | 2237.5 | 2208.9 | 2186.9 | 2184.6 |
| 45° | 2308.0 | 2305.8 | 2330.0 | 2371.8 | 2418.1 | 2442.3 | 2424.7 | 2387.3 | 2343.2 | 2314.6 | 2314.6 |
| 47.5° | 2429.1 | 2426.9 | 2466.5 | 2534.8 | 2594.3 | 2614.1 | 2596.5 | 2548.0 | 2488.6 | 2446.7 | 2440.1 |
| 50° | 2554.6 | 2563.4 | 2605.3 | 2702.2 | 2779.3 | 2801.3 | 2779.3 | 2715.4 | 2636.1 | 2581.1 | 2572.2 |
| 52.5° | 2697.8 | 2704.4 | 2759.4 | 2865.2 | 2959.8 | 3010.5 | 2977.5 | 2882.8 | 2781.5 | 2715.4 | 2706.6 |
| 55° | 2829.9 | 2834.3 | 2913.6 | 3041.3 | 3158.1 | 3226.3 | 3173.5 | 3052.3 | 2924.6 | 2840.9 | 2832.1 |
| 57.5° | 2922.4 | 2933.4 | 3034.7 | 3199.9 | 3349.6 | 3428.9 | 3349.6 | 3219.7 | 3050.1 | 2946.6 | 2940.0 |
| 60° | 2981.9 | 2999.5 | 3116.2 | 3323.2 | 3530.2 | 3616.1 | 3534.6 | 3354.1 | 3144.8 | 3010.5 | 3003.9 |
| 62.5° | 2951.0 | 2975.3 | 3125.0 | 3395.9 | 3684.4 | 3776.9 | 3671.2 | 3417.9 | 3133.8 | 2964.3 | 2946.6 |
| 65° | 2735.2 | 2752.8 | 2964.3 | 3343.0 | 3741.7 | 3884.8 | 3693.2 | 3347.4 | 2984.1 | 2796.9 | 2761.6 |
| 67.5° | 2288.2 | 2319.0 | 2598.7 | 3087.6 | 3618.3 | 3783.5 | 3541.2 | 3094.2 | 2655.9 | 2426.9 | 2387.3 |
| 70° | 1757.4 | 1812.5 | 2118.6 | 2649.3 | 3232.9 | 3420.1 | 3153.6 | 2611.9 | 2096.6 | 1863.1 | 1790.4 |
| 72.5° | 1015.2 | 1101.1 | 1550.4 | 2067.9 | 2572.2 | 2713.2 | 2338.8 | 1825.7 | 1391.8 | 1226.7 | 1206.8 |
| 75° | 336.9 | 367.8 | 737.8 | 1191.4 | 1640.7 | 1711.2 | 1462.3 | 1151.8 | 916.1 | 784.0 | 790.6 |
| 77.5° | 165.2 | 165.2 | 222.4 | 436.0 | 746.6 | 880.9 | 799.4 | 557.2 | 400.8 | 303.9 | 295.1 |
| 80° | 132.1 | 132.1 | 154.2 | 213.6 | 251.1 | 295.1 | 251.1 | 182.8 | 149.8 | 136.5 | 143.1 |
| 82.5° | 63.9 | 61.7 | 72.7 | 103.5 | 105.7 | 101.3 | 94.7 | 94.7 | 90.3 | 83.7 | 81.5 |
| 85° | 4.4 | 4.4 | 8.8 | 19.8 | 33.0 | 44.0 | 50.7 | 48.4 | 46.2 | 39.6 | 44.0 |
| 87.5° | 2.2 | 2.2 | 2.2 | 2.2 | 2.2 | 2.2 | 2.2 | 4.4 | 4.4 | 4.4 | 4.4 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Test Information

Test Method: LM-79-2008 Report
 Number: SP1-1908-441-10-R4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/28/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **SA1C-722-U-5WQ**
 Description: McGRAW EDISON ROADWAY AND AREA LUMINAIRE

THIS IS A REVISION OF SP1-1908-441-4-R3. TO UPDATE THE CATALOG INFORMATION.TESTED IN SITU. ROADWAY AND AREA LUMINAIRE. (1) 70 CRI, 5000K, 1050MA LIGHTSQUARE WITH 16 LEDS AND TYPE V WIDE OPTICS.

Spectral Parameters

CCT (K): 2237
 CIE u': 0.2876
 CIE v': 0.5346
 Duv: -0.0006
 CIE x: 0.5005
 CIE y: 0.4134
 CIE z: 0.0860
 Peak Wavelength (nm): 603
 Dominant Wavelength (nm): 587
 Purity: 74.5
 Rf: 69.8
 Rg: 99.2

| | | | |
|-----------|------|------|-------|
| CRI (Ra): | 72.0 | | |
| R1: | 68.9 | R9: | -17.4 |
| R2: | 83.0 | R10: | 61.3 |
| R3: | 95.2 | R11: | 59.8 |
| R4: | 66.2 | R12: | 50.5 |
| R5: | 65.9 | R13: | 71.1 |
| R6: | 76.3 | R14: | 96.9 |
| R7: | 76.7 | | |
| R8: | 43.8 | | |



Test Conditions


Stabilization Time: 71M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.7/41%
 Sphere Temperature (°C): 25.6

REPORT NUMBER: SP1-1908-441-10-R4


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/28/2019 | 12/28/2019 |
| Power Meter | IN0071 | 12/5/2018 | 12/5/2019 |
| AC Power Source | IN0063 | 12/5/2018 | 12/5/2019 |
| DC Power Source | IN0208 | 12/5/2018 | 12/5/2019 |
| Sphere Thermometer | IN0085 | 12/5/2018 | 12/5/2019 |
| Room Thermometer | IN0046 | 12/5/2018 | 12/5/2019 |

REPORT NUMBER: SP1-1908-441-10-R4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 4-step quadrangle

REPORT NUMBER: SP1-1908-441-10-R4

Photopic Flux vs. Wavelength




Photopic Lumens: 5530.5

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1768 | 0.0 | 490 | 5206 | 0.7 | 620 | 130919 | 34.1 | 750 | 8553 | 0.0 | 880 | 2713 | 0.0 |
| 365 | 1569 | 0.0 | 495 | 7286 | 1.3 | 625 | 125335 | 27.7 | 755 | 7696 | 0.0 | 885 | 2316 | 0.0 |
| 370 | 1594 | 0.0 | 500 | 10654 | 2.4 | 630 | 118388 | 21.4 | 760 | 6978 | 0.0 | 890 | 2539 | 0.0 |
| 375 | 1744 | 0.0 | 505 | 15189 | 4.2 | 635 | 111855 | 16.8 | 765 | 6377 | 0.0 | 895 | 1933 | 0.0 |
| 380 | 1659 | 0.0 | 510 | 20541 | 7.1 | 640 | 104062 | 12.4 | 770 | 5600 | 0.0 | 900 | 2216 | 0.0 |
| 385 | 1504 | 0.0 | 515 | 26492 | 11.0 | 645 | 96365 | 9.3 | 775 | 5000 | 0.0 | 905 | 2067 | 0.0 |
| 390 | 1541 | 0.0 | 520 | 32294 | 15.7 | 650 | 88651 | 6.5 | 780 | 4709 | 0.0 | 910 | 1959 | 0.0 |
| 395 | 1355 | 0.0 | 525 | 38123 | 20.5 | 655 | 81152 | 4.7 | 785 | 4305 | 0.0 | 915 | 1874 | 0.0 |
| 400 | 1243 | 0.0 | 530 | 43232 | 25.5 | 660 | 73523 | 3.1 | 790 | 4040 | 0.0 | 920 | 1484 | 0.0 |
| 405 | 1417 | 0.0 | 535 | 48012 | 29.8 | 665 | 66123 | 2.1 | 795 | 3642 | 0.0 | 925 | 1914 | 0.0 |
| 410 | 2147 | 0.0 | 540 | 52623 | 34.3 | 670 | 58677 | 1.3 | 800 | 3594 | 0.0 | 930 | 1948 | 0.0 |
| 415 | 3837 | 0.0 | 545 | 57516 | 38.3 | 675 | 52349 | 0.9 | 805 | 3190 | 0.0 | 935 | 2079 | 0.0 |
| 420 | 7159 | 0.0 | 550 | 62613 | 42.5 | 680 | 46159 | 0.5 | 810 | 3241 | 0.0 | 940 | 2263 | 0.0 |
| 425 | 12599 | 0.1 | 555 | 68554 | 46.8 | 685 | 40525 | 0.3 | 815 | 2732 | 0.0 | 945 | 1688 | 0.0 |
| 430 | 19019 | 0.2 | 560 | 75325 | 51.2 | 690 | 35615 | 0.2 | 820 | 2612 | 0.0 | 950 | 1560 | 0.0 |
| 435 | 24875 | 0.3 | 565 | 82533 | 54.9 | 695 | 31158 | 0.1 | 825 | 2966 | 0.0 | 955 | 2826 | 0.0 |
| 440 | 29103 | 0.5 | 570 | 90909 | 59.1 | 700 | 27409 | 0.1 | 830 | 2574 | 0.0 | 960 | 1477 | 0.0 |
| 445 | 29901 | 0.6 | 575 | 99621 | 62.0 | 705 | 24204 | 0.1 | 835 | 2633 | 0.0 | 965 | 1568 | 0.0 |
| 450 | 24862 | 0.6 | 580 | 108484 | 64.5 | 710 | 21558 | 0.0 | 840 | 2526 | 0.0 | 970 | 2030 | 0.0 |
| 455 | 15942 | 0.5 | 585 | 116679 | 64.8 | 715 | 19222 | 0.0 | 845 | 2631 | 0.0 | 975 | 1986 | 0.0 |
| 460 | 9916 | 0.4 | 590 | 123752 | 64.0 | 720 | 17310 | 0.0 | 850 | 2079 | 0.0 | 980 | 2540 | 0.0 |
| 465 | 7051 | 0.4 | 595 | 129324 | 61.3 | 725 | 15280 | 0.0 | 855 | 2309 | 0.0 | 985 | 1139 | 0.0 |
| 470 | 5227 | 0.3 | 600 | 134082 | 57.8 | 730 | 13282 | 0.0 | 860 | 2528 | 0.0 | 990 | 2018 | 0.0 |
| 475 | 4257 | 0.3 | 605 | 135698 | 52.6 | 735 | 11753 | 0.0 | 865 | 2121 | 0.0 | 995 | 3445 | 0.0 |
| 480 | 4052 | 0.4 | 610 | 135144 | 46.4 | 740 | 10654 | 0.0 | 870 | 2751 | 0.0 | 1000 | 3704 | 0.0 |
| 485 | 4298 | 0.5 | 615 | 134180 | 40.5 | 745 | 9451 | 0.0 | 875 | 2317 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-10-R4

Scotopic Flux vs. Wavelength




Scotopic Lumens: 4696.9

S/P: 0.85

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|----------------|-----------------------------------|-----------------------------|
| 360 | 1768 | 0.0 | 490 | 5206 | 4.3 | 620 | 130919 | 0.1 | 750 | 8553 | 0.0 | 880 | 2713 | 0.0 |
| 365 | 1569 | 0.0 | 495 | 7286 | 6.0 | 625 | 125335 | 0.1 | 755 | 7696 | 0.0 | 885 | 2316 | 0.0 |
| 370 | 1594 | 0.0 | 500 | 10654 | 8.6 | 630 | 118388 | 0.0 | 760 | 6978 | 0.0 | 890 | 2539 | 0.0 |
| 375 | 1744 | 0.0 | 505 | 15189 | 11.7 | 635 | 111855 | 0.0 | 765 | 6377 | 0.0 | 895 | 1933 | 0.0 |
| 380 | 1659 | 0.0 | 510 | 20541 | 14.7 | 640 | 104062 | 0.0 | 770 | 5600 | 0.0 | 900 | 2216 | 0.0 |
| 385 | 1504 | 0.0 | 515 | 26492 | 17.3 | 645 | 96365 | 0.0 | 775 | 5000 | 0.0 | 905 | 2067 | 0.0 |
| 390 | 1541 | 0.0 | 520 | 32294 | 18.8 | 650 | 88651 | 0.0 | 780 | 4709 | 0.0 | 910 | 1959 | 0.0 |
| 395 | 1355 | 0.0 | 525 | 38123 | 19.3 | 655 | 81152 | 0.0 | 785 | 4305 | 0.0 | 915 | 1874 | 0.0 |
| 400 | 1243 | 0.0 | 530 | 43232 | 18.7 | 660 | 73523 | 0.0 | 790 | 4040 | 0.0 | 920 | 1484 | 0.0 |
| 405 | 1417 | 0.0 | 535 | 48012 | 17.3 | 665 | 66123 | 0.0 | 795 | 3642 | 0.0 | 925 | 1914 | 0.0 |
| 410 | 2147 | 0.1 | 540 | 52623 | 15.4 | 670 | 58677 | 0.0 | 800 | 3594 | 0.0 | 930 | 1948 | 0.0 |
| 415 | 3837 | 0.3 | 545 | 57516 | 13.4 | 675 | 52349 | 0.0 | 805 | 3190 | 0.0 | 935 | 2079 | 0.0 |
| 420 | 7159 | 0.8 | 550 | 62613 | 11.2 | 680 | 46159 | 0.0 | 810 | 3241 | 0.0 | 940 | 2263 | 0.0 |
| 425 | 12599 | 2.0 | 555 | 68554 | 9.2 | 685 | 40525 | 0.0 | 815 | 2732 | 0.0 | 945 | 1688 | 0.0 |
| 430 | 19019 | 4.0 | 560 | 75325 | 7.4 | 690 | 35615 | 0.0 | 820 | 2612 | 0.0 | 950 | 1560 | 0.0 |
| 435 | 24875 | 6.6 | 565 | 82533 | 5.8 | 695 | 31158 | 0.0 | 825 | 2966 | 0.0 | 955 | 2826 | 0.0 |
| 440 | 29103 | 9.7 | 570 | 90909 | 4.4 | 700 | 27409 | 0.0 | 830 | 2574 | 0.0 | 960 | 1477 | 0.0 |
| 445 | 29901 | 11.8 | 575 | 99621 | 3.3 | 705 | 24204 | 0.0 | 835 | 2633 | 0.0 | 965 | 1568 | 0.0 |
| 450 | 24862 | 11.5 | 580 | 108484 | 2.4 | 710 | 21558 | 0.0 | 840 | 2526 | 0.0 | 970 | 2030 | 0.0 |
| 455 | 15942 | 8.4 | 585 | 116679 | 1.7 | 715 | 19222 | 0.0 | 845 | 2631 | 0.0 | 975 | 1986 | 0.0 |
| 460 | 9916 | 5.8 | 590 | 123752 | 1.2 | 720 | 17310 | 0.0 | 850 | 2079 | 0.0 | 980 | 2540 | 0.0 |
| 465 | 7051 | 4.6 | 595 | 129324 | 0.8 | 725 | 15280 | 0.0 | 855 | 2309 | 0.0 | 985 | 1139 | 0.0 |
| 470 | 5227 | 3.7 | 600 | 134082 | 0.6 | 730 | 13282 | 0.0 | 860 | 2528 | 0.0 | 990 | 2018 | 0.0 |
| 475 | 4257 | 3.3 | 605 | 135698 | 0.4 | 735 | 11753 | 0.0 | 865 | 2121 | 0.0 | 995 | 3445 | 0.0 |
| 480 | 4052 | 3.3 | 610 | 135144 | 0.2 | 740 | 10654 | 0.0 | 870 | 2751 | 0.0 | 1000 | 3704 | 0.0 |
| 485 | 4298 | 3.5 | 615 | 134180 | 0.2 | 745 | 9451 | 0.0 | 875 | 2317 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-10-R4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 1470.8 M/P: 0.27


| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 1768 | 0.0 | 490 | 5206 | 8.0 | 620 | 130919 | 1.6 | 750 | 8553 | 0.0 | 880 | 2713 | 0.0 |
| 365 | 1569 | 0.0 | 495 | 7286 | 11.8 | 625 | 125335 | 1.1 | 755 | 7696 | 0.0 | 885 | 2316 | 0.0 |
| 370 | 1594 | 0.0 | 500 | 10654 | 17.8 | 630 | 118388 | 0.7 | 760 | 6978 | 0.0 | 890 | 2539 | 0.0 |
| 375 | 1744 | 0.0 | 505 | 15189 | 25.8 | 635 | 111855 | 0.4 | 765 | 6377 | 0.0 | 895 | 1933 | 0.0 |
| 380 | 1659 | 0.0 | 510 | 20541 | 34.8 | 640 | 104062 | 0.3 | 770 | 5600 | 0.0 | 900 | 2216 | 0.0 |
| 385 | 1504 | 0.0 | 515 | 26492 | 43.9 | 645 | 96365 | 0.2 | 775 | 5000 | 0.0 | 905 | 2067 | 0.0 |
| 390 | 1541 | 0.0 | 520 | 32294 | 51.3 | 650 | 88651 | 0.1 | 780 | 4709 | 0.0 | 910 | 1959 | 0.0 |
| 395 | 1355 | 0.0 | 525 | 38123 | 57.0 | 655 | 81152 | 0.1 | 785 | 4305 | 0.0 | 915 | 1874 | 0.0 |
| 400 | 1243 | 0.0 | 530 | 43232 | 59.6 | 660 | 73523 | 0.0 | 790 | 4040 | 0.0 | 920 | 1484 | 0.0 |
| 405 | 1417 | 0.0 | 535 | 48012 | 59.8 | 665 | 66123 | 0.0 | 795 | 3642 | 0.0 | 925 | 1914 | 0.0 |
| 410 | 2147 | 0.1 | 540 | 52623 | 58.1 | 670 | 58677 | 0.0 | 800 | 3594 | 0.0 | 930 | 1948 | 0.0 |
| 415 | 3837 | 0.4 | 545 | 57516 | 55.1 | 675 | 52349 | 0.0 | 805 | 3190 | 0.0 | 935 | 2079 | 0.0 |
| 420 | 7159 | 1.2 | 550 | 62613 | 51.2 | 680 | 46159 | 0.0 | 810 | 3241 | 0.0 | 940 | 2263 | 0.0 |
| 425 | 12599 | 3.1 | 555 | 68554 | 46.9 | 685 | 40525 | 0.0 | 815 | 2732 | 0.0 | 945 | 1688 | 0.0 |
| 430 | 19019 | 6.5 | 560 | 75325 | 42.1 | 690 | 35615 | 0.0 | 820 | 2612 | 0.0 | 950 | 1560 | 0.0 |
| 435 | 24875 | 11.1 | 565 | 82533 | 37.0 | 695 | 31158 | 0.0 | 825 | 2966 | 0.0 | 955 | 2826 | 0.0 |
| 440 | 29103 | 16.3 | 570 | 90909 | 32.1 | 700 | 27409 | 0.0 | 830 | 2574 | 0.0 | 960 | 1477 | 0.0 |
| 445 | 29901 | 20.0 | 575 | 99621 | 27.1 | 705 | 24204 | 0.0 | 835 | 2633 | 0.0 | 965 | 1568 | 0.0 |
| 450 | 24862 | 19.3 | 580 | 108484 | 22.4 | 710 | 21558 | 0.0 | 840 | 2526 | 0.0 | 970 | 2030 | 0.0 |
| 455 | 15942 | 13.9 | 585 | 116679 | 17.8 | 715 | 19222 | 0.0 | 845 | 2631 | 0.0 | 975 | 1986 | 0.0 |
| 460 | 9916 | 9.6 | 590 | 123752 | 13.8 | 720 | 17310 | 0.0 | 850 | 2079 | 0.0 | 980 | 2540 | 0.0 |
| 465 | 7051 | 7.4 | 595 | 129324 | 10.3 | 725 | 15280 | 0.0 | 855 | 2309 | 0.0 | 985 | 1139 | 0.0 |
| 470 | 5227 | 6.0 | 600 | 134082 | 7.6 | 730 | 13282 | 0.0 | 860 | 2528 | 0.0 | 990 | 2018 | 0.0 |
| 475 | 4257 | 5.3 | 605 | 135698 | 5.3 | 735 | 11753 | 0.0 | 865 | 2121 | 0.0 | 995 | 3445 | 0.0 |
| 480 | 4052 | 5.5 | 610 | 135144 | 3.7 | 740 | 10654 | 0.0 | 870 | 2751 | 0.0 | 1000 | 3704 | 0.0 |
| 485 | 4298 | 6.2 | 615 | 134180 | 2.5 | 745 | 9451 | 0.0 | 875 | 2317 | 0.0 | | | |

REPORT NUMBER: SP1-1908-441-10-R4





TM-30-18

Summary

$R_f = 69.8$
 $R_g = 99.2$
 $CIE R_a = 72.0$
 $R_g = -17.4$



Color Vector Graphics




REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)




| | | | |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 56 | CES51 = 74 | CES76 = 56 |
| CES02 = 65 | CES27 = 76 | CES52 = 76 | CES77 = 81 |
| CES03 = 32 | CES28 = 83 | CES53 = 65 | CES78 = 63 |
| CES04 = 72 | CES29 = 46 | CES54 = 78 | CES79 = 84 |
| CES05 = 52 | CES30 = 48 | CES55 = 75 | CES80 = 84 |
| CES06 = 52 | CES31 = 51 | CES56 = 65 | CES81 = 63 |
| CES07 = 44 | CES32 = 51 | CES57 = 62 | CES82 = 92 |
| CES08 = 42 | CES33 = 53 | CES58 = 66 | CES83 = 83 |
| CES09 = 29 | CES34 = 70 | CES59 = 84 | CES84 = 92 |
| CES10 = 78 | CES35 = 85 | CES60 = 90 | CES85 = 81 |
| CES11 = 61 | CES36 = 78 | CES61 = 84 | CES86 = 56 |
| CES12 = 68 | CES37 = 80 | CES62 = 70 | CES87 = 78 |
| CES13 = 45 | CES38 = 53 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 84 | CES65 = 67 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 90 |
| CES17 = 51 | CES42 = 79 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 64 | CES68 = 69 | CES93 = 79 |
| CES19 = 74 | CES44 = 98 | CES69 = 80 | CES94 = 52 |
| CES20 = 68 | CES45 = 73 | CES70 = 63 | CES95 = 76 |
| CES21 = 89 | CES46 = 67 | CES71 = 63 | CES96 = 78 |
| CES22 = 81 | CES47 = 60 | CES72 = 87 | CES97 = 77 |
| CES23 = 92 | CES48 = 48 | CES73 = 56 | CES98 = 71 |
| CES24 = 92 | CES49 = 64 | CES74 = 87 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 | |



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18


Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-1908-441-10-R4

TM-30-18

Measure Comparisons



(END OF REPORT)