

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: INVUE

Report Number: P871392

Luminaire Tested: EMM2-HSN-SA1B-840-U-5WQ

Issue Date: 09/05/2024

Test Information

Test Method: LM-79-2024
Report Number: P871392
Test Lab: INNOVATION CENTER(G3)
Issue Date: 5/19/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: INVUE
Catalog Number: EMM2-HSN-SA1B-840-U-5WQ
Description: EPIC MODERN SHORT HOUSING DISCRETE LED ARRAYS 60W 80CRI 4000K FIXTURE w/ TYPE V SQUARE WIDE DISTRIBUTION OPTIC
Light Source: (10) 4000K CCT, 80 CRI LEDS
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6134.1 lumens
Efficiency: N/A
Efficacy: 139.4 lumens/watt
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
IES Classification: Type V - Short
BUG Rating: B3 - U0 - G1

Input Watts (W): 44
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.99
Total Harmonic Distortion (THDi): 6.91%
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P871392

CATALOG NUMBER: EMM2-HSN-SA1B-840-U-5WQ

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4.4 fc
 Type V - Short - N/A

REPORT NUMBER: P871392

CATALOG NUMBER: EMM2-HSN-SA1B-840-U-5WQ

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 72.5-Deg Vertical

REPORT NUMBER: P871392

CATALOG NUMBER: EMM2-HSN-SA1B-840-U-5WQ

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|--------|
| House Side | Lumens | 3067.0 | 0.0 | 3067.0 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Street Side | Lumens | 3067.0 | 0.0 | 3067.0 |
| | % Fixture | 50.0 | 0.0 | 50.0 |
| Total | Lumens | 6134.1 | 0.0 | 6134.1 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

Coefficient of Utilization

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 38.8 | 0.6 |
| 10°-20° | 129.5 | 2.1 |
| 20°-30° | 267.3 | 4.4 |
| 30°-40° | 492.0 | 8.0 |
| 40°-50° | 865.1 | 14.1 |
| 50°-60° | 1254.7 | 20.5 |
| 60°-70° | 1635.7 | 26.7 |
| 70°-80° | 1359.6 | 22.2 |
| 80°-90° | 91.3 | 1.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 6134.1 | 100.0 |
| 0°-180° | 6134.1 | 100.0 |



REPORT NUMBER: P871392


CATALOG NUMBER: EMM2-HSN-SA1B-840-U-5WQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|------|-------------|--------|-----------|-------------------------|------|---------|
| | | | | B | U | G |
| FL | (0°-30°) | 217.8 | 3.6 | | | |
| FM | (30°-60°) | 1305.9 | 21.3 | | | |
| FH | (60°-80°) | 1497.7 | 24.4 | | | G1/1800 |
| FVH | (80°-90°) | 45.6 | 0.7 | | | G1/100 |
| BL | (0°-30°) | 217.8 | 3.6 | B1/500 | | |
| BM | (30°-60°) | 1305.9 | 21.3 | B2/2500 | | |
| BH | (60°-80°) | 1497.7 | 24.4 | B3/2500 | | G1/1800 |
| BVH | (80°-90°) | 45.6 | 0.7 | | | G1/100 |
| UL | (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH | (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G1

Type V Short





REPORT NUMBER: P871392

CATALOG NUMBER: EMM2-HSN-SA1B-840-U-5WQ

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 85° | 90° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 405.0 | 405.0 | 405.0 | 405.0 | 405.0 | 405.0 | 405.0 | 405.0 | 405.0 | 405.0 | 405.0 |
| 2.5° | 403.7 | 404.3 | 404.3 | 404.3 | 405.0 | 405.6 | 406.2 | 406.9 | 408.1 | 408.8 | 408.8 |
| 5° | 405.6 | 405.0 | 404.3 | 405.6 | 405.6 | 405.6 | 406.2 | 406.9 | 406.9 | 406.9 | 407.5 |
| 7.5° | 403.7 | 404.3 | 403.7 | 403.7 | 405.6 | 406.2 | 405.6 | 405.0 | 405.0 | 405.6 | 405.6 |
| 10° | 410.7 | 410.0 | 409.4 | 409.4 | 411.3 | 411.9 | 411.3 | 410.7 | 410.7 | 411.9 | 411.9 |
| 12.5° | 426.6 | 427.8 | 424.0 | 424.0 | 426.6 | 427.8 | 425.9 | 425.3 | 425.9 | 427.2 | 427.2 |
| 15° | 451.4 | 450.7 | 448.2 | 445.6 | 448.2 | 450.1 | 447.5 | 446.3 | 446.9 | 450.1 | 447.5 |
| 17.5° | 478.7 | 479.3 | 476.8 | 474.2 | 476.2 | 478.7 | 474.9 | 471.7 | 472.3 | 473.6 | 472.3 |
| 20° | 509.2 | 508.6 | 507.9 | 507.9 | 511.8 | 514.9 | 509.2 | 501.6 | 499.7 | 498.4 | 498.4 |
| 22.5° | 531.5 | 533.4 | 534.0 | 539.7 | 548.6 | 551.8 | 544.2 | 534.0 | 526.4 | 522.6 | 520.0 |
| 25° | 566.4 | 564.5 | 563.2 | 569.6 | 583.0 | 588.7 | 579.1 | 565.2 | 557.5 | 556.9 | 558.8 |
| 27.5° | 598.2 | 598.2 | 600.8 | 607.1 | 619.8 | 625.5 | 617.3 | 603.3 | 599.5 | 599.5 | 597.6 |
| 30° | 639.5 | 637.6 | 640.2 | 651.0 | 660.5 | 664.3 | 657.3 | 647.8 | 644.6 | 644.6 | 641.4 |
| 32.5° | 687.9 | 688.5 | 692.3 | 699.3 | 708.8 | 709.5 | 706.9 | 702.5 | 700.6 | 698.7 | 701.8 |
| 35° | 761.6 | 761.6 | 760.3 | 765.4 | 768.0 | 769.2 | 770.5 | 768.6 | 768.6 | 768.6 | 766.0 |
| 37.5° | 853.1 | 848.1 | 847.4 | 843.0 | 839.8 | 843.0 | 848.7 | 855.0 | 860.1 | 857.0 | 855.7 |
| 40° | 944.0 | 941.5 | 933.9 | 926.9 | 924.3 | 925.6 | 932.6 | 946.0 | 951.7 | 951.7 | 956.8 |
| 42.5° | 1041.9 | 1036.9 | 1027.3 | 1019.1 | 1012.1 | 1014.0 | 1020.3 | 1036.9 | 1049.6 | 1055.3 | 1052.8 |
| 45° | 1129.7 | 1125.2 | 1115.7 | 1108.1 | 1103.0 | 1102.3 | 1110.6 | 1121.4 | 1138.6 | 1143.7 | 1147.5 |
| 47.5° | 1204.7 | 1201.5 | 1193.2 | 1185.6 | 1187.5 | 1188.2 | 1190.7 | 1200.2 | 1214.2 | 1221.2 | 1220.6 |
| 50° | 1265.7 | 1263.2 | 1255.5 | 1258.7 | 1263.8 | 1268.9 | 1265.7 | 1272.1 | 1281.0 | 1284.2 | 1286.7 |
| 52.5° | 1321.7 | 1317.8 | 1312.8 | 1318.5 | 1331.8 | 1342.0 | 1343.9 | 1339.5 | 1342.0 | 1343.9 | 1342.0 |
| 55° | 1377.0 | 1372.5 | 1371.3 | 1381.4 | 1401.8 | 1420.8 | 1418.9 | 1406.2 | 1403.0 | 1399.2 | 1397.3 |
| 57.5° | 1422.1 | 1418.9 | 1424.0 | 1441.2 | 1480.6 | 1506.0 | 1497.8 | 1468.5 | 1455.8 | 1446.9 | 1444.4 |
| 60° | 1450.7 | 1450.1 | 1461.5 | 1501.6 | 1561.3 | 1596.9 | 1583.6 | 1533.4 | 1504.8 | 1496.5 | 1492.7 |
| 62.5° | 1466.0 | 1466.6 | 1487.0 | 1558.2 | 1653.5 | 1701.8 | 1678.3 | 1601.4 | 1556.9 | 1548.6 | 1549.9 |
| 65° | 1480.0 | 1478.1 | 1504.8 | 1605.8 | 1753.3 | 1818.8 | 1787.0 | 1683.4 | 1618.5 | 1602.0 | 1602.0 |
| 67.5° | 1490.1 | 1492.0 | 1532.1 | 1653.5 | 1850.6 | 1944.0 | 1897.6 | 1770.5 | 1684.7 | 1659.9 | 1656.7 |
| 70° | 1361.7 | 1380.2 | 1505.4 | 1685.3 | 1927.5 | 2054.7 | 1993.6 | 1823.9 | 1687.2 | 1616.6 | 1609.6 |
| 72.5° | 1034.3 | 1051.5 | 1322.3 | 1628.7 | 1966.9 | 2128.4 | 2029.2 | 1755.9 | 1533.4 | 1443.7 | 1417.0 |
| 75° | 682.1 | 694.2 | 985.4 | 1422.7 | 1857.6 | 2058.5 | 1848.0 | 1512.4 | 1207.2 | 1090.9 | 1097.9 |
| 77.5° | 303.9 | 342.7 | 628.1 | 1110.0 | 1530.2 | 1656.7 | 1409.4 | 1031.8 | 737.4 | 624.3 | 612.2 |
| 80° | 127.1 | 139.2 | 237.1 | 591.9 | 886.8 | 848.7 | 600.1 | 345.8 | 220.0 | 171.0 | 165.3 |
| 82.5° | 36.9 | 38.1 | 47.0 | 102.4 | 180.5 | 212.3 | 127.8 | 64.8 | 61.7 | 49.0 | 45.1 |
| 85° | 2.5 | 2.5 | 3.8 | 6.4 | 8.9 | 14.6 | 16.5 | 19.1 | 21.6 | 18.4 | 18.4 |
| 87.5° | 1.3 | 1.3 | 1.3 | 1.9 | 1.9 | 2.5 | 1.9 | 1.9 | 1.9 | 1.9 | 1.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269




Test Information

Test Method: LM-79-2019
 Report Number: SP1-2309-178-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 09/22/2023
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGRAW-EDISON
 Catalog Number: **GALN-SA2A-840-U-T4W**
 Description: GALLEON 2 AREA AND ROADWAY LUMINAIRE. (2) 80 CRI, 4000K, 615MA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV WIDE OPTICS

LIGHTSQUARES WITH 16 LEDS EACH AND TYPE IV WIDE OPTICS

Spectral Parameters

| | | | | | |
|---------------------------|--------|-----------|------|------|------|
| CCT (K): | 3867 | CRI (Ra): | 79.8 | R9: | -8.6 |
| CIE u': | 0.2254 | R1: | 76.6 | R10: | 66.3 |
| CIE v': | 0.5090 | R2: | 84.7 | R11: | 80.5 |
| Duv: | 0.0039 | R3: | 93.7 | R12: | 67.3 |
| CIE x: | 0.3895 | R4: | 80.6 | R13: | 77.9 |
| CIE y: | 0.3908 | R5: | 77.9 | R14: | 96.6 |
| CIE z: | 0.2197 | R6: | 81.2 | | |
| Peak Wavelength (nm): | 593 | R7: | 84.2 | | |
| Dominant Wavelength (nm): | 577 | R8: | 59.0 | | |
| Purity: | 34.3 | | | | |
| Rf: | 82.7 | | | | |
| Rg: | 96.5 | | | | |



Test Conditions


Stabilization Time: 25M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 24.8/46%
 Sphere Temperature (°C): 24.7

REPORT NUMBER: SP1-2309-178-2

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | 76INCH SPHERE IN0058 | 8/9/2023 | 2/9/2024 |
| Power Meter | XITRON 2801 IN0071 | 11/29/2022 | 11/29/2023 |
| AC Power Source | CHROMA 61603 IN0063 | 11/28/2022 | 11/28/2023 |
| DC Power Source | AGILENT E3634A IN0208 | 11/28/2022 | 11/28/2023 |
| Sphere Thermometer | ONSET IN0085 | 11/28/2022 | 11/28/2023 |
| Room Thermometer | ONSET IN0046 | 11/28/2022 | 11/28/2023 |

REPORT NUMBER: SP1-2309-178-2

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2309-178-2

Photopic Flux vs. Wavelength



#####

| λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) | λ (nm) | Power ($\mu\text{W}/\text{nm}$) | Lumens (ϕ/nm) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360 | 3123 | NR | 490 | 57459 | NR | 620 | 129941 | NR | 750 | 5858 | NR | 880 | 4622 | NR |
| 365 | 3041 | NR | 495 | 69038 | NR | 625 | 121678 | NR | 755 | 5395 | NR | 885 | 3949 | NR |
| 370 | 2965 | NR | 500 | 79493 | NR | 630 | 112252 | NR | 760 | 5011 | NR | 890 | 4035 | NR |
| 375 | 3195 | NR | 505 | 87950 | NR | 635 | 102369 | NR | 765 | 4514 | NR | 895 | 3391 | NR |
| 380 | 3028 | NR | 510 | 94704 | NR | 640 | 93616 | NR | 770 | 4375 | NR | 900 | 3268 | NR |
| 385 | 2738 | NR | 515 | 100214 | NR | 645 | 84211 | NR | 775 | 3450 | NR | 905 | 2767 | NR |
| 390 | 2690 | NR | 520 | 103961 | NR | 650 | 75380 | NR | 780 | 3547 | NR | 910 | 3391 | NR |
| 395 | 2604 | NR | 525 | 106854 | NR | 655 | 66946 | NR | 785 | 3648 | NR | 915 | 3784 | NR |
| 400 | 2384 | NR | 530 | 109533 | NR | 660 | 59483 | NR | 790 | 3081 | NR | 920 | 3790 | NR |
| 405 | 3031 | NR | 535 | 112417 | NR | 665 | 51858 | NR | 795 | 3104 | NR | 925 | 3175 | NR |
| 410 | 5239 | NR | 540 | 115725 | NR | 670 | 44882 | NR | 800 | 3444 | NR | 930 | 3642 | NR |
| 415 | 10499 | NR | 545 | 119091 | NR | 675 | 38742 | NR | 805 | 3315 | NR | 935 | 3040 | NR |
| 420 | 20790 | NR | 550 | 122884 | NR | 680 | 33597 | NR | 810 | 3022 | NR | 940 | 4039 | NR |
| 425 | 39276 | NR | 555 | 128300 | NR | 685 | 29101 | NR | 815 | 2832 | NR | 945 | 4797 | NR |
| 430 | 66418 | NR | 560 | 133274 | NR | 690 | 24855 | NR | 820 | 3142 | NR | 950 | 4945 | NR |
| 435 | 101961 | NR | 565 | 139112 | NR | 695 | 21367 | NR | 825 | 3115 | NR | 955 | 3757 | NR |
| 440 | 134023 | NR | 570 | 144467 | NR | 700 | 18479 | NR | 830 | 2520 | NR | 960 | 4539 | NR |
| 445 | 129385 | NR | 575 | 149331 | NR | 705 | 16131 | NR | 835 | 2783 | NR | 965 | 4857 | NR |
| 450 | 90434 | NR | 580 | 154784 | NR | 710 | 14388 | NR | 840 | 3364 | NR | 970 | 4463 | NR |
| 455 | 63521 | NR | 585 | 156899 | NR | 715 | 12865 | NR | 845 | 3807 | NR | 975 | 3718 | NR |
| 460 | 48429 | NR | 590 | 157796 | NR | 720 | 11277 | NR | 850 | 2907 | NR | 980 | 3955 | NR |
| 465 | 36445 | NR | 595 | 157849 | NR | 725 | 10063 | NR | 855 | 3470 | NR | 985 | 4314 | NR |
| 470 | 31953 | NR | 600 | 155418 | NR | 730 | 8942 | NR | 860 | 3820 | NR | 990 | 4478 | NR |
| 475 | 32768 | NR | 605 | 151601 | NR | 735 | 7722 | NR | 865 | 3922 | NR | 995 | 2959 | NR |
| 480 | 37631 | NR | 610 | 146416 | NR | 740 | 6964 | NR | 870 | 4061 | NR | 1000 | 4570 | NR |
| 485 | 46354 | NR | 615 | 139241 | NR | 745 | 6117 | NR | 875 | 3975 | NR | | | |

REPORT NUMBER: SP1-2309-178-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: 14236

S/P: 1.59

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3123 | NR | 490 | 57459 | NR | 620 | 129941 | NR | 750 | 5858 | NR | 880 | 4622 | NR |
| 365 | 3041 | NR | 495 | 69038 | NR | 625 | 121678 | NR | 755 | 5395 | NR | 885 | 3949 | NR |
| 370 | 2965 | NR | 500 | 79493 | NR | 630 | 112252 | NR | 760 | 5011 | NR | 890 | 4035 | NR |
| 375 | 3195 | NR | 505 | 87950 | NR | 635 | 102369 | NR | 765 | 4514 | NR | 895 | 3391 | NR |
| 380 | 3028 | NR | 510 | 94704 | NR | 640 | 93616 | NR | 770 | 4375 | NR | 900 | 3268 | NR |
| 385 | 2738 | NR | 515 | 100214 | NR | 645 | 84211 | NR | 775 | 3450 | NR | 905 | 2767 | NR |
| 390 | 2690 | NR | 520 | 103961 | NR | 650 | 75380 | NR | 780 | 3547 | NR | 910 | 3391 | NR |
| 395 | 2604 | NR | 525 | 106854 | NR | 655 | 66946 | NR | 785 | 3648 | NR | 915 | 3784 | NR |
| 400 | 2384 | NR | 530 | 109533 | NR | 660 | 59483 | NR | 790 | 3081 | NR | 920 | 3790 | NR |
| 405 | 3031 | NR | 535 | 112417 | NR | 665 | 51858 | NR | 795 | 3104 | NR | 925 | 3175 | NR |
| 410 | 5239 | NR | 540 | 115725 | NR | 670 | 44882 | NR | 800 | 3444 | NR | 930 | 3642 | NR |
| 415 | 10499 | NR | 545 | 119091 | NR | 675 | 38742 | NR | 805 | 3315 | NR | 935 | 3040 | NR |
| 420 | 20790 | NR | 550 | 122884 | NR | 680 | 33597 | NR | 810 | 3022 | NR | 940 | 4039 | NR |
| 425 | 39276 | NR | 555 | 128300 | NR | 685 | 29101 | NR | 815 | 2832 | NR | 945 | 4797 | NR |
| 430 | 66418 | NR | 560 | 133274 | NR | 690 | 24855 | NR | 820 | 3142 | NR | 950 | 4945 | NR |
| 435 | 101961 | NR | 565 | 139112 | NR | 695 | 21367 | NR | 825 | 3115 | NR | 955 | 3757 | NR |
| 440 | 134023 | NR | 570 | 144467 | NR | 700 | 18479 | NR | 830 | 2520 | NR | 960 | 4539 | NR |
| 445 | 129385 | NR | 575 | 149331 | NR | 705 | 16131 | NR | 835 | 2783 | NR | 965 | 4857 | NR |
| 450 | 90434 | NR | 580 | 154784 | NR | 710 | 14388 | NR | 840 | 3364 | NR | 970 | 4463 | NR |
| 455 | 63521 | NR | 585 | 156899 | NR | 715 | 12865 | NR | 845 | 3807 | NR | 975 | 3718 | NR |
| 460 | 48429 | NR | 590 | 157796 | NR | 720 | 11277 | NR | 850 | 2907 | NR | 980 | 3955 | NR |
| 465 | 36445 | NR | 595 | 157849 | NR | 725 | 10063 | NR | 855 | 3470 | NR | 985 | 4314 | NR |
| 470 | 31953 | NR | 600 | 155418 | NR | 730 | 8942 | NR | 860 | 3820 | NR | 990 | 4478 | NR |
| 475 | 32768 | NR | 605 | 151601 | NR | 735 | 7722 | NR | 865 | 3922 | NR | 995 | 2959 | NR |
| 480 | 37631 | NR | 610 | 146416 | NR | 740 | 6964 | NR | 870 | 4061 | NR | 1000 | 4570 | NR |
| 485 | 46354 | NR | 615 | 139241 | NR | 745 | 6117 | NR | 875 | 3975 | NR | | | |

REPORT NUMBER: SP1-2309-178-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: 5542.6 M/P: 0.62

| λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) | λ (nm) | Power (µW/nm) | Lumens (φ/nm) |
|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|--------|---------------|---------------|
| 360 | 3123 | NR | 490 | 57459 | NR | 620 | 129941 | NR | 750 | 5858 | NR | 880 | 4622 | NR |
| 365 | 3041 | NR | 495 | 69038 | NR | 625 | 121678 | NR | 755 | 5395 | NR | 885 | 3949 | NR |
| 370 | 2965 | NR | 500 | 79493 | NR | 630 | 112252 | NR | 760 | 5011 | NR | 890 | 4035 | NR |
| 375 | 3195 | NR | 505 | 87950 | NR | 635 | 102369 | NR | 765 | 4514 | NR | 895 | 3391 | NR |
| 380 | 3028 | NR | 510 | 94704 | NR | 640 | 93616 | NR | 770 | 4375 | NR | 900 | 3268 | NR |
| 385 | 2738 | NR | 515 | 100214 | NR | 645 | 84211 | NR | 775 | 3450 | NR | 905 | 2767 | NR |
| 390 | 2690 | NR | 520 | 103961 | NR | 650 | 75380 | NR | 780 | 3547 | NR | 910 | 3391 | NR |
| 395 | 2604 | NR | 525 | 106854 | NR | 655 | 66946 | NR | 785 | 3648 | NR | 915 | 3784 | NR |
| 400 | 2384 | NR | 530 | 109533 | NR | 660 | 59483 | NR | 790 | 3081 | NR | 920 | 3790 | NR |
| 405 | 3031 | NR | 535 | 112417 | NR | 665 | 51858 | NR | 795 | 3104 | NR | 925 | 3175 | NR |
| 410 | 5239 | NR | 540 | 115725 | NR | 670 | 44882 | NR | 800 | 3444 | NR | 930 | 3642 | NR |
| 415 | 10499 | NR | 545 | 119091 | NR | 675 | 38742 | NR | 805 | 3315 | NR | 935 | 3040 | NR |
| 420 | 20790 | NR | 550 | 122884 | NR | 680 | 33597 | NR | 810 | 3022 | NR | 940 | 4039 | NR |
| 425 | 39276 | NR | 555 | 128300 | NR | 685 | 29101 | NR | 815 | 2832 | NR | 945 | 4797 | NR |
| 430 | 66418 | NR | 560 | 133274 | NR | 690 | 24855 | NR | 820 | 3142 | NR | 950 | 4945 | NR |
| 435 | 101961 | NR | 565 | 139112 | NR | 695 | 21367 | NR | 825 | 3115 | NR | 955 | 3757 | NR |
| 440 | 134023 | NR | 570 | 144467 | NR | 700 | 18479 | NR | 830 | 2520 | NR | 960 | 4539 | NR |
| 445 | 129385 | NR | 575 | 149331 | NR | 705 | 16131 | NR | 835 | 2783 | NR | 965 | 4857 | NR |
| 450 | 90434 | NR | 580 | 154784 | NR | 710 | 14388 | NR | 840 | 3364 | NR | 970 | 4463 | NR |
| 455 | 63521 | NR | 585 | 156899 | NR | 715 | 12865 | NR | 845 | 3807 | NR | 975 | 3718 | NR |
| 460 | 48429 | NR | 590 | 157796 | NR | 720 | 11277 | NR | 850 | 2907 | NR | 980 | 3955 | NR |
| 465 | 36445 | NR | 595 | 157849 | NR | 725 | 10063 | NR | 855 | 3470 | NR | 985 | 4314 | NR |
| 470 | 31953 | NR | 600 | 155418 | NR | 730 | 8942 | NR | 860 | 3820 | NR | 990 | 4478 | NR |
| 475 | 32768 | NR | 605 | 151601 | NR | 735 | 7722 | NR | 865 | 3922 | NR | 995 | 2959 | NR |
| 480 | 37631 | NR | 610 | 146416 | NR | 740 | 6964 | NR | 870 | 4061 | NR | 1000 | 4570 | NR |
| 485 | 46354 | NR | 615 | 139241 | NR | 745 | 6117 | NR | 875 | 3975 | NR | | | |

REPORT NUMBER: SP1-2309-178-2




TM-30-18

Summary

$R_f = 82.7$
 $R_g = 96.5$
 CIE $R_a = 79.8$
 $R_g = -8.6$



Color Vector Graphics



REPORT NUMBER: SP1-2309-178-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 76 | CES51 = 94 | CES76 = 73 |
| CES02 = 61 | CES27 = 91 | CES52 = 94 | CES77 = 85 |
| CES03 = 31 | CES28 = 90 | CES53 = 86 | CES78 = 73 |
| CES04 = 69 | CES29 = 73 | CES54 = 88 | CES79 = 91 |
| CES05 = 48 | CES30 = 76 | CES55 = 88 | CES80 = 89 |
| CES06 = 50 | CES31 = 77 | CES56 = 81 | CES81 = 80 |
| CES07 = 40 | CES32 = 74 | CES57 = 80 | CES82 = 95 |
| CES08 = 39 | CES33 = 78 | CES58 = 82 | CES83 = 92 |
| CES09 = 29 | CES34 = 84 | CES59 = 91 | CES84 = 92 |
| CES10 = 74 | CES35 = 92 | CES60 = 96 | CES85 = 85 |
| CES11 = 57 | CES36 = 97 | CES61 = 92 | CES86 = 73 |
| CES12 = 63 | CES37 = 89 | CES62 = 90 | CES87 = 85 |
| CES13 = 42 | CES38 = 83 | CES63 = 83 | CES88 = 83 |
| CES14 = 74 | CES39 = 95 | CES64 = 83 | CES89 = 77 |
| CES15 = 71 | CES40 = 91 | CES65 = 77 | CES90 = 82 |
| CES16 = 47 | CES41 = 90 | CES66 = 82 | CES91 = 91 |
| CES17 = 49 | CES42 = 90 | CES67 = 80 | CES92 = 68 |
| CES18 = 56 | CES43 = 86 | CES68 = 83 | CES93 = 82 |
| CES19 = 71 | CES44 = 99 | CES69 = 90 | CES94 = 61 |
| CES20 = 65 | CES45 = 91 | CES70 = 77 | CES95 = 76 |
| CES21 = 86 | CES46 = 87 | CES71 = 77 | CES96 = 82 |
| CES22 = 78 | CES47 = 85 | CES72 = 92 | CES97 = 89 |
| CES23 = 91 | CES48 = 77 | CES73 = 71 | CES98 = 81 |
| CES24 = 90 | CES49 = 87 | CES74 = 97 | CES99 = 70 |
| CES25 = 71 | CES50 = 93 | CES75 = 76 | |



REPORT NUMBER: SP1-2309-178-2

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2309-178-2

TM-30-18

Measure Comparisons



(END OF REPORT)