

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P188929

Luminaire Tested: **L80808NF9035AH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P188929
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27058)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: L80808NF9035AH
Description: HALO TRACK L LED 08, 850 LM, NARROW FLOOD, ALUMINIUM HAZE

Light Source: EATON LED 3500K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1009.4 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 0.36 / 0.36 / 0.38
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 11.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P188929

CATALOG NUMBER: L80808NF9035AH

Luminous Intensity Polar Plot





TEST NUMBER: P188929

CATALOG NUMBER: L80808NF9035AH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	113	111	109	108	107	105	104	103	102	101	100	99	98	97			
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93			
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90			
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88			
5	102	96	92	89	100	95	91	88	93	90	88	92	89	87	90	88	86	85			
6	99	93	88	86	97	92	88	85	91	87	85	89	86	84	88	86	84	83			
7	96	90	86	83	95	89	85	83	88	85	82	87	84	82	86	83	81	80			
8	94	87	83	80	93	87	83	80	86	82	80	85	82	80	84	81	79	78			
9	91	85	81	78	90	84	80	78	83	80	78	83	80	77	82	79	77	76			
10	89	82	79	76	88	82	78	76	81	78	76	81	78	75	80	77	75	74			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1160017
5°	1025421
10°	635704
15°	331534
20°	195480
25°	71956
30°	25092
35°	6264
40°	3521
45°	2419
50°	2286
55°	2141
60°	1974
65°	2335
70°	2116
75°	1864
80°	1389
85°	0



TEST NUMBER: P188929

CATALOG NUMBER: L80808NF9035AH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	385.1	38.2
10°-20°	424.3	42.0
20°-30°	159.3	15.8
30°-40°	21.6	2.1
40°-50°	6.7	0.7
50°-60°	5.0	0.5
60°-70°	4.3	0.4
70°-80°	2.6	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	968.7	96.0
0°-40°	990.3	98.1
0°-60°	1002.0	99.3
0°-90°	1009.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1009.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5290	
5°	4658	385
15°	1460	424
25°	297	159
35°	23	22
45°	8	7
55°	6	5
65°	4	4
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P188929

CATALOG NUMBER: L80808NF9035AH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5290.1
1°	5245.5
2°	5163.1
3°	5046.1
4°	4883.5
5°	4658.5
6°	4378.9
7°	4051.4
8°	3663.7
9°	3257.1
10°	2855.0
11°	2485.2
12°	2164.4
13°	1883.7
14°	1655.3
15°	1460.4
16°	1305.5
17°	1174.1
18°	1063.8
19°	955.8
20°	837.7
21°	714.0
22°	594.8
23°	482.3
24°	383.2
25°	297.4
26°	237.3
27°	197.2
28°	162.6
29°	129.2
30°	99.1
32.5°	49.0
35°	23.4
37.5°	15.6
40°	12.3
42.5°	10.0
45°	7.8
47.5°	7.8
50°	6.7
52.5°	5.6
55°	5.6
57.5°	5.6
60°	4.5
62.5°	4.5
65°	4.5



TEST NUMBER: P188929

CATALOG NUMBER: L80808NF9035AH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	4.5
70°	3.3
72.5°	3.3
75°	2.2
77.5°	2.2
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)