

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P148245

Luminaire Tested: **VXS-F05-LED-E1-5XQ**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P148245
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33676)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-F05-LED-E1-5XQ
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE EXTRA WIDE
Light Source: (35) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13127.4 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type V - Short - Non-Cutoff
BUG Rating: B4 - U0 - G3

Input Watts (W): 133.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P148245

CATALOG NUMBER: VXS-F05-LED-E1-5XQ

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 3.1 fc
 Type V - Short - Non-Cutoff

REPORT NUMBER: P148245

CATALOG NUMBER: VXS-F05-LED-E1-5XQ

Luminous Intensity Polar Plot



REPORT NUMBER: P148245

CATALOG NUMBER: VXS-F05-LED-E1-5XQ

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	6563.7	0.0	6563.7
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	6563.7	0.0	6563.7
	% Fixture	50.0	0.0	50.0
Total	Lumens	13127.4	0.0	13127.4
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.5	0.9
10°-20°	350.6	2.7
20°-30°	587.2	4.5
30°-40°	895.2	6.8
40°-50°	1429.4	10.9
50°-60°	2197.7	16.7
60°-70°	3199.9	24.4
70°-80°	3604.7	27.5
80°-90°	744.1	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	13127.4	100.0
0°-180°	13127.4	100.0



REPORT NUMBER: P148245


CATALOG NUMBER: VXS-F05-LED-E1-5XQ

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	528.2	4.0			
FM	(30°-60°)	2261.1	17.2			
FH	(60°-80°)	3402.3	25.9			G2/5000
FVH	(80°-90°)	372.1	2.8			G3/500
BL	(0°-30°)	528.2	4.0	B2/1000		
BM	(30°-60°)	2261.1	17.2	B2/2500		
BH	(60°-80°)	3402.3	25.9	B4/5000		G2/5000
BVH	(80°-90°)	372.1	2.8			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G3

Type V Short



REPORT NUMBER: P148245

CATALOG NUMBER: VXS-F05-LED-E1-5XQ

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1243.8	1243.8	1243.8	1243.8	1243.8	1243.8	1243.8	1243.8	1243.8	1243.8	1243.8
2.5°	1245.8	1246.5	1246.2	1245.5	1245.8	1245.5	1244.8	1244.5	1242.1	1243.4	1245.5
5°	1245.8	1245.2	1244.8	1244.5	1244.5	1245.5	1244.5	1243.4	1243.1	1243.8	1242.8
7.5°	1245.2	1243.8	1243.1	1242.8	1243.1	1243.4	1242.4	1241.0	1242.1	1241.0	1239.7
10°	1243.1	1242.1	1242.4	1241.0	1241.3	1241.0	1239.7	1238.7	1239.3	1238.3	1236.6
12.5°	1243.7	1242.1	1241.8	1241.0	1240.7	1240.4	1238.7	1236.9	1237.2	1236.6	1234.8
15°	1243.7	1242.8	1242.5	1241.0	1240.6	1240.0	1237.9	1237.2	1237.2	1236.3	1234.2
17.5°	1244.6	1243.7	1243.7	1242.1	1241.3	1241.0	1238.7	1237.6	1238.7	1236.6	1235.2
20°	1246.5	1245.8	1246.2	1245.2	1243.8	1243.8	1242.1	1241.5	1241.7	1241.5	1237.6
22.5°	1250.7	1250.7	1251.4	1251.0	1250.7	1251.0	1249.6	1249.6	1249.9	1249.9	1246.8
25°	1262.4	1262.0	1262.7	1262.7	1263.0	1265.5	1264.5	1264.0	1265.8	1265.8	1262.7
27.5°	1284.4	1283.7	1284.5	1285.1	1286.8	1289.8	1289.2	1290.3	1293.1	1292.3	1289.5
30°	1309.8	1309.1	1310.9	1313.0	1314.3	1319.2	1317.1	1322.3	1324.6	1326.7	1324.6
32.5°	1346.9	1346.9	1350.1	1351.4	1354.6	1359.4	1360.0	1364.1	1367.3	1370.8	1368.3
35°	1396.5	1395.8	1398.2	1400.6	1404.5	1408.9	1410.6	1416.2	1420.9	1423.3	1418.9
37.5°	1472.1	1468.4	1472.8	1474.3	1477.4	1478.3	1483.2	1490.1	1495.2	1494.5	1491.4
40°	1574.7	1574.0	1572.2	1570.2	1575.0	1576.8	1576.8	1586.0	1594.3	1593.0	1592.5
42.5°	1694.4	1691.3	1689.2	1689.2	1691.9	1692.6	1703.3	1710.3	1716.1	1717.4	1716.1
45°	1823.0	1819.9	1820.6	1819.3	1820.3	1824.8	1830.9	1843.6	1854.7	1855.0	1849.1
47.5°	1961.2	1951.7	1959.3	1948.6	1955.1	1958.5	1974.1	1992.6	2011.8	2015.3	2010.2
50°	2101.7	2100.6	2099.9	2097.8	2100.9	2108.5	2127.5	2156.7	2175.2	2187.7	2179.4
52.5°	2255.0	2249.8	2247.5	2244.0	2247.2	2262.0	2288.4	2313.9	2347.3	2361.3	2350.1
55°	2404.4	2402.7	2393.7	2393.4	2399.9	2422.9	2451.8	2483.1	2519.3	2535.0	2530.9
57.5°	2557.7	2547.8	2545.1	2540.9	2554.0	2575.6	2611.1	2667.5	2705.0	2722.9	2712.5
60°	2707.8	2700.1	2694.3	2692.8	2701.9	2732.1	2783.0	2850.8	2897.2	2920.6	2904.1
62.5°	2868.7	2863.8	2857.0	2849.1	2868.0	2906.9	2970.2	3045.2	3113.6	3142.5	3117.4
65°	3068.8	3059.0	3051.3	3041.3	3056.9	3105.7	3185.2	3290.8	3382.6	3416.4	3398.4
67.5°	3280.0	3270.8	3271.5	3265.3	3292.8	3360.6	3463.1	3606.5	3729.6	3787.2	3753.4
70°	3464.5	3469.6	3471.0	3496.2	3543.6	3646.7	3817.4	4042.0	4228.7	4316.5	4280.4
71°	3410.2	3421.5	3439.0	3465.1	3546.9	3669.1	3902.0	4174.1	4396.9	4545.5	4495.6
72.5°	3256.0	3262.9	3271.8	3311.7	3404.2	3566.0	3805.7	4116.6	4403.1	4595.4	4537.6
75°	3033.2	3039.6	3042.7	3070.6	3154.9	3296.0	3515.3	3791.3	4044.0	4207.8	4191.6
77.5°	2696.7	2697.7	2721.9	2764.8	2859.5	3020.7	3251.8	3538.0	3775.8	3903.0	3822.2
80°	1936.6	1923.5	1948.2	2003.6	2120.6	2305.7	2542.3	2869.0	3132.8	3251.8	3126.6
82.5°	736.8	776.7	839.6	931.1	970.7	1176.4	1397.2	1589.1	1811.4	2059.7	1997.4
85°	79.2	89.1	111.7	138.7	175.1	242.2	334.7	456.8	563.1	661.8	587.5
87.5°	29.6	30.3	33.7	38.9	39.6	41.2	44.0	51.3	47.9	41.2	33.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P148245

CATALOG NUMBER: VXS-F05-LED-E1-5XQ

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1243.8	1243.8	1243.8	1243.8	1243.8	1243.8	1243.8	1243.8
2.5°	1243.8	1244.1	1243.7	1244.1	1244.1	1242.7	1243.1	1242.4
5°	1243.4	1242.5	1242.7	1243.1	1242.7	1243.4	1242.4	1243.1
7.5°	1241.7	1239.7	1240.3	1240.3	1239.7	1240.7	1240.0	1239.7
10°	1238.3	1235.5	1236.9	1236.3	1235.9	1236.3	1236.2	1236.3
12.5°	1235.1	1233.5	1233.8	1233.5	1233.2	1234.2	1233.8	1234.1
15°	1234.5	1231.7	1231.4	1230.7	1231.1	1231.7	1231.7	1232.7
17.5°	1233.8	1230.4	1230.1	1229.3	1229.6	1231.0	1231.4	1230.7
20°	1235.9	1233.2	1232.4	1231.7	1231.4	1233.2	1232.7	1232.7
22.5°	1245.6	1242.1	1241.7	1239.0	1237.9	1239.0	1238.2	1238.3
25°	1260.9	1256.9	1255.5	1251.7	1248.9	1248.9	1247.9	1247.3
27.5°	1288.9	1282.7	1281.2	1278.1	1274.4	1275.1	1273.1	1272.7
30°	1321.1	1315.6	1310.9	1306.4	1302.0	1300.2	1297.8	1297.4
32.5°	1363.5	1357.3	1351.5	1345.9	1339.8	1337.3	1333.3	1331.2
35°	1415.4	1407.2	1400.3	1396.5	1390.4	1387.2	1384.5	1387.6
37.5°	1488.0	1478.0	1474.6	1470.2	1466.0	1461.1	1462.2	1461.1
40°	1588.5	1579.5	1576.1	1568.2	1567.2	1561.7	1565.1	1561.7
42.5°	1712.6	1696.2	1693.7	1687.5	1685.4	1682.3	1683.7	1681.3
45°	1847.8	1833.0	1830.3	1820.3	1820.6	1813.5	1816.2	1816.2
47.5°	1999.8	1984.4	1971.6	1964.4	1961.7	1957.2	1959.6	1959.2
50°	2156.7	2135.8	2121.7	2107.5	2101.3	2103.0	2098.2	2106.4
52.5°	2325.2	2293.9	2274.0	2260.5	2248.8	2251.3	2251.9	2254.3
55°	2499.6	2459.7	2430.8	2413.3	2402.6	2403.3	2406.4	2409.1
57.5°	2675.0	2625.2	2585.9	2559.8	2553.0	2556.1	2556.1	2555.6
60°	2857.0	2797.1	2746.6	2717.0	2710.9	2709.1	2722.5	2718.0
62.5°	3052.3	2980.5	2928.2	2890.4	2881.5	2887.6	2899.7	2896.9
65°	3311.4	3212.0	3144.6	3107.0	3091.9	3098.1	3114.3	3113.6
67.5°	3645.4	3506.4	3417.3	3369.1	3358.1	3365.7	3374.7	3383.3
70°	4144.9	3946.3	3819.1	3714.8	3670.2	3661.6	3670.5	3670.9
71°	4320.6	4092.5	3889.9	3762.7	3689.4	3658.4	3660.9	3645.4
72.5°	4313.4	4032.3	3795.3	3662.2	3560.4	3535.6	3523.6	3505.1
75°	4022.7	3769.5	3563.8	3418.7	3320.6	3291.4	3270.1	3269.0
77.5°	3648.1	3461.3	3234.7	3080.9	2961.6	2913.1	2891.4	2890.7
80°	2932.6	2653.1	2487.3	2394.7	2250.6	2208.9	2165.0	2148.4
82.5°	1773.5	1385.8	1126.8	1001.2	931.8	767.5	688.6	651.5
85°	413.1	293.4	202.3	132.7	95.6	76.1	58.4	51.6
87.5°	27.9	22.0	19.6	15.9	12.0	11.7	7.3	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)