

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P148241

Luminaire Tested: **VXS-E05-LED-E1-5XQ-7050**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P148241
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33676)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-E05-LED-E1-5XQ-7050
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 5 SQUARE EXTRA WIDE
Light Source: (105) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16317 lumens
Efficiency: N/A
Efficacy: 128.2 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type V - Short - Non-Cutoff
BUG Rating: B4 - U0 - G3

Input Watts (W): 127.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P148241

CATALOG NUMBER: VXS-E05-LED-E1-5XQ-7050

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 25 foot mounting height. Maximum calculated value = 2.5 fc
 Type V - Short - Non-Cutoff

REPORT NUMBER: P148241

CATALOG NUMBER: VXS-E05-LED-E1-5XQ-7050

Luminous Intensity Polar Plot



REPORT NUMBER: P148241

CATALOG NUMBER: VXS-E05-LED-E1-5XQ-7050


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	8158.5	0.0	8158.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	8158.5	0.0	8158.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	16317.0	0.0	16317.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.3	0.9
10°-20°	435.8	2.7
20°-30°	729.8	4.5
30°-40°	1112.7	6.8
40°-50°	1776.7	10.9
50°-60°	2731.7	16.7
60°-70°	3977.4	24.4
70°-80°	4480.6	27.5
80°-90°	924.9	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	16317.0	100.0
0°-180°	16317.0	100.0

Coefficient of Utilization



REPORT NUMBER: P148241


CATALOG NUMBER: VXS-E05-LED-E1-5XQ-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	656.5	4.0			
FM	(30°-60°)	2810.5	17.2			
FH	(60°-80°)	4229.0	25.9			G2/5000
FVH	(80°-90°)	462.5	2.8			G3/500
BL	(0°-30°)	656.5	4.0	B2/1000		
BM	(30°-60°)	2810.5	17.2	B3/5000		
BH	(60°-80°)	4229.0	25.9	B4/5000		G2/5000
BVH	(80°-90°)	462.5	2.8			G3/500
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G3

Type V Short



REPORT NUMBER: P148241

CATALOG NUMBER: VXS-E05-LED-E1-5XQ-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1546.0	1546.0	1546.0	1546.0	1546.0	1546.0	1546.0	1546.0	1546.0	1546.0	1546.0
2.5°	1548.6	1549.4	1549.0	1548.1	1548.6	1548.2	1547.3	1546.8	1543.8	1545.5	1548.2
5°	1548.6	1547.7	1547.3	1546.8	1546.8	1548.1	1546.8	1545.5	1545.1	1546.0	1544.7
7.5°	1547.8	1545.9	1545.1	1544.7	1545.2	1545.5	1544.2	1542.6	1543.8	1542.6	1540.8
10°	1545.2	1543.8	1544.2	1542.6	1543.0	1542.6	1540.8	1539.6	1540.4	1539.2	1537.0
12.5°	1546.0	1543.8	1543.4	1542.6	1542.2	1541.8	1539.6	1537.4	1537.8	1537.0	1534.9
15°	1546.0	1544.7	1544.2	1542.6	1542.2	1541.2	1538.8	1537.8	1537.8	1536.6	1534.0
17.5°	1546.8	1546.0	1546.0	1543.8	1543.0	1542.6	1539.6	1538.2	1539.6	1537.0	1535.3
20°	1549.3	1548.6	1549.0	1547.7	1546.0	1545.9	1543.8	1543.0	1543.4	1543.0	1538.2
22.5°	1554.5	1554.5	1555.3	1555.0	1554.5	1554.9	1553.3	1553.3	1553.7	1553.7	1549.8
25°	1569.1	1568.7	1569.5	1569.5	1569.9	1572.8	1571.6	1571.2	1573.4	1573.4	1569.5
27.5°	1596.5	1595.6	1596.5	1597.3	1599.5	1603.3	1602.4	1603.7	1607.2	1606.3	1602.9
30°	1628.1	1627.3	1629.3	1631.9	1633.7	1639.7	1637.1	1643.4	1646.5	1649.0	1646.5
32.5°	1674.3	1674.3	1678.1	1679.8	1683.7	1689.6	1690.6	1695.6	1699.5	1703.7	1700.7
35°	1735.8	1734.9	1737.9	1740.9	1745.7	1751.2	1753.4	1760.2	1766.2	1769.2	1763.6
37.5°	1829.8	1825.2	1830.8	1832.4	1836.3	1837.6	1843.5	1852.1	1858.5	1857.6	1853.8
40°	1957.3	1956.5	1954.3	1951.7	1957.7	1959.9	1959.9	1971.4	1981.7	1979.9	1979.5
42.5°	2106.1	2102.2	2099.7	2099.7	2103.1	2103.9	2117.2	2125.8	2133.1	2134.7	2133.1
45°	2265.9	2262.2	2263.0	2261.2	2262.6	2268.2	2275.9	2291.6	2305.3	2305.7	2298.4
47.5°	2437.8	2425.9	2435.2	2422.0	2430.2	2434.4	2453.7	2476.8	2500.7	2505.0	2498.5
50°	2612.3	2611.0	2610.2	2607.6	2611.4	2620.8	2644.4	2680.7	2703.8	2719.2	2708.9
52.5°	2802.9	2796.6	2793.6	2789.2	2793.1	2811.5	2844.5	2876.1	2917.5	2935.1	2920.9
55°	2988.6	2986.4	2975.2	2974.8	2983.0	3011.6	3047.6	3086.4	3131.3	3151.0	3145.9
57.5°	3179.3	3166.8	3163.4	3158.2	3174.5	3201.5	3245.5	3315.6	3362.2	3384.5	3371.6
60°	3365.7	3356.3	3349.0	3347.3	3358.3	3396.0	3459.3	3543.4	3601.2	3630.3	3609.7
62.5°	3565.8	3559.8	3551.2	3541.3	3564.9	3613.2	3691.8	3785.1	3870.2	3906.0	3874.8
65°	3814.5	3802.2	3792.7	3780.3	3799.6	3860.3	3959.1	4090.4	4204.6	4246.4	4224.1
67.5°	4077.1	4065.5	4066.3	4058.7	4092.8	4177.1	4304.5	4482.8	4635.9	4707.3	4665.3
70°	4306.2	4312.6	4314.3	4345.5	4404.6	4532.8	4744.9	5024.0	5256.2	5365.3	5320.4
71°	4238.8	4252.7	4274.6	4307.2	4408.8	4560.6	4850.1	5188.2	5465.3	5649.9	5588.0
72.5°	4047.0	4055.6	4066.7	4116.4	4231.4	4432.3	4730.4	5116.9	5473.0	5712.0	5640.2
75°	3770.1	3778.2	3782.1	3816.7	3921.5	4096.8	4369.5	4712.3	5026.6	5230.2	5210.1
77.5°	3351.9	3353.3	3383.2	3436.6	3554.2	3754.7	4042.0	4397.7	4693.2	4851.3	4750.9
80°	2407.0	2390.8	2421.7	2490.4	2635.9	2865.8	3160.0	3566.2	3894.1	4042.0	3886.4
82.5°	915.9	965.4	1043.6	1157.3	1206.5	1462.2	1736.7	1975.2	2251.4	2560.2	2482.7
85°	98.3	110.7	139.0	172.3	217.6	300.9	416.0	567.8	699.9	822.6	730.3
87.5°	36.8	37.6	41.9	48.3	49.1	51.3	54.7	63.7	59.5	51.3	41.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P148241

CATALOG NUMBER: VXS-E05-LED-E1-5XQ-7050

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1546.0	1546.0	1546.0	1546.0	1546.0	1546.0	1546.0	1546.0
2.5°	1546.0	1546.4	1546.0	1546.4	1546.4	1544.7	1545.1	1544.2
5°	1545.6	1544.2	1544.7	1545.2	1544.7	1545.5	1544.2	1545.1
7.5°	1543.4	1540.8	1541.8	1541.7	1540.8	1542.2	1541.2	1540.8
10°	1539.2	1535.8	1537.4	1536.6	1536.2	1536.6	1536.6	1536.6
12.5°	1535.3	1533.2	1533.6	1533.2	1532.7	1534.0	1533.6	1534.1
15°	1534.4	1531.0	1530.6	1529.7	1530.2	1531.0	1531.0	1532.2
17.5°	1533.6	1529.3	1528.9	1528.1	1528.5	1530.2	1530.6	1529.7
20°	1536.2	1532.7	1531.9	1531.0	1530.6	1532.7	1532.3	1532.2
22.5°	1548.2	1543.8	1543.4	1540.0	1538.8	1540.0	1539.2	1539.2
25°	1567.4	1562.3	1560.5	1555.9	1552.4	1552.4	1551.1	1550.3
27.5°	1602.0	1594.3	1592.5	1588.7	1584.0	1584.9	1582.4	1582.0
30°	1642.2	1635.3	1629.4	1623.8	1618.2	1616.2	1613.2	1612.6
32.5°	1694.8	1687.0	1679.8	1673.0	1665.3	1662.3	1657.1	1654.6
35°	1759.4	1749.0	1740.5	1735.9	1728.1	1724.4	1720.8	1724.8
37.5°	1849.5	1837.1	1832.8	1827.4	1822.2	1816.2	1817.5	1816.2
40°	1974.4	1963.3	1959.0	1949.2	1947.9	1941.0	1945.3	1941.0
42.5°	2128.7	2108.2	2105.2	2097.5	2095.0	2091.2	2092.8	2089.8
45°	2296.8	2278.3	2274.9	2262.6	2263.0	2254.0	2257.4	2257.4
47.5°	2485.8	2466.5	2450.7	2441.7	2438.3	2432.7	2435.8	2435.2
50°	2680.6	2654.6	2637.1	2619.6	2611.8	2614.0	2608.0	2618.2
52.5°	2890.2	2851.3	2826.5	2809.8	2795.3	2798.3	2799.2	2802.1
55°	3106.9	3057.4	3021.5	2999.6	2986.4	2987.3	2991.1	2994.5
57.5°	3325.0	3263.0	3214.3	3181.8	3173.3	3177.1	3177.1	3176.7
60°	3551.2	3476.8	3413.9	3377.2	3369.4	3367.4	3384.0	3378.4
62.5°	3794.0	3704.7	3639.7	3592.6	3581.6	3589.2	3604.1	3600.8
65°	4116.0	3992.4	3908.6	3862.0	3843.2	3850.9	3871.0	3870.1
67.5°	4531.1	4358.3	4247.7	4187.8	4174.1	4183.5	4194.6	4205.4
70°	5151.9	4905.2	4746.9	4617.5	4561.9	4551.2	4562.3	4562.7
71°	5370.4	5086.9	4835.1	4676.9	4585.8	4547.4	4550.4	4531.2
72.5°	5361.5	5012.1	4717.5	4552.1	4425.5	4394.7	4379.8	4356.7
75°	5000.1	4685.4	4429.8	4249.3	4127.5	4091.2	4064.7	4063.4
77.5°	4534.5	4302.4	4020.6	3829.5	3681.1	3620.9	3594.0	3593.1
80°	3645.2	3297.6	3091.6	2976.6	2797.4	2745.7	2691.0	2670.5
82.5°	2204.4	1722.6	1400.6	1244.6	1158.2	953.8	856.0	809.7
85°	513.5	364.8	251.4	165.0	118.9	94.5	72.7	64.1
87.5°	34.6	27.4	24.4	19.7	14.9	14.5	9.0	7.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)