

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P151611

Luminaire Tested: **VXS-E05-LED-E1-SL4-HSS-7050**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P151611
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33728)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-E05-LED-E1-SL4-HSS-7050
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL AND
HOUSE SIDE SHIELD
Light Source: (105) 5000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10439.7 lumens
Efficiency: N/A
Efficacy: 82.0 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B1 - U0 - G3

Input Watts (W): 127.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P151611

CATALOG NUMBER: VXS-E05-LED-E1-SL4-HSS-7050

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 5.8 fc
 Type IV - Short - Semi-Cutoff

REPORT NUMBER: P151611

CATALOG NUMBER: VXS-E05-LED-E1-SL4-HSS-7050

Luminous Intensity Polar Plot



REPORT NUMBER: P151611

CATALOG NUMBER: VXS-E05-LED-E1-SL4-HSS-7050

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	310.9	0.0	310.9
	% Fixture	3.0	0.0	3.0
Street Side	Lumens	10128.8	0.0	10128.8
	% Fixture	97.0	0.0	97.0
Total	Lumens	10439.7	0.0	10439.7
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.0	0.8
10°-20°	279.4	2.7
20°-30°	534.7	5.1
30°-40°	889.3	8.5
40°-50°	1203.3	11.5
50°-60°	1881.9	18.0
60°-70°	3869.1	37.1
70°-80°	1556.9	14.9
80°-90°	144.0	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10439.7	100.0
0°-180°	10439.7	100.0

Coefficient of Utilization



REPORT NUMBER: P151611


CATALOG NUMBER: VXS-E05-LED-E1-SL4-HSS-7050

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	776.9	7.4			
FM	(30°-60°)	3832.5	36.7			
FH	(60°-80°)	5380.6	51.5			G3/7500
FVH	(80°-90°)	138.7	1.3			G2/225
BL	(0°-30°)	118.2	1.1	B1/500		
BM	(30°-60°)	142.0	1.4	B0/220		
BH	(60°-80°)	45.4	0.4	B0/110		G0/110
BVH	(80°-90°)	5.4	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G3

Type IV Short



REPORT NUMBER: P151611

CATALOG NUMBER: VXS-E05-LED-E1-SL4-HSS-7050

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	788.4	788.4	788.4	788.4	788.4	788.4	788.4	788.4	788.4	788.4	788.4
2.5°	1051.7	1039.8	1026.1	1026.1	1009.0	1009.0	998.8	971.4	968.0	952.5	937.2
5°	1342.5	1332.2	1315.1	1299.7	1286.0	1262.1	1245.0	1212.5	1176.6	1142.4	1111.6
7.5°	1626.4	1621.2	1590.5	1585.3	1563.1	1523.7	1489.5	1441.7	1380.1	1332.2	1275.8
10°	1889.7	1877.8	1870.9	1841.9	1809.3	1766.6	1713.6	1655.4	1583.6	1508.4	1428.0
12.5°	2098.3	2091.5	2060.7	2048.8	2014.6	1971.8	1905.2	1829.8	1758.0	1660.6	1566.5
15°	2254.0	2242.1	2221.6	2202.7	2161.7	2124.0	2062.5	1980.4	1893.2	1787.2	1674.3
17.5°	2383.9	2361.8	2356.6	2327.6	2284.8	2240.3	2171.9	2096.7	1994.1	1888.1	1764.9
20°	2558.4	2527.7	2517.4	2474.6	2425.1	2363.4	2284.8	2190.8	2083.0	1966.7	1840.1
22.5°	2763.6	2741.5	2719.2	2681.6	2618.2	2531.1	2416.5	2313.9	2177.1	2048.8	1912.0
25°	3054.4	3035.5	2999.7	2948.4	2869.6	2765.4	2626.8	2476.4	2315.5	2151.4	1990.7
27.5°	3336.6	3319.5	3293.8	3254.5	3165.5	3051.0	2879.9	2688.4	2484.9	2286.5	2108.6
30°	3601.7	3586.2	3560.6	3521.2	3442.6	3329.7	3136.5	2931.2	2678.1	2447.3	2233.5
32.5°	3887.3	3882.1	3853.1	3796.6	3728.2	3576.0	3365.6	3145.0	2888.5	2621.7	2372.0
35°	4210.5	4171.1	4143.7	4087.4	3971.0	3808.6	3562.3	3321.1	3051.0	2777.3	2498.5
37.5°	4484.0	4446.4	4412.2	4340.4	4198.4	3991.5	3712.7	3447.7	3168.9	2890.2	2606.3
40°	4684.1	4665.4	4624.4	4530.3	4371.2	4125.0	3823.9	3534.9	3254.5	2974.0	2693.6
42.5°	4833.0	4803.8	4757.7	4660.2	4472.1	4191.6	3868.4	3570.9	3293.8	3025.3	2749.9
45°	4887.7	4863.7	4821.0	4714.9	4511.4	4210.5	3866.7	3560.6	3295.5	3040.7	2787.6
47.5°	4855.2	4831.3	4793.6	4694.4	4494.3	4188.2	3836.0	3531.5	3278.4	3045.8	2821.8
50°	4747.5	4733.8	4704.7	4620.9	4441.3	4145.5	3808.6	3516.2	3275.0	3071.5	2869.6
52.5°	4737.2	4728.6	4692.7	4608.9	4425.9	4131.8	3805.2	3524.7	3304.0	3103.9	2903.8
55°	5788.9	5667.6	5395.6	5164.8	4785.1	4333.6	3977.8	3663.2	3427.2	3232.2	3092.0
57.5°	8227.7	8046.4	7688.9	7249.4	6377.2	5520.4	4834.7	4338.8	4094.2	4005.2	4058.2
60°	9370.1	9337.5	9281.1	9072.4	8626.1	7889.0	7068.2	6180.6	5824.9	5794.1	5901.9
62.5°	9912.2	9891.6	9908.8	9883.1	9744.6	9529.1	9293.1	8910.1	8557.7	8330.3	7848.0
65°	10161.9	10175.5	10273.1	10349.9	10367.0	10423.5	10596.3	11073.4	11422.3	10835.6	9496.6
67.5°	9527.4	9607.8	9831.8	10112.2	10440.6	10758.8	11271.8	12277.3	12993.9	12304.7	10403.0
69°	7887.4	7926.6	8473.9	9002.4	9804.5	10365.4	11109.3	12427.9	13233.4	12455.2	10331.2
70°	6209.6	6245.6	6832.1	7550.5	8906.6	9628.3	10601.3	12173.1	13009.3	12255.1	9961.8
72.5°	2801.2	2749.9	2956.9	3341.7	4815.9	5961.7	7663.3	9862.6	10733.1	9818.1	7453.0
75°	1956.5	1934.2	1956.5	1958.1	2187.4	2821.8	3560.6	5346.0	6611.5	5705.2	3560.6
77.5°	1515.2	1499.8	1484.5	1467.4	1494.7	1674.3	1746.1	1896.6	2462.7	2329.2	1357.9
80°	1198.9	1185.2	1222.8	1210.8	1210.8	1231.3	1217.6	1161.2	1055.1	978.2	875.6
82.5°	557.5	560.9	560.9	608.8	733.7	856.8	896.2	839.7	745.6	634.5	511.3
85°	53.1	59.9	100.9	155.6	309.5	348.9	350.6	290.8	290.8	229.1	184.7
87.5°	0.0	1.8	1.8	1.8	15.4	42.8	36.0	10.3	5.2	5.2	8.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P151611

CATALOG NUMBER: VXS-E05-LED-E1-SL4-HSS-7050

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	788.4	788.4	788.4	788.4	788.4	788.4	788.4	788.4	788.4	788.4	788.4
2.5°	909.8	904.7	884.1	863.6	844.9	824.4	805.5	786.6	766.1	750.8	731.9
5°	1063.7	1026.1	983.3	942.3	901.2	858.5	814.1	774.7	733.7	696.1	660.1
7.5°	1219.4	1145.8	1087.7	1014.1	947.5	880.7	819.2	755.9	697.7	643.0	591.7
10°	1351.1	1262.1	1171.5	1077.4	981.7	892.7	807.3	731.9	655.0	588.3	525.0
12.5°	1458.8	1345.9	1234.7	1116.8	1009.0	896.2	790.1	699.5	608.8	533.6	468.6
15°	1556.3	1426.3	1292.8	1156.1	1019.3	891.0	773.0	660.1	567.8	482.3	408.7
17.5°	1634.9	1486.1	1335.6	1181.8	1034.6	884.1	750.8	632.7	525.0	436.1	364.2
20°	1703.3	1547.7	1385.3	1212.5	1044.9	882.5	731.9	598.5	487.4	393.4	323.2
22.5°	1766.6	1611.0	1436.6	1251.8	1060.3	880.7	714.8	573.0	454.9	360.8	290.8
25°	1838.4	1674.3	1491.3	1292.8	1087.7	887.6	704.6	552.4	425.8	330.1	265.1
27.5°	1918.9	1746.1	1556.3	1344.2	1123.6	901.2	701.1	530.2	400.2	301.0	244.6
30°	2031.7	1831.6	1621.2	1395.5	1156.1	916.7	697.7	516.5	374.5	278.8	224.0
32.5°	2130.9	1915.4	1693.1	1448.5	1192.0	932.0	696.1	497.6	350.6	256.5	208.6
35°	2235.2	1992.3	1754.6	1499.8	1222.8	949.1	694.3	483.9	328.4	234.3	193.3
37.5°	2325.8	2057.3	1802.5	1544.2	1257.0	964.6	696.1	472.0	307.9	215.4	179.6
40°	2402.8	2124.0	1855.5	1585.3	1292.8	988.5	697.7	460.0	287.4	198.3	167.6
42.5°	2471.2	2187.4	1912.0	1631.5	1333.9	1015.9	708.0	449.7	270.3	183.0	155.6
45°	2524.2	2245.5	1973.6	1696.5	1400.6	1060.3	726.8	442.9	253.1	169.3	145.4
47.5°	2579.0	2331.0	2077.8	1799.1	1498.1	1130.5	759.3	441.2	239.4	159.1	136.8
50°	2654.2	2416.5	2170.3	1903.4	1587.0	1202.3	798.7	442.9	222.3	148.8	128.3
52.5°	2708.9	2503.7	2289.9	2084.7	1799.1	1421.1	950.9	473.7	213.8	140.2	118.0
55°	3032.1	2996.3	3001.3	3035.5	2814.9	2418.2	1590.5	684.0	251.4	159.1	116.3
57.5°	4275.4	4402.0	4475.5	4473.8	4109.5	3408.4	2136.0	879.1	280.5	184.7	138.5
60°	5910.4	5814.6	5679.5	5346.0	4862.1	3890.7	2389.1	945.7	242.8	147.0	126.5
62.5°	7355.4	6794.5	6296.9	5756.5	5122.0	4058.2	2440.4	940.6	212.0	111.2	88.9
65°	8256.7	7247.8	6443.9	5766.7	5019.4	3918.0	2308.7	863.6	179.6	90.7	73.6
67.5°	8472.2	7003.2	5865.9	5002.3	4193.4	3049.2	1694.8	649.8	140.2	75.2	65.0
69°	8001.9	6225.1	4860.3	3880.4	3051.0	2023.1	1048.3	410.5	107.8	68.4	59.9
70°	7360.6	5414.4	3959.1	3114.2	2259.2	1421.1	733.7	289.0	87.3	63.3	54.7
72.5°	4735.4	2844.0	1946.2	1354.5	932.0	566.1	287.4	129.9	66.7	53.1	44.5
75°	1836.7	1051.7	762.7	579.8	453.2	314.7	174.4	83.8	56.5	44.5	34.2
77.5°	904.7	692.6	566.1	388.2	225.7	140.2	94.1	65.0	46.2	32.5	22.3
80°	714.8	475.4	283.9	176.2	133.4	100.9	71.8	53.1	34.2	20.5	15.4
82.5°	366.0	200.1	147.0	119.7	99.2	78.7	58.1	37.6	22.3	13.7	12.0
85°	114.6	83.8	75.2	73.6	68.4	56.5	41.0	23.9	13.7	8.6	8.6
87.5°	8.6	12.0	15.4	12.0	13.7	12.0	15.4	10.3	6.8	6.8	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P151611

CATALOG NUMBER: VXS-E05-LED-E1-SL4-HSS-7050

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	788.4	788.4	788.4	788.4	788.4	788.4	788.4	788.4	788.4	788.4	788.4
2.5°	718.2	697.7	679.0	666.9	644.8	636.2	627.7	624.2	608.8	612.2	598.5
5°	627.7	591.7	564.4	537.0	511.3	492.5	477.1	458.3	442.9	436.1	422.4
7.5°	545.6	499.4	463.4	434.4	403.6	379.7	359.2	345.5	331.8	318.1	311.3
10°	473.7	424.1	383.1	354.0	325.0	304.5	289.0	278.8	270.3	265.1	263.3
12.5°	407.0	359.2	321.6	295.9	273.7	263.3	256.5	251.4	249.6	248.0	248.0
15°	355.8	307.9	278.8	259.9	249.6	244.6	242.8	239.4	236.0	234.3	234.3
17.5°	307.9	271.9	251.4	241.1	236.0	232.5	229.1	225.7	222.3	220.6	220.6
20°	275.3	246.2	236.0	229.1	224.0	220.6	215.4	212.0	210.4	208.6	206.9
22.5°	249.6	230.9	224.0	218.9	212.0	206.9	203.5	200.1	196.7	194.9	193.3
25°	230.9	218.9	213.8	206.9	200.1	194.9	189.8	184.7	181.2	179.6	176.2
27.5°	217.2	208.6	201.8	193.3	186.4	181.2	176.2	171.0	167.6	164.1	162.5
30°	205.2	196.7	188.1	181.2	172.7	167.6	160.7	155.6	153.9	150.5	147.0
32.5°	193.3	184.7	176.2	167.6	159.1	152.2	148.8	142.0	138.5	136.8	133.4
35°	179.6	171.0	160.7	153.9	145.4	138.5	133.4	128.3	124.9	121.5	119.7
37.5°	167.6	157.3	147.0	138.5	131.7	124.9	119.7	114.6	111.2	107.8	106.0
40°	153.9	143.6	133.4	124.9	118.0	112.8	107.8	102.6	99.2	97.5	97.5
42.5°	142.0	129.9	119.7	112.8	107.8	100.9	95.8	90.7	88.9	87.3	88.9
45°	129.9	118.0	109.4	102.6	97.5	90.7	85.5	82.1	80.4	82.1	83.8
47.5°	119.7	107.8	99.2	94.1	88.9	83.8	78.7	75.2	75.2	78.7	82.1
50°	109.4	97.5	90.7	87.3	82.1	77.0	70.2	68.4	70.2	73.6	77.0
52.5°	99.2	85.5	80.4	78.7	73.6	68.4	63.3	61.6	63.3	66.7	65.0
55°	88.9	75.2	73.6	71.8	66.7	59.9	54.7	54.7	54.7	53.1	49.6
57.5°	85.5	66.7	65.0	63.3	58.1	51.3	47.9	44.5	42.8	37.6	36.0
60°	88.9	59.9	59.9	56.5	51.3	44.5	39.4	34.2	30.8	27.4	27.4
62.5°	71.8	54.7	53.1	49.6	42.8	36.0	30.8	25.7	23.9	22.3	22.3
65°	58.1	49.6	46.2	41.0	36.0	29.1	23.9	20.5	18.9	18.9	20.5
67.5°	53.1	44.5	39.4	34.2	29.1	22.3	18.9	17.1	17.1	18.9	18.9
69°	49.6	41.0	36.0	30.8	25.7	20.5	17.1	17.1	17.1	17.1	18.9
70°	46.2	39.4	34.2	29.1	22.3	17.1	15.4	15.4	17.1	17.1	18.9
72.5°	36.0	30.8	29.1	23.9	17.1	15.4	13.7	15.4	15.4	17.1	17.1
75°	27.4	22.3	22.3	18.9	13.7	12.0	12.0	13.7	13.7	15.4	15.4
77.5°	18.9	15.4	15.4	13.7	12.0	10.3	10.3	12.0	13.7	13.7	15.4
80°	13.7	12.0	10.3	12.0	10.3	8.6	10.3	12.0	12.0	13.7	13.7
82.5°	10.3	10.3	10.3	10.3	8.6	8.6	10.3	10.3	12.0	13.7	13.7
85°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	10.3	10.3	12.0	12.0
87.5°	5.2	5.2	5.2	6.8	6.8	8.6	8.6	8.6	8.6	10.3	10.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P151611

CATALOG NUMBER: VXS-E05-LED-E1-SL4-HSS-7050

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	788.4	788.4	788.4	788.4
2.5°	595.1	593.5	586.6	588.3
5°	417.3	407.0	413.9	412.1
7.5°	306.1	304.5	302.7	306.1
10°	261.7	261.7	259.9	261.7
12.5°	246.2	246.2	246.2	246.2
15°	234.3	234.3	232.5	232.5
17.5°	220.6	220.6	220.6	218.9
20°	206.9	205.2	205.2	205.2
22.5°	191.5	189.8	189.8	189.8
25°	176.2	174.4	174.4	174.4
27.5°	160.7	159.1	157.3	157.3
30°	145.4	143.6	142.0	142.0
32.5°	129.9	128.3	126.5	126.5
35°	116.3	116.3	114.6	112.8
37.5°	104.4	104.4	104.4	104.4
40°	95.8	97.5	97.5	97.5
42.5°	90.7	92.3	94.1	95.8
45°	87.3	90.7	92.3	92.3
47.5°	85.5	87.3	88.9	88.9
50°	78.7	77.0	77.0	77.0
52.5°	63.3	59.9	58.1	56.5
55°	46.2	44.5	41.0	41.0
57.5°	32.5	32.5	30.8	30.8
60°	25.7	25.7	23.9	25.7
62.5°	22.3	22.3	22.3	22.3
65°	20.5	20.5	20.5	20.5
67.5°	20.5	20.5	20.5	20.5
69°	18.9	18.9	18.9	18.9
70°	18.9	18.9	18.9	18.9
72.5°	17.1	17.1	17.1	17.1
75°	15.4	17.1	17.1	17.1
77.5°	15.4	15.4	15.4	15.4
80°	13.7	13.7	15.4	15.4
82.5°	13.7	13.7	13.7	13.7
85°	12.0	12.0	13.7	13.7
87.5°	10.3	10.3	12.0	12.0
90°	0.0	0.0	0.0	0.0

(END OF REPORT)