

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P150468

Luminaire Tested: **VXS-E05-LED-E1-SL3-HSS-8030**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P150468
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33727)
Test Lab: INNOVATION CENTER-P3
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: VXS-E05-LED-E1-SL3-HSS-8030
Description: VISION SITE SMALL LED LUMINAIRE
(5) LIGHTBARS WITH AccuLED OPTICS - TYPE 3 W/ SPILL LIGHT CONTROL AND
HOUSE SIDE SHIELD
Light Source: (105) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7316.6 lumens
Efficiency: N/A
Efficacy: 57.5 lumens/watt
Luminous Opening: Rectangular (W 0.83' x L: 1' x H: 0')
IES Classification: Type III - Short - Non-Cutoff
BUG Rating: B0 - U0 - G2

Input Watts (W): 127.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT




REPORT NUMBER: P150468

CATALOG NUMBER: VXS-E05-LED-E1-SL3-HSS-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 12.1 fc
Type III - Short - Non-Cutoff

REPORT NUMBER: P150468

CATALOG NUMBER: VXS-E05-LED-E1-SL3-HSS-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P150468

CATALOG NUMBER: VXS-E05-LED-E1-SL3-HSS-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	158.5	0.0	158.5
	% Fixture	2.2	0.0	2.2
Street Side	Lumens	7158.1	0.0	7158.1
	% Fixture	97.8	0.0	97.8
Total	Lumens	7316.6	0.0	7316.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.7	0.3
10°-20°	104.8	1.4
20°-30°	226.1	3.1
30°-40°	482.8	6.6
40°-50°	1067.8	14.6
50°-60°	1809.5	24.7
60°-70°	2414.7	33.0
70°-80°	1063.6	14.5
80°-90°	122.5	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7316.6	100.0
0°-180°	7316.6	100.0

Coefficient of Utilization



REPORT NUMBER: P150468


CATALOG NUMBER: VXS-E05-LED-E1-SL3-HSS-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	305.6	4.2			
FM	(30°-60°)	3290.5	45.0			
FH	(60°-80°)	3444.3	47.1			G2/5000
FVH	(80°-90°)	117.6	1.6			G2/225
BL	(0°-30°)	50.0	0.7	B0/110		
BM	(30°-60°)	69.6	1.0	B0/220		
BH	(60°-80°)	34.0	0.5	B0/110		G0/110
BVH	(80°-90°)	4.9	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type III Short



REPORT NUMBER: P150468

CATALOG NUMBER: VXS-E05-LED-E1-SL3-HSS-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	67°	68°
0°	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8
2.5°	278.5	277.1	271.5	271.5	263.0	257.4	250.4	243.3	243.3	242.0	240.5
5°	368.5	360.1	358.7	343.2	330.6	312.2	295.4	272.8	270.1	267.3	265.9
7.5°	468.4	467.0	454.3	436.1	410.8	377.0	343.2	306.6	301.0	298.2	292.5
10°	597.8	590.8	573.9	543.0	505.0	460.0	405.1	347.5	340.4	334.8	332.0
12.5°	721.7	708.9	699.1	659.7	611.9	545.8	479.7	396.7	391.1	384.0	372.7
15°	837.0	825.7	808.8	775.0	721.7	638.7	561.2	460.0	445.9	436.1	427.7
17.5°	926.9	920.0	900.2	862.3	804.6	731.5	638.7	524.7	513.5	500.7	485.3
20°	1012.7	1002.9	972.0	920.0	858.0	801.8	730.1	609.1	593.6	578.1	561.2
22.5°	1094.4	1084.6	1033.9	948.1	882.0	858.0	832.7	704.8	680.8	668.2	651.3
25°	1208.3	1187.3	1108.4	972.0	883.4	901.7	945.3	828.5	806.0	787.8	761.0
27.5°	1361.7	1333.5	1209.7	1007.2	889.0	949.5	1074.7	979.1	955.1	934.0	904.5
30°	1534.6	1516.4	1368.7	1091.6	929.8	1019.8	1219.6	1170.4	1142.2	1116.9	1081.8
32.5°	1709.1	1683.7	1537.5	1251.9	1039.5	1156.3	1401.0	1392.5	1356.1	1332.1	1294.1
35°	1862.4	1849.7	1741.5	1514.9	1289.9	1395.4	1643.0	1652.8	1620.4	1595.1	1553.0
37.5°	1966.5	1966.5	1945.4	1797.7	1688.0	1766.7	1998.9	2000.2	1967.9	1910.3	1889.1
40°	2020.0	2035.4	2111.4	2139.5	2133.9	2235.1	2465.9	2440.5	2413.8	2384.2	2314.0
42.5°	2129.6	2143.7	2305.5	2499.6	2626.2	2759.9	2918.8	2910.4	2878.0	2824.6	2759.9
45°	2315.3	2333.7	2526.3	2834.4	3094.6	3284.6	3385.8	3346.4	3314.1	3263.4	3229.6
47.5°	2551.7	2586.8	2804.9	3186.1	3499.8	3813.5	3919.0	3814.8	3786.7	3747.4	3692.4
50°	2803.4	2837.2	3069.3	3505.4	3859.9	4234.0	4409.8	4234.0	4193.3	4180.5	4118.7
52.5°	3021.5	3049.6	3273.3	3751.5	4135.5	4574.4	4830.5	4598.3	4568.8	4526.6	4481.6
55°	3150.9	3173.4	3383.0	3869.7	4322.6	4881.0	5237.0	5033.0	4989.4	4972.5	4907.8
57.5°	3194.5	3217.0	3405.5	3885.2	4423.9	5161.0	5730.7	5737.7	5685.7	5625.2	5605.5
60°	3194.5	3219.8	3378.8	3847.2	4522.4	5459.2	6389.0	6975.5	6863.0	6851.8	6780.1
62.5°	3062.3	3086.2	3246.5	3730.5	4654.6	5861.6	7306.1	8341.5	8309.1	8236.0	8117.8
65°	2775.3	2789.4	2946.9	3432.2	4603.9	6231.5	8100.9	9250.2	9198.1	9054.6	8902.7
66°	2645.9	2657.2	2804.9	3262.1	4438.0	6282.1	8241.6	9364.0	9278.2	9157.3	8985.7
67.5°	2458.9	2478.5	2582.6	2945.5	4039.9	6106.3	8153.0	9283.9	9209.3	9063.0	8891.4
70°	1641.6	1627.5	1994.6	2260.5	3077.7	4975.3	7314.6	8335.9	8337.2	8268.3	8199.4
72.5°	779.3	787.8	894.6	1391.2	2014.3	3323.9	5822.2	6653.5	6749.1	6625.3	6539.5
75°	559.9	572.5	637.2	851.0	1201.2	1994.6	3774.1	4653.2	4656.1	4436.6	4241.0
77.5°	163.2	170.2	239.2	524.7	900.2	1346.1	2167.7	2586.8	2526.3	2368.8	2221.1
80°	67.6	67.6	70.4	167.4	361.6	914.3	1516.4	1991.8	1984.8	1924.2	1837.1
82.5°	25.3	26.7	33.8	68.9	85.8	225.1	1011.4	1728.8	1724.6	1638.8	1576.9
85°	2.8	2.8	8.4	29.5	32.3	42.2	202.6	762.4	758.1	762.4	668.2
87.5°	0.0	0.0	1.5	2.8	4.2	5.6	8.4	29.5	32.3	31.0	28.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P150468

CATALOG NUMBER: VXS-E05-LED-E1-SL3-HSS-8030

CANDELA DISTRIBUTION (continued):

	69°	70°	71°	72°	73°	74°	75°	76°	77°	78°	79°
0°	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8
2.5°	240.5	237.7	237.7	236.3	236.3	236.3	234.9	233.5	233.5	232.1	230.7
5°	263.0	260.2	258.9	256.1	254.6	253.2	250.4	249.0	246.1	244.8	243.3
7.5°	289.7	284.1	282.7	278.5	274.3	271.5	268.7	264.5	261.7	256.1	254.6
10°	323.5	316.5	310.9	305.3	301.0	294.0	289.7	284.1	278.5	274.3	270.1
12.5°	367.2	357.3	348.8	343.2	333.4	325.0	316.5	312.2	301.0	295.4	288.4
15°	414.9	403.7	393.9	382.6	375.5	361.6	350.3	337.6	332.0	322.1	310.9
17.5°	476.9	458.5	443.1	431.8	417.8	403.7	391.1	378.3	361.6	350.3	336.2
20°	543.0	527.5	506.4	486.7	469.8	453.0	434.6	417.8	402.3	384.0	367.2
22.5°	627.4	604.9	579.6	559.9	537.3	519.1	493.8	471.2	445.9	422.0	402.3
25°	734.3	704.8	680.8	652.6	626.0	597.8	566.8	538.8	506.4	483.9	450.2
27.5°	866.5	838.3	806.0	769.4	742.7	700.5	659.7	624.6	586.5	551.4	513.5
30°	1035.3	994.5	960.7	925.6	872.1	831.3	783.5	735.6	683.6	648.5	590.8
32.5°	1237.8	1194.2	1143.6	1093.0	1043.7	986.1	926.9	867.9	810.3	745.5	686.4
35°	1485.4	1433.4	1375.8	1320.8	1244.9	1183.0	1108.4	1026.8	962.2	887.6	813.1
37.5°	1813.2	1727.4	1676.7	1619.1	1516.4	1432.0	1349.0	1267.4	1153.5	1074.7	969.2
40°	2223.9	2173.3	2090.3	1997.4	1904.6	1793.5	1680.9	1572.6	1440.4	1330.7	1208.3
42.5°	2706.4	2631.8	2547.5	2413.8	2319.6	2188.7	2060.7	1917.3	1755.5	1614.8	1471.4
45°	3159.4	3070.7	3006.0	2872.3	2773.9	2619.2	2464.5	2312.5	2125.5	1944.0	1778.0
47.5°	3648.8	3575.8	3468.8	3360.5	3260.6	3086.2	2918.8	2734.5	2537.6	2322.4	2107.2
50°	4079.3	4021.7	3948.5	3817.6	3706.5	3560.2	3363.3	3162.2	2913.2	2699.4	2454.6
52.5°	4445.0	4400.0	4297.3	4204.5	4104.6	3966.7	3790.9	3598.2	3329.5	3094.6	2816.2
55°	4876.9	4844.6	4754.5	4696.8	4608.2	4476.0	4311.4	4132.7	3848.6	3592.5	3277.5
57.5°	5584.5	5559.1	5480.3	5456.4	5369.2	5253.9	5051.3	4860.0	4528.0	4210.2	3850.1
60°	6756.2	6705.5	6590.2	6531.1	6346.8	6192.1	5929.0	5666.0	5265.1	4860.0	4426.7
62.5°	8010.9	7868.8	7649.3	7460.8	7199.3	6930.6	6578.9	6176.6	5706.7	5225.7	4727.8
65°	8687.5	8445.5	8168.4	7868.8	7529.8	7134.5	6691.4	6208.9	5703.9	5196.2	4670.1
66°	8764.9	8491.9	8197.9	7864.6	7487.6	7067.0	6616.9	6110.5	5585.8	5090.7	4564.6
67.5°	8667.8	8382.3	8071.4	7701.5	7293.5	6857.4	6384.8	5858.7	5353.7	4851.5	4339.5
70°	7988.4	7704.2	7427.2	7037.5	6602.8	6163.9	5716.6	5128.6	4650.4	4189.0	3733.3
72.5°	6379.2	6186.4	5912.1	5578.8	5155.3	4640.5	4267.8	3741.7	3326.7	2879.4	2526.3
75°	3986.4	3714.9	3376.0	2951.2	2627.7	2209.8	1991.8	1592.3	1356.1	1149.2	949.5
77.5°	2038.2	1834.3	1596.6	1357.4	1128.1	900.2	696.3	492.3	332.0	230.7	171.6
80°	1683.7	1503.7	1306.7	1088.7	886.2	687.9	495.1	337.6	215.2	140.6	109.7
82.5°	1391.2	1239.3	1063.4	860.8	685.1	540.1	375.5	244.8	151.9	98.4	77.4
85°	592.2	537.3	414.9	329.1	247.6	182.9	128.0	85.8	60.5	49.2	45.0
87.5°	25.3	28.1	26.7	21.1	15.4	15.4	14.1	11.3	11.3	11.3	11.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P150468

CATALOG NUMBER: VXS-E05-LED-E1-SL3-HSS-8030

CANDELA DISTRIBUTION (continued):

	80°	81°	82°	83°	84°	85°	95°	105°	115°	125°	135°
0°	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8
2.5°	230.7	229.3	227.9	227.9	226.4	225.1	216.6	209.6	201.1	195.5	189.9
5°	240.5	239.2	236.3	234.9	232.1	230.7	212.4	196.9	184.2	174.4	167.4
7.5°	250.4	249.0	244.8	240.5	239.2	236.3	206.7	187.0	170.2	159.0	151.9
10°	263.0	258.9	254.6	249.0	244.8	240.5	201.1	175.9	157.5	147.7	140.6
12.5°	281.3	274.3	267.3	260.2	254.6	247.6	198.3	166.0	147.7	136.5	129.4
15°	302.4	292.5	284.1	275.8	265.9	258.9	192.7	157.5	139.3	128.0	119.6
17.5°	322.1	310.9	298.2	285.6	275.8	265.9	187.0	149.1	130.8	119.6	111.1
20°	350.3	333.4	317.9	302.4	288.4	275.8	178.7	140.6	123.8	111.1	102.7
22.5°	381.2	361.6	341.9	320.7	302.4	285.6	171.6	133.7	116.8	104.0	94.2
25°	420.6	396.7	369.9	343.2	322.1	299.6	164.6	126.6	109.7	97.1	87.3
27.5°	475.4	441.7	412.1	378.3	346.0	320.7	159.0	120.9	102.7	90.1	80.2
30°	550.1	500.7	454.3	417.8	379.8	343.2	153.4	114.0	97.1	83.0	71.7
32.5°	633.0	575.3	521.9	467.0	419.2	377.0	147.7	108.3	90.1	76.0	66.1
35°	735.6	662.5	590.8	527.5	469.8	413.6	142.1	102.7	84.4	68.9	59.1
37.5°	883.4	791.9	697.7	616.1	541.6	467.0	137.8	97.1	77.4	61.9	52.0
40°	1085.9	967.8	852.4	741.3	644.2	551.4	132.2	91.4	71.7	56.3	46.4
42.5°	1305.4	1161.9	1009.9	884.8	751.2	634.4	126.6	85.8	66.1	50.7	40.8
45°	1578.2	1399.6	1215.3	1045.2	882.0	731.5	120.9	80.2	59.1	45.0	35.1
47.5°	1876.5	1648.6	1440.4	1226.6	1032.4	852.4	114.0	76.0	53.5	39.4	31.0
50°	2183.1	1942.6	1679.6	1436.2	1205.5	973.4	106.9	68.9	47.9	35.1	25.3
52.5°	2513.7	2229.5	1960.8	1658.4	1389.7	1132.3	99.9	63.3	43.6	31.0	21.1
55°	2934.3	2616.4	2301.2	1962.3	1638.8	1316.6	92.8	56.3	38.0	26.7	16.9
57.5°	3463.2	3086.2	2699.4	2316.8	1924.2	1558.5	87.3	49.2	32.3	22.5	14.1
60°	3962.5	3522.3	3053.9	2613.6	2170.5	1744.2	78.8	43.6	28.1	18.2	14.1
62.5°	4221.3	3719.2	3214.2	2728.9	2256.3	1810.4	70.4	36.6	23.9	15.4	12.6
65°	4158.0	3646.0	3156.5	2667.0	2204.2	1768.2	61.9	32.3	21.1	14.1	12.6
66°	4066.6	3560.2	3067.9	2602.3	2160.6	1723.1	57.7	31.0	19.7	14.1	11.3
67.5°	3866.8	3377.4	2907.6	2474.3	2041.0	1637.3	52.0	28.1	18.2	12.6	11.3
70°	3302.8	2858.3	2482.7	2097.3	1744.2	1379.9	42.2	23.9	15.4	11.3	11.3
72.5°	2185.9	1883.5	1633.2	1405.3	1174.5	911.5	35.1	19.7	12.6	11.3	9.8
75°	824.2	745.5	640.0	575.3	502.2	440.3	28.1	12.6	9.8	9.8	9.8
77.5°	146.3	135.0	119.6	109.7	101.2	92.8	22.5	8.4	8.4	9.8	9.8
80°	98.4	91.4	83.0	76.0	70.4	63.3	15.4	7.0	8.4	8.4	9.8
82.5°	70.4	66.1	61.9	56.3	52.0	46.4	9.8	7.0	8.4	8.4	8.4
85°	42.2	39.4	36.6	33.8	29.5	28.1	7.0	7.0	7.0	8.4	8.4
87.5°	11.3	9.8	11.3	11.3	8.4	9.8	5.6	5.6	5.6	7.0	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P150468

CATALOG NUMBER: VXS-E05-LED-E1-SL3-HSS-8030

CANDELA DISTRIBUTION (continued):

	145°	155°	165°	175°	180°
0°	220.8	220.8	220.8	220.8	220.8
2.5°	187.0	187.0	184.2	188.5	188.5
5°	161.8	161.8	160.3	161.8	161.8
7.5°	147.7	146.3	146.3	146.3	147.7
10°	135.0	133.7	133.7	133.7	133.7
12.5°	123.8	122.4	120.9	122.4	122.4
15°	114.0	111.1	111.1	111.1	111.1
17.5°	105.5	102.7	101.2	101.2	101.2
20°	97.1	92.8	92.8	92.8	92.8
22.5°	88.6	84.4	84.4	84.4	84.4
25°	80.2	76.0	76.0	76.0	76.0
27.5°	73.2	68.9	68.9	68.9	68.9
30°	64.7	61.9	61.9	63.3	61.9
32.5°	59.1	54.8	54.8	56.3	56.3
35°	52.0	49.2	49.2	49.2	49.2
37.5°	45.0	42.2	42.2	42.2	42.2
40°	39.4	36.6	35.1	36.6	36.6
42.5°	33.8	31.0	29.5	29.5	29.5
45°	29.5	25.3	23.9	25.3	25.3
47.5°	23.9	21.1	21.1	22.5	22.5
50°	18.2	18.2	19.7	22.5	22.5
52.5°	16.9	16.9	19.7	22.5	22.5
55°	15.4	16.9	19.7	21.1	22.5
57.5°	14.1	16.9	19.7	21.1	21.1
60°	14.1	15.4	18.2	21.1	21.1
62.5°	12.6	14.1	16.9	19.7	19.7
65°	12.6	14.1	16.9	19.7	19.7
66°	12.6	14.1	16.9	19.7	19.7
67.5°	12.6	14.1	16.9	19.7	19.7
70°	12.6	14.1	16.9	18.2	18.2
72.5°	11.3	12.6	15.4	18.2	18.2
75°	11.3	12.6	15.4	18.2	18.2
77.5°	11.3	12.6	15.4	18.2	18.2
80°	11.3	12.6	15.4	16.9	18.2
82.5°	9.8	12.6	14.1	16.9	16.9
85°	9.8	11.3	14.1	15.4	16.9
87.5°	8.4	9.8	11.3	14.1	14.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)