

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P672663

Luminaire Tested: **CCP-SA-2E-727-U-5NQ**

Issue Date: 04/16/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P672663  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-2E-727-U-5NQ  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/ 5NQ  
distribution lens  
Light Source: (32) 2700K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11899.2 lumens  
Efficiency: N/A  
Efficacy: 111.6 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G1


Input Watts (W): 106.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P672663

CATALOG NUMBER: CCP-SA-2E-727-U-5NQ

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 6.2 fc  
 Type V - Short - N/A

REPORT NUMBER: P672663  
CATALOG NUMBER: CCP-SA-2E-727-U-5NQ

## Luminous Intensity Polar Plot



REPORT NUMBER: P672663

CATALOG NUMBER: CCP-SA-2E-727-U-5NQ

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 5949.6   | 0.0    | 5949.6  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 5949.6   | 0.0    | 5949.6  |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 11899.2  | 0.0    | 11899.2 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 135.5   | 1.1       |
| 10°-20°   | 442.4   | 3.7       |
| 20°-30°   | 839.0   | 7.1       |
| 30°-40°   | 1407.1  | 11.8      |
| 40°-50°   | 2226.5  | 18.7      |
| 50°-60°   | 3497.9  | 29.4      |
| 60°-70°   | 2955.5  | 24.8      |
| 70°-80°   | 344.1   | 2.9       |
| 80°-90°   | 51.3    | 0.4       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 11899.2 | 100.0     |
| 0°-180°   | 11899.2 | 100.0     |



REPORT NUMBER: P672663


CATALOG NUMBER: CCP-SA-2E-727-U-5NQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 708.4  | 6.0       |                         |      |         |
| FM   | (30°-60°)   | 3565.8 | 30.0      |                         |      |         |
| FH   | (60°-80°)   | 1649.8 | 13.9      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 25.6   | 0.2       |                         |      | G1/100  |
| BL   | (0°-30°)    | 708.4  | 6.0       | B2/1000                 |      |         |
| BM   | (30°-60°)   | 3565.8 | 30.0      | B3/5000                 |      |         |
| BH   | (60°-80°)   | 1649.8 | 13.9      | B3/2500                 |      | G1/1800 |
| BVH  | (80°-90°)   | 25.6   | 0.2       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G1**

Type V Short



REPORT NUMBER: P672663

CATALOG NUMBER: CCP-SA-2E-727-U-5NQ

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1368.2 | 1368.2 | 1368.2 | 1368.2 | 1368.2 | 1368.2 | 1368.2 | 1368.2 | 1368.2 | 1368.2 | 1368.2 |
| 2.5°  | 1375.7 | 1371.6 | 1375.7 | 1375.7 | 1373.2 | 1374.1 | 1370.7 | 1369.9 | 1374.1 | 1370.7 | 1369.9 |
| 5°    | 1404.2 | 1400.8 | 1404.2 | 1401.7 | 1397.5 | 1398.3 | 1393.3 | 1391.6 | 1396.6 | 1391.6 | 1392.5 |
| 7.5°  | 1436.8 | 1430.9 | 1432.6 | 1435.1 | 1430.9 | 1430.9 | 1426.7 | 1424.2 | 1426.7 | 1421.7 | 1425.1 |
| 10°   | 1464.4 | 1459.4 | 1461.9 | 1465.2 | 1464.4 | 1466.9 | 1462.7 | 1461.0 | 1458.5 | 1452.7 | 1457.7 |
| 12.5° | 1500.3 | 1498.7 | 1502.0 | 1506.2 | 1504.5 | 1507.9 | 1498.7 | 1496.2 | 1495.3 | 1488.6 | 1494.5 |
| 15°   | 1547.2 | 1543.0 | 1548.8 | 1553.9 | 1551.4 | 1557.2 | 1549.7 | 1546.3 | 1542.2 | 1533.8 | 1538.8 |
| 17.5° | 1594.0 | 1590.7 | 1599.0 | 1601.5 | 1602.4 | 1607.4 | 1601.5 | 1596.5 | 1594.8 | 1589.0 | 1585.6 |
| 20°   | 1650.0 | 1645.9 | 1652.6 | 1657.6 | 1653.4 | 1659.2 | 1656.7 | 1653.4 | 1651.7 | 1642.5 | 1641.7 |
| 22.5° | 1712.8 | 1706.9 | 1716.9 | 1722.8 | 1716.9 | 1722.8 | 1717.8 | 1716.9 | 1717.8 | 1704.4 | 1706.1 |
| 25°   | 1783.0 | 1783.9 | 1793.9 | 1798.1 | 1794.7 | 1798.1 | 1790.5 | 1795.6 | 1793.1 | 1778.8 | 1773.8 |
| 27.5° | 1873.3 | 1870.0 | 1880.9 | 1893.4 | 1885.0 | 1885.0 | 1881.7 | 1886.7 | 1885.9 | 1872.5 | 1869.2 |
| 30°   | 1978.7 | 1977.9 | 1993.8 | 2001.3 | 1989.6 | 1984.6 | 1983.7 | 1996.3 | 1997.1 | 1982.9 | 1977.0 |
| 32.5° | 2089.1 | 2089.1 | 2108.3 | 2117.5 | 2100.8 | 2097.5 | 2094.1 | 2110.9 | 2108.3 | 2089.1 | 2076.6 |
| 35°   | 2210.4 | 2205.4 | 2231.3 | 2244.7 | 2227.9 | 2217.9 | 2216.2 | 2231.3 | 2227.9 | 2201.2 | 2186.1 |
| 37.5° | 2330.0 | 2333.3 | 2363.4 | 2378.5 | 2358.4 | 2345.9 | 2350.0 | 2360.1 | 2360.9 | 2331.6 | 2315.7 |
| 40°   | 2476.3 | 2477.2 | 2514.8 | 2526.5 | 2500.6 | 2481.3 | 2487.2 | 2509.8 | 2508.1 | 2472.1 | 2452.1 |
| 42.5° | 2640.2 | 2636.9 | 2683.7 | 2693.8 | 2658.6 | 2621.8 | 2639.4 | 2674.5 | 2682.9 | 2642.7 | 2621.8 |
| 45°   | 2815.9 | 2820.9 | 2869.4 | 2880.3 | 2825.1 | 2778.2 | 2815.9 | 2868.6 | 2879.4 | 2835.9 | 2810.0 |
| 47.5° | 3029.1 | 3035.0 | 3093.5 | 3097.7 | 3035.0 | 2973.9 | 3024.1 | 3092.7 | 3096.9 | 3036.6 | 3006.5 |
| 50°   | 3272.5 | 3292.6 | 3357.8 | 3366.2 | 3304.3 | 3225.7 | 3297.6 | 3358.6 | 3342.7 | 3262.5 | 3234.9 |
| 52.5° | 3548.5 | 3564.4 | 3666.4 | 3701.5 | 3647.2 | 3562.7 | 3620.4 | 3658.0 | 3607.0 | 3501.6 | 3459.0 |
| 55°   | 3783.5 | 3810.2 | 3945.7 | 4052.8 | 4093.7 | 4030.2 | 4023.5 | 3968.3 | 3826.1 | 3665.6 | 3621.2 |
| 57.5° | 3849.5 | 3875.5 | 4085.4 | 4361.4 | 4604.7 | 4636.5 | 4489.3 | 4212.5 | 3906.4 | 3658.9 | 3613.7 |
| 60°   | 3581.1 | 3616.2 | 3923.1 | 4445.8 | 5144.2 | 5431.8 | 4900.0 | 4233.4 | 3698.2 | 3366.2 | 3309.3 |
| 62.5° | 2812.5 | 2877.7 | 3274.2 | 4093.7 | 5361.6 | 6156.1 | 5068.9 | 3873.0 | 3070.1 | 2677.9 | 2602.6 |
| 65°   | 1529.6 | 1585.6 | 2023.0 | 3050.9 | 4920.9 | 6310.8 | 4654.9 | 2948.8 | 2008.0 | 1614.1 | 1573.1 |
| 67.5° | 573.7  | 614.7  | 815.4  | 1507.9 | 3479.1 | 5395.0 | 3533.4 | 1688.5 | 911.6  | 654.0  | 596.3  |
| 70°   | 244.2  | 249.2  | 295.2  | 525.2  | 1581.5 | 3510.0 | 1808.9 | 573.7  | 304.4  | 245.9  | 239.2  |
| 72.5° | 175.6  | 176.5  | 189.0  | 232.5  | 481.7  | 1539.7 | 546.9  | 240.9  | 185.7  | 167.3  | 167.3  |
| 75°   | 140.5  | 141.3  | 148.9  | 168.1  | 227.5  | 453.3  | 235.8  | 168.9  | 143.8  | 131.3  | 129.6  |
| 77.5° | 110.4  | 112.1  | 119.6  | 131.3  | 152.2  | 207.4  | 159.7  | 133.0  | 115.4  | 103.7  | 102.0  |
| 80°   | 82.0   | 84.5   | 94.5   | 100.4  | 107.0  | 138.0  | 116.2  | 103.7  | 92.0   | 79.4   | 76.9   |
| 82.5° | 54.4   | 56.9   | 70.3   | 74.4   | 73.6   | 87.0   | 80.3   | 79.4   | 70.3   | 52.7   | 50.2   |
| 85°   | 32.6   | 34.3   | 45.2   | 48.5   | 45.2   | 42.7   | 51.0   | 55.2   | 49.3   | 34.3   | 31.8   |
| 87.5° | 14.2   | 14.2   | 20.1   | 20.9   | 20.1   | 15.9   | 24.3   | 28.4   | 29.3   | 17.6   | 15.9   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

INVUE

Report Number: SP1-2012-088-8-R2

Luminaire Tested: CCW-SA1B-727-U-SL4

Test Date: 01/20/2021

### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2012-088-8-R2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 01/20/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: INVUE  
 Catalog Number: **CCW-SA1B-727-U-SL4**  
 Description: INVUE WALL PACK

\*\*\*THIS IS A REVISION OF SP1-2012-088-8. TO UPDATE THE CATALOG INFORMATION.\*\*\*TESTED  
 IN SITU. INVUE WALL PACK LIGHT SQUARE SL4 OPTICS 1-SQUARE

### Spectral Parameters

|                           |         |           |      |      |      |
|---------------------------|---------|-----------|------|------|------|
| CCT (K):                  | 2705    | CRI (Ra): | 73.8 |      |      |
| CIE u':                   | 0.2629  | R1:       | 72.2 | R9:  | -7.6 |
| CIE v':                   | 0.5237  | R2:       | 81.9 | R10: | 56.9 |
| Duv:                      | -0.0024 | R3:       | 89.3 | R11: | 66.0 |
| CIE x:                    | 0.4552  | R4:       | 71.3 | R12: | 47.9 |
| CIE y:                    | 0.4030  | R5:       | 69.5 | R13: | 73.4 |
| CIE z:                    | 0.1418  | R6:       | 73.6 | R14: | 93.2 |
| Peak Wavelength (nm):     | 603     | R7:       | 80.1 |      |      |
| Dominant Wavelength (nm): | 585     | R8:       | 52.8 |      |      |
| Purity:                   | 57.7    |           |      |      |      |
| Rf:                       | 71.2    |           |      |      |      |
| Rg:                       | 100.1   |           |      |      |      |



### Test Conditions

Stabilization Time: 177M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.8/34%  
 Sphere Temperature (°C): 24.7

REPORT NUMBER: SP1-2012-088-8-R2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 7/29/2020        | 1/29/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2012-088-8-R2

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2012-088-8-R2

### Photopic Flux vs. Wavelength



#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 926              | 0.0              | 490       | 3601             | 0.5              | 620       | 58340            | 15.2             | 750       | 3861             | 0.0              | 880       | 1742             | 0.0              |
| 365       | 867              | 0.0              | 495       | 5135             | 0.9              | 625       | 56180            | 12.4             | 755       | 3520             | 0.0              | 885       | 1920             | 0.0              |
| 370       | 1032             | 0.0              | 500       | 7689             | 1.7              | 630       | 53018            | 9.6              | 760       | 3223             | 0.0              | 890       | 1286             | 0.0              |
| 375       | 1034             | 0.0              | 505       | 11015            | 3.1              | 635       | 49683            | 7.5              | 765       | 2910             | 0.0              | 895       | 1660             | 0.0              |
| 380       | 979              | 0.0              | 510       | 14817            | 5.1              | 640       | 46308            | 5.5              | 770       | 2560             | 0.0              | 900       | 1274             | 0.0              |
| 385       | 938              | 0.0              | 515       | 18962            | 7.9              | 645       | 42927            | 4.1              | 775       | 2242             | 0.0              | 905       | 1020             | 0.0              |
| 390       | 893              | 0.0              | 520       | 22933            | 11.1             | 650       | 39728            | 2.9              | 780       | 2156             | 0.0              | 910       | 1258             | 0.0              |
| 395       | 757              | 0.0              | 525       | 26438            | 14.2             | 655       | 36260            | 2.1              | 785       | 1926             | 0.0              | 915       | 1481             | 0.0              |
| 400       | 728              | 0.0              | 530       | 29492            | 17.4             | 660       | 32543            | 1.4              | 790       | 1871             | 0.0              | 920       | 923              | 0.0              |
| 405       | 812              | 0.0              | 535       | 32054            | 19.9             | 665       | 29105            | 0.9              | 795       | 1697             | 0.0              | 925       | 1444             | 0.0              |
| 410       | 1197             | 0.0              | 540       | 34386            | 22.4             | 670       | 25817            | 0.6              | 800       | 1691             | 0.0              | 930       | 1315             | 0.0              |
| 415       | 2254             | 0.0              | 545       | 36784            | 24.5             | 675       | 22832            | 0.4              | 805       | 1967             | 0.0              | 935       | 1037             | 0.0              |
| 420       | 4742             | 0.0              | 550       | 39017            | 26.5             | 680       | 20201            | 0.2              | 810       | 1719             | 0.0              | 940       | 1195             | 0.0              |
| 425       | 8975             | 0.0              | 555       | 41253            | 28.2             | 685       | 17863            | 0.2              | 815       | 1436             | 0.0              | 945       | 914              | 0.0              |
| 430       | 14905            | 0.1              | 560       | 43733            | 29.7             | 690       | 15761            | 0.1              | 820       | 1465             | 0.0              | 950       | 1373             | 0.0              |
| 435       | 22096            | 0.3              | 565       | 46694            | 31.0             | 695       | 13762            | 0.1              | 825       | 1365             | 0.0              | 955       | 692              | 0.0              |
| 440       | 28868            | 0.5              | 570       | 49493            | 32.2             | 700       | 12064            | 0.0              | 830       | 1404             | 0.0              | 960       | 844              | 0.0              |
| 445       | 31683            | 0.7              | 575       | 52587            | 32.7             | 705       | 10683            | 0.0              | 835       | 1222             | 0.0              | 965       | 1427             | 0.0              |
| 450       | 25690            | 0.7              | 580       | 55129            | 32.8             | 710       | 9480             | 0.0              | 840       | 1144             | 0.0              | 970       | 654              | 0.0              |
| 455       | 14802            | 0.5              | 585       | 57737            | 32.1             | 715       | 8582             | 0.0              | 845       | 1078             | 0.0              | 975       | 1127             | 0.0              |
| 460       | 8755             | 0.4              | 590       | 59688            | 30.9             | 720       | 7530             | 0.0              | 850       | 1254             | 0.0              | 980       | 1935             | 0.0              |
| 465       | 5978             | 0.3              | 595       | 61458            | 29.1             | 725       | 6824             | 0.0              | 855       | 1203             | 0.0              | 985       | 1754             | 0.0              |
| 470       | 4047             | 0.3              | 600       | 62443            | 26.9             | 730       | 5968             | 0.0              | 860       | 1183             | 0.0              | 990       | 1822             | 0.0              |
| 475       | 3070             | 0.2              | 605       | 62403            | 24.2             | 735       | 5266             | 0.0              | 865       | 1505             | 0.0              | 995       | 1176             | 0.0              |
| 480       | 2814             | 0.3              | 610       | 61581            | 21.2             | 740       | 4712             | 0.0              | 870       | 1624             | 0.0              | 1000      | 2143             | 0.0              |
| 485       | 2926             | 0.3              | 615       | 60386            | 18.2             | 745       | 4264             | 0.0              | 875       | 1559             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2012-088-8-R2

### Scotopic Flux vs. Wavelength



Scotopic Lumens: 1073.3

S/P: 0.36

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 926              | 0.0              | 490       | 3601             | 5.5              | 620       | 58340            | 0.7              | 750       | 3861             | 0.0              | 880       | 1742             | 0.0              |
| 365       | 867              | 0.0              | 495       | 5135             | 8.3              | 625       | 56180            | 0.5              | 755       | 3520             | 0.0              | 885       | 1920             | 0.0              |
| 370       | 1032             | 0.0              | 500       | 7689             | 12.9             | 630       | 53018            | 0.3              | 760       | 3223             | 0.0              | 890       | 1286             | 0.0              |
| 375       | 1034             | 0.0              | 505       | 11015            | 18.7             | 635       | 49683            | 0.2              | 765       | 2910             | 0.0              | 895       | 1660             | 0.0              |
| 380       | 979              | 0.0              | 510       | 14817            | 25.1             | 640       | 46308            | 0.1              | 770       | 2560             | 0.0              | 900       | 1274             | 0.0              |
| 385       | 938              | 0.0              | 515       | 18962            | 31.4             | 645       | 42927            | 0.1              | 775       | 2242             | 0.0              | 905       | 1020             | 0.0              |
| 390       | 893              | 0.0              | 520       | 22933            | 36.5             | 650       | 39728            | 0.0              | 780       | 2156             | 0.0              | 910       | 1258             | 0.0              |
| 395       | 757              | 0.0              | 525       | 26438            | 39.6             | 655       | 36260            | 0.0              | 785       | 1926             | 0.0              | 915       | 1481             | 0.0              |
| 400       | 728              | 0.0              | 530       | 29492            | 40.7             | 660       | 32543            | 0.0              | 790       | 1871             | 0.0              | 920       | 923              | 0.0              |
| 405       | 812              | 0.0              | 535       | 32054            | 39.9             | 665       | 29105            | 0.0              | 795       | 1697             | 0.0              | 925       | 1444             | 0.0              |
| 410       | 1197             | 0.1              | 540       | 34386            | 38.0             | 670       | 25817            | 0.0              | 800       | 1691             | 0.0              | 930       | 1315             | 0.0              |
| 415       | 2254             | 0.2              | 545       | 36784            | 35.3             | 675       | 22832            | 0.0              | 805       | 1967             | 0.0              | 935       | 1037             | 0.0              |
| 420       | 4742             | 0.8              | 550       | 39017            | 31.9             | 680       | 20201            | 0.0              | 810       | 1719             | 0.0              | 940       | 1195             | 0.0              |
| 425       | 8975             | 2.2              | 555       | 41253            | 28.2             | 685       | 17863            | 0.0              | 815       | 1436             | 0.0              | 945       | 914              | 0.0              |
| 430       | 14905            | 5.1              | 560       | 43733            | 24.4             | 690       | 15761            | 0.0              | 820       | 1465             | 0.0              | 950       | 1373             | 0.0              |
| 435       | 22096            | 9.9              | 565       | 46694            | 20.9             | 695       | 13762            | 0.0              | 825       | 1365             | 0.0              | 955       | 692              | 0.0              |
| 440       | 28868            | 16.1             | 570       | 49493            | 17.5             | 700       | 12064            | 0.0              | 830       | 1404             | 0.0              | 960       | 844              | 0.0              |
| 445       | 31683            | 21.2             | 575       | 52587            | 14.3             | 705       | 10683            | 0.0              | 835       | 1222             | 0.0              | 965       | 1427             | 0.0              |
| 450       | 25690            | 19.9             | 580       | 55129            | 11.4             | 710       | 9480             | 0.0              | 840       | 1144             | 0.0              | 970       | 654              | 0.0              |
| 455       | 14802            | 12.9             | 585       | 57737            | 8.8              | 715       | 8582             | 0.0              | 845       | 1078             | 0.0              | 975       | 1127             | 0.0              |
| 460       | 8755             | 8.5              | 590       | 59688            | 6.6              | 720       | 7530             | 0.0              | 850       | 1254             | 0.0              | 980       | 1935             | 0.0              |
| 465       | 5978             | 6.3              | 595       | 61458            | 4.9              | 725       | 6824             | 0.0              | 855       | 1203             | 0.0              | 985       | 1754             | 0.0              |
| 470       | 4047             | 4.7              | 600       | 62443            | 3.5              | 730       | 5968             | 0.0              | 860       | 1183             | 0.0              | 990       | 1822             | 0.0              |
| 475       | 3070             | 3.8              | 605       | 62403            | 2.5              | 735       | 5266             | 0.0              | 865       | 1505             | 0.0              | 995       | 1176             | 0.0              |
| 480       | 2814             | 3.8              | 610       | 61581            | 1.7              | 740       | 4712             | 0.0              | 870       | 1624             | 0.0              | 1000      | 2143             | 0.0              |
| 485       | 2926             | 4.2              | 615       | 60386            | 1.1              | 745       | 4264             | 0.0              | 875       | 1559             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2012-088-8-R2

### Melanopic Flux vs. Wavelength



**Melanopic Lumens: 3157.6 S/P: 1.07**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 926              | 0.0              | 490       | 3601             | 3.0              | 620       | 58340            | 0.0              | 750       | 3861             | 0.0              | 880       | 1742             | 0.0              |
| 365       | 867              | 0.0              | 495       | 5135             | 4.2              | 625       | 56180            | 0.0              | 755       | 3520             | 0.0              | 885       | 1920             | 0.0              |
| 370       | 1032             | 0.0              | 500       | 7689             | 6.2              | 630       | 53018            | 0.0              | 760       | 3223             | 0.0              | 890       | 1286             | 0.0              |
| 375       | 1034             | 0.0              | 505       | 11015            | 8.5              | 635       | 49683            | 0.0              | 765       | 2910             | 0.0              | 895       | 1660             | 0.0              |
| 380       | 979              | 0.0              | 510       | 14817            | 10.6             | 640       | 46308            | 0.0              | 770       | 2560             | 0.0              | 900       | 1274             | 0.0              |
| 385       | 938              | 0.0              | 515       | 18962            | 12.4             | 645       | 42927            | 0.0              | 775       | 2242             | 0.0              | 905       | 1020             | 0.0              |
| 390       | 893              | 0.0              | 520       | 22933            | 13.4             | 650       | 39728            | 0.0              | 780       | 2156             | 0.0              | 910       | 1258             | 0.0              |
| 395       | 757              | 0.0              | 525       | 26438            | 13.4             | 655       | 36260            | 0.0              | 785       | 1926             | 0.0              | 915       | 1481             | 0.0              |
| 400       | 728              | 0.0              | 530       | 29492            | 12.7             | 660       | 32543            | 0.0              | 790       | 1871             | 0.0              | 920       | 923              | 0.0              |
| 405       | 812              | 0.0              | 535       | 32054            | 11.5             | 665       | 29105            | 0.0              | 795       | 1697             | 0.0              | 925       | 1444             | 0.0              |
| 410       | 1197             | 0.0              | 540       | 34386            | 10.1             | 670       | 25817            | 0.0              | 800       | 1691             | 0.0              | 930       | 1315             | 0.0              |
| 415       | 2254             | 0.1              | 545       | 36784            | 8.5              | 675       | 22832            | 0.0              | 805       | 1967             | 0.0              | 935       | 1037             | 0.0              |
| 420       | 4742             | 0.5              | 550       | 39017            | 7.0              | 680       | 20201            | 0.0              | 810       | 1719             | 0.0              | 940       | 1195             | 0.0              |
| 425       | 8975             | 1.4              | 555       | 41253            | 5.6              | 685       | 17863            | 0.0              | 815       | 1436             | 0.0              | 945       | 914              | 0.0              |
| 430       | 14905            | 3.1              | 560       | 43733            | 4.3              | 690       | 15761            | 0.0              | 820       | 1465             | 0.0              | 950       | 1373             | 0.0              |
| 435       | 22096            | 5.9              | 565       | 46694            | 3.3              | 695       | 13762            | 0.0              | 825       | 1365             | 0.0              | 955       | 692              | 0.0              |
| 440       | 28868            | 9.6              | 570       | 49493            | 2.4              | 700       | 12064            | 0.0              | 830       | 1404             | 0.0              | 960       | 844              | 0.0              |
| 445       | 31683            | 12.5             | 575       | 52587            | 1.8              | 705       | 10683            | 0.0              | 835       | 1222             | 0.0              | 965       | 1427             | 0.0              |
| 450       | 25690            | 11.8             | 580       | 55129            | 1.2              | 710       | 9480             | 0.0              | 840       | 1144             | 0.0              | 970       | 654              | 0.0              |
| 455       | 14802            | 7.8              | 585       | 57737            | 0.9              | 715       | 8582             | 0.0              | 845       | 1078             | 0.0              | 975       | 1127             | 0.0              |
| 460       | 8755             | 5.2              | 590       | 59688            | 0.6              | 720       | 7530             | 0.0              | 850       | 1254             | 0.0              | 980       | 1935             | 0.0              |
| 465       | 5978             | 3.9              | 595       | 61458            | 0.4              | 725       | 6824             | 0.0              | 855       | 1203             | 0.0              | 985       | 1754             | 0.0              |
| 470       | 4047             | 2.9              | 600       | 62443            | 0.3              | 730       | 5968             | 0.0              | 860       | 1183             | 0.0              | 990       | 1822             | 0.0              |
| 475       | 3070             | 2.3              | 605       | 62403            | 0.2              | 735       | 5266             | 0.0              | 865       | 1505             | 0.0              | 995       | 1176             | 0.0              |
| 480       | 2814             | 2.3              | 610       | 61581            | 0.1              | 740       | 4712             | 0.0              | 870       | 1624             | 0.0              | 1000      | 2143             | 0.0              |
| 485       | 2926             | 2.4              | 615       | 60386            | 0.1              | 745       | 4264             | 0.0              | 875       | 1559             | 0.0              |           |                  |                  |



### Summary

$R_f = 71.2$   
 $R_g = 100.1$   
 CIE  $R_a = 73.8$   
 $R_g = -7.6$

### Spectral Power Distribution Comparison




### Color Vector Graphics







**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 55 | CES51 = 78 | CES76 = 50 |
| CES02 = 63 | CES27 = 77 | CES52 = 80 | CES77 = 75 |
| CES03 = 31 | CES28 = 80 | CES53 = 68 | CES78 = 56 |
| CES04 = 71 | CES29 = 46 | CES54 = 80 | CES79 = 81 |
| CES05 = 50 | CES30 = 51 | CES55 = 78 | CES80 = 80 |
| CES06 = 52 | CES31 = 51 | CES56 = 67 | CES81 = 73 |
| CES07 = 43 | CES32 = 49 | CES57 = 64 | CES82 = 91 |
| CES08 = 41 | CES33 = 55 | CES58 = 67 | CES83 = 84 |
| CES09 = 29 | CES34 = 65 | CES59 = 86 | CES84 = 89 |
| CES10 = 77 | CES35 = 82 | CES60 = 91 | CES85 = 84 |
| CES11 = 60 | CES36 = 84 | CES61 = 85 | CES86 = 66 |
| CES12 = 66 | CES37 = 75 | CES62 = 75 | CES87 = 78 |
| CES13 = 44 | CES38 = 59 | CES63 = 70 | CES88 = 75 |
| CES14 = 74 | CES39 = 91 | CES64 = 70 | CES89 = 68 |
| CES15 = 72 | CES40 = 85 | CES65 = 67 | CES90 = 71 |
| CES16 = 48 | CES41 = 78 | CES66 = 64 | CES91 = 97 |
| CES17 = 51 | CES42 = 74 | CES67 = 62 | CES92 = 71 |
| CES18 = 57 | CES43 = 63 | CES68 = 68 | CES93 = 82 |
| CES19 = 73 | CES44 = 98 | CES69 = 77 | CES94 = 58 |
| CES20 = 67 | CES45 = 75 | CES70 = 60 | CES95 = 77 |
| CES21 = 88 | CES46 = 70 | CES71 = 59 | CES96 = 80 |
| CES22 = 80 | CES47 = 65 | CES72 = 86 | CES97 = 80 |
| CES23 = 92 | CES48 = 56 | CES73 = 52 | CES98 = 74 |
| CES24 = 91 | CES49 = 68 | CES74 = 93 | CES99 = 68 |
| CES25 = 73 | CES50 = 78 | CES75 = 59 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**


(END OF REPORT)