

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P672595

Luminaire Tested: **CCP-SA-2D-830-U-5MQ**

Issue Date: 04/16/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P672595  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-2D-830-U-5MQ  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @800mA w/ 5MQ  
distribution lens  
Light Source: (32) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9147.7 lumens  
Efficiency: N/A  
Efficacy: 113.2 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B3 - U0 - G2

Input Watts (W): 80.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT


REPORT NUMBER: P672595

CATALOG NUMBER: CCP-SA-2D-830-U-5MQ

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 4.5 fc

Type V - Short - N/A

REPORT NUMBER: P672595  
CATALOG NUMBER: CCP-SA-2D-830-U-5MQ

## Luminous Intensity Polar Plot



REPORT NUMBER: P672595

CATALOG NUMBER: CCP-SA-2D-830-U-5MQ

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 4573.9   | 0.0    | 4573.9 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 4573.9   | 0.0    | 4573.9 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 9147.7   | 0.0    | 9147.7 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 95.7   | 1.0       |
| 10°-20°   | 283.2  | 3.1       |
| 20°-30°   | 483.6  | 5.3       |
| 30°-40°   | 771.8  | 8.4       |
| 40°-50°   | 1245.4 | 13.6      |
| 50°-60°   | 1994.2 | 21.8      |
| 60°-70°   | 2919.5 | 31.9      |
| 70°-80°   | 1284.0 | 14.0      |
| 80°-90°   | 70.4   | 0.8       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 9147.7 | 100.0     |
| 0°-180°   | 9147.7 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P672595


CATALOG NUMBER: CCP-SA-2D-830-U-5MQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 431.3  | 4.7       |                         |      |         |
| FM   | (30°-60°)   | 2005.7 | 21.9      |                         |      |         |
| FH   | (60°-80°)   | 2101.7 | 23.0      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 35.2   | 0.4       |                         |      | G1/100  |
| BL   | (0°-30°)    | 431.3  | 4.7       | B1/500                  |      |         |
| BM   | (30°-60°)   | 2005.7 | 21.9      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 2101.7 | 23.0      | B3/2500                 |      | G2/5000 |
| BVH  | (80°-90°)   | 35.2   | 0.4       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G2**

Type V Short





REPORT NUMBER: P672595

CATALOG NUMBER: CCP-SA-2D-830-U-5MQ

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 1006.0 | 1006.0 | 1006.0 | 1006.0 | 1006.0 | 1006.0 | 1006.0 | 1006.0 | 1006.0 | 1006.0 | 1006.0 |
| 2.5°  | 1004.7 | 1004.0 | 1005.3 | 1006.0 | 1004.7 | 1005.3 | 1001.4 | 1001.4 | 1003.4 | 1001.4 | 1004.0 |
| 5°    | 1009.2 | 1007.9 | 1009.2 | 1009.2 | 1006.0 | 1006.0 | 1001.4 | 1000.1 | 1001.4 | 998.2  | 1000.8 |
| 7.5°  | 1009.8 | 1007.2 | 1009.2 | 1008.5 | 1006.0 | 1006.0 | 999.5  | 996.9  | 997.5  | 994.3  | 996.2  |
| 10°   | 1003.4 | 1002.1 | 1004.7 | 1003.4 | 1001.4 | 1001.4 | 996.2  | 992.3  | 992.3  | 989.1  | 991.0  |
| 12.5° | 999.5  | 998.2  | 1001.4 | 1002.1 | 1000.8 | 1001.4 | 994.9  | 989.7  | 987.8  | 983.9  | 985.2  |
| 15°   | 999.5  | 996.9  | 1002.1 | 1003.4 | 1004.7 | 1009.2 | 999.5  | 990.4  | 986.5  | 981.3  | 982.6  |
| 17.5° | 998.8  | 997.5  | 1003.4 | 1007.9 | 1009.2 | 1014.4 | 1003.4 | 993.6  | 989.1  | 981.3  | 982.6  |
| 20°   | 998.8  | 998.2  | 1005.3 | 1013.7 | 1017.6 | 1022.2 | 1010.5 | 1001.4 | 993.6  | 985.2  | 985.2  |
| 22.5° | 1002.1 | 1001.4 | 1011.1 | 1023.5 | 1034.5 | 1042.2 | 1028.6 | 1013.7 | 1003.4 | 992.3  | 991.0  |
| 25°   | 1015.7 | 1014.4 | 1026.0 | 1041.0 | 1055.9 | 1063.6 | 1050.0 | 1035.1 | 1020.2 | 1007.9 | 1006.6 |
| 27.5° | 1043.5 | 1042.9 | 1054.6 | 1072.7 | 1083.1 | 1088.9 | 1077.3 | 1064.3 | 1049.4 | 1035.1 | 1034.5 |
| 30°   | 1081.1 | 1081.1 | 1096.0 | 1114.8 | 1120.7 | 1125.2 | 1113.5 | 1104.5 | 1088.9 | 1073.4 | 1072.1 |
| 32.5° | 1126.5 | 1129.1 | 1146.6 | 1167.3 | 1171.2 | 1173.8 | 1161.5 | 1155.7 | 1138.8 | 1122.0 | 1119.4 |
| 35°   | 1186.1 | 1186.8 | 1208.2 | 1228.9 | 1234.1 | 1236.7 | 1222.4 | 1217.3 | 1201.7 | 1183.5 | 1179.7 |
| 37.5° | 1262.0 | 1260.0 | 1280.1 | 1303.5 | 1308.6 | 1311.9 | 1300.2 | 1296.3 | 1276.9 | 1258.7 | 1252.9 |
| 40°   | 1346.9 | 1348.2 | 1370.9 | 1392.9 | 1396.1 | 1397.4 | 1391.6 | 1385.8 | 1367.6 | 1346.9 | 1339.8 |
| 42.5° | 1445.4 | 1445.4 | 1472.0 | 1497.9 | 1497.9 | 1491.4 | 1488.8 | 1487.5 | 1470.0 | 1446.7 | 1438.9 |
| 45°   | 1558.2 | 1559.5 | 1592.5 | 1612.0 | 1613.3 | 1595.8 | 1598.4 | 1606.2 | 1589.3 | 1559.5 | 1549.1 |
| 47.5° | 1682.0 | 1683.9 | 1722.8 | 1744.2 | 1740.3 | 1717.6 | 1731.9 | 1735.8 | 1716.3 | 1678.1 | 1664.5 |
| 50°   | 1812.3 | 1818.1 | 1861.5 | 1899.1 | 1893.9 | 1860.9 | 1879.7 | 1881.0 | 1849.2 | 1805.1 | 1786.3 |
| 52.5° | 1952.9 | 1966.5 | 2024.2 | 2064.4 | 2069.6 | 2028.1 | 2044.3 | 2043.0 | 2002.2 | 1941.9 | 1929.6 |
| 55°   | 2127.3 | 2135.1 | 2192.1 | 2249.1 | 2268.6 | 2217.4 | 2235.5 | 2226.4 | 2171.4 | 2102.6 | 2081.9 |
| 57.5° | 2301.6 | 2313.3 | 2386.5 | 2450.7 | 2489.6 | 2446.2 | 2450.1 | 2426.7 | 2357.4 | 2274.4 | 2264.0 |
| 60°   | 2508.4 | 2513.6 | 2594.6 | 2678.2 | 2745.6 | 2719.7 | 2701.6 | 2652.9 | 2571.3 | 2488.3 | 2473.4 |
| 62.5° | 2677.6 | 2687.9 | 2808.5 | 2931.7 | 3045.7 | 3050.3 | 2995.2 | 2922.6 | 2792.3 | 2653.6 | 2623.8 |
| 65°   | 2724.2 | 2741.1 | 2910.3 | 3153.3 | 3390.6 | 3496.2 | 3345.2 | 3123.5 | 2832.5 | 2623.1 | 2578.4 |
| 67.5° | 2507.1 | 2539.5 | 2781.3 | 3185.1 | 3711.4 | 4028.3 | 3623.9 | 3028.2 | 2621.8 | 2377.5 | 2334.7 |
| 70°   | 1949.7 | 1963.9 | 2247.8 | 2802.0 | 3716.6 | 4366.7 | 3511.8 | 2629.6 | 2149.3 | 1886.8 | 1823.9 |
| 72.5° | 1035.8 | 1042.9 | 1298.9 | 1886.8 | 3024.3 | 3772.3 | 2901.8 | 1840.1 | 1265.2 | 1026.7 | 954.7  |
| 75°   | 334.5  | 343.5  | 447.2  | 772.6  | 1668.4 | 2535.0 | 1711.2 | 765.5  | 436.2  | 352.0  | 333.2  |
| 77.5° | 170.5  | 169.8  | 188.6  | 248.9  | 561.3  | 1242.5 | 593.7  | 268.3  | 188.6  | 169.2  | 164.0  |
| 80°   | 106.3  | 104.4  | 118.6  | 136.1  | 196.4  | 363.0  | 213.2  | 150.4  | 119.3  | 102.4  | 101.8  |
| 82.5° | 60.3   | 60.3   | 79.7   | 87.5   | 110.8  | 149.7  | 124.4  | 103.1  | 81.7   | 60.9   | 59.0   |
| 85°   | 33.7   | 29.8   | 49.9   | 55.1   | 63.5   | 73.9   | 75.8   | 66.8   | 55.1   | 33.7   | 35.0   |
| 87.5° | 12.3   | 13.6   | 23.3   | 22.0   | 25.3   | 17.5   | 31.1   | 35.0   | 31.1   | 16.2   | 13.6   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

INVUE

Report Number: SP1-2012-088-3

Luminaire Tested: WIS-SA-830-2D-U-SL4

Test Date: 01/11/2021

### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2012-088-3  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 01/11/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: INVUE  
 Catalog Number: **WIS-SA-830-2D-U-SL4**  
 Description: INVUE. WALL PACK LIGHT SQUARE SL4 OPTICS 2-SQUARE.

### Spectral Parameters

|                           |        |           |      |      |      |
|---------------------------|--------|-----------|------|------|------|
| CCT (K):                  | 3049   | CRI (Ra): | 81.7 |      |      |
| CIE u':                   | 0.2482 | R1:       | 79.6 | R9:  | 1.9  |
| CIE v':                   | 0.5224 | R2:       | 90.6 | R10: | 79.3 |
| Duv:                      | 0.0015 | R3:       | 95.7 | R11: | 78.7 |
| CIE x:                    | 0.4354 | R4:       | 79.4 | R12: | 72.2 |
| CIE y:                    | 0.4072 | R5:       | 80.2 | R13: | 82.2 |
| CIE z:                    | 0.1574 | R6:       | 89.0 | R14: | 98.1 |
| Peak Wavelength (nm):     | 601    | R7:       | 82.2 |      |      |
| Dominant Wavelength (nm): | 582    | R8:       | 57.0 |      |      |
| Purity:                   | 53     |           |      |      |      |
| Rf:                       | 85.1   |           |      |      |      |
| Rg:                       | 94.3   |           |      |      |      |



### Test Conditions

Stabilization Time: 83M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.6/29%  
 Sphere Temperature (°C): 25.6

REPORT NUMBER: SP1-2012-088-3

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 7/29/2020        | 1/29/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2012-088-3

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2012-088-3

### Photopic Flux vs. Wavelength



#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2750             | 0.0              | 490       | 47173            | 6.7              | 620       | 161309           | 42.0             | 750       | 8155             | 0.0              | 880       | 3493             | 0.0              |
| 365       | 2250             | 0.0              | 495       | 54281            | 9.8              | 625       | 153301           | 33.8             | 755       | 7110             | 0.0              | 885       | 4023             | 0.0              |
| 370       | 2449             | 0.0              | 500       | 61837            | 13.6             | 630       | 143292           | 25.9             | 760       | 6829             | 0.0              | 890       | 2983             | 0.0              |
| 375       | 2752             | 0.0              | 505       | 68833            | 19.3             | 635       | 132368           | 19.9             | 765       | 6022             | 0.0              | 895       | 2605             | 0.0              |
| 380       | 2834             | 0.0              | 510       | 74324            | 25.5             | 640       | 122334           | 14.6             | 770       | 5682             | 0.0              | 900       | 3576             | 0.0              |
| 385       | 2613             | 0.0              | 515       | 79410            | 32.9             | 645       | 112200           | 10.8             | 775       | 5247             | 0.0              | 905       | 2786             | 0.0              |
| 390       | 2589             | 0.0              | 520       | 83815            | 40.6             | 650       | 102448           | 7.5              | 780       | 4493             | 0.0              | 910       | 2480             | 0.0              |
| 395       | 2344             | 0.0              | 525       | 87774            | 47.1             | 655       | 91886            | 5.3              | 785       | 4667             | 0.0              | 915       | 2633             | 0.0              |
| 400       | 2067             | 0.0              | 530       | 91247            | 53.7             | 660       | 81865            | 3.4              | 790       | 3736             | 0.0              | 920       | 2726             | 0.0              |
| 405       | 2087             | 0.0              | 535       | 94694            | 58.7             | 665       | 72448            | 2.3              | 795       | 3568             | 0.0              | 925       | 3905             | 0.0              |
| 410       | 2663             | 0.0              | 540       | 98431            | 64.1             | 670       | 63654            | 1.4              | 800       | 3190             | 0.0              | 930       | 2414             | 0.0              |
| 415       | 3760             | 0.0              | 545       | 103765           | 69.1             | 675       | 55284            | 0.9              | 805       | 3215             | 0.0              | 935       | 3414             | 0.0              |
| 420       | 5815             | 0.0              | 550       | 109130           | 74.2             | 680       | 47949            | 0.6              | 810       | 3108             | 0.0              | 940       | 2725             | 0.0              |
| 425       | 9591             | 0.1              | 555       | 115271           | 78.7             | 685       | 42173            | 0.4              | 815       | 3889             | 0.0              | 945       | 4070             | 0.0              |
| 430       | 15806            | 0.1              | 560       | 123390           | 83.9             | 690       | 36755            | 0.2              | 820       | 2869             | 0.0              | 950       | 2640             | 0.0              |
| 435       | 26035            | 0.3              | 565       | 131926           | 87.7             | 695       | 31630            | 0.1              | 825       | 2776             | 0.0              | 955       | 2231             | 0.0              |
| 440       | 41509            | 0.7              | 570       | 141815           | 92.2             | 700       | 27642            | 0.1              | 830       | 2538             | 0.0              | 960       | 3598             | 0.0              |
| 445       | 62857            | 1.3              | 575       | 151359           | 94.2             | 705       | 24213            | 0.1              | 835       | 3283             | 0.0              | 965       | 1098             | 0.0              |
| 450       | 81434            | 2.1              | 580       | 160364           | 95.3             | 710       | 21007            | 0.0              | 840       | 2477             | 0.0              | 970       | 3057             | 0.0              |
| 455       | 77103            | 2.6              | 585       | 166836           | 92.7             | 715       | 18986            | 0.0              | 845       | 3781             | 0.0              | 975       | 152              | 0.0              |
| 460       | 62408            | 2.6              | 590       | 172885           | 89.4             | 720       | 16766            | 0.0              | 850       | 3525             | 0.0              | 980       | 1629             | 0.0              |
| 465       | 52134            | 2.7              | 595       | 176548           | 83.7             | 725       | 14792            | 0.0              | 855       | 4413             | 0.0              | 985       | 5600             | 0.0              |
| 470       | 44297            | 2.8              | 600       | 178427           | 76.9             | 730       | 12553            | 0.0              | 860       | 3598             | 0.0              | 990       | 5671             | 0.0              |
| 475       | 38679            | 3.0              | 605       | 177729           | 68.8             | 735       | 11291            | 0.0              | 865       | 3617             | 0.0              | 995       | 1881             | 0.0              |
| 480       | 38032            | 3.6              | 610       | 174846           | 60.1             | 740       | 9818             | 0.0              | 870       | 3567             | 0.0              | 1000      | 3484             | 0.0              |
| 485       | 41652            | 4.9              | 615       | 169274           | 51.1             | 745       | 8656             | 0.0              | 875       | 4346             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2012-088-3


### Scotopic Flux vs. Wavelength


**Scotopic Lumens: 4584.8**
**S/P: 0.52**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2750             | 0.0              | 490       | 47173            | 72.6             | 620       | 161309           | 2.0              | 750       | 8155             | 0.0              | 880       | 3493             | 0.0              |
| 365       | 2250             | 0.0              | 495       | 54281            | 87.7             | 625       | 153301           | 1.3              | 755       | 7110             | 0.0              | 885       | 4023             | 0.0              |
| 370       | 2449             | 0.0              | 500       | 61837            | 103.4            | 630       | 143292           | 0.8              | 760       | 6829             | 0.0              | 890       | 2983             | 0.0              |
| 375       | 2752             | 0.0              | 505       | 68833            | 117.0            | 635       | 132368           | 0.5              | 765       | 6022             | 0.0              | 895       | 2605             | 0.0              |
| 380       | 2834             | 0.0              | 510       | 74324            | 126.0            | 640       | 122334           | 0.3              | 770       | 5682             | 0.0              | 900       | 3576             | 0.0              |
| 385       | 2613             | 0.0              | 515       | 79410            | 131.6            | 645       | 112200           | 0.2              | 775       | 5247             | 0.0              | 905       | 2786             | 0.0              |
| 390       | 2589             | 0.0              | 520       | 83815            | 133.2            | 650       | 102448           | 0.1              | 780       | 4493             | 0.0              | 910       | 2480             | 0.0              |
| 395       | 2344             | 0.0              | 525       | 87774            | 131.3            | 655       | 91886            | 0.1              | 785       | 4667             | 0.0              | 915       | 2633             | 0.0              |
| 400       | 2067             | 0.0              | 530       | 91247            | 125.8            | 660       | 81865            | 0.0              | 790       | 3736             | 0.0              | 920       | 2726             | 0.0              |
| 405       | 2087             | 0.1              | 535       | 94694            | 118.0            | 665       | 72448            | 0.0              | 795       | 3568             | 0.0              | 925       | 3905             | 0.0              |
| 410       | 2663             | 0.2              | 540       | 98431            | 108.8            | 670       | 63654            | 0.0              | 800       | 3190             | 0.0              | 930       | 2414             | 0.0              |
| 415       | 3760             | 0.4              | 545       | 103765           | 99.5             | 675       | 55284            | 0.0              | 805       | 3215             | 0.0              | 935       | 3414             | 0.0              |
| 420       | 5815             | 1.0              | 550       | 109130           | 89.2             | 680       | 47949            | 0.0              | 810       | 3108             | 0.0              | 940       | 2725             | 0.0              |
| 425       | 9591             | 2.3              | 555       | 115271           | 78.8             | 685       | 42173            | 0.0              | 815       | 3889             | 0.0              | 945       | 4070             | 0.0              |
| 430       | 15806            | 5.4              | 560       | 123390           | 69.0             | 690       | 36755            | 0.0              | 820       | 2869             | 0.0              | 950       | 2640             | 0.0              |
| 435       | 26035            | 11.6             | 565       | 131926           | 59.2             | 695       | 31630            | 0.0              | 825       | 2776             | 0.0              | 955       | 2231             | 0.0              |
| 440       | 41509            | 23.2             | 570       | 141815           | 50.0             | 700       | 27642            | 0.0              | 830       | 2538             | 0.0              | 960       | 3598             | 0.0              |
| 445       | 62857            | 42.1             | 575       | 151359           | 41.2             | 705       | 24213            | 0.0              | 835       | 3283             | 0.0              | 965       | 1098             | 0.0              |
| 450       | 81434            | 63.1             | 580       | 160364           | 33.0             | 710       | 21007            | 0.0              | 840       | 2477             | 0.0              | 970       | 3057             | 0.0              |
| 455       | 77103            | 67.4             | 585       | 166836           | 25.5             | 715       | 18986            | 0.0              | 845       | 3781             | 0.0              | 975       | 152              | 0.0              |
| 460       | 62408            | 60.3             | 590       | 172885           | 19.3             | 720       | 16766            | 0.0              | 850       | 3525             | 0.0              | 980       | 1629             | 0.0              |
| 465       | 52134            | 55.1             | 595       | 176548           | 14.1             | 725       | 14792            | 0.0              | 855       | 4413             | 0.0              | 985       | 5600             | 0.0              |
| 470       | 44297            | 51.0             | 600       | 178427           | 10.1             | 730       | 12553            | 0.0              | 860       | 3598             | 0.0              | 990       | 5671             | 0.0              |
| 475       | 38679            | 48.4             | 605       | 177729           | 7.0              | 735       | 11291            | 0.0              | 865       | 3617             | 0.0              | 995       | 1881             | 0.0              |
| 480       | 38032            | 51.4             | 610       | 174846           | 4.7              | 740       | 9818             | 0.0              | 870       | 3567             | 0.0              | 1000      | 3484             | 0.0              |
| 485       | 41652            | 60.4             | 615       | 169274           | 3.1              | 745       | 8656             | 0.0              | 875       | 4346             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2012-088-3

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: 12033.4      S/P: 1.36**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2750             | 0.0              | 490       | 47173            | 39.3             | 620       | 161309           | 0.1              | 750       | 8155             | 0.0              | 880       | 3493             | 0.0              |
| 365       | 2250             | 0.0              | 495       | 54281            | 44.8             | 625       | 153301           | 0.1              | 755       | 7110             | 0.0              | 885       | 4023             | 0.0              |
| 370       | 2449             | 0.0              | 500       | 61837            | 49.7             | 630       | 143292           | 0.0              | 760       | 6829             | 0.0              | 890       | 2983             | 0.0              |
| 375       | 2752             | 0.0              | 505       | 68833            | 52.8             | 635       | 132368           | 0.0              | 765       | 6022             | 0.0              | 895       | 2605             | 0.0              |
| 380       | 2834             | 0.0              | 510       | 74324            | 53.4             | 640       | 122334           | 0.0              | 770       | 5682             | 0.0              | 900       | 3576             | 0.0              |
| 385       | 2613             | 0.0              | 515       | 79410            | 51.9             | 645       | 112200           | 0.0              | 775       | 5247             | 0.0              | 905       | 2786             | 0.0              |
| 390       | 2589             | 0.0              | 520       | 83815            | 48.8             | 650       | 102448           | 0.0              | 780       | 4493             | 0.0              | 910       | 2480             | 0.0              |
| 395       | 2344             | 0.0              | 525       | 87774            | 44.5             | 655       | 91886            | 0.0              | 785       | 4667             | 0.0              | 915       | 2633             | 0.0              |
| 400       | 2067             | 0.0              | 530       | 91247            | 39.4             | 660       | 81865            | 0.0              | 790       | 3736             | 0.0              | 920       | 2726             | 0.0              |
| 405       | 2087             | 0.0              | 535       | 94694            | 34.1             | 665       | 72448            | 0.0              | 795       | 3568             | 0.0              | 925       | 3905             | 0.0              |
| 410       | 2663             | 0.1              | 540       | 98431            | 28.8             | 670       | 63654            | 0.0              | 800       | 3190             | 0.0              | 930       | 2414             | 0.0              |
| 415       | 3760             | 0.2              | 545       | 103765           | 24.1             | 675       | 55284            | 0.0              | 805       | 3215             | 0.0              | 935       | 3414             | 0.0              |
| 420       | 5815             | 0.7              | 550       | 109130           | 19.6             | 680       | 47949            | 0.0              | 810       | 3108             | 0.0              | 940       | 2725             | 0.0              |
| 425       | 9591             | 1.5              | 555       | 115271           | 15.5             | 685       | 42173            | 0.0              | 815       | 3889             | 0.0              | 945       | 4070             | 0.0              |
| 430       | 15806            | 3.3              | 560       | 123390           | 12.2             | 690       | 36755            | 0.0              | 820       | 2869             | 0.0              | 950       | 2640             | 0.0              |
| 435       | 26035            | 6.9              | 565       | 131926           | 9.3              | 695       | 31630            | 0.0              | 825       | 2776             | 0.0              | 955       | 2231             | 0.0              |
| 440       | 41509            | 13.9             | 570       | 141815           | 6.9              | 700       | 27642            | 0.0              | 830       | 2538             | 0.0              | 960       | 3598             | 0.0              |
| 445       | 62857            | 24.8             | 575       | 151359           | 5.0              | 705       | 24213            | 0.0              | 835       | 3283             | 0.0              | 965       | 1098             | 0.0              |
| 450       | 81434            | 37.5             | 580       | 160364           | 3.6              | 710       | 21007            | 0.0              | 840       | 2477             | 0.0              | 970       | 3057             | 0.0              |
| 455       | 77103            | 40.4             | 585       | 166836           | 2.5              | 715       | 18986            | 0.0              | 845       | 3781             | 0.0              | 975       | 152              | 0.0              |
| 460       | 62408            | 36.8             | 590       | 172885           | 1.7              | 720       | 16766            | 0.0              | 850       | 3525             | 0.0              | 980       | 1629             | 0.0              |
| 465       | 52134            | 34.1             | 595       | 176548           | 1.1              | 725       | 14792            | 0.0              | 855       | 4413             | 0.0              | 985       | 5600             | 0.0              |
| 470       | 44297            | 31.7             | 600       | 178427           | 0.8              | 730       | 12553            | 0.0              | 860       | 3598             | 0.0              | 990       | 5671             | 0.0              |
| 475       | 38679            | 29.5             | 605       | 177729           | 0.5              | 735       | 11291            | 0.0              | 865       | 3617             | 0.0              | 995       | 1881             | 0.0              |
| 480       | 38032            | 30.6             | 610       | 174846           | 0.3              | 740       | 9818             | 0.0              | 870       | 3567             | 0.0              | 1000      | 3484             | 0.0              |
| 485       | 41652            | 34.3             | 615       | 169274           | 0.2              | 745       | 8656             | 0.0              | 875       | 4346             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2012-088-3


TM-30-18

### Summary

$R_f = 85.1$   
 $R_g = 94.3$   
 CIE  $R_a = 81.7$   
 $R_g = 1.9$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 85 | CES51 = 93 | CES76 = 82 |
| CES02 = 63 | CES27 = 94 | CES52 = 93 | CES77 = 85 |
| CES03 = 31 | CES28 = 95 | CES53 = 89 | CES78 = 82 |
| CES04 = 70 | CES29 = 90 | CES54 = 90 | CES79 = 91 |
| CES05 = 49 | CES30 = 96 | CES55 = 89 | CES80 = 90 |
| CES06 = 51 | CES31 = 91 | CES56 = 86 | CES81 = 72 |
| CES07 = 42 | CES32 = 85 | CES57 = 85 | CES82 = 96 |
| CES08 = 41 | CES33 = 95 | CES58 = 86 | CES83 = 95 |
| CES09 = 29 | CES34 = 92 | CES59 = 91 | CES84 = 92 |
| CES10 = 76 | CES35 = 96 | CES60 = 92 | CES85 = 77 |
| CES11 = 59 | CES36 = 87 | CES61 = 88 | CES86 = 68 |
| CES12 = 65 | CES37 = 96 | CES62 = 90 | CES87 = 84 |
| CES13 = 43 | CES38 = 94 | CES63 = 88 | CES88 = 87 |
| CES14 = 74 | CES39 = 98 | CES64 = 81 | CES89 = 75 |
| CES15 = 71 | CES40 = 96 | CES65 = 79 | CES90 = 88 |
| CES16 = 47 | CES41 = 97 | CES66 = 80 | CES91 = 79 |
| CES17 = 50 | CES42 = 98 | CES67 = 78 | CES92 = 65 |
| CES18 = 56 | CES43 = 92 | CES68 = 82 | CES93 = 78 |
| CES19 = 72 | CES44 = 99 | CES69 = 87 | CES94 = 61 |
| CES20 = 66 | CES45 = 93 | CES70 = 80 | CES95 = 74 |
| CES21 = 87 | CES46 = 90 | CES71 = 77 | CES96 = 83 |
| CES22 = 79 | CES47 = 95 | CES72 = 92 | CES97 = 88 |
| CES23 = 92 | CES48 = 84 | CES73 = 75 | CES98 = 84 |
| CES24 = 91 | CES49 = 91 | CES74 = 92 | CES99 = 75 |
| CES25 = 72 | CES50 = 94 | CES75 = 80 |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)