

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P822960

Luminaire Tested: **MSA-SA1D-735-U-5NQ**

Issue Date: 04/10/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P822960  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1910-543-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 04/10/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: MSA-SA1D-735-U-5NQ  
Description: MESA POST TOP DECORATIVE LUMINAIRE. (1) LIGHTSQUARES WITH 16 LEDS  
EACH AND TYPE V NARROW OPTICS.  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6537 lumens  
Efficiency: N/A  
Efficacy: 97.6 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B2 - U0 - G1

Input Watts (W): 67  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P822960  
 CATALOG NUMBER: MSA-SA1D-735-U-5NQ

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 3.1 fc  
 Type V - Short - N/A

REPORT NUMBER: P822960  
CATALOG NUMBER: MSA-SA1D-735-U-5NQ

## Luminous Intensity Polar Plot



REPORT NUMBER: P822960

CATALOG NUMBER: MSA-SA1D-735-U-5NQ


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 3268.5   | 0.0    | 3268.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 3268.5   | 0.0    | 3268.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 6537.0   | 0.0    | 6537.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 40.3   | 0.6       |
| 10°-20°   | 177.6  | 2.7       |
| 20°-30°   | 372.3  | 5.7       |
| 30°-40°   | 701.4  | 10.7      |
| 40°-50°   | 1273.0 | 19.5      |
| 50°-60°   | 2151.0 | 32.9      |
| 60°-70°   | 1608.0 | 24.6      |
| 70°-80°   | 179.9  | 2.8       |
| 80°-90°   | 33.5   | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 6537.0 | 100.0     |
| 0°-180°   | 6537.0 | 100.0     |



REPORT NUMBER: P822960


CATALOG NUMBER: MSA-SA1D-735-U-5NQ

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 295.1  | 4.5       |                         |      |         |
| FM   | (30°-60°)   | 2062.7 | 31.6      |                         |      |         |
| FH   | (60°-80°)   | 894.0  | 13.7      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 16.7   | 0.3       |                         |      | G1/100  |
| BL   | (0°-30°)    | 295.1  | 4.5       | B1/500                  |      |         |
| BM   | (30°-60°)   | 2062.7 | 31.6      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 894.0  | 13.7      | B2/1000                 |      | G1/1800 |
| BVH  | (80°-90°)   | 16.7   | 0.3       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G1**

Type V Short



REPORT NUMBER: P822960

CATALOG NUMBER: MSA-SA1D-735-U-5NQ

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 267.3  | 267.3  | 267.3  | 267.3  | 267.3  | 267.3  | 267.3  | 267.3  | 267.3  | 267.3  | 267.3  |
| 2.5°  | 325.0  | 319.2  | 298.7  | 305.8  | 313.3  | 312.3  | 310.4  | 304.8  | 299.7  | 320.7  | 325.0  |
| 5°    | 414.4  | 401.1  | 393.9  | 388.0  | 386.7  | 372.4  | 392.0  | 389.9  | 396.5  | 407.7  | 418.6  |
| 7.5°  | 485.6  | 473.2  | 454.2  | 450.2  | 428.7  | 412.8  | 429.7  | 450.8  | 457.4  | 477.9  | 490.1  |
| 10°   | 511.7  | 500.8  | 504.3  | 486.4  | 485.4  | 489.9  | 486.2  | 491.0  | 508.5  | 506.1  | 515.2  |
| 12.5° | 570.2  | 572.1  | 560.9  | 556.4  | 565.4  | 585.1  | 568.4  | 562.5  | 558.2  | 576.3  | 581.9  |
| 15°   | 625.0  | 635.9  | 617.6  | 614.6  | 610.9  | 629.2  | 611.1  | 620.0  | 627.6  | 631.3  | 629.2  |
| 17.5° | 702.6  | 703.2  | 682.7  | 650.0  | 662.2  | 668.1  | 660.1  | 644.9  | 681.4  | 699.7  | 700.7  |
| 20°   | 753.7  | 755.5  | 715.2  | 664.0  | 698.7  | 704.0  | 700.0  | 668.3  | 716.8  | 747.3  | 746.0  |
| 22.5° | 808.7  | 802.4  | 747.6  | 710.3  | 722.5  | 725.8  | 717.2  | 713.3  | 747.3  | 802.9  | 794.7  |
| 25°   | 845.7  | 857.4  | 802.9  | 779.0  | 768.6  | 761.1  | 772.0  | 774.2  | 809.0  | 859.6  | 831.6  |
| 27.5° | 934.0  | 913.8  | 828.5  | 837.5  | 815.4  | 765.1  | 813.0  | 839.4  | 831.9  | 918.1  | 939.1  |
| 30°   | 1012.5 | 1013.0 | 893.3  | 910.6  | 869.6  | 828.9  | 880.8  | 918.8  | 909.5  | 1019.9 | 1000.0 |
| 32.5° | 1112.7 | 1116.4 | 1005.3 | 959.0  | 931.3  | 923.7  | 917.3  | 959.3  | 1017.3 | 1106.6 | 1108.5 |
| 35°   | 1221.0 | 1252.9 | 1101.8 | 1053.2 | 1006.1 | 972.0  | 1008.7 | 1067.0 | 1104.8 | 1247.6 | 1222.4 |
| 37.5° | 1431.9 | 1378.2 | 1254.5 | 1163.0 | 1132.9 | 1119.4 | 1138.8 | 1172.6 | 1254.2 | 1377.4 | 1420.7 |
| 40°   | 1556.6 | 1541.7 | 1373.4 | 1296.8 | 1180.8 | 1217.0 | 1206.3 | 1298.9 | 1366.5 | 1550.3 | 1554.2 |
| 42.5° | 1747.3 | 1672.3 | 1521.0 | 1423.7 | 1319.4 | 1256.6 | 1323.2 | 1447.3 | 1528.9 | 1684.2 | 1757.6 |
| 45°   | 1898.1 | 1801.8 | 1685.1 | 1611.1 | 1479.5 | 1433.0 | 1456.9 | 1616.0 | 1718.3 | 1825.0 | 1921.5 |
| 47.5° | 2064.9 | 1960.6 | 1843.8 | 1712.5 | 1584.0 | 1659.8 | 1617.5 | 1757.4 | 1857.4 | 2010.3 | 2100.8 |
| 50°   | 2274.4 | 2159.0 | 2009.6 | 1901.0 | 1816.0 | 1842.5 | 1835.9 | 1935.6 | 2059.0 | 2198.4 | 2301.1 |
| 52.5° | 2505.3 | 2374.6 | 2230.5 | 2129.7 | 2093.9 | 2027.9 | 2114.1 | 2155.0 | 2246.0 | 2373.6 | 2494.1 |
| 55°   | 2666.7 | 2536.1 | 2448.9 | 2481.3 | 2471.7 | 2365.9 | 2441.4 | 2445.7 | 2401.9 | 2447.8 | 2569.1 |
| 57.5° | 2641.7 | 2517.0 | 2505.0 | 2627.6 | 2810.8 | 2913.2 | 2796.5 | 2545.4 | 2381.1 | 2359.6 | 2488.0 |
| 60°   | 2309.8 | 2203.1 | 2312.7 | 2589.3 | 3123.1 | 3434.8 | 2985.3 | 2470.1 | 2199.4 | 2087.4 | 2211.4 |
| 62.5° | 1591.7 | 1519.6 | 1746.8 | 2179.2 | 3160.5 | 3837.2 | 2978.4 | 2146.5 | 1705.9 | 1502.7 | 1598.9 |
| 65°   | 754.5  | 728.4  | 920.2  | 1381.7 | 2632.7 | 3729.8 | 2602.1 | 1452.4 | 981.9  | 784.3  | 806.1  |
| 67.5° | 283.8  | 270.7  | 337.8  | 610.4  | 1658.2 | 2958.2 | 1749.2 | 716.5  | 379.8  | 295.2  | 305.3  |
| 70°   | 161.2  | 151.9  | 160.6  | 222.6  | 667.6  | 1675.5 | 754.5  | 245.8  | 161.4  | 147.1  | 156.6  |
| 72.5° | 126.9  | 119.7  | 121.0  | 134.6  | 230.3  | 657.7  | 244.2  | 140.1  | 117.3  | 111.4  | 120.0  |
| 75°   | 104.8  | 98.4   | 98.1   | 105.6  | 134.3  | 213.5  | 138.1  | 107.1  | 94.9   | 90.6   | 97.6   |
| 77.5° | 83.3   | 79.6   | 80.6   | 86.5   | 96.2   | 119.4  | 100.0  | 86.7   | 77.9   | 72.9   | 77.7   |
| 80°   | 60.9   | 60.4   | 64.7   | 70.0   | 71.8   | 80.3   | 75.0   | 70.0   | 62.2   | 55.1   | 56.9   |
| 82.5° | 39.9   | 40.2   | 48.2   | 52.4   | 51.6   | 51.3   | 53.8   | 53.5   | 46.6   | 36.4   | 36.4   |
| 85°   | 22.9   | 23.4   | 29.5   | 33.0   | 32.4   | 25.8   | 34.0   | 34.3   | 29.8   | 22.1   | 21.2   |
| 87.5° | 7.5    | 9.3    | 12.8   | 13.6   | 13.0   | 7.2    | 13.0   | 14.3   | 13.0   | 9.3    | 8.2    |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

STREETWORKS

Report Number: SP1-2101-121-7

Luminaire Tested: IFLD-S-SA2A-735-U-T2

Test Date: 03/04/2021




### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2101-121-7  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 03/04/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-735-U-T2**  
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.

### Spectral Parameters

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 3388   | CRI (Ra): | 73.1 |      |       |
| CIE u':                   | 0.2371 | R1:       | 68.9 | R9:  | -34.6 |
| CIE v':                   | 0.5177 | R2:       | 81.1 | R10: | 57.8  |
| Duv:                      | 0.0032 | R3:       | 93.1 | R11: | 68.6  |
| CIE x:                    | 0.4153 | R4:       | 71.6 | R12: | 53.9  |
| CIE y:                    | 0.4030 | R5:       | 69.4 | R13: | 70.9  |
| CIE z:                    | 0.1817 | R6:       | 75.0 | R14: | 96.2  |
| Peak Wavelength (nm):     | 590    | R7:       | 79.5 |      |       |
| Dominant Wavelength (nm): | 580    | R8:       | 46.4 |      |       |
| Purity:                   | 45.7   |           |      |      |       |
| Rf:                       | 76.9   |           |      |      |       |
| Rg:                       | 94.4   |           |      |      |       |



### Test Conditions


Stabilization Time: 81M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.0/30%  
 Sphere Temperature (°C): 24.1

REPORT NUMBER: SP1-2101-121-7


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-7

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-7

### Photopic Flux vs. Wavelength




#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2672             | 0.0              | 490       | 34553            | 4.9              | 620       | 136720           | 35.6             | 750       | 5870             | 0.0              | 880       | 4216             | 0.0              |
| 365       | 2252             | 0.0              | 495       | 44336            | 8.0              | 625       | 126308           | 27.9             | 755       | 5421             | 0.0              | 885       | 4132             | 0.0              |
| 370       | 2217             | 0.0              | 500       | 54643            | 12.1             | 630       | 114625           | 20.7             | 760       | 5097             | 0.0              | 890       | 3992             | 0.0              |
| 375       | 2697             | 0.0              | 505       | 64676            | 18.1             | 635       | 103216           | 15.5             | 765       | 4626             | 0.0              | 895       | 3214             | 0.0              |
| 380       | 3039             | 0.0              | 510       | 73825            | 25.4             | 640       | 92605            | 11.1             | 770       | 3782             | 0.0              | 900       | 2580             | 0.0              |
| 385       | 2655             | 0.0              | 515       | 81872            | 33.9             | 645       | 83234            | 8.0              | 775       | 3506             | 0.0              | 905       | 1776             | 0.0              |
| 390       | 2357             | 0.0              | 520       | 88574            | 43.0             | 650       | 73263            | 5.4              | 780       | 3507             | 0.0              | 910       | 3995             | 0.0              |
| 395       | 2186             | 0.0              | 525       | 93289            | 50.1             | 655       | 64627            | 3.7              | 785       | 3267             | 0.0              | 915       | 4288             | 0.0              |
| 400       | 2015             | 0.0              | 530       | 98393            | 57.9             | 660       | 56614            | 2.4              | 790       | 2849             | 0.0              | 920       | 2446             | 0.0              |
| 405       | 2234             | 0.0              | 535       | 103269           | 64.0             | 665       | 49537            | 1.6              | 795       | 3037             | 0.0              | 925       | 3009             | 0.0              |
| 410       | 3412             | 0.0              | 540       | 107316           | 69.9             | 670       | 42866            | 0.9              | 800       | 2716             | 0.0              | 930       | 3026             | 0.0              |
| 415       | 6135             | 0.0              | 545       | 113101           | 75.3             | 675       | 36708            | 0.6              | 805       | 2648             | 0.0              | 935       | 4734             | 0.0              |
| 420       | 12146            | 0.0              | 550       | 120690           | 82.0             | 680       | 31814            | 0.4              | 810       | 3187             | 0.0              | 940       | 3719             | 0.0              |
| 425       | 23983            | 0.1              | 555       | 128583           | 87.8             | 685       | 27485            | 0.2              | 815       | 2931             | 0.0              | 945       | 1480             | 0.0              |
| 430       | 42142            | 0.3              | 560       | 137796           | 93.6             | 690       | 23698            | 0.1              | 820       | 2717             | 0.0              | 950       | 3450             | 0.0              |
| 435       | 68228            | 0.8              | 565       | 146577           | 97.5             | 695       | 20309            | 0.1              | 825       | 2236             | 0.0              | 955       | 5051             | 0.0              |
| 440       | 99323            | 1.6              | 570       | 154581           | 100.5            | 700       | 17890            | 0.1              | 830       | 2628             | 0.0              | 960       | 3176             | 0.0              |
| 445       | 115584           | 2.4              | 575       | 162633           | 101.2            | 705       | 15500            | 0.0              | 835       | 3140             | 0.0              | 965       | 5178             | 0.0              |
| 450       | 94997            | 2.5              | 580       | 168101           | 99.9             | 710       | 13699            | 0.0              | 840       | 3675             | 0.0              | 970       | 6385             | 0.0              |
| 455       | 61433            | 2.1              | 585       | 173145           | 96.2             | 715       | 12398            | 0.0              | 845       | 3283             | 0.0              | 975       | 3810             | 0.0              |
| 460       | 43373            | 1.8              | 590       | 174675           | 90.3             | 720       | 11147            | 0.0              | 850       | 3055             | 0.0              | 980       | 4322             | 0.0              |
| 465       | 32472            | 1.7              | 595       | 173724           | 82.3             | 725       | 9761             | 0.0              | 855       | 2932             | 0.0              | 985       | 4200             | 0.0              |
| 470       | 24257            | 1.5              | 600       | 171241           | 73.8             | 730       | 8651             | 0.0              | 860       | 3382             | 0.0              | 990       | 4661             | 0.0              |
| 475       | 21690            | 1.7              | 605       | 165134           | 64.0             | 735       | 7730             | 0.0              | 865       | 2605             | 0.0              | 995       | 6746             | 0.0              |
| 480       | 23173            | 2.2              | 610       | 156652           | 53.8             | 740       | 6847             | 0.0              | 870       | 3325             | 0.0              | 1000      | 4150             | 0.0              |
| 485       | 27564            | 3.3              | 615       | 147879           | 44.6             | 745       | 6124             | 0.0              | 875       | 3325             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-7

### Scotopic Flux vs. Wavelength




Scotopic Lumens: 12126

S/P: 1.36

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2672             | 0.0              | 490       | 34553            | 53.2             | 620       | 136720           | 1.7              | 750       | 5870             | 0.0              | 880       | 4216             | 0.0              |
| 365       | 2252             | 0.0              | 495       | 44336            | 71.7             | 625       | 126308           | 1.1              | 755       | 5421             | 0.0              | 885       | 4132             | 0.0              |
| 370       | 2217             | 0.0              | 500       | 54643            | 91.4             | 630       | 114625           | 0.6              | 760       | 5097             | 0.0              | 890       | 3992             | 0.0              |
| 375       | 2697             | 0.0              | 505       | 64676            | 110.0            | 635       | 103216           | 0.4              | 765       | 4626             | 0.0              | 895       | 3214             | 0.0              |
| 380       | 3039             | 0.0              | 510       | 73825            | 125.1            | 640       | 92605            | 0.2              | 770       | 3782             | 0.0              | 900       | 2580             | 0.0              |
| 385       | 2655             | 0.0              | 515       | 81872            | 135.7            | 645       | 83234            | 0.1              | 775       | 3506             | 0.0              | 905       | 1776             | 0.0              |
| 390       | 2357             | 0.0              | 520       | 88574            | 140.8            | 650       | 73263            | 0.1              | 780       | 3507             | 0.0              | 910       | 3995             | 0.0              |
| 395       | 2186             | 0.0              | 525       | 93289            | 139.6            | 655       | 64627            | 0.1              | 785       | 3267             | 0.0              | 915       | 4288             | 0.0              |
| 400       | 2015             | 0.0              | 530       | 98393            | 135.7            | 660       | 56614            | 0.0              | 790       | 2849             | 0.0              | 920       | 2446             | 0.0              |
| 405       | 2234             | 0.1              | 535       | 103269           | 128.7            | 665       | 49537            | 0.0              | 795       | 3037             | 0.0              | 925       | 3009             | 0.0              |
| 410       | 3412             | 0.2              | 540       | 107316           | 118.6            | 670       | 42866            | 0.0              | 800       | 2716             | 0.0              | 930       | 3026             | 0.0              |
| 415       | 6135             | 0.6              | 545       | 113101           | 108.4            | 675       | 36708            | 0.0              | 805       | 2648             | 0.0              | 935       | 4734             | 0.0              |
| 420       | 12146            | 2.0              | 550       | 120690           | 98.7             | 680       | 31814            | 0.0              | 810       | 3187             | 0.0              | 940       | 3719             | 0.0              |
| 425       | 23983            | 5.9              | 555       | 128583           | 87.9             | 685       | 27485            | 0.0              | 815       | 2931             | 0.0              | 945       | 1480             | 0.0              |
| 430       | 42142            | 14.3             | 560       | 137796           | 77.0             | 690       | 23698            | 0.0              | 820       | 2717             | 0.0              | 950       | 3450             | 0.0              |
| 435       | 68228            | 30.5             | 565       | 146577           | 65.8             | 695       | 20309            | 0.0              | 825       | 2236             | 0.0              | 955       | 5051             | 0.0              |
| 440       | 99323            | 55.5             | 570       | 154581           | 54.6             | 700       | 17890            | 0.0              | 830       | 2628             | 0.0              | 960       | 3176             | 0.0              |
| 445       | 115584           | 77.4             | 575       | 162633           | 44.3             | 705       | 15500            | 0.0              | 835       | 3140             | 0.0              | 965       | 5178             | 0.0              |
| 450       | 94997            | 73.6             | 580       | 168101           | 34.6             | 710       | 13699            | 0.0              | 840       | 3675             | 0.0              | 970       | 6385             | 0.0              |
| 455       | 61433            | 53.7             | 585       | 173145           | 26.5             | 715       | 12398            | 0.0              | 845       | 3283             | 0.0              | 975       | 3810             | 0.0              |
| 460       | 43373            | 41.9             | 590       | 174675           | 19.5             | 720       | 11147            | 0.0              | 850       | 3055             | 0.0              | 980       | 4322             | 0.0              |
| 465       | 32472            | 34.3             | 595       | 173724           | 13.9             | 725       | 9761             | 0.0              | 855       | 2932             | 0.0              | 985       | 4200             | 0.0              |
| 470       | 24257            | 27.9             | 600       | 171241           | 9.7              | 730       | 8651             | 0.0              | 860       | 3382             | 0.0              | 990       | 4661             | 0.0              |
| 475       | 21690            | 27.1             | 605       | 165134           | 6.5              | 735       | 7730             | 0.0              | 865       | 2605             | 0.0              | 995       | 6746             | 0.0              |
| 480       | 23173            | 31.3             | 610       | 156652           | 4.2              | 740       | 6847             | 0.0              | 870       | 3325             | 0.0              | 1000      | 4150             | 0.0              |
| 485       | 27564            | 40.0             | 615       | 147879           | 2.7              | 745       | 6124             | 0.0              | 875       | 3325             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-7

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: 4490.7**
**M/P: 0.5**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2672             | 0.0              | 490       | 34553            | 28.8             | 620       | 136720           | 0.1              | 750       | 5870             | 0.0              | 880       | 4216             | 0.0              |
| 365       | 2252             | 0.0              | 495       | 44336            | 36.6             | 625       | 126308           | 0.1              | 755       | 5421             | 0.0              | 885       | 4132             | 0.0              |
| 370       | 2217             | 0.0              | 500       | 54643            | 43.9             | 630       | 114625           | 0.0              | 760       | 5097             | 0.0              | 890       | 3992             | 0.0              |
| 375       | 2697             | 0.0              | 505       | 64676            | 49.6             | 635       | 103216           | 0.0              | 765       | 4626             | 0.0              | 895       | 3214             | 0.0              |
| 380       | 3039             | 0.0              | 510       | 73825            | 53.0             | 640       | 92605            | 0.0              | 770       | 3782             | 0.0              | 900       | 2580             | 0.0              |
| 385       | 2655             | 0.0              | 515       | 81872            | 53.5             | 645       | 83234            | 0.0              | 775       | 3506             | 0.0              | 905       | 1776             | 0.0              |
| 390       | 2357             | 0.0              | 520       | 88574            | 51.6             | 650       | 73263            | 0.0              | 780       | 3507             | 0.0              | 910       | 3995             | 0.0              |
| 395       | 2186             | 0.0              | 525       | 93289            | 47.3             | 655       | 64627            | 0.0              | 785       | 3267             | 0.0              | 915       | 4288             | 0.0              |
| 400       | 2015             | 0.0              | 530       | 98393            | 42.5             | 660       | 56614            | 0.0              | 790       | 2849             | 0.0              | 920       | 2446             | 0.0              |
| 405       | 2234             | 0.0              | 535       | 103269           | 37.2             | 665       | 49537            | 0.0              | 795       | 3037             | 0.0              | 925       | 3009             | 0.0              |
| 410       | 3412             | 0.1              | 540       | 107316           | 31.4             | 670       | 42866            | 0.0              | 800       | 2716             | 0.0              | 930       | 3026             | 0.0              |
| 415       | 6135             | 0.4              | 545       | 113101           | 26.3             | 675       | 36708            | 0.0              | 805       | 2648             | 0.0              | 935       | 4734             | 0.0              |
| 420       | 12146            | 1.4              | 550       | 120690           | 21.7             | 680       | 31814            | 0.0              | 810       | 3187             | 0.0              | 940       | 3719             | 0.0              |
| 425       | 23983            | 3.7              | 555       | 128583           | 17.3             | 685       | 27485            | 0.0              | 815       | 2931             | 0.0              | 945       | 1480             | 0.0              |
| 430       | 42142            | 8.9              | 560       | 137796           | 13.6             | 690       | 23698            | 0.0              | 820       | 2717             | 0.0              | 950       | 3450             | 0.0              |
| 435       | 68228            | 18.2             | 565       | 146577           | 10.3             | 695       | 20309            | 0.0              | 825       | 2236             | 0.0              | 955       | 5051             | 0.0              |
| 440       | 99323            | 33.2             | 570       | 154581           | 7.6              | 700       | 17890            | 0.0              | 830       | 2628             | 0.0              | 960       | 3176             | 0.0              |
| 445       | 115584           | 45.6             | 575       | 162633           | 5.4              | 705       | 15500            | 0.0              | 835       | 3140             | 0.0              | 965       | 5178             | 0.0              |
| 450       | 94997            | 43.8             | 580       | 168101           | 3.8              | 710       | 13699            | 0.0              | 840       | 3675             | 0.0              | 970       | 6385             | 0.0              |
| 455       | 61433            | 32.2             | 585       | 173145           | 2.6              | 715       | 12398            | 0.0              | 845       | 3283             | 0.0              | 975       | 3810             | 0.0              |
| 460       | 43373            | 25.6             | 590       | 174675           | 1.7              | 720       | 11147            | 0.0              | 850       | 3055             | 0.0              | 980       | 4322             | 0.0              |
| 465       | 32472            | 21.2             | 595       | 173724           | 1.1              | 725       | 9761             | 0.0              | 855       | 2932             | 0.0              | 985       | 4200             | 0.0              |
| 470       | 24257            | 17.4             | 600       | 171241           | 0.7              | 730       | 8651             | 0.0              | 860       | 3382             | 0.0              | 990       | 4661             | 0.0              |
| 475       | 21690            | 16.6             | 605       | 165134           | 0.5              | 735       | 7730             | 0.0              | 865       | 2605             | 0.0              | 995       | 6746             | 0.0              |
| 480       | 23173            | 18.6             | 610       | 156652           | 0.3              | 740       | 6847             | 0.0              | 870       | 3325             | 0.0              | 1000      | 4150             | 0.0              |
| 485       | 27564            | 22.7             | 615       | 147879           | 0.2              | 745       | 6124             | 0.0              | 875       | 3325             | 0.0              |           |                  |                  |


REPORT NUMBER: SP1-2101-121-7

TM-30-18





### Summary

$R_f = 76.9$   
 $R_g = 94.4$   
 CIE  $R_a = 73.1$   
 $R_g = -34.6$

### Spectral Power Distribution Comparison




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 68 | CES51 = 90 | CES76 = 63 |
| CES02 = 62 | CES27 = 88 | CES52 = 89 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 80 | CES78 = 65 |
| CES04 = 70 | CES29 = 67 | CES54 = 84 | CES79 = 87 |
| CES05 = 48 | CES30 = 74 | CES55 = 84 | CES80 = 86 |
| CES06 = 51 | CES31 = 71 | CES56 = 75 | CES81 = 75 |
| CES07 = 40 | CES32 = 67 | CES57 = 74 | CES82 = 94 |
| CES08 = 39 | CES33 = 74 | CES58 = 76 | CES83 = 91 |
| CES09 = 29 | CES34 = 78 | CES59 = 87 | CES84 = 89 |
| CES10 = 75 | CES35 = 89 | CES60 = 93 | CES85 = 80 |
| CES11 = 58 | CES36 = 98 | CES61 = 86 | CES86 = 66 |
| CES12 = 64 | CES37 = 86 | CES62 = 89 | CES87 = 79 |
| CES13 = 43 | CES38 = 82 | CES63 = 77 | CES88 = 79 |
| CES14 = 74 | CES39 = 95 | CES64 = 74 | CES89 = 70 |
| CES15 = 71 | CES40 = 91 | CES65 = 68 | CES90 = 77 |
| CES16 = 47 | CES41 = 89 | CES66 = 71 | CES91 = 88 |
| CES17 = 50 | CES42 = 88 | CES67 = 69 | CES92 = 60 |
| CES18 = 56 | CES43 = 82 | CES68 = 74 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 82 | CES94 = 52 |
| CES20 = 65 | CES45 = 87 | CES70 = 67 | CES95 = 69 |
| CES21 = 86 | CES46 = 82 | CES71 = 66 | CES96 = 78 |
| CES22 = 79 | CES47 = 82 | CES72 = 88 | CES97 = 85 |
| CES23 = 92 | CES48 = 72 | CES73 = 59 | CES98 = 76 |
| CES24 = 91 | CES49 = 82 | CES74 = 97 | CES99 = 63 |
| CES25 = 72 | CES50 = 88 | CES75 = 66 |            |







Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)