

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671823

Luminaire Tested: **CCP-SA-1B-740-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671823
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1B-740-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @450mA w/ SLR
distribution lens
Light Source: (16) 4000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2866 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G1

Input Watts (W): 24
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 4.1 fc

Type IV - Short - N/A

REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	589.7	0.0	589.7
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	2276.3	0.0	2276.3
	% Fixture	79.4	0.0	79.4
Total	Lumens	2866.0	0.0	2866.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.1	2.5
10°-20°	150.2	5.2
20°-30°	219.7	7.7
30°-40°	309.5	10.8
40°-50°	425.3	14.8
50°-60°	579.7	20.2
60°-70°	634.4	22.1
70°-80°	366.4	12.8
80°-90°	109.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2866.0	100.0
0°-180°	2866.0	100.0

Coefficient of Utilization



REPORT NUMBER: P671823


CATALOG NUMBER: CCP-SA-1B-740-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	294.4	10.3			
FM	(30°-60°)	1045.9	36.5			
FH	(60°-80°)	842.8	29.4			G1/1800
FVH	(80°-90°)	93.3	3.3			G1/100
BL	(0°-30°)	146.6	5.1	B1/500		
BM	(30°-60°)	268.5	9.4	B1/1000		
BH	(60°-80°)	158.0	5.5	B1/500		G1/500
BVH	(80°-90°)	16.5	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2
2.5°	944.5	939.4	935.6	931.8	926.7	922.9	917.8	912.7	906.3	901.3	894.9
5°	889.8	874.6	859.3	850.4	840.2	831.3	821.2	809.7	798.3	785.6	774.1
7.5°	830.1	811.0	791.9	776.7	760.2	744.9	728.4	714.4	700.4	686.4	672.4
10°	774.1	756.3	738.5	719.5	699.1	680.1	659.7	640.7	621.6	602.5	583.5
12.5°	737.3	715.7	695.3	673.7	653.4	631.8	610.2	592.4	574.6	555.5	537.7
15°	720.8	700.4	681.3	659.7	638.1	616.5	594.9	574.6	555.5	535.2	514.8
17.5°	760.2	730.9	701.7	673.7	645.8	617.8	589.8	564.4	539.0	513.6	488.1
20°	811.0	774.1	738.5	704.2	668.6	634.3	598.7	563.1	527.5	491.9	456.3
22.5°	875.8	833.9	793.2	748.7	703.0	658.5	612.7	568.2	523.7	478.0	433.5
25°	991.5	941.9	892.4	828.8	764.0	700.4	635.6	577.1	519.9	461.4	403.0
27.5°	1090.7	1023.3	957.2	880.9	804.6	728.4	652.1	584.7	518.6	451.3	383.9
30°	1149.1	1083.0	1016.9	924.1	832.6	739.8	647.0	572.0	498.3	423.3	348.3
32.5°	1202.5	1128.8	1055.1	953.4	850.4	748.7	645.8	563.1	481.8	399.1	316.5
35°	1276.2	1194.9	1114.8	996.6	878.4	760.2	641.9	556.8	470.3	385.2	298.7
37.5°	1355.1	1254.6	1155.5	1024.6	893.6	762.7	631.8	547.9	464.0	380.1	296.2
40°	1441.5	1319.5	1198.7	1053.8	910.2	765.2	620.3	536.4	452.5	367.4	283.5
42.5°	1497.4	1365.2	1233.0	1076.7	921.6	765.2	608.9	526.3	443.6	359.7	277.1
45°	1529.2	1400.8	1273.7	1104.6	935.6	766.5	597.4	516.1	434.7	352.1	270.8
47.5°	1543.2	1423.7	1304.2	1126.3	949.6	771.6	593.6	511.0	427.1	344.5	260.6
50°	1580.1	1474.6	1369.0	1178.4	989.0	798.3	607.6	518.6	430.9	341.9	253.0
52.5°	1601.7	1511.4	1421.2	1225.4	1029.6	833.9	638.1	539.0	439.8	340.7	241.5
55°	1680.5	1594.0	1507.6	1299.1	1089.4	880.9	671.2	561.9	452.5	341.9	232.6
57.5°	1780.9	1689.4	1599.1	1374.1	1149.1	924.1	699.1	582.2	464.0	347.0	228.8
60°	1850.8	1761.8	1674.1	1435.1	1194.9	955.9	715.7	593.6	471.6	348.3	226.3
62.5°	1858.4	1744.0	1630.9	1398.3	1165.7	931.8	699.1	580.9	462.7	343.2	225.0
65°	1810.1	1676.7	1543.2	1320.7	1098.3	875.8	653.4	545.3	437.3	328.0	219.9
67.5°	1713.5	1557.2	1400.8	1197.4	994.1	790.7	587.3	494.5	403.0	310.2	217.4
70°	1488.5	1351.2	1215.2	1038.5	863.1	686.4	509.7	433.5	358.5	282.2	205.9
72.5°	1249.6	1121.2	994.1	850.4	708.0	564.4	420.8	363.6	306.4	247.9	190.7
75°	957.2	860.6	765.2	658.5	551.7	443.6	336.9	294.9	253.0	211.0	169.1
77.5°	672.4	620.3	569.5	489.4	409.3	329.2	249.1	221.2	193.2	165.3	137.3
80°	456.3	427.1	399.1	341.9	284.7	226.3	169.1	151.3	132.2	114.4	95.3
82.5°	283.5	282.2	279.7	240.3	200.8	161.4	122.0	106.8	92.8	77.5	62.3
85°	129.7	151.3	171.6	150.0	128.4	106.8	85.2	75.0	64.8	53.4	43.2
87.5°	40.7	49.6	57.2	54.7	50.8	48.3	44.5	38.1	31.8	25.4	19.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2
2.5°	889.8	886.0	880.9	875.8	869.5	864.4	858.0	851.7	850.4	847.9	846.6
5°	766.5	758.9	750.0	742.4	734.7	725.8	718.2	709.3	703.0	695.3	689.0
7.5°	658.5	645.8	631.8	617.8	605.1	592.4	578.4	565.7	559.3	553.0	546.6
10°	572.0	559.3	547.9	535.2	526.3	518.6	509.7	500.8	493.2	485.6	478.0
12.5°	528.8	519.9	511.0	502.1	491.9	483.0	472.9	462.7	453.8	446.2	437.3
15°	502.1	489.4	475.4	462.7	448.7	436.0	422.0	408.0	397.9	389.0	378.8
17.5°	470.3	451.3	433.5	414.4	399.1	383.9	367.4	352.1	340.7	328.0	316.5
20°	434.7	413.1	390.2	368.6	350.8	334.3	316.5	298.7	286.0	272.0	259.3
22.5°	404.2	376.3	347.0	317.8	298.7	279.7	259.3	240.3	228.8	216.1	204.7
25°	371.2	340.7	308.9	277.1	258.0	237.7	218.6	198.3	189.4	181.8	172.9
27.5°	353.4	322.9	291.1	260.6	242.8	223.7	205.9	186.9	180.5	172.9	166.5
30°	317.8	288.6	258.0	227.5	214.8	203.4	190.7	178.0	175.4	174.1	171.6
32.5°	286.0	255.5	225.0	194.5	183.0	171.6	160.2	148.7	147.5	144.9	143.6
35°	269.5	240.3	209.7	180.5	170.3	158.9	148.7	137.3	134.7	130.9	128.4
37.5°	265.7	235.2	203.4	172.9	162.7	152.5	141.1	130.9	128.4	125.8	123.3
40°	255.5	226.3	198.3	169.1	158.9	148.7	137.3	127.1	124.6	122.0	119.5
42.5°	247.9	219.9	190.7	161.4	152.5	143.6	133.5	124.6	122.0	119.5	115.7
45°	241.5	212.3	181.8	152.5	146.2	139.8	132.2	125.8	123.3	119.5	116.9
47.5°	231.4	203.4	174.1	144.9	138.6	133.5	127.1	120.8	118.2	115.7	113.1
50°	223.7	194.5	165.3	136.0	130.9	125.8	120.8	115.7	115.7	116.9	116.9
52.5°	213.6	185.6	157.6	129.7	124.6	119.5	114.4	109.3	110.6	111.9	113.1
55°	204.7	178.0	150.0	122.0	116.9	111.9	105.5	100.4	101.7	103.0	104.2
57.5°	200.8	172.9	144.9	116.9	111.9	105.5	100.4	94.1	94.1	94.1	94.1
60°	198.3	169.1	141.1	111.9	105.5	100.4	94.1	87.7	86.4	86.4	85.2
62.5°	197.0	167.8	139.8	110.6	103.0	96.6	89.0	81.4	80.1	78.8	77.5
65°	191.9	165.3	137.3	109.3	100.4	92.8	83.9	75.0	73.7	73.7	72.5
67.5°	190.7	162.7	136.0	108.0	99.2	89.0	80.1	69.9	68.6	67.4	66.1
70°	180.5	156.4	130.9	105.5	95.3	86.4	76.3	66.1	64.8	62.3	61.0
72.5°	167.8	146.2	123.3	100.4	90.3	80.1	69.9	59.7	58.5	57.2	54.7
75°	148.7	128.4	108.0	87.7	78.8	71.2	62.3	53.4	52.1	50.8	48.3
77.5°	122.0	105.5	90.3	73.7	67.4	61.0	54.7	48.3	47.0	45.8	43.2
80°	86.4	76.3	67.4	57.2	53.4	48.3	44.5	39.4	39.4	38.1	38.1
82.5°	57.2	52.1	47.0	41.9	39.4	36.9	34.3	31.8	31.8	30.5	30.5
85°	40.7	38.1	34.3	31.8	30.5	28.0	26.7	24.2	24.2	24.2	24.2
87.5°	19.1	19.1	17.8	17.8	16.5	16.5	15.3	14.0	14.0	14.0	14.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2
2.5°	844.1	840.2	836.4	831.3	827.5	822.4	816.1	811.0	804.6	804.6	803.4
5°	681.3	677.5	673.7	668.6	664.8	659.7	655.9	650.8	645.8	645.8	644.5
7.5°	540.2	532.6	525.0	516.1	508.5	503.4	498.3	491.9	486.9	483.0	479.2
10°	470.3	462.7	453.8	446.2	437.3	430.9	424.6	416.9	410.6	405.5	400.4
12.5°	428.4	419.5	410.6	401.7	392.8	383.9	376.3	367.4	358.5	352.1	345.8
15°	368.6	359.7	350.8	341.9	333.0	322.9	312.7	301.3	291.1	286.0	282.2
17.5°	303.8	294.9	284.7	275.8	265.7	258.0	250.4	242.8	235.2	230.1	226.3
20°	245.3	235.2	225.0	214.8	204.7	199.6	194.5	189.4	184.3	180.5	178.0
22.5°	191.9	185.6	180.5	174.1	167.8	164.0	161.4	157.6	153.8	153.8	153.8
25°	164.0	160.2	157.6	153.8	150.0	148.7	147.5	144.9	143.6	142.4	142.4
27.5°	158.9	155.1	151.3	147.5	143.6	142.4	141.1	138.6	137.3	137.3	137.3
30°	169.1	167.8	166.5	165.3	164.0	161.4	157.6	155.1	151.3	148.7	146.2
32.5°	141.1	139.8	139.8	138.6	137.3	139.8	141.1	143.6	144.9	146.2	147.5
35°	124.6	122.0	119.5	116.9	114.4	113.1	111.9	110.6	109.3	109.3	108.0
37.5°	120.8	118.2	115.7	113.1	110.6	109.3	108.0	106.8	105.5	105.5	104.2
40°	116.9	114.4	113.1	110.6	108.0	106.8	105.5	103.0	101.7	100.4	100.4
42.5°	113.1	111.9	109.3	108.0	105.5	104.2	103.0	100.4	99.2	97.9	96.6
45°	113.1	110.6	108.0	105.5	103.0	101.7	99.2	97.9	95.3	95.3	94.1
47.5°	110.6	108.0	105.5	103.0	100.4	99.2	96.6	95.3	92.8	91.5	90.3
50°	116.9	113.1	108.0	104.2	99.2	97.9	95.3	94.1	91.5	90.3	89.0
52.5°	114.4	110.6	105.5	101.7	96.6	94.1	92.8	90.3	87.7	86.4	85.2
55°	105.5	101.7	99.2	95.3	91.5	89.0	86.4	83.9	81.4	80.1	80.1
57.5°	94.1	92.8	91.5	90.3	89.0	86.4	83.9	80.1	77.5	76.3	75.0
60°	83.9	85.2	86.4	87.7	89.0	85.2	81.4	77.5	73.7	72.5	71.2
62.5°	76.3	78.8	81.4	82.6	85.2	81.4	77.5	73.7	69.9	68.6	67.4
65°	71.2	72.5	72.5	73.7	73.7	71.2	69.9	67.4	64.8	63.6	63.6
67.5°	64.8	64.8	64.8	63.6	63.6	62.3	62.3	61.0	59.7	58.5	58.5
70°	58.5	58.5	58.5	57.2	57.2	55.9	55.9	54.7	53.4	53.4	52.1
72.5°	53.4	53.4	52.1	52.1	50.8	50.8	50.8	49.6	49.6	48.3	48.3
75°	47.0	47.0	45.8	45.8	44.5	44.5	44.5	43.2	43.2	43.2	41.9
77.5°	41.9	41.9	40.7	40.7	39.4	39.4	39.4	38.1	38.1	36.9	36.9
80°	36.9	36.9	35.6	35.6	34.3	34.3	33.1	33.1	31.8	31.8	30.5
82.5°	29.2	29.2	29.2	29.2	29.2	28.0	28.0	26.7	25.4	25.4	24.2
85°	24.2	24.2	24.2	22.9	22.9	22.9	21.6	21.6	20.3	19.1	19.1
87.5°	14.0	14.0	14.0	12.7	12.7	12.7	12.7	12.7	12.7	12.7	11.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2
2.5°	803.4	802.1	797.0	791.9	797.0	802.1	802.1	802.1	800.8	800.8	800.8
5°	644.5	643.2	640.7	638.1	638.1	636.9	639.4	641.9	644.5	647.0	649.6
7.5°	474.1	470.3	466.5	462.7	465.2	466.5	470.3	472.9	476.7	479.2	485.6
10°	395.3	390.2	386.4	382.6	380.1	377.5	375.0	373.7	371.2	368.6	371.2
12.5°	338.1	331.8	325.4	317.8	316.5	315.2	312.7	310.2	307.6	305.1	303.8
15°	277.1	272.0	269.5	265.7	260.6	255.5	253.0	251.7	249.1	246.6	245.3
17.5°	221.2	216.1	212.3	208.5	207.2	204.7	204.7	204.7	204.7	204.7	204.7
20°	174.1	170.3	170.3	169.1	169.1	167.8	169.1	170.3	170.3	171.6	172.9
22.5°	152.5	152.5	151.3	150.0	151.3	151.3	152.5	153.8	155.1	156.4	157.6
25°	141.1	139.8	141.1	142.4	142.4	142.4	143.6	143.6	144.9	144.9	144.9
27.5°	136.0	136.0	137.3	137.3	138.6	138.6	138.6	137.3	137.3	136.0	136.0
30°	143.6	141.1	141.1	141.1	139.8	138.6	137.3	137.3	136.0	134.7	133.5
32.5°	148.7	150.0	148.7	146.2	144.9	142.4	141.1	138.6	137.3	134.7	132.2
35°	108.0	106.8	109.3	110.6	111.9	113.1	114.4	115.7	115.7	116.9	116.9
37.5°	104.2	103.0	103.0	101.7	101.7	101.7	101.7	101.7	100.4	100.4	101.7
40°	99.2	97.9	97.9	96.6	96.6	95.3	95.3	95.3	95.3	95.3	95.3
42.5°	95.3	94.1	94.1	94.1	94.1	92.8	92.8	91.5	91.5	90.3	90.3
45°	94.1	92.8	91.5	90.3	90.3	89.0	89.0	89.0	87.7	87.7	87.7
47.5°	89.0	87.7	87.7	86.4	86.4	85.2	85.2	85.2	83.9	83.9	83.9
50°	86.4	85.2	85.2	83.9	83.9	82.6	82.6	82.6	81.4	81.4	81.4
52.5°	82.6	81.4	81.4	81.4	80.1	78.8	78.8	78.8	77.5	77.5	77.5
55°	78.8	77.5	77.5	77.5	76.3	75.0	75.0	75.0	73.7	73.7	73.7
57.5°	73.7	72.5	72.5	71.2	71.2	71.2	71.2	71.2	69.9	69.9	69.9
60°	69.9	68.6	68.6	67.4	67.4	66.1	66.1	66.1	66.1	66.1	66.1
62.5°	66.1	64.8	63.6	62.3	63.6	63.6	63.6	63.6	62.3	62.3	62.3
65°	62.3	61.0	59.7	58.5	58.5	58.5	58.5	58.5	58.5	58.5	58.5
67.5°	57.2	55.9	54.7	53.4	54.7	54.7	54.7	54.7	54.7	54.7	54.7
70°	52.1	50.8	50.8	49.6	49.6	48.3	48.3	49.6	49.6	49.6	49.6
72.5°	47.0	45.8	45.8	44.5	44.5	44.5	44.5	44.5	44.5	44.5	44.5
75°	41.9	40.7	40.7	39.4	39.4	39.4	39.4	39.4	39.4	39.4	39.4
77.5°	35.6	34.3	34.3	34.3	34.3	34.3	34.3	35.6	35.6	35.6	35.6
80°	30.5	29.2	29.2	29.2	29.2	29.2	29.2	29.2	29.2	29.2	29.2
82.5°	24.2	22.9	22.9	22.9	22.9	22.9	22.9	22.9	22.9	22.9	22.9
85°	17.8	16.5	16.5	16.5	17.8	17.8	17.8	17.8	17.8	17.8	17.8
87.5°	11.4	10.2	10.2	10.2	11.4	11.4	11.4	11.4	10.2	10.2	10.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2
2.5°	800.8	800.8	800.8	799.6	798.3	797.0	795.7	799.6	802.1	805.9	808.5
5°	650.8	653.4	654.7	658.5	662.3	666.1	669.9	672.4	675.0	676.3	678.8
7.5°	490.7	497.0	502.1	507.2	512.3	516.1	521.2	525.0	528.8	532.6	536.4
10°	372.5	375.0	376.3	381.3	385.2	390.2	394.1	397.9	401.7	404.2	408.0
12.5°	302.5	300.0	298.7	298.7	298.7	298.7	298.7	301.3	303.8	306.4	308.9
15°	244.1	242.8	241.5	240.3	239.0	236.4	235.2	237.7	240.3	242.8	245.3
17.5°	204.7	204.7	204.7	203.4	202.1	200.8	199.6	200.8	202.1	202.1	203.4
20°	175.4	176.7	178.0	179.2	179.2	180.5	180.5	181.8	183.0	183.0	184.3
22.5°	157.6	158.9	158.9	158.9	160.2	160.2	160.2	161.4	162.7	164.0	165.3
25°	143.6	143.6	142.4	142.4	143.6	143.6	143.6	143.6	144.9	144.9	144.9
27.5°	136.0	134.7	134.7	134.7	134.7	133.5	133.5	133.5	133.5	133.5	133.5
30°	132.2	130.9	129.7	128.4	128.4	127.1	125.8	125.8	125.8	125.8	125.8
32.5°	130.9	128.4	125.8	124.6	124.6	123.3	122.0	120.8	120.8	119.5	118.2
35°	116.9	115.7	115.7	114.4	113.1	111.9	110.6	110.6	110.6	109.3	109.3
37.5°	101.7	103.0	103.0	103.0	104.2	104.2	104.2	104.2	105.5	105.5	105.5
40°	95.3	95.3	95.3	96.6	97.9	97.9	99.2	99.2	100.4	100.4	100.4
42.5°	90.3	89.0	89.0	90.3	90.3	91.5	91.5	92.8	94.1	94.1	95.3
45°	87.7	86.4	86.4	86.4	86.4	85.2	85.2	86.4	87.7	89.0	90.3
47.5°	82.6	82.6	81.4	81.4	81.4	81.4	81.4	81.4	82.6	82.6	82.6
50°	80.1	80.1	78.8	78.8	78.8	78.8	78.8	78.8	78.8	78.8	78.8
52.5°	77.5	76.3	76.3	76.3	76.3	75.0	75.0	75.0	75.0	75.0	75.0
55°	73.7	72.5	72.5	72.5	72.5	72.5	72.5	72.5	73.7	73.7	73.7
57.5°	69.9	68.6	68.6	68.6	69.9	69.9	69.9	69.9	71.2	71.2	71.2
60°	66.1	66.1	66.1	66.1	66.1	66.1	66.1	67.4	67.4	68.6	68.6
62.5°	62.3	62.3	62.3	62.3	63.6	63.6	63.6	63.6	64.8	64.8	64.8
65°	58.5	58.5	58.5	58.5	59.7	59.7	59.7	59.7	59.7	59.7	59.7
67.5°	54.7	54.7	54.7	54.7	54.7	54.7	54.7	55.9	55.9	57.2	57.2
70°	49.6	48.3	48.3	49.6	49.6	50.8	50.8	52.1	52.1	53.4	53.4
72.5°	44.5	44.5	44.5	44.5	44.5	44.5	44.5	45.8	47.0	47.0	48.3
75°	39.4	39.4	39.4	39.4	40.7	40.7	40.7	41.9	41.9	43.2	43.2
77.5°	35.6	34.3	34.3	34.3	35.6	35.6	35.6	36.9	36.9	38.1	38.1
80°	29.2	29.2	29.2	29.2	30.5	30.5	30.5	30.5	31.8	31.8	31.8
82.5°	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	25.4	25.4	25.4
85°	17.8	17.8	17.8	17.8	19.1	19.1	19.1	19.1	19.1	19.1	19.1
87.5°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	12.7	12.7	12.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2
2.5°	808.5	808.5	808.5	808.5	811.0	812.3	814.8	816.1	814.8	813.5	811.0
5°	680.1	681.3	681.3	682.6	682.6	682.6	682.6	682.6	685.2	687.7	690.2
7.5°	537.7	539.0	540.2	541.5	541.5	541.5	540.2	540.2	541.5	541.5	542.8
10°	411.9	416.9	420.8	424.6	422.0	418.2	415.7	411.9	411.9	411.9	410.6
12.5°	311.4	312.7	315.2	316.5	315.2	315.2	314.0	312.7	314.0	316.5	317.8
15°	246.6	246.6	247.9	247.9	249.1	250.4	250.4	251.7	254.2	255.5	258.0
17.5°	204.7	205.9	205.9	207.2	207.2	208.5	208.5	208.5	211.0	213.6	217.4
20°	184.3	184.3	184.3	184.3	184.3	183.0	183.0	181.8	183.0	185.6	186.9
22.5°	165.3	166.5	166.5	166.5	165.3	164.0	161.4	160.2	160.2	161.4	161.4
25°	144.9	143.6	143.6	142.4	142.4	143.6	143.6	143.6	144.9	144.9	146.2
27.5°	133.5	132.2	132.2	130.9	130.9	132.2	132.2	132.2	132.2	132.2	132.2
30°	124.6	124.6	123.3	122.0	123.3	123.3	124.6	124.6	125.8	125.8	127.1
32.5°	118.2	116.9	116.9	115.7	116.9	116.9	118.2	118.2	119.5	120.8	120.8
35°	109.3	109.3	109.3	109.3	109.3	109.3	108.0	108.0	108.0	108.0	108.0
37.5°	104.2	104.2	103.0	101.7	101.7	101.7	101.7	101.7	100.4	99.2	97.9
40°	100.4	99.2	99.2	97.9	96.6	96.6	95.3	94.1	94.1	92.8	92.8
42.5°	95.3	94.1	94.1	92.8	91.5	91.5	90.3	89.0	89.0	89.0	87.7
45°	89.0	89.0	87.7	86.4	86.4	86.4	85.2	85.2	85.2	85.2	83.9
47.5°	82.6	82.6	81.4	81.4	81.4	81.4	80.1	80.1	80.1	80.1	80.1
50°	78.8	78.8	78.8	78.8	78.8	78.8	77.5	77.5	77.5	77.5	77.5
52.5°	75.0	75.0	75.0	75.0	75.0	75.0	75.0	75.0	75.0	75.0	75.0
55°	73.7	73.7	73.7	73.7	73.7	73.7	72.5	72.5	72.5	73.7	73.7
57.5°	71.2	71.2	69.9	69.9	69.9	69.9	69.9	69.9	69.9	69.9	69.9
60°	68.6	68.6	68.6	68.6	68.6	68.6	68.6	68.6	68.6	68.6	68.6
62.5°	64.8	64.8	64.8	64.8	64.8	66.1	66.1	66.1	66.1	66.1	64.8
65°	59.7	61.0	61.0	61.0	61.0	61.0	61.0	61.0	61.0	61.0	61.0
67.5°	57.2	57.2	57.2	57.2	57.2	57.2	57.2	57.2	57.2	57.2	57.2
70°	53.4	53.4	52.1	52.1	52.1	53.4	53.4	53.4	53.4	53.4	53.4
72.5°	48.3	48.3	48.3	48.3	48.3	48.3	48.3	48.3	48.3	49.6	49.6
75°	43.2	43.2	43.2	43.2	43.2	43.2	43.2	43.2	43.2	43.2	43.2
77.5°	38.1	38.1	36.9	36.9	36.9	38.1	38.1	38.1	38.1	39.4	39.4
80°	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	31.8	33.1	33.1
82.5°	25.4	25.4	25.4	25.4	25.4	25.4	25.4	25.4	25.4	26.7	26.7
85°	19.1	20.3	20.3	20.3	20.3	20.3	20.3	20.3	20.3	21.6	21.6
87.5°	12.7	12.7	12.7	12.7	12.7	12.7	11.4	11.4	11.4	11.4	10.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2
2.5°	809.7	811.0	812.3	812.3	813.5	814.8	814.8	819.9	825.0	827.5	830.1
5°	692.8	691.5	691.5	690.2	689.0	692.8	696.6	704.2	711.9	713.1	715.7
7.5°	542.8	544.1	545.3	545.3	546.6	542.8	537.7	539.0	540.2	546.6	551.7
10°	410.6	411.9	413.1	413.1	414.4	413.1	410.6	414.4	418.2	423.3	429.7
12.5°	319.1	322.9	326.7	329.2	333.0	335.6	336.9	341.9	345.8	352.1	358.5
15°	260.6	263.1	265.7	268.2	270.8	273.3	275.8	280.9	286.0	293.6	301.3
17.5°	219.9	219.9	221.2	221.2	221.2	223.7	226.3	228.8	230.1	237.7	245.3
20°	188.1	186.9	185.6	184.3	183.0	185.6	186.9	188.1	189.4	194.5	198.3
22.5°	161.4	161.4	162.7	162.7	162.7	161.4	158.9	160.2	160.2	162.7	166.5
25°	146.2	146.2	146.2	144.9	144.9	146.2	147.5	147.5	146.2	147.5	148.7
27.5°	132.2	133.5	133.5	134.7	134.7	136.0	136.0	136.0	136.0	137.3	138.6
30°	127.1	127.1	128.4	128.4	128.4	129.7	130.9	130.9	130.9	132.2	134.7
32.5°	122.0	123.3	124.6	125.8	127.1	128.4	128.4	129.7	129.7	130.9	132.2
35°	108.0	106.8	106.8	105.5	104.2	104.2	104.2	104.2	103.0	104.2	104.2
37.5°	96.6	96.6	96.6	95.3	95.3	96.6	96.6	96.6	96.6	97.9	97.9
40°	91.5	91.5	91.5	91.5	91.5	91.5	91.5	92.8	92.8	94.1	95.3
42.5°	87.7	87.7	87.7	87.7	87.7	89.0	89.0	89.0	89.0	90.3	90.3
45°	83.9	83.9	83.9	83.9	83.9	83.9	83.9	85.2	85.2	86.4	87.7
47.5°	80.1	80.1	80.1	80.1	80.1	81.4	82.6	82.6	82.6	83.9	83.9
50°	77.5	77.5	77.5	77.5	77.5	78.8	78.8	80.1	80.1	81.4	82.6
52.5°	75.0	75.0	75.0	75.0	75.0	76.3	76.3	77.5	77.5	78.8	80.1
55°	73.7	73.7	73.7	72.5	72.5	73.7	73.7	75.0	75.0	76.3	76.3
57.5°	69.9	69.9	69.9	69.9	69.9	69.9	69.9	71.2	71.2	72.5	73.7
60°	68.6	68.6	67.4	67.4	66.1	67.4	67.4	68.6	68.6	69.9	69.9
62.5°	64.8	64.8	64.8	63.6	63.6	64.8	64.8	64.8	64.8	66.1	67.4
65°	61.0	61.0	61.0	59.7	59.7	61.0	61.0	61.0	61.0	62.3	63.6
67.5°	57.2	57.2	57.2	55.9	55.9	55.9	55.9	57.2	57.2	58.5	59.7
70°	53.4	53.4	53.4	52.1	52.1	52.1	50.8	52.1	53.4	54.7	54.7
72.5°	49.6	49.6	49.6	48.3	48.3	48.3	47.0	48.3	48.3	49.6	49.6
75°	43.2	43.2	43.2	43.2	43.2	43.2	41.9	41.9	41.9	43.2	43.2
77.5°	39.4	39.4	39.4	38.1	38.1	38.1	36.9	36.9	36.9	38.1	38.1
80°	33.1	33.1	33.1	31.8	31.8	31.8	30.5	30.5	30.5	31.8	31.8
82.5°	26.7	26.7	26.7	25.4	25.4	25.4	24.2	24.2	24.2	25.4	25.4
85°	21.6	21.6	21.6	21.6	21.6	21.6	20.3	20.3	20.3	21.6	22.9
87.5°	10.2	10.2	11.4	11.4	11.4	11.4	10.2	10.2	8.9	8.9	10.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2
2.5°	832.6	835.2	841.5	846.6	853.0	858.0	861.9	866.9	870.7	874.6	877.1
5°	716.9	718.2	724.6	730.9	736.0	742.4	751.3	760.2	769.1	778.0	784.3
7.5°	558.0	563.1	570.8	579.7	587.3	594.9	603.8	614.0	622.9	631.8	640.7
10°	434.7	439.8	447.5	455.1	461.4	469.1	479.2	489.4	499.6	509.7	519.9
12.5°	364.8	371.2	380.1	389.0	396.6	405.5	418.2	429.7	442.4	453.8	466.5
15°	307.6	315.2	326.7	339.4	350.8	362.3	375.0	387.7	399.1	411.9	424.6
17.5°	253.0	260.6	270.8	282.2	292.4	302.5	317.8	331.8	347.0	361.0	375.0
20°	203.4	207.2	217.4	227.5	237.7	247.9	259.3	270.8	282.2	293.6	311.4
22.5°	169.1	171.6	176.7	180.5	185.6	189.4	200.8	212.3	222.5	233.9	250.4
25°	148.7	150.0	153.8	156.4	160.2	162.7	170.3	176.7	184.3	190.7	205.9
27.5°	138.6	139.8	141.1	142.4	143.6	144.9	150.0	155.1	158.9	164.0	178.0
30°	136.0	137.3	141.1	143.6	147.5	150.0	152.5	155.1	157.6	160.2	169.1
32.5°	133.5	134.7	134.7	133.5	133.5	132.2	134.7	136.0	138.6	139.8	147.5
35°	105.5	105.5	106.8	108.0	109.3	110.6	114.4	116.9	120.8	123.3	129.7
37.5°	99.2	99.2	100.4	103.0	104.2	105.5	108.0	110.6	113.1	115.7	122.0
40°	95.3	96.6	97.9	99.2	100.4	101.7	104.2	105.5	108.0	109.3	114.4
42.5°	91.5	91.5	92.8	95.3	96.6	97.9	100.4	101.7	104.2	105.5	110.6
45°	89.0	90.3	91.5	92.8	92.8	94.1	96.6	99.2	100.4	103.0	108.0
47.5°	85.2	85.2	87.7	89.0	91.5	92.8	95.3	96.6	99.2	100.4	105.5
50°	82.6	83.9	86.4	87.7	90.3	91.5	95.3	97.9	101.7	104.2	106.8
52.5°	80.1	81.4	83.9	85.2	87.7	89.0	94.1	99.2	103.0	108.0	108.0
55°	77.5	77.5	80.1	83.9	86.4	89.0	91.5	95.3	97.9	100.4	100.4
57.5°	73.7	75.0	77.5	81.4	83.9	86.4	89.0	91.5	92.8	95.3	94.1
60°	71.2	71.2	75.0	78.8	82.6	86.4	86.4	86.4	85.2	85.2	85.2
62.5°	67.4	68.6	73.7	80.1	85.2	90.3	86.4	82.6	78.8	75.0	76.3
65°	64.8	66.1	68.6	72.5	75.0	77.5	75.0	73.7	71.2	68.6	69.9
67.5°	59.7	61.0	62.3	62.3	63.6	63.6	63.6	63.6	63.6	63.6	64.8
70°	55.9	55.9	55.9	57.2	57.2	57.2	57.2	57.2	57.2	57.2	58.5
72.5°	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8	52.1
75°	44.5	44.5	44.5	44.5	44.5	44.5	44.5	44.5	44.5	44.5	45.8
77.5°	39.4	39.4	39.4	39.4	39.4	39.4	39.4	39.4	38.1	38.1	39.4
80°	33.1	33.1	33.1	33.1	31.8	31.8	31.8	31.8	31.8	31.8	33.1
82.5°	26.7	26.7	26.7	26.7	25.4	25.4	25.4	25.4	24.2	24.2	25.4
85°	24.2	25.4	25.4	26.7	26.7	26.7	25.4	24.2	22.9	21.6	21.6
87.5°	10.2	10.2	10.2	10.2	8.9	8.9	8.9	8.9	8.9	8.9	8.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2
2.5°	880.9	883.5	886.0	889.8	894.9	898.7	902.5	910.2	919.1	926.7	934.3
5°	790.7	797.0	803.4	811.0	818.6	825.0	832.6	847.9	863.1	877.1	892.4
7.5°	648.3	657.2	664.8	677.5	689.0	701.7	713.1	732.2	750.0	769.1	786.9
10°	530.1	540.2	550.4	566.9	584.7	601.3	617.8	633.0	649.6	664.8	680.1
12.5°	479.2	490.7	503.4	513.6	525.0	535.2	545.3	563.1	580.9	598.7	616.5
15°	437.3	450.0	462.7	475.4	486.9	499.6	511.0	526.3	542.8	558.0	573.3
17.5°	389.0	401.7	415.7	429.7	443.6	457.6	471.6	493.2	514.8	535.2	556.8
20°	328.0	345.8	362.3	381.3	400.4	419.5	438.6	461.4	484.3	505.9	528.8
22.5°	266.9	283.5	300.0	322.9	345.8	367.4	390.2	420.8	450.0	480.5	509.7
25°	222.5	237.7	253.0	278.4	302.5	328.0	352.1	389.0	424.6	461.4	497.0
27.5°	191.9	205.9	219.9	246.6	273.3	298.7	325.4	366.1	405.5	446.2	485.6
30°	178.0	186.9	195.8	221.2	246.6	270.8	296.2	335.6	375.0	414.4	453.8
32.5°	155.1	162.7	170.3	193.2	216.1	237.7	260.6	301.3	340.7	381.3	420.8
35°	137.3	143.6	150.0	171.6	191.9	213.6	233.9	274.6	315.2	355.9	396.6
37.5°	127.1	133.5	138.6	157.6	178.0	197.0	216.1	256.8	296.2	336.9	376.3
40°	119.5	123.3	128.4	147.5	165.3	184.3	202.1	239.0	277.1	314.0	350.8
42.5°	114.4	119.5	123.3	139.8	157.6	174.1	190.7	226.3	261.9	296.2	331.8
45°	113.1	118.2	123.3	137.3	151.3	164.0	178.0	212.3	246.6	280.9	315.2
47.5°	110.6	114.4	119.5	130.9	141.1	152.5	162.7	197.0	231.4	264.4	298.7
50°	109.3	110.6	113.1	123.3	133.5	143.6	153.8	188.1	222.5	256.8	291.1
52.5°	108.0	108.0	108.0	116.9	125.8	133.5	142.4	176.7	212.3	246.6	280.9
55°	100.4	99.2	99.2	108.0	115.7	124.6	132.2	166.5	200.8	233.9	268.2
57.5°	92.8	91.5	90.3	97.9	105.5	113.1	120.8	155.1	190.7	225.0	259.3
60°	85.2	83.9	83.9	91.5	97.9	105.5	111.9	147.5	181.8	217.4	251.7
62.5°	76.3	77.5	77.5	83.9	91.5	97.9	104.2	139.8	176.7	212.3	247.9
65°	69.9	71.2	71.2	78.8	86.4	94.1	101.7	136.0	171.6	205.9	240.3
67.5°	64.8	66.1	66.1	75.0	82.6	91.5	99.2	129.7	161.4	191.9	222.5
70°	59.7	59.7	61.0	69.9	78.8	87.7	96.6	123.3	150.0	175.4	202.1
72.5°	53.4	54.7	55.9	64.8	72.5	81.4	89.0	113.1	137.3	161.4	185.6
75°	47.0	48.3	49.6	57.2	64.8	72.5	80.1	103.0	124.6	147.5	169.1
77.5°	41.9	43.2	44.5	50.8	57.2	63.6	69.9	86.4	104.2	120.8	137.3
80°	34.3	34.3	35.6	40.7	45.8	49.6	54.7	66.1	77.5	87.7	99.2
82.5°	25.4	26.7	26.7	30.5	33.1	36.9	39.4	45.8	50.8	57.2	62.3
85°	21.6	20.3	20.3	22.9	24.2	26.7	28.0	31.8	34.3	38.1	40.7
87.5°	8.9	7.6	7.6	8.9	11.4	12.7	14.0	14.0	15.3	15.3	15.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2
2.5°	938.1	940.7	944.5	947.0	953.4	958.5	964.8	969.9	973.7	980.1	977.5
5°	903.8	915.2	926.7	938.1	947.0	955.9	963.5	972.4	982.6	1001.7	1006.8
7.5°	802.1	817.4	831.3	846.6	864.4	882.2	900.0	917.8	934.3	958.5	973.7
10°	701.7	723.3	743.6	765.2	781.8	798.3	813.5	830.1	853.0	877.1	905.1
12.5°	638.1	659.7	681.3	703.0	727.1	750.0	774.1	797.0	818.6	837.7	869.5
15°	596.2	620.3	643.2	666.1	695.3	723.3	752.5	780.5	812.3	837.7	859.3
17.5°	586.0	615.2	643.2	672.4	703.0	733.5	764.0	794.5	826.3	864.4	892.4
20°	568.2	607.6	647.0	686.4	725.8	764.0	803.4	841.5	883.5	929.2	941.9
22.5°	558.0	605.1	653.4	700.4	753.8	808.5	861.9	915.2	959.7	994.1	1032.2
25°	556.8	615.2	675.0	733.5	800.8	866.9	934.3	1000.4	1057.6	1091.9	1122.4
27.5°	555.5	626.7	696.6	766.5	849.1	930.5	1013.1	1094.5	1147.9	1197.4	1222.9
30°	540.2	625.4	711.9	797.0	889.8	982.6	1075.4	1168.2	1222.9	1257.2	1269.9
32.5°	521.2	621.6	722.0	822.4	928.0	1033.5	1137.7	1243.2	1286.4	1315.7	1305.5
35°	505.9	616.5	725.8	835.2	947.0	1060.2	1172.0	1283.9	1346.2	1386.8	1370.3
37.5°	491.9	607.6	723.3	839.0	969.9	1100.8	1231.8	1362.7	1422.4	1465.7	1446.6
40°	475.4	598.7	723.3	846.6	996.6	1145.3	1295.3	1444.0	1521.6	1558.4	1529.2
42.5°	461.4	589.8	719.5	847.9	1008.0	1168.2	1328.4	1488.5	1575.0	1627.1	1590.2
45°	443.6	572.0	699.1	827.5	1004.2	1180.9	1356.3	1533.0	1633.4	1674.1	1623.3
47.5°	424.6	551.7	677.5	803.4	991.5	1179.6	1367.8	1555.9	1648.7	1697.0	1650.0
50°	418.2	545.3	671.2	798.3	1001.7	1206.3	1409.7	1613.1	1680.5	1719.9	1657.6
52.5°	416.9	551.7	687.7	822.4	1027.1	1230.5	1435.1	1638.5	1693.2	1735.1	1679.2
55°	413.1	559.3	704.2	849.1	1062.7	1277.5	1491.1	1704.6	1759.3	1789.8	1747.9
57.5°	416.9	574.6	730.9	888.5	1108.5	1328.4	1548.3	1768.2	1834.3	1855.9	1847.0
60°	419.5	587.3	753.8	921.6	1136.4	1351.2	1566.1	1780.9	1849.5	1902.9	1913.1
62.5°	413.1	578.4	742.4	907.6	1102.1	1296.6	1491.1	1685.6	1798.7	1877.5	1923.3
65°	394.1	546.6	700.4	853.0	1032.2	1212.7	1391.9	1571.2	1690.6	1807.6	1844.5
67.5°	352.1	481.8	611.4	741.1	897.4	1053.8	1208.9	1365.2	1515.2	1628.4	1679.2
70°	305.1	406.8	509.7	611.4	753.8	896.2	1038.5	1180.9	1313.1	1437.7	1486.0
72.5°	265.7	344.5	424.6	503.4	605.1	705.5	807.2	907.6	1064.0	1188.5	1235.6
75°	226.3	283.5	339.4	396.6	466.5	536.4	605.1	675.0	785.6	897.4	944.5
77.5°	174.1	212.3	249.1	286.0	334.3	381.3	429.7	476.7	554.2	638.1	662.3
80°	120.8	142.4	162.7	184.3	222.5	260.6	298.7	336.9	387.7	434.7	471.6
82.5°	75.0	89.0	101.7	114.4	144.9	175.4	204.7	235.2	255.5	258.0	294.9
85°	48.3	57.2	64.8	72.5	90.3	109.3	127.1	144.9	129.7	120.8	143.6
87.5°	19.1	24.2	28.0	31.8	30.5	29.2	28.0	26.7	22.9	20.3	25.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2
2.5°	980.1	983.9	987.7	990.2	994.1	995.3	996.6	996.6	997.9	999.1	1001.7
5°	1027.1	1034.7	1042.4	1048.7	1056.3	1062.7	1067.8	1074.1	1079.2	1079.2	1077.9
7.5°	987.7	1006.8	1025.8	1044.9	1064.0	1077.9	1090.7	1104.6	1117.4	1119.9	1122.4
10°	935.6	955.9	975.0	995.3	1014.4	1036.0	1056.3	1076.7	1098.3	1102.1	1107.2
12.5°	887.3	911.4	935.6	958.5	982.6	997.9	1013.1	1027.1	1042.4	1052.5	1062.7
15°	886.0	906.3	926.7	945.7	966.1	975.0	983.9	991.5	1000.4	1000.4	1001.7
17.5°	915.2	928.0	940.7	952.1	964.8	966.1	968.6	969.9	971.2	967.4	963.5
20°	972.4	977.5	982.6	987.7	992.8	983.9	976.3	967.4	958.5	948.3	939.4
22.5°	1056.3	1044.9	1033.5	1022.0	1010.6	995.3	978.8	963.5	947.0	934.3	921.6
25°	1135.2	1121.2	1107.2	1093.2	1079.2	1046.2	1013.1	978.8	945.7	931.8	917.8
27.5°	1240.7	1219.0	1197.4	1175.8	1154.2	1109.7	1065.2	1020.7	976.3	952.1	929.2
30°	1266.1	1241.9	1217.8	1192.4	1168.2	1125.0	1083.0	1039.8	996.6	968.6	941.9
32.5°	1302.9	1275.0	1247.0	1219.0	1191.1	1149.1	1107.2	1064.0	1022.0	996.6	969.9
35°	1364.0	1332.2	1300.4	1267.4	1235.6	1192.4	1150.4	1107.2	1064.0	1034.7	1006.8
37.5°	1416.1	1379.2	1342.4	1305.5	1268.6	1230.5	1191.1	1152.9	1113.5	1084.3	1056.3
40°	1474.6	1433.9	1393.2	1353.8	1313.1	1277.5	1241.9	1205.1	1169.5	1146.6	1123.7
42.5°	1525.4	1475.8	1427.5	1379.2	1329.6	1305.5	1282.6	1258.5	1234.3	1222.9	1210.1
45°	1561.0	1515.2	1468.2	1422.4	1376.7	1358.9	1341.1	1323.3	1305.5	1316.9	1328.4
47.5°	1576.2	1539.4	1503.8	1468.2	1431.3	1437.7	1444.0	1449.1	1455.5	1470.7	1487.3
50°	1590.2	1569.9	1548.3	1527.9	1506.3	1530.5	1553.4	1577.5	1601.7	1633.4	1665.2
52.5°	1618.2	1606.8	1596.6	1585.1	1573.7	1615.7	1657.6	1699.5	1741.5	1777.1	1812.7
55°	1702.1	1693.2	1684.3	1674.1	1665.2	1725.0	1783.4	1843.2	1902.9	1939.8	1976.7
57.5°	1817.8	1812.7	1806.3	1801.2	1794.9	1853.4	1910.6	1967.8	2026.2	2061.8	2098.7
60°	1905.5	1906.7	1906.7	1908.0	1908.0	1952.5	1997.0	2042.8	2087.3	2117.8	2149.5
62.5°	1952.5	1950.0	1947.4	1944.9	1942.3	1979.2	2016.1	2052.9	2089.8	2112.7	2135.6
65°	1901.7	1915.6	1929.6	1943.6	1957.6	1962.7	1966.5	1971.6	1975.4	1989.4	2003.4
67.5°	1731.3	1759.3	1786.0	1814.0	1840.6	1821.6	1803.8	1784.7	1765.6	1769.5	1772.0
70°	1541.9	1573.7	1606.8	1638.5	1670.3	1625.8	1581.3	1535.6	1491.1	1475.8	1460.6
72.5°	1300.4	1328.4	1357.6	1385.6	1413.5	1358.9	1305.5	1250.8	1196.2	1169.5	1142.8
75°	994.1	1027.1	1061.4	1094.5	1127.5	1066.5	1004.2	943.2	880.9	863.1	846.6
77.5°	724.6	764.0	803.4	842.8	882.2	827.5	772.9	716.9	662.3	652.1	641.9
80°	527.5	558.0	587.3	617.8	647.0	615.2	583.5	551.7	519.9	518.6	517.4
82.5°	355.9	382.6	408.0	434.7	460.2	447.5	436.0	423.3	410.6	423.3	437.3
85°	183.0	219.9	258.0	294.9	331.8	328.0	325.4	321.6	317.8	334.3	349.6
87.5°	36.9	68.6	100.4	130.9	162.7	155.1	147.5	138.6	130.9	136.0	139.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2
2.5°	1002.9	1004.2	1004.2	1004.2	1004.2	1004.2	1001.7	1000.4	997.9	995.3	991.5
5°	1077.9	1076.7	1071.6	1066.5	1060.2	1055.1	1051.3	1046.2	1042.4	1037.3	1029.6
7.5°	1125.0	1127.5	1118.6	1111.0	1102.1	1093.2	1084.3	1075.4	1066.5	1057.6	1039.8
10°	1111.0	1114.8	1109.7	1104.6	1098.3	1093.2	1083.0	1071.6	1061.4	1050.0	1028.4
12.5°	1071.6	1081.8	1079.2	1076.7	1074.1	1071.6	1065.2	1057.6	1051.3	1043.6	1019.5
15°	1001.7	1001.7	1002.9	1004.2	1004.2	1005.5	1006.8	1008.0	1009.3	1010.6	996.6
17.5°	959.7	955.9	955.9	955.9	955.9	955.9	961.0	967.4	972.4	977.5	973.7
20°	929.2	920.3	919.1	919.1	917.8	916.5	925.4	935.6	944.5	953.4	958.5
22.5°	908.9	896.2	894.9	893.6	892.4	891.1	902.5	914.0	925.4	936.8	954.6
25°	903.8	889.8	891.1	892.4	892.4	893.6	902.5	911.4	920.3	929.2	959.7
27.5°	905.1	882.2	883.5	884.7	884.7	886.0	900.0	912.7	926.7	939.4	977.5
30°	914.0	887.3	884.7	882.2	879.6	877.1	896.2	915.2	934.3	953.4	982.6
32.5°	944.5	919.1	912.7	906.3	900.0	893.6	916.5	938.1	961.0	982.6	1006.8
35°	977.5	949.6	947.0	944.5	940.7	938.1	958.5	980.1	1000.4	1020.7	1042.4
37.5°	1027.1	999.1	996.6	992.8	990.2	986.4	1009.3	1030.9	1053.8	1075.4	1094.5
40°	1100.8	1077.9	1076.7	1076.7	1075.4	1074.1	1091.9	1111.0	1128.8	1146.6	1159.3
42.5°	1198.7	1187.3	1191.1	1196.2	1200.0	1203.8	1217.8	1233.0	1247.0	1261.0	1257.2
45°	1339.8	1351.2	1352.5	1353.8	1355.1	1356.3	1360.1	1365.2	1369.0	1372.9	1357.6
47.5°	1502.5	1517.8	1525.4	1533.0	1539.4	1547.0	1541.9	1535.6	1530.5	1524.1	1486.0
50°	1695.7	1727.5	1726.2	1725.0	1722.4	1721.2	1711.0	1700.8	1689.4	1679.2	1623.3
52.5°	1848.3	1883.9	1890.2	1896.6	1902.9	1909.3	1890.2	1871.2	1850.8	1831.7	1761.8
55°	2012.3	2049.1	2050.4	2051.7	2051.7	2052.9	2026.2	1999.5	1971.6	1944.9	1872.4
57.5°	2134.3	2169.9	2166.1	2163.5	2159.7	2155.9	2124.1	2092.3	2060.6	2028.8	1956.3
60°	2180.0	2210.6	2202.9	2195.3	2186.4	2178.8	2154.6	2130.5	2105.0	2080.9	2011.0
62.5°	2158.4	2181.3	2169.9	2159.7	2148.3	2136.8	2106.3	2074.5	2044.0	2012.3	1961.4
65°	2016.1	2030.1	2014.8	2000.8	1986.8	1971.6	1946.2	1920.7	1894.0	1868.6	1834.3
67.5°	1775.8	1778.4	1777.1	1775.8	1774.5	1773.3	1736.4	1699.5	1661.4	1624.5	1622.0
70°	1446.6	1431.3	1433.9	1437.7	1440.2	1442.8	1414.8	1388.1	1360.1	1332.2	1344.9
72.5°	1116.1	1089.4	1095.7	1103.4	1109.7	1116.1	1093.2	1071.6	1048.7	1025.8	1043.6
75°	828.8	812.3	818.6	826.3	832.6	839.0	830.1	821.2	811.0	802.1	818.6
77.5°	631.8	621.6	622.9	622.9	624.1	624.1	625.4	628.0	629.2	630.5	648.3
80°	514.8	513.6	512.3	511.0	508.5	507.2	519.9	532.6	545.3	558.0	566.9
82.5°	450.0	462.7	455.1	448.7	441.1	433.5	444.9	456.3	467.8	479.2	475.4
85°	366.1	381.3	367.4	353.4	338.1	324.1	334.3	343.2	353.4	362.3	357.2
87.5°	144.9	148.7	125.8	104.2	81.4	58.5	92.8	125.8	160.2	193.2	198.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2	915.2
2.5°	987.7	982.6	978.8	977.5	975.0	973.7	971.2	968.6	964.8	962.3	958.5
5°	1020.7	1013.1	1004.2	991.5	980.1	967.4	954.6	943.2	931.8	919.1	907.6
7.5°	1022.0	1004.2	986.4	969.9	952.1	935.6	917.8	902.5	886.0	869.5	854.2
10°	1008.0	986.4	964.8	943.2	922.9	901.3	879.6	861.9	842.8	823.7	805.9
12.5°	996.6	972.4	948.3	922.9	898.7	873.3	847.9	830.1	812.3	794.5	776.7
15°	982.6	967.4	953.4	930.5	907.6	884.7	861.9	837.7	814.8	790.7	766.5
17.5°	971.2	967.4	963.5	948.3	933.0	916.5	901.3	877.1	853.0	827.5	803.4
20°	964.8	969.9	975.0	967.4	959.7	950.8	943.2	925.4	907.6	888.5	870.7
22.5°	972.4	991.5	1009.3	1010.6	1013.1	1014.4	1015.7	999.1	982.6	964.8	948.3
25°	990.2	1020.7	1051.3	1067.8	1084.3	1102.1	1118.6	1108.5	1098.3	1088.1	1077.9
27.5°	1014.4	1052.5	1090.7	1114.8	1137.7	1161.8	1186.0	1184.7	1183.5	1180.9	1179.6
30°	1010.6	1039.8	1069.0	1098.3	1127.5	1156.8	1186.0	1201.3	1215.2	1230.5	1245.7
32.5°	1032.2	1056.3	1081.8	1112.3	1142.8	1174.6	1205.1	1236.8	1267.4	1299.1	1330.9
35°	1065.2	1086.8	1109.7	1142.8	1177.1	1210.1	1244.5	1282.6	1322.0	1361.4	1399.6
37.5°	1114.8	1133.9	1154.2	1182.2	1211.4	1239.4	1268.6	1324.6	1380.5	1437.7	1493.6
40°	1172.0	1184.7	1197.4	1224.1	1250.8	1277.5	1304.2	1374.1	1444.0	1514.0	1583.9
42.5°	1254.6	1250.8	1247.0	1268.6	1291.5	1313.1	1336.0	1399.6	1463.1	1526.7	1590.2
45°	1342.4	1327.1	1311.8	1322.0	1333.5	1343.6	1355.1	1419.9	1484.7	1550.8	1615.7
47.5°	1447.9	1409.7	1371.6	1362.7	1353.8	1343.6	1334.7	1404.6	1474.6	1545.7	1615.7
50°	1567.3	1510.1	1454.2	1431.3	1407.2	1384.3	1360.1	1417.3	1475.8	1534.3	1591.5
52.5°	1691.9	1620.7	1550.8	1515.2	1479.6	1442.8	1407.2	1455.5	1505.1	1554.6	1602.9
55°	1798.7	1726.2	1652.5	1610.6	1568.6	1526.7	1484.7	1533.0	1581.3	1629.6	1677.9
57.5°	1883.9	1811.4	1739.0	1699.5	1658.9	1619.5	1578.8	1624.5	1671.6	1718.6	1764.4
60°	1942.3	1872.4	1802.5	1764.4	1726.2	1688.1	1650.0	1704.6	1759.3	1815.2	1869.9
62.5°	1911.8	1861.0	1810.1	1793.6	1777.1	1759.3	1742.8	1794.9	1845.7	1897.8	1950.0
65°	1800.0	1765.6	1731.3	1747.9	1765.6	1782.2	1800.0	1834.3	1868.6	1904.2	1938.5
67.5°	1618.2	1615.7	1611.8	1648.7	1685.6	1723.7	1760.6	1783.4	1805.1	1827.9	1850.8
70°	1357.6	1371.6	1384.3	1447.9	1511.4	1575.0	1638.5	1647.4	1656.3	1665.2	1674.1
72.5°	1062.7	1080.5	1099.6	1183.5	1266.1	1350.0	1433.9	1428.8	1423.7	1417.3	1412.3
75°	836.4	853.0	870.7	948.3	1025.8	1103.4	1180.9	1159.3	1139.0	1117.4	1095.7
77.5°	667.4	685.2	704.2	776.7	849.1	922.9	995.3	943.2	891.1	839.0	786.9
80°	574.6	583.5	591.1	640.7	689.0	738.5	788.1	734.7	680.1	625.4	572.0
82.5°	471.6	466.5	462.7	491.9	521.2	550.4	579.7	528.8	478.0	425.8	375.0
85°	352.1	347.0	341.9	357.2	372.5	389.0	404.2	345.8	287.3	227.5	169.1
87.5°	204.7	209.7	214.8	231.4	247.9	265.7	282.2	222.5	162.7	101.7	41.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671823
 CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	915.2	915.2
2.5°	950.8	944.5
5°	898.7	889.8
7.5°	841.5	830.1
10°	789.4	774.1
12.5°	756.3	737.3
15°	743.6	720.8
17.5°	781.8	760.2
20°	840.2	811.0
22.5°	911.4	875.8
25°	1034.7	991.5
27.5°	1135.2	1090.7
30°	1197.4	1149.1
32.5°	1266.1	1202.5
35°	1337.3	1276.2
37.5°	1423.7	1355.1
40°	1512.7	1441.5
42.5°	1543.2	1497.4
45°	1572.4	1529.2
47.5°	1578.8	1543.2
50°	1585.1	1580.1
52.5°	1602.9	1601.7
55°	1679.2	1680.5
57.5°	1773.3	1780.9
60°	1859.7	1850.8
62.5°	1904.2	1858.4
65°	1873.7	1810.1
67.5°	1782.2	1713.5
70°	1581.3	1488.5
72.5°	1330.9	1249.6
75°	1025.8	957.2
77.5°	729.6	672.4
80°	513.6	456.3
82.5°	329.2	283.5
85°	148.7	129.7
87.5°	41.9	40.7
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P671823

CATALOG NUMBER: CCP-SA-1B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)