

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P671861

Luminaire Tested: **CCP-SA-2A-827-U-SLR**

Issue Date: 04/16/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P671861  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-2A-827-U-SLR  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @350mA w/ SLR  
distribution lens  
Light Source: (32) 2700K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3337.9 lumens  
Efficiency: N/A  
Efficacy: 92.2 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G2


Input Watts (W): 36.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 4.7 fc  
 Type IV - Short - N/A

REPORT NUMBER: P671861  
CATALOG NUMBER: CCP-SA-2A-827-U-SLR

## Luminous Intensity Polar Plot



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 686.8    | 0.0    | 686.8  |
|                    | % Fixture | 20.6     | 0.0    | 20.6   |
| <b>Street Side</b> | Lumens    | 2651.1   | 0.0    | 2651.1 |
|                    | % Fixture | 79.4     | 0.0    | 79.4   |
| <b>Total</b>       | Lumens    | 3337.9   | 0.0    | 3337.9 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 82.8   | 2.5       |
| 10°-20°   | 174.9  | 5.2       |
| 20°-30°   | 255.8  | 7.7       |
| 30°-40°   | 360.4  | 10.8      |
| 40°-50°   | 495.3  | 14.8      |
| 50°-60°   | 675.1  | 20.2      |
| 60°-70°   | 738.9  | 22.1      |
| 70°-80°   | 426.7  | 12.8      |
| 80°-90°   | 127.9  | 3.8       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 3337.9 | 100.0     |
| 0°-180°   | 3337.9 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P671861


CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 342.8  | 10.3      |                         |      |         |
| FM   | (30°-60°)   | 1218.1 | 36.5      |                         |      |         |
| FH   | (60°-80°)   | 981.5  | 29.4      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 108.6  | 3.3       |                         |      | G2/225  |
| BL   | (0°-30°)    | 170.7  | 5.1       | B1/500                  |      |         |
| BM   | (30°-60°)   | 312.7  | 9.4       | B1/1000                 |      |         |
| BH   | (60°-80°)   | 184.1  | 5.5       | B1/500                  |      | G1/500  |
| BVH  | (80°-90°)   | 19.3   | 0.6       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G2**

Type IV Short



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5°  | 25°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 |
| 2.5°   | 1100.0 | 1094.1 | 1089.6 | 1085.2 | 1079.2 | 1074.8 | 1068.9 | 1063.0 | 1055.6 | 1049.6 | 1042.2 |
| 5°     | 1036.3 | 1018.5 | 1000.8 | 990.4  | 978.6  | 968.2  | 956.4  | 943.0  | 929.7  | 914.9  | 901.6  |
| 7.5°   | 966.7  | 944.5  | 922.3  | 904.6  | 885.3  | 867.5  | 848.3  | 832.0  | 815.7  | 799.4  | 783.2  |
| 10°    | 901.6  | 880.9  | 860.1  | 837.9  | 814.2  | 792.0  | 768.4  | 746.1  | 723.9  | 701.7  | 679.5  |
| 12.5°  | 858.7  | 833.5  | 809.8  | 784.6  | 760.9  | 735.8  | 710.6  | 689.9  | 669.2  | 647.0  | 626.2  |
| 15°    | 839.4  | 815.7  | 793.5  | 768.4  | 743.2  | 718.0  | 692.8  | 669.2  | 647.0  | 623.3  | 599.6  |
| 17.5°  | 885.3  | 851.3  | 817.2  | 784.6  | 752.1  | 719.5  | 686.9  | 657.3  | 627.7  | 598.1  | 568.5  |
| 20°    | 944.5  | 901.6  | 860.1  | 820.2  | 778.7  | 738.7  | 697.3  | 655.8  | 614.4  | 572.9  | 531.5  |
| 22.5°  | 1020.0 | 971.2  | 923.8  | 872.0  | 818.7  | 766.9  | 713.6  | 661.8  | 609.9  | 556.6  | 504.8  |
| 25°    | 1154.7 | 1097.0 | 1039.3 | 965.3  | 889.7  | 815.7  | 740.2  | 672.1  | 605.5  | 537.4  | 469.3  |
| 27.5°  | 1270.2 | 1191.8 | 1114.8 | 1025.9 | 937.1  | 848.3  | 759.5  | 681.0  | 604.0  | 525.6  | 447.1  |
| 30°    | 1338.3 | 1261.3 | 1184.4 | 1076.3 | 969.7  | 861.6  | 753.5  | 666.2  | 580.3  | 493.0  | 405.6  |
| 32.5°  | 1400.5 | 1314.6 | 1228.8 | 1110.3 | 990.4  | 872.0  | 752.1  | 655.8  | 561.1  | 464.9  | 368.6  |
| 35°    | 1486.4 | 1391.6 | 1298.4 | 1160.7 | 1023.0 | 885.3  | 747.6  | 648.4  | 547.8  | 448.6  | 347.9  |
| 37.5°  | 1578.2 | 1461.2 | 1345.7 | 1193.2 | 1040.8 | 888.3  | 735.8  | 638.1  | 540.4  | 442.7  | 344.9  |
| 40°    | 1678.8 | 1536.7 | 1396.1 | 1227.3 | 1060.0 | 891.2  | 722.5  | 624.7  | 527.0  | 427.8  | 330.1  |
| 42.5°  | 1744.0 | 1590.0 | 1436.0 | 1253.9 | 1073.3 | 891.2  | 709.1  | 612.9  | 516.7  | 419.0  | 322.7  |
| 45°    | 1781.0 | 1631.5 | 1483.4 | 1286.5 | 1089.6 | 892.7  | 695.8  | 601.1  | 506.3  | 410.1  | 315.3  |
| 47.5°  | 1797.3 | 1658.1 | 1518.9 | 1311.7 | 1105.9 | 898.6  | 691.4  | 595.1  | 497.4  | 401.2  | 303.5  |
| 50°    | 1840.2 | 1717.3 | 1594.4 | 1372.4 | 1151.8 | 929.7  | 707.7  | 604.0  | 501.9  | 398.2  | 294.6  |
| 52.5°  | 1865.4 | 1760.3 | 1655.1 | 1427.2 | 1199.2 | 971.2  | 743.2  | 627.7  | 512.2  | 396.8  | 281.3  |
| 55°    | 1957.2 | 1856.5 | 1755.8 | 1513.0 | 1268.7 | 1025.9 | 781.7  | 654.4  | 527.0  | 398.2  | 270.9  |
| 57.5°  | 2074.1 | 1967.5 | 1862.4 | 1600.4 | 1338.3 | 1076.3 | 814.2  | 678.0  | 540.4  | 404.2  | 266.5  |
| 60°    | 2155.5 | 2051.9 | 1949.7 | 1671.4 | 1391.6 | 1113.3 | 833.5  | 691.4  | 549.2  | 405.6  | 263.5  |
| 62.5°  | 2164.4 | 2031.2 | 1899.4 | 1628.5 | 1357.6 | 1085.2 | 814.2  | 676.6  | 538.9  | 399.7  | 262.0  |
| 65°    | 2108.2 | 1952.7 | 1797.3 | 1538.2 | 1279.1 | 1020.0 | 760.9  | 635.1  | 509.3  | 382.0  | 256.1  |
| 67.5°  | 1995.6 | 1813.5 | 1631.5 | 1394.6 | 1157.7 | 920.8  | 684.0  | 575.9  | 469.3  | 361.2  | 253.2  |
| 70°    | 1733.6 | 1573.7 | 1415.3 | 1209.5 | 1005.2 | 799.4  | 593.7  | 504.8  | 417.5  | 328.7  | 239.8  |
| 72.5°  | 1455.3 | 1305.8 | 1157.7 | 990.4  | 824.6  | 657.3  | 490.0  | 423.4  | 356.8  | 288.7  | 222.1  |
| 75°    | 1114.8 | 1002.3 | 891.2  | 766.9  | 642.5  | 516.7  | 392.3  | 343.5  | 294.6  | 245.8  | 196.9  |
| 77.5°  | 783.2  | 722.5  | 663.2  | 570.0  | 476.7  | 383.4  | 290.2  | 257.6  | 225.0  | 192.5  | 159.9  |
| 80°    | 531.5  | 497.4  | 464.9  | 398.2  | 331.6  | 263.5  | 196.9  | 176.2  | 154.0  | 133.2  | 111.0  |
| 82.5°  | 330.1  | 328.7  | 325.7  | 279.8  | 233.9  | 188.0  | 142.1  | 124.4  | 108.1  | 90.3   | 72.5   |
| 85°    | 151.0  | 176.2  | 199.9  | 174.7  | 149.5  | 124.4  | 99.2   | 87.3   | 75.5   | 62.2   | 50.3   |
| 87.5°  | 47.4   | 57.7   | 66.6   | 63.7   | 59.2   | 56.3   | 51.8   | 44.4   | 37.0   | 29.6   | 22.2   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 25° |
|--------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 27.5°  | 30°    | 32.5°  | 35°    | 37.5°  | 40°    | 42.5°  | 45°    | 47.5°  | 50°    | 52.5°  |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 |
| 2.5°   | 1036.3 | 1031.9 | 1025.9 | 1020.0 | 1012.6 | 1006.7 | 999.3  | 991.9  | 990.4  | 987.5  | 986.0  |
| 5°     | 892.7  | 883.8  | 873.5  | 864.6  | 855.7  | 845.3  | 836.5  | 826.1  | 818.7  | 809.8  | 802.4  |
| 7.5°   | 766.9  | 752.1  | 735.8  | 719.5  | 704.7  | 689.9  | 673.6  | 658.8  | 651.4  | 644.0  | 636.6  |
| 10°    | 666.2  | 651.4  | 638.1  | 623.3  | 612.9  | 604.0  | 593.7  | 583.3  | 574.4  | 565.5  | 556.6  |
| 12.5°  | 615.9  | 605.5  | 595.1  | 584.8  | 572.9  | 562.6  | 550.7  | 538.9  | 528.5  | 519.6  | 509.3  |
| 15°    | 584.8  | 570.0  | 553.7  | 538.9  | 522.6  | 507.8  | 491.5  | 475.2  | 463.4  | 453.0  | 441.2  |
| 17.5°  | 547.8  | 525.6  | 504.8  | 482.6  | 464.9  | 447.1  | 427.8  | 410.1  | 396.8  | 382.0  | 368.6  |
| 20°    | 506.3  | 481.1  | 454.5  | 429.3  | 408.6  | 389.4  | 368.6  | 347.9  | 333.1  | 316.8  | 302.0  |
| 22.5°  | 470.8  | 438.2  | 404.2  | 370.1  | 347.9  | 325.7  | 302.0  | 279.8  | 266.5  | 251.7  | 238.4  |
| 25°    | 432.3  | 396.8  | 359.7  | 322.7  | 300.5  | 276.8  | 254.6  | 230.9  | 220.6  | 211.7  | 201.3  |
| 27.5°  | 411.6  | 376.0  | 339.0  | 303.5  | 282.8  | 260.6  | 239.8  | 217.6  | 210.2  | 201.3  | 193.9  |
| 30°    | 370.1  | 336.1  | 300.5  | 265.0  | 250.2  | 236.9  | 222.1  | 207.3  | 204.3  | 202.8  | 199.9  |
| 32.5°  | 333.1  | 297.6  | 262.0  | 226.5  | 213.2  | 199.9  | 186.5  | 173.2  | 171.7  | 168.8  | 167.3  |
| 35°    | 313.9  | 279.8  | 244.3  | 210.2  | 198.4  | 185.1  | 173.2  | 159.9  | 156.9  | 152.5  | 149.5  |
| 37.5°  | 309.4  | 273.9  | 236.9  | 201.3  | 189.5  | 177.7  | 164.3  | 152.5  | 149.5  | 146.6  | 143.6  |
| 40°    | 297.6  | 263.5  | 230.9  | 196.9  | 185.1  | 173.2  | 159.9  | 148.0  | 145.1  | 142.1  | 139.2  |
| 42.5°  | 288.7  | 256.1  | 222.1  | 188.0  | 177.7  | 167.3  | 155.4  | 145.1  | 142.1  | 139.2  | 134.7  |
| 45°    | 281.3  | 247.2  | 211.7  | 177.7  | 170.3  | 162.8  | 154.0  | 146.6  | 143.6  | 139.2  | 136.2  |
| 47.5°  | 269.4  | 236.9  | 202.8  | 168.8  | 161.4  | 155.4  | 148.0  | 140.6  | 137.7  | 134.7  | 131.8  |
| 50°    | 260.6  | 226.5  | 192.5  | 158.4  | 152.5  | 146.6  | 140.6  | 134.7  | 134.7  | 136.2  | 136.2  |
| 52.5°  | 248.7  | 216.1  | 183.6  | 151.0  | 145.1  | 139.2  | 133.2  | 127.3  | 128.8  | 130.3  | 131.8  |
| 55°    | 238.4  | 207.3  | 174.7  | 142.1  | 136.2  | 130.3  | 122.9  | 117.0  | 118.4  | 119.9  | 121.4  |
| 57.5°  | 233.9  | 201.3  | 168.8  | 136.2  | 130.3  | 122.9  | 117.0  | 109.6  | 109.6  | 109.6  | 109.6  |
| 60°    | 230.9  | 196.9  | 164.3  | 130.3  | 122.9  | 117.0  | 109.6  | 102.2  | 100.7  | 100.7  | 99.2   |
| 62.5°  | 229.5  | 195.4  | 162.8  | 128.8  | 119.9  | 112.5  | 103.6  | 94.7   | 93.3   | 91.8   | 90.3   |
| 65°    | 223.5  | 192.5  | 159.9  | 127.3  | 117.0  | 108.1  | 97.7   | 87.3   | 85.9   | 85.9   | 84.4   |
| 67.5°  | 222.1  | 189.5  | 158.4  | 125.8  | 115.5  | 103.6  | 93.3   | 81.4   | 79.9   | 78.5   | 77.0   |
| 70°    | 210.2  | 182.1  | 152.5  | 122.9  | 111.0  | 100.7  | 88.8   | 77.0   | 75.5   | 72.5   | 71.1   |
| 72.5°  | 195.4  | 170.3  | 143.6  | 117.0  | 105.1  | 93.3   | 81.4   | 69.6   | 68.1   | 66.6   | 63.7   |
| 75°    | 173.2  | 149.5  | 125.8  | 102.2  | 91.8   | 82.9   | 72.5   | 62.2   | 60.7   | 59.2   | 56.3   |
| 77.5°  | 142.1  | 122.9  | 105.1  | 85.9   | 78.5   | 71.1   | 63.7   | 56.3   | 54.8   | 53.3   | 50.3   |
| 80°    | 100.7  | 88.8   | 78.5   | 66.6   | 62.2   | 56.3   | 51.8   | 45.9   | 45.9   | 44.4   | 44.4   |
| 82.5°  | 66.6   | 60.7   | 54.8   | 48.9   | 45.9   | 42.9   | 40.0   | 37.0   | 37.0   | 35.5   | 35.5   |
| 85°    | 47.4   | 44.4   | 40.0   | 37.0   | 35.5   | 32.6   | 31.1   | 28.1   | 28.1   | 28.1   | 28.1   |
| 87.5°  | 22.2   | 22.2   | 20.7   | 20.7   | 19.2   | 19.2   | 17.8   | 16.3   | 16.3   | 16.3   | 16.3   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° | 47.5° | 50° | 52.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 55°    | 57.5°  | 60°    | 62.5°  | 65°    | 67.5°  | 70°    | 72.5°  | 75°    | 77.5°  | 80°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 |
| 2.5°   | 983.0  | 978.6  | 974.1  | 968.2  | 963.8  | 957.8  | 950.4  | 944.5  | 937.1  | 937.1  | 935.6  |
| 5°     | 793.5  | 789.1  | 784.6  | 778.7  | 774.3  | 768.4  | 763.9  | 758.0  | 752.1  | 752.1  | 750.6  |
| 7.5°   | 629.2  | 620.3  | 611.4  | 601.1  | 592.2  | 586.3  | 580.3  | 572.9  | 567.0  | 562.6  | 558.1  |
| 10°    | 547.8  | 538.9  | 528.5  | 519.6  | 509.3  | 501.9  | 494.5  | 485.6  | 478.2  | 472.3  | 466.3  |
| 12.5°  | 498.9  | 488.5  | 478.2  | 467.8  | 457.5  | 447.1  | 438.2  | 427.8  | 417.5  | 410.1  | 402.7  |
| 15°    | 429.3  | 419.0  | 408.6  | 398.2  | 387.9  | 376.0  | 364.2  | 350.9  | 339.0  | 333.1  | 328.7  |
| 17.5°  | 353.8  | 343.5  | 331.6  | 321.3  | 309.4  | 300.5  | 291.6  | 282.8  | 273.9  | 268.0  | 263.5  |
| 20°    | 285.7  | 273.9  | 262.0  | 250.2  | 238.4  | 232.4  | 226.5  | 220.6  | 214.7  | 210.2  | 207.3  |
| 22.5°  | 223.5  | 216.1  | 210.2  | 202.8  | 195.4  | 191.0  | 188.0  | 183.6  | 179.1  | 179.1  | 179.1  |
| 25°    | 191.0  | 186.5  | 183.6  | 179.1  | 174.7  | 173.2  | 171.7  | 168.8  | 167.3  | 165.8  | 165.8  |
| 27.5°  | 185.1  | 180.6  | 176.2  | 171.7  | 167.3  | 165.8  | 164.3  | 161.4  | 159.9  | 159.9  | 159.9  |
| 30°    | 196.9  | 195.4  | 193.9  | 192.5  | 191.0  | 188.0  | 183.6  | 180.6  | 176.2  | 173.2  | 170.3  |
| 32.5°  | 164.3  | 162.8  | 162.8  | 161.4  | 159.9  | 162.8  | 164.3  | 167.3  | 168.8  | 170.3  | 171.7  |
| 35°    | 145.1  | 142.1  | 139.2  | 136.2  | 133.2  | 131.8  | 130.3  | 128.8  | 127.3  | 127.3  | 125.8  |
| 37.5°  | 140.6  | 137.7  | 134.7  | 131.8  | 128.8  | 127.3  | 125.8  | 124.4  | 122.9  | 122.9  | 121.4  |
| 40°    | 136.2  | 133.2  | 131.8  | 128.8  | 125.8  | 124.4  | 122.9  | 119.9  | 118.4  | 117.0  | 117.0  |
| 42.5°  | 131.8  | 130.3  | 127.3  | 125.8  | 122.9  | 121.4  | 119.9  | 117.0  | 115.5  | 114.0  | 112.5  |
| 45°    | 131.8  | 128.8  | 125.8  | 122.9  | 119.9  | 118.4  | 115.5  | 114.0  | 111.0  | 111.0  | 109.6  |
| 47.5°  | 128.8  | 125.8  | 122.9  | 119.9  | 117.0  | 115.5  | 112.5  | 111.0  | 108.1  | 106.6  | 105.1  |
| 50°    | 136.2  | 131.8  | 125.8  | 121.4  | 115.5  | 114.0  | 111.0  | 109.6  | 106.6  | 105.1  | 103.6  |
| 52.5°  | 133.2  | 128.8  | 122.9  | 118.4  | 112.5  | 109.6  | 108.1  | 105.1  | 102.2  | 100.7  | 99.2   |
| 55°    | 122.9  | 118.4  | 115.5  | 111.0  | 106.6  | 103.6  | 100.7  | 97.7   | 94.7   | 93.3   | 93.3   |
| 57.5°  | 109.6  | 108.1  | 106.6  | 105.1  | 103.6  | 100.7  | 97.7   | 93.3   | 90.3   | 88.8   | 87.3   |
| 60°    | 97.7   | 99.2   | 100.7  | 102.2  | 103.6  | 99.2   | 94.7   | 90.3   | 85.9   | 84.4   | 82.9   |
| 62.5°  | 88.8   | 91.8   | 94.7   | 96.2   | 99.2   | 94.7   | 90.3   | 85.9   | 81.4   | 79.9   | 78.5   |
| 65°    | 82.9   | 84.4   | 84.4   | 85.9   | 85.9   | 82.9   | 81.4   | 78.5   | 75.5   | 74.0   | 74.0   |
| 67.5°  | 75.5   | 75.5   | 75.5   | 74.0   | 74.0   | 72.5   | 72.5   | 71.1   | 69.6   | 68.1   | 68.1   |
| 70°    | 68.1   | 68.1   | 68.1   | 66.6   | 66.6   | 65.1   | 65.1   | 63.7   | 62.2   | 62.2   | 60.7   |
| 72.5°  | 62.2   | 62.2   | 60.7   | 60.7   | 59.2   | 59.2   | 59.2   | 57.7   | 57.7   | 56.3   | 56.3   |
| 75°    | 54.8   | 54.8   | 53.3   | 53.3   | 51.8   | 51.8   | 51.8   | 50.3   | 50.3   | 50.3   | 48.9   |
| 77.5°  | 48.9   | 48.9   | 47.4   | 47.4   | 45.9   | 45.9   | 45.9   | 44.4   | 44.4   | 42.9   | 42.9   |
| 80°    | 42.9   | 42.9   | 41.5   | 41.5   | 40.0   | 40.0   | 38.5   | 38.5   | 37.0   | 37.0   | 35.5   |
| 82.5°  | 34.1   | 34.1   | 34.1   | 34.1   | 34.1   | 32.6   | 32.6   | 31.1   | 29.6   | 29.6   | 28.1   |
| 85°    | 28.1   | 28.1   | 28.1   | 26.6   | 26.6   | 26.6   | 25.2   | 25.2   | 23.7   | 22.2   | 22.2   |
| 87.5°  | 16.3   | 16.3   | 16.3   | 14.8   | 14.8   | 14.8   | 14.8   | 14.8   | 14.8   | 14.8   | 13.3   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° | 75° | 77.5° | 80° |
|--------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |

REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 82.5°  | 85°    | 87.5°  | 90°    | 92.5°  | 95°    | 97.5°  | 100°   | 102.5° | 105°   | 107.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 |
| 2.5°   | 935.6  | 934.2  | 928.2  | 922.3  | 928.2  | 934.2  | 934.2  | 934.2  | 932.7  | 932.7  | 932.7  |
| 5°     | 750.6  | 749.1  | 746.1  | 743.2  | 743.2  | 741.7  | 744.7  | 747.6  | 750.6  | 753.5  | 756.5  |
| 7.5°   | 552.2  | 547.8  | 543.3  | 538.9  | 541.8  | 543.3  | 547.8  | 550.7  | 555.2  | 558.1  | 565.5  |
| 10°    | 460.4  | 454.5  | 450.1  | 445.6  | 442.7  | 439.7  | 436.7  | 435.3  | 432.3  | 429.3  | 432.3  |
| 12.5°  | 393.8  | 386.4  | 379.0  | 370.1  | 368.6  | 367.2  | 364.2  | 361.2  | 358.3  | 355.3  | 353.8  |
| 15°    | 322.7  | 316.8  | 313.9  | 309.4  | 303.5  | 297.6  | 294.6  | 293.1  | 290.2  | 287.2  | 285.7  |
| 17.5°  | 257.6  | 251.7  | 247.2  | 242.8  | 241.3  | 238.4  | 238.4  | 238.4  | 238.4  | 238.4  | 238.4  |
| 20°    | 202.8  | 198.4  | 198.4  | 196.9  | 196.9  | 195.4  | 196.9  | 198.4  | 198.4  | 199.9  | 201.3  |
| 22.5°  | 177.7  | 177.7  | 176.2  | 174.7  | 176.2  | 176.2  | 177.7  | 179.1  | 180.6  | 182.1  | 183.6  |
| 25°    | 164.3  | 162.8  | 164.3  | 165.8  | 165.8  | 165.8  | 167.3  | 167.3  | 168.8  | 168.8  | 168.8  |
| 27.5°  | 158.4  | 158.4  | 159.9  | 159.9  | 161.4  | 161.4  | 161.4  | 159.9  | 159.9  | 158.4  | 158.4  |
| 30°    | 167.3  | 164.3  | 164.3  | 164.3  | 162.8  | 161.4  | 159.9  | 159.9  | 158.4  | 156.9  | 155.4  |
| 32.5°  | 173.2  | 174.7  | 173.2  | 170.3  | 168.8  | 165.8  | 164.3  | 161.4  | 159.9  | 156.9  | 154.0  |
| 35°    | 125.8  | 124.4  | 127.3  | 128.8  | 130.3  | 131.8  | 133.2  | 134.7  | 134.7  | 136.2  | 136.2  |
| 37.5°  | 121.4  | 119.9  | 119.9  | 118.4  | 118.4  | 118.4  | 118.4  | 118.4  | 117.0  | 117.0  | 118.4  |
| 40°    | 115.5  | 114.0  | 114.0  | 112.5  | 112.5  | 111.0  | 111.0  | 111.0  | 111.0  | 111.0  | 111.0  |
| 42.5°  | 111.0  | 109.6  | 109.6  | 109.6  | 109.6  | 108.1  | 108.1  | 106.6  | 106.6  | 105.1  | 105.1  |
| 45°    | 109.6  | 108.1  | 106.6  | 105.1  | 105.1  | 103.6  | 103.6  | 103.6  | 102.2  | 102.2  | 102.2  |
| 47.5°  | 103.6  | 102.2  | 102.2  | 100.7  | 100.7  | 99.2   | 99.2   | 99.2   | 97.7   | 97.7   | 97.7   |
| 50°    | 100.7  | 99.2   | 99.2   | 97.7   | 97.7   | 96.2   | 96.2   | 96.2   | 94.7   | 94.7   | 94.7   |
| 52.5°  | 96.2   | 94.7   | 94.7   | 94.7   | 93.3   | 91.8   | 91.8   | 91.8   | 90.3   | 90.3   | 90.3   |
| 55°    | 91.8   | 90.3   | 90.3   | 90.3   | 88.8   | 87.3   | 87.3   | 87.3   | 85.9   | 85.9   | 85.9   |
| 57.5°  | 85.9   | 84.4   | 84.4   | 82.9   | 82.9   | 82.9   | 82.9   | 82.9   | 81.4   | 81.4   | 81.4   |
| 60°    | 81.4   | 79.9   | 79.9   | 78.5   | 78.5   | 77.0   | 77.0   | 77.0   | 77.0   | 77.0   | 77.0   |
| 62.5°  | 77.0   | 75.5   | 74.0   | 72.5   | 74.0   | 74.0   | 74.0   | 74.0   | 72.5   | 72.5   | 72.5   |
| 65°    | 72.5   | 71.1   | 69.6   | 68.1   | 68.1   | 68.1   | 68.1   | 68.1   | 68.1   | 68.1   | 68.1   |
| 67.5°  | 66.6   | 65.1   | 63.7   | 62.2   | 63.7   | 63.7   | 63.7   | 63.7   | 63.7   | 63.7   | 63.7   |
| 70°    | 60.7   | 59.2   | 59.2   | 57.7   | 57.7   | 56.3   | 56.3   | 57.7   | 57.7   | 57.7   | 57.7   |
| 72.5°  | 54.8   | 53.3   | 53.3   | 51.8   | 51.8   | 51.8   | 51.8   | 51.8   | 51.8   | 51.8   | 51.8   |
| 75°    | 48.9   | 47.4   | 47.4   | 45.9   | 45.9   | 45.9   | 45.9   | 45.9   | 45.9   | 45.9   | 45.9   |
| 77.5°  | 41.5   | 40.0   | 40.0   | 40.0   | 40.0   | 40.0   | 40.0   | 41.5   | 41.5   | 41.5   | 41.5   |
| 80°    | 35.5   | 34.1   | 34.1   | 34.1   | 34.1   | 34.1   | 34.1   | 34.1   | 34.1   | 34.1   | 34.1   |
| 82.5°  | 28.1   | 26.6   | 26.6   | 26.6   | 26.6   | 26.6   | 26.6   | 26.6   | 26.6   | 26.6   | 26.6   |
| 85°    | 20.7   | 19.2   | 19.2   | 19.2   | 20.7   | 20.7   | 20.7   | 20.7   | 20.7   | 20.7   | 20.7   |
| 87.5°  | 13.3   | 11.8   | 11.8   | 11.8   | 13.3   | 13.3   | 13.3   | 13.3   | 11.8   | 11.8   | 11.8   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° | 92.5° | 95° | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|------|--------|------|--------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 110°   | 112.5° | 115°   | 117.5° | 120°   | 122.5° | 125°   | 127.5° | 130°   | 132.5° | 135°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 |
| 2.5°   | 932.7  | 932.7  | 932.7  | 931.2  | 929.7  | 928.2  | 926.8  | 931.2  | 934.2  | 938.6  | 941.6  |
| 5°     | 758.0  | 760.9  | 762.4  | 766.9  | 771.3  | 775.8  | 780.2  | 783.2  | 786.1  | 787.6  | 790.6  |
| 7.5°   | 571.5  | 578.9  | 584.8  | 590.7  | 596.6  | 601.1  | 607.0  | 611.4  | 615.9  | 620.3  | 624.7  |
| 10°    | 433.8  | 436.7  | 438.2  | 444.1  | 448.6  | 454.5  | 458.9  | 463.4  | 467.8  | 470.8  | 475.2  |
| 12.5°  | 352.3  | 349.4  | 347.9  | 347.9  | 347.9  | 347.9  | 347.9  | 350.9  | 353.8  | 356.8  | 359.7  |
| 15°    | 284.2  | 282.8  | 281.3  | 279.8  | 278.3  | 275.4  | 273.9  | 276.8  | 279.8  | 282.8  | 285.7  |
| 17.5°  | 238.4  | 238.4  | 238.4  | 236.9  | 235.4  | 233.9  | 232.4  | 233.9  | 235.4  | 235.4  | 236.9  |
| 20°    | 204.3  | 205.8  | 207.3  | 208.7  | 208.7  | 210.2  | 210.2  | 211.7  | 213.2  | 213.2  | 214.7  |
| 22.5°  | 183.6  | 185.1  | 185.1  | 185.1  | 186.5  | 186.5  | 186.5  | 188.0  | 189.5  | 191.0  | 192.5  |
| 25°    | 167.3  | 167.3  | 165.8  | 165.8  | 167.3  | 167.3  | 167.3  | 167.3  | 168.8  | 168.8  | 168.8  |
| 27.5°  | 158.4  | 156.9  | 156.9  | 156.9  | 156.9  | 155.4  | 155.4  | 155.4  | 155.4  | 155.4  | 155.4  |
| 30°    | 154.0  | 152.5  | 151.0  | 149.5  | 149.5  | 148.0  | 146.6  | 146.6  | 146.6  | 146.6  | 146.6  |
| 32.5°  | 152.5  | 149.5  | 146.6  | 145.1  | 145.1  | 143.6  | 142.1  | 140.6  | 140.6  | 139.2  | 137.7  |
| 35°    | 136.2  | 134.7  | 134.7  | 133.2  | 131.8  | 130.3  | 128.8  | 128.8  | 128.8  | 127.3  | 127.3  |
| 37.5°  | 118.4  | 119.9  | 119.9  | 119.9  | 121.4  | 121.4  | 121.4  | 121.4  | 122.9  | 122.9  | 122.9  |
| 40°    | 111.0  | 111.0  | 111.0  | 112.5  | 114.0  | 114.0  | 115.5  | 115.5  | 117.0  | 117.0  | 117.0  |
| 42.5°  | 105.1  | 103.6  | 103.6  | 105.1  | 105.1  | 106.6  | 106.6  | 108.1  | 109.6  | 109.6  | 111.0  |
| 45°    | 102.2  | 100.7  | 100.7  | 100.7  | 100.7  | 99.2   | 99.2   | 100.7  | 102.2  | 103.6  | 105.1  |
| 47.5°  | 96.2   | 96.2   | 94.7   | 94.7   | 94.7   | 94.7   | 94.7   | 94.7   | 96.2   | 96.2   | 96.2   |
| 50°    | 93.3   | 93.3   | 91.8   | 91.8   | 91.8   | 91.8   | 91.8   | 91.8   | 91.8   | 91.8   | 91.8   |
| 52.5°  | 90.3   | 88.8   | 88.8   | 88.8   | 88.8   | 87.3   | 87.3   | 87.3   | 87.3   | 87.3   | 87.3   |
| 55°    | 85.9   | 84.4   | 84.4   | 84.4   | 84.4   | 84.4   | 84.4   | 84.4   | 85.9   | 85.9   | 85.9   |
| 57.5°  | 81.4   | 79.9   | 79.9   | 79.9   | 81.4   | 81.4   | 81.4   | 81.4   | 82.9   | 82.9   | 82.9   |
| 60°    | 77.0   | 77.0   | 77.0   | 77.0   | 77.0   | 77.0   | 77.0   | 78.5   | 78.5   | 79.9   | 79.9   |
| 62.5°  | 72.5   | 72.5   | 72.5   | 72.5   | 74.0   | 74.0   | 74.0   | 74.0   | 75.5   | 75.5   | 75.5   |
| 65°    | 68.1   | 68.1   | 68.1   | 68.1   | 69.6   | 69.6   | 69.6   | 69.6   | 69.6   | 69.6   | 69.6   |
| 67.5°  | 63.7   | 63.7   | 63.7   | 63.7   | 63.7   | 63.7   | 63.7   | 65.1   | 65.1   | 66.6   | 66.6   |
| 70°    | 57.7   | 56.3   | 56.3   | 57.7   | 57.7   | 59.2   | 59.2   | 60.7   | 60.7   | 62.2   | 62.2   |
| 72.5°  | 51.8   | 51.8   | 51.8   | 51.8   | 51.8   | 51.8   | 51.8   | 53.3   | 54.8   | 54.8   | 56.3   |
| 75°    | 45.9   | 45.9   | 45.9   | 45.9   | 47.4   | 47.4   | 47.4   | 48.9   | 48.9   | 50.3   | 50.3   |
| 77.5°  | 41.5   | 40.0   | 40.0   | 40.0   | 41.5   | 41.5   | 41.5   | 42.9   | 42.9   | 44.4   | 44.4   |
| 80°    | 34.1   | 34.1   | 34.1   | 34.1   | 35.5   | 35.5   | 35.5   | 35.5   | 37.0   | 37.0   | 37.0   |
| 82.5°  | 28.1   | 28.1   | 28.1   | 28.1   | 28.1   | 28.1   | 28.1   | 28.1   | 29.6   | 29.6   | 29.6   |
| 85°    | 20.7   | 20.7   | 20.7   | 20.7   | 22.2   | 22.2   | 22.2   | 22.2   | 22.2   | 22.2   | 22.2   |
| 87.5°  | 13.3   | 13.3   | 13.3   | 13.3   | 13.3   | 13.3   | 13.3   | 13.3   | 14.8   | 14.8   | 14.8   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140°   | 142.5° | 145°   | 147.5° | 150°   | 152.5° | 155°   | 157.5° | 160°   | 162.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 |
| 2.5°   | 941.6  | 941.6  | 941.6  | 941.6  | 944.5  | 946.0  | 949.0  | 950.4  | 949.0  | 947.5  | 944.5  |
| 5°     | 792.0  | 793.5  | 793.5  | 795.0  | 795.0  | 795.0  | 795.0  | 795.0  | 798.0  | 800.9  | 803.9  |
| 7.5°   | 626.2  | 627.7  | 629.2  | 630.7  | 630.7  | 630.7  | 629.2  | 629.2  | 630.7  | 630.7  | 632.2  |
| 10°    | 479.7  | 485.6  | 490.0  | 494.5  | 491.5  | 487.1  | 484.1  | 479.7  | 479.7  | 479.7  | 478.2  |
| 12.5°  | 362.7  | 364.2  | 367.2  | 368.6  | 367.2  | 367.2  | 365.7  | 364.2  | 365.7  | 368.6  | 370.1  |
| 15°    | 287.2  | 287.2  | 288.7  | 288.7  | 290.2  | 291.6  | 291.6  | 293.1  | 296.1  | 297.6  | 300.5  |
| 17.5°  | 238.4  | 239.8  | 239.8  | 241.3  | 241.3  | 242.8  | 242.8  | 242.8  | 245.8  | 248.7  | 253.2  |
| 20°    | 214.7  | 214.7  | 214.7  | 214.7  | 214.7  | 213.2  | 213.2  | 211.7  | 213.2  | 216.1  | 217.6  |
| 22.5°  | 192.5  | 193.9  | 193.9  | 193.9  | 192.5  | 191.0  | 188.0  | 186.5  | 186.5  | 188.0  | 188.0  |
| 25°    | 168.8  | 167.3  | 167.3  | 165.8  | 165.8  | 167.3  | 167.3  | 167.3  | 168.8  | 168.8  | 170.3  |
| 27.5°  | 155.4  | 154.0  | 154.0  | 152.5  | 152.5  | 154.0  | 154.0  | 154.0  | 154.0  | 154.0  | 154.0  |
| 30°    | 145.1  | 145.1  | 143.6  | 142.1  | 143.6  | 143.6  | 145.1  | 145.1  | 146.6  | 146.6  | 148.0  |
| 32.5°  | 137.7  | 136.2  | 136.2  | 134.7  | 136.2  | 136.2  | 137.7  | 137.7  | 139.2  | 140.6  | 140.6  |
| 35°    | 127.3  | 127.3  | 127.3  | 127.3  | 127.3  | 127.3  | 125.8  | 125.8  | 125.8  | 125.8  | 125.8  |
| 37.5°  | 121.4  | 121.4  | 119.9  | 118.4  | 118.4  | 118.4  | 118.4  | 118.4  | 117.0  | 115.5  | 114.0  |
| 40°    | 117.0  | 115.5  | 115.5  | 114.0  | 112.5  | 112.5  | 111.0  | 109.6  | 109.6  | 108.1  | 108.1  |
| 42.5°  | 111.0  | 109.6  | 109.6  | 108.1  | 106.6  | 106.6  | 105.1  | 103.6  | 103.6  | 103.6  | 102.2  |
| 45°    | 103.6  | 103.6  | 102.2  | 100.7  | 100.7  | 100.7  | 99.2   | 99.2   | 99.2   | 99.2   | 97.7   |
| 47.5°  | 96.2   | 96.2   | 94.7   | 94.7   | 94.7   | 94.7   | 93.3   | 93.3   | 93.3   | 93.3   | 93.3   |
| 50°    | 91.8   | 91.8   | 91.8   | 91.8   | 91.8   | 91.8   | 90.3   | 90.3   | 90.3   | 90.3   | 90.3   |
| 52.5°  | 87.3   | 87.3   | 87.3   | 87.3   | 87.3   | 87.3   | 87.3   | 87.3   | 87.3   | 87.3   | 87.3   |
| 55°    | 85.9   | 85.9   | 85.9   | 85.9   | 85.9   | 85.9   | 84.4   | 84.4   | 84.4   | 85.9   | 85.9   |
| 57.5°  | 82.9   | 82.9   | 81.4   | 81.4   | 81.4   | 81.4   | 81.4   | 81.4   | 81.4   | 81.4   | 81.4   |
| 60°    | 79.9   | 79.9   | 79.9   | 79.9   | 79.9   | 79.9   | 79.9   | 79.9   | 79.9   | 79.9   | 79.9   |
| 62.5°  | 75.5   | 75.5   | 75.5   | 75.5   | 75.5   | 77.0   | 77.0   | 77.0   | 77.0   | 77.0   | 75.5   |
| 65°    | 69.6   | 71.1   | 71.1   | 71.1   | 71.1   | 71.1   | 71.1   | 71.1   | 71.1   | 71.1   | 71.1   |
| 67.5°  | 66.6   | 66.6   | 66.6   | 66.6   | 66.6   | 66.6   | 66.6   | 66.6   | 66.6   | 66.6   | 66.6   |
| 70°    | 62.2   | 62.2   | 60.7   | 60.7   | 60.7   | 62.2   | 62.2   | 62.2   | 62.2   | 62.2   | 62.2   |
| 72.5°  | 56.3   | 56.3   | 56.3   | 56.3   | 56.3   | 56.3   | 56.3   | 56.3   | 56.3   | 57.7   | 57.7   |
| 75°    | 50.3   | 50.3   | 50.3   | 50.3   | 50.3   | 50.3   | 50.3   | 50.3   | 50.3   | 50.3   | 50.3   |
| 77.5°  | 44.4   | 44.4   | 42.9   | 42.9   | 42.9   | 44.4   | 44.4   | 44.4   | 44.4   | 45.9   | 45.9   |
| 80°    | 37.0   | 37.0   | 37.0   | 37.0   | 37.0   | 37.0   | 37.0   | 37.0   | 37.0   | 38.5   | 38.5   |
| 82.5°  | 29.6   | 29.6   | 29.6   | 29.6   | 29.6   | 29.6   | 29.6   | 29.6   | 29.6   | 31.1   | 31.1   |
| 85°    | 22.2   | 23.7   | 23.7   | 23.7   | 23.7   | 23.7   | 23.7   | 23.7   | 23.7   | 25.2   | 25.2   |
| 87.5°  | 14.8   | 14.8   | 14.8   | 14.8   | 14.8   | 14.8   | 13.3   | 13.3   | 13.3   | 13.3   | 11.8   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 165°   | 167.5° | 170°   | 172.5° | 175°   | 177.5° | 180°   | 182.5° | 185°   | 187.5° | 190°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 |
| 2.5°   | 943.0  | 944.5  | 946.0  | 946.0  | 947.5  | 949.0  | 949.0  | 954.9  | 960.8  | 963.8  | 966.7  |
| 5°     | 806.8  | 805.4  | 805.4  | 803.9  | 802.4  | 806.8  | 811.3  | 820.2  | 829.1  | 830.5  | 833.5  |
| 7.5°   | 632.2  | 633.6  | 635.1  | 635.1  | 636.6  | 632.2  | 626.2  | 627.7  | 629.2  | 636.6  | 642.5  |
| 10°    | 478.2  | 479.7  | 481.1  | 481.1  | 482.6  | 481.1  | 478.2  | 482.6  | 487.1  | 493.0  | 500.4  |
| 12.5°  | 371.6  | 376.0  | 380.5  | 383.4  | 387.9  | 390.8  | 392.3  | 398.2  | 402.7  | 410.1  | 417.5  |
| 15°    | 303.5  | 306.5  | 309.4  | 312.4  | 315.3  | 318.3  | 321.3  | 327.2  | 333.1  | 342.0  | 350.9  |
| 17.5°  | 256.1  | 256.1  | 257.6  | 257.6  | 257.6  | 260.6  | 263.5  | 266.5  | 268.0  | 276.8  | 285.7  |
| 20°    | 219.1  | 217.6  | 216.1  | 214.7  | 213.2  | 216.1  | 217.6  | 219.1  | 220.6  | 226.5  | 230.9  |
| 22.5°  | 188.0  | 188.0  | 189.5  | 189.5  | 189.5  | 188.0  | 185.1  | 186.5  | 186.5  | 189.5  | 193.9  |
| 25°    | 170.3  | 170.3  | 170.3  | 168.8  | 168.8  | 170.3  | 171.7  | 171.7  | 170.3  | 171.7  | 173.2  |
| 27.5°  | 154.0  | 155.4  | 155.4  | 156.9  | 156.9  | 158.4  | 158.4  | 158.4  | 158.4  | 159.9  | 161.4  |
| 30°    | 148.0  | 148.0  | 149.5  | 149.5  | 149.5  | 151.0  | 152.5  | 152.5  | 152.5  | 154.0  | 156.9  |
| 32.5°  | 142.1  | 143.6  | 145.1  | 146.6  | 148.0  | 149.5  | 149.5  | 151.0  | 151.0  | 152.5  | 154.0  |
| 35°    | 125.8  | 124.4  | 124.4  | 122.9  | 121.4  | 121.4  | 121.4  | 121.4  | 119.9  | 121.4  | 121.4  |
| 37.5°  | 112.5  | 112.5  | 112.5  | 111.0  | 111.0  | 112.5  | 112.5  | 112.5  | 112.5  | 114.0  | 114.0  |
| 40°    | 106.6  | 106.6  | 106.6  | 106.6  | 106.6  | 106.6  | 106.6  | 108.1  | 108.1  | 109.6  | 111.0  |
| 42.5°  | 102.2  | 102.2  | 102.2  | 102.2  | 102.2  | 103.6  | 103.6  | 103.6  | 103.6  | 105.1  | 105.1  |
| 45°    | 97.7   | 97.7   | 97.7   | 97.7   | 97.7   | 97.7   | 97.7   | 99.2   | 99.2   | 100.7  | 102.2  |
| 47.5°  | 93.3   | 93.3   | 93.3   | 93.3   | 93.3   | 94.7   | 96.2   | 96.2   | 96.2   | 97.7   | 97.7   |
| 50°    | 90.3   | 90.3   | 90.3   | 90.3   | 90.3   | 91.8   | 91.8   | 93.3   | 93.3   | 94.7   | 96.2   |
| 52.5°  | 87.3   | 87.3   | 87.3   | 87.3   | 87.3   | 88.8   | 88.8   | 90.3   | 90.3   | 91.8   | 93.3   |
| 55°    | 85.9   | 85.9   | 85.9   | 84.4   | 84.4   | 85.9   | 85.9   | 87.3   | 87.3   | 88.8   | 88.8   |
| 57.5°  | 81.4   | 81.4   | 81.4   | 81.4   | 81.4   | 81.4   | 81.4   | 82.9   | 82.9   | 84.4   | 85.9   |
| 60°    | 79.9   | 79.9   | 78.5   | 78.5   | 77.0   | 78.5   | 78.5   | 79.9   | 79.9   | 81.4   | 81.4   |
| 62.5°  | 75.5   | 75.5   | 75.5   | 74.0   | 74.0   | 75.5   | 75.5   | 75.5   | 75.5   | 77.0   | 78.5   |
| 65°    | 71.1   | 71.1   | 71.1   | 69.6   | 69.6   | 71.1   | 71.1   | 71.1   | 71.1   | 72.5   | 74.0   |
| 67.5°  | 66.6   | 66.6   | 66.6   | 65.1   | 65.1   | 65.1   | 65.1   | 66.6   | 66.6   | 68.1   | 69.6   |
| 70°    | 62.2   | 62.2   | 62.2   | 60.7   | 60.7   | 60.7   | 59.2   | 60.7   | 62.2   | 63.7   | 63.7   |
| 72.5°  | 57.7   | 57.7   | 57.7   | 56.3   | 56.3   | 56.3   | 54.8   | 56.3   | 56.3   | 57.7   | 57.7   |
| 75°    | 50.3   | 50.3   | 50.3   | 50.3   | 50.3   | 50.3   | 48.9   | 48.9   | 48.9   | 50.3   | 50.3   |
| 77.5°  | 45.9   | 45.9   | 45.9   | 44.4   | 44.4   | 44.4   | 42.9   | 42.9   | 42.9   | 44.4   | 44.4   |
| 80°    | 38.5   | 38.5   | 38.5   | 37.0   | 37.0   | 37.0   | 35.5   | 35.5   | 35.5   | 37.0   | 37.0   |
| 82.5°  | 31.1   | 31.1   | 31.1   | 29.6   | 29.6   | 29.6   | 28.1   | 28.1   | 28.1   | 29.6   | 29.6   |
| 85°    | 25.2   | 25.2   | 25.2   | 25.2   | 25.2   | 25.2   | 23.7   | 23.7   | 23.7   | 25.2   | 26.6   |
| 87.5°  | 11.8   | 11.8   | 13.3   | 13.3   | 13.3   | 13.3   | 11.8   | 11.8   | 10.4   | 10.4   | 11.8   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° | 190° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195°   | 197.5° | 200°   | 202.5° | 205°   | 207.5° | 210°   | 212.5° | 215°   | 217.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 |
| 2.5°   | 969.7  | 972.7  | 980.1  | 986.0  | 993.4  | 999.3  | 1003.7 | 1009.7 | 1014.1 | 1018.5 | 1021.5 |
| 5°     | 835.0  | 836.5  | 843.9  | 851.3  | 857.2  | 864.6  | 874.9  | 885.3  | 895.7  | 906.0  | 913.4  |
| 7.5°   | 649.9  | 655.8  | 664.7  | 675.1  | 684.0  | 692.8  | 703.2  | 715.1  | 725.4  | 735.8  | 746.1  |
| 10°    | 506.3  | 512.2  | 521.1  | 530.0  | 537.4  | 546.3  | 558.1  | 570.0  | 581.8  | 593.7  | 605.5  |
| 12.5°  | 424.9  | 432.3  | 442.7  | 453.0  | 461.9  | 472.3  | 487.1  | 500.4  | 515.2  | 528.5  | 543.3  |
| 15°    | 358.3  | 367.2  | 380.5  | 395.3  | 408.6  | 421.9  | 436.7  | 451.5  | 464.9  | 479.7  | 494.5  |
| 17.5°  | 294.6  | 303.5  | 315.3  | 328.7  | 340.5  | 352.3  | 370.1  | 386.4  | 404.2  | 420.4  | 436.7  |
| 20°    | 236.9  | 241.3  | 253.2  | 265.0  | 276.8  | 288.7  | 302.0  | 315.3  | 328.7  | 342.0  | 362.7  |
| 22.5°  | 196.9  | 199.9  | 205.8  | 210.2  | 216.1  | 220.6  | 233.9  | 247.2  | 259.1  | 272.4  | 291.6  |
| 25°    | 173.2  | 174.7  | 179.1  | 182.1  | 186.5  | 189.5  | 198.4  | 205.8  | 214.7  | 222.1  | 239.8  |
| 27.5°  | 161.4  | 162.8  | 164.3  | 165.8  | 167.3  | 168.8  | 174.7  | 180.6  | 185.1  | 191.0  | 207.3  |
| 30°    | 158.4  | 159.9  | 164.3  | 167.3  | 171.7  | 174.7  | 177.7  | 180.6  | 183.6  | 186.5  | 196.9  |
| 32.5°  | 155.4  | 156.9  | 156.9  | 155.4  | 155.4  | 154.0  | 156.9  | 158.4  | 161.4  | 162.8  | 171.7  |
| 35°    | 122.9  | 122.9  | 124.4  | 125.8  | 127.3  | 128.8  | 133.2  | 136.2  | 140.6  | 143.6  | 151.0  |
| 37.5°  | 115.5  | 115.5  | 117.0  | 119.9  | 121.4  | 122.9  | 125.8  | 128.8  | 131.8  | 134.7  | 142.1  |
| 40°    | 111.0  | 112.5  | 114.0  | 115.5  | 117.0  | 118.4  | 121.4  | 122.9  | 125.8  | 127.3  | 133.2  |
| 42.5°  | 106.6  | 106.6  | 108.1  | 111.0  | 112.5  | 114.0  | 117.0  | 118.4  | 121.4  | 122.9  | 128.8  |
| 45°    | 103.6  | 105.1  | 106.6  | 108.1  | 108.1  | 109.6  | 112.5  | 115.5  | 117.0  | 119.9  | 125.8  |
| 47.5°  | 99.2   | 99.2   | 102.2  | 103.6  | 106.6  | 108.1  | 111.0  | 112.5  | 115.5  | 117.0  | 122.9  |
| 50°    | 96.2   | 97.7   | 100.7  | 102.2  | 105.1  | 106.6  | 111.0  | 114.0  | 118.4  | 121.4  | 124.4  |
| 52.5°  | 93.3   | 94.7   | 97.7   | 99.2   | 102.2  | 103.6  | 109.6  | 115.5  | 119.9  | 125.8  | 125.8  |
| 55°    | 90.3   | 90.3   | 93.3   | 97.7   | 100.7  | 103.6  | 106.6  | 111.0  | 114.0  | 117.0  | 117.0  |
| 57.5°  | 85.9   | 87.3   | 90.3   | 94.7   | 97.7   | 100.7  | 103.6  | 106.6  | 108.1  | 111.0  | 109.6  |
| 60°    | 82.9   | 82.9   | 87.3   | 91.8   | 96.2   | 100.7  | 100.7  | 100.7  | 99.2   | 99.2   | 99.2   |
| 62.5°  | 78.5   | 79.9   | 85.9   | 93.3   | 99.2   | 105.1  | 100.7  | 96.2   | 91.8   | 87.3   | 88.8   |
| 65°    | 75.5   | 77.0   | 79.9   | 84.4   | 87.3   | 90.3   | 87.3   | 85.9   | 82.9   | 79.9   | 81.4   |
| 67.5°  | 69.6   | 71.1   | 72.5   | 72.5   | 74.0   | 74.0   | 74.0   | 74.0   | 74.0   | 74.0   | 75.5   |
| 70°    | 65.1   | 65.1   | 65.1   | 66.6   | 66.6   | 66.6   | 66.6   | 66.6   | 66.6   | 66.6   | 68.1   |
| 72.5°  | 59.2   | 59.2   | 59.2   | 59.2   | 59.2   | 59.2   | 59.2   | 59.2   | 59.2   | 59.2   | 60.7   |
| 75°    | 51.8   | 51.8   | 51.8   | 51.8   | 51.8   | 51.8   | 51.8   | 51.8   | 51.8   | 51.8   | 53.3   |
| 77.5°  | 45.9   | 45.9   | 45.9   | 45.9   | 45.9   | 45.9   | 45.9   | 45.9   | 44.4   | 44.4   | 45.9   |
| 80°    | 38.5   | 38.5   | 38.5   | 38.5   | 37.0   | 37.0   | 37.0   | 37.0   | 37.0   | 37.0   | 38.5   |
| 82.5°  | 31.1   | 31.1   | 31.1   | 31.1   | 29.6   | 29.6   | 29.6   | 29.6   | 28.1   | 28.1   | 29.6   |
| 85°    | 28.1   | 29.6   | 29.6   | 31.1   | 31.1   | 31.1   | 29.6   | 28.1   | 26.6   | 25.2   | 25.2   |
| 87.5°  | 11.8   | 11.8   | 11.8   | 11.8   | 10.4   | 10.4   | 10.4   | 10.4   | 10.4   | 10.4   | 10.4   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° | 217.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 220°   | 222.5° | 225°   | 227.5° | 230°   | 232.5° | 235°   | 237.5° | 240°   | 242.5° | 245°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 |
| 2.5°   | 1025.9 | 1028.9 | 1031.9 | 1036.3 | 1042.2 | 1046.7 | 1051.1 | 1060.0 | 1070.4 | 1079.2 | 1088.1 |
| 5°     | 920.8  | 928.2  | 935.6  | 944.5  | 953.4  | 960.8  | 969.7  | 987.5  | 1005.2 | 1021.5 | 1039.3 |
| 7.5°   | 755.0  | 765.4  | 774.3  | 789.1  | 802.4  | 817.2  | 830.5  | 852.7  | 873.5  | 895.7  | 916.4  |
| 10°    | 617.3  | 629.2  | 641.0  | 660.3  | 681.0  | 700.3  | 719.5  | 737.3  | 756.5  | 774.3  | 792.0  |
| 12.5°  | 558.1  | 571.5  | 586.3  | 598.1  | 611.4  | 623.3  | 635.1  | 655.8  | 676.6  | 697.3  | 718.0  |
| 15°    | 509.3  | 524.1  | 538.9  | 553.7  | 567.0  | 581.8  | 595.1  | 612.9  | 632.2  | 649.9  | 667.7  |
| 17.5°  | 453.0  | 467.8  | 484.1  | 500.4  | 516.7  | 533.0  | 549.2  | 574.4  | 599.6  | 623.3  | 648.4  |
| 20°    | 382.0  | 402.7  | 421.9  | 444.1  | 466.3  | 488.5  | 510.8  | 537.4  | 564.1  | 589.2  | 615.9  |
| 22.5°  | 310.9  | 330.1  | 349.4  | 376.0  | 402.7  | 427.8  | 454.5  | 490.0  | 524.1  | 559.6  | 593.7  |
| 25°    | 259.1  | 276.8  | 294.6  | 324.2  | 352.3  | 382.0  | 410.1  | 453.0  | 494.5  | 537.4  | 578.9  |
| 27.5°  | 223.5  | 239.8  | 256.1  | 287.2  | 318.3  | 347.9  | 379.0  | 426.4  | 472.3  | 519.6  | 565.5  |
| 30°    | 207.3  | 217.6  | 228.0  | 257.6  | 287.2  | 315.3  | 344.9  | 390.8  | 436.7  | 482.6  | 528.5  |
| 32.5°  | 180.6  | 189.5  | 198.4  | 225.0  | 251.7  | 276.8  | 303.5  | 350.9  | 396.8  | 444.1  | 490.0  |
| 35°    | 159.9  | 167.3  | 174.7  | 199.9  | 223.5  | 248.7  | 272.4  | 319.8  | 367.2  | 414.5  | 461.9  |
| 37.5°  | 148.0  | 155.4  | 161.4  | 183.6  | 207.3  | 229.5  | 251.7  | 299.1  | 344.9  | 392.3  | 438.2  |
| 40°    | 139.2  | 143.6  | 149.5  | 171.7  | 192.5  | 214.7  | 235.4  | 278.3  | 322.7  | 365.7  | 408.6  |
| 42.5°  | 133.2  | 139.2  | 143.6  | 162.8  | 183.6  | 202.8  | 222.1  | 263.5  | 305.0  | 344.9  | 386.4  |
| 45°    | 131.8  | 137.7  | 143.6  | 159.9  | 176.2  | 191.0  | 207.3  | 247.2  | 287.2  | 327.2  | 367.2  |
| 47.5°  | 128.8  | 133.2  | 139.2  | 152.5  | 164.3  | 177.7  | 189.5  | 229.5  | 269.4  | 307.9  | 347.9  |
| 50°    | 127.3  | 128.8  | 131.8  | 143.6  | 155.4  | 167.3  | 179.1  | 219.1  | 259.1  | 299.1  | 339.0  |
| 52.5°  | 125.8  | 125.8  | 125.8  | 136.2  | 146.6  | 155.4  | 165.8  | 205.8  | 247.2  | 287.2  | 327.2  |
| 55°    | 117.0  | 115.5  | 115.5  | 125.8  | 134.7  | 145.1  | 154.0  | 193.9  | 233.9  | 272.4  | 312.4  |
| 57.5°  | 108.1  | 106.6  | 105.1  | 114.0  | 122.9  | 131.8  | 140.6  | 180.6  | 222.1  | 262.0  | 302.0  |
| 60°    | 99.2   | 97.7   | 97.7   | 106.6  | 114.0  | 122.9  | 130.3  | 171.7  | 211.7  | 253.2  | 293.1  |
| 62.5°  | 88.8   | 90.3   | 90.3   | 97.7   | 106.6  | 114.0  | 121.4  | 162.8  | 205.8  | 247.2  | 288.7  |
| 65°    | 81.4   | 82.9   | 82.9   | 91.8   | 100.7  | 109.6  | 118.4  | 158.4  | 199.9  | 239.8  | 279.8  |
| 67.5°  | 75.5   | 77.0   | 77.0   | 87.3   | 96.2   | 106.6  | 115.5  | 151.0  | 188.0  | 223.5  | 259.1  |
| 70°    | 69.6   | 69.6   | 71.1   | 81.4   | 91.8   | 102.2  | 112.5  | 143.6  | 174.7  | 204.3  | 235.4  |
| 72.5°  | 62.2   | 63.7   | 65.1   | 75.5   | 84.4   | 94.7   | 103.6  | 131.8  | 159.9  | 188.0  | 216.1  |
| 75°    | 54.8   | 56.3   | 57.7   | 66.6   | 75.5   | 84.4   | 93.3   | 119.9  | 145.1  | 171.7  | 196.9  |
| 77.5°  | 48.9   | 50.3   | 51.8   | 59.2   | 66.6   | 74.0   | 81.4   | 100.7  | 121.4  | 140.6  | 159.9  |
| 80°    | 40.0   | 40.0   | 41.5   | 47.4   | 53.3   | 57.7   | 63.7   | 77.0   | 90.3   | 102.2  | 115.5  |
| 82.5°  | 29.6   | 31.1   | 31.1   | 35.5   | 38.5   | 42.9   | 45.9   | 53.3   | 59.2   | 66.6   | 72.5   |
| 85°    | 25.2   | 23.7   | 23.7   | 26.6   | 28.1   | 31.1   | 32.6   | 37.0   | 40.0   | 44.4   | 47.4   |
| 87.5°  | 10.4   | 8.9    | 8.9    | 10.4   | 13.3   | 14.8   | 16.3   | 16.3   | 17.8   | 17.8   | 17.8   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° | 245° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°   | 252.5° | 255°   | 257.5° | 260°   | 262.5° | 265°   | 267.5° | 270°   | 272.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 |
| 2.5°   | 1092.6 | 1095.5 | 1100.0 | 1102.9 | 1110.3 | 1116.3 | 1123.7 | 1129.6 | 1134.0 | 1141.4 | 1138.5 |
| 5°     | 1052.6 | 1065.9 | 1079.2 | 1092.6 | 1102.9 | 1113.3 | 1122.2 | 1132.5 | 1144.4 | 1166.6 | 1172.5 |
| 7.5°   | 934.2  | 951.9  | 968.2  | 986.0  | 1006.7 | 1027.4 | 1048.2 | 1068.9 | 1088.1 | 1116.3 | 1134.0 |
| 10°    | 817.2  | 842.4  | 866.1  | 891.2  | 910.5  | 929.7  | 947.5  | 966.7  | 993.4  | 1021.5 | 1054.1 |
| 12.5°  | 743.2  | 768.4  | 793.5  | 818.7  | 846.8  | 873.5  | 901.6  | 928.2  | 953.4  | 975.6  | 1012.6 |
| 15°    | 694.3  | 722.5  | 749.1  | 775.8  | 809.8  | 842.4  | 876.4  | 909.0  | 946.0  | 975.6  | 1000.8 |
| 17.5°  | 682.5  | 716.5  | 749.1  | 783.2  | 818.7  | 854.2  | 889.7  | 925.3  | 962.3  | 1006.7 | 1039.3 |
| 20°    | 661.8  | 707.7  | 753.5  | 799.4  | 845.3  | 889.7  | 935.6  | 980.1  | 1028.9 | 1082.2 | 1097.0 |
| 22.5°  | 649.9  | 704.7  | 760.9  | 815.7  | 877.9  | 941.6  | 1003.7 | 1065.9 | 1117.7 | 1157.7 | 1202.1 |
| 25°    | 648.4  | 716.5  | 786.1  | 854.2  | 932.7  | 1009.7 | 1088.1 | 1165.1 | 1231.7 | 1271.7 | 1307.2 |
| 27.5°  | 647.0  | 729.9  | 811.3  | 892.7  | 988.9  | 1083.7 | 1179.9 | 1274.7 | 1336.8 | 1394.6 | 1424.2 |
| 30°    | 629.2  | 728.4  | 829.1  | 928.2  | 1036.3 | 1144.4 | 1252.5 | 1360.5 | 1424.2 | 1464.2 | 1479.0 |
| 32.5°  | 607.0  | 723.9  | 840.9  | 957.8  | 1080.7 | 1203.6 | 1325.0 | 1447.9 | 1498.2 | 1532.3 | 1520.4 |
| 35°    | 589.2  | 718.0  | 845.3  | 972.7  | 1102.9 | 1234.7 | 1365.0 | 1495.3 | 1567.8 | 1615.2 | 1595.9 |
| 37.5°  | 572.9  | 707.7  | 842.4  | 977.1  | 1129.6 | 1282.1 | 1434.6 | 1587.0 | 1656.6 | 1707.0 | 1684.7 |
| 40°    | 553.7  | 697.3  | 842.4  | 986.0  | 1160.7 | 1333.9 | 1508.6 | 1681.8 | 1772.1 | 1815.0 | 1781.0 |
| 42.5°  | 537.4  | 686.9  | 837.9  | 987.5  | 1174.0 | 1360.5 | 1547.1 | 1733.6 | 1834.3 | 1895.0 | 1852.0 |
| 45°    | 516.7  | 666.2  | 814.2  | 963.8  | 1169.6 | 1375.3 | 1579.6 | 1785.4 | 1902.4 | 1949.7 | 1890.5 |
| 47.5°  | 494.5  | 642.5  | 789.1  | 935.6  | 1154.7 | 1373.9 | 1593.0 | 1812.1 | 1920.1 | 1976.4 | 1921.6 |
| 50°    | 487.1  | 635.1  | 781.7  | 929.7  | 1166.6 | 1404.9 | 1641.8 | 1878.7 | 1957.2 | 2003.0 | 1930.5 |
| 52.5°  | 485.6  | 642.5  | 800.9  | 957.8  | 1196.2 | 1433.1 | 1671.4 | 1908.3 | 1972.0 | 2020.8 | 1955.7 |
| 55°    | 481.1  | 651.4  | 820.2  | 988.9  | 1237.7 | 1487.8 | 1736.6 | 1985.3 | 2048.9 | 2084.5 | 2035.6 |
| 57.5°  | 485.6  | 669.2  | 851.3  | 1034.8 | 1290.9 | 1547.1 | 1803.2 | 2059.3 | 2136.3 | 2161.5 | 2151.1 |
| 60°    | 488.5  | 684.0  | 877.9  | 1073.3 | 1323.5 | 1573.7 | 1823.9 | 2074.1 | 2154.0 | 2216.2 | 2228.1 |
| 62.5°  | 481.1  | 673.6  | 864.6  | 1057.0 | 1283.5 | 1510.1 | 1736.6 | 1963.1 | 2094.8 | 2186.6 | 2239.9 |
| 65°    | 458.9  | 636.6  | 815.7  | 993.4  | 1202.1 | 1412.3 | 1621.1 | 1829.8 | 1969.0 | 2105.2 | 2148.1 |
| 67.5°  | 410.1  | 561.1  | 712.1  | 863.1  | 1045.2 | 1227.3 | 1407.9 | 1590.0 | 1764.7 | 1896.5 | 1955.7 |
| 70°    | 355.3  | 473.7  | 593.7  | 712.1  | 877.9  | 1043.7 | 1209.5 | 1375.3 | 1529.3 | 1674.4 | 1730.6 |
| 72.5°  | 309.4  | 401.2  | 494.5  | 586.3  | 704.7  | 821.6  | 940.1  | 1057.0 | 1239.1 | 1384.2 | 1439.0 |
| 75°    | 263.5  | 330.1  | 395.3  | 461.9  | 543.3  | 624.7  | 704.7  | 786.1  | 914.9  | 1045.2 | 1100.0 |
| 77.5°  | 202.8  | 247.2  | 290.2  | 333.1  | 389.4  | 444.1  | 500.4  | 555.2  | 645.5  | 743.2  | 771.3  |
| 80°    | 140.6  | 165.8  | 189.5  | 214.7  | 259.1  | 303.5  | 347.9  | 392.3  | 451.5  | 506.3  | 549.2  |
| 82.5°  | 87.3   | 103.6  | 118.4  | 133.2  | 168.8  | 204.3  | 238.4  | 273.9  | 297.6  | 300.5  | 343.5  |
| 85°    | 56.3   | 66.6   | 75.5   | 84.4   | 105.1  | 127.3  | 148.0  | 168.8  | 151.0  | 140.6  | 167.3  |
| 87.5°  | 22.2   | 28.1   | 32.6   | 37.0   | 35.5   | 34.1   | 32.6   | 31.1   | 26.6   | 23.7   | 29.6   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° | 272.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 275°   | 277.5° | 280°   | 282.5° | 285°   | 287.5° | 290°   | 292.5° | 295°   | 297.5° | 300°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 |
| 2.5°   | 1141.4 | 1145.9 | 1150.3 | 1153.3 | 1157.7 | 1159.2 | 1160.7 | 1160.7 | 1162.2 | 1163.6 | 1166.6 |
| 5°     | 1196.2 | 1205.1 | 1214.0 | 1221.4 | 1230.3 | 1237.7 | 1243.6 | 1251.0 | 1256.9 | 1256.9 | 1255.4 |
| 7.5°   | 1150.3 | 1172.5 | 1194.7 | 1216.9 | 1239.1 | 1255.4 | 1270.2 | 1286.5 | 1301.3 | 1304.3 | 1307.2 |
| 10°    | 1089.6 | 1113.3 | 1135.5 | 1159.2 | 1181.4 | 1206.6 | 1230.3 | 1253.9 | 1279.1 | 1283.5 | 1289.5 |
| 12.5°  | 1033.4 | 1061.5 | 1089.6 | 1116.3 | 1144.4 | 1162.2 | 1179.9 | 1196.2 | 1214.0 | 1225.8 | 1237.7 |
| 15°    | 1031.9 | 1055.6 | 1079.2 | 1101.5 | 1125.1 | 1135.5 | 1145.9 | 1154.7 | 1165.1 | 1165.1 | 1166.6 |
| 17.5°  | 1065.9 | 1080.7 | 1095.5 | 1108.9 | 1123.7 | 1125.1 | 1128.1 | 1129.6 | 1131.1 | 1126.6 | 1122.2 |
| 20°    | 1132.5 | 1138.5 | 1144.4 | 1150.3 | 1156.2 | 1145.9 | 1137.0 | 1126.6 | 1116.3 | 1104.4 | 1094.1 |
| 22.5°  | 1230.3 | 1216.9 | 1203.6 | 1190.3 | 1177.0 | 1159.2 | 1139.9 | 1122.2 | 1102.9 | 1088.1 | 1073.3 |
| 25°    | 1322.0 | 1305.8 | 1289.5 | 1273.2 | 1256.9 | 1218.4 | 1179.9 | 1139.9 | 1101.5 | 1085.2 | 1068.9 |
| 27.5°  | 1444.9 | 1419.7 | 1394.6 | 1369.4 | 1344.2 | 1292.4 | 1240.6 | 1188.8 | 1137.0 | 1108.9 | 1082.2 |
| 30°    | 1474.5 | 1446.4 | 1418.3 | 1388.7 | 1360.5 | 1310.2 | 1261.3 | 1211.0 | 1160.7 | 1128.1 | 1097.0 |
| 32.5°  | 1517.5 | 1484.9 | 1452.3 | 1419.7 | 1387.2 | 1338.3 | 1289.5 | 1239.1 | 1190.3 | 1160.7 | 1129.6 |
| 35°    | 1588.5 | 1551.5 | 1514.5 | 1476.0 | 1439.0 | 1388.7 | 1339.8 | 1289.5 | 1239.1 | 1205.1 | 1172.5 |
| 37.5°  | 1649.2 | 1606.3 | 1563.4 | 1520.4 | 1477.5 | 1433.1 | 1387.2 | 1342.8 | 1296.9 | 1262.8 | 1230.3 |
| 40°    | 1717.3 | 1669.9 | 1622.6 | 1576.7 | 1529.3 | 1487.8 | 1446.4 | 1403.5 | 1362.0 | 1335.4 | 1308.7 |
| 42.5°  | 1776.5 | 1718.8 | 1662.5 | 1606.3 | 1548.5 | 1520.4 | 1493.8 | 1465.6 | 1437.5 | 1424.2 | 1409.4 |
| 45°    | 1818.0 | 1764.7 | 1709.9 | 1656.6 | 1603.3 | 1582.6 | 1561.9 | 1541.1 | 1520.4 | 1533.7 | 1547.1 |
| 47.5°  | 1835.8 | 1792.8 | 1751.4 | 1709.9 | 1667.0 | 1674.4 | 1681.8 | 1687.7 | 1695.1 | 1712.9 | 1732.1 |
| 50°    | 1852.0 | 1828.4 | 1803.2 | 1779.5 | 1754.3 | 1782.5 | 1809.1 | 1837.2 | 1865.4 | 1902.4 | 1939.4 |
| 52.5°  | 1884.6 | 1871.3 | 1859.4 | 1846.1 | 1832.8 | 1881.6 | 1930.5 | 1979.4 | 2028.2 | 2069.7 | 2111.1 |
| 55°    | 1982.3 | 1972.0 | 1961.6 | 1949.7 | 1939.4 | 2009.0 | 2077.1 | 2146.6 | 2216.2 | 2259.2 | 2302.1 |
| 57.5°  | 2117.0 | 2111.1 | 2103.7 | 2097.8 | 2090.4 | 2158.5 | 2225.1 | 2291.7 | 2359.8 | 2401.3 | 2444.2 |
| 60°    | 2219.2 | 2220.7 | 2220.7 | 2222.2 | 2222.2 | 2274.0 | 2325.8 | 2379.1 | 2430.9 | 2466.4 | 2503.4 |
| 62.5°  | 2274.0 | 2271.0 | 2268.0 | 2265.1 | 2262.1 | 2305.1 | 2348.0 | 2390.9 | 2433.9 | 2460.5 | 2487.2 |
| 65°    | 2214.7 | 2231.0 | 2247.3 | 2263.6 | 2279.9 | 2285.8 | 2290.3 | 2296.2 | 2300.6 | 2316.9 | 2333.2 |
| 67.5°  | 2016.4 | 2048.9 | 2080.0 | 2112.6 | 2143.7 | 2121.5 | 2100.8 | 2078.5 | 2056.3 | 2060.8 | 2063.7 |
| 70°    | 1795.8 | 1832.8 | 1871.3 | 1908.3 | 1945.3 | 1893.5 | 1841.7 | 1788.4 | 1736.6 | 1718.8 | 1701.0 |
| 72.5°  | 1514.5 | 1547.1 | 1581.1 | 1613.7 | 1646.3 | 1582.6 | 1520.4 | 1456.8 | 1393.1 | 1362.0 | 1330.9 |
| 75°    | 1157.7 | 1196.2 | 1236.2 | 1274.7 | 1313.2 | 1242.1 | 1169.6 | 1098.5 | 1025.9 | 1005.2 | 986.0  |
| 77.5°  | 843.9  | 889.7  | 935.6  | 981.5  | 1027.4 | 963.8  | 900.1  | 835.0  | 771.3  | 759.5  | 747.6  |
| 80°    | 614.4  | 649.9  | 684.0  | 719.5  | 753.5  | 716.5  | 679.5  | 642.5  | 605.5  | 604.0  | 602.5  |
| 82.5°  | 414.5  | 445.6  | 475.2  | 506.3  | 535.9  | 521.1  | 507.8  | 493.0  | 478.2  | 493.0  | 509.3  |
| 85°    | 213.2  | 256.1  | 300.5  | 343.5  | 386.4  | 382.0  | 379.0  | 374.6  | 370.1  | 389.4  | 407.1  |
| 87.5°  | 42.9   | 79.9   | 117.0  | 152.5  | 189.5  | 180.6  | 171.7  | 161.4  | 152.5  | 158.4  | 162.8  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° | 300° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305°   | 307.5° | 310°   | 312.5° | 315°   | 317.5° | 320°   | 322.5° | 325°   | 327.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 |
| 2.5°   | 1168.1 | 1169.6 | 1169.6 | 1169.6 | 1169.6 | 1169.6 | 1166.6 | 1165.1 | 1162.2 | 1159.2 | 1154.7 |
| 5°     | 1255.4 | 1253.9 | 1248.0 | 1242.1 | 1234.7 | 1228.8 | 1224.3 | 1218.4 | 1214.0 | 1208.0 | 1199.2 |
| 7.5°   | 1310.2 | 1313.2 | 1302.8 | 1293.9 | 1283.5 | 1273.2 | 1262.8 | 1252.5 | 1242.1 | 1231.7 | 1211.0 |
| 10°    | 1293.9 | 1298.4 | 1292.4 | 1286.5 | 1279.1 | 1273.2 | 1261.3 | 1248.0 | 1236.2 | 1222.8 | 1197.7 |
| 12.5°  | 1248.0 | 1259.9 | 1256.9 | 1253.9 | 1251.0 | 1248.0 | 1240.6 | 1231.7 | 1224.3 | 1215.4 | 1187.3 |
| 15°    | 1166.6 | 1166.6 | 1168.1 | 1169.6 | 1169.6 | 1171.0 | 1172.5 | 1174.0 | 1175.5 | 1177.0 | 1160.7 |
| 17.5°  | 1117.7 | 1113.3 | 1113.3 | 1113.3 | 1113.3 | 1113.3 | 1119.2 | 1126.6 | 1132.5 | 1138.5 | 1134.0 |
| 20°    | 1082.2 | 1071.8 | 1070.4 | 1070.4 | 1068.9 | 1067.4 | 1077.8 | 1089.6 | 1100.0 | 1110.3 | 1116.3 |
| 22.5°  | 1058.5 | 1043.7 | 1042.2 | 1040.8 | 1039.3 | 1037.8 | 1051.1 | 1064.4 | 1077.8 | 1091.1 | 1111.8 |
| 25°    | 1052.6 | 1036.3 | 1037.8 | 1039.3 | 1039.3 | 1040.8 | 1051.1 | 1061.5 | 1071.8 | 1082.2 | 1117.7 |
| 27.5°  | 1054.1 | 1027.4 | 1028.9 | 1030.4 | 1030.4 | 1031.9 | 1048.2 | 1063.0 | 1079.2 | 1094.1 | 1138.5 |
| 30°    | 1064.4 | 1033.4 | 1030.4 | 1027.4 | 1024.5 | 1021.5 | 1043.7 | 1065.9 | 1088.1 | 1110.3 | 1144.4 |
| 32.5°  | 1100.0 | 1070.4 | 1063.0 | 1055.6 | 1048.2 | 1040.8 | 1067.4 | 1092.6 | 1119.2 | 1144.4 | 1172.5 |
| 35°    | 1138.5 | 1105.9 | 1102.9 | 1100.0 | 1095.5 | 1092.6 | 1116.3 | 1141.4 | 1165.1 | 1188.8 | 1214.0 |
| 37.5°  | 1196.2 | 1163.6 | 1160.7 | 1156.2 | 1153.3 | 1148.8 | 1175.5 | 1200.6 | 1227.3 | 1252.5 | 1274.7 |
| 40°    | 1282.1 | 1255.4 | 1253.9 | 1253.9 | 1252.5 | 1251.0 | 1271.7 | 1293.9 | 1314.6 | 1335.4 | 1350.2 |
| 42.5°  | 1396.1 | 1382.7 | 1387.2 | 1393.1 | 1397.5 | 1402.0 | 1418.3 | 1436.0 | 1452.3 | 1468.6 | 1464.2 |
| 45°    | 1560.4 | 1573.7 | 1575.2 | 1576.7 | 1578.2 | 1579.6 | 1584.1 | 1590.0 | 1594.4 | 1598.9 | 1581.1 |
| 47.5°  | 1749.9 | 1767.7 | 1776.5 | 1785.4 | 1792.8 | 1801.7 | 1795.8 | 1788.4 | 1782.5 | 1775.1 | 1730.6 |
| 50°    | 1974.9 | 2011.9 | 2010.4 | 2009.0 | 2006.0 | 2004.5 | 1992.7 | 1980.8 | 1967.5 | 1955.7 | 1890.5 |
| 52.5°  | 2152.6 | 2194.0 | 2201.4 | 2208.8 | 2216.2 | 2223.6 | 2201.4 | 2179.2 | 2155.5 | 2133.3 | 2051.9 |
| 55°    | 2343.5 | 2386.5 | 2388.0 | 2389.4 | 2389.4 | 2390.9 | 2359.8 | 2328.7 | 2296.2 | 2265.1 | 2180.7 |
| 57.5°  | 2485.7 | 2527.1 | 2522.7 | 2519.7 | 2515.3 | 2510.8 | 2473.8 | 2436.8 | 2399.8 | 2362.8 | 2278.4 |
| 60°    | 2539.0 | 2574.5 | 2565.6 | 2556.7 | 2546.4 | 2537.5 | 2509.4 | 2481.2 | 2451.6 | 2423.5 | 2342.1 |
| 62.5°  | 2513.8 | 2540.4 | 2527.1 | 2515.3 | 2502.0 | 2488.6 | 2453.1 | 2416.1 | 2380.6 | 2343.5 | 2284.3 |
| 65°    | 2348.0 | 2364.3 | 2346.5 | 2330.2 | 2313.9 | 2296.2 | 2266.6 | 2237.0 | 2205.9 | 2176.3 | 2136.3 |
| 67.5°  | 2068.2 | 2071.1 | 2069.7 | 2068.2 | 2066.7 | 2065.2 | 2022.3 | 1979.4 | 1934.9 | 1892.0 | 1889.0 |
| 70°    | 1684.7 | 1667.0 | 1669.9 | 1674.4 | 1677.3 | 1680.3 | 1647.7 | 1616.6 | 1584.1 | 1551.5 | 1566.3 |
| 72.5°  | 1299.8 | 1268.7 | 1276.1 | 1285.0 | 1292.4 | 1299.8 | 1273.2 | 1248.0 | 1221.4 | 1194.7 | 1215.4 |
| 75°    | 965.3  | 946.0  | 953.4  | 962.3  | 969.7  | 977.1  | 966.7  | 956.4  | 944.5  | 934.2  | 953.4  |
| 77.5°  | 735.8  | 723.9  | 725.4  | 725.4  | 726.9  | 726.9  | 728.4  | 731.3  | 732.8  | 734.3  | 755.0  |
| 80°    | 599.6  | 598.1  | 596.6  | 595.1  | 592.2  | 590.7  | 605.5  | 620.3  | 635.1  | 649.9  | 660.3  |
| 82.5°  | 524.1  | 538.9  | 530.0  | 522.6  | 513.7  | 504.8  | 518.2  | 531.5  | 544.8  | 558.1  | 553.7  |
| 85°    | 426.4  | 444.1  | 427.8  | 411.6  | 393.8  | 377.5  | 389.4  | 399.7  | 411.6  | 421.9  | 416.0  |
| 87.5°  | 168.8  | 173.2  | 146.6  | 121.4  | 94.7   | 68.1   | 108.1  | 146.6  | 186.5  | 225.0  | 230.9  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305° | 307.5° | 310° | 312.5° | 315° | 317.5° | 320° | 322.5° | 325° | 327.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 330°   | 332.5° | 335°   | 337.5° | 340°   | 342.5° | 345°   | 347.5° | 350°   | 352.5° | 355°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 | 1065.9 |
| 2.5°   | 1150.3 | 1144.4 | 1139.9 | 1138.5 | 1135.5 | 1134.0 | 1131.1 | 1128.1 | 1123.7 | 1120.7 | 1116.3 |
| 5°     | 1188.8 | 1179.9 | 1169.6 | 1154.7 | 1141.4 | 1126.6 | 1111.8 | 1098.5 | 1085.2 | 1070.4 | 1057.0 |
| 7.5°   | 1190.3 | 1169.6 | 1148.8 | 1129.6 | 1108.9 | 1089.6 | 1068.9 | 1051.1 | 1031.9 | 1012.6 | 994.9  |
| 10°    | 1174.0 | 1148.8 | 1123.7 | 1098.5 | 1074.8 | 1049.6 | 1024.5 | 1003.7 | 981.5  | 959.3  | 938.6  |
| 12.5°  | 1160.7 | 1132.5 | 1104.4 | 1074.8 | 1046.7 | 1017.1 | 987.5  | 966.7  | 946.0  | 925.3  | 904.6  |
| 15°    | 1144.4 | 1126.6 | 1110.3 | 1083.7 | 1057.0 | 1030.4 | 1003.7 | 975.6  | 949.0  | 920.8  | 892.7  |
| 17.5°  | 1131.1 | 1126.6 | 1122.2 | 1104.4 | 1086.6 | 1067.4 | 1049.6 | 1021.5 | 993.4  | 963.8  | 935.6  |
| 20°    | 1123.7 | 1129.6 | 1135.5 | 1126.6 | 1117.7 | 1107.4 | 1098.5 | 1077.8 | 1057.0 | 1034.8 | 1014.1 |
| 22.5°  | 1132.5 | 1154.7 | 1175.5 | 1177.0 | 1179.9 | 1181.4 | 1182.9 | 1163.6 | 1144.4 | 1123.7 | 1104.4 |
| 25°    | 1153.3 | 1188.8 | 1224.3 | 1243.6 | 1262.8 | 1283.5 | 1302.8 | 1290.9 | 1279.1 | 1267.3 | 1255.4 |
| 27.5°  | 1181.4 | 1225.8 | 1270.2 | 1298.4 | 1325.0 | 1353.1 | 1381.3 | 1379.8 | 1378.3 | 1375.3 | 1373.9 |
| 30°    | 1177.0 | 1211.0 | 1245.1 | 1279.1 | 1313.2 | 1347.2 | 1381.3 | 1399.0 | 1415.3 | 1433.1 | 1450.8 |
| 32.5°  | 1202.1 | 1230.3 | 1259.9 | 1295.4 | 1330.9 | 1367.9 | 1403.5 | 1440.5 | 1476.0 | 1513.0 | 1550.0 |
| 35°    | 1240.6 | 1265.8 | 1292.4 | 1330.9 | 1370.9 | 1409.4 | 1449.4 | 1493.8 | 1539.7 | 1585.6 | 1630.0 |
| 37.5°  | 1298.4 | 1320.6 | 1344.2 | 1376.8 | 1410.9 | 1443.4 | 1477.5 | 1542.6 | 1607.8 | 1674.4 | 1739.5 |
| 40°    | 1365.0 | 1379.8 | 1394.6 | 1425.7 | 1456.8 | 1487.8 | 1518.9 | 1600.4 | 1681.8 | 1763.2 | 1844.6 |
| 42.5°  | 1461.2 | 1456.8 | 1452.3 | 1477.5 | 1504.1 | 1529.3 | 1555.9 | 1630.0 | 1704.0 | 1778.0 | 1852.0 |
| 45°    | 1563.4 | 1545.6 | 1527.8 | 1539.7 | 1553.0 | 1564.8 | 1578.2 | 1653.7 | 1729.2 | 1806.1 | 1881.6 |
| 47.5°  | 1686.2 | 1641.8 | 1597.4 | 1587.0 | 1576.7 | 1564.8 | 1554.5 | 1635.9 | 1717.3 | 1800.2 | 1881.6 |
| 50°    | 1825.4 | 1758.8 | 1693.6 | 1667.0 | 1638.9 | 1612.2 | 1584.1 | 1650.7 | 1718.8 | 1786.9 | 1853.5 |
| 52.5°  | 1970.5 | 1887.6 | 1806.1 | 1764.7 | 1723.2 | 1680.3 | 1638.9 | 1695.1 | 1752.8 | 1810.6 | 1866.8 |
| 55°    | 2094.8 | 2010.4 | 1924.6 | 1875.7 | 1826.9 | 1778.0 | 1729.2 | 1785.4 | 1841.7 | 1897.9 | 1954.2 |
| 57.5°  | 2194.0 | 2109.6 | 2025.3 | 1979.4 | 1932.0 | 1886.1 | 1838.7 | 1892.0 | 1946.8 | 2001.6 | 2054.9 |
| 60°    | 2262.1 | 2180.7 | 2099.3 | 2054.9 | 2010.4 | 1966.0 | 1921.6 | 1985.3 | 2048.9 | 2114.1 | 2177.7 |
| 62.5°  | 2226.6 | 2167.4 | 2108.2 | 2088.9 | 2069.7 | 2048.9 | 2029.7 | 2090.4 | 2149.6 | 2210.3 | 2271.0 |
| 65°    | 2096.3 | 2056.3 | 2016.4 | 2035.6 | 2056.3 | 2075.6 | 2096.3 | 2136.3 | 2176.3 | 2217.7 | 2257.7 |
| 67.5°  | 1884.6 | 1881.6 | 1877.2 | 1920.1 | 1963.1 | 2007.5 | 2050.4 | 2077.1 | 2102.2 | 2128.9 | 2155.5 |
| 70°    | 1581.1 | 1597.4 | 1612.2 | 1686.2 | 1760.3 | 1834.3 | 1908.3 | 1918.7 | 1929.0 | 1939.4 | 1949.7 |
| 72.5°  | 1237.7 | 1258.4 | 1280.6 | 1378.3 | 1474.5 | 1572.2 | 1669.9 | 1664.0 | 1658.1 | 1650.7 | 1644.8 |
| 75°    | 974.1  | 993.4  | 1014.1 | 1104.4 | 1194.7 | 1285.0 | 1375.3 | 1350.2 | 1326.5 | 1301.3 | 1276.1 |
| 77.5°  | 777.2  | 798.0  | 820.2  | 904.6  | 988.9  | 1074.8 | 1159.2 | 1098.5 | 1037.8 | 977.1  | 916.4  |
| 80°    | 669.2  | 679.5  | 688.4  | 746.1  | 802.4  | 860.1  | 917.9  | 855.7  | 792.0  | 728.4  | 666.2  |
| 82.5°  | 549.2  | 543.3  | 538.9  | 572.9  | 607.0  | 641.0  | 675.1  | 615.9  | 556.6  | 495.9  | 436.7  |
| 85°    | 410.1  | 404.2  | 398.2  | 416.0  | 433.8  | 453.0  | 470.8  | 402.7  | 334.6  | 265.0  | 196.9  |
| 87.5°  | 238.4  | 244.3  | 250.2  | 269.4  | 288.7  | 309.4  | 328.7  | 259.1  | 189.5  | 118.4  | 48.9   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671861

CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 332.5° | 335° | 337.5° | 340° | 342.5° | 345° | 347.5° | 350° | 352.5° | 355° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P671861  
 CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360°   |
|--------|--------|--------|
| 0°     | 1065.9 | 1065.9 |
| 2.5°   | 1107.4 | 1100.0 |
| 5°     | 1046.7 | 1036.3 |
| 7.5°   | 980.1  | 966.7  |
| 10°    | 919.4  | 901.6  |
| 12.5°  | 880.9  | 858.7  |
| 15°    | 866.1  | 839.4  |
| 17.5°  | 910.5  | 885.3  |
| 20°    | 978.6  | 944.5  |
| 22.5°  | 1061.5 | 1020.0 |
| 25°    | 1205.1 | 1154.7 |
| 27.5°  | 1322.0 | 1270.2 |
| 30°    | 1394.6 | 1338.3 |
| 32.5°  | 1474.5 | 1400.5 |
| 35°    | 1557.4 | 1486.4 |
| 37.5°  | 1658.1 | 1578.2 |
| 40°    | 1761.7 | 1678.8 |
| 42.5°  | 1797.3 | 1744.0 |
| 45°    | 1831.3 | 1781.0 |
| 47.5°  | 1838.7 | 1797.3 |
| 50°    | 1846.1 | 1840.2 |
| 52.5°  | 1866.8 | 1865.4 |
| 55°    | 1955.7 | 1957.2 |
| 57.5°  | 2065.2 | 2074.1 |
| 60°    | 2165.9 | 2155.5 |
| 62.5°  | 2217.7 | 2164.4 |
| 65°    | 2182.2 | 2108.2 |
| 67.5°  | 2075.6 | 1995.6 |
| 70°    | 1841.7 | 1733.6 |
| 72.5°  | 1550.0 | 1455.3 |
| 75°    | 1194.7 | 1114.8 |
| 77.5°  | 849.8  | 783.2  |
| 80°    | 598.1  | 531.5  |
| 82.5°  | 383.4  | 330.1  |
| 85°    | 173.2  | 151.0  |
| 87.5°  | 48.9   | 47.4   |
| 90°    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    |



REPORT NUMBER: P671861  
CATALOG NUMBER: CCP-SA-2A-827-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

(END OF REPORT)