

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671884

Luminaire Tested: **CCP-SA-2B-835-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671884
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-2B-835-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @450mA w/ SLR
distribution lens
Light Source: (32) 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4722.6 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 46
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 6.7 fc

Type IV - Short - N/A

REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	971.7	0.0	971.7
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3750.9	0.0	3750.9
	% Fixture	79.4	0.0	79.4
Total	Lumens	4722.6	0.0	4722.6
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.2	2.5
10°-20°	247.4	5.2
20°-30°	362.0	7.7
30°-40°	510.0	10.8
40°-50°	700.8	14.8
50°-60°	955.1	20.2
60°-70°	1045.4	22.1
70°-80°	603.7	12.8
80°-90°	181.0	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4722.6	100.0
0°-180°	4722.6	100.0

Coefficient of Utilization



REPORT NUMBER: P671884


CATALOG NUMBER: CCP-SA-2B-835-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	485.0	10.3			
FM	(30°-60°)	1723.4	36.5			
FH	(60°-80°)	1388.7	29.4			G1/1800
FVH	(80°-90°)	153.7	3.3			G2/225
BL	(0°-30°)	241.6	5.1	B1/500		
BM	(30°-60°)	442.5	9.4	B1/1000		
BH	(60°-80°)	260.4	5.5	B1/500		G1/500
BVH	(80°-90°)	27.3	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1
2.5°	1556.3	1547.9	1541.6	1535.3	1526.9	1520.7	1512.3	1503.9	1493.4	1485.1	1474.6
5°	1466.2	1441.1	1415.9	1401.3	1384.5	1369.9	1353.1	1334.2	1315.4	1294.4	1275.6
7.5°	1367.8	1336.3	1304.9	1279.8	1252.6	1227.4	1200.2	1177.2	1154.1	1131.1	1108.0
10°	1275.6	1246.3	1216.9	1185.5	1152.0	1120.6	1087.1	1055.7	1024.2	992.8	961.4
12.5°	1214.9	1179.2	1145.7	1110.1	1076.6	1041.0	1005.4	976.1	946.7	915.3	886.0
15°	1187.6	1154.1	1122.7	1087.1	1051.5	1015.9	980.3	946.7	915.3	881.8	848.3
17.5°	1252.6	1204.4	1156.2	1110.1	1064.0	1018.0	971.9	930.0	888.1	846.2	804.3
20°	1336.3	1275.6	1216.9	1160.4	1101.7	1045.2	986.5	927.9	869.2	810.6	752.0
22.5°	1443.2	1374.0	1307.0	1233.7	1158.3	1085.0	1009.6	936.3	863.0	787.6	714.3
25°	1633.8	1552.1	1470.4	1365.7	1258.8	1154.1	1047.3	950.9	856.7	760.3	664.0
27.5°	1797.1	1686.1	1577.2	1451.5	1325.9	1200.2	1074.5	963.5	854.6	743.6	632.6
30°	1893.5	1784.6	1675.7	1522.8	1371.9	1219.0	1066.1	942.6	821.1	697.5	573.9
32.5°	1981.5	1860.0	1738.5	1570.9	1401.3	1233.7	1064.0	927.9	793.8	657.7	521.5
35°	2103.0	1968.9	1836.9	1642.1	1447.4	1252.6	1057.8	917.4	775.0	634.7	492.2
37.5°	2232.8	2067.3	1904.0	1688.2	1472.5	1256.7	1041.0	902.8	764.5	626.3	488.0
40°	2375.2	2174.2	1975.2	1736.4	1499.7	1260.9	1022.2	883.9	745.7	605.3	467.1
42.5°	2467.4	2249.6	2031.7	1774.1	1518.6	1260.9	1003.3	867.2	731.0	592.8	456.6
45°	2519.8	2308.2	2098.8	1820.2	1541.6	1263.0	984.5	850.4	716.3	580.2	446.1
47.5°	2542.8	2345.9	2149.0	1855.8	1564.6	1271.4	978.2	842.0	703.8	567.6	429.4
50°	2603.6	2429.7	2255.9	1941.7	1629.6	1315.4	1001.2	854.6	710.1	563.4	416.8
52.5°	2639.2	2490.5	2341.7	2019.2	1696.6	1374.0	1051.5	888.1	724.7	561.3	398.0
55°	2769.0	2626.6	2484.2	2140.7	1795.1	1451.5	1105.9	925.8	745.7	563.4	383.3
57.5°	2934.5	2783.7	2635.0	2264.2	1893.5	1522.8	1152.0	959.3	764.5	571.8	377.0
60°	3049.7	2903.1	2758.6	2364.8	1968.9	1575.1	1179.2	978.2	777.1	573.9	372.8
62.5°	3062.3	2873.8	2687.3	2304.0	1920.7	1535.3	1152.0	957.2	762.4	565.5	370.7
65°	2982.7	2762.7	2542.8	2176.3	1809.7	1443.2	1076.6	898.6	720.5	540.4	362.4
67.5°	2823.5	2565.9	2308.2	1973.1	1638.0	1302.8	967.7	814.8	664.0	511.1	358.2
70°	2452.7	2226.5	2002.4	1711.3	1422.2	1131.1	839.9	714.3	590.7	465.0	339.3
72.5°	2059.0	1847.4	1638.0	1401.3	1166.7	930.0	693.3	599.0	504.8	408.4	314.2
75°	1577.2	1418.0	1260.9	1085.0	909.0	731.0	555.1	485.9	416.8	347.7	278.6
77.5°	1108.0	1022.2	938.4	806.4	674.5	542.5	410.5	364.5	318.4	272.3	226.2
80°	752.0	703.8	657.7	563.4	469.2	372.8	278.6	249.3	217.8	188.5	157.1
82.5°	467.1	465.0	460.8	395.9	330.9	266.0	201.1	175.9	152.9	127.8	102.6
85°	213.6	249.3	282.8	247.2	211.6	175.9	140.3	123.6	106.8	88.0	71.2
87.5°	67.0	81.7	94.3	90.1	83.8	79.6	73.3	62.8	52.4	41.9	31.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1
2.5°	1466.2	1459.9	1451.5	1443.2	1432.7	1424.3	1413.8	1403.4	1401.3	1397.1	1395.0
5°	1263.0	1250.5	1235.8	1223.2	1210.7	1196.0	1183.4	1168.8	1158.3	1145.7	1135.3
7.5°	1085.0	1064.0	1041.0	1018.0	997.0	976.1	953.0	932.1	921.6	911.1	900.7
10°	942.6	921.6	902.8	881.8	867.2	854.6	839.9	825.3	812.7	800.1	787.6
12.5°	871.3	856.7	842.0	827.4	810.6	795.9	779.2	762.4	747.8	735.2	720.5
15°	827.4	806.4	783.4	762.4	739.4	718.4	695.4	672.4	655.6	640.9	624.2
17.5°	775.0	743.6	714.3	682.8	657.7	632.6	605.3	580.2	561.3	540.4	521.5
20°	716.3	680.7	643.0	607.4	578.1	550.9	521.5	492.2	471.3	448.2	427.3
22.5°	666.1	620.0	571.8	523.6	492.2	460.8	427.3	395.9	377.0	356.1	337.2
25°	611.6	561.3	509.0	456.6	425.2	391.7	360.3	326.8	312.1	299.5	284.9
27.5°	582.3	532.0	479.7	429.4	400.1	368.6	339.3	307.9	297.4	284.9	274.4
30°	523.6	475.5	425.2	374.9	354.0	335.1	314.2	293.2	289.1	287.0	282.8
32.5°	471.3	421.0	370.7	320.5	301.6	282.8	263.9	245.1	243.0	238.8	236.7
35°	444.1	395.9	345.6	297.4	280.7	261.8	245.1	226.2	222.0	215.7	211.6
37.5°	437.8	387.5	335.1	284.9	268.1	251.3	232.5	215.7	211.6	207.4	203.2
40°	421.0	372.8	326.8	278.6	261.8	245.1	226.2	209.5	205.3	201.1	196.9
42.5°	408.4	362.4	314.2	266.0	251.3	236.7	219.9	205.3	201.1	196.9	190.6
45°	398.0	349.8	299.5	251.3	240.9	230.4	217.8	207.4	203.2	196.9	192.7
47.5°	381.2	335.1	287.0	238.8	228.3	219.9	209.5	199.0	194.8	190.6	186.4
50°	368.6	320.5	272.3	224.1	215.7	207.4	199.0	190.6	190.6	192.7	192.7
52.5°	351.9	305.8	259.7	213.6	205.3	196.9	188.5	180.1	182.2	184.3	186.4
55°	337.2	293.2	247.2	201.1	192.7	184.3	173.8	165.5	167.6	169.7	171.8
57.5°	330.9	284.9	238.8	192.7	184.3	173.8	165.5	155.0	155.0	155.0	155.0
60°	326.8	278.6	232.5	184.3	173.8	165.5	155.0	144.5	142.4	142.4	140.3
62.5°	324.7	276.5	230.4	182.2	169.7	159.2	146.6	134.1	132.0	129.9	127.8
65°	316.3	272.3	226.2	180.1	165.5	152.9	138.2	123.6	121.5	121.5	119.4
67.5°	314.2	268.1	224.1	178.0	163.4	146.6	132.0	115.2	113.1	111.0	108.9
70°	297.4	257.6	215.7	173.8	157.1	142.4	125.7	108.9	106.8	102.6	100.5
72.5°	276.5	240.9	203.2	165.5	148.7	132.0	115.2	98.4	96.4	94.3	90.1
75°	245.1	211.6	178.0	144.5	129.9	117.3	102.6	88.0	85.9	83.8	79.6
77.5°	201.1	173.8	148.7	121.5	111.0	100.5	90.1	79.6	77.5	75.4	71.2
80°	142.4	125.7	111.0	94.3	88.0	79.6	73.3	64.9	64.9	62.8	62.8
82.5°	94.3	85.9	77.5	69.1	64.9	60.7	56.6	52.4	52.4	50.3	50.3
85°	67.0	62.8	56.6	52.4	50.3	46.1	44.0	39.8	39.8	39.8	39.8
87.5°	31.4	31.4	29.3	29.3	27.2	27.2	25.1	23.0	23.0	23.0	23.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1
2.5°	1390.8	1384.5	1378.2	1369.9	1363.6	1355.2	1344.7	1336.3	1325.9	1325.9	1323.8
5°	1122.7	1116.4	1110.1	1101.7	1095.5	1087.1	1080.8	1072.4	1064.0	1064.0	1062.0
7.5°	890.2	877.6	865.1	850.4	837.8	829.5	821.1	810.6	802.2	795.9	789.7
10°	775.0	762.4	747.8	735.2	720.5	710.1	699.6	687.0	676.5	668.2	659.8
12.5°	705.9	691.2	676.5	661.9	647.2	632.6	620.0	605.3	590.7	580.2	569.7
15°	607.4	592.8	578.1	563.4	548.8	532.0	515.3	496.4	479.7	471.3	465.0
17.5°	500.6	485.9	469.2	454.5	437.8	425.2	412.6	400.1	387.5	379.1	372.8
20°	404.3	387.5	370.7	354.0	337.2	328.8	320.5	312.1	303.7	297.4	293.2
22.5°	316.3	305.8	297.4	287.0	276.5	270.2	266.0	259.7	253.4	253.4	253.4
25°	270.2	263.9	259.7	253.4	247.2	245.1	243.0	238.8	236.7	234.6	234.6
27.5°	261.8	255.5	249.3	243.0	236.7	234.6	232.5	228.3	226.2	226.2	226.2
30°	278.6	276.5	274.4	272.3	270.2	266.0	259.7	255.5	249.3	245.1	240.9
32.5°	232.5	230.4	230.4	228.3	226.2	230.4	232.5	236.7	238.8	240.9	243.0
35°	205.3	201.1	196.9	192.7	188.5	186.4	184.3	182.2	180.1	180.1	178.0
37.5°	199.0	194.8	190.6	186.4	182.2	180.1	178.0	175.9	173.8	173.8	171.8
40°	192.7	188.5	186.4	182.2	178.0	175.9	173.8	169.7	167.6	165.5	165.5
42.5°	186.4	184.3	180.1	178.0	173.8	171.8	169.7	165.5	163.4	161.3	159.2
45°	186.4	182.2	178.0	173.8	169.7	167.6	163.4	161.3	157.1	157.1	155.0
47.5°	182.2	178.0	173.8	169.7	165.5	163.4	159.2	157.1	152.9	150.8	148.7
50°	192.7	186.4	178.0	171.8	163.4	161.3	157.1	155.0	150.8	148.7	146.6
52.5°	188.5	182.2	173.8	167.6	159.2	155.0	152.9	148.7	144.5	142.4	140.3
55°	173.8	167.6	163.4	157.1	150.8	146.6	142.4	138.2	134.1	132.0	132.0
57.5°	155.0	152.9	150.8	148.7	146.6	142.4	138.2	132.0	127.8	125.7	123.6
60°	138.2	140.3	142.4	144.5	146.6	140.3	134.1	127.8	121.5	119.4	117.3
62.5°	125.7	129.9	134.1	136.1	140.3	134.1	127.8	121.5	115.2	113.1	111.0
65°	117.3	119.4	119.4	121.5	121.5	117.3	115.2	111.0	106.8	104.7	104.7
67.5°	106.8	106.8	106.8	104.7	104.7	102.6	102.6	100.5	98.4	96.4	96.4
70°	96.4	96.4	96.4	94.3	94.3	92.2	92.2	90.1	88.0	88.0	85.9
72.5°	88.0	88.0	85.9	85.9	83.8	83.8	83.8	81.7	81.7	79.6	79.6
75°	77.5	77.5	75.4	75.4	73.3	73.3	73.3	71.2	71.2	71.2	69.1
77.5°	69.1	69.1	67.0	67.0	64.9	64.9	64.9	62.8	62.8	60.7	60.7
80°	60.7	60.7	58.6	58.6	56.6	56.6	54.5	54.5	52.4	52.4	50.3
82.5°	48.2	48.2	48.2	48.2	48.2	46.1	46.1	44.0	41.9	41.9	39.8
85°	39.8	39.8	39.8	37.7	37.7	37.7	35.6	35.6	33.5	31.4	31.4
87.5°	23.0	23.0	23.0	20.9	20.9	20.9	20.9	20.9	20.9	20.9	18.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1
2.5°	1323.8	1321.7	1313.3	1304.9	1313.3	1321.7	1321.7	1321.7	1319.6	1319.6	1319.6
5°	1062.0	1059.9	1055.7	1051.5	1051.5	1049.4	1053.6	1057.8	1062.0	1066.1	1070.3
7.5°	781.3	775.0	768.7	762.4	766.6	768.7	775.0	779.2	785.5	789.7	800.1
10°	651.4	643.0	636.8	630.5	626.3	622.1	617.9	615.8	611.6	607.4	611.6
12.5°	557.2	546.7	536.2	523.6	521.5	519.5	515.3	511.1	506.9	502.7	500.6
15°	456.6	448.2	444.1	437.8	429.4	421.0	416.8	414.7	410.5	406.3	404.3
17.5°	364.5	356.1	349.8	343.5	341.4	337.2	337.2	337.2	337.2	337.2	337.2
20°	287.0	280.7	280.7	278.6	278.6	276.5	278.6	280.7	280.7	282.8	284.9
22.5°	251.3	251.3	249.3	247.2	249.3	249.3	251.3	253.4	255.5	257.6	259.7
25°	232.5	230.4	232.5	234.6	234.6	234.6	236.7	236.7	238.8	238.8	238.8
27.5°	224.1	224.1	226.2	226.2	228.3	228.3	228.3	226.2	226.2	224.1	224.1
30°	236.7	232.5	232.5	232.5	230.4	228.3	226.2	226.2	224.1	222.0	219.9
32.5°	245.1	247.2	245.1	240.9	238.8	234.6	232.5	228.3	226.2	222.0	217.8
35°	178.0	175.9	180.1	182.2	184.3	186.4	188.5	190.6	190.6	192.7	192.7
37.5°	171.8	169.7	169.7	167.6	167.6	167.6	167.6	167.6	165.5	165.5	167.6
40°	163.4	161.3	161.3	159.2	159.2	157.1	157.1	157.1	157.1	157.1	157.1
42.5°	157.1	155.0	155.0	155.0	155.0	152.9	152.9	150.8	150.8	148.7	148.7
45°	155.0	152.9	150.8	148.7	148.7	146.6	146.6	146.6	144.5	144.5	144.5
47.5°	146.6	144.5	144.5	142.4	142.4	140.3	140.3	140.3	138.2	138.2	138.2
50°	142.4	140.3	140.3	138.2	138.2	136.1	136.1	136.1	134.1	134.1	134.1
52.5°	136.1	134.1	134.1	134.1	132.0	129.9	129.9	129.9	127.8	127.8	127.8
55°	129.9	127.8	127.8	127.8	125.7	123.6	123.6	123.6	121.5	121.5	121.5
57.5°	121.5	119.4	119.4	117.3	117.3	117.3	117.3	117.3	115.2	115.2	115.2
60°	115.2	113.1	113.1	111.0	111.0	108.9	108.9	108.9	108.9	108.9	108.9
62.5°	108.9	106.8	104.7	102.6	104.7	104.7	104.7	104.7	102.6	102.6	102.6
65°	102.6	100.5	98.4	96.4	96.4	96.4	96.4	96.4	96.4	96.4	96.4
67.5°	94.3	92.2	90.1	88.0	90.1	90.1	90.1	90.1	90.1	90.1	90.1
70°	85.9	83.8	83.8	81.7	81.7	79.6	79.6	81.7	81.7	81.7	81.7
72.5°	77.5	75.4	75.4	73.3	73.3	73.3	73.3	73.3	73.3	73.3	73.3
75°	69.1	67.0	67.0	64.9	64.9	64.9	64.9	64.9	64.9	64.9	64.9
77.5°	58.6	56.6	56.6	56.6	56.6	56.6	56.6	58.6	58.6	58.6	58.6
80°	50.3	48.2	48.2	48.2	48.2	48.2	48.2	48.2	48.2	48.2	48.2
82.5°	39.8	37.7	37.7	37.7	37.7	37.7	37.7	37.7	37.7	37.7	37.7
85°	29.3	27.2	27.2	27.2	29.3	29.3	29.3	29.3	29.3	29.3	29.3
87.5°	18.9	16.8	16.8	16.8	18.9	18.9	18.9	18.9	16.8	16.8	16.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1
2.5°	1319.6	1319.6	1319.6	1317.5	1315.4	1313.3	1311.2	1317.5	1321.7	1328.0	1332.2
5°	1072.4	1076.6	1078.7	1085.0	1091.3	1097.6	1103.8	1108.0	1112.2	1114.3	1118.5
7.5°	808.5	819.0	827.4	835.7	844.1	850.4	858.8	865.1	871.3	877.6	883.9
10°	613.7	617.9	620.0	628.4	634.7	643.0	649.3	655.6	661.9	666.1	672.4
12.5°	498.5	494.3	492.2	492.2	492.2	492.2	492.2	496.4	500.6	504.8	509.0
15°	402.2	400.1	398.0	395.9	393.8	389.6	387.5	391.7	395.9	400.1	404.3
17.5°	337.2	337.2	337.2	335.1	333.0	330.9	328.8	330.9	333.0	333.0	335.1
20°	289.1	291.1	293.2	295.3	295.3	297.4	297.4	299.5	301.6	301.6	303.7
22.5°	259.7	261.8	261.8	261.8	263.9	263.9	263.9	266.0	268.1	270.2	272.3
25°	236.7	236.7	234.6	234.6	236.7	236.7	236.7	236.7	238.8	238.8	238.8
27.5°	224.1	222.0	222.0	222.0	222.0	219.9	219.9	219.9	219.9	219.9	219.9
30°	217.8	215.7	213.6	211.6	211.6	209.5	207.4	207.4	207.4	207.4	207.4
32.5°	215.7	211.6	207.4	205.3	205.3	203.2	201.1	199.0	199.0	196.9	194.8
35°	192.7	190.6	190.6	188.5	186.4	184.3	182.2	182.2	182.2	180.1	180.1
37.5°	167.6	169.7	169.7	169.7	171.8	171.8	171.8	171.8	173.8	173.8	173.8
40°	157.1	157.1	157.1	159.2	161.3	161.3	163.4	163.4	165.5	165.5	165.5
42.5°	148.7	146.6	146.6	148.7	148.7	150.8	150.8	152.9	155.0	155.0	157.1
45°	144.5	142.4	142.4	142.4	142.4	140.3	140.3	142.4	144.5	146.6	148.7
47.5°	136.1	136.1	134.1	134.1	134.1	134.1	134.1	134.1	136.1	136.1	136.1
50°	132.0	132.0	129.9	129.9	129.9	129.9	129.9	129.9	129.9	129.9	129.9
52.5°	127.8	125.7	125.7	125.7	125.7	123.6	123.6	123.6	123.6	123.6	123.6
55°	121.5	119.4	119.4	119.4	119.4	119.4	119.4	119.4	121.5	121.5	121.5
57.5°	115.2	113.1	113.1	113.1	115.2	115.2	115.2	115.2	117.3	117.3	117.3
60°	108.9	108.9	108.9	108.9	108.9	108.9	108.9	111.0	111.0	113.1	113.1
62.5°	102.6	102.6	102.6	102.6	104.7	104.7	104.7	104.7	106.8	106.8	106.8
65°	96.4	96.4	96.4	96.4	98.4	98.4	98.4	98.4	98.4	98.4	98.4
67.5°	90.1	90.1	90.1	90.1	90.1	90.1	90.1	92.2	92.2	94.3	94.3
70°	81.7	79.6	79.6	81.7	81.7	83.8	83.8	85.9	85.9	88.0	88.0
72.5°	73.3	73.3	73.3	73.3	73.3	73.3	73.3	75.4	77.5	77.5	79.6
75°	64.9	64.9	64.9	64.9	67.0	67.0	67.0	69.1	69.1	71.2	71.2
77.5°	58.6	56.6	56.6	56.6	58.6	58.6	58.6	60.7	60.7	62.8	62.8
80°	48.2	48.2	48.2	48.2	50.3	50.3	50.3	50.3	52.4	52.4	52.4
82.5°	39.8	39.8	39.8	39.8	39.8	39.8	39.8	39.8	41.9	41.9	41.9
85°	29.3	29.3	29.3	29.3	31.4	31.4	31.4	31.4	31.4	31.4	31.4
87.5°	18.9	18.9	18.9	18.9	18.9	18.9	18.9	18.9	20.9	20.9	20.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1
2.5°	1332.2	1332.2	1332.2	1332.2	1336.3	1338.4	1342.6	1344.7	1342.6	1340.5	1336.3
5°	1120.6	1122.7	1122.7	1124.8	1124.8	1124.8	1124.8	1124.8	1129.0	1133.2	1137.4
7.5°	886.0	888.1	890.2	892.3	892.3	892.3	890.2	890.2	892.3	892.3	894.4
10°	678.6	687.0	693.3	699.6	695.4	689.1	684.9	678.6	678.6	678.6	676.5
12.5°	513.2	515.3	519.5	521.5	519.5	519.5	517.4	515.3	517.4	521.5	523.6
15°	406.3	406.3	408.4	408.4	410.5	412.6	412.6	414.7	418.9	421.0	425.2
17.5°	337.2	339.3	339.3	341.4	341.4	343.5	343.5	343.5	347.7	351.9	358.2
20°	303.7	303.7	303.7	303.7	303.7	301.6	301.6	299.5	301.6	305.8	307.9
22.5°	272.3	274.4	274.4	274.4	272.3	270.2	266.0	263.9	263.9	266.0	266.0
25°	238.8	236.7	236.7	234.6	234.6	236.7	236.7	236.7	238.8	238.8	240.9
27.5°	219.9	217.8	217.8	215.7	215.7	217.8	217.8	217.8	217.8	217.8	217.8
30°	205.3	205.3	203.2	201.1	203.2	203.2	205.3	205.3	207.4	207.4	209.5
32.5°	194.8	192.7	192.7	190.6	192.7	192.7	194.8	194.8	196.9	199.0	199.0
35°	180.1	180.1	180.1	180.1	180.1	180.1	178.0	178.0	178.0	178.0	178.0
37.5°	171.8	171.8	169.7	167.6	167.6	167.6	167.6	167.6	165.5	163.4	161.3
40°	165.5	163.4	163.4	161.3	159.2	159.2	157.1	155.0	155.0	152.9	152.9
42.5°	157.1	155.0	155.0	152.9	150.8	150.8	148.7	146.6	146.6	146.6	144.5
45°	146.6	146.6	144.5	142.4	142.4	142.4	140.3	140.3	140.3	140.3	138.2
47.5°	136.1	136.1	134.1	134.1	134.1	134.1	132.0	132.0	132.0	132.0	132.0
50°	129.9	129.9	129.9	129.9	129.9	129.9	127.8	127.8	127.8	127.8	127.8
52.5°	123.6	123.6	123.6	123.6	123.6	123.6	123.6	123.6	123.6	123.6	123.6
55°	121.5	121.5	121.5	121.5	121.5	121.5	119.4	119.4	119.4	121.5	121.5
57.5°	117.3	117.3	115.2	115.2	115.2	115.2	115.2	115.2	115.2	115.2	115.2
60°	113.1	113.1	113.1	113.1	113.1	113.1	113.1	113.1	113.1	113.1	113.1
62.5°	106.8	106.8	106.8	106.8	106.8	108.9	108.9	108.9	108.9	108.9	106.8
65°	98.4	100.5	100.5	100.5	100.5	100.5	100.5	100.5	100.5	100.5	100.5
67.5°	94.3	94.3	94.3	94.3	94.3	94.3	94.3	94.3	94.3	94.3	94.3
70°	88.0	88.0	85.9	85.9	85.9	88.0	88.0	88.0	88.0	88.0	88.0
72.5°	79.6	79.6	79.6	79.6	79.6	79.6	79.6	79.6	79.6	81.7	81.7
75°	71.2	71.2	71.2	71.2	71.2	71.2	71.2	71.2	71.2	71.2	71.2
77.5°	62.8	62.8	60.7	60.7	60.7	62.8	62.8	62.8	62.8	64.9	64.9
80°	52.4	52.4	52.4	52.4	52.4	52.4	52.4	52.4	52.4	54.5	54.5
82.5°	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	44.0	44.0
85°	31.4	33.5	33.5	33.5	33.5	33.5	33.5	33.5	33.5	35.6	35.6
87.5°	20.9	20.9	20.9	20.9	20.9	20.9	18.9	18.9	18.9	18.9	16.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1
2.5°	1334.2	1336.3	1338.4	1338.4	1340.5	1342.6	1342.6	1351.0	1359.4	1363.6	1367.8
5°	1141.5	1139.4	1139.4	1137.4	1135.3	1141.5	1147.8	1160.4	1173.0	1175.1	1179.2
7.5°	894.4	896.5	898.6	898.6	900.7	894.4	886.0	888.1	890.2	900.7	909.0
10°	676.5	678.6	680.7	680.7	682.8	680.7	676.5	682.8	689.1	697.5	708.0
12.5°	525.7	532.0	538.3	542.5	548.8	553.0	555.1	563.4	569.7	580.2	590.7
15°	429.4	433.6	437.8	442.0	446.1	450.3	454.5	462.9	471.3	483.8	496.4
17.5°	362.4	362.4	364.5	364.5	364.5	368.6	372.8	377.0	379.1	391.7	404.3
20°	310.0	307.9	305.8	303.7	301.6	305.8	307.9	310.0	312.1	320.5	326.8
22.5°	266.0	266.0	268.1	268.1	268.1	266.0	261.8	263.9	263.9	268.1	274.4
25°	240.9	240.9	240.9	238.8	238.8	240.9	243.0	243.0	240.9	243.0	245.1
27.5°	217.8	219.9	219.9	222.0	222.0	224.1	224.1	224.1	224.1	226.2	228.3
30°	209.5	209.5	211.6	211.6	211.6	213.6	215.7	215.7	215.7	217.8	222.0
32.5°	201.1	203.2	205.3	207.4	209.5	211.6	211.6	213.6	213.6	215.7	217.8
35°	178.0	175.9	175.9	173.8	171.8	171.8	171.8	171.8	169.7	171.8	171.8
37.5°	159.2	159.2	159.2	157.1	157.1	159.2	159.2	159.2	159.2	161.3	161.3
40°	150.8	150.8	150.8	150.8	150.8	150.8	150.8	152.9	152.9	155.0	157.1
42.5°	144.5	144.5	144.5	144.5	144.5	146.6	146.6	146.6	146.6	148.7	148.7
45°	138.2	138.2	138.2	138.2	138.2	138.2	138.2	140.3	140.3	142.4	144.5
47.5°	132.0	132.0	132.0	132.0	132.0	134.1	136.1	136.1	136.1	138.2	138.2
50°	127.8	127.8	127.8	127.8	127.8	129.9	129.9	132.0	132.0	134.1	136.1
52.5°	123.6	123.6	123.6	123.6	123.6	125.7	125.7	127.8	127.8	129.9	132.0
55°	121.5	121.5	121.5	119.4	119.4	121.5	121.5	123.6	123.6	125.7	125.7
57.5°	115.2	115.2	115.2	115.2	115.2	115.2	115.2	117.3	117.3	119.4	121.5
60°	113.1	113.1	111.0	111.0	108.9	111.0	111.0	113.1	113.1	115.2	115.2
62.5°	106.8	106.8	106.8	104.7	104.7	106.8	106.8	106.8	106.8	108.9	111.0
65°	100.5	100.5	100.5	98.4	98.4	100.5	100.5	100.5	100.5	102.6	104.7
67.5°	94.3	94.3	94.3	92.2	92.2	92.2	92.2	94.3	94.3	96.4	98.4
70°	88.0	88.0	88.0	85.9	85.9	85.9	83.8	85.9	88.0	90.1	90.1
72.5°	81.7	81.7	81.7	79.6	79.6	79.6	77.5	79.6	79.6	81.7	81.7
75°	71.2	71.2	71.2	71.2	71.2	71.2	69.1	69.1	69.1	71.2	71.2
77.5°	64.9	64.9	64.9	62.8	62.8	62.8	60.7	60.7	60.7	62.8	62.8
80°	54.5	54.5	54.5	52.4	52.4	52.4	50.3	50.3	50.3	52.4	52.4
82.5°	44.0	44.0	44.0	41.9	41.9	41.9	39.8	39.8	39.8	41.9	41.9
85°	35.6	35.6	35.6	35.6	35.6	35.6	33.5	33.5	33.5	35.6	37.7
87.5°	16.8	16.8	18.9	18.9	18.9	18.9	16.8	16.8	14.7	14.7	16.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1
2.5°	1371.9	1376.1	1386.6	1395.0	1405.5	1413.8	1420.1	1428.5	1434.8	1441.1	1445.3
5°	1181.3	1183.4	1193.9	1204.4	1212.8	1223.2	1237.9	1252.6	1267.2	1281.9	1292.4
7.5°	919.5	927.9	940.5	955.1	967.7	980.3	994.9	1011.7	1026.3	1041.0	1055.7
10°	716.3	724.7	737.3	749.9	760.3	772.9	789.7	806.4	823.2	839.9	856.7
12.5°	601.1	611.6	626.3	640.9	653.5	668.2	689.1	708.0	728.9	747.8	768.7
15°	506.9	519.5	538.3	559.3	578.1	597.0	617.9	638.8	657.7	678.6	699.6
17.5°	416.8	429.4	446.1	465.0	481.8	498.5	523.6	546.7	571.8	594.9	617.9
20°	335.1	341.4	358.2	374.9	391.7	408.4	427.3	446.1	465.0	483.8	513.2
22.5°	278.6	282.8	291.1	297.4	305.8	312.1	330.9	349.8	366.6	385.4	412.6
25°	245.1	247.2	253.4	257.6	263.9	268.1	280.7	291.1	303.7	314.2	339.3
27.5°	228.3	230.4	232.5	234.6	236.7	238.8	247.2	255.5	261.8	270.2	293.2
30°	224.1	226.2	232.5	236.7	243.0	247.2	251.3	255.5	259.7	263.9	278.6
32.5°	219.9	222.0	222.0	219.9	219.9	217.8	222.0	224.1	228.3	230.4	243.0
35°	173.8	173.8	175.9	178.0	180.1	182.2	188.5	192.7	199.0	203.2	213.6
37.5°	163.4	163.4	165.5	169.7	171.8	173.8	178.0	182.2	186.4	190.6	201.1
40°	157.1	159.2	161.3	163.4	165.5	167.6	171.8	173.8	178.0	180.1	188.5
42.5°	150.8	150.8	152.9	157.1	159.2	161.3	165.5	167.6	171.8	173.8	182.2
45°	146.6	148.7	150.8	152.9	152.9	155.0	159.2	163.4	165.5	169.7	178.0
47.5°	140.3	140.3	144.5	146.6	150.8	152.9	157.1	159.2	163.4	165.5	173.8
50°	136.1	138.2	142.4	144.5	148.7	150.8	157.1	161.3	167.6	171.8	175.9
52.5°	132.0	134.1	138.2	140.3	144.5	146.6	155.0	163.4	169.7	178.0	178.0
55°	127.8	127.8	132.0	138.2	142.4	146.6	150.8	157.1	161.3	165.5	165.5
57.5°	121.5	123.6	127.8	134.1	138.2	142.4	146.6	150.8	152.9	157.1	155.0
60°	117.3	117.3	123.6	129.9	136.1	142.4	142.4	142.4	140.3	140.3	140.3
62.5°	111.0	113.1	121.5	132.0	140.3	148.7	142.4	136.1	129.9	123.6	125.7
65°	106.8	108.9	113.1	119.4	123.6	127.8	123.6	121.5	117.3	113.1	115.2
67.5°	98.4	100.5	102.6	102.6	104.7	104.7	104.7	104.7	104.7	104.7	106.8
70°	92.2	92.2	92.2	94.3	94.3	94.3	94.3	94.3	94.3	94.3	96.4
72.5°	83.8	83.8	83.8	83.8	83.8	83.8	83.8	83.8	83.8	83.8	85.9
75°	73.3	73.3	73.3	73.3	73.3	73.3	73.3	73.3	73.3	73.3	75.4
77.5°	64.9	64.9	64.9	64.9	64.9	64.9	64.9	64.9	62.8	62.8	64.9
80°	54.5	54.5	54.5	54.5	52.4	52.4	52.4	52.4	52.4	52.4	54.5
82.5°	44.0	44.0	44.0	44.0	41.9	41.9	41.9	41.9	39.8	39.8	41.9
85°	39.8	41.9	41.9	44.0	44.0	44.0	41.9	39.8	37.7	35.6	35.6
87.5°	16.8	16.8	16.8	16.8	14.7	14.7	14.7	14.7	14.7	14.7	14.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1
2.5°	1451.5	1455.7	1459.9	1466.2	1474.6	1480.9	1487.1	1499.7	1514.4	1526.9	1539.5
5°	1302.8	1313.3	1323.8	1336.3	1348.9	1359.4	1371.9	1397.1	1422.2	1445.3	1470.4
7.5°	1068.2	1082.9	1095.5	1116.4	1135.3	1156.2	1175.1	1206.5	1235.8	1267.2	1296.5
10°	873.4	890.2	907.0	934.2	963.5	990.7	1018.0	1043.1	1070.3	1095.5	1120.6
12.5°	789.7	808.5	829.5	846.2	865.1	881.8	898.6	927.9	957.2	986.5	1015.9
15°	720.5	741.5	762.4	783.4	802.2	823.2	842.0	867.2	894.4	919.5	944.7
17.5°	640.9	661.9	684.9	708.0	731.0	754.0	777.1	812.7	848.3	881.8	917.4
20°	540.4	569.7	597.0	628.4	659.8	691.2	722.6	760.3	798.0	833.6	871.3
22.5°	439.9	467.1	494.3	532.0	569.7	605.3	643.0	693.3	741.5	791.7	839.9
25°	366.6	391.7	416.8	458.7	498.5	540.4	580.2	640.9	699.6	760.3	819.0
27.5°	316.3	339.3	362.4	406.3	450.3	492.2	536.2	603.2	668.2	735.2	800.1
30°	293.2	307.9	322.6	364.5	406.3	446.1	488.0	553.0	617.9	682.8	747.8
32.5°	255.5	268.1	280.7	318.4	356.1	391.7	429.4	496.4	561.3	628.4	693.3
35°	226.2	236.7	247.2	282.8	316.3	351.9	385.4	452.4	519.5	586.5	653.5
37.5°	209.5	219.9	228.3	259.7	293.2	324.7	356.1	423.1	488.0	555.1	620.0
40°	196.9	203.2	211.6	243.0	272.3	303.7	333.0	393.8	456.6	517.4	578.1
42.5°	188.5	196.9	203.2	230.4	259.7	287.0	314.2	372.8	431.5	488.0	546.7
45°	186.4	194.8	203.2	226.2	249.3	270.2	293.2	349.8	406.3	462.9	519.5
47.5°	182.2	188.5	196.9	215.7	232.5	251.3	268.1	324.7	381.2	435.7	492.2
50°	180.1	182.2	186.4	203.2	219.9	236.7	253.4	310.0	366.6	423.1	479.7
52.5°	178.0	178.0	178.0	192.7	207.4	219.9	234.6	291.1	349.8	406.3	462.9
55°	165.5	163.4	163.4	178.0	190.6	205.3	217.8	274.4	330.9	385.4	442.0
57.5°	152.9	150.8	148.7	161.3	173.8	186.4	199.0	255.5	314.2	370.7	427.3
60°	140.3	138.2	138.2	150.8	161.3	173.8	184.3	243.0	299.5	358.2	414.7
62.5°	125.7	127.8	127.8	138.2	150.8	161.3	171.8	230.4	291.1	349.8	408.4
65°	115.2	117.3	117.3	129.9	142.4	155.0	167.6	224.1	282.8	339.3	395.9
67.5°	106.8	108.9	108.9	123.6	136.1	150.8	163.4	213.6	266.0	316.3	366.6
70°	98.4	98.4	100.5	115.2	129.9	144.5	159.2	203.2	247.2	289.1	333.0
72.5°	88.0	90.1	92.2	106.8	119.4	134.1	146.6	186.4	226.2	266.0	305.8
75°	77.5	79.6	81.7	94.3	106.8	119.4	132.0	169.7	205.3	243.0	278.6
77.5°	69.1	71.2	73.3	83.8	94.3	104.7	115.2	142.4	171.8	199.0	226.2
80°	56.6	56.6	58.6	67.0	75.4	81.7	90.1	108.9	127.8	144.5	163.4
82.5°	41.9	44.0	44.0	50.3	54.5	60.7	64.9	75.4	83.8	94.3	102.6
85°	35.6	33.5	33.5	37.7	39.8	44.0	46.1	52.4	56.6	62.8	67.0
87.5°	14.7	12.6	12.6	14.7	18.9	20.9	23.0	23.0	25.1	25.1	25.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1
2.5°	1545.8	1550.0	1556.3	1560.5	1570.9	1579.3	1589.8	1598.2	1604.4	1614.9	1610.7
5°	1489.2	1508.1	1526.9	1545.8	1560.5	1575.1	1587.7	1602.4	1619.1	1650.5	1658.9
7.5°	1321.7	1346.8	1369.9	1395.0	1424.3	1453.6	1483.0	1512.3	1539.5	1579.3	1604.4
10°	1156.2	1191.8	1225.3	1260.9	1288.2	1315.4	1340.5	1367.8	1405.5	1445.3	1491.3
12.5°	1051.5	1087.1	1122.7	1158.3	1198.1	1235.8	1275.6	1313.3	1348.9	1380.3	1432.7
15°	982.4	1022.2	1059.9	1097.6	1145.7	1191.8	1240.0	1286.1	1338.4	1380.3	1415.9
17.5°	965.6	1013.8	1059.9	1108.0	1158.3	1208.6	1258.8	1309.1	1361.5	1424.3	1470.4
20°	936.3	1001.2	1066.1	1131.1	1196.0	1258.8	1323.8	1386.6	1455.7	1531.1	1552.1
22.5°	919.5	997.0	1076.6	1154.1	1242.1	1332.2	1420.1	1508.1	1581.4	1638.0	1700.8
25°	917.4	1013.8	1112.2	1208.6	1319.6	1428.5	1539.5	1648.4	1742.7	1799.2	1849.5
27.5°	915.3	1032.6	1147.8	1263.0	1399.2	1533.2	1669.4	1803.4	1891.4	1973.1	2015.0
30°	890.2	1030.5	1173.0	1313.3	1466.2	1619.1	1772.0	1924.9	2015.0	2071.5	2092.5
32.5°	858.8	1024.2	1189.7	1355.2	1529.0	1702.9	1874.6	2048.5	2119.7	2167.9	2151.1
35°	833.6	1015.9	1196.0	1376.1	1560.5	1746.9	1931.2	2115.5	2218.2	2285.2	2258.0
37.5°	810.6	1001.2	1191.8	1382.4	1598.2	1813.9	2029.6	2245.4	2343.8	2415.0	2383.6
40°	783.4	986.5	1191.8	1395.0	1642.1	1887.2	2134.4	2379.4	2507.2	2568.0	2519.8
42.5°	760.3	971.9	1185.5	1397.1	1661.0	1924.9	2188.8	2452.7	2595.2	2681.1	2620.3
45°	731.0	942.6	1152.0	1363.6	1654.7	1945.9	2234.9	2526.1	2691.5	2758.6	2674.8
47.5°	699.6	909.0	1116.4	1323.8	1633.8	1943.8	2253.8	2563.8	2716.7	2796.3	2718.8
50°	689.1	898.6	1105.9	1315.4	1650.5	1987.8	2322.9	2658.0	2769.0	2834.0	2731.3
52.5°	687.0	909.0	1133.2	1355.2	1692.4	2027.5	2364.8	2699.9	2790.0	2859.1	2766.9
55°	680.7	921.6	1160.4	1399.2	1751.1	2105.0	2456.9	2808.8	2898.9	2949.2	2880.0
57.5°	687.0	946.7	1204.4	1464.1	1826.5	2188.8	2551.2	2913.6	3022.5	3058.1	3043.4
60°	691.2	967.7	1242.1	1518.6	1872.6	2226.5	2580.5	2934.5	3047.6	3135.6	3152.3
62.5°	680.7	953.0	1223.2	1495.5	1816.0	2136.5	2456.9	2777.4	2963.8	3093.7	3169.1
65°	649.3	900.7	1154.1	1405.5	1700.8	1998.2	2293.6	2588.9	2785.8	2978.5	3039.2
67.5°	580.2	793.8	1007.5	1221.1	1478.8	1736.4	1991.9	2249.6	2496.7	2683.2	2766.9
70°	502.7	670.3	839.9	1007.5	1242.1	1476.7	1711.3	1945.9	2163.7	2369.0	2448.6
72.5°	437.8	567.6	699.6	829.5	997.0	1162.5	1330.1	1495.5	1753.2	1958.4	2035.9
75°	372.8	467.1	559.3	653.5	768.7	883.9	997.0	1112.2	1294.4	1478.8	1556.3
77.5°	287.0	349.8	410.5	471.3	550.9	628.4	708.0	785.5	913.2	1051.5	1091.3
80°	199.0	234.6	268.1	303.7	366.6	429.4	492.2	555.1	638.8	716.3	777.1
82.5°	123.6	146.6	167.6	188.5	238.8	289.1	337.2	387.5	421.0	425.2	485.9
85°	79.6	94.3	106.8	119.4	148.7	180.1	209.5	238.8	213.6	199.0	236.7
87.5°	31.4	39.8	46.1	52.4	50.3	48.2	46.1	44.0	37.7	33.5	41.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1
2.5°	1614.9	1621.2	1627.5	1631.7	1638.0	1640.1	1642.1	1642.1	1644.2	1646.3	1650.5
5°	1692.4	1705.0	1717.6	1728.0	1740.6	1751.1	1759.4	1769.9	1778.3	1778.3	1776.2
7.5°	1627.5	1658.9	1690.3	1721.7	1753.2	1776.2	1797.1	1820.2	1841.1	1845.3	1849.5
10°	1541.6	1575.1	1606.5	1640.1	1671.5	1707.1	1740.6	1774.1	1809.7	1816.0	1824.4
12.5°	1462.0	1501.8	1541.6	1579.3	1619.1	1644.2	1669.4	1692.4	1717.6	1734.3	1751.1
15°	1459.9	1493.4	1526.9	1558.4	1591.9	1606.5	1621.2	1633.8	1648.4	1648.4	1650.5
17.5°	1508.1	1529.0	1550.0	1568.8	1589.8	1591.9	1596.1	1598.2	1600.3	1594.0	1587.7
20°	1602.4	1610.7	1619.1	1627.5	1635.9	1621.2	1608.6	1594.0	1579.3	1562.6	1547.9
22.5°	1740.6	1721.7	1702.9	1684.0	1665.2	1640.1	1612.8	1587.7	1560.5	1539.5	1518.6
25°	1870.5	1847.4	1824.4	1801.3	1778.3	1723.8	1669.4	1612.8	1558.4	1535.3	1512.3
27.5°	2044.3	2008.7	1973.1	1937.5	1901.9	1828.6	1755.3	1681.9	1608.6	1568.8	1531.1
30°	2086.2	2046.4	2006.6	1964.7	1924.9	1853.7	1784.6	1713.4	1642.1	1596.1	1552.1
32.5°	2146.9	2100.9	2054.8	2008.7	1962.6	1893.5	1824.4	1753.2	1684.0	1642.1	1598.2
35°	2247.5	2195.1	2142.8	2088.3	2035.9	1964.7	1895.6	1824.4	1753.2	1705.0	1658.9
37.5°	2333.4	2272.6	2211.9	2151.1	2090.4	2027.5	1962.6	1899.8	1834.8	1786.7	1740.6
40°	2429.7	2362.7	2295.7	2230.7	2163.7	2105.0	2046.4	1985.7	1927.0	1889.3	1851.6
42.5°	2513.5	2431.8	2352.2	2272.6	2190.9	2151.1	2113.4	2073.6	2033.8	2015.0	1994.0
45°	2572.1	2496.7	2419.2	2343.8	2268.4	2239.1	2209.8	2180.5	2151.1	2170.0	2188.8
47.5°	2597.3	2536.5	2477.9	2419.2	2358.5	2369.0	2379.4	2387.8	2398.3	2423.4	2450.7
50°	2620.3	2586.8	2551.2	2517.7	2482.1	2521.9	2559.6	2599.4	2639.2	2691.5	2743.9
52.5°	2666.4	2647.5	2630.8	2611.9	2593.1	2662.2	2731.3	2800.4	2869.6	2928.2	2986.9
55°	2804.6	2790.0	2775.3	2758.6	2743.9	2842.3	2938.7	3037.1	3135.6	3196.3	3257.1
57.5°	2995.2	2986.9	2976.4	2968.0	2957.5	3053.9	3148.1	3242.4	3338.8	3397.4	3458.1
60°	3139.8	3141.9	3141.9	3144.0	3144.0	3217.3	3290.6	3366.0	3439.3	3489.6	3541.9
62.5°	3217.3	3213.1	3208.9	3204.7	3200.5	3261.3	3322.0	3382.7	3443.5	3481.2	3518.9
65°	3133.5	3156.5	3179.6	3202.6	3225.6	3234.0	3240.3	3248.7	3255.0	3278.0	3301.1
67.5°	2852.8	2898.9	2942.9	2989.0	3032.9	3001.5	2972.2	2940.8	2909.4	2915.7	2919.8
70°	2540.7	2593.1	2647.5	2699.9	2752.3	2679.0	2605.7	2530.2	2456.9	2431.8	2406.7
72.5°	2142.8	2188.8	2237.0	2283.1	2329.2	2239.1	2151.1	2061.1	1971.0	1927.0	1883.0
75°	1638.0	1692.4	1749.0	1803.4	1857.9	1757.3	1654.7	1554.2	1451.5	1422.2	1395.0
77.5°	1193.9	1258.8	1323.8	1388.7	1453.6	1363.6	1273.5	1181.3	1091.3	1074.5	1057.8
80°	869.2	919.5	967.7	1018.0	1066.1	1013.8	961.4	909.0	856.7	854.6	852.5
82.5°	586.5	630.5	672.4	716.3	758.2	737.3	718.4	697.5	676.5	697.5	720.5
85°	301.6	362.4	425.2	485.9	546.7	540.4	536.2	529.9	523.6	550.9	576.0
87.5°	60.7	113.1	165.5	215.7	268.1	255.5	243.0	228.3	215.7	224.1	230.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1
2.5°	1652.6	1654.7	1654.7	1654.7	1654.7	1654.7	1650.5	1648.4	1644.2	1640.1	1633.8
5°	1776.2	1774.1	1765.7	1757.3	1746.9	1738.5	1732.2	1723.8	1717.6	1709.2	1696.6
7.5°	1853.7	1857.9	1843.2	1830.7	1816.0	1801.3	1786.7	1772.0	1757.3	1742.7	1713.4
10°	1830.7	1836.9	1828.6	1820.2	1809.7	1801.3	1784.6	1765.7	1749.0	1730.1	1694.5
12.5°	1765.7	1782.5	1778.3	1774.1	1769.9	1765.7	1755.3	1742.7	1732.2	1719.6	1679.9
15°	1650.5	1650.5	1652.6	1654.7	1654.7	1656.8	1658.9	1661.0	1663.1	1665.2	1642.1
17.5°	1581.4	1575.1	1575.1	1575.1	1575.1	1575.1	1583.5	1594.0	1602.4	1610.7	1604.4
20°	1531.1	1516.5	1514.4	1514.4	1512.3	1510.2	1524.9	1541.6	1556.3	1570.9	1579.3
22.5°	1497.6	1476.7	1474.6	1472.5	1470.4	1468.3	1487.1	1506.0	1524.9	1543.7	1573.0
25°	1489.2	1466.2	1468.3	1470.4	1470.4	1472.5	1487.1	1501.8	1516.5	1531.1	1581.4
27.5°	1491.3	1453.6	1455.7	1457.8	1457.8	1459.9	1483.0	1503.9	1526.9	1547.9	1610.7
30°	1506.0	1462.0	1457.8	1453.6	1449.4	1445.3	1476.7	1508.1	1539.5	1570.9	1619.1
32.5°	1556.3	1514.4	1503.9	1493.4	1483.0	1472.5	1510.2	1545.8	1583.5	1619.1	1658.9
35°	1610.7	1564.6	1560.5	1556.3	1550.0	1545.8	1579.3	1614.9	1648.4	1681.9	1717.6
37.5°	1692.4	1646.3	1642.1	1635.9	1631.7	1625.4	1663.1	1698.7	1736.4	1772.0	1803.4
40°	1813.9	1776.2	1774.1	1774.1	1772.0	1769.9	1799.2	1830.7	1860.0	1889.3	1910.3
42.5°	1975.2	1956.3	1962.6	1971.0	1977.3	1983.6	2006.6	2031.7	2054.8	2077.8	2071.5
45°	2207.7	2226.5	2228.6	2230.7	2232.8	2234.9	2241.2	2249.6	2255.9	2262.1	2237.0
47.5°	2475.8	2500.9	2513.5	2526.1	2536.5	2549.1	2540.7	2530.2	2521.9	2511.4	2448.6
50°	2794.2	2846.5	2844.4	2842.3	2838.2	2836.1	2819.3	2802.5	2783.7	2766.9	2674.8
52.5°	3045.5	3104.2	3114.6	3125.1	3135.6	3146.1	3114.6	3083.2	3049.7	3018.3	2903.1
55°	3315.7	3376.5	3378.6	3380.6	3380.6	3382.7	3338.8	3294.8	3248.7	3204.7	3085.3
57.5°	3516.8	3575.4	3569.2	3565.0	3558.7	3552.4	3500.0	3447.7	3395.3	3342.9	3223.6
60°	3592.2	3642.5	3629.9	3617.3	3602.7	3590.1	3550.3	3510.5	3468.6	3428.8	3313.6
62.5°	3556.6	3594.3	3575.4	3558.7	3539.8	3521.0	3470.7	3418.3	3368.1	3315.7	3231.9
65°	3322.0	3345.0	3319.9	3296.9	3273.8	3248.7	3206.8	3164.9	3120.9	3079.0	3022.5
67.5°	2926.1	2930.3	2928.2	2926.1	2924.0	2921.9	2861.2	2800.4	2737.6	2676.9	2672.7
70°	2383.6	2358.5	2362.7	2369.0	2373.2	2377.3	2331.3	2287.3	2241.2	2195.1	2216.1
72.5°	1839.0	1795.1	1805.5	1818.1	1828.6	1839.0	1801.3	1765.7	1728.0	1690.3	1719.6
75°	1365.7	1338.4	1348.9	1361.5	1371.9	1382.4	1367.8	1353.1	1336.3	1321.7	1348.9
77.5°	1041.0	1024.2	1026.3	1026.3	1028.4	1028.4	1030.5	1034.7	1036.8	1038.9	1068.2
80°	848.3	846.2	844.1	842.0	837.8	835.7	856.7	877.6	898.6	919.5	934.2
82.5°	741.5	762.4	749.9	739.4	726.8	714.3	733.1	752.0	770.8	789.7	783.4
85°	603.2	628.4	605.3	582.3	557.2	534.1	550.9	565.5	582.3	597.0	588.6
87.5°	238.8	245.1	207.4	171.8	134.1	96.4	152.9	207.4	263.9	318.4	326.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1	1508.1
2.5°	1627.5	1619.1	1612.8	1610.7	1606.5	1604.4	1600.3	1596.1	1589.8	1585.6	1579.3
5°	1681.9	1669.4	1654.7	1633.8	1614.9	1594.0	1573.0	1554.2	1535.3	1514.4	1495.5
7.5°	1684.0	1654.7	1625.4	1598.2	1568.8	1541.6	1512.3	1487.1	1459.9	1432.7	1407.6
10°	1661.0	1625.4	1589.8	1554.2	1520.7	1485.1	1449.4	1420.1	1388.7	1357.3	1328.0
12.5°	1642.1	1602.4	1562.6	1520.7	1480.9	1439.0	1397.1	1367.8	1338.4	1309.1	1279.8
15°	1619.1	1594.0	1570.9	1533.2	1495.5	1457.8	1420.1	1380.3	1342.6	1302.8	1263.0
17.5°	1600.3	1594.0	1587.7	1562.6	1537.4	1510.2	1485.1	1445.3	1405.5	1363.6	1323.8
20°	1589.8	1598.2	1606.5	1594.0	1581.4	1566.7	1554.2	1524.9	1495.5	1464.1	1434.8
22.5°	1602.4	1633.8	1663.1	1665.2	1669.4	1671.5	1673.6	1646.3	1619.1	1589.8	1562.6
25°	1631.7	1681.9	1732.2	1759.4	1786.7	1816.0	1843.2	1826.5	1809.7	1793.0	1776.2
27.5°	1671.5	1734.3	1797.1	1836.9	1874.6	1914.4	1954.2	1952.1	1950.1	1945.9	1943.8
30°	1665.2	1713.4	1761.5	1809.7	1857.9	1906.1	1954.2	1979.4	2002.4	2027.5	2052.7
32.5°	1700.8	1740.6	1782.5	1832.8	1883.0	1935.4	1985.7	2038.0	2088.3	2140.7	2193.0
35°	1755.3	1790.9	1828.6	1883.0	1939.6	1994.0	2050.6	2113.4	2178.4	2243.3	2306.1
37.5°	1836.9	1868.4	1901.9	1948.0	1996.1	2042.2	2090.4	2182.5	2274.7	2369.0	2461.1
40°	1931.2	1952.1	1973.1	2017.1	2061.1	2105.0	2149.0	2264.2	2379.4	2494.6	2609.8
42.5°	2067.3	2061.1	2054.8	2090.4	2128.1	2163.7	2201.4	2306.1	2410.9	2515.6	2620.3
45°	2211.9	2186.7	2161.6	2178.4	2197.2	2214.0	2232.8	2339.6	2446.5	2555.4	2662.2
47.5°	2385.7	2322.9	2260.0	2245.4	2230.7	2214.0	2199.3	2314.5	2429.7	2547.0	2662.2
50°	2582.6	2488.4	2396.2	2358.5	2318.7	2281.0	2241.2	2335.5	2431.8	2528.2	2622.4
52.5°	2787.9	2670.6	2555.4	2496.7	2438.1	2377.3	2318.7	2398.3	2480.0	2561.7	2641.3
55°	2963.8	2844.4	2722.9	2653.8	2584.7	2515.6	2446.5	2526.1	2605.7	2685.2	2764.8
57.5°	3104.2	2984.8	2865.4	2800.4	2733.4	2668.5	2601.5	2676.9	2754.4	2831.9	2907.3
60°	3200.5	3085.3	2970.1	2907.3	2844.4	2781.6	2718.8	2808.8	2898.9	2991.1	3081.1
62.5°	3150.2	3066.5	2982.7	2955.4	2928.2	2898.9	2871.7	2957.5	3041.3	3127.2	3213.1
65°	2965.9	2909.4	2852.8	2880.0	2909.4	2936.6	2965.9	3022.5	3079.0	3137.7	3194.2
67.5°	2666.4	2662.2	2655.9	2716.7	2777.4	2840.2	2901.0	2938.7	2974.3	3012.0	3049.7
70°	2237.0	2260.0	2281.0	2385.7	2490.5	2595.2	2699.9	2714.6	2729.2	2743.9	2758.6
72.5°	1751.1	1780.4	1811.8	1950.1	2086.2	2224.4	2362.7	2354.3	2345.9	2335.5	2327.1
75°	1378.2	1405.5	1434.8	1562.6	1690.3	1818.1	1945.9	1910.3	1876.7	1841.1	1805.5
77.5°	1099.7	1129.0	1160.4	1279.8	1399.2	1520.7	1640.1	1554.2	1468.3	1382.4	1296.5
80°	946.7	961.4	974.0	1055.7	1135.3	1216.9	1298.6	1210.7	1120.6	1030.5	942.6
82.5°	777.1	768.7	762.4	810.6	858.8	907.0	955.1	871.3	787.6	701.7	617.9
85°	580.2	571.8	563.4	588.6	613.7	640.9	666.1	569.7	473.4	374.9	278.6
87.5°	337.2	345.6	354.0	381.2	408.4	437.8	465.0	366.6	268.1	167.6	69.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1508.1	1508.1
2.5°	1566.7	1556.3
5°	1480.9	1466.2
7.5°	1386.6	1367.8
10°	1300.7	1275.6
12.5°	1246.3	1214.9
15°	1225.3	1187.6
17.5°	1288.2	1252.6
20°	1384.5	1336.3
22.5°	1501.8	1443.2
25°	1705.0	1633.8
27.5°	1870.5	1797.1
30°	1973.1	1893.5
32.5°	2086.2	1981.5
35°	2203.5	2103.0
37.5°	2345.9	2232.8
40°	2492.5	2375.2
42.5°	2542.8	2467.4
45°	2591.0	2519.8
47.5°	2601.5	2542.8
50°	2611.9	2603.6
52.5°	2641.3	2639.2
55°	2766.9	2769.0
57.5°	2921.9	2934.5
60°	3064.4	3049.7
62.5°	3137.7	3062.3
65°	3087.4	2982.7
67.5°	2936.6	2823.5
70°	2605.7	2452.7
72.5°	2193.0	2059.0
75°	1690.3	1577.2
77.5°	1202.3	1108.0
80°	846.2	752.0
82.5°	542.5	467.1
85°	245.1	213.6
87.5°	69.1	67.0
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671884

CATALOG NUMBER: CCP-SA-2B-835-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)