

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P672867

Luminaire Tested: **CCP-SA1E-827-U-RW**

Issue Date: 04/16/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P672867  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA1E-827-U-RW  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/ RW  
distribution lens  
Light Source: (16) 2700K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5112.5 lumens  
Efficiency: N/A  
Efficacy: 91.1 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type II - Medium  
BUG Rating: B2 - U0 - G2


Input Watts (W): 56.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P672867

CATALOG NUMBER: CCP-SA1E-827-U-RW

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 2.7 fc  
 Type II - Medium - N/A

REPORT NUMBER: P672867  
CATALOG NUMBER: CCP-SA1E-827-U-RW

## Luminous Intensity Polar Plot



REPORT NUMBER: P672867

CATALOG NUMBER: CCP-SA1E-827-U-RW


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 2556.3   | 0.0    | 2556.3 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 2556.3   | 0.0    | 2556.3 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 5112.5   | 0.0    | 5112.5 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 51.5   | 1.0       |
| 10°-20°   | 173.4  | 3.4       |
| 20°-30°   | 338.6  | 6.6       |
| 30°-40°   | 584.2  | 11.4      |
| 40°-50°   | 946.3  | 18.5      |
| 50°-60°   | 1287.0 | 25.2      |
| 60°-70°   | 1187.3 | 23.2      |
| 70°-80°   | 496.8  | 9.7       |
| 80°-90°   | 47.4   | 0.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 5112.5 | 100.0     |
| 0°-180°   | 5112.5 | 100.0     |



REPORT NUMBER: P672867


CATALOG NUMBER: CCP-SA1E-827-U-RW

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 281.8  | 5.5       |                         |      |         |
| FM   | (30°-60°)   | 1408.7 | 27.6      |                         |      |         |
| FH   | (60°-80°)   | 842.0  | 16.5      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 23.7   | 0.5       |                         |      | G1/100  |
| BL   | (0°-30°)    | 281.8  | 5.5       | B1/500                  |      |         |
| BM   | (30°-60°)   | 1408.7 | 27.6      | B2/2500                 |      |         |
| BH   | (60°-80°)   | 842.0  | 16.5      | B2/1000                 |      | G2/1000 |
| BVH  | (80°-90°)   | 23.7   | 0.5       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G2**

Type II Medium



REPORT NUMBER: P672867

CATALOG NUMBER: CCP-SA1E-827-U-RW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 520.1  | 520.1  | 520.1  | 520.1  | 520.1  | 520.1  | 520.1  | 520.1  | 520.1  | 520.1  | 520.1  |
| 2.5°  | 516.8  | 516.8  | 518.3  | 520.1  | 520.9  | 522.3  | 522.7  | 522.7  | 524.9  | 524.5  | 524.9  |
| 5°    | 515.3  | 515.3  | 517.9  | 521.2  | 524.9  | 529.3  | 533.7  | 536.3  | 541.8  | 542.9  | 543.3  |
| 7.5°  | 516.8  | 517.2  | 520.9  | 526.4  | 532.6  | 540.7  | 549.2  | 556.1  | 565.3  | 568.6  | 570.8  |
| 10°   | 522.3  | 522.7  | 527.5  | 535.2  | 544.8  | 556.5  | 568.6  | 579.7  | 594.4  | 601.0  | 602.1  |
| 12.5° | 530.8  | 531.2  | 538.1  | 550.6  | 564.2  | 578.9  | 592.5  | 606.5  | 624.9  | 634.8  | 637.0  |
| 15°   | 543.6  | 542.5  | 553.6  | 572.0  | 591.1  | 609.4  | 621.6  | 635.2  | 654.7  | 667.5  | 670.8  |
| 17.5° | 561.3  | 562.0  | 575.6  | 599.2  | 622.7  | 641.4  | 653.6  | 661.3  | 678.2  | 691.4  | 694.7  |
| 20°   | 583.3  | 586.7  | 603.9  | 631.1  | 658.7  | 678.5  | 687.0  | 685.9  | 695.5  | 706.9  | 709.4  |
| 22.5° | 614.6  | 616.8  | 637.7  | 668.3  | 699.9  | 720.5  | 723.8  | 711.6  | 711.3  | 718.6  | 721.9  |
| 25°   | 651.3  | 653.2  | 675.2  | 710.5  | 744.0  | 765.7  | 762.4  | 741.4  | 730.4  | 730.7  | 733.0  |
| 27.5° | 694.4  | 698.0  | 720.8  | 756.8  | 791.4  | 811.2  | 806.5  | 776.0  | 754.3  | 747.7  | 746.2  |
| 30°   | 750.2  | 754.3  | 777.4  | 812.0  | 842.5  | 860.1  | 852.8  | 814.2  | 781.8  | 770.8  | 768.6  |
| 32.5° | 823.0  | 822.6  | 846.5  | 880.0  | 901.3  | 912.7  | 898.4  | 854.6  | 813.8  | 799.1  | 796.2  |
| 35°   | 898.0  | 901.7  | 925.2  | 957.5  | 973.7  | 974.5  | 951.7  | 902.4  | 853.9  | 828.5  | 823.0  |
| 37.5° | 982.5  | 984.4  | 1011.6 | 1042.1 | 1052.7 | 1046.9 | 1013.0 | 958.3  | 902.4  | 875.6  | 866.0  |
| 40°   | 1069.3 | 1071.1 | 1102.7 | 1132.1 | 1143.9 | 1129.9 | 1085.5 | 1020.0 | 959.7  | 930.3  | 924.8  |
| 42.5° | 1149.8 | 1154.6 | 1189.9 | 1224.4 | 1235.8 | 1219.6 | 1166.0 | 1087.7 | 1020.4 | 992.1  | 984.7  |
| 45°   | 1216.7 | 1221.8 | 1261.5 | 1305.6 | 1325.9 | 1312.6 | 1252.0 | 1163.8 | 1090.2 | 1059.7 | 1047.2 |
| 47.5° | 1267.0 | 1273.7 | 1315.9 | 1368.9 | 1408.2 | 1405.6 | 1343.5 | 1244.3 | 1165.2 | 1129.2 | 1117.8 |
| 50°   | 1301.6 | 1308.6 | 1354.2 | 1411.1 | 1470.3 | 1490.2 | 1436.5 | 1333.2 | 1248.7 | 1208.2 | 1200.5 |
| 52.5° | 1304.2 | 1310.4 | 1362.6 | 1433.6 | 1512.6 | 1556.3 | 1528.0 | 1426.9 | 1340.6 | 1298.7 | 1293.1 |
| 55°   | 1246.8 | 1251.2 | 1320.7 | 1415.2 | 1529.9 | 1607.1 | 1611.5 | 1529.1 | 1438.7 | 1396.4 | 1393.9 |
| 57.5° | 1115.2 | 1121.5 | 1204.6 | 1329.5 | 1501.2 | 1639.8 | 1683.9 | 1636.1 | 1549.7 | 1510.0 | 1507.8 |
| 60°   | 900.9  | 909.0  | 1003.9 | 1170.0 | 1397.5 | 1631.3 | 1745.3 | 1736.4 | 1671.0 | 1632.4 | 1630.9 |
| 62.5° | 635.5  | 638.5  | 737.4  | 920.4  | 1194.6 | 1541.6 | 1775.0 | 1834.2 | 1796.7 | 1757.8 | 1760.0 |
| 65°   | 373.5  | 377.5  | 449.9  | 614.6  | 906.1  | 1335.4 | 1723.6 | 1902.2 | 1897.4 | 1861.8 | 1865.5 |
| 67.5° | 197.4  | 197.4  | 233.8  | 336.0  | 569.7  | 999.8  | 1518.8 | 1864.7 | 1927.2 | 1896.0 | 1897.8 |
| 70°   | 136.4  | 136.0  | 142.6  | 168.7  | 275.3  | 619.7  | 1136.2 | 1668.4 | 1866.6 | 1854.8 | 1859.6 |
| 72.5° | 115.4  | 114.7  | 115.1  | 118.7  | 140.0  | 280.1  | 689.9  | 1285.1 | 1664.0 | 1682.0 | 1686.1 |
| 75°   | 101.1  | 100.0  | 99.2   | 98.5   | 100.3  | 127.2  | 314.6  | 792.9  | 1233.6 | 1346.8 | 1344.6 |
| 77.5° | 87.1   | 86.4   | 85.6   | 83.1   | 80.1   | 83.4   | 128.7  | 356.6  | 634.4  | 748.8  | 740.7  |
| 80°   | 71.7   | 71.7   | 72.8   | 69.1   | 63.6   | 61.4   | 76.8   | 133.1  | 210.6  | 219.8  | 202.2  |
| 82.5° | 56.2   | 56.2   | 61.8   | 56.6   | 50.0   | 44.5   | 53.3   | 70.9   | 85.6   | 69.5   | 56.6   |
| 85°   | 39.7   | 40.1   | 51.5   | 47.1   | 38.6   | 25.7   | 33.1   | 42.3   | 48.2   | 30.5   | 23.9   |
| 87.5° | 16.2   | 17.3   | 32.0   | 25.4   | 24.3   | 12.9   | 15.4   | 18.7   | 23.9   | 12.9   | 10.3   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

STREETWORKS

Report Number: SP1-2101-121-9

Luminaire Tested: IFLD-S-SA2A-827-U-T2

Test Date: 03/05/2021


### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2101-121-9  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 03/05/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **IFLD-S-SA2A-827-U-T2**  
 Description: STREETWORKS INF FLOOD

PROGRAMMED @ 615mA.

### Spectral Parameters

|                           |        |           |      |      |      |
|---------------------------|--------|-----------|------|------|------|
| CCT (K):                  | 2709   | CRI (Ra): | 82.1 |      |      |
| CIE u':                   | 0.2620 | R1:       | 80.4 | R9:  | 4.5  |
| CIE v':                   | 0.5273 | R2:       | 91.2 | R10: | 81.3 |
| Duv:                      | 0.0001 | R3:       | 95.2 | R11: | 81.0 |
| CIE x:                    | 0.4591 | R4:       | 80.5 | R12: | 79.0 |
| CIE y:                    | 0.4107 | R5:       | 81.2 | R13: | 82.9 |
| CIE z:                    | 0.1301 | R6:       | 90.9 | R14: | 97.9 |
| Peak Wavelength (nm):     | 606    | R7:       | 81.1 |      |      |
| Dominant Wavelength (nm): | 584    | R8:       | 56.0 |      |      |
| Purity:                   | 61.2   |           |      |      |      |
| Rf:                       | 85.2   |           |      |      |      |
| Rg:                       | 96.4   |           |      |      |      |



### Test Conditions


Stabilization Time: 60M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 24.9/31%  
 Sphere Temperature (°C): 24.4

REPORT NUMBER: SP1-2101-121-9


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2101-121-9

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**




CCT = 2709K  
 CIE  $x$  = 0.4591  
 CIE  $y$  = 0.4107  
 Duv = 0.0001

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2101-121-9

### Photopic Flux vs. Wavelength




#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2013             | 0.0              | 490       | 33356            | 4.7              | 620       | 150993           | 39.3             | 750       | 7593             | 0.0              | 880       | 2373             | 0.0              |
| 365       | 1908             | 0.0              | 495       | 40031            | 7.3              | 625       | 145077           | 32.0             | 755       | 6765             | 0.0              | 885       | 2481             | 0.0              |
| 370       | 1889             | 0.0              | 500       | 46287            | 10.2             | 630       | 136072           | 24.6             | 760       | 6000             | 0.0              | 890       | 2394             | 0.0              |
| 375       | 2095             | 0.0              | 505       | 51783            | 14.5             | 635       | 126417           | 19.0             | 765       | 5393             | 0.0              | 895       | 2574             | 0.0              |
| 380       | 2228             | 0.0              | 510       | 56588            | 19.4             | 640       | 116412           | 13.9             | 770       | 5030             | 0.0              | 900       | 2048             | 0.0              |
| 385       | 2074             | 0.0              | 515       | 60751            | 25.2             | 645       | 107525           | 10.4             | 775       | 4491             | 0.0              | 905       | 2381             | 0.0              |
| 390       | 1820             | 0.0              | 520       | 63966            | 31.0             | 650       | 97857            | 7.2              | 780       | 3943             | 0.0              | 910       | 2017             | 0.0              |
| 395       | 1728             | 0.0              | 525       | 66683            | 35.8             | 655       | 88582            | 5.1              | 785       | 3682             | 0.0              | 915       | 1904             | 0.0              |
| 400       | 1557             | 0.0              | 530       | 69869            | 41.1             | 660       | 79462            | 3.3              | 790       | 3402             | 0.0              | 920       | 2254             | 0.0              |
| 405       | 1644             | 0.0              | 535       | 72510            | 45.0             | 665       | 70606            | 2.2              | 795       | 3156             | 0.0              | 925       | 1998             | 0.0              |
| 410       | 2044             | 0.0              | 540       | 75299            | 49.1             | 670       | 61774            | 1.4              | 800       | 3062             | 0.0              | 930       | 1776             | 0.0              |
| 415       | 3009             | 0.0              | 545       | 79297            | 52.8             | 675       | 53771            | 0.9              | 805       | 2712             | 0.0              | 935       | 2086             | 0.0              |
| 420       | 4992             | 0.0              | 550       | 84946            | 57.7             | 680       | 46786            | 0.5              | 810       | 2896             | 0.0              | 940       | 1766             | 0.0              |
| 425       | 8631             | 0.0              | 555       | 90790            | 62.0             | 685       | 40747            | 0.4              | 815       | 2605             | 0.0              | 945       | 1738             | 0.0              |
| 430       | 14680            | 0.1              | 560       | 98231            | 66.8             | 690       | 35400            | 0.2              | 820       | 2901             | 0.0              | 950       | 2303             | 0.0              |
| 435       | 23899            | 0.3              | 565       | 105738           | 70.3             | 695       | 30445            | 0.1              | 825       | 2541             | 0.0              | 955       | 2567             | 0.0              |
| 440       | 38159            | 0.6              | 570       | 114034           | 74.1             | 700       | 26278            | 0.1              | 830       | 2014             | 0.0              | 960       | 2492             | 0.0              |
| 445       | 53061            | 1.1              | 575       | 123632           | 76.9             | 705       | 22703            | 0.0              | 835       | 2258             | 0.0              | 965       | 810              | 0.0              |
| 450       | 53893            | 1.4              | 580       | 132443           | 78.7             | 710       | 19853            | 0.0              | 840       | 2203             | 0.0              | 970       | 3201             | 0.0              |
| 455       | 41221            | 1.4              | 585       | 141502           | 78.6             | 715       | 17730            | 0.0              | 845       | 2073             | 0.0              | 975       | 1858             | 0.0              |
| 460       | 32969            | 1.4              | 590       | 148917           | 77.0             | 720       | 15616            | 0.0              | 850       | 2096             | 0.0              | 980       | 1769             | 0.0              |
| 465       | 28048            | 1.4              | 595       | 154326           | 73.2             | 725       | 13986            | 0.0              | 855       | 2751             | 0.0              | 985       | 1043             | 0.0              |
| 470       | 23347            | 1.5              | 600       | 159208           | 68.6             | 730       | 12029            | 0.0              | 860       | 2501             | 0.0              | 990       | 2950             | 0.0              |
| 475       | 22136            | 1.7              | 605       | 161290           | 62.5             | 735       | 10461            | 0.0              | 865       | 2512             | 0.0              | 995       | 1643             | 0.0              |
| 480       | 24192            | 2.3              | 610       | 159549           | 54.8             | 740       | 9230             | 0.0              | 870       | 2913             | 0.0              | 1000      | 292              | 0.0              |
| 485       | 28231            | 3.3              | 615       | 156663           | 47.3             | 745       | 8376             | 0.0              | 875       | 2299             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-9


### Scotopic Flux vs. Wavelength


**Scotopic Lumens: 8911.3**
**S/P: 1.22**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2013             | 0.0              | 490       | 33356            | 51.4             | 620       | 150993           | 1.9              | 750       | 7593             | 0.0              | 880       | 2373             | 0.0              |
| 365       | 1908             | 0.0              | 495       | 40031            | 64.7             | 625       | 145077           | 1.2              | 755       | 6765             | 0.0              | 885       | 2481             | 0.0              |
| 370       | 1889             | 0.0              | 500       | 46287            | 77.4             | 630       | 136072           | 0.8              | 760       | 6000             | 0.0              | 890       | 2394             | 0.0              |
| 375       | 2095             | 0.0              | 505       | 51783            | 88.0             | 635       | 126417           | 0.5              | 765       | 5393             | 0.0              | 895       | 2574             | 0.0              |
| 380       | 2228             | 0.0              | 510       | 56588            | 95.9             | 640       | 116412           | 0.3              | 770       | 5030             | 0.0              | 900       | 2048             | 0.0              |
| 385       | 2074             | 0.0              | 515       | 60751            | 100.7            | 645       | 107525           | 0.2              | 775       | 4491             | 0.0              | 905       | 2381             | 0.0              |
| 390       | 1820             | 0.0              | 520       | 63966            | 101.7            | 650       | 97857            | 0.1              | 780       | 3943             | 0.0              | 910       | 2017             | 0.0              |
| 395       | 1728             | 0.0              | 525       | 66683            | 99.8             | 655       | 88582            | 0.1              | 785       | 3682             | 0.0              | 915       | 1904             | 0.0              |
| 400       | 1557             | 0.0              | 530       | 69869            | 96.3             | 660       | 79462            | 0.0              | 790       | 3402             | 0.0              | 920       | 2254             | 0.0              |
| 405       | 1644             | 0.1              | 535       | 72510            | 90.4             | 665       | 70606            | 0.0              | 795       | 3156             | 0.0              | 925       | 1998             | 0.0              |
| 410       | 2044             | 0.1              | 540       | 75299            | 83.2             | 670       | 61774            | 0.0              | 800       | 3062             | 0.0              | 930       | 1776             | 0.0              |
| 415       | 3009             | 0.3              | 545       | 79297            | 76.0             | 675       | 53771            | 0.0              | 805       | 2712             | 0.0              | 935       | 2086             | 0.0              |
| 420       | 4992             | 0.8              | 550       | 84946            | 69.5             | 680       | 46786            | 0.0              | 810       | 2896             | 0.0              | 940       | 1766             | 0.0              |
| 425       | 8631             | 2.1              | 555       | 90790            | 62.0             | 685       | 40747            | 0.0              | 815       | 2605             | 0.0              | 945       | 1738             | 0.0              |
| 430       | 14680            | 5.0              | 560       | 98231            | 54.9             | 690       | 35400            | 0.0              | 820       | 2901             | 0.0              | 950       | 2303             | 0.0              |
| 435       | 23899            | 10.7             | 565       | 105738           | 47.4             | 695       | 30445            | 0.0              | 825       | 2541             | 0.0              | 955       | 2567             | 0.0              |
| 440       | 38159            | 21.3             | 570       | 114034           | 40.2             | 700       | 26278            | 0.0              | 830       | 2014             | 0.0              | 960       | 2492             | 0.0              |
| 445       | 53061            | 35.5             | 575       | 123632           | 33.7             | 705       | 22703            | 0.0              | 835       | 2258             | 0.0              | 965       | 810              | 0.0              |
| 450       | 53893            | 41.8             | 580       | 132443           | 27.3             | 710       | 19853            | 0.0              | 840       | 2203             | 0.0              | 970       | 3201             | 0.0              |
| 455       | 41221            | 36.0             | 585       | 141502           | 21.6             | 715       | 17730            | 0.0              | 845       | 2073             | 0.0              | 975       | 1858             | 0.0              |
| 460       | 32969            | 31.8             | 590       | 148917           | 16.6             | 720       | 15616            | 0.0              | 850       | 2096             | 0.0              | 980       | 1769             | 0.0              |
| 465       | 28048            | 29.6             | 595       | 154326           | 12.3             | 725       | 13986            | 0.0              | 855       | 2751             | 0.0              | 985       | 1043             | 0.0              |
| 470       | 23347            | 26.9             | 600       | 159208           | 9.0              | 730       | 12029            | 0.0              | 860       | 2501             | 0.0              | 990       | 2950             | 0.0              |
| 475       | 22136            | 27.7             | 605       | 161290           | 6.3              | 735       | 10461            | 0.0              | 865       | 2512             | 0.0              | 995       | 1643             | 0.0              |
| 480       | 24192            | 32.7             | 610       | 159549           | 4.3              | 740       | 9230             | 0.0              | 870       | 2913             | 0.0              | 1000      | 292              | 0.0              |
| 485       | 28231            | 40.9             | 615       | 156663           | 2.9              | 745       | 8376             | 0.0              | 875       | 2299             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-9

### Melanopic Flux vs. Wavelength



**Melanopic Lumens: 3277.6**

**M/P: 0.45**


| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 2013             | 0.0              | 490       | 33356            | 27.8             | 620       | 150993           | 0.1              | 750       | 7593             | 0.0              | 880       | 2373             | 0.0              |
| 365       | 1908             | 0.0              | 495       | 40031            | 33.0             | 625       | 145077           | 0.1              | 755       | 6765             | 0.0              | 885       | 2481             | 0.0              |
| 370       | 1889             | 0.0              | 500       | 46287            | 37.2             | 630       | 136072           | 0.0              | 760       | 6000             | 0.0              | 890       | 2394             | 0.0              |
| 375       | 2095             | 0.0              | 505       | 51783            | 39.7             | 635       | 126417           | 0.0              | 765       | 5393             | 0.0              | 895       | 2574             | 0.0              |
| 380       | 2228             | 0.0              | 510       | 56588            | 40.6             | 640       | 116412           | 0.0              | 770       | 5030             | 0.0              | 900       | 2048             | 0.0              |
| 385       | 2074             | 0.0              | 515       | 60751            | 39.7             | 645       | 107525           | 0.0              | 775       | 4491             | 0.0              | 905       | 2381             | 0.0              |
| 390       | 1820             | 0.0              | 520       | 63966            | 37.2             | 650       | 97857            | 0.0              | 780       | 3943             | 0.0              | 910       | 2017             | 0.0              |
| 395       | 1728             | 0.0              | 525       | 66683            | 33.8             | 655       | 88582            | 0.0              | 785       | 3682             | 0.0              | 915       | 1904             | 0.0              |
| 400       | 1557             | 0.0              | 530       | 69869            | 30.2             | 660       | 79462            | 0.0              | 790       | 3402             | 0.0              | 920       | 2254             | 0.0              |
| 405       | 1644             | 0.0              | 535       | 72510            | 26.1             | 665       | 70606            | 0.0              | 795       | 3156             | 0.0              | 925       | 1998             | 0.0              |
| 410       | 2044             | 0.1              | 540       | 75299            | 22.0             | 670       | 61774            | 0.0              | 800       | 3062             | 0.0              | 930       | 1776             | 0.0              |
| 415       | 3009             | 0.2              | 545       | 79297            | 18.4             | 675       | 53771            | 0.0              | 805       | 2712             | 0.0              | 935       | 2086             | 0.0              |
| 420       | 4992             | 0.6              | 550       | 84946            | 15.2             | 680       | 46786            | 0.0              | 810       | 2896             | 0.0              | 940       | 1766             | 0.0              |
| 425       | 8631             | 1.3              | 555       | 90790            | 12.2             | 685       | 40747            | 0.0              | 815       | 2605             | 0.0              | 945       | 1738             | 0.0              |
| 430       | 14680            | 3.1              | 560       | 98231            | 9.7              | 690       | 35400            | 0.0              | 820       | 2901             | 0.0              | 950       | 2303             | 0.0              |
| 435       | 23899            | 6.4              | 565       | 105738           | 7.4              | 695       | 30445            | 0.0              | 825       | 2541             | 0.0              | 955       | 2567             | 0.0              |
| 440       | 38159            | 12.8             | 570       | 114034           | 5.6              | 700       | 26278            | 0.0              | 830       | 2014             | 0.0              | 960       | 2492             | 0.0              |
| 445       | 53061            | 20.9             | 575       | 123632           | 4.1              | 705       | 22703            | 0.0              | 835       | 2258             | 0.0              | 965       | 810              | 0.0              |
| 450       | 53893            | 24.8             | 580       | 132443           | 3.0              | 710       | 19853            | 0.0              | 840       | 2203             | 0.0              | 970       | 3201             | 0.0              |
| 455       | 41221            | 21.6             | 585       | 141502           | 2.1              | 715       | 17730            | 0.0              | 845       | 2073             | 0.0              | 975       | 1858             | 0.0              |
| 460       | 32969            | 19.4             | 590       | 148917           | 1.5              | 720       | 15616            | 0.0              | 850       | 2096             | 0.0              | 980       | 1769             | 0.0              |
| 465       | 28048            | 18.3             | 595       | 154326           | 1.0              | 725       | 13986            | 0.0              | 855       | 2751             | 0.0              | 985       | 1043             | 0.0              |
| 470       | 23347            | 16.7             | 600       | 159208           | 0.7              | 730       | 12029            | 0.0              | 860       | 2501             | 0.0              | 990       | 2950             | 0.0              |
| 475       | 22136            | 16.9             | 605       | 161290           | 0.4              | 735       | 10461            | 0.0              | 865       | 2512             | 0.0              | 995       | 1643             | 0.0              |
| 480       | 24192            | 19.4             | 610       | 159549           | 0.3              | 740       | 9230             | 0.0              | 870       | 2913             | 0.0              | 1000      | 292              | 0.0              |
| 485       | 28231            | 23.3             | 615       | 156663           | 0.2              | 745       | 8376             | 0.0              | 875       | 2299             | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2101-121-9





TM-30-18

### Summary

$R_f = 85.2$   
 $R_g = 96.4$   
 CIE  $R_a = 82.1$   
 $R_9 = 4.5$







### Color Vector Graphics





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 83 | CES51 = 95 | CES76 = 83 |
| CES02 = 64 | CES27 = 95 | CES52 = 94 | CES77 = 85 |
| CES03 = 31 | CES28 = 94 | CES53 = 89 | CES78 = 82 |
| CES04 = 71 | CES29 = 82 | CES54 = 92 | CES79 = 89 |
| CES05 = 50 | CES30 = 87 | CES55 = 92 | CES80 = 89 |
| CES06 = 52 | CES31 = 85 | CES56 = 87 | CES81 = 69 |
| CES07 = 43 | CES32 = 80 | CES57 = 87 | CES82 = 96 |
| CES08 = 42 | CES33 = 86 | CES58 = 88 | CES83 = 93 |
| CES09 = 29 | CES34 = 91 | CES59 = 92 | CES84 = 93 |
| CES10 = 77 | CES35 = 96 | CES60 = 96 | CES85 = 78 |
| CES11 = 60 | CES36 = 96 | CES61 = 91 | CES86 = 65 |
| CES12 = 66 | CES37 = 95 | CES62 = 97 | CES87 = 85 |
| CES13 = 44 | CES38 = 93 | CES63 = 87 | CES88 = 86 |
| CES14 = 74 | CES39 = 97 | CES64 = 86 | CES89 = 74 |
| CES15 = 72 | CES40 = 94 | CES65 = 81 | CES90 = 86 |
| CES16 = 48 | CES41 = 93 | CES66 = 85 | CES91 = 87 |
| CES17 = 50 | CES42 = 95 | CES67 = 84 | CES92 = 67 |
| CES18 = 57 | CES43 = 88 | CES68 = 85 | CES93 = 80 |
| CES19 = 73 | CES44 = 99 | CES69 = 91 | CES94 = 61 |
| CES20 = 67 | CES45 = 92 | CES70 = 82 | CES95 = 77 |
| CES21 = 87 | CES46 = 88 | CES71 = 83 | CES96 = 84 |
| CES22 = 79 | CES47 = 88 | CES72 = 93 | CES97 = 88 |
| CES23 = 92 | CES48 = 81 | CES73 = 78 | CES98 = 84 |
| CES24 = 91 | CES49 = 88 | CES74 = 91 | CES99 = 76 |
| CES25 = 72 | CES50 = 94 | CES75 = 85 |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)