

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675994

Luminaire Tested: **CCW-SA-2C-740-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P675994
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2C-740-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @615mA w/
SLR distribution lens
Light Source: (32) 4000K CCT, 70 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7503.3 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G3

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 10.6 fc

Type IV - Short - N/A

REPORT NUMBER: P675994
CATALOG NUMBER: CCW-SA-2C-740-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1543.9	0.0	1543.9
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	5959.5	0.0	5959.5
	% Fixture	79.4	0.0	79.4
Total	Lumens	7503.3	0.0	7503.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.2	2.5
10°-20°	393.1	5.2
20°-30°	575.1	7.7
30°-40°	810.3	10.8
40°-50°	1113.4	14.8
50°-60°	1517.6	20.2
60°-70°	1661.0	22.1
70°-80°	959.2	12.8
80°-90°	287.5	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7503.3	100.0
0°-180°	7503.3	100.0

Coefficient of Utilization



REPORT NUMBER: P675994


CATALOG NUMBER: CCW-SA-2C-740-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	770.6	10.3			
FM	(30°-60°)	2738.2	36.5			
FH	(60°-80°)	2206.4	29.4			G2/5000
FVH	(80°-90°)	244.2	3.3			G3/500
BL	(0°-30°)	383.8	5.1	B1/500		
BM	(30°-60°)	703.0	9.4	B1/1000		
BH	(60°-80°)	413.7	5.5	B1/500		G1/500
BVH	(80°-90°)	43.3	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G3

Type IV Short



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1
2.5°	2472.6	2459.3	2449.3	2439.4	2426.0	2416.1	2402.7	2389.4	2372.8	2359.5	2342.8
5°	2329.5	2289.6	2249.7	2226.4	2199.7	2176.5	2149.8	2119.9	2089.9	2056.6	2026.7
7.5°	2173.1	2123.2	2073.3	2033.4	1990.1	1950.2	1906.9	1870.3	1833.7	1797.1	1760.5
10°	2026.7	1980.1	1933.5	1883.6	1830.3	1780.4	1727.2	1677.3	1627.3	1577.4	1527.5
12.5°	1930.2	1873.6	1820.4	1763.8	1710.5	1654.0	1597.4	1550.8	1504.2	1454.3	1407.7
15°	1886.9	1833.7	1783.8	1727.2	1670.6	1614.0	1557.5	1504.2	1454.3	1401.0	1347.8
17.5°	1990.1	1913.5	1837.0	1763.8	1690.6	1617.4	1544.1	1477.6	1411.0	1344.5	1277.9
20°	2123.2	2026.7	1933.5	1843.7	1750.5	1660.6	1567.4	1474.3	1381.1	1287.9	1194.7
22.5°	2292.9	2183.1	2076.6	1960.1	1840.3	1723.9	1604.1	1487.6	1371.1	1251.3	1134.8
25°	2595.8	2466.0	2336.2	2169.8	2000.1	1833.7	1664.0	1510.9	1361.1	1208.0	1054.9
27.5°	2855.3	2679.0	2505.9	2306.2	2106.6	1906.9	1707.2	1530.8	1357.8	1181.4	1005.0
30°	3008.4	2835.4	2662.3	2419.4	2179.8	1936.8	1693.9	1497.6	1304.5	1108.2	911.8
32.5°	3148.2	2955.2	2762.2	2495.9	2226.4	1960.1	1690.6	1474.3	1261.3	1045.0	828.6
35°	3341.2	3128.2	2918.6	2609.1	2299.6	1990.1	1680.6	1457.6	1231.3	1008.4	782.1
37.5°	3547.5	3284.6	3025.1	2682.3	2339.5	1996.7	1654.0	1434.3	1214.7	995.0	775.4
40°	3773.8	3454.4	3138.2	2758.8	2382.8	2003.4	1624.0	1404.4	1184.7	961.8	742.1
42.5°	3920.3	3574.2	3228.1	2818.7	2412.7	2003.4	1594.1	1377.8	1161.4	941.8	725.5
45°	4003.5	3667.4	3334.6	2892.0	2449.3	2006.7	1564.1	1351.1	1138.1	921.8	708.8
47.5°	4040.1	3727.3	3414.4	2948.5	2485.9	2020.0	1554.1	1337.8	1118.2	901.9	682.2
50°	4136.6	3860.4	3584.2	3085.0	2589.1	2089.9	1590.7	1357.8	1128.2	895.2	662.3
52.5°	4193.2	3956.9	3720.6	3208.1	2695.6	2183.1	1670.6	1411.0	1151.5	891.9	632.3
55°	4399.5	4173.2	3946.9	3401.1	2852.0	2306.2	1757.1	1470.9	1184.7	895.2	609.0
57.5°	4662.4	4422.8	4186.5	3597.5	3008.4	2419.4	1830.3	1524.2	1214.7	908.5	599.0
60°	4845.4	4612.5	4382.9	3757.2	3128.2	2502.6	1873.6	1554.1	1234.7	911.8	592.4
62.5°	4865.4	4565.9	4269.7	3660.7	3051.7	2439.4	1830.3	1520.9	1211.4	898.5	589.0
65°	4738.9	4389.5	4040.1	3457.7	2875.3	2292.9	1710.5	1427.7	1144.8	858.6	575.7
67.5°	4486.0	4076.7	3667.4	3134.9	2602.4	2070.0	1537.5	1294.6	1054.9	812.0	569.1
70°	3897.0	3537.6	3181.5	2718.9	2259.6	1797.1	1334.5	1134.8	938.5	738.8	539.1
72.5°	3271.3	2935.2	2602.4	2226.4	1853.6	1477.6	1101.5	951.8	802.0	648.9	499.2
75°	2505.9	2253.0	2003.4	1723.9	1444.3	1161.4	881.9	772.1	662.3	552.4	442.6
77.5°	1760.5	1624.0	1490.9	1281.2	1071.6	861.9	652.3	579.1	505.8	432.6	359.4
80°	1194.7	1118.2	1045.0	895.2	745.5	592.4	442.6	396.0	346.1	299.5	249.6
82.5°	742.1	738.8	732.1	629.0	525.8	422.6	319.5	279.5	242.9	203.0	163.1
85°	339.4	396.0	449.3	392.7	336.1	279.5	223.0	196.3	169.7	139.8	113.1
87.5°	106.5	129.8	149.8	143.1	133.1	126.5	116.5	99.8	83.2	66.6	49.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1
2.5°	2329.5	2319.6	2306.2	2292.9	2276.3	2263.0	2246.3	2229.7	2226.4	2219.7	2216.4
5°	2006.7	1986.8	1963.5	1943.5	1923.5	1900.2	1880.3	1857.0	1840.3	1820.4	1803.7
7.5°	1723.9	1690.6	1654.0	1617.4	1584.1	1550.8	1514.2	1480.9	1464.3	1447.6	1431.0
10°	1497.6	1464.3	1434.3	1401.0	1377.8	1357.8	1334.5	1311.2	1291.2	1271.3	1251.3
12.5°	1384.4	1361.1	1337.8	1314.5	1287.9	1264.6	1238.0	1211.4	1188.1	1168.1	1144.8
15°	1314.5	1281.2	1244.6	1211.4	1174.8	1141.5	1104.9	1068.3	1041.6	1018.3	991.7
17.5°	1231.3	1181.4	1134.8	1084.9	1045.0	1005.0	961.8	921.8	891.9	858.6	828.6
20°	1138.1	1081.6	1021.7	965.1	918.5	875.2	828.6	782.1	748.8	712.2	678.9
22.5°	1058.3	985.1	908.5	832.0	782.1	732.1	678.9	629.0	599.0	565.7	535.8
25°	971.7	891.9	808.7	725.5	675.6	622.3	572.4	519.2	495.9	475.9	452.6
27.5°	925.2	845.3	762.1	682.2	635.6	585.7	539.1	489.2	472.6	452.6	436.0
30°	832.0	755.4	675.6	595.7	562.4	532.5	499.2	465.9	459.3	455.9	449.3
32.5°	748.8	668.9	589.0	509.2	479.2	449.3	419.3	389.4	386.0	379.4	376.1
35°	705.5	629.0	549.1	472.6	445.9	416.0	389.4	359.4	352.8	342.8	336.1
37.5°	695.5	615.7	532.5	452.6	426.0	399.3	369.4	342.8	336.1	329.5	322.8
40°	668.9	592.4	519.2	442.6	416.0	389.4	359.4	332.8	326.1	319.5	312.8
42.5°	648.9	575.7	499.2	422.6	399.3	376.1	349.4	326.1	319.5	312.8	302.8
45°	632.3	555.8	475.9	399.3	382.7	366.1	346.1	329.5	322.8	312.8	306.2
47.5°	605.7	532.5	455.9	379.4	362.7	349.4	332.8	316.2	309.5	302.8	296.2
50°	585.7	509.2	432.6	356.1	342.8	329.5	316.2	302.8	302.8	306.2	306.2
52.5°	559.1	485.9	412.7	339.4	326.1	312.8	299.5	286.2	289.5	292.9	296.2
55°	535.8	465.9	392.7	319.5	306.2	292.9	276.2	262.9	266.2	269.6	272.9
57.5°	525.8	452.6	379.4	306.2	292.9	276.2	262.9	246.3	246.3	246.3	246.3
60°	519.2	442.6	369.4	292.9	276.2	262.9	246.3	229.6	226.3	226.3	223.0
62.5°	515.8	439.3	366.1	289.5	269.6	252.9	233.0	213.0	209.7	206.3	203.0
65°	502.5	432.6	359.4	286.2	262.9	242.9	219.6	196.3	193.0	193.0	189.7
67.5°	499.2	426.0	356.1	282.9	259.6	233.0	209.7	183.0	179.7	176.4	173.1
70°	472.6	409.3	342.8	276.2	249.6	226.3	199.7	173.1	169.7	163.1	159.7
72.5°	439.3	382.7	322.8	262.9	236.3	209.7	183.0	156.4	153.1	149.8	143.1
75°	389.4	336.1	282.9	229.6	206.3	186.4	163.1	139.8	136.4	133.1	126.5
77.5°	319.5	276.2	236.3	193.0	176.4	159.7	143.1	126.5	123.1	119.8	113.1
80°	226.3	199.7	176.4	149.8	139.8	126.5	116.5	103.2	103.2	99.8	99.8
82.5°	149.8	136.4	123.1	109.8	103.2	96.5	89.9	83.2	83.2	79.9	79.9
85°	106.5	99.8	89.9	83.2	79.9	73.2	69.9	63.2	63.2	63.2	63.2
87.5°	49.9	49.9	46.6	46.6	43.3	43.3	39.9	36.6	36.6	36.6	36.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1
2.5°	2209.7	2199.7	2189.8	2176.5	2166.5	2153.2	2136.5	2123.2	2106.6	2106.6	2103.2
5°	1783.8	1773.8	1763.8	1750.5	1740.5	1727.2	1717.2	1703.9	1690.6	1690.6	1687.2
7.5°	1414.4	1394.4	1374.4	1351.1	1331.2	1317.9	1304.5	1287.9	1274.6	1264.6	1254.6
10°	1231.3	1211.4	1188.1	1168.1	1144.8	1128.2	1111.5	1091.6	1074.9	1061.6	1048.3
12.5°	1121.5	1098.2	1074.9	1051.6	1028.3	1005.0	985.1	961.8	938.5	921.8	905.2
15°	965.1	941.8	918.5	895.2	871.9	845.3	818.7	788.7	762.1	748.8	738.8
17.5°	795.4	772.1	745.5	722.2	695.5	675.6	655.6	635.6	615.7	602.4	592.4
20°	642.3	615.7	589.0	562.4	535.8	522.5	509.2	495.9	482.5	472.6	465.9
22.5°	502.5	485.9	472.6	455.9	439.3	429.3	422.6	412.7	402.7	402.7	402.7
25°	429.3	419.3	412.7	402.7	392.7	389.4	386.0	379.4	376.1	372.7	372.7
27.5°	416.0	406.0	396.0	386.0	376.1	372.7	369.4	362.7	359.4	359.4	359.4
30°	442.6	439.3	436.0	432.6	429.3	422.6	412.7	406.0	396.0	389.4	382.7
32.5°	369.4	366.1	366.1	362.7	359.4	366.1	369.4	376.1	379.4	382.7	386.0
35°	326.1	319.5	312.8	306.2	299.5	296.2	292.9	289.5	286.2	286.2	282.9
37.5°	316.2	309.5	302.8	296.2	289.5	286.2	282.9	279.5	276.2	276.2	272.9
40°	306.2	299.5	296.2	289.5	282.9	279.5	276.2	269.6	266.2	262.9	262.9
42.5°	296.2	292.9	286.2	282.9	276.2	272.9	269.6	262.9	259.6	256.2	252.9
45°	296.2	289.5	282.9	276.2	269.6	266.2	259.6	256.2	249.6	249.6	246.3
47.5°	289.5	282.9	276.2	269.6	262.9	259.6	252.9	249.6	242.9	239.6	236.3
50°	306.2	296.2	282.9	272.9	259.6	256.2	249.6	246.3	239.6	236.3	233.0
52.5°	299.5	289.5	276.2	266.2	252.9	246.3	242.9	236.3	229.6	226.3	223.0
55°	276.2	266.2	259.6	249.6	239.6	233.0	226.3	219.6	213.0	209.7	209.7
57.5°	246.3	242.9	239.6	236.3	233.0	226.3	219.6	209.7	203.0	199.7	196.3
60°	219.6	223.0	226.3	229.6	233.0	223.0	213.0	203.0	193.0	189.7	186.4
62.5°	199.7	206.3	213.0	216.3	223.0	213.0	203.0	193.0	183.0	179.7	176.4
65°	186.4	189.7	189.7	193.0	193.0	186.4	183.0	176.4	169.7	166.4	166.4
67.5°	169.7	169.7	169.7	166.4	166.4	163.1	163.1	159.7	156.4	153.1	153.1
70°	153.1	153.1	153.1	149.8	149.8	146.4	146.4	143.1	139.8	139.8	136.4
72.5°	139.8	139.8	136.4	136.4	133.1	133.1	133.1	129.8	129.8	126.5	126.5
75°	123.1	123.1	119.8	119.8	116.5	116.5	116.5	113.1	113.1	113.1	109.8
77.5°	109.8	109.8	106.5	106.5	103.2	103.2	103.2	99.8	99.8	96.5	96.5
80°	96.5	96.5	93.2	93.2	89.9	89.9	86.5	86.5	83.2	83.2	79.9
82.5°	76.5	76.5	76.5	76.5	76.5	73.2	73.2	69.9	66.6	66.6	63.2
85°	63.2	63.2	63.2	59.9	59.9	59.9	56.6	56.6	53.2	49.9	49.9
87.5°	36.6	36.6	36.6	33.3	33.3	33.3	33.3	33.3	33.3	33.3	30.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994
 CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1
2.5°	2103.2	2099.9	2086.6	2073.3	2086.6	2099.9	2099.9	2099.9	2096.6	2096.6	2096.6
5°	1687.2	1683.9	1677.3	1670.6	1670.6	1667.3	1673.9	1680.6	1687.2	1693.9	1700.6
7.5°	1241.3	1231.3	1221.3	1211.4	1218.0	1221.3	1231.3	1238.0	1248.0	1254.6	1271.3
10°	1035.0	1021.7	1011.7	1001.7	995.0	988.4	981.7	978.4	971.7	965.1	971.7
12.5°	885.2	868.6	851.9	832.0	828.6	825.3	818.7	812.0	805.4	798.7	795.4
15°	725.5	712.2	705.5	695.5	682.2	668.9	662.3	658.9	652.3	645.6	642.3
17.5°	579.1	565.7	555.8	545.8	542.4	535.8	535.8	535.8	535.8	535.8	535.8
20°	455.9	445.9	445.9	442.6	442.6	439.3	442.6	445.9	445.9	449.3	452.6
22.5°	399.3	399.3	396.0	392.7	396.0	396.0	399.3	402.7	406.0	409.3	412.7
25°	369.4	366.1	369.4	372.7	372.7	372.7	376.1	376.1	379.4	379.4	379.4
27.5°	356.1	356.1	359.4	359.4	362.7	362.7	362.7	359.4	359.4	356.1	356.1
30°	376.1	369.4	369.4	369.4	366.1	362.7	359.4	359.4	356.1	352.8	349.4
32.5°	389.4	392.7	389.4	382.7	379.4	372.7	369.4	362.7	359.4	352.8	346.1
35°	282.9	279.5	286.2	289.5	292.9	296.2	299.5	302.8	302.8	306.2	306.2
37.5°	272.9	269.6	269.6	266.2	266.2	266.2	266.2	266.2	262.9	262.9	266.2
40°	259.6	256.2	256.2	252.9	252.9	249.6	249.6	249.6	249.6	249.6	249.6
42.5°	249.6	246.3	246.3	246.3	246.3	242.9	242.9	239.6	239.6	236.3	236.3
45°	246.3	242.9	239.6	236.3	236.3	233.0	233.0	233.0	229.6	229.6	229.6
47.5°	233.0	229.6	229.6	226.3	226.3	223.0	223.0	223.0	219.6	219.6	219.6
50°	226.3	223.0	223.0	219.6	219.6	216.3	216.3	216.3	213.0	213.0	213.0
52.5°	216.3	213.0	213.0	213.0	209.7	206.3	206.3	206.3	203.0	203.0	203.0
55°	206.3	203.0	203.0	203.0	199.7	196.3	196.3	196.3	193.0	193.0	193.0
57.5°	193.0	189.7	189.7	186.4	186.4	186.4	186.4	186.4	183.0	183.0	183.0
60°	183.0	179.7	179.7	176.4	176.4	173.1	173.1	173.1	173.1	173.1	173.1
62.5°	173.1	169.7	166.4	163.1	166.4	166.4	166.4	166.4	163.1	163.1	163.1
65°	163.1	159.7	156.4	153.1	153.1	153.1	153.1	153.1	153.1	153.1	153.1
67.5°	149.8	146.4	143.1	139.8	143.1	143.1	143.1	143.1	143.1	143.1	143.1
70°	136.4	133.1	133.1	129.8	129.8	126.5	126.5	129.8	129.8	129.8	129.8
72.5°	123.1	119.8	119.8	116.5	116.5	116.5	116.5	116.5	116.5	116.5	116.5
75°	109.8	106.5	106.5	103.2	103.2	103.2	103.2	103.2	103.2	103.2	103.2
77.5°	93.2	89.9	89.9	89.9	89.9	89.9	89.9	93.2	93.2	93.2	93.2
80°	79.9	76.5	76.5	76.5	76.5	76.5	76.5	76.5	76.5	76.5	76.5
82.5°	63.2	59.9	59.9	59.9	59.9	59.9	59.9	59.9	59.9	59.9	59.9
85°	46.6	43.3	43.3	43.3	46.6	46.6	46.6	46.6	46.6	46.6	46.6
87.5°	30.0	26.6	26.6	26.6	30.0	30.0	30.0	30.0	26.6	26.6	26.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1
2.5°	2096.6	2096.6	2096.6	2093.3	2089.9	2086.6	2083.3	2093.3	2099.9	2109.9	2116.5
5°	1703.9	1710.5	1713.9	1723.9	1733.8	1743.8	1753.8	1760.5	1767.1	1770.4	1777.1
7.5°	1284.6	1301.2	1314.5	1327.8	1341.1	1351.1	1364.4	1374.4	1384.4	1394.4	1404.4
10°	975.1	981.7	985.1	998.4	1008.4	1021.7	1031.7	1041.6	1051.6	1058.3	1068.3
12.5°	792.0	785.4	782.1	782.1	782.1	782.1	782.1	788.7	795.4	802.0	808.7
15°	639.0	635.6	632.3	629.0	625.6	619.0	615.7	622.3	629.0	635.6	642.3
17.5°	535.8	535.8	535.8	532.5	529.1	525.8	522.5	525.8	529.1	529.1	532.5
20°	459.3	462.6	465.9	469.2	469.2	472.6	472.6	475.9	479.2	479.2	482.5
22.5°	412.7	416.0	416.0	416.0	419.3	419.3	419.3	422.6	426.0	429.3	432.6
25°	376.1	376.1	372.7	372.7	376.1	376.1	376.1	376.1	379.4	379.4	379.4
27.5°	356.1	352.8	352.8	352.8	352.8	349.4	349.4	349.4	349.4	349.4	349.4
30°	346.1	342.8	339.4	336.1	336.1	332.8	329.5	329.5	329.5	329.5	329.5
32.5°	342.8	336.1	329.5	326.1	326.1	322.8	319.5	316.2	316.2	312.8	309.5
35°	306.2	302.8	302.8	299.5	296.2	292.9	289.5	289.5	289.5	286.2	286.2
37.5°	266.2	269.6	269.6	269.6	272.9	272.9	272.9	272.9	276.2	276.2	276.2
40°	249.6	249.6	249.6	252.9	256.2	256.2	259.6	259.6	262.9	262.9	262.9
42.5°	236.3	233.0	233.0	236.3	236.3	239.6	239.6	242.9	246.3	246.3	249.6
45°	229.6	226.3	226.3	226.3	226.3	223.0	223.0	226.3	229.6	233.0	236.3
47.5°	216.3	216.3	213.0	213.0	213.0	213.0	213.0	213.0	216.3	216.3	216.3
50°	209.7	209.7	206.3	206.3	206.3	206.3	206.3	206.3	206.3	206.3	206.3
52.5°	203.0	199.7	199.7	199.7	199.7	196.3	196.3	196.3	196.3	196.3	196.3
55°	193.0	189.7	189.7	189.7	189.7	189.7	189.7	189.7	193.0	193.0	193.0
57.5°	183.0	179.7	179.7	179.7	183.0	183.0	183.0	183.0	186.4	186.4	186.4
60°	173.1	173.1	173.1	173.1	173.1	173.1	173.1	176.4	176.4	179.7	179.7
62.5°	163.1	163.1	163.1	163.1	166.4	166.4	166.4	166.4	169.7	169.7	169.7
65°	153.1	153.1	153.1	153.1	156.4	156.4	156.4	156.4	156.4	156.4	156.4
67.5°	143.1	143.1	143.1	143.1	143.1	143.1	143.1	146.4	146.4	149.8	149.8
70°	129.8	126.5	126.5	129.8	129.8	133.1	133.1	136.4	136.4	139.8	139.8
72.5°	116.5	116.5	116.5	116.5	116.5	116.5	116.5	119.8	123.1	123.1	126.5
75°	103.2	103.2	103.2	103.2	106.5	106.5	106.5	109.8	109.8	113.1	113.1
77.5°	93.2	89.9	89.9	89.9	93.2	93.2	93.2	96.5	96.5	99.8	99.8
80°	76.5	76.5	76.5	76.5	79.9	79.9	79.9	79.9	83.2	83.2	83.2
82.5°	63.2	63.2	63.2	63.2	63.2	63.2	63.2	63.2	66.6	66.6	66.6
85°	46.6	46.6	46.6	46.6	49.9	49.9	49.9	49.9	49.9	49.9	49.9
87.5°	30.0	30.0	30.0	30.0	30.0	30.0	30.0	30.0	33.3	33.3	33.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994
 CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1
2.5°	2116.5	2116.5	2116.5	2116.5	2123.2	2126.5	2133.2	2136.5	2133.2	2129.9	2123.2
5°	1780.4	1783.8	1783.8	1787.1	1787.1	1787.1	1787.1	1787.1	1793.7	1800.4	1807.1
7.5°	1407.7	1411.0	1414.4	1417.7	1417.7	1417.7	1414.4	1414.4	1417.7	1417.7	1421.0
10°	1078.2	1091.6	1101.5	1111.5	1104.9	1094.9	1088.2	1078.2	1078.2	1078.2	1074.9
12.5°	815.3	818.7	825.3	828.6	825.3	825.3	822.0	818.7	822.0	828.6	832.0
15°	645.6	645.6	648.9	648.9	652.3	655.6	655.6	658.9	665.6	668.9	675.6
17.5°	535.8	539.1	539.1	542.4	542.4	545.8	545.8	545.8	552.4	559.1	569.1
20°	482.5	482.5	482.5	482.5	482.5	479.2	479.2	475.9	479.2	485.9	489.2
22.5°	432.6	436.0	436.0	436.0	432.6	429.3	422.6	419.3	419.3	422.6	422.6
25°	379.4	376.1	376.1	372.7	372.7	376.1	376.1	376.1	379.4	379.4	382.7
27.5°	349.4	346.1	346.1	342.8	342.8	346.1	346.1	346.1	346.1	346.1	346.1
30°	326.1	326.1	322.8	319.5	322.8	322.8	326.1	326.1	329.5	329.5	332.8
32.5°	309.5	306.2	306.2	302.8	306.2	306.2	309.5	309.5	312.8	316.2	316.2
35°	286.2	286.2	286.2	286.2	286.2	286.2	282.9	282.9	282.9	282.9	282.9
37.5°	272.9	272.9	269.6	266.2	266.2	266.2	266.2	266.2	262.9	259.6	256.2
40°	262.9	259.6	259.6	256.2	252.9	252.9	249.6	246.3	246.3	242.9	242.9
42.5°	249.6	246.3	246.3	242.9	239.6	239.6	236.3	233.0	233.0	233.0	229.6
45°	233.0	233.0	229.6	226.3	226.3	226.3	223.0	223.0	223.0	223.0	219.6
47.5°	216.3	216.3	213.0	213.0	213.0	213.0	209.7	209.7	209.7	209.7	209.7
50°	206.3	206.3	206.3	206.3	206.3	206.3	203.0	203.0	203.0	203.0	203.0
52.5°	196.3	196.3	196.3	196.3	196.3	196.3	196.3	196.3	196.3	196.3	196.3
55°	193.0	193.0	193.0	193.0	193.0	193.0	189.7	189.7	189.7	193.0	193.0
57.5°	186.4	186.4	183.0	183.0	183.0	183.0	183.0	183.0	183.0	183.0	183.0
60°	179.7	179.7	179.7	179.7	179.7	179.7	179.7	179.7	179.7	179.7	179.7
62.5°	169.7	169.7	169.7	169.7	169.7	173.1	173.1	173.1	173.1	173.1	169.7
65°	156.4	159.7	159.7	159.7	159.7	159.7	159.7	159.7	159.7	159.7	159.7
67.5°	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8	149.8
70°	139.8	139.8	136.4	136.4	136.4	139.8	139.8	139.8	139.8	139.8	139.8
72.5°	126.5	126.5	126.5	126.5	126.5	126.5	126.5	126.5	126.5	129.8	129.8
75°	113.1	113.1	113.1	113.1	113.1	113.1	113.1	113.1	113.1	113.1	113.1
77.5°	99.8	99.8	96.5	96.5	96.5	99.8	99.8	99.8	99.8	103.2	103.2
80°	83.2	83.2	83.2	83.2	83.2	83.2	83.2	83.2	83.2	86.5	86.5
82.5°	66.6	66.6	66.6	66.6	66.6	66.6	66.6	66.6	66.6	69.9	69.9
85°	49.9	53.2	53.2	53.2	53.2	53.2	53.2	53.2	53.2	56.6	56.6
87.5°	33.3	33.3	33.3	33.3	33.3	33.3	30.0	30.0	30.0	30.0	26.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1
2.5°	2119.9	2123.2	2126.5	2126.5	2129.9	2133.2	2133.2	2146.5	2159.8	2166.5	2173.1
5°	1813.7	1810.4	1810.4	1807.1	1803.7	1813.7	1823.7	1843.7	1863.6	1867.0	1873.6
7.5°	1421.0	1424.3	1427.7	1427.7	1431.0	1421.0	1407.7	1411.0	1414.4	1431.0	1444.3
10°	1074.9	1078.2	1081.6	1081.6	1084.9	1081.6	1074.9	1084.9	1094.9	1108.2	1124.8
12.5°	835.3	845.3	855.3	861.9	871.9	878.6	881.9	895.2	905.2	921.8	938.5
15°	682.2	688.9	695.5	702.2	708.8	715.5	722.2	735.5	748.8	768.7	788.7
17.5°	575.7	575.7	579.1	579.1	579.1	585.7	592.4	599.0	602.4	622.3	642.3
20°	492.5	489.2	485.9	482.5	479.2	485.9	489.2	492.5	495.9	509.2	519.2
22.5°	422.6	422.6	426.0	426.0	426.0	422.6	416.0	419.3	419.3	426.0	436.0
25°	382.7	382.7	382.7	379.4	379.4	382.7	386.0	386.0	382.7	386.0	389.4
27.5°	346.1	349.4	349.4	352.8	352.8	356.1	356.1	356.1	356.1	359.4	362.7
30°	332.8	332.8	336.1	336.1	336.1	339.4	342.8	342.8	342.8	346.1	352.8
32.5°	319.5	322.8	326.1	329.5	332.8	336.1	336.1	339.4	339.4	342.8	346.1
35°	282.9	279.5	279.5	276.2	272.9	272.9	272.9	272.9	269.6	272.9	272.9
37.5°	252.9	252.9	252.9	249.6	249.6	252.9	252.9	252.9	252.9	256.2	256.2
40°	239.6	239.6	239.6	239.6	239.6	239.6	239.6	242.9	242.9	246.3	249.6
42.5°	229.6	229.6	229.6	229.6	229.6	233.0	233.0	233.0	233.0	236.3	236.3
45°	219.6	219.6	219.6	219.6	219.6	219.6	219.6	223.0	223.0	226.3	229.6
47.5°	209.7	209.7	209.7	209.7	209.7	213.0	216.3	216.3	216.3	219.6	219.6
50°	203.0	203.0	203.0	203.0	203.0	206.3	206.3	209.7	209.7	213.0	216.3
52.5°	196.3	196.3	196.3	196.3	196.3	199.7	199.7	203.0	203.0	206.3	209.7
55°	193.0	193.0	193.0	189.7	189.7	193.0	193.0	196.3	196.3	199.7	199.7
57.5°	183.0	183.0	183.0	183.0	183.0	183.0	183.0	186.4	186.4	189.7	193.0
60°	179.7	179.7	176.4	176.4	173.1	176.4	176.4	179.7	179.7	183.0	183.0
62.5°	169.7	169.7	169.7	166.4	166.4	169.7	169.7	169.7	169.7	173.1	176.4
65°	159.7	159.7	159.7	156.4	156.4	159.7	159.7	159.7	159.7	163.1	166.4
67.5°	149.8	149.8	149.8	146.4	146.4	146.4	146.4	149.8	149.8	153.1	156.4
70°	139.8	139.8	139.8	136.4	136.4	136.4	133.1	136.4	139.8	143.1	143.1
72.5°	129.8	129.8	129.8	126.5	126.5	126.5	123.1	126.5	126.5	129.8	129.8
75°	113.1	113.1	113.1	113.1	113.1	113.1	109.8	109.8	109.8	113.1	113.1
77.5°	103.2	103.2	103.2	99.8	99.8	99.8	96.5	96.5	96.5	99.8	99.8
80°	86.5	86.5	86.5	83.2	83.2	83.2	79.9	79.9	79.9	83.2	83.2
82.5°	69.9	69.9	69.9	66.6	66.6	66.6	63.2	63.2	63.2	66.6	66.6
85°	56.6	56.6	56.6	56.6	56.6	56.6	53.2	53.2	53.2	56.6	59.9
87.5°	26.6	26.6	30.0	30.0	30.0	30.0	26.6	26.6	23.3	23.3	26.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994
 CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1
2.5°	2179.8	2186.4	2203.1	2216.4	2233.0	2246.3	2256.3	2269.6	2279.6	2289.6	2296.3
5°	1876.9	1880.3	1896.9	1913.5	1926.9	1943.5	1966.8	1990.1	2013.4	2036.7	2053.3
7.5°	1461.0	1474.3	1494.2	1517.5	1537.5	1557.5	1580.8	1607.4	1630.7	1654.0	1677.3
10°	1138.1	1151.5	1171.4	1191.4	1208.0	1228.0	1254.6	1281.2	1307.9	1334.5	1361.1
12.5°	955.1	971.7	995.0	1018.3	1038.3	1061.6	1094.9	1124.8	1158.1	1188.1	1221.3
15°	805.4	825.3	855.3	888.6	918.5	948.5	981.7	1015.0	1045.0	1078.2	1111.5
17.5°	662.3	682.2	708.8	738.8	765.4	792.0	832.0	868.6	908.5	945.1	981.7
20°	532.5	542.4	569.1	595.7	622.3	648.9	678.9	708.8	738.8	768.7	815.3
22.5°	442.6	449.3	462.6	472.6	485.9	495.9	525.8	555.8	582.4	612.3	655.6
25°	389.4	392.7	402.7	409.3	419.3	426.0	445.9	462.6	482.5	499.2	539.1
27.5°	362.7	366.1	369.4	372.7	376.1	379.4	392.7	406.0	416.0	429.3	465.9
30°	356.1	359.4	369.4	376.1	386.0	392.7	399.3	406.0	412.7	419.3	442.6
32.5°	349.4	352.8	352.8	349.4	349.4	346.1	352.8	356.1	362.7	366.1	386.0
35°	276.2	276.2	279.5	282.9	286.2	289.5	299.5	306.2	316.2	322.8	339.4
37.5°	259.6	259.6	262.9	269.6	272.9	276.2	282.9	289.5	296.2	302.8	319.5
40°	249.6	252.9	256.2	259.6	262.9	266.2	272.9	276.2	282.9	286.2	299.5
42.5°	239.6	239.6	242.9	249.6	252.9	256.2	262.9	266.2	272.9	276.2	289.5
45°	233.0	236.3	239.6	242.9	242.9	246.3	252.9	259.6	262.9	269.6	282.9
47.5°	223.0	223.0	229.6	233.0	239.6	242.9	249.6	252.9	259.6	262.9	276.2
50°	216.3	219.6	226.3	229.6	236.3	239.6	249.6	256.2	266.2	272.9	279.5
52.5°	209.7	213.0	219.6	223.0	229.6	233.0	246.3	259.6	269.6	282.9	282.9
55°	203.0	203.0	209.7	219.6	226.3	233.0	239.6	249.6	256.2	262.9	262.9
57.5°	193.0	196.3	203.0	213.0	219.6	226.3	233.0	239.6	242.9	249.6	246.3
60°	186.4	186.4	196.3	206.3	216.3	226.3	226.3	226.3	223.0	223.0	223.0
62.5°	176.4	179.7	193.0	209.7	223.0	236.3	226.3	216.3	206.3	196.3	199.7
65°	169.7	173.1	179.7	189.7	196.3	203.0	196.3	193.0	186.4	179.7	183.0
67.5°	156.4	159.7	163.1	163.1	166.4	166.4	166.4	166.4	166.4	166.4	169.7
70°	146.4	146.4	146.4	149.8	149.8	149.8	149.8	149.8	149.8	149.8	153.1
72.5°	133.1	133.1	133.1	133.1	133.1	133.1	133.1	133.1	133.1	133.1	136.4
75°	116.5	116.5	116.5	116.5	116.5	116.5	116.5	116.5	116.5	116.5	119.8
77.5°	103.2	103.2	103.2	103.2	103.2	103.2	103.2	103.2	99.8	99.8	103.2
80°	86.5	86.5	86.5	86.5	83.2	83.2	83.2	83.2	83.2	83.2	86.5
82.5°	69.9	69.9	69.9	69.9	66.6	66.6	66.6	66.6	63.2	63.2	66.6
85°	63.2	66.6	66.6	69.9	69.9	69.9	66.6	63.2	59.9	56.6	56.6
87.5°	26.6	26.6	26.6	26.6	23.3	23.3	23.3	23.3	23.3	23.3	23.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1
2.5°	2306.2	2312.9	2319.6	2329.5	2342.8	2352.8	2362.8	2382.8	2406.1	2426.0	2446.0
5°	2070.0	2086.6	2103.2	2123.2	2143.2	2159.8	2179.8	2219.7	2259.6	2296.3	2336.2
7.5°	1697.2	1720.5	1740.5	1773.8	1803.7	1837.0	1867.0	1916.9	1963.5	2013.4	2060.0
10°	1387.7	1414.4	1441.0	1484.2	1530.8	1574.1	1617.4	1657.3	1700.6	1740.5	1780.4
12.5°	1254.6	1284.6	1317.9	1344.5	1374.4	1401.0	1427.7	1474.3	1520.9	1567.4	1614.0
15°	1144.8	1178.1	1211.4	1244.6	1274.6	1307.9	1337.8	1377.8	1421.0	1461.0	1500.9
17.5°	1018.3	1051.6	1088.2	1124.8	1161.4	1198.0	1234.7	1291.2	1347.8	1401.0	1457.6
20°	858.6	905.2	948.5	998.4	1048.3	1098.2	1148.1	1208.0	1267.9	1324.5	1384.4
22.5°	698.9	742.1	785.4	845.3	905.2	961.8	1021.7	1101.5	1178.1	1257.9	1334.5
25°	582.4	622.3	662.3	728.8	792.0	858.6	921.8	1018.3	1111.5	1208.0	1301.2
27.5°	502.5	539.1	575.7	645.6	715.5	782.1	851.9	958.4	1061.6	1168.1	1271.3
30°	465.9	489.2	512.5	579.1	645.6	708.8	775.4	878.6	981.7	1084.9	1188.1
32.5°	406.0	426.0	445.9	505.8	565.7	622.3	682.2	788.7	891.9	998.4	1101.5
35°	359.4	376.1	392.7	449.3	502.5	559.1	612.3	718.8	825.3	931.8	1038.3
37.5°	332.8	349.4	362.7	412.7	465.9	515.8	565.7	672.2	775.4	881.9	985.1
40°	312.8	322.8	336.1	386.0	432.6	482.5	529.1	625.6	725.5	822.0	918.5
42.5°	299.5	312.8	322.8	366.1	412.7	455.9	499.2	592.4	685.5	775.4	868.6
45°	296.2	309.5	322.8	359.4	396.0	429.3	465.9	555.8	645.6	735.5	825.3
47.5°	289.5	299.5	312.8	342.8	369.4	399.3	426.0	515.8	605.7	692.2	782.1
50°	286.2	289.5	296.2	322.8	349.4	376.1	402.7	492.5	582.4	672.2	762.1
52.5°	282.9	282.9	282.9	306.2	329.5	349.4	372.7	462.6	555.8	645.6	735.5
55°	262.9	259.6	259.6	282.9	302.8	326.1	346.1	436.0	525.8	612.3	702.2
57.5°	242.9	239.6	236.3	256.2	276.2	296.2	316.2	406.0	499.2	589.0	678.9
60°	223.0	219.6	219.6	239.6	256.2	276.2	292.9	386.0	475.9	569.1	658.9
62.5°	199.7	203.0	203.0	219.6	239.6	256.2	272.9	366.1	462.6	555.8	648.9
65°	183.0	186.4	186.4	206.3	226.3	246.3	266.2	356.1	449.3	539.1	629.0
67.5°	169.7	173.1	173.1	196.3	216.3	239.6	259.6	339.4	422.6	502.5	582.4
70°	156.4	156.4	159.7	183.0	206.3	229.6	252.9	322.8	392.7	459.3	529.1
72.5°	139.8	143.1	146.4	169.7	189.7	213.0	233.0	296.2	359.4	422.6	485.9
75°	123.1	126.5	129.8	149.8	169.7	189.7	209.7	269.6	326.1	386.0	442.6
77.5°	109.8	113.1	116.5	133.1	149.8	166.4	183.0	226.3	272.9	316.2	359.4
80°	89.9	89.9	93.2	106.5	119.8	129.8	143.1	173.1	203.0	229.6	259.6
82.5°	66.6	69.9	69.9	79.9	86.5	96.5	103.2	119.8	133.1	149.8	163.1
85°	56.6	53.2	53.2	59.9	63.2	69.9	73.2	83.2	89.9	99.8	106.5
87.5°	23.3	20.0	20.0	23.3	30.0	33.3	36.6	36.6	39.9	39.9	39.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1
2.5°	2456.0	2462.7	2472.6	2479.3	2495.9	2509.2	2525.9	2539.2	2549.2	2565.8	2559.2
5°	2366.1	2396.1	2426.0	2456.0	2479.3	2502.6	2522.6	2545.8	2572.5	2622.4	2635.7
7.5°	2099.9	2139.8	2176.5	2216.4	2263.0	2309.6	2356.2	2402.7	2446.0	2509.2	2549.2
10°	1837.0	1893.6	1946.8	2003.4	2046.7	2089.9	2129.9	2173.1	2233.0	2296.3	2369.5
12.5°	1670.6	1727.2	1783.8	1840.3	1903.6	1963.5	2026.7	2086.6	2143.2	2193.1	2276.3
15°	1560.8	1624.0	1683.9	1743.8	1820.4	1893.6	1970.1	2043.3	2126.5	2193.1	2249.7
17.5°	1534.2	1610.7	1683.9	1760.5	1840.3	1920.2	2000.1	2079.9	2163.1	2263.0	2336.2
20°	1487.6	1590.7	1693.9	1797.1	1900.2	2000.1	2103.2	2203.1	2312.9	2432.7	2466.0
22.5°	1461.0	1584.1	1710.5	1833.7	1973.4	2116.5	2256.3	2396.1	2512.6	2602.4	2702.3
25°	1457.6	1610.7	1767.1	1920.2	2096.6	2269.6	2446.0	2619.1	2768.8	2858.7	2938.5
27.5°	1454.3	1640.7	1823.7	2006.7	2223.0	2436.0	2652.3	2865.3	3005.1	3134.9	3201.4
30°	1414.4	1637.3	1863.6	2086.6	2329.5	2572.5	2815.4	3058.3	3201.4	3291.3	3324.6
32.5°	1364.4	1627.3	1890.3	2153.2	2429.4	2705.6	2978.5	3254.7	3367.8	3444.4	3417.8
35°	1324.5	1614.0	1900.2	2186.4	2479.3	2775.5	3068.3	3361.2	3524.3	3630.7	3587.5
37.5°	1287.9	1590.7	1893.6	2196.4	2539.2	2882.0	3224.7	3567.5	3723.9	3837.1	3787.2
40°	1244.6	1567.4	1893.6	2216.4	2609.1	2998.4	3391.1	3780.5	3983.5	4080.0	4003.5
42.5°	1208.0	1544.1	1883.6	2219.7	2639.0	3058.3	3477.7	3897.0	4123.3	4259.7	4163.2
45°	1161.4	1497.6	1830.3	2166.5	2629.0	3091.6	3550.9	4013.5	4276.4	4382.9	4249.7
47.5°	1111.5	1444.3	1773.8	2103.2	2595.8	3088.3	3580.8	4073.4	4316.3	4442.8	4319.6
50°	1094.9	1427.7	1757.1	2089.9	2622.4	3158.2	3690.6	4223.1	4399.5	4502.7	4339.6
52.5°	1091.6	1444.3	1800.4	2153.2	2688.9	3221.4	3757.2	4289.7	4432.8	4542.6	4396.2
55°	1081.6	1464.3	1843.7	2223.0	2782.1	3344.5	3903.6	4462.7	4605.8	4685.7	4575.9
57.5°	1091.6	1504.2	1913.5	2326.2	2901.9	3477.7	4053.4	4629.1	4802.2	4858.7	4835.4
60°	1098.2	1537.5	1973.4	2412.7	2975.1	3537.6	4100.0	4662.4	4842.1	4981.9	5008.5
62.5°	1081.6	1514.2	1943.5	2376.1	2885.3	3394.5	3903.6	4412.8	4709.0	4915.3	5035.1
65°	1031.7	1431.0	1833.7	2233.0	2702.3	3174.8	3644.1	4113.3	4426.1	4732.3	4828.8
67.5°	921.8	1261.3	1600.7	1940.2	2349.5	2758.8	3164.8	3574.2	3966.9	4263.0	4396.2
70°	798.7	1064.9	1334.5	1600.7	1973.4	2346.2	2718.9	3091.6	3437.7	3763.9	3890.3
72.5°	695.5	901.9	1111.5	1317.9	1584.1	1847.0	2113.2	2376.1	2785.5	3111.6	3234.7
75°	592.4	742.1	888.6	1038.3	1221.3	1404.4	1584.1	1767.1	2056.6	2349.5	2472.6
77.5°	455.9	555.8	652.3	748.8	875.2	998.4	1124.8	1248.0	1451.0	1670.6	1733.8
80°	316.2	372.7	426.0	482.5	582.4	682.2	782.1	881.9	1015.0	1138.1	1234.7
82.5°	196.3	233.0	266.2	299.5	379.4	459.3	535.8	615.7	668.9	675.6	772.1
85°	126.5	149.8	169.7	189.7	236.3	286.2	332.8	379.4	339.4	316.2	376.1
87.5°	49.9	63.2	73.2	83.2	79.9	76.5	73.2	69.9	59.9	53.2	66.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1
2.5°	2565.8	2575.8	2585.8	2592.4	2602.4	2605.8	2609.1	2609.1	2612.4	2615.7	2622.4
5°	2688.9	2708.9	2728.9	2745.5	2765.5	2782.1	2795.4	2812.1	2825.4	2825.4	2822.1
7.5°	2585.8	2635.7	2685.6	2735.5	2785.5	2822.1	2855.3	2892.0	2925.2	2931.9	2938.5
10°	2449.3	2502.6	2552.5	2605.8	2655.7	2712.2	2765.5	2818.7	2875.3	2885.3	2898.6
12.5°	2322.9	2386.1	2449.3	2509.2	2572.5	2612.4	2652.3	2688.9	2728.9	2755.5	2782.1
15°	2319.6	2372.8	2426.0	2476.0	2529.2	2552.5	2575.8	2595.8	2619.1	2619.1	2622.4
17.5°	2396.1	2429.4	2462.7	2492.6	2525.9	2529.2	2535.9	2539.2	2542.5	2532.5	2522.6
20°	2545.8	2559.2	2572.5	2585.8	2599.1	2575.8	2555.8	2532.5	2509.2	2482.6	2459.3
22.5°	2765.5	2735.5	2705.6	2675.6	2645.7	2605.8	2562.5	2522.6	2479.3	2446.0	2412.7
25°	2971.8	2935.2	2898.6	2862.0	2825.4	2738.9	2652.3	2562.5	2476.0	2439.4	2402.7
27.5°	3248.0	3191.5	3134.9	3078.3	3021.7	2905.3	2788.8	2672.3	2555.8	2492.6	2432.7
30°	3314.6	3251.4	3188.1	3121.6	3058.3	2945.2	2835.4	2722.2	2609.1	2535.9	2466.0
32.5°	3411.1	3337.9	3264.7	3191.5	3118.2	3008.4	2898.6	2785.5	2675.6	2609.1	2539.2
35°	3570.8	3487.6	3404.4	3317.9	3234.7	3121.6	3011.8	2898.6	2785.5	2708.9	2635.7
37.5°	3707.3	3610.8	3514.3	3417.8	3321.3	3221.4	3118.2	3018.4	2915.2	2838.7	2765.5
40°	3860.4	3753.9	3647.4	3544.2	3437.7	3344.5	3251.4	3154.9	3061.7	3001.8	2941.9
42.5°	3993.5	3863.7	3737.2	3610.8	3481.0	3417.8	3357.9	3294.6	3231.4	3201.4	3168.2
45°	4086.7	3966.9	3843.7	3723.9	3604.1	3557.5	3510.9	3464.4	3417.8	3447.7	3477.7
47.5°	4126.6	4030.1	3936.9	3843.7	3747.2	3763.9	3780.5	3793.8	3810.5	3850.4	3893.7
50°	4163.2	4110.0	4053.4	4000.1	3943.6	4006.8	4066.7	4129.9	4193.2	4276.4	4359.6
52.5°	4236.4	4206.5	4179.9	4149.9	4119.9	4229.8	4339.6	4449.4	4559.2	4652.4	4745.6
55°	4456.1	4432.8	4409.5	4382.9	4359.6	4516.0	4669.1	4825.5	4981.9	5078.4	5174.9
57.5°	4758.9	4745.6	4729.0	4715.6	4699.0	4852.1	5001.8	5151.6	5304.7	5397.9	5494.4
60°	4988.5	4991.9	4991.9	4995.2	4995.2	5111.7	5228.1	5347.9	5464.4	5544.3	5627.5
62.5°	5111.7	5105.0	5098.4	5091.7	5085.0	5181.6	5278.1	5374.6	5471.1	5531.0	5590.9
65°	4978.5	5015.2	5051.8	5088.4	5125.0	5138.3	5148.3	5161.6	5171.6	5208.2	5244.8
67.5°	4532.6	4605.8	4675.7	4748.9	4818.8	4768.9	4722.3	4672.4	4622.5	4632.4	4639.1
70°	4036.8	4119.9	4206.5	4289.7	4372.9	4256.4	4139.9	4020.1	3903.6	3863.7	3823.8
72.5°	3404.4	3477.7	3554.2	3627.4	3700.6	3557.5	3417.8	3274.7	3131.6	3061.7	2991.8
75°	2602.4	2688.9	2778.8	2865.3	2951.9	2792.1	2629.0	2469.3	2306.2	2259.6	2216.4
77.5°	1896.9	2000.1	2103.2	2206.4	2309.6	2166.5	2023.4	1876.9	1733.8	1707.2	1680.6
80°	1381.1	1461.0	1537.5	1617.4	1693.9	1610.7	1527.5	1444.3	1361.1	1357.8	1354.5
82.5°	931.8	1001.7	1068.3	1138.1	1204.7	1171.4	1141.5	1108.2	1074.9	1108.2	1144.8
85°	479.2	575.7	675.6	772.1	868.6	858.6	851.9	842.0	832.0	875.2	915.2
87.5°	96.5	179.7	262.9	342.8	426.0	406.0	386.0	362.7	342.8	356.1	366.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1
2.5°	2625.7	2629.0	2629.0	2629.0	2629.0	2629.0	2622.4	2619.1	2612.4	2605.8	2595.8
5°	2822.1	2818.7	2805.4	2792.1	2775.5	2762.2	2752.2	2738.9	2728.9	2715.6	2695.6
7.5°	2945.2	2951.9	2928.6	2908.6	2885.3	2862.0	2838.7	2815.4	2792.1	2768.8	2722.2
10°	2908.6	2918.6	2905.3	2892.0	2875.3	2862.0	2835.4	2805.4	2778.8	2748.9	2692.3
12.5°	2805.4	2832.0	2825.4	2818.7	2812.1	2805.4	2788.8	2768.8	2752.2	2732.2	2669.0
15°	2622.4	2622.4	2625.7	2629.0	2629.0	2632.4	2635.7	2639.0	2642.4	2645.7	2609.1
17.5°	2512.6	2502.6	2502.6	2502.6	2502.6	2502.6	2515.9	2532.5	2545.8	2559.2	2549.2
20°	2432.7	2409.4	2406.1	2406.1	2402.7	2399.4	2422.7	2449.3	2472.6	2495.9	2509.2
22.5°	2379.5	2346.2	2342.8	2339.5	2336.2	2332.9	2362.8	2392.8	2422.7	2452.7	2499.3
25°	2366.1	2329.5	2332.9	2336.2	2336.2	2339.5	2362.8	2386.1	2409.4	2432.7	2512.6
27.5°	2369.5	2309.6	2312.9	2316.2	2316.2	2319.6	2356.2	2389.4	2426.0	2459.3	2559.2
30°	2392.8	2322.9	2316.2	2309.6	2302.9	2296.3	2346.2	2396.1	2446.0	2495.9	2572.5
32.5°	2472.6	2406.1	2389.4	2372.8	2356.2	2339.5	2399.4	2456.0	2515.9	2572.5	2635.7
35°	2559.2	2485.9	2479.3	2472.6	2462.7	2456.0	2509.2	2565.8	2619.1	2672.3	2728.9
37.5°	2688.9	2615.7	2609.1	2599.1	2592.4	2582.5	2642.4	2698.9	2758.8	2815.4	2865.3
40°	2882.0	2822.1	2818.7	2818.7	2815.4	2812.1	2858.7	2908.6	2955.2	3001.8	3035.1
42.5°	3138.2	3108.3	3118.2	3131.6	3141.5	3151.5	3188.1	3228.1	3264.7	3301.3	3291.3
45°	3507.6	3537.6	3540.9	3544.2	3547.5	3550.9	3560.9	3574.2	3584.2	3594.1	3554.2
47.5°	3933.6	3973.5	3993.5	4013.5	4030.1	4050.1	4036.8	4020.1	4006.8	3990.2	3890.3
50°	4439.4	4522.6	4519.3	4516.0	4509.3	4506.0	4479.4	4452.7	4422.8	4396.2	4249.7
52.5°	4838.8	4932.0	4948.6	4965.2	4981.9	4998.5	4948.6	4898.7	4845.4	4795.5	4612.5
55°	5268.1	5364.6	5367.9	5371.2	5371.2	5374.6	5304.7	5234.8	5161.6	5091.7	4902.0
57.5°	5587.6	5680.7	5670.8	5664.1	5654.1	5644.1	5560.9	5477.7	5394.5	5311.3	5121.6
60°	5707.4	5787.2	5767.3	5747.3	5724.0	5704.0	5640.8	5577.6	5511.0	5447.8	5264.7
62.5°	5650.8	5710.7	5680.7	5654.1	5624.2	5594.2	5514.3	5431.1	5351.3	5268.1	5135.0
65°	5278.1	5314.7	5274.7	5238.1	5201.5	5161.6	5095.0	5028.5	4958.6	4892.0	4802.2
67.5°	4649.1	4655.7	4652.4	4649.1	4645.8	4642.4	4545.9	4449.4	4349.6	4253.1	4246.4
70°	3787.2	3747.2	3753.9	3763.9	3770.5	3777.2	3704.0	3634.1	3560.9	3487.6	3520.9
72.5°	2921.9	2852.0	2868.7	2888.6	2905.3	2921.9	2862.0	2805.4	2745.5	2685.6	2732.2
75°	2169.8	2126.5	2143.2	2163.1	2179.8	2196.4	2173.1	2149.8	2123.2	2099.9	2143.2
77.5°	1654.0	1627.3	1630.7	1630.7	1634.0	1634.0	1637.3	1644.0	1647.3	1650.6	1697.2
80°	1347.8	1344.5	1341.1	1337.8	1331.2	1327.8	1361.1	1394.4	1427.7	1461.0	1484.2
82.5°	1178.1	1211.4	1191.4	1174.8	1154.8	1134.8	1164.8	1194.7	1224.7	1254.6	1244.6
85°	958.4	998.4	961.8	925.2	885.2	848.6	875.2	898.5	925.2	948.5	935.1
87.5°	379.4	389.4	329.5	272.9	213.0	153.1	242.9	329.5	419.3	505.8	519.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1	2396.1
2.5°	2585.8	2572.5	2562.5	2559.2	2552.5	2549.2	2542.5	2535.9	2525.9	2519.2	2509.2
5°	2672.3	2652.3	2629.0	2595.8	2565.8	2532.5	2499.3	2469.3	2439.4	2406.1	2376.1
7.5°	2675.6	2629.0	2582.5	2539.2	2492.6	2449.3	2402.7	2362.8	2319.6	2276.3	2236.4
10°	2639.0	2582.5	2525.9	2469.3	2416.1	2359.5	2302.9	2256.3	2206.4	2156.5	2109.9
12.5°	2609.1	2545.8	2482.6	2416.1	2352.8	2286.3	2219.7	2173.1	2126.5	2079.9	2033.4
15°	2572.5	2532.5	2495.9	2436.0	2376.1	2316.2	2256.3	2193.1	2133.2	2070.0	2006.7
17.5°	2542.5	2532.5	2522.6	2482.6	2442.7	2399.4	2359.5	2296.3	2233.0	2166.5	2103.2
20°	2525.9	2539.2	2552.5	2532.5	2512.6	2489.3	2469.3	2422.7	2376.1	2326.2	2279.6
22.5°	2545.8	2595.8	2642.4	2645.7	2652.3	2655.7	2659.0	2615.7	2572.5	2525.9	2482.6
25°	2592.4	2672.3	2752.2	2795.4	2838.7	2885.3	2928.6	2901.9	2875.3	2848.7	2822.1
27.5°	2655.7	2755.5	2855.3	2918.6	2978.5	3041.7	3104.9	3101.6	3098.3	3091.6	3088.3
30°	2645.7	2722.2	2798.8	2875.3	2951.9	3028.4	3104.9	3144.9	3181.5	3221.4	3261.3
32.5°	2702.3	2765.5	2832.0	2911.9	2991.8	3075.0	3154.9	3238.1	3317.9	3401.1	3484.3
35°	2788.8	2845.4	2905.3	2991.8	3081.6	3168.2	3258.0	3357.9	3461.0	3564.2	3664.0
37.5°	2918.6	2968.5	3021.7	3095.0	3171.5	3244.7	3321.3	3467.7	3614.1	3763.9	3910.3
40°	3068.3	3101.6	3134.9	3204.8	3274.7	3344.5	3414.4	3597.5	3780.5	3963.5	4146.6
42.5°	3284.6	3274.7	3264.7	3321.3	3381.2	3437.7	3497.6	3664.0	3830.4	3996.8	4163.2
45°	3514.3	3474.3	3434.4	3461.0	3491.0	3517.6	3547.5	3717.3	3887.0	4060.0	4229.8
47.5°	3790.5	3690.6	3590.8	3567.5	3544.2	3517.6	3494.3	3677.3	3860.4	4046.7	4229.8
50°	4103.3	3953.6	3807.1	3747.2	3684.0	3624.1	3560.9	3710.6	3863.7	4016.8	4166.5
52.5°	4429.4	4243.1	4060.0	3966.9	3873.7	3777.2	3684.0	3810.5	3940.2	4070.0	4196.5
55°	4709.0	4519.3	4326.3	4216.5	4106.6	3996.8	3887.0	4013.5	4139.9	4266.4	4392.8
57.5°	4932.0	4742.3	4552.6	4449.4	4342.9	4239.8	4133.3	4253.1	4376.2	4499.3	4619.1
60°	5085.0	4902.0	4719.0	4619.1	4519.3	4419.5	4319.6	4462.7	4605.8	4752.3	4895.4
62.5°	5005.2	4872.1	4738.9	4695.7	4652.4	4605.8	4562.6	4699.0	4832.1	4968.6	5105.0
65°	4712.3	4622.5	4532.6	4575.9	4622.5	4665.7	4712.3	4802.2	4892.0	4985.2	5075.1
67.5°	4236.4	4229.8	4219.8	4316.3	4412.8	4512.6	4609.2	4669.1	4725.6	4785.5	4845.4
70°	3554.2	3590.8	3624.1	3790.5	3956.9	4123.3	4289.7	4313.0	4336.3	4359.6	4382.9
72.5°	2782.1	2828.7	2878.6	3098.3	3314.6	3534.2	3753.9	3740.6	3727.3	3710.6	3697.3
75°	2189.8	2233.0	2279.6	2482.6	2685.6	2888.6	3091.6	3035.1	2981.8	2925.2	2868.7
77.5°	1747.2	1793.7	1843.7	2033.4	2223.0	2416.1	2605.8	2469.3	2332.9	2196.4	2060.0
80°	1504.2	1527.5	1547.5	1677.3	1803.7	1933.5	2063.3	1923.5	1780.4	1637.3	1497.6
82.5°	1234.7	1221.3	1211.4	1287.9	1364.4	1441.0	1517.5	1384.4	1251.3	1114.8	981.7
85°	921.8	908.5	895.2	935.1	975.1	1018.3	1058.3	905.2	752.1	595.7	442.6
87.5°	535.8	549.1	562.4	605.7	648.9	695.5	738.8	582.4	426.0	266.2	109.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675994

CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	2396.1	2396.1
2.5°	2489.3	2472.6
5°	2352.8	2329.5
7.5°	2203.1	2173.1
10°	2066.6	2026.7
12.5°	1980.1	1930.2
15°	1946.8	1886.9
17.5°	2046.7	1990.1
20°	2199.7	2123.2
22.5°	2386.1	2292.9
25°	2708.9	2595.8
27.5°	2971.8	2855.3
30°	3134.9	3008.4
32.5°	3314.6	3148.2
35°	3501.0	3341.2
37.5°	3727.3	3547.5
40°	3960.2	3773.8
42.5°	4040.1	3920.3
45°	4116.6	4003.5
47.5°	4133.3	4040.1
50°	4149.9	4136.6
52.5°	4196.5	4193.2
55°	4396.2	4399.5
57.5°	4642.4	4662.4
60°	4868.7	4845.4
62.5°	4985.2	4865.4
65°	4905.3	4738.9
67.5°	4665.7	4486.0
70°	4139.9	3897.0
72.5°	3484.3	3271.3
75°	2685.6	2505.9
77.5°	1910.2	1760.5
80°	1344.5	1194.7
82.5°	861.9	742.1
85°	389.4	339.4
87.5°	109.8	106.5
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P675994
CATALOG NUMBER: CCW-SA-2C-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)