

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675995

Luminaire Tested: **CCW-SA-2D-740-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P675995
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2D-740-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @800mA w/
SLR distribution lens
Light Source: (32) 4000K CCT, 70 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9255.4 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G3

Input Watts (W): 80.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P675995

CATALOG NUMBER: CCW-SA-2D-740-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 13.1 fc

Type IV - Short - N/A

REPORT NUMBER: P675995
CATALOG NUMBER: CCW-SA-2D-740-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P675995

CATALOG NUMBER: CCW-SA-2D-740-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1904.3	0.0	1904.3
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	7351.0	0.0	7351.0
	% Fixture	79.4	0.0	79.4
Total	Lumens	9255.4	0.0	9255.4
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.7	2.5
10°-20°	484.9	5.2
20°-30°	709.4	7.7
30°-40°	999.4	10.8
40°-50°	1373.4	14.8
50°-60°	1871.9	20.2
60°-70°	2048.8	22.1
70°-80°	1183.2	12.8
80°-90°	354.7	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9255.4	100.0
0°-180°	9255.4	100.0

Coefficient of Utilization



REPORT NUMBER: P675995


CATALOG NUMBER: CCW-SA-2D-740-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	950.6	10.3			
FM	(30°-60°)	3377.6	36.5			
FH	(60°-80°)	2721.6	29.4			G2/5000
FVH	(80°-90°)	301.3	3.3			G3/500
BL	(0°-30°)	473.4	5.1	B1/500		
BM	(30°-60°)	867.2	9.4	B1/1000		
BH	(60°-80°)	510.4	5.5	B2/1000		G2/1000
BVH	(80°-90°)	53.4	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short





REPORT NUMBER: P675995

CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6
2.5°	3050.0	3033.6	3021.3	3009.0	2992.5	2980.2	2963.8	2947.4	2926.9	2910.4	2889.9
5°	2873.5	2824.2	2775.0	2746.2	2713.4	2684.7	2651.8	2614.9	2577.9	2536.9	2499.9
7.5°	2680.6	2619.0	2557.4	2508.2	2454.8	2405.5	2352.2	2307.0	2261.9	2216.7	2171.5
10°	2499.9	2442.5	2385.0	2323.4	2257.7	2196.2	2130.5	2068.9	2007.3	1945.8	1884.2
12.5°	2380.9	2311.1	2245.4	2175.6	2110.0	2040.2	1970.4	1912.9	1855.5	1793.9	1736.4
15°	2327.5	2261.9	2200.3	2130.5	2060.7	1990.9	1921.1	1855.5	1793.9	1728.2	1662.5
17.5°	2454.8	2360.4	2266.0	2175.6	2085.3	1995.0	1904.7	1822.6	1740.5	1658.4	1576.3
20°	2619.0	2499.9	2385.0	2274.2	2159.2	2048.4	1933.5	1818.5	1703.6	1588.6	1473.7
22.5°	2828.3	2692.9	2561.5	2417.8	2270.1	2126.4	1978.6	1834.9	1691.3	1543.5	1399.8
25°	3201.9	3041.8	2881.7	2676.5	2467.1	2261.9	2052.5	1863.7	1678.9	1490.1	1301.3
27.5°	3522.1	3304.5	3091.1	2844.8	2598.5	2352.2	2105.9	1888.3	1674.8	1457.3	1239.7
30°	3710.9	3497.5	3284.0	2984.3	2688.8	2389.1	2089.4	1847.2	1609.2	1367.0	1124.8
32.5°	3883.3	3645.2	3407.1	3078.7	2746.2	2417.8	2085.3	1818.5	1555.8	1289.0	1022.1
35°	4121.4	3858.7	3600.1	3218.3	2836.6	2454.8	2073.0	1798.0	1518.8	1243.8	964.7
37.5°	4375.9	4051.6	3731.4	3308.6	2885.8	2463.0	2040.2	1769.3	1498.3	1227.4	956.5
40°	4655.1	4261.0	3871.0	3403.0	2939.2	2471.2	2003.2	1732.3	1461.4	1186.3	915.4
42.5°	4835.7	4408.8	3981.8	3476.9	2976.1	2471.2	1966.3	1699.5	1432.6	1161.7	894.9
45°	4938.3	4523.7	4113.2	3567.2	3021.3	2475.3	1929.3	1666.6	1403.9	1137.1	874.4
47.5°	4983.5	4597.6	4211.7	3637.0	3066.4	2491.7	1917.0	1650.2	1379.3	1112.5	841.5
50°	5102.5	4761.8	4421.1	3805.3	3193.7	2577.9	1962.2	1674.8	1391.6	1104.2	816.9
52.5°	5172.3	4880.8	4589.4	3957.2	3325.0	2692.9	2060.7	1740.5	1420.3	1100.1	779.9
55°	5426.8	5147.7	4868.5	4195.3	3518.0	2844.8	2167.4	1814.4	1461.4	1104.2	751.2
57.5°	5751.1	5455.5	5164.1	4437.5	3710.9	2984.3	2257.7	1880.1	1498.3	1120.7	738.9
60°	5976.9	5689.5	5406.3	4634.5	3858.7	3087.0	2311.1	1917.0	1523.0	1124.8	730.7
62.5°	6001.5	5632.1	5266.7	4515.5	3764.3	3009.0	2257.7	1876.0	1494.2	1108.3	726.6
65°	5845.5	5414.5	4983.5	4265.1	3546.7	2828.3	2110.0	1761.0	1412.1	1059.1	710.2
67.5°	5533.5	5028.6	4523.7	3866.9	3210.1	2553.3	1896.5	1596.8	1301.3	1001.6	702.0
70°	4807.0	4363.6	3924.4	3353.8	2787.3	2216.7	1646.1	1399.8	1157.6	911.3	665.0
72.5°	4035.2	3620.6	3210.1	2746.2	2286.5	1822.6	1358.8	1174.0	989.3	800.5	615.7
75°	3091.1	2779.1	2471.2	2126.4	1781.6	1432.6	1087.8	952.4	816.9	681.4	546.0
77.5°	2171.5	2003.2	1839.0	1580.4	1321.8	1063.2	804.6	714.3	624.0	533.6	443.3
80°	1473.7	1379.3	1289.0	1104.2	919.5	730.7	546.0	488.5	426.9	369.4	307.9
82.5°	915.4	911.3	903.1	775.8	648.6	521.3	394.1	344.8	299.7	250.4	201.1
85°	418.7	488.5	554.2	484.4	414.6	344.8	275.0	242.2	209.4	172.4	139.6
87.5°	131.4	160.1	184.7	176.5	164.2	156.0	143.7	123.1	102.6	82.1	61.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995
 CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995

CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6
2.5°	2873.5	2861.2	2844.8	2828.3	2807.8	2791.4	2770.9	2750.3	2746.2	2738.0	2733.9
5°	2475.3	2450.7	2421.9	2397.3	2372.7	2344.0	2319.3	2290.6	2270.1	2245.4	2224.9
7.5°	2126.4	2085.3	2040.2	1995.0	1954.0	1912.9	1867.8	1826.7	1806.2	1785.7	1765.1
10°	1847.2	1806.2	1769.3	1728.2	1699.5	1674.8	1646.1	1617.4	1592.7	1568.1	1543.5
12.5°	1707.7	1678.9	1650.2	1621.5	1588.6	1559.9	1527.1	1494.2	1465.5	1440.9	1412.1
15°	1621.5	1580.4	1535.3	1494.2	1449.1	1408.0	1362.9	1317.7	1284.9	1256.1	1223.3
17.5°	1518.8	1457.3	1399.8	1338.2	1289.0	1239.7	1186.3	1137.1	1100.1	1059.1	1022.1
20°	1403.9	1334.1	1260.2	1190.4	1133.0	1079.6	1022.1	964.7	923.6	878.5	837.4
22.5°	1305.4	1215.1	1120.7	1026.2	964.7	903.1	837.4	775.8	738.9	697.8	660.9
25°	1198.7	1100.1	997.5	894.9	833.3	767.6	706.1	640.4	611.6	587.0	558.3
27.5°	1141.2	1042.7	940.0	841.5	784.1	722.5	665.0	603.4	582.9	558.3	537.8
30°	1026.2	931.8	833.3	734.8	693.7	656.8	615.7	574.7	566.5	562.4	554.2
32.5°	923.6	825.1	726.6	628.1	591.1	554.2	517.2	480.3	476.2	468.0	463.9
35°	870.3	775.8	677.3	582.9	550.1	513.1	480.3	443.3	435.1	422.8	414.6
37.5°	857.9	759.4	656.8	558.3	525.4	492.6	455.7	422.8	414.6	406.4	398.2
40°	825.1	730.7	640.4	546.0	513.1	480.3	443.3	410.5	402.3	394.1	385.9
42.5°	800.5	710.2	615.7	521.3	492.6	463.9	431.0	402.3	394.1	385.9	373.6
45°	779.9	685.5	587.0	492.6	472.1	451.5	426.9	406.4	398.2	385.9	377.7
47.5°	747.1	656.8	562.4	468.0	447.4	431.0	410.5	390.0	381.8	373.6	365.3
50°	722.5	628.1	533.6	439.2	422.8	406.4	390.0	373.6	373.6	377.7	377.7
52.5°	689.6	599.3	509.0	418.7	402.3	385.9	369.4	353.0	357.1	361.2	365.3
55°	660.9	574.7	484.4	394.1	377.7	361.2	340.7	324.3	328.4	332.5	336.6
57.5°	648.6	558.3	468.0	377.7	361.2	340.7	324.3	303.8	303.8	303.8	303.8
60°	640.4	546.0	455.7	361.2	340.7	324.3	303.8	283.2	279.1	279.1	275.0
62.5°	636.3	541.9	451.5	357.1	332.5	312.0	287.3	262.7	258.6	254.5	250.4
65°	619.9	533.6	443.3	353.0	324.3	299.7	270.9	242.2	238.1	238.1	234.0
67.5°	615.7	525.4	439.2	348.9	320.2	287.3	258.6	225.8	221.7	217.6	213.5
70°	582.9	504.9	422.8	340.7	307.9	279.1	246.3	213.5	209.4	201.1	197.0
72.5°	541.9	472.1	398.2	324.3	291.5	258.6	225.8	192.9	188.8	184.7	176.5
75°	480.3	414.6	348.9	283.2	254.5	229.9	201.1	172.4	168.3	164.2	156.0
77.5°	394.1	340.7	291.5	238.1	217.6	197.0	176.5	156.0	151.9	147.8	139.6
80°	279.1	246.3	217.6	184.7	172.4	156.0	143.7	127.3	127.3	123.1	123.1
82.5°	184.7	168.3	151.9	135.5	127.3	119.0	110.8	102.6	102.6	98.5	98.5
85°	131.4	123.1	110.8	102.6	98.5	90.3	86.2	78.0	78.0	78.0	78.0
87.5°	61.6	61.6	57.5	57.5	53.4	53.4	49.3	45.2	45.2	45.2	45.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995
 CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675995

CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6
2.5°	2725.7	2713.4	2701.1	2684.7	2672.4	2655.9	2635.4	2619.0	2598.5	2598.5	2594.4
5°	2200.3	2188.0	2175.6	2159.2	2146.9	2130.5	2118.2	2101.8	2085.3	2085.3	2081.2
7.5°	1744.6	1720.0	1695.4	1666.6	1642.0	1625.6	1609.2	1588.6	1572.2	1559.9	1547.6
10°	1518.8	1494.2	1465.5	1440.9	1412.1	1391.6	1371.1	1346.4	1325.9	1309.5	1293.1
12.5°	1383.4	1354.6	1325.9	1297.2	1268.4	1239.7	1215.1	1186.3	1157.6	1137.1	1116.6
15°	1190.4	1161.7	1133.0	1104.2	1075.5	1042.7	1009.8	972.9	940.0	923.6	911.3
17.5°	981.1	952.4	919.5	890.8	857.9	833.3	808.7	784.1	759.4	743.0	730.7
20°	792.3	759.4	726.6	693.7	660.9	644.5	628.1	611.6	595.2	582.9	574.7
22.5°	619.9	599.3	582.9	562.4	541.9	529.5	521.3	509.0	496.7	496.7	496.7
25°	529.5	517.2	509.0	496.7	484.4	480.3	476.2	468.0	463.9	459.8	459.8
27.5°	513.1	500.8	488.5	476.2	463.9	459.8	455.7	447.4	443.3	443.3	443.3
30°	546.0	541.9	537.8	533.6	529.5	521.3	509.0	500.8	488.5	480.3	472.1
32.5°	455.7	451.5	451.5	447.4	443.3	451.5	455.7	463.9	468.0	472.1	476.2
35°	402.3	394.1	385.9	377.7	369.4	365.3	361.2	357.1	353.0	353.0	348.9
37.5°	390.0	381.8	373.6	365.3	357.1	353.0	348.9	344.8	340.7	340.7	336.6
40°	377.7	369.4	365.3	357.1	348.9	344.8	340.7	332.5	328.4	324.3	324.3
42.5°	365.3	361.2	353.0	348.9	340.7	336.6	332.5	324.3	320.2	316.1	312.0
45°	365.3	357.1	348.9	340.7	332.5	328.4	320.2	316.1	307.9	307.9	303.8
47.5°	357.1	348.9	340.7	332.5	324.3	320.2	312.0	307.9	299.7	295.6	291.5
50°	377.7	365.3	348.9	336.6	320.2	316.1	307.9	303.8	295.6	291.5	287.3
52.5°	369.4	357.1	340.7	328.4	312.0	303.8	299.7	291.5	283.2	279.1	275.0
55°	340.7	328.4	320.2	307.9	295.6	287.3	279.1	270.9	262.7	258.6	258.6
57.5°	303.8	299.7	295.6	291.5	287.3	279.1	270.9	258.6	250.4	246.3	242.2
60°	270.9	275.0	279.1	283.2	287.3	275.0	262.7	250.4	238.1	234.0	229.9
62.5°	246.3	254.5	262.7	266.8	275.0	262.7	250.4	238.1	225.8	221.7	217.6
65°	229.9	234.0	234.0	238.1	238.1	229.9	225.8	217.6	209.4	205.2	205.2
67.5°	209.4	209.4	209.4	205.2	205.2	201.1	201.1	197.0	192.9	188.8	188.8
70°	188.8	188.8	188.8	184.7	184.7	180.6	180.6	176.5	172.4	172.4	168.3
72.5°	172.4	172.4	168.3	168.3	164.2	164.2	164.2	160.1	160.1	156.0	156.0
75°	151.9	151.9	147.8	147.8	143.7	143.7	143.7	139.6	139.6	139.6	135.5
77.5°	135.5	135.5	131.4	131.4	127.3	127.3	127.3	123.1	123.1	119.0	119.0
80°	119.0	119.0	114.9	114.9	110.8	110.8	106.7	106.7	102.6	102.6	98.5
82.5°	94.4	94.4	94.4	94.4	94.4	90.3	90.3	86.2	82.1	82.1	78.0
85°	78.0	78.0	78.0	73.9	73.9	73.9	69.8	69.8	65.7	61.6	61.6
87.5°	45.2	45.2	45.2	41.0	41.0	41.0	41.0	41.0	41.0	41.0	36.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995
 CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675995

CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6
2.5°	2594.4	2590.3	2573.8	2557.4	2573.8	2590.3	2590.3	2590.3	2586.1	2586.1	2586.1
5°	2081.2	2077.1	2068.9	2060.7	2060.7	2056.6	2064.8	2073.0	2081.2	2089.4	2097.7
7.5°	1531.2	1518.8	1506.5	1494.2	1502.4	1506.5	1518.8	1527.1	1539.4	1547.6	1568.1
10°	1276.7	1260.2	1247.9	1235.6	1227.4	1219.2	1211.0	1206.9	1198.7	1190.4	1198.7
12.5°	1091.9	1071.4	1050.9	1026.2	1022.1	1018.0	1009.8	1001.6	993.4	985.2	981.1
15°	894.9	878.5	870.3	857.9	841.5	825.1	816.9	812.8	804.6	796.4	792.3
17.5°	714.3	697.8	685.5	673.2	669.1	660.9	660.9	660.9	660.9	660.9	660.9
20°	562.4	550.1	550.1	546.0	546.0	541.9	546.0	550.1	550.1	554.2	558.3
22.5°	492.6	492.6	488.5	484.4	488.5	488.5	492.6	496.7	500.8	504.9	509.0
25°	455.7	451.5	455.7	459.8	459.8	459.8	463.9	463.9	468.0	468.0	468.0
27.5°	439.2	439.2	443.3	443.3	447.4	447.4	447.4	443.3	443.3	439.2	439.2
30°	463.9	455.7	455.7	455.7	451.5	447.4	443.3	443.3	439.2	435.1	431.0
32.5°	480.3	484.4	480.3	472.1	468.0	459.8	455.7	447.4	443.3	435.1	426.9
35°	348.9	344.8	353.0	357.1	361.2	365.3	369.4	373.6	373.6	377.7	377.7
37.5°	336.6	332.5	332.5	328.4	328.4	328.4	328.4	328.4	324.3	324.3	328.4
40°	320.2	316.1	316.1	312.0	312.0	307.9	307.9	307.9	307.9	307.9	307.9
42.5°	307.9	303.8	303.8	303.8	303.8	299.7	299.7	295.6	295.6	291.5	291.5
45°	303.8	299.7	295.6	291.5	291.5	287.3	287.3	287.3	283.2	283.2	283.2
47.5°	287.3	283.2	283.2	279.1	279.1	275.0	275.0	275.0	270.9	270.9	270.9
50°	279.1	275.0	275.0	270.9	270.9	266.8	266.8	266.8	262.7	262.7	262.7
52.5°	266.8	262.7	262.7	262.7	258.6	254.5	254.5	254.5	250.4	250.4	250.4
55°	254.5	250.4	250.4	250.4	246.3	242.2	242.2	242.2	238.1	238.1	238.1
57.5°	238.1	234.0	234.0	229.9	229.9	229.9	229.9	229.9	225.8	225.8	225.8
60°	225.8	221.7	221.7	217.6	217.6	213.5	213.5	213.5	213.5	213.5	213.5
62.5°	213.5	209.4	205.2	201.1	205.2	205.2	205.2	205.2	201.1	201.1	201.1
65°	201.1	197.0	192.9	188.8	188.8	188.8	188.8	188.8	188.8	188.8	188.8
67.5°	184.7	180.6	176.5	172.4	176.5	176.5	176.5	176.5	176.5	176.5	176.5
70°	168.3	164.2	164.2	160.1	160.1	156.0	156.0	160.1	160.1	160.1	160.1
72.5°	151.9	147.8	147.8	143.7	143.7	143.7	143.7	143.7	143.7	143.7	143.7
75°	135.5	131.4	131.4	127.3	127.3	127.3	127.3	127.3	127.3	127.3	127.3
77.5°	114.9	110.8	110.8	110.8	110.8	110.8	110.8	114.9	114.9	114.9	114.9
80°	98.5	94.4	94.4	94.4	94.4	94.4	94.4	94.4	94.4	94.4	94.4
82.5°	78.0	73.9	73.9	73.9	73.9	73.9	73.9	73.9	73.9	73.9	73.9
85°	57.5	53.4	53.4	53.4	57.5	57.5	57.5	57.5	57.5	57.5	57.5
87.5°	36.9	32.8	32.8	32.8	36.9	36.9	36.9	36.9	32.8	32.8	32.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995
 CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995

CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6
2.5°	2586.1	2586.1	2586.1	2582.0	2577.9	2573.8	2569.7	2582.0	2590.3	2602.6	2610.8
5°	2101.8	2110.0	2114.1	2126.4	2138.7	2151.0	2163.3	2171.5	2179.8	2183.9	2192.1
7.5°	1584.5	1605.1	1621.5	1637.9	1654.3	1666.6	1683.0	1695.4	1707.7	1720.0	1732.3
10°	1202.8	1211.0	1215.1	1231.5	1243.8	1260.2	1272.5	1284.9	1297.2	1305.4	1317.7
12.5°	977.0	968.8	964.7	964.7	964.7	964.7	964.7	972.9	981.1	989.3	997.5
15°	788.2	784.1	779.9	775.8	771.7	763.5	759.4	767.6	775.8	784.1	792.3
17.5°	660.9	660.9	660.9	656.8	652.7	648.6	644.5	648.6	652.7	652.7	656.8
20°	566.5	570.6	574.7	578.8	578.8	582.9	582.9	587.0	591.1	591.1	595.2
22.5°	509.0	513.1	513.1	513.1	517.2	517.2	517.2	521.3	525.4	529.5	533.6
25°	463.9	463.9	459.8	459.8	463.9	463.9	463.9	463.9	468.0	468.0	468.0
27.5°	439.2	435.1	435.1	435.1	435.1	431.0	431.0	431.0	431.0	431.0	431.0
30°	426.9	422.8	418.7	414.6	414.6	410.5	406.4	406.4	406.4	406.4	406.4
32.5°	422.8	414.6	406.4	402.3	402.3	398.2	394.1	390.0	390.0	385.9	381.8
35°	377.7	373.6	373.6	369.4	365.3	361.2	357.1	357.1	357.1	353.0	353.0
37.5°	328.4	332.5	332.5	332.5	336.6	336.6	336.6	336.6	340.7	340.7	340.7
40°	307.9	307.9	307.9	312.0	316.1	316.1	320.2	320.2	324.3	324.3	324.3
42.5°	291.5	287.3	287.3	291.5	291.5	295.6	295.6	299.7	303.8	303.8	307.9
45°	283.2	279.1	279.1	279.1	279.1	275.0	275.0	279.1	283.2	287.3	291.5
47.5°	266.8	266.8	262.7	262.7	262.7	262.7	262.7	262.7	266.8	266.8	266.8
50°	258.6	258.6	254.5	254.5	254.5	254.5	254.5	254.5	254.5	254.5	254.5
52.5°	250.4	246.3	246.3	246.3	246.3	242.2	242.2	242.2	242.2	242.2	242.2
55°	238.1	234.0	234.0	234.0	234.0	234.0	234.0	234.0	238.1	238.1	238.1
57.5°	225.8	221.7	221.7	221.7	225.8	225.8	225.8	225.8	229.9	229.9	229.9
60°	213.5	213.5	213.5	213.5	213.5	213.5	213.5	217.6	217.6	221.7	221.7
62.5°	201.1	201.1	201.1	201.1	205.2	205.2	205.2	205.2	209.4	209.4	209.4
65°	188.8	188.8	188.8	188.8	192.9	192.9	192.9	192.9	192.9	192.9	192.9
67.5°	176.5	176.5	176.5	176.5	176.5	176.5	176.5	180.6	180.6	184.7	184.7
70°	160.1	156.0	156.0	160.1	160.1	164.2	164.2	168.3	168.3	172.4	172.4
72.5°	143.7	143.7	143.7	143.7	143.7	143.7	143.7	147.8	151.9	151.9	156.0
75°	127.3	127.3	127.3	127.3	131.4	131.4	131.4	135.5	135.5	139.6	139.6
77.5°	114.9	110.8	110.8	110.8	114.9	114.9	114.9	119.0	119.0	123.1	123.1
80°	94.4	94.4	94.4	94.4	98.5	98.5	98.5	98.5	102.6	102.6	102.6
82.5°	78.0	78.0	78.0	78.0	78.0	78.0	78.0	78.0	82.1	82.1	82.1
85°	57.5	57.5	57.5	57.5	61.6	61.6	61.6	61.6	61.6	61.6	61.6
87.5°	36.9	36.9	36.9	36.9	36.9	36.9	36.9	36.9	41.0	41.0	41.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995
 CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675995

CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6
2.5°	2610.8	2610.8	2610.8	2610.8	2619.0	2623.1	2631.3	2635.4	2631.3	2627.2	2619.0
5°	2196.2	2200.3	2200.3	2204.4	2204.4	2204.4	2204.4	2204.4	2212.6	2220.8	2229.0
7.5°	1736.4	1740.5	1744.6	1748.7	1748.7	1748.7	1744.6	1744.6	1748.7	1748.7	1752.8
10°	1330.0	1346.4	1358.8	1371.1	1362.9	1350.5	1342.3	1330.0	1330.0	1330.0	1325.9
12.5°	1005.7	1009.8	1018.0	1022.1	1018.0	1018.0	1013.9	1009.8	1013.9	1022.1	1026.2
15°	796.4	796.4	800.5	800.5	804.6	808.7	808.7	812.8	821.0	825.1	833.3
17.5°	660.9	665.0	665.0	669.1	669.1	673.2	673.2	673.2	681.4	689.6	702.0
20°	595.2	595.2	595.2	595.2	595.2	591.1	591.1	587.0	591.1	599.3	603.4
22.5°	533.6	537.8	537.8	537.8	533.6	529.5	521.3	517.2	517.2	521.3	521.3
25°	468.0	463.9	463.9	459.8	459.8	463.9	463.9	463.9	468.0	468.0	472.1
27.5°	431.0	426.9	426.9	422.8	422.8	426.9	426.9	426.9	426.9	426.9	426.9
30°	402.3	402.3	398.2	394.1	398.2	398.2	402.3	402.3	406.4	406.4	410.5
32.5°	381.8	377.7	377.7	373.6	377.7	377.7	381.8	381.8	385.9	390.0	390.0
35°	353.0	353.0	353.0	353.0	353.0	353.0	348.9	348.9	348.9	348.9	348.9
37.5°	336.6	336.6	332.5	328.4	328.4	328.4	328.4	328.4	324.3	320.2	316.1
40°	324.3	320.2	320.2	316.1	312.0	312.0	307.9	303.8	303.8	299.7	299.7
42.5°	307.9	303.8	303.8	299.7	295.6	295.6	291.5	287.3	287.3	287.3	283.2
45°	287.3	287.3	283.2	279.1	279.1	279.1	275.0	275.0	275.0	275.0	270.9
47.5°	266.8	266.8	262.7	262.7	262.7	262.7	258.6	258.6	258.6	258.6	258.6
50°	254.5	254.5	254.5	254.5	254.5	254.5	250.4	250.4	250.4	250.4	250.4
52.5°	242.2	242.2	242.2	242.2	242.2	242.2	242.2	242.2	242.2	242.2	242.2
55°	238.1	238.1	238.1	238.1	238.1	238.1	234.0	234.0	234.0	238.1	238.1
57.5°	229.9	229.9	225.8	225.8	225.8	225.8	225.8	225.8	225.8	225.8	225.8
60°	221.7	221.7	221.7	221.7	221.7	221.7	221.7	221.7	221.7	221.7	221.7
62.5°	209.4	209.4	209.4	209.4	209.4	213.5	213.5	213.5	213.5	213.5	209.4
65°	192.9	197.0	197.0	197.0	197.0	197.0	197.0	197.0	197.0	197.0	197.0
67.5°	184.7	184.7	184.7	184.7	184.7	184.7	184.7	184.7	184.7	184.7	184.7
70°	172.4	172.4	168.3	168.3	168.3	172.4	172.4	172.4	172.4	172.4	172.4
72.5°	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	160.1	160.1
75°	139.6	139.6	139.6	139.6	139.6	139.6	139.6	139.6	139.6	139.6	139.6
77.5°	123.1	123.1	119.0	119.0	119.0	123.1	123.1	123.1	123.1	127.3	127.3
80°	102.6	102.6	102.6	102.6	102.6	102.6	102.6	102.6	102.6	106.7	106.7
82.5°	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1	82.1	86.2	86.2
85°	61.6	65.7	65.7	65.7	65.7	65.7	65.7	65.7	65.7	69.8	69.8
87.5°	41.0	41.0	41.0	41.0	41.0	41.0	36.9	36.9	36.9	36.9	32.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995
 CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675995

CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6
2.5°	2614.9	2619.0	2623.1	2623.1	2627.2	2631.3	2631.3	2647.7	2664.1	2672.4	2680.6
5°	2237.2	2233.1	2233.1	2229.0	2224.9	2237.2	2249.5	2274.2	2298.8	2302.9	2311.1
7.5°	1752.8	1756.9	1761.0	1761.0	1765.1	1752.8	1736.4	1740.5	1744.6	1765.1	1781.6
10°	1325.9	1330.0	1334.1	1334.1	1338.2	1334.1	1325.9	1338.2	1350.5	1367.0	1387.5
12.5°	1030.4	1042.7	1055.0	1063.2	1075.5	1083.7	1087.8	1104.2	1116.6	1137.1	1157.6
15°	841.5	849.7	857.9	866.2	874.4	882.6	890.8	907.2	923.6	948.3	972.9
17.5°	710.2	710.2	714.3	714.3	714.3	722.5	730.7	738.9	743.0	767.6	792.3
20°	607.5	603.4	599.3	595.2	591.1	599.3	603.4	607.5	611.6	628.1	640.4
22.5°	521.3	521.3	525.4	525.4	525.4	521.3	513.1	517.2	517.2	525.4	537.8
25°	472.1	472.1	472.1	468.0	468.0	472.1	476.2	476.2	472.1	476.2	480.3
27.5°	426.9	431.0	431.0	435.1	435.1	439.2	439.2	439.2	439.2	443.3	447.4
30°	410.5	410.5	414.6	414.6	414.6	418.7	422.8	422.8	422.8	426.9	435.1
32.5°	394.1	398.2	402.3	406.4	410.5	414.6	414.6	418.7	418.7	422.8	426.9
35°	348.9	344.8	344.8	340.7	336.6	336.6	336.6	336.6	332.5	336.6	336.6
37.5°	312.0	312.0	312.0	307.9	307.9	312.0	312.0	312.0	312.0	316.1	316.1
40°	295.6	295.6	295.6	295.6	295.6	295.6	295.6	299.7	299.7	303.8	307.9
42.5°	283.2	283.2	283.2	283.2	283.2	287.3	287.3	287.3	287.3	291.5	291.5
45°	270.9	270.9	270.9	270.9	270.9	270.9	270.9	275.0	275.0	279.1	283.2
47.5°	258.6	258.6	258.6	258.6	258.6	262.7	266.8	266.8	266.8	270.9	270.9
50°	250.4	250.4	250.4	250.4	250.4	254.5	254.5	258.6	258.6	262.7	266.8
52.5°	242.2	242.2	242.2	242.2	242.2	246.3	246.3	250.4	250.4	254.5	258.6
55°	238.1	238.1	238.1	234.0	234.0	238.1	238.1	242.2	242.2	246.3	246.3
57.5°	225.8	225.8	225.8	225.8	225.8	225.8	225.8	229.9	229.9	234.0	238.1
60°	221.7	221.7	217.6	217.6	213.5	217.6	217.6	221.7	221.7	225.8	225.8
62.5°	209.4	209.4	209.4	205.2	205.2	209.4	209.4	209.4	209.4	213.5	217.6
65°	197.0	197.0	197.0	192.9	192.9	197.0	197.0	197.0	197.0	201.1	205.2
67.5°	184.7	184.7	184.7	180.6	180.6	180.6	180.6	184.7	184.7	188.8	192.9
70°	172.4	172.4	172.4	168.3	168.3	168.3	164.2	168.3	172.4	176.5	176.5
72.5°	160.1	160.1	160.1	156.0	156.0	156.0	151.9	156.0	156.0	160.1	160.1
75°	139.6	139.6	139.6	139.6	139.6	139.6	135.5	135.5	135.5	139.6	139.6
77.5°	127.3	127.3	127.3	123.1	123.1	123.1	119.0	119.0	119.0	123.1	123.1
80°	106.7	106.7	106.7	102.6	102.6	102.6	98.5	98.5	98.5	102.6	102.6
82.5°	86.2	86.2	86.2	82.1	82.1	82.1	78.0	78.0	78.0	82.1	82.1
85°	69.8	69.8	69.8	69.8	69.8	69.8	65.7	65.7	65.7	69.8	73.9
87.5°	32.8	32.8	36.9	36.9	36.9	36.9	32.8	32.8	28.7	28.7	32.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995
 CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675995

CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6
2.5°	2688.8	2697.0	2717.5	2733.9	2754.5	2770.9	2783.2	2799.6	2811.9	2824.2	2832.4
5°	2315.2	2319.3	2339.8	2360.4	2376.8	2397.3	2426.1	2454.8	2483.5	2512.3	2532.8
7.5°	1802.1	1818.5	1843.1	1871.9	1896.5	1921.1	1949.9	1982.7	2011.4	2040.2	2068.9
10°	1403.9	1420.3	1445.0	1469.6	1490.1	1514.7	1547.6	1580.4	1613.3	1646.1	1678.9
12.5°	1178.1	1198.7	1227.4	1256.1	1280.8	1309.5	1350.5	1387.5	1428.5	1465.5	1506.5
15°	993.4	1018.0	1055.0	1096.0	1133.0	1169.9	1211.0	1252.0	1289.0	1330.0	1371.1
17.5°	816.9	841.5	874.4	911.3	944.1	977.0	1026.2	1071.4	1120.7	1165.8	1211.0
20°	656.8	669.1	702.0	734.8	767.6	800.5	837.4	874.4	911.3	948.3	1005.7
22.5°	546.0	554.2	570.6	582.9	599.3	611.6	648.6	685.5	718.4	755.3	808.7
25°	480.3	484.4	496.7	504.9	517.2	525.4	550.1	570.6	595.2	615.7	665.0
27.5°	447.4	451.5	455.7	459.8	463.9	468.0	484.4	500.8	513.1	529.5	574.7
30°	439.2	443.3	455.7	463.9	476.2	484.4	492.6	500.8	509.0	517.2	546.0
32.5°	431.0	435.1	435.1	431.0	431.0	426.9	435.1	439.2	447.4	451.5	476.2
35°	340.7	340.7	344.8	348.9	353.0	357.1	369.4	377.7	390.0	398.2	418.7
37.5°	320.2	320.2	324.3	332.5	336.6	340.7	348.9	357.1	365.3	373.6	394.1
40°	307.9	312.0	316.1	320.2	324.3	328.4	336.6	340.7	348.9	353.0	369.4
42.5°	295.6	295.6	299.7	307.9	312.0	316.1	324.3	328.4	336.6	340.7	357.1
45°	287.3	291.5	295.6	299.7	299.7	303.8	312.0	320.2	324.3	332.5	348.9
47.5°	275.0	275.0	283.2	287.3	295.6	299.7	307.9	312.0	320.2	324.3	340.7
50°	266.8	270.9	279.1	283.2	291.5	295.6	307.9	316.1	328.4	336.6	344.8
52.5°	258.6	262.7	270.9	275.0	283.2	287.3	303.8	320.2	332.5	348.9	348.9
55°	250.4	250.4	258.6	270.9	279.1	287.3	295.6	307.9	316.1	324.3	324.3
57.5°	238.1	242.2	250.4	262.7	270.9	279.1	287.3	295.6	299.7	307.9	303.8
60°	229.9	229.9	242.2	254.5	266.8	279.1	279.1	279.1	275.0	275.0	275.0
62.5°	217.6	221.7	238.1	258.6	275.0	291.5	279.1	266.8	254.5	242.2	246.3
65°	209.4	213.5	221.7	234.0	242.2	250.4	242.2	238.1	229.9	221.7	225.8
67.5°	192.9	197.0	201.1	201.1	205.2	205.2	205.2	205.2	205.2	205.2	209.4
70°	180.6	180.6	180.6	184.7	184.7	184.7	184.7	184.7	184.7	184.7	188.8
72.5°	164.2	164.2	164.2	164.2	164.2	164.2	164.2	164.2	164.2	164.2	168.3
75°	143.7	143.7	143.7	143.7	143.7	143.7	143.7	143.7	143.7	143.7	147.8
77.5°	127.3	127.3	127.3	127.3	127.3	127.3	127.3	127.3	123.1	123.1	127.3
80°	106.7	106.7	106.7	106.7	102.6	102.6	102.6	102.6	102.6	102.6	106.7
82.5°	86.2	86.2	86.2	86.2	82.1	82.1	82.1	82.1	78.0	78.0	82.1
85°	78.0	82.1	82.1	86.2	86.2	86.2	82.1	78.0	73.9	69.8	69.8
87.5°	32.8	32.8	32.8	32.8	28.7	28.7	28.7	28.7	28.7	28.7	28.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995
 CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995

CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6
2.5°	2844.8	2853.0	2861.2	2873.5	2889.9	2902.2	2914.5	2939.2	2967.9	2992.5	3017.2
5°	2553.3	2573.8	2594.4	2619.0	2643.6	2664.1	2688.8	2738.0	2787.3	2832.4	2881.7
7.5°	2093.5	2122.3	2146.9	2188.0	2224.9	2266.0	2302.9	2364.5	2421.9	2483.5	2541.0
10°	1711.8	1744.6	1777.5	1830.8	1888.3	1941.7	1995.0	2044.3	2097.7	2146.9	2196.2
12.5°	1547.6	1584.5	1625.6	1658.4	1695.4	1728.2	1761.0	1818.5	1876.0	1933.5	1990.9
15°	1412.1	1453.2	1494.2	1535.3	1572.2	1613.3	1650.2	1699.5	1752.8	1802.1	1851.4
17.5°	1256.1	1297.2	1342.3	1387.5	1432.6	1477.8	1523.0	1592.7	1662.5	1728.2	1798.0
20°	1059.1	1116.6	1169.9	1231.5	1293.1	1354.6	1416.2	1490.1	1564.0	1633.8	1707.7
22.5°	862.0	915.4	968.8	1042.7	1116.6	1186.3	1260.2	1358.8	1453.2	1551.7	1646.1
25°	718.4	767.6	816.9	899.0	977.0	1059.1	1137.1	1256.1	1371.1	1490.1	1605.1
27.5°	619.9	665.0	710.2	796.4	882.6	964.7	1050.9	1182.2	1309.5	1440.9	1568.1
30°	574.7	603.4	632.2	714.3	796.4	874.4	956.5	1083.7	1211.0	1338.2	1465.5
32.5°	500.8	525.4	550.1	624.0	697.8	767.6	841.5	972.9	1100.1	1231.5	1358.8
35°	443.3	463.9	484.4	554.2	619.9	689.6	755.3	886.7	1018.0	1149.4	1280.8
37.5°	410.5	431.0	447.4	509.0	574.7	636.3	697.8	829.2	956.5	1087.8	1215.1
40°	385.9	398.2	414.6	476.2	533.6	595.2	652.7	771.7	894.9	1013.9	1133.0
42.5°	369.4	385.9	398.2	451.5	509.0	562.4	615.7	730.7	845.6	956.5	1071.4
45°	365.3	381.8	398.2	443.3	488.5	529.5	574.7	685.5	796.4	907.2	1018.0
47.5°	357.1	369.4	385.9	422.8	455.7	492.6	525.4	636.3	747.1	853.8	964.7
50°	353.0	357.1	365.3	398.2	431.0	463.9	496.7	607.5	718.4	829.2	940.0
52.5°	348.9	348.9	348.9	377.7	406.4	431.0	459.8	570.6	685.5	796.4	907.2
55°	324.3	320.2	320.2	348.9	373.6	402.3	426.9	537.8	648.6	755.3	866.2
57.5°	299.7	295.6	291.5	316.1	340.7	365.3	390.0	500.8	615.7	726.6	837.4
60°	275.0	270.9	270.9	295.6	316.1	340.7	361.2	476.2	587.0	702.0	812.8
62.5°	246.3	250.4	250.4	270.9	295.6	316.1	336.6	451.5	570.6	685.5	800.5
65°	225.8	229.9	229.9	254.5	279.1	303.8	328.4	439.2	554.2	665.0	775.8
67.5°	209.4	213.5	213.5	242.2	266.8	295.6	320.2	418.7	521.3	619.9	718.4
70°	192.9	192.9	197.0	225.8	254.5	283.2	312.0	398.2	484.4	566.5	652.7
72.5°	172.4	176.5	180.6	209.4	234.0	262.7	287.3	365.3	443.3	521.3	599.3
75°	151.9	156.0	160.1	184.7	209.4	234.0	258.6	332.5	402.3	476.2	546.0
77.5°	135.5	139.6	143.7	164.2	184.7	205.2	225.8	279.1	336.6	390.0	443.3
80°	110.8	110.8	114.9	131.4	147.8	160.1	176.5	213.5	250.4	283.2	320.2
82.5°	82.1	86.2	86.2	98.5	106.7	119.0	127.3	147.8	164.2	184.7	201.1
85°	69.8	65.7	65.7	73.9	78.0	86.2	90.3	102.6	110.8	123.1	131.4
87.5°	28.7	24.6	24.6	28.7	36.9	41.0	45.2	45.2	49.3	49.3	49.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995
 CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675995

CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6
2.5°	3029.5	3037.7	3050.0	3058.2	3078.7	3095.2	3115.7	3132.1	3144.4	3165.0	3156.7
5°	2918.7	2955.6	2992.5	3029.5	3058.2	3087.0	3111.6	3140.3	3173.2	3234.7	3251.2
7.5°	2590.3	2639.5	2684.7	2733.9	2791.4	2848.9	2906.3	2963.8	3017.2	3095.2	3144.4
10°	2266.0	2335.7	2401.4	2471.2	2524.6	2577.9	2627.2	2680.6	2754.5	2832.4	2922.8
12.5°	2060.7	2130.5	2200.3	2270.1	2348.1	2421.9	2499.9	2573.8	2643.6	2705.2	2807.8
15°	1925.2	2003.2	2077.1	2151.0	2245.4	2335.7	2430.2	2520.5	2623.1	2705.2	2775.0
17.5°	1892.4	1986.8	2077.1	2171.5	2270.1	2368.6	2467.1	2565.6	2668.2	2791.4	2881.7
20°	1834.9	1962.2	2089.4	2216.7	2344.0	2467.1	2594.4	2717.5	2853.0	3000.8	3041.8
22.5°	1802.1	1954.0	2110.0	2261.9	2434.3	2610.8	2783.2	2955.6	3099.3	3210.1	3333.3
25°	1798.0	1986.8	2179.8	2368.6	2586.1	2799.6	3017.2	3230.6	3415.4	3526.2	3624.7
27.5°	1793.9	2023.8	2249.5	2475.3	2742.1	3004.9	3271.7	3534.4	3706.8	3866.9	3949.0
30°	1744.6	2019.7	2298.8	2573.8	2873.5	3173.2	3472.8	3772.5	3949.0	4059.8	4100.9
32.5°	1683.0	2007.3	2331.6	2655.9	2996.6	3337.4	3674.0	4014.7	4154.3	4248.7	4215.8
35°	1633.8	1990.9	2344.0	2697.0	3058.2	3423.6	3784.8	4146.0	4347.2	4478.6	4425.2
37.5°	1588.6	1962.2	2335.7	2709.3	3132.1	3554.9	3977.7	4400.6	4593.5	4733.1	4671.5
40°	1535.3	1933.5	2335.7	2733.9	3218.3	3698.6	4183.0	4663.3	4913.7	5032.7	4938.3
42.5°	1490.1	1904.7	2323.4	2738.0	3255.3	3772.5	4289.7	4807.0	5086.1	5254.4	5135.4
45°	1432.6	1847.2	2257.7	2672.4	3242.9	3813.5	4380.0	4950.6	5274.9	5406.3	5242.1
47.5°	1371.1	1781.6	2188.0	2594.4	3201.9	3809.4	4417.0	5024.5	5324.2	5480.2	5328.3
50°	1350.5	1761.0	2167.4	2577.9	3234.7	3895.6	4552.4	5209.2	5426.8	5554.1	5352.9
52.5°	1346.4	1781.6	2220.8	2655.9	3316.8	3973.6	4634.5	5291.3	5467.9	5603.3	5422.7
55°	1334.1	1806.2	2274.2	2742.1	3431.8	4125.5	4815.2	5504.8	5681.3	5779.8	5644.4
57.5°	1346.4	1855.5	2360.4	2869.4	3579.6	4289.7	4999.9	5710.1	5923.5	5993.3	5964.6
60°	1354.6	1896.5	2434.3	2976.1	3669.9	4363.6	5057.4	5751.1	5972.8	6145.2	6178.0
62.5°	1334.1	1867.8	2397.3	2931.0	3559.0	4187.1	4815.2	5443.2	5808.6	6063.1	6210.9
65°	1272.5	1765.1	2261.9	2754.5	3333.3	3916.2	4495.0	5073.8	5459.6	5837.3	5956.4
67.5°	1137.1	1555.8	1974.5	2393.2	2898.1	3403.0	3903.9	4408.8	4893.2	5258.5	5422.7
70°	985.2	1313.6	1646.1	1974.5	2434.3	2894.0	3353.8	3813.5	4240.5	4642.8	4798.7
72.5°	857.9	1112.5	1371.1	1625.6	1954.0	2278.3	2606.7	2931.0	3435.9	3838.2	3990.1
75°	730.7	915.4	1096.0	1280.8	1506.5	1732.3	1954.0	2179.8	2536.9	2898.1	3050.0
77.5°	562.4	685.5	804.6	923.6	1079.6	1231.5	1387.5	1539.4	1789.8	2060.7	2138.7
80°	390.0	459.8	525.4	595.2	718.4	841.5	964.7	1087.8	1252.0	1403.9	1523.0
82.5°	242.2	287.3	328.4	369.4	468.0	566.5	660.9	759.4	825.1	833.3	952.4
85°	156.0	184.7	209.4	234.0	291.5	353.0	410.5	468.0	418.7	390.0	463.9
87.5°	61.6	78.0	90.3	102.6	98.5	94.4	90.3	86.2	73.9	65.7	82.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995
 CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995

CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6
2.5°	3165.0	3177.3	3189.6	3197.8	3210.1	3214.2	3218.3	3218.3	3222.4	3226.5	3234.7
5°	3316.8	3341.5	3366.1	3386.6	3411.3	3431.8	3448.2	3468.7	3485.1	3485.1	3481.0
7.5°	3189.6	3251.2	3312.7	3374.3	3435.9	3481.0	3522.1	3567.2	3608.3	3616.5	3624.7
10°	3021.3	3087.0	3148.5	3214.2	3275.8	3345.6	3411.3	3476.9	3546.7	3559.0	3575.5
12.5°	2865.3	2943.3	3021.3	3095.2	3173.2	3222.4	3271.7	3316.8	3366.1	3398.9	3431.8
15°	2861.2	2926.9	2992.5	3054.1	3119.8	3148.5	3177.3	3201.9	3230.6	3230.6	3234.7
17.5°	2955.6	2996.6	3037.7	3074.6	3115.7	3119.8	3128.0	3132.1	3136.2	3123.9	3111.6
20°	3140.3	3156.7	3173.2	3189.6	3206.0	3177.3	3152.6	3123.9	3095.2	3062.3	3033.6
22.5°	3411.3	3374.3	3337.4	3300.4	3263.5	3214.2	3160.8	3111.6	3058.2	3017.2	2976.1
25°	3665.8	3620.6	3575.5	3530.3	3485.1	3378.4	3271.7	3160.8	3054.1	3009.0	2963.8
27.5°	4006.5	3936.7	3866.9	3797.1	3727.3	3583.7	3440.0	3296.3	3152.6	3074.6	3000.8
30°	4088.6	4010.6	3932.6	3850.5	3772.5	3632.9	3497.5	3357.9	3218.3	3128.0	3041.8
32.5°	4207.6	4117.3	4027.0	3936.7	3846.4	3710.9	3575.5	3435.9	3300.4	3218.3	3132.1
35°	4404.7	4302.0	4199.4	4092.7	3990.1	3850.5	3715.0	3575.5	3435.9	3341.5	3251.2
37.5°	4573.0	4453.9	4334.9	4215.8	4096.8	3973.6	3846.4	3723.2	3596.0	3501.6	3411.3
40°	4761.8	4630.4	4499.1	4371.8	4240.5	4125.5	4010.6	3891.5	3776.6	3702.7	3628.8
42.5°	4926.0	4765.9	4609.9	4453.9	4293.8	4215.8	4141.9	4063.9	3986.0	3949.0	3908.0
45°	5040.9	4893.2	4741.3	4593.5	4445.7	4388.2	4330.8	4273.3	4215.8	4252.8	4289.7
47.5°	5090.2	4971.2	4856.2	4741.3	4622.2	4642.8	4663.3	4679.7	4700.2	4749.5	4802.8
50°	5135.4	5069.7	4999.9	4934.2	4864.4	4942.4	5016.3	5094.3	5172.3	5274.9	5377.5
52.5°	5225.7	5188.7	5155.9	5118.9	5082.0	5217.5	5352.9	5488.4	5623.8	5738.8	5853.7
55°	5496.6	5467.9	5439.1	5406.3	5377.5	5570.5	5759.3	5952.2	6145.2	6264.2	6383.3
57.5°	5870.1	5853.7	5833.2	5816.8	5796.3	5985.1	6169.8	6354.5	6543.4	6658.3	6777.3
60°	6153.4	6157.5	6157.5	6161.6	6161.6	6305.3	6448.9	6596.7	6740.4	6838.9	6941.5
62.5°	6305.3	6297.1	6288.9	6280.6	6272.4	6391.5	6510.5	6629.6	6748.6	6822.5	6896.4
65°	6141.1	6186.2	6231.4	6276.5	6321.7	6338.1	6350.4	6366.8	6379.2	6424.3	6469.5
67.5°	5591.0	5681.3	5767.5	5857.8	5944.0	5882.5	5825.0	5763.4	5701.8	5714.2	5722.4
70°	4979.4	5082.0	5188.7	5291.3	5394.0	5250.3	5106.6	4958.8	4815.2	4765.9	4716.6
72.5°	4199.4	4289.7	4384.1	4474.4	4564.8	4388.2	4215.8	4039.3	3862.8	3776.6	3690.4
75°	3210.1	3316.8	3427.7	3534.4	3641.1	3444.1	3242.9	3045.9	2844.8	2787.3	2733.9
77.5°	2339.8	2467.1	2594.4	2721.6	2848.9	2672.4	2495.8	2315.2	2138.7	2105.9	2073.0
80°	1703.6	1802.1	1896.5	1995.0	2089.4	1986.8	1884.2	1781.6	1678.9	1674.8	1670.7
82.5°	1149.4	1235.6	1317.7	1403.9	1486.0	1445.0	1408.0	1367.0	1325.9	1367.0	1412.1
85°	591.1	710.2	833.3	952.4	1071.4	1059.1	1050.9	1038.6	1026.2	1079.6	1128.9
87.5°	119.0	221.7	324.3	422.8	525.4	500.8	476.2	447.4	422.8	439.2	451.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995
 CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675995

CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6
2.5°	3238.8	3242.9	3242.9	3242.9	3242.9	3242.9	3234.7	3230.6	3222.4	3214.2	3201.9
5°	3481.0	3476.9	3460.5	3444.1	3423.6	3407.1	3394.8	3378.4	3366.1	3349.7	3325.0
7.5°	3632.9	3641.1	3612.4	3587.8	3559.0	3530.3	3501.6	3472.8	3444.1	3415.4	3357.9
10°	3587.8	3600.1	3583.7	3567.2	3546.7	3530.3	3497.5	3460.5	3427.7	3390.7	3320.9
12.5°	3460.5	3493.4	3485.1	3476.9	3468.7	3460.5	3440.0	3415.4	3394.8	3370.2	3292.2
15°	3234.7	3234.7	3238.8	3242.9	3242.9	3247.1	3251.2	3255.3	3259.4	3263.5	3218.3
17.5°	3099.3	3087.0	3087.0	3087.0	3087.0	3087.0	3103.4	3123.9	3140.3	3156.7	3144.4
20°	3000.8	2972.0	2967.9	2967.9	2963.8	2959.7	2988.4	3021.3	3050.0	3078.7	3095.2
22.5°	2935.1	2894.0	2889.9	2885.8	2881.7	2877.6	2914.5	2951.5	2988.4	3025.4	3082.9
25°	2918.7	2873.5	2877.6	2881.7	2881.7	2885.8	2914.5	2943.3	2972.0	3000.8	3099.3
27.5°	2922.8	2848.9	2853.0	2857.1	2857.1	2861.2	2906.3	2947.4	2992.5	3033.6	3156.7
30°	2951.5	2865.3	2857.1	2848.9	2840.7	2832.4	2894.0	2955.6	3017.2	3078.7	3173.2
32.5°	3050.0	2967.9	2947.4	2926.9	2906.3	2885.8	2959.7	3029.5	3103.4	3173.2	3251.2
35°	3156.7	3066.4	3058.2	3050.0	3037.7	3029.5	3095.2	3165.0	3230.6	3296.3	3366.1
37.5°	3316.8	3226.5	3218.3	3206.0	3197.8	3185.5	3259.4	3329.2	3403.0	3472.8	3534.4
40°	3554.9	3481.0	3476.9	3476.9	3472.8	3468.7	3526.2	3587.8	3645.2	3702.7	3743.8
42.5°	3871.0	3834.1	3846.4	3862.8	3875.1	3887.4	3932.6	3981.8	4027.0	4072.2	4059.8
45°	4326.7	4363.6	4367.7	4371.8	4375.9	4380.0	4392.3	4408.8	4421.1	4433.4	4384.1
47.5°	4852.1	4901.4	4926.0	4950.6	4971.2	4995.8	4979.4	4958.8	4942.4	4921.9	4798.7
50°	5476.1	5578.7	5574.6	5570.5	5562.3	5558.2	5525.3	5492.5	5455.5	5422.7	5242.1
52.5°	5968.7	6083.6	6104.1	6124.7	6145.2	6165.7	6104.1	6042.6	5976.9	5915.3	5689.5
55°	6498.2	6617.3	6621.4	6625.5	6625.5	6629.6	6543.4	6457.2	6366.8	6280.6	6046.7
57.5°	6892.3	7007.2	6994.9	6986.7	6974.4	6962.1	6859.4	6756.8	6654.2	6551.6	6317.6
60°	7040.1	7138.6	7114.0	7089.3	7060.6	7036.0	6958.0	6880.0	6797.9	6719.9	6494.1
62.5°	6970.3	7044.2	7007.2	6974.4	6937.4	6900.5	6802.0	6699.4	6600.8	6498.2	6334.0
65°	6510.5	6555.7	6506.4	6461.3	6416.1	6366.8	6284.7	6202.6	6116.4	6034.3	5923.5
67.5°	5734.7	5742.9	5738.8	5734.7	5730.6	5726.5	5607.4	5488.4	5365.2	5246.2	5238.0
70°	4671.5	4622.2	4630.4	4642.8	4651.0	4659.2	4568.9	4482.7	4392.3	4302.0	4343.1
72.5°	3604.2	3518.0	3538.5	3563.1	3583.7	3604.2	3530.3	3460.5	3386.6	3312.7	3370.2
75°	2676.5	2623.1	2643.6	2668.2	2688.8	2709.3	2680.6	2651.8	2619.0	2590.3	2643.6
77.5°	2040.2	2007.3	2011.4	2011.4	2015.6	2015.6	2019.7	2027.9	2032.0	2036.1	2093.5
80°	1662.5	1658.4	1654.3	1650.2	1642.0	1637.9	1678.9	1720.0	1761.0	1802.1	1830.8
82.5°	1453.2	1494.2	1469.6	1449.1	1424.4	1399.8	1436.7	1473.7	1510.6	1547.6	1535.3
85°	1182.2	1231.5	1186.3	1141.2	1091.9	1046.8	1079.6	1108.3	1141.2	1169.9	1153.5
87.5°	468.0	480.3	406.4	336.6	262.7	188.8	299.7	406.4	517.2	624.0	640.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995

CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675995

CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6	2955.6
2.5°	3189.6	3173.2	3160.8	3156.7	3148.5	3144.4	3136.2	3128.0	3115.7	3107.5	3095.2
5°	3296.3	3271.7	3242.9	3201.9	3165.0	3123.9	3082.9	3045.9	3009.0	2967.9	2931.0
7.5°	3300.4	3242.9	3185.5	3132.1	3074.6	3021.3	2963.8	2914.5	2861.2	2807.8	2758.6
10°	3255.3	3185.5	3115.7	3045.9	2980.2	2910.4	2840.7	2783.2	2721.6	2660.0	2602.6
12.5°	3218.3	3140.3	3062.3	2980.2	2902.2	2820.1	2738.0	2680.6	2623.1	2565.6	2508.2
15°	3173.2	3123.9	3078.7	3004.9	2931.0	2857.1	2783.2	2705.2	2631.3	2553.3	2475.3
17.5°	3136.2	3123.9	3111.6	3062.3	3013.1	2959.7	2910.4	2832.4	2754.5	2672.4	2594.4
20°	3115.7	3132.1	3148.5	3123.9	3099.3	3070.5	3045.9	2988.4	2931.0	2869.4	2811.9
22.5°	3140.3	3201.9	3259.4	3263.5	3271.7	3275.8	3279.9	3226.5	3173.2	3115.7	3062.3
25°	3197.8	3296.3	3394.8	3448.2	3501.6	3559.0	3612.4	3579.6	3546.7	3513.9	3481.0
27.5°	3275.8	3398.9	3522.1	3600.1	3674.0	3752.0	3830.0	3825.9	3821.8	3813.5	3809.4
30°	3263.5	3357.9	3452.3	3546.7	3641.1	3735.5	3830.0	3879.2	3924.4	3973.6	4022.9
32.5°	3333.3	3411.3	3493.4	3591.9	3690.4	3793.0	3891.5	3994.2	4092.7	4195.3	4297.9
35°	3440.0	3509.8	3583.7	3690.4	3801.2	3908.0	4018.8	4141.9	4269.2	4396.5	4519.6
37.5°	3600.1	3661.7	3727.3	3817.6	3912.1	4002.4	4096.8	4277.4	4458.0	4642.8	4823.4
40°	3784.8	3825.9	3866.9	3953.1	4039.3	4125.5	4211.7	4437.5	4663.3	4889.1	5114.8
42.5°	4051.6	4039.3	4027.0	4096.8	4170.7	4240.5	4314.4	4519.6	4724.9	4930.1	5135.4
45°	4334.9	4285.6	4236.4	4269.2	4306.1	4339.0	4375.9	4585.3	4794.6	5008.1	5217.5
47.5°	4675.6	4552.4	4429.3	4400.6	4371.8	4339.0	4310.2	4536.0	4761.8	4991.7	5217.5
50°	5061.5	4876.7	4696.1	4622.2	4544.2	4470.3	4392.3	4577.1	4765.9	4954.7	5139.5
52.5°	5463.8	5233.9	5008.1	4893.2	4778.2	4659.2	4544.2	4700.2	4860.3	5020.4	5176.4
55°	5808.6	5574.6	5336.5	5201.0	5065.6	4930.1	4794.6	4950.6	5106.6	5262.6	5418.6
57.5°	6083.6	5849.6	5615.6	5488.4	5357.0	5229.8	5098.4	5246.2	5398.1	5550.0	5697.7
60°	6272.4	6046.7	5820.9	5697.7	5574.6	5451.4	5328.3	5504.8	5681.3	5861.9	6038.5
62.5°	6173.9	6009.7	5845.5	5792.2	5738.8	5681.3	5628.0	5796.3	5960.5	6128.8	6297.1
65°	5812.7	5701.8	5591.0	5644.4	5701.8	5755.2	5812.7	5923.5	6034.3	6149.3	6260.1
67.5°	5225.7	5217.5	5205.1	5324.2	5443.2	5566.4	5685.4	5759.3	5829.1	5903.0	5976.9
70°	4384.1	4429.3	4470.3	4675.6	4880.8	5086.1	5291.3	5320.1	5348.8	5377.5	5406.3
72.5°	3431.8	3489.2	3550.8	3821.8	4088.6	4359.5	4630.4	4614.0	4597.6	4577.1	4560.7
75°	2701.1	2754.5	2811.9	3062.3	3312.7	3563.1	3813.5	3743.8	3678.1	3608.3	3538.5
77.5°	2155.1	2212.6	2274.2	2508.2	2742.1	2980.2	3214.2	3045.9	2877.6	2709.3	2541.0
80°	1855.5	1884.2	1908.8	2068.9	2224.9	2385.0	2545.1	2372.7	2196.2	2019.7	1847.2
82.5°	1523.0	1506.5	1494.2	1588.6	1683.0	1777.5	1871.9	1707.7	1543.5	1375.2	1211.0
85°	1137.1	1120.7	1104.2	1153.5	1202.8	1256.1	1305.4	1116.6	927.7	734.8	546.0
87.5°	660.9	677.3	693.7	747.1	800.5	857.9	911.3	718.4	525.4	328.4	135.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995
 CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675995
 CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	2955.6	2955.6
2.5°	3070.5	3050.0
5°	2902.2	2873.5
7.5°	2717.5	2680.6
10°	2549.2	2499.9
12.5°	2442.5	2380.9
15°	2401.4	2327.5
17.5°	2524.6	2454.8
20°	2713.4	2619.0
22.5°	2943.3	2828.3
25°	3341.5	3201.9
27.5°	3665.8	3522.1
30°	3866.9	3710.9
32.5°	4088.6	3883.3
35°	4318.5	4121.4
37.5°	4597.6	4375.9
40°	4884.9	4655.1
42.5°	4983.5	4835.7
45°	5077.9	4938.3
47.5°	5098.4	4983.5
50°	5118.9	5102.5
52.5°	5176.4	5172.3
55°	5422.7	5426.8
57.5°	5726.5	5751.1
60°	6005.6	5976.9
62.5°	6149.3	6001.5
65°	6050.8	5845.5
67.5°	5755.2	5533.5
70°	5106.6	4807.0
72.5°	4297.9	4035.2
75°	3312.7	3091.1
77.5°	2356.3	2171.5
80°	1658.4	1473.7
82.5°	1063.2	915.4
85°	480.3	418.7
87.5°	135.5	131.4
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P675995
CATALOG NUMBER: CCW-SA-2D-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)