

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671826

Luminaire Tested: **CCP-SA-1E-740-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671826
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1E-740-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/ SLR
distribution lens
Light Source: (16) 4000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5673.9 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 56.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 8.1 fc

Type IV - Short - N/A

REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1167.4	0.0	1167.4
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	4506.4	0.0	4506.4
	% Fixture	79.4	0.0	79.4
Total	Lumens	5673.9	0.0	5673.9
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.8	2.5
10°-20°	297.3	5.2
20°-30°	434.9	7.7
30°-40°	612.7	10.8
40°-50°	841.9	14.8
50°-60°	1147.6	20.2
60°-70°	1256.0	22.1
70°-80°	725.3	12.8
80°-90°	217.4	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5673.9	100.0
0°-180°	5673.9	100.0

Coefficient of Utilization



REPORT NUMBER: P671826


CATALOG NUMBER: CCP-SA-1E-740-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	582.7	10.3			
FM	(30°-60°)	2070.6	36.5			
FH	(60°-80°)	1668.5	29.4			G1/1800
FVH	(80°-90°)	184.7	3.3			G2/225
BL	(0°-30°)	290.2	5.1	B1/500		
BM	(30°-60°)	531.6	9.4	B1/1000		
BH	(60°-80°)	312.9	5.5	B1/500		G1/500
BVH	(80°-90°)	32.7	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9
2.5°	1869.8	1859.7	1852.1	1844.6	1834.5	1827.0	1816.9	1806.8	1794.3	1784.2	1771.6
5°	1761.6	1731.4	1701.2	1683.5	1663.4	1645.8	1625.7	1603.0	1580.4	1555.2	1532.5
7.5°	1643.3	1605.5	1567.8	1537.6	1504.9	1474.7	1442.0	1414.3	1386.6	1358.9	1331.2
10°	1532.5	1497.3	1462.1	1424.3	1384.1	1346.3	1306.1	1268.3	1230.6	1192.8	1155.1
12.5°	1459.6	1416.8	1376.5	1333.7	1293.5	1250.7	1207.9	1172.7	1137.5	1099.7	1064.5
15°	1426.9	1386.6	1348.8	1306.1	1263.3	1220.5	1177.7	1137.5	1099.7	1059.4	1019.2
17.5°	1504.9	1447.0	1389.1	1333.7	1278.4	1223.0	1167.7	1117.3	1067.0	1016.7	966.3
20°	1605.5	1532.5	1462.1	1394.1	1323.7	1255.7	1185.3	1114.8	1044.3	973.9	903.4
22.5°	1733.9	1650.8	1570.3	1482.2	1391.6	1303.5	1213.0	1124.9	1036.8	946.2	858.1
25°	1962.9	1864.7	1766.6	1640.8	1512.4	1386.6	1258.3	1142.5	1029.2	913.5	797.7
27.5°	2159.2	2025.8	1894.9	1743.9	1592.9	1442.0	1291.0	1157.6	1026.7	893.4	760.0
30°	2274.9	2144.1	2013.2	1829.5	1648.3	1464.6	1280.9	1132.4	986.5	838.0	689.5
32.5°	2380.6	2234.7	2088.7	1887.4	1683.5	1482.2	1278.4	1114.8	953.8	790.2	626.6
35°	2526.6	2365.5	2207.0	1972.9	1738.9	1504.9	1270.8	1102.2	931.1	762.5	591.4
37.5°	2682.6	2483.8	2287.5	2028.3	1769.1	1509.9	1250.7	1084.6	918.5	752.4	586.3
40°	2853.7	2612.1	2373.1	2086.2	1801.8	1514.9	1228.1	1062.0	895.9	727.3	561.2
42.5°	2964.4	2702.7	2441.0	2131.5	1824.5	1514.9	1205.4	1041.8	878.3	712.2	548.6
45°	3027.4	2773.2	2521.5	2186.8	1852.1	1517.5	1182.8	1021.7	860.6	697.1	536.0
47.5°	3055.0	2818.5	2581.9	2229.6	1879.8	1527.5	1175.2	1011.6	845.5	682.0	515.9
50°	3128.0	2919.1	2710.3	2332.8	1957.8	1580.4	1202.9	1026.7	853.1	676.9	500.8
52.5°	3170.8	2992.1	2813.4	2425.9	2038.4	1650.8	1263.3	1067.0	870.7	674.4	478.1
55°	3326.8	3155.7	2984.6	2571.9	2156.6	1743.9	1328.7	1112.3	895.9	676.9	460.5
57.5°	3525.6	3344.4	3165.8	2720.3	2274.9	1829.5	1384.1	1152.6	918.5	687.0	453.0
60°	3664.0	3487.9	3314.2	2841.1	2365.5	1892.4	1416.8	1175.2	933.6	689.5	447.9
62.5°	3679.1	3452.6	3228.7	2768.2	2307.6	1844.6	1384.1	1150.0	916.0	679.5	445.4
65°	3583.5	3319.3	3055.0	2614.6	2174.3	1733.9	1293.5	1079.6	865.7	649.3	435.4
67.5°	3392.2	3082.7	2773.2	2370.5	1967.9	1565.3	1162.6	978.9	797.7	614.0	430.3
70°	2946.8	2675.0	2405.8	2056.0	1708.7	1358.9	1009.1	858.1	709.7	558.7	407.7
72.5°	2473.7	2219.6	1967.9	1683.5	1401.7	1117.3	833.0	719.7	606.5	490.7	377.5
75°	1894.9	1703.7	1514.9	1303.5	1092.2	878.3	666.9	583.8	500.8	417.7	334.7
77.5°	1331.2	1228.1	1127.4	968.9	810.3	651.8	493.2	437.9	382.5	327.1	271.8
80°	903.4	845.5	790.2	676.9	563.7	447.9	334.7	299.5	261.7	226.5	188.7
82.5°	561.2	558.7	553.6	475.6	397.6	319.6	241.6	211.4	183.7	153.5	123.3
85°	256.7	299.5	339.7	296.9	254.2	211.4	168.6	148.5	128.3	105.7	85.6
87.5°	80.5	98.1	113.2	108.2	100.7	95.6	88.1	75.5	62.9	50.3	37.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9
2.5°	1761.6	1754.0	1743.9	1733.9	1721.3	1711.2	1698.6	1686.1	1683.5	1678.5	1676.0
5°	1517.5	1502.4	1484.7	1469.6	1454.5	1436.9	1421.8	1404.2	1391.6	1376.5	1363.9
7.5°	1303.5	1278.4	1250.7	1223.0	1197.9	1172.7	1145.0	1119.8	1107.3	1094.7	1082.1
10°	1132.4	1107.3	1084.6	1059.4	1041.8	1026.7	1009.1	991.5	976.4	961.3	946.2
12.5°	1046.9	1029.2	1011.6	994.0	973.9	956.3	936.1	916.0	898.4	883.3	865.7
15°	994.0	968.9	941.2	916.0	888.3	863.2	835.5	807.8	787.7	770.0	749.9
17.5°	931.1	893.4	858.1	820.4	790.2	760.0	727.3	697.1	674.4	649.3	626.6
20°	860.6	817.9	772.6	729.8	694.6	661.8	626.6	591.4	566.2	538.5	513.4
22.5°	800.2	744.9	687.0	629.1	591.4	553.6	513.4	475.6	453.0	427.8	405.2
25°	734.8	674.4	611.5	548.6	510.8	470.6	432.8	392.6	375.0	359.9	342.2
27.5°	699.6	639.2	576.3	515.9	480.7	442.9	407.7	369.9	357.3	342.2	329.7
30°	629.1	571.2	510.8	450.5	425.3	402.6	377.5	352.3	347.3	344.8	339.7
32.5°	566.2	505.8	445.4	385.0	362.4	339.7	317.1	294.4	291.9	286.9	284.4
35°	533.5	475.6	415.2	357.3	337.2	314.6	294.4	271.8	266.7	259.2	254.2
37.5°	525.9	465.6	402.6	342.2	322.1	302.0	279.3	259.2	254.2	249.1	244.1
40°	505.8	447.9	392.6	334.7	314.6	294.4	271.8	251.7	246.6	241.6	236.6
42.5°	490.7	435.4	377.5	319.6	302.0	284.4	264.2	246.6	241.6	236.6	229.0
45°	478.1	420.3	359.9	302.0	289.4	276.8	261.7	249.1	244.1	236.6	231.5
47.5°	458.0	402.6	344.8	286.9	274.3	264.2	251.7	239.1	234.0	229.0	224.0
50°	442.9	385.0	327.1	269.3	259.2	249.1	239.1	229.0	229.0	231.5	231.5
52.5°	422.8	367.4	312.0	256.7	246.6	236.6	226.5	216.4	218.9	221.5	224.0
55°	405.2	352.3	296.9	241.6	231.5	221.5	208.9	198.8	201.3	203.8	206.4
57.5°	397.6	342.2	286.9	231.5	221.5	208.9	198.8	186.2	186.2	186.2	186.2
60°	392.6	334.7	279.3	221.5	208.9	198.8	186.2	173.6	171.1	171.1	168.6
62.5°	390.1	332.2	276.8	218.9	203.8	191.3	176.2	161.1	158.5	156.0	153.5
65°	380.0	327.1	271.8	216.4	198.8	183.7	166.1	148.5	146.0	146.0	143.4
67.5°	377.5	322.1	269.3	213.9	196.3	176.2	158.5	138.4	135.9	133.4	130.9
70°	357.3	309.5	259.2	208.9	188.7	171.1	151.0	130.9	128.3	123.3	120.8
72.5°	332.2	289.4	244.1	198.8	178.7	158.5	138.4	118.3	115.8	113.2	108.2
75°	294.4	254.2	213.9	173.6	156.0	140.9	123.3	105.7	103.2	100.7	95.6
77.5°	241.6	208.9	178.7	146.0	133.4	120.8	108.2	95.6	93.1	90.6	85.6
80°	171.1	151.0	133.4	113.2	105.7	95.6	88.1	78.0	78.0	75.5	75.5
82.5°	113.2	103.2	93.1	83.0	78.0	73.0	67.9	62.9	62.9	60.4	60.4
85°	80.5	75.5	67.9	62.9	60.4	55.4	52.8	47.8	47.8	47.8	47.8
87.5°	37.7	37.7	35.2	35.2	32.7	32.7	30.2	27.7	27.7	27.7	27.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9
2.5°	1671.0	1663.4	1655.9	1645.8	1638.2	1628.2	1615.6	1605.5	1592.9	1592.9	1590.4
5°	1348.8	1341.3	1333.7	1323.7	1316.1	1306.1	1298.5	1288.4	1278.4	1278.4	1275.9
7.5°	1069.5	1054.4	1039.3	1021.7	1006.6	996.5	986.5	973.9	963.8	956.3	948.7
10°	931.1	916.0	898.4	883.3	865.7	853.1	840.5	825.4	812.8	802.8	792.7
12.5°	848.1	830.4	812.8	795.2	777.6	760.0	744.9	727.3	709.7	697.1	684.5
15°	729.8	712.2	694.6	676.9	659.3	639.2	619.1	596.4	576.3	566.2	558.7
17.5°	601.4	583.8	563.7	546.1	525.9	510.8	495.8	480.7	465.6	455.5	447.9
20°	485.7	465.6	445.4	425.3	405.2	395.1	385.0	375.0	364.9	357.3	352.3
22.5°	380.0	367.4	357.3	344.8	332.2	324.6	319.6	312.0	304.5	304.5	304.5
25°	324.6	317.1	312.0	304.5	296.9	294.4	291.9	286.9	284.4	281.8	281.8
27.5°	314.6	307.0	299.5	291.9	284.4	281.8	279.3	274.3	271.8	271.8	271.8
30°	334.7	332.2	329.7	327.1	324.6	319.6	312.0	307.0	299.5	294.4	289.4
32.5°	279.3	276.8	276.8	274.3	271.8	276.8	279.3	284.4	286.9	289.4	291.9
35°	246.6	241.6	236.6	231.5	226.5	224.0	221.5	218.9	216.4	216.4	213.9
37.5°	239.1	234.0	229.0	224.0	218.9	216.4	213.9	211.4	208.9	208.9	206.4
40°	231.5	226.5	224.0	218.9	213.9	211.4	208.9	203.8	201.3	198.8	198.8
42.5°	224.0	221.5	216.4	213.9	208.9	206.4	203.8	198.8	196.3	193.8	191.3
45°	224.0	218.9	213.9	208.9	203.8	201.3	196.3	193.8	188.7	188.7	186.2
47.5°	218.9	213.9	208.9	203.8	198.8	196.3	191.3	188.7	183.7	181.2	178.7
50°	231.5	224.0	213.9	206.4	196.3	193.8	188.7	186.2	181.2	178.7	176.2
52.5°	226.5	218.9	208.9	201.3	191.3	186.2	183.7	178.7	173.6	171.1	168.6
55°	208.9	201.3	196.3	188.7	181.2	176.2	171.1	166.1	161.1	158.5	158.5
57.5°	186.2	183.7	181.2	178.7	176.2	171.1	166.1	158.5	153.5	151.0	148.5
60°	166.1	168.6	171.1	173.6	176.2	168.6	161.1	153.5	146.0	143.4	140.9
62.5°	151.0	156.0	161.1	163.6	168.6	161.1	153.5	146.0	138.4	135.9	133.4
65°	140.9	143.4	143.4	146.0	146.0	140.9	138.4	133.4	128.3	125.8	125.8
67.5°	128.3	128.3	128.3	125.8	125.8	123.3	123.3	120.8	118.3	115.8	115.8
70°	115.8	115.8	115.8	113.2	113.2	110.7	110.7	108.2	105.7	105.7	103.2
72.5°	105.7	105.7	103.2	103.2	100.7	100.7	100.7	98.1	98.1	95.6	95.6
75°	93.1	93.1	90.6	90.6	88.1	88.1	88.1	85.6	85.6	85.6	83.0
77.5°	83.0	83.0	80.5	80.5	78.0	78.0	78.0	75.5	75.5	73.0	73.0
80°	73.0	73.0	70.5	70.5	67.9	67.9	65.4	65.4	62.9	62.9	60.4
82.5°	57.9	57.9	57.9	57.9	57.9	55.4	55.4	52.8	50.3	50.3	47.8
85°	47.8	47.8	47.8	45.3	45.3	45.3	42.8	42.8	40.3	37.7	37.7
87.5°	27.7	27.7	27.7	25.2	25.2	25.2	25.2	25.2	25.2	25.2	22.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9
2.5°	1590.4	1587.9	1577.8	1567.8	1577.8	1587.9	1587.9	1587.9	1585.4	1585.4	1585.4
5°	1275.9	1273.3	1268.3	1263.3	1263.3	1260.8	1265.8	1270.8	1275.9	1280.9	1285.9
7.5°	938.7	931.1	923.6	916.0	921.0	923.6	931.1	936.1	943.7	948.7	961.3
10°	782.6	772.6	765.0	757.5	752.4	747.4	742.4	739.9	734.8	729.8	734.8
12.5°	669.4	656.8	644.2	629.1	626.6	624.1	619.1	614.0	609.0	604.0	601.4
15°	548.6	538.5	533.5	525.9	515.9	505.8	500.8	498.3	493.2	488.2	485.7
17.5°	437.9	427.8	420.3	412.7	410.2	405.2	405.2	405.2	405.2	405.2	405.2
20°	344.8	337.2	337.2	334.7	334.7	332.2	334.7	337.2	337.2	339.7	342.2
22.5°	302.0	302.0	299.5	296.9	299.5	299.5	302.0	304.5	307.0	309.5	312.0
25°	279.3	276.8	279.3	281.8	281.8	281.8	284.4	284.4	286.9	286.9	286.9
27.5°	269.3	269.3	271.8	271.8	274.3	274.3	274.3	271.8	271.8	269.3	269.3
30°	284.4	279.3	279.3	279.3	276.8	274.3	271.8	271.8	269.3	266.7	264.2
32.5°	294.4	296.9	294.4	289.4	286.9	281.8	279.3	274.3	271.8	266.7	261.7
35°	213.9	211.4	216.4	218.9	221.5	224.0	226.5	229.0	229.0	231.5	231.5
37.5°	206.4	203.8	203.8	201.3	201.3	201.3	201.3	201.3	198.8	198.8	201.3
40°	196.3	193.8	193.8	191.3	191.3	188.7	188.7	188.7	188.7	188.7	188.7
42.5°	188.7	186.2	186.2	186.2	186.2	183.7	183.7	181.2	181.2	178.7	178.7
45°	186.2	183.7	181.2	178.7	178.7	176.2	176.2	176.2	173.6	173.6	173.6
47.5°	176.2	173.6	173.6	171.1	171.1	168.6	168.6	168.6	166.1	166.1	166.1
50°	171.1	168.6	168.6	166.1	166.1	163.6	163.6	163.6	161.1	161.1	161.1
52.5°	163.6	161.1	161.1	161.1	158.5	156.0	156.0	156.0	153.5	153.5	153.5
55°	156.0	153.5	153.5	153.5	151.0	148.5	148.5	148.5	146.0	146.0	146.0
57.5°	146.0	143.4	143.4	140.9	140.9	140.9	140.9	140.9	138.4	138.4	138.4
60°	138.4	135.9	135.9	133.4	133.4	130.9	130.9	130.9	130.9	130.9	130.9
62.5°	130.9	128.3	125.8	123.3	125.8	125.8	125.8	125.8	123.3	123.3	123.3
65°	123.3	120.8	118.3	115.8	115.8	115.8	115.8	115.8	115.8	115.8	115.8
67.5°	113.2	110.7	108.2	105.7	108.2	108.2	108.2	108.2	108.2	108.2	108.2
70°	103.2	100.7	100.7	98.1	98.1	95.6	95.6	98.1	98.1	98.1	98.1
72.5°	93.1	90.6	90.6	88.1	88.1	88.1	88.1	88.1	88.1	88.1	88.1
75°	83.0	80.5	80.5	78.0	78.0	78.0	78.0	78.0	78.0	78.0	78.0
77.5°	70.5	67.9	67.9	67.9	67.9	67.9	67.9	70.5	70.5	70.5	70.5
80°	60.4	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9
82.5°	47.8	45.3	45.3	45.3	45.3	45.3	45.3	45.3	45.3	45.3	45.3
85°	35.2	32.7	32.7	32.7	35.2	35.2	35.2	35.2	35.2	35.2	35.2
87.5°	22.6	20.1	20.1	20.1	22.6	22.6	22.6	22.6	20.1	20.1	20.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9
2.5°	1585.4	1585.4	1585.4	1582.9	1580.4	1577.8	1575.3	1582.9	1587.9	1595.5	1600.5
5°	1288.4	1293.5	1296.0	1303.5	1311.1	1318.6	1326.2	1331.2	1336.3	1338.8	1343.8
7.5°	971.4	984.0	994.0	1004.1	1014.2	1021.7	1031.8	1039.3	1046.9	1054.4	1062.0
10°	737.3	742.4	744.9	755.0	762.5	772.6	780.1	787.7	795.2	800.2	807.8
12.5°	598.9	593.9	591.4	591.4	591.4	591.4	591.4	596.4	601.4	606.5	611.5
15°	483.2	480.7	478.1	475.6	473.1	468.1	465.6	470.6	475.6	480.7	485.7
17.5°	405.2	405.2	405.2	402.6	400.1	397.6	395.1	397.6	400.1	400.1	402.6
20°	347.3	349.8	352.3	354.8	354.8	357.3	357.3	359.9	362.4	362.4	364.9
22.5°	312.0	314.6	314.6	314.6	317.1	317.1	317.1	319.6	322.1	324.6	327.1
25°	284.4	284.4	281.8	281.8	284.4	284.4	284.4	284.4	286.9	286.9	286.9
27.5°	269.3	266.7	266.7	266.7	266.7	264.2	264.2	264.2	264.2	264.2	264.2
30°	261.7	259.2	256.7	254.2	254.2	251.7	249.1	249.1	249.1	249.1	249.1
32.5°	259.2	254.2	249.1	246.6	246.6	244.1	241.6	239.1	239.1	236.6	234.0
35°	231.5	229.0	229.0	226.5	224.0	221.5	218.9	218.9	218.9	216.4	216.4
37.5°	201.3	203.8	203.8	203.8	206.4	206.4	206.4	206.4	208.9	208.9	208.9
40°	188.7	188.7	188.7	191.3	193.8	193.8	196.3	196.3	198.8	198.8	198.8
42.5°	178.7	176.2	176.2	178.7	178.7	181.2	181.2	183.7	186.2	186.2	188.7
45°	173.6	171.1	171.1	171.1	171.1	168.6	168.6	171.1	173.6	176.2	178.7
47.5°	163.6	163.6	161.1	161.1	161.1	161.1	161.1	161.1	163.6	163.6	163.6
50°	158.5	158.5	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0
52.5°	153.5	151.0	151.0	151.0	151.0	148.5	148.5	148.5	148.5	148.5	148.5
55°	146.0	143.4	143.4	143.4	143.4	143.4	143.4	143.4	146.0	146.0	146.0
57.5°	138.4	135.9	135.9	135.9	138.4	138.4	138.4	138.4	140.9	140.9	140.9
60°	130.9	130.9	130.9	130.9	130.9	130.9	130.9	133.4	133.4	135.9	135.9
62.5°	123.3	123.3	123.3	123.3	125.8	125.8	125.8	125.8	128.3	128.3	128.3
65°	115.8	115.8	115.8	115.8	118.3	118.3	118.3	118.3	118.3	118.3	118.3
67.5°	108.2	108.2	108.2	108.2	108.2	108.2	108.2	110.7	110.7	113.2	113.2
70°	98.1	95.6	95.6	98.1	98.1	100.7	100.7	103.2	103.2	105.7	105.7
72.5°	88.1	88.1	88.1	88.1	88.1	88.1	88.1	90.6	93.1	93.1	95.6
75°	78.0	78.0	78.0	78.0	80.5	80.5	80.5	83.0	83.0	85.6	85.6
77.5°	70.5	67.9	67.9	67.9	70.5	70.5	70.5	73.0	73.0	75.5	75.5
80°	57.9	57.9	57.9	57.9	60.4	60.4	60.4	60.4	62.9	62.9	62.9
82.5°	47.8	47.8	47.8	47.8	47.8	47.8	47.8	47.8	50.3	50.3	50.3
85°	35.2	35.2	35.2	35.2	37.7	37.7	37.7	37.7	37.7	37.7	37.7
87.5°	22.6	22.6	22.6	22.6	22.6	22.6	22.6	22.6	25.2	25.2	25.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9
2.5°	1600.5	1600.5	1600.5	1600.5	1605.5	1608.0	1613.1	1615.6	1613.1	1610.6	1605.5
5°	1346.3	1348.8	1348.8	1351.4	1351.4	1351.4	1351.4	1351.4	1356.4	1361.4	1366.5
7.5°	1064.5	1067.0	1069.5	1072.0	1072.0	1072.0	1069.5	1069.5	1072.0	1072.0	1074.5
10°	815.3	825.4	833.0	840.5	835.5	827.9	822.9	815.3	815.3	815.3	812.8
12.5°	616.5	619.1	624.1	626.6	624.1	624.1	621.6	619.1	621.6	626.6	629.1
15°	488.2	488.2	490.7	490.7	493.2	495.8	495.8	498.3	503.3	505.8	510.8
17.5°	405.2	407.7	407.7	410.2	410.2	412.7	412.7	412.7	417.7	422.8	430.3
20°	364.9	364.9	364.9	364.9	364.9	362.4	362.4	359.9	362.4	367.4	369.9
22.5°	327.1	329.7	329.7	329.7	327.1	324.6	319.6	317.1	317.1	319.6	319.6
25°	286.9	284.4	284.4	281.8	281.8	284.4	284.4	284.4	286.9	286.9	289.4
27.5°	264.2	261.7	261.7	259.2	259.2	261.7	261.7	261.7	261.7	261.7	261.7
30°	246.6	246.6	244.1	241.6	244.1	244.1	246.6	246.6	249.1	249.1	251.7
32.5°	234.0	231.5	231.5	229.0	231.5	231.5	234.0	234.0	236.6	239.1	239.1
35°	216.4	216.4	216.4	216.4	216.4	216.4	213.9	213.9	213.9	213.9	213.9
37.5°	206.4	206.4	203.8	201.3	201.3	201.3	201.3	201.3	198.8	196.3	193.8
40°	198.8	196.3	196.3	193.8	191.3	191.3	188.7	186.2	186.2	183.7	183.7
42.5°	188.7	186.2	186.2	183.7	181.2	181.2	178.7	176.2	176.2	176.2	173.6
45°	176.2	176.2	173.6	171.1	171.1	171.1	168.6	168.6	168.6	168.6	166.1
47.5°	163.6	163.6	161.1	161.1	161.1	161.1	158.5	158.5	158.5	158.5	158.5
50°	156.0	156.0	156.0	156.0	156.0	156.0	153.5	153.5	153.5	153.5	153.5
52.5°	148.5	148.5	148.5	148.5	148.5	148.5	148.5	148.5	148.5	148.5	148.5
55°	146.0	146.0	146.0	146.0	146.0	146.0	143.4	143.4	143.4	146.0	146.0
57.5°	140.9	140.9	138.4	138.4	138.4	138.4	138.4	138.4	138.4	138.4	138.4
60°	135.9	135.9	135.9	135.9	135.9	135.9	135.9	135.9	135.9	135.9	135.9
62.5°	128.3	128.3	128.3	128.3	128.3	130.9	130.9	130.9	130.9	130.9	128.3
65°	118.3	120.8	120.8	120.8	120.8	120.8	120.8	120.8	120.8	120.8	120.8
67.5°	113.2	113.2	113.2	113.2	113.2	113.2	113.2	113.2	113.2	113.2	113.2
70°	105.7	105.7	103.2	103.2	103.2	105.7	105.7	105.7	105.7	105.7	105.7
72.5°	95.6	95.6	95.6	95.6	95.6	95.6	95.6	95.6	95.6	98.1	98.1
75°	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6	85.6
77.5°	75.5	75.5	73.0	73.0	73.0	75.5	75.5	75.5	75.5	78.0	78.0
80°	62.9	62.9	62.9	62.9	62.9	62.9	62.9	62.9	62.9	65.4	65.4
82.5°	50.3	50.3	50.3	50.3	50.3	50.3	50.3	50.3	50.3	52.8	52.8
85°	37.7	40.3	40.3	40.3	40.3	40.3	40.3	40.3	40.3	42.8	42.8
87.5°	25.2	25.2	25.2	25.2	25.2	25.2	22.6	22.6	22.6	22.6	20.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9
2.5°	1603.0	1605.5	1608.0	1608.0	1610.6	1613.1	1613.1	1623.1	1633.2	1638.2	1643.3
5°	1371.5	1369.0	1369.0	1366.5	1363.9	1371.5	1379.0	1394.1	1409.2	1411.8	1416.8
7.5°	1074.5	1077.1	1079.6	1079.6	1082.1	1074.5	1064.5	1067.0	1069.5	1082.1	1092.2
10°	812.8	815.3	817.9	817.9	820.4	817.9	812.8	820.4	827.9	838.0	850.6
12.5°	631.6	639.2	646.7	651.8	659.3	664.4	666.9	676.9	684.5	697.1	709.7
15°	515.9	520.9	525.9	531.0	536.0	541.0	546.1	556.1	566.2	581.3	596.4
17.5°	435.4	435.4	437.9	437.9	437.9	442.9	447.9	453.0	455.5	470.6	485.7
20°	372.4	369.9	367.4	364.9	362.4	367.4	369.9	372.4	375.0	385.0	392.6
22.5°	319.6	319.6	322.1	322.1	322.1	319.6	314.6	317.1	317.1	322.1	329.7
25°	289.4	289.4	289.4	286.9	286.9	289.4	291.9	291.9	289.4	291.9	294.4
27.5°	261.7	264.2	264.2	266.7	266.7	269.3	269.3	269.3	269.3	271.8	274.3
30°	251.7	251.7	254.2	254.2	254.2	256.7	259.2	259.2	259.2	261.7	266.7
32.5°	241.6	244.1	246.6	249.1	251.7	254.2	254.2	256.7	256.7	259.2	261.7
35°	213.9	211.4	211.4	208.9	206.4	206.4	206.4	206.4	203.8	206.4	206.4
37.5°	191.3	191.3	191.3	188.7	188.7	191.3	191.3	191.3	191.3	193.8	193.8
40°	181.2	181.2	181.2	181.2	181.2	181.2	181.2	183.7	183.7	186.2	188.7
42.5°	173.6	173.6	173.6	173.6	173.6	176.2	176.2	176.2	176.2	178.7	178.7
45°	166.1	166.1	166.1	166.1	166.1	166.1	166.1	168.6	168.6	171.1	173.6
47.5°	158.5	158.5	158.5	158.5	158.5	161.1	163.6	163.6	163.6	166.1	166.1
50°	153.5	153.5	153.5	153.5	153.5	156.0	156.0	158.5	158.5	161.1	163.6
52.5°	148.5	148.5	148.5	148.5	148.5	151.0	151.0	153.5	153.5	156.0	158.5
55°	146.0	146.0	146.0	143.4	143.4	146.0	146.0	148.5	148.5	151.0	151.0
57.5°	138.4	138.4	138.4	138.4	138.4	138.4	138.4	140.9	140.9	143.4	146.0
60°	135.9	135.9	133.4	133.4	130.9	133.4	133.4	135.9	135.9	138.4	138.4
62.5°	128.3	128.3	128.3	125.8	125.8	128.3	128.3	128.3	128.3	130.9	133.4
65°	120.8	120.8	120.8	118.3	118.3	120.8	120.8	120.8	120.8	123.3	125.8
67.5°	113.2	113.2	113.2	110.7	110.7	110.7	110.7	113.2	113.2	115.8	118.3
70°	105.7	105.7	105.7	103.2	103.2	103.2	100.7	103.2	105.7	108.2	108.2
72.5°	98.1	98.1	98.1	95.6	95.6	95.6	93.1	95.6	95.6	98.1	98.1
75°	85.6	85.6	85.6	85.6	85.6	85.6	83.0	83.0	83.0	85.6	85.6
77.5°	78.0	78.0	78.0	75.5	75.5	75.5	73.0	73.0	73.0	75.5	75.5
80°	65.4	65.4	65.4	62.9	62.9	62.9	60.4	60.4	60.4	62.9	62.9
82.5°	52.8	52.8	52.8	50.3	50.3	50.3	47.8	47.8	47.8	50.3	50.3
85°	42.8	42.8	42.8	42.8	42.8	42.8	40.3	40.3	40.3	42.8	45.3
87.5°	20.1	20.1	22.6	22.6	22.6	22.6	20.1	20.1	17.6	17.6	20.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9
2.5°	1648.3	1653.3	1665.9	1676.0	1688.6	1698.6	1706.2	1716.3	1723.8	1731.4	1736.4
5°	1419.3	1421.8	1434.4	1447.0	1457.1	1469.6	1487.3	1504.9	1522.5	1540.1	1552.7
7.5°	1104.7	1114.8	1129.9	1147.5	1162.6	1177.7	1195.3	1215.5	1233.1	1250.7	1268.3
10°	860.6	870.7	885.8	900.9	913.5	928.6	948.7	968.9	989.0	1009.1	1029.2
12.5°	722.2	734.8	752.4	770.0	785.1	802.8	827.9	850.6	875.7	898.4	923.6
15°	609.0	624.1	646.7	671.9	694.6	717.2	742.4	767.5	790.2	815.3	840.5
17.5°	500.8	515.9	536.0	558.7	578.8	598.9	629.1	656.8	687.0	714.7	742.4
20°	402.6	410.2	430.3	450.5	470.6	490.7	513.4	536.0	558.7	581.3	616.5
22.5°	334.7	339.7	349.8	357.3	367.4	375.0	397.6	420.3	440.4	463.0	495.8
25°	294.4	296.9	304.5	309.5	317.1	322.1	337.2	349.8	364.9	377.5	407.7
27.5°	274.3	276.8	279.3	281.8	284.4	286.9	296.9	307.0	314.6	324.6	352.3
30°	269.3	271.8	279.3	284.4	291.9	296.9	302.0	307.0	312.0	317.1	334.7
32.5°	264.2	266.7	266.7	264.2	264.2	261.7	266.7	269.3	274.3	276.8	291.9
35°	208.9	208.9	211.4	213.9	216.4	218.9	226.5	231.5	239.1	244.1	256.7
37.5°	196.3	196.3	198.8	203.8	206.4	208.9	213.9	218.9	224.0	229.0	241.6
40°	188.7	191.3	193.8	196.3	198.8	201.3	206.4	208.9	213.9	216.4	226.5
42.5°	181.2	181.2	183.7	188.7	191.3	193.8	198.8	201.3	206.4	208.9	218.9
45°	176.2	178.7	181.2	183.7	183.7	186.2	191.3	196.3	198.8	203.8	213.9
47.5°	168.6	168.6	173.6	176.2	181.2	183.7	188.7	191.3	196.3	198.8	208.9
50°	163.6	166.1	171.1	173.6	178.7	181.2	188.7	193.8	201.3	206.4	211.4
52.5°	158.5	161.1	166.1	168.6	173.6	176.2	186.2	196.3	203.8	213.9	213.9
55°	153.5	153.5	158.5	166.1	171.1	176.2	181.2	188.7	193.8	198.8	198.8
57.5°	146.0	148.5	153.5	161.1	166.1	171.1	176.2	181.2	183.7	188.7	186.2
60°	140.9	140.9	148.5	156.0	163.6	171.1	171.1	171.1	168.6	168.6	168.6
62.5°	133.4	135.9	146.0	158.5	168.6	178.7	171.1	163.6	156.0	148.5	151.0
65°	128.3	130.9	135.9	143.4	148.5	153.5	148.5	146.0	140.9	135.9	138.4
67.5°	118.3	120.8	123.3	123.3	125.8	125.8	125.8	125.8	125.8	125.8	128.3
70°	110.7	110.7	110.7	113.2	113.2	113.2	113.2	113.2	113.2	113.2	115.8
72.5°	100.7	100.7	100.7	100.7	100.7	100.7	100.7	100.7	100.7	100.7	103.2
75°	88.1	88.1	88.1	88.1	88.1	88.1	88.1	88.1	88.1	88.1	90.6
77.5°	78.0	78.0	78.0	78.0	78.0	78.0	78.0	78.0	75.5	75.5	78.0
80°	65.4	65.4	65.4	65.4	62.9	62.9	62.9	62.9	62.9	62.9	65.4
82.5°	52.8	52.8	52.8	52.8	50.3	50.3	50.3	50.3	47.8	47.8	50.3
85°	47.8	50.3	50.3	52.8	52.8	52.8	50.3	47.8	45.3	42.8	42.8
87.5°	20.1	20.1	20.1	20.1	17.6	17.6	17.6	17.6	17.6	17.6	17.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9
2.5°	1743.9	1749.0	1754.0	1761.6	1771.6	1779.2	1786.7	1801.8	1819.4	1834.5	1849.6
5°	1565.3	1577.8	1590.4	1605.5	1620.6	1633.2	1648.3	1678.5	1708.7	1736.4	1766.6
7.5°	1283.4	1301.0	1316.1	1341.3	1363.9	1389.1	1411.8	1449.5	1484.7	1522.5	1557.7
10°	1049.4	1069.5	1089.6	1122.4	1157.6	1190.3	1223.0	1253.2	1285.9	1316.1	1346.3
12.5°	948.7	971.4	996.5	1016.7	1039.3	1059.4	1079.6	1114.8	1150.0	1185.3	1220.5
15°	865.7	890.8	916.0	941.2	963.8	989.0	1011.6	1041.8	1074.5	1104.7	1134.9
17.5°	770.0	795.2	822.9	850.6	878.3	905.9	933.6	976.4	1019.2	1059.4	1102.2
20°	649.3	684.5	717.2	755.0	792.7	830.4	868.2	913.5	958.8	1001.6	1046.9
22.5°	528.5	561.2	593.9	639.2	684.5	727.3	772.6	833.0	890.8	951.2	1009.1
25°	440.4	470.6	500.8	551.1	598.9	649.3	697.1	770.0	840.5	913.5	984.0
27.5°	380.0	407.7	435.4	488.2	541.0	591.4	644.2	724.8	802.8	883.3	961.3
30°	352.3	369.9	387.5	437.9	488.2	536.0	586.3	664.4	742.4	820.4	898.4
32.5°	307.0	322.1	337.2	382.5	427.8	470.6	515.9	596.4	674.4	755.0	833.0
35°	271.8	284.4	296.9	339.7	380.0	422.8	463.0	543.6	624.1	704.6	785.1
37.5°	251.7	264.2	274.3	312.0	352.3	390.1	427.8	508.3	586.3	666.9	744.9
40°	236.6	244.1	254.2	291.9	327.1	364.9	400.1	473.1	548.6	621.6	694.6
42.5°	226.5	236.6	244.1	276.8	312.0	344.8	377.5	447.9	518.4	586.3	656.8
45°	224.0	234.0	244.1	271.8	299.5	324.6	352.3	420.3	488.2	556.1	624.1
47.5°	218.9	226.5	236.6	259.2	279.3	302.0	322.1	390.1	458.0	523.4	591.4
50°	216.4	218.9	224.0	244.1	264.2	284.4	304.5	372.4	440.4	508.3	576.3
52.5°	213.9	213.9	213.9	231.5	249.1	264.2	281.8	349.8	420.3	488.2	556.1
55°	198.8	196.3	196.3	213.9	229.0	246.6	261.7	329.7	397.6	463.0	531.0
57.5°	183.7	181.2	178.7	193.8	208.9	224.0	239.1	307.0	377.5	445.4	513.4
60°	168.6	166.1	166.1	181.2	193.8	208.9	221.5	291.9	359.9	430.3	498.3
62.5°	151.0	153.5	153.5	166.1	181.2	193.8	206.4	276.8	349.8	420.3	490.7
65°	138.4	140.9	140.9	156.0	171.1	186.2	201.3	269.3	339.7	407.7	475.6
67.5°	128.3	130.9	130.9	148.5	163.6	181.2	196.3	256.7	319.6	380.0	440.4
70°	118.3	118.3	120.8	138.4	156.0	173.6	191.3	244.1	296.9	347.3	400.1
72.5°	105.7	108.2	110.7	128.3	143.4	161.1	176.2	224.0	271.8	319.6	367.4
75°	93.1	95.6	98.1	113.2	128.3	143.4	158.5	203.8	246.6	291.9	334.7
77.5°	83.0	85.6	88.1	100.7	113.2	125.8	138.4	171.1	206.4	239.1	271.8
80°	67.9	67.9	70.5	80.5	90.6	98.1	108.2	130.9	153.5	173.6	196.3
82.5°	50.3	52.8	52.8	60.4	65.4	73.0	78.0	90.6	100.7	113.2	123.3
85°	42.8	40.3	40.3	45.3	47.8	52.8	55.4	62.9	67.9	75.5	80.5
87.5°	17.6	15.1	15.1	17.6	22.6	25.2	27.7	27.7	30.2	30.2	30.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9
2.5°	1857.2	1862.2	1869.8	1874.8	1887.4	1897.4	1910.0	1920.1	1927.6	1940.2	1935.2
5°	1789.2	1811.9	1834.5	1857.2	1874.8	1892.4	1907.5	1925.1	1945.3	1983.0	1993.1
7.5°	1587.9	1618.1	1645.8	1676.0	1711.2	1746.5	1781.7	1816.9	1849.6	1897.4	1927.6
10°	1389.1	1431.9	1472.2	1514.9	1547.6	1580.4	1610.6	1643.3	1688.6	1736.4	1791.7
12.5°	1263.3	1306.1	1348.8	1391.6	1439.4	1484.7	1532.5	1577.8	1620.6	1658.4	1721.3
15°	1180.2	1228.1	1273.3	1318.6	1376.5	1431.9	1489.8	1545.1	1608.0	1658.4	1701.2
17.5°	1160.1	1218.0	1273.3	1331.2	1391.6	1452.0	1512.4	1572.8	1635.7	1711.2	1766.6
20°	1124.9	1202.9	1280.9	1358.9	1436.9	1512.4	1590.4	1665.9	1749.0	1839.6	1864.7
22.5°	1104.7	1197.9	1293.5	1386.6	1492.3	1600.5	1706.2	1811.9	1900.0	1967.9	2043.4
25°	1102.2	1218.0	1336.3	1452.0	1585.4	1716.3	1849.6	1980.5	2093.7	2161.7	2222.1
27.5°	1099.7	1240.6	1379.0	1517.5	1681.0	1842.1	2005.7	2166.7	2272.4	2370.5	2420.9
30°	1069.5	1238.1	1409.2	1577.8	1761.6	1945.3	2129.0	2312.7	2420.9	2488.8	2514.0
32.5°	1031.8	1230.6	1429.4	1628.2	1837.0	2045.9	2252.3	2461.1	2546.7	2604.6	2584.4
35°	1001.6	1220.5	1436.9	1653.3	1874.8	2098.8	2320.2	2541.7	2665.0	2745.5	2712.8
37.5°	973.9	1202.9	1431.9	1660.9	1920.1	2179.3	2438.5	2697.7	2816.0	2901.5	2863.8
40°	941.2	1185.3	1431.9	1676.0	1972.9	2267.4	2564.3	2858.7	3012.3	3085.2	3027.4
42.5°	913.5	1167.7	1424.3	1678.5	1995.6	2312.7	2629.7	2946.8	3117.9	3221.1	3148.1
45°	878.3	1132.4	1384.1	1638.2	1988.0	2337.8	2685.1	3034.9	3233.7	3314.2	3213.6
47.5°	840.5	1092.2	1341.3	1590.4	1962.9	2335.3	2707.8	3080.2	3263.9	3359.5	3266.4
50°	827.9	1079.6	1328.7	1580.4	1983.0	2388.2	2790.8	3193.4	3326.8	3404.8	3281.5
52.5°	825.4	1092.2	1361.4	1628.2	2033.3	2436.0	2841.1	3243.8	3352.0	3435.0	3324.3
55°	817.9	1107.3	1394.1	1681.0	2103.8	2529.1	2951.9	3374.6	3482.8	3543.2	3460.2
57.5°	825.4	1137.5	1447.0	1759.0	2194.4	2629.7	3065.1	3500.5	3631.3	3674.1	3656.5
60°	830.4	1162.6	1492.3	1824.5	2249.8	2675.0	3100.3	3525.6	3661.5	3767.2	3787.3
62.5°	817.9	1145.0	1469.6	1796.8	2181.8	2566.8	2951.9	3336.9	3560.8	3716.9	3807.5
65°	780.1	1082.1	1386.6	1688.6	2043.4	2400.7	2755.6	3110.4	3346.9	3578.5	3651.4
67.5°	697.1	953.8	1210.4	1467.1	1776.6	2086.2	2393.2	2702.7	2999.7	3223.6	3324.3
70°	604.0	805.3	1009.1	1210.4	1492.3	1774.1	2056.0	2337.8	2599.5	2846.2	2941.8
72.5°	525.9	682.0	840.5	996.5	1197.9	1396.7	1598.0	1796.8	2106.3	2352.9	2446.0
75°	447.9	561.2	671.9	785.1	923.6	1062.0	1197.9	1336.3	1555.2	1776.6	1869.8
77.5°	344.8	420.3	493.2	566.2	661.8	755.0	850.6	943.7	1097.2	1263.3	1311.1
80°	239.1	281.8	322.1	364.9	440.4	515.9	591.4	666.9	767.5	860.6	933.6
82.5°	148.5	176.2	201.3	226.5	286.9	347.3	405.2	465.6	505.8	510.8	583.8
85°	95.6	113.2	128.3	143.4	178.7	216.4	251.7	286.9	256.7	239.1	284.4
87.5°	37.7	47.8	55.4	62.9	60.4	57.9	55.4	52.8	45.3	40.3	50.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9
2.5°	1940.2	1947.8	1955.3	1960.4	1967.9	1970.4	1972.9	1972.9	1975.5	1978.0	1983.0
5°	2033.3	2048.4	2063.5	2076.1	2091.2	2103.8	2113.9	2126.4	2136.5	2136.5	2134.0
7.5°	1955.3	1993.1	2030.8	2068.6	2106.3	2134.0	2159.2	2186.8	2212.0	2217.0	2222.1
10°	1852.1	1892.4	1930.2	1970.4	2008.2	2050.9	2091.2	2131.5	2174.3	2181.8	2191.9
12.5°	1756.5	1804.3	1852.1	1897.4	1945.3	1975.5	2005.7	2033.3	2063.5	2083.7	2103.8
15°	1754.0	1794.3	1834.5	1872.3	1912.5	1930.2	1947.8	1962.9	1980.5	1980.5	1983.0
17.5°	1811.9	1837.0	1862.2	1884.9	1910.0	1912.5	1917.6	1920.1	1922.6	1915.1	1907.5
20°	1925.1	1935.2	1945.3	1955.3	1965.4	1947.8	1932.7	1915.1	1897.4	1877.3	1859.7
22.5°	2091.2	2068.6	2045.9	2023.3	2000.6	1970.4	1937.7	1907.5	1874.8	1849.6	1824.5
25°	2247.2	2219.6	2191.9	2164.2	2136.5	2071.1	2005.7	1937.7	1872.3	1844.6	1816.9
27.5°	2456.1	2413.3	2370.5	2327.8	2285.0	2196.9	2108.8	2020.8	1932.7	1884.9	1839.6
30°	2506.4	2458.6	2410.8	2360.5	2312.7	2227.1	2144.1	2058.5	1972.9	1917.6	1864.7
32.5°	2579.4	2524.1	2468.7	2413.3	2358.0	2274.9	2191.9	2106.3	2023.3	1972.9	1920.1
35°	2700.2	2637.3	2574.4	2509.0	2446.0	2360.5	2277.4	2191.9	2106.3	2048.4	1993.1
37.5°	2803.4	2730.4	2657.4	2584.4	2511.5	2436.0	2358.0	2282.5	2204.5	2146.6	2091.2
40°	2919.1	2838.6	2758.1	2680.1	2599.5	2529.1	2458.6	2385.6	2315.2	2269.9	2224.6
42.5°	3019.8	2921.7	2826.0	2730.4	2632.3	2584.4	2539.1	2491.3	2443.5	2420.9	2395.7
45°	3090.3	2999.7	2906.6	2816.0	2725.4	2690.1	2654.9	2619.7	2584.4	2607.1	2629.7
47.5°	3120.5	3047.5	2977.0	2906.6	2833.6	2846.2	2858.7	2868.8	2881.4	2911.6	2944.3
50°	3148.1	3107.9	3065.1	3024.8	2982.1	3029.9	3075.2	3123.0	3170.8	3233.7	3296.6
52.5°	3203.5	3180.9	3160.7	3138.1	3115.4	3198.5	3281.5	3364.6	3447.6	3518.1	3588.5
55°	3369.6	3352.0	3334.4	3314.2	3296.6	3414.9	3530.7	3648.9	3767.2	3840.2	3913.2
57.5°	3598.6	3588.5	3575.9	3565.9	3553.3	3669.1	3782.3	3895.5	4011.3	4081.8	4154.7
60°	3772.2	3774.8	3774.8	3777.3	3777.3	3865.3	3953.4	4044.0	4132.1	4192.5	4255.4
62.5°	3865.3	3860.3	3855.3	3850.2	3845.2	3918.2	3991.2	4064.1	4137.1	4182.4	4227.7
65°	3764.7	3792.4	3820.0	3847.7	3875.4	3885.5	3893.0	3903.1	3910.6	3938.3	3966.0
67.5°	3427.5	3482.8	3535.7	3591.0	3643.9	3606.1	3570.9	3533.2	3495.4	3503.0	3508.0
70°	3052.5	3115.4	3180.9	3243.8	3306.7	3218.6	3130.5	3039.9	2951.9	2921.7	2891.5
72.5°	2574.4	2629.7	2687.6	2743.0	2798.3	2690.1	2584.4	2476.2	2368.0	2315.2	2262.3
75°	1967.9	2033.3	2101.3	2166.7	2232.1	2111.3	1988.0	1867.2	1743.9	1708.7	1676.0
77.5°	1434.4	1512.4	1590.4	1668.4	1746.5	1638.2	1530.0	1419.3	1311.1	1291.0	1270.8
80°	1044.3	1104.7	1162.6	1223.0	1280.9	1218.0	1155.1	1092.2	1029.2	1026.7	1024.2
82.5°	704.6	757.5	807.8	860.6	911.0	885.8	863.2	838.0	812.8	838.0	865.7
85°	362.4	435.4	510.8	583.8	656.8	649.3	644.2	636.7	629.1	661.8	692.0
87.5°	73.0	135.9	198.8	259.2	322.1	307.0	291.9	274.3	259.2	269.3	276.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9
2.5°	1985.5	1988.0	1988.0	1988.0	1988.0	1988.0	1983.0	1980.5	1975.5	1970.4	1962.9
5°	2134.0	2131.5	2121.4	2111.3	2098.8	2088.7	2081.1	2071.1	2063.5	2053.5	2038.4
7.5°	2227.1	2232.1	2214.5	2199.4	2181.8	2164.2	2146.6	2129.0	2111.3	2093.7	2058.5
10°	2199.4	2207.0	2196.9	2186.8	2174.3	2164.2	2144.1	2121.4	2101.3	2078.6	2035.8
12.5°	2121.4	2141.5	2136.5	2131.5	2126.4	2121.4	2108.8	2093.7	2081.1	2066.0	2018.2
15°	1983.0	1983.0	1985.5	1988.0	1988.0	1990.6	1993.1	1995.6	1998.1	2000.6	1972.9
17.5°	1900.0	1892.4	1892.4	1892.4	1892.4	1892.4	1902.5	1915.1	1925.1	1935.2	1927.6
20°	1839.6	1821.9	1819.4	1819.4	1816.9	1814.4	1832.0	1852.1	1869.8	1887.4	1897.4
22.5°	1799.3	1774.1	1771.6	1769.1	1766.6	1764.1	1786.7	1809.4	1832.0	1854.7	1889.9
25°	1789.2	1761.6	1764.1	1766.6	1766.6	1769.1	1786.7	1804.3	1821.9	1839.6	1900.0
27.5°	1791.7	1746.5	1749.0	1751.5	1751.5	1754.0	1781.7	1806.8	1834.5	1859.7	1935.2
30°	1809.4	1756.5	1751.5	1746.5	1741.4	1736.4	1774.1	1811.9	1849.6	1887.4	1945.3
32.5°	1869.8	1819.4	1806.8	1794.3	1781.7	1769.1	1814.4	1857.2	1902.5	1945.3	1993.1
35°	1935.2	1879.8	1874.8	1869.8	1862.2	1857.2	1897.4	1940.2	1980.5	2020.8	2063.5
37.5°	2033.3	1978.0	1972.9	1965.4	1960.4	1952.8	1998.1	2040.9	2086.2	2129.0	2166.7
40°	2179.3	2134.0	2131.5	2131.5	2129.0	2126.4	2161.7	2199.4	2234.7	2269.9	2295.0
42.5°	2373.1	2350.4	2358.0	2368.0	2375.6	2383.1	2410.8	2441.0	2468.7	2496.4	2488.8
45°	2652.4	2675.0	2677.6	2680.1	2682.6	2685.1	2692.7	2702.7	2710.3	2717.8	2687.6
47.5°	2974.5	3004.7	3019.8	3034.9	3047.5	3062.6	3052.5	3039.9	3029.9	3017.3	2941.8
50°	3357.0	3419.9	3417.4	3414.9	3409.9	3407.3	3387.2	3367.1	3344.4	3324.3	3213.6
52.5°	3659.0	3729.5	3742.0	3754.6	3767.2	3779.8	3742.0	3704.3	3664.0	3626.3	3487.9
55°	3983.6	4056.6	4059.1	4061.6	4061.6	4064.1	4011.3	3958.5	3903.1	3850.2	3706.8
57.5°	4225.2	4295.7	4288.1	4283.1	4275.5	4268.0	4205.1	4142.2	4079.2	4016.3	3872.9
60°	4315.8	4376.2	4361.1	4346.0	4328.4	4313.3	4265.5	4217.7	4167.3	4119.5	3981.1
62.5°	4273.0	4318.3	4295.7	4275.5	4252.9	4230.2	4169.8	4106.9	4046.5	3983.6	3883.0
65°	3991.2	4018.9	3988.7	3961.0	3933.3	3903.1	3852.8	3802.4	3749.6	3699.3	3631.3
67.5°	3515.6	3520.6	3518.1	3515.6	3513.0	3510.5	3437.5	3364.6	3289.1	3216.1	3211.1
70°	2863.8	2833.6	2838.6	2846.2	2851.2	2856.2	2800.9	2748.0	2692.7	2637.3	2662.5
72.5°	2209.5	2156.6	2169.2	2184.3	2196.9	2209.5	2164.2	2121.4	2076.1	2030.8	2066.0
75°	1640.8	1608.0	1620.6	1635.7	1648.3	1660.9	1643.3	1625.7	1605.5	1587.9	1620.6
77.5°	1250.7	1230.6	1233.1	1233.1	1235.6	1235.6	1238.1	1243.2	1245.7	1248.2	1283.4
80°	1019.2	1016.7	1014.2	1011.6	1006.6	1004.1	1029.2	1054.4	1079.6	1104.7	1122.4
82.5°	890.8	916.0	900.9	888.3	873.2	858.1	880.8	903.4	926.1	948.7	941.2
85°	724.8	755.0	727.3	699.6	669.4	641.7	661.8	679.5	699.6	717.2	707.1
87.5°	286.9	294.4	249.1	206.4	161.1	115.8	183.7	249.1	317.1	382.5	392.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9	1811.9
2.5°	1955.3	1945.3	1937.7	1935.2	1930.2	1927.6	1922.6	1917.6	1910.0	1905.0	1897.4
5°	2020.8	2005.7	1988.0	1962.9	1940.2	1915.1	1889.9	1867.2	1844.6	1819.4	1796.8
7.5°	2023.3	1988.0	1952.8	1920.1	1884.9	1852.1	1816.9	1786.7	1754.0	1721.3	1691.1
10°	1995.6	1952.8	1910.0	1867.2	1827.0	1784.2	1741.4	1706.2	1668.4	1630.7	1595.5
12.5°	1972.9	1925.1	1877.3	1827.0	1779.2	1728.8	1678.5	1643.3	1608.0	1572.8	1537.6
15°	1945.3	1915.1	1887.4	1842.1	1796.8	1751.5	1706.2	1658.4	1613.1	1565.3	1517.5
17.5°	1922.6	1915.1	1907.5	1877.3	1847.1	1814.4	1784.2	1736.4	1688.6	1638.2	1590.4
20°	1910.0	1920.1	1930.2	1915.1	1900.0	1882.3	1867.2	1832.0	1796.8	1759.0	1723.8
22.5°	1925.1	1962.9	1998.1	2000.6	2005.7	2008.2	2010.7	1978.0	1945.3	1910.0	1877.3
25°	1960.4	2020.8	2081.1	2113.9	2146.6	2181.8	2214.5	2194.4	2174.3	2154.1	2134.0
27.5°	2008.2	2083.7	2159.2	2207.0	2252.3	2300.1	2347.9	2345.4	2342.9	2337.8	2335.3
30°	2000.6	2058.5	2116.4	2174.3	2232.1	2290.0	2347.9	2378.1	2405.8	2436.0	2466.2
32.5°	2043.4	2091.2	2141.5	2201.9	2262.3	2325.2	2385.6	2448.6	2509.0	2571.9	2634.8
35°	2108.8	2151.6	2196.9	2262.3	2330.3	2395.7	2463.7	2539.1	2617.2	2695.2	2770.7
37.5°	2207.0	2244.7	2285.0	2340.3	2398.2	2453.6	2511.5	2622.2	2732.9	2846.2	2956.9
40°	2320.2	2345.4	2370.5	2423.4	2476.2	2529.1	2581.9	2720.3	2858.7	2997.2	3135.6
42.5°	2483.8	2476.2	2468.7	2511.5	2556.8	2599.5	2644.8	2770.7	2896.5	3022.3	3148.1
45°	2657.4	2627.2	2597.0	2617.2	2639.8	2659.9	2682.6	2810.9	2939.3	3070.1	3198.5
47.5°	2866.3	2790.8	2715.3	2697.7	2680.1	2659.9	2642.3	2780.7	2919.1	3060.1	3198.5
50°	3102.8	2989.6	2878.9	2833.6	2785.8	2740.5	2692.7	2805.9	2921.7	3037.4	3150.7
52.5°	3349.5	3208.5	3070.1	2999.7	2929.2	2856.2	2785.8	2881.4	2979.5	3077.7	3173.3
55°	3560.8	3417.4	3271.5	3188.4	3105.4	3022.3	2939.3	3034.9	3130.5	3226.2	3321.8
57.5°	3729.5	3586.0	3442.6	3364.6	3284.0	3206.0	3125.5	3216.1	3309.2	3402.3	3492.9
60°	3845.2	3706.8	3568.4	3492.9	3417.4	3341.9	3266.4	3374.6	3482.8	3593.6	3701.8
62.5°	3784.8	3684.2	3583.5	3550.8	3518.1	3482.8	3450.1	3553.3	3654.0	3757.1	3860.3
65°	3563.4	3495.4	3427.5	3460.2	3495.4	3528.1	3563.4	3631.3	3699.3	3769.7	3837.7
67.5°	3203.5	3198.5	3190.9	3263.9	3336.9	3412.4	3485.4	3530.7	3573.4	3618.7	3664.0
70°	2687.6	2715.3	2740.5	2866.3	2992.1	3117.9	3243.8	3261.4	3279.0	3296.6	3314.2
72.5°	2103.8	2139.0	2176.8	2342.9	2506.4	2672.5	2838.6	2828.5	2818.5	2805.9	2795.8
75°	1655.9	1688.6	1723.8	1877.3	2030.8	2184.3	2337.8	2295.0	2254.8	2212.0	2169.2
77.5°	1321.2	1356.4	1394.1	1537.6	1681.0	1827.0	1970.4	1867.2	1764.1	1660.9	1557.7
80°	1137.5	1155.1	1170.2	1268.3	1363.9	1462.1	1560.2	1454.5	1346.3	1238.1	1132.4
82.5°	933.6	923.6	916.0	973.9	1031.8	1089.6	1147.5	1046.9	946.2	843.0	742.4
85°	697.1	687.0	676.9	707.1	737.3	770.0	800.2	684.5	568.7	450.5	334.7
87.5°	405.2	415.2	425.3	458.0	490.7	525.9	558.7	440.4	322.1	201.3	83.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671826
 CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1811.9	1811.9
2.5°	1882.3	1869.8
5°	1779.2	1761.6
7.5°	1665.9	1643.3
10°	1562.7	1532.5
12.5°	1497.3	1459.6
15°	1472.2	1426.9
17.5°	1547.6	1504.9
20°	1663.4	1605.5
22.5°	1804.3	1733.9
25°	2048.4	1962.9
27.5°	2247.2	2159.2
30°	2370.5	2274.9
32.5°	2506.4	2380.6
35°	2647.4	2526.6
37.5°	2818.5	2682.6
40°	2994.6	2853.7
42.5°	3055.0	2964.4
45°	3112.9	3027.4
47.5°	3125.5	3055.0
50°	3138.1	3128.0
52.5°	3173.3	3170.8
55°	3324.3	3326.8
57.5°	3510.5	3525.6
60°	3681.6	3664.0
62.5°	3769.7	3679.1
65°	3709.3	3583.5
67.5°	3528.1	3392.2
70°	3130.5	2946.8
72.5°	2634.8	2473.7
75°	2030.8	1894.9
77.5°	1444.5	1331.2
80°	1016.7	903.4
82.5°	651.8	561.2
85°	294.4	256.7
87.5°	83.0	80.5
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P671826

CATALOG NUMBER: CCP-SA-1E-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)