

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671848

Luminaire Tested: **CCP-SA-1E-760-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671848
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-1E-760-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/ SLR
distribution lens
Light Source: (16) 5700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5803.8 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 56.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 8.2 fc

Type IV - Short - N/A

REPORT NUMBER: P671848
CATALOG NUMBER: CCP-SA-1E-760-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1194.2	0.0	1194.2
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	4609.6	0.0	4609.6
	% Fixture	79.4	0.0	79.4
Total	Lumens	5803.8	0.0	5803.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.0	2.5
10°-20°	304.1	5.2
20°-30°	444.9	7.7
30°-40°	626.7	10.8
40°-50°	861.2	14.8
50°-60°	1173.8	20.2
60°-70°	1284.8	22.1
70°-80°	741.9	12.8
80°-90°	222.4	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5803.8	100.0
0°-180°	5803.8	100.0

Coefficient of Utilization



REPORT NUMBER: P671848


CATALOG NUMBER: CCP-SA-1E-760-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	596.1	10.3			
FM	(30°-60°)	2118.0	36.5			
FH	(60°-80°)	1706.7	29.4			G1/1800
FVH	(80°-90°)	188.9	3.3			G2/225
BL	(0°-30°)	296.9	5.1	B1/500		
BM	(30°-60°)	543.8	9.4	B1/1000		
BH	(60°-80°)	320.0	5.5	B1/500		G1/500
BVH	(80°-90°)	33.5	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4
2.5°	1912.6	1902.3	1894.6	1886.8	1876.5	1868.8	1858.5	1848.2	1835.4	1825.1	1812.2
5°	1801.9	1771.0	1740.1	1722.1	1701.5	1683.5	1662.9	1639.7	1616.6	1590.8	1567.6
7.5°	1680.9	1642.3	1603.7	1572.8	1539.3	1508.4	1475.0	1446.7	1418.3	1390.0	1361.7
10°	1567.6	1531.6	1495.6	1457.0	1415.8	1377.2	1336.0	1297.4	1258.7	1220.1	1181.5
12.5°	1493.0	1449.2	1408.0	1364.3	1323.1	1279.3	1235.6	1199.5	1163.5	1124.9	1088.9
15°	1459.5	1418.3	1379.7	1336.0	1292.2	1248.5	1204.7	1163.5	1124.9	1083.7	1042.5
17.5°	1539.3	1480.1	1420.9	1364.3	1307.7	1251.0	1194.4	1142.9	1091.4	1039.9	988.5
20°	1642.3	1567.6	1495.6	1426.1	1354.0	1284.5	1212.4	1140.3	1068.3	996.2	924.1
22.5°	1773.6	1688.6	1606.3	1516.2	1423.5	1333.4	1240.7	1150.6	1060.5	967.9	877.8
25°	2007.8	1907.4	1807.0	1678.3	1547.1	1418.3	1287.1	1168.7	1052.8	934.4	816.0
27.5°	2208.6	2072.2	1938.3	1783.9	1629.4	1475.0	1320.5	1184.1	1050.2	913.8	777.4
30°	2327.0	2193.2	2059.3	1871.4	1686.1	1498.1	1310.2	1158.4	1009.1	857.2	705.3
32.5°	2435.1	2285.8	2136.5	1930.6	1722.1	1516.2	1307.7	1140.3	975.6	808.3	641.0
35°	2584.4	2419.7	2257.5	2018.1	1778.7	1539.3	1299.9	1127.5	952.4	780.0	604.9
37.5°	2744.0	2540.7	2339.9	2074.7	1809.6	1544.5	1279.3	1109.4	939.6	769.7	599.8
40°	2919.1	2671.9	2427.4	2134.0	1843.1	1549.6	1256.2	1086.3	916.4	743.9	574.0
42.5°	3032.3	2764.6	2496.9	2180.3	1866.2	1549.6	1233.0	1065.7	898.4	728.5	561.2
45°	3096.7	2836.7	2579.3	2236.9	1894.6	1552.2	1209.8	1045.1	880.4	713.0	548.3
47.5°	3125.0	2883.0	2641.1	2280.7	1922.9	1562.5	1202.1	1034.8	864.9	697.6	527.7
50°	3199.6	2986.0	2772.3	2386.2	2002.7	1616.6	1230.4	1050.2	872.6	692.4	512.3
52.5°	3243.4	3060.6	2877.9	2481.5	2085.0	1688.6	1292.2	1091.4	890.6	689.9	489.1
55°	3403.0	3228.0	3052.9	2630.8	2206.0	1783.9	1359.1	1137.8	916.4	692.4	471.1
57.5°	3606.4	3421.0	3238.3	2782.6	2327.0	1871.4	1415.8	1179.0	939.6	702.7	463.3
60°	3747.9	3567.7	3390.1	2906.2	2419.7	1935.7	1449.2	1202.1	955.0	705.3	458.2
62.5°	3763.4	3531.7	3302.6	2831.5	2360.5	1886.8	1415.8	1176.4	937.0	695.0	455.6
65°	3665.6	3395.3	3125.0	2674.5	2224.0	1773.6	1323.1	1104.3	885.5	664.1	445.3
67.5°	3469.9	3153.3	2836.7	2424.8	2013.0	1601.1	1189.2	1001.3	816.0	628.1	440.2
70°	3014.3	2736.3	2460.9	2103.1	1747.8	1390.0	1032.2	877.8	725.9	571.5	417.0
72.5°	2530.4	2270.4	2013.0	1722.1	1433.8	1142.9	852.0	736.2	620.4	502.0	386.1
75°	1938.3	1742.7	1549.6	1333.4	1117.2	898.4	682.1	597.2	512.3	427.3	342.4
77.5°	1361.7	1256.2	1153.2	991.0	828.9	666.7	504.5	447.9	391.3	334.6	278.0
80°	924.1	864.9	808.3	692.4	576.6	458.2	342.4	306.3	267.7	231.7	193.1
82.5°	574.0	571.5	566.3	486.5	406.7	326.9	247.1	216.2	187.9	157.0	126.1
85°	262.6	306.3	347.5	303.7	260.0	216.2	172.5	151.9	131.3	108.1	87.5
87.5°	82.4	100.4	115.8	110.7	103.0	97.8	90.1	77.2	64.4	51.5	38.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4
2.5°	1801.9	1794.2	1783.9	1773.6	1760.7	1750.4	1737.5	1724.7	1722.1	1716.9	1714.4
5°	1552.2	1536.8	1518.7	1503.3	1487.8	1469.8	1454.4	1436.4	1423.5	1408.0	1395.2
7.5°	1333.4	1307.7	1279.3	1251.0	1225.3	1199.5	1171.2	1145.5	1132.6	1119.7	1106.9
10°	1158.4	1132.6	1109.4	1083.7	1065.7	1050.2	1032.2	1014.2	998.8	983.3	967.9
12.5°	1070.8	1052.8	1034.8	1016.8	996.2	978.2	957.6	937.0	919.0	903.5	885.5
15°	1016.8	991.0	962.7	937.0	908.7	882.9	854.6	826.3	805.7	787.7	767.1
17.5°	952.4	913.8	877.8	839.2	808.3	777.4	743.9	713.0	689.9	664.1	641.0
20°	880.4	836.6	790.3	746.5	710.5	677.0	641.0	604.9	579.2	550.9	525.1
22.5°	818.6	761.9	702.7	643.5	604.9	566.3	525.1	486.5	463.3	437.6	414.4
25°	751.6	689.9	625.5	561.2	522.5	481.4	442.8	401.6	383.5	368.1	350.1
27.5°	715.6	653.8	589.5	527.7	491.7	453.0	417.0	378.4	365.5	350.1	337.2
30°	643.5	584.3	522.5	460.8	435.0	411.9	386.1	360.4	355.2	352.7	347.5
32.5°	579.2	517.4	455.6	393.8	370.7	347.5	324.3	301.2	298.6	293.5	290.9
35°	545.7	486.5	424.7	365.5	344.9	321.8	301.2	278.0	272.9	265.1	260.0
37.5°	538.0	476.2	411.9	350.1	329.5	308.9	285.7	265.1	260.0	254.8	249.7
40°	517.4	458.2	401.6	342.4	321.8	301.2	278.0	257.4	252.3	247.1	242.0
42.5°	502.0	445.3	386.1	326.9	308.9	290.9	270.3	252.3	247.1	242.0	234.2
45°	489.1	429.9	368.1	308.9	296.0	283.2	267.7	254.8	249.7	242.0	236.8
47.5°	468.5	411.9	352.7	293.5	280.6	270.3	257.4	244.5	239.4	234.2	229.1
50°	453.0	393.8	334.6	275.4	265.1	254.8	244.5	234.2	234.2	236.8	236.8
52.5°	432.5	375.8	319.2	262.6	252.3	242.0	231.7	221.4	223.9	226.5	229.1
55°	414.4	360.4	303.7	247.1	236.8	226.5	213.7	203.4	205.9	208.5	211.1
57.5°	406.7	350.1	293.5	236.8	226.5	213.7	203.4	190.5	190.5	190.5	190.5
60°	401.6	342.4	285.7	226.5	213.7	203.4	190.5	177.6	175.0	175.0	172.5
62.5°	399.0	339.8	283.2	223.9	208.5	195.6	180.2	164.7	162.2	159.6	157.0
65°	388.7	334.6	278.0	221.4	203.4	187.9	169.9	151.9	149.3	149.3	146.7
67.5°	386.1	329.5	275.4	218.8	200.8	180.2	162.2	141.6	139.0	136.4	133.9
70°	365.5	316.6	265.1	213.7	193.1	175.0	154.4	133.9	131.3	126.1	123.6
72.5°	339.8	296.0	249.7	203.4	182.8	162.2	141.6	121.0	118.4	115.8	110.7
75°	301.2	260.0	218.8	177.6	159.6	144.2	126.1	108.1	105.5	103.0	97.8
77.5°	247.1	213.7	182.8	149.3	136.4	123.6	110.7	97.8	95.2	92.7	87.5
80°	175.0	154.4	136.4	115.8	108.1	97.8	90.1	79.8	79.8	77.2	77.2
82.5°	115.8	105.5	95.2	84.9	79.8	74.6	69.5	64.4	64.4	61.8	61.8
85°	82.4	77.2	69.5	64.4	61.8	56.6	54.1	48.9	48.9	48.9	48.9
87.5°	38.6	38.6	36.0	36.0	33.5	33.5	30.9	28.3	28.3	28.3	28.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4
2.5°	1709.2	1701.5	1693.8	1683.5	1675.8	1665.5	1652.6	1642.3	1629.4	1629.4	1626.8
5°	1379.7	1372.0	1364.3	1354.0	1346.3	1336.0	1328.3	1318.0	1307.7	1307.7	1305.1
7.5°	1094.0	1078.6	1063.1	1045.1	1029.7	1019.4	1009.1	996.2	985.9	978.2	970.4
10°	952.4	937.0	919.0	903.5	885.5	872.6	859.8	844.3	831.4	821.1	810.9
12.5°	867.5	849.5	831.4	813.4	795.4	777.4	761.9	743.9	725.9	713.0	700.2
15°	746.5	728.5	710.5	692.4	674.4	653.8	633.2	610.1	589.5	579.2	571.5
17.5°	615.2	597.2	576.6	558.6	538.0	522.5	507.1	491.7	476.2	465.9	458.2
20°	496.8	476.2	455.6	435.0	414.4	404.1	393.8	383.5	373.2	365.5	360.4
22.5°	388.7	375.8	365.5	352.7	339.8	332.1	326.9	319.2	311.5	311.5	311.5
25°	332.1	324.3	319.2	311.5	303.7	301.2	298.6	293.5	290.9	288.3	288.3
27.5°	321.8	314.0	306.3	298.6	290.9	288.3	285.7	280.6	278.0	278.0	278.0
30°	342.4	339.8	337.2	334.6	332.1	326.9	319.2	314.0	306.3	301.2	296.0
32.5°	285.7	283.2	283.2	280.6	278.0	283.2	285.7	290.9	293.5	296.0	298.6
35°	252.3	247.1	242.0	236.8	231.7	229.1	226.5	223.9	221.4	221.4	218.8
37.5°	244.5	239.4	234.2	229.1	223.9	221.4	218.8	216.2	213.7	213.7	211.1
40°	236.8	231.7	229.1	223.9	218.8	216.2	213.7	208.5	205.9	203.4	203.4
42.5°	229.1	226.5	221.4	218.8	213.7	211.1	208.5	203.4	200.8	198.2	195.6
45°	229.1	223.9	218.8	213.7	208.5	205.9	200.8	198.2	193.1	193.1	190.5
47.5°	223.9	218.8	213.7	208.5	203.4	200.8	195.6	193.1	187.9	185.3	182.8
50°	236.8	229.1	218.8	211.1	200.8	198.2	193.1	190.5	185.3	182.8	180.2
52.5°	231.7	223.9	213.7	205.9	195.6	190.5	187.9	182.8	177.6	175.0	172.5
55°	213.7	205.9	200.8	193.1	185.3	180.2	175.0	169.9	164.7	162.2	162.2
57.5°	190.5	187.9	185.3	182.8	180.2	175.0	169.9	162.2	157.0	154.4	151.9
60°	169.9	172.5	175.0	177.6	180.2	172.5	164.7	157.0	149.3	146.7	144.2
62.5°	154.4	159.6	164.7	167.3	172.5	164.7	157.0	149.3	141.6	139.0	136.4
65°	144.2	146.7	146.7	149.3	149.3	144.2	141.6	136.4	131.3	128.7	128.7
67.5°	131.3	131.3	131.3	128.7	128.7	126.1	126.1	123.6	121.0	118.4	118.4
70°	118.4	118.4	118.4	115.8	115.8	113.3	113.3	110.7	108.1	108.1	105.5
72.5°	108.1	108.1	105.5	105.5	103.0	103.0	103.0	100.4	100.4	97.8	97.8
75°	95.2	95.2	92.7	92.7	90.1	90.1	90.1	87.5	87.5	87.5	84.9
77.5°	84.9	84.9	82.4	82.4	79.8	79.8	79.8	77.2	77.2	74.6	74.6
80°	74.6	74.6	72.1	72.1	69.5	69.5	66.9	66.9	64.4	64.4	61.8
82.5°	59.2	59.2	59.2	59.2	59.2	56.6	56.6	54.1	51.5	51.5	48.9
85°	48.9	48.9	48.9	46.3	46.3	46.3	43.8	43.8	41.2	38.6	38.6
87.5°	28.3	28.3	28.3	25.7	25.7	25.7	25.7	25.7	25.7	25.7	23.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4
2.5°	1626.8	1624.3	1614.0	1603.7	1614.0	1624.3	1624.3	1624.3	1621.7	1621.7	1621.7
5°	1305.1	1302.5	1297.4	1292.2	1292.2	1289.6	1294.8	1299.9	1305.1	1310.2	1315.4
7.5°	960.2	952.4	944.7	937.0	942.1	944.7	952.4	957.6	965.3	970.4	983.3
10°	800.6	790.3	782.5	774.8	769.7	764.5	759.4	756.8	751.6	746.5	751.6
12.5°	684.7	671.8	659.0	643.5	641.0	638.4	633.2	628.1	622.9	617.8	615.2
15°	561.2	550.9	545.7	538.0	527.7	517.4	512.3	509.7	504.5	499.4	496.8
17.5°	447.9	437.6	429.9	422.2	419.6	414.4	414.4	414.4	414.4	414.4	414.4
20°	352.7	344.9	344.9	342.4	342.4	339.8	342.4	344.9	344.9	347.5	350.1
22.5°	308.9	308.9	306.3	303.7	306.3	306.3	308.9	311.5	314.0	316.6	319.2
25°	285.7	283.2	285.7	288.3	288.3	288.3	290.9	290.9	293.5	293.5	293.5
27.5°	275.4	275.4	278.0	278.0	280.6	280.6	280.6	278.0	278.0	275.4	275.4
30°	290.9	285.7	285.7	285.7	283.2	280.6	278.0	278.0	275.4	272.9	270.3
32.5°	301.2	303.7	301.2	296.0	293.5	288.3	285.7	280.6	278.0	272.9	267.7
35°	218.8	216.2	221.4	223.9	226.5	229.1	231.7	234.2	234.2	236.8	236.8
37.5°	211.1	208.5	208.5	205.9	205.9	205.9	205.9	205.9	203.4	203.4	205.9
40°	200.8	198.2	198.2	195.6	195.6	193.1	193.1	193.1	193.1	193.1	193.1
42.5°	193.1	190.5	190.5	190.5	190.5	187.9	187.9	185.3	185.3	182.8	182.8
45°	190.5	187.9	185.3	182.8	182.8	180.2	180.2	180.2	177.6	177.6	177.6
47.5°	180.2	177.6	177.6	175.0	175.0	172.5	172.5	172.5	169.9	169.9	169.9
50°	175.0	172.5	172.5	169.9	169.9	167.3	167.3	167.3	164.7	164.7	164.7
52.5°	167.3	164.7	164.7	164.7	162.2	159.6	159.6	159.6	157.0	157.0	157.0
55°	159.6	157.0	157.0	157.0	154.4	151.9	151.9	151.9	149.3	149.3	149.3
57.5°	149.3	146.7	146.7	144.2	144.2	144.2	144.2	144.2	141.6	141.6	141.6
60°	141.6	139.0	139.0	136.4	136.4	133.9	133.9	133.9	133.9	133.9	133.9
62.5°	133.9	131.3	128.7	126.1	128.7	128.7	128.7	128.7	126.1	126.1	126.1
65°	126.1	123.6	121.0	118.4	118.4	118.4	118.4	118.4	118.4	118.4	118.4
67.5°	115.8	113.3	110.7	108.1	110.7	110.7	110.7	110.7	110.7	110.7	110.7
70°	105.5	103.0	103.0	100.4	100.4	97.8	97.8	100.4	100.4	100.4	100.4
72.5°	95.2	92.7	92.7	90.1	90.1	90.1	90.1	90.1	90.1	90.1	90.1
75°	84.9	82.4	82.4	79.8	79.8	79.8	79.8	79.8	79.8	79.8	79.8
77.5°	72.1	69.5	69.5	69.5	69.5	69.5	69.5	72.1	72.1	72.1	72.1
80°	61.8	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.2
82.5°	48.9	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3
85°	36.0	33.5	33.5	33.5	36.0	36.0	36.0	36.0	36.0	36.0	36.0
87.5°	23.2	20.6	20.6	20.6	23.2	23.2	23.2	23.2	20.6	20.6	20.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4
2.5°	1621.7	1621.7	1621.7	1619.1	1616.6	1614.0	1611.4	1619.1	1624.3	1632.0	1637.1
5°	1318.0	1323.1	1325.7	1333.4	1341.1	1348.8	1356.6	1361.7	1366.9	1369.4	1374.6
7.5°	993.6	1006.5	1016.8	1027.1	1037.4	1045.1	1055.4	1063.1	1070.8	1078.6	1086.3
10°	754.2	759.4	761.9	772.2	780.0	790.3	798.0	805.7	813.4	818.6	826.3
12.5°	612.6	607.5	604.9	604.9	604.9	604.9	604.9	610.1	615.2	620.4	625.5
15°	494.2	491.7	489.1	486.5	483.9	478.8	476.2	481.4	486.5	491.7	496.8
17.5°	414.4	414.4	414.4	411.9	409.3	406.7	404.1	406.7	409.3	409.3	411.9
20°	355.2	357.8	360.4	363.0	363.0	365.5	365.5	368.1	370.7	370.7	373.2
22.5°	319.2	321.8	321.8	321.8	324.3	324.3	324.3	326.9	329.5	332.1	334.6
25°	290.9	290.9	288.3	288.3	290.9	290.9	290.9	290.9	293.5	293.5	293.5
27.5°	275.4	272.9	272.9	272.9	272.9	270.3	270.3	270.3	270.3	270.3	270.3
30°	267.7	265.1	262.6	260.0	260.0	257.4	254.8	254.8	254.8	254.8	254.8
32.5°	265.1	260.0	254.8	252.3	252.3	249.7	247.1	244.5	244.5	242.0	239.4
35°	236.8	234.2	234.2	231.7	229.1	226.5	223.9	223.9	223.9	221.4	221.4
37.5°	205.9	208.5	208.5	208.5	211.1	211.1	211.1	211.1	213.7	213.7	213.7
40°	193.1	193.1	193.1	195.6	198.2	198.2	200.8	200.8	203.4	203.4	203.4
42.5°	182.8	180.2	180.2	182.8	182.8	185.3	185.3	187.9	190.5	190.5	193.1
45°	177.6	175.0	175.0	175.0	175.0	172.5	172.5	175.0	177.6	180.2	182.8
47.5°	167.3	167.3	164.7	164.7	164.7	164.7	164.7	164.7	167.3	167.3	167.3
50°	162.2	162.2	159.6	159.6	159.6	159.6	159.6	159.6	159.6	159.6	159.6
52.5°	157.0	154.4	154.4	154.4	154.4	151.9	151.9	151.9	151.9	151.9	151.9
55°	149.3	146.7	146.7	146.7	146.7	146.7	146.7	146.7	149.3	149.3	149.3
57.5°	141.6	139.0	139.0	139.0	141.6	141.6	141.6	141.6	144.2	144.2	144.2
60°	133.9	133.9	133.9	133.9	133.9	133.9	133.9	136.4	136.4	139.0	139.0
62.5°	126.1	126.1	126.1	126.1	128.7	128.7	128.7	128.7	131.3	131.3	131.3
65°	118.4	118.4	118.4	118.4	121.0	121.0	121.0	121.0	121.0	121.0	121.0
67.5°	110.7	110.7	110.7	110.7	110.7	110.7	110.7	113.3	113.3	115.8	115.8
70°	100.4	97.8	97.8	100.4	100.4	103.0	103.0	105.5	105.5	108.1	108.1
72.5°	90.1	90.1	90.1	90.1	90.1	90.1	90.1	92.7	95.2	95.2	97.8
75°	79.8	79.8	79.8	79.8	82.4	82.4	82.4	84.9	84.9	87.5	87.5
77.5°	72.1	69.5	69.5	69.5	72.1	72.1	72.1	74.6	74.6	77.2	77.2
80°	59.2	59.2	59.2	59.2	61.8	61.8	61.8	61.8	64.4	64.4	64.4
82.5°	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	51.5	51.5	51.5
85°	36.0	36.0	36.0	36.0	38.6	38.6	38.6	38.6	38.6	38.6	38.6
87.5°	23.2	23.2	23.2	23.2	23.2	23.2	23.2	23.2	25.7	25.7	25.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848
 CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4
2.5°	1637.1	1637.1	1637.1	1637.1	1642.3	1644.9	1650.0	1652.6	1650.0	1647.4	1642.3
5°	1377.2	1379.7	1379.7	1382.3	1382.3	1382.3	1382.3	1382.3	1387.5	1392.6	1397.8
7.5°	1088.9	1091.4	1094.0	1096.6	1096.6	1096.6	1094.0	1094.0	1096.6	1096.6	1099.2
10°	834.0	844.3	852.0	859.8	854.6	846.9	841.7	834.0	834.0	834.0	831.4
12.5°	630.7	633.2	638.4	641.0	638.4	638.4	635.8	633.2	635.8	641.0	643.5
15°	499.4	499.4	502.0	502.0	504.5	507.1	507.1	509.7	514.8	517.4	522.5
17.5°	414.4	417.0	417.0	419.6	419.6	422.2	422.2	422.2	427.3	432.5	440.2
20°	373.2	373.2	373.2	373.2	373.2	370.7	370.7	368.1	370.7	375.8	378.4
22.5°	334.6	337.2	337.2	337.2	334.6	332.1	326.9	324.3	324.3	326.9	326.9
25°	293.5	290.9	290.9	288.3	288.3	290.9	290.9	290.9	293.5	293.5	296.0
27.5°	270.3	267.7	267.7	265.1	265.1	267.7	267.7	267.7	267.7	267.7	267.7
30°	252.3	252.3	249.7	247.1	249.7	249.7	252.3	252.3	254.8	254.8	257.4
32.5°	239.4	236.8	236.8	234.2	236.8	236.8	239.4	239.4	242.0	244.5	244.5
35°	221.4	221.4	221.4	221.4	221.4	221.4	218.8	218.8	218.8	218.8	218.8
37.5°	211.1	211.1	208.5	205.9	205.9	205.9	205.9	205.9	203.4	200.8	198.2
40°	203.4	200.8	200.8	198.2	195.6	195.6	193.1	190.5	190.5	187.9	187.9
42.5°	193.1	190.5	190.5	187.9	185.3	185.3	182.8	180.2	180.2	180.2	177.6
45°	180.2	180.2	177.6	175.0	175.0	175.0	172.5	172.5	172.5	172.5	169.9
47.5°	167.3	167.3	164.7	164.7	164.7	164.7	162.2	162.2	162.2	162.2	162.2
50°	159.6	159.6	159.6	159.6	159.6	159.6	157.0	157.0	157.0	157.0	157.0
52.5°	151.9	151.9	151.9	151.9	151.9	151.9	151.9	151.9	151.9	151.9	151.9
55°	149.3	149.3	149.3	149.3	149.3	149.3	146.7	146.7	146.7	149.3	149.3
57.5°	144.2	144.2	141.6	141.6	141.6	141.6	141.6	141.6	141.6	141.6	141.6
60°	139.0	139.0	139.0	139.0	139.0	139.0	139.0	139.0	139.0	139.0	139.0
62.5°	131.3	131.3	131.3	131.3	131.3	133.9	133.9	133.9	133.9	133.9	131.3
65°	121.0	123.6	123.6	123.6	123.6	123.6	123.6	123.6	123.6	123.6	123.6
67.5°	115.8	115.8	115.8	115.8	115.8	115.8	115.8	115.8	115.8	115.8	115.8
70°	108.1	108.1	105.5	105.5	105.5	108.1	108.1	108.1	108.1	108.1	108.1
72.5°	97.8	97.8	97.8	97.8	97.8	97.8	97.8	97.8	97.8	100.4	100.4
75°	87.5	87.5	87.5	87.5	87.5	87.5	87.5	87.5	87.5	87.5	87.5
77.5°	77.2	77.2	74.6	74.6	74.6	77.2	77.2	77.2	77.2	79.8	79.8
80°	64.4	64.4	64.4	64.4	64.4	64.4	64.4	64.4	64.4	66.9	66.9
82.5°	51.5	51.5	51.5	51.5	51.5	51.5	51.5	51.5	51.5	54.1	54.1
85°	38.6	41.2	41.2	41.2	41.2	41.2	41.2	41.2	41.2	43.8	43.8
87.5°	25.7	25.7	25.7	25.7	25.7	25.7	23.2	23.2	23.2	23.2	20.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4
2.5°	1639.7	1642.3	1644.9	1644.9	1647.4	1650.0	1650.0	1660.3	1670.6	1675.8	1680.9
5°	1402.9	1400.3	1400.3	1397.8	1395.2	1402.9	1410.6	1426.1	1441.5	1444.1	1449.2
7.5°	1099.2	1101.7	1104.3	1104.3	1106.9	1099.2	1088.9	1091.4	1094.0	1106.9	1117.2
10°	831.4	834.0	836.6	836.6	839.2	836.6	831.4	839.2	846.9	857.2	870.1
12.5°	646.1	653.8	661.6	666.7	674.4	679.6	682.1	692.4	700.2	713.0	725.9
15°	527.7	532.8	538.0	543.1	548.3	553.4	558.6	568.9	579.2	594.6	610.1
17.5°	445.3	445.3	447.9	447.9	447.9	453.0	458.2	463.3	465.9	481.4	496.8
20°	381.0	378.4	375.8	373.2	370.7	375.8	378.4	381.0	383.5	393.8	401.6
22.5°	326.9	326.9	329.5	329.5	329.5	326.9	321.8	324.3	324.3	329.5	337.2
25°	296.0	296.0	296.0	293.5	293.5	296.0	298.6	298.6	296.0	298.6	301.2
27.5°	267.7	270.3	270.3	272.9	272.9	275.4	275.4	275.4	275.4	278.0	280.6
30°	257.4	257.4	260.0	260.0	260.0	262.6	265.1	265.1	265.1	267.7	272.9
32.5°	247.1	249.7	252.3	254.8	257.4	260.0	260.0	262.6	262.6	265.1	267.7
35°	218.8	216.2	216.2	213.7	211.1	211.1	211.1	211.1	208.5	211.1	211.1
37.5°	195.6	195.6	195.6	193.1	193.1	195.6	195.6	195.6	195.6	198.2	198.2
40°	185.3	185.3	185.3	185.3	185.3	185.3	185.3	187.9	187.9	190.5	193.1
42.5°	177.6	177.6	177.6	177.6	177.6	180.2	180.2	180.2	180.2	182.8	182.8
45°	169.9	169.9	169.9	169.9	169.9	169.9	169.9	172.5	172.5	175.0	177.6
47.5°	162.2	162.2	162.2	162.2	162.2	164.7	167.3	167.3	167.3	169.9	169.9
50°	157.0	157.0	157.0	157.0	157.0	159.6	159.6	162.2	162.2	164.7	167.3
52.5°	151.9	151.9	151.9	151.9	151.9	154.4	154.4	157.0	157.0	159.6	162.2
55°	149.3	149.3	149.3	146.7	146.7	149.3	149.3	151.9	151.9	154.4	154.4
57.5°	141.6	141.6	141.6	141.6	141.6	141.6	141.6	144.2	144.2	146.7	149.3
60°	139.0	139.0	136.4	136.4	133.9	136.4	136.4	139.0	139.0	141.6	141.6
62.5°	131.3	131.3	131.3	128.7	128.7	131.3	131.3	131.3	131.3	133.9	136.4
65°	123.6	123.6	123.6	121.0	121.0	123.6	123.6	123.6	123.6	126.1	128.7
67.5°	115.8	115.8	115.8	113.3	113.3	113.3	113.3	115.8	115.8	118.4	121.0
70°	108.1	108.1	108.1	105.5	105.5	105.5	103.0	105.5	108.1	110.7	110.7
72.5°	100.4	100.4	100.4	97.8	97.8	97.8	95.2	97.8	97.8	100.4	100.4
75°	87.5	87.5	87.5	87.5	87.5	87.5	84.9	84.9	84.9	87.5	87.5
77.5°	79.8	79.8	79.8	77.2	77.2	77.2	74.6	74.6	74.6	77.2	77.2
80°	66.9	66.9	66.9	64.4	64.4	64.4	61.8	61.8	61.8	64.4	64.4
82.5°	54.1	54.1	54.1	51.5	51.5	51.5	48.9	48.9	48.9	51.5	51.5
85°	43.8	43.8	43.8	43.8	43.8	43.8	41.2	41.2	41.2	43.8	46.3
87.5°	20.6	20.6	23.2	23.2	23.2	23.2	20.6	20.6	18.0	18.0	20.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4
2.5°	1686.1	1691.2	1704.1	1714.4	1727.2	1737.5	1745.3	1755.6	1763.3	1771.0	1776.1
5°	1451.8	1454.4	1467.3	1480.1	1490.4	1503.3	1521.3	1539.3	1557.3	1575.4	1588.2
7.5°	1130.0	1140.3	1155.8	1173.8	1189.2	1204.7	1222.7	1243.3	1261.3	1279.3	1297.4
10°	880.4	890.6	906.1	921.5	934.4	949.9	970.4	991.0	1011.6	1032.2	1052.8
12.5°	738.8	751.6	769.7	787.7	803.1	821.1	846.9	870.1	895.8	919.0	944.7
15°	622.9	638.4	661.6	687.3	710.5	733.6	759.4	785.1	808.3	834.0	859.8
17.5°	512.3	527.7	548.3	571.5	592.0	612.6	643.5	671.8	702.7	731.1	759.4
20°	411.9	419.6	440.2	460.8	481.4	502.0	525.1	548.3	571.5	594.6	630.7
22.5°	342.4	347.5	357.8	365.5	375.8	383.5	406.7	429.9	450.5	473.6	507.1
25°	301.2	303.7	311.5	316.6	324.3	329.5	344.9	357.8	373.2	386.1	417.0
27.5°	280.6	283.2	285.7	288.3	290.9	293.5	303.7	314.0	321.8	332.1	360.4
30°	275.4	278.0	285.7	290.9	298.6	303.7	308.9	314.0	319.2	324.3	342.4
32.5°	270.3	272.9	272.9	270.3	270.3	267.7	272.9	275.4	280.6	283.2	298.6
35°	213.7	213.7	216.2	218.8	221.4	223.9	231.7	236.8	244.5	249.7	262.6
37.5°	200.8	200.8	203.4	208.5	211.1	213.7	218.8	223.9	229.1	234.2	247.1
40°	193.1	195.6	198.2	200.8	203.4	205.9	211.1	213.7	218.8	221.4	231.7
42.5°	185.3	185.3	187.9	193.1	195.6	198.2	203.4	205.9	211.1	213.7	223.9
45°	180.2	182.8	185.3	187.9	187.9	190.5	195.6	200.8	203.4	208.5	218.8
47.5°	172.5	172.5	177.6	180.2	185.3	187.9	193.1	195.6	200.8	203.4	213.7
50°	167.3	169.9	175.0	177.6	182.8	185.3	193.1	198.2	205.9	211.1	216.2
52.5°	162.2	164.7	169.9	172.5	177.6	180.2	190.5	200.8	208.5	218.8	218.8
55°	157.0	157.0	162.2	169.9	175.0	180.2	185.3	193.1	198.2	203.4	203.4
57.5°	149.3	151.9	157.0	164.7	169.9	175.0	180.2	185.3	187.9	193.1	190.5
60°	144.2	144.2	151.9	159.6	167.3	175.0	175.0	175.0	172.5	172.5	172.5
62.5°	136.4	139.0	149.3	162.2	172.5	182.8	175.0	167.3	159.6	151.9	154.4
65°	131.3	133.9	139.0	146.7	151.9	157.0	151.9	149.3	144.2	139.0	141.6
67.5°	121.0	123.6	126.1	126.1	128.7	128.7	128.7	128.7	128.7	128.7	131.3
70°	113.3	113.3	113.3	115.8	115.8	115.8	115.8	115.8	115.8	115.8	118.4
72.5°	103.0	103.0	103.0	103.0	103.0	103.0	103.0	103.0	103.0	103.0	105.5
75°	90.1	90.1	90.1	90.1	90.1	90.1	90.1	90.1	90.1	90.1	92.7
77.5°	79.8	79.8	79.8	79.8	79.8	79.8	79.8	79.8	77.2	77.2	79.8
80°	66.9	66.9	66.9	66.9	64.4	64.4	64.4	64.4	64.4	64.4	66.9
82.5°	54.1	54.1	54.1	54.1	51.5	51.5	51.5	51.5	48.9	48.9	51.5
85°	48.9	51.5	51.5	54.1	54.1	54.1	51.5	48.9	46.3	43.8	43.8
87.5°	20.6	20.6	20.6	20.6	18.0	18.0	18.0	18.0	18.0	18.0	18.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4
2.5°	1783.9	1789.0	1794.2	1801.9	1812.2	1819.9	1827.6	1843.1	1861.1	1876.5	1892.0
5°	1601.1	1614.0	1626.8	1642.3	1657.7	1670.6	1686.1	1716.9	1747.8	1776.1	1807.0
7.5°	1312.8	1330.8	1346.3	1372.0	1395.2	1420.9	1444.1	1482.7	1518.7	1557.3	1593.4
10°	1073.4	1094.0	1114.6	1148.1	1184.1	1217.6	1251.0	1281.9	1315.4	1346.3	1377.2
12.5°	970.4	993.6	1019.4	1039.9	1063.1	1083.7	1104.3	1140.3	1176.4	1212.4	1248.5
15°	885.5	911.2	937.0	962.7	985.9	1011.6	1034.8	1065.7	1099.2	1130.0	1160.9
17.5°	787.7	813.4	841.7	870.1	898.4	926.7	955.0	998.8	1042.5	1083.7	1127.5
20°	664.1	700.2	733.6	772.2	810.9	849.5	888.1	934.4	980.7	1024.5	1070.8
22.5°	540.6	574.0	607.5	653.8	700.2	743.9	790.3	852.0	911.2	973.0	1032.2
25°	450.5	481.4	512.3	563.7	612.6	664.1	713.0	787.7	859.8	934.4	1006.5
27.5°	388.7	417.0	445.3	499.4	553.4	604.9	659.0	741.3	821.1	903.5	983.3
30°	360.4	378.4	396.4	447.9	499.4	548.3	599.8	679.6	759.4	839.2	919.0
32.5°	314.0	329.5	344.9	391.3	437.6	481.4	527.7	610.1	689.9	772.2	852.0
35°	278.0	290.9	303.7	347.5	388.7	432.5	473.6	556.0	638.4	720.8	803.1
37.5°	257.4	270.3	280.6	319.2	360.4	399.0	437.6	520.0	599.8	682.1	761.9
40°	242.0	249.7	260.0	298.6	334.6	373.2	409.3	483.9	561.2	635.8	710.5
42.5°	231.7	242.0	249.7	283.2	319.2	352.7	386.1	458.2	530.3	599.8	671.8
45°	229.1	239.4	249.7	278.0	306.3	332.1	360.4	429.9	499.4	568.9	638.4
47.5°	223.9	231.7	242.0	265.1	285.7	308.9	329.5	399.0	468.5	535.4	604.9
50°	221.4	223.9	229.1	249.7	270.3	290.9	311.5	381.0	450.5	520.0	589.5
52.5°	218.8	218.8	218.8	236.8	254.8	270.3	288.3	357.8	429.9	499.4	568.9
55°	203.4	200.8	200.8	218.8	234.2	252.3	267.7	337.2	406.7	473.6	543.1
57.5°	187.9	185.3	182.8	198.2	213.7	229.1	244.5	314.0	386.1	455.6	525.1
60°	172.5	169.9	169.9	185.3	198.2	213.7	226.5	298.6	368.1	440.2	509.7
62.5°	154.4	157.0	157.0	169.9	185.3	198.2	211.1	283.2	357.8	429.9	502.0
65°	141.6	144.2	144.2	159.6	175.0	190.5	205.9	275.4	347.5	417.0	486.5
67.5°	131.3	133.9	133.9	151.9	167.3	185.3	200.8	262.6	326.9	388.7	450.5
70°	121.0	121.0	123.6	141.6	159.6	177.6	195.6	249.7	303.7	355.2	409.3
72.5°	108.1	110.7	113.3	131.3	146.7	164.7	180.2	229.1	278.0	326.9	375.8
75°	95.2	97.8	100.4	115.8	131.3	146.7	162.2	208.5	252.3	298.6	342.4
77.5°	84.9	87.5	90.1	103.0	115.8	128.7	141.6	175.0	211.1	244.5	278.0
80°	69.5	69.5	72.1	82.4	92.7	100.4	110.7	133.9	157.0	177.6	200.8
82.5°	51.5	54.1	54.1	61.8	66.9	74.6	79.8	92.7	103.0	115.8	126.1
85°	43.8	41.2	41.2	46.3	48.9	54.1	56.6	64.4	69.5	77.2	82.4
87.5°	18.0	15.4	15.4	18.0	23.2	25.7	28.3	28.3	30.9	30.9	30.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4
2.5°	1899.7	1904.9	1912.6	1917.7	1930.6	1940.9	1953.8	1964.1	1971.8	1984.7	1979.5
5°	1830.2	1853.4	1876.5	1899.7	1917.7	1935.7	1951.2	1969.2	1989.8	2028.4	2038.7
7.5°	1624.3	1655.2	1683.5	1714.4	1750.4	1786.4	1822.5	1858.5	1892.0	1940.9	1971.8
10°	1420.9	1464.7	1505.9	1549.6	1583.1	1616.6	1647.4	1680.9	1727.2	1776.1	1832.8
12.5°	1292.2	1336.0	1379.7	1423.5	1472.4	1518.7	1567.6	1614.0	1657.7	1696.4	1760.7
15°	1207.3	1256.2	1302.5	1348.8	1408.0	1464.7	1523.9	1580.5	1644.9	1696.4	1740.1
17.5°	1186.7	1245.9	1302.5	1361.7	1423.5	1485.3	1547.1	1608.8	1673.2	1750.4	1807.0
20°	1150.6	1230.4	1310.2	1390.0	1469.8	1547.1	1626.8	1704.1	1789.0	1881.7	1907.4
22.5°	1130.0	1225.3	1323.1	1418.3	1526.5	1637.1	1745.3	1853.4	1943.5	2013.0	2090.2
25°	1127.5	1245.9	1366.9	1485.3	1621.7	1755.6	1892.0	2025.8	2141.7	2211.2	2273.0
27.5°	1124.9	1269.0	1410.6	1552.2	1719.5	1884.3	2051.6	2216.3	2324.4	2424.8	2476.3
30°	1094.0	1266.5	1441.5	1614.0	1801.9	1989.8	2177.7	2365.6	2476.3	2545.8	2571.6
32.5°	1055.4	1258.7	1462.1	1665.5	1879.1	2092.8	2303.8	2517.5	2605.0	2664.2	2643.6
35°	1024.5	1248.5	1469.8	1691.2	1917.7	2146.8	2373.3	2599.9	2726.0	2808.4	2774.9
37.5°	996.2	1230.4	1464.7	1698.9	1964.1	2229.2	2494.3	2759.5	2880.5	2968.0	2929.4
40°	962.7	1212.4	1464.7	1714.4	2018.1	2319.3	2623.0	2924.2	3081.2	3155.9	3096.7
42.5°	934.4	1194.4	1457.0	1716.9	2041.3	2365.6	2690.0	3014.3	3189.3	3294.9	3220.2
45°	898.4	1158.4	1415.8	1675.8	2033.6	2391.4	2746.6	3104.4	3307.8	3390.1	3287.2
47.5°	859.8	1117.2	1372.0	1626.8	2007.8	2388.8	2769.8	3150.7	3338.6	3436.5	3341.2
50°	846.9	1104.3	1359.1	1616.6	2028.4	2442.8	2854.7	3266.6	3403.0	3482.8	3356.7
52.5°	844.3	1117.2	1392.6	1665.5	2079.9	2491.8	2906.2	3318.1	3428.7	3513.7	3400.4
55°	836.6	1132.6	1426.1	1719.5	2152.0	2587.0	3019.5	3451.9	3562.6	3624.4	3539.4
57.5°	844.3	1163.5	1480.1	1799.3	2244.6	2690.0	3135.3	3580.6	3714.5	3758.2	3740.2
60°	849.5	1189.2	1526.5	1866.2	2301.3	2736.3	3171.3	3606.4	3745.4	3853.5	3874.1
62.5°	836.6	1171.2	1503.3	1837.9	2231.8	2625.6	3019.5	3413.3	3642.4	3802.0	3894.7
65°	798.0	1106.9	1418.3	1727.2	2090.2	2455.7	2818.7	3181.6	3423.6	3660.4	3735.1
67.5°	713.0	975.6	1238.2	1500.7	1817.3	2134.0	2448.0	2764.6	3068.4	3297.5	3400.4
70°	617.8	823.7	1032.2	1238.2	1526.5	1814.8	2103.1	2391.4	2659.1	2911.3	3009.2
72.5°	538.0	697.6	859.8	1019.4	1225.3	1428.6	1634.6	1837.9	2154.5	2406.8	2502.1
75°	458.2	574.0	687.3	803.1	944.7	1086.3	1225.3	1366.9	1590.8	1817.3	1912.6
77.5°	352.7	429.9	504.5	579.2	677.0	772.2	870.1	965.3	1122.3	1292.2	1341.1
80°	244.5	288.3	329.5	373.2	450.5	527.7	604.9	682.1	785.1	880.4	955.0
82.5°	151.9	180.2	205.9	231.7	293.5	355.2	414.4	476.2	517.4	522.5	597.2
85°	97.8	115.8	131.3	146.7	182.8	221.4	257.4	293.5	262.6	244.5	290.9
87.5°	38.6	48.9	56.6	64.4	61.8	59.2	56.6	54.1	46.3	41.2	51.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4
2.5°	1984.7	1992.4	2000.1	2005.2	2013.0	2015.5	2018.1	2018.1	2020.7	2023.3	2028.4
5°	2079.9	2095.3	2110.8	2123.7	2139.1	2152.0	2162.3	2175.1	2185.4	2185.4	2182.9
7.5°	2000.1	2038.7	2077.3	2115.9	2154.5	2182.9	2208.6	2236.9	2262.7	2267.8	2273.0
10°	1894.6	1935.7	1974.4	2015.5	2054.2	2097.9	2139.1	2180.3	2224.0	2231.8	2242.1
12.5°	1796.7	1845.7	1894.6	1940.9	1989.8	2020.7	2051.6	2079.9	2110.8	2131.4	2152.0
15°	1794.2	1835.4	1876.5	1915.2	1956.3	1974.4	1992.4	2007.8	2025.8	2025.8	2028.4
17.5°	1853.4	1879.1	1904.9	1928.0	1953.8	1956.3	1961.5	1964.1	1966.6	1958.9	1951.2
20°	1969.2	1979.5	1989.8	2000.1	2010.4	1992.4	1976.9	1958.9	1940.9	1920.3	1902.3
22.5°	2139.1	2115.9	2092.8	2069.6	2046.4	2015.5	1982.1	1951.2	1917.7	1892.0	1866.2
25°	2298.7	2270.4	2242.1	2213.8	2185.4	2118.5	2051.6	1982.1	1915.2	1886.8	1858.5
27.5°	2512.4	2468.6	2424.8	2381.1	2337.3	2247.2	2157.1	2067.0	1976.9	1928.0	1881.7
30°	2563.8	2514.9	2466.0	2414.5	2365.6	2278.1	2193.2	2105.6	2018.1	1961.5	1907.4
32.5°	2638.5	2581.9	2525.2	2468.6	2412.0	2327.0	2242.1	2154.5	2069.6	2018.1	1964.1
35°	2762.0	2697.7	2633.3	2566.4	2502.1	2414.5	2329.6	2242.1	2154.5	2095.3	2038.7
37.5°	2867.6	2792.9	2718.3	2643.6	2569.0	2491.8	2412.0	2334.7	2254.9	2195.7	2139.1
40°	2986.0	2903.6	2821.2	2741.4	2659.1	2587.0	2514.9	2440.3	2368.2	2321.9	2275.5
42.5°	3089.0	2988.6	2890.7	2792.9	2692.5	2643.6	2597.3	2548.4	2499.5	2476.3	2450.6
45°	3161.0	3068.4	2973.1	2880.5	2787.8	2751.7	2715.7	2679.7	2643.6	2666.8	2690.0
47.5°	3191.9	3117.3	3045.2	2973.1	2898.5	2911.3	2924.2	2934.5	2947.4	2978.3	3011.7
50°	3220.2	3179.0	3135.3	3094.1	3050.3	3099.3	3145.6	3194.5	3243.4	3307.8	3372.1
52.5°	3276.9	3253.7	3233.1	3209.9	3186.8	3271.7	3356.7	3441.6	3526.6	3598.6	3670.7
55°	3446.8	3428.7	3410.7	3390.1	3372.1	3493.1	3611.5	3732.5	3853.5	3928.1	4002.8
57.5°	3681.0	3670.7	3657.8	3647.5	3634.7	3753.1	3868.9	3984.8	4103.2	4175.2	4249.9
60°	3858.6	3861.2	3861.2	3863.8	3863.8	3953.9	4044.0	4136.6	4226.7	4288.5	4352.9
62.5°	3953.9	3948.7	3943.6	3938.4	3933.3	4007.9	4082.6	4157.2	4231.9	4278.2	4324.5
65°	3850.9	3879.2	3907.5	3935.8	3964.2	3974.5	3982.2	3992.5	4000.2	4028.5	4056.8
67.5°	3506.0	3562.6	3616.7	3673.3	3727.3	3688.7	3652.7	3614.1	3575.5	3583.2	3588.3
70°	3122.4	3186.8	3253.7	3318.1	3382.4	3292.3	3202.2	3109.5	3019.5	2988.6	2957.7
72.5°	2633.3	2690.0	2749.2	2805.8	2862.4	2751.7	2643.6	2532.9	2422.3	2368.2	2314.1
75°	2013.0	2079.9	2149.4	2216.3	2283.3	2159.7	2033.6	1910.0	1783.9	1747.8	1714.4
77.5°	1467.3	1547.1	1626.8	1706.6	1786.4	1675.8	1565.1	1451.8	1341.1	1320.5	1299.9
80°	1068.3	1130.0	1189.2	1251.0	1310.2	1245.9	1181.5	1117.2	1052.8	1050.2	1047.7
82.5°	720.8	774.8	826.3	880.4	931.8	906.1	882.9	857.2	831.4	857.2	885.5
85°	370.7	445.3	522.5	597.2	671.8	664.1	659.0	651.3	643.5	677.0	707.9
87.5°	74.6	139.0	203.4	265.1	329.5	314.0	298.6	280.6	265.1	275.4	283.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4
2.5°	2031.0	2033.6	2033.6	2033.6	2033.6	2033.6	2028.4	2025.8	2020.7	2015.5	2007.8
5°	2182.9	2180.3	2170.0	2159.7	2146.8	2136.5	2128.8	2118.5	2110.8	2100.5	2085.0
7.5°	2278.1	2283.3	2265.2	2249.8	2231.8	2213.8	2195.7	2177.7	2159.7	2141.7	2105.6
10°	2249.8	2257.5	2247.2	2236.9	2224.0	2213.8	2193.2	2170.0	2149.4	2126.2	2082.5
12.5°	2170.0	2190.6	2185.4	2180.3	2175.1	2170.0	2157.1	2141.7	2128.8	2113.4	2064.5
15°	2028.4	2028.4	2031.0	2033.6	2033.6	2036.1	2038.7	2041.3	2043.9	2046.4	2018.1
17.5°	1943.5	1935.7	1935.7	1935.7	1935.7	1935.7	1946.0	1958.9	1969.2	1979.5	1971.8
20°	1881.7	1863.7	1861.1	1861.1	1858.5	1855.9	1874.0	1894.6	1912.6	1930.6	1940.9
22.5°	1840.5	1814.8	1812.2	1809.6	1807.0	1804.5	1827.6	1850.8	1874.0	1897.1	1933.2
25°	1830.2	1801.9	1804.5	1807.0	1807.0	1809.6	1827.6	1845.7	1863.7	1881.7	1943.5
27.5°	1832.8	1786.4	1789.0	1791.6	1791.6	1794.2	1822.5	1848.2	1876.5	1902.3	1979.5
30°	1850.8	1796.7	1791.6	1786.4	1781.3	1776.1	1814.8	1853.4	1892.0	1930.6	1989.8
32.5°	1912.6	1861.1	1848.2	1835.4	1822.5	1809.6	1855.9	1899.7	1946.0	1989.8	2038.7
35°	1979.5	1922.9	1917.7	1912.6	1904.9	1899.7	1940.9	1984.7	2025.8	2067.0	2110.8
37.5°	2079.9	2023.3	2018.1	2010.4	2005.2	1997.5	2043.9	2087.6	2134.0	2177.7	2216.3
40°	2229.2	2182.9	2180.3	2180.3	2177.7	2175.1	2211.2	2249.8	2285.8	2321.9	2347.6
42.5°	2427.4	2404.2	2412.0	2422.3	2430.0	2437.7	2466.0	2496.9	2525.2	2553.5	2545.8
45°	2713.1	2736.3	2738.9	2741.4	2744.0	2746.6	2754.3	2764.6	2772.3	2780.1	2749.2
47.5°	3042.6	3073.5	3089.0	3104.4	3117.3	3132.7	3122.4	3109.5	3099.3	3086.4	3009.2
50°	3433.9	3498.2	3495.7	3493.1	3487.9	3485.4	3464.8	3444.2	3421.0	3400.4	3287.2
52.5°	3742.8	3814.9	3827.7	3840.6	3853.5	3866.3	3827.7	3789.1	3747.9	3709.3	3567.7
55°	4074.8	4149.5	4152.1	4154.6	4154.6	4157.2	4103.2	4049.1	3992.5	3938.4	3791.7
57.5°	4322.0	4394.0	4386.3	4381.2	4373.4	4365.7	4301.4	4237.0	4172.7	4108.3	3961.6
60°	4414.6	4476.4	4461.0	4445.5	4427.5	4412.1	4363.1	4314.2	4262.8	4213.8	4072.3
62.5°	4370.9	4417.2	4394.0	4373.4	4350.3	4327.1	4265.3	4201.0	4139.2	4074.8	3971.9
65°	4082.6	4110.9	4080.0	4051.7	4023.4	3992.5	3941.0	3889.5	3835.5	3784.0	3714.5
67.5°	3596.1	3601.2	3598.6	3596.1	3593.5	3590.9	3516.3	3441.6	3364.4	3289.7	3284.6
70°	2929.4	2898.5	2903.6	2911.3	2916.5	2921.6	2865.0	2810.9	2754.3	2697.7	2723.4
72.5°	2260.1	2206.0	2218.9	2234.3	2247.2	2260.1	2213.8	2170.0	2123.7	2077.3	2113.4
75°	1678.3	1644.9	1657.7	1673.2	1686.1	1698.9	1680.9	1662.9	1642.3	1624.3	1657.7
77.5°	1279.3	1258.7	1261.3	1261.3	1263.9	1263.9	1266.5	1271.6	1274.2	1276.8	1312.8
80°	1042.5	1039.9	1037.4	1034.8	1029.7	1027.1	1052.8	1078.6	1104.3	1130.0	1148.1
82.5°	911.2	937.0	921.5	908.7	893.2	877.8	900.9	924.1	947.3	970.4	962.7
85°	741.3	772.2	743.9	715.6	684.7	656.4	677.0	695.0	715.6	733.6	723.3
87.5°	293.5	301.2	254.8	211.1	164.7	118.4	187.9	254.8	324.3	391.3	401.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4	1853.4
2.5°	2000.1	1989.8	1982.1	1979.5	1974.4	1971.8	1966.6	1961.5	1953.8	1948.6	1940.9
5°	2067.0	2051.6	2033.6	2007.8	1984.7	1958.9	1933.2	1910.0	1886.8	1861.1	1837.9
7.5°	2069.6	2033.6	1997.5	1964.1	1928.0	1894.6	1858.5	1827.6	1794.2	1760.7	1729.8
10°	2041.3	1997.5	1953.8	1910.0	1868.8	1825.1	1781.3	1745.3	1706.6	1668.0	1632.0
12.5°	2018.1	1969.2	1920.3	1868.8	1819.9	1768.4	1716.9	1680.9	1644.9	1608.8	1572.8
15°	1989.8	1958.9	1930.6	1884.3	1837.9	1791.6	1745.3	1696.4	1650.0	1601.1	1552.2
17.5°	1966.6	1958.9	1951.2	1920.3	1889.4	1855.9	1825.1	1776.1	1727.2	1675.8	1626.8
20°	1953.8	1964.1	1974.4	1958.9	1943.5	1925.4	1910.0	1874.0	1837.9	1799.3	1763.3
22.5°	1969.2	2007.8	2043.9	2046.4	2051.6	2054.2	2056.7	2023.3	1989.8	1953.8	1920.3
25°	2005.2	2067.0	2128.8	2162.3	2195.7	2231.8	2265.2	2244.6	2224.0	2203.5	2182.9
27.5°	2054.2	2131.4	2208.6	2257.5	2303.8	2352.8	2401.7	2399.1	2396.5	2391.4	2388.8
30°	2046.4	2105.6	2164.8	2224.0	2283.3	2342.5	2401.7	2432.6	2460.9	2491.8	2522.6
32.5°	2090.2	2139.1	2190.6	2252.4	2314.1	2378.5	2440.3	2504.6	2566.4	2630.8	2695.1
35°	2157.1	2200.9	2247.2	2314.1	2383.6	2450.6	2520.1	2597.3	2677.1	2756.9	2834.1
37.5°	2257.5	2296.1	2337.3	2393.9	2453.1	2509.8	2569.0	2682.2	2795.5	2911.3	3024.6
40°	2373.3	2399.1	2424.8	2478.9	2532.9	2587.0	2641.1	2782.6	2924.2	3065.8	3207.4
42.5°	2540.7	2532.9	2525.2	2569.0	2615.3	2659.1	2705.4	2834.1	2962.8	3091.5	3220.2
45°	2718.3	2687.4	2656.5	2677.1	2700.3	2720.9	2744.0	2875.3	3006.6	3140.4	3271.7
47.5°	2931.9	2854.7	2777.5	2759.5	2741.4	2720.9	2702.8	2844.4	2986.0	3130.1	3271.7
50°	3173.9	3058.1	2944.8	2898.5	2849.6	2803.2	2754.3	2870.2	2988.6	3107.0	3222.8
52.5°	3426.2	3282.0	3140.4	3068.4	2996.3	2921.6	2849.6	2947.4	3047.8	3148.2	3246.0
55°	3642.4	3495.7	3346.4	3261.4	3176.5	3091.5	3006.6	3104.4	3202.2	3300.0	3397.9
57.5°	3814.9	3668.1	3521.4	3441.6	3359.2	3279.4	3197.1	3289.7	3385.0	3480.2	3572.9
60°	3933.3	3791.7	3650.1	3572.9	3495.7	3418.4	3341.2	3451.9	3562.6	3675.9	3786.5
62.5°	3871.5	3768.5	3665.6	3632.1	3598.6	3562.6	3529.1	3634.7	3737.6	3843.2	3948.7
65°	3645.0	3575.5	3506.0	3539.4	3575.5	3608.9	3645.0	3714.5	3784.0	3856.0	3925.5
67.5°	3276.9	3271.7	3264.0	3338.6	3413.3	3490.5	3565.2	3611.5	3655.3	3701.6	3747.9
70°	2749.2	2777.5	2803.2	2931.9	3060.6	3189.3	3318.1	3336.1	3354.1	3372.1	3390.1
72.5°	2152.0	2188.0	2226.6	2396.5	2563.8	2733.7	2903.6	2893.3	2883.0	2870.2	2859.9
75°	1693.8	1727.2	1763.3	1920.3	2077.3	2234.3	2391.4	2347.6	2306.4	2262.7	2218.9
77.5°	1351.4	1387.5	1426.1	1572.8	1719.5	1868.8	2015.5	1910.0	1804.5	1698.9	1593.4
80°	1163.5	1181.5	1197.0	1297.4	1395.2	1495.6	1596.0	1487.8	1377.2	1266.5	1158.4
82.5°	955.0	944.7	937.0	996.2	1055.4	1114.6	1173.8	1070.8	967.9	862.3	759.4
85°	713.0	702.7	692.4	723.3	754.2	787.7	818.6	700.2	581.8	460.8	342.4
87.5°	414.4	424.7	435.0	468.5	502.0	538.0	571.5	450.5	329.5	205.9	84.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671848
 CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1853.4	1853.4
2.5°	1925.4	1912.6
5°	1819.9	1801.9
7.5°	1704.1	1680.9
10°	1598.5	1567.6
12.5°	1531.6	1493.0
15°	1505.9	1459.5
17.5°	1583.1	1539.3
20°	1701.5	1642.3
22.5°	1845.7	1773.6
25°	2095.3	2007.8
27.5°	2298.7	2208.6
30°	2424.8	2327.0
32.5°	2563.8	2435.1
35°	2708.0	2584.4
37.5°	2883.0	2744.0
40°	3063.2	2919.1
42.5°	3125.0	3032.3
45°	3184.2	3096.7
47.5°	3197.1	3125.0
50°	3209.9	3199.6
52.5°	3246.0	3243.4
55°	3400.4	3403.0
57.5°	3590.9	3606.4
60°	3766.0	3747.9
62.5°	3856.0	3763.4
65°	3794.3	3665.6
67.5°	3608.9	3469.9
70°	3202.2	3014.3
72.5°	2695.1	2530.4
75°	2077.3	1938.3
77.5°	1477.6	1361.7
80°	1039.9	924.1
82.5°	666.7	574.0
85°	301.2	262.6
87.5°	84.9	82.4
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P671848

CATALOG NUMBER: CCP-SA-1E-760-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)