

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P671851

Luminaire Tested: **CCP-SA-2B-760-U-SLR**

Issue Date: 04/16/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P671851  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-2B-760-U-SLR  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @450mA w/ SLR  
distribution lens  
Light Source: (32) 5700K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5862.5 lumens  
Efficiency: N/A  
Efficacy: 127.4 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G2


Input Watts (W): 46  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 8.3 fc  
 Type IV - Short - N/A

REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

## Luminous Intensity Polar Plot



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1206.2   | 0.0    | 1206.2 |
|                    | % Fixture | 20.6     | 0.0    | 20.6   |
| <b>Street Side</b> | Lumens    | 4656.2   | 0.0    | 4656.2 |
|                    | % Fixture | 79.4     | 0.0    | 79.4   |
| <b>Total</b>       | Lumens    | 5862.5   | 0.0    | 5862.5 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 145.5  | 2.5       |
| 10°-20°   | 307.1  | 5.2       |
| 20°-30°   | 449.4  | 7.7       |
| 30°-40°   | 633.1  | 10.8      |
| 40°-50°   | 869.9  | 14.8      |
| 50°-60°   | 1185.7 | 20.2      |
| 60°-70°   | 1297.7 | 22.1      |
| 70°-80°   | 749.4  | 12.8      |
| 80°-90°   | 224.7  | 3.8       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 5862.5 | 100.0     |
| 0°-180°   | 5862.5 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P671851


CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 602.1  | 10.3      |                         |      |         |
| FM   | (30°-60°)   | 2139.4 | 36.5      |                         |      |         |
| FH   | (60°-80°)   | 1723.9 | 29.4      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 190.8  | 3.3       |                         |      | G2/225  |
| BL   | (0°-30°)    | 299.9  | 5.1       | B1/500                  |      |         |
| BM   | (30°-60°)   | 549.3  | 9.4       | B1/1000                 |      |         |
| BH   | (60°-80°)   | 323.3  | 5.5       | B1/500                  |      | G1/500  |
| BVH  | (80°-90°)   | 33.8   | 0.6       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G2**

Type IV Short



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5°  | 25°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 |
| 2.5°   | 1931.9 | 1921.5 | 1913.7 | 1905.9 | 1895.5 | 1887.7 | 1877.3 | 1866.9 | 1853.9 | 1843.5 | 1830.5 |
| 5°     | 1820.1 | 1788.9 | 1757.7 | 1739.5 | 1718.7 | 1700.5 | 1679.7 | 1656.3 | 1632.9 | 1606.9 | 1583.5 |
| 7.5°   | 1697.9 | 1658.9 | 1619.9 | 1588.7 | 1554.9 | 1523.7 | 1489.9 | 1461.3 | 1432.7 | 1404.1 | 1375.5 |
| 10°    | 1583.5 | 1547.1 | 1510.7 | 1471.7 | 1430.1 | 1391.1 | 1349.5 | 1310.5 | 1271.5 | 1232.5 | 1193.5 |
| 12.5°  | 1508.1 | 1463.9 | 1422.3 | 1378.1 | 1336.5 | 1292.3 | 1248.1 | 1211.7 | 1175.3 | 1136.3 | 1099.9 |
| 15°    | 1474.3 | 1432.7 | 1393.7 | 1349.5 | 1305.3 | 1261.1 | 1216.9 | 1175.3 | 1136.3 | 1094.7 | 1053.1 |
| 17.5°  | 1554.9 | 1495.1 | 1435.3 | 1378.1 | 1320.9 | 1263.7 | 1206.5 | 1154.5 | 1102.5 | 1050.5 | 998.5  |
| 20°    | 1658.9 | 1583.5 | 1510.7 | 1440.5 | 1367.7 | 1297.5 | 1224.7 | 1151.9 | 1079.1 | 1006.3 | 933.5  |
| 22.5°  | 1791.5 | 1705.7 | 1622.5 | 1531.5 | 1437.9 | 1346.9 | 1253.3 | 1162.3 | 1071.3 | 977.7  | 886.7  |
| 25°    | 2028.1 | 1926.7 | 1825.3 | 1695.3 | 1562.7 | 1432.7 | 1300.1 | 1180.5 | 1063.5 | 943.9  | 824.3  |
| 27.5°  | 2230.9 | 2093.1 | 1957.9 | 1801.9 | 1645.9 | 1489.9 | 1333.9 | 1196.1 | 1060.9 | 923.1  | 785.3  |
| 30°    | 2350.6 | 2215.3 | 2080.1 | 1890.3 | 1703.1 | 1513.3 | 1323.5 | 1170.1 | 1019.3 | 865.9  | 712.4  |
| 32.5°  | 2459.8 | 2309.0 | 2158.1 | 1950.1 | 1739.5 | 1531.5 | 1320.9 | 1151.9 | 985.5  | 816.5  | 647.4  |
| 35°    | 2610.6 | 2444.2 | 2280.4 | 2038.5 | 1796.7 | 1554.9 | 1313.1 | 1138.9 | 962.1  | 787.9  | 611.0  |
| 37.5°  | 2771.8 | 2566.4 | 2363.6 | 2095.7 | 1827.9 | 1560.1 | 1292.3 | 1120.7 | 949.1  | 777.5  | 605.8  |
| 40°    | 2948.6 | 2699.0 | 2452.0 | 2155.5 | 1861.7 | 1565.3 | 1268.9 | 1097.3 | 925.7  | 751.4  | 579.8  |
| 42.5°  | 3063.0 | 2792.6 | 2522.2 | 2202.3 | 1885.1 | 1565.3 | 1245.5 | 1076.5 | 907.5  | 735.8  | 566.8  |
| 45°    | 3128.0 | 2865.4 | 2605.4 | 2259.5 | 1913.7 | 1567.9 | 1222.1 | 1055.7 | 889.3  | 720.2  | 553.8  |
| 47.5°  | 3156.6 | 2912.2 | 2667.8 | 2303.8 | 1942.3 | 1578.3 | 1214.3 | 1045.3 | 873.7  | 704.6  | 533.0  |
| 50°    | 3232.0 | 3016.2 | 2800.4 | 2410.4 | 2022.9 | 1632.9 | 1242.9 | 1060.9 | 881.5  | 699.4  | 517.4  |
| 52.5°  | 3276.2 | 3091.6 | 2907.0 | 2506.6 | 2106.1 | 1705.7 | 1305.3 | 1102.5 | 899.7  | 696.8  | 494.0  |
| 55°    | 3437.4 | 3260.6 | 3083.8 | 2657.4 | 2228.3 | 1801.9 | 1372.9 | 1149.3 | 925.7  | 699.4  | 475.8  |
| 57.5°  | 3642.8 | 3455.6 | 3271.0 | 2810.8 | 2350.6 | 1890.3 | 1430.1 | 1190.9 | 949.1  | 709.8  | 468.0  |
| 60°    | 3785.9 | 3603.8 | 3424.4 | 2935.6 | 2444.2 | 1955.3 | 1463.9 | 1214.3 | 964.7  | 712.4  | 462.8  |
| 62.5°  | 3801.5 | 3567.4 | 3336.0 | 2860.2 | 2384.4 | 1905.9 | 1430.1 | 1188.3 | 946.5  | 702.0  | 460.2  |
| 65°    | 3702.6 | 3429.6 | 3156.6 | 2701.6 | 2246.5 | 1791.5 | 1336.5 | 1115.5 | 894.5  | 670.8  | 449.8  |
| 67.5°  | 3505.0 | 3185.2 | 2865.4 | 2449.4 | 2033.3 | 1617.3 | 1201.3 | 1011.5 | 824.3  | 634.4  | 444.6  |
| 70°    | 3044.8 | 2764.0 | 2485.8 | 2124.3 | 1765.5 | 1404.1 | 1042.7 | 886.7  | 733.2  | 577.2  | 421.2  |
| 72.5°  | 2556.0 | 2293.4 | 2033.3 | 1739.5 | 1448.3 | 1154.5 | 860.7  | 743.6  | 626.6  | 507.0  | 390.0  |
| 75°    | 1957.9 | 1760.3 | 1565.3 | 1346.9 | 1128.5 | 907.5  | 689.0  | 603.2  | 517.4  | 431.6  | 345.8  |
| 77.5°  | 1375.5 | 1268.9 | 1164.9 | 1001.1 | 837.3  | 673.4  | 509.6  | 452.4  | 395.2  | 338.0  | 280.8  |
| 80°    | 933.5  | 873.7  | 816.5  | 699.4  | 582.4  | 462.8  | 345.8  | 309.4  | 270.4  | 234.0  | 195.0  |
| 82.5°  | 579.8  | 577.2  | 572.0  | 491.4  | 410.8  | 330.2  | 249.6  | 218.4  | 189.8  | 158.6  | 127.4  |
| 85°    | 265.2  | 309.4  | 351.0  | 306.8  | 262.6  | 218.4  | 174.2  | 153.4  | 132.6  | 109.2  | 88.4   |
| 87.5°  | 83.2   | 101.4  | 117.0  | 111.8  | 104.0  | 98.8   | 91.0   | 78.0   | 65.0   | 52.0   | 39.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 25° |
|--------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 27.5°  | 30°    | 32.5°  | 35°    | 37.5°  | 40°    | 42.5°  | 45°    | 47.5°  | 50°    | 52.5°  |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 |
| 2.5°   | 1820.1 | 1812.3 | 1801.9 | 1791.5 | 1778.5 | 1768.1 | 1755.1 | 1742.1 | 1739.5 | 1734.3 | 1731.7 |
| 5°     | 1567.9 | 1552.3 | 1534.1 | 1518.5 | 1502.9 | 1484.7 | 1469.1 | 1450.9 | 1437.9 | 1422.3 | 1409.3 |
| 7.5°   | 1346.9 | 1320.9 | 1292.3 | 1263.7 | 1237.7 | 1211.7 | 1183.1 | 1157.1 | 1144.1 | 1131.1 | 1118.1 |
| 10°    | 1170.1 | 1144.1 | 1120.7 | 1094.7 | 1076.5 | 1060.9 | 1042.7 | 1024.5 | 1008.9 | 993.3  | 977.7  |
| 12.5°  | 1081.7 | 1063.5 | 1045.3 | 1027.1 | 1006.3 | 988.1  | 967.3  | 946.5  | 928.3  | 912.7  | 894.5  |
| 15°    | 1027.1 | 1001.1 | 972.5  | 946.5  | 917.9  | 891.9  | 863.3  | 834.7  | 813.9  | 795.7  | 774.9  |
| 17.5°  | 962.1  | 923.1  | 886.7  | 847.7  | 816.5  | 785.3  | 751.4  | 720.2  | 696.8  | 670.8  | 647.4  |
| 20°    | 889.3  | 845.1  | 798.3  | 754.1  | 717.6  | 683.8  | 647.4  | 611.0  | 585.0  | 556.4  | 530.4  |
| 22.5°  | 826.9  | 769.7  | 709.8  | 650.0  | 611.0  | 572.0  | 530.4  | 491.4  | 468.0  | 442.0  | 418.6  |
| 25°    | 759.3  | 696.8  | 631.8  | 566.8  | 527.8  | 486.2  | 447.2  | 405.6  | 387.4  | 371.8  | 353.6  |
| 27.5°  | 722.8  | 660.4  | 595.4  | 533.0  | 496.6  | 457.6  | 421.2  | 382.2  | 369.2  | 353.6  | 340.6  |
| 30°    | 650.0  | 590.2  | 527.8  | 465.4  | 439.4  | 416.0  | 390.0  | 364.0  | 358.8  | 356.2  | 351.0  |
| 32.5°  | 585.0  | 522.6  | 460.2  | 397.8  | 374.4  | 351.0  | 327.6  | 304.2  | 301.6  | 296.4  | 293.8  |
| 35°    | 551.2  | 491.4  | 429.0  | 369.2  | 348.4  | 325.0  | 304.2  | 280.8  | 275.6  | 267.8  | 262.6  |
| 37.5°  | 543.4  | 481.0  | 416.0  | 353.6  | 332.8  | 312.0  | 288.6  | 267.8  | 262.6  | 257.4  | 252.2  |
| 40°    | 522.6  | 462.8  | 405.6  | 345.8  | 325.0  | 304.2  | 280.8  | 260.0  | 254.8  | 249.6  | 244.4  |
| 42.5°  | 507.0  | 449.8  | 390.0  | 330.2  | 312.0  | 293.8  | 273.0  | 254.8  | 249.6  | 244.4  | 236.6  |
| 45°    | 494.0  | 434.2  | 371.8  | 312.0  | 299.0  | 286.0  | 270.4  | 257.4  | 252.2  | 244.4  | 239.2  |
| 47.5°  | 473.2  | 416.0  | 356.2  | 296.4  | 283.4  | 273.0  | 260.0  | 247.0  | 241.8  | 236.6  | 231.4  |
| 50°    | 457.6  | 397.8  | 338.0  | 278.2  | 267.8  | 257.4  | 247.0  | 236.6  | 236.6  | 239.2  | 239.2  |
| 52.5°  | 436.8  | 379.6  | 322.4  | 265.2  | 254.8  | 244.4  | 234.0  | 223.6  | 226.2  | 228.8  | 231.4  |
| 55°    | 418.6  | 364.0  | 306.8  | 249.6  | 239.2  | 228.8  | 215.8  | 205.4  | 208.0  | 210.6  | 213.2  |
| 57.5°  | 410.8  | 353.6  | 296.4  | 239.2  | 228.8  | 215.8  | 205.4  | 192.4  | 192.4  | 192.4  | 192.4  |
| 60°    | 405.6  | 345.8  | 288.6  | 228.8  | 215.8  | 205.4  | 192.4  | 179.4  | 176.8  | 176.8  | 174.2  |
| 62.5°  | 403.0  | 343.2  | 286.0  | 226.2  | 210.6  | 197.6  | 182.0  | 166.4  | 163.8  | 161.2  | 158.6  |
| 65°    | 392.6  | 338.0  | 280.8  | 223.6  | 205.4  | 189.8  | 171.6  | 153.4  | 150.8  | 150.8  | 148.2  |
| 67.5°  | 390.0  | 332.8  | 278.2  | 221.0  | 202.8  | 182.0  | 163.8  | 143.0  | 140.4  | 137.8  | 135.2  |
| 70°    | 369.2  | 319.8  | 267.8  | 215.8  | 195.0  | 176.8  | 156.0  | 135.2  | 132.6  | 127.4  | 124.8  |
| 72.5°  | 343.2  | 299.0  | 252.2  | 205.4  | 184.6  | 163.8  | 143.0  | 122.2  | 119.6  | 117.0  | 111.8  |
| 75°    | 304.2  | 262.6  | 221.0  | 179.4  | 161.2  | 145.6  | 127.4  | 109.2  | 106.6  | 104.0  | 98.8   |
| 77.5°  | 249.6  | 215.8  | 184.6  | 150.8  | 137.8  | 124.8  | 111.8  | 98.8   | 96.2   | 93.6   | 88.4   |
| 80°    | 176.8  | 156.0  | 137.8  | 117.0  | 109.2  | 98.8   | 91.0   | 80.6   | 80.6   | 78.0   | 78.0   |
| 82.5°  | 117.0  | 106.6  | 96.2   | 85.8   | 80.6   | 75.4   | 70.2   | 65.0   | 65.0   | 62.4   | 62.4   |
| 85°    | 83.2   | 78.0   | 70.2   | 65.0   | 62.4   | 57.2   | 54.6   | 49.4   | 49.4   | 49.4   | 49.4   |
| 87.5°  | 39.0   | 39.0   | 36.4   | 36.4   | 33.8   | 33.8   | 31.2   | 28.6   | 28.6   | 28.6   | 28.6   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° | 47.5° | 50° | 52.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |

REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 55°    | 57.5°  | 60°    | 62.5°  | 65°    | 67.5°  | 70°    | 72.5°  | 75°    | 77.5°  | 80°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 |
| 2.5°   | 1726.5 | 1718.7 | 1710.9 | 1700.5 | 1692.7 | 1682.3 | 1669.3 | 1658.9 | 1645.9 | 1645.9 | 1643.3 |
| 5°     | 1393.7 | 1385.9 | 1378.1 | 1367.7 | 1359.9 | 1349.5 | 1341.7 | 1331.3 | 1320.9 | 1320.9 | 1318.3 |
| 7.5°   | 1105.1 | 1089.5 | 1073.9 | 1055.7 | 1040.1 | 1029.7 | 1019.3 | 1006.3 | 995.9  | 988.1  | 980.3  |
| 10°    | 962.1  | 946.5  | 928.3  | 912.7  | 894.5  | 881.5  | 868.5  | 852.9  | 839.9  | 829.5  | 819.1  |
| 12.5°  | 876.3  | 858.1  | 839.9  | 821.7  | 803.5  | 785.3  | 769.7  | 751.4  | 733.2  | 720.2  | 707.2  |
| 15°    | 754.1  | 735.8  | 717.6  | 699.4  | 681.2  | 660.4  | 639.6  | 616.2  | 595.4  | 585.0  | 577.2  |
| 17.5°  | 621.4  | 603.2  | 582.4  | 564.2  | 543.4  | 527.8  | 512.2  | 496.6  | 481.0  | 470.6  | 462.8  |
| 20°    | 501.8  | 481.0  | 460.2  | 439.4  | 418.6  | 408.2  | 397.8  | 387.4  | 377.0  | 369.2  | 364.0  |
| 22.5°  | 392.6  | 379.6  | 369.2  | 356.2  | 343.2  | 335.4  | 330.2  | 322.4  | 314.6  | 314.6  | 314.6  |
| 25°    | 335.4  | 327.6  | 322.4  | 314.6  | 306.8  | 304.2  | 301.6  | 296.4  | 293.8  | 291.2  | 291.2  |
| 27.5°  | 325.0  | 317.2  | 309.4  | 301.6  | 293.8  | 291.2  | 288.6  | 283.4  | 280.8  | 280.8  | 280.8  |
| 30°    | 345.8  | 343.2  | 340.6  | 338.0  | 335.4  | 330.2  | 322.4  | 317.2  | 309.4  | 304.2  | 299.0  |
| 32.5°  | 288.6  | 286.0  | 286.0  | 283.4  | 280.8  | 286.0  | 288.6  | 293.8  | 296.4  | 299.0  | 301.6  |
| 35°    | 254.8  | 249.6  | 244.4  | 239.2  | 234.0  | 231.4  | 228.8  | 226.2  | 223.6  | 223.6  | 221.0  |
| 37.5°  | 247.0  | 241.8  | 236.6  | 231.4  | 226.2  | 223.6  | 221.0  | 218.4  | 215.8  | 215.8  | 213.2  |
| 40°    | 239.2  | 234.0  | 231.4  | 226.2  | 221.0  | 218.4  | 215.8  | 210.6  | 208.0  | 205.4  | 205.4  |
| 42.5°  | 231.4  | 228.8  | 223.6  | 221.0  | 215.8  | 213.2  | 210.6  | 205.4  | 202.8  | 200.2  | 197.6  |
| 45°    | 231.4  | 226.2  | 221.0  | 215.8  | 210.6  | 208.0  | 202.8  | 200.2  | 195.0  | 195.0  | 192.4  |
| 47.5°  | 226.2  | 221.0  | 215.8  | 210.6  | 205.4  | 202.8  | 197.6  | 195.0  | 189.8  | 187.2  | 184.6  |
| 50°    | 239.2  | 231.4  | 221.0  | 213.2  | 202.8  | 200.2  | 195.0  | 192.4  | 187.2  | 184.6  | 182.0  |
| 52.5°  | 234.0  | 226.2  | 215.8  | 208.0  | 197.6  | 192.4  | 189.8  | 184.6  | 179.4  | 176.8  | 174.2  |
| 55°    | 215.8  | 208.0  | 202.8  | 195.0  | 187.2  | 182.0  | 176.8  | 171.6  | 166.4  | 163.8  | 163.8  |
| 57.5°  | 192.4  | 189.8  | 187.2  | 184.6  | 182.0  | 176.8  | 171.6  | 163.8  | 158.6  | 156.0  | 153.4  |
| 60°    | 171.6  | 174.2  | 176.8  | 179.4  | 182.0  | 174.2  | 166.4  | 158.6  | 150.8  | 148.2  | 145.6  |
| 62.5°  | 156.0  | 161.2  | 166.4  | 169.0  | 174.2  | 166.4  | 158.6  | 150.8  | 143.0  | 140.4  | 137.8  |
| 65°    | 145.6  | 148.2  | 148.2  | 150.8  | 150.8  | 145.6  | 143.0  | 137.8  | 132.6  | 130.0  | 130.0  |
| 67.5°  | 132.6  | 132.6  | 132.6  | 130.0  | 130.0  | 127.4  | 127.4  | 124.8  | 122.2  | 119.6  | 119.6  |
| 70°    | 119.6  | 119.6  | 119.6  | 117.0  | 117.0  | 114.4  | 114.4  | 111.8  | 109.2  | 109.2  | 106.6  |
| 72.5°  | 109.2  | 109.2  | 106.6  | 106.6  | 104.0  | 104.0  | 104.0  | 101.4  | 101.4  | 98.8   | 98.8   |
| 75°    | 96.2   | 96.2   | 93.6   | 93.6   | 91.0   | 91.0   | 91.0   | 88.4   | 88.4   | 88.4   | 85.8   |
| 77.5°  | 85.8   | 85.8   | 83.2   | 83.2   | 80.6   | 80.6   | 80.6   | 78.0   | 78.0   | 75.4   | 75.4   |
| 80°    | 75.4   | 75.4   | 72.8   | 72.8   | 70.2   | 70.2   | 67.6   | 67.6   | 65.0   | 65.0   | 62.4   |
| 82.5°  | 59.8   | 59.8   | 59.8   | 59.8   | 59.8   | 57.2   | 57.2   | 54.6   | 52.0   | 52.0   | 49.4   |
| 85°    | 49.4   | 49.4   | 49.4   | 46.8   | 46.8   | 46.8   | 44.2   | 44.2   | 41.6   | 39.0   | 39.0   |
| 87.5°  | 28.6   | 28.6   | 28.6   | 26.0   | 26.0   | 26.0   | 26.0   | 26.0   | 26.0   | 26.0   | 23.4   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° | 75° | 77.5° | 80° |
|--------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 82.5°  | 85°    | 87.5°  | 90°    | 92.5°  | 95°    | 97.5°  | 100°   | 102.5° | 105°   | 107.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 |
| 2.5°   | 1643.3 | 1640.7 | 1630.3 | 1619.9 | 1630.3 | 1640.7 | 1640.7 | 1640.7 | 1638.1 | 1638.1 | 1638.1 |
| 5°     | 1318.3 | 1315.7 | 1310.5 | 1305.3 | 1305.3 | 1302.7 | 1307.9 | 1313.1 | 1318.3 | 1323.5 | 1328.7 |
| 7.5°   | 969.9  | 962.1  | 954.3  | 946.5  | 951.7  | 954.3  | 962.1  | 967.3  | 975.1  | 980.3  | 993.3  |
| 10°    | 808.7  | 798.3  | 790.5  | 782.7  | 777.5  | 772.3  | 767.1  | 764.5  | 759.3  | 754.1  | 759.3  |
| 12.5°  | 691.6  | 678.6  | 665.6  | 650.0  | 647.4  | 644.8  | 639.6  | 634.4  | 629.2  | 624.0  | 621.4  |
| 15°    | 566.8  | 556.4  | 551.2  | 543.4  | 533.0  | 522.6  | 517.4  | 514.8  | 509.6  | 504.4  | 501.8  |
| 17.5°  | 452.4  | 442.0  | 434.2  | 426.4  | 423.8  | 418.6  | 418.6  | 418.6  | 418.6  | 418.6  | 418.6  |
| 20°    | 356.2  | 348.4  | 348.4  | 345.8  | 345.8  | 343.2  | 345.8  | 348.4  | 348.4  | 351.0  | 353.6  |
| 22.5°  | 312.0  | 312.0  | 309.4  | 306.8  | 309.4  | 309.4  | 312.0  | 314.6  | 317.2  | 319.8  | 322.4  |
| 25°    | 288.6  | 286.0  | 288.6  | 291.2  | 291.2  | 291.2  | 293.8  | 293.8  | 296.4  | 296.4  | 296.4  |
| 27.5°  | 278.2  | 278.2  | 280.8  | 280.8  | 283.4  | 283.4  | 283.4  | 280.8  | 280.8  | 278.2  | 278.2  |
| 30°    | 293.8  | 288.6  | 288.6  | 288.6  | 286.0  | 283.4  | 280.8  | 280.8  | 278.2  | 275.6  | 273.0  |
| 32.5°  | 304.2  | 306.8  | 304.2  | 299.0  | 296.4  | 291.2  | 288.6  | 283.4  | 280.8  | 275.6  | 270.4  |
| 35°    | 221.0  | 218.4  | 223.6  | 226.2  | 228.8  | 231.4  | 234.0  | 236.6  | 236.6  | 239.2  | 239.2  |
| 37.5°  | 213.2  | 210.6  | 210.6  | 208.0  | 208.0  | 208.0  | 208.0  | 208.0  | 205.4  | 205.4  | 208.0  |
| 40°    | 202.8  | 200.2  | 200.2  | 197.6  | 197.6  | 195.0  | 195.0  | 195.0  | 195.0  | 195.0  | 195.0  |
| 42.5°  | 195.0  | 192.4  | 192.4  | 192.4  | 192.4  | 189.8  | 189.8  | 187.2  | 187.2  | 184.6  | 184.6  |
| 45°    | 192.4  | 189.8  | 187.2  | 184.6  | 184.6  | 182.0  | 182.0  | 182.0  | 179.4  | 179.4  | 179.4  |
| 47.5°  | 182.0  | 179.4  | 179.4  | 176.8  | 176.8  | 174.2  | 174.2  | 174.2  | 171.6  | 171.6  | 171.6  |
| 50°    | 176.8  | 174.2  | 174.2  | 171.6  | 171.6  | 169.0  | 169.0  | 169.0  | 166.4  | 166.4  | 166.4  |
| 52.5°  | 169.0  | 166.4  | 166.4  | 166.4  | 163.8  | 161.2  | 161.2  | 161.2  | 158.6  | 158.6  | 158.6  |
| 55°    | 161.2  | 158.6  | 158.6  | 158.6  | 156.0  | 153.4  | 153.4  | 153.4  | 150.8  | 150.8  | 150.8  |
| 57.5°  | 150.8  | 148.2  | 148.2  | 145.6  | 145.6  | 145.6  | 145.6  | 145.6  | 143.0  | 143.0  | 143.0  |
| 60°    | 143.0  | 140.4  | 140.4  | 137.8  | 137.8  | 135.2  | 135.2  | 135.2  | 135.2  | 135.2  | 135.2  |
| 62.5°  | 135.2  | 132.6  | 130.0  | 127.4  | 130.0  | 130.0  | 130.0  | 130.0  | 127.4  | 127.4  | 127.4  |
| 65°    | 127.4  | 124.8  | 122.2  | 119.6  | 119.6  | 119.6  | 119.6  | 119.6  | 119.6  | 119.6  | 119.6  |
| 67.5°  | 117.0  | 114.4  | 111.8  | 109.2  | 111.8  | 111.8  | 111.8  | 111.8  | 111.8  | 111.8  | 111.8  |
| 70°    | 106.6  | 104.0  | 104.0  | 101.4  | 101.4  | 98.8   | 98.8   | 101.4  | 101.4  | 101.4  | 101.4  |
| 72.5°  | 96.2   | 93.6   | 93.6   | 91.0   | 91.0   | 91.0   | 91.0   | 91.0   | 91.0   | 91.0   | 91.0   |
| 75°    | 85.8   | 83.2   | 83.2   | 80.6   | 80.6   | 80.6   | 80.6   | 80.6   | 80.6   | 80.6   | 80.6   |
| 77.5°  | 72.8   | 70.2   | 70.2   | 70.2   | 70.2   | 70.2   | 70.2   | 72.8   | 72.8   | 72.8   | 72.8   |
| 80°    | 62.4   | 59.8   | 59.8   | 59.8   | 59.8   | 59.8   | 59.8   | 59.8   | 59.8   | 59.8   | 59.8   |
| 82.5°  | 49.4   | 46.8   | 46.8   | 46.8   | 46.8   | 46.8   | 46.8   | 46.8   | 46.8   | 46.8   | 46.8   |
| 85°    | 36.4   | 33.8   | 33.8   | 33.8   | 36.4   | 36.4   | 36.4   | 36.4   | 36.4   | 36.4   | 36.4   |
| 87.5°  | 23.4   | 20.8   | 20.8   | 20.8   | 23.4   | 23.4   | 23.4   | 23.4   | 20.8   | 20.8   | 20.8   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° | 92.5° | 95° | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|------|--------|------|--------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 110°   | 112.5° | 115°   | 117.5° | 120°   | 122.5° | 125°   | 127.5° | 130°   | 132.5° | 135°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 |
| 2.5°   | 1638.1 | 1638.1 | 1638.1 | 1635.5 | 1632.9 | 1630.3 | 1627.7 | 1635.5 | 1640.7 | 1648.5 | 1653.7 |
| 5°     | 1331.3 | 1336.5 | 1339.1 | 1346.9 | 1354.7 | 1362.5 | 1370.3 | 1375.5 | 1380.7 | 1383.3 | 1388.5 |
| 7.5°   | 1003.7 | 1016.7 | 1027.1 | 1037.5 | 1047.9 | 1055.7 | 1066.1 | 1073.9 | 1081.7 | 1089.5 | 1097.3 |
| 10°    | 761.9  | 767.1  | 769.7  | 780.1  | 787.9  | 798.3  | 806.1  | 813.9  | 821.7  | 826.9  | 834.7  |
| 12.5°  | 618.8  | 613.6  | 611.0  | 611.0  | 611.0  | 611.0  | 611.0  | 616.2  | 621.4  | 626.6  | 631.8  |
| 15°    | 499.2  | 496.6  | 494.0  | 491.4  | 488.8  | 483.6  | 481.0  | 486.2  | 491.4  | 496.6  | 501.8  |
| 17.5°  | 418.6  | 418.6  | 418.6  | 416.0  | 413.4  | 410.8  | 408.2  | 410.8  | 413.4  | 413.4  | 416.0  |
| 20°    | 358.8  | 361.4  | 364.0  | 366.6  | 366.6  | 369.2  | 369.2  | 371.8  | 374.4  | 374.4  | 377.0  |
| 22.5°  | 322.4  | 325.0  | 325.0  | 325.0  | 327.6  | 327.6  | 327.6  | 330.2  | 332.8  | 335.4  | 338.0  |
| 25°    | 293.8  | 293.8  | 291.2  | 291.2  | 293.8  | 293.8  | 293.8  | 293.8  | 296.4  | 296.4  | 296.4  |
| 27.5°  | 278.2  | 275.6  | 275.6  | 275.6  | 275.6  | 273.0  | 273.0  | 273.0  | 273.0  | 273.0  | 273.0  |
| 30°    | 270.4  | 267.8  | 265.2  | 262.6  | 262.6  | 260.0  | 257.4  | 257.4  | 257.4  | 257.4  | 257.4  |
| 32.5°  | 267.8  | 262.6  | 257.4  | 254.8  | 254.8  | 252.2  | 249.6  | 247.0  | 247.0  | 244.4  | 241.8  |
| 35°    | 239.2  | 236.6  | 236.6  | 234.0  | 231.4  | 228.8  | 226.2  | 226.2  | 226.2  | 223.6  | 223.6  |
| 37.5°  | 208.0  | 210.6  | 210.6  | 210.6  | 213.2  | 213.2  | 213.2  | 213.2  | 215.8  | 215.8  | 215.8  |
| 40°    | 195.0  | 195.0  | 195.0  | 197.6  | 200.2  | 200.2  | 202.8  | 202.8  | 205.4  | 205.4  | 205.4  |
| 42.5°  | 184.6  | 182.0  | 182.0  | 184.6  | 184.6  | 187.2  | 187.2  | 189.8  | 192.4  | 192.4  | 195.0  |
| 45°    | 179.4  | 176.8  | 176.8  | 176.8  | 176.8  | 174.2  | 174.2  | 176.8  | 179.4  | 182.0  | 184.6  |
| 47.5°  | 169.0  | 169.0  | 166.4  | 166.4  | 166.4  | 166.4  | 166.4  | 166.4  | 169.0  | 169.0  | 169.0  |
| 50°    | 163.8  | 163.8  | 161.2  | 161.2  | 161.2  | 161.2  | 161.2  | 161.2  | 161.2  | 161.2  | 161.2  |
| 52.5°  | 158.6  | 156.0  | 156.0  | 156.0  | 156.0  | 153.4  | 153.4  | 153.4  | 153.4  | 153.4  | 153.4  |
| 55°    | 150.8  | 148.2  | 148.2  | 148.2  | 148.2  | 148.2  | 148.2  | 148.2  | 150.8  | 150.8  | 150.8  |
| 57.5°  | 143.0  | 140.4  | 140.4  | 140.4  | 143.0  | 143.0  | 143.0  | 143.0  | 145.6  | 145.6  | 145.6  |
| 60°    | 135.2  | 135.2  | 135.2  | 135.2  | 135.2  | 135.2  | 135.2  | 137.8  | 137.8  | 140.4  | 140.4  |
| 62.5°  | 127.4  | 127.4  | 127.4  | 127.4  | 130.0  | 130.0  | 130.0  | 130.0  | 132.6  | 132.6  | 132.6  |
| 65°    | 119.6  | 119.6  | 119.6  | 119.6  | 122.2  | 122.2  | 122.2  | 122.2  | 122.2  | 122.2  | 122.2  |
| 67.5°  | 111.8  | 111.8  | 111.8  | 111.8  | 111.8  | 111.8  | 111.8  | 114.4  | 114.4  | 117.0  | 117.0  |
| 70°    | 101.4  | 98.8   | 98.8   | 101.4  | 101.4  | 104.0  | 104.0  | 106.6  | 106.6  | 109.2  | 109.2  |
| 72.5°  | 91.0   | 91.0   | 91.0   | 91.0   | 91.0   | 91.0   | 91.0   | 93.6   | 96.2   | 96.2   | 98.8   |
| 75°    | 80.6   | 80.6   | 80.6   | 80.6   | 83.2   | 83.2   | 83.2   | 85.8   | 85.8   | 88.4   | 88.4   |
| 77.5°  | 72.8   | 70.2   | 70.2   | 70.2   | 72.8   | 72.8   | 72.8   | 75.4   | 75.4   | 78.0   | 78.0   |
| 80°    | 59.8   | 59.8   | 59.8   | 59.8   | 62.4   | 62.4   | 62.4   | 62.4   | 65.0   | 65.0   | 65.0   |
| 82.5°  | 49.4   | 49.4   | 49.4   | 49.4   | 49.4   | 49.4   | 49.4   | 49.4   | 52.0   | 52.0   | 52.0   |
| 85°    | 36.4   | 36.4   | 36.4   | 36.4   | 39.0   | 39.0   | 39.0   | 39.0   | 39.0   | 39.0   | 39.0   |
| 87.5°  | 23.4   | 23.4   | 23.4   | 23.4   | 23.4   | 23.4   | 23.4   | 23.4   | 26.0   | 26.0   | 26.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140°   | 142.5° | 145°   | 147.5° | 150°   | 152.5° | 155°   | 157.5° | 160°   | 162.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 |
| 2.5°   | 1653.7 | 1653.7 | 1653.7 | 1653.7 | 1658.9 | 1661.5 | 1666.7 | 1669.3 | 1666.7 | 1664.1 | 1658.9 |
| 5°     | 1391.1 | 1393.7 | 1393.7 | 1396.3 | 1396.3 | 1396.3 | 1396.3 | 1396.3 | 1401.5 | 1406.7 | 1411.9 |
| 7.5°   | 1099.9 | 1102.5 | 1105.1 | 1107.7 | 1107.7 | 1107.7 | 1105.1 | 1105.1 | 1107.7 | 1107.7 | 1110.3 |
| 10°    | 842.5  | 852.9  | 860.7  | 868.5  | 863.3  | 855.5  | 850.3  | 842.5  | 842.5  | 842.5  | 839.9  |
| 12.5°  | 637.0  | 639.6  | 644.8  | 647.4  | 644.8  | 644.8  | 642.2  | 639.6  | 642.2  | 647.4  | 650.0  |
| 15°    | 504.4  | 504.4  | 507.0  | 507.0  | 509.6  | 512.2  | 512.2  | 514.8  | 520.0  | 522.6  | 527.8  |
| 17.5°  | 418.6  | 421.2  | 421.2  | 423.8  | 423.8  | 426.4  | 426.4  | 426.4  | 431.6  | 436.8  | 444.6  |
| 20°    | 377.0  | 377.0  | 377.0  | 377.0  | 377.0  | 374.4  | 374.4  | 371.8  | 374.4  | 379.6  | 382.2  |
| 22.5°  | 338.0  | 340.6  | 340.6  | 340.6  | 338.0  | 335.4  | 330.2  | 327.6  | 327.6  | 330.2  | 330.2  |
| 25°    | 296.4  | 293.8  | 293.8  | 291.2  | 291.2  | 293.8  | 293.8  | 293.8  | 296.4  | 296.4  | 299.0  |
| 27.5°  | 273.0  | 270.4  | 270.4  | 267.8  | 267.8  | 270.4  | 270.4  | 270.4  | 270.4  | 270.4  | 270.4  |
| 30°    | 254.8  | 254.8  | 252.2  | 249.6  | 252.2  | 252.2  | 254.8  | 254.8  | 257.4  | 257.4  | 260.0  |
| 32.5°  | 241.8  | 239.2  | 239.2  | 236.6  | 239.2  | 239.2  | 241.8  | 241.8  | 244.4  | 247.0  | 247.0  |
| 35°    | 223.6  | 223.6  | 223.6  | 223.6  | 223.6  | 223.6  | 221.0  | 221.0  | 221.0  | 221.0  | 221.0  |
| 37.5°  | 213.2  | 213.2  | 210.6  | 208.0  | 208.0  | 208.0  | 208.0  | 208.0  | 205.4  | 202.8  | 200.2  |
| 40°    | 205.4  | 202.8  | 202.8  | 200.2  | 197.6  | 197.6  | 195.0  | 192.4  | 192.4  | 189.8  | 189.8  |
| 42.5°  | 195.0  | 192.4  | 192.4  | 189.8  | 187.2  | 187.2  | 184.6  | 182.0  | 182.0  | 182.0  | 179.4  |
| 45°    | 182.0  | 182.0  | 179.4  | 176.8  | 176.8  | 176.8  | 174.2  | 174.2  | 174.2  | 174.2  | 171.6  |
| 47.5°  | 169.0  | 169.0  | 166.4  | 166.4  | 166.4  | 166.4  | 163.8  | 163.8  | 163.8  | 163.8  | 163.8  |
| 50°    | 161.2  | 161.2  | 161.2  | 161.2  | 161.2  | 161.2  | 158.6  | 158.6  | 158.6  | 158.6  | 158.6  |
| 52.5°  | 153.4  | 153.4  | 153.4  | 153.4  | 153.4  | 153.4  | 153.4  | 153.4  | 153.4  | 153.4  | 153.4  |
| 55°    | 150.8  | 150.8  | 150.8  | 150.8  | 150.8  | 150.8  | 148.2  | 148.2  | 148.2  | 150.8  | 150.8  |
| 57.5°  | 145.6  | 145.6  | 143.0  | 143.0  | 143.0  | 143.0  | 143.0  | 143.0  | 143.0  | 143.0  | 143.0  |
| 60°    | 140.4  | 140.4  | 140.4  | 140.4  | 140.4  | 140.4  | 140.4  | 140.4  | 140.4  | 140.4  | 140.4  |
| 62.5°  | 132.6  | 132.6  | 132.6  | 132.6  | 132.6  | 135.2  | 135.2  | 135.2  | 135.2  | 135.2  | 132.6  |
| 65°    | 122.2  | 124.8  | 124.8  | 124.8  | 124.8  | 124.8  | 124.8  | 124.8  | 124.8  | 124.8  | 124.8  |
| 67.5°  | 117.0  | 117.0  | 117.0  | 117.0  | 117.0  | 117.0  | 117.0  | 117.0  | 117.0  | 117.0  | 117.0  |
| 70°    | 109.2  | 109.2  | 106.6  | 106.6  | 106.6  | 109.2  | 109.2  | 109.2  | 109.2  | 109.2  | 109.2  |
| 72.5°  | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 101.4  | 101.4  |
| 75°    | 88.4   | 88.4   | 88.4   | 88.4   | 88.4   | 88.4   | 88.4   | 88.4   | 88.4   | 88.4   | 88.4   |
| 77.5°  | 78.0   | 78.0   | 75.4   | 75.4   | 75.4   | 78.0   | 78.0   | 78.0   | 78.0   | 80.6   | 80.6   |
| 80°    | 65.0   | 65.0   | 65.0   | 65.0   | 65.0   | 65.0   | 65.0   | 65.0   | 65.0   | 67.6   | 67.6   |
| 82.5°  | 52.0   | 52.0   | 52.0   | 52.0   | 52.0   | 52.0   | 52.0   | 52.0   | 52.0   | 54.6   | 54.6   |
| 85°    | 39.0   | 41.6   | 41.6   | 41.6   | 41.6   | 41.6   | 41.6   | 41.6   | 41.6   | 44.2   | 44.2   |
| 87.5°  | 26.0   | 26.0   | 26.0   | 26.0   | 26.0   | 26.0   | 23.4   | 23.4   | 23.4   | 23.4   | 20.8   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 165°   | 167.5° | 170°   | 172.5° | 175°   | 177.5° | 180°   | 182.5° | 185°   | 187.5° | 190°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 |
| 2.5°   | 1656.3 | 1658.9 | 1661.5 | 1661.5 | 1664.1 | 1666.7 | 1666.7 | 1677.1 | 1687.5 | 1692.7 | 1697.9 |
| 5°     | 1417.1 | 1414.5 | 1414.5 | 1411.9 | 1409.3 | 1417.1 | 1424.9 | 1440.5 | 1456.1 | 1458.7 | 1463.9 |
| 7.5°   | 1110.3 | 1112.9 | 1115.5 | 1115.5 | 1118.1 | 1110.3 | 1099.9 | 1102.5 | 1105.1 | 1118.1 | 1128.5 |
| 10°    | 839.9  | 842.5  | 845.1  | 845.1  | 847.7  | 845.1  | 839.9  | 847.7  | 855.5  | 865.9  | 878.9  |
| 12.5°  | 652.6  | 660.4  | 668.2  | 673.4  | 681.2  | 686.4  | 689.0  | 699.4  | 707.2  | 720.2  | 733.2  |
| 15°    | 533.0  | 538.2  | 543.4  | 548.6  | 553.8  | 559.0  | 564.2  | 574.6  | 585.0  | 600.6  | 616.2  |
| 17.5°  | 449.8  | 449.8  | 452.4  | 452.4  | 452.4  | 457.6  | 462.8  | 468.0  | 470.6  | 486.2  | 501.8  |
| 20°    | 384.8  | 382.2  | 379.6  | 377.0  | 374.4  | 379.6  | 382.2  | 384.8  | 387.4  | 397.8  | 405.6  |
| 22.5°  | 330.2  | 330.2  | 332.8  | 332.8  | 332.8  | 330.2  | 325.0  | 327.6  | 327.6  | 332.8  | 340.6  |
| 25°    | 299.0  | 299.0  | 299.0  | 296.4  | 296.4  | 299.0  | 301.6  | 301.6  | 299.0  | 301.6  | 304.2  |
| 27.5°  | 270.4  | 273.0  | 273.0  | 275.6  | 275.6  | 278.2  | 278.2  | 278.2  | 278.2  | 280.8  | 283.4  |
| 30°    | 260.0  | 260.0  | 262.6  | 262.6  | 262.6  | 265.2  | 267.8  | 267.8  | 267.8  | 270.4  | 275.6  |
| 32.5°  | 249.6  | 252.2  | 254.8  | 257.4  | 260.0  | 262.6  | 262.6  | 265.2  | 265.2  | 267.8  | 270.4  |
| 35°    | 221.0  | 218.4  | 218.4  | 215.8  | 213.2  | 213.2  | 213.2  | 213.2  | 210.6  | 213.2  | 213.2  |
| 37.5°  | 197.6  | 197.6  | 197.6  | 195.0  | 195.0  | 197.6  | 197.6  | 197.6  | 197.6  | 200.2  | 200.2  |
| 40°    | 187.2  | 187.2  | 187.2  | 187.2  | 187.2  | 187.2  | 187.2  | 189.8  | 189.8  | 192.4  | 195.0  |
| 42.5°  | 179.4  | 179.4  | 179.4  | 179.4  | 179.4  | 182.0  | 182.0  | 182.0  | 182.0  | 184.6  | 184.6  |
| 45°    | 171.6  | 171.6  | 171.6  | 171.6  | 171.6  | 171.6  | 171.6  | 174.2  | 174.2  | 176.8  | 179.4  |
| 47.5°  | 163.8  | 163.8  | 163.8  | 163.8  | 163.8  | 166.4  | 169.0  | 169.0  | 169.0  | 171.6  | 171.6  |
| 50°    | 158.6  | 158.6  | 158.6  | 158.6  | 158.6  | 161.2  | 161.2  | 163.8  | 163.8  | 166.4  | 169.0  |
| 52.5°  | 153.4  | 153.4  | 153.4  | 153.4  | 153.4  | 156.0  | 156.0  | 158.6  | 158.6  | 161.2  | 163.8  |
| 55°    | 150.8  | 150.8  | 150.8  | 148.2  | 148.2  | 150.8  | 150.8  | 153.4  | 153.4  | 156.0  | 156.0  |
| 57.5°  | 143.0  | 143.0  | 143.0  | 143.0  | 143.0  | 143.0  | 143.0  | 145.6  | 145.6  | 148.2  | 150.8  |
| 60°    | 140.4  | 140.4  | 137.8  | 137.8  | 135.2  | 137.8  | 137.8  | 140.4  | 140.4  | 143.0  | 143.0  |
| 62.5°  | 132.6  | 132.6  | 132.6  | 130.0  | 130.0  | 132.6  | 132.6  | 132.6  | 132.6  | 135.2  | 137.8  |
| 65°    | 124.8  | 124.8  | 124.8  | 122.2  | 122.2  | 124.8  | 124.8  | 124.8  | 124.8  | 127.4  | 130.0  |
| 67.5°  | 117.0  | 117.0  | 117.0  | 114.4  | 114.4  | 114.4  | 114.4  | 117.0  | 117.0  | 119.6  | 122.2  |
| 70°    | 109.2  | 109.2  | 109.2  | 106.6  | 106.6  | 106.6  | 104.0  | 106.6  | 109.2  | 111.8  | 111.8  |
| 72.5°  | 101.4  | 101.4  | 101.4  | 98.8   | 98.8   | 98.8   | 96.2   | 98.8   | 98.8   | 101.4  | 101.4  |
| 75°    | 88.4   | 88.4   | 88.4   | 88.4   | 88.4   | 88.4   | 85.8   | 85.8   | 85.8   | 88.4   | 88.4   |
| 77.5°  | 80.6   | 80.6   | 80.6   | 78.0   | 78.0   | 78.0   | 75.4   | 75.4   | 75.4   | 78.0   | 78.0   |
| 80°    | 67.6   | 67.6   | 67.6   | 65.0   | 65.0   | 65.0   | 62.4   | 62.4   | 62.4   | 65.0   | 65.0   |
| 82.5°  | 54.6   | 54.6   | 54.6   | 52.0   | 52.0   | 52.0   | 49.4   | 49.4   | 49.4   | 52.0   | 52.0   |
| 85°    | 44.2   | 44.2   | 44.2   | 44.2   | 44.2   | 44.2   | 41.6   | 41.6   | 41.6   | 44.2   | 46.8   |
| 87.5°  | 20.8   | 20.8   | 23.4   | 23.4   | 23.4   | 23.4   | 20.8   | 20.8   | 18.2   | 18.2   | 20.8   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° | 190° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195°   | 197.5° | 200°   | 202.5° | 205°   | 207.5° | 210°   | 212.5° | 215°   | 217.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 |
| 2.5°   | 1703.1 | 1708.3 | 1721.3 | 1731.7 | 1744.7 | 1755.1 | 1762.9 | 1773.3 | 1781.1 | 1788.9 | 1794.1 |
| 5°     | 1466.5 | 1469.1 | 1482.1 | 1495.1 | 1505.5 | 1518.5 | 1536.7 | 1554.9 | 1573.1 | 1591.3 | 1604.3 |
| 7.5°   | 1141.5 | 1151.9 | 1167.5 | 1185.7 | 1201.3 | 1216.9 | 1235.1 | 1255.9 | 1274.1 | 1292.3 | 1310.5 |
| 10°    | 889.3  | 899.7  | 915.3  | 930.9  | 943.9  | 959.5  | 980.3  | 1001.1 | 1021.9 | 1042.7 | 1063.5 |
| 12.5°  | 746.2  | 759.3  | 777.5  | 795.7  | 811.3  | 829.5  | 855.5  | 878.9  | 904.9  | 928.3  | 954.3  |
| 15°    | 629.2  | 644.8  | 668.2  | 694.2  | 717.6  | 741.0  | 767.1  | 793.1  | 816.5  | 842.5  | 868.5  |
| 17.5°  | 517.4  | 533.0  | 553.8  | 577.2  | 598.0  | 618.8  | 650.0  | 678.6  | 709.8  | 738.4  | 767.1  |
| 20°    | 416.0  | 423.8  | 444.6  | 465.4  | 486.2  | 507.0  | 530.4  | 553.8  | 577.2  | 600.6  | 637.0  |
| 22.5°  | 345.8  | 351.0  | 361.4  | 369.2  | 379.6  | 387.4  | 410.8  | 434.2  | 455.0  | 478.4  | 512.2  |
| 25°    | 304.2  | 306.8  | 314.6  | 319.8  | 327.6  | 332.8  | 348.4  | 361.4  | 377.0  | 390.0  | 421.2  |
| 27.5°  | 283.4  | 286.0  | 288.6  | 291.2  | 293.8  | 296.4  | 306.8  | 317.2  | 325.0  | 335.4  | 364.0  |
| 30°    | 278.2  | 280.8  | 288.6  | 293.8  | 301.6  | 306.8  | 312.0  | 317.2  | 322.4  | 327.6  | 345.8  |
| 32.5°  | 273.0  | 275.6  | 275.6  | 273.0  | 273.0  | 270.4  | 275.6  | 278.2  | 283.4  | 286.0  | 301.6  |
| 35°    | 215.8  | 215.8  | 218.4  | 221.0  | 223.6  | 226.2  | 234.0  | 239.2  | 247.0  | 252.2  | 265.2  |
| 37.5°  | 202.8  | 202.8  | 205.4  | 210.6  | 213.2  | 215.8  | 221.0  | 226.2  | 231.4  | 236.6  | 249.6  |
| 40°    | 195.0  | 197.6  | 200.2  | 202.8  | 205.4  | 208.0  | 213.2  | 215.8  | 221.0  | 223.6  | 234.0  |
| 42.5°  | 187.2  | 187.2  | 189.8  | 195.0  | 197.6  | 200.2  | 205.4  | 208.0  | 213.2  | 215.8  | 226.2  |
| 45°    | 182.0  | 184.6  | 187.2  | 189.8  | 189.8  | 192.4  | 197.6  | 202.8  | 205.4  | 210.6  | 221.0  |
| 47.5°  | 174.2  | 174.2  | 179.4  | 182.0  | 187.2  | 189.8  | 195.0  | 197.6  | 202.8  | 205.4  | 215.8  |
| 50°    | 169.0  | 171.6  | 176.8  | 179.4  | 184.6  | 187.2  | 195.0  | 200.2  | 208.0  | 213.2  | 218.4  |
| 52.5°  | 163.8  | 166.4  | 171.6  | 174.2  | 179.4  | 182.0  | 192.4  | 202.8  | 210.6  | 221.0  | 221.0  |
| 55°    | 158.6  | 158.6  | 163.8  | 171.6  | 176.8  | 182.0  | 187.2  | 195.0  | 200.2  | 205.4  | 205.4  |
| 57.5°  | 150.8  | 153.4  | 158.6  | 166.4  | 171.6  | 176.8  | 182.0  | 187.2  | 189.8  | 195.0  | 192.4  |
| 60°    | 145.6  | 145.6  | 153.4  | 161.2  | 169.0  | 176.8  | 176.8  | 176.8  | 174.2  | 174.2  | 174.2  |
| 62.5°  | 137.8  | 140.4  | 150.8  | 163.8  | 174.2  | 184.6  | 176.8  | 169.0  | 161.2  | 153.4  | 156.0  |
| 65°    | 132.6  | 135.2  | 140.4  | 148.2  | 153.4  | 158.6  | 153.4  | 150.8  | 145.6  | 140.4  | 143.0  |
| 67.5°  | 122.2  | 124.8  | 127.4  | 127.4  | 130.0  | 130.0  | 130.0  | 130.0  | 130.0  | 130.0  | 132.6  |
| 70°    | 114.4  | 114.4  | 114.4  | 117.0  | 117.0  | 117.0  | 117.0  | 117.0  | 117.0  | 117.0  | 119.6  |
| 72.5°  | 104.0  | 104.0  | 104.0  | 104.0  | 104.0  | 104.0  | 104.0  | 104.0  | 104.0  | 104.0  | 106.6  |
| 75°    | 91.0   | 91.0   | 91.0   | 91.0   | 91.0   | 91.0   | 91.0   | 91.0   | 91.0   | 91.0   | 93.6   |
| 77.5°  | 80.6   | 80.6   | 80.6   | 80.6   | 80.6   | 80.6   | 80.6   | 80.6   | 78.0   | 78.0   | 80.6   |
| 80°    | 67.6   | 67.6   | 67.6   | 67.6   | 65.0   | 65.0   | 65.0   | 65.0   | 65.0   | 65.0   | 67.6   |
| 82.5°  | 54.6   | 54.6   | 54.6   | 54.6   | 52.0   | 52.0   | 52.0   | 52.0   | 49.4   | 49.4   | 52.0   |
| 85°    | 49.4   | 52.0   | 52.0   | 54.6   | 54.6   | 54.6   | 52.0   | 49.4   | 46.8   | 44.2   | 44.2   |
| 87.5°  | 20.8   | 20.8   | 20.8   | 20.8   | 18.2   | 18.2   | 18.2   | 18.2   | 18.2   | 18.2   | 18.2   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° | 217.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 220°   | 222.5° | 225°   | 227.5° | 230°   | 232.5° | 235°   | 237.5° | 240°   | 242.5° | 245°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 |
| 2.5°   | 1801.9 | 1807.1 | 1812.3 | 1820.1 | 1830.5 | 1838.3 | 1846.1 | 1861.7 | 1879.9 | 1895.5 | 1911.1 |
| 5°     | 1617.3 | 1630.3 | 1643.3 | 1658.9 | 1674.5 | 1687.5 | 1703.1 | 1734.3 | 1765.5 | 1794.1 | 1825.3 |
| 7.5°   | 1326.1 | 1344.3 | 1359.9 | 1385.9 | 1409.3 | 1435.3 | 1458.7 | 1497.7 | 1534.1 | 1573.1 | 1609.5 |
| 10°    | 1084.3 | 1105.1 | 1125.9 | 1159.7 | 1196.1 | 1229.9 | 1263.7 | 1294.9 | 1328.7 | 1359.9 | 1391.1 |
| 12.5°  | 980.3  | 1003.7 | 1029.7 | 1050.5 | 1073.9 | 1094.7 | 1115.5 | 1151.9 | 1188.3 | 1224.7 | 1261.1 |
| 15°    | 894.5  | 920.5  | 946.5  | 972.5  | 995.9  | 1021.9 | 1045.3 | 1076.5 | 1110.3 | 1141.5 | 1172.7 |
| 17.5°  | 795.7  | 821.7  | 850.3  | 878.9  | 907.5  | 936.1  | 964.7  | 1008.9 | 1053.1 | 1094.7 | 1138.9 |
| 20°    | 670.8  | 707.2  | 741.0  | 780.1  | 819.1  | 858.1  | 897.1  | 943.9  | 990.7  | 1034.9 | 1081.7 |
| 22.5°  | 546.0  | 579.8  | 613.6  | 660.4  | 707.2  | 751.4  | 798.3  | 860.7  | 920.5  | 982.9  | 1042.7 |
| 25°    | 455.0  | 486.2  | 517.4  | 569.4  | 618.8  | 670.8  | 720.2  | 795.7  | 868.5  | 943.9  | 1016.7 |
| 27.5°  | 392.6  | 421.2  | 449.8  | 504.4  | 559.0  | 611.0  | 665.6  | 748.8  | 829.5  | 912.7  | 993.3  |
| 30°    | 364.0  | 382.2  | 400.4  | 452.4  | 504.4  | 553.8  | 605.8  | 686.4  | 767.1  | 847.7  | 928.3  |
| 32.5°  | 317.2  | 332.8  | 348.4  | 395.2  | 442.0  | 486.2  | 533.0  | 616.2  | 696.8  | 780.1  | 860.7  |
| 35°    | 280.8  | 293.8  | 306.8  | 351.0  | 392.6  | 436.8  | 478.4  | 561.6  | 644.8  | 728.0  | 811.3  |
| 37.5°  | 260.0  | 273.0  | 283.4  | 322.4  | 364.0  | 403.0  | 442.0  | 525.2  | 605.8  | 689.0  | 769.7  |
| 40°    | 244.4  | 252.2  | 262.6  | 301.6  | 338.0  | 377.0  | 413.4  | 488.8  | 566.8  | 642.2  | 717.6  |
| 42.5°  | 234.0  | 244.4  | 252.2  | 286.0  | 322.4  | 356.2  | 390.0  | 462.8  | 535.6  | 605.8  | 678.6  |
| 45°    | 231.4  | 241.8  | 252.2  | 280.8  | 309.4  | 335.4  | 364.0  | 434.2  | 504.4  | 574.6  | 644.8  |
| 47.5°  | 226.2  | 234.0  | 244.4  | 267.8  | 288.6  | 312.0  | 332.8  | 403.0  | 473.2  | 540.8  | 611.0  |
| 50°    | 223.6  | 226.2  | 231.4  | 252.2  | 273.0  | 293.8  | 314.6  | 384.8  | 455.0  | 525.2  | 595.4  |
| 52.5°  | 221.0  | 221.0  | 221.0  | 239.2  | 257.4  | 273.0  | 291.2  | 361.4  | 434.2  | 504.4  | 574.6  |
| 55°    | 205.4  | 202.8  | 202.8  | 221.0  | 236.6  | 254.8  | 270.4  | 340.6  | 410.8  | 478.4  | 548.6  |
| 57.5°  | 189.8  | 187.2  | 184.6  | 200.2  | 215.8  | 231.4  | 247.0  | 317.2  | 390.0  | 460.2  | 530.4  |
| 60°    | 174.2  | 171.6  | 171.6  | 187.2  | 200.2  | 215.8  | 228.8  | 301.6  | 371.8  | 444.6  | 514.8  |
| 62.5°  | 156.0  | 158.6  | 158.6  | 171.6  | 187.2  | 200.2  | 213.2  | 286.0  | 361.4  | 434.2  | 507.0  |
| 65°    | 143.0  | 145.6  | 145.6  | 161.2  | 176.8  | 192.4  | 208.0  | 278.2  | 351.0  | 421.2  | 491.4  |
| 67.5°  | 132.6  | 135.2  | 135.2  | 153.4  | 169.0  | 187.2  | 202.8  | 265.2  | 330.2  | 392.6  | 455.0  |
| 70°    | 122.2  | 122.2  | 124.8  | 143.0  | 161.2  | 179.4  | 197.6  | 252.2  | 306.8  | 358.8  | 413.4  |
| 72.5°  | 109.2  | 111.8  | 114.4  | 132.6  | 148.2  | 166.4  | 182.0  | 231.4  | 280.8  | 330.2  | 379.6  |
| 75°    | 96.2   | 98.8   | 101.4  | 117.0  | 132.6  | 148.2  | 163.8  | 210.6  | 254.8  | 301.6  | 345.8  |
| 77.5°  | 85.8   | 88.4   | 91.0   | 104.0  | 117.0  | 130.0  | 143.0  | 176.8  | 213.2  | 247.0  | 280.8  |
| 80°    | 70.2   | 70.2   | 72.8   | 83.2   | 93.6   | 101.4  | 111.8  | 135.2  | 158.6  | 179.4  | 202.8  |
| 82.5°  | 52.0   | 54.6   | 54.6   | 62.4   | 67.6   | 75.4   | 80.6   | 93.6   | 104.0  | 117.0  | 127.4  |
| 85°    | 44.2   | 41.6   | 41.6   | 46.8   | 49.4   | 54.6   | 57.2   | 65.0   | 70.2   | 78.0   | 83.2   |
| 87.5°  | 18.2   | 15.6   | 15.6   | 18.2   | 23.4   | 26.0   | 28.6   | 28.6   | 31.2   | 31.2   | 31.2   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° | 245° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°   | 252.5° | 255°   | 257.5° | 260°   | 262.5° | 265°   | 267.5° | 270°   | 272.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 |
| 2.5°   | 1918.9 | 1924.1 | 1931.9 | 1937.1 | 1950.1 | 1960.5 | 1973.5 | 1983.9 | 1991.7 | 2004.7 | 1999.5 |
| 5°     | 1848.7 | 1872.1 | 1895.5 | 1918.9 | 1937.1 | 1955.3 | 1970.9 | 1989.1 | 2009.9 | 2048.9 | 2059.3 |
| 7.5°   | 1640.7 | 1671.9 | 1700.5 | 1731.7 | 1768.1 | 1804.5 | 1840.9 | 1877.3 | 1911.1 | 1960.5 | 1991.7 |
| 10°    | 1435.3 | 1479.5 | 1521.1 | 1565.3 | 1599.1 | 1632.9 | 1664.1 | 1697.9 | 1744.7 | 1794.1 | 1851.3 |
| 12.5°  | 1305.3 | 1349.5 | 1393.7 | 1437.9 | 1487.3 | 1534.1 | 1583.5 | 1630.3 | 1674.5 | 1713.5 | 1778.5 |
| 15°    | 1219.5 | 1268.9 | 1315.7 | 1362.5 | 1422.3 | 1479.5 | 1539.3 | 1596.5 | 1661.5 | 1713.5 | 1757.7 |
| 17.5°  | 1198.7 | 1258.5 | 1315.7 | 1375.5 | 1437.9 | 1500.3 | 1562.7 | 1625.1 | 1690.1 | 1768.1 | 1825.3 |
| 20°    | 1162.3 | 1242.9 | 1323.5 | 1404.1 | 1484.7 | 1562.7 | 1643.3 | 1721.3 | 1807.1 | 1900.7 | 1926.7 |
| 22.5°  | 1141.5 | 1237.7 | 1336.5 | 1432.7 | 1541.9 | 1653.7 | 1762.9 | 1872.1 | 1963.1 | 2033.3 | 2111.3 |
| 25°    | 1138.9 | 1258.5 | 1380.7 | 1500.3 | 1638.1 | 1773.3 | 1911.1 | 2046.3 | 2163.3 | 2233.5 | 2296.0 |
| 27.5°  | 1136.3 | 1281.9 | 1424.9 | 1567.9 | 1736.9 | 1903.3 | 2072.3 | 2238.7 | 2348.0 | 2449.4 | 2501.4 |
| 30°    | 1105.1 | 1279.3 | 1456.1 | 1630.3 | 1820.1 | 2009.9 | 2199.7 | 2389.6 | 2501.4 | 2571.6 | 2597.6 |
| 32.5°  | 1066.1 | 1271.5 | 1476.9 | 1682.3 | 1898.1 | 2113.9 | 2327.2 | 2543.0 | 2631.4 | 2691.2 | 2670.4 |
| 35°    | 1034.9 | 1261.1 | 1484.7 | 1708.3 | 1937.1 | 2168.5 | 2397.4 | 2626.2 | 2753.6 | 2836.8 | 2803.0 |
| 37.5°  | 1006.3 | 1242.9 | 1479.5 | 1716.1 | 1983.9 | 2251.7 | 2519.6 | 2787.4 | 2909.6 | 2998.0 | 2959.0 |
| 40°    | 972.5  | 1224.7 | 1479.5 | 1731.7 | 2038.5 | 2342.8 | 2649.6 | 2953.8 | 3112.4 | 3187.8 | 3128.0 |
| 42.5°  | 943.9  | 1206.5 | 1471.7 | 1734.3 | 2061.9 | 2389.6 | 2717.2 | 3044.8 | 3221.6 | 3328.2 | 3252.8 |
| 45°    | 907.5  | 1170.1 | 1430.1 | 1692.7 | 2054.1 | 2415.6 | 2774.4 | 3135.8 | 3341.2 | 3424.4 | 3320.4 |
| 47.5°  | 868.5  | 1128.5 | 1385.9 | 1643.3 | 2028.1 | 2413.0 | 2797.8 | 3182.6 | 3372.4 | 3471.2 | 3375.0 |
| 50°    | 855.5  | 1115.5 | 1372.9 | 1632.9 | 2048.9 | 2467.6 | 2883.6 | 3299.6 | 3437.4 | 3518.0 | 3390.6 |
| 52.5°  | 852.9  | 1128.5 | 1406.7 | 1682.3 | 2100.9 | 2517.0 | 2935.6 | 3351.6 | 3463.4 | 3549.2 | 3434.8 |
| 55°    | 845.1  | 1144.1 | 1440.5 | 1736.9 | 2173.7 | 2613.2 | 3050.0 | 3486.8 | 3598.6 | 3661.0 | 3575.2 |
| 57.5°  | 852.9  | 1175.3 | 1495.1 | 1817.5 | 2267.4 | 2717.2 | 3167.0 | 3616.8 | 3752.0 | 3796.3 | 3778.1 |
| 60°    | 858.1  | 1201.3 | 1541.9 | 1885.1 | 2324.6 | 2764.0 | 3203.4 | 3642.8 | 3783.3 | 3892.5 | 3913.3 |
| 62.5°  | 845.1  | 1183.1 | 1518.5 | 1856.5 | 2254.3 | 2652.2 | 3050.0 | 3447.8 | 3679.2 | 3840.5 | 3934.1 |
| 65°    | 806.1  | 1118.1 | 1432.7 | 1744.7 | 2111.3 | 2480.6 | 2847.2 | 3213.8 | 3458.2 | 3697.4 | 3772.9 |
| 67.5°  | 720.2  | 985.5  | 1250.7 | 1515.9 | 1835.7 | 2155.5 | 2472.8 | 2792.6 | 3099.4 | 3330.8 | 3434.8 |
| 70°    | 624.0  | 832.1  | 1042.7 | 1250.7 | 1541.9 | 1833.1 | 2124.3 | 2415.6 | 2686.0 | 2940.8 | 3039.6 |
| 72.5°  | 543.4  | 704.6  | 868.5  | 1029.7 | 1237.7 | 1443.1 | 1651.1 | 1856.5 | 2176.3 | 2431.2 | 2527.4 |
| 75°    | 462.8  | 579.8  | 694.2  | 811.3  | 954.3  | 1097.3 | 1237.7 | 1380.7 | 1606.9 | 1835.7 | 1931.9 |
| 77.5°  | 356.2  | 434.2  | 509.6  | 585.0  | 683.8  | 780.1  | 878.9  | 975.1  | 1133.7 | 1305.3 | 1354.7 |
| 80°    | 247.0  | 291.2  | 332.8  | 377.0  | 455.0  | 533.0  | 611.0  | 689.0  | 793.1  | 889.3  | 964.7  |
| 82.5°  | 153.4  | 182.0  | 208.0  | 234.0  | 296.4  | 358.8  | 418.6  | 481.0  | 522.6  | 527.8  | 603.2  |
| 85°    | 98.8   | 117.0  | 132.6  | 148.2  | 184.6  | 223.6  | 260.0  | 296.4  | 265.2  | 247.0  | 293.8  |
| 87.5°  | 39.0   | 49.4   | 57.2   | 65.0   | 62.4   | 59.8   | 57.2   | 54.6   | 46.8   | 41.6   | 52.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° | 272.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 275°   | 277.5° | 280°   | 282.5° | 285°   | 287.5° | 290°   | 292.5° | 295°   | 297.5° | 300°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 |
| 2.5°   | 2004.7 | 2012.5 | 2020.3 | 2025.5 | 2033.3 | 2035.9 | 2038.5 | 2038.5 | 2041.1 | 2043.7 | 2048.9 |
| 5°     | 2100.9 | 2116.5 | 2132.1 | 2145.1 | 2160.7 | 2173.7 | 2184.1 | 2197.1 | 2207.5 | 2207.5 | 2204.9 |
| 7.5°   | 2020.3 | 2059.3 | 2098.3 | 2137.3 | 2176.3 | 2204.9 | 2230.9 | 2259.5 | 2285.6 | 2290.8 | 2296.0 |
| 10°    | 1913.7 | 1955.3 | 1994.3 | 2035.9 | 2074.9 | 2119.1 | 2160.7 | 2202.3 | 2246.5 | 2254.3 | 2264.8 |
| 12.5°  | 1814.9 | 1864.3 | 1913.7 | 1960.5 | 2009.9 | 2041.1 | 2072.3 | 2100.9 | 2132.1 | 2152.9 | 2173.7 |
| 15°    | 1812.3 | 1853.9 | 1895.5 | 1934.5 | 1976.1 | 1994.3 | 2012.5 | 2028.1 | 2046.3 | 2046.3 | 2048.9 |
| 17.5°  | 1872.1 | 1898.1 | 1924.1 | 1947.5 | 1973.5 | 1976.1 | 1981.3 | 1983.9 | 1986.5 | 1978.7 | 1970.9 |
| 20°    | 1989.1 | 1999.5 | 2009.9 | 2020.3 | 2030.7 | 2012.5 | 1996.9 | 1978.7 | 1960.5 | 1939.7 | 1921.5 |
| 22.5°  | 2160.7 | 2137.3 | 2113.9 | 2090.5 | 2067.1 | 2035.9 | 2002.1 | 1970.9 | 1937.1 | 1911.1 | 1885.1 |
| 25°    | 2322.0 | 2293.4 | 2264.8 | 2236.1 | 2207.5 | 2139.9 | 2072.3 | 2002.1 | 1934.5 | 1905.9 | 1877.3 |
| 27.5°  | 2537.8 | 2493.6 | 2449.4 | 2405.2 | 2361.0 | 2270.0 | 2178.9 | 2087.9 | 1996.9 | 1947.5 | 1900.7 |
| 30°    | 2589.8 | 2540.4 | 2491.0 | 2439.0 | 2389.6 | 2301.2 | 2215.3 | 2126.9 | 2038.5 | 1981.3 | 1926.7 |
| 32.5°  | 2665.2 | 2608.0 | 2550.8 | 2493.6 | 2436.4 | 2350.6 | 2264.8 | 2176.3 | 2090.5 | 2038.5 | 1983.9 |
| 35°    | 2790.0 | 2725.0 | 2660.0 | 2592.4 | 2527.4 | 2439.0 | 2353.2 | 2264.8 | 2176.3 | 2116.5 | 2059.3 |
| 37.5°  | 2896.6 | 2821.2 | 2745.8 | 2670.4 | 2595.0 | 2517.0 | 2436.4 | 2358.4 | 2277.8 | 2217.9 | 2160.7 |
| 40°    | 3016.2 | 2933.0 | 2849.8 | 2769.2 | 2686.0 | 2613.2 | 2540.4 | 2465.0 | 2392.2 | 2345.4 | 2298.6 |
| 42.5°  | 3120.2 | 3018.8 | 2920.0 | 2821.2 | 2719.8 | 2670.4 | 2623.6 | 2574.2 | 2524.8 | 2501.4 | 2475.4 |
| 45°    | 3193.0 | 3099.4 | 3003.2 | 2909.6 | 2816.0 | 2779.6 | 2743.2 | 2706.8 | 2670.4 | 2693.8 | 2717.2 |
| 47.5°  | 3224.2 | 3148.8 | 3076.0 | 3003.2 | 2927.8 | 2940.8 | 2953.8 | 2964.2 | 2977.2 | 3008.4 | 3042.2 |
| 50°    | 3252.8 | 3211.2 | 3167.0 | 3125.4 | 3081.2 | 3130.6 | 3177.4 | 3226.8 | 3276.2 | 3341.2 | 3406.2 |
| 52.5°  | 3310.0 | 3286.6 | 3265.8 | 3242.4 | 3219.0 | 3304.8 | 3390.6 | 3476.4 | 3562.2 | 3635.0 | 3707.8 |
| 55°    | 3481.6 | 3463.4 | 3445.2 | 3424.4 | 3406.2 | 3528.4 | 3648.0 | 3770.3 | 3892.5 | 3967.9 | 4043.3 |
| 57.5°  | 3718.2 | 3707.8 | 3694.8 | 3684.4 | 3671.4 | 3791.1 | 3908.1 | 4025.1 | 4144.7 | 4217.5 | 4292.9 |
| 60°    | 3897.7 | 3900.3 | 3900.3 | 3902.9 | 3902.9 | 3993.9 | 4084.9 | 4178.5 | 4269.5 | 4331.9 | 4396.9 |
| 62.5°  | 3993.9 | 3988.7 | 3983.5 | 3978.3 | 3973.1 | 4048.5 | 4123.9 | 4199.3 | 4274.7 | 4321.5 | 4368.3 |
| 65°    | 3889.9 | 3918.5 | 3947.1 | 3975.7 | 4004.3 | 4014.7 | 4022.5 | 4032.9 | 4040.7 | 4069.3 | 4097.9 |
| 67.5°  | 3541.4 | 3598.6 | 3653.2 | 3710.4 | 3765.0 | 3726.0 | 3689.6 | 3650.6 | 3611.6 | 3619.4 | 3624.6 |
| 70°    | 3154.0 | 3219.0 | 3286.6 | 3351.6 | 3416.6 | 3325.6 | 3234.6 | 3141.0 | 3050.0 | 3018.8 | 2987.6 |
| 72.5°  | 2660.0 | 2717.2 | 2777.0 | 2834.2 | 2891.4 | 2779.6 | 2670.4 | 2558.6 | 2446.8 | 2392.2 | 2337.6 |
| 75°    | 2033.3 | 2100.9 | 2171.1 | 2238.7 | 2306.4 | 2181.5 | 2054.1 | 1929.3 | 1801.9 | 1765.5 | 1731.7 |
| 77.5°  | 1482.1 | 1562.7 | 1643.3 | 1723.9 | 1804.5 | 1692.7 | 1580.9 | 1466.5 | 1354.7 | 1333.9 | 1313.1 |
| 80°    | 1079.1 | 1141.5 | 1201.3 | 1263.7 | 1323.5 | 1258.5 | 1193.5 | 1128.5 | 1063.5 | 1060.9 | 1058.3 |
| 82.5°  | 728.0  | 782.7  | 834.7  | 889.3  | 941.3  | 915.3  | 891.9  | 865.9  | 839.9  | 865.9  | 894.5  |
| 85°    | 374.4  | 449.8  | 527.8  | 603.2  | 678.6  | 670.8  | 665.6  | 657.8  | 650.0  | 683.8  | 715.0  |
| 87.5°  | 75.4   | 140.4  | 205.4  | 267.8  | 332.8  | 317.2  | 301.6  | 283.4  | 267.8  | 278.2  | 286.0  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° | 300° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305°   | 307.5° | 310°   | 312.5° | 315°   | 317.5° | 320°   | 322.5° | 325°   | 327.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 |
| 2.5°   | 2051.5 | 2054.1 | 2054.1 | 2054.1 | 2054.1 | 2054.1 | 2048.9 | 2046.3 | 2041.1 | 2035.9 | 2028.1 |
| 5°     | 2204.9 | 2202.3 | 2191.9 | 2181.5 | 2168.5 | 2158.1 | 2150.3 | 2139.9 | 2132.1 | 2121.7 | 2106.1 |
| 7.5°   | 2301.2 | 2306.4 | 2288.2 | 2272.6 | 2254.3 | 2236.1 | 2217.9 | 2199.7 | 2181.5 | 2163.3 | 2126.9 |
| 10°    | 2272.6 | 2280.4 | 2270.0 | 2259.5 | 2246.5 | 2236.1 | 2215.3 | 2191.9 | 2171.1 | 2147.7 | 2103.5 |
| 12.5°  | 2191.9 | 2212.7 | 2207.5 | 2202.3 | 2197.1 | 2191.9 | 2178.9 | 2163.3 | 2150.3 | 2134.7 | 2085.3 |
| 15°    | 2048.9 | 2048.9 | 2051.5 | 2054.1 | 2054.1 | 2056.7 | 2059.3 | 2061.9 | 2064.5 | 2067.1 | 2038.5 |
| 17.5°  | 1963.1 | 1955.3 | 1955.3 | 1955.3 | 1955.3 | 1955.3 | 1965.7 | 1978.7 | 1989.1 | 1999.5 | 1991.7 |
| 20°    | 1900.7 | 1882.5 | 1879.9 | 1879.9 | 1877.3 | 1874.7 | 1892.9 | 1913.7 | 1931.9 | 1950.1 | 1960.5 |
| 22.5°  | 1859.1 | 1833.1 | 1830.5 | 1827.9 | 1825.3 | 1822.7 | 1846.1 | 1869.5 | 1892.9 | 1916.3 | 1952.7 |
| 25°    | 1848.7 | 1820.1 | 1822.7 | 1825.3 | 1825.3 | 1827.9 | 1846.1 | 1864.3 | 1882.5 | 1900.7 | 1963.1 |
| 27.5°  | 1851.3 | 1804.5 | 1807.1 | 1809.7 | 1809.7 | 1812.3 | 1840.9 | 1866.9 | 1895.5 | 1921.5 | 1999.5 |
| 30°    | 1869.5 | 1814.9 | 1809.7 | 1804.5 | 1799.3 | 1794.1 | 1833.1 | 1872.1 | 1911.1 | 1950.1 | 2009.9 |
| 32.5°  | 1931.9 | 1879.9 | 1866.9 | 1853.9 | 1840.9 | 1827.9 | 1874.7 | 1918.9 | 1965.7 | 2009.9 | 2059.3 |
| 35°    | 1999.5 | 1942.3 | 1937.1 | 1931.9 | 1924.1 | 1918.9 | 1960.5 | 2004.7 | 2046.3 | 2087.9 | 2132.1 |
| 37.5°  | 2100.9 | 2043.7 | 2038.5 | 2030.7 | 2025.5 | 2017.7 | 2064.5 | 2108.7 | 2155.5 | 2199.7 | 2238.7 |
| 40°    | 2251.7 | 2204.9 | 2202.3 | 2202.3 | 2199.7 | 2197.1 | 2233.5 | 2272.6 | 2309.0 | 2345.4 | 2371.4 |
| 42.5°  | 2452.0 | 2428.6 | 2436.4 | 2446.8 | 2454.6 | 2462.4 | 2491.0 | 2522.2 | 2550.8 | 2579.4 | 2571.6 |
| 45°    | 2740.6 | 2764.0 | 2766.6 | 2769.2 | 2771.8 | 2774.4 | 2782.2 | 2792.6 | 2800.4 | 2808.2 | 2777.0 |
| 47.5°  | 3073.4 | 3104.6 | 3120.2 | 3135.8 | 3148.8 | 3164.4 | 3154.0 | 3141.0 | 3130.6 | 3117.6 | 3039.6 |
| 50°    | 3468.6 | 3533.6 | 3531.0 | 3528.4 | 3523.2 | 3520.6 | 3499.8 | 3479.0 | 3455.6 | 3434.8 | 3320.4 |
| 52.5°  | 3780.7 | 3853.5 | 3866.5 | 3879.5 | 3892.5 | 3905.5 | 3866.5 | 3827.5 | 3785.9 | 3746.8 | 3603.8 |
| 55°    | 4116.1 | 4191.5 | 4194.1 | 4196.7 | 4196.7 | 4199.3 | 4144.7 | 4090.1 | 4032.9 | 3978.3 | 3830.1 |
| 57.5°  | 4365.7 | 4438.5 | 4430.7 | 4425.5 | 4417.7 | 4409.9 | 4344.9 | 4279.9 | 4214.9 | 4149.9 | 4001.7 |
| 60°    | 4459.3 | 4521.7 | 4506.1 | 4490.5 | 4472.3 | 4456.7 | 4407.3 | 4357.9 | 4305.9 | 4256.5 | 4113.5 |
| 62.5°  | 4415.1 | 4461.9 | 4438.5 | 4417.7 | 4394.3 | 4370.9 | 4308.5 | 4243.5 | 4181.1 | 4116.1 | 4012.1 |
| 65°    | 4123.9 | 4152.5 | 4121.3 | 4092.7 | 4064.1 | 4032.9 | 3980.9 | 3928.9 | 3874.3 | 3822.3 | 3752.0 |
| 67.5°  | 3632.4 | 3637.6 | 3635.0 | 3632.4 | 3629.8 | 3627.2 | 3551.8 | 3476.4 | 3398.4 | 3323.0 | 3317.8 |
| 70°    | 2959.0 | 2927.8 | 2933.0 | 2940.8 | 2946.0 | 2951.2 | 2894.0 | 2839.4 | 2782.2 | 2725.0 | 2751.0 |
| 72.5°  | 2283.0 | 2228.3 | 2241.3 | 2256.9 | 2270.0 | 2283.0 | 2236.1 | 2191.9 | 2145.1 | 2098.3 | 2134.7 |
| 75°    | 1695.3 | 1661.5 | 1674.5 | 1690.1 | 1703.1 | 1716.1 | 1697.9 | 1679.7 | 1658.9 | 1640.7 | 1674.5 |
| 77.5°  | 1292.3 | 1271.5 | 1274.1 | 1274.1 | 1276.7 | 1276.7 | 1279.3 | 1284.5 | 1287.1 | 1289.7 | 1326.1 |
| 80°    | 1053.1 | 1050.5 | 1047.9 | 1045.3 | 1040.1 | 1037.5 | 1063.5 | 1089.5 | 1115.5 | 1141.5 | 1159.7 |
| 82.5°  | 920.5  | 946.5  | 930.9  | 917.9  | 902.3  | 886.7  | 910.1  | 933.5  | 956.9  | 980.3  | 972.5  |
| 85°    | 748.8  | 780.1  | 751.4  | 722.8  | 691.6  | 663.0  | 683.8  | 702.0  | 722.8  | 741.0  | 730.6  |
| 87.5°  | 296.4  | 304.2  | 257.4  | 213.2  | 166.4  | 119.6  | 189.8  | 257.4  | 327.6  | 395.2  | 405.6  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305° | 307.5° | 310° | 312.5° | 315° | 317.5° | 320° | 322.5° | 325° | 327.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 330°   | 332.5° | 335°   | 337.5° | 340°   | 342.5° | 345°   | 347.5° | 350°   | 352.5° | 355°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 | 1872.1 |
| 2.5°   | 2020.3 | 2009.9 | 2002.1 | 1999.5 | 1994.3 | 1991.7 | 1986.5 | 1981.3 | 1973.5 | 1968.3 | 1960.5 |
| 5°     | 2087.9 | 2072.3 | 2054.1 | 2028.1 | 2004.7 | 1978.7 | 1952.7 | 1929.3 | 1905.9 | 1879.9 | 1856.5 |
| 7.5°   | 2090.5 | 2054.1 | 2017.7 | 1983.9 | 1947.5 | 1913.7 | 1877.3 | 1846.1 | 1812.3 | 1778.5 | 1747.3 |
| 10°    | 2061.9 | 2017.7 | 1973.5 | 1929.3 | 1887.7 | 1843.5 | 1799.3 | 1762.9 | 1723.9 | 1684.9 | 1648.5 |
| 12.5°  | 2038.5 | 1989.1 | 1939.7 | 1887.7 | 1838.3 | 1786.3 | 1734.3 | 1697.9 | 1661.5 | 1625.1 | 1588.7 |
| 15°    | 2009.9 | 1978.7 | 1950.1 | 1903.3 | 1856.5 | 1809.7 | 1762.9 | 1713.5 | 1666.7 | 1617.3 | 1567.9 |
| 17.5°  | 1986.5 | 1978.7 | 1970.9 | 1939.7 | 1908.5 | 1874.7 | 1843.5 | 1794.1 | 1744.7 | 1692.7 | 1643.3 |
| 20°    | 1973.5 | 1983.9 | 1994.3 | 1978.7 | 1963.1 | 1944.9 | 1929.3 | 1892.9 | 1856.5 | 1817.5 | 1781.1 |
| 22.5°  | 1989.1 | 2028.1 | 2064.5 | 2067.1 | 2072.3 | 2074.9 | 2077.5 | 2043.7 | 2009.9 | 1973.5 | 1939.7 |
| 25°    | 2025.5 | 2087.9 | 2150.3 | 2184.1 | 2217.9 | 2254.3 | 2288.2 | 2267.4 | 2246.5 | 2225.7 | 2204.9 |
| 27.5°  | 2074.9 | 2152.9 | 2230.9 | 2280.4 | 2327.2 | 2376.6 | 2426.0 | 2423.4 | 2420.8 | 2415.6 | 2413.0 |
| 30°    | 2067.1 | 2126.9 | 2186.7 | 2246.5 | 2306.4 | 2366.2 | 2426.0 | 2457.2 | 2485.8 | 2517.0 | 2548.2 |
| 32.5°  | 2111.3 | 2160.7 | 2212.7 | 2275.2 | 2337.6 | 2402.6 | 2465.0 | 2530.0 | 2592.4 | 2657.4 | 2722.4 |
| 35°    | 2178.9 | 2223.1 | 2270.0 | 2337.6 | 2407.8 | 2475.4 | 2545.6 | 2623.6 | 2704.2 | 2784.8 | 2862.8 |
| 37.5°  | 2280.4 | 2319.4 | 2361.0 | 2418.2 | 2478.0 | 2535.2 | 2595.0 | 2709.4 | 2823.8 | 2940.8 | 3055.2 |
| 40°    | 2397.4 | 2423.4 | 2449.4 | 2504.0 | 2558.6 | 2613.2 | 2667.8 | 2810.8 | 2953.8 | 3096.8 | 3239.8 |
| 42.5°  | 2566.4 | 2558.6 | 2550.8 | 2595.0 | 2641.8 | 2686.0 | 2732.8 | 2862.8 | 2992.8 | 3122.8 | 3252.8 |
| 45°    | 2745.8 | 2714.6 | 2683.4 | 2704.2 | 2727.6 | 2748.4 | 2771.8 | 2904.4 | 3037.0 | 3172.2 | 3304.8 |
| 47.5°  | 2961.6 | 2883.6 | 2805.6 | 2787.4 | 2769.2 | 2748.4 | 2730.2 | 2873.2 | 3016.2 | 3161.8 | 3304.8 |
| 50°    | 3206.0 | 3089.0 | 2974.6 | 2927.8 | 2878.4 | 2831.6 | 2782.2 | 2899.2 | 3018.8 | 3138.4 | 3255.4 |
| 52.5°  | 3460.8 | 3315.2 | 3172.2 | 3099.4 | 3026.6 | 2951.2 | 2878.4 | 2977.2 | 3078.6 | 3180.0 | 3278.8 |
| 55°    | 3679.2 | 3531.0 | 3380.2 | 3294.4 | 3208.6 | 3122.8 | 3037.0 | 3135.8 | 3234.6 | 3333.4 | 3432.2 |
| 57.5°  | 3853.5 | 3705.2 | 3557.0 | 3476.4 | 3393.2 | 3312.6 | 3229.4 | 3323.0 | 3419.2 | 3515.4 | 3609.0 |
| 60°    | 3973.1 | 3830.1 | 3687.0 | 3609.0 | 3531.0 | 3453.0 | 3375.0 | 3486.8 | 3598.6 | 3713.0 | 3824.9 |
| 62.5°  | 3910.7 | 3806.7 | 3702.6 | 3668.8 | 3635.0 | 3598.6 | 3564.8 | 3671.4 | 3775.5 | 3882.1 | 3988.7 |
| 65°    | 3681.8 | 3611.6 | 3541.4 | 3575.2 | 3611.6 | 3645.4 | 3681.8 | 3752.0 | 3822.3 | 3895.1 | 3965.3 |
| 67.5°  | 3310.0 | 3304.8 | 3297.0 | 3372.4 | 3447.8 | 3525.8 | 3601.2 | 3648.0 | 3692.2 | 3739.0 | 3785.9 |
| 70°    | 2777.0 | 2805.6 | 2831.6 | 2961.6 | 3091.6 | 3221.6 | 3351.6 | 3369.8 | 3388.0 | 3406.2 | 3424.4 |
| 72.5°  | 2173.7 | 2210.1 | 2249.1 | 2420.8 | 2589.8 | 2761.4 | 2933.0 | 2922.6 | 2912.2 | 2899.2 | 2888.8 |
| 75°    | 1710.9 | 1744.7 | 1781.1 | 1939.7 | 2098.3 | 2256.9 | 2415.6 | 2371.4 | 2329.8 | 2285.6 | 2241.3 |
| 77.5°  | 1365.1 | 1401.5 | 1440.5 | 1588.7 | 1736.9 | 1887.7 | 2035.9 | 1929.3 | 1822.7 | 1716.1 | 1609.5 |
| 80°    | 1175.3 | 1193.5 | 1209.1 | 1310.5 | 1409.3 | 1510.7 | 1612.1 | 1502.9 | 1391.1 | 1279.3 | 1170.1 |
| 82.5°  | 964.7  | 954.3  | 946.5  | 1006.3 | 1066.1 | 1125.9 | 1185.7 | 1081.7 | 977.7  | 871.1  | 767.1  |
| 85°    | 720.2  | 709.8  | 699.4  | 730.6  | 761.9  | 795.7  | 826.9  | 707.2  | 587.6  | 465.4  | 345.8  |
| 87.5°  | 418.6  | 429.0  | 439.4  | 473.2  | 507.0  | 543.4  | 577.2  | 455.0  | 332.8  | 208.0  | 85.8   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 332.5° | 335° | 337.5° | 340° | 342.5° | 345° | 347.5° | 350° | 352.5° | 355° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P671851  
 CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360°   |
|--------|--------|--------|
| 0°     | 1872.1 | 1872.1 |
| 2.5°   | 1944.9 | 1931.9 |
| 5°     | 1838.3 | 1820.1 |
| 7.5°   | 1721.3 | 1697.9 |
| 10°    | 1614.7 | 1583.5 |
| 12.5°  | 1547.1 | 1508.1 |
| 15°    | 1521.1 | 1474.3 |
| 17.5°  | 1599.1 | 1554.9 |
| 20°    | 1718.7 | 1658.9 |
| 22.5°  | 1864.3 | 1791.5 |
| 25°    | 2116.5 | 2028.1 |
| 27.5°  | 2322.0 | 2230.9 |
| 30°    | 2449.4 | 2350.6 |
| 32.5°  | 2589.8 | 2459.8 |
| 35°    | 2735.4 | 2610.6 |
| 37.5°  | 2912.2 | 2771.8 |
| 40°    | 3094.2 | 2948.6 |
| 42.5°  | 3156.6 | 3063.0 |
| 45°    | 3216.4 | 3128.0 |
| 47.5°  | 3229.4 | 3156.6 |
| 50°    | 3242.4 | 3232.0 |
| 52.5°  | 3278.8 | 3276.2 |
| 55°    | 3434.8 | 3437.4 |
| 57.5°  | 3627.2 | 3642.8 |
| 60°    | 3804.1 | 3785.9 |
| 62.5°  | 3895.1 | 3801.5 |
| 65°    | 3832.7 | 3702.6 |
| 67.5°  | 3645.4 | 3505.0 |
| 70°    | 3234.6 | 3044.8 |
| 72.5°  | 2722.4 | 2556.0 |
| 75°    | 2098.3 | 1957.9 |
| 77.5°  | 1492.5 | 1375.5 |
| 80°    | 1050.5 | 933.5  |
| 82.5°  | 673.4  | 579.8  |
| 85°    | 304.2  | 265.2  |
| 87.5°  | 85.8   | 83.2   |
| 90°    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    |

REPORT NUMBER: P671851

CATALOG NUMBER: CCP-SA-2B-760-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

(END OF REPORT)