

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P671896

Luminaire Tested: **CCP-SA-2C-840-U-SLR**

Issue Date: 04/16/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P671896  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-2C-840-U-SLR  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @615mA w/ SLR  
distribution lens  
Light Source: (32) 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6397.3 lumens  
Efficiency: N/A  
Efficacy: 103.0 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G2


Input Watts (W): 62.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 9.1 fc  
 Type IV - Short - N/A

REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

## Luminous Intensity Polar Plot



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1316.3   | 0.0    | 1316.3 |
|                    | % Fixture | 20.6     | 0.0    | 20.6   |
| <b>Street Side</b> | Lumens    | 5081.0   | 0.0    | 5081.0 |
|                    | % Fixture | 79.4     | 0.0    | 79.4   |
| <b>Total</b>       | Lumens    | 6397.3   | 0.0    | 6397.3 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 158.7  | 2.5       |
| 10°-20°   | 335.2  | 5.2       |
| 20°-30°   | 490.4  | 7.7       |
| 30°-40°   | 690.8  | 10.8      |
| 40°-50°   | 949.3  | 14.8      |
| 50°-60°   | 1293.9 | 20.2      |
| 60°-70°   | 1416.1 | 22.1      |
| 70°-80°   | 817.8  | 12.8      |
| 80°-90°   | 245.1  | 3.8       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 6397.3 | 100.0     |
| 0°-180°   | 6397.3 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P671896


CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 657.0  | 10.3      |                         |      |         |
| FM   | (30°-60°)   | 2334.6 | 36.5      |                         |      |         |
| FH   | (60°-80°)   | 1881.2 | 29.4      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 208.2  | 3.3       |                         |      | G2/225  |
| BL   | (0°-30°)    | 327.2  | 5.1       | B1/500                  |      |         |
| BM   | (30°-60°)   | 599.4  | 9.4       | B1/1000                 |      |         |
| BH   | (60°-80°)   | 352.8  | 5.5       | B1/500                  |      | G1/500  |
| BVH  | (80°-90°)   | 36.9   | 0.6       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G2**

Type IV Short



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5°  | 25°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 |
| 2.5°   | 2108.2 | 2096.8 | 2088.3 | 2079.8 | 2068.4 | 2059.9 | 2048.6 | 2037.2 | 2023.0 | 2011.7 | 1997.5 |
| 5°     | 1986.2 | 1952.1 | 1918.1 | 1898.2 | 1875.5 | 1855.6 | 1832.9 | 1807.4 | 1781.9 | 1753.5 | 1728.0 |
| 7.5°   | 1852.8 | 1810.2 | 1767.7 | 1733.6 | 1696.7 | 1662.7 | 1625.8 | 1594.6 | 1563.4 | 1532.2 | 1501.0 |
| 10°    | 1728.0 | 1688.2 | 1648.5 | 1606.0 | 1560.6 | 1518.0 | 1472.6 | 1430.0 | 1387.5 | 1344.9 | 1302.4 |
| 12.5°  | 1645.7 | 1597.4 | 1552.0 | 1503.8 | 1458.4 | 1410.2 | 1361.9 | 1322.2 | 1282.5 | 1239.9 | 1200.2 |
| 15°    | 1608.8 | 1563.4 | 1520.8 | 1472.6 | 1424.4 | 1376.1 | 1327.9 | 1282.5 | 1239.9 | 1194.5 | 1149.1 |
| 17.5°  | 1696.7 | 1631.5 | 1566.2 | 1503.8 | 1441.4 | 1379.0 | 1316.5 | 1259.8 | 1203.0 | 1146.3 | 1089.6 |
| 20°    | 1810.2 | 1728.0 | 1648.5 | 1571.9 | 1492.5 | 1415.8 | 1336.4 | 1257.0 | 1177.5 | 1098.1 | 1018.6 |
| 22.5°  | 1955.0 | 1861.3 | 1770.5 | 1671.2 | 1569.1 | 1469.8 | 1367.6 | 1268.3 | 1169.0 | 1066.9 | 967.5  |
| 25°    | 2213.2 | 2102.5 | 1991.8 | 1850.0 | 1705.3 | 1563.4 | 1418.7 | 1288.2 | 1160.5 | 1030.0 | 899.4  |
| 27.5°  | 2434.5 | 2284.1 | 2136.5 | 1966.3 | 1796.1 | 1625.8 | 1455.6 | 1305.2 | 1157.6 | 1007.3 | 856.9  |
| 30°    | 2565.0 | 2417.4 | 2269.9 | 2062.8 | 1858.5 | 1651.4 | 1444.2 | 1276.8 | 1112.3 | 944.8  | 777.4  |
| 32.5°  | 2684.2 | 2519.6 | 2355.0 | 2128.0 | 1898.2 | 1671.2 | 1441.4 | 1257.0 | 1075.4 | 890.9  | 706.5  |
| 35°    | 2848.7 | 2667.1 | 2488.4 | 2224.5 | 1960.6 | 1696.7 | 1432.9 | 1242.8 | 1049.8 | 859.7  | 666.8  |
| 37.5°  | 3024.6 | 2800.5 | 2579.2 | 2286.9 | 1994.7 | 1702.4 | 1410.2 | 1222.9 | 1035.6 | 848.4  | 661.1  |
| 40°    | 3217.6 | 2945.2 | 2675.6 | 2352.2 | 2031.6 | 1708.1 | 1384.6 | 1197.4 | 1010.1 | 820.0  | 632.7  |
| 42.5°  | 3342.4 | 3047.3 | 2752.3 | 2403.3 | 2057.1 | 1708.1 | 1359.1 | 1174.7 | 990.2  | 803.0  | 618.5  |
| 45°    | 3413.4 | 3126.8 | 2843.0 | 2465.7 | 2088.3 | 1710.9 | 1333.6 | 1152.0 | 970.4  | 786.0  | 604.4  |
| 47.5°  | 3444.6 | 3177.9 | 2911.1 | 2513.9 | 2119.5 | 1722.3 | 1325.1 | 1140.6 | 953.4  | 768.9  | 581.7  |
| 50°    | 3526.9 | 3291.4 | 3055.9 | 2630.2 | 2207.5 | 1781.9 | 1356.3 | 1157.6 | 961.9  | 763.3  | 564.6  |
| 52.5°  | 3575.1 | 3373.6 | 3172.2 | 2735.2 | 2298.3 | 1861.3 | 1424.4 | 1203.0 | 981.7  | 760.4  | 539.1  |
| 55°    | 3751.0 | 3558.1 | 3365.1 | 2899.8 | 2431.6 | 1966.3 | 1498.1 | 1254.1 | 1010.1 | 763.3  | 519.2  |
| 57.5°  | 3975.2 | 3770.9 | 3569.4 | 3067.2 | 2565.0 | 2062.8 | 1560.6 | 1299.5 | 1035.6 | 774.6  | 510.7  |
| 60°    | 4131.2 | 3932.6 | 3736.8 | 3203.4 | 2667.1 | 2133.7 | 1597.4 | 1325.1 | 1052.7 | 777.4  | 505.1  |
| 62.5°  | 4148.2 | 3892.9 | 3640.4 | 3121.1 | 2601.9 | 2079.8 | 1560.6 | 1296.7 | 1032.8 | 766.1  | 502.2  |
| 65°    | 4040.4 | 3742.5 | 3444.6 | 2948.0 | 2451.5 | 1955.0 | 1458.4 | 1217.2 | 976.1  | 732.0  | 490.9  |
| 67.5°  | 3824.8 | 3475.8 | 3126.8 | 2672.8 | 2218.8 | 1764.8 | 1310.9 | 1103.7 | 899.4  | 692.3  | 485.2  |
| 70°    | 3322.6 | 3016.1 | 2712.5 | 2318.1 | 1926.6 | 1532.2 | 1137.8 | 967.5  | 800.1  | 629.9  | 459.7  |
| 72.5°  | 2789.1 | 2502.6 | 2218.8 | 1898.2 | 1580.4 | 1259.8 | 939.2  | 811.5  | 683.8  | 553.3  | 425.6  |
| 75°    | 2136.5 | 1920.9 | 1708.1 | 1469.8 | 1231.4 | 990.2  | 751.9  | 658.3  | 564.6  | 471.0  | 377.4  |
| 77.5°  | 1501.0 | 1384.6 | 1271.1 | 1092.4 | 913.6  | 734.9  | 556.1  | 493.7  | 431.3  | 368.9  | 306.4  |
| 80°    | 1018.6 | 953.4  | 890.9  | 763.3  | 635.6  | 505.1  | 377.4  | 337.6  | 295.1  | 255.4  | 212.8  |
| 82.5°  | 632.7  | 629.9  | 624.2  | 536.3  | 448.3  | 360.3  | 272.4  | 238.3  | 207.1  | 173.1  | 139.0  |
| 85°    | 289.4  | 337.6  | 383.0  | 334.8  | 286.6  | 238.3  | 190.1  | 167.4  | 144.7  | 119.2  | 96.5   |
| 87.5°  | 90.8   | 110.7  | 127.7  | 122.0  | 113.5  | 107.8  | 99.3   | 85.1   | 70.9   | 56.7   | 42.6   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 25° |
|--------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 27.5°  | 30°    | 32.5°  | 35°    | 37.5°  | 40°    | 42.5°  | 45°    | 47.5°  | 50°    | 52.5°  |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 |
| 2.5°   | 1986.2 | 1977.6 | 1966.3 | 1955.0 | 1940.8 | 1929.4 | 1915.2 | 1901.0 | 1898.2 | 1892.5 | 1889.7 |
| 5°     | 1710.9 | 1693.9 | 1674.1 | 1657.0 | 1640.0 | 1620.1 | 1603.1 | 1583.3 | 1569.1 | 1552.0 | 1537.9 |
| 7.5°   | 1469.8 | 1441.4 | 1410.2 | 1379.0 | 1350.6 | 1322.2 | 1291.0 | 1262.6 | 1248.4 | 1234.3 | 1220.1 |
| 10°    | 1276.8 | 1248.4 | 1222.9 | 1194.5 | 1174.7 | 1157.6 | 1137.8 | 1117.9 | 1100.9 | 1083.9 | 1066.9 |
| 12.5°  | 1180.3 | 1160.5 | 1140.6 | 1120.8 | 1098.1 | 1078.2 | 1055.5 | 1032.8 | 1012.9 | 995.9  | 976.1  |
| 15°    | 1120.8 | 1092.4 | 1061.2 | 1032.8 | 1001.6 | 973.2  | 942.0  | 910.8  | 888.1  | 868.2  | 845.5  |
| 17.5°  | 1049.8 | 1007.3 | 967.5  | 925.0  | 890.9  | 856.9  | 820.0  | 786.0  | 760.4  | 732.0  | 706.5  |
| 20°    | 970.4  | 922.1  | 871.1  | 822.8  | 783.1  | 746.2  | 706.5  | 666.8  | 638.4  | 607.2  | 578.8  |
| 22.5°  | 902.3  | 839.9  | 774.6  | 709.3  | 666.8  | 624.2  | 578.8  | 536.3  | 510.7  | 482.4  | 456.8  |
| 25°    | 828.5  | 760.4  | 689.5  | 618.5  | 576.0  | 530.6  | 488.0  | 442.6  | 422.8  | 405.7  | 385.9  |
| 27.5°  | 788.8  | 720.7  | 649.8  | 581.7  | 541.9  | 499.4  | 459.7  | 417.1  | 402.9  | 385.9  | 371.7  |
| 30°    | 709.3  | 644.1  | 576.0  | 507.9  | 479.5  | 454.0  | 425.6  | 397.2  | 391.6  | 388.7  | 383.0  |
| 32.5°  | 638.4  | 570.3  | 502.2  | 434.1  | 408.6  | 383.0  | 357.5  | 332.0  | 329.1  | 323.5  | 320.6  |
| 35°    | 601.5  | 536.3  | 468.2  | 402.9  | 380.2  | 354.7  | 332.0  | 306.4  | 300.8  | 292.2  | 286.6  |
| 37.5°  | 593.0  | 524.9  | 454.0  | 385.9  | 363.2  | 340.5  | 314.9  | 292.2  | 286.6  | 280.9  | 275.2  |
| 40°    | 570.3  | 505.1  | 442.6  | 377.4  | 354.7  | 332.0  | 306.4  | 283.7  | 278.1  | 272.4  | 266.7  |
| 42.5°  | 553.3  | 490.9  | 425.6  | 360.3  | 340.5  | 320.6  | 297.9  | 278.1  | 272.4  | 266.7  | 258.2  |
| 45°    | 539.1  | 473.8  | 405.7  | 340.5  | 326.3  | 312.1  | 295.1  | 280.9  | 275.2  | 266.7  | 261.0  |
| 47.5°  | 516.4  | 454.0  | 388.7  | 323.5  | 309.3  | 297.9  | 283.7  | 269.6  | 263.9  | 258.2  | 252.5  |
| 50°    | 499.4  | 434.1  | 368.9  | 303.6  | 292.2  | 280.9  | 269.6  | 258.2  | 258.2  | 261.0  | 261.0  |
| 52.5°  | 476.7  | 414.3  | 351.8  | 289.4  | 278.1  | 266.7  | 255.4  | 244.0  | 246.9  | 249.7  | 252.5  |
| 55°    | 456.8  | 397.2  | 334.8  | 272.4  | 261.0  | 249.7  | 235.5  | 224.2  | 227.0  | 229.8  | 232.7  |
| 57.5°  | 448.3  | 385.9  | 323.5  | 261.0  | 249.7  | 235.5  | 224.2  | 210.0  | 210.0  | 210.0  | 210.0  |
| 60°    | 442.6  | 377.4  | 314.9  | 249.7  | 235.5  | 224.2  | 210.0  | 195.8  | 192.9  | 192.9  | 190.1  |
| 62.5°  | 439.8  | 374.5  | 312.1  | 246.9  | 229.8  | 215.6  | 198.6  | 181.6  | 178.8  | 175.9  | 173.1  |
| 65°    | 428.4  | 368.9  | 306.4  | 244.0  | 224.2  | 207.1  | 187.3  | 167.4  | 164.6  | 164.6  | 161.7  |
| 67.5°  | 425.6  | 363.2  | 303.6  | 241.2  | 221.3  | 198.6  | 178.8  | 156.1  | 153.2  | 150.4  | 147.5  |
| 70°    | 402.9  | 349.0  | 292.2  | 235.5  | 212.8  | 192.9  | 170.2  | 147.5  | 144.7  | 139.0  | 136.2  |
| 72.5°  | 374.5  | 326.3  | 275.2  | 224.2  | 201.5  | 178.8  | 156.1  | 133.4  | 130.5  | 127.7  | 122.0  |
| 75°    | 332.0  | 286.6  | 241.2  | 195.8  | 175.9  | 158.9  | 139.0  | 119.2  | 116.3  | 113.5  | 107.8  |
| 77.5°  | 272.4  | 235.5  | 201.5  | 164.6  | 150.4  | 136.2  | 122.0  | 107.8  | 105.0  | 102.1  | 96.5   |
| 80°    | 192.9  | 170.2  | 150.4  | 127.7  | 119.2  | 107.8  | 99.3   | 88.0   | 88.0   | 85.1   | 85.1   |
| 82.5°  | 127.7  | 116.3  | 105.0  | 93.6   | 88.0   | 82.3   | 76.6   | 70.9   | 70.9   | 68.1   | 68.1   |
| 85°    | 90.8   | 85.1   | 76.6   | 70.9   | 68.1   | 62.4   | 59.6   | 53.9   | 53.9   | 53.9   | 53.9   |
| 87.5°  | 42.6   | 42.6   | 39.7   | 39.7   | 36.9   | 36.9   | 34.0   | 31.2   | 31.2   | 31.2   | 31.2   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° | 47.5° | 50° | 52.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 55°    | 57.5°  | 60°    | 62.5°  | 65°    | 67.5°  | 70°    | 72.5°  | 75°    | 77.5°  | 80°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 |
| 2.5°   | 1884.0 | 1875.5 | 1867.0 | 1855.6 | 1847.1 | 1835.8 | 1821.6 | 1810.2 | 1796.1 | 1796.1 | 1793.2 |
| 5°     | 1520.8 | 1512.3 | 1503.8 | 1492.5 | 1483.9 | 1472.6 | 1464.1 | 1452.7 | 1441.4 | 1441.4 | 1438.5 |
| 7.5°   | 1205.9 | 1188.9 | 1171.8 | 1152.0 | 1134.9 | 1123.6 | 1112.3 | 1098.1 | 1086.7 | 1078.2 | 1069.7 |
| 10°    | 1049.8 | 1032.8 | 1012.9 | 995.9  | 976.1  | 961.9  | 947.7  | 930.7  | 916.5  | 905.1  | 893.8  |
| 12.5°  | 956.2  | 936.3  | 916.5  | 896.6  | 876.7  | 856.9  | 839.9  | 820.0  | 800.1  | 786.0  | 771.8  |
| 15°    | 822.8  | 803.0  | 783.1  | 763.3  | 743.4  | 720.7  | 698.0  | 672.5  | 649.8  | 638.4  | 629.9  |
| 17.5°  | 678.1  | 658.3  | 635.6  | 615.7  | 593.0  | 576.0  | 559.0  | 541.9  | 524.9  | 513.6  | 505.1  |
| 20°    | 547.6  | 524.9  | 502.2  | 479.5  | 456.8  | 445.5  | 434.1  | 422.8  | 411.4  | 402.9  | 397.2  |
| 22.5°  | 428.4  | 414.3  | 402.9  | 388.7  | 374.5  | 366.0  | 360.3  | 351.8  | 343.3  | 343.3  | 343.3  |
| 25°    | 366.0  | 357.5  | 351.8  | 343.3  | 334.8  | 332.0  | 329.1  | 323.5  | 320.6  | 317.8  | 317.8  |
| 27.5°  | 354.7  | 346.2  | 337.6  | 329.1  | 320.6  | 317.8  | 314.9  | 309.3  | 306.4  | 306.4  | 306.4  |
| 30°    | 377.4  | 374.5  | 371.7  | 368.9  | 366.0  | 360.3  | 351.8  | 346.2  | 337.6  | 332.0  | 326.3  |
| 32.5°  | 314.9  | 312.1  | 312.1  | 309.3  | 306.4  | 312.1  | 314.9  | 320.6  | 323.5  | 326.3  | 329.1  |
| 35°    | 278.1  | 272.4  | 266.7  | 261.0  | 255.4  | 252.5  | 249.7  | 246.9  | 244.0  | 244.0  | 241.2  |
| 37.5°  | 269.6  | 263.9  | 258.2  | 252.5  | 246.9  | 244.0  | 241.2  | 238.3  | 235.5  | 235.5  | 232.7  |
| 40°    | 261.0  | 255.4  | 252.5  | 246.9  | 241.2  | 238.3  | 235.5  | 229.8  | 227.0  | 224.2  | 224.2  |
| 42.5°  | 252.5  | 249.7  | 244.0  | 241.2  | 235.5  | 232.7  | 229.8  | 224.2  | 221.3  | 218.5  | 215.6  |
| 45°    | 252.5  | 246.9  | 241.2  | 235.5  | 229.8  | 227.0  | 221.3  | 218.5  | 212.8  | 212.8  | 210.0  |
| 47.5°  | 246.9  | 241.2  | 235.5  | 229.8  | 224.2  | 221.3  | 215.6  | 212.8  | 207.1  | 204.3  | 201.5  |
| 50°    | 261.0  | 252.5  | 241.2  | 232.7  | 221.3  | 218.5  | 212.8  | 210.0  | 204.3  | 201.5  | 198.6  |
| 52.5°  | 255.4  | 246.9  | 235.5  | 227.0  | 215.6  | 210.0  | 207.1  | 201.5  | 195.8  | 192.9  | 190.1  |
| 55°    | 235.5  | 227.0  | 221.3  | 212.8  | 204.3  | 198.6  | 192.9  | 187.3  | 181.6  | 178.8  | 178.8  |
| 57.5°  | 210.0  | 207.1  | 204.3  | 201.5  | 198.6  | 192.9  | 187.3  | 178.8  | 173.1  | 170.2  | 167.4  |
| 60°    | 187.3  | 190.1  | 192.9  | 195.8  | 198.6  | 190.1  | 181.6  | 173.1  | 164.6  | 161.7  | 158.9  |
| 62.5°  | 170.2  | 175.9  | 181.6  | 184.4  | 190.1  | 181.6  | 173.1  | 164.6  | 156.1  | 153.2  | 150.4  |
| 65°    | 158.9  | 161.7  | 161.7  | 164.6  | 164.6  | 158.9  | 156.1  | 150.4  | 144.7  | 141.9  | 141.9  |
| 67.5°  | 144.7  | 144.7  | 144.7  | 141.9  | 141.9  | 139.0  | 139.0  | 136.2  | 133.4  | 130.5  | 130.5  |
| 70°    | 130.5  | 130.5  | 130.5  | 127.7  | 127.7  | 124.8  | 124.8  | 122.0  | 119.2  | 119.2  | 116.3  |
| 72.5°  | 119.2  | 119.2  | 116.3  | 116.3  | 113.5  | 113.5  | 113.5  | 110.7  | 110.7  | 107.8  | 107.8  |
| 75°    | 105.0  | 105.0  | 102.1  | 102.1  | 99.3   | 99.3   | 99.3   | 96.5   | 96.5   | 96.5   | 93.6   |
| 77.5°  | 93.6   | 93.6   | 90.8   | 90.8   | 88.0   | 88.0   | 88.0   | 85.1   | 85.1   | 82.3   | 82.3   |
| 80°    | 82.3   | 82.3   | 79.4   | 79.4   | 76.6   | 76.6   | 73.8   | 73.8   | 70.9   | 70.9   | 68.1   |
| 82.5°  | 65.3   | 65.3   | 65.3   | 65.3   | 65.3   | 62.4   | 62.4   | 59.6   | 56.7   | 56.7   | 53.9   |
| 85°    | 53.9   | 53.9   | 53.9   | 51.1   | 51.1   | 51.1   | 48.2   | 48.2   | 45.4   | 42.6   | 42.6   |
| 87.5°  | 31.2   | 31.2   | 31.2   | 28.4   | 28.4   | 28.4   | 28.4   | 28.4   | 28.4   | 28.4   | 25.5   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° | 75° | 77.5° | 80° |
|--------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |

REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 82.5°  | 85°    | 87.5°  | 90°    | 92.5°  | 95°    | 97.5°  | 100°   | 102.5° | 105°   | 107.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 |
| 2.5°   | 1793.2 | 1790.4 | 1779.0 | 1767.7 | 1779.0 | 1790.4 | 1790.4 | 1790.4 | 1787.5 | 1787.5 | 1787.5 |
| 5°     | 1438.5 | 1435.7 | 1430.0 | 1424.4 | 1424.4 | 1421.5 | 1427.2 | 1432.9 | 1438.5 | 1444.2 | 1449.9 |
| 7.5°   | 1058.3 | 1049.8 | 1041.3 | 1032.8 | 1038.5 | 1041.3 | 1049.8 | 1055.5 | 1064.0 | 1069.7 | 1083.9 |
| 10°    | 882.4  | 871.1  | 862.6  | 854.0  | 848.4  | 842.7  | 837.0  | 834.2  | 828.5  | 822.8  | 828.5  |
| 12.5°  | 754.7  | 740.6  | 726.4  | 709.3  | 706.5  | 703.7  | 698.0  | 692.3  | 686.6  | 681.0  | 678.1  |
| 15°    | 618.5  | 607.2  | 601.5  | 593.0  | 581.7  | 570.3  | 564.6  | 561.8  | 556.1  | 550.5  | 547.6  |
| 17.5°  | 493.7  | 482.4  | 473.8  | 465.3  | 462.5  | 456.8  | 456.8  | 456.8  | 456.8  | 456.8  | 456.8  |
| 20°    | 388.7  | 380.2  | 380.2  | 377.4  | 377.4  | 374.5  | 377.4  | 380.2  | 380.2  | 383.0  | 385.9  |
| 22.5°  | 340.5  | 340.5  | 337.6  | 334.8  | 337.6  | 337.6  | 340.5  | 343.3  | 346.2  | 349.0  | 351.8  |
| 25°    | 314.9  | 312.1  | 314.9  | 317.8  | 317.8  | 317.8  | 320.6  | 320.6  | 323.5  | 323.5  | 323.5  |
| 27.5°  | 303.6  | 303.6  | 306.4  | 306.4  | 309.3  | 309.3  | 309.3  | 306.4  | 306.4  | 303.6  | 303.6  |
| 30°    | 320.6  | 314.9  | 314.9  | 314.9  | 312.1  | 309.3  | 306.4  | 306.4  | 303.6  | 300.8  | 297.9  |
| 32.5°  | 332.0  | 334.8  | 332.0  | 326.3  | 323.5  | 317.8  | 314.9  | 309.3  | 306.4  | 300.8  | 295.1  |
| 35°    | 241.2  | 238.3  | 244.0  | 246.9  | 249.7  | 252.5  | 255.4  | 258.2  | 258.2  | 261.0  | 261.0  |
| 37.5°  | 232.7  | 229.8  | 229.8  | 227.0  | 227.0  | 227.0  | 227.0  | 227.0  | 224.2  | 224.2  | 227.0  |
| 40°    | 221.3  | 218.5  | 218.5  | 215.6  | 215.6  | 212.8  | 212.8  | 212.8  | 212.8  | 212.8  | 212.8  |
| 42.5°  | 212.8  | 210.0  | 210.0  | 210.0  | 210.0  | 207.1  | 207.1  | 204.3  | 204.3  | 201.5  | 201.5  |
| 45°    | 210.0  | 207.1  | 204.3  | 201.5  | 201.5  | 198.6  | 198.6  | 198.6  | 195.8  | 195.8  | 195.8  |
| 47.5°  | 198.6  | 195.8  | 195.8  | 192.9  | 192.9  | 190.1  | 190.1  | 190.1  | 187.3  | 187.3  | 187.3  |
| 50°    | 192.9  | 190.1  | 190.1  | 187.3  | 187.3  | 184.4  | 184.4  | 184.4  | 181.6  | 181.6  | 181.6  |
| 52.5°  | 184.4  | 181.6  | 181.6  | 181.6  | 178.8  | 175.9  | 175.9  | 175.9  | 173.1  | 173.1  | 173.1  |
| 55°    | 175.9  | 173.1  | 173.1  | 173.1  | 170.2  | 167.4  | 167.4  | 167.4  | 164.6  | 164.6  | 164.6  |
| 57.5°  | 164.6  | 161.7  | 161.7  | 158.9  | 158.9  | 158.9  | 158.9  | 158.9  | 156.1  | 156.1  | 156.1  |
| 60°    | 156.1  | 153.2  | 153.2  | 150.4  | 150.4  | 147.5  | 147.5  | 147.5  | 147.5  | 147.5  | 147.5  |
| 62.5°  | 147.5  | 144.7  | 141.9  | 139.0  | 141.9  | 141.9  | 141.9  | 141.9  | 139.0  | 139.0  | 139.0  |
| 65°    | 139.0  | 136.2  | 133.4  | 130.5  | 130.5  | 130.5  | 130.5  | 130.5  | 130.5  | 130.5  | 130.5  |
| 67.5°  | 127.7  | 124.8  | 122.0  | 119.2  | 122.0  | 122.0  | 122.0  | 122.0  | 122.0  | 122.0  | 122.0  |
| 70°    | 116.3  | 113.5  | 113.5  | 110.7  | 110.7  | 107.8  | 107.8  | 110.7  | 110.7  | 110.7  | 110.7  |
| 72.5°  | 105.0  | 102.1  | 102.1  | 99.3   | 99.3   | 99.3   | 99.3   | 99.3   | 99.3   | 99.3   | 99.3   |
| 75°    | 93.6   | 90.8   | 90.8   | 88.0   | 88.0   | 88.0   | 88.0   | 88.0   | 88.0   | 88.0   | 88.0   |
| 77.5°  | 79.4   | 76.6   | 76.6   | 76.6   | 76.6   | 76.6   | 76.6   | 79.4   | 79.4   | 79.4   | 79.4   |
| 80°    | 68.1   | 65.3   | 65.3   | 65.3   | 65.3   | 65.3   | 65.3   | 65.3   | 65.3   | 65.3   | 65.3   |
| 82.5°  | 53.9   | 51.1   | 51.1   | 51.1   | 51.1   | 51.1   | 51.1   | 51.1   | 51.1   | 51.1   | 51.1   |
| 85°    | 39.7   | 36.9   | 36.9   | 36.9   | 39.7   | 39.7   | 39.7   | 39.7   | 39.7   | 39.7   | 39.7   |
| 87.5°  | 25.5   | 22.7   | 22.7   | 22.7   | 25.5   | 25.5   | 25.5   | 25.5   | 22.7   | 22.7   | 22.7   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° | 92.5° | 95° | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|------|--------|------|--------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 110°   | 112.5° | 115°   | 117.5° | 120°   | 122.5° | 125°   | 127.5° | 130°   | 132.5° | 135°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 |
| 2.5°   | 1787.5 | 1787.5 | 1787.5 | 1784.7 | 1781.9 | 1779.0 | 1776.2 | 1784.7 | 1790.4 | 1798.9 | 1804.6 |
| 5°     | 1452.7 | 1458.4 | 1461.2 | 1469.8 | 1478.3 | 1486.8 | 1495.3 | 1501.0 | 1506.6 | 1509.5 | 1515.2 |
| 7.5°   | 1095.2 | 1109.4 | 1120.8 | 1132.1 | 1143.5 | 1152.0 | 1163.3 | 1171.8 | 1180.3 | 1188.9 | 1197.4 |
| 10°    | 831.4  | 837.0  | 839.9  | 851.2  | 859.7  | 871.1  | 879.6  | 888.1  | 896.6  | 902.3  | 910.8  |
| 12.5°  | 675.3  | 669.6  | 666.8  | 666.8  | 666.8  | 666.8  | 666.8  | 672.5  | 678.1  | 683.8  | 689.5  |
| 15°    | 544.8  | 541.9  | 539.1  | 536.3  | 533.4  | 527.8  | 524.9  | 530.6  | 536.3  | 541.9  | 547.6  |
| 17.5°  | 456.8  | 456.8  | 456.8  | 454.0  | 451.1  | 448.3  | 445.5  | 448.3  | 451.1  | 451.1  | 454.0  |
| 20°    | 391.6  | 394.4  | 397.2  | 400.1  | 400.1  | 402.9  | 402.9  | 405.7  | 408.6  | 408.6  | 411.4  |
| 22.5°  | 351.8  | 354.7  | 354.7  | 354.7  | 357.5  | 357.5  | 357.5  | 360.3  | 363.2  | 366.0  | 368.9  |
| 25°    | 320.6  | 320.6  | 317.8  | 317.8  | 320.6  | 320.6  | 320.6  | 320.6  | 323.5  | 323.5  | 323.5  |
| 27.5°  | 303.6  | 300.8  | 300.8  | 300.8  | 300.8  | 297.9  | 297.9  | 297.9  | 297.9  | 297.9  | 297.9  |
| 30°    | 295.1  | 292.2  | 289.4  | 286.6  | 286.6  | 283.7  | 280.9  | 280.9  | 280.9  | 280.9  | 280.9  |
| 32.5°  | 292.2  | 286.6  | 280.9  | 278.1  | 278.1  | 275.2  | 272.4  | 269.6  | 269.6  | 266.7  | 263.9  |
| 35°    | 261.0  | 258.2  | 258.2  | 255.4  | 252.5  | 249.7  | 246.9  | 246.9  | 246.9  | 244.0  | 244.0  |
| 37.5°  | 227.0  | 229.8  | 229.8  | 229.8  | 232.7  | 232.7  | 232.7  | 232.7  | 235.5  | 235.5  | 235.5  |
| 40°    | 212.8  | 212.8  | 212.8  | 215.6  | 218.5  | 218.5  | 221.3  | 221.3  | 224.2  | 224.2  | 224.2  |
| 42.5°  | 201.5  | 198.6  | 198.6  | 201.5  | 201.5  | 204.3  | 204.3  | 207.1  | 210.0  | 210.0  | 212.8  |
| 45°    | 195.8  | 192.9  | 192.9  | 192.9  | 192.9  | 190.1  | 190.1  | 192.9  | 195.8  | 198.6  | 201.5  |
| 47.5°  | 184.4  | 184.4  | 181.6  | 181.6  | 181.6  | 181.6  | 181.6  | 181.6  | 184.4  | 184.4  | 184.4  |
| 50°    | 178.8  | 178.8  | 175.9  | 175.9  | 175.9  | 175.9  | 175.9  | 175.9  | 175.9  | 175.9  | 175.9  |
| 52.5°  | 173.1  | 170.2  | 170.2  | 170.2  | 170.2  | 167.4  | 167.4  | 167.4  | 167.4  | 167.4  | 167.4  |
| 55°    | 164.6  | 161.7  | 161.7  | 161.7  | 161.7  | 161.7  | 161.7  | 161.7  | 164.6  | 164.6  | 164.6  |
| 57.5°  | 156.1  | 153.2  | 153.2  | 153.2  | 156.1  | 156.1  | 156.1  | 156.1  | 158.9  | 158.9  | 158.9  |
| 60°    | 147.5  | 147.5  | 147.5  | 147.5  | 147.5  | 147.5  | 147.5  | 150.4  | 150.4  | 153.2  | 153.2  |
| 62.5°  | 139.0  | 139.0  | 139.0  | 139.0  | 141.9  | 141.9  | 141.9  | 141.9  | 144.7  | 144.7  | 144.7  |
| 65°    | 130.5  | 130.5  | 130.5  | 130.5  | 133.4  | 133.4  | 133.4  | 133.4  | 133.4  | 133.4  | 133.4  |
| 67.5°  | 122.0  | 122.0  | 122.0  | 122.0  | 122.0  | 122.0  | 122.0  | 124.8  | 124.8  | 127.7  | 127.7  |
| 70°    | 110.7  | 107.8  | 107.8  | 110.7  | 110.7  | 113.5  | 113.5  | 116.3  | 116.3  | 119.2  | 119.2  |
| 72.5°  | 99.3   | 99.3   | 99.3   | 99.3   | 99.3   | 99.3   | 99.3   | 102.1  | 105.0  | 105.0  | 107.8  |
| 75°    | 88.0   | 88.0   | 88.0   | 88.0   | 90.8   | 90.8   | 90.8   | 93.6   | 93.6   | 96.5   | 96.5   |
| 77.5°  | 79.4   | 76.6   | 76.6   | 76.6   | 79.4   | 79.4   | 79.4   | 82.3   | 82.3   | 85.1   | 85.1   |
| 80°    | 65.3   | 65.3   | 65.3   | 65.3   | 68.1   | 68.1   | 68.1   | 68.1   | 70.9   | 70.9   | 70.9   |
| 82.5°  | 53.9   | 53.9   | 53.9   | 53.9   | 53.9   | 53.9   | 53.9   | 53.9   | 56.7   | 56.7   | 56.7   |
| 85°    | 39.7   | 39.7   | 39.7   | 39.7   | 42.6   | 42.6   | 42.6   | 42.6   | 42.6   | 42.6   | 42.6   |
| 87.5°  | 25.5   | 25.5   | 25.5   | 25.5   | 25.5   | 25.5   | 25.5   | 25.5   | 28.4   | 28.4   | 28.4   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140°   | 142.5° | 145°   | 147.5° | 150°   | 152.5° | 155°   | 157.5° | 160°   | 162.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 |
| 2.5°   | 1804.6 | 1804.6 | 1804.6 | 1804.6 | 1810.2 | 1813.1 | 1818.8 | 1821.6 | 1818.8 | 1815.9 | 1810.2 |
| 5°     | 1518.0 | 1520.8 | 1520.8 | 1523.7 | 1523.7 | 1523.7 | 1523.7 | 1523.7 | 1529.3 | 1535.0 | 1540.7 |
| 7.5°   | 1200.2 | 1203.0 | 1205.9 | 1208.7 | 1208.7 | 1208.7 | 1205.9 | 1205.9 | 1208.7 | 1208.7 | 1211.6 |
| 10°    | 919.3  | 930.7  | 939.2  | 947.7  | 942.0  | 933.5  | 927.8  | 919.3  | 919.3  | 919.3  | 916.5  |
| 12.5°  | 695.2  | 698.0  | 703.7  | 706.5  | 703.7  | 703.7  | 700.8  | 698.0  | 700.8  | 706.5  | 709.3  |
| 15°    | 550.5  | 550.5  | 553.3  | 553.3  | 556.1  | 559.0  | 559.0  | 561.8  | 567.5  | 570.3  | 576.0  |
| 17.5°  | 456.8  | 459.7  | 459.7  | 462.5  | 462.5  | 465.3  | 465.3  | 465.3  | 471.0  | 476.7  | 485.2  |
| 20°    | 411.4  | 411.4  | 411.4  | 411.4  | 411.4  | 408.6  | 408.6  | 405.7  | 408.6  | 414.3  | 417.1  |
| 22.5°  | 368.9  | 371.7  | 371.7  | 371.7  | 368.9  | 366.0  | 360.3  | 357.5  | 357.5  | 360.3  | 360.3  |
| 25°    | 323.5  | 320.6  | 320.6  | 317.8  | 317.8  | 320.6  | 320.6  | 320.6  | 323.5  | 323.5  | 326.3  |
| 27.5°  | 297.9  | 295.1  | 295.1  | 292.2  | 292.2  | 295.1  | 295.1  | 295.1  | 295.1  | 295.1  | 295.1  |
| 30°    | 278.1  | 278.1  | 275.2  | 272.4  | 275.2  | 275.2  | 278.1  | 278.1  | 280.9  | 280.9  | 283.7  |
| 32.5°  | 263.9  | 261.0  | 261.0  | 258.2  | 261.0  | 261.0  | 263.9  | 263.9  | 266.7  | 269.6  | 269.6  |
| 35°    | 244.0  | 244.0  | 244.0  | 244.0  | 244.0  | 244.0  | 241.2  | 241.2  | 241.2  | 241.2  | 241.2  |
| 37.5°  | 232.7  | 232.7  | 229.8  | 227.0  | 227.0  | 227.0  | 227.0  | 227.0  | 224.2  | 221.3  | 218.5  |
| 40°    | 224.2  | 221.3  | 221.3  | 218.5  | 215.6  | 215.6  | 212.8  | 210.0  | 210.0  | 207.1  | 207.1  |
| 42.5°  | 212.8  | 210.0  | 210.0  | 207.1  | 204.3  | 204.3  | 201.5  | 198.6  | 198.6  | 198.6  | 195.8  |
| 45°    | 198.6  | 198.6  | 195.8  | 192.9  | 192.9  | 192.9  | 190.1  | 190.1  | 190.1  | 190.1  | 187.3  |
| 47.5°  | 184.4  | 184.4  | 181.6  | 181.6  | 181.6  | 181.6  | 178.8  | 178.8  | 178.8  | 178.8  | 178.8  |
| 50°    | 175.9  | 175.9  | 175.9  | 175.9  | 175.9  | 175.9  | 173.1  | 173.1  | 173.1  | 173.1  | 173.1  |
| 52.5°  | 167.4  | 167.4  | 167.4  | 167.4  | 167.4  | 167.4  | 167.4  | 167.4  | 167.4  | 167.4  | 167.4  |
| 55°    | 164.6  | 164.6  | 164.6  | 164.6  | 164.6  | 164.6  | 161.7  | 161.7  | 161.7  | 164.6  | 164.6  |
| 57.5°  | 158.9  | 158.9  | 156.1  | 156.1  | 156.1  | 156.1  | 156.1  | 156.1  | 156.1  | 156.1  | 156.1  |
| 60°    | 153.2  | 153.2  | 153.2  | 153.2  | 153.2  | 153.2  | 153.2  | 153.2  | 153.2  | 153.2  | 153.2  |
| 62.5°  | 144.7  | 144.7  | 144.7  | 144.7  | 144.7  | 147.5  | 147.5  | 147.5  | 147.5  | 147.5  | 144.7  |
| 65°    | 133.4  | 136.2  | 136.2  | 136.2  | 136.2  | 136.2  | 136.2  | 136.2  | 136.2  | 136.2  | 136.2  |
| 67.5°  | 127.7  | 127.7  | 127.7  | 127.7  | 127.7  | 127.7  | 127.7  | 127.7  | 127.7  | 127.7  | 127.7  |
| 70°    | 119.2  | 119.2  | 116.3  | 116.3  | 116.3  | 119.2  | 119.2  | 119.2  | 119.2  | 119.2  | 119.2  |
| 72.5°  | 107.8  | 107.8  | 107.8  | 107.8  | 107.8  | 107.8  | 107.8  | 107.8  | 107.8  | 110.7  | 110.7  |
| 75°    | 96.5   | 96.5   | 96.5   | 96.5   | 96.5   | 96.5   | 96.5   | 96.5   | 96.5   | 96.5   | 96.5   |
| 77.5°  | 85.1   | 85.1   | 82.3   | 82.3   | 82.3   | 85.1   | 85.1   | 85.1   | 85.1   | 88.0   | 88.0   |
| 80°    | 70.9   | 70.9   | 70.9   | 70.9   | 70.9   | 70.9   | 70.9   | 70.9   | 70.9   | 73.8   | 73.8   |
| 82.5°  | 56.7   | 56.7   | 56.7   | 56.7   | 56.7   | 56.7   | 56.7   | 56.7   | 56.7   | 59.6   | 59.6   |
| 85°    | 42.6   | 45.4   | 45.4   | 45.4   | 45.4   | 45.4   | 45.4   | 45.4   | 45.4   | 48.2   | 48.2   |
| 87.5°  | 28.4   | 28.4   | 28.4   | 28.4   | 28.4   | 28.4   | 25.5   | 25.5   | 25.5   | 25.5   | 22.7   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 165°   | 167.5° | 170°   | 172.5° | 175°   | 177.5° | 180°   | 182.5° | 185°   | 187.5° | 190°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 |
| 2.5°   | 1807.4 | 1810.2 | 1813.1 | 1813.1 | 1815.9 | 1818.8 | 1818.8 | 1830.1 | 1841.5 | 1847.1 | 1852.8 |
| 5°     | 1546.4 | 1543.5 | 1543.5 | 1540.7 | 1537.9 | 1546.4 | 1554.9 | 1571.9 | 1588.9 | 1591.8 | 1597.4 |
| 7.5°   | 1211.6 | 1214.4 | 1217.2 | 1217.2 | 1220.1 | 1211.6 | 1200.2 | 1203.0 | 1205.9 | 1220.1 | 1231.4 |
| 10°    | 916.5  | 919.3  | 922.1  | 922.1  | 925.0  | 922.1  | 916.5  | 925.0  | 933.5  | 944.8  | 959.0  |
| 12.5°  | 712.2  | 720.7  | 729.2  | 734.9  | 743.4  | 749.1  | 751.9  | 763.3  | 771.8  | 786.0  | 800.1  |
| 15°    | 581.7  | 587.3  | 593.0  | 598.7  | 604.4  | 610.0  | 615.7  | 627.1  | 638.4  | 655.4  | 672.5  |
| 17.5°  | 490.9  | 490.9  | 493.7  | 493.7  | 493.7  | 499.4  | 505.1  | 510.7  | 513.6  | 530.6  | 547.6  |
| 20°    | 419.9  | 417.1  | 414.3  | 411.4  | 408.6  | 414.3  | 417.1  | 419.9  | 422.8  | 434.1  | 442.6  |
| 22.5°  | 360.3  | 360.3  | 363.2  | 363.2  | 363.2  | 360.3  | 354.7  | 357.5  | 357.5  | 363.2  | 371.7  |
| 25°    | 326.3  | 326.3  | 326.3  | 323.5  | 323.5  | 326.3  | 329.1  | 329.1  | 326.3  | 329.1  | 332.0  |
| 27.5°  | 295.1  | 297.9  | 297.9  | 300.8  | 300.8  | 303.6  | 303.6  | 303.6  | 303.6  | 306.4  | 309.3  |
| 30°    | 283.7  | 283.7  | 286.6  | 286.6  | 286.6  | 289.4  | 292.2  | 292.2  | 292.2  | 295.1  | 300.8  |
| 32.5°  | 272.4  | 275.2  | 278.1  | 280.9  | 283.7  | 286.6  | 286.6  | 289.4  | 289.4  | 292.2  | 295.1  |
| 35°    | 241.2  | 238.3  | 238.3  | 235.5  | 232.7  | 232.7  | 232.7  | 232.7  | 229.8  | 232.7  | 232.7  |
| 37.5°  | 215.6  | 215.6  | 215.6  | 212.8  | 212.8  | 215.6  | 215.6  | 215.6  | 215.6  | 218.5  | 218.5  |
| 40°    | 204.3  | 204.3  | 204.3  | 204.3  | 204.3  | 204.3  | 204.3  | 207.1  | 207.1  | 210.0  | 212.8  |
| 42.5°  | 195.8  | 195.8  | 195.8  | 195.8  | 195.8  | 198.6  | 198.6  | 198.6  | 198.6  | 201.5  | 201.5  |
| 45°    | 187.3  | 187.3  | 187.3  | 187.3  | 187.3  | 187.3  | 187.3  | 190.1  | 190.1  | 192.9  | 195.8  |
| 47.5°  | 178.8  | 178.8  | 178.8  | 178.8  | 178.8  | 181.6  | 184.4  | 184.4  | 184.4  | 187.3  | 187.3  |
| 50°    | 173.1  | 173.1  | 173.1  | 173.1  | 173.1  | 175.9  | 175.9  | 178.8  | 178.8  | 181.6  | 184.4  |
| 52.5°  | 167.4  | 167.4  | 167.4  | 167.4  | 167.4  | 170.2  | 170.2  | 173.1  | 173.1  | 175.9  | 178.8  |
| 55°    | 164.6  | 164.6  | 164.6  | 161.7  | 161.7  | 164.6  | 164.6  | 167.4  | 167.4  | 170.2  | 170.2  |
| 57.5°  | 156.1  | 156.1  | 156.1  | 156.1  | 156.1  | 156.1  | 156.1  | 158.9  | 158.9  | 161.7  | 164.6  |
| 60°    | 153.2  | 153.2  | 150.4  | 150.4  | 147.5  | 150.4  | 150.4  | 153.2  | 153.2  | 156.1  | 156.1  |
| 62.5°  | 144.7  | 144.7  | 144.7  | 141.9  | 141.9  | 144.7  | 144.7  | 144.7  | 144.7  | 147.5  | 150.4  |
| 65°    | 136.2  | 136.2  | 136.2  | 133.4  | 133.4  | 136.2  | 136.2  | 136.2  | 136.2  | 139.0  | 141.9  |
| 67.5°  | 127.7  | 127.7  | 127.7  | 124.8  | 124.8  | 124.8  | 124.8  | 127.7  | 127.7  | 130.5  | 133.4  |
| 70°    | 119.2  | 119.2  | 119.2  | 116.3  | 116.3  | 116.3  | 113.5  | 116.3  | 119.2  | 122.0  | 122.0  |
| 72.5°  | 110.7  | 110.7  | 110.7  | 107.8  | 107.8  | 107.8  | 105.0  | 107.8  | 107.8  | 110.7  | 110.7  |
| 75°    | 96.5   | 96.5   | 96.5   | 96.5   | 96.5   | 96.5   | 93.6   | 93.6   | 93.6   | 96.5   | 96.5   |
| 77.5°  | 88.0   | 88.0   | 88.0   | 85.1   | 85.1   | 85.1   | 82.3   | 82.3   | 82.3   | 85.1   | 85.1   |
| 80°    | 73.8   | 73.8   | 73.8   | 70.9   | 70.9   | 70.9   | 68.1   | 68.1   | 68.1   | 70.9   | 70.9   |
| 82.5°  | 59.6   | 59.6   | 59.6   | 56.7   | 56.7   | 56.7   | 53.9   | 53.9   | 53.9   | 56.7   | 56.7   |
| 85°    | 48.2   | 48.2   | 48.2   | 48.2   | 48.2   | 48.2   | 45.4   | 45.4   | 45.4   | 48.2   | 51.1   |
| 87.5°  | 22.7   | 22.7   | 25.5   | 25.5   | 25.5   | 25.5   | 22.7   | 22.7   | 19.9   | 19.9   | 22.7   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° | 190° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195°   | 197.5° | 200°   | 202.5° | 205°   | 207.5° | 210°   | 212.5° | 215°   | 217.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 |
| 2.5°   | 1858.5 | 1864.2 | 1878.3 | 1889.7 | 1903.9 | 1915.2 | 1923.7 | 1935.1 | 1943.6 | 1952.1 | 1957.8 |
| 5°     | 1600.3 | 1603.1 | 1617.3 | 1631.5 | 1642.8 | 1657.0 | 1676.9 | 1696.7 | 1716.6 | 1736.5 | 1750.7 |
| 7.5°   | 1245.6 | 1257.0 | 1274.0 | 1293.8 | 1310.9 | 1327.9 | 1347.8 | 1370.5 | 1390.3 | 1410.2 | 1430.0 |
| 10°    | 970.4  | 981.7  | 998.8  | 1015.8 | 1030.0 | 1047.0 | 1069.7 | 1092.4 | 1115.1 | 1137.8 | 1160.5 |
| 12.5°  | 814.3  | 828.5  | 848.4  | 868.2  | 885.3  | 905.1  | 933.5  | 959.0  | 987.4  | 1012.9 | 1041.3 |
| 15°    | 686.6  | 703.7  | 729.2  | 757.6  | 783.1  | 808.7  | 837.0  | 865.4  | 890.9  | 919.3  | 947.7  |
| 17.5°  | 564.6  | 581.7  | 604.4  | 629.9  | 652.6  | 675.3  | 709.3  | 740.6  | 774.6  | 805.8  | 837.0  |
| 20°    | 454.0  | 462.5  | 485.2  | 507.9  | 530.6  | 553.3  | 578.8  | 604.4  | 629.9  | 655.4  | 695.2  |
| 22.5°  | 377.4  | 383.0  | 394.4  | 402.9  | 414.3  | 422.8  | 448.3  | 473.8  | 496.5  | 522.1  | 559.0  |
| 25°    | 332.0  | 334.8  | 343.3  | 349.0  | 357.5  | 363.2  | 380.2  | 394.4  | 411.4  | 425.6  | 459.7  |
| 27.5°  | 309.3  | 312.1  | 314.9  | 317.8  | 320.6  | 323.5  | 334.8  | 346.2  | 354.7  | 366.0  | 397.2  |
| 30°    | 303.6  | 306.4  | 314.9  | 320.6  | 329.1  | 334.8  | 340.5  | 346.2  | 351.8  | 357.5  | 377.4  |
| 32.5°  | 297.9  | 300.8  | 300.8  | 297.9  | 297.9  | 295.1  | 300.8  | 303.6  | 309.3  | 312.1  | 329.1  |
| 35°    | 235.5  | 235.5  | 238.3  | 241.2  | 244.0  | 246.9  | 255.4  | 261.0  | 269.6  | 275.2  | 289.4  |
| 37.5°  | 221.3  | 221.3  | 224.2  | 229.8  | 232.7  | 235.5  | 241.2  | 246.9  | 252.5  | 258.2  | 272.4  |
| 40°    | 212.8  | 215.6  | 218.5  | 221.3  | 224.2  | 227.0  | 232.7  | 235.5  | 241.2  | 244.0  | 255.4  |
| 42.5°  | 204.3  | 204.3  | 207.1  | 212.8  | 215.6  | 218.5  | 224.2  | 227.0  | 232.7  | 235.5  | 246.9  |
| 45°    | 198.6  | 201.5  | 204.3  | 207.1  | 207.1  | 210.0  | 215.6  | 221.3  | 224.2  | 229.8  | 241.2  |
| 47.5°  | 190.1  | 190.1  | 195.8  | 198.6  | 204.3  | 207.1  | 212.8  | 215.6  | 221.3  | 224.2  | 235.5  |
| 50°    | 184.4  | 187.3  | 192.9  | 195.8  | 201.5  | 204.3  | 212.8  | 218.5  | 227.0  | 232.7  | 238.3  |
| 52.5°  | 178.8  | 181.6  | 187.3  | 190.1  | 195.8  | 198.6  | 210.0  | 221.3  | 229.8  | 241.2  | 241.2  |
| 55°    | 173.1  | 173.1  | 178.8  | 187.3  | 192.9  | 198.6  | 204.3  | 212.8  | 218.5  | 224.2  | 224.2  |
| 57.5°  | 164.6  | 167.4  | 173.1  | 181.6  | 187.3  | 192.9  | 198.6  | 204.3  | 207.1  | 212.8  | 210.0  |
| 60°    | 158.9  | 158.9  | 167.4  | 175.9  | 184.4  | 192.9  | 192.9  | 192.9  | 190.1  | 190.1  | 190.1  |
| 62.5°  | 150.4  | 153.2  | 164.6  | 178.8  | 190.1  | 201.5  | 192.9  | 184.4  | 175.9  | 167.4  | 170.2  |
| 65°    | 144.7  | 147.5  | 153.2  | 161.7  | 167.4  | 173.1  | 167.4  | 164.6  | 158.9  | 153.2  | 156.1  |
| 67.5°  | 133.4  | 136.2  | 139.0  | 139.0  | 141.9  | 141.9  | 141.9  | 141.9  | 141.9  | 141.9  | 144.7  |
| 70°    | 124.8  | 124.8  | 124.8  | 127.7  | 127.7  | 127.7  | 127.7  | 127.7  | 127.7  | 127.7  | 130.5  |
| 72.5°  | 113.5  | 113.5  | 113.5  | 113.5  | 113.5  | 113.5  | 113.5  | 113.5  | 113.5  | 113.5  | 116.3  |
| 75°    | 99.3   | 99.3   | 99.3   | 99.3   | 99.3   | 99.3   | 99.3   | 99.3   | 99.3   | 99.3   | 102.1  |
| 77.5°  | 88.0   | 88.0   | 88.0   | 88.0   | 88.0   | 88.0   | 88.0   | 88.0   | 85.1   | 85.1   | 88.0   |
| 80°    | 73.8   | 73.8   | 73.8   | 73.8   | 70.9   | 70.9   | 70.9   | 70.9   | 70.9   | 70.9   | 73.8   |
| 82.5°  | 59.6   | 59.6   | 59.6   | 59.6   | 56.7   | 56.7   | 56.7   | 56.7   | 53.9   | 53.9   | 56.7   |
| 85°    | 53.9   | 56.7   | 56.7   | 59.6   | 59.6   | 59.6   | 56.7   | 53.9   | 51.1   | 48.2   | 48.2   |
| 87.5°  | 22.7   | 22.7   | 22.7   | 22.7   | 19.9   | 19.9   | 19.9   | 19.9   | 19.9   | 19.9   | 19.9   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° | 217.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 220°   | 222.5° | 225°   | 227.5° | 230°   | 232.5° | 235°   | 237.5° | 240°   | 242.5° | 245°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 |
| 2.5°   | 1966.3 | 1972.0 | 1977.6 | 1986.2 | 1997.5 | 2006.0 | 2014.5 | 2031.6 | 2051.4 | 2068.4 | 2085.5 |
| 5°     | 1764.8 | 1779.0 | 1793.2 | 1810.2 | 1827.3 | 1841.5 | 1858.5 | 1892.5 | 1926.6 | 1957.8 | 1991.8 |
| 7.5°   | 1447.1 | 1466.9 | 1483.9 | 1512.3 | 1537.9 | 1566.2 | 1591.8 | 1634.3 | 1674.1 | 1716.6 | 1756.3 |
| 10°    | 1183.2 | 1205.9 | 1228.6 | 1265.5 | 1305.2 | 1342.1 | 1379.0 | 1413.0 | 1449.9 | 1483.9 | 1518.0 |
| 12.5°  | 1069.7 | 1095.2 | 1123.6 | 1146.3 | 1171.8 | 1194.5 | 1217.2 | 1257.0 | 1296.7 | 1336.4 | 1376.1 |
| 15°    | 976.1  | 1004.4 | 1032.8 | 1061.2 | 1086.7 | 1115.1 | 1140.6 | 1174.7 | 1211.6 | 1245.6 | 1279.7 |
| 17.5°  | 868.2  | 896.6  | 927.8  | 959.0  | 990.2  | 1021.5 | 1052.7 | 1100.9 | 1149.1 | 1194.5 | 1242.8 |
| 20°    | 732.0  | 771.8  | 808.7  | 851.2  | 893.8  | 936.3  | 978.9  | 1030.0 | 1081.0 | 1129.3 | 1180.3 |
| 22.5°  | 595.8  | 632.7  | 669.6  | 720.7  | 771.8  | 820.0  | 871.1  | 939.2  | 1004.4 | 1072.5 | 1137.8 |
| 25°    | 496.5  | 530.6  | 564.6  | 621.4  | 675.3  | 732.0  | 786.0  | 868.2  | 947.7  | 1030.0 | 1109.4 |
| 27.5°  | 428.4  | 459.7  | 490.9  | 550.5  | 610.0  | 666.8  | 726.4  | 817.2  | 905.1  | 995.9  | 1083.9 |
| 30°    | 397.2  | 417.1  | 437.0  | 493.7  | 550.5  | 604.4  | 661.1  | 749.1  | 837.0  | 925.0  | 1012.9 |
| 32.5°  | 346.2  | 363.2  | 380.2  | 431.3  | 482.4  | 530.6  | 581.7  | 672.5  | 760.4  | 851.2  | 939.2  |
| 35°    | 306.4  | 320.6  | 334.8  | 383.0  | 428.4  | 476.7  | 522.1  | 612.9  | 703.7  | 794.5  | 885.3  |
| 37.5°  | 283.7  | 297.9  | 309.3  | 351.8  | 397.2  | 439.8  | 482.4  | 573.1  | 661.1  | 751.9  | 839.9  |
| 40°    | 266.7  | 275.2  | 286.6  | 329.1  | 368.9  | 411.4  | 451.1  | 533.4  | 618.5  | 700.8  | 783.1  |
| 42.5°  | 255.4  | 266.7  | 275.2  | 312.1  | 351.8  | 388.7  | 425.6  | 505.1  | 584.5  | 661.1  | 740.6  |
| 45°    | 252.5  | 263.9  | 275.2  | 306.4  | 337.6  | 366.0  | 397.2  | 473.8  | 550.5  | 627.1  | 703.7  |
| 47.5°  | 246.9  | 255.4  | 266.7  | 292.2  | 314.9  | 340.5  | 363.2  | 439.8  | 516.4  | 590.2  | 666.8  |
| 50°    | 244.0  | 246.9  | 252.5  | 275.2  | 297.9  | 320.6  | 343.3  | 419.9  | 496.5  | 573.1  | 649.8  |
| 52.5°  | 241.2  | 241.2  | 241.2  | 261.0  | 280.9  | 297.9  | 317.8  | 394.4  | 473.8  | 550.5  | 627.1  |
| 55°    | 224.2  | 221.3  | 221.3  | 241.2  | 258.2  | 278.1  | 295.1  | 371.7  | 448.3  | 522.1  | 598.7  |
| 57.5°  | 207.1  | 204.3  | 201.5  | 218.5  | 235.5  | 252.5  | 269.6  | 346.2  | 425.6  | 502.2  | 578.8  |
| 60°    | 190.1  | 187.3  | 187.3  | 204.3  | 218.5  | 235.5  | 249.7  | 329.1  | 405.7  | 485.2  | 561.8  |
| 62.5°  | 170.2  | 173.1  | 173.1  | 187.3  | 204.3  | 218.5  | 232.7  | 312.1  | 394.4  | 473.8  | 553.3  |
| 65°    | 156.1  | 158.9  | 158.9  | 175.9  | 192.9  | 210.0  | 227.0  | 303.6  | 383.0  | 459.7  | 536.3  |
| 67.5°  | 144.7  | 147.5  | 147.5  | 167.4  | 184.4  | 204.3  | 221.3  | 289.4  | 360.3  | 428.4  | 496.5  |
| 70°    | 133.4  | 133.4  | 136.2  | 156.1  | 175.9  | 195.8  | 215.6  | 275.2  | 334.8  | 391.6  | 451.1  |
| 72.5°  | 119.2  | 122.0  | 124.8  | 144.7  | 161.7  | 181.6  | 198.6  | 252.5  | 306.4  | 360.3  | 414.3  |
| 75°    | 105.0  | 107.8  | 110.7  | 127.7  | 144.7  | 161.7  | 178.8  | 229.8  | 278.1  | 329.1  | 377.4  |
| 77.5°  | 93.6   | 96.5   | 99.3   | 113.5  | 127.7  | 141.9  | 156.1  | 192.9  | 232.7  | 269.6  | 306.4  |
| 80°    | 76.6   | 76.6   | 79.4   | 90.8   | 102.1  | 110.7  | 122.0  | 147.5  | 173.1  | 195.8  | 221.3  |
| 82.5°  | 56.7   | 59.6   | 59.6   | 68.1   | 73.8   | 82.3   | 88.0   | 102.1  | 113.5  | 127.7  | 139.0  |
| 85°    | 48.2   | 45.4   | 45.4   | 51.1   | 53.9   | 59.6   | 62.4   | 70.9   | 76.6   | 85.1   | 90.8   |
| 87.5°  | 19.9   | 17.0   | 17.0   | 19.9   | 25.5   | 28.4   | 31.2   | 31.2   | 34.0   | 34.0   | 34.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° | 245° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°   | 252.5° | 255°   | 257.5° | 260°   | 262.5° | 265°   | 267.5° | 270°   | 272.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 |
| 2.5°   | 2094.0 | 2099.7 | 2108.2 | 2113.8 | 2128.0 | 2139.4 | 2153.6 | 2164.9 | 2173.4 | 2187.6 | 2181.9 |
| 5°     | 2017.4 | 2042.9 | 2068.4 | 2094.0 | 2113.8 | 2133.7 | 2150.7 | 2170.6 | 2193.3 | 2235.9 | 2247.2 |
| 7.5°   | 1790.4 | 1824.4 | 1855.6 | 1889.7 | 1929.4 | 1969.1 | 2008.9 | 2048.6 | 2085.5 | 2139.4 | 2173.4 |
| 10°    | 1566.2 | 1614.5 | 1659.9 | 1708.1 | 1745.0 | 1781.9 | 1815.9 | 1852.8 | 1903.9 | 1957.8 | 2020.2 |
| 12.5°  | 1424.4 | 1472.6 | 1520.8 | 1569.1 | 1623.0 | 1674.1 | 1728.0 | 1779.0 | 1827.3 | 1869.8 | 1940.8 |
| 15°    | 1330.7 | 1384.6 | 1435.7 | 1486.8 | 1552.0 | 1614.5 | 1679.7 | 1742.1 | 1813.1 | 1869.8 | 1918.1 |
| 17.5°  | 1308.0 | 1373.3 | 1435.7 | 1501.0 | 1569.1 | 1637.2 | 1705.3 | 1773.4 | 1844.3 | 1929.4 | 1991.8 |
| 20°    | 1268.3 | 1356.3 | 1444.2 | 1532.2 | 1620.1 | 1705.3 | 1793.2 | 1878.3 | 1972.0 | 2074.1 | 2102.5 |
| 22.5°  | 1245.6 | 1350.6 | 1458.4 | 1563.4 | 1682.6 | 1804.6 | 1923.7 | 2042.9 | 2142.2 | 2218.8 | 2303.9 |
| 25°    | 1242.8 | 1373.3 | 1506.6 | 1637.2 | 1787.5 | 1935.1 | 2085.5 | 2233.0 | 2360.7 | 2437.3 | 2505.4 |
| 27.5°  | 1239.9 | 1398.8 | 1554.9 | 1710.9 | 1895.4 | 2077.0 | 2261.4 | 2443.0 | 2562.1 | 2672.8 | 2729.6 |
| 30°    | 1205.9 | 1396.0 | 1588.9 | 1779.0 | 1986.2 | 2193.3 | 2400.4 | 2607.5 | 2729.6 | 2806.2 | 2834.5 |
| 32.5°  | 1163.3 | 1387.5 | 1611.6 | 1835.8 | 2071.3 | 2306.8 | 2539.4 | 2775.0 | 2871.4 | 2936.7 | 2914.0 |
| 35°    | 1129.3 | 1376.1 | 1620.1 | 1864.2 | 2113.8 | 2366.4 | 2616.1 | 2865.7 | 3004.8 | 3095.6 | 3058.7 |
| 37.5°  | 1098.1 | 1356.3 | 1614.5 | 1872.7 | 2164.9 | 2457.2 | 2749.4 | 3041.7 | 3175.0 | 3271.5 | 3228.9 |
| 40°    | 1061.2 | 1336.4 | 1614.5 | 1889.7 | 2224.5 | 2556.5 | 2891.3 | 3223.3 | 3396.3 | 3478.6 | 3413.4 |
| 42.5°  | 1030.0 | 1316.5 | 1606.0 | 1892.5 | 2250.0 | 2607.5 | 2965.1 | 3322.6 | 3515.5 | 3631.8 | 3549.6 |
| 45°    | 990.2  | 1276.8 | 1560.6 | 1847.1 | 2241.5 | 2635.9 | 3027.5 | 3421.9 | 3646.0 | 3736.8 | 3623.3 |
| 47.5°  | 947.7  | 1231.4 | 1512.3 | 1793.2 | 2213.2 | 2633.1 | 3053.0 | 3472.9 | 3680.1 | 3787.9 | 3682.9 |
| 50°    | 933.5  | 1217.2 | 1498.1 | 1781.9 | 2235.9 | 2692.7 | 3146.6 | 3600.6 | 3751.0 | 3839.0 | 3699.9 |
| 52.5°  | 930.7  | 1231.4 | 1535.0 | 1835.8 | 2292.6 | 2746.6 | 3203.4 | 3657.4 | 3779.4 | 3873.0 | 3748.2 |
| 55°    | 922.1  | 1248.4 | 1571.9 | 1895.4 | 2372.0 | 2851.6 | 3328.2 | 3804.9 | 3926.9 | 3995.0 | 3901.4 |
| 57.5°  | 930.7  | 1282.5 | 1631.5 | 1983.3 | 2474.2 | 2965.1 | 3455.9 | 3946.8 | 4094.3 | 4142.6 | 4122.7 |
| 60°    | 936.3  | 1310.9 | 1682.6 | 2057.1 | 2536.6 | 3016.1 | 3495.6 | 3975.2 | 4128.4 | 4247.5 | 4270.2 |
| 62.5°  | 922.1  | 1291.0 | 1657.0 | 2025.9 | 2460.0 | 2894.1 | 3328.2 | 3762.4 | 4014.9 | 4190.8 | 4292.9 |
| 65°    | 879.6  | 1220.1 | 1563.4 | 1903.9 | 2303.9 | 2706.9 | 3106.9 | 3507.0 | 3773.7 | 4034.7 | 4117.0 |
| 67.5°  | 786.0  | 1075.4 | 1364.8 | 1654.2 | 2003.2 | 2352.2 | 2698.3 | 3047.3 | 3382.1 | 3634.7 | 3748.2 |
| 70°    | 681.0  | 908.0  | 1137.8 | 1364.8 | 1682.6 | 2000.3 | 2318.1 | 2635.9 | 2931.0 | 3209.1 | 3316.9 |
| 72.5°  | 593.0  | 768.9  | 947.7  | 1123.6 | 1350.6 | 1574.7 | 1801.7 | 2025.9 | 2374.9 | 2652.9 | 2757.9 |
| 75°    | 505.1  | 632.7  | 757.6  | 885.3  | 1041.3 | 1197.4 | 1350.6 | 1506.6 | 1753.5 | 2003.2 | 2108.2 |
| 77.5°  | 388.7  | 473.8  | 556.1  | 638.4  | 746.2  | 851.2  | 959.0  | 1064.0 | 1237.1 | 1424.4 | 1478.3 |
| 80°    | 269.6  | 317.8  | 363.2  | 411.4  | 496.5  | 581.7  | 666.8  | 751.9  | 865.4  | 970.4  | 1052.7 |
| 82.5°  | 167.4  | 198.6  | 227.0  | 255.4  | 323.5  | 391.6  | 456.8  | 524.9  | 570.3  | 576.0  | 658.3  |
| 85°    | 107.8  | 127.7  | 144.7  | 161.7  | 201.5  | 244.0  | 283.7  | 323.5  | 289.4  | 269.6  | 320.6  |
| 87.5°  | 42.6   | 53.9   | 62.4   | 70.9   | 68.1   | 65.3   | 62.4   | 59.6   | 51.1   | 45.4   | 56.7   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° | 272.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 275°   | 277.5° | 280°   | 282.5° | 285°   | 287.5° | 290°   | 292.5° | 295°   | 297.5° | 300°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 |
| 2.5°   | 2187.6 | 2196.1 | 2204.6 | 2210.3 | 2218.8 | 2221.7 | 2224.5 | 2224.5 | 2227.3 | 2230.2 | 2235.9 |
| 5°     | 2292.6 | 2309.6 | 2326.6 | 2340.8 | 2357.9 | 2372.0 | 2383.4 | 2397.6 | 2408.9 | 2408.9 | 2406.1 |
| 7.5°   | 2204.6 | 2247.2 | 2289.8 | 2332.3 | 2374.9 | 2406.1 | 2434.5 | 2465.7 | 2494.1 | 2499.7 | 2505.4 |
| 10°    | 2088.3 | 2133.7 | 2176.3 | 2221.7 | 2264.2 | 2312.5 | 2357.9 | 2403.3 | 2451.5 | 2460.0 | 2471.4 |
| 12.5°  | 1980.5 | 2034.4 | 2088.3 | 2139.4 | 2193.3 | 2227.3 | 2261.4 | 2292.6 | 2326.6 | 2349.3 | 2372.0 |
| 15°    | 1977.6 | 2023.0 | 2068.4 | 2111.0 | 2156.4 | 2176.3 | 2196.1 | 2213.2 | 2233.0 | 2233.0 | 2235.9 |
| 17.5°  | 2042.9 | 2071.3 | 2099.7 | 2125.2 | 2153.6 | 2156.4 | 2162.1 | 2164.9 | 2167.8 | 2159.2 | 2150.7 |
| 20°    | 2170.6 | 2181.9 | 2193.3 | 2204.6 | 2216.0 | 2196.1 | 2179.1 | 2159.2 | 2139.4 | 2116.7 | 2096.8 |
| 22.5°  | 2357.9 | 2332.3 | 2306.8 | 2281.2 | 2255.7 | 2221.7 | 2184.8 | 2150.7 | 2113.8 | 2085.5 | 2057.1 |
| 25°    | 2533.8 | 2502.6 | 2471.4 | 2440.1 | 2408.9 | 2335.2 | 2261.4 | 2184.8 | 2111.0 | 2079.8 | 2048.6 |
| 27.5°  | 2769.3 | 2721.0 | 2672.8 | 2624.6 | 2576.3 | 2477.0 | 2377.7 | 2278.4 | 2179.1 | 2125.2 | 2074.1 |
| 30°    | 2826.0 | 2772.1 | 2718.2 | 2661.5 | 2607.5 | 2511.1 | 2417.4 | 2321.0 | 2224.5 | 2162.1 | 2102.5 |
| 32.5°  | 2908.3 | 2845.9 | 2783.5 | 2721.0 | 2658.6 | 2565.0 | 2471.4 | 2374.9 | 2281.2 | 2224.5 | 2164.9 |
| 35°    | 3044.5 | 2973.6 | 2902.6 | 2828.9 | 2757.9 | 2661.5 | 2567.8 | 2471.4 | 2374.9 | 2309.6 | 2247.2 |
| 37.5°  | 3160.8 | 3078.6 | 2996.3 | 2914.0 | 2831.7 | 2746.6 | 2658.6 | 2573.5 | 2485.5 | 2420.3 | 2357.9 |
| 40°    | 3291.4 | 3200.6 | 3109.8 | 3021.8 | 2931.0 | 2851.6 | 2772.1 | 2689.8 | 2610.4 | 2559.3 | 2508.2 |
| 42.5°  | 3404.8 | 3294.2 | 3186.4 | 3078.6 | 2967.9 | 2914.0 | 2862.9 | 2809.0 | 2755.1 | 2729.6 | 2701.2 |
| 45°    | 3484.3 | 3382.1 | 3277.2 | 3175.0 | 3072.9 | 3033.2 | 2993.4 | 2953.7 | 2914.0 | 2939.5 | 2965.1 |
| 47.5°  | 3518.3 | 3436.1 | 3356.6 | 3277.2 | 3194.9 | 3209.1 | 3223.3 | 3234.6 | 3248.8 | 3282.8 | 3319.7 |
| 50°    | 3549.6 | 3504.2 | 3455.9 | 3410.5 | 3362.3 | 3416.2 | 3467.3 | 3521.2 | 3575.1 | 3646.0 | 3717.0 |
| 52.5°  | 3612.0 | 3586.4 | 3563.7 | 3538.2 | 3512.7 | 3606.3 | 3699.9 | 3793.6 | 3887.2 | 3966.6 | 4046.1 |
| 55°    | 3799.2 | 3779.4 | 3759.5 | 3736.8 | 3717.0 | 3850.3 | 3980.8 | 4114.2 | 4247.5 | 4329.8 | 4412.1 |
| 57.5°  | 4057.4 | 4046.1 | 4031.9 | 4020.6 | 4006.4 | 4136.9 | 4264.6 | 4392.3 | 4522.8 | 4602.2 | 4684.5 |
| 60°    | 4253.2 | 4256.1 | 4256.1 | 4258.9 | 4258.9 | 4358.2 | 4457.5 | 4559.7 | 4659.0 | 4727.1 | 4798.0 |
| 62.5°  | 4358.2 | 4352.5 | 4346.9 | 4341.2 | 4335.5 | 4417.8 | 4500.1 | 4582.4 | 4664.6 | 4715.7 | 4766.8 |
| 65°    | 4244.7 | 4275.9 | 4307.1 | 4338.3 | 4369.6 | 4380.9 | 4389.4 | 4400.8 | 4409.3 | 4440.5 | 4471.7 |
| 67.5°  | 3864.5 | 3926.9 | 3986.5 | 4048.9 | 4108.5 | 4066.0 | 4026.2 | 3983.7 | 3941.1 | 3949.6 | 3955.3 |
| 70°    | 3441.7 | 3512.7 | 3586.4 | 3657.4 | 3728.3 | 3629.0 | 3529.7 | 3427.5 | 3328.2 | 3294.2 | 3260.1 |
| 72.5°  | 2902.6 | 2965.1 | 3030.3 | 3092.7 | 3155.2 | 3033.2 | 2914.0 | 2792.0 | 2670.0 | 2610.4 | 2550.8 |
| 75°    | 2218.8 | 2292.6 | 2369.2 | 2443.0 | 2516.8 | 2380.6 | 2241.5 | 2105.3 | 1966.3 | 1926.6 | 1889.7 |
| 77.5°  | 1617.3 | 1705.3 | 1793.2 | 1881.2 | 1969.1 | 1847.1 | 1725.1 | 1600.3 | 1478.3 | 1455.6 | 1432.9 |
| 80°    | 1177.5 | 1245.6 | 1310.9 | 1379.0 | 1444.2 | 1373.3 | 1302.4 | 1231.4 | 1160.5 | 1157.6 | 1154.8 |
| 82.5°  | 794.5  | 854.0  | 910.8  | 970.4  | 1027.1 | 998.8  | 973.2  | 944.8  | 916.5  | 944.8  | 976.1  |
| 85°    | 408.6  | 490.9  | 576.0  | 658.3  | 740.6  | 732.0  | 726.4  | 717.9  | 709.3  | 746.2  | 780.3  |
| 87.5°  | 82.3   | 153.2  | 224.2  | 292.2  | 363.2  | 346.2  | 329.1  | 309.3  | 292.2  | 303.6  | 312.1  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° | 300° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305°   | 307.5° | 310°   | 312.5° | 315°   | 317.5° | 320°   | 322.5° | 325°   | 327.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 |
| 2.5°   | 2238.7 | 2241.5 | 2241.5 | 2241.5 | 2241.5 | 2241.5 | 2235.9 | 2233.0 | 2227.3 | 2221.7 | 2213.2 |
| 5°     | 2406.1 | 2403.3 | 2391.9 | 2380.6 | 2366.4 | 2355.0 | 2346.5 | 2335.2 | 2326.6 | 2315.3 | 2298.3 |
| 7.5°   | 2511.1 | 2516.8 | 2496.9 | 2479.9 | 2460.0 | 2440.1 | 2420.3 | 2400.4 | 2380.6 | 2360.7 | 2321.0 |
| 10°    | 2479.9 | 2488.4 | 2477.0 | 2465.7 | 2451.5 | 2440.1 | 2417.4 | 2391.9 | 2369.2 | 2343.7 | 2295.4 |
| 12.5°  | 2391.9 | 2414.6 | 2408.9 | 2403.3 | 2397.6 | 2391.9 | 2377.7 | 2360.7 | 2346.5 | 2329.5 | 2275.6 |
| 15°    | 2235.9 | 2235.9 | 2238.7 | 2241.5 | 2241.5 | 2244.4 | 2247.2 | 2250.0 | 2252.9 | 2255.7 | 2224.5 |
| 17.5°  | 2142.2 | 2133.7 | 2133.7 | 2133.7 | 2133.7 | 2133.7 | 2145.1 | 2159.2 | 2170.6 | 2181.9 | 2173.4 |
| 20°    | 2074.1 | 2054.3 | 2051.4 | 2051.4 | 2048.6 | 2045.7 | 2065.6 | 2088.3 | 2108.2 | 2128.0 | 2139.4 |
| 22.5°  | 2028.7 | 2000.3 | 1997.5 | 1994.7 | 1991.8 | 1989.0 | 2014.5 | 2040.1 | 2065.6 | 2091.1 | 2130.9 |
| 25°    | 2017.4 | 1986.2 | 1989.0 | 1991.8 | 1991.8 | 1994.7 | 2014.5 | 2034.4 | 2054.3 | 2074.1 | 2142.2 |
| 27.5°  | 2020.2 | 1969.1 | 1972.0 | 1974.8 | 1974.8 | 1977.6 | 2008.9 | 2037.2 | 2068.4 | 2096.8 | 2181.9 |
| 30°    | 2040.1 | 1980.5 | 1974.8 | 1969.1 | 1963.5 | 1957.8 | 2000.3 | 2042.9 | 2085.5 | 2128.0 | 2193.3 |
| 32.5°  | 2108.2 | 2051.4 | 2037.2 | 2023.0 | 2008.9 | 1994.7 | 2045.7 | 2094.0 | 2145.1 | 2193.3 | 2247.2 |
| 35°    | 2181.9 | 2119.5 | 2113.8 | 2108.2 | 2099.7 | 2094.0 | 2139.4 | 2187.6 | 2233.0 | 2278.4 | 2326.6 |
| 37.5°  | 2292.6 | 2230.2 | 2224.5 | 2216.0 | 2210.3 | 2201.8 | 2252.9 | 2301.1 | 2352.2 | 2400.4 | 2443.0 |
| 40°    | 2457.2 | 2406.1 | 2403.3 | 2403.3 | 2400.4 | 2397.6 | 2437.3 | 2479.9 | 2519.6 | 2559.3 | 2587.7 |
| 42.5°  | 2675.6 | 2650.1 | 2658.6 | 2670.0 | 2678.5 | 2687.0 | 2718.2 | 2752.3 | 2783.5 | 2814.7 | 2806.2 |
| 45°    | 2990.6 | 3016.1 | 3019.0 | 3021.8 | 3024.6 | 3027.5 | 3036.0 | 3047.3 | 3055.9 | 3064.4 | 3030.3 |
| 47.5°  | 3353.8 | 3387.8 | 3404.8 | 3421.9 | 3436.1 | 3453.1 | 3441.7 | 3427.5 | 3416.2 | 3402.0 | 3316.9 |
| 50°    | 3785.1 | 3856.0 | 3853.2 | 3850.3 | 3844.6 | 3841.8 | 3819.1 | 3796.4 | 3770.9 | 3748.2 | 3623.3 |
| 52.5°  | 4125.5 | 4205.0 | 4219.2 | 4233.4 | 4247.5 | 4261.7 | 4219.2 | 4176.6 | 4131.2 | 4088.7 | 3932.6 |
| 55°    | 4491.6 | 4573.8 | 4576.7 | 4579.5 | 4579.5 | 4582.4 | 4522.8 | 4463.2 | 4400.8 | 4341.2 | 4179.5 |
| 57.5°  | 4764.0 | 4843.4 | 4834.9 | 4829.2 | 4820.7 | 4812.2 | 4741.3 | 4670.3 | 4599.4 | 4528.4 | 4366.7 |
| 60°    | 4866.1 | 4934.2 | 4917.2 | 4900.1 | 4880.3 | 4863.3 | 4809.3 | 4755.4 | 4698.7 | 4644.8 | 4488.7 |
| 62.5°  | 4817.9 | 4868.9 | 4843.4 | 4820.7 | 4795.2 | 4769.6 | 4701.5 | 4630.6 | 4562.5 | 4491.6 | 4378.1 |
| 65°    | 4500.1 | 4531.3 | 4497.2 | 4466.0 | 4434.8 | 4400.8 | 4344.0 | 4287.3 | 4227.7 | 4170.9 | 4094.3 |
| 67.5°  | 3963.8 | 3969.5 | 3966.6 | 3963.8 | 3961.0 | 3958.1 | 3875.9 | 3793.6 | 3708.4 | 3626.2 | 3620.5 |
| 70°    | 3228.9 | 3194.9 | 3200.6 | 3209.1 | 3214.7 | 3220.4 | 3158.0 | 3098.4 | 3036.0 | 2973.6 | 3001.9 |
| 72.5°  | 2491.2 | 2431.6 | 2445.8 | 2462.8 | 2477.0 | 2491.2 | 2440.1 | 2391.9 | 2340.8 | 2289.8 | 2329.5 |
| 75°    | 1850.0 | 1813.1 | 1827.3 | 1844.3 | 1858.5 | 1872.7 | 1852.8 | 1832.9 | 1810.2 | 1790.4 | 1827.3 |
| 77.5°  | 1410.2 | 1387.5 | 1390.3 | 1390.3 | 1393.2 | 1393.2 | 1396.0 | 1401.7 | 1404.5 | 1407.3 | 1447.1 |
| 80°    | 1149.1 | 1146.3 | 1143.5 | 1140.6 | 1134.9 | 1132.1 | 1160.5 | 1188.9 | 1217.2 | 1245.6 | 1265.5 |
| 82.5°  | 1004.4 | 1032.8 | 1015.8 | 1001.6 | 984.6  | 967.5  | 993.1  | 1018.6 | 1044.2 | 1069.7 | 1061.2 |
| 85°    | 817.2  | 851.2  | 820.0  | 788.8  | 754.7  | 723.5  | 746.2  | 766.1  | 788.8  | 808.7  | 797.3  |
| 87.5°  | 323.5  | 332.0  | 280.9  | 232.7  | 181.6  | 130.5  | 207.1  | 280.9  | 357.5  | 431.3  | 442.6  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305° | 307.5° | 310° | 312.5° | 315° | 317.5° | 320° | 322.5° | 325° | 327.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 330°   | 332.5° | 335°   | 337.5° | 340°   | 342.5° | 345°   | 347.5° | 350°   | 352.5° | 355°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 | 2042.9 |
| 2.5°   | 2204.6 | 2193.3 | 2184.8 | 2181.9 | 2176.3 | 2173.4 | 2167.8 | 2162.1 | 2153.6 | 2147.9 | 2139.4 |
| 5°     | 2278.4 | 2261.4 | 2241.5 | 2213.2 | 2187.6 | 2159.2 | 2130.9 | 2105.3 | 2079.8 | 2051.4 | 2025.9 |
| 7.5°   | 2281.2 | 2241.5 | 2201.8 | 2164.9 | 2125.2 | 2088.3 | 2048.6 | 2014.5 | 1977.6 | 1940.8 | 1906.7 |
| 10°    | 2250.0 | 2201.8 | 2153.6 | 2105.3 | 2059.9 | 2011.7 | 1963.5 | 1923.7 | 1881.2 | 1838.6 | 1798.9 |
| 12.5°  | 2224.5 | 2170.6 | 2116.7 | 2059.9 | 2006.0 | 1949.3 | 1892.5 | 1852.8 | 1813.1 | 1773.4 | 1733.6 |
| 15°    | 2193.3 | 2159.2 | 2128.0 | 2077.0 | 2025.9 | 1974.8 | 1923.7 | 1869.8 | 1818.8 | 1764.8 | 1710.9 |
| 17.5°  | 2167.8 | 2159.2 | 2150.7 | 2116.7 | 2082.6 | 2045.7 | 2011.7 | 1957.8 | 1903.9 | 1847.1 | 1793.2 |
| 20°    | 2153.6 | 2164.9 | 2176.3 | 2159.2 | 2142.2 | 2122.4 | 2105.3 | 2065.6 | 2025.9 | 1983.3 | 1943.6 |
| 22.5°  | 2170.6 | 2213.2 | 2252.9 | 2255.7 | 2261.4 | 2264.2 | 2267.1 | 2230.2 | 2193.3 | 2153.6 | 2116.7 |
| 25°    | 2210.3 | 2278.4 | 2346.5 | 2383.4 | 2420.3 | 2460.0 | 2496.9 | 2474.2 | 2451.5 | 2428.8 | 2406.1 |
| 27.5°  | 2264.2 | 2349.3 | 2434.5 | 2488.4 | 2539.4 | 2593.4 | 2647.3 | 2644.4 | 2641.6 | 2635.9 | 2633.1 |
| 30°    | 2255.7 | 2321.0 | 2386.2 | 2451.5 | 2516.8 | 2582.0 | 2647.3 | 2681.3 | 2712.5 | 2746.6 | 2780.6 |
| 32.5°  | 2303.9 | 2357.9 | 2414.6 | 2482.7 | 2550.8 | 2621.7 | 2689.8 | 2760.8 | 2828.9 | 2899.8 | 2970.7 |
| 35°    | 2377.7 | 2426.0 | 2477.0 | 2550.8 | 2627.4 | 2701.2 | 2777.8 | 2862.9 | 2950.9 | 3038.8 | 3123.9 |
| 37.5°  | 2488.4 | 2530.9 | 2576.3 | 2638.8 | 2704.0 | 2766.4 | 2831.7 | 2956.5 | 3081.4 | 3209.1 | 3333.9 |
| 40°    | 2616.1 | 2644.4 | 2672.8 | 2732.4 | 2792.0 | 2851.6 | 2911.1 | 3067.2 | 3223.3 | 3379.3 | 3535.4 |
| 42.5°  | 2800.5 | 2792.0 | 2783.5 | 2831.7 | 2882.8 | 2931.0 | 2982.1 | 3123.9 | 3265.8 | 3407.7 | 3549.6 |
| 45°    | 2996.3 | 2962.2 | 2928.2 | 2950.9 | 2976.4 | 2999.1 | 3024.6 | 3169.3 | 3314.1 | 3461.6 | 3606.3 |
| 47.5°  | 3231.8 | 3146.6 | 3061.5 | 3041.7 | 3021.8 | 2999.1 | 2979.2 | 3135.3 | 3291.4 | 3450.2 | 3606.3 |
| 50°    | 3498.5 | 3370.8 | 3246.0 | 3194.9 | 3141.0 | 3089.9 | 3036.0 | 3163.7 | 3294.2 | 3424.7 | 3552.4 |
| 52.5°  | 3776.5 | 3617.7 | 3461.6 | 3382.1 | 3302.7 | 3220.4 | 3141.0 | 3248.8 | 3359.5 | 3470.1 | 3577.9 |
| 55°    | 4014.9 | 3853.2 | 3688.6 | 3595.0 | 3501.3 | 3407.7 | 3314.1 | 3421.9 | 3529.7 | 3637.5 | 3745.3 |
| 57.5°  | 4205.0 | 4043.3 | 3881.5 | 3793.6 | 3702.8 | 3614.8 | 3524.0 | 3626.2 | 3731.1 | 3836.1 | 3938.3 |
| 60°    | 4335.5 | 4179.5 | 4023.4 | 3938.3 | 3853.2 | 3768.0 | 3682.9 | 3804.9 | 3926.9 | 4051.8 | 4173.8 |
| 62.5°  | 4267.4 | 4153.9 | 4040.4 | 4003.5 | 3966.6 | 3926.9 | 3890.0 | 4006.4 | 4119.9 | 4236.2 | 4352.5 |
| 65°    | 4017.7 | 3941.1 | 3864.5 | 3901.4 | 3941.1 | 3978.0 | 4017.7 | 4094.3 | 4170.9 | 4250.4 | 4327.0 |
| 67.5°  | 3612.0 | 3606.3 | 3597.8 | 3680.1 | 3762.4 | 3847.5 | 3929.8 | 3980.8 | 4029.1 | 4080.1 | 4131.2 |
| 70°    | 3030.3 | 3061.5 | 3089.9 | 3231.8 | 3373.6 | 3515.5 | 3657.4 | 3677.2 | 3697.1 | 3717.0 | 3736.8 |
| 72.5°  | 2372.0 | 2411.8 | 2454.3 | 2641.6 | 2826.0 | 3013.3 | 3200.6 | 3189.2 | 3177.9 | 3163.7 | 3152.3 |
| 75°    | 1867.0 | 1903.9 | 1943.6 | 2116.7 | 2289.8 | 2462.8 | 2635.9 | 2587.7 | 2542.3 | 2494.1 | 2445.8 |
| 77.5°  | 1489.6 | 1529.3 | 1571.9 | 1733.6 | 1895.4 | 2059.9 | 2221.7 | 2105.3 | 1989.0 | 1872.7 | 1756.3 |
| 80°    | 1282.5 | 1302.4 | 1319.4 | 1430.0 | 1537.9 | 1648.5 | 1759.2 | 1640.0 | 1518.0 | 1396.0 | 1276.8 |
| 82.5°  | 1052.7 | 1041.3 | 1032.8 | 1098.1 | 1163.3 | 1228.6 | 1293.8 | 1180.3 | 1066.9 | 950.5  | 837.0  |
| 85°    | 786.0  | 774.6  | 763.3  | 797.3  | 831.4  | 868.2  | 902.3  | 771.8  | 641.2  | 507.9  | 377.4  |
| 87.5°  | 456.8  | 468.2  | 479.5  | 516.4  | 553.3  | 593.0  | 629.9  | 496.5  | 363.2  | 227.0  | 93.6   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 332.5° | 335° | 337.5° | 340° | 342.5° | 345° | 347.5° | 350° | 352.5° | 355° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P671896

CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360°   |
|--------|--------|--------|
| 0°     | 2042.9 | 2042.9 |
| 2.5°   | 2122.4 | 2108.2 |
| 5°     | 2006.0 | 1986.2 |
| 7.5°   | 1878.3 | 1852.8 |
| 10°    | 1762.0 | 1728.0 |
| 12.5°  | 1688.2 | 1645.7 |
| 15°    | 1659.9 | 1608.8 |
| 17.5°  | 1745.0 | 1696.7 |
| 20°    | 1875.5 | 1810.2 |
| 22.5°  | 2034.4 | 1955.0 |
| 25°    | 2309.6 | 2213.2 |
| 27.5°  | 2533.8 | 2434.5 |
| 30°    | 2672.8 | 2565.0 |
| 32.5°  | 2826.0 | 2684.2 |
| 35°    | 2984.9 | 2848.7 |
| 37.5°  | 3177.9 | 3024.6 |
| 40°    | 3376.5 | 3217.6 |
| 42.5°  | 3444.6 | 3342.4 |
| 45°    | 3509.8 | 3413.4 |
| 47.5°  | 3524.0 | 3444.6 |
| 50°    | 3538.2 | 3526.9 |
| 52.5°  | 3577.9 | 3575.1 |
| 55°    | 3748.2 | 3751.0 |
| 57.5°  | 3958.1 | 3975.2 |
| 60°    | 4151.1 | 4131.2 |
| 62.5°  | 4250.4 | 4148.2 |
| 65°    | 4182.3 | 4040.4 |
| 67.5°  | 3978.0 | 3824.8 |
| 70°    | 3529.7 | 3322.6 |
| 72.5°  | 2970.7 | 2789.1 |
| 75°    | 2289.8 | 2136.5 |
| 77.5°  | 1628.7 | 1501.0 |
| 80°    | 1146.3 | 1018.6 |
| 82.5°  | 734.9  | 632.7  |
| 85°    | 332.0  | 289.4  |
| 87.5°  | 93.6   | 90.8   |
| 90°    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    |



REPORT NUMBER: P671896  
CATALOG NUMBER: CCP-SA-2C-840-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

(END OF REPORT)