

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P671897

Luminaire Tested: **CCP-SA-2D-840-U-SLR**

Issue Date: 04/16/2023

Test Information

Test Method: LM-79-08
Report Number: P671897
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/16/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCP-SA-2D-840-U-SLR
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @800mA w/ SLR
distribution lens
Light Source: (32) 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7891.2 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G3

Input Watts (W): 80.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 11.2 fc

Type IV - Short - N/A

REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1623.7	0.0	1623.7
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	6267.5	0.0	6267.5
	% Fixture	79.4	0.0	79.4
Total	Lumens	7891.2	0.0	7891.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.8	2.5
10°-20°	413.4	5.2
20°-30°	604.9	7.7
30°-40°	852.1	10.8
40°-50°	1170.9	14.8
50°-60°	1596.0	20.2
60°-70°	1746.8	22.1
70°-80°	1008.8	12.8
80°-90°	302.4	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7891.2	100.0
0°-180°	7891.2	100.0

Coefficient of Utilization



REPORT NUMBER: P671897


CATALOG NUMBER: CCP-SA-2D-840-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	810.4	10.3			
FM	(30°-60°)	2879.7	36.5			
FH	(60°-80°)	2320.5	29.4			G2/5000
FVH	(80°-90°)	256.9	3.3			G3/500
BL	(0°-30°)	403.6	5.1	B1/500		
BM	(30°-60°)	739.4	9.4	B1/1000		
BH	(60°-80°)	435.1	5.5	B1/500		G1/500
BVH	(80°-90°)	45.5	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G3

Type IV Short





REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9
2.5°	2600.4	2586.4	2575.9	2565.4	2551.4	2540.9	2526.9	2512.9	2495.4	2481.4	2463.9
5°	2449.9	2407.9	2365.9	2341.4	2313.4	2288.9	2260.9	2229.4	2197.9	2163.0	2131.5
7.5°	2285.4	2232.9	2180.5	2138.5	2093.0	2051.0	2005.5	1967.0	1928.5	1890.0	1851.5
10°	2131.5	2082.5	2033.5	1981.0	1925.0	1872.5	1816.5	1764.0	1711.5	1659.0	1606.5
12.5°	2030.0	1970.5	1914.5	1855.0	1799.0	1739.5	1680.0	1631.0	1582.0	1529.5	1480.5
15°	1984.5	1928.5	1876.0	1816.5	1757.0	1697.5	1638.0	1582.0	1529.5	1473.5	1417.5
17.5°	2093.0	2012.5	1932.0	1855.0	1778.0	1701.0	1624.0	1554.0	1484.0	1414.0	1344.0
20°	2232.9	2131.5	2033.5	1939.0	1841.0	1746.5	1648.5	1550.5	1452.5	1354.5	1256.5
22.5°	2411.4	2295.9	2184.0	2061.5	1935.5	1813.0	1687.0	1564.5	1442.0	1316.0	1193.5
25°	2729.9	2593.4	2456.9	2281.9	2103.5	1928.5	1750.0	1589.0	1431.5	1270.5	1109.5
27.5°	3002.9	2817.4	2635.4	2425.4	2215.4	2005.5	1795.5	1610.0	1428.0	1242.5	1057.0
30°	3163.9	2981.9	2799.9	2544.4	2292.4	2037.0	1781.5	1575.0	1372.0	1165.5	959.0
32.5°	3310.9	3107.9	2904.9	2624.9	2341.4	2061.5	1778.0	1550.5	1326.5	1099.0	871.5
35°	3513.9	3289.9	3069.4	2743.9	2418.4	2093.0	1767.5	1533.0	1295.0	1060.5	822.5
37.5°	3730.9	3454.4	3181.4	2820.9	2460.4	2100.0	1739.5	1508.5	1277.5	1046.5	815.5
40°	3968.9	3632.9	3300.4	2901.4	2505.9	2107.0	1708.0	1477.0	1246.0	1011.5	780.5
42.5°	4122.9	3758.9	3394.9	2964.4	2537.4	2107.0	1676.5	1449.0	1221.5	990.5	763.0
45°	4210.4	3856.9	3506.9	3041.4	2575.9	2110.5	1645.0	1421.0	1197.0	969.5	745.5
47.5°	4248.9	3919.9	3590.9	3100.9	2614.4	2124.5	1634.5	1407.0	1176.0	948.5	717.5
50°	4350.4	4059.9	3769.4	3244.4	2722.9	2197.9	1673.0	1428.0	1186.5	941.5	696.5
52.5°	4409.9	4161.4	3912.9	3373.9	2834.9	2295.9	1757.0	1484.0	1211.0	938.0	665.0
55°	4626.9	4388.9	4150.9	3576.9	2999.4	2425.4	1848.0	1547.0	1246.0	941.5	640.5
57.5°	4903.4	4651.4	4402.9	3783.4	3163.9	2544.4	1925.0	1603.0	1277.5	955.5	630.0
60°	5095.9	4850.9	4609.4	3951.4	3289.9	2631.9	1970.5	1634.5	1298.5	959.0	623.0
62.5°	5116.9	4801.9	4490.4	3849.9	3209.4	2565.4	1925.0	1599.5	1274.0	945.0	619.5
65°	4983.9	4616.4	4248.9	3636.4	3023.9	2411.4	1799.0	1501.5	1204.0	903.0	605.5
67.5°	4717.9	4287.4	3856.9	3296.9	2736.9	2177.0	1617.0	1361.5	1109.5	854.0	598.5
70°	4098.4	3720.4	3345.9	2859.4	2376.4	1890.0	1403.5	1193.5	987.0	777.0	567.0
72.5°	3440.4	3086.9	2736.9	2341.4	1949.5	1554.0	1158.5	1001.0	843.5	682.5	525.0
75°	2635.4	2369.4	2107.0	1813.0	1519.0	1221.5	927.5	812.0	696.5	581.0	465.5
77.5°	1851.5	1708.0	1568.0	1347.5	1127.0	906.5	686.0	609.0	532.0	455.0	378.0
80°	1256.5	1176.0	1099.0	941.5	784.0	623.0	465.5	416.5	364.0	315.0	262.5
82.5°	780.5	777.0	770.0	661.5	553.0	444.5	336.0	294.0	255.5	213.5	171.5
85°	357.0	416.5	472.5	413.0	353.5	294.0	234.5	206.5	178.5	147.0	119.0
87.5°	112.0	136.5	157.5	150.5	140.0	133.0	122.5	105.0	87.5	70.0	52.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9
2.5°	2449.9	2439.4	2425.4	2411.4	2393.9	2379.9	2362.4	2344.9	2341.4	2334.4	2330.9
5°	2110.5	2089.5	2065.0	2044.0	2023.0	1998.5	1977.5	1953.0	1935.5	1914.5	1897.0
7.5°	1813.0	1778.0	1739.5	1701.0	1666.0	1631.0	1592.5	1557.5	1540.0	1522.5	1505.0
10°	1575.0	1540.0	1508.5	1473.5	1449.0	1428.0	1403.5	1379.0	1358.0	1337.0	1316.0
12.5°	1456.0	1431.5	1407.0	1382.5	1354.5	1330.0	1302.0	1274.0	1249.5	1228.5	1204.0
15°	1382.5	1347.5	1309.0	1274.0	1235.5	1200.5	1162.0	1123.5	1095.5	1071.0	1043.0
17.5°	1295.0	1242.5	1193.5	1141.0	1099.0	1057.0	1011.5	969.5	938.0	903.0	871.5
20°	1197.0	1137.5	1074.5	1015.0	966.0	920.5	871.5	822.5	787.5	749.0	714.0
22.5°	1113.0	1036.0	955.5	875.0	822.5	770.0	714.0	661.5	630.0	595.0	563.5
25°	1022.0	938.0	850.5	763.0	710.5	654.5	602.0	546.0	521.5	500.5	476.0
27.5°	973.0	889.0	801.5	717.5	668.5	616.0	567.0	514.5	497.0	476.0	458.5
30°	875.0	794.5	710.5	626.5	591.5	560.0	525.0	490.0	483.0	479.5	472.5
32.5°	787.5	703.5	619.5	535.5	504.0	472.5	441.0	409.5	406.0	399.0	395.5
35°	742.0	661.5	577.5	497.0	469.0	437.5	409.5	378.0	371.0	360.5	353.5
37.5°	731.5	647.5	560.0	476.0	448.0	420.0	388.5	360.5	353.5	346.5	339.5
40°	703.5	623.0	546.0	465.5	437.5	409.5	378.0	350.0	343.0	336.0	329.0
42.5°	682.5	605.5	525.0	444.5	420.0	395.5	367.5	343.0	336.0	329.0	318.5
45°	665.0	584.5	500.5	420.0	402.5	385.0	364.0	346.5	339.5	329.0	322.0
47.5°	637.0	560.0	479.5	399.0	381.5	367.5	350.0	332.5	325.5	318.5	311.5
50°	616.0	535.5	455.0	374.5	360.5	346.5	332.5	318.5	318.5	322.0	322.0
52.5°	588.0	511.0	434.0	357.0	343.0	329.0	315.0	301.0	304.5	308.0	311.5
55°	563.5	490.0	413.0	336.0	322.0	308.0	290.5	276.5	280.0	283.5	287.0
57.5°	553.0	476.0	399.0	322.0	308.0	290.5	276.5	259.0	259.0	259.0	259.0
60°	546.0	465.5	388.5	308.0	290.5	276.5	259.0	241.5	238.0	238.0	234.5
62.5°	542.5	462.0	385.0	304.5	283.5	266.0	245.0	224.0	220.5	217.0	213.5
65°	528.5	455.0	378.0	301.0	276.5	255.5	231.0	206.5	203.0	203.0	199.5
67.5°	525.0	448.0	374.5	297.5	273.0	245.0	220.5	192.5	189.0	185.5	182.0
70°	497.0	430.5	360.5	290.5	262.5	238.0	210.0	182.0	178.5	171.5	168.0
72.5°	462.0	402.5	339.5	276.5	248.5	220.5	192.5	164.5	161.0	157.5	150.5
75°	409.5	353.5	297.5	241.5	217.0	196.0	171.5	147.0	143.5	140.0	133.0
77.5°	336.0	290.5	248.5	203.0	185.5	168.0	150.5	133.0	129.5	126.0	119.0
80°	238.0	210.0	185.5	157.5	147.0	133.0	122.5	108.5	108.5	105.0	105.0
82.5°	157.5	143.5	129.5	115.5	108.5	101.5	94.5	87.5	87.5	84.0	84.0
85°	112.0	105.0	94.5	87.5	84.0	77.0	73.5	66.5	66.5	66.5	66.5
87.5°	52.5	52.5	49.0	49.0	45.5	45.5	42.0	38.5	38.5	38.5	38.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9
2.5°	2323.9	2313.4	2302.9	2288.9	2278.4	2264.4	2246.9	2232.9	2215.4	2215.4	2211.9
5°	1876.0	1865.5	1855.0	1841.0	1830.5	1816.5	1806.0	1792.0	1778.0	1778.0	1774.5
7.5°	1487.5	1466.5	1445.5	1421.0	1400.0	1386.0	1372.0	1354.5	1340.5	1330.0	1319.5
10°	1295.0	1274.0	1249.5	1228.5	1204.0	1186.5	1169.0	1148.0	1130.5	1116.5	1102.5
12.5°	1179.5	1155.0	1130.5	1106.0	1081.5	1057.0	1036.0	1011.5	987.0	969.5	952.0
15°	1015.0	990.5	966.0	941.5	917.0	889.0	861.0	829.5	801.5	787.5	777.0
17.5°	836.5	812.0	784.0	759.5	731.5	710.5	689.5	668.5	647.5	633.5	623.0
20°	675.5	647.5	619.5	591.5	563.5	549.5	535.5	521.5	507.5	497.0	490.0
22.5°	528.5	511.0	497.0	479.5	462.0	451.5	444.5	434.0	423.5	423.5	423.5
25°	451.5	441.0	434.0	423.5	413.0	409.5	406.0	399.0	395.5	392.0	392.0
27.5°	437.5	427.0	416.5	406.0	395.5	392.0	388.5	381.5	378.0	378.0	378.0
30°	465.5	462.0	458.5	455.0	451.5	444.5	434.0	427.0	416.5	409.5	402.5
32.5°	388.5	385.0	385.0	381.5	378.0	385.0	388.5	395.5	399.0	402.5	406.0
35°	343.0	336.0	329.0	322.0	315.0	311.5	308.0	304.5	301.0	301.0	297.5
37.5°	332.5	325.5	318.5	311.5	304.5	301.0	297.5	294.0	290.5	290.5	287.0
40°	322.0	315.0	311.5	304.5	297.5	294.0	290.5	283.5	280.0	276.5	276.5
42.5°	311.5	308.0	301.0	297.5	290.5	287.0	283.5	276.5	273.0	269.5	266.0
45°	311.5	304.5	297.5	290.5	283.5	280.0	273.0	269.5	262.5	262.5	259.0
47.5°	304.5	297.5	290.5	283.5	276.5	273.0	266.0	262.5	255.5	252.0	248.5
50°	322.0	311.5	297.5	287.0	273.0	269.5	262.5	259.0	252.0	248.5	245.0
52.5°	315.0	304.5	290.5	280.0	266.0	259.0	255.5	248.5	241.5	238.0	234.5
55°	290.5	280.0	273.0	262.5	252.0	245.0	238.0	231.0	224.0	220.5	220.5
57.5°	259.0	255.5	252.0	248.5	245.0	238.0	231.0	220.5	213.5	210.0	206.5
60°	231.0	234.5	238.0	241.5	245.0	234.5	224.0	213.5	203.0	199.5	196.0
62.5°	210.0	217.0	224.0	227.5	234.5	224.0	213.5	203.0	192.5	189.0	185.5
65°	196.0	199.5	199.5	203.0	203.0	196.0	192.5	185.5	178.5	175.0	175.0
67.5°	178.5	178.5	178.5	175.0	175.0	171.5	171.5	168.0	164.5	161.0	161.0
70°	161.0	161.0	161.0	157.5	157.5	154.0	154.0	150.5	147.0	147.0	143.5
72.5°	147.0	147.0	143.5	143.5	140.0	140.0	140.0	136.5	136.5	133.0	133.0
75°	129.5	129.5	126.0	126.0	122.5	122.5	122.5	119.0	119.0	119.0	115.5
77.5°	115.5	115.5	112.0	112.0	108.5	108.5	108.5	105.0	105.0	101.5	101.5
80°	101.5	101.5	98.0	98.0	94.5	94.5	91.0	91.0	87.5	87.5	84.0
82.5°	80.5	80.5	80.5	80.5	80.5	77.0	77.0	73.5	70.0	70.0	66.5
85°	66.5	66.5	66.5	63.0	63.0	63.0	59.5	59.5	56.0	52.5	52.5
87.5°	38.5	38.5	38.5	35.0	35.0	35.0	35.0	35.0	35.0	35.0	31.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9
2.5°	2211.9	2208.4	2194.4	2180.5	2194.4	2208.4	2208.4	2208.4	2204.9	2204.9	2204.9
5°	1774.5	1771.0	1764.0	1757.0	1757.0	1753.5	1760.5	1767.5	1774.5	1781.5	1788.5
7.5°	1305.5	1295.0	1284.5	1274.0	1281.0	1284.5	1295.0	1302.0	1312.5	1319.5	1337.0
10°	1088.5	1074.5	1064.0	1053.5	1046.5	1039.5	1032.5	1029.0	1022.0	1015.0	1022.0
12.5°	931.0	913.5	896.0	875.0	871.5	868.0	861.0	854.0	847.0	840.0	836.5
15°	763.0	749.0	742.0	731.5	717.5	703.5	696.5	693.0	686.0	679.0	675.5
17.5°	609.0	595.0	584.5	574.0	570.5	563.5	563.5	563.5	563.5	563.5	563.5
20°	479.5	469.0	469.0	465.5	465.5	462.0	465.5	469.0	469.0	472.5	476.0
22.5°	420.0	420.0	416.5	413.0	416.5	416.5	420.0	423.5	427.0	430.5	434.0
25°	388.5	385.0	388.5	392.0	392.0	392.0	395.5	395.5	399.0	399.0	399.0
27.5°	374.5	374.5	378.0	378.0	381.5	381.5	381.5	378.0	378.0	374.5	374.5
30°	395.5	388.5	388.5	388.5	385.0	381.5	378.0	378.0	374.5	371.0	367.5
32.5°	409.5	413.0	409.5	402.5	399.0	392.0	388.5	381.5	378.0	371.0	364.0
35°	297.5	294.0	301.0	304.5	308.0	311.5	315.0	318.5	318.5	322.0	322.0
37.5°	287.0	283.5	283.5	280.0	280.0	280.0	280.0	280.0	276.5	276.5	280.0
40°	273.0	269.5	269.5	266.0	266.0	262.5	262.5	262.5	262.5	262.5	262.5
42.5°	262.5	259.0	259.0	259.0	259.0	255.5	255.5	252.0	252.0	248.5	248.5
45°	259.0	255.5	252.0	248.5	248.5	245.0	245.0	245.0	241.5	241.5	241.5
47.5°	245.0	241.5	241.5	238.0	238.0	234.5	234.5	234.5	231.0	231.0	231.0
50°	238.0	234.5	234.5	231.0	231.0	227.5	227.5	227.5	224.0	224.0	224.0
52.5°	227.5	224.0	224.0	224.0	220.5	217.0	217.0	217.0	213.5	213.5	213.5
55°	217.0	213.5	213.5	213.5	210.0	206.5	206.5	206.5	203.0	203.0	203.0
57.5°	203.0	199.5	199.5	196.0	196.0	196.0	196.0	196.0	192.5	192.5	192.5
60°	192.5	189.0	189.0	185.5	185.5	182.0	182.0	182.0	182.0	182.0	182.0
62.5°	182.0	178.5	175.0	171.5	175.0	175.0	175.0	175.0	171.5	171.5	171.5
65°	171.5	168.0	164.5	161.0	161.0	161.0	161.0	161.0	161.0	161.0	161.0
67.5°	157.5	154.0	150.5	147.0	150.5	150.5	150.5	150.5	150.5	150.5	150.5
70°	143.5	140.0	140.0	136.5	136.5	133.0	133.0	136.5	136.5	136.5	136.5
72.5°	129.5	126.0	126.0	122.5	122.5	122.5	122.5	122.5	122.5	122.5	122.5
75°	115.5	112.0	112.0	108.5	108.5	108.5	108.5	108.5	108.5	108.5	108.5
77.5°	98.0	94.5	94.5	94.5	94.5	94.5	94.5	98.0	98.0	98.0	98.0
80°	84.0	80.5	80.5	80.5	80.5	80.5	80.5	80.5	80.5	80.5	80.5
82.5°	66.5	63.0	63.0	63.0	63.0	63.0	63.0	63.0	63.0	63.0	63.0
85°	49.0	45.5	45.5	45.5	49.0	49.0	49.0	49.0	49.0	49.0	49.0
87.5°	31.5	28.0	28.0	28.0	31.5	31.5	31.5	31.5	28.0	28.0	28.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9
2.5°	2204.9	2204.9	2204.9	2201.4	2197.9	2194.4	2191.0	2201.4	2208.4	2218.9	2225.9
5°	1792.0	1799.0	1802.5	1813.0	1823.5	1834.0	1844.5	1851.5	1858.5	1862.0	1869.0
7.5°	1351.0	1368.5	1382.5	1396.5	1410.5	1421.0	1435.0	1445.5	1456.0	1466.5	1477.0
10°	1025.5	1032.5	1036.0	1050.0	1060.5	1074.5	1085.0	1095.5	1106.0	1113.0	1123.5
12.5°	833.0	826.0	822.5	822.5	822.5	822.5	822.5	829.5	836.5	843.5	850.5
15°	672.0	668.5	665.0	661.5	658.0	651.0	647.5	654.5	661.5	668.5	675.5
17.5°	563.5	563.5	563.5	560.0	556.5	553.0	549.5	553.0	556.5	556.5	560.0
20°	483.0	486.5	490.0	493.5	493.5	497.0	497.0	500.5	504.0	504.0	507.5
22.5°	434.0	437.5	437.5	437.5	441.0	441.0	441.0	444.5	448.0	451.5	455.0
25°	395.5	395.5	392.0	392.0	395.5	395.5	395.5	395.5	399.0	399.0	399.0
27.5°	374.5	371.0	371.0	371.0	371.0	367.5	367.5	367.5	367.5	367.5	367.5
30°	364.0	360.5	357.0	353.5	353.5	350.0	346.5	346.5	346.5	346.5	346.5
32.5°	360.5	353.5	346.5	343.0	343.0	339.5	336.0	332.5	332.5	329.0	325.5
35°	322.0	318.5	318.5	315.0	311.5	308.0	304.5	304.5	304.5	301.0	301.0
37.5°	280.0	283.5	283.5	283.5	287.0	287.0	287.0	287.0	290.5	290.5	290.5
40°	262.5	262.5	262.5	266.0	269.5	269.5	273.0	273.0	276.5	276.5	276.5
42.5°	248.5	245.0	245.0	248.5	248.5	252.0	252.0	255.5	259.0	259.0	262.5
45°	241.5	238.0	238.0	238.0	238.0	234.5	234.5	238.0	241.5	245.0	248.5
47.5°	227.5	227.5	224.0	224.0	224.0	224.0	224.0	224.0	227.5	227.5	227.5
50°	220.5	220.5	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0
52.5°	213.5	210.0	210.0	210.0	210.0	206.5	206.5	206.5	206.5	206.5	206.5
55°	203.0	199.5	199.5	199.5	199.5	199.5	199.5	199.5	203.0	203.0	203.0
57.5°	192.5	189.0	189.0	189.0	192.5	192.5	192.5	192.5	196.0	196.0	196.0
60°	182.0	182.0	182.0	182.0	182.0	182.0	182.0	185.5	185.5	189.0	189.0
62.5°	171.5	171.5	171.5	171.5	175.0	175.0	175.0	175.0	178.5	178.5	178.5
65°	161.0	161.0	161.0	161.0	164.5	164.5	164.5	164.5	164.5	164.5	164.5
67.5°	150.5	150.5	150.5	150.5	150.5	150.5	150.5	154.0	154.0	157.5	157.5
70°	136.5	133.0	133.0	136.5	136.5	140.0	140.0	143.5	143.5	147.0	147.0
72.5°	122.5	122.5	122.5	122.5	122.5	122.5	122.5	126.0	129.5	129.5	133.0
75°	108.5	108.5	108.5	108.5	112.0	112.0	112.0	115.5	115.5	119.0	119.0
77.5°	98.0	94.5	94.5	94.5	98.0	98.0	98.0	101.5	101.5	105.0	105.0
80°	80.5	80.5	80.5	80.5	84.0	84.0	84.0	84.0	87.5	87.5	87.5
82.5°	66.5	66.5	66.5	66.5	66.5	66.5	66.5	66.5	70.0	70.0	70.0
85°	49.0	49.0	49.0	49.0	52.5	52.5	52.5	52.5	52.5	52.5	52.5
87.5°	31.5	31.5	31.5	31.5	31.5	31.5	31.5	31.5	35.0	35.0	35.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9
2.5°	2225.9	2225.9	2225.9	2225.9	2232.9	2236.4	2243.4	2246.9	2243.4	2239.9	2232.9
5°	1872.5	1876.0	1876.0	1879.5	1879.5	1879.5	1879.5	1879.5	1886.5	1893.5	1900.5
7.5°	1480.5	1484.0	1487.5	1491.0	1491.0	1491.0	1487.5	1487.5	1491.0	1491.0	1494.5
10°	1134.0	1148.0	1158.5	1169.0	1162.0	1151.5	1144.5	1134.0	1134.0	1134.0	1130.5
12.5°	857.5	861.0	868.0	871.5	868.0	868.0	864.5	861.0	864.5	871.5	875.0
15°	679.0	679.0	682.5	682.5	686.0	689.5	689.5	693.0	700.0	703.5	710.5
17.5°	563.5	567.0	567.0	570.5	570.5	574.0	574.0	574.0	581.0	588.0	598.5
20°	507.5	507.5	507.5	507.5	507.5	504.0	504.0	500.5	504.0	511.0	514.5
22.5°	455.0	458.5	458.5	458.5	455.0	451.5	444.5	441.0	441.0	444.5	444.5
25°	399.0	395.5	395.5	392.0	392.0	395.5	395.5	395.5	399.0	399.0	402.5
27.5°	367.5	364.0	364.0	360.5	360.5	364.0	364.0	364.0	364.0	364.0	364.0
30°	343.0	343.0	339.5	336.0	339.5	339.5	343.0	343.0	346.5	346.5	350.0
32.5°	325.5	322.0	322.0	318.5	322.0	322.0	325.5	325.5	329.0	332.5	332.5
35°	301.0	301.0	301.0	301.0	301.0	301.0	297.5	297.5	297.5	297.5	297.5
37.5°	287.0	287.0	283.5	280.0	280.0	280.0	280.0	280.0	276.5	273.0	269.5
40°	276.5	273.0	273.0	269.5	266.0	266.0	262.5	259.0	259.0	255.5	255.5
42.5°	262.5	259.0	259.0	255.5	252.0	252.0	248.5	245.0	245.0	245.0	241.5
45°	245.0	245.0	241.5	238.0	238.0	238.0	234.5	234.5	234.5	234.5	231.0
47.5°	227.5	227.5	224.0	224.0	224.0	224.0	220.5	220.5	220.5	220.5	220.5
50°	217.0	217.0	217.0	217.0	217.0	217.0	213.5	213.5	213.5	213.5	213.5
52.5°	206.5	206.5	206.5	206.5	206.5	206.5	206.5	206.5	206.5	206.5	206.5
55°	203.0	203.0	203.0	203.0	203.0	203.0	199.5	199.5	199.5	203.0	203.0
57.5°	196.0	196.0	192.5	192.5	192.5	192.5	192.5	192.5	192.5	192.5	192.5
60°	189.0	189.0	189.0	189.0	189.0	189.0	189.0	189.0	189.0	189.0	189.0
62.5°	178.5	178.5	178.5	178.5	178.5	182.0	182.0	182.0	182.0	182.0	178.5
65°	164.5	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0
67.5°	157.5	157.5	157.5	157.5	157.5	157.5	157.5	157.5	157.5	157.5	157.5
70°	147.0	147.0	143.5	143.5	143.5	147.0	147.0	147.0	147.0	147.0	147.0
72.5°	133.0	133.0	133.0	133.0	133.0	133.0	133.0	133.0	133.0	136.5	136.5
75°	119.0	119.0	119.0	119.0	119.0	119.0	119.0	119.0	119.0	119.0	119.0
77.5°	105.0	105.0	101.5	101.5	101.5	105.0	105.0	105.0	105.0	108.5	108.5
80°	87.5	87.5	87.5	87.5	87.5	87.5	87.5	87.5	87.5	91.0	91.0
82.5°	70.0	70.0	70.0	70.0	70.0	70.0	70.0	70.0	70.0	73.5	73.5
85°	52.5	56.0	56.0	56.0	56.0	56.0	56.0	56.0	56.0	59.5	59.5
87.5°	35.0	35.0	35.0	35.0	35.0	35.0	31.5	31.5	31.5	31.5	28.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9
2.5°	2229.4	2232.9	2236.4	2236.4	2239.9	2243.4	2243.4	2257.4	2271.4	2278.4	2285.4
5°	1907.5	1904.0	1904.0	1900.5	1897.0	1907.5	1918.0	1939.0	1960.0	1963.5	1970.5
7.5°	1494.5	1498.0	1501.5	1501.5	1505.0	1494.5	1480.5	1484.0	1487.5	1505.0	1519.0
10°	1130.5	1134.0	1137.5	1137.5	1141.0	1137.5	1130.5	1141.0	1151.5	1165.5	1183.0
12.5°	878.5	889.0	899.5	906.5	917.0	924.0	927.5	941.5	952.0	969.5	987.0
15°	717.5	724.5	731.5	738.5	745.5	752.5	759.5	773.5	787.5	808.5	829.5
17.5°	605.5	605.5	609.0	609.0	609.0	616.0	623.0	630.0	633.5	654.5	675.5
20°	518.0	514.5	511.0	507.5	504.0	511.0	514.5	518.0	521.5	535.5	546.0
22.5°	444.5	444.5	448.0	448.0	448.0	444.5	437.5	441.0	441.0	448.0	458.5
25°	402.5	402.5	402.5	399.0	399.0	402.5	406.0	406.0	402.5	406.0	409.5
27.5°	364.0	367.5	367.5	371.0	371.0	374.5	374.5	374.5	374.5	378.0	381.5
30°	350.0	350.0	353.5	353.5	353.5	357.0	360.5	360.5	360.5	364.0	371.0
32.5°	336.0	339.5	343.0	346.5	350.0	353.5	353.5	357.0	357.0	360.5	364.0
35°	297.5	294.0	294.0	290.5	287.0	287.0	287.0	287.0	283.5	287.0	287.0
37.5°	266.0	266.0	266.0	262.5	262.5	266.0	266.0	266.0	266.0	269.5	269.5
40°	252.0	252.0	252.0	252.0	252.0	252.0	252.0	255.5	255.5	259.0	262.5
42.5°	241.5	241.5	241.5	241.5	241.5	245.0	245.0	245.0	245.0	248.5	248.5
45°	231.0	231.0	231.0	231.0	231.0	231.0	231.0	234.5	234.5	238.0	241.5
47.5°	220.5	220.5	220.5	220.5	220.5	224.0	227.5	227.5	227.5	231.0	231.0
50°	213.5	213.5	213.5	213.5	213.5	217.0	217.0	220.5	220.5	224.0	227.5
52.5°	206.5	206.5	206.5	206.5	206.5	210.0	210.0	213.5	213.5	217.0	220.5
55°	203.0	203.0	203.0	199.5	199.5	203.0	203.0	206.5	206.5	210.0	210.0
57.5°	192.5	192.5	192.5	192.5	192.5	192.5	192.5	196.0	196.0	199.5	203.0
60°	189.0	189.0	185.5	185.5	182.0	185.5	185.5	189.0	189.0	192.5	192.5
62.5°	178.5	178.5	178.5	175.0	175.0	178.5	178.5	178.5	178.5	182.0	185.5
65°	168.0	168.0	168.0	164.5	164.5	168.0	168.0	168.0	168.0	171.5	175.0
67.5°	157.5	157.5	157.5	154.0	154.0	154.0	154.0	157.5	157.5	161.0	164.5
70°	147.0	147.0	147.0	143.5	143.5	143.5	140.0	143.5	147.0	150.5	150.5
72.5°	136.5	136.5	136.5	133.0	133.0	133.0	129.5	133.0	133.0	136.5	136.5
75°	119.0	119.0	119.0	119.0	119.0	119.0	115.5	115.5	115.5	119.0	119.0
77.5°	108.5	108.5	108.5	105.0	105.0	105.0	101.5	101.5	101.5	105.0	105.0
80°	91.0	91.0	91.0	87.5	87.5	87.5	84.0	84.0	84.0	87.5	87.5
82.5°	73.5	73.5	73.5	70.0	70.0	70.0	66.5	66.5	66.5	70.0	70.0
85°	59.5	59.5	59.5	59.5	59.5	59.5	56.0	56.0	56.0	59.5	63.0
87.5°	28.0	28.0	31.5	31.5	31.5	31.5	28.0	28.0	24.5	24.5	28.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9
2.5°	2292.4	2299.4	2316.9	2330.9	2348.4	2362.4	2372.9	2386.9	2397.4	2407.9	2414.9
5°	1974.0	1977.5	1995.0	2012.5	2026.5	2044.0	2068.5	2093.0	2117.5	2142.0	2159.5
7.5°	1536.5	1550.5	1571.5	1596.0	1617.0	1638.0	1662.5	1690.5	1715.0	1739.5	1764.0
10°	1197.0	1211.0	1232.0	1253.0	1270.5	1291.5	1319.5	1347.5	1375.5	1403.5	1431.5
12.5°	1004.5	1022.0	1046.5	1071.0	1092.0	1116.5	1151.5	1183.0	1218.0	1249.5	1284.5
15°	847.0	868.0	899.5	934.5	966.0	997.5	1032.5	1067.5	1099.0	1134.0	1169.0
17.5°	696.5	717.5	745.5	777.0	805.0	833.0	875.0	913.5	955.5	994.0	1032.5
20°	560.0	570.5	598.5	626.5	654.5	682.5	714.0	745.5	777.0	808.5	857.5
22.5°	465.5	472.5	486.5	497.0	511.0	521.5	553.0	584.5	612.5	644.0	689.5
25°	409.5	413.0	423.5	430.5	441.0	448.0	469.0	486.5	507.5	525.0	567.0
27.5°	381.5	385.0	388.5	392.0	395.5	399.0	413.0	427.0	437.5	451.5	490.0
30°	374.5	378.0	388.5	395.5	406.0	413.0	420.0	427.0	434.0	441.0	465.5
32.5°	367.5	371.0	371.0	367.5	367.5	364.0	371.0	374.5	381.5	385.0	406.0
35°	290.5	290.5	294.0	297.5	301.0	304.5	315.0	322.0	332.5	339.5	357.0
37.5°	273.0	273.0	276.5	283.5	287.0	290.5	297.5	304.5	311.5	318.5	336.0
40°	262.5	266.0	269.5	273.0	276.5	280.0	287.0	290.5	297.5	301.0	315.0
42.5°	252.0	252.0	255.5	262.5	266.0	269.5	276.5	280.0	287.0	290.5	304.5
45°	245.0	248.5	252.0	255.5	255.5	259.0	266.0	273.0	276.5	283.5	297.5
47.5°	234.5	234.5	241.5	245.0	252.0	255.5	262.5	266.0	273.0	276.5	290.5
50°	227.5	231.0	238.0	241.5	248.5	252.0	262.5	269.5	280.0	287.0	294.0
52.5°	220.5	224.0	231.0	234.5	241.5	245.0	259.0	273.0	283.5	297.5	297.5
55°	213.5	213.5	220.5	231.0	238.0	245.0	252.0	262.5	269.5	276.5	276.5
57.5°	203.0	206.5	213.5	224.0	231.0	238.0	245.0	252.0	255.5	262.5	259.0
60°	196.0	196.0	206.5	217.0	227.5	238.0	238.0	238.0	234.5	234.5	234.5
62.5°	185.5	189.0	203.0	220.5	234.5	248.5	238.0	227.5	217.0	206.5	210.0
65°	178.5	182.0	189.0	199.5	206.5	213.5	206.5	203.0	196.0	189.0	192.5
67.5°	164.5	168.0	171.5	171.5	175.0	175.0	175.0	175.0	175.0	175.0	178.5
70°	154.0	154.0	154.0	157.5	157.5	157.5	157.5	157.5	157.5	157.5	161.0
72.5°	140.0	140.0	140.0	140.0	140.0	140.0	140.0	140.0	140.0	140.0	143.5
75°	122.5	122.5	122.5	122.5	122.5	122.5	122.5	122.5	122.5	122.5	126.0
77.5°	108.5	108.5	108.5	108.5	108.5	108.5	108.5	108.5	105.0	105.0	108.5
80°	91.0	91.0	91.0	91.0	87.5	87.5	87.5	87.5	87.5	87.5	91.0
82.5°	73.5	73.5	73.5	73.5	70.0	70.0	70.0	70.0	66.5	66.5	70.0
85°	66.5	70.0	70.0	73.5	73.5	73.5	70.0	66.5	63.0	59.5	59.5
87.5°	28.0	28.0	28.0	28.0	24.5	24.5	24.5	24.5	24.5	24.5	24.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9
2.5°	2425.4	2432.4	2439.4	2449.9	2463.9	2474.4	2484.9	2505.9	2530.4	2551.4	2572.4
5°	2177.0	2194.4	2211.9	2232.9	2253.9	2271.4	2292.4	2334.4	2376.4	2414.9	2456.9
7.5°	1785.0	1809.5	1830.5	1865.5	1897.0	1932.0	1963.5	2016.0	2065.0	2117.5	2166.5
10°	1459.5	1487.5	1515.5	1561.0	1610.0	1655.5	1701.0	1743.0	1788.5	1830.5	1872.5
12.5°	1319.5	1351.0	1386.0	1414.0	1445.5	1473.5	1501.5	1550.5	1599.5	1648.5	1697.5
15°	1204.0	1239.0	1274.0	1309.0	1340.5	1375.5	1407.0	1449.0	1494.5	1536.5	1578.5
17.5°	1071.0	1106.0	1144.5	1183.0	1221.5	1260.0	1298.5	1358.0	1417.5	1473.5	1533.0
20°	903.0	952.0	997.5	1050.0	1102.5	1155.0	1207.5	1270.5	1333.5	1393.0	1456.0
22.5°	735.0	780.5	826.0	889.0	952.0	1011.5	1074.5	1158.5	1239.0	1323.0	1403.5
25°	612.5	654.5	696.5	766.5	833.0	903.0	969.5	1071.0	1169.0	1270.5	1368.5
27.5°	528.5	567.0	605.5	679.0	752.5	822.5	896.0	1008.0	1116.5	1228.5	1337.0
30°	490.0	514.5	539.0	609.0	679.0	745.5	815.5	924.0	1032.5	1141.0	1249.5
32.5°	427.0	448.0	469.0	532.0	595.0	654.5	717.5	829.5	938.0	1050.0	1158.5
35°	378.0	395.5	413.0	472.5	528.5	588.0	644.0	756.0	868.0	980.0	1092.0
37.5°	350.0	367.5	381.5	434.0	490.0	542.5	595.0	707.0	815.5	927.5	1036.0
40°	329.0	339.5	353.5	406.0	455.0	507.5	556.5	658.0	763.0	864.5	966.0
42.5°	315.0	329.0	339.5	385.0	434.0	479.5	525.0	623.0	721.0	815.5	913.5
45°	311.5	325.5	339.5	378.0	416.5	451.5	490.0	584.5	679.0	773.5	868.0
47.5°	304.5	315.0	329.0	360.5	388.5	420.0	448.0	542.5	637.0	728.0	822.5
50°	301.0	304.5	311.5	339.5	367.5	395.5	423.5	518.0	612.5	707.0	801.5
52.5°	297.5	297.5	297.5	322.0	346.5	367.5	392.0	486.5	584.5	679.0	773.5
55°	276.5	273.0	273.0	297.5	318.5	343.0	364.0	458.5	553.0	644.0	738.5
57.5°	255.5	252.0	248.5	269.5	290.5	311.5	332.5	427.0	525.0	619.5	714.0
60°	234.5	231.0	231.0	252.0	269.5	290.5	308.0	406.0	500.5	598.5	693.0
62.5°	210.0	213.5	213.5	231.0	252.0	269.5	287.0	385.0	486.5	584.5	682.5
65°	192.5	196.0	196.0	217.0	238.0	259.0	280.0	374.5	472.5	567.0	661.5
67.5°	178.5	182.0	182.0	206.5	227.5	252.0	273.0	357.0	444.5	528.5	612.5
70°	164.5	164.5	168.0	192.5	217.0	241.5	266.0	339.5	413.0	483.0	556.5
72.5°	147.0	150.5	154.0	178.5	199.5	224.0	245.0	311.5	378.0	444.5	511.0
75°	129.5	133.0	136.5	157.5	178.5	199.5	220.5	283.5	343.0	406.0	465.5
77.5°	115.5	119.0	122.5	140.0	157.5	175.0	192.5	238.0	287.0	332.5	378.0
80°	94.5	94.5	98.0	112.0	126.0	136.5	150.5	182.0	213.5	241.5	273.0
82.5°	70.0	73.5	73.5	84.0	91.0	101.5	108.5	126.0	140.0	157.5	171.5
85°	59.5	56.0	56.0	63.0	66.5	73.5	77.0	87.5	94.5	105.0	112.0
87.5°	24.5	21.0	21.0	24.5	31.5	35.0	38.5	38.5	42.0	42.0	42.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9
2.5°	2582.9	2589.9	2600.4	2607.4	2624.9	2638.9	2656.4	2670.4	2680.9	2698.4	2691.4
5°	2488.4	2519.9	2551.4	2582.9	2607.4	2631.9	2652.9	2677.4	2705.4	2757.9	2771.9
7.5°	2208.4	2250.4	2288.9	2330.9	2379.9	2428.9	2477.9	2526.9	2572.4	2638.9	2680.9
10°	1932.0	1991.5	2047.5	2107.0	2152.5	2197.9	2239.9	2285.4	2348.4	2414.9	2491.9
12.5°	1757.0	1816.5	1876.0	1935.5	2002.0	2065.0	2131.5	2194.4	2253.9	2306.4	2393.9
15°	1641.5	1708.0	1771.0	1834.0	1914.5	1991.5	2072.0	2149.0	2236.4	2306.4	2365.9
17.5°	1613.5	1694.0	1771.0	1851.5	1935.5	2019.5	2103.5	2187.5	2274.9	2379.9	2456.9
20°	1564.5	1673.0	1781.5	1890.0	1998.5	2103.5	2211.9	2316.9	2432.4	2558.4	2593.4
22.5°	1536.5	1666.0	1799.0	1928.5	2075.5	2225.9	2372.9	2519.9	2642.4	2736.9	2841.9
25°	1533.0	1694.0	1858.5	2019.5	2204.9	2386.9	2572.4	2754.4	2911.9	3006.4	3090.4
27.5°	1529.5	1725.5	1918.0	2110.5	2337.9	2561.9	2789.4	3013.4	3160.4	3296.9	3366.9
30°	1487.5	1722.0	1960.0	2194.4	2449.9	2705.4	2960.9	3216.4	3366.9	3461.4	3496.4
32.5°	1435.0	1711.5	1988.0	2264.4	2554.9	2845.4	3132.4	3422.9	3541.9	3622.4	3594.4
35°	1393.0	1697.5	1998.5	2299.4	2607.4	2918.9	3226.9	3534.9	3706.4	3818.4	3772.9
37.5°	1354.5	1673.0	1991.5	2309.9	2670.4	3030.9	3391.4	3751.9	3916.4	4035.4	3982.9
40°	1309.0	1648.5	1991.5	2330.9	2743.9	3153.4	3566.4	3975.9	4189.4	4290.9	4210.4
42.5°	1270.5	1624.0	1981.0	2334.4	2775.4	3216.4	3657.4	4098.4	4336.4	4479.9	4378.4
45°	1221.5	1575.0	1925.0	2278.4	2764.9	3251.4	3734.4	4220.9	4497.4	4609.4	4469.4
47.5°	1169.0	1519.0	1865.5	2211.9	2729.9	3247.9	3765.9	4283.9	4539.4	4672.4	4542.9
50°	1151.5	1501.5	1848.0	2197.9	2757.9	3321.4	3881.4	4441.4	4626.9	4735.4	4563.9
52.5°	1148.0	1519.0	1893.5	2264.4	2827.9	3387.9	3951.4	4511.4	4661.9	4777.4	4623.4
55°	1137.5	1540.0	1939.0	2337.9	2925.9	3517.4	4105.4	4693.4	4843.9	4927.9	4812.4
57.5°	1148.0	1582.0	2012.5	2446.4	3051.9	3657.4	4262.9	4868.4	5050.4	5109.9	5085.4
60°	1155.0	1617.0	2075.5	2537.4	3128.9	3720.4	4311.9	4903.4	5092.4	5239.4	5267.4
62.5°	1137.5	1592.5	2044.0	2498.9	3034.4	3569.9	4105.4	4640.9	4952.4	5169.4	5295.4
65°	1085.0	1505.0	1928.5	2348.4	2841.9	3338.9	3832.4	4325.9	4654.9	4976.9	5078.4
67.5°	969.5	1326.5	1683.5	2040.5	2470.9	2901.4	3328.4	3758.9	4171.9	4483.4	4623.4
70°	840.0	1120.0	1403.5	1683.5	2075.5	2467.4	2859.4	3251.4	3615.4	3958.4	4091.4
72.5°	731.5	948.5	1169.0	1386.0	1666.0	1942.5	2222.4	2498.9	2929.4	3272.4	3401.9
75°	623.0	780.5	934.5	1092.0	1284.5	1477.0	1666.0	1858.5	2163.0	2470.9	2600.4
77.5°	479.5	584.5	686.0	787.5	920.5	1050.0	1183.0	1312.5	1526.0	1757.0	1823.5
80°	332.5	392.0	448.0	507.5	612.5	717.5	822.5	927.5	1067.5	1197.0	1298.5
82.5°	206.5	245.0	280.0	315.0	399.0	483.0	563.5	647.5	703.5	710.5	812.0
85°	133.0	157.5	178.5	199.5	248.5	301.0	350.0	399.0	357.0	332.5	395.5
87.5°	52.5	66.5	77.0	87.5	84.0	80.5	77.0	73.5	63.0	56.0	70.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9
2.5°	2698.4	2708.9	2719.4	2726.4	2736.9	2740.4	2743.9	2743.9	2747.4	2750.9	2757.9
5°	2827.9	2848.9	2869.9	2887.4	2908.4	2925.9	2939.9	2957.4	2971.4	2971.4	2967.9
7.5°	2719.4	2771.9	2824.4	2876.9	2929.4	2967.9	3002.9	3041.4	3076.4	3083.4	3090.4
10°	2575.9	2631.9	2684.4	2740.4	2792.9	2852.4	2908.4	2964.4	3023.9	3034.4	3048.4
12.5°	2442.9	2509.4	2575.9	2638.9	2705.4	2747.4	2789.4	2827.9	2869.9	2897.9	2925.9
15°	2439.4	2495.4	2551.4	2603.9	2659.9	2684.4	2708.9	2729.9	2754.4	2754.4	2757.9
17.5°	2519.9	2554.9	2589.9	2621.4	2656.4	2659.9	2666.9	2670.4	2673.9	2663.4	2652.9
20°	2677.4	2691.4	2705.4	2719.4	2733.4	2708.9	2687.9	2663.4	2638.9	2610.9	2586.4
22.5°	2908.4	2876.9	2845.4	2813.9	2782.4	2740.4	2694.9	2652.9	2607.4	2572.4	2537.4
25°	3125.4	3086.9	3048.4	3009.9	2971.4	2880.4	2789.4	2694.9	2603.9	2565.4	2526.9
27.5°	3415.9	3356.4	3296.9	3237.4	3177.9	3055.4	2932.9	2810.4	2687.9	2621.4	2558.4
30°	3485.9	3419.4	3352.9	3282.9	3216.4	3097.4	2981.9	2862.9	2743.9	2666.9	2593.4
32.5°	3587.4	3510.4	3433.4	3356.4	3279.4	3163.9	3048.4	2929.4	2813.9	2743.9	2670.4
35°	3755.4	3667.9	3580.4	3489.4	3401.9	3282.9	3167.4	3048.4	2929.4	2848.9	2771.9
37.5°	3898.9	3797.4	3695.9	3594.4	3492.9	3387.9	3279.4	3174.4	3065.9	2985.4	2908.4
40°	4059.9	3947.9	3835.9	3727.4	3615.4	3517.4	3419.4	3317.9	3219.9	3156.9	3093.9
42.5°	4199.9	4063.4	3930.4	3797.4	3660.9	3594.4	3531.4	3464.9	3398.4	3366.9	3331.9
45°	4297.9	4171.9	4042.4	3916.4	3790.4	3741.4	3692.4	3643.4	3594.4	3625.9	3657.4
47.5°	4339.9	4238.4	4140.4	4042.4	3940.9	3958.4	3975.9	3989.9	4007.4	4049.4	4094.9
50°	4378.4	4322.4	4262.9	4206.9	4147.4	4213.9	4276.9	4343.4	4409.9	4497.4	4584.9
52.5°	4455.4	4423.9	4395.9	4364.4	4332.9	4448.4	4563.9	4679.4	4794.9	4892.9	4990.9
55°	4686.4	4661.9	4637.4	4609.4	4584.9	4749.4	4910.4	5074.9	5239.4	5340.9	5442.4
57.5°	5004.9	4990.9	4973.4	4959.4	4941.9	5102.9	5260.4	5417.9	5578.9	5676.9	5778.4
60°	5246.4	5249.9	5249.9	5253.4	5253.4	5375.9	5498.4	5624.4	5746.9	5830.9	5918.4
62.5°	5375.9	5368.9	5361.9	5354.9	5347.9	5449.4	5550.9	5652.4	5753.9	5816.9	5879.9
65°	5235.9	5274.4	5312.9	5351.4	5389.9	5403.9	5414.4	5428.4	5438.9	5477.4	5515.9
67.5°	4766.9	4843.9	4917.4	4994.4	5067.9	5015.4	4966.4	4913.9	4861.4	4871.9	4878.9
70°	4245.4	4332.9	4423.9	4511.4	4598.9	4476.4	4353.9	4227.9	4105.4	4063.4	4021.4
72.5°	3580.4	3657.4	3737.9	3814.9	3891.9	3741.4	3594.4	3443.9	3293.4	3219.9	3146.4
75°	2736.9	2827.9	2922.4	3013.4	3104.4	2936.4	2764.9	2596.9	2425.4	2376.4	2330.9
77.5°	1995.0	2103.5	2211.9	2320.4	2428.9	2278.4	2128.0	1974.0	1823.5	1795.5	1767.5
80°	1452.5	1536.5	1617.0	1701.0	1781.5	1694.0	1606.5	1519.0	1431.5	1428.0	1424.5
82.5°	980.0	1053.5	1123.5	1197.0	1267.0	1232.0	1200.5	1165.5	1130.5	1165.5	1204.0
85°	504.0	605.5	710.5	812.0	913.5	903.0	896.0	885.5	875.0	920.5	962.5
87.5°	101.5	189.0	276.5	360.5	448.0	427.0	406.0	381.5	360.5	374.5	385.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9
2.5°	2761.4	2764.9	2764.9	2764.9	2764.9	2764.9	2757.9	2754.4	2747.4	2740.4	2729.9
5°	2967.9	2964.4	2950.4	2936.4	2918.9	2904.9	2894.4	2880.4	2869.9	2855.9	2834.9
7.5°	3097.4	3104.4	3079.9	3058.9	3034.4	3009.9	2985.4	2960.9	2936.4	2911.9	2862.9
10°	3058.9	3069.4	3055.4	3041.4	3023.9	3009.9	2981.9	2950.4	2922.4	2890.9	2831.4
12.5°	2950.4	2978.4	2971.4	2964.4	2957.4	2950.4	2932.9	2911.9	2894.4	2873.4	2806.9
15°	2757.9	2757.9	2761.4	2764.9	2764.9	2768.4	2771.9	2775.4	2778.9	2782.4	2743.9
17.5°	2642.4	2631.9	2631.9	2631.9	2631.9	2631.9	2645.9	2663.4	2677.4	2691.4	2680.9
20°	2558.4	2533.9	2530.4	2530.4	2526.9	2523.4	2547.9	2575.9	2600.4	2624.9	2638.9
22.5°	2502.4	2467.4	2463.9	2460.4	2456.9	2453.4	2484.9	2516.4	2547.9	2579.4	2628.4
25°	2488.4	2449.9	2453.4	2456.9	2456.9	2460.4	2484.9	2509.4	2533.9	2558.4	2642.4
27.5°	2491.9	2428.9	2432.4	2435.9	2435.9	2439.4	2477.9	2512.9	2551.4	2586.4	2691.4
30°	2516.4	2442.9	2435.9	2428.9	2421.9	2414.9	2467.4	2519.9	2572.4	2624.9	2705.4
32.5°	2600.4	2530.4	2512.9	2495.4	2477.9	2460.4	2523.4	2582.9	2645.9	2705.4	2771.9
35°	2691.4	2614.4	2607.4	2600.4	2589.9	2582.9	2638.9	2698.4	2754.4	2810.4	2869.9
37.5°	2827.9	2750.9	2743.9	2733.4	2726.4	2715.9	2778.9	2838.4	2901.4	2960.9	3013.4
40°	3030.9	2967.9	2964.4	2964.4	2960.9	2957.4	3006.4	3058.9	3107.9	3156.9	3191.9
42.5°	3300.4	3268.9	3279.4	3293.4	3303.9	3314.4	3352.9	3394.9	3433.4	3471.9	3461.4
45°	3688.9	3720.4	3723.9	3727.4	3730.9	3734.4	3744.9	3758.9	3769.4	3779.9	3737.9
47.5°	4136.9	4178.9	4199.9	4220.9	4238.4	4259.4	4245.4	4227.9	4213.9	4196.4	4091.4
50°	4668.9	4756.4	4752.9	4749.4	4742.4	4738.9	4710.9	4682.9	4651.4	4623.4	4469.4
52.5°	5088.9	5186.9	5204.4	5221.9	5239.4	5256.9	5204.4	5151.9	5095.9	5043.4	4850.9
55°	5540.4	5641.9	5645.4	5648.9	5648.9	5652.4	5578.9	5505.4	5428.4	5354.9	5155.4
57.5°	5876.4	5974.4	5963.9	5956.9	5946.4	5935.9	5848.4	5760.9	5673.4	5585.9	5386.4
60°	6002.4	6086.4	6065.4	6044.4	6019.9	5998.9	5932.4	5865.9	5795.9	5729.4	5536.9
62.5°	5942.9	6005.9	5974.4	5946.4	5914.9	5883.4	5799.4	5711.9	5627.9	5540.4	5400.4
65°	5550.9	5589.4	5547.4	5508.9	5470.4	5428.4	5358.4	5288.4	5214.9	5144.9	5050.4
67.5°	4889.4	4896.4	4892.9	4889.4	4885.9	4882.4	4780.9	4679.4	4574.4	4472.9	4465.9
70°	3982.9	3940.9	3947.9	3958.4	3965.4	3972.4	3895.4	3821.9	3744.9	3667.9	3702.9
72.5°	3072.9	2999.4	3016.9	3037.9	3055.4	3072.9	3009.9	2950.4	2887.4	2824.4	2873.4
75°	2281.9	2236.4	2253.9	2274.9	2292.4	2309.9	2285.4	2260.9	2232.9	2208.4	2253.9
77.5°	1739.5	1711.5	1715.0	1715.0	1718.5	1718.5	1722.0	1729.0	1732.5	1736.0	1785.0
80°	1417.5	1414.0	1410.5	1407.0	1400.0	1396.5	1431.5	1466.5	1501.5	1536.5	1561.0
82.5°	1239.0	1274.0	1253.0	1235.5	1214.5	1193.5	1225.0	1256.5	1288.0	1319.5	1309.0
85°	1008.0	1050.0	1011.5	973.0	931.0	892.5	920.5	945.0	973.0	997.5	983.5
87.5°	399.0	409.5	346.5	287.0	224.0	161.0	255.5	346.5	441.0	532.0	546.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9	2519.9
2.5°	2719.4	2705.4	2694.9	2691.4	2684.4	2680.9	2673.9	2666.9	2656.4	2649.4	2638.9
5°	2810.4	2789.4	2764.9	2729.9	2698.4	2663.4	2628.4	2596.9	2565.4	2530.4	2498.9
7.5°	2813.9	2764.9	2715.9	2670.4	2621.4	2575.9	2526.9	2484.9	2439.4	2393.9	2351.9
10°	2775.4	2715.9	2656.4	2596.9	2540.9	2481.4	2421.9	2372.9	2320.4	2267.9	2218.9
12.5°	2743.9	2677.4	2610.9	2540.9	2474.4	2404.4	2334.4	2285.4	2236.4	2187.5	2138.5
15°	2705.4	2663.4	2624.9	2561.9	2498.9	2435.9	2372.9	2306.4	2243.4	2177.0	2110.5
17.5°	2673.9	2663.4	2652.9	2610.9	2568.9	2523.4	2481.4	2414.9	2348.4	2278.4	2211.9
20°	2656.4	2670.4	2684.4	2663.4	2642.4	2617.9	2596.9	2547.9	2498.9	2446.4	2397.4
22.5°	2677.4	2729.9	2778.9	2782.4	2789.4	2792.9	2796.4	2750.9	2705.4	2656.4	2610.9
25°	2726.4	2810.4	2894.4	2939.9	2985.4	3034.4	3079.9	3051.9	3023.9	2995.9	2967.9
27.5°	2792.9	2897.9	3002.9	3069.4	3132.4	3198.9	3265.4	3261.9	3258.4	3251.4	3247.9
30°	2782.4	2862.9	2943.4	3023.9	3104.4	3184.9	3265.4	3307.4	3345.9	3387.9	3429.9
32.5°	2841.9	2908.4	2978.4	3062.4	3146.4	3233.9	3317.9	3405.4	3489.4	3576.9	3664.4
35°	2932.9	2992.4	3055.4	3146.4	3240.9	3331.9	3426.4	3531.4	3639.9	3748.4	3853.4
37.5°	3069.4	3121.9	3177.9	3254.9	3335.4	3412.4	3492.9	3646.9	3800.9	3958.4	4112.4
40°	3226.9	3261.9	3296.9	3370.4	3443.9	3517.4	3590.9	3783.4	3975.9	4168.4	4360.9
42.5°	3454.4	3443.9	3433.4	3492.9	3555.9	3615.4	3678.4	3853.4	4028.4	4203.4	4378.4
45°	3695.9	3653.9	3611.9	3639.9	3671.4	3699.4	3730.9	3909.4	4087.9	4269.9	4448.4
47.5°	3986.4	3881.4	3776.4	3751.9	3727.4	3699.4	3674.9	3867.4	4059.9	4255.9	4448.4
50°	4315.4	4157.9	4003.9	3940.9	3874.4	3811.4	3744.9	3902.4	4063.4	4224.4	4381.9
52.5°	4658.4	4462.4	4269.9	4171.9	4073.9	3972.4	3874.4	4007.4	4143.9	4280.4	4413.4
55°	4952.4	4752.9	4549.9	4434.4	4318.9	4203.4	4087.9	4220.9	4353.9	4486.9	4619.9
57.5°	5186.9	4987.4	4787.9	4679.4	4567.4	4458.9	4346.9	4472.9	4602.4	4731.9	4857.9
60°	5347.9	5155.4	4962.9	4857.9	4752.9	4647.9	4542.9	4693.4	4843.9	4997.9	5148.4
62.5°	5263.9	5123.9	4983.9	4938.4	4892.9	4843.9	4798.4	4941.9	5081.9	5225.4	5368.9
65°	4955.9	4861.4	4766.9	4812.4	4861.4	4906.9	4955.9	5050.4	5144.9	5242.9	5337.4
67.5°	4455.4	4448.4	4437.9	4539.4	4640.9	4745.9	4847.4	4910.4	4969.9	5032.9	5095.9
70°	3737.9	3776.4	3811.4	3986.4	4161.4	4336.4	4511.4	4535.9	4560.4	4584.9	4609.4
72.5°	2925.9	2974.9	3027.4	3258.4	3485.9	3716.9	3947.9	3933.9	3919.9	3902.4	3888.4
75°	2302.9	2348.4	2397.4	2610.9	2824.4	3037.9	3251.4	3191.9	3135.9	3076.4	3016.9
77.5°	1837.5	1886.5	1939.0	2138.5	2337.9	2540.9	2740.4	2596.9	2453.4	2309.9	2166.5
80°	1582.0	1606.5	1627.5	1764.0	1897.0	2033.5	2170.0	2023.0	1872.5	1722.0	1575.0
82.5°	1298.5	1284.5	1274.0	1354.5	1435.0	1515.5	1596.0	1456.0	1316.0	1172.5	1032.5
85°	969.5	955.5	941.5	983.5	1025.5	1071.0	1113.0	952.0	791.0	626.5	465.5
87.5°	563.5	577.5	591.5	637.0	682.5	731.5	777.0	612.5	448.0	280.0	115.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P671897
 CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	2519.9	2519.9
2.5°	2617.9	2600.4
5°	2474.4	2449.9
7.5°	2316.9	2285.4
10°	2173.5	2131.5
12.5°	2082.5	2030.0
15°	2047.5	1984.5
17.5°	2152.5	2093.0
20°	2313.4	2232.9
22.5°	2509.4	2411.4
25°	2848.9	2729.9
27.5°	3125.4	3002.9
30°	3296.9	3163.9
32.5°	3485.9	3310.9
35°	3681.9	3513.9
37.5°	3919.9	3730.9
40°	4164.9	3968.9
42.5°	4248.9	4122.9
45°	4329.4	4210.4
47.5°	4346.9	4248.9
50°	4364.4	4350.4
52.5°	4413.4	4409.9
55°	4623.4	4626.9
57.5°	4882.4	4903.4
60°	5120.4	5095.9
62.5°	5242.9	5116.9
65°	5158.9	4983.9
67.5°	4906.9	4717.9
70°	4353.9	4098.4
72.5°	3664.4	3440.4
75°	2824.4	2635.4
77.5°	2009.0	1851.5
80°	1414.0	1256.5
82.5°	906.5	780.5
85°	409.5	357.0
87.5°	115.5	112.0
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P671897

CATALOG NUMBER: CCP-SA-2D-840-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)