

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P671899

Luminaire Tested: **CCP-SA-1A-850-U-SLR**

Issue Date: 04/16/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P671899  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA-1A-850-U-SLR  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @350mA w/ SLR  
distribution lens  
Light Source: (16) 5000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1981.1 lumens  
Efficiency: N/A  
Efficacy: 110.1 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B0 - U0 - G1


Input Watts (W): 18  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 2.8 fc  
 Type IV - Short - N/A

REPORT NUMBER: P671899  
CATALOG NUMBER: CCP-SA-1A-850-U-SLR

## Luminous Intensity Polar Plot



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 407.6    | 0.0    | 407.6  |
|                    | % Fixture | 20.6     | 0.0    | 20.6   |
| <b>Street Side</b> | Lumens    | 1573.5   | 0.0    | 1573.5 |
|                    | % Fixture | 79.4     | 0.0    | 79.4   |
| <b>Total</b>       | Lumens    | 1981.1   | 0.0    | 1981.1 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 49.2   | 2.5       |
| 10°-20°   | 103.8  | 5.2       |
| 20°-30°   | 151.9  | 7.7       |
| 30°-40°   | 213.9  | 10.8      |
| 40°-50°   | 294.0  | 14.8      |
| 50°-60°   | 400.7  | 20.2      |
| 60°-70°   | 438.6  | 22.1      |
| 70°-80°   | 253.3  | 12.8      |
| 80°-90°   | 75.9   | 3.8       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 1981.1 | 100.0     |
| 0°-180°   | 1981.1 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P671899


CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |        |
|------|-------------|--------|-----------|-------------------------|------|--------|
|      |             |        |           | B                       | U    | G      |
| FL   | (0°-30°)    | 203.5  | 10.3      |                         |      |        |
| FM   | (30°-60°)   | 723.0  | 36.5      |                         |      |        |
| FH   | (60°-80°)   | 582.6  | 29.4      |                         |      | G0/660 |
| FVH  | (80°-90°)   | 64.5   | 3.3       |                         |      | G1/100 |
| BL   | (0°-30°)    | 101.3  | 5.1       | B0/110                  |      |        |
| BM   | (30°-60°)   | 185.6  | 9.4       | B0/220                  |      |        |
| BH   | (60°-80°)   | 109.2  | 5.5       | B0/110                  |      | G0/110 |
| BVH  | (80°-90°)   | 11.4   | 0.6       |                         |      | G1/100 |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |        |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |        |

**BUG Rating: B0-U0-G1**

Type IV Short



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°     | 7.5°  | 10°   | 12.5° | 15°   | 17.5° | 20°   | 22.5° | 25°   |
|--------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 632.7  | 632.7  | 632.7  | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 |
| 2.5°   | 652.9  | 649.3  | 646.7  | 644.1 | 640.6 | 637.9 | 634.4 | 630.9 | 626.5 | 623.0 | 618.6 |
| 5°     | 615.1  | 604.5  | 594.0  | 587.8 | 580.8 | 574.7 | 567.6 | 559.7 | 551.8 | 543.0 | 535.1 |
| 7.5°   | 573.8  | 560.6  | 547.4  | 536.9 | 525.5 | 514.9 | 503.5 | 493.8 | 484.2 | 474.5 | 464.8 |
| 10°    | 535.1  | 522.8  | 510.5  | 497.3 | 483.3 | 470.1 | 456.0 | 442.9 | 429.7 | 416.5 | 403.3 |
| 12.5°  | 509.6  | 494.7  | 480.6  | 465.7 | 451.6 | 436.7 | 421.8 | 409.5 | 397.2 | 384.0 | 371.7 |
| 15°    | 498.2  | 484.2  | 471.0  | 456.0 | 441.1 | 426.2 | 411.2 | 397.2 | 384.0 | 369.9 | 355.9 |
| 17.5°  | 525.5  | 505.2  | 485.0  | 465.7 | 446.4 | 427.0 | 407.7 | 390.1 | 372.6 | 355.0 | 337.4 |
| 20°    | 560.6  | 535.1  | 510.5  | 486.8 | 462.2 | 438.5 | 413.9 | 389.3 | 364.7 | 340.0 | 315.4 |
| 22.5°  | 605.4  | 576.4  | 548.3  | 517.5 | 485.9 | 455.2 | 423.5 | 392.8 | 362.0 | 330.4 | 299.6 |
| 25°    | 685.4  | 651.1  | 616.8  | 572.9 | 528.1 | 484.2 | 439.3 | 398.9 | 359.4 | 319.0 | 278.5 |
| 27.5°  | 753.9  | 707.3  | 661.6  | 608.9 | 556.2 | 503.5 | 450.8 | 404.2 | 358.5 | 311.9 | 265.4 |
| 30°    | 794.3  | 748.6  | 702.9  | 638.8 | 575.5 | 511.4 | 447.2 | 395.4 | 344.4 | 292.6 | 240.8 |
| 32.5°  | 831.2  | 780.3  | 729.3  | 659.0 | 587.8 | 517.5 | 446.4 | 389.3 | 333.0 | 275.9 | 218.8 |
| 35°    | 882.2  | 826.0  | 770.6  | 688.9 | 607.2 | 525.5 | 443.7 | 384.9 | 325.1 | 266.2 | 206.5 |
| 37.5°  | 936.7  | 867.3  | 798.7  | 708.2 | 617.7 | 527.2 | 436.7 | 378.7 | 320.7 | 262.7 | 204.7 |
| 40°    | 996.4  | 912.1  | 828.6  | 728.4 | 629.1 | 529.0 | 428.8 | 370.8 | 312.8 | 253.9 | 195.9 |
| 42.5°  | 1035.1 | 943.7  | 852.3  | 744.2 | 637.0 | 529.0 | 420.9 | 363.8 | 306.7 | 248.7 | 191.6 |
| 45°    | 1057.1 | 968.3  | 880.4  | 763.6 | 646.7 | 529.8 | 413.0 | 356.7 | 300.5 | 243.4 | 187.2 |
| 47.5°  | 1066.7 | 984.1  | 901.5  | 778.5 | 656.4 | 533.4 | 410.3 | 353.2 | 295.2 | 238.1 | 180.1 |
| 50°    | 1092.2 | 1019.3 | 946.3  | 814.5 | 683.6 | 551.8 | 420.0 | 358.5 | 297.9 | 236.4 | 174.9 |
| 52.5°  | 1107.1 | 1044.8 | 982.4  | 847.0 | 711.7 | 576.4 | 441.1 | 372.6 | 304.0 | 235.5 | 166.9 |
| 55°    | 1161.6 | 1101.9 | 1042.1 | 898.0 | 753.0 | 608.9 | 463.9 | 388.4 | 312.8 | 236.4 | 160.8 |
| 57.5°  | 1231.0 | 1167.8 | 1105.4 | 949.9 | 794.3 | 638.8 | 483.3 | 402.4 | 320.7 | 239.9 | 158.2 |
| 60°    | 1279.4 | 1217.9 | 1157.2 | 992.0 | 826.0 | 660.8 | 494.7 | 410.3 | 326.0 | 240.8 | 156.4 |
| 62.5°  | 1284.6 | 1205.6 | 1127.3 | 966.5 | 805.8 | 644.1 | 483.3 | 401.6 | 319.8 | 237.2 | 155.5 |
| 65°    | 1251.2 | 1159.0 | 1066.7 | 913.0 | 759.2 | 605.4 | 451.6 | 377.0 | 302.3 | 226.7 | 152.0 |
| 67.5°  | 1184.5 | 1076.4 | 968.3  | 827.7 | 687.1 | 546.5 | 406.0 | 341.8 | 278.5 | 214.4 | 150.3 |
| 70°    | 1028.9 | 934.0  | 840.0  | 717.9 | 596.6 | 474.5 | 352.4 | 299.6 | 247.8 | 195.1 | 142.3 |
| 72.5°  | 863.7  | 775.0  | 687.1  | 587.8 | 489.4 | 390.1 | 290.8 | 251.3 | 211.8 | 171.3 | 131.8 |
| 75°    | 661.6  | 594.9  | 529.0  | 455.2 | 381.3 | 306.7 | 232.9 | 203.9 | 174.9 | 145.9 | 116.9 |
| 77.5°  | 464.8  | 428.8  | 393.6  | 338.3 | 282.9 | 227.6 | 172.2 | 152.9 | 133.6 | 114.2 | 94.9  |
| 80°    | 315.4  | 295.2  | 275.9  | 236.4 | 196.8 | 156.4 | 116.9 | 104.6 | 91.4  | 79.1  | 65.9  |
| 82.5°  | 195.9  | 195.1  | 193.3  | 166.1 | 138.8 | 111.6 | 84.4  | 73.8  | 64.1  | 53.6  | 43.1  |
| 85°    | 89.6   | 104.6  | 118.6  | 103.7 | 88.7  | 73.8  | 58.9  | 51.8  | 44.8  | 36.9  | 29.9  |
| 87.5°  | 28.1   | 34.3   | 39.5   | 37.8  | 35.1  | 33.4  | 30.8  | 26.4  | 22.0  | 17.6  | 13.2  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 25° |
|--------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30°   | 32.5° | 35°   | 37.5° | 40°   | 42.5° | 45°   | 47.5° | 50°   | 52.5° |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 |
| 2.5°   | 615.1 | 612.4 | 608.9 | 605.4 | 601.0 | 597.5 | 593.1 | 588.7 | 587.8 | 586.1 | 585.2 |
| 5°     | 529.8 | 524.6 | 518.4 | 513.2 | 507.9 | 501.7 | 496.5 | 490.3 | 485.9 | 480.6 | 476.2 |
| 7.5°   | 455.2 | 446.4 | 436.7 | 427.0 | 418.3 | 409.5 | 399.8 | 391.0 | 386.6 | 382.2 | 377.8 |
| 10°    | 395.4 | 386.6 | 378.7 | 369.9 | 363.8 | 358.5 | 352.4 | 346.2 | 340.9 | 335.7 | 330.4 |
| 12.5°  | 365.5 | 359.4 | 353.2 | 347.1 | 340.0 | 333.9 | 326.9 | 319.8 | 313.7 | 308.4 | 302.3 |
| 15°    | 347.1 | 338.3 | 328.6 | 319.8 | 310.2 | 301.4 | 291.7 | 282.1 | 275.0 | 268.9 | 261.8 |
| 17.5°  | 325.1 | 311.9 | 299.6 | 286.5 | 275.9 | 265.4 | 253.9 | 243.4 | 235.5 | 226.7 | 218.8 |
| 20°    | 300.5 | 285.6 | 269.8 | 254.8 | 242.5 | 231.1 | 218.8 | 206.5 | 197.7 | 188.0 | 179.3 |
| 22.5°  | 279.4 | 260.1 | 239.9 | 219.7 | 206.5 | 193.3 | 179.3 | 166.1 | 158.2 | 149.4 | 141.5 |
| 25°    | 256.6 | 235.5 | 213.5 | 191.6 | 178.4 | 164.3 | 151.1 | 137.1 | 130.9 | 125.7 | 119.5 |
| 27.5°  | 244.3 | 223.2 | 201.2 | 180.1 | 167.8 | 154.6 | 142.3 | 129.2 | 124.8 | 119.5 | 115.1 |
| 30°    | 219.7 | 199.5 | 178.4 | 157.3 | 148.5 | 140.6 | 131.8 | 123.0 | 121.3 | 120.4 | 118.6 |
| 32.5°  | 197.7 | 176.6 | 155.5 | 134.4 | 126.5 | 118.6 | 110.7 | 102.8 | 101.9 | 100.2 | 99.3  |
| 35°    | 186.3 | 166.1 | 145.0 | 124.8 | 117.7 | 109.8 | 102.8 | 94.9  | 93.1  | 90.5  | 88.7  |
| 37.5°  | 183.6 | 162.6 | 140.6 | 119.5 | 112.5 | 105.4 | 97.5  | 90.5  | 88.7  | 87.0  | 85.2  |
| 40°    | 176.6 | 156.4 | 137.1 | 116.9 | 109.8 | 102.8 | 94.9  | 87.9  | 86.1  | 84.4  | 82.6  |
| 42.5°  | 171.3 | 152.0 | 131.8 | 111.6 | 105.4 | 99.3  | 92.3  | 86.1  | 84.4  | 82.6  | 80.0  |
| 45°    | 166.9 | 146.7 | 125.7 | 105.4 | 101.0 | 96.7  | 91.4  | 87.0  | 85.2  | 82.6  | 80.8  |
| 47.5°  | 159.9 | 140.6 | 120.4 | 100.2 | 95.8  | 92.3  | 87.9  | 83.5  | 81.7  | 80.0  | 78.2  |
| 50°    | 154.6 | 134.4 | 114.2 | 94.0  | 90.5  | 87.0  | 83.5  | 80.0  | 80.0  | 80.8  | 80.8  |
| 52.5°  | 147.6 | 128.3 | 109.0 | 89.6  | 86.1  | 82.6  | 79.1  | 75.6  | 76.4  | 77.3  | 78.2  |
| 55°    | 141.5 | 123.0 | 103.7 | 84.4  | 80.8  | 77.3  | 72.9  | 69.4  | 70.3  | 71.2  | 72.1  |
| 57.5°  | 138.8 | 119.5 | 100.2 | 80.8  | 77.3  | 72.9  | 69.4  | 65.0  | 65.0  | 65.0  | 65.0  |
| 60°    | 137.1 | 116.9 | 97.5  | 77.3  | 72.9  | 69.4  | 65.0  | 60.6  | 59.8  | 59.8  | 58.9  |
| 62.5°  | 136.2 | 116.0 | 96.7  | 76.4  | 71.2  | 66.8  | 61.5  | 56.2  | 55.4  | 54.5  | 53.6  |
| 65°    | 132.7 | 114.2 | 94.9  | 75.6  | 69.4  | 64.1  | 58.0  | 51.8  | 51.0  | 51.0  | 50.1  |
| 67.5°  | 131.8 | 112.5 | 94.0  | 74.7  | 68.5  | 61.5  | 55.4  | 48.3  | 47.4  | 46.6  | 45.7  |
| 70°    | 124.8 | 108.1 | 90.5  | 72.9  | 65.9  | 59.8  | 52.7  | 45.7  | 44.8  | 43.1  | 42.2  |
| 72.5°  | 116.0 | 101.0 | 85.2  | 69.4  | 62.4  | 55.4  | 48.3  | 41.3  | 40.4  | 39.5  | 37.8  |
| 75°    | 102.8 | 88.7  | 74.7  | 60.6  | 54.5  | 49.2  | 43.1  | 36.9  | 36.0  | 35.1  | 33.4  |
| 77.5°  | 84.4  | 72.9  | 62.4  | 51.0  | 46.6  | 42.2  | 37.8  | 33.4  | 32.5  | 31.6  | 29.9  |
| 80°    | 59.8  | 52.7  | 46.6  | 39.5  | 36.9  | 33.4  | 30.8  | 27.2  | 27.2  | 26.4  | 26.4  |
| 82.5°  | 39.5  | 36.0  | 32.5  | 29.0  | 27.2  | 25.5  | 23.7  | 22.0  | 22.0  | 21.1  | 21.1  |
| 85°    | 28.1  | 26.4  | 23.7  | 22.0  | 21.1  | 19.3  | 18.5  | 16.7  | 16.7  | 16.7  | 16.7  |
| 87.5°  | 13.2  | 13.2  | 12.3  | 12.3  | 11.4  | 11.4  | 10.5  | 9.7   | 9.7   | 9.7   | 9.7   |
| 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° | 47.5° | 50° | 52.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |

REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 55°   | 57.5° | 60°   | 62.5° | 65°   | 67.5° | 70°   | 72.5° | 75°   | 77.5° | 80°   |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 |
| 2.5°   | 583.4 | 580.8 | 578.2 | 574.7 | 572.0 | 568.5 | 564.1 | 560.6 | 556.2 | 556.2 | 555.3 |
| 5°     | 471.0 | 468.3 | 465.7 | 462.2 | 459.6 | 456.0 | 453.4 | 449.9 | 446.4 | 446.4 | 445.5 |
| 7.5°   | 373.4 | 368.2 | 362.9 | 356.7 | 351.5 | 348.0 | 344.4 | 340.0 | 336.5 | 333.9 | 331.3 |
| 10°    | 325.1 | 319.8 | 313.7 | 308.4 | 302.3 | 297.9 | 293.5 | 288.2 | 283.8 | 280.3 | 276.8 |
| 12.5°  | 296.1 | 290.0 | 283.8 | 277.7 | 271.5 | 265.4 | 260.1 | 253.9 | 247.8 | 243.4 | 239.0 |
| 15°    | 254.8 | 248.7 | 242.5 | 236.4 | 230.2 | 223.2 | 216.2 | 208.2 | 201.2 | 197.7 | 195.1 |
| 17.5°  | 210.0 | 203.9 | 196.8 | 190.7 | 183.6 | 178.4 | 173.1 | 167.8 | 162.6 | 159.0 | 156.4 |
| 20°    | 169.6 | 162.6 | 155.5 | 148.5 | 141.5 | 138.0 | 134.4 | 130.9 | 127.4 | 124.8 | 123.0 |
| 22.5°  | 132.7 | 128.3 | 124.8 | 120.4 | 116.0 | 113.3 | 111.6 | 109.0 | 106.3 | 106.3 | 106.3 |
| 25°    | 113.3 | 110.7 | 109.0 | 106.3 | 103.7 | 102.8 | 101.9 | 100.2 | 99.3  | 98.4  | 98.4  |
| 27.5°  | 109.8 | 107.2 | 104.6 | 101.9 | 99.3  | 98.4  | 97.5  | 95.8  | 94.9  | 94.9  | 94.9  |
| 30°    | 116.9 | 116.0 | 115.1 | 114.2 | 113.3 | 111.6 | 109.0 | 107.2 | 104.6 | 102.8 | 101.0 |
| 32.5°  | 97.5  | 96.7  | 96.7  | 95.8  | 94.9  | 96.7  | 97.5  | 99.3  | 100.2 | 101.0 | 101.9 |
| 35°    | 86.1  | 84.4  | 82.6  | 80.8  | 79.1  | 78.2  | 77.3  | 76.4  | 75.6  | 75.6  | 74.7  |
| 37.5°  | 83.5  | 81.7  | 80.0  | 78.2  | 76.4  | 75.6  | 74.7  | 73.8  | 72.9  | 72.9  | 72.1  |
| 40°    | 80.8  | 79.1  | 78.2  | 76.4  | 74.7  | 73.8  | 72.9  | 71.2  | 70.3  | 69.4  | 69.4  |
| 42.5°  | 78.2  | 77.3  | 75.6  | 74.7  | 72.9  | 72.1  | 71.2  | 69.4  | 68.5  | 67.7  | 66.8  |
| 45°    | 78.2  | 76.4  | 74.7  | 72.9  | 71.2  | 70.3  | 68.5  | 67.7  | 65.9  | 65.9  | 65.0  |
| 47.5°  | 76.4  | 74.7  | 72.9  | 71.2  | 69.4  | 68.5  | 66.8  | 65.9  | 64.1  | 63.3  | 62.4  |
| 50°    | 80.8  | 78.2  | 74.7  | 72.1  | 68.5  | 67.7  | 65.9  | 65.0  | 63.3  | 62.4  | 61.5  |
| 52.5°  | 79.1  | 76.4  | 72.9  | 70.3  | 66.8  | 65.0  | 64.1  | 62.4  | 60.6  | 59.8  | 58.9  |
| 55°    | 72.9  | 70.3  | 68.5  | 65.9  | 63.3  | 61.5  | 59.8  | 58.0  | 56.2  | 55.4  | 55.4  |
| 57.5°  | 65.0  | 64.1  | 63.3  | 62.4  | 61.5  | 59.8  | 58.0  | 55.4  | 53.6  | 52.7  | 51.8  |
| 60°    | 58.0  | 58.9  | 59.8  | 60.6  | 61.5  | 58.9  | 56.2  | 53.6  | 51.0  | 50.1  | 49.2  |
| 62.5°  | 52.7  | 54.5  | 56.2  | 57.1  | 58.9  | 56.2  | 53.6  | 51.0  | 48.3  | 47.4  | 46.6  |
| 65°    | 49.2  | 50.1  | 50.1  | 51.0  | 51.0  | 49.2  | 48.3  | 46.6  | 44.8  | 43.9  | 43.9  |
| 67.5°  | 44.8  | 44.8  | 44.8  | 43.9  | 43.9  | 43.1  | 43.1  | 42.2  | 41.3  | 40.4  | 40.4  |
| 70°    | 40.4  | 40.4  | 40.4  | 39.5  | 39.5  | 38.7  | 38.7  | 37.8  | 36.9  | 36.9  | 36.0  |
| 72.5°  | 36.9  | 36.9  | 36.0  | 36.0  | 35.1  | 35.1  | 35.1  | 34.3  | 34.3  | 33.4  | 33.4  |
| 75°    | 32.5  | 32.5  | 31.6  | 31.6  | 30.8  | 30.8  | 30.8  | 29.9  | 29.9  | 29.9  | 29.0  |
| 77.5°  | 29.0  | 29.0  | 28.1  | 28.1  | 27.2  | 27.2  | 27.2  | 26.4  | 26.4  | 25.5  | 25.5  |
| 80°    | 25.5  | 25.5  | 24.6  | 24.6  | 23.7  | 23.7  | 22.8  | 22.8  | 22.0  | 22.0  | 21.1  |
| 82.5°  | 20.2  | 20.2  | 20.2  | 20.2  | 20.2  | 19.3  | 19.3  | 18.5  | 17.6  | 17.6  | 16.7  |
| 85°    | 16.7  | 16.7  | 16.7  | 15.8  | 15.8  | 15.8  | 14.9  | 14.9  | 14.1  | 13.2  | 13.2  |
| 87.5°  | 9.7   | 9.7   | 9.7   | 8.8   | 8.8   | 8.8   | 8.8   | 8.8   | 8.8   | 8.8   | 7.9   |
| 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° | 75° | 77.5° | 80° |
|--------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85°   | 87.5° | 90°   | 92.5° | 95°   | 97.5° | 100°  | 102.5° | 105°  | 107.5° |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|--------|-------|--------|
| 0°     | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7 | 632.7  | 632.7 | 632.7  |
| 2.5°   | 555.3 | 554.4 | 550.9 | 547.4 | 550.9 | 554.4 | 554.4 | 554.4 | 553.6  | 553.6 | 553.6  |
| 5°     | 445.5 | 444.6 | 442.9 | 441.1 | 441.1 | 440.2 | 442.0 | 443.7 | 445.5  | 447.2 | 449.0  |
| 7.5°   | 327.7 | 325.1 | 322.5 | 319.8 | 321.6 | 322.5 | 325.1 | 326.9 | 329.5  | 331.3 | 335.7  |
| 10°    | 273.3 | 269.8 | 267.1 | 264.5 | 262.7 | 261.0 | 259.2 | 258.3 | 256.6  | 254.8 | 256.6  |
| 12.5°  | 233.7 | 229.3 | 224.9 | 219.7 | 218.8 | 217.9 | 216.2 | 214.4 | 212.6  | 210.9 | 210.0  |
| 15°    | 191.6 | 188.0 | 186.3 | 183.6 | 180.1 | 176.6 | 174.9 | 174.0 | 172.2  | 170.5 | 169.6  |
| 17.5°  | 152.9 | 149.4 | 146.7 | 144.1 | 143.2 | 141.5 | 141.5 | 141.5 | 141.5  | 141.5 | 141.5  |
| 20°    | 120.4 | 117.7 | 117.7 | 116.9 | 116.9 | 116.0 | 116.9 | 117.7 | 117.7  | 118.6 | 119.5  |
| 22.5°  | 105.4 | 105.4 | 104.6 | 103.7 | 104.6 | 104.6 | 105.4 | 106.3 | 107.2  | 108.1 | 109.0  |
| 25°    | 97.5  | 96.7  | 97.5  | 98.4  | 98.4  | 98.4  | 99.3  | 99.3  | 100.2  | 100.2 | 100.2  |
| 27.5°  | 94.0  | 94.0  | 94.9  | 94.9  | 95.8  | 95.8  | 95.8  | 94.9  | 94.9   | 94.0  | 94.0   |
| 30°    | 99.3  | 97.5  | 97.5  | 97.5  | 96.7  | 95.8  | 94.9  | 94.9  | 94.0   | 93.1  | 92.3   |
| 32.5°  | 102.8 | 103.7 | 102.8 | 101.0 | 100.2 | 98.4  | 97.5  | 95.8  | 94.9   | 93.1  | 91.4   |
| 35°    | 74.7  | 73.8  | 75.6  | 76.4  | 77.3  | 78.2  | 79.1  | 80.0  | 80.0   | 80.8  | 80.8   |
| 37.5°  | 72.1  | 71.2  | 71.2  | 70.3  | 70.3  | 70.3  | 70.3  | 70.3  | 69.4   | 69.4  | 70.3   |
| 40°    | 68.5  | 67.7  | 67.7  | 66.8  | 66.8  | 65.9  | 65.9  | 65.9  | 65.9   | 65.9  | 65.9   |
| 42.5°  | 65.9  | 65.0  | 65.0  | 65.0  | 65.0  | 64.1  | 64.1  | 63.3  | 63.3   | 62.4  | 62.4   |
| 45°    | 65.0  | 64.1  | 63.3  | 62.4  | 62.4  | 61.5  | 61.5  | 61.5  | 60.6   | 60.6  | 60.6   |
| 47.5°  | 61.5  | 60.6  | 60.6  | 59.8  | 59.8  | 58.9  | 58.9  | 58.9  | 58.0   | 58.0  | 58.0   |
| 50°    | 59.8  | 58.9  | 58.9  | 58.0  | 58.0  | 57.1  | 57.1  | 57.1  | 56.2   | 56.2  | 56.2   |
| 52.5°  | 57.1  | 56.2  | 56.2  | 56.2  | 55.4  | 54.5  | 54.5  | 54.5  | 53.6   | 53.6  | 53.6   |
| 55°    | 54.5  | 53.6  | 53.6  | 53.6  | 52.7  | 51.8  | 51.8  | 51.8  | 51.0   | 51.0  | 51.0   |
| 57.5°  | 51.0  | 50.1  | 50.1  | 49.2  | 49.2  | 49.2  | 49.2  | 49.2  | 48.3   | 48.3  | 48.3   |
| 60°    | 48.3  | 47.4  | 47.4  | 46.6  | 46.6  | 45.7  | 45.7  | 45.7  | 45.7   | 45.7  | 45.7   |
| 62.5°  | 45.7  | 44.8  | 43.9  | 43.1  | 43.9  | 43.9  | 43.9  | 43.9  | 43.1   | 43.1  | 43.1   |
| 65°    | 43.1  | 42.2  | 41.3  | 40.4  | 40.4  | 40.4  | 40.4  | 40.4  | 40.4   | 40.4  | 40.4   |
| 67.5°  | 39.5  | 38.7  | 37.8  | 36.9  | 37.8  | 37.8  | 37.8  | 37.8  | 37.8   | 37.8  | 37.8   |
| 70°    | 36.0  | 35.1  | 35.1  | 34.3  | 34.3  | 33.4  | 33.4  | 34.3  | 34.3   | 34.3  | 34.3   |
| 72.5°  | 32.5  | 31.6  | 31.6  | 30.8  | 30.8  | 30.8  | 30.8  | 30.8  | 30.8   | 30.8  | 30.8   |
| 75°    | 29.0  | 28.1  | 28.1  | 27.2  | 27.2  | 27.2  | 27.2  | 27.2  | 27.2   | 27.2  | 27.2   |
| 77.5°  | 24.6  | 23.7  | 23.7  | 23.7  | 23.7  | 23.7  | 23.7  | 24.6  | 24.6   | 24.6  | 24.6   |
| 80°    | 21.1  | 20.2  | 20.2  | 20.2  | 20.2  | 20.2  | 20.2  | 20.2  | 20.2   | 20.2  | 20.2   |
| 82.5°  | 16.7  | 15.8  | 15.8  | 15.8  | 15.8  | 15.8  | 15.8  | 15.8  | 15.8   | 15.8  | 15.8   |
| 85°    | 12.3  | 11.4  | 11.4  | 11.4  | 12.3  | 12.3  | 12.3  | 12.3  | 12.3   | 12.3  | 12.3   |
| 87.5°  | 7.9   | 7.0   | 7.0   | 7.0   | 7.9   | 7.9   | 7.9   | 7.9   | 7.0    | 7.0   | 7.0    |
| 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |
| 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° | 92.5° | 95° | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|------|--------|------|--------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 110°  | 112.5° | 115°  | 117.5° | 120°  | 122.5° | 125°  | 127.5° | 130°  | 132.5° | 135°  |
|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°     | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 |
| 2.5°   | 553.6 | 553.6  | 553.6 | 552.7  | 551.8 | 550.9  | 550.1 | 552.7  | 554.4 | 557.1  | 558.8 |
| 5°     | 449.9 | 451.6  | 452.5 | 455.2  | 457.8 | 460.4  | 463.1 | 464.8  | 466.6 | 467.5  | 469.2 |
| 7.5°   | 339.2 | 343.6  | 347.1 | 350.6  | 354.1 | 356.7  | 360.3 | 362.9  | 365.5 | 368.2  | 370.8 |
| 10°    | 257.5 | 259.2  | 260.1 | 263.6  | 266.2 | 269.8  | 272.4 | 275.0  | 277.7 | 279.4  | 282.1 |
| 12.5°  | 209.1 | 207.4  | 206.5 | 206.5  | 206.5 | 206.5  | 206.5 | 208.2  | 210.0 | 211.8  | 213.5 |
| 15°    | 168.7 | 167.8  | 166.9 | 166.1  | 165.2 | 163.4  | 162.6 | 164.3  | 166.1 | 167.8  | 169.6 |
| 17.5°  | 141.5 | 141.5  | 141.5 | 140.6  | 139.7 | 138.8  | 138.0 | 138.8  | 139.7 | 139.7  | 140.6 |
| 20°    | 121.3 | 122.1  | 123.0 | 123.9  | 123.9 | 124.8  | 124.8 | 125.7  | 126.5 | 126.5  | 127.4 |
| 22.5°  | 109.0 | 109.8  | 109.8 | 109.8  | 110.7 | 110.7  | 110.7 | 111.6  | 112.5 | 113.3  | 114.2 |
| 25°    | 99.3  | 99.3   | 98.4  | 98.4   | 99.3  | 99.3   | 99.3  | 99.3   | 100.2 | 100.2  | 100.2 |
| 27.5°  | 94.0  | 93.1   | 93.1  | 93.1   | 93.1  | 92.3   | 92.3  | 92.3   | 92.3  | 92.3   | 92.3  |
| 30°    | 91.4  | 90.5   | 89.6  | 88.7   | 88.7  | 87.9   | 87.0  | 87.0   | 87.0  | 87.0   | 87.0  |
| 32.5°  | 90.5  | 88.7   | 87.0  | 86.1   | 86.1  | 85.2   | 84.4  | 83.5   | 83.5  | 82.6   | 81.7  |
| 35°    | 80.8  | 80.0   | 80.0  | 79.1   | 78.2  | 77.3   | 76.4  | 76.4   | 76.4  | 75.6   | 75.6  |
| 37.5°  | 70.3  | 71.2   | 71.2  | 71.2   | 72.1  | 72.1   | 72.1  | 72.1   | 72.9  | 72.9   | 72.9  |
| 40°    | 65.9  | 65.9   | 65.9  | 66.8   | 67.7  | 67.7   | 68.5  | 68.5   | 69.4  | 69.4   | 69.4  |
| 42.5°  | 62.4  | 61.5   | 61.5  | 62.4   | 62.4  | 63.3   | 63.3  | 64.1   | 65.0  | 65.0   | 65.9  |
| 45°    | 60.6  | 59.8   | 59.8  | 59.8   | 59.8  | 58.9   | 58.9  | 59.8   | 60.6  | 61.5   | 62.4  |
| 47.5°  | 57.1  | 57.1   | 56.2  | 56.2   | 56.2  | 56.2   | 56.2  | 56.2   | 57.1  | 57.1   | 57.1  |
| 50°    | 55.4  | 55.4   | 54.5  | 54.5   | 54.5  | 54.5   | 54.5  | 54.5   | 54.5  | 54.5   | 54.5  |
| 52.5°  | 53.6  | 52.7   | 52.7  | 52.7   | 52.7  | 51.8   | 51.8  | 51.8   | 51.8  | 51.8   | 51.8  |
| 55°    | 51.0  | 50.1   | 50.1  | 50.1   | 50.1  | 50.1   | 50.1  | 50.1   | 51.0  | 51.0   | 51.0  |
| 57.5°  | 48.3  | 47.4   | 47.4  | 47.4   | 48.3  | 48.3   | 48.3  | 48.3   | 49.2  | 49.2   | 49.2  |
| 60°    | 45.7  | 45.7   | 45.7  | 45.7   | 45.7  | 45.7   | 45.7  | 46.6   | 46.6  | 47.4   | 47.4  |
| 62.5°  | 43.1  | 43.1   | 43.1  | 43.1   | 43.9  | 43.9   | 43.9  | 43.9   | 44.8  | 44.8   | 44.8  |
| 65°    | 40.4  | 40.4   | 40.4  | 40.4   | 41.3  | 41.3   | 41.3  | 41.3   | 41.3  | 41.3   | 41.3  |
| 67.5°  | 37.8  | 37.8   | 37.8  | 37.8   | 37.8  | 37.8   | 37.8  | 38.7   | 38.7  | 39.5   | 39.5  |
| 70°    | 34.3  | 33.4   | 33.4  | 34.3   | 34.3  | 35.1   | 35.1  | 36.0   | 36.0  | 36.9   | 36.9  |
| 72.5°  | 30.8  | 30.8   | 30.8  | 30.8   | 30.8  | 30.8   | 30.8  | 31.6   | 32.5  | 32.5   | 33.4  |
| 75°    | 27.2  | 27.2   | 27.2  | 27.2   | 28.1  | 28.1   | 28.1  | 29.0   | 29.0  | 29.9   | 29.9  |
| 77.5°  | 24.6  | 23.7   | 23.7  | 23.7   | 24.6  | 24.6   | 24.6  | 25.5   | 25.5  | 26.4   | 26.4  |
| 80°    | 20.2  | 20.2   | 20.2  | 20.2   | 21.1  | 21.1   | 21.1  | 21.1   | 22.0  | 22.0   | 22.0  |
| 82.5°  | 16.7  | 16.7   | 16.7  | 16.7   | 16.7  | 16.7   | 16.7  | 16.7   | 17.6  | 17.6   | 17.6  |
| 85°    | 12.3  | 12.3   | 12.3  | 12.3   | 13.2  | 13.2   | 13.2  | 13.2   | 13.2  | 13.2   | 13.2  |
| 87.5°  | 7.9   | 7.9    | 7.9   | 7.9    | 7.9   | 7.9    | 7.9   | 7.9    | 8.8   | 8.8    | 8.8   |
| 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140°  | 142.5° | 145°  | 147.5° | 150°  | 152.5° | 155°  | 157.5° | 160°  | 162.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0°     | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  |
| 2.5°   | 558.8  | 558.8 | 558.8  | 558.8 | 560.6  | 561.5 | 563.2  | 564.1 | 563.2  | 562.4 | 560.6  |
| 5°     | 470.1  | 471.0 | 471.0  | 471.9 | 471.9  | 471.9 | 471.9  | 471.9 | 473.6  | 475.4 | 477.1  |
| 7.5°   | 371.7  | 372.6 | 373.4  | 374.3 | 374.3  | 374.3 | 373.4  | 373.4 | 374.3  | 374.3 | 375.2  |
| 10°    | 284.7  | 288.2 | 290.8  | 293.5 | 291.7  | 289.1 | 287.3  | 284.7 | 284.7  | 284.7 | 283.8  |
| 12.5°  | 215.3  | 216.2 | 217.9  | 218.8 | 217.9  | 217.9 | 217.0  | 216.2 | 217.0  | 218.8 | 219.7  |
| 15°    | 170.5  | 170.5 | 171.3  | 171.3 | 172.2  | 173.1 | 173.1  | 174.0 | 175.7  | 176.6 | 178.4  |
| 17.5°  | 141.5  | 142.3 | 142.3  | 143.2 | 143.2  | 144.1 | 144.1  | 144.1 | 145.9  | 147.6 | 150.3  |
| 20°    | 127.4  | 127.4 | 127.4  | 127.4 | 127.4  | 126.5 | 126.5  | 125.7 | 126.5  | 128.3 | 129.2  |
| 22.5°  | 114.2  | 115.1 | 115.1  | 115.1 | 114.2  | 113.3 | 111.6  | 110.7 | 110.7  | 111.6 | 111.6  |
| 25°    | 100.2  | 99.3  | 99.3   | 98.4  | 98.4   | 99.3  | 99.3   | 99.3  | 100.2  | 100.2 | 101.0  |
| 27.5°  | 92.3   | 91.4  | 91.4   | 90.5  | 90.5   | 91.4  | 91.4   | 91.4  | 91.4   | 91.4  | 91.4   |
| 30°    | 86.1   | 86.1  | 85.2   | 84.4  | 85.2   | 85.2  | 86.1   | 86.1  | 87.0   | 87.0  | 87.9   |
| 32.5°  | 81.7   | 80.8  | 80.8   | 80.0  | 80.8   | 80.8  | 81.7   | 81.7  | 82.6   | 83.5  | 83.5   |
| 35°    | 75.6   | 75.6  | 75.6   | 75.6  | 75.6   | 75.6  | 74.7   | 74.7  | 74.7   | 74.7  | 74.7   |
| 37.5°  | 72.1   | 72.1  | 71.2   | 70.3  | 70.3   | 70.3  | 70.3   | 70.3  | 69.4   | 68.5  | 67.7   |
| 40°    | 69.4   | 68.5  | 68.5   | 67.7  | 66.8   | 66.8  | 65.9   | 65.0  | 65.0   | 64.1  | 64.1   |
| 42.5°  | 65.9   | 65.0  | 65.0   | 64.1  | 63.3   | 63.3  | 62.4   | 61.5  | 61.5   | 61.5  | 60.6   |
| 45°    | 61.5   | 61.5  | 60.6   | 59.8  | 59.8   | 59.8  | 58.9   | 58.9  | 58.9   | 58.9  | 58.0   |
| 47.5°  | 57.1   | 57.1  | 56.2   | 56.2  | 56.2   | 56.2  | 55.4   | 55.4  | 55.4   | 55.4  | 55.4   |
| 50°    | 54.5   | 54.5  | 54.5   | 54.5  | 54.5   | 54.5  | 53.6   | 53.6  | 53.6   | 53.6  | 53.6   |
| 52.5°  | 51.8   | 51.8  | 51.8   | 51.8  | 51.8   | 51.8  | 51.8   | 51.8  | 51.8   | 51.8  | 51.8   |
| 55°    | 51.0   | 51.0  | 51.0   | 51.0  | 51.0   | 51.0  | 50.1   | 50.1  | 50.1   | 51.0  | 51.0   |
| 57.5°  | 49.2   | 49.2  | 48.3   | 48.3  | 48.3   | 48.3  | 48.3   | 48.3  | 48.3   | 48.3  | 48.3   |
| 60°    | 47.4   | 47.4  | 47.4   | 47.4  | 47.4   | 47.4  | 47.4   | 47.4  | 47.4   | 47.4  | 47.4   |
| 62.5°  | 44.8   | 44.8  | 44.8   | 44.8  | 44.8   | 45.7  | 45.7   | 45.7  | 45.7   | 45.7  | 44.8   |
| 65°    | 41.3   | 42.2  | 42.2   | 42.2  | 42.2   | 42.2  | 42.2   | 42.2  | 42.2   | 42.2  | 42.2   |
| 67.5°  | 39.5   | 39.5  | 39.5   | 39.5  | 39.5   | 39.5  | 39.5   | 39.5  | 39.5   | 39.5  | 39.5   |
| 70°    | 36.9   | 36.9  | 36.0   | 36.0  | 36.0   | 36.9  | 36.9   | 36.9  | 36.9   | 36.9  | 36.9   |
| 72.5°  | 33.4   | 33.4  | 33.4   | 33.4  | 33.4   | 33.4  | 33.4   | 33.4  | 33.4   | 34.3  | 34.3   |
| 75°    | 29.9   | 29.9  | 29.9   | 29.9  | 29.9   | 29.9  | 29.9   | 29.9  | 29.9   | 29.9  | 29.9   |
| 77.5°  | 26.4   | 26.4  | 25.5   | 25.5  | 25.5   | 26.4  | 26.4   | 26.4  | 26.4   | 27.2  | 27.2   |
| 80°    | 22.0   | 22.0  | 22.0   | 22.0  | 22.0   | 22.0  | 22.0   | 22.0  | 22.0   | 22.8  | 22.8   |
| 82.5°  | 17.6   | 17.6  | 17.6   | 17.6  | 17.6   | 17.6  | 17.6   | 17.6  | 17.6   | 18.5  | 18.5   |
| 85°    | 13.2   | 14.1  | 14.1   | 14.1  | 14.1   | 14.1  | 14.1   | 14.1  | 14.1   | 14.9  | 14.9   |
| 87.5°  | 8.8    | 8.8   | 8.8    | 8.8   | 8.8    | 8.8   | 7.9    | 7.9   | 7.9    | 7.9   | 7.0    |
| 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 165°  | 167.5° | 170°  | 172.5° | 175°  | 177.5° | 180°  | 182.5° | 185°  | 187.5° | 190°  |
|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°     | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 |
| 2.5°   | 559.7 | 560.6  | 561.5 | 561.5  | 562.4 | 563.2  | 563.2 | 566.7  | 570.3 | 572.0  | 573.8 |
| 5°     | 478.9 | 478.0  | 478.0 | 477.1  | 476.2 | 478.9  | 481.5 | 486.8  | 492.1 | 492.9  | 494.7 |
| 7.5°   | 375.2 | 376.1  | 377.0 | 377.0  | 377.8 | 375.2  | 371.7 | 372.6  | 373.4 | 377.8  | 381.3 |
| 10°    | 283.8 | 284.7  | 285.6 | 285.6  | 286.5 | 285.6  | 283.8 | 286.5  | 289.1 | 292.6  | 297.0 |
| 12.5°  | 220.5 | 223.2  | 225.8 | 227.6  | 230.2 | 232.0  | 232.9 | 236.4  | 239.0 | 243.4  | 247.8 |
| 15°    | 180.1 | 181.9  | 183.6 | 185.4  | 187.2 | 188.9  | 190.7 | 194.2  | 197.7 | 203.0  | 208.2 |
| 17.5°  | 152.0 | 152.0  | 152.9 | 152.9  | 152.9 | 154.6  | 156.4 | 158.2  | 159.0 | 164.3  | 169.6 |
| 20°    | 130.0 | 129.2  | 128.3 | 127.4  | 126.5 | 128.3  | 129.2 | 130.0  | 130.9 | 134.4  | 137.1 |
| 22.5°  | 111.6 | 111.6  | 112.5 | 112.5  | 112.5 | 111.6  | 109.8 | 110.7  | 110.7 | 112.5  | 115.1 |
| 25°    | 101.0 | 101.0  | 101.0 | 100.2  | 100.2 | 101.0  | 101.9 | 101.9  | 101.0 | 101.9  | 102.8 |
| 27.5°  | 91.4  | 92.3   | 92.3  | 93.1   | 93.1  | 94.0   | 94.0  | 94.0   | 94.0  | 94.9   | 95.8  |
| 30°    | 87.9  | 87.9   | 88.7  | 88.7   | 88.7  | 89.6   | 90.5  | 90.5   | 90.5  | 91.4   | 93.1  |
| 32.5°  | 84.4  | 85.2   | 86.1  | 87.0   | 87.9  | 88.7   | 88.7  | 89.6   | 89.6  | 90.5   | 91.4  |
| 35°    | 74.7  | 73.8   | 73.8  | 72.9   | 72.1  | 72.1   | 72.1  | 72.1   | 71.2  | 72.1   | 72.1  |
| 37.5°  | 66.8  | 66.8   | 66.8  | 65.9   | 65.9  | 66.8   | 66.8  | 66.8   | 66.8  | 67.7   | 67.7  |
| 40°    | 63.3  | 63.3   | 63.3  | 63.3   | 63.3  | 63.3   | 63.3  | 64.1   | 64.1  | 65.0   | 65.9  |
| 42.5°  | 60.6  | 60.6   | 60.6  | 60.6   | 60.6  | 61.5   | 61.5  | 61.5   | 61.5  | 62.4   | 62.4  |
| 45°    | 58.0  | 58.0   | 58.0  | 58.0   | 58.0  | 58.0   | 58.0  | 58.9   | 58.9  | 59.8   | 60.6  |
| 47.5°  | 55.4  | 55.4   | 55.4  | 55.4   | 55.4  | 56.2   | 57.1  | 57.1   | 57.1  | 58.0   | 58.0  |
| 50°    | 53.6  | 53.6   | 53.6  | 53.6   | 53.6  | 54.5   | 54.5  | 55.4   | 55.4  | 56.2   | 57.1  |
| 52.5°  | 51.8  | 51.8   | 51.8  | 51.8   | 51.8  | 52.7   | 52.7  | 53.6   | 53.6  | 54.5   | 55.4  |
| 55°    | 51.0  | 51.0   | 51.0  | 50.1   | 50.1  | 51.0   | 51.0  | 51.8   | 51.8  | 52.7   | 52.7  |
| 57.5°  | 48.3  | 48.3   | 48.3  | 48.3   | 48.3  | 48.3   | 48.3  | 49.2   | 49.2  | 50.1   | 51.0  |
| 60°    | 47.4  | 47.4   | 46.6  | 46.6   | 45.7  | 46.6   | 46.6  | 47.4   | 47.4  | 48.3   | 48.3  |
| 62.5°  | 44.8  | 44.8   | 44.8  | 43.9   | 43.9  | 44.8   | 44.8  | 44.8   | 44.8  | 45.7   | 46.6  |
| 65°    | 42.2  | 42.2   | 42.2  | 41.3   | 41.3  | 42.2   | 42.2  | 42.2   | 42.2  | 43.1   | 43.9  |
| 67.5°  | 39.5  | 39.5   | 39.5  | 38.7   | 38.7  | 38.7   | 38.7  | 39.5   | 39.5  | 40.4   | 41.3  |
| 70°    | 36.9  | 36.9   | 36.9  | 36.0   | 36.0  | 36.0   | 35.1  | 36.0   | 36.9  | 37.8   | 37.8  |
| 72.5°  | 34.3  | 34.3   | 34.3  | 33.4   | 33.4  | 33.4   | 32.5  | 33.4   | 33.4  | 34.3   | 34.3  |
| 75°    | 29.9  | 29.9   | 29.9  | 29.9   | 29.9  | 29.9   | 29.0  | 29.0   | 29.0  | 29.9   | 29.9  |
| 77.5°  | 27.2  | 27.2   | 27.2  | 26.4   | 26.4  | 26.4   | 25.5  | 25.5   | 25.5  | 26.4   | 26.4  |
| 80°    | 22.8  | 22.8   | 22.8  | 22.0   | 22.0  | 22.0   | 21.1  | 21.1   | 21.1  | 22.0   | 22.0  |
| 82.5°  | 18.5  | 18.5   | 18.5  | 17.6   | 17.6  | 17.6   | 16.7  | 16.7   | 16.7  | 17.6   | 17.6  |
| 85°    | 14.9  | 14.9   | 14.9  | 14.9   | 14.9  | 14.9   | 14.1  | 14.1   | 14.1  | 14.9   | 15.8  |
| 87.5°  | 7.0   | 7.0    | 7.9   | 7.9    | 7.9   | 7.9    | 7.0   | 7.0    | 6.2   | 6.2    | 7.0   |
| 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° | 190° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  | 217.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0°     | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  |
| 2.5°   | 575.5  | 577.3 | 581.7  | 585.2 | 589.6  | 593.1 | 595.7  | 599.3 | 601.9  | 604.5 | 606.3  |
| 5°     | 495.6  | 496.5 | 500.8  | 505.2 | 508.8  | 513.2 | 519.3  | 525.5 | 531.6  | 537.8 | 542.1  |
| 7.5°   | 385.7  | 389.3 | 394.5  | 400.7 | 406.0  | 411.2 | 417.4  | 424.4 | 430.6  | 436.7 | 442.9  |
| 10°    | 300.5  | 304.0 | 309.3  | 314.6 | 319.0  | 324.2 | 331.3  | 338.3 | 345.3  | 352.4 | 359.4  |
| 12.5°  | 252.2  | 256.6 | 262.7  | 268.9 | 274.1  | 280.3 | 289.1  | 297.0 | 305.8  | 313.7 | 322.5  |
| 15°    | 212.6  | 217.9 | 225.8  | 234.6 | 242.5  | 250.4 | 259.2  | 268.0 | 275.9  | 284.7 | 293.5  |
| 17.5°  | 174.9  | 180.1 | 187.2  | 195.1 | 202.1  | 209.1 | 219.7  | 229.3 | 239.9  | 249.5 | 259.2  |
| 20°    | 140.6  | 143.2 | 150.3  | 157.3 | 164.3  | 171.3 | 179.3  | 187.2 | 195.1  | 203.0 | 215.3  |
| 22.5°  | 116.9  | 118.6 | 122.1  | 124.8 | 128.3  | 130.9 | 138.8  | 146.7 | 153.8  | 161.7 | 173.1  |
| 25°    | 102.8  | 103.7 | 106.3  | 108.1 | 110.7  | 112.5 | 117.7  | 122.1 | 127.4  | 131.8 | 142.3  |
| 27.5°  | 95.8   | 96.7  | 97.5   | 98.4  | 99.3   | 100.2 | 103.7  | 107.2 | 109.8  | 113.3 | 123.0  |
| 30°    | 94.0   | 94.9  | 97.5   | 99.3  | 101.9  | 103.7 | 105.4  | 107.2 | 109.0  | 110.7 | 116.9  |
| 32.5°  | 92.3   | 93.1  | 93.1   | 92.3  | 92.3   | 91.4  | 93.1   | 94.0  | 95.8   | 96.7  | 101.9  |
| 35°    | 72.9   | 72.9  | 73.8   | 74.7  | 75.6   | 76.4  | 79.1   | 80.8  | 83.5   | 85.2  | 89.6   |
| 37.5°  | 68.5   | 68.5  | 69.4   | 71.2  | 72.1   | 72.9  | 74.7   | 76.4  | 78.2   | 80.0  | 84.4   |
| 40°    | 65.9   | 66.8  | 67.7   | 68.5  | 69.4   | 70.3  | 72.1   | 72.9  | 74.7   | 75.6  | 79.1   |
| 42.5°  | 63.3   | 63.3  | 64.1   | 65.9  | 66.8   | 67.7  | 69.4   | 70.3  | 72.1   | 72.9  | 76.4   |
| 45°    | 61.5   | 62.4  | 63.3   | 64.1  | 64.1   | 65.0  | 66.8   | 68.5  | 69.4   | 71.2  | 74.7   |
| 47.5°  | 58.9   | 58.9  | 60.6   | 61.5  | 63.3   | 64.1  | 65.9   | 66.8  | 68.5   | 69.4  | 72.9   |
| 50°    | 57.1   | 58.0  | 59.8   | 60.6  | 62.4   | 63.3  | 65.9   | 67.7  | 70.3   | 72.1  | 73.8   |
| 52.5°  | 55.4   | 56.2  | 58.0   | 58.9  | 60.6   | 61.5  | 65.0   | 68.5  | 71.2   | 74.7  | 74.7   |
| 55°    | 53.6   | 53.6  | 55.4   | 58.0  | 59.8   | 61.5  | 63.3   | 65.9  | 67.7   | 69.4  | 69.4   |
| 57.5°  | 51.0   | 51.8  | 53.6   | 56.2  | 58.0   | 59.8  | 61.5   | 63.3  | 64.1   | 65.9  | 65.0   |
| 60°    | 49.2   | 49.2  | 51.8   | 54.5  | 57.1   | 59.8  | 59.8   | 59.8  | 58.9   | 58.9  | 58.9   |
| 62.5°  | 46.6   | 47.4  | 51.0   | 55.4  | 58.9   | 62.4  | 59.8   | 57.1  | 54.5   | 51.8  | 52.7   |
| 65°    | 44.8   | 45.7  | 47.4   | 50.1  | 51.8   | 53.6  | 51.8   | 51.0  | 49.2   | 47.4  | 48.3   |
| 67.5°  | 41.3   | 42.2  | 43.1   | 43.1  | 43.9   | 43.9  | 43.9   | 43.9  | 43.9   | 43.9  | 44.8   |
| 70°    | 38.7   | 38.7  | 38.7   | 39.5  | 39.5   | 39.5  | 39.5   | 39.5  | 39.5   | 39.5  | 40.4   |
| 72.5°  | 35.1   | 35.1  | 35.1   | 35.1  | 35.1   | 35.1  | 35.1   | 35.1  | 35.1   | 35.1  | 36.0   |
| 75°    | 30.8   | 30.8  | 30.8   | 30.8  | 30.8   | 30.8  | 30.8   | 30.8  | 30.8   | 30.8  | 31.6   |
| 77.5°  | 27.2   | 27.2  | 27.2   | 27.2  | 27.2   | 27.2  | 27.2   | 27.2  | 26.4   | 26.4  | 27.2   |
| 80°    | 22.8   | 22.8  | 22.8   | 22.8  | 22.0   | 22.0  | 22.0   | 22.0  | 22.0   | 22.0  | 22.8   |
| 82.5°  | 18.5   | 18.5  | 18.5   | 18.5  | 17.6   | 17.6  | 17.6   | 17.6  | 16.7   | 16.7  | 17.6   |
| 85°    | 16.7   | 17.6  | 17.6   | 18.5  | 18.5   | 18.5  | 17.6   | 16.7  | 15.8   | 14.9  | 14.9   |
| 87.5°  | 7.0    | 7.0   | 7.0    | 7.0   | 6.2    | 6.2   | 6.2    | 6.2   | 6.2    | 6.2   | 6.2    |
| 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° | 217.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 220°  | 222.5° | 225°  | 227.5° | 230°  | 232.5° | 235°  | 237.5° | 240°  | 242.5° | 245°  |
|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0°     | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 |
| 2.5°   | 608.9 | 610.7  | 612.4 | 615.1  | 618.6 | 621.2  | 623.9 | 629.1  | 635.3 | 640.6  | 645.8 |
| 5°     | 546.5 | 550.9  | 555.3 | 560.6  | 565.9 | 570.3  | 575.5 | 586.1  | 596.6 | 606.3  | 616.8 |
| 7.5°   | 448.1 | 454.3  | 459.6 | 468.3  | 476.2 | 485.0  | 492.9 | 506.1  | 518.4 | 531.6  | 543.9 |
| 10°    | 366.4 | 373.4  | 380.5 | 391.9  | 404.2 | 415.6  | 427.0 | 437.6  | 449.0 | 459.6  | 470.1 |
| 12.5°  | 331.3 | 339.2  | 348.0 | 355.0  | 362.9 | 369.9  | 377.0 | 389.3  | 401.6 | 413.9  | 426.2 |
| 15°    | 302.3 | 311.1  | 319.8 | 328.6  | 336.5 | 345.3  | 353.2 | 363.8  | 375.2 | 385.7  | 396.3 |
| 17.5°  | 268.9 | 277.7  | 287.3 | 297.0  | 306.7 | 316.3  | 326.0 | 340.9  | 355.9 | 369.9  | 384.9 |
| 20°    | 226.7 | 239.0  | 250.4 | 263.6  | 276.8 | 290.0  | 303.1 | 319.0  | 334.8 | 349.7  | 365.5 |
| 22.5°  | 184.5 | 195.9  | 207.4 | 223.2  | 239.0 | 253.9  | 269.8 | 290.8  | 311.1 | 332.1  | 352.4 |
| 25°    | 153.8 | 164.3  | 174.9 | 192.4  | 209.1 | 226.7  | 243.4 | 268.9  | 293.5 | 319.0  | 343.6 |
| 27.5°  | 132.7 | 142.3  | 152.0 | 170.5  | 188.9 | 206.5  | 224.9 | 253.1  | 280.3 | 308.4  | 335.7 |
| 30°    | 123.0 | 129.2  | 135.3 | 152.9  | 170.5 | 187.2  | 204.7 | 232.0  | 259.2 | 286.5  | 313.7 |
| 32.5°  | 107.2 | 112.5  | 117.7 | 133.6  | 149.4 | 164.3  | 180.1 | 208.2  | 235.5 | 263.6  | 290.8 |
| 35°    | 94.9  | 99.3   | 103.7 | 118.6  | 132.7 | 147.6  | 161.7 | 189.8  | 217.9 | 246.0  | 274.1 |
| 37.5°  | 87.9  | 92.3   | 95.8  | 109.0  | 123.0 | 136.2  | 149.4 | 177.5  | 204.7 | 232.9  | 260.1 |
| 40°    | 82.6  | 85.2   | 88.7  | 101.9  | 114.2 | 127.4  | 139.7 | 165.2  | 191.6 | 217.0  | 242.5 |
| 42.5°  | 79.1  | 82.6   | 85.2  | 96.7   | 109.0 | 120.4  | 131.8 | 156.4  | 181.0 | 204.7  | 229.3 |
| 45°    | 78.2  | 81.7   | 85.2  | 94.9   | 104.6 | 113.3  | 123.0 | 146.7  | 170.5 | 194.2  | 217.9 |
| 47.5°  | 76.4  | 79.1   | 82.6  | 90.5   | 97.5  | 105.4  | 112.5 | 136.2  | 159.9 | 182.8  | 206.5 |
| 50°    | 75.6  | 76.4   | 78.2  | 85.2   | 92.3  | 99.3   | 106.3 | 130.0  | 153.8 | 177.5  | 201.2 |
| 52.5°  | 74.7  | 74.7   | 74.7  | 80.8   | 87.0  | 92.3   | 98.4  | 122.1  | 146.7 | 170.5  | 194.2 |
| 55°    | 69.4  | 68.5   | 68.5  | 74.7   | 80.0  | 86.1   | 91.4  | 115.1  | 138.8 | 161.7  | 185.4 |
| 57.5°  | 64.1  | 63.3   | 62.4  | 67.7   | 72.9  | 78.2   | 83.5  | 107.2  | 131.8 | 155.5  | 179.3 |
| 60°    | 58.9  | 58.0   | 58.0  | 63.3   | 67.7  | 72.9   | 77.3  | 101.9  | 125.7 | 150.3  | 174.0 |
| 62.5°  | 52.7  | 53.6   | 53.6  | 58.0   | 63.3  | 67.7   | 72.1  | 96.7   | 122.1 | 146.7  | 171.3 |
| 65°    | 48.3  | 49.2   | 49.2  | 54.5   | 59.8  | 65.0   | 70.3  | 94.0   | 118.6 | 142.3  | 166.1 |
| 67.5°  | 44.8  | 45.7   | 45.7  | 51.8   | 57.1  | 63.3   | 68.5  | 89.6   | 111.6 | 132.7  | 153.8 |
| 70°    | 41.3  | 41.3   | 42.2  | 48.3   | 54.5  | 60.6   | 66.8  | 85.2   | 103.7 | 121.3  | 139.7 |
| 72.5°  | 36.9  | 37.8   | 38.7  | 44.8   | 50.1  | 56.2   | 61.5  | 78.2   | 94.9  | 111.6  | 128.3 |
| 75°    | 32.5  | 33.4   | 34.3  | 39.5   | 44.8  | 50.1   | 55.4  | 71.2   | 86.1  | 101.9  | 116.9 |
| 77.5°  | 29.0  | 29.9   | 30.8  | 35.1   | 39.5  | 43.9   | 48.3  | 59.8   | 72.1  | 83.5   | 94.9  |
| 80°    | 23.7  | 23.7   | 24.6  | 28.1   | 31.6  | 34.3   | 37.8  | 45.7   | 53.6  | 60.6   | 68.5  |
| 82.5°  | 17.6  | 18.5   | 18.5  | 21.1   | 22.8  | 25.5   | 27.2  | 31.6   | 35.1  | 39.5   | 43.1  |
| 85°    | 14.9  | 14.1   | 14.1  | 15.8   | 16.7  | 18.5   | 19.3  | 22.0   | 23.7  | 26.4   | 28.1  |
| 87.5°  | 6.2   | 5.3    | 5.3   | 6.2    | 7.9   | 8.8    | 9.7   | 9.7    | 10.5  | 10.5   | 10.5  |
| 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° | 245° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°   | 267.5° | 270°   | 272.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|--------|--------|--------|--------|
| 0°     | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7 | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  |
| 2.5°   | 648.5  | 650.2 | 652.9  | 654.6 | 659.0  | 662.5 | 666.9  | 670.4  | 673.1  | 677.5  | 675.7  |
| 5°     | 624.7  | 632.7 | 640.6  | 648.5 | 654.6  | 660.8 | 666.0  | 672.2  | 679.2  | 692.4  | 695.9  |
| 7.5°   | 554.4  | 565.0 | 574.7  | 585.2 | 597.5  | 609.8 | 622.1  | 634.4  | 645.8  | 662.5  | 673.1  |
| 10°    | 485.0  | 500.0 | 514.0  | 529.0 | 540.4  | 551.8 | 562.4  | 573.8  | 589.6  | 606.3  | 625.6  |
| 12.5°  | 441.1  | 456.0 | 471.0  | 485.9 | 502.6  | 518.4 | 535.1  | 550.9  | 565.9  | 579.1  | 601.0  |
| 15°    | 412.1  | 428.8 | 444.6  | 460.4 | 480.6  | 500.0 | 520.2  | 539.5  | 561.5  | 579.1  | 594.0  |
| 17.5°  | 405.1  | 425.3 | 444.6  | 464.8 | 485.9  | 507.0 | 528.1  | 549.2  | 571.1  | 597.5  | 616.8  |
| 20°    | 392.8  | 420.0 | 447.2  | 474.5 | 501.7  | 528.1 | 555.3  | 581.7  | 610.7  | 642.3  | 651.1  |
| 22.5°  | 385.7  | 418.3 | 451.6  | 484.2 | 521.1  | 558.8 | 595.7  | 632.7  | 663.4  | 687.1  | 713.5  |
| 25°    | 384.9  | 425.3 | 466.6  | 507.0 | 553.6  | 599.3 | 645.8  | 691.5  | 731.1  | 754.8  | 775.9  |
| 27.5°  | 384.0  | 433.2 | 481.5  | 529.8 | 587.0  | 643.2 | 700.3  | 756.5  | 793.4  | 827.7  | 845.3  |
| 30°    | 373.4  | 432.3 | 492.1  | 550.9 | 615.1  | 679.2 | 743.4  | 807.5  | 845.3  | 869.0  | 877.8  |
| 32.5°  | 360.3  | 429.7 | 499.1  | 568.5 | 641.4  | 714.4 | 786.4  | 859.4  | 889.2  | 909.4  | 902.4  |
| 35°    | 349.7  | 426.2 | 501.7  | 577.3 | 654.6  | 732.8 | 810.1  | 887.5  | 930.5  | 958.6  | 947.2  |
| 37.5°  | 340.0  | 420.0 | 500.0  | 579.9 | 670.4  | 760.9 | 851.4  | 941.9  | 983.2  | 1013.1 | 999.9  |
| 40°    | 328.6  | 413.9 | 500.0  | 585.2 | 688.9  | 791.7 | 895.4  | 998.2  | 1051.8 | 1077.3 | 1057.1 |
| 42.5°  | 319.0  | 407.7 | 497.3  | 586.1 | 696.8  | 807.5 | 918.2  | 1028.9 | 1088.7 | 1124.7 | 1099.2 |
| 45°    | 306.7  | 395.4 | 483.3  | 572.0 | 694.2  | 816.3 | 937.6  | 1059.7 | 1129.1 | 1157.2 | 1122.1 |
| 47.5°  | 293.5  | 381.3 | 468.3  | 555.3 | 685.4  | 815.4 | 945.5  | 1075.5 | 1139.7 | 1173.0 | 1140.5 |
| 50°    | 289.1  | 377.0 | 463.9  | 551.8 | 692.4  | 833.9 | 974.5  | 1115.0 | 1161.6 | 1188.9 | 1145.8 |
| 52.5°  | 288.2  | 381.3 | 475.4  | 568.5 | 710.0  | 850.6 | 992.0  | 1132.6 | 1170.4 | 1199.4 | 1160.7 |
| 55°    | 285.6  | 386.6 | 486.8  | 587.0 | 734.6  | 883.1 | 1030.7 | 1178.3 | 1216.1 | 1237.2 | 1208.2 |
| 57.5°  | 288.2  | 397.2 | 505.2  | 614.2 | 766.2  | 918.2 | 1070.2 | 1222.2 | 1267.9 | 1282.9 | 1276.7 |
| 60°    | 290.0  | 406.0 | 521.1  | 637.0 | 785.5  | 934.0 | 1082.5 | 1231.0 | 1278.5 | 1315.4 | 1322.4 |
| 62.5°  | 285.6  | 399.8 | 513.2  | 627.4 | 761.8  | 896.3 | 1030.7 | 1165.1 | 1243.3 | 1297.8 | 1329.4 |
| 65°    | 272.4  | 377.8 | 484.2  | 589.6 | 713.5  | 838.3 | 962.2  | 1086.1 | 1168.6 | 1249.5 | 1275.0 |
| 67.5°  | 243.4  | 333.0 | 422.6  | 512.3 | 620.3  | 728.4 | 835.6  | 943.7  | 1047.4 | 1125.6 | 1160.7 |
| 70°    | 210.9  | 281.2 | 352.4  | 422.6 | 521.1  | 619.5 | 717.9  | 816.3  | 907.7  | 993.8  | 1027.2 |
| 72.5°  | 183.6  | 238.1 | 293.5  | 348.0 | 418.3  | 487.7 | 558.0  | 627.4  | 735.5  | 821.6  | 854.1  |
| 75°    | 156.4  | 195.9 | 234.6  | 274.1 | 322.5  | 370.8 | 418.3  | 466.6  | 543.0  | 620.3  | 652.9  |
| 77.5°  | 120.4  | 146.7 | 172.2  | 197.7 | 231.1  | 263.6 | 297.0  | 329.5  | 383.1  | 441.1  | 457.8  |
| 80°    | 83.5   | 98.4  | 112.5  | 127.4 | 153.8  | 180.1 | 206.5  | 232.9  | 268.0  | 300.5  | 326.0  |
| 82.5°  | 51.8   | 61.5  | 70.3   | 79.1  | 100.2  | 121.3 | 141.5  | 162.6  | 176.6  | 178.4  | 203.9  |
| 85°    | 33.4   | 39.5  | 44.8   | 50.1  | 62.4   | 75.6  | 87.9   | 100.2  | 89.6   | 83.5   | 99.3   |
| 87.5°  | 13.2   | 16.7  | 19.3   | 22.0  | 21.1   | 20.2  | 19.3   | 18.5   | 15.8   | 14.1   | 17.6   |
| 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° | 272.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 275°   | 277.5° | 280°   | 282.5° | 285°   | 287.5° | 290°   | 292.5° | 295°   | 297.5° | 300°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  |
| 2.5°   | 677.5  | 680.1  | 682.7  | 684.5  | 687.1  | 688.0  | 688.9  | 688.9  | 689.8  | 690.6  | 692.4  |
| 5°     | 710.0  | 715.2  | 720.5  | 724.9  | 730.2  | 734.6  | 738.1  | 742.5  | 746.0  | 746.0  | 745.1  |
| 7.5°   | 682.7  | 695.9  | 709.1  | 722.3  | 735.5  | 745.1  | 753.9  | 763.6  | 772.4  | 774.1  | 775.9  |
| 10°    | 646.7  | 660.8  | 673.9  | 688.0  | 701.2  | 716.1  | 730.2  | 744.2  | 759.2  | 761.8  | 765.3  |
| 12.5°  | 613.3  | 630.0  | 646.7  | 662.5  | 679.2  | 689.8  | 700.3  | 710.0  | 720.5  | 727.5  | 734.6  |
| 15°    | 612.4  | 626.5  | 640.6  | 653.7  | 667.8  | 673.9  | 680.1  | 685.4  | 691.5  | 691.5  | 692.4  |
| 17.5°  | 632.7  | 641.4  | 650.2  | 658.1  | 666.9  | 667.8  | 669.6  | 670.4  | 671.3  | 668.7  | 666.0  |
| 20°    | 672.2  | 675.7  | 679.2  | 682.7  | 686.3  | 680.1  | 674.8  | 668.7  | 662.5  | 655.5  | 649.3  |
| 22.5°  | 730.2  | 722.3  | 714.4  | 706.5  | 698.6  | 688.0  | 676.6  | 666.0  | 654.6  | 645.8  | 637.0  |
| 25°    | 784.7  | 775.0  | 765.3  | 755.7  | 746.0  | 723.2  | 700.3  | 676.6  | 653.7  | 644.1  | 634.4  |
| 27.5°  | 857.6  | 842.7  | 827.7  | 812.8  | 797.8  | 767.1  | 736.3  | 705.6  | 674.8  | 658.1  | 642.3  |
| 30°    | 875.2  | 858.5  | 841.8  | 824.2  | 807.5  | 777.6  | 748.6  | 718.8  | 688.9  | 669.6  | 651.1  |
| 32.5°  | 900.6  | 881.3  | 862.0  | 842.7  | 823.3  | 794.3  | 765.3  | 735.5  | 706.5  | 688.9  | 670.4  |
| 35°    | 942.8  | 920.9  | 898.9  | 876.0  | 854.1  | 824.2  | 795.2  | 765.3  | 735.5  | 715.2  | 695.9  |
| 37.5°  | 978.9  | 953.4  | 927.9  | 902.4  | 876.9  | 850.6  | 823.3  | 797.0  | 769.7  | 749.5  | 730.2  |
| 40°    | 1019.3 | 991.2  | 963.0  | 935.8  | 907.7  | 883.1  | 858.5  | 833.0  | 808.4  | 792.6  | 776.8  |
| 42.5°  | 1054.4 | 1020.1 | 986.8  | 953.4  | 919.1  | 902.4  | 886.6  | 869.9  | 853.2  | 845.3  | 836.5  |
| 45°    | 1079.0 | 1047.4 | 1014.9 | 983.2  | 951.6  | 939.3  | 927.0  | 914.7  | 902.4  | 910.3  | 918.2  |
| 47.5°  | 1089.6 | 1064.1 | 1039.5 | 1014.9 | 989.4  | 993.8  | 998.2  | 1001.7 | 1006.1 | 1016.6 | 1028.1 |
| 50°    | 1099.2 | 1085.2 | 1070.2 | 1056.2 | 1041.2 | 1057.9 | 1073.7 | 1090.4 | 1107.1 | 1129.1 | 1151.1 |
| 52.5°  | 1118.6 | 1110.7 | 1103.6 | 1095.7 | 1087.8 | 1116.8 | 1145.8 | 1174.8 | 1203.8 | 1228.4 | 1253.0 |
| 55°    | 1176.6 | 1170.4 | 1164.3 | 1157.2 | 1151.1 | 1192.4 | 1232.8 | 1274.1 | 1315.4 | 1340.9 | 1366.3 |
| 57.5°  | 1256.5 | 1253.0 | 1248.6 | 1245.1 | 1240.7 | 1281.1 | 1320.7 | 1360.2 | 1400.6 | 1425.2 | 1450.7 |
| 60°    | 1317.1 | 1318.0 | 1318.0 | 1318.9 | 1318.9 | 1349.7 | 1380.4 | 1412.0 | 1442.8 | 1463.9 | 1485.9 |
| 62.5°  | 1349.7 | 1347.9 | 1346.1 | 1344.4 | 1342.6 | 1368.1 | 1393.6 | 1419.1 | 1444.6 | 1460.4 | 1476.2 |
| 65°    | 1314.5 | 1324.2 | 1333.8 | 1343.5 | 1353.2 | 1356.7 | 1359.3 | 1362.8 | 1365.5 | 1375.1 | 1384.8 |
| 67.5°  | 1196.8 | 1216.1 | 1234.5 | 1253.9 | 1272.3 | 1259.2 | 1246.8 | 1233.7 | 1220.5 | 1223.1 | 1224.9 |
| 70°    | 1065.8 | 1087.8 | 1110.7 | 1132.6 | 1154.6 | 1123.8 | 1093.1 | 1061.4 | 1030.7 | 1020.1 | 1009.6 |
| 72.5°  | 898.9  | 918.2  | 938.4  | 957.8  | 977.1  | 939.3  | 902.4  | 864.6  | 826.8  | 808.4  | 789.9  |
| 75°    | 687.1  | 710.0  | 733.7  | 756.5  | 779.4  | 737.2  | 694.2  | 652.0  | 608.9  | 596.6  | 585.2  |
| 77.5°  | 500.8  | 528.1  | 555.3  | 582.6  | 609.8  | 572.0  | 534.2  | 495.6  | 457.8  | 450.8  | 443.7  |
| 80°    | 364.7  | 385.7  | 406.0  | 427.0  | 447.2  | 425.3  | 403.3  | 381.3  | 359.4  | 358.5  | 357.6  |
| 82.5°  | 246.0  | 264.5  | 282.1  | 300.5  | 318.1  | 309.3  | 301.4  | 292.6  | 283.8  | 292.6  | 302.3  |
| 85°    | 126.5  | 152.0  | 178.4  | 203.9  | 229.3  | 226.7  | 224.9  | 222.3  | 219.7  | 231.1  | 241.6  |
| 87.5°  | 25.5   | 47.4   | 69.4   | 90.5   | 112.5  | 107.2  | 101.9  | 95.8   | 90.5   | 94.0   | 96.7   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° | 300° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305°   | 307.5° | 310°   | 312.5° | 315°   | 317.5° | 320°   | 322.5° | 325°   | 327.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  |
| 2.5°   | 693.3  | 694.2  | 694.2  | 694.2  | 694.2  | 694.2  | 692.4  | 691.5  | 689.8  | 688.0  | 685.4  |
| 5°     | 745.1  | 744.2  | 740.7  | 737.2  | 732.8  | 729.3  | 726.7  | 723.2  | 720.5  | 717.0  | 711.7  |
| 7.5°   | 777.6  | 779.4  | 773.2  | 768.0  | 761.8  | 755.7  | 749.5  | 743.4  | 737.2  | 731.1  | 718.8  |
| 10°    | 768.0  | 770.6  | 767.1  | 763.6  | 759.2  | 755.7  | 748.6  | 740.7  | 733.7  | 725.8  | 710.9  |
| 12.5°  | 740.7  | 747.8  | 746.0  | 744.2  | 742.5  | 740.7  | 736.3  | 731.1  | 726.7  | 721.4  | 704.7  |
| 15°    | 692.4  | 692.4  | 693.3  | 694.2  | 694.2  | 695.0  | 695.9  | 696.8  | 697.7  | 698.6  | 688.9  |
| 17.5°  | 663.4  | 660.8  | 660.8  | 660.8  | 660.8  | 660.8  | 664.3  | 668.7  | 672.2  | 675.7  | 673.1  |
| 20°    | 642.3  | 636.2  | 635.3  | 635.3  | 634.4  | 633.5  | 639.7  | 646.7  | 652.9  | 659.0  | 662.5  |
| 22.5°  | 628.3  | 619.5  | 618.6  | 617.7  | 616.8  | 616.0  | 623.9  | 631.8  | 639.7  | 647.6  | 659.9  |
| 25°    | 624.7  | 615.1  | 616.0  | 616.8  | 616.8  | 617.7  | 623.9  | 630.0  | 636.2  | 642.3  | 663.4  |
| 27.5°  | 625.6  | 609.8  | 610.7  | 611.6  | 611.6  | 612.4  | 622.1  | 630.9  | 640.6  | 649.3  | 675.7  |
| 30°    | 631.8  | 613.3  | 611.6  | 609.8  | 608.0  | 606.3  | 619.5  | 632.7  | 645.8  | 659.0  | 679.2  |
| 32.5°  | 652.9  | 635.3  | 630.9  | 626.5  | 622.1  | 617.7  | 633.5  | 648.5  | 664.3  | 679.2  | 695.9  |
| 35°    | 675.7  | 656.4  | 654.6  | 652.9  | 650.2  | 648.5  | 662.5  | 677.5  | 691.5  | 705.6  | 720.5  |
| 37.5°  | 710.0  | 690.6  | 688.9  | 686.3  | 684.5  | 681.9  | 697.7  | 712.6  | 728.4  | 743.4  | 756.5  |
| 40°    | 760.9  | 745.1  | 744.2  | 744.2  | 743.4  | 742.5  | 754.8  | 768.0  | 780.3  | 792.6  | 801.4  |
| 42.5°  | 828.6  | 820.7  | 823.3  | 826.8  | 829.5  | 832.1  | 841.8  | 852.3  | 862.0  | 871.7  | 869.0  |
| 45°    | 926.1  | 934.0  | 934.9  | 935.8  | 936.7  | 937.6  | 940.2  | 943.7  | 946.3  | 949.0  | 938.4  |
| 47.5°  | 1038.6 | 1049.1 | 1054.4 | 1059.7 | 1064.1 | 1069.4 | 1065.8 | 1061.4 | 1057.9 | 1053.5 | 1027.2 |
| 50°    | 1172.2 | 1194.1 | 1193.2 | 1192.4 | 1190.6 | 1189.7 | 1182.7 | 1175.7 | 1167.8 | 1160.7 | 1122.1 |
| 52.5°  | 1277.6 | 1302.2 | 1306.6 | 1311.0 | 1315.4 | 1319.8 | 1306.6 | 1293.4 | 1279.4 | 1266.2 | 1217.9 |
| 55°    | 1391.0 | 1416.4 | 1417.3 | 1418.2 | 1418.2 | 1419.1 | 1400.6 | 1382.2 | 1362.8 | 1344.4 | 1294.3 |
| 57.5°  | 1475.3 | 1499.9 | 1497.3 | 1495.5 | 1492.9 | 1490.2 | 1468.3 | 1446.3 | 1424.3 | 1402.4 | 1352.3 |
| 60°    | 1506.9 | 1528.0 | 1522.8 | 1517.5 | 1511.3 | 1506.1 | 1489.4 | 1472.7 | 1455.1 | 1438.4 | 1390.1 |
| 62.5°  | 1492.0 | 1507.8 | 1499.9 | 1492.9 | 1485.0 | 1477.1 | 1456.0 | 1434.0 | 1412.9 | 1391.0 | 1355.8 |
| 65°    | 1393.6 | 1403.3 | 1392.7 | 1383.0 | 1373.4 | 1362.8 | 1345.3 | 1327.7 | 1309.2 | 1291.7 | 1267.9 |
| 67.5°  | 1227.5 | 1229.3 | 1228.4 | 1227.5 | 1226.6 | 1225.8 | 1200.3 | 1174.8 | 1148.4 | 1123.0 | 1121.2 |
| 70°    | 999.9  | 989.4  | 991.2  | 993.8  | 995.5  | 997.3  | 978.0  | 959.5  | 940.2  | 920.9  | 929.6  |
| 72.5°  | 771.5  | 753.0  | 757.4  | 762.7  | 767.1  | 771.5  | 755.7  | 740.7  | 724.9  | 709.1  | 721.4  |
| 75°    | 572.9  | 561.5  | 565.9  | 571.1  | 575.5  | 579.9  | 573.8  | 567.6  | 560.6  | 554.4  | 565.9  |
| 77.5°  | 436.7  | 429.7  | 430.6  | 430.6  | 431.4  | 431.4  | 432.3  | 434.1  | 434.9  | 435.8  | 448.1  |
| 80°    | 355.9  | 355.0  | 354.1  | 353.2  | 351.5  | 350.6  | 359.4  | 368.2  | 377.0  | 385.7  | 391.9  |
| 82.5°  | 311.1  | 319.8  | 314.6  | 310.2  | 304.9  | 299.6  | 307.5  | 315.4  | 323.4  | 331.3  | 328.6  |
| 85°    | 253.1  | 263.6  | 253.9  | 244.3  | 233.7  | 224.1  | 231.1  | 237.2  | 244.3  | 250.4  | 246.9  |
| 87.5°  | 100.2  | 102.8  | 87.0   | 72.1   | 56.2   | 40.4   | 64.1   | 87.0   | 110.7  | 133.6  | 137.1  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305° | 307.5° | 310° | 312.5° | 315° | 317.5° | 320° | 322.5° | 325° | 327.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 330°   | 332.5° | 335°   | 337.5° | 340°   | 342.5° | 345°   | 347.5° | 350°   | 352.5° | 355°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  | 632.7  |
| 2.5°   | 682.7  | 679.2  | 676.6  | 675.7  | 673.9  | 673.1  | 671.3  | 669.6  | 666.9  | 665.2  | 662.5  |
| 5°     | 705.6  | 700.3  | 694.2  | 685.4  | 677.5  | 668.7  | 659.9  | 652.0  | 644.1  | 635.3  | 627.4  |
| 7.5°   | 706.5  | 694.2  | 681.9  | 670.4  | 658.1  | 646.7  | 634.4  | 623.9  | 612.4  | 601.0  | 590.5  |
| 10°    | 696.8  | 681.9  | 666.9  | 652.0  | 637.9  | 623.0  | 608.0  | 595.7  | 582.6  | 569.4  | 557.1  |
| 12.5°  | 688.9  | 672.2  | 655.5  | 637.9  | 621.2  | 603.7  | 586.1  | 573.8  | 561.5  | 549.2  | 536.9  |
| 15°    | 679.2  | 668.7  | 659.0  | 643.2  | 627.4  | 611.6  | 595.7  | 579.1  | 563.2  | 546.5  | 529.8  |
| 17.5°  | 671.3  | 668.7  | 666.0  | 655.5  | 645.0  | 633.5  | 623.0  | 606.3  | 589.6  | 572.0  | 555.3  |
| 20°    | 666.9  | 670.4  | 673.9  | 668.7  | 663.4  | 657.3  | 652.0  | 639.7  | 627.4  | 614.2  | 601.9  |
| 22.5°  | 672.2  | 685.4  | 697.7  | 698.6  | 700.3  | 701.2  | 702.1  | 690.6  | 679.2  | 666.9  | 655.5  |
| 25°    | 684.5  | 705.6  | 726.7  | 738.1  | 749.5  | 761.8  | 773.2  | 766.2  | 759.2  | 752.2  | 745.1  |
| 27.5°  | 701.2  | 727.5  | 753.9  | 770.6  | 786.4  | 803.1  | 819.8  | 818.9  | 818.1  | 816.3  | 815.4  |
| 30°    | 698.6  | 718.8  | 739.0  | 759.2  | 779.4  | 799.6  | 819.8  | 830.4  | 840.0  | 850.6  | 861.1  |
| 32.5°  | 713.5  | 730.2  | 747.8  | 768.8  | 789.9  | 811.9  | 833.0  | 855.0  | 876.0  | 898.0  | 920.0  |
| 35°    | 736.3  | 751.3  | 767.1  | 789.9  | 813.7  | 836.5  | 860.2  | 886.6  | 913.8  | 941.1  | 967.4  |
| 37.5°  | 770.6  | 783.8  | 797.8  | 817.2  | 837.4  | 856.7  | 876.9  | 915.6  | 954.2  | 993.8  | 1032.5 |
| 40°    | 810.1  | 818.9  | 827.7  | 846.2  | 864.6  | 883.1  | 901.5  | 949.9  | 998.2  | 1046.5 | 1094.8 |
| 42.5°  | 867.3  | 864.6  | 862.0  | 876.9  | 892.7  | 907.7  | 923.5  | 967.4  | 1011.4 | 1055.3 | 1099.2 |
| 45°    | 927.9  | 917.3  | 906.8  | 913.8  | 921.7  | 928.8  | 936.7  | 981.5  | 1026.3 | 1072.0 | 1116.8 |
| 47.5°  | 1000.8 | 974.5  | 948.1  | 941.9  | 935.8  | 928.8  | 922.6  | 970.9  | 1019.3 | 1068.5 | 1116.8 |
| 50°    | 1083.4 | 1043.9 | 1005.2 | 989.4  | 972.7  | 956.9  | 940.2  | 979.7  | 1020.1 | 1060.6 | 1100.1 |
| 52.5°  | 1169.5 | 1120.3 | 1072.0 | 1047.4 | 1022.8 | 997.3  | 972.7  | 1006.1 | 1040.4 | 1074.6 | 1108.0 |
| 55°    | 1243.3 | 1193.2 | 1142.3 | 1113.3 | 1084.3 | 1055.3 | 1026.3 | 1059.7 | 1093.1 | 1126.5 | 1159.9 |
| 57.5°  | 1302.2 | 1252.1 | 1202.0 | 1174.8 | 1146.7 | 1119.4 | 1091.3 | 1123.0 | 1155.5 | 1188.0 | 1219.6 |
| 60°    | 1342.6 | 1294.3 | 1246.0 | 1219.6 | 1193.2 | 1166.9 | 1140.5 | 1178.3 | 1216.1 | 1254.8 | 1292.5 |
| 62.5°  | 1321.5 | 1286.4 | 1251.2 | 1239.8 | 1228.4 | 1216.1 | 1204.7 | 1240.7 | 1275.8 | 1311.9 | 1347.9 |
| 65°    | 1244.2 | 1220.5 | 1196.8 | 1208.2 | 1220.5 | 1231.9 | 1244.2 | 1267.9 | 1291.7 | 1316.3 | 1340.0 |
| 67.5°  | 1118.6 | 1116.8 | 1114.2 | 1139.7 | 1165.1 | 1191.5 | 1217.0 | 1232.8 | 1247.7 | 1263.5 | 1279.4 |
| 70°    | 938.4  | 948.1  | 956.9  | 1000.8 | 1044.8 | 1088.7 | 1132.6 | 1138.8 | 1144.9 | 1151.1 | 1157.2 |
| 72.5°  | 734.6  | 746.9  | 760.1  | 818.1  | 875.2  | 933.2  | 991.2  | 987.6  | 984.1  | 979.7  | 976.2  |
| 75°    | 578.2  | 589.6  | 601.9  | 655.5  | 709.1  | 762.7  | 816.3  | 801.4  | 787.3  | 772.4  | 757.4  |
| 77.5°  | 461.3  | 473.6  | 486.8  | 536.9  | 587.0  | 637.9  | 688.0  | 652.0  | 616.0  | 579.9  | 543.9  |
| 80°    | 397.2  | 403.3  | 408.6  | 442.9  | 476.2  | 510.5  | 544.8  | 507.9  | 470.1  | 432.3  | 395.4  |
| 82.5°  | 326.0  | 322.5  | 319.8  | 340.0  | 360.3  | 380.5  | 400.7  | 365.5  | 330.4  | 294.4  | 259.2  |
| 85°    | 243.4  | 239.9  | 236.4  | 246.9  | 257.5  | 268.9  | 279.4  | 239.0  | 198.6  | 157.3  | 116.9  |
| 87.5°  | 141.5  | 145.0  | 148.5  | 159.9  | 171.3  | 183.6  | 195.1  | 153.8  | 112.5  | 70.3   | 29.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 332.5° | 335° | 337.5° | 340° | 342.5° | 345° | 347.5° | 350° | 352.5° | 355° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P671899  
 CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360°   |
|--------|--------|--------|
| 0°     | 632.7  | 632.7  |
| 2.5°   | 657.3  | 652.9  |
| 5°     | 621.2  | 615.1  |
| 7.5°   | 581.7  | 573.8  |
| 10°    | 545.7  | 535.1  |
| 12.5°  | 522.8  | 509.6  |
| 15°    | 514.0  | 498.2  |
| 17.5°  | 540.4  | 525.5  |
| 20°    | 580.8  | 560.6  |
| 22.5°  | 630.0  | 605.4  |
| 25°    | 715.2  | 685.4  |
| 27.5°  | 784.7  | 753.9  |
| 30°    | 827.7  | 794.3  |
| 32.5°  | 875.2  | 831.2  |
| 35°    | 924.4  | 882.2  |
| 37.5°  | 984.1  | 936.7  |
| 40°    | 1045.6 | 996.4  |
| 42.5°  | 1066.7 | 1035.1 |
| 45°    | 1086.9 | 1057.1 |
| 47.5°  | 1091.3 | 1066.7 |
| 50°    | 1095.7 | 1092.2 |
| 52.5°  | 1108.0 | 1107.1 |
| 55°    | 1160.7 | 1161.6 |
| 57.5°  | 1225.8 | 1231.0 |
| 60°    | 1285.5 | 1279.4 |
| 62.5°  | 1316.3 | 1284.6 |
| 65°    | 1295.2 | 1251.2 |
| 67.5°  | 1231.9 | 1184.5 |
| 70°    | 1093.1 | 1028.9 |
| 72.5°  | 920.0  | 863.7  |
| 75°    | 709.1  | 661.6  |
| 77.5°  | 504.4  | 464.8  |
| 80°    | 355.0  | 315.4  |
| 82.5°  | 227.6  | 195.9  |
| 85°    | 102.8  | 89.6   |
| 87.5°  | 29.0   | 28.1   |
| 90°    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    |

REPORT NUMBER: P671899

CATALOG NUMBER: CCP-SA-1A-850-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

(END OF REPORT)