

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P672853

Luminaire Tested: **CCP-SA1B-760-U-RW**

Issue Date: 04/16/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P672853  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 04/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCP-SA1B-760-U-RW  
Description: INVUE CLEAR CURVE POLE MOUNT LIGHT SQUARE LUMINAIRE @450mA w/ RW  
distribution lens  
Light Source: (16) 5700K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3593.6 lumens  
Efficiency: N/A  
Efficacy: 149.7 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type II - Medium  
BUG Rating: B2 - U0 - G2


Input Watts (W): 24  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P672853

CATALOG NUMBER: CCP-SA1B-760-U-RW

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 1.9 fc  
 Type II - Medium - N/A

REPORT NUMBER: P672853  
CATALOG NUMBER: CCP-SA1B-760-U-RW

## Luminous Intensity Polar Plot



REPORT NUMBER: P672853

CATALOG NUMBER: CCP-SA1B-760-U-RW


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1796.8   | 0.0    | 1796.8 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Street Side</b> | Lumens    | 1796.8   | 0.0    | 1796.8 |
|                    | % Fixture | 50.0     | 0.0    | 50.0   |
| <b>Total</b>       | Lumens    | 3593.6   | 0.0    | 3593.6 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 36.2   | 1.0       |
| 10°-20°   | 121.9  | 3.4       |
| 20°-30°   | 238.0  | 6.6       |
| 30°-40°   | 410.6  | 11.4      |
| 40°-50°   | 665.1  | 18.5      |
| 50°-60°   | 904.6  | 25.2      |
| 60°-70°   | 834.5  | 23.2      |
| 70°-80°   | 349.2  | 9.7       |
| 80°-90°   | 33.3   | 0.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 3593.6 | 100.0     |
| 0°-180°   | 3593.6 | 100.0     |



REPORT NUMBER: P672853


CATALOG NUMBER: CCP-SA1B-760-U-RW

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 198.1  | 5.5       |                         |      |         |
| FM   | (30°-60°)   | 990.2  | 27.6      |                         |      |         |
| FH   | (60°-80°)   | 591.9  | 16.5      |                         |      | G0/660  |
| FVH  | (80°-90°)   | 16.7   | 0.5       |                         |      | G1/100  |
| BL   | (0°-30°)    | 198.1  | 5.5       | B1/500                  |      |         |
| BM   | (30°-60°)   | 990.2  | 27.6      | B1/1000                 |      |         |
| BH   | (60°-80°)   | 591.9  | 16.5      | B2/1000                 |      | G2/1000 |
| BVH  | (80°-90°)   | 16.7   | 0.5       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B2-U0-G2**

Type II Medium



REPORT NUMBER: P672853

CATALOG NUMBER: CCP-SA1B-760-U-RW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 5°    | 15°   | 25°    | 35°    | 45°    | 55°    | 65°    | 75°    | 85°    | 90°    |
|-------|-------|-------|-------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 365.6 | 365.6 | 365.6 | 365.6  | 365.6  | 365.6  | 365.6  | 365.6  | 365.6  | 365.6  | 365.6  |
| 2.5°  | 363.3 | 363.3 | 364.3 | 365.6  | 366.1  | 367.1  | 367.4  | 367.4  | 369.0  | 368.7  | 369.0  |
| 5°    | 362.2 | 362.2 | 364.0 | 366.4  | 369.0  | 372.1  | 375.2  | 377.0  | 380.8  | 381.6  | 381.9  |
| 7.5°  | 363.3 | 363.5 | 366.1 | 370.0  | 374.4  | 380.1  | 386.0  | 390.9  | 397.4  | 399.7  | 401.2  |
| 10°   | 367.1 | 367.4 | 370.8 | 376.2  | 382.9  | 391.2  | 399.7  | 407.4  | 417.8  | 422.4  | 423.2  |
| 12.5° | 373.1 | 373.3 | 378.3 | 387.0  | 396.6  | 406.9  | 416.5  | 426.3  | 439.2  | 446.2  | 447.8  |
| 15°   | 382.1 | 381.4 | 389.1 | 402.0  | 415.5  | 428.4  | 436.9  | 446.5  | 460.2  | 469.2  | 471.5  |
| 17.5° | 394.5 | 395.0 | 404.6 | 421.1  | 437.7  | 450.9  | 459.4  | 464.8  | 476.7  | 486.0  | 488.3  |
| 20°   | 410.0 | 412.4 | 424.5 | 443.6  | 463.0  | 477.0  | 482.9  | 482.1  | 488.8  | 496.8  | 498.7  |
| 22.5° | 432.0 | 433.5 | 448.3 | 469.7  | 491.9  | 506.4  | 508.7  | 500.2  | 499.9  | 505.1  | 507.4  |
| 25°   | 457.8 | 459.1 | 474.6 | 499.4  | 522.9  | 538.2  | 535.9  | 521.1  | 513.4  | 513.6  | 515.2  |
| 27.5° | 488.1 | 490.6 | 506.7 | 532.0  | 556.3  | 570.2  | 566.9  | 545.4  | 530.2  | 525.5  | 524.5  |
| 30°   | 527.3 | 530.2 | 546.5 | 570.7  | 592.2  | 604.6  | 599.4  | 572.3  | 549.6  | 541.8  | 540.3  |
| 32.5° | 578.5 | 578.2 | 595.0 | 618.5  | 633.5  | 641.5  | 631.5  | 600.7  | 572.0  | 561.7  | 559.6  |
| 35°   | 631.2 | 633.8 | 650.3 | 673.1  | 684.4  | 684.9  | 668.9  | 634.3  | 600.2  | 582.4  | 578.5  |
| 37.5° | 690.6 | 691.9 | 711.0 | 732.5  | 740.0  | 735.8  | 712.1  | 673.6  | 634.3  | 615.4  | 608.7  |
| 40°   | 751.6 | 752.9 | 775.1 | 795.8  | 804.0  | 794.2  | 763.0  | 717.0  | 674.6  | 653.9  | 650.1  |
| 42.5° | 808.2 | 811.5 | 836.3 | 860.6  | 868.6  | 857.3  | 819.5  | 764.5  | 717.2  | 697.3  | 692.2  |
| 45°   | 855.2 | 858.8 | 886.7 | 917.7  | 931.9  | 922.6  | 880.0  | 818.0  | 766.3  | 744.9  | 736.1  |
| 47.5° | 890.6 | 895.3 | 925.0 | 962.2  | 989.8  | 988.0  | 944.3  | 874.6  | 819.0  | 793.7  | 785.7  |
| 50°   | 914.9 | 919.8 | 951.8 | 991.9  | 1033.5 | 1047.4 | 1009.7 | 937.1  | 877.7  | 849.3  | 843.8  |
| 52.5° | 916.7 | 921.1 | 957.8 | 1007.6 | 1063.2 | 1093.9 | 1074.0 | 1003.0 | 942.3  | 912.8  | 908.9  |
| 55°   | 876.4 | 879.5 | 928.3 | 994.7  | 1075.3 | 1129.6 | 1132.7 | 1074.8 | 1011.3 | 981.5  | 979.7  |
| 57.5° | 783.9 | 788.3 | 846.7 | 934.5  | 1055.2 | 1152.6 | 1183.6 | 1150.0 | 1089.3 | 1061.4 | 1059.8 |
| 60°   | 633.3 | 638.9 | 705.6 | 822.4  | 982.3  | 1146.6 | 1226.7 | 1220.5 | 1174.5 | 1147.4 | 1146.4 |
| 62.5° | 446.7 | 448.8 | 518.3 | 647.0  | 839.7  | 1083.6 | 1247.7 | 1289.3 | 1262.9 | 1235.5 | 1237.1 |
| 65°   | 262.5 | 265.3 | 316.2 | 432.0  | 636.9  | 938.7  | 1211.5 | 1337.1 | 1333.7 | 1308.6 | 1311.2 |
| 67.5° | 138.7 | 138.7 | 164.3 | 236.1  | 400.5  | 702.8  | 1067.6 | 1310.7 | 1354.6 | 1332.7 | 1334.0 |
| 70°   | 95.9  | 95.6  | 100.2 | 118.6  | 193.5  | 435.6  | 798.6  | 1172.7 | 1312.0 | 1303.7 | 1307.1 |
| 72.5° | 81.1  | 80.6  | 80.9  | 83.5   | 98.4   | 196.9  | 485.0  | 903.3  | 1169.6 | 1182.3 | 1185.1 |
| 75°   | 71.1  | 70.3  | 69.8  | 69.2   | 70.5   | 89.4   | 221.2  | 557.3  | 867.1  | 946.7  | 945.1  |
| 77.5° | 61.2  | 60.7  | 60.2  | 58.4   | 56.3   | 58.6   | 90.4   | 250.6  | 445.9  | 526.3  | 520.6  |
| 80°   | 50.4  | 50.4  | 51.2  | 48.6   | 44.7   | 43.1   | 54.0   | 93.5   | 148.0  | 154.5  | 142.1  |
| 82.5° | 39.5  | 39.5  | 43.4  | 39.8   | 35.1   | 31.3   | 37.5   | 49.9   | 60.2   | 48.8   | 39.8   |
| 85°   | 27.9  | 28.2  | 36.2  | 33.1   | 27.1   | 18.1   | 23.3   | 29.7   | 33.8   | 21.4   | 16.8   |
| 87.5° | 11.4  | 12.1  | 22.5  | 17.8   | 17.1   | 9.0    | 10.9   | 13.2   | 16.8   | 9.0    | 7.2    |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

INVUE

Report Number: SP1-2012-088-5-R3

Luminaire Tested: CCW-SA1A-760-U-SL2-HSS

Test Date: 01/19/2021


### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2012-088-5-R3  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 01/19/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: INVUE  
 Catalog Number: **CCW-SA1A-760-U-SL2-HSS**  
 Description: INVUE WALL PACK

\*\*\*THIS IS A REVISION OF SP1-2012-088-5-R2. TO UPDATE THE CATALOG INFORMATION.\*\*\*TESTED IN SITU. INVUE WALL PACK LIGHT SQUARE T2 OPTICS 1-SQUARE WITH HOUSE SIDE SHIELD

### Spectral Parameters

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 5447   | CRI (Ra): | 71.9 |      |       |
| CIE u':                   | 0.2053 | R1:       | 70.7 | R9:  | -27.5 |
| CIE v':                   | 0.4809 | R2:       | 74.8 | R10: | 41.5  |
| Duv:                      | 0.0027 | R3:       | 78.7 | R11: | 74.9  |
| CIE x:                    | 0.3337 | R4:       | 74.0 | R12: | 49.9  |
| CIE y:                    | 0.3473 | R5:       | 72.5 | R13: | 70.2  |
| CIE z:                    | 0.3190 | R6:       | 67.7 | R14: | 88.1  |
| Peak Wavelength (nm):     | 443    | R7:       | 77.7 |      |       |
| Dominant Wavelength (nm): | 556    | R8:       | 58.8 |      |       |
| Purity:                   | 4.5    |           |      |      |       |
| Rf:                       | 72.3   |           |      |      |       |
| Rg:                       | 97.2   |           |      |      |       |



### Test Conditions


Stabilization Time: 75M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.4/18%  
 Sphere Temperature (°C): 25.3

REPORT NUMBER: SP1-2012-088-5-R3


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 7/29/2020        | 1/29/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2012-088-5-R3

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-2012-088-5-R3

### Photopic Flux vs. Wavelength




#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 828              | 0.0              | 490       | 9471             | 1.3              | 620       | 23317            | 6.1              | 750       | 1157             | 0.0              | 880       | 1136             | 0.0              |
| 365       | 696              | 0.0              | 495       | 12752            | 2.3              | 625       | 21413            | 4.7              | 755       | 1067             | 0.0              | 885       | 773              | 0.0              |
| 370       | 807              | 0.0              | 500       | 16685            | 3.7              | 630       | 19344            | 3.5              | 760       | 1059             | 0.0              | 890       | 872              | 0.0              |
| 375       | 837              | 0.0              | 505       | 20565            | 5.8              | 635       | 17464            | 2.6              | 765       | 1009             | 0.0              | 895       | 891              | 0.0              |
| 380       | 757              | 0.0              | 510       | 24119            | 8.3              | 640       | 15745            | 1.9              | 770       | 774              | 0.0              | 900       | 807              | 0.0              |
| 385       | 706              | 0.0              | 515       | 27181            | 11.3             | 645       | 14060            | 1.4              | 775       | 761              | 0.0              | 905       | 899              | 0.0              |
| 390       | 746              | 0.0              | 520       | 29555            | 14.3             | 650       | 12579            | 0.9              | 780       | 653              | 0.0              | 910       | 506              | 0.0              |
| 395       | 660              | 0.0              | 525       | 31307            | 16.8             | 655       | 11181            | 0.6              | 785       | 704              | 0.0              | 915       | 598              | 0.0              |
| 400       | 671              | 0.0              | 530       | 32558            | 19.2             | 660       | 9847             | 0.4              | 790       | 663              | 0.0              | 920       | 510              | 0.0              |
| 405       | 848              | 0.0              | 535       | 33301            | 20.7             | 665       | 8641             | 0.3              | 795       | 493              | 0.0              | 925       | 874              | 0.0              |
| 410       | 1490             | 0.0              | 540       | 33727            | 22.0             | 670       | 7535             | 0.2              | 800       | 584              | 0.0              | 930       | 549              | 0.0              |
| 415       | 3203             | 0.0              | 545       | 34356            | 22.9             | 675       | 6542             | 0.1              | 805       | 739              | 0.0              | 935       | 720              | 0.0              |
| 420       | 7298             | 0.0              | 550       | 34589            | 23.5             | 680       | 5664             | 0.1              | 810       | 601              | 0.0              | 940       | 754              | 0.0              |
| 425       | 15315            | 0.1              | 555       | 34855            | 23.8             | 685       | 4962             | 0.0              | 815       | 677              | 0.0              | 945       | 931              | 0.0              |
| 430       | 27886            | 0.2              | 560       | 35083            | 23.8             | 690       | 4369             | 0.0              | 820       | 726              | 0.0              | 950       | 811              | 0.0              |
| 435       | 45485            | 0.5              | 565       | 35553            | 23.6             | 695       | 3785             | 0.0              | 825       | 693              | 0.0              | 955       | 955              | 0.0              |
| 440       | 61965            | 1.0              | 570       | 35511            | 23.1             | 700       | 3318             | 0.0              | 830       | 619              | 0.0              | 960       | 1025             | 0.0              |
| 445       | 62721            | 1.3              | 575       | 35515            | 22.1             | 705       | 2962             | 0.0              | 835       | 738              | 0.0              | 965       | 916              | 0.0              |
| 450       | 44754            | 1.2              | 580       | 35114            | 20.9             | 710       | 2689             | 0.0              | 840       | 681              | 0.0              | 970       | 695              | 0.0              |
| 455       | 26152            | 0.9              | 585       | 34546            | 19.2             | 715       | 2476             | 0.0              | 845       | 691              | 0.0              | 975       | 568              | 0.0              |
| 460       | 17101            | 0.7              | 590       | 33522            | 17.3             | 720       | 2192             | 0.0              | 850       | 710              | 0.0              | 980       | 643              | 0.0              |
| 465       | 11400            | 0.6              | 595       | 32326            | 15.3             | 725       | 1939             | 0.0              | 855       | 1025             | 0.0              | 985       | 804              | 0.0              |
| 470       | 7763             | 0.5              | 600       | 30973            | 13.3             | 730       | 1698             | 0.0              | 860       | 889              | 0.0              | 990       | 812              | 0.0              |
| 475       | 6419             | 0.5              | 605       | 29160            | 11.3             | 735       | 1533             | 0.0              | 865       | 885              | 0.0              | 995       | 496              | 0.0              |
| 480       | 6330             | 0.6              | 610       | 27373            | 9.4              | 740       | 1375             | 0.0              | 870       | 905              | 0.0              | 1000      | 659              | 0.0              |
| 485       | 7299             | 0.9              | 615       | 25423            | 7.7              | 745       | 1254             | 0.0              | 875       | 739              | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2012-088-5-R3

### Scotopic Flux vs. Wavelength




Scotopic Lumens: 1610.2

S/P: 0.74

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 828              | 0.0              | 490       | 9471             | 14.6             | 620       | 23317            | 0.3              | 750       | 1157             | 0.0              | 880       | 1136             | 0.0              |
| 365       | 696              | 0.0              | 495       | 12752            | 20.6             | 625       | 21413            | 0.2              | 755       | 1067             | 0.0              | 885       | 773              | 0.0              |
| 370       | 807              | 0.0              | 500       | 16685            | 27.9             | 630       | 19344            | 0.1              | 760       | 1059             | 0.0              | 890       | 872              | 0.0              |
| 375       | 837              | 0.0              | 505       | 20565            | 35.0             | 635       | 17464            | 0.1              | 765       | 1009             | 0.0              | 895       | 891              | 0.0              |
| 380       | 757              | 0.0              | 510       | 24119            | 40.9             | 640       | 15745            | 0.0              | 770       | 774              | 0.0              | 900       | 807              | 0.0              |
| 385       | 706              | 0.0              | 515       | 27181            | 45.1             | 645       | 14060            | 0.0              | 775       | 761              | 0.0              | 905       | 899              | 0.0              |
| 390       | 746              | 0.0              | 520       | 29555            | 47.0             | 650       | 12579            | 0.0              | 780       | 653              | 0.0              | 910       | 506              | 0.0              |
| 395       | 660              | 0.0              | 525       | 31307            | 46.8             | 655       | 11181            | 0.0              | 785       | 704              | 0.0              | 915       | 598              | 0.0              |
| 400       | 671              | 0.0              | 530       | 32558            | 44.9             | 660       | 9847             | 0.0              | 790       | 663              | 0.0              | 920       | 510              | 0.0              |
| 405       | 848              | 0.0              | 535       | 33301            | 41.5             | 665       | 8641             | 0.0              | 795       | 493              | 0.0              | 925       | 874              | 0.0              |
| 410       | 1490             | 0.1              | 540       | 33727            | 37.3             | 670       | 7535             | 0.0              | 800       | 584              | 0.0              | 930       | 549              | 0.0              |
| 415       | 3203             | 0.3              | 545       | 34356            | 32.9             | 675       | 6542             | 0.0              | 805       | 739              | 0.0              | 935       | 720              | 0.0              |
| 420       | 7298             | 1.2              | 550       | 34589            | 28.3             | 680       | 5664             | 0.0              | 810       | 601              | 0.0              | 940       | 754              | 0.0              |
| 425       | 15315            | 3.7              | 555       | 34855            | 23.8             | 685       | 4962             | 0.0              | 815       | 677              | 0.0              | 945       | 931              | 0.0              |
| 430       | 27886            | 9.5              | 560       | 35083            | 19.6             | 690       | 4369             | 0.0              | 820       | 726              | 0.0              | 950       | 811              | 0.0              |
| 435       | 45485            | 20.3             | 565       | 35553            | 16.0             | 695       | 3785             | 0.0              | 825       | 693              | 0.0              | 955       | 955              | 0.0              |
| 440       | 61965            | 34.6             | 570       | 35511            | 12.5             | 700       | 3318             | 0.0              | 830       | 619              | 0.0              | 960       | 1025             | 0.0              |
| 445       | 62721            | 42.0             | 575       | 35515            | 9.7              | 705       | 2962             | 0.0              | 835       | 738              | 0.0              | 965       | 916              | 0.0              |
| 450       | 44754            | 34.7             | 580       | 35114            | 7.2              | 710       | 2689             | 0.0              | 840       | 681              | 0.0              | 970       | 695              | 0.0              |
| 455       | 26152            | 22.9             | 585       | 34546            | 5.3              | 715       | 2476             | 0.0              | 845       | 691              | 0.0              | 975       | 568              | 0.0              |
| 460       | 17101            | 16.5             | 590       | 33522            | 3.7              | 720       | 2192             | 0.0              | 850       | 710              | 0.0              | 980       | 643              | 0.0              |
| 465       | 11400            | 12.0             | 595       | 32326            | 2.6              | 725       | 1939             | 0.0              | 855       | 1025             | 0.0              | 985       | 804              | 0.0              |
| 470       | 7763             | 8.9              | 600       | 30973            | 1.7              | 730       | 1698             | 0.0              | 860       | 889              | 0.0              | 990       | 812              | 0.0              |
| 475       | 6419             | 8.0              | 605       | 29160            | 1.1              | 735       | 1533             | 0.0              | 865       | 885              | 0.0              | 995       | 496              | 0.0              |
| 480       | 6330             | 8.5              | 610       | 27373            | 0.7              | 740       | 1375             | 0.0              | 870       | 905              | 0.0              | 1000      | 659              | 0.0              |
| 485       | 7299             | 10.6             | 615       | 25423            | 0.5              | 745       | 1254             | 0.0              | 875       | 739              | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2012-088-5-R3

### Melanopic Flux vs. Wavelength




**Melanopic Lumens: 4010.3**      **S/P: 1.85**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 828              | 0.0              | 490       | 9471             | 7.9              | 620       | 23317            | 0.0              | 750       | 1157             | 0.0              | 880       | 1136             | 0.0              |
| 365       | 696              | 0.0              | 495       | 12752            | 10.5             | 625       | 21413            | 0.0              | 755       | 1067             | 0.0              | 885       | 773              | 0.0              |
| 370       | 807              | 0.0              | 500       | 16685            | 13.4             | 630       | 19344            | 0.0              | 760       | 1059             | 0.0              | 890       | 872              | 0.0              |
| 375       | 837              | 0.0              | 505       | 20565            | 15.8             | 635       | 17464            | 0.0              | 765       | 1009             | 0.0              | 895       | 891              | 0.0              |
| 380       | 757              | 0.0              | 510       | 24119            | 17.3             | 640       | 15745            | 0.0              | 770       | 774              | 0.0              | 900       | 807              | 0.0              |
| 385       | 706              | 0.0              | 515       | 27181            | 17.8             | 645       | 14060            | 0.0              | 775       | 761              | 0.0              | 905       | 899              | 0.0              |
| 390       | 746              | 0.0              | 520       | 29555            | 17.2             | 650       | 12579            | 0.0              | 780       | 653              | 0.0              | 910       | 506              | 0.0              |
| 395       | 660              | 0.0              | 525       | 31307            | 15.9             | 655       | 11181            | 0.0              | 785       | 704              | 0.0              | 915       | 598              | 0.0              |
| 400       | 671              | 0.0              | 530       | 32558            | 14.1             | 660       | 9847             | 0.0              | 790       | 663              | 0.0              | 920       | 510              | 0.0              |
| 405       | 848              | 0.0              | 535       | 33301            | 12.0             | 665       | 8641             | 0.0              | 795       | 493              | 0.0              | 925       | 874              | 0.0              |
| 410       | 1490             | 0.1              | 540       | 33727            | 9.9              | 670       | 7535             | 0.0              | 800       | 584              | 0.0              | 930       | 549              | 0.0              |
| 415       | 3203             | 0.2              | 545       | 34356            | 8.0              | 675       | 6542             | 0.0              | 805       | 739              | 0.0              | 935       | 720              | 0.0              |
| 420       | 7298             | 0.8              | 550       | 34589            | 6.2              | 680       | 5664             | 0.0              | 810       | 601              | 0.0              | 940       | 754              | 0.0              |
| 425       | 15315            | 2.4              | 555       | 34855            | 4.7              | 685       | 4962             | 0.0              | 815       | 677              | 0.0              | 945       | 931              | 0.0              |
| 430       | 27886            | 5.9              | 560       | 35083            | 3.5              | 690       | 4369             | 0.0              | 820       | 726              | 0.0              | 950       | 811              | 0.0              |
| 435       | 45485            | 12.1             | 565       | 35553            | 2.5              | 695       | 3785             | 0.0              | 825       | 693              | 0.0              | 955       | 955              | 0.0              |
| 440       | 61965            | 20.7             | 570       | 35511            | 1.7              | 700       | 3318             | 0.0              | 830       | 619              | 0.0              | 960       | 1025             | 0.0              |
| 445       | 62721            | 24.7             | 575       | 35515            | 1.2              | 705       | 2962             | 0.0              | 835       | 738              | 0.0              | 965       | 916              | 0.0              |
| 450       | 44754            | 20.6             | 580       | 35114            | 0.8              | 710       | 2689             | 0.0              | 840       | 681              | 0.0              | 970       | 695              | 0.0              |
| 455       | 26152            | 13.7             | 585       | 34546            | 0.5              | 715       | 2476             | 0.0              | 845       | 691              | 0.0              | 975       | 568              | 0.0              |
| 460       | 17101            | 10.1             | 590       | 33522            | 0.3              | 720       | 2192             | 0.0              | 850       | 710              | 0.0              | 980       | 643              | 0.0              |
| 465       | 11400            | 7.4              | 595       | 32326            | 0.2              | 725       | 1939             | 0.0              | 855       | 1025             | 0.0              | 985       | 804              | 0.0              |
| 470       | 7763             | 5.6              | 600       | 30973            | 0.1              | 730       | 1698             | 0.0              | 860       | 889              | 0.0              | 990       | 812              | 0.0              |
| 475       | 6419             | 4.9              | 605       | 29160            | 0.1              | 735       | 1533             | 0.0              | 865       | 885              | 0.0              | 995       | 496              | 0.0              |
| 480       | 6330             | 5.1              | 610       | 27373            | 0.0              | 740       | 1375             | 0.0              | 870       | 905              | 0.0              | 1000      | 659              | 0.0              |
| 485       | 7299             | 6.0              | 615       | 25423            | 0.0              | 745       | 1254             | 0.0              | 875       | 739              | 0.0              |           |                  |                  |





### Summary

$R_f = 72.3$   
 $R_g = 97.2$   
 CIE  $R_a = 71.9$   
 $R_g = -27.5$

### Spectral Power Distribution Comparison







### Color Vector Graphics





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 55 | CES51 = 89 | CES76 = 43 |
| CES02 = 59 | CES27 = 80 | CES52 = 90 | CES77 = 64 |
| CES03 = 30 | CES28 = 77 | CES53 = 77 | CES78 = 46 |
| CES04 = 69 | CES29 = 51 | CES54 = 82 | CES79 = 74 |
| CES05 = 46 | CES30 = 61 | CES55 = 81 | CES80 = 70 |
| CES06 = 50 | CES31 = 56 | CES56 = 71 | CES81 = 72 |
| CES07 = 38 | CES32 = 52 | CES57 = 69 | CES82 = 88 |
| CES08 = 38 | CES33 = 63 | CES58 = 70 | CES83 = 83 |
| CES09 = 29 | CES34 = 63 | CES59 = 88 | CES84 = 87 |
| CES10 = 72 | CES35 = 79 | CES60 = 92 | CES85 = 83 |
| CES11 = 55 | CES36 = 93 | CES61 = 88 | CES86 = 76 |
| CES12 = 61 | CES37 = 73 | CES62 = 82 | CES87 = 75 |
| CES13 = 41 | CES38 = 70 | CES63 = 75 | CES88 = 78 |
| CES14 = 74 | CES39 = 91 | CES64 = 72 | CES89 = 76 |
| CES15 = 70 | CES40 = 83 | CES65 = 65 | CES90 = 76 |
| CES16 = 46 | CES41 = 85 | CES66 = 66 | CES91 = 89 |
| CES17 = 48 | CES42 = 71 | CES67 = 64 | CES92 = 69 |
| CES18 = 55 | CES43 = 69 | CES68 = 70 | CES93 = 82 |
| CES19 = 71 | CES44 = 98 | CES69 = 80 | CES94 = 60 |
| CES20 = 64 | CES45 = 79 | CES70 = 58 | CES95 = 72 |
| CES21 = 85 | CES46 = 79 | CES71 = 54 | CES96 = 79 |
| CES22 = 77 | CES47 = 76 | CES72 = 84 | CES97 = 84 |
| CES23 = 91 | CES48 = 69 | CES73 = 47 | CES98 = 73 |
| CES24 = 90 | CES49 = 79 | CES74 = 94 | CES99 = 62 |
| CES25 = 71 | CES50 = 87 | CES75 = 50 |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)