

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: INVUE

Report Number: P1459797

Luminaire Tested: LXW-CX-AMB-X-U-A-GM-CBP

Issue Date: 5/26/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1459797  
TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2509-539-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 5/27/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: INVUE  
Catalog Number: LXW-CX-AMB-X-U-A-GM-CBP  
Description: LuxeScape OUTDOOR ARCHITECTURAL WALL MOUNT LUMINAIRE  
ASYMMETRIC OPTIC, GRAPHITE METALLIC PAINTED FINISH  
Light Source: 1571K CCT, 0 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 138 lumens  
Efficiency: N/A  
Efficacy: 15.5 lumens/watt  
Luminous Opening: Circular (Dia: 0.4' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G0  
  
Input Watts (W): 8.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: N/R  
Total Harmonic Distortion (THDi): N/R  
Frequency (hertz): 60  
Stabilization Time: HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1459797  
 CATALOG NUMBER: LXW-CX-AMB-X-U-A-GM-CBP

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 0.2 fc  
 Type III - Short - N/A

REPORT NUMBER: P1459797  
CATALOG NUMBER: LXW-CX-AMB-X-U-A-GM-CBP

### Luminous Intensity Polar Plot



— Vertical Plane Through 62-Deg Lateral    - - - Horizontal Cone Through 61-Deg Vertical

REPORT NUMBER: P1459797

CATALOG NUMBER: LXW-CX-AMB-X-U-A-GM-CBP


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	44.3	0.0	44.3
	% Fixture	32.1	0.0	32.1
<b>Street Side</b>	Lumens	93.8	0.0	93.8
	% Fixture	67.9	0.0	67.9
<b>Total</b>	Lumens	138.0	0.0	138.0
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.5	0.3
10°-20°	2.3	1.7
20°-30°	5.4	3.9
30°-40°	10.0	7.2
40°-50°	21.3	15.4
50°-60°	37.4	27.1
60°-70°	37.2	26.9
70°-80°	21.3	15.4
80°-90°	2.8	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	138.0	100.0
0°-180°	138.0	100.0



REPORT NUMBER: P1459797


CATALOG NUMBER: LXW-CX-AMB-X-U-A-GM-CBP

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	4.6	3.3			
FM	(30°-60°)	45.8	33.1			
FH	(60°-80°)	41.6	30.1			G0/660
FVH	(80°-90°)	1.9	1.3			G0/10
BL	(0°-30°)	3.6	2.6	B0/110		
BM	(30°-60°)	22.9	16.6	B0/220		
BH	(60°-80°)	16.8	12.2	B0/110		G0/110
BVH	(80°-90°)	0.9	0.7			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B0-U0-G0**

Type III Short





REPORT NUMBER: P1459797

CATALOG NUMBER: LXW-CX-AMB-X-U-A-GM-CBP

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	62°	65°	75°	85°
0°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
2.5°	2.9	2.9	2.9	3.1	2.9	2.6	2.6	2.6	2.6	2.4	2.4
5°	4.8	4.8	4.8	4.6	4.4	4.4	4.0	3.7	3.5	3.3	3.3
7.5°	7.5	7.3	7.9	7.7	6.8	5.9	5.5	5.3	5.1	4.8	4.6
10°	9.4	9.9	9.0	8.8	8.3	7.3	6.2	5.7	5.5	5.3	4.8
12.5°	11.0	10.3	9.9	10.1	9.0	7.7	6.6	5.7	5.5	5.3	5.1
15°	11.6	11.9	11.6	11.2	9.9	8.1	6.8	6.2	6.2	5.7	5.9
17.5°	13.0	13.0	12.7	11.4	10.3	8.6	7.7	7.5	7.3	6.6	6.6
20°	13.8	14.1	14.1	11.9	10.8	9.4	9.0	8.6	8.3	7.9	7.3
22.5°	14.7	15.2	14.7	13.0	11.6	10.5	10.5	10.3	10.1	9.2	8.8
25°	15.8	15.8	15.4	13.4	12.5	11.9	13.2	13.4	13.0	11.0	10.3
27.5°	16.7	16.9	16.0	14.5	13.4	13.8	16.0	16.0	15.8	13.0	11.6
30°	17.6	17.6	16.9	15.2	14.3	15.8	17.8	17.8	17.8	15.8	13.2
32.5°	18.2	18.2	17.6	15.8	15.2	17.6	19.6	20.0	19.8	17.8	14.5
35°	18.7	18.9	18.0	16.5	16.0	19.3	21.3	21.8	21.8	20.0	15.8
37.5°	19.6	19.6	18.9	16.9	17.4	21.8	24.0	24.4	24.4	22.4	17.6
40°	20.4	20.2	19.8	18.0	18.9	24.8	27.0	27.7	27.7	25.9	19.8
42.5°	21.8	21.8	21.3	19.6	21.8	31.2	33.6	35.2	35.2	32.5	24.4
45°	25.5	25.5	25.7	23.7	27.7	43.1	48.6	50.1	49.7	45.0	31.9
47.5°	27.5	27.2	28.3	25.7	33.0	53.4	60.2	62.6	62.2	57.8	39.6
50°	29.7	29.7	31.4	28.6	39.3	64.8	73.4	75.6	75.4	69.2	46.4
52.5°	30.3	30.5	32.7	29.9	43.5	73.2	85.3	88.3	87.7	78.4	51.6
55°	30.5	31.0	33.0	29.7	45.5	77.8	91.2	93.2	92.7	83.5	54.9
57.5°	30.1	30.5	31.9	27.9	46.4	78.4	91.2	93.2	92.5	84.8	56.5
60°	28.8	29.2	30.3	26.6	46.1	78.0	91.0	94.0	93.2	85.0	56.7
61°	28.1	28.3	29.4	25.9	45.7	77.6	91.6	94.5	93.6	84.8	56.3
62.5°	26.8	27.2	28.1	24.6	44.4	76.5	91.0	93.8	93.2	83.9	55.2
65°	24.2	24.6	25.0	22.0	42.0	72.7	85.7	87.2	87.0	79.1	51.9
67.5°	21.1	21.3	22.0	19.1	38.7	67.2	78.0	80.0	79.5	72.7	47.7
70°	17.6	17.8	18.5	15.8	34.7	60.0	70.3	72.5	72.1	65.5	42.6
72.5°	13.6	13.8	14.3	12.3	29.4	51.2	60.2	62.4	62.2	56.5	36.5
75°	9.7	9.9	10.3	9.0	23.1	41.5	48.1	49.4	49.9	45.7	28.8
77.5°	6.2	6.2	6.4	5.7	16.5	30.3	35.4	36.5	36.9	33.6	20.9
80°	3.3	3.3	3.3	3.1	9.4	18.9	22.2	23.3	23.1	21.3	12.5
82.5°	1.5	1.5	1.5	1.3	3.5	7.3	9.0	9.9	10.5	9.0	5.1
85°	0.7	0.7	0.9	0.4	0.9	1.3	1.5	1.8	2.0	2.0	1.3
87.5°	0.7	0.7	0.7	0.2	0.4	0.7	0.9	0.9	0.9	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1459797

CATALOG NUMBER: LXW-CX-AMB-X-U-A-GM-CBP

**CANDELA DISTRIBUTION (continued):**

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2
2.5°	2.4	2.4	2.4	2.4	2.9	2.6	2.6	2.4	2.2	2.2	2.2
5°	3.1	2.9	3.1	3.5	3.5	3.7	4.0	4.0	3.7	3.7	3.7
7.5°	4.6	4.4	4.4	4.6	5.3	5.9	5.9	5.5	5.1	4.6	4.6
10°	4.8	4.8	5.1	5.7	7.3	7.5	7.5	6.6	6.2	5.9	5.9
12.5°	5.1	5.1	5.5	6.2	7.9	7.9	7.9	7.5	6.8	6.2	6.2
15°	5.9	5.9	6.4	7.3	8.1	8.6	8.8	8.3	7.5	5.9	5.9
17.5°	6.6	7.0	7.5	8.1	8.8	9.2	9.2	8.8	7.5	6.4	5.9
20°	7.5	7.9	9.0	9.0	9.2	9.7	9.7	9.0	7.3	6.4	6.2
22.5°	8.6	9.2	10.1	9.9	9.9	10.1	10.3	9.4	7.5	6.6	6.4
25°	10.3	10.5	11.0	10.8	10.8	10.3	11.0	10.1	8.3	7.3	7.3
27.5°	11.6	11.6	12.1	11.6	11.4	11.2	11.4	10.8	9.0	8.1	7.9
30°	12.5	12.7	13.2	12.5	12.1	11.6	11.9	11.2	9.7	8.8	8.8
32.5°	13.6	13.8	13.8	13.4	12.5	12.1	12.3	11.4	9.9	9.4	9.2
35°	14.7	14.7	14.7	14.1	13.2	12.7	12.7	11.9	10.3	9.9	9.7
37.5°	15.8	15.8	15.8	14.9	13.8	13.4	13.2	12.3	11.0	10.5	10.3
40°	17.6	17.1	17.1	16.0	14.7	14.1	13.8	12.5	11.6	11.2	11.2
42.5°	20.9	20.0	19.8	17.8	16.3	15.4	14.9	13.6	12.7	12.3	12.1
45°	26.1	24.4	24.4	21.1	19.1	18.5	17.8	16.0	15.4	14.7	14.5
47.5°	31.2	28.6	28.6	24.0	21.1	20.7	19.8	17.8	17.1	16.5	16.3
50°	36.0	32.1	32.1	26.4	23.1	22.6	21.5	20.0	19.1	18.5	18.5
52.5°	39.6	34.7	34.7	27.9	24.2	24.0	22.9	21.1	20.2	19.6	19.6
55°	41.1	35.4	35.4	28.6	24.6	24.4	23.3	21.8	20.7	20.2	20.2
57.5°	41.3	34.7	34.7	28.3	24.4	24.2	22.6	21.1	20.7	20.4	20.2
60°	40.7	33.6	33.6	27.5	23.5	23.3	22.0	20.4	20.2	20.0	20.0
61°	40.2	33.2	33.0	26.8	23.1	22.9	21.5	20.2	20.0	19.8	19.8
62.5°	39.6	32.1	32.1	25.9	22.2	22.2	20.9	19.8	19.3	19.3	19.3
65°	36.9	29.7	29.4	24.0	20.4	20.4	19.3	18.7	18.2	18.2	18.2
67.5°	33.4	26.4	26.1	21.3	18.2	18.2	17.4	16.9	16.7	16.7	16.9
70°	29.2	22.9	22.4	18.2	15.6	15.8	14.9	15.2	14.9	14.9	15.2
72.5°	24.8	18.9	18.5	14.7	12.7	13.2	12.7	13.2	12.7	13.0	13.2
75°	19.3	14.5	14.1	11.0	9.9	10.3	10.1	10.8	10.5	10.8	10.8
77.5°	13.4	9.9	9.4	7.5	7.0	7.5	7.5	8.1	7.9	8.3	8.3
80°	7.7	5.9	5.5	4.4	4.4	4.6	4.8	5.5	5.5	5.7	5.9
82.5°	3.1	2.4	2.4	2.0	2.2	2.4	2.4	3.1	3.1	3.3	3.3
85°	0.7	0.9	1.1	0.9	0.9	0.9	0.7	1.1	1.1	1.3	1.3
87.5°	0.4	0.4	0.7	0.7	0.7	0.7	0.4	0.7	0.9	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Invue

Report Number: SP1-2509-539-4

Test Date: 04/14/2026

Luminaire Tested: Luxscape Bollard

Data in this report applies to families of products including ;Luxscape


**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2509-539-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 04/15/2026  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Invue  
 Catalog Number: **Luxscape Bollard**  
 Description: LXS-C1-AMB-LED-XX-Dx-S-GM-SPECULAR REFLECTOR

**Spectral Parameters**

CCT (K): 1571  
 CIE u': 0.3487  
 CIE v': 0.5475  
 Duv: 0.0106  
 CIE x: 0.5886  
 CIE y: 0.4107  
 CIE z: 0.0007  
 Peak Wavelength (nm): 596  
 Dominant Wavelength (nm): 592  
 Purity: 99.96896  
 R<sub>f</sub>: 1.4  
 R<sub>g</sub>: 0.2

CRI (Ra):	-19.0		
R1:	-31.4	R9:	-376.7
R2:	52.4	R10:	27.7
R3:	21.1	R11:	-91.5
R4:	-63.8	R12:	-12.3
R5:	-37.6	R13:	-13.7
R6:	40.7	R14:	48.6
R7:	-3.9	R15:	-63.0
R8:	-129.2		



**Test Conditions**


Stabilization Time: 95M  
 Operation Time: 2H 35M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2509-539-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2509-539-4

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



REPORT NUMBER: SP1-2509-539-4

**Photopic Flux vs. Wavelength**




**Photopic Lumens: NR**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	0	NR	620	41	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	19	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	10	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	6	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	4	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	3	NR	775	0	NR	905	0	NR
390	0	NR	520	1	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	1	NR	655	2	NR	785	0	NR	915	0	NR
400	0	NR	530	1	NR	660	1	NR	790	0	NR	920	0	NR
405	0	NR	535	2	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	3	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	6	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	10	NR	680	1	NR	810	0	NR	940	0	NR
425	0	NR	555	16	NR	685	0	NR	815	0	NR	945	0	NR
430	0	NR	560	28	NR	690	0	NR	820	0	NR	950	0	NR
435	0	NR	565	48	NR	695	0	NR	825	0	NR	955	0	NR
440	0	NR	570	84	NR	700	0	NR	830	0	NR	960	0	NR
445	0	NR	575	143	NR	705	0	NR	835	0	NR	965	0	NR
450	0	NR	580	243	NR	710	0	NR	840	0	NR	970	0	NR
455	0	NR	585	409	NR	715	0	NR	845	0	NR	975	0	NR
460	0	NR	590	686	NR	720	0	NR	850	0	NR	980	0	NR
465	0	NR	595	980	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	854	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	466	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	216	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	90	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2509-539-4

**Scotopic Flux vs. Wavelength**




**Scotopic Lumens: NR**

**S/P: 0.23**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	0	NR	620	41	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	19	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	10	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	6	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	4	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	3	NR	775	0	NR	905	0	NR
390	0	NR	520	1	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	1	NR	655	2	NR	785	0	NR	915	0	NR
400	0	NR	530	1	NR	660	1	NR	790	0	NR	920	0	NR
405	0	NR	535	2	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	3	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	6	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	10	NR	680	1	NR	810	0	NR	940	0	NR
425	0	NR	555	16	NR	685	0	NR	815	0	NR	945	0	NR
430	0	NR	560	28	NR	690	0	NR	820	0	NR	950	0	NR
435	0	NR	565	48	NR	695	0	NR	825	0	NR	955	0	NR
440	0	NR	570	84	NR	700	0	NR	830	0	NR	960	0	NR
445	0	NR	575	143	NR	705	0	NR	835	0	NR	965	0	NR
450	0	NR	580	243	NR	710	0	NR	840	0	NR	970	0	NR
455	0	NR	585	409	NR	715	0	NR	845	0	NR	975	0	NR
460	0	NR	590	686	NR	720	0	NR	850	0	NR	980	0	NR
465	0	NR	595	980	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	854	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	466	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	216	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	90	NR	745	0	NR	875	0	NR			

REPORT NUMBER: SP1-2509-539-4

**Melanopic Flux vs. Wavelength**




**Melanopic Lumens: NR**

**M/P: 0.13**





$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	0	NR	620	41	NR	750	0	NR	880	0	NR
365	0	NR	495	0	NR	625	19	NR	755	0	NR	885	0	NR
370	0	NR	500	0	NR	630	10	NR	760	0	NR	890	0	NR
375	0	NR	505	0	NR	635	6	NR	765	0	NR	895	0	NR
380	0	NR	510	0	NR	640	4	NR	770	0	NR	900	0	NR
385	0	NR	515	0	NR	645	3	NR	775	0	NR	905	0	NR
390	0	NR	520	1	NR	650	2	NR	780	0	NR	910	0	NR
395	0	NR	525	1	NR	655	2	NR	785	0	NR	915	0	NR
400	0	NR	530	1	NR	660	1	NR	790	0	NR	920	0	NR
405	0	NR	535	2	NR	665	1	NR	795	0	NR	925	0	NR
410	0	NR	540	3	NR	670	1	NR	800	0	NR	930	0	NR
415	0	NR	545	6	NR	675	1	NR	805	0	NR	935	0	NR
420	0	NR	550	10	NR	680	1	NR	810	0	NR	940	0	NR
425	0	NR	555	16	NR	685	0	NR	815	0	NR	945	0	NR
430	0	NR	560	28	NR	690	0	NR	820	0	NR	950	0	NR
435	0	NR	565	48	NR	695	0	NR	825	0	NR	955	0	NR
440	0	NR	570	84	NR	700	0	NR	830	0	NR	960	0	NR
445	0	NR	575	143	NR	705	0	NR	835	0	NR	965	0	NR
450	0	NR	580	243	NR	710	0	NR	840	0	NR	970	0	NR
455	0	NR	585	409	NR	715	0	NR	845	0	NR	975	0	NR
460	0	NR	590	686	NR	720	0	NR	850	0	NR	980	0	NR
465	0	NR	595	980	NR	725	0	NR	855	0	NR	985	0	NR
470	0	NR	600	854	NR	730	0	NR	860	0	NR	990	0	NR
475	0	NR	605	466	NR	735	0	NR	865	0	NR	995	0	NR
480	0	NR	610	216	NR	740	0	NR	870	0	NR	1000	0	NR
485	0	NR	615	90	NR	745	0	NR	875	0	NR			

**Summary**

$R_f = 1.4$   
 $R_g = 0.2$   
 $CIE R_a = -19.0$   
 $R_g = -376.7$




**Color Vector Graphics**






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



CES01 = 90	CES26 = 0	CES51 = 19	CES76 = 0
CES02 = 69	CES27 = 30	CES52 = 2	CES77 = 0
CES03 = 31	CES28 = 23	CES53 = 0	CES78 = 0
CES04 = 77	CES29 = 0	CES54 = 15	CES79 = 2
CES05 = 52	CES30 = 30	CES55 = 8	CES80 = 1
CES06 = 56	CES31 = 0	CES56 = 0	CES81 = 0
CES07 = 41	CES32 = 0	CES57 = 0	CES82 = 50
CES08 = 38	CES33 = 19	CES58 = 0	CES83 = 20
CES09 = 29	CES34 = 0	CES59 = 11	CES84 = 56
CES10 = 87	CES35 = 22	CES60 = 60	CES85 = 10
CES11 = 70	CES36 = 77	CES61 = 14	CES86 = 0
CES12 = 75	CES37 = 5	CES62 = 53	CES87 = 3
CES13 = 47	CES38 = 39	CES63 = 68	CES88 = 2
CES14 = 76	CES39 = 74	CES64 = 0	CES89 = 1
CES15 = 74	CES40 = 46	CES65 = 0	CES90 = 3
CES16 = 49	CES41 = 74	CES66 = 0	CES91 = 58
CES17 = 56	CES42 = 0	CES67 = 0	CES92 = 0
CES18 = 59	CES43 = 0	CES68 = 0	CES93 = 3
CES19 = 80	CES44 = 95	CES69 = 26	CES94 = 0
CES20 = 71	CES45 = 1	CES70 = 0	CES95 = 1
CES21 = 94	CES46 = 6	CES71 = 0	CES96 = 3
CES22 = 87	CES47 = 68	CES72 = 42	CES97 = 1
CES23 = 94	CES48 = 0	CES73 = 0	CES98 = 0
CES24 = 95	CES49 = 7	CES74 = 63	CES99 = 0
CES25 = 79	CES50 = 11	CES75 = 0	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)