

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1303000

Luminaire Tested: P3RT09R659024DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1303000
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-94)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3RT09R659024DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 817.0 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.84
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1303000
CATALOG NUMBER: P3RT09R659024DE010 E3CBUS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1303000
 CATALOG NUMBER: P3RT09R659024DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			89
3	104	98	93	90	102	96	92	89	94	90	87	92	89	86	89	87	85	83			83
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	78			78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74			74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	73	71	69			69
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			65
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62			62
9	79	69	64	60	77	69	64	60	68	63	60	67	63	60	66	62	60	58			58
10	75	66	61	57	74	66	60	57	65	60	57	64	60	57	63	59	56	55			55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	239433
5°	226150
10°	219390
15°	210330
20°	191023
25°	166171
30°	114980
35°	66789
40°	17662
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 0 cd/sqm



TEST NUMBER: P1303000

CATALOG NUMBER: P3RT09R659024DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.0	11.9
10°-20°	257.3	31.5
20°-30°	302.2	37.0
30°-40°	153.1	18.7
40°-50°	7.4	0.9
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	656.5	80.4
0°-40°	809.6	99.1
0°-60°	817.0	100.0
0°-90°	817.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	817.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1092	
5°	1027	97
15°	926	257
25°	687	302
35°	250	153
45°	0	7
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1303000
CATALOG NUMBER: P3RT09R659024DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1091.9
2.5°	1068.0
5°	1027.4
7.5°	1002.2
10°	985.3
12.5°	962.9
15°	926.5
17.5°	874.6
20°	818.6
22.5°	761.1
25°	686.8
27.5°	570.5
30°	454.1
32.5°	353.2
35°	249.5
37.5°	145.8
40°	61.7
42.5°	9.8
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)