

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1445796

Luminaire Tested: P3ART13R709030DE010 E3CLSWW1MMS

Issue Date: 5/8/2026

Test Information

Test Method: LM-79-2019
Report Number: P1445796
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-15)
Test Lab: INNOVATION CENTER
Issue Date: 5/8/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3ART13R709030DE010 E3CLSWW1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3CLSWW1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 495.0 lumens
Efficiency: N/A
Efficacy: 33.9 lumens/watt
Spacing Criteria (0/90/45): 1.47 / 0.85 / 1.23
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1445796
CATALOG NUMBER: P3ART13R709030DE010 E3CLSWW1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1445796

CATALOG NUMBER: P3ART13R709030DE010 E3CLSWW1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89	89	89
2	103	96	91	86	101	95	89	85	91	87	83	88	85	81	85	82	80	78	78	78
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68	68	68
4	88	78	70	65	86	77	70	64	74	68	63	72	67	63	70	66	62	60	60	60
5	82	71	63	57	80	70	62	57	68	61	56	66	60	56	64	59	55	53	53	53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47	47	47
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	43	43	43
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	39	39	39
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35	35	35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32	32	32

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	54491	54491	54491	54491	54491
5°	67070	62426	53159	46665	44200
10°	81896	70339	50010	38766	35648
15°	99433	77140	45585	32191	28695
20°	111380	81907	40627	26206	23265
25°	118555	82892	36002	21751	18340
30°	121588	80341	31650	18484	15648
35°	117624	77791	27813	15794	13518
40°	107716	73137	24503	14055	12051
45°	95359	60968	21770	13056	10885
50°	79042	52194	19172	11974	10064
55°	59563	43468	17701	11278	9137
60°	46794	32629	16007	10482	8026
65°	34971	24023	13854	8717	6538
70°	22504	15323	9873	6283	3590
75°	9489	8303	4745	2372	1186
80°	1768	1768	0	0	0
85°	0	0	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 95359 cd/sqm



TEST NUMBER: P1445796

CATALOG NUMBER: P3ART13R709030DE010 E3CLSWW1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.6	4.8
10°-20°	67.8	13.7
20°-30°	99.2	20.0
30°-40°	108.1	21.8
40°-50°	93.5	18.9
50°-60°	62.7	12.7
60°-70°	32.4	6.5
70°-80°	7.6	1.5
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	190.6	38.5
0°-40°	298.7	60.3
0°-60°	454.9	91.9
0°-90°	495.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	495.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	248	248	248	248	248	
5°	305	284	242	212	201	31
15°	438	340	201	142	126	124
25°	490	343	149	90	76	225
35°	439	291	104	59	50	272
45°	308	197	70	42	35	235
55°	156	114	46	30	24	144
65°	67	46	27	17	13	68
75°	11	10	6	3	1	15
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P1445796

CATALOG NUMBER: P3ART13R709030DE010 E3CLSWW1MMS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	248.5	248.5	248.5	248.5	248.5	248.5	248.5	248.5	248.5	248.5	248.5
2.5°	276.6	275.2	275.2	272.4	269.6	266.8	262.5	258.3	254.1	249.9	247.1
5°	304.7	306.1	304.7	299.0	292.0	283.6	275.2	265.3	255.5	247.1	241.5
7.5°	336.9	336.9	332.7	325.7	315.9	301.8	287.8	271.0	255.5	241.5	234.5
10°	367.8	367.8	360.8	349.6	334.1	315.9	296.2	273.8	252.7	233.1	224.6
12.5°	405.7	404.3	395.9	377.7	355.2	328.5	301.8	273.8	248.5	224.6	213.4
15°	438.0	436.6	425.4	402.9	373.5	339.8	303.3	271.0	240.1	213.4	200.8
17.5°	461.9	459.1	446.5	422.6	388.9	346.8	304.7	265.3	230.2	200.8	188.1
20°	477.3	475.9	461.9	433.8	397.3	351.0	303.3	258.3	220.4	188.1	174.1
22.5°	487.2	484.4	470.3	439.4	397.3	349.6	297.6	248.5	207.8	175.5	161.5
25°	490.0	488.6	471.7	438.0	393.1	342.6	289.2	238.7	195.1	162.9	148.8
26°	490.0	488.6	471.7	436.6	390.3	338.4	285.0	234.5	190.9	157.2	144.6
27.5°	488.6	487.2	468.9	432.4	384.7	331.3	276.6	226.0	182.5	150.2	136.2
30°	480.2	477.3	459.1	422.6	372.0	317.3	262.5	213.4	169.9	137.6	125.0
32.5°	461.9	459.1	439.4	405.7	358.0	301.8	247.1	199.4	157.2	125.0	113.7
35°	439.4	436.6	417.0	384.7	338.4	290.6	230.2	183.9	143.2	115.1	103.9
37.5°	411.4	407.1	390.3	356.6	314.5	278.0	216.2	168.5	130.6	103.9	94.1
40°	376.3	374.9	359.4	328.5	286.4	255.5	207.8	168.5	119.3	94.1	85.6
42.5°	342.6	339.8	325.7	299.0	261.1	223.2	182.5	161.5	110.9	84.2	77.2
45°	307.5	304.7	292.0	269.6	234.5	196.6	168.5	139.0	95.5	77.2	70.2
47.5°	269.6	266.8	256.9	240.1	209.2	175.5	143.2	113.7	87.0	68.8	63.2
50°	231.7	233.1	224.6	207.8	183.9	153.0	123.5	95.5	74.4	61.8	56.2
52.5°	193.7	192.3	186.7	175.5	158.6	132.0	105.3	81.4	64.6	54.8	51.9
55°	155.8	157.2	154.4	147.4	133.4	113.7	88.4	70.2	57.6	49.1	46.3
57.5°	129.2	130.6	125.0	120.7	109.5	92.7	73.0	59.0	49.1	43.5	40.7
60°	106.7	108.1	103.9	98.3	89.9	74.4	59.0	49.1	43.5	39.3	36.5
62.5°	87.0	85.6	82.8	77.2	70.2	59.0	47.7	40.7	36.5	33.7	32.3
65°	67.4	67.4	64.6	60.4	54.8	46.3	37.9	33.7	30.9	28.1	26.7
67.5°	50.5	50.5	47.7	44.9	39.3	33.7	29.5	26.7	25.3	22.5	21.1
70°	35.1	35.1	33.7	32.3	28.1	23.9	22.5	19.7	18.3	16.8	15.4
72.5°	22.5	22.5	22.5	19.7	18.3	15.4	15.4	14.0	12.6	11.2	11.2
75°	11.2	12.6	11.2	11.2	9.8	9.8	8.4	8.4	7.0	7.0	5.6
77.5°	4.2	4.2	4.2	4.2	4.2	4.2	2.8	2.8	2.8	2.8	2.8
80°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1445796

CATALOG NUMBER: P3ART13R709030DE010 E3CLSWW1MMS

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	248.5	248.5	248.5	248.5	248.5	248.5	248.5	248.5	248.5	248.5
2.5°	244.3	240.1	237.3	233.1	230.2	227.4	226.0	224.6	224.6	224.6
5°	237.3	230.2	223.2	216.2	212.0	207.8	203.6	202.2	200.8	200.8
7.5°	228.8	217.6	207.8	199.4	192.3	188.1	183.9	181.1	179.7	179.7
10°	217.6	203.6	192.3	181.1	174.1	168.5	165.7	161.5	161.5	160.1
12.5°	205.0	188.1	175.5	165.7	158.6	151.6	147.4	144.6	143.2	143.2
15°	190.9	174.1	160.1	148.8	141.8	134.8	130.6	127.8	126.4	126.4
17.5°	176.9	158.6	144.6	133.4	126.4	119.3	115.1	112.3	112.3	110.9
20°	162.9	144.6	130.6	119.3	112.3	106.7	102.5	99.7	98.3	99.7
22.5°	150.2	132.0	117.9	108.1	99.7	94.1	89.9	88.4	87.0	87.0
25°	136.2	119.3	106.7	96.9	89.9	84.2	80.0	78.6	77.2	75.8
26°	132.0	115.1	102.5	92.7	85.6	80.0	77.2	74.4	73.0	73.0
27.5°	126.4	108.1	96.9	87.0	80.0	75.8	71.6	70.2	68.8	68.8
30°	113.7	98.3	87.0	78.6	73.0	67.4	64.6	63.2	61.8	61.8
32.5°	103.9	88.4	78.6	71.6	66.0	61.8	59.0	56.2	56.2	56.2
35°	94.1	80.0	71.6	64.6	59.0	54.8	53.4	51.9	50.5	50.5
37.5°	85.6	73.0	64.6	59.0	54.8	50.5	47.7	46.3	46.3	46.3
40°	77.2	67.4	59.0	53.4	49.1	46.3	43.5	42.1	42.1	42.1
42.5°	70.2	60.4	54.8	49.1	44.9	42.1	40.7	39.3	37.9	37.9
45°	64.6	56.2	49.1	44.9	42.1	39.3	36.5	35.1	35.1	35.1
47.5°	57.6	51.9	44.9	40.7	37.9	35.1	33.7	32.3	32.3	32.3
50°	53.4	47.7	42.1	37.9	35.1	32.3	30.9	29.5	29.5	29.5
52.5°	47.7	43.5	39.3	35.1	32.3	29.5	28.1	26.7	26.7	26.7
55°	43.5	39.3	35.1	32.3	29.5	26.7	25.3	23.9	23.9	23.9
57.5°	39.3	35.1	32.3	29.5	26.7	25.3	22.5	22.5	21.1	21.1
60°	35.1	30.9	28.1	26.7	23.9	22.5	19.7	18.3	18.3	18.3
62.5°	29.5	28.1	25.3	22.5	19.7	18.3	16.8	15.4	15.4	15.4
65°	25.3	23.9	21.1	18.3	16.8	15.4	14.0	12.6	12.6	12.6
67.5°	21.1	18.3	16.8	15.4	14.0	12.6	11.2	9.8	8.4	9.8
70°	15.4	14.0	12.6	11.2	9.8	8.4	7.0	7.0	5.6	5.6
72.5°	9.8	8.4	8.4	7.0	5.6	5.6	4.2	4.2	2.8	2.8
75°	5.6	5.6	4.2	4.2	2.8	2.8	1.4	1.4	1.4	1.4
77.5°	2.8	1.4	1.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)