

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1303315

Luminaire Tested: P3RT05R259030DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1303315
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-87)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3RT05R259030DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 687.0 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.39
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1303315
CATALOG NUMBER: P3RT05R259030DE010 E3CBUS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1303315
 CATALOG NUMBER: P3RT05R259030DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95	95	95
3	109	105	101	99	107	103	100	98	101	99	97	99	97	95	97	95	94	92	92	92
4	106	101	98	95	105	100	97	94	98	95	93	96	94	92	95	93	91	90	90	90
5	103	98	94	92	102	97	94	91	96	93	90	94	92	90	93	91	89	88	88	88
6	101	95	91	89	100	95	91	88	93	90	88	92	89	87	91	89	87	86	86	86
7	98	93	89	86	97	92	89	86	91	88	86	90	87	85	89	87	85	84	84	84
8	96	90	87	84	95	90	86	84	89	86	84	88	85	83	87	85	83	82	82	82
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	86	83	81	80	80	80
10	92	86	83	80	91	86	82	80	85	82	80	84	82	80	84	81	80	79	79	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	792524
5°	734117
10°	552784
15°	256891
20°	80834
25°	31260
30°	9065
35°	2918
40°	945
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 0 cd/sqm



TEST NUMBER: P1303315
 CATALOG NUMBER: P3RT05R259030DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	291.4	42.4
10°-20°	321.2	46.7
20°-30°	66.0	9.6
30°-40°	8.0	1.2
40°-50°	0.5	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	678.5	98.8
0°-40°	686.5	99.9
0°-60°	687.0	100.0
0°-90°	687.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	687.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3614	
5°	3335	291
15°	1132	321
25°	129	66
35°	11	8
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1303315
CATALOG NUMBER: P3RT05R259030DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3614.2
2.5°	3544.7
5°	3335.1
7.5°	2984.3
10°	2482.6
12.5°	1828.8
15°	1131.6
17.5°	615.8
20°	346.4
22.5°	211.8
25°	129.2
27.5°	72.8
30°	35.8
32.5°	16.3
35°	10.9
37.5°	6.5
40°	3.3
42.5°	1.1
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)