

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675960

Luminaire Tested: **CCW-SA-2B-727-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P675960
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2B-727-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @450mA w/
SLR distribution lens
Light Source: (32) 2700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4793.1 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 46
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 6.8 fc

Type IV - Short - N/A

REPORT NUMBER: P675960
CATALOG NUMBER: CCW-SA-2B-727-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	986.2	0.0	986.2
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3806.9	0.0	3806.9
	% Fixture	79.4	0.0	79.4
Total	Lumens	4793.1	0.0	4793.1
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.9	2.5
10°-20°	251.1	5.2
20°-30°	367.4	7.7
30°-40°	517.6	10.8
40°-50°	711.2	14.8
50°-60°	969.4	20.2
60°-70°	1061.0	22.1
70°-80°	612.7	12.8
80°-90°	183.7	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4793.1	100.0
0°-180°	4793.1	100.0

Coefficient of Utilization



REPORT NUMBER: P675960


CATALOG NUMBER: CCW-SA-2B-727-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	492.3	10.3			
FM	(30°-60°)	1749.1	36.5			
FH	(60°-80°)	1409.4	29.4			G1/1800
FVH	(80°-90°)	156.0	3.3			G2/225
BL	(0°-30°)	245.2	5.1	B1/500		
BM	(30°-60°)	449.1	9.4	B1/1000		
BH	(60°-80°)	264.3	5.5	B1/500		G1/500
BVH	(80°-90°)	27.7	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6
2.5°	1579.5	1571.0	1564.6	1558.2	1549.7	1543.4	1534.9	1526.4	1515.7	1507.2	1496.6
5°	1488.1	1462.6	1437.1	1422.2	1405.2	1390.3	1373.3	1354.2	1335.0	1313.8	1294.6
7.5°	1388.2	1356.3	1324.4	1298.9	1271.3	1245.7	1218.1	1194.7	1171.3	1148.0	1124.6
10°	1294.6	1264.9	1235.1	1203.2	1169.2	1137.3	1103.3	1071.4	1039.5	1007.6	975.8
12.5°	1233.0	1196.8	1162.8	1126.7	1092.7	1056.5	1020.4	990.6	960.9	929.0	899.2
15°	1205.4	1171.3	1139.5	1103.3	1067.2	1031.0	994.9	960.9	929.0	895.0	861.0
17.5°	1271.3	1222.4	1173.5	1126.7	1079.9	1033.2	986.4	943.9	901.4	858.8	816.3
20°	1356.3	1294.6	1235.1	1177.7	1118.2	1060.8	1001.3	941.7	882.2	822.7	763.2
22.5°	1464.7	1394.6	1326.5	1252.1	1175.6	1101.2	1024.7	950.3	875.8	799.3	724.9
25°	1658.2	1575.2	1492.3	1386.0	1277.6	1171.3	1062.9	965.1	869.5	771.7	673.9
27.5°	1824.0	1711.3	1600.8	1473.2	1345.7	1218.1	1090.6	977.9	867.3	754.7	642.0
30°	1921.8	1811.2	1700.7	1545.5	1392.4	1237.2	1082.1	956.6	833.3	707.9	582.5
32.5°	2011.0	1887.7	1764.4	1594.4	1422.2	1252.1	1079.9	941.7	805.7	667.5	529.3
35°	2134.3	1998.3	1864.4	1666.7	1469.0	1271.3	1073.6	931.1	786.6	644.1	499.6
37.5°	2266.1	2098.2	1932.4	1713.4	1494.5	1275.5	1056.5	916.2	775.9	635.6	495.3
40°	2410.7	2206.6	2004.7	1762.3	1522.1	1279.8	1037.4	897.1	756.8	614.4	474.1
42.5°	2504.2	2283.2	2062.1	1800.6	1541.2	1279.8	1018.3	880.1	741.9	601.6	463.4
45°	2557.4	2342.7	2130.1	1847.4	1564.6	1281.9	999.1	863.1	727.0	588.9	452.8
47.5°	2580.8	2380.9	2181.1	1883.5	1588.0	1290.4	992.8	854.6	714.3	576.1	435.8
50°	2642.4	2466.0	2289.5	1970.7	1653.9	1335.0	1016.2	867.3	720.7	571.9	423.0
52.5°	2678.6	2527.6	2376.7	2049.3	1721.9	1394.6	1067.2	901.4	735.5	569.7	403.9
55°	2810.4	2665.8	2521.2	2172.6	1821.8	1473.2	1122.4	939.6	756.8	571.9	389.0
57.5°	2978.3	2825.2	2674.3	2298.0	1921.8	1545.5	1169.2	973.6	775.9	580.4	382.7
60°	3095.2	2946.4	2799.7	2400.1	1998.3	1598.6	1196.8	992.8	788.7	582.5	378.4
62.5°	3108.0	2916.7	2727.5	2338.4	1949.4	1558.2	1169.2	971.5	773.8	574.0	376.3
65°	3027.2	2804.0	2580.8	2208.8	1836.7	1464.7	1092.7	912.0	731.3	548.5	367.8
67.5°	2865.6	2604.2	2342.7	2002.5	1662.4	1322.3	982.1	827.0	673.9	518.7	363.5
70°	2489.4	2259.8	2032.3	1736.8	1443.4	1148.0	852.5	724.9	599.5	471.9	344.4
72.5°	2089.7	1875.0	1662.4	1422.2	1184.1	943.9	703.7	608.0	512.3	414.5	318.9
75°	1600.8	1439.2	1279.8	1101.2	922.6	741.9	563.3	493.2	423.0	352.9	282.7
77.5°	1124.6	1037.4	952.4	818.4	684.5	550.6	416.7	369.9	323.1	276.4	229.6
80°	763.2	714.3	667.5	571.9	476.2	378.4	282.7	253.0	221.1	191.3	159.4
82.5°	474.1	471.9	467.7	401.8	335.9	270.0	204.1	178.6	155.2	129.7	104.2
85°	216.8	253.0	287.0	250.8	214.7	178.6	142.4	125.4	108.4	89.3	72.3
87.5°	68.0	82.9	95.7	91.4	85.0	80.8	74.4	63.8	53.1	42.5	31.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960
 CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6
2.5°	1488.1	1481.7	1473.2	1464.7	1454.1	1445.6	1434.9	1424.3	1422.2	1417.9	1415.8
5°	1281.9	1269.1	1254.2	1241.5	1228.7	1213.9	1201.1	1186.2	1175.6	1162.8	1152.2
7.5°	1101.2	1079.9	1056.5	1033.2	1011.9	990.6	967.3	946.0	935.4	924.7	914.1
10°	956.6	935.4	916.2	895.0	880.1	867.3	852.5	837.6	824.8	812.1	799.3
12.5°	884.4	869.5	854.6	839.7	822.7	807.8	790.8	773.8	758.9	746.2	731.3
15°	839.7	818.4	795.1	773.8	750.4	729.2	705.8	682.4	665.4	650.5	633.5
17.5°	786.6	754.7	724.9	693.0	667.5	642.0	614.4	588.9	569.7	548.5	529.3
20°	727.0	690.9	652.6	616.5	586.7	559.1	529.3	499.6	478.3	454.9	433.7
22.5°	676.0	629.2	580.4	531.5	499.6	467.7	433.7	401.8	382.7	361.4	342.3
25°	620.7	569.7	516.6	463.4	431.5	397.5	365.6	331.6	316.8	304.0	289.1
27.5°	591.0	540.0	486.8	435.8	406.0	374.1	344.4	312.5	301.9	289.1	278.5
30°	531.5	482.6	431.5	380.5	359.3	340.1	318.9	297.6	293.4	291.2	287.0
32.5°	478.3	427.3	376.3	325.3	306.1	287.0	267.9	248.7	246.6	242.3	240.2
35°	450.7	401.8	350.8	301.9	284.9	265.7	248.7	229.6	225.3	219.0	214.7
37.5°	444.3	393.3	340.1	289.1	272.1	255.1	236.0	219.0	214.7	210.5	206.2
40°	427.3	378.4	331.6	282.7	265.7	248.7	229.6	212.6	208.3	204.1	199.8
42.5°	414.5	367.8	318.9	270.0	255.1	240.2	223.2	208.3	204.1	199.8	193.5
45°	403.9	355.0	304.0	255.1	244.5	233.8	221.1	210.5	206.2	199.8	195.6
47.5°	386.9	340.1	291.2	242.3	231.7	223.2	212.6	202.0	197.7	193.5	189.2
50°	374.1	325.3	276.4	227.5	219.0	210.5	202.0	193.5	193.5	195.6	195.6
52.5°	357.1	310.4	263.6	216.8	208.3	199.8	191.3	182.8	184.9	187.1	189.2
55°	342.3	297.6	250.8	204.1	195.6	187.1	176.4	167.9	170.1	172.2	174.3
57.5°	335.9	289.1	242.3	195.6	187.1	176.4	167.9	157.3	157.3	157.3	157.3
60°	331.6	282.7	236.0	187.1	176.4	167.9	157.3	146.7	144.6	144.6	142.4
62.5°	329.5	280.6	233.8	184.9	172.2	161.6	148.8	136.1	133.9	131.8	129.7
65°	321.0	276.4	229.6	182.8	167.9	155.2	140.3	125.4	123.3	123.3	121.2
67.5°	318.9	272.1	227.5	180.7	165.8	148.8	133.9	116.9	114.8	112.7	110.5
70°	301.9	261.5	219.0	176.4	159.4	144.6	127.6	110.5	108.4	104.2	102.0
72.5°	280.6	244.5	206.2	167.9	150.9	133.9	116.9	99.9	97.8	95.7	91.4
75°	248.7	214.7	180.7	146.7	131.8	119.0	104.2	89.3	87.2	85.0	80.8
77.5°	204.1	176.4	150.9	123.3	112.7	102.0	91.4	80.8	78.7	76.5	72.3
80°	144.6	127.6	112.7	95.7	89.3	80.8	74.4	65.9	65.9	63.8	63.8
82.5°	95.7	87.2	78.7	70.2	65.9	61.6	57.4	53.1	53.1	51.0	51.0
85°	68.0	63.8	57.4	53.1	51.0	46.8	44.6	40.4	40.4	40.4	40.4
87.5°	31.9	31.9	29.8	29.8	27.6	27.6	25.5	23.4	23.4	23.4	23.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6
2.5°	1411.6	1405.2	1398.8	1390.3	1383.9	1375.4	1364.8	1356.3	1345.7	1345.7	1343.5
5°	1139.5	1133.1	1126.7	1118.2	1111.8	1103.3	1096.9	1088.4	1079.9	1079.9	1077.8
7.5°	903.5	890.7	878.0	863.1	850.3	841.8	833.3	822.7	814.2	807.8	801.4
10°	786.6	773.8	758.9	746.2	731.3	720.7	710.0	697.3	686.6	678.1	669.6
12.5°	716.4	701.5	686.6	671.8	656.9	642.0	629.2	614.4	599.5	588.9	578.2
15°	616.5	601.6	586.7	571.9	557.0	540.0	523.0	503.8	486.8	478.3	471.9
17.5°	508.1	493.2	476.2	461.3	444.3	431.5	418.8	406.0	393.3	384.8	378.4
20°	410.3	393.3	376.3	359.3	342.3	333.8	325.3	316.8	308.2	301.9	297.6
22.5°	321.0	310.4	301.9	291.2	280.6	274.2	270.0	263.6	257.2	257.2	257.2
25°	274.2	267.9	263.6	257.2	250.8	248.7	246.6	242.3	240.2	238.1	238.1
27.5°	265.7	259.4	253.0	246.6	240.2	238.1	236.0	231.7	229.6	229.6	229.6
30°	282.7	280.6	278.5	276.4	274.2	270.0	263.6	259.4	253.0	248.7	244.5
32.5°	236.0	233.8	233.8	231.7	229.6	233.8	236.0	240.2	242.3	244.5	246.6
35°	208.3	204.1	199.8	195.6	191.3	189.2	187.1	184.9	182.8	182.8	180.7
37.5°	202.0	197.7	193.5	189.2	184.9	182.8	180.7	178.6	176.4	176.4	174.3
40°	195.6	191.3	189.2	184.9	180.7	178.6	176.4	172.2	170.1	167.9	167.9
42.5°	189.2	187.1	182.8	180.7	176.4	174.3	172.2	167.9	165.8	163.7	161.6
45°	189.2	184.9	180.7	176.4	172.2	170.1	165.8	163.7	159.4	159.4	157.3
47.5°	184.9	180.7	176.4	172.2	167.9	165.8	161.6	159.4	155.2	153.1	150.9
50°	195.6	189.2	180.7	174.3	165.8	163.7	159.4	157.3	153.1	150.9	148.8
52.5°	191.3	184.9	176.4	170.1	161.6	157.3	155.2	150.9	146.7	144.6	142.4
55°	176.4	170.1	165.8	159.4	153.1	148.8	144.6	140.3	136.1	133.9	133.9
57.5°	157.3	155.2	153.1	150.9	148.8	144.6	140.3	133.9	129.7	127.6	125.4
60°	140.3	142.4	144.6	146.7	148.8	142.4	136.1	129.7	123.3	121.2	119.0
62.5°	127.6	131.8	136.1	138.2	142.4	136.1	129.7	123.3	116.9	114.8	112.7
65°	119.0	121.2	121.2	123.3	123.3	119.0	116.9	112.7	108.4	106.3	106.3
67.5°	108.4	108.4	108.4	106.3	106.3	104.2	104.2	102.0	99.9	97.8	97.8
70°	97.8	97.8	97.8	95.7	95.7	93.5	93.5	91.4	89.3	89.3	87.2
72.5°	89.3	89.3	87.2	87.2	85.0	85.0	85.0	82.9	82.9	80.8	80.8
75°	78.7	78.7	76.5	76.5	74.4	74.4	74.4	72.3	72.3	72.3	70.2
77.5°	70.2	70.2	68.0	68.0	65.9	65.9	65.9	63.8	63.8	61.6	61.6
80°	61.6	61.6	59.5	59.5	57.4	57.4	55.3	55.3	53.1	53.1	51.0
82.5°	48.9	48.9	48.9	48.9	48.9	46.8	46.8	44.6	42.5	42.5	40.4
85°	40.4	40.4	40.4	38.3	38.3	38.3	36.1	36.1	34.0	31.9	31.9
87.5°	23.4	23.4	23.4	21.3	21.3	21.3	21.3	21.3	21.3	21.3	19.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960
 CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6
2.5°	1343.5	1341.4	1332.9	1324.4	1332.9	1341.4	1341.4	1341.4	1339.3	1339.3	1339.3
5°	1077.8	1075.7	1071.4	1067.2	1067.2	1065.0	1069.3	1073.6	1077.8	1082.1	1086.3
7.5°	792.9	786.6	780.2	773.8	778.1	780.2	786.6	790.8	797.2	801.4	812.1
10°	661.1	652.6	646.3	639.9	635.6	631.4	627.1	625.0	620.7	616.5	620.7
12.5°	565.5	554.8	544.2	531.5	529.3	527.2	523.0	518.7	514.5	510.2	508.1
15°	463.4	454.9	450.7	444.3	435.8	427.3	423.0	420.9	416.7	412.4	410.3
17.5°	369.9	361.4	355.0	348.6	346.5	342.3	342.3	342.3	342.3	342.3	342.3
20°	291.2	284.9	284.9	282.7	282.7	280.6	282.7	284.9	284.9	287.0	289.1
22.5°	255.1	255.1	253.0	250.8	253.0	253.0	255.1	257.2	259.4	261.5	263.6
25°	236.0	233.8	236.0	238.1	238.1	238.1	240.2	240.2	242.3	242.3	242.3
27.5°	227.5	227.5	229.6	229.6	231.7	231.7	231.7	229.6	229.6	227.5	227.5
30°	240.2	236.0	236.0	236.0	233.8	231.7	229.6	229.6	227.5	225.3	223.2
32.5°	248.7	250.8	248.7	244.5	242.3	238.1	236.0	231.7	229.6	225.3	221.1
35°	180.7	178.6	182.8	184.9	187.1	189.2	191.3	193.5	193.5	195.6	195.6
37.5°	174.3	172.2	172.2	170.1	170.1	170.1	170.1	170.1	167.9	167.9	170.1
40°	165.8	163.7	163.7	161.6	161.6	159.4	159.4	159.4	159.4	159.4	159.4
42.5°	159.4	157.3	157.3	157.3	157.3	155.2	155.2	153.1	153.1	150.9	150.9
45°	157.3	155.2	153.1	150.9	150.9	148.8	148.8	148.8	146.7	146.7	146.7
47.5°	148.8	146.7	146.7	144.6	144.6	142.4	142.4	142.4	140.3	140.3	140.3
50°	144.6	142.4	142.4	140.3	140.3	138.2	138.2	138.2	136.1	136.1	136.1
52.5°	138.2	136.1	136.1	136.1	133.9	131.8	131.8	131.8	129.7	129.7	129.7
55°	131.8	129.7	129.7	129.7	127.6	125.4	125.4	125.4	123.3	123.3	123.3
57.5°	123.3	121.2	121.2	119.0	119.0	119.0	119.0	119.0	116.9	116.9	116.9
60°	116.9	114.8	114.8	112.7	112.7	110.5	110.5	110.5	110.5	110.5	110.5
62.5°	110.5	108.4	106.3	104.2	106.3	106.3	106.3	106.3	104.2	104.2	104.2
65°	104.2	102.0	99.9	97.8	97.8	97.8	97.8	97.8	97.8	97.8	97.8
67.5°	95.7	93.5	91.4	89.3	91.4	91.4	91.4	91.4	91.4	91.4	91.4
70°	87.2	85.0	85.0	82.9	82.9	80.8	80.8	82.9	82.9	82.9	82.9
72.5°	78.7	76.5	76.5	74.4	74.4	74.4	74.4	74.4	74.4	74.4	74.4
75°	70.2	68.0	68.0	65.9	65.9	65.9	65.9	65.9	65.9	65.9	65.9
77.5°	59.5	57.4	57.4	57.4	57.4	57.4	57.4	59.5	59.5	59.5	59.5
80°	51.0	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9
82.5°	40.4	38.3	38.3	38.3	38.3	38.3	38.3	38.3	38.3	38.3	38.3
85°	29.8	27.6	27.6	27.6	29.8	29.8	29.8	29.8	29.8	29.8	29.8
87.5°	19.1	17.0	17.0	17.0	19.1	19.1	19.1	19.1	17.0	17.0	17.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960
 CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6
2.5°	1339.3	1339.3	1339.3	1337.2	1335.0	1332.9	1330.8	1337.2	1341.4	1347.8	1352.0
5°	1088.4	1092.7	1094.8	1101.2	1107.6	1113.9	1120.3	1124.6	1128.8	1130.9	1135.2
7.5°	820.6	831.2	839.7	848.2	856.7	863.1	871.6	878.0	884.4	890.7	897.1
10°	622.9	627.1	629.2	637.8	644.1	652.6	659.0	665.4	671.8	676.0	682.4
12.5°	506.0	501.7	499.6	499.6	499.6	499.6	499.6	503.8	508.1	512.3	516.6
15°	408.2	406.0	403.9	401.8	399.7	395.4	393.3	397.5	401.8	406.0	410.3
17.5°	342.3	342.3	342.3	340.1	338.0	335.9	333.8	335.9	338.0	338.0	340.1
20°	293.4	295.5	297.6	299.7	299.7	301.9	301.9	304.0	306.1	306.1	308.2
22.5°	263.6	265.7	265.7	265.7	267.9	267.9	267.9	270.0	272.1	274.2	276.4
25°	240.2	240.2	238.1	238.1	240.2	240.2	240.2	240.2	242.3	242.3	242.3
27.5°	227.5	225.3	225.3	225.3	225.3	223.2	223.2	223.2	223.2	223.2	223.2
30°	221.1	219.0	216.8	214.7	214.7	212.6	210.5	210.5	210.5	210.5	210.5
32.5°	219.0	214.7	210.5	208.3	208.3	206.2	204.1	202.0	202.0	199.8	197.7
35°	195.6	193.5	193.5	191.3	189.2	187.1	184.9	184.9	184.9	182.8	182.8
37.5°	170.1	172.2	172.2	172.2	174.3	174.3	174.3	174.3	176.4	176.4	176.4
40°	159.4	159.4	159.4	161.6	163.7	163.7	165.8	165.8	167.9	167.9	167.9
42.5°	150.9	148.8	148.8	150.9	150.9	153.1	153.1	155.2	157.3	157.3	159.4
45°	146.7	144.6	144.6	144.6	144.6	142.4	142.4	144.6	146.7	148.8	150.9
47.5°	138.2	138.2	136.1	136.1	136.1	136.1	136.1	136.1	138.2	138.2	138.2
50°	133.9	133.9	131.8	131.8	131.8	131.8	131.8	131.8	131.8	131.8	131.8
52.5°	129.7	127.6	127.6	127.6	127.6	125.4	125.4	125.4	125.4	125.4	125.4
55°	123.3	121.2	121.2	121.2	121.2	121.2	121.2	121.2	123.3	123.3	123.3
57.5°	116.9	114.8	114.8	114.8	116.9	116.9	116.9	116.9	119.0	119.0	119.0
60°	110.5	110.5	110.5	110.5	110.5	110.5	110.5	112.7	112.7	114.8	114.8
62.5°	104.2	104.2	104.2	104.2	106.3	106.3	106.3	106.3	108.4	108.4	108.4
65°	97.8	97.8	97.8	97.8	99.9	99.9	99.9	99.9	99.9	99.9	99.9
67.5°	91.4	91.4	91.4	91.4	91.4	91.4	91.4	93.5	93.5	95.7	95.7
70°	82.9	80.8	80.8	82.9	82.9	85.0	85.0	87.2	87.2	89.3	89.3
72.5°	74.4	74.4	74.4	74.4	74.4	74.4	74.4	76.5	78.7	78.7	80.8
75°	65.9	65.9	65.9	65.9	68.0	68.0	68.0	70.2	70.2	72.3	72.3
77.5°	59.5	57.4	57.4	57.4	59.5	59.5	59.5	61.6	61.6	63.8	63.8
80°	48.9	48.9	48.9	48.9	51.0	51.0	51.0	51.0	53.1	53.1	53.1
82.5°	40.4	40.4	40.4	40.4	40.4	40.4	40.4	40.4	42.5	42.5	42.5
85°	29.8	29.8	29.8	29.8	31.9	31.9	31.9	31.9	31.9	31.9	31.9
87.5°	19.1	19.1	19.1	19.1	19.1	19.1	19.1	19.1	21.3	21.3	21.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960
 CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6
2.5°	1352.0	1352.0	1352.0	1352.0	1356.3	1358.4	1362.7	1364.8	1362.7	1360.5	1356.3
5°	1137.3	1139.5	1139.5	1141.6	1141.6	1141.6	1141.6	1141.6	1145.8	1150.1	1154.3
7.5°	899.2	901.4	903.5	905.6	905.6	905.6	903.5	903.5	905.6	905.6	907.7
10°	688.8	697.3	703.7	710.0	705.8	699.4	695.2	688.8	688.8	688.8	686.6
12.5°	520.8	523.0	527.2	529.3	527.2	527.2	525.1	523.0	525.1	529.3	531.5
15°	412.4	412.4	414.5	414.5	416.7	418.8	418.8	420.9	425.2	427.3	431.5
17.5°	342.3	344.4	344.4	346.5	346.5	348.6	348.6	348.6	352.9	357.1	363.5
20°	308.2	308.2	308.2	308.2	308.2	306.1	306.1	304.0	306.1	310.4	312.5
22.5°	276.4	278.5	278.5	278.5	276.4	274.2	270.0	267.9	267.9	270.0	270.0
25°	242.3	240.2	240.2	238.1	238.1	240.2	240.2	240.2	242.3	242.3	244.5
27.5°	223.2	221.1	221.1	219.0	219.0	221.1	221.1	221.1	221.1	221.1	221.1
30°	208.3	208.3	206.2	204.1	206.2	206.2	208.3	208.3	210.5	210.5	212.6
32.5°	197.7	195.6	195.6	193.5	195.6	195.6	197.7	197.7	199.8	202.0	202.0
35°	182.8	182.8	182.8	182.8	182.8	182.8	180.7	180.7	180.7	180.7	180.7
37.5°	174.3	174.3	172.2	170.1	170.1	170.1	170.1	170.1	167.9	165.8	163.7
40°	167.9	165.8	165.8	163.7	161.6	161.6	159.4	157.3	157.3	155.2	155.2
42.5°	159.4	157.3	157.3	155.2	153.1	153.1	150.9	148.8	148.8	148.8	146.7
45°	148.8	148.8	146.7	144.6	144.6	144.6	142.4	142.4	142.4	142.4	140.3
47.5°	138.2	138.2	136.1	136.1	136.1	136.1	133.9	133.9	133.9	133.9	133.9
50°	131.8	131.8	131.8	131.8	131.8	131.8	129.7	129.7	129.7	129.7	129.7
52.5°	125.4	125.4	125.4	125.4	125.4	125.4	125.4	125.4	125.4	125.4	125.4
55°	123.3	123.3	123.3	123.3	123.3	123.3	121.2	121.2	121.2	123.3	123.3
57.5°	119.0	119.0	116.9	116.9	116.9	116.9	116.9	116.9	116.9	116.9	116.9
60°	114.8	114.8	114.8	114.8	114.8	114.8	114.8	114.8	114.8	114.8	114.8
62.5°	108.4	108.4	108.4	108.4	108.4	110.5	110.5	110.5	110.5	110.5	108.4
65°	99.9	102.0	102.0	102.0	102.0	102.0	102.0	102.0	102.0	102.0	102.0
67.5°	95.7	95.7	95.7	95.7	95.7	95.7	95.7	95.7	95.7	95.7	95.7
70°	89.3	89.3	87.2	87.2	87.2	89.3	89.3	89.3	89.3	89.3	89.3
72.5°	80.8	80.8	80.8	80.8	80.8	80.8	80.8	80.8	80.8	82.9	82.9
75°	72.3	72.3	72.3	72.3	72.3	72.3	72.3	72.3	72.3	72.3	72.3
77.5°	63.8	63.8	61.6	61.6	61.6	63.8	63.8	63.8	63.8	65.9	65.9
80°	53.1	53.1	53.1	53.1	53.1	53.1	53.1	53.1	53.1	55.3	55.3
82.5°	42.5	42.5	42.5	42.5	42.5	42.5	42.5	42.5	42.5	44.6	44.6
85°	31.9	34.0	34.0	34.0	34.0	34.0	34.0	34.0	34.0	36.1	36.1
87.5°	21.3	21.3	21.3	21.3	21.3	21.3	19.1	19.1	19.1	19.1	17.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960
 CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6
2.5°	1354.2	1356.3	1358.4	1358.4	1360.5	1362.7	1362.7	1371.2	1379.7	1383.9	1388.2
5°	1158.6	1156.5	1156.5	1154.3	1152.2	1158.6	1165.0	1177.7	1190.5	1192.6	1196.8
7.5°	907.7	909.9	912.0	912.0	914.1	907.7	899.2	901.4	903.5	914.1	922.6
10°	686.6	688.8	690.9	690.9	693.0	690.9	686.6	693.0	699.4	707.9	718.5
12.5°	533.6	540.0	546.3	550.6	557.0	561.2	563.3	571.9	578.2	588.9	599.5
15°	435.8	440.0	444.3	448.6	452.8	457.1	461.3	469.8	478.3	491.1	503.8
17.5°	367.8	367.8	369.9	369.9	369.9	374.1	378.4	382.7	384.8	397.5	410.3
20°	314.6	312.5	310.4	308.2	306.1	310.4	312.5	314.6	316.8	325.3	331.6
22.5°	270.0	270.0	272.1	272.1	272.1	270.0	265.7	267.9	267.9	272.1	278.5
25°	244.5	244.5	244.5	242.3	242.3	244.5	246.6	246.6	244.5	246.6	248.7
27.5°	221.1	223.2	223.2	225.3	225.3	227.5	227.5	227.5	227.5	229.6	231.7
30°	212.6	212.6	214.7	214.7	214.7	216.8	219.0	219.0	219.0	221.1	225.3
32.5°	204.1	206.2	208.3	210.5	212.6	214.7	214.7	216.8	216.8	219.0	221.1
35°	180.7	178.6	178.6	176.4	174.3	174.3	174.3	174.3	172.2	174.3	174.3
37.5°	161.6	161.6	161.6	159.4	159.4	161.6	161.6	161.6	161.6	163.7	163.7
40°	153.1	153.1	153.1	153.1	153.1	153.1	153.1	155.2	155.2	157.3	159.4
42.5°	146.7	146.7	146.7	146.7	146.7	148.8	148.8	148.8	148.8	150.9	150.9
45°	140.3	140.3	140.3	140.3	140.3	140.3	140.3	142.4	142.4	144.6	146.7
47.5°	133.9	133.9	133.9	133.9	133.9	136.1	138.2	138.2	138.2	140.3	140.3
50°	129.7	129.7	129.7	129.7	129.7	131.8	131.8	133.9	133.9	136.1	138.2
52.5°	125.4	125.4	125.4	125.4	125.4	127.6	127.6	129.7	129.7	131.8	133.9
55°	123.3	123.3	123.3	121.2	121.2	123.3	123.3	125.4	125.4	127.6	127.6
57.5°	116.9	116.9	116.9	116.9	116.9	116.9	116.9	119.0	119.0	121.2	123.3
60°	114.8	114.8	112.7	112.7	110.5	112.7	112.7	114.8	114.8	116.9	116.9
62.5°	108.4	108.4	108.4	106.3	106.3	108.4	108.4	108.4	108.4	110.5	112.7
65°	102.0	102.0	102.0	99.9	99.9	102.0	102.0	102.0	102.0	104.2	106.3
67.5°	95.7	95.7	95.7	93.5	93.5	93.5	93.5	95.7	95.7	97.8	99.9
70°	89.3	89.3	89.3	87.2	87.2	87.2	85.0	87.2	89.3	91.4	91.4
72.5°	82.9	82.9	82.9	80.8	80.8	80.8	78.7	80.8	80.8	82.9	82.9
75°	72.3	72.3	72.3	72.3	72.3	72.3	70.2	70.2	70.2	72.3	72.3
77.5°	65.9	65.9	65.9	63.8	63.8	63.8	61.6	61.6	61.6	63.8	63.8
80°	55.3	55.3	55.3	53.1	53.1	53.1	51.0	51.0	51.0	53.1	53.1
82.5°	44.6	44.6	44.6	42.5	42.5	42.5	40.4	40.4	40.4	42.5	42.5
85°	36.1	36.1	36.1	36.1	36.1	36.1	34.0	34.0	34.0	36.1	38.3
87.5°	17.0	17.0	19.1	19.1	19.1	19.1	17.0	17.0	14.9	14.9	17.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960
 CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6
2.5°	1392.4	1396.7	1407.3	1415.8	1426.4	1434.9	1441.3	1449.8	1456.2	1462.6	1466.8
5°	1199.0	1201.1	1211.7	1222.4	1230.9	1241.5	1256.4	1271.3	1286.1	1301.0	1311.6
7.5°	933.2	941.7	954.5	969.4	982.1	994.9	1009.8	1026.8	1041.7	1056.5	1071.4
10°	727.0	735.5	748.3	761.1	771.7	784.4	801.4	818.4	835.5	852.5	869.5
12.5°	610.1	620.7	635.6	650.5	663.3	678.1	699.4	718.5	739.8	758.9	780.2
15°	514.5	527.2	546.3	567.6	586.7	605.9	627.1	648.4	667.5	688.8	710.0
17.5°	423.0	435.8	452.8	471.9	488.9	506.0	531.5	554.8	580.4	603.7	627.1
20°	340.1	346.5	363.5	380.5	397.5	414.5	433.7	452.8	471.9	491.1	520.8
22.5°	282.7	287.0	295.5	301.9	310.4	316.8	335.9	355.0	372.0	391.2	418.8
25°	248.7	250.8	257.2	261.5	267.9	272.1	284.9	295.5	308.2	318.9	344.4
27.5°	231.7	233.8	236.0	238.1	240.2	242.3	250.8	259.4	265.7	274.2	297.6
30°	227.5	229.6	236.0	240.2	246.6	250.8	255.1	259.4	263.6	267.9	282.7
32.5°	223.2	225.3	225.3	223.2	223.2	221.1	225.3	227.5	231.7	233.8	246.6
35°	176.4	176.4	178.6	180.7	182.8	184.9	191.3	195.6	202.0	206.2	216.8
37.5°	165.8	165.8	167.9	172.2	174.3	176.4	180.7	184.9	189.2	193.5	204.1
40°	159.4	161.6	163.7	165.8	167.9	170.1	174.3	176.4	180.7	182.8	191.3
42.5°	153.1	153.1	155.2	159.4	161.6	163.7	167.9	170.1	174.3	176.4	184.9
45°	148.8	150.9	153.1	155.2	155.2	157.3	161.6	165.8	167.9	172.2	180.7
47.5°	142.4	142.4	146.7	148.8	153.1	155.2	159.4	161.6	165.8	167.9	176.4
50°	138.2	140.3	144.6	146.7	150.9	153.1	159.4	163.7	170.1	174.3	178.6
52.5°	133.9	136.1	140.3	142.4	146.7	148.8	157.3	165.8	172.2	180.7	180.7
55°	129.7	129.7	133.9	140.3	144.6	148.8	153.1	159.4	163.7	167.9	167.9
57.5°	123.3	125.4	129.7	136.1	140.3	144.6	148.8	153.1	155.2	159.4	157.3
60°	119.0	119.0	125.4	131.8	138.2	144.6	144.6	144.6	142.4	142.4	142.4
62.5°	112.7	114.8	123.3	133.9	142.4	150.9	144.6	138.2	131.8	125.4	127.6
65°	108.4	110.5	114.8	121.2	125.4	129.7	125.4	123.3	119.0	114.8	116.9
67.5°	99.9	102.0	104.2	104.2	106.3	106.3	106.3	106.3	106.3	106.3	108.4
70°	93.5	93.5	93.5	95.7	95.7	95.7	95.7	95.7	95.7	95.7	97.8
72.5°	85.0	85.0	85.0	85.0	85.0	85.0	85.0	85.0	85.0	85.0	87.2
75°	74.4	74.4	74.4	74.4	74.4	74.4	74.4	74.4	74.4	74.4	76.5
77.5°	65.9	65.9	65.9	65.9	65.9	65.9	65.9	65.9	63.8	63.8	65.9
80°	55.3	55.3	55.3	55.3	53.1	53.1	53.1	53.1	53.1	53.1	55.3
82.5°	44.6	44.6	44.6	44.6	42.5	42.5	42.5	42.5	40.4	40.4	42.5
85°	40.4	42.5	42.5	44.6	44.6	44.6	42.5	40.4	38.3	36.1	36.1
87.5°	17.0	17.0	17.0	17.0	14.9	14.9	14.9	14.9	14.9	14.9	14.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960
 CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6
2.5°	1473.2	1477.5	1481.7	1488.1	1496.6	1503.0	1509.3	1522.1	1537.0	1549.7	1562.5
5°	1322.3	1332.9	1343.5	1356.3	1369.0	1379.7	1392.4	1417.9	1443.4	1466.8	1492.3
7.5°	1084.2	1099.1	1111.8	1133.1	1152.2	1173.5	1192.6	1224.5	1254.2	1286.1	1315.9
10°	886.5	903.5	920.5	948.1	977.9	1005.5	1033.2	1058.7	1086.3	1111.8	1137.3
12.5°	801.4	820.6	841.8	858.8	878.0	895.0	912.0	941.7	971.5	1001.3	1031.0
15°	731.3	752.5	773.8	795.1	814.2	835.5	854.6	880.1	907.7	933.2	958.8
17.5°	650.5	671.8	695.2	718.5	741.9	765.3	788.7	824.8	861.0	895.0	931.1
20°	548.5	578.2	605.9	637.8	669.6	701.5	733.4	771.7	809.9	846.1	884.4
22.5°	446.4	474.1	501.7	540.0	578.2	614.4	652.6	703.7	752.5	803.6	852.5
25°	372.0	397.5	423.0	465.6	506.0	548.5	588.9	650.5	710.0	771.7	831.2
27.5°	321.0	344.4	367.8	412.4	457.1	499.6	544.2	612.2	678.1	746.2	812.1
30°	297.6	312.5	327.4	369.9	412.4	452.8	495.3	561.2	627.1	693.0	758.9
32.5°	259.4	272.1	284.9	323.1	361.4	397.5	435.8	503.8	569.7	637.8	703.7
35°	229.6	240.2	250.8	287.0	321.0	357.1	391.2	459.2	527.2	595.2	663.3
37.5°	212.6	223.2	231.7	263.6	297.6	329.5	361.4	429.4	495.3	563.3	629.2
40°	199.8	206.2	214.7	246.6	276.4	308.2	338.0	399.7	463.4	525.1	586.7
42.5°	191.3	199.8	206.2	233.8	263.6	291.2	318.9	378.4	437.9	495.3	554.8
45°	189.2	197.7	206.2	229.6	253.0	274.2	297.6	355.0	412.4	469.8	527.2
47.5°	184.9	191.3	199.8	219.0	236.0	255.1	272.1	329.5	386.9	442.2	499.6
50°	182.8	184.9	189.2	206.2	223.2	240.2	257.2	314.6	372.0	429.4	486.8
52.5°	180.7	180.7	180.7	195.6	210.5	223.2	238.1	295.5	355.0	412.4	469.8
55°	167.9	165.8	165.8	180.7	193.5	208.3	221.1	278.5	335.9	391.2	448.6
57.5°	155.2	153.1	150.9	163.7	176.4	189.2	202.0	259.4	318.9	376.3	433.7
60°	142.4	140.3	140.3	153.1	163.7	176.4	187.1	246.6	304.0	363.5	420.9
62.5°	127.6	129.7	129.7	140.3	153.1	163.7	174.3	233.8	295.5	355.0	414.5
65°	116.9	119.0	119.0	131.8	144.6	157.3	170.1	227.5	287.0	344.4	401.8
67.5°	108.4	110.5	110.5	125.4	138.2	153.1	165.8	216.8	270.0	321.0	372.0
70°	99.9	99.9	102.0	116.9	131.8	146.7	161.6	206.2	250.8	293.4	338.0
72.5°	89.3	91.4	93.5	108.4	121.2	136.1	148.8	189.2	229.6	270.0	310.4
75°	78.7	80.8	82.9	95.7	108.4	121.2	133.9	172.2	208.3	246.6	282.7
77.5°	70.2	72.3	74.4	85.0	95.7	106.3	116.9	144.6	174.3	202.0	229.6
80°	57.4	57.4	59.5	68.0	76.5	82.9	91.4	110.5	129.7	146.7	165.8
82.5°	42.5	44.6	44.6	51.0	55.3	61.6	65.9	76.5	85.0	95.7	104.2
85°	36.1	34.0	34.0	38.3	40.4	44.6	46.8	53.1	57.4	63.8	68.0
87.5°	14.9	12.8	12.8	14.9	19.1	21.3	23.4	23.4	25.5	25.5	25.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960
 CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6
2.5°	1568.9	1573.1	1579.5	1583.8	1594.4	1602.9	1613.5	1622.0	1628.4	1639.0	1634.8
5°	1511.5	1530.6	1549.7	1568.9	1583.8	1598.6	1611.4	1626.3	1643.3	1675.2	1683.7
7.5°	1341.4	1366.9	1390.3	1415.8	1445.6	1475.3	1505.1	1534.9	1562.5	1602.9	1628.4
10°	1173.5	1209.6	1243.6	1279.8	1307.4	1335.0	1360.5	1388.2	1426.4	1466.8	1513.6
12.5°	1067.2	1103.3	1139.5	1175.6	1216.0	1254.2	1294.6	1332.9	1369.0	1400.9	1454.1
15°	997.0	1037.4	1075.7	1113.9	1162.8	1209.6	1258.5	1305.3	1358.4	1400.9	1437.1
17.5°	980.0	1028.9	1075.7	1124.6	1175.6	1226.6	1277.6	1328.7	1381.8	1445.6	1492.3
20°	950.3	1016.2	1082.1	1148.0	1213.9	1277.6	1343.5	1407.3	1477.5	1554.0	1575.2
22.5°	933.2	1011.9	1092.7	1171.3	1260.6	1352.0	1441.3	1530.6	1605.0	1662.4	1726.2
25°	931.1	1028.9	1128.8	1226.6	1339.3	1449.8	1562.5	1673.0	1768.7	1826.1	1877.1
27.5°	929.0	1048.0	1165.0	1281.9	1420.1	1556.1	1694.3	1830.4	1919.6	2002.5	2045.1
30°	903.5	1045.9	1190.5	1332.9	1488.1	1643.3	1798.5	1953.6	2045.1	2102.5	2123.7
32.5°	871.6	1039.5	1207.5	1375.4	1551.9	1728.3	1902.6	2079.1	2151.4	2200.2	2183.2
35°	846.1	1031.0	1213.9	1396.7	1583.8	1773.0	1960.0	2147.1	2251.3	2319.3	2291.7
37.5°	822.7	1016.2	1209.6	1403.1	1622.0	1841.0	2059.9	2278.9	2378.8	2451.1	2419.2
40°	795.1	1001.3	1209.6	1415.8	1666.7	1915.4	2166.2	2415.0	2544.6	2606.3	2557.4
42.5°	771.7	986.4	1203.2	1417.9	1685.8	1953.6	2221.5	2489.4	2633.9	2721.1	2659.4
45°	741.9	956.6	1169.2	1383.9	1679.4	1974.9	2268.3	2563.8	2731.7	2799.7	2714.7
47.5°	710.0	922.6	1133.1	1343.5	1658.2	1972.8	2287.4	2602.0	2757.2	2838.0	2759.3
50°	699.4	912.0	1122.4	1335.0	1675.2	2017.4	2357.6	2697.7	2810.4	2876.3	2772.1
52.5°	697.3	922.6	1150.1	1375.4	1717.7	2057.8	2400.1	2740.2	2831.6	2901.8	2808.2
55°	690.9	935.4	1177.7	1420.1	1777.2	2136.5	2493.6	2850.8	2942.2	2993.2	2923.0
57.5°	697.3	960.9	1222.4	1486.0	1853.7	2221.5	2589.3	2957.0	3067.6	3103.7	3088.8
60°	701.5	982.1	1260.6	1541.2	1900.5	2259.8	2619.0	2978.3	3093.1	3182.4	3199.4
62.5°	690.9	967.3	1241.5	1517.9	1843.1	2168.4	2493.6	2818.9	3008.1	3139.9	3216.4
65°	659.0	914.1	1171.3	1426.4	1726.2	2028.1	2327.8	2627.5	2827.4	3022.9	3084.6
67.5°	588.9	805.7	1022.5	1239.4	1500.8	1762.3	2021.7	2283.2	2534.0	2723.2	2808.2
70°	510.2	680.3	852.5	1022.5	1260.6	1498.7	1736.8	1974.9	2196.0	2404.3	2485.1
72.5°	444.3	576.1	710.0	841.8	1011.9	1179.8	1349.9	1517.9	1779.3	1987.7	2066.3
75°	378.4	474.1	567.6	663.3	780.2	897.1	1011.9	1128.8	1313.8	1500.8	1579.5
77.5°	291.2	355.0	416.7	478.3	559.1	637.8	718.5	797.2	926.9	1067.2	1107.6
80°	202.0	238.1	272.1	308.2	372.0	435.8	499.6	563.3	648.4	727.0	788.7
82.5°	125.4	148.8	170.1	191.3	242.3	293.4	342.3	393.3	427.3	431.5	493.2
85°	80.8	95.7	108.4	121.2	150.9	182.8	212.6	242.3	216.8	202.0	240.2
87.5°	31.9	40.4	46.8	53.1	51.0	48.9	46.8	44.6	38.3	34.0	42.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960
 CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6
2.5°	1639.0	1645.4	1651.8	1656.0	1662.4	1664.5	1666.7	1666.7	1668.8	1670.9	1675.2
5°	1717.7	1730.4	1743.2	1753.8	1766.6	1777.2	1785.7	1796.3	1804.8	1804.8	1802.7
7.5°	1651.8	1683.7	1715.6	1747.4	1779.3	1802.7	1824.0	1847.4	1868.6	1872.9	1877.1
10°	1564.6	1598.6	1630.5	1664.5	1696.4	1732.6	1766.6	1800.6	1836.7	1843.1	1851.6
12.5°	1483.8	1524.2	1564.6	1602.9	1643.3	1668.8	1694.3	1717.7	1743.2	1760.2	1777.2
15°	1481.7	1515.7	1549.7	1581.6	1615.6	1630.5	1645.4	1658.2	1673.0	1673.0	1675.2
17.5°	1530.6	1551.9	1573.1	1592.3	1613.5	1615.6	1619.9	1622.0	1624.1	1617.8	1611.4
20°	1626.3	1634.8	1643.3	1651.8	1660.3	1645.4	1632.6	1617.8	1602.9	1585.9	1571.0
22.5°	1766.6	1747.4	1728.3	1709.2	1690.0	1664.5	1636.9	1611.4	1583.8	1562.5	1541.2
25°	1898.4	1875.0	1851.6	1828.2	1804.8	1749.6	1694.3	1636.9	1581.6	1558.2	1534.9
27.5°	2074.8	2038.7	2002.5	1966.4	1930.3	1855.9	1781.5	1707.1	1632.6	1592.3	1554.0
30°	2117.3	2076.9	2036.6	1994.0	1953.6	1881.4	1811.2	1738.9	1666.7	1619.9	1575.2
32.5°	2179.0	2132.2	2085.5	2038.7	1991.9	1921.8	1851.6	1779.3	1709.2	1666.7	1622.0
35°	2281.0	2227.9	2174.7	2119.5	2066.3	1994.0	1923.9	1851.6	1779.3	1730.4	1683.7
37.5°	2368.2	2306.5	2244.9	2183.2	2121.6	2057.8	1991.9	1928.1	1862.2	1813.3	1766.6
40°	2466.0	2398.0	2329.9	2264.0	2196.0	2136.5	2076.9	2015.3	1955.8	1917.5	1879.2
42.5°	2551.0	2468.1	2387.3	2306.5	2223.6	2183.2	2145.0	2104.6	2064.2	2045.1	2023.8
45°	2610.5	2534.0	2455.3	2378.8	2302.3	2272.5	2242.8	2213.0	2183.2	2202.4	2221.5
47.5°	2636.0	2574.4	2514.9	2455.3	2393.7	2404.3	2415.0	2423.5	2434.1	2459.6	2487.2
50°	2659.4	2625.4	2589.3	2555.3	2519.1	2559.5	2597.8	2638.2	2678.6	2731.7	2784.9
52.5°	2706.2	2687.1	2670.1	2650.9	2631.8	2701.9	2772.1	2842.3	2912.4	2971.9	3031.5
55°	2846.5	2831.6	2816.7	2799.7	2784.9	2884.8	2982.6	3082.5	3182.4	3244.0	3305.7
57.5°	3040.0	3031.5	3020.8	3012.3	3001.7	3099.5	3195.1	3290.8	3388.6	3448.1	3509.8
60°	3186.6	3188.8	3188.8	3190.9	3190.9	3265.3	3339.7	3416.2	3490.6	3541.7	3594.8
62.5°	3265.3	3261.0	3256.8	3252.5	3248.3	3309.9	3371.6	3433.2	3494.9	3533.2	3571.4
65°	3180.3	3203.6	3227.0	3250.4	3273.8	3282.3	3288.7	3297.2	3303.6	3326.9	3350.3
67.5°	2895.4	2942.2	2986.8	3033.6	3078.2	3046.3	3016.6	2984.7	2952.8	2959.2	2963.4
70°	2578.6	2631.8	2687.1	2740.2	2793.4	2719.0	2644.5	2568.0	2493.6	2468.1	2442.6
72.5°	2174.7	2221.5	2270.4	2317.2	2363.9	2272.5	2183.2	2091.8	2000.4	1955.8	1911.1
75°	1662.4	1717.7	1775.1	1830.4	1885.6	1783.6	1679.4	1577.4	1473.2	1443.4	1415.8
77.5°	1211.7	1277.6	1343.5	1409.4	1475.3	1383.9	1292.5	1199.0	1107.6	1090.6	1073.6
80°	882.2	933.2	982.1	1033.2	1082.1	1028.9	975.8	922.6	869.5	867.3	865.2
82.5°	595.2	639.9	682.4	727.0	769.6	748.3	729.2	707.9	686.6	707.9	731.3
85°	306.1	367.8	431.5	493.2	554.8	548.5	544.2	537.8	531.5	559.1	584.6
87.5°	61.6	114.8	167.9	219.0	272.1	259.4	246.6	231.7	219.0	227.5	233.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960
 CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6
2.5°	1677.3	1679.4	1679.4	1679.4	1679.4	1679.4	1675.2	1673.0	1668.8	1664.5	1658.2
5°	1802.7	1800.6	1792.1	1783.6	1773.0	1764.4	1758.1	1749.6	1743.2	1734.7	1721.9
7.5°	1881.4	1885.6	1870.7	1858.0	1843.1	1828.2	1813.3	1798.5	1783.6	1768.7	1738.9
10°	1858.0	1864.4	1855.9	1847.4	1836.7	1828.2	1811.2	1792.1	1775.1	1755.9	1719.8
12.5°	1792.1	1809.1	1804.8	1800.6	1796.3	1792.1	1781.5	1768.7	1758.1	1745.3	1704.9
15°	1675.2	1675.2	1677.3	1679.4	1679.4	1681.5	1683.7	1685.8	1687.9	1690.0	1666.7
17.5°	1605.0	1598.6	1598.6	1598.6	1598.6	1598.6	1607.1	1617.8	1626.3	1634.8	1628.4
20°	1554.0	1539.1	1537.0	1537.0	1534.9	1532.7	1547.6	1564.6	1579.5	1594.4	1602.9
22.5°	1520.0	1498.7	1496.6	1494.5	1492.3	1490.2	1509.3	1528.5	1547.6	1566.7	1596.5
25°	1511.5	1488.1	1490.2	1492.3	1492.3	1494.5	1509.3	1524.2	1539.1	1554.0	1605.0
27.5°	1513.6	1475.3	1477.5	1479.6	1479.6	1481.7	1505.1	1526.4	1549.7	1571.0	1634.8
30°	1528.5	1483.8	1479.6	1475.3	1471.1	1466.8	1498.7	1530.6	1562.5	1594.4	1643.3
32.5°	1579.5	1537.0	1526.4	1515.7	1505.1	1494.5	1532.7	1568.9	1607.1	1643.3	1683.7
35°	1634.8	1588.0	1583.8	1579.5	1573.1	1568.9	1602.9	1639.0	1673.0	1707.1	1743.2
37.5°	1717.7	1670.9	1666.7	1660.3	1656.0	1649.7	1687.9	1724.1	1762.3	1798.5	1830.4
40°	1841.0	1802.7	1800.6	1800.6	1798.5	1796.3	1826.1	1858.0	1887.7	1917.5	1938.8
42.5°	2004.7	1985.5	1991.9	2000.4	2006.8	2013.2	2036.6	2062.1	2085.5	2108.8	2102.5
45°	2240.6	2259.8	2261.9	2264.0	2266.1	2268.3	2274.7	2283.2	2289.5	2295.9	2270.4
47.5°	2512.7	2538.3	2551.0	2563.8	2574.4	2587.2	2578.6	2568.0	2559.5	2548.9	2485.1
50°	2835.9	2889.0	2886.9	2884.8	2880.5	2878.4	2861.4	2844.4	2825.2	2808.2	2714.7
52.5°	3091.0	3150.5	3161.1	3171.8	3182.4	3193.0	3161.1	3129.2	3095.2	3063.3	2946.4
55°	3365.2	3426.9	3429.0	3431.1	3431.1	3433.2	3388.6	3344.0	3297.2	3252.5	3131.4
57.5°	3569.3	3628.8	3622.4	3618.2	3611.8	3605.4	3552.3	3499.1	3446.0	3392.8	3271.7
60°	3645.8	3696.8	3684.1	3671.3	3656.4	3643.7	3603.3	3562.9	3520.4	3480.0	3363.1
62.5°	3609.7	3647.9	3628.8	3611.8	3592.7	3573.5	3522.5	3469.4	3418.4	3365.2	3280.2
65°	3371.6	3395.0	3369.5	3346.1	3322.7	3297.2	3254.7	3212.1	3167.5	3125.0	3067.6
67.5°	2969.8	2974.1	2971.9	2969.8	2967.7	2965.6	2903.9	2842.3	2778.5	2716.8	2712.6
70°	2419.2	2393.7	2398.0	2404.3	2408.6	2412.8	2366.1	2321.4	2274.7	2227.9	2249.1
72.5°	1866.5	1821.8	1832.5	1845.2	1855.9	1866.5	1828.2	1792.1	1753.8	1715.6	1745.3
75°	1386.0	1358.4	1369.0	1381.8	1392.4	1403.1	1388.2	1373.3	1356.3	1341.4	1369.0
77.5°	1056.5	1039.5	1041.7	1041.7	1043.8	1043.8	1045.9	1050.2	1052.3	1054.4	1084.2
80°	861.0	858.8	856.7	854.6	850.3	848.2	869.5	890.7	912.0	933.2	948.1
82.5°	752.5	773.8	761.1	750.4	737.7	724.9	744.0	763.2	782.3	801.4	795.1
85°	612.2	637.8	614.4	591.0	565.5	542.1	559.1	574.0	591.0	605.9	597.4
87.5°	242.3	248.7	210.5	174.3	136.1	97.8	155.2	210.5	267.9	323.1	331.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960

CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6	1530.6
2.5°	1651.8	1643.3	1636.9	1634.8	1630.5	1628.4	1624.1	1619.9	1613.5	1609.3	1602.9
5°	1707.1	1694.3	1679.4	1658.2	1639.0	1617.8	1596.5	1577.4	1558.2	1537.0	1517.9
7.5°	1709.2	1679.4	1649.7	1622.0	1592.3	1564.6	1534.9	1509.3	1481.7	1454.1	1428.6
10°	1685.8	1649.7	1613.5	1577.4	1543.4	1507.2	1471.1	1441.3	1409.4	1377.5	1347.8
12.5°	1666.7	1626.3	1585.9	1543.4	1503.0	1460.5	1417.9	1388.2	1358.4	1328.7	1298.9
15°	1643.3	1617.8	1594.4	1556.1	1517.9	1479.6	1441.3	1400.9	1362.7	1322.3	1281.9
17.5°	1624.1	1617.8	1611.4	1585.9	1560.4	1532.7	1507.2	1466.8	1426.4	1383.9	1343.5
20°	1613.5	1622.0	1630.5	1617.8	1605.0	1590.1	1577.4	1547.6	1517.9	1486.0	1456.2
22.5°	1626.3	1658.2	1687.9	1690.0	1694.3	1696.4	1698.5	1670.9	1643.3	1613.5	1585.9
25°	1656.0	1707.1	1758.1	1785.7	1813.3	1843.1	1870.7	1853.7	1836.7	1819.7	1802.7
27.5°	1696.4	1760.2	1824.0	1864.4	1902.6	1943.0	1983.4	1981.3	1979.2	1974.9	1972.8
30°	1690.0	1738.9	1787.8	1836.7	1885.6	1934.5	1983.4	2008.9	2032.3	2057.8	2083.3
32.5°	1726.2	1766.6	1809.1	1860.1	1911.1	1964.3	2015.3	2068.4	2119.5	2172.6	2225.8
35°	1781.5	1817.6	1855.9	1911.1	1968.5	2023.8	2081.2	2145.0	2210.9	2276.8	2340.6
37.5°	1864.4	1896.3	1930.3	1977.0	2025.9	2072.7	2121.6	2215.1	2308.7	2404.3	2497.9
40°	1960.0	1981.3	2002.5	2047.2	2091.8	2136.5	2181.1	2298.0	2415.0	2531.9	2648.8
42.5°	2098.2	2091.8	2085.5	2121.6	2159.9	2196.0	2234.3	2340.6	2446.8	2553.1	2659.4
45°	2244.9	2219.4	2193.9	2210.9	2230.0	2247.0	2266.1	2374.6	2483.0	2593.5	2701.9
47.5°	2421.3	2357.6	2293.8	2278.9	2264.0	2247.0	2232.1	2349.1	2466.0	2585.0	2701.9
50°	2621.2	2525.5	2432.0	2393.7	2353.3	2315.0	2274.7	2370.3	2468.1	2565.9	2661.6
52.5°	2829.5	2710.4	2593.5	2534.0	2474.5	2412.8	2353.3	2434.1	2517.0	2599.9	2680.7
55°	3008.1	2886.9	2763.6	2693.4	2623.3	2553.1	2483.0	2563.8	2644.5	2725.3	2806.1
57.5°	3150.5	3029.3	2908.2	2842.3	2774.2	2708.3	2640.3	2716.8	2795.5	2874.1	2950.7
60°	3248.3	3131.4	3014.4	2950.7	2886.9	2823.1	2759.3	2850.8	2942.2	3035.7	3127.1
62.5°	3197.3	3112.2	3027.2	2999.6	2971.9	2942.2	2914.5	3001.7	3086.7	3173.9	3261.0
65°	3010.2	2952.8	2895.4	2923.0	2952.8	2980.4	3010.2	3067.6	3125.0	3184.5	3241.9
67.5°	2706.2	2701.9	2695.6	2757.2	2818.9	2882.6	2944.3	2982.6	3018.7	3057.0	3095.2
70°	2270.4	2293.8	2315.0	2421.3	2527.6	2633.9	2740.2	2755.1	2770.0	2784.9	2799.7
72.5°	1777.2	1807.0	1838.9	1979.2	2117.3	2257.6	2398.0	2389.4	2380.9	2370.3	2361.8
75°	1398.8	1426.4	1456.2	1585.9	1715.6	1845.2	1974.9	1938.8	1904.8	1868.6	1832.5
77.5°	1116.1	1145.8	1177.7	1298.9	1420.1	1543.4	1664.5	1577.4	1490.2	1403.1	1315.9
80°	960.9	975.8	988.5	1071.4	1152.2	1235.1	1318.0	1228.7	1137.3	1045.9	956.6
82.5°	788.7	780.2	773.8	822.7	871.6	920.5	969.4	884.4	799.3	712.2	627.1
85°	588.9	580.4	571.9	597.4	622.9	650.5	676.0	578.2	480.4	380.5	282.7
87.5°	342.3	350.8	359.3	386.9	414.5	444.3	471.9	372.0	272.1	170.1	70.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960
 CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675960
 CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1530.6	1530.6
2.5°	1590.1	1579.5
5°	1503.0	1488.1
7.5°	1407.3	1388.2
10°	1320.1	1294.6
12.5°	1264.9	1233.0
15°	1243.6	1205.4
17.5°	1307.4	1271.3
20°	1405.2	1356.3
22.5°	1524.2	1464.7
25°	1730.4	1658.2
27.5°	1898.4	1824.0
30°	2002.5	1921.8
32.5°	2117.3	2011.0
35°	2236.4	2134.3
37.5°	2380.9	2266.1
40°	2529.8	2410.7
42.5°	2580.8	2504.2
45°	2629.7	2557.4
47.5°	2640.3	2580.8
50°	2650.9	2642.4
52.5°	2680.7	2678.6
55°	2808.2	2810.4
57.5°	2965.6	2978.3
60°	3110.1	3095.2
62.5°	3184.5	3108.0
65°	3133.5	3027.2
67.5°	2980.4	2865.6
70°	2644.5	2489.4
72.5°	2225.8	2089.7
75°	1715.6	1600.8
77.5°	1220.2	1124.6
80°	858.8	763.2
82.5°	550.6	474.1
85°	248.7	216.8
87.5°	70.2	68.0
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P675960
CATALOG NUMBER: CCW-SA-2B-727-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)