

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675970

Luminaire Tested: **CCW-SA-2A-730-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P675970
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2A-730-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @350mA w/
SLR distribution lens
Light Source: (32) 3000K CCT, 70 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4134.8 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 36.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 15 foot mounting height. Maximum calculated value = 5.9 fc
 Type IV - Short - N/A

REPORT NUMBER: P675970
CATALOG NUMBER: CCW-SA-2A-730-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	850.8	0.0	850.8
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	3284.0	0.0	3284.0
	% Fixture	79.4	0.0	79.4
Total	Lumens	4134.8	0.0	4134.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.6	2.5
10°-20°	216.6	5.2
20°-30°	316.9	7.7
30°-40°	446.5	10.8
40°-50°	613.5	14.8
50°-60°	836.3	20.2
60°-70°	915.3	22.1
70°-80°	528.6	12.8
80°-90°	158.4	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	4134.8	100.0
0°-180°	4134.8	100.0

Coefficient of Utilization



REPORT NUMBER: P675970


CATALOG NUMBER: CCW-SA-2A-730-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	424.7	10.3			
FM	(30°-60°)	1508.9	36.5			
FH	(60°-80°)	1215.9	29.4			G1/1800
FVH	(80°-90°)	134.6	3.3			G2/225
BL	(0°-30°)	211.5	5.1	B1/500		
BM	(30°-60°)	387.4	9.4	B1/1000		
BH	(60°-80°)	228.0	5.5	B1/500		G1/500
BVH	(80°-90°)	23.9	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4
2.5°	1362.6	1355.2	1349.7	1344.2	1336.9	1331.4	1324.1	1316.7	1307.6	1300.2	1291.1
5°	1283.7	1261.7	1239.7	1226.9	1212.2	1199.4	1184.7	1168.2	1151.7	1133.3	1116.8
7.5°	1197.5	1170.0	1142.5	1120.5	1096.7	1074.7	1050.8	1030.6	1010.5	990.3	970.1
10°	1116.8	1091.2	1065.5	1038.0	1008.6	981.1	951.8	924.3	896.8	869.3	841.8
12.5°	1063.7	1032.5	1003.1	972.0	942.6	911.4	880.3	854.6	828.9	801.4	775.7
15°	1039.8	1010.5	983.0	951.8	920.6	889.4	858.3	828.9	801.4	772.1	742.7
17.5°	1096.7	1054.5	1012.3	972.0	931.6	891.3	850.9	814.2	777.6	740.9	704.2
20°	1170.0	1116.8	1065.5	1016.0	964.6	915.1	863.8	812.4	761.1	709.7	658.4
22.5°	1263.6	1203.0	1144.3	1080.2	1014.1	950.0	883.9	819.8	755.6	689.5	625.4
25°	1430.4	1358.9	1287.4	1195.7	1102.2	1010.5	916.9	832.6	750.1	665.7	581.3
27.5°	1573.5	1476.3	1380.9	1270.9	1160.9	1050.8	940.8	843.6	748.2	651.0	553.8
30°	1657.8	1562.5	1467.1	1333.2	1201.2	1067.3	933.5	825.3	718.9	610.7	502.5
32.5°	1734.9	1628.5	1522.1	1375.4	1226.9	1080.2	931.6	812.4	695.0	575.8	456.6
35°	1841.2	1723.9	1608.3	1437.8	1267.2	1096.7	926.1	803.2	678.5	555.7	431.0
37.5°	1954.9	1810.1	1667.0	1478.1	1289.2	1100.3	911.4	790.4	669.4	548.3	427.3
40°	2079.6	1903.6	1729.4	1520.3	1313.1	1104.0	894.9	773.9	652.9	530.0	409.0
42.5°	2160.3	1969.6	1778.9	1553.3	1329.6	1104.0	878.4	759.2	640.0	519.0	399.8
45°	2206.2	2020.9	1837.6	1593.7	1349.7	1105.8	861.9	744.6	627.2	508.0	390.6
47.5°	2226.3	2054.0	1881.6	1624.8	1369.9	1113.2	856.4	737.2	616.2	497.0	375.9
50°	2279.5	2127.3	1975.1	1700.0	1426.8	1151.7	876.6	748.2	621.7	493.3	364.9
52.5°	2310.7	2180.5	2050.3	1767.9	1485.5	1203.0	920.6	777.6	634.5	491.5	348.4
55°	2424.4	2299.7	2175.0	1874.2	1571.6	1270.9	968.3	810.6	652.9	493.3	335.6
57.5°	2569.3	2437.2	2307.0	1982.4	1657.8	1333.2	1008.6	839.9	669.4	500.7	330.1
60°	2670.1	2541.8	2415.2	2070.5	1723.9	1379.1	1032.5	856.4	680.4	502.5	326.4
62.5°	2681.2	2516.1	2352.9	2017.3	1681.7	1344.2	1008.6	838.1	667.5	495.2	324.6
65°	2611.5	2418.9	2226.3	1905.4	1584.5	1263.6	942.6	786.7	630.9	473.1	317.3
67.5°	2472.1	2246.5	2020.9	1727.5	1434.1	1140.7	847.3	713.4	581.3	447.5	313.6
70°	2147.5	1949.4	1753.2	1498.3	1245.2	990.3	735.4	625.4	517.2	407.1	297.1
72.5°	1802.7	1617.5	1434.1	1226.9	1021.5	814.2	607.0	524.5	442.0	357.6	275.1
75°	1380.9	1241.5	1104.0	950.0	795.9	640.0	486.0	425.5	364.9	304.4	243.9
77.5°	970.1	894.9	821.6	706.0	590.5	475.0	359.4	319.1	278.8	238.4	198.1
80°	658.4	616.2	575.8	493.3	410.8	326.4	243.9	218.2	190.7	165.1	137.5
82.5°	409.0	407.1	403.5	346.6	289.8	232.9	176.1	154.0	133.9	111.9	89.9
85°	187.1	218.2	247.6	216.4	185.2	154.0	122.9	108.2	93.5	77.0	62.4
87.5°	58.7	71.5	82.5	78.9	73.4	69.7	64.2	55.0	45.8	36.7	27.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970
 CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4
2.5°	1283.7	1278.2	1270.9	1263.6	1254.4	1247.0	1237.9	1228.7	1226.9	1223.2	1221.4
5°	1105.8	1094.8	1082.0	1071.0	1060.0	1047.2	1036.1	1023.3	1014.1	1003.1	994.0
7.5°	950.0	931.6	911.4	891.3	872.9	854.6	834.4	816.1	806.9	797.7	788.6
10°	825.3	806.9	790.4	772.1	759.2	748.2	735.4	722.6	711.6	700.5	689.5
12.5°	762.9	750.1	737.2	724.4	709.7	696.9	682.2	667.5	654.7	643.7	630.9
15°	724.4	706.0	685.9	667.5	647.4	629.0	608.9	588.7	574.0	561.2	546.5
17.5°	678.5	651.0	625.4	597.8	575.8	553.8	530.0	508.0	491.5	473.1	456.6
20°	627.2	596.0	563.0	531.8	506.2	482.3	456.6	431.0	412.6	392.5	374.1
22.5°	583.2	542.8	500.7	458.5	431.0	403.5	374.1	346.6	330.1	311.8	295.3
25°	535.5	491.5	445.6	399.8	372.3	342.9	315.4	286.1	273.3	262.2	249.4
27.5°	509.8	465.8	420.0	375.9	350.3	322.8	297.1	269.6	260.4	249.4	240.2
30°	458.5	416.3	372.3	328.3	309.9	293.4	275.1	256.7	253.1	251.2	247.6
32.5°	412.6	368.6	324.6	280.6	264.1	247.6	231.1	214.6	212.7	209.1	207.2
35°	388.8	346.6	302.6	260.4	245.7	229.2	214.6	198.1	194.4	188.9	185.2
37.5°	383.3	339.3	293.4	249.4	234.7	220.1	203.6	188.9	185.2	181.6	177.9
40°	368.6	326.4	286.1	243.9	229.2	214.6	198.1	183.4	179.7	176.1	172.4
42.5°	357.6	317.3	275.1	232.9	220.1	207.2	192.6	179.7	176.1	172.4	166.9
45°	348.4	306.3	262.2	220.1	210.9	201.7	190.7	181.6	177.9	172.4	168.7
47.5°	333.8	293.4	251.2	209.1	199.9	192.6	183.4	174.2	170.6	166.9	163.2
50°	322.8	280.6	238.4	196.2	188.9	181.6	174.2	166.9	166.9	168.7	168.7
52.5°	308.1	267.7	227.4	187.1	179.7	172.4	165.1	157.7	159.5	161.4	163.2
55°	295.3	256.7	216.4	176.1	168.7	161.4	152.2	144.9	146.7	148.5	150.4
57.5°	289.8	249.4	209.1	168.7	161.4	152.2	144.9	135.7	135.7	135.7	135.7
60°	286.1	243.9	203.6	161.4	152.2	144.9	135.7	126.5	124.7	124.7	122.9
62.5°	284.3	242.1	201.7	159.5	148.5	139.4	128.4	117.4	115.5	113.7	111.9
65°	276.9	238.4	198.1	157.7	144.9	133.9	121.0	108.2	106.4	106.4	104.5
67.5°	275.1	234.7	196.2	155.9	143.0	128.4	115.5	100.9	99.0	97.2	95.4
70°	260.4	225.6	188.9	152.2	137.5	124.7	110.0	95.4	93.5	89.9	88.0
72.5°	242.1	210.9	177.9	144.9	130.2	115.5	100.9	86.2	84.4	82.5	78.9
75°	214.6	185.2	155.9	126.5	113.7	102.7	89.9	77.0	75.2	73.4	69.7
77.5°	176.1	152.2	130.2	106.4	97.2	88.0	78.9	69.7	67.9	66.0	62.4
80°	124.7	110.0	97.2	82.5	77.0	69.7	64.2	56.9	56.9	55.0	55.0
82.5°	82.5	75.2	67.9	60.5	56.9	53.2	49.5	45.8	45.8	44.0	44.0
85°	58.7	55.0	49.5	45.8	44.0	40.3	38.5	34.8	34.8	34.8	34.8
87.5°	27.5	27.5	25.7	25.7	23.8	23.8	22.0	20.2	20.2	20.2	20.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4
2.5°	1217.7	1212.2	1206.7	1199.4	1193.9	1186.5	1177.4	1170.0	1160.9	1160.9	1159.0
5°	983.0	977.5	972.0	964.6	959.1	951.8	946.3	939.0	931.6	931.6	929.8
7.5°	779.4	768.4	757.4	744.6	733.6	726.2	718.9	709.7	702.4	696.9	691.4
10°	678.5	667.5	654.7	643.7	630.9	621.7	612.5	601.5	592.3	585.0	577.7
12.5°	618.0	605.2	592.3	579.5	566.7	553.8	542.8	530.0	517.2	508.0	498.8
15°	531.8	519.0	506.2	493.3	480.5	465.8	451.1	434.6	420.0	412.6	407.1
17.5°	438.3	425.5	410.8	398.0	383.3	372.3	361.3	350.3	339.3	331.9	326.4
20°	353.9	339.3	324.6	309.9	295.3	287.9	280.6	273.3	265.9	260.4	256.7
22.5°	276.9	267.7	260.4	251.2	242.1	236.6	232.9	227.4	221.9	221.9	221.9
25°	236.6	231.1	227.4	221.9	216.4	214.6	212.7	209.1	207.2	205.4	205.4
27.5°	229.2	223.7	218.2	212.7	207.2	205.4	203.6	199.9	198.1	198.1	198.1
30°	243.9	242.1	240.2	238.4	236.6	232.9	227.4	223.7	218.2	214.6	210.9
32.5°	203.6	201.7	201.7	199.9	198.1	201.7	203.6	207.2	209.1	210.9	212.7
35°	179.7	176.1	172.4	168.7	165.1	163.2	161.4	159.5	157.7	157.7	155.9
37.5°	174.2	170.6	166.9	163.2	159.5	157.7	155.9	154.0	152.2	152.2	150.4
40°	168.7	165.1	163.2	159.5	155.9	154.0	152.2	148.5	146.7	144.9	144.9
42.5°	163.2	161.4	157.7	155.9	152.2	150.4	148.5	144.9	143.0	141.2	139.4
45°	163.2	159.5	155.9	152.2	148.5	146.7	143.0	141.2	137.5	137.5	135.7
47.5°	159.5	155.9	152.2	148.5	144.9	143.0	139.4	137.5	133.9	132.0	130.2
50°	168.7	163.2	155.9	150.4	143.0	141.2	137.5	135.7	132.0	130.2	128.4
52.5°	165.1	159.5	152.2	146.7	139.4	135.7	133.9	130.2	126.5	124.7	122.9
55°	152.2	146.7	143.0	137.5	132.0	128.4	124.7	121.0	117.4	115.5	115.5
57.5°	135.7	133.9	132.0	130.2	128.4	124.7	121.0	115.5	111.9	110.0	108.2
60°	121.0	122.9	124.7	126.5	128.4	122.9	117.4	111.9	106.4	104.5	102.7
62.5°	110.0	113.7	117.4	119.2	122.9	117.4	111.9	106.4	100.9	99.0	97.2
65°	102.7	104.5	104.5	106.4	106.4	102.7	100.9	97.2	93.5	91.7	91.7
67.5°	93.5	93.5	93.5	91.7	91.7	89.9	89.9	88.0	86.2	84.4	84.4
70°	84.4	84.4	84.4	82.5	82.5	80.7	80.7	78.9	77.0	77.0	75.2
72.5°	77.0	77.0	75.2	75.2	73.4	73.4	73.4	71.5	71.5	69.7	69.7
75°	67.9	67.9	66.0	66.0	64.2	64.2	64.2	62.4	62.4	62.4	60.5
77.5°	60.5	60.5	58.7	58.7	56.9	56.9	56.9	55.0	55.0	53.2	53.2
80°	53.2	53.2	51.3	51.3	49.5	49.5	47.7	47.7	45.8	45.8	44.0
82.5°	42.2	42.2	42.2	42.2	42.2	40.3	40.3	38.5	36.7	36.7	34.8
85°	34.8	34.8	34.8	33.0	33.0	33.0	31.2	31.2	29.3	27.5	27.5
87.5°	20.2	20.2	20.2	18.3	18.3	18.3	18.3	18.3	18.3	18.3	16.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4
2.5°	1159.0	1157.2	1149.9	1142.5	1149.9	1157.2	1157.2	1157.2	1155.4	1155.4	1155.4
5°	929.8	927.9	924.3	920.6	920.6	918.8	922.4	926.1	929.8	933.5	937.1
7.5°	684.0	678.5	673.0	667.5	671.2	673.0	678.5	682.2	687.7	691.4	700.5
10°	570.3	563.0	557.5	552.0	548.3	544.7	541.0	539.2	535.5	531.8	535.5
12.5°	487.8	478.6	469.5	458.5	456.6	454.8	451.1	447.5	443.8	440.1	438.3
15°	399.8	392.5	388.8	383.3	375.9	368.6	364.9	363.1	359.4	355.8	353.9
17.5°	319.1	311.8	306.3	300.8	298.9	295.3	295.3	295.3	295.3	295.3	295.3
20°	251.2	245.7	245.7	243.9	243.9	242.1	243.9	245.7	245.7	247.6	249.4
22.5°	220.1	220.1	218.2	216.4	218.2	218.2	220.1	221.9	223.7	225.6	227.4
25°	203.6	201.7	203.6	205.4	205.4	205.4	207.2	207.2	209.1	209.1	209.1
27.5°	196.2	196.2	198.1	198.1	199.9	199.9	199.9	198.1	198.1	196.2	196.2
30°	207.2	203.6	203.6	203.6	201.7	199.9	198.1	198.1	196.2	194.4	192.6
32.5°	214.6	216.4	214.6	210.9	209.1	205.4	203.6	199.9	198.1	194.4	190.7
35°	155.9	154.0	157.7	159.5	161.4	163.2	165.1	166.9	166.9	168.7	168.7
37.5°	150.4	148.5	148.5	146.7	146.7	146.7	146.7	146.7	144.9	144.9	146.7
40°	143.0	141.2	141.2	139.4	139.4	137.5	137.5	137.5	137.5	137.5	137.5
42.5°	137.5	135.7	135.7	135.7	135.7	133.9	133.9	132.0	132.0	130.2	130.2
45°	135.7	133.9	132.0	130.2	130.2	128.4	128.4	128.4	126.5	126.5	126.5
47.5°	128.4	126.5	126.5	124.7	124.7	122.9	122.9	122.9	121.0	121.0	121.0
50°	124.7	122.9	122.9	121.0	121.0	119.2	119.2	119.2	117.4	117.4	117.4
52.5°	119.2	117.4	117.4	117.4	115.5	113.7	113.7	113.7	111.9	111.9	111.9
55°	113.7	111.9	111.9	111.9	110.0	108.2	108.2	108.2	106.4	106.4	106.4
57.5°	106.4	104.5	104.5	102.7	102.7	102.7	102.7	102.7	100.9	100.9	100.9
60°	100.9	99.0	99.0	97.2	97.2	95.4	95.4	95.4	95.4	95.4	95.4
62.5°	95.4	93.5	91.7	89.9	91.7	91.7	91.7	91.7	89.9	89.9	89.9
65°	89.9	88.0	86.2	84.4	84.4	84.4	84.4	84.4	84.4	84.4	84.4
67.5°	82.5	80.7	78.9	77.0	78.9	78.9	78.9	78.9	78.9	78.9	78.9
70°	75.2	73.4	73.4	71.5	71.5	69.7	69.7	71.5	71.5	71.5	71.5
72.5°	67.9	66.0	66.0	64.2	64.2	64.2	64.2	64.2	64.2	64.2	64.2
75°	60.5	58.7	58.7	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9
77.5°	51.3	49.5	49.5	49.5	49.5	49.5	49.5	51.3	51.3	51.3	51.3
80°	44.0	42.2	42.2	42.2	42.2	42.2	42.2	42.2	42.2	42.2	42.2
82.5°	34.8	33.0	33.0	33.0	33.0	33.0	33.0	33.0	33.0	33.0	33.0
85°	25.7	23.8	23.8	23.8	25.7	25.7	25.7	25.7	25.7	25.7	25.7
87.5°	16.5	14.7	14.7	14.7	16.5	16.5	16.5	16.5	14.7	14.7	14.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4
2.5°	1155.4	1155.4	1155.4	1153.5	1151.7	1149.9	1148.0	1153.5	1157.2	1162.7	1166.4
5°	939.0	942.6	944.5	950.0	955.5	961.0	966.5	970.1	973.8	975.6	979.3
7.5°	707.9	717.1	724.4	731.7	739.1	744.6	751.9	757.4	762.9	768.4	773.9
10°	537.3	541.0	542.8	550.2	555.7	563.0	568.5	574.0	579.5	583.2	588.7
12.5°	436.5	432.8	431.0	431.0	431.0	431.0	431.0	434.6	438.3	442.0	445.6
15°	352.1	350.3	348.4	346.6	344.8	341.1	339.3	342.9	346.6	350.3	353.9
17.5°	295.3	295.3	295.3	293.4	291.6	289.8	287.9	289.8	291.6	291.6	293.4
20°	253.1	254.9	256.7	258.6	258.6	260.4	260.4	262.2	264.1	264.1	265.9
22.5°	227.4	229.2	229.2	229.2	231.1	231.1	231.1	232.9	234.7	236.6	238.4
25°	207.2	207.2	205.4	205.4	207.2	207.2	207.2	207.2	209.1	209.1	209.1
27.5°	196.2	194.4	194.4	194.4	194.4	192.6	192.6	192.6	192.6	192.6	192.6
30°	190.7	188.9	187.1	185.2	185.2	183.4	181.6	181.6	181.6	181.6	181.6
32.5°	188.9	185.2	181.6	179.7	179.7	177.9	176.1	174.2	174.2	172.4	170.6
35°	168.7	166.9	166.9	165.1	163.2	161.4	159.5	159.5	159.5	157.7	157.7
37.5°	146.7	148.5	148.5	148.5	150.4	150.4	150.4	150.4	152.2	152.2	152.2
40°	137.5	137.5	137.5	139.4	141.2	141.2	143.0	143.0	144.9	144.9	144.9
42.5°	130.2	128.4	128.4	130.2	130.2	132.0	132.0	133.9	135.7	135.7	137.5
45°	126.5	124.7	124.7	124.7	124.7	122.9	122.9	124.7	126.5	128.4	130.2
47.5°	119.2	119.2	117.4	117.4	117.4	117.4	117.4	117.4	119.2	119.2	119.2
50°	115.5	115.5	113.7	113.7	113.7	113.7	113.7	113.7	113.7	113.7	113.7
52.5°	111.9	110.0	110.0	110.0	110.0	108.2	108.2	108.2	108.2	108.2	108.2
55°	106.4	104.5	104.5	104.5	104.5	104.5	104.5	104.5	106.4	106.4	106.4
57.5°	100.9	99.0	99.0	99.0	100.9	100.9	100.9	100.9	102.7	102.7	102.7
60°	95.4	95.4	95.4	95.4	95.4	95.4	95.4	97.2	97.2	99.0	99.0
62.5°	89.9	89.9	89.9	89.9	91.7	91.7	91.7	91.7	93.5	93.5	93.5
65°	84.4	84.4	84.4	84.4	86.2	86.2	86.2	86.2	86.2	86.2	86.2
67.5°	78.9	78.9	78.9	78.9	78.9	78.9	78.9	80.7	80.7	82.5	82.5
70°	71.5	69.7	69.7	71.5	71.5	73.4	73.4	75.2	75.2	77.0	77.0
72.5°	64.2	64.2	64.2	64.2	64.2	64.2	64.2	66.0	67.9	67.9	69.7
75°	56.9	56.9	56.9	56.9	58.7	58.7	58.7	60.5	60.5	62.4	62.4
77.5°	51.3	49.5	49.5	49.5	51.3	51.3	51.3	53.2	53.2	55.0	55.0
80°	42.2	42.2	42.2	42.2	44.0	44.0	44.0	44.0	45.8	45.8	45.8
82.5°	34.8	34.8	34.8	34.8	34.8	34.8	34.8	34.8	36.7	36.7	36.7
85°	25.7	25.7	25.7	25.7	27.5	27.5	27.5	27.5	27.5	27.5	27.5
87.5°	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	18.3	18.3	18.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970
 CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4
2.5°	1166.4	1166.4	1166.4	1166.4	1170.0	1171.9	1175.5	1177.4	1175.5	1173.7	1170.0
5°	981.1	983.0	983.0	984.8	984.8	984.8	984.8	984.8	988.5	992.1	995.8
7.5°	775.7	777.6	779.4	781.2	781.2	781.2	779.4	779.4	781.2	781.2	783.1
10°	594.2	601.5	607.0	612.5	608.9	603.4	599.7	594.2	594.2	594.2	592.3
12.5°	449.3	451.1	454.8	456.6	454.8	454.8	453.0	451.1	453.0	456.6	458.5
15°	355.8	355.8	357.6	357.6	359.4	361.3	361.3	363.1	366.8	368.6	372.3
17.5°	295.3	297.1	297.1	298.9	298.9	300.8	300.8	300.8	304.4	308.1	313.6
20°	265.9	265.9	265.9	265.9	265.9	264.1	264.1	262.2	264.1	267.7	269.6
22.5°	238.4	240.2	240.2	240.2	238.4	236.6	232.9	231.1	231.1	232.9	232.9
25°	209.1	207.2	207.2	205.4	205.4	207.2	207.2	207.2	209.1	209.1	210.9
27.5°	192.6	190.7	190.7	188.9	188.9	190.7	190.7	190.7	190.7	190.7	190.7
30°	179.7	179.7	177.9	176.1	177.9	177.9	179.7	179.7	181.6	181.6	183.4
32.5°	170.6	168.7	168.7	166.9	168.7	168.7	170.6	170.6	172.4	174.2	174.2
35°	157.7	157.7	157.7	157.7	157.7	157.7	155.9	155.9	155.9	155.9	155.9
37.5°	150.4	150.4	148.5	146.7	146.7	146.7	146.7	146.7	144.9	143.0	141.2
40°	144.9	143.0	143.0	141.2	139.4	139.4	137.5	135.7	135.7	133.9	133.9
42.5°	137.5	135.7	135.7	133.9	132.0	132.0	130.2	128.4	128.4	128.4	126.5
45°	128.4	128.4	126.5	124.7	124.7	124.7	122.9	122.9	122.9	122.9	121.0
47.5°	119.2	119.2	117.4	117.4	117.4	117.4	115.5	115.5	115.5	115.5	115.5
50°	113.7	113.7	113.7	113.7	113.7	113.7	111.9	111.9	111.9	111.9	111.9
52.5°	108.2	108.2	108.2	108.2	108.2	108.2	108.2	108.2	108.2	108.2	108.2
55°	106.4	106.4	106.4	106.4	106.4	106.4	104.5	104.5	104.5	106.4	106.4
57.5°	102.7	102.7	100.9	100.9	100.9	100.9	100.9	100.9	100.9	100.9	100.9
60°	99.0	99.0	99.0	99.0	99.0	99.0	99.0	99.0	99.0	99.0	99.0
62.5°	93.5	93.5	93.5	93.5	93.5	95.4	95.4	95.4	95.4	95.4	93.5
65°	86.2	88.0	88.0	88.0	88.0	88.0	88.0	88.0	88.0	88.0	88.0
67.5°	82.5	82.5	82.5	82.5	82.5	82.5	82.5	82.5	82.5	82.5	82.5
70°	77.0	77.0	75.2	75.2	75.2	77.0	77.0	77.0	77.0	77.0	77.0
72.5°	69.7	69.7	69.7	69.7	69.7	69.7	69.7	69.7	69.7	71.5	71.5
75°	62.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4	62.4
77.5°	55.0	55.0	53.2	53.2	53.2	55.0	55.0	55.0	55.0	56.9	56.9
80°	45.8	45.8	45.8	45.8	45.8	45.8	45.8	45.8	45.8	47.7	47.7
82.5°	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7	38.5	38.5
85°	27.5	29.3	29.3	29.3	29.3	29.3	29.3	29.3	29.3	31.2	31.2
87.5°	18.3	18.3	18.3	18.3	18.3	18.3	16.5	16.5	16.5	16.5	14.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970
 CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4
2.5°	1168.2	1170.0	1171.9	1171.9	1173.7	1175.5	1175.5	1182.9	1190.2	1193.9	1197.5
5°	999.5	997.6	997.6	995.8	994.0	999.5	1005.0	1016.0	1027.0	1028.8	1032.5
7.5°	783.1	784.9	786.7	786.7	788.6	783.1	775.7	777.6	779.4	788.6	795.9
10°	592.3	594.2	596.0	596.0	597.8	596.0	592.3	597.8	603.4	610.7	619.9
12.5°	460.3	465.8	471.3	475.0	480.5	484.1	486.0	493.3	498.8	508.0	517.2
15°	375.9	379.6	383.3	387.0	390.6	394.3	398.0	405.3	412.6	423.6	434.6
17.5°	317.3	317.3	319.1	319.1	319.1	322.8	326.4	330.1	331.9	342.9	353.9
20°	271.4	269.6	267.7	265.9	264.1	267.7	269.6	271.4	273.3	280.6	286.1
22.5°	232.9	232.9	234.7	234.7	234.7	232.9	229.2	231.1	231.1	234.7	240.2
25°	210.9	210.9	210.9	209.1	209.1	210.9	212.7	212.7	210.9	212.7	214.6
27.5°	190.7	192.6	192.6	194.4	194.4	196.2	196.2	196.2	196.2	198.1	199.9
30°	183.4	183.4	185.2	185.2	185.2	187.1	188.9	188.9	188.9	190.7	194.4
32.5°	176.1	177.9	179.7	181.6	183.4	185.2	185.2	187.1	187.1	188.9	190.7
35°	155.9	154.0	154.0	152.2	150.4	150.4	150.4	150.4	148.5	150.4	150.4
37.5°	139.4	139.4	139.4	137.5	137.5	139.4	139.4	139.4	139.4	141.2	141.2
40°	132.0	132.0	132.0	132.0	132.0	132.0	132.0	133.9	133.9	135.7	137.5
42.5°	126.5	126.5	126.5	126.5	126.5	128.4	128.4	128.4	128.4	130.2	130.2
45°	121.0	121.0	121.0	121.0	121.0	121.0	121.0	122.9	122.9	124.7	126.5
47.5°	115.5	115.5	115.5	115.5	115.5	117.4	119.2	119.2	119.2	121.0	121.0
50°	111.9	111.9	111.9	111.9	111.9	113.7	113.7	115.5	115.5	117.4	119.2
52.5°	108.2	108.2	108.2	108.2	108.2	110.0	110.0	111.9	111.9	113.7	115.5
55°	106.4	106.4	106.4	104.5	104.5	106.4	106.4	108.2	108.2	110.0	110.0
57.5°	100.9	100.9	100.9	100.9	100.9	100.9	100.9	102.7	102.7	104.5	106.4
60°	99.0	99.0	97.2	97.2	95.4	97.2	97.2	99.0	99.0	100.9	100.9
62.5°	93.5	93.5	93.5	91.7	91.7	93.5	93.5	93.5	93.5	95.4	97.2
65°	88.0	88.0	88.0	86.2	86.2	88.0	88.0	88.0	88.0	89.9	91.7
67.5°	82.5	82.5	82.5	80.7	80.7	80.7	80.7	82.5	82.5	84.4	86.2
70°	77.0	77.0	77.0	75.2	75.2	75.2	73.4	75.2	77.0	78.9	78.9
72.5°	71.5	71.5	71.5	69.7	69.7	69.7	67.9	69.7	69.7	71.5	71.5
75°	62.4	62.4	62.4	62.4	62.4	62.4	60.5	60.5	60.5	62.4	62.4
77.5°	56.9	56.9	56.9	55.0	55.0	55.0	53.2	53.2	53.2	55.0	55.0
80°	47.7	47.7	47.7	45.8	45.8	45.8	44.0	44.0	44.0	45.8	45.8
82.5°	38.5	38.5	38.5	36.7	36.7	36.7	34.8	34.8	34.8	36.7	36.7
85°	31.2	31.2	31.2	31.2	31.2	31.2	29.3	29.3	29.3	31.2	33.0
87.5°	14.7	14.7	16.5	16.5	16.5	16.5	14.7	14.7	12.8	12.8	14.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970
 CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4
2.5°	1201.2	1204.9	1214.0	1221.4	1230.5	1237.9	1243.4	1250.7	1256.2	1261.7	1265.4
5°	1034.3	1036.1	1045.3	1054.5	1061.8	1071.0	1083.8	1096.7	1109.5	1122.3	1131.5
7.5°	805.1	812.4	823.4	836.3	847.3	858.3	871.1	885.8	898.6	911.4	924.3
10°	627.2	634.5	645.5	656.5	665.7	676.7	691.4	706.0	720.7	735.4	750.1
12.5°	526.3	535.5	548.3	561.2	572.2	585.0	603.4	619.9	638.2	654.7	673.0
15°	443.8	454.8	471.3	489.6	506.2	522.7	541.0	559.3	575.8	594.2	612.5
17.5°	364.9	375.9	390.6	407.1	421.8	436.5	458.5	478.6	500.7	520.8	541.0
20°	293.4	298.9	313.6	328.3	342.9	357.6	374.1	390.6	407.1	423.6	449.3
22.5°	243.9	247.6	254.9	260.4	267.7	273.3	289.8	306.3	320.9	337.4	361.3
25°	214.6	216.4	221.9	225.6	231.1	234.7	245.7	254.9	265.9	275.1	297.1
27.5°	199.9	201.7	203.6	205.4	207.2	209.1	216.4	223.7	229.2	236.6	256.7
30°	196.2	198.1	203.6	207.2	212.7	216.4	220.1	223.7	227.4	231.1	243.9
32.5°	192.6	194.4	194.4	192.6	192.6	190.7	194.4	196.2	199.9	201.7	212.7
35°	152.2	152.2	154.0	155.9	157.7	159.5	165.1	168.7	174.2	177.9	187.1
37.5°	143.0	143.0	144.9	148.5	150.4	152.2	155.9	159.5	163.2	166.9	176.1
40°	137.5	139.4	141.2	143.0	144.9	146.7	150.4	152.2	155.9	157.7	165.1
42.5°	132.0	132.0	133.9	137.5	139.4	141.2	144.9	146.7	150.4	152.2	159.5
45°	128.4	130.2	132.0	133.9	133.9	135.7	139.4	143.0	144.9	148.5	155.9
47.5°	122.9	122.9	126.5	128.4	132.0	133.9	137.5	139.4	143.0	144.9	152.2
50°	119.2	121.0	124.7	126.5	130.2	132.0	137.5	141.2	146.7	150.4	154.0
52.5°	115.5	117.4	121.0	122.9	126.5	128.4	135.7	143.0	148.5	155.9	155.9
55°	111.9	111.9	115.5	121.0	124.7	128.4	132.0	137.5	141.2	144.9	144.9
57.5°	106.4	108.2	111.9	117.4	121.0	124.7	128.4	132.0	133.9	137.5	135.7
60°	102.7	102.7	108.2	113.7	119.2	124.7	124.7	124.7	122.9	122.9	122.9
62.5°	97.2	99.0	106.4	115.5	122.9	130.2	124.7	119.2	113.7	108.2	110.0
65°	93.5	95.4	99.0	104.5	108.2	111.9	108.2	106.4	102.7	99.0	100.9
67.5°	86.2	88.0	89.9	89.9	91.7	91.7	91.7	91.7	91.7	91.7	93.5
70°	80.7	80.7	80.7	82.5	82.5	82.5	82.5	82.5	82.5	82.5	84.4
72.5°	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	75.2
75°	64.2	64.2	64.2	64.2	64.2	64.2	64.2	64.2	64.2	64.2	66.0
77.5°	56.9	56.9	56.9	56.9	56.9	56.9	56.9	56.9	55.0	55.0	56.9
80°	47.7	47.7	47.7	47.7	45.8	45.8	45.8	45.8	45.8	45.8	47.7
82.5°	38.5	38.5	38.5	38.5	36.7	36.7	36.7	36.7	34.8	34.8	36.7
85°	34.8	36.7	36.7	38.5	38.5	38.5	36.7	34.8	33.0	31.2	31.2
87.5°	14.7	14.7	14.7	14.7	12.8	12.8	12.8	12.8	12.8	12.8	12.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4
2.5°	1270.9	1274.6	1278.2	1283.7	1291.1	1296.6	1302.1	1313.1	1325.9	1336.9	1347.9
5°	1140.7	1149.9	1159.0	1170.0	1181.0	1190.2	1201.2	1223.2	1245.2	1265.4	1287.4
7.5°	935.3	948.1	959.1	977.5	994.0	1012.3	1028.8	1056.3	1082.0	1109.5	1135.2
10°	764.7	779.4	794.1	817.9	843.6	867.4	891.3	913.3	937.1	959.1	981.1
12.5°	691.4	707.9	726.2	740.9	757.4	772.1	786.7	812.4	838.1	863.8	889.4
15°	630.9	649.2	667.5	685.9	702.4	720.7	737.2	759.2	783.1	805.1	827.1
17.5°	561.2	579.5	599.7	619.9	640.0	660.2	680.4	711.6	742.7	772.1	803.2
20°	473.1	498.8	522.7	550.2	577.7	605.2	632.7	665.7	698.7	729.9	762.9
22.5°	385.1	409.0	432.8	465.8	498.8	530.0	563.0	607.0	649.2	693.2	735.4
25°	320.9	342.9	364.9	401.6	436.5	473.1	508.0	561.2	612.5	665.7	717.1
27.5°	276.9	297.1	317.3	355.8	394.3	431.0	469.5	528.2	585.0	643.7	700.5
30°	256.7	269.6	282.4	319.1	355.8	390.6	427.3	484.1	541.0	597.8	654.7
32.5°	223.7	234.7	245.7	278.8	311.8	342.9	375.9	434.6	491.5	550.2	607.0
35°	198.1	207.2	216.4	247.6	276.9	308.1	337.4	396.1	454.8	513.5	572.2
37.5°	183.4	192.6	199.9	227.4	256.7	284.3	311.8	370.4	427.3	486.0	542.8
40°	172.4	177.9	185.2	212.7	238.4	265.9	291.6	344.8	399.8	453.0	506.2
42.5°	165.1	172.4	177.9	201.7	227.4	251.2	275.1	326.4	377.8	427.3	478.6
45°	163.2	170.6	177.9	198.1	218.2	236.6	256.7	306.3	355.8	405.3	454.8
47.5°	159.5	165.1	172.4	188.9	203.6	220.1	234.7	284.3	333.8	381.4	431.0
50°	157.7	159.5	163.2	177.9	192.6	207.2	221.9	271.4	320.9	370.4	420.0
52.5°	155.9	155.9	155.9	168.7	181.6	192.6	205.4	254.9	306.3	355.8	405.3
55°	144.9	143.0	143.0	155.9	166.9	179.7	190.7	240.2	289.8	337.4	387.0
57.5°	133.9	132.0	130.2	141.2	152.2	163.2	174.2	223.7	275.1	324.6	374.1
60°	122.9	121.0	121.0	132.0	141.2	152.2	161.4	212.7	262.2	313.6	363.1
62.5°	110.0	111.9	111.9	121.0	132.0	141.2	150.4	201.7	254.9	306.3	357.6
65°	100.9	102.7	102.7	113.7	124.7	135.7	146.7	196.2	247.6	297.1	346.6
67.5°	93.5	95.4	95.4	108.2	119.2	132.0	143.0	187.1	232.9	276.9	320.9
70°	86.2	86.2	88.0	100.9	113.7	126.5	139.4	177.9	216.4	253.1	291.6
72.5°	77.0	78.9	80.7	93.5	104.5	117.4	128.4	163.2	198.1	232.9	267.7
75°	67.9	69.7	71.5	82.5	93.5	104.5	115.5	148.5	179.7	212.7	243.9
77.5°	60.5	62.4	64.2	73.4	82.5	91.7	100.9	124.7	150.4	174.2	198.1
80°	49.5	49.5	51.3	58.7	66.0	71.5	78.9	95.4	111.9	126.5	143.0
82.5°	36.7	38.5	38.5	44.0	47.7	53.2	56.9	66.0	73.4	82.5	89.9
85°	31.2	29.3	29.3	33.0	34.8	38.5	40.3	45.8	49.5	55.0	58.7
87.5°	12.8	11.0	11.0	12.8	16.5	18.3	20.2	20.2	22.0	22.0	22.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970
 CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4
2.5°	1353.4	1357.1	1362.6	1366.3	1375.4	1382.8	1391.9	1399.3	1404.8	1413.9	1410.3
5°	1303.9	1320.4	1336.9	1353.4	1366.3	1379.1	1390.1	1402.9	1417.6	1445.1	1452.4
7.5°	1157.2	1179.2	1199.4	1221.4	1247.0	1272.7	1298.4	1324.1	1347.9	1382.8	1404.8
10°	1012.3	1043.5	1072.8	1104.0	1127.8	1151.7	1173.7	1197.5	1230.5	1265.4	1305.7
12.5°	920.6	951.8	983.0	1014.1	1049.0	1082.0	1116.8	1149.9	1181.0	1208.5	1254.4
15°	860.1	894.9	927.9	961.0	1003.1	1043.5	1085.7	1126.0	1171.9	1208.5	1239.7
17.5°	845.4	887.6	927.9	970.1	1014.1	1058.2	1102.2	1146.2	1192.0	1247.0	1287.4
20°	819.8	876.6	933.5	990.3	1047.2	1102.2	1159.0	1214.0	1274.6	1340.6	1358.9
22.5°	805.1	872.9	942.6	1010.5	1087.5	1166.4	1243.4	1320.4	1384.6	1434.1	1489.1
25°	803.2	887.6	973.8	1058.2	1155.4	1250.7	1347.9	1443.3	1525.8	1575.3	1619.3
27.5°	801.4	904.1	1005.0	1105.8	1225.0	1342.4	1461.6	1579.0	1656.0	1727.5	1764.2
30°	779.4	902.3	1027.0	1149.9	1283.7	1417.6	1551.5	1685.3	1764.2	1813.7	1832.1
32.5°	751.9	896.8	1041.7	1186.5	1338.7	1491.0	1641.3	1793.5	1855.9	1898.1	1883.4
35°	729.9	889.4	1047.2	1204.9	1366.3	1529.5	1690.8	1852.2	1942.1	2000.8	1976.9
37.5°	709.7	876.6	1043.5	1210.4	1399.3	1588.2	1777.0	1965.9	2052.1	2114.5	2087.0
40°	685.9	863.8	1043.5	1221.4	1437.8	1652.3	1868.7	2083.3	2195.2	2248.4	2206.2
42.5°	665.7	850.9	1038.0	1223.2	1454.3	1685.3	1916.4	2147.5	2272.2	2347.4	2294.2
45°	640.0	825.3	1008.6	1193.9	1448.8	1703.7	1956.8	2211.7	2356.6	2415.2	2341.9
47.5°	612.5	795.9	977.5	1159.0	1430.4	1701.9	1973.3	2244.7	2378.6	2448.2	2380.4
50°	603.4	786.7	968.3	1151.7	1445.1	1740.4	2033.8	2327.2	2424.4	2481.3	2391.4
52.5°	601.5	795.9	992.1	1186.5	1481.8	1775.2	2070.5	2363.9	2442.7	2503.3	2422.6
55°	596.0	806.9	1016.0	1225.0	1533.1	1843.1	2151.2	2459.3	2538.1	2582.1	2521.6
57.5°	601.5	828.9	1054.5	1281.9	1599.2	1916.4	2233.7	2550.9	2646.3	2677.5	2664.6
60°	605.2	847.3	1087.5	1329.6	1639.5	1949.4	2259.4	2569.3	2668.3	2745.3	2760.0
62.5°	596.0	834.4	1071.0	1309.4	1590.0	1870.6	2151.2	2431.7	2595.0	2708.7	2774.7
65°	568.5	788.6	1010.5	1230.5	1489.1	1749.5	2008.1	2266.7	2439.1	2607.8	2661.0
67.5°	508.0	695.0	882.1	1069.2	1294.7	1520.3	1744.0	1969.6	2186.0	2349.2	2422.6
70°	440.1	586.8	735.4	882.1	1087.5	1292.9	1498.3	1703.7	1894.4	2074.1	2143.8
72.5°	383.3	497.0	612.5	726.2	872.9	1017.8	1164.5	1309.4	1535.0	1714.7	1782.5
75°	326.4	409.0	489.6	572.2	673.0	773.9	872.9	973.8	1133.3	1294.7	1362.6
77.5°	251.2	306.3	359.4	412.6	482.3	550.2	619.9	687.7	799.6	920.6	955.5
80°	174.2	205.4	234.7	265.9	320.9	375.9	431.0	486.0	559.3	627.2	680.4
82.5°	108.2	128.4	146.7	165.1	209.1	253.1	295.3	339.3	368.6	372.3	425.5
85°	69.7	82.5	93.5	104.5	130.2	157.7	183.4	209.1	187.1	174.2	207.2
87.5°	27.5	34.8	40.3	45.8	44.0	42.2	40.3	38.5	33.0	29.3	36.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970
 CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4
2.5°	1413.9	1419.4	1424.9	1428.6	1434.1	1435.9	1437.8	1437.8	1439.6	1441.4	1445.1
5°	1481.8	1492.8	1503.8	1513.0	1524.0	1533.1	1540.5	1549.6	1557.0	1557.0	1555.1
7.5°	1424.9	1452.4	1480.0	1507.5	1535.0	1555.1	1573.5	1593.7	1612.0	1615.7	1619.3
10°	1349.7	1379.1	1406.6	1435.9	1463.4	1494.6	1524.0	1553.3	1584.5	1590.0	1597.3
12.5°	1280.1	1314.9	1349.7	1382.8	1417.6	1439.6	1461.6	1481.8	1503.8	1518.5	1533.1
15°	1278.2	1307.6	1336.9	1364.4	1393.8	1406.6	1419.4	1430.4	1443.3	1443.3	1445.1
17.5°	1320.4	1338.7	1357.1	1373.6	1391.9	1393.8	1397.4	1399.3	1401.1	1395.6	1390.1
20°	1402.9	1410.3	1417.6	1424.9	1432.3	1419.4	1408.4	1395.6	1382.8	1368.1	1355.2
22.5°	1524.0	1507.5	1491.0	1474.4	1457.9	1435.9	1412.1	1390.1	1366.3	1347.9	1329.6
25°	1637.7	1617.5	1597.3	1577.1	1557.0	1509.3	1461.6	1412.1	1364.4	1344.2	1324.1
27.5°	1789.9	1758.7	1727.5	1696.4	1665.2	1601.0	1536.8	1472.6	1408.4	1373.6	1340.6
30°	1826.6	1791.7	1756.9	1720.2	1685.3	1623.0	1562.5	1500.1	1437.8	1397.4	1358.9
32.5°	1879.7	1839.4	1799.0	1758.7	1718.4	1657.8	1597.3	1535.0	1474.4	1437.8	1399.3
35°	1967.8	1921.9	1876.1	1828.4	1782.5	1720.2	1659.7	1597.3	1535.0	1492.8	1452.4
37.5°	2043.0	1989.8	1936.6	1883.4	1830.2	1775.2	1718.4	1663.3	1606.5	1564.3	1524.0
40°	2127.3	2068.6	2009.9	1953.1	1894.4	1843.1	1791.7	1738.5	1687.2	1654.2	1621.2
42.5°	2200.7	2129.1	2059.5	1989.8	1918.3	1883.4	1850.4	1815.6	1780.7	1764.2	1745.9
45°	2252.0	2186.0	2118.1	2052.1	1986.1	1960.4	1934.8	1909.1	1883.4	1899.9	1916.4
47.5°	2274.0	2220.8	2169.5	2118.1	2065.0	2074.1	2083.3	2090.6	2099.8	2121.8	2145.7
50°	2294.2	2264.9	2233.7	2204.3	2173.2	2208.0	2241.0	2275.9	2310.7	2356.6	2402.4
52.5°	2334.5	2318.0	2303.4	2286.9	2270.4	2330.9	2391.4	2451.9	2512.4	2563.8	2615.1
55°	2455.6	2442.7	2429.9	2415.2	2402.4	2488.6	2573.0	2659.1	2745.3	2798.5	2851.7
57.5°	2622.5	2615.1	2606.0	2598.6	2589.5	2673.8	2756.3	2838.9	2923.2	2974.6	3027.8
60°	2749.0	2750.8	2750.8	2752.7	2752.7	2816.9	2881.0	2947.1	3011.3	3055.3	3101.1
62.5°	2816.9	2813.2	2809.5	2805.9	2802.2	2855.4	2908.6	2961.7	3014.9	3047.9	3080.9
65°	2743.5	2763.7	2783.8	2804.0	2824.2	2831.5	2837.0	2844.4	2849.9	2870.0	2890.2
67.5°	2497.8	2538.1	2576.6	2617.0	2655.5	2628.0	2602.3	2574.8	2547.3	2552.8	2556.4
70°	2224.5	2270.4	2318.0	2363.9	2409.7	2345.5	2281.4	2215.3	2151.2	2129.1	2107.1
72.5°	1876.1	1916.4	1958.6	1998.9	2039.3	1960.4	1883.4	1804.6	1725.7	1687.2	1648.7
75°	1434.1	1481.8	1531.3	1579.0	1626.7	1538.6	1448.8	1360.7	1270.9	1245.2	1221.4
77.5°	1045.3	1102.2	1159.0	1215.9	1272.7	1193.9	1115.0	1034.3	955.5	940.8	926.1
80°	761.1	805.1	847.3	891.3	933.5	887.6	841.8	795.9	750.1	748.2	746.4
82.5°	513.5	552.0	588.7	627.2	663.9	645.5	629.0	610.7	592.3	610.7	630.9
85°	264.1	317.3	372.3	425.5	478.6	473.1	469.5	464.0	458.5	482.3	504.3
87.5°	53.2	99.0	144.9	188.9	234.7	223.7	212.7	199.9	188.9	196.2	201.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970
 CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4
2.5°	1446.9	1448.8	1448.8	1448.8	1448.8	1448.8	1445.1	1443.3	1439.6	1435.9	1430.4
5°	1555.1	1553.3	1546.0	1538.6	1529.5	1522.1	1516.6	1509.3	1503.8	1496.5	1485.5
7.5°	1623.0	1626.7	1613.8	1602.8	1590.0	1577.1	1564.3	1551.5	1538.6	1525.8	1500.1
10°	1602.8	1608.3	1601.0	1593.7	1584.5	1577.1	1562.5	1546.0	1531.3	1514.8	1483.6
12.5°	1546.0	1560.6	1557.0	1553.3	1549.6	1546.0	1536.8	1525.8	1516.6	1505.6	1470.8
15°	1445.1	1445.1	1446.9	1448.8	1448.8	1450.6	1452.4	1454.3	1456.1	1457.9	1437.8
17.5°	1384.6	1379.1	1379.1	1379.1	1379.1	1379.1	1386.4	1395.6	1402.9	1410.3	1404.8
20°	1340.6	1327.7	1325.9	1325.9	1324.1	1322.2	1335.1	1349.7	1362.6	1375.4	1382.8
22.5°	1311.2	1292.9	1291.1	1289.2	1287.4	1285.6	1302.1	1318.6	1335.1	1351.6	1377.3
25°	1303.9	1283.7	1285.6	1287.4	1287.4	1289.2	1302.1	1314.9	1327.7	1340.6	1384.6
27.5°	1305.7	1272.7	1274.6	1276.4	1276.4	1278.2	1298.4	1316.7	1336.9	1355.2	1410.3
30°	1318.6	1280.1	1276.4	1272.7	1269.1	1265.4	1292.9	1320.4	1347.9	1375.4	1417.6
32.5°	1362.6	1325.9	1316.7	1307.6	1298.4	1289.2	1322.2	1353.4	1386.4	1417.6	1452.4
35°	1410.3	1369.9	1366.3	1362.6	1357.1	1353.4	1382.8	1413.9	1443.3	1472.6	1503.8
37.5°	1481.8	1441.4	1437.8	1432.3	1428.6	1423.1	1456.1	1487.3	1520.3	1551.5	1579.0
40°	1588.2	1555.1	1553.3	1553.3	1551.5	1549.6	1575.3	1602.8	1628.5	1654.2	1672.5
42.5°	1729.4	1712.9	1718.4	1725.7	1731.2	1736.7	1756.9	1778.9	1799.0	1819.2	1813.7
45°	1932.9	1949.4	1951.3	1953.1	1954.9	1956.8	1962.3	1969.6	1975.1	1980.6	1958.6
47.5°	2167.7	2189.7	2200.7	2211.7	2220.8	2231.8	2224.5	2215.3	2208.0	2198.8	2143.8
50°	2446.4	2492.3	2490.4	2488.6	2484.9	2483.1	2468.4	2453.7	2437.2	2422.6	2341.9
52.5°	2666.5	2717.8	2727.0	2736.2	2745.3	2754.5	2727.0	2699.5	2670.1	2642.6	2541.8
55°	2903.1	2956.2	2958.1	2959.9	2959.9	2961.7	2923.2	2884.7	2844.4	2805.9	2701.3
57.5°	3079.1	3130.5	3125.0	3121.3	3115.8	3110.3	3064.4	3018.6	2972.7	2926.9	2822.4
60°	3145.1	3189.1	3178.1	3167.1	3154.3	3143.3	3108.4	3073.6	3036.9	3002.1	2901.2
62.5°	3114.0	3147.0	3130.5	3115.8	3099.3	3082.8	3038.8	2992.9	2948.9	2903.1	2829.7
65°	2908.6	2928.7	2906.7	2886.5	2866.4	2844.4	2807.7	2771.0	2732.5	2695.8	2646.3
67.5°	2561.9	2565.6	2563.8	2561.9	2560.1	2558.3	2505.1	2451.9	2396.9	2343.7	2340.0
70°	2087.0	2065.0	2068.6	2074.1	2077.8	2081.5	2041.1	2002.6	1962.3	1921.9	1940.3
72.5°	1610.2	1571.6	1580.8	1591.8	1601.0	1610.2	1577.1	1546.0	1513.0	1480.0	1505.6
75°	1195.7	1171.9	1181.0	1192.0	1201.2	1210.4	1197.5	1184.7	1170.0	1157.2	1181.0
77.5°	911.4	896.8	898.6	898.6	900.4	900.4	902.3	905.9	907.8	909.6	935.3
80°	742.7	740.9	739.1	737.2	733.6	731.7	750.1	768.4	786.7	805.1	817.9
82.5°	649.2	667.5	656.5	647.4	636.4	625.4	641.9	658.4	674.9	691.4	685.9
85°	528.2	550.2	530.0	509.8	487.8	467.6	482.3	495.2	509.8	522.7	515.3
87.5°	209.1	214.6	181.6	150.4	117.4	84.4	133.9	181.6	231.1	278.8	286.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4	1320.4
2.5°	1424.9	1417.6	1412.1	1410.3	1406.6	1404.8	1401.1	1397.4	1391.9	1388.3	1382.8
5°	1472.6	1461.6	1448.8	1430.4	1413.9	1395.6	1377.3	1360.7	1344.2	1325.9	1309.4
7.5°	1474.4	1448.8	1423.1	1399.3	1373.6	1349.7	1324.1	1302.1	1278.2	1254.4	1232.4
10°	1454.3	1423.1	1391.9	1360.7	1331.4	1300.2	1269.1	1243.4	1215.9	1188.4	1162.7
12.5°	1437.8	1402.9	1368.1	1331.4	1296.6	1259.9	1223.2	1197.5	1171.9	1146.2	1120.5
15°	1417.6	1395.6	1375.4	1342.4	1309.4	1276.4	1243.4	1208.5	1175.5	1140.7	1105.8
17.5°	1401.1	1395.6	1390.1	1368.1	1346.1	1322.2	1300.2	1265.4	1230.5	1193.9	1159.0
20°	1391.9	1399.3	1406.6	1395.6	1384.6	1371.8	1360.7	1335.1	1309.4	1281.9	1256.2
22.5°	1402.9	1430.4	1456.1	1457.9	1461.6	1463.4	1465.3	1441.4	1417.6	1391.9	1368.1
25°	1428.6	1472.6	1516.6	1540.5	1564.3	1590.0	1613.8	1599.2	1584.5	1569.8	1555.1
27.5°	1463.4	1518.5	1573.5	1608.3	1641.3	1676.2	1711.0	1709.2	1707.4	1703.7	1701.9
30°	1457.9	1500.1	1542.3	1584.5	1626.7	1668.8	1711.0	1733.0	1753.2	1775.2	1797.2
32.5°	1489.1	1524.0	1560.6	1604.7	1648.7	1694.5	1738.5	1784.4	1828.4	1874.2	1920.1
35°	1536.8	1568.0	1601.0	1648.7	1698.2	1745.9	1795.4	1850.4	1907.2	1964.1	2019.1
37.5°	1608.3	1635.8	1665.2	1705.5	1747.7	1788.0	1830.2	1910.9	1991.6	2074.1	2154.8
40°	1690.8	1709.2	1727.5	1766.0	1804.6	1843.1	1881.6	1982.4	2083.3	2184.2	2285.0
42.5°	1810.1	1804.6	1799.0	1830.2	1863.2	1894.4	1927.4	2019.1	2110.8	2202.5	2294.2
45°	1936.6	1914.6	1892.6	1907.2	1923.8	1938.4	1954.9	2048.5	2142.0	2237.3	2330.9
47.5°	2088.8	2033.8	1978.8	1965.9	1953.1	1938.4	1925.6	2026.5	2127.3	2230.0	2330.9
50°	2261.2	2178.7	2098.0	2065.0	2030.1	1997.1	1962.3	2044.8	2129.1	2213.5	2296.0
52.5°	2440.9	2338.2	2237.3	2186.0	2134.7	2081.5	2030.1	2099.8	2171.3	2242.9	2312.5
55°	2595.0	2490.4	2384.1	2323.5	2263.0	2202.5	2142.0	2211.7	2281.4	2351.1	2420.7
57.5°	2717.8	2613.3	2508.8	2451.9	2393.2	2336.4	2277.7	2343.7	2411.6	2479.4	2545.4
60°	2802.2	2701.3	2600.5	2545.4	2490.4	2435.4	2380.4	2459.3	2538.1	2618.8	2697.7
62.5°	2758.2	2684.8	2611.5	2587.6	2563.8	2538.1	2514.3	2589.5	2662.8	2738.0	2813.2
65°	2596.8	2547.3	2497.8	2521.6	2547.3	2571.1	2596.8	2646.3	2695.8	2747.2	2796.7
67.5°	2334.5	2330.9	2325.4	2378.6	2431.7	2486.8	2539.9	2573.0	2604.1	2637.1	2670.1
70°	1958.6	1978.8	1997.1	2088.8	2180.5	2272.2	2363.9	2376.7	2389.6	2402.4	2415.2
72.5°	1533.1	1558.8	1586.3	1707.4	1826.6	1947.6	2068.6	2061.3	2054.0	2044.8	2037.5
75°	1206.7	1230.5	1256.2	1368.1	1480.0	1591.8	1703.7	1672.5	1643.2	1612.0	1580.8
77.5°	962.8	988.5	1016.0	1120.5	1225.0	1331.4	1435.9	1360.7	1285.6	1210.4	1135.2
80°	828.9	841.8	852.8	924.3	994.0	1065.5	1137.0	1060.0	981.1	902.3	825.3
82.5°	680.4	673.0	667.5	709.7	751.9	794.1	836.3	762.9	689.5	614.4	541.0
85°	508.0	500.7	493.3	515.3	537.3	561.2	583.2	498.8	414.5	328.3	243.9
87.5°	295.3	302.6	309.9	333.8	357.6	383.3	407.1	320.9	234.7	146.7	60.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970

CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675970
 CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1320.4	1320.4
2.5°	1371.8	1362.6
5°	1296.6	1283.7
7.5°	1214.0	1197.5
10°	1138.8	1116.8
12.5°	1091.2	1063.7
15°	1072.8	1039.8
17.5°	1127.8	1096.7
20°	1212.2	1170.0
22.5°	1314.9	1263.6
25°	1492.8	1430.4
27.5°	1637.7	1573.5
30°	1727.5	1657.8
32.5°	1826.6	1734.9
35°	1929.3	1841.2
37.5°	2054.0	1954.9
40°	2182.3	2079.6
42.5°	2226.3	2160.3
45°	2268.5	2206.2
47.5°	2277.7	2226.3
50°	2286.9	2279.5
52.5°	2312.5	2310.7
55°	2422.6	2424.4
57.5°	2558.3	2569.3
60°	2683.0	2670.1
62.5°	2747.2	2681.2
65°	2703.2	2611.5
67.5°	2571.1	2472.1
70°	2281.4	2147.5
72.5°	1920.1	1802.7
75°	1480.0	1380.9
77.5°	1052.7	970.1
80°	740.9	658.4
82.5°	475.0	409.0
85°	214.6	187.1
87.5°	60.5	58.7
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0



REPORT NUMBER: P675970
CATALOG NUMBER: CCW-SA-2A-730-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)