

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P675990

Luminaire Tested: **CCW-SA-1E-740-U-SLR**

Issue Date: 04/25/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P675990  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/25/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCW-SA-1E-740-U-SLR  
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @1050mA w/  
SLR distribution lens  
Light Source: (16) 4000K CCT, 70 CRI LEDs  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5673.9 lumens  
Efficiency: N/A  
Efficacy: 101.1 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G2

Input Watts (W): 56.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT


REPORT NUMBER: P675990

CATALOG NUMBER: CCW-SA-1E-740-U-SLR

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 8.1 fc

Type IV - Short - N/A

REPORT NUMBER: P675990  
CATALOG NUMBER: CCW-SA-1E-740-U-SLR

## Luminous Intensity Polar Plot



REPORT NUMBER: P675990

CATALOG NUMBER: CCW-SA-1E-740-U-SLR


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1167.4   | 0.0    | 1167.4 |
|                    | % Fixture | 20.6     | 0.0    | 20.6   |
| <b>Street Side</b> | Lumens    | 4506.4   | 0.0    | 4506.4 |
|                    | % Fixture | 79.4     | 0.0    | 79.4   |
| <b>Total</b>       | Lumens    | 5673.9   | 0.0    | 5673.9 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 140.8  | 2.5       |
| 10°-20°   | 297.3  | 5.2       |
| 20°-30°   | 434.9  | 7.7       |
| 30°-40°   | 612.7  | 10.8      |
| 40°-50°   | 841.9  | 14.8      |
| 50°-60°   | 1147.6 | 20.2      |
| 60°-70°   | 1256.0 | 22.1      |
| 70°-80°   | 725.3  | 12.8      |
| 80°-90°   | 217.4  | 3.8       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 5673.9 | 100.0     |
| 0°-180°   | 5673.9 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P675990


CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 582.7  | 10.3      |                         |      |         |
| FM   | (30°-60°)   | 2070.6 | 36.5      |                         |      |         |
| FH   | (60°-80°)   | 1668.5 | 29.4      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 184.7  | 3.3       |                         |      | G2/225  |
| BL   | (0°-30°)    | 290.2  | 5.1       | B1/500                  |      |         |
| BM   | (30°-60°)   | 531.6  | 9.4       | B1/1000                 |      |         |
| BH   | (60°-80°)   | 312.9  | 5.5       | B1/500                  |      | G1/500  |
| BVH  | (80°-90°)   | 32.7   | 0.6       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G2**

Type IV Short



REPORT NUMBER: P675990

CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5°  | 25°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 |
| 2.5°   | 1869.8 | 1859.7 | 1852.1 | 1844.6 | 1834.5 | 1827.0 | 1816.9 | 1806.8 | 1794.3 | 1784.2 | 1771.6 |
| 5°     | 1761.6 | 1731.4 | 1701.2 | 1683.5 | 1663.4 | 1645.8 | 1625.7 | 1603.0 | 1580.4 | 1555.2 | 1532.5 |
| 7.5°   | 1643.3 | 1605.5 | 1567.8 | 1537.6 | 1504.9 | 1474.7 | 1442.0 | 1414.3 | 1386.6 | 1358.9 | 1331.2 |
| 10°    | 1532.5 | 1497.3 | 1462.1 | 1424.3 | 1384.1 | 1346.3 | 1306.1 | 1268.3 | 1230.6 | 1192.8 | 1155.1 |
| 12.5°  | 1459.6 | 1416.8 | 1376.5 | 1333.7 | 1293.5 | 1250.7 | 1207.9 | 1172.7 | 1137.5 | 1099.7 | 1064.5 |
| 15°    | 1426.9 | 1386.6 | 1348.8 | 1306.1 | 1263.3 | 1220.5 | 1177.7 | 1137.5 | 1099.7 | 1059.4 | 1019.2 |
| 17.5°  | 1504.9 | 1447.0 | 1389.1 | 1333.7 | 1278.4 | 1223.0 | 1167.7 | 1117.3 | 1067.0 | 1016.7 | 966.3  |
| 20°    | 1605.5 | 1532.5 | 1462.1 | 1394.1 | 1323.7 | 1255.7 | 1185.3 | 1114.8 | 1044.3 | 973.9  | 903.4  |
| 22.5°  | 1733.9 | 1650.8 | 1570.3 | 1482.2 | 1391.6 | 1303.5 | 1213.0 | 1124.9 | 1036.8 | 946.2  | 858.1  |
| 25°    | 1962.9 | 1864.7 | 1766.6 | 1640.8 | 1512.4 | 1386.6 | 1258.3 | 1142.5 | 1029.2 | 913.5  | 797.7  |
| 27.5°  | 2159.2 | 2025.8 | 1894.9 | 1743.9 | 1592.9 | 1442.0 | 1291.0 | 1157.6 | 1026.7 | 893.4  | 760.0  |
| 30°    | 2274.9 | 2144.1 | 2013.2 | 1829.5 | 1648.3 | 1464.6 | 1280.9 | 1132.4 | 986.5  | 838.0  | 689.5  |
| 32.5°  | 2380.6 | 2234.7 | 2088.7 | 1887.4 | 1683.5 | 1482.2 | 1278.4 | 1114.8 | 953.8  | 790.2  | 626.6  |
| 35°    | 2526.6 | 2365.5 | 2207.0 | 1972.9 | 1738.9 | 1504.9 | 1270.8 | 1102.2 | 931.1  | 762.5  | 591.4  |
| 37.5°  | 2682.6 | 2483.8 | 2287.5 | 2028.3 | 1769.1 | 1509.9 | 1250.7 | 1084.6 | 918.5  | 752.4  | 586.3  |
| 40°    | 2853.7 | 2612.1 | 2373.1 | 2086.2 | 1801.8 | 1514.9 | 1228.1 | 1062.0 | 895.9  | 727.3  | 561.2  |
| 42.5°  | 2964.4 | 2702.7 | 2441.0 | 2131.5 | 1824.5 | 1514.9 | 1205.4 | 1041.8 | 878.3  | 712.2  | 548.6  |
| 45°    | 3027.4 | 2773.2 | 2521.5 | 2186.8 | 1852.1 | 1517.5 | 1182.8 | 1021.7 | 860.6  | 697.1  | 536.0  |
| 47.5°  | 3055.0 | 2818.5 | 2581.9 | 2229.6 | 1879.8 | 1527.5 | 1175.2 | 1011.6 | 845.5  | 682.0  | 515.9  |
| 50°    | 3128.0 | 2919.1 | 2710.3 | 2332.8 | 1957.8 | 1580.4 | 1202.9 | 1026.7 | 853.1  | 676.9  | 500.8  |
| 52.5°  | 3170.8 | 2992.1 | 2813.4 | 2425.9 | 2038.4 | 1650.8 | 1263.3 | 1067.0 | 870.7  | 674.4  | 478.1  |
| 55°    | 3326.8 | 3155.7 | 2984.6 | 2571.9 | 2156.6 | 1743.9 | 1328.7 | 1112.3 | 895.9  | 676.9  | 460.5  |
| 57.5°  | 3525.6 | 3344.4 | 3165.8 | 2720.3 | 2274.9 | 1829.5 | 1384.1 | 1152.6 | 918.5  | 687.0  | 453.0  |
| 60°    | 3664.0 | 3487.9 | 3314.2 | 2841.1 | 2365.5 | 1892.4 | 1416.8 | 1175.2 | 933.6  | 689.5  | 447.9  |
| 62.5°  | 3679.1 | 3452.6 | 3228.7 | 2768.2 | 2307.6 | 1844.6 | 1384.1 | 1150.0 | 916.0  | 679.5  | 445.4  |
| 65°    | 3583.5 | 3319.3 | 3055.0 | 2614.6 | 2174.3 | 1733.9 | 1293.5 | 1079.6 | 865.7  | 649.3  | 435.4  |
| 67.5°  | 3392.2 | 3082.7 | 2773.2 | 2370.5 | 1967.9 | 1565.3 | 1162.6 | 978.9  | 797.7  | 614.0  | 430.3  |
| 70°    | 2946.8 | 2675.0 | 2405.8 | 2056.0 | 1708.7 | 1358.9 | 1009.1 | 858.1  | 709.7  | 558.7  | 407.7  |
| 72.5°  | 2473.7 | 2219.6 | 1967.9 | 1683.5 | 1401.7 | 1117.3 | 833.0  | 719.7  | 606.5  | 490.7  | 377.5  |
| 75°    | 1894.9 | 1703.7 | 1514.9 | 1303.5 | 1092.2 | 878.3  | 666.9  | 583.8  | 500.8  | 417.7  | 334.7  |
| 77.5°  | 1331.2 | 1228.1 | 1127.4 | 968.9  | 810.3  | 651.8  | 493.2  | 437.9  | 382.5  | 327.1  | 271.8  |
| 80°    | 903.4  | 845.5  | 790.2  | 676.9  | 563.7  | 447.9  | 334.7  | 299.5  | 261.7  | 226.5  | 188.7  |
| 82.5°  | 561.2  | 558.7  | 553.6  | 475.6  | 397.6  | 319.6  | 241.6  | 211.4  | 183.7  | 153.5  | 123.3  |
| 85°    | 256.7  | 299.5  | 339.7  | 296.9  | 254.2  | 211.4  | 168.6  | 148.5  | 128.3  | 105.7  | 85.6   |
| 87.5°  | 80.5   | 98.1   | 113.2  | 108.2  | 100.7  | 95.6   | 88.1   | 75.5   | 62.9   | 50.3   | 37.7   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P675990  
 CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 25° |
|--------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P675990

CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 27.5°  | 30°    | 32.5°  | 35°    | 37.5°  | 40°    | 42.5°  | 45°    | 47.5°  | 50°    | 52.5°  |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 |
| 2.5°   | 1761.6 | 1754.0 | 1743.9 | 1733.9 | 1721.3 | 1711.2 | 1698.6 | 1686.1 | 1683.5 | 1678.5 | 1676.0 |
| 5°     | 1517.5 | 1502.4 | 1484.7 | 1469.6 | 1454.5 | 1436.9 | 1421.8 | 1404.2 | 1391.6 | 1376.5 | 1363.9 |
| 7.5°   | 1303.5 | 1278.4 | 1250.7 | 1223.0 | 1197.9 | 1172.7 | 1145.0 | 1119.8 | 1107.3 | 1094.7 | 1082.1 |
| 10°    | 1132.4 | 1107.3 | 1084.6 | 1059.4 | 1041.8 | 1026.7 | 1009.1 | 991.5  | 976.4  | 961.3  | 946.2  |
| 12.5°  | 1046.9 | 1029.2 | 1011.6 | 994.0  | 973.9  | 956.3  | 936.1  | 916.0  | 898.4  | 883.3  | 865.7  |
| 15°    | 994.0  | 968.9  | 941.2  | 916.0  | 888.3  | 863.2  | 835.5  | 807.8  | 787.7  | 770.0  | 749.9  |
| 17.5°  | 931.1  | 893.4  | 858.1  | 820.4  | 790.2  | 760.0  | 727.3  | 697.1  | 674.4  | 649.3  | 626.6  |
| 20°    | 860.6  | 817.9  | 772.6  | 729.8  | 694.6  | 661.8  | 626.6  | 591.4  | 566.2  | 538.5  | 513.4  |
| 22.5°  | 800.2  | 744.9  | 687.0  | 629.1  | 591.4  | 553.6  | 513.4  | 475.6  | 453.0  | 427.8  | 405.2  |
| 25°    | 734.8  | 674.4  | 611.5  | 548.6  | 510.8  | 470.6  | 432.8  | 392.6  | 375.0  | 359.9  | 342.2  |
| 27.5°  | 699.6  | 639.2  | 576.3  | 515.9  | 480.7  | 442.9  | 407.7  | 369.9  | 357.3  | 342.2  | 329.7  |
| 30°    | 629.1  | 571.2  | 510.8  | 450.5  | 425.3  | 402.6  | 377.5  | 352.3  | 347.3  | 344.8  | 339.7  |
| 32.5°  | 566.2  | 505.8  | 445.4  | 385.0  | 362.4  | 339.7  | 317.1  | 294.4  | 291.9  | 286.9  | 284.4  |
| 35°    | 533.5  | 475.6  | 415.2  | 357.3  | 337.2  | 314.6  | 294.4  | 271.8  | 266.7  | 259.2  | 254.2  |
| 37.5°  | 525.9  | 465.6  | 402.6  | 342.2  | 322.1  | 302.0  | 279.3  | 259.2  | 254.2  | 249.1  | 244.1  |
| 40°    | 505.8  | 447.9  | 392.6  | 334.7  | 314.6  | 294.4  | 271.8  | 251.7  | 246.6  | 241.6  | 236.6  |
| 42.5°  | 490.7  | 435.4  | 377.5  | 319.6  | 302.0  | 284.4  | 264.2  | 246.6  | 241.6  | 236.6  | 229.0  |
| 45°    | 478.1  | 420.3  | 359.9  | 302.0  | 289.4  | 276.8  | 261.7  | 249.1  | 244.1  | 236.6  | 231.5  |
| 47.5°  | 458.0  | 402.6  | 344.8  | 286.9  | 274.3  | 264.2  | 251.7  | 239.1  | 234.0  | 229.0  | 224.0  |
| 50°    | 442.9  | 385.0  | 327.1  | 269.3  | 259.2  | 249.1  | 239.1  | 229.0  | 229.0  | 231.5  | 231.5  |
| 52.5°  | 422.8  | 367.4  | 312.0  | 256.7  | 246.6  | 236.6  | 226.5  | 216.4  | 218.9  | 221.5  | 224.0  |
| 55°    | 405.2  | 352.3  | 296.9  | 241.6  | 231.5  | 221.5  | 208.9  | 198.8  | 201.3  | 203.8  | 206.4  |
| 57.5°  | 397.6  | 342.2  | 286.9  | 231.5  | 221.5  | 208.9  | 198.8  | 186.2  | 186.2  | 186.2  | 186.2  |
| 60°    | 392.6  | 334.7  | 279.3  | 221.5  | 208.9  | 198.8  | 186.2  | 173.6  | 171.1  | 171.1  | 168.6  |
| 62.5°  | 390.1  | 332.2  | 276.8  | 218.9  | 203.8  | 191.3  | 176.2  | 161.1  | 158.5  | 156.0  | 153.5  |
| 65°    | 380.0  | 327.1  | 271.8  | 216.4  | 198.8  | 183.7  | 166.1  | 148.5  | 146.0  | 146.0  | 143.4  |
| 67.5°  | 377.5  | 322.1  | 269.3  | 213.9  | 196.3  | 176.2  | 158.5  | 138.4  | 135.9  | 133.4  | 130.9  |
| 70°    | 357.3  | 309.5  | 259.2  | 208.9  | 188.7  | 171.1  | 151.0  | 130.9  | 128.3  | 123.3  | 120.8  |
| 72.5°  | 332.2  | 289.4  | 244.1  | 198.8  | 178.7  | 158.5  | 138.4  | 118.3  | 115.8  | 113.2  | 108.2  |
| 75°    | 294.4  | 254.2  | 213.9  | 173.6  | 156.0  | 140.9  | 123.3  | 105.7  | 103.2  | 100.7  | 95.6   |
| 77.5°  | 241.6  | 208.9  | 178.7  | 146.0  | 133.4  | 120.8  | 108.2  | 95.6   | 93.1   | 90.6   | 85.6   |
| 80°    | 171.1  | 151.0  | 133.4  | 113.2  | 105.7  | 95.6   | 88.1   | 78.0   | 78.0   | 75.5   | 75.5   |
| 82.5°  | 113.2  | 103.2  | 93.1   | 83.0   | 78.0   | 73.0   | 67.9   | 62.9   | 62.9   | 60.4   | 60.4   |
| 85°    | 80.5   | 75.5   | 67.9   | 62.9   | 60.4   | 55.4   | 52.8   | 47.8   | 47.8   | 47.8   | 47.8   |
| 87.5°  | 37.7   | 37.7   | 35.2   | 35.2   | 32.7   | 32.7   | 30.2   | 27.7   | 27.7   | 27.7   | 27.7   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P675990

CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° | 47.5° | 50° | 52.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |



REPORT NUMBER: P675990

CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 55°    | 57.5°  | 60°    | 62.5°  | 65°    | 67.5°  | 70°    | 72.5°  | 75°    | 77.5°  | 80°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 |
| 2.5°   | 1671.0 | 1663.4 | 1655.9 | 1645.8 | 1638.2 | 1628.2 | 1615.6 | 1605.5 | 1592.9 | 1592.9 | 1590.4 |
| 5°     | 1348.8 | 1341.3 | 1333.7 | 1323.7 | 1316.1 | 1306.1 | 1298.5 | 1288.4 | 1278.4 | 1278.4 | 1275.9 |
| 7.5°   | 1069.5 | 1054.4 | 1039.3 | 1021.7 | 1006.6 | 996.5  | 986.5  | 973.9  | 963.8  | 956.3  | 948.7  |
| 10°    | 931.1  | 916.0  | 898.4  | 883.3  | 865.7  | 853.1  | 840.5  | 825.4  | 812.8  | 802.8  | 792.7  |
| 12.5°  | 848.1  | 830.4  | 812.8  | 795.2  | 777.6  | 760.0  | 744.9  | 727.3  | 709.7  | 697.1  | 684.5  |
| 15°    | 729.8  | 712.2  | 694.6  | 676.9  | 659.3  | 639.2  | 619.1  | 596.4  | 576.3  | 566.2  | 558.7  |
| 17.5°  | 601.4  | 583.8  | 563.7  | 546.1  | 525.9  | 510.8  | 495.8  | 480.7  | 465.6  | 455.5  | 447.9  |
| 20°    | 485.7  | 465.6  | 445.4  | 425.3  | 405.2  | 395.1  | 385.0  | 375.0  | 364.9  | 357.3  | 352.3  |
| 22.5°  | 380.0  | 367.4  | 357.3  | 344.8  | 332.2  | 324.6  | 319.6  | 312.0  | 304.5  | 304.5  | 304.5  |
| 25°    | 324.6  | 317.1  | 312.0  | 304.5  | 296.9  | 294.4  | 291.9  | 286.9  | 284.4  | 281.8  | 281.8  |
| 27.5°  | 314.6  | 307.0  | 299.5  | 291.9  | 284.4  | 281.8  | 279.3  | 274.3  | 271.8  | 271.8  | 271.8  |
| 30°    | 334.7  | 332.2  | 329.7  | 327.1  | 324.6  | 319.6  | 312.0  | 307.0  | 299.5  | 294.4  | 289.4  |
| 32.5°  | 279.3  | 276.8  | 276.8  | 274.3  | 271.8  | 276.8  | 279.3  | 284.4  | 286.9  | 289.4  | 291.9  |
| 35°    | 246.6  | 241.6  | 236.6  | 231.5  | 226.5  | 224.0  | 221.5  | 218.9  | 216.4  | 216.4  | 213.9  |
| 37.5°  | 239.1  | 234.0  | 229.0  | 224.0  | 218.9  | 216.4  | 213.9  | 211.4  | 208.9  | 208.9  | 206.4  |
| 40°    | 231.5  | 226.5  | 224.0  | 218.9  | 213.9  | 211.4  | 208.9  | 203.8  | 201.3  | 198.8  | 198.8  |
| 42.5°  | 224.0  | 221.5  | 216.4  | 213.9  | 208.9  | 206.4  | 203.8  | 198.8  | 196.3  | 193.8  | 191.3  |
| 45°    | 224.0  | 218.9  | 213.9  | 208.9  | 203.8  | 201.3  | 196.3  | 193.8  | 188.7  | 188.7  | 186.2  |
| 47.5°  | 218.9  | 213.9  | 208.9  | 203.8  | 198.8  | 196.3  | 191.3  | 188.7  | 183.7  | 181.2  | 178.7  |
| 50°    | 231.5  | 224.0  | 213.9  | 206.4  | 196.3  | 193.8  | 188.7  | 186.2  | 181.2  | 178.7  | 176.2  |
| 52.5°  | 226.5  | 218.9  | 208.9  | 201.3  | 191.3  | 186.2  | 183.7  | 178.7  | 173.6  | 171.1  | 168.6  |
| 55°    | 208.9  | 201.3  | 196.3  | 188.7  | 181.2  | 176.2  | 171.1  | 166.1  | 161.1  | 158.5  | 158.5  |
| 57.5°  | 186.2  | 183.7  | 181.2  | 178.7  | 176.2  | 171.1  | 166.1  | 158.5  | 153.5  | 151.0  | 148.5  |
| 60°    | 166.1  | 168.6  | 171.1  | 173.6  | 176.2  | 168.6  | 161.1  | 153.5  | 146.0  | 143.4  | 140.9  |
| 62.5°  | 151.0  | 156.0  | 161.1  | 163.6  | 168.6  | 161.1  | 153.5  | 146.0  | 138.4  | 135.9  | 133.4  |
| 65°    | 140.9  | 143.4  | 143.4  | 146.0  | 146.0  | 140.9  | 138.4  | 133.4  | 128.3  | 125.8  | 125.8  |
| 67.5°  | 128.3  | 128.3  | 128.3  | 125.8  | 125.8  | 123.3  | 123.3  | 120.8  | 118.3  | 115.8  | 115.8  |
| 70°    | 115.8  | 115.8  | 115.8  | 113.2  | 113.2  | 110.7  | 110.7  | 108.2  | 105.7  | 105.7  | 103.2  |
| 72.5°  | 105.7  | 105.7  | 103.2  | 103.2  | 100.7  | 100.7  | 100.7  | 98.1   | 98.1   | 95.6   | 95.6   |
| 75°    | 93.1   | 93.1   | 90.6   | 90.6   | 88.1   | 88.1   | 88.1   | 85.6   | 85.6   | 85.6   | 83.0   |
| 77.5°  | 83.0   | 83.0   | 80.5   | 80.5   | 78.0   | 78.0   | 78.0   | 75.5   | 75.5   | 73.0   | 73.0   |
| 80°    | 73.0   | 73.0   | 70.5   | 70.5   | 67.9   | 67.9   | 65.4   | 65.4   | 62.9   | 62.9   | 60.4   |
| 82.5°  | 57.9   | 57.9   | 57.9   | 57.9   | 57.9   | 55.4   | 55.4   | 52.8   | 50.3   | 50.3   | 47.8   |
| 85°    | 47.8   | 47.8   | 47.8   | 45.3   | 45.3   | 45.3   | 42.8   | 42.8   | 40.3   | 37.7   | 37.7   |
| 87.5°  | 27.7   | 27.7   | 27.7   | 25.2   | 25.2   | 25.2   | 25.2   | 25.2   | 25.2   | 25.2   | 22.6   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P675990  
 CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° | 75° | 77.5° | 80° |
|--------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P675990

CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 82.5°  | 85°    | 87.5°  | 90°    | 92.5°  | 95°    | 97.5°  | 100°   | 102.5° | 105°   | 107.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 |
| 2.5°   | 1590.4 | 1587.9 | 1577.8 | 1567.8 | 1577.8 | 1587.9 | 1587.9 | 1587.9 | 1585.4 | 1585.4 | 1585.4 |
| 5°     | 1275.9 | 1273.3 | 1268.3 | 1263.3 | 1263.3 | 1260.8 | 1265.8 | 1270.8 | 1275.9 | 1280.9 | 1285.9 |
| 7.5°   | 938.7  | 931.1  | 923.6  | 916.0  | 921.0  | 923.6  | 931.1  | 936.1  | 943.7  | 948.7  | 961.3  |
| 10°    | 782.6  | 772.6  | 765.0  | 757.5  | 752.4  | 747.4  | 742.4  | 739.9  | 734.8  | 729.8  | 734.8  |
| 12.5°  | 669.4  | 656.8  | 644.2  | 629.1  | 626.6  | 624.1  | 619.1  | 614.0  | 609.0  | 604.0  | 601.4  |
| 15°    | 548.6  | 538.5  | 533.5  | 525.9  | 515.9  | 505.8  | 500.8  | 498.3  | 493.2  | 488.2  | 485.7  |
| 17.5°  | 437.9  | 427.8  | 420.3  | 412.7  | 410.2  | 405.2  | 405.2  | 405.2  | 405.2  | 405.2  | 405.2  |
| 20°    | 344.8  | 337.2  | 337.2  | 334.7  | 334.7  | 332.2  | 334.7  | 337.2  | 337.2  | 339.7  | 342.2  |
| 22.5°  | 302.0  | 302.0  | 299.5  | 296.9  | 299.5  | 299.5  | 302.0  | 304.5  | 307.0  | 309.5  | 312.0  |
| 25°    | 279.3  | 276.8  | 279.3  | 281.8  | 281.8  | 281.8  | 284.4  | 284.4  | 286.9  | 286.9  | 286.9  |
| 27.5°  | 269.3  | 269.3  | 271.8  | 271.8  | 274.3  | 274.3  | 274.3  | 271.8  | 271.8  | 269.3  | 269.3  |
| 30°    | 284.4  | 279.3  | 279.3  | 279.3  | 276.8  | 274.3  | 271.8  | 271.8  | 269.3  | 266.7  | 264.2  |
| 32.5°  | 294.4  | 296.9  | 294.4  | 289.4  | 286.9  | 281.8  | 279.3  | 274.3  | 271.8  | 266.7  | 261.7  |
| 35°    | 213.9  | 211.4  | 216.4  | 218.9  | 221.5  | 224.0  | 226.5  | 229.0  | 229.0  | 231.5  | 231.5  |
| 37.5°  | 206.4  | 203.8  | 203.8  | 201.3  | 201.3  | 201.3  | 201.3  | 201.3  | 198.8  | 198.8  | 201.3  |
| 40°    | 196.3  | 193.8  | 193.8  | 191.3  | 191.3  | 188.7  | 188.7  | 188.7  | 188.7  | 188.7  | 188.7  |
| 42.5°  | 188.7  | 186.2  | 186.2  | 186.2  | 186.2  | 183.7  | 183.7  | 181.2  | 181.2  | 178.7  | 178.7  |
| 45°    | 186.2  | 183.7  | 181.2  | 178.7  | 178.7  | 176.2  | 176.2  | 176.2  | 173.6  | 173.6  | 173.6  |
| 47.5°  | 176.2  | 173.6  | 173.6  | 171.1  | 171.1  | 168.6  | 168.6  | 168.6  | 166.1  | 166.1  | 166.1  |
| 50°    | 171.1  | 168.6  | 168.6  | 166.1  | 166.1  | 163.6  | 163.6  | 163.6  | 161.1  | 161.1  | 161.1  |
| 52.5°  | 163.6  | 161.1  | 161.1  | 161.1  | 158.5  | 156.0  | 156.0  | 156.0  | 153.5  | 153.5  | 153.5  |
| 55°    | 156.0  | 153.5  | 153.5  | 153.5  | 151.0  | 148.5  | 148.5  | 148.5  | 146.0  | 146.0  | 146.0  |
| 57.5°  | 146.0  | 143.4  | 143.4  | 140.9  | 140.9  | 140.9  | 140.9  | 140.9  | 138.4  | 138.4  | 138.4  |
| 60°    | 138.4  | 135.9  | 135.9  | 133.4  | 133.4  | 130.9  | 130.9  | 130.9  | 130.9  | 130.9  | 130.9  |
| 62.5°  | 130.9  | 128.3  | 125.8  | 123.3  | 125.8  | 125.8  | 125.8  | 125.8  | 123.3  | 123.3  | 123.3  |
| 65°    | 123.3  | 120.8  | 118.3  | 115.8  | 115.8  | 115.8  | 115.8  | 115.8  | 115.8  | 115.8  | 115.8  |
| 67.5°  | 113.2  | 110.7  | 108.2  | 105.7  | 108.2  | 108.2  | 108.2  | 108.2  | 108.2  | 108.2  | 108.2  |
| 70°    | 103.2  | 100.7  | 100.7  | 98.1   | 98.1   | 95.6   | 95.6   | 98.1   | 98.1   | 98.1   | 98.1   |
| 72.5°  | 93.1   | 90.6   | 90.6   | 88.1   | 88.1   | 88.1   | 88.1   | 88.1   | 88.1   | 88.1   | 88.1   |
| 75°    | 83.0   | 80.5   | 80.5   | 78.0   | 78.0   | 78.0   | 78.0   | 78.0   | 78.0   | 78.0   | 78.0   |
| 77.5°  | 70.5   | 67.9   | 67.9   | 67.9   | 67.9   | 67.9   | 67.9   | 70.5   | 70.5   | 70.5   | 70.5   |
| 80°    | 60.4   | 57.9   | 57.9   | 57.9   | 57.9   | 57.9   | 57.9   | 57.9   | 57.9   | 57.9   | 57.9   |
| 82.5°  | 47.8   | 45.3   | 45.3   | 45.3   | 45.3   | 45.3   | 45.3   | 45.3   | 45.3   | 45.3   | 45.3   |
| 85°    | 35.2   | 32.7   | 32.7   | 32.7   | 35.2   | 35.2   | 35.2   | 35.2   | 35.2   | 35.2   | 35.2   |
| 87.5°  | 22.6   | 20.1   | 20.1   | 20.1   | 22.6   | 22.6   | 22.6   | 22.6   | 20.1   | 20.1   | 20.1   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P675990  
 CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° | 92.5° | 95° | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|------|--------|------|--------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P675990

CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 110°   | 112.5° | 115°   | 117.5° | 120°   | 122.5° | 125°   | 127.5° | 130°   | 132.5° | 135°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 |
| 2.5°   | 1585.4 | 1585.4 | 1585.4 | 1582.9 | 1580.4 | 1577.8 | 1575.3 | 1582.9 | 1587.9 | 1595.5 | 1600.5 |
| 5°     | 1288.4 | 1293.5 | 1296.0 | 1303.5 | 1311.1 | 1318.6 | 1326.2 | 1331.2 | 1336.3 | 1338.8 | 1343.8 |
| 7.5°   | 971.4  | 984.0  | 994.0  | 1004.1 | 1014.2 | 1021.7 | 1031.8 | 1039.3 | 1046.9 | 1054.4 | 1062.0 |
| 10°    | 737.3  | 742.4  | 744.9  | 755.0  | 762.5  | 772.6  | 780.1  | 787.7  | 795.2  | 800.2  | 807.8  |
| 12.5°  | 598.9  | 593.9  | 591.4  | 591.4  | 591.4  | 591.4  | 591.4  | 596.4  | 601.4  | 606.5  | 611.5  |
| 15°    | 483.2  | 480.7  | 478.1  | 475.6  | 473.1  | 468.1  | 465.6  | 470.6  | 475.6  | 480.7  | 485.7  |
| 17.5°  | 405.2  | 405.2  | 405.2  | 402.6  | 400.1  | 397.6  | 395.1  | 397.6  | 400.1  | 400.1  | 402.6  |
| 20°    | 347.3  | 349.8  | 352.3  | 354.8  | 354.8  | 357.3  | 357.3  | 359.9  | 362.4  | 362.4  | 364.9  |
| 22.5°  | 312.0  | 314.6  | 314.6  | 314.6  | 317.1  | 317.1  | 317.1  | 319.6  | 322.1  | 324.6  | 327.1  |
| 25°    | 284.4  | 284.4  | 281.8  | 281.8  | 284.4  | 284.4  | 284.4  | 284.4  | 286.9  | 286.9  | 286.9  |
| 27.5°  | 269.3  | 266.7  | 266.7  | 266.7  | 266.7  | 264.2  | 264.2  | 264.2  | 264.2  | 264.2  | 264.2  |
| 30°    | 261.7  | 259.2  | 256.7  | 254.2  | 254.2  | 251.7  | 249.1  | 249.1  | 249.1  | 249.1  | 249.1  |
| 32.5°  | 259.2  | 254.2  | 249.1  | 246.6  | 246.6  | 244.1  | 241.6  | 239.1  | 239.1  | 236.6  | 234.0  |
| 35°    | 231.5  | 229.0  | 229.0  | 226.5  | 224.0  | 221.5  | 218.9  | 218.9  | 218.9  | 216.4  | 216.4  |
| 37.5°  | 201.3  | 203.8  | 203.8  | 203.8  | 206.4  | 206.4  | 206.4  | 206.4  | 208.9  | 208.9  | 208.9  |
| 40°    | 188.7  | 188.7  | 188.7  | 191.3  | 193.8  | 193.8  | 196.3  | 196.3  | 198.8  | 198.8  | 198.8  |
| 42.5°  | 178.7  | 176.2  | 176.2  | 178.7  | 178.7  | 181.2  | 181.2  | 183.7  | 186.2  | 186.2  | 188.7  |
| 45°    | 173.6  | 171.1  | 171.1  | 171.1  | 171.1  | 168.6  | 168.6  | 171.1  | 173.6  | 176.2  | 178.7  |
| 47.5°  | 163.6  | 163.6  | 161.1  | 161.1  | 161.1  | 161.1  | 161.1  | 161.1  | 163.6  | 163.6  | 163.6  |
| 50°    | 158.5  | 158.5  | 156.0  | 156.0  | 156.0  | 156.0  | 156.0  | 156.0  | 156.0  | 156.0  | 156.0  |
| 52.5°  | 153.5  | 151.0  | 151.0  | 151.0  | 151.0  | 148.5  | 148.5  | 148.5  | 148.5  | 148.5  | 148.5  |
| 55°    | 146.0  | 143.4  | 143.4  | 143.4  | 143.4  | 143.4  | 143.4  | 143.4  | 146.0  | 146.0  | 146.0  |
| 57.5°  | 138.4  | 135.9  | 135.9  | 135.9  | 138.4  | 138.4  | 138.4  | 138.4  | 140.9  | 140.9  | 140.9  |
| 60°    | 130.9  | 130.9  | 130.9  | 130.9  | 130.9  | 130.9  | 130.9  | 133.4  | 133.4  | 135.9  | 135.9  |
| 62.5°  | 123.3  | 123.3  | 123.3  | 123.3  | 125.8  | 125.8  | 125.8  | 125.8  | 128.3  | 128.3  | 128.3  |
| 65°    | 115.8  | 115.8  | 115.8  | 115.8  | 118.3  | 118.3  | 118.3  | 118.3  | 118.3  | 118.3  | 118.3  |
| 67.5°  | 108.2  | 108.2  | 108.2  | 108.2  | 108.2  | 108.2  | 108.2  | 110.7  | 110.7  | 113.2  | 113.2  |
| 70°    | 98.1   | 95.6   | 95.6   | 98.1   | 98.1   | 100.7  | 100.7  | 103.2  | 103.2  | 105.7  | 105.7  |
| 72.5°  | 88.1   | 88.1   | 88.1   | 88.1   | 88.1   | 88.1   | 88.1   | 90.6   | 93.1   | 93.1   | 95.6   |
| 75°    | 78.0   | 78.0   | 78.0   | 78.0   | 80.5   | 80.5   | 80.5   | 83.0   | 83.0   | 85.6   | 85.6   |
| 77.5°  | 70.5   | 67.9   | 67.9   | 67.9   | 70.5   | 70.5   | 70.5   | 73.0   | 73.0   | 75.5   | 75.5   |
| 80°    | 57.9   | 57.9   | 57.9   | 57.9   | 60.4   | 60.4   | 60.4   | 60.4   | 62.9   | 62.9   | 62.9   |
| 82.5°  | 47.8   | 47.8   | 47.8   | 47.8   | 47.8   | 47.8   | 47.8   | 47.8   | 50.3   | 50.3   | 50.3   |
| 85°    | 35.2   | 35.2   | 35.2   | 35.2   | 37.7   | 37.7   | 37.7   | 37.7   | 37.7   | 37.7   | 37.7   |
| 87.5°  | 22.6   | 22.6   | 22.6   | 22.6   | 22.6   | 22.6   | 22.6   | 22.6   | 25.2   | 25.2   | 25.2   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P675990  
 CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P675990

CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140°   | 142.5° | 145°   | 147.5° | 150°   | 152.5° | 155°   | 157.5° | 160°   | 162.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 |
| 2.5°   | 1600.5 | 1600.5 | 1600.5 | 1600.5 | 1605.5 | 1608.0 | 1613.1 | 1615.6 | 1613.1 | 1610.6 | 1605.5 |
| 5°     | 1346.3 | 1348.8 | 1348.8 | 1351.4 | 1351.4 | 1351.4 | 1351.4 | 1351.4 | 1356.4 | 1361.4 | 1366.5 |
| 7.5°   | 1064.5 | 1067.0 | 1069.5 | 1072.0 | 1072.0 | 1072.0 | 1069.5 | 1069.5 | 1072.0 | 1072.0 | 1074.5 |
| 10°    | 815.3  | 825.4  | 833.0  | 840.5  | 835.5  | 827.9  | 822.9  | 815.3  | 815.3  | 815.3  | 812.8  |
| 12.5°  | 616.5  | 619.1  | 624.1  | 626.6  | 624.1  | 624.1  | 621.6  | 619.1  | 621.6  | 626.6  | 629.1  |
| 15°    | 488.2  | 488.2  | 490.7  | 490.7  | 493.2  | 495.8  | 495.8  | 498.3  | 503.3  | 505.8  | 510.8  |
| 17.5°  | 405.2  | 407.7  | 407.7  | 410.2  | 410.2  | 412.7  | 412.7  | 412.7  | 417.7  | 422.8  | 430.3  |
| 20°    | 364.9  | 364.9  | 364.9  | 364.9  | 364.9  | 362.4  | 362.4  | 359.9  | 362.4  | 367.4  | 369.9  |
| 22.5°  | 327.1  | 329.7  | 329.7  | 329.7  | 327.1  | 324.6  | 319.6  | 317.1  | 317.1  | 319.6  | 319.6  |
| 25°    | 286.9  | 284.4  | 284.4  | 281.8  | 281.8  | 284.4  | 284.4  | 284.4  | 286.9  | 286.9  | 289.4  |
| 27.5°  | 264.2  | 261.7  | 261.7  | 259.2  | 259.2  | 261.7  | 261.7  | 261.7  | 261.7  | 261.7  | 261.7  |
| 30°    | 246.6  | 246.6  | 244.1  | 241.6  | 244.1  | 244.1  | 246.6  | 246.6  | 249.1  | 249.1  | 251.7  |
| 32.5°  | 234.0  | 231.5  | 231.5  | 229.0  | 231.5  | 231.5  | 234.0  | 234.0  | 236.6  | 239.1  | 239.1  |
| 35°    | 216.4  | 216.4  | 216.4  | 216.4  | 216.4  | 216.4  | 213.9  | 213.9  | 213.9  | 213.9  | 213.9  |
| 37.5°  | 206.4  | 206.4  | 203.8  | 201.3  | 201.3  | 201.3  | 201.3  | 201.3  | 198.8  | 196.3  | 193.8  |
| 40°    | 198.8  | 196.3  | 196.3  | 193.8  | 191.3  | 191.3  | 188.7  | 186.2  | 186.2  | 183.7  | 183.7  |
| 42.5°  | 188.7  | 186.2  | 186.2  | 183.7  | 181.2  | 181.2  | 178.7  | 176.2  | 176.2  | 176.2  | 173.6  |
| 45°    | 176.2  | 176.2  | 173.6  | 171.1  | 171.1  | 171.1  | 168.6  | 168.6  | 168.6  | 168.6  | 166.1  |
| 47.5°  | 163.6  | 163.6  | 161.1  | 161.1  | 161.1  | 161.1  | 158.5  | 158.5  | 158.5  | 158.5  | 158.5  |
| 50°    | 156.0  | 156.0  | 156.0  | 156.0  | 156.0  | 156.0  | 153.5  | 153.5  | 153.5  | 153.5  | 153.5  |
| 52.5°  | 148.5  | 148.5  | 148.5  | 148.5  | 148.5  | 148.5  | 148.5  | 148.5  | 148.5  | 148.5  | 148.5  |
| 55°    | 146.0  | 146.0  | 146.0  | 146.0  | 146.0  | 146.0  | 143.4  | 143.4  | 143.4  | 146.0  | 146.0  |
| 57.5°  | 140.9  | 140.9  | 138.4  | 138.4  | 138.4  | 138.4  | 138.4  | 138.4  | 138.4  | 138.4  | 138.4  |
| 60°    | 135.9  | 135.9  | 135.9  | 135.9  | 135.9  | 135.9  | 135.9  | 135.9  | 135.9  | 135.9  | 135.9  |
| 62.5°  | 128.3  | 128.3  | 128.3  | 128.3  | 128.3  | 130.9  | 130.9  | 130.9  | 130.9  | 130.9  | 128.3  |
| 65°    | 118.3  | 120.8  | 120.8  | 120.8  | 120.8  | 120.8  | 120.8  | 120.8  | 120.8  | 120.8  | 120.8  |
| 67.5°  | 113.2  | 113.2  | 113.2  | 113.2  | 113.2  | 113.2  | 113.2  | 113.2  | 113.2  | 113.2  | 113.2  |
| 70°    | 105.7  | 105.7  | 103.2  | 103.2  | 103.2  | 105.7  | 105.7  | 105.7  | 105.7  | 105.7  | 105.7  |
| 72.5°  | 95.6   | 95.6   | 95.6   | 95.6   | 95.6   | 95.6   | 95.6   | 95.6   | 95.6   | 98.1   | 98.1   |
| 75°    | 85.6   | 85.6   | 85.6   | 85.6   | 85.6   | 85.6   | 85.6   | 85.6   | 85.6   | 85.6   | 85.6   |
| 77.5°  | 75.5   | 75.5   | 73.0   | 73.0   | 73.0   | 75.5   | 75.5   | 75.5   | 75.5   | 78.0   | 78.0   |
| 80°    | 62.9   | 62.9   | 62.9   | 62.9   | 62.9   | 62.9   | 62.9   | 62.9   | 62.9   | 65.4   | 65.4   |
| 82.5°  | 50.3   | 50.3   | 50.3   | 50.3   | 50.3   | 50.3   | 50.3   | 50.3   | 50.3   | 52.8   | 52.8   |
| 85°    | 37.7   | 40.3   | 40.3   | 40.3   | 40.3   | 40.3   | 40.3   | 40.3   | 40.3   | 42.8   | 42.8   |
| 87.5°  | 25.2   | 25.2   | 25.2   | 25.2   | 25.2   | 25.2   | 22.6   | 22.6   | 22.6   | 22.6   | 20.1   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P675990  
 CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P675990

CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 165°   | 167.5° | 170°   | 172.5° | 175°   | 177.5° | 180°   | 182.5° | 185°   | 187.5° | 190°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 |
| 2.5°   | 1603.0 | 1605.5 | 1608.0 | 1608.0 | 1610.6 | 1613.1 | 1613.1 | 1623.1 | 1633.2 | 1638.2 | 1643.3 |
| 5°     | 1371.5 | 1369.0 | 1369.0 | 1366.5 | 1363.9 | 1371.5 | 1379.0 | 1394.1 | 1409.2 | 1411.8 | 1416.8 |
| 7.5°   | 1074.5 | 1077.1 | 1079.6 | 1079.6 | 1082.1 | 1074.5 | 1064.5 | 1067.0 | 1069.5 | 1082.1 | 1092.2 |
| 10°    | 812.8  | 815.3  | 817.9  | 817.9  | 820.4  | 817.9  | 812.8  | 820.4  | 827.9  | 838.0  | 850.6  |
| 12.5°  | 631.6  | 639.2  | 646.7  | 651.8  | 659.3  | 664.4  | 666.9  | 676.9  | 684.5  | 697.1  | 709.7  |
| 15°    | 515.9  | 520.9  | 525.9  | 531.0  | 536.0  | 541.0  | 546.1  | 556.1  | 566.2  | 581.3  | 596.4  |
| 17.5°  | 435.4  | 435.4  | 437.9  | 437.9  | 437.9  | 442.9  | 447.9  | 453.0  | 455.5  | 470.6  | 485.7  |
| 20°    | 372.4  | 369.9  | 367.4  | 364.9  | 362.4  | 367.4  | 369.9  | 372.4  | 375.0  | 385.0  | 392.6  |
| 22.5°  | 319.6  | 319.6  | 322.1  | 322.1  | 322.1  | 319.6  | 314.6  | 317.1  | 317.1  | 322.1  | 329.7  |
| 25°    | 289.4  | 289.4  | 289.4  | 286.9  | 286.9  | 289.4  | 291.9  | 291.9  | 289.4  | 291.9  | 294.4  |
| 27.5°  | 261.7  | 264.2  | 264.2  | 266.7  | 266.7  | 269.3  | 269.3  | 269.3  | 269.3  | 271.8  | 274.3  |
| 30°    | 251.7  | 251.7  | 254.2  | 254.2  | 254.2  | 256.7  | 259.2  | 259.2  | 259.2  | 261.7  | 266.7  |
| 32.5°  | 241.6  | 244.1  | 246.6  | 249.1  | 251.7  | 254.2  | 254.2  | 256.7  | 256.7  | 259.2  | 261.7  |
| 35°    | 213.9  | 211.4  | 211.4  | 208.9  | 206.4  | 206.4  | 206.4  | 206.4  | 203.8  | 206.4  | 206.4  |
| 37.5°  | 191.3  | 191.3  | 191.3  | 188.7  | 188.7  | 191.3  | 191.3  | 191.3  | 191.3  | 193.8  | 193.8  |
| 40°    | 181.2  | 181.2  | 181.2  | 181.2  | 181.2  | 181.2  | 181.2  | 183.7  | 183.7  | 186.2  | 188.7  |
| 42.5°  | 173.6  | 173.6  | 173.6  | 173.6  | 173.6  | 176.2  | 176.2  | 176.2  | 176.2  | 178.7  | 178.7  |
| 45°    | 166.1  | 166.1  | 166.1  | 166.1  | 166.1  | 166.1  | 166.1  | 168.6  | 168.6  | 171.1  | 173.6  |
| 47.5°  | 158.5  | 158.5  | 158.5  | 158.5  | 158.5  | 161.1  | 163.6  | 163.6  | 163.6  | 166.1  | 166.1  |
| 50°    | 153.5  | 153.5  | 153.5  | 153.5  | 153.5  | 156.0  | 156.0  | 158.5  | 158.5  | 161.1  | 163.6  |
| 52.5°  | 148.5  | 148.5  | 148.5  | 148.5  | 148.5  | 151.0  | 151.0  | 153.5  | 153.5  | 156.0  | 158.5  |
| 55°    | 146.0  | 146.0  | 146.0  | 143.4  | 143.4  | 146.0  | 146.0  | 148.5  | 148.5  | 151.0  | 151.0  |
| 57.5°  | 138.4  | 138.4  | 138.4  | 138.4  | 138.4  | 138.4  | 138.4  | 140.9  | 140.9  | 143.4  | 146.0  |
| 60°    | 135.9  | 135.9  | 133.4  | 133.4  | 130.9  | 133.4  | 133.4  | 135.9  | 135.9  | 138.4  | 138.4  |
| 62.5°  | 128.3  | 128.3  | 128.3  | 125.8  | 125.8  | 128.3  | 128.3  | 128.3  | 128.3  | 130.9  | 133.4  |
| 65°    | 120.8  | 120.8  | 120.8  | 118.3  | 118.3  | 120.8  | 120.8  | 120.8  | 120.8  | 123.3  | 125.8  |
| 67.5°  | 113.2  | 113.2  | 113.2  | 110.7  | 110.7  | 110.7  | 110.7  | 113.2  | 113.2  | 115.8  | 118.3  |
| 70°    | 105.7  | 105.7  | 105.7  | 103.2  | 103.2  | 103.2  | 100.7  | 103.2  | 105.7  | 108.2  | 108.2  |
| 72.5°  | 98.1   | 98.1   | 98.1   | 95.6   | 95.6   | 95.6   | 93.1   | 95.6   | 95.6   | 98.1   | 98.1   |
| 75°    | 85.6   | 85.6   | 85.6   | 85.6   | 85.6   | 85.6   | 83.0   | 83.0   | 83.0   | 85.6   | 85.6   |
| 77.5°  | 78.0   | 78.0   | 78.0   | 75.5   | 75.5   | 75.5   | 73.0   | 73.0   | 73.0   | 75.5   | 75.5   |
| 80°    | 65.4   | 65.4   | 65.4   | 62.9   | 62.9   | 62.9   | 60.4   | 60.4   | 60.4   | 62.9   | 62.9   |
| 82.5°  | 52.8   | 52.8   | 52.8   | 50.3   | 50.3   | 50.3   | 47.8   | 47.8   | 47.8   | 50.3   | 50.3   |
| 85°    | 42.8   | 42.8   | 42.8   | 42.8   | 42.8   | 42.8   | 40.3   | 40.3   | 40.3   | 42.8   | 45.3   |
| 87.5°  | 20.1   | 20.1   | 22.6   | 22.6   | 22.6   | 22.6   | 20.1   | 20.1   | 17.6   | 17.6   | 20.1   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P675990  
 CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° | 190° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P675990

CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195°   | 197.5° | 200°   | 202.5° | 205°   | 207.5° | 210°   | 212.5° | 215°   | 217.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 |
| 2.5°   | 1648.3 | 1653.3 | 1665.9 | 1676.0 | 1688.6 | 1698.6 | 1706.2 | 1716.3 | 1723.8 | 1731.4 | 1736.4 |
| 5°     | 1419.3 | 1421.8 | 1434.4 | 1447.0 | 1457.1 | 1469.6 | 1487.3 | 1504.9 | 1522.5 | 1540.1 | 1552.7 |
| 7.5°   | 1104.7 | 1114.8 | 1129.9 | 1147.5 | 1162.6 | 1177.7 | 1195.3 | 1215.5 | 1233.1 | 1250.7 | 1268.3 |
| 10°    | 860.6  | 870.7  | 885.8  | 900.9  | 913.5  | 928.6  | 948.7  | 968.9  | 989.0  | 1009.1 | 1029.2 |
| 12.5°  | 722.2  | 734.8  | 752.4  | 770.0  | 785.1  | 802.8  | 827.9  | 850.6  | 875.7  | 898.4  | 923.6  |
| 15°    | 609.0  | 624.1  | 646.7  | 671.9  | 694.6  | 717.2  | 742.4  | 767.5  | 790.2  | 815.3  | 840.5  |
| 17.5°  | 500.8  | 515.9  | 536.0  | 558.7  | 578.8  | 598.9  | 629.1  | 656.8  | 687.0  | 714.7  | 742.4  |
| 20°    | 402.6  | 410.2  | 430.3  | 450.5  | 470.6  | 490.7  | 513.4  | 536.0  | 558.7  | 581.3  | 616.5  |
| 22.5°  | 334.7  | 339.7  | 349.8  | 357.3  | 367.4  | 375.0  | 397.6  | 420.3  | 440.4  | 463.0  | 495.8  |
| 25°    | 294.4  | 296.9  | 304.5  | 309.5  | 317.1  | 322.1  | 337.2  | 349.8  | 364.9  | 377.5  | 407.7  |
| 27.5°  | 274.3  | 276.8  | 279.3  | 281.8  | 284.4  | 286.9  | 296.9  | 307.0  | 314.6  | 324.6  | 352.3  |
| 30°    | 269.3  | 271.8  | 279.3  | 284.4  | 291.9  | 296.9  | 302.0  | 307.0  | 312.0  | 317.1  | 334.7  |
| 32.5°  | 264.2  | 266.7  | 266.7  | 264.2  | 264.2  | 261.7  | 266.7  | 269.3  | 274.3  | 276.8  | 291.9  |
| 35°    | 208.9  | 208.9  | 211.4  | 213.9  | 216.4  | 218.9  | 226.5  | 231.5  | 239.1  | 244.1  | 256.7  |
| 37.5°  | 196.3  | 196.3  | 198.8  | 203.8  | 206.4  | 208.9  | 213.9  | 218.9  | 224.0  | 229.0  | 241.6  |
| 40°    | 188.7  | 191.3  | 193.8  | 196.3  | 198.8  | 201.3  | 206.4  | 208.9  | 213.9  | 216.4  | 226.5  |
| 42.5°  | 181.2  | 181.2  | 183.7  | 188.7  | 191.3  | 193.8  | 198.8  | 201.3  | 206.4  | 208.9  | 218.9  |
| 45°    | 176.2  | 178.7  | 181.2  | 183.7  | 183.7  | 186.2  | 191.3  | 196.3  | 198.8  | 203.8  | 213.9  |
| 47.5°  | 168.6  | 168.6  | 173.6  | 176.2  | 181.2  | 183.7  | 188.7  | 191.3  | 196.3  | 198.8  | 208.9  |
| 50°    | 163.6  | 166.1  | 171.1  | 173.6  | 178.7  | 181.2  | 188.7  | 193.8  | 201.3  | 206.4  | 211.4  |
| 52.5°  | 158.5  | 161.1  | 166.1  | 168.6  | 173.6  | 176.2  | 186.2  | 196.3  | 203.8  | 213.9  | 213.9  |
| 55°    | 153.5  | 153.5  | 158.5  | 166.1  | 171.1  | 176.2  | 181.2  | 188.7  | 193.8  | 198.8  | 198.8  |
| 57.5°  | 146.0  | 148.5  | 153.5  | 161.1  | 166.1  | 171.1  | 176.2  | 181.2  | 183.7  | 188.7  | 186.2  |
| 60°    | 140.9  | 140.9  | 148.5  | 156.0  | 163.6  | 171.1  | 171.1  | 171.1  | 168.6  | 168.6  | 168.6  |
| 62.5°  | 133.4  | 135.9  | 146.0  | 158.5  | 168.6  | 178.7  | 171.1  | 163.6  | 156.0  | 148.5  | 151.0  |
| 65°    | 128.3  | 130.9  | 135.9  | 143.4  | 148.5  | 153.5  | 148.5  | 146.0  | 140.9  | 135.9  | 138.4  |
| 67.5°  | 118.3  | 120.8  | 123.3  | 123.3  | 125.8  | 125.8  | 125.8  | 125.8  | 125.8  | 125.8  | 128.3  |
| 70°    | 110.7  | 110.7  | 110.7  | 113.2  | 113.2  | 113.2  | 113.2  | 113.2  | 113.2  | 113.2  | 115.8  |
| 72.5°  | 100.7  | 100.7  | 100.7  | 100.7  | 100.7  | 100.7  | 100.7  | 100.7  | 100.7  | 100.7  | 103.2  |
| 75°    | 88.1   | 88.1   | 88.1   | 88.1   | 88.1   | 88.1   | 88.1   | 88.1   | 88.1   | 88.1   | 90.6   |
| 77.5°  | 78.0   | 78.0   | 78.0   | 78.0   | 78.0   | 78.0   | 78.0   | 78.0   | 75.5   | 75.5   | 78.0   |
| 80°    | 65.4   | 65.4   | 65.4   | 65.4   | 62.9   | 62.9   | 62.9   | 62.9   | 62.9   | 62.9   | 65.4   |
| 82.5°  | 52.8   | 52.8   | 52.8   | 52.8   | 50.3   | 50.3   | 50.3   | 50.3   | 47.8   | 47.8   | 50.3   |
| 85°    | 47.8   | 50.3   | 50.3   | 52.8   | 52.8   | 52.8   | 50.3   | 47.8   | 45.3   | 42.8   | 42.8   |
| 87.5°  | 20.1   | 20.1   | 20.1   | 20.1   | 17.6   | 17.6   | 17.6   | 17.6   | 17.6   | 17.6   | 17.6   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P675990  
 CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° | 217.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P675990

CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 220°   | 222.5° | 225°   | 227.5° | 230°   | 232.5° | 235°   | 237.5° | 240°   | 242.5° | 245°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 |
| 2.5°   | 1743.9 | 1749.0 | 1754.0 | 1761.6 | 1771.6 | 1779.2 | 1786.7 | 1801.8 | 1819.4 | 1834.5 | 1849.6 |
| 5°     | 1565.3 | 1577.8 | 1590.4 | 1605.5 | 1620.6 | 1633.2 | 1648.3 | 1678.5 | 1708.7 | 1736.4 | 1766.6 |
| 7.5°   | 1283.4 | 1301.0 | 1316.1 | 1341.3 | 1363.9 | 1389.1 | 1411.8 | 1449.5 | 1484.7 | 1522.5 | 1557.7 |
| 10°    | 1049.4 | 1069.5 | 1089.6 | 1122.4 | 1157.6 | 1190.3 | 1223.0 | 1253.2 | 1285.9 | 1316.1 | 1346.3 |
| 12.5°  | 948.7  | 971.4  | 996.5  | 1016.7 | 1039.3 | 1059.4 | 1079.6 | 1114.8 | 1150.0 | 1185.3 | 1220.5 |
| 15°    | 865.7  | 890.8  | 916.0  | 941.2  | 963.8  | 989.0  | 1011.6 | 1041.8 | 1074.5 | 1104.7 | 1134.9 |
| 17.5°  | 770.0  | 795.2  | 822.9  | 850.6  | 878.3  | 905.9  | 933.6  | 976.4  | 1019.2 | 1059.4 | 1102.2 |
| 20°    | 649.3  | 684.5  | 717.2  | 755.0  | 792.7  | 830.4  | 868.2  | 913.5  | 958.8  | 1001.6 | 1046.9 |
| 22.5°  | 528.5  | 561.2  | 593.9  | 639.2  | 684.5  | 727.3  | 772.6  | 833.0  | 890.8  | 951.2  | 1009.1 |
| 25°    | 440.4  | 470.6  | 500.8  | 551.1  | 598.9  | 649.3  | 697.1  | 770.0  | 840.5  | 913.5  | 984.0  |
| 27.5°  | 380.0  | 407.7  | 435.4  | 488.2  | 541.0  | 591.4  | 644.2  | 724.8  | 802.8  | 883.3  | 961.3  |
| 30°    | 352.3  | 369.9  | 387.5  | 437.9  | 488.2  | 536.0  | 586.3  | 664.4  | 742.4  | 820.4  | 898.4  |
| 32.5°  | 307.0  | 322.1  | 337.2  | 382.5  | 427.8  | 470.6  | 515.9  | 596.4  | 674.4  | 755.0  | 833.0  |
| 35°    | 271.8  | 284.4  | 296.9  | 339.7  | 380.0  | 422.8  | 463.0  | 543.6  | 624.1  | 704.6  | 785.1  |
| 37.5°  | 251.7  | 264.2  | 274.3  | 312.0  | 352.3  | 390.1  | 427.8  | 508.3  | 586.3  | 666.9  | 744.9  |
| 40°    | 236.6  | 244.1  | 254.2  | 291.9  | 327.1  | 364.9  | 400.1  | 473.1  | 548.6  | 621.6  | 694.6  |
| 42.5°  | 226.5  | 236.6  | 244.1  | 276.8  | 312.0  | 344.8  | 377.5  | 447.9  | 518.4  | 586.3  | 656.8  |
| 45°    | 224.0  | 234.0  | 244.1  | 271.8  | 299.5  | 324.6  | 352.3  | 420.3  | 488.2  | 556.1  | 624.1  |
| 47.5°  | 218.9  | 226.5  | 236.6  | 259.2  | 279.3  | 302.0  | 322.1  | 390.1  | 458.0  | 523.4  | 591.4  |
| 50°    | 216.4  | 218.9  | 224.0  | 244.1  | 264.2  | 284.4  | 304.5  | 372.4  | 440.4  | 508.3  | 576.3  |
| 52.5°  | 213.9  | 213.9  | 213.9  | 231.5  | 249.1  | 264.2  | 281.8  | 349.8  | 420.3  | 488.2  | 556.1  |
| 55°    | 198.8  | 196.3  | 196.3  | 213.9  | 229.0  | 246.6  | 261.7  | 329.7  | 397.6  | 463.0  | 531.0  |
| 57.5°  | 183.7  | 181.2  | 178.7  | 193.8  | 208.9  | 224.0  | 239.1  | 307.0  | 377.5  | 445.4  | 513.4  |
| 60°    | 168.6  | 166.1  | 166.1  | 181.2  | 193.8  | 208.9  | 221.5  | 291.9  | 359.9  | 430.3  | 498.3  |
| 62.5°  | 151.0  | 153.5  | 153.5  | 166.1  | 181.2  | 193.8  | 206.4  | 276.8  | 349.8  | 420.3  | 490.7  |
| 65°    | 138.4  | 140.9  | 140.9  | 156.0  | 171.1  | 186.2  | 201.3  | 269.3  | 339.7  | 407.7  | 475.6  |
| 67.5°  | 128.3  | 130.9  | 130.9  | 148.5  | 163.6  | 181.2  | 196.3  | 256.7  | 319.6  | 380.0  | 440.4  |
| 70°    | 118.3  | 118.3  | 120.8  | 138.4  | 156.0  | 173.6  | 191.3  | 244.1  | 296.9  | 347.3  | 400.1  |
| 72.5°  | 105.7  | 108.2  | 110.7  | 128.3  | 143.4  | 161.1  | 176.2  | 224.0  | 271.8  | 319.6  | 367.4  |
| 75°    | 93.1   | 95.6   | 98.1   | 113.2  | 128.3  | 143.4  | 158.5  | 203.8  | 246.6  | 291.9  | 334.7  |
| 77.5°  | 83.0   | 85.6   | 88.1   | 100.7  | 113.2  | 125.8  | 138.4  | 171.1  | 206.4  | 239.1  | 271.8  |
| 80°    | 67.9   | 67.9   | 70.5   | 80.5   | 90.6   | 98.1   | 108.2  | 130.9  | 153.5  | 173.6  | 196.3  |
| 82.5°  | 50.3   | 52.8   | 52.8   | 60.4   | 65.4   | 73.0   | 78.0   | 90.6   | 100.7  | 113.2  | 123.3  |
| 85°    | 42.8   | 40.3   | 40.3   | 45.3   | 47.8   | 52.8   | 55.4   | 62.9   | 67.9   | 75.5   | 80.5   |
| 87.5°  | 17.6   | 15.1   | 15.1   | 17.6   | 22.6   | 25.2   | 27.7   | 27.7   | 30.2   | 30.2   | 30.2   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P675990  
 CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° | 245° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P675990

CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°   | 252.5° | 255°   | 257.5° | 260°   | 262.5° | 265°   | 267.5° | 270°   | 272.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 |
| 2.5°   | 1857.2 | 1862.2 | 1869.8 | 1874.8 | 1887.4 | 1897.4 | 1910.0 | 1920.1 | 1927.6 | 1940.2 | 1935.2 |
| 5°     | 1789.2 | 1811.9 | 1834.5 | 1857.2 | 1874.8 | 1892.4 | 1907.5 | 1925.1 | 1945.3 | 1983.0 | 1993.1 |
| 7.5°   | 1587.9 | 1618.1 | 1645.8 | 1676.0 | 1711.2 | 1746.5 | 1781.7 | 1816.9 | 1849.6 | 1897.4 | 1927.6 |
| 10°    | 1389.1 | 1431.9 | 1472.2 | 1514.9 | 1547.6 | 1580.4 | 1610.6 | 1643.3 | 1688.6 | 1736.4 | 1791.7 |
| 12.5°  | 1263.3 | 1306.1 | 1348.8 | 1391.6 | 1439.4 | 1484.7 | 1532.5 | 1577.8 | 1620.6 | 1658.4 | 1721.3 |
| 15°    | 1180.2 | 1228.1 | 1273.3 | 1318.6 | 1376.5 | 1431.9 | 1489.8 | 1545.1 | 1608.0 | 1658.4 | 1701.2 |
| 17.5°  | 1160.1 | 1218.0 | 1273.3 | 1331.2 | 1391.6 | 1452.0 | 1512.4 | 1572.8 | 1635.7 | 1711.2 | 1766.6 |
| 20°    | 1124.9 | 1202.9 | 1280.9 | 1358.9 | 1436.9 | 1512.4 | 1590.4 | 1665.9 | 1749.0 | 1839.6 | 1864.7 |
| 22.5°  | 1104.7 | 1197.9 | 1293.5 | 1386.6 | 1492.3 | 1600.5 | 1706.2 | 1811.9 | 1900.0 | 1967.9 | 2043.4 |
| 25°    | 1102.2 | 1218.0 | 1336.3 | 1452.0 | 1585.4 | 1716.3 | 1849.6 | 1980.5 | 2093.7 | 2161.7 | 2222.1 |
| 27.5°  | 1099.7 | 1240.6 | 1379.0 | 1517.5 | 1681.0 | 1842.1 | 2005.7 | 2166.7 | 2272.4 | 2370.5 | 2420.9 |
| 30°    | 1069.5 | 1238.1 | 1409.2 | 1577.8 | 1761.6 | 1945.3 | 2129.0 | 2312.7 | 2420.9 | 2488.8 | 2514.0 |
| 32.5°  | 1031.8 | 1230.6 | 1429.4 | 1628.2 | 1837.0 | 2045.9 | 2252.3 | 2461.1 | 2546.7 | 2604.6 | 2584.4 |
| 35°    | 1001.6 | 1220.5 | 1436.9 | 1653.3 | 1874.8 | 2098.8 | 2320.2 | 2541.7 | 2665.0 | 2745.5 | 2712.8 |
| 37.5°  | 973.9  | 1202.9 | 1431.9 | 1660.9 | 1920.1 | 2179.3 | 2438.5 | 2697.7 | 2816.0 | 2901.5 | 2863.8 |
| 40°    | 941.2  | 1185.3 | 1431.9 | 1676.0 | 1972.9 | 2267.4 | 2564.3 | 2858.7 | 3012.3 | 3085.2 | 3027.4 |
| 42.5°  | 913.5  | 1167.7 | 1424.3 | 1678.5 | 1995.6 | 2312.7 | 2629.7 | 2946.8 | 3117.9 | 3221.1 | 3148.1 |
| 45°    | 878.3  | 1132.4 | 1384.1 | 1638.2 | 1988.0 | 2337.8 | 2685.1 | 3034.9 | 3233.7 | 3314.2 | 3213.6 |
| 47.5°  | 840.5  | 1092.2 | 1341.3 | 1590.4 | 1962.9 | 2335.3 | 2707.8 | 3080.2 | 3263.9 | 3359.5 | 3266.4 |
| 50°    | 827.9  | 1079.6 | 1328.7 | 1580.4 | 1983.0 | 2388.2 | 2790.8 | 3193.4 | 3326.8 | 3404.8 | 3281.5 |
| 52.5°  | 825.4  | 1092.2 | 1361.4 | 1628.2 | 2033.3 | 2436.0 | 2841.1 | 3243.8 | 3352.0 | 3435.0 | 3324.3 |
| 55°    | 817.9  | 1107.3 | 1394.1 | 1681.0 | 2103.8 | 2529.1 | 2951.9 | 3374.6 | 3482.8 | 3543.2 | 3460.2 |
| 57.5°  | 825.4  | 1137.5 | 1447.0 | 1759.0 | 2194.4 | 2629.7 | 3065.1 | 3500.5 | 3631.3 | 3674.1 | 3656.5 |
| 60°    | 830.4  | 1162.6 | 1492.3 | 1824.5 | 2249.8 | 2675.0 | 3100.3 | 3525.6 | 3661.5 | 3767.2 | 3787.3 |
| 62.5°  | 817.9  | 1145.0 | 1469.6 | 1796.8 | 2181.8 | 2566.8 | 2951.9 | 3336.9 | 3560.8 | 3716.9 | 3807.5 |
| 65°    | 780.1  | 1082.1 | 1386.6 | 1688.6 | 2043.4 | 2400.7 | 2755.6 | 3110.4 | 3346.9 | 3578.5 | 3651.4 |
| 67.5°  | 697.1  | 953.8  | 1210.4 | 1467.1 | 1776.6 | 2086.2 | 2393.2 | 2702.7 | 2999.7 | 3223.6 | 3324.3 |
| 70°    | 604.0  | 805.3  | 1009.1 | 1210.4 | 1492.3 | 1774.1 | 2056.0 | 2337.8 | 2599.5 | 2846.2 | 2941.8 |
| 72.5°  | 525.9  | 682.0  | 840.5  | 996.5  | 1197.9 | 1396.7 | 1598.0 | 1796.8 | 2106.3 | 2352.9 | 2446.0 |
| 75°    | 447.9  | 561.2  | 671.9  | 785.1  | 923.6  | 1062.0 | 1197.9 | 1336.3 | 1555.2 | 1776.6 | 1869.8 |
| 77.5°  | 344.8  | 420.3  | 493.2  | 566.2  | 661.8  | 755.0  | 850.6  | 943.7  | 1097.2 | 1263.3 | 1311.1 |
| 80°    | 239.1  | 281.8  | 322.1  | 364.9  | 440.4  | 515.9  | 591.4  | 666.9  | 767.5  | 860.6  | 933.6  |
| 82.5°  | 148.5  | 176.2  | 201.3  | 226.5  | 286.9  | 347.3  | 405.2  | 465.6  | 505.8  | 510.8  | 583.8  |
| 85°    | 95.6   | 113.2  | 128.3  | 143.4  | 178.7  | 216.4  | 251.7  | 286.9  | 256.7  | 239.1  | 284.4  |
| 87.5°  | 37.7   | 47.8   | 55.4   | 62.9   | 60.4   | 57.9   | 55.4   | 52.8   | 45.3   | 40.3   | 50.3   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P675990  
 CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° | 272.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P675990

CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 275°   | 277.5° | 280°   | 282.5° | 285°   | 287.5° | 290°   | 292.5° | 295°   | 297.5° | 300°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 |
| 2.5°   | 1940.2 | 1947.8 | 1955.3 | 1960.4 | 1967.9 | 1970.4 | 1972.9 | 1972.9 | 1975.5 | 1978.0 | 1983.0 |
| 5°     | 2033.3 | 2048.4 | 2063.5 | 2076.1 | 2091.2 | 2103.8 | 2113.9 | 2126.4 | 2136.5 | 2136.5 | 2134.0 |
| 7.5°   | 1955.3 | 1993.1 | 2030.8 | 2068.6 | 2106.3 | 2134.0 | 2159.2 | 2186.8 | 2212.0 | 2217.0 | 2222.1 |
| 10°    | 1852.1 | 1892.4 | 1930.2 | 1970.4 | 2008.2 | 2050.9 | 2091.2 | 2131.5 | 2174.3 | 2181.8 | 2191.9 |
| 12.5°  | 1756.5 | 1804.3 | 1852.1 | 1897.4 | 1945.3 | 1975.5 | 2005.7 | 2033.3 | 2063.5 | 2083.7 | 2103.8 |
| 15°    | 1754.0 | 1794.3 | 1834.5 | 1872.3 | 1912.5 | 1930.2 | 1947.8 | 1962.9 | 1980.5 | 1980.5 | 1983.0 |
| 17.5°  | 1811.9 | 1837.0 | 1862.2 | 1884.9 | 1910.0 | 1912.5 | 1917.6 | 1920.1 | 1922.6 | 1915.1 | 1907.5 |
| 20°    | 1925.1 | 1935.2 | 1945.3 | 1955.3 | 1965.4 | 1947.8 | 1932.7 | 1915.1 | 1897.4 | 1877.3 | 1859.7 |
| 22.5°  | 2091.2 | 2068.6 | 2045.9 | 2023.3 | 2000.6 | 1970.4 | 1937.7 | 1907.5 | 1874.8 | 1849.6 | 1824.5 |
| 25°    | 2247.2 | 2219.6 | 2191.9 | 2164.2 | 2136.5 | 2071.1 | 2005.7 | 1937.7 | 1872.3 | 1844.6 | 1816.9 |
| 27.5°  | 2456.1 | 2413.3 | 2370.5 | 2327.8 | 2285.0 | 2196.9 | 2108.8 | 2020.8 | 1932.7 | 1884.9 | 1839.6 |
| 30°    | 2506.4 | 2458.6 | 2410.8 | 2360.5 | 2312.7 | 2227.1 | 2144.1 | 2058.5 | 1972.9 | 1917.6 | 1864.7 |
| 32.5°  | 2579.4 | 2524.1 | 2468.7 | 2413.3 | 2358.0 | 2274.9 | 2191.9 | 2106.3 | 2023.3 | 1972.9 | 1920.1 |
| 35°    | 2700.2 | 2637.3 | 2574.4 | 2509.0 | 2446.0 | 2360.5 | 2277.4 | 2191.9 | 2106.3 | 2048.4 | 1993.1 |
| 37.5°  | 2803.4 | 2730.4 | 2657.4 | 2584.4 | 2511.5 | 2436.0 | 2358.0 | 2282.5 | 2204.5 | 2146.6 | 2091.2 |
| 40°    | 2919.1 | 2838.6 | 2758.1 | 2680.1 | 2599.5 | 2529.1 | 2458.6 | 2385.6 | 2315.2 | 2269.9 | 2224.6 |
| 42.5°  | 3019.8 | 2921.7 | 2826.0 | 2730.4 | 2632.3 | 2584.4 | 2539.1 | 2491.3 | 2443.5 | 2420.9 | 2395.7 |
| 45°    | 3090.3 | 2999.7 | 2906.6 | 2816.0 | 2725.4 | 2690.1 | 2654.9 | 2619.7 | 2584.4 | 2607.1 | 2629.7 |
| 47.5°  | 3120.5 | 3047.5 | 2977.0 | 2906.6 | 2833.6 | 2846.2 | 2858.7 | 2868.8 | 2881.4 | 2911.6 | 2944.3 |
| 50°    | 3148.1 | 3107.9 | 3065.1 | 3024.8 | 2982.1 | 3029.9 | 3075.2 | 3123.0 | 3170.8 | 3233.7 | 3296.6 |
| 52.5°  | 3203.5 | 3180.9 | 3160.7 | 3138.1 | 3115.4 | 3198.5 | 3281.5 | 3364.6 | 3447.6 | 3518.1 | 3588.5 |
| 55°    | 3369.6 | 3352.0 | 3334.4 | 3314.2 | 3296.6 | 3414.9 | 3530.7 | 3648.9 | 3767.2 | 3840.2 | 3913.2 |
| 57.5°  | 3598.6 | 3588.5 | 3575.9 | 3565.9 | 3553.3 | 3669.1 | 3782.3 | 3895.5 | 4011.3 | 4081.8 | 4154.7 |
| 60°    | 3772.2 | 3774.8 | 3774.8 | 3777.3 | 3777.3 | 3865.3 | 3953.4 | 4044.0 | 4132.1 | 4192.5 | 4255.4 |
| 62.5°  | 3865.3 | 3860.3 | 3855.3 | 3850.2 | 3845.2 | 3918.2 | 3991.2 | 4064.1 | 4137.1 | 4182.4 | 4227.7 |
| 65°    | 3764.7 | 3792.4 | 3820.0 | 3847.7 | 3875.4 | 3885.5 | 3893.0 | 3903.1 | 3910.6 | 3938.3 | 3966.0 |
| 67.5°  | 3427.5 | 3482.8 | 3535.7 | 3591.0 | 3643.9 | 3606.1 | 3570.9 | 3533.2 | 3495.4 | 3503.0 | 3508.0 |
| 70°    | 3052.5 | 3115.4 | 3180.9 | 3243.8 | 3306.7 | 3218.6 | 3130.5 | 3039.9 | 2951.9 | 2921.7 | 2891.5 |
| 72.5°  | 2574.4 | 2629.7 | 2687.6 | 2743.0 | 2798.3 | 2690.1 | 2584.4 | 2476.2 | 2368.0 | 2315.2 | 2262.3 |
| 75°    | 1967.9 | 2033.3 | 2101.3 | 2166.7 | 2232.1 | 2111.3 | 1988.0 | 1867.2 | 1743.9 | 1708.7 | 1676.0 |
| 77.5°  | 1434.4 | 1512.4 | 1590.4 | 1668.4 | 1746.5 | 1638.2 | 1530.0 | 1419.3 | 1311.1 | 1291.0 | 1270.8 |
| 80°    | 1044.3 | 1104.7 | 1162.6 | 1223.0 | 1280.9 | 1218.0 | 1155.1 | 1092.2 | 1029.2 | 1026.7 | 1024.2 |
| 82.5°  | 704.6  | 757.5  | 807.8  | 860.6  | 911.0  | 885.8  | 863.2  | 838.0  | 812.8  | 838.0  | 865.7  |
| 85°    | 362.4  | 435.4  | 510.8  | 583.8  | 656.8  | 649.3  | 644.2  | 636.7  | 629.1  | 661.8  | 692.0  |
| 87.5°  | 73.0   | 135.9  | 198.8  | 259.2  | 322.1  | 307.0  | 291.9  | 274.3  | 259.2  | 269.3  | 276.8  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P675990  
 CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° | 300° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P675990

CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305°   | 307.5° | 310°   | 312.5° | 315°   | 317.5° | 320°   | 322.5° | 325°   | 327.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 |
| 2.5°   | 1985.5 | 1988.0 | 1988.0 | 1988.0 | 1988.0 | 1988.0 | 1983.0 | 1980.5 | 1975.5 | 1970.4 | 1962.9 |
| 5°     | 2134.0 | 2131.5 | 2121.4 | 2111.3 | 2098.8 | 2088.7 | 2081.1 | 2071.1 | 2063.5 | 2053.5 | 2038.4 |
| 7.5°   | 2227.1 | 2232.1 | 2214.5 | 2199.4 | 2181.8 | 2164.2 | 2146.6 | 2129.0 | 2111.3 | 2093.7 | 2058.5 |
| 10°    | 2199.4 | 2207.0 | 2196.9 | 2186.8 | 2174.3 | 2164.2 | 2144.1 | 2121.4 | 2101.3 | 2078.6 | 2035.8 |
| 12.5°  | 2121.4 | 2141.5 | 2136.5 | 2131.5 | 2126.4 | 2121.4 | 2108.8 | 2093.7 | 2081.1 | 2066.0 | 2018.2 |
| 15°    | 1983.0 | 1983.0 | 1985.5 | 1988.0 | 1988.0 | 1990.6 | 1993.1 | 1995.6 | 1998.1 | 2000.6 | 1972.9 |
| 17.5°  | 1900.0 | 1892.4 | 1892.4 | 1892.4 | 1892.4 | 1892.4 | 1902.5 | 1915.1 | 1925.1 | 1935.2 | 1927.6 |
| 20°    | 1839.6 | 1821.9 | 1819.4 | 1819.4 | 1816.9 | 1814.4 | 1832.0 | 1852.1 | 1869.8 | 1887.4 | 1897.4 |
| 22.5°  | 1799.3 | 1774.1 | 1771.6 | 1769.1 | 1766.6 | 1764.1 | 1786.7 | 1809.4 | 1832.0 | 1854.7 | 1889.9 |
| 25°    | 1789.2 | 1761.6 | 1764.1 | 1766.6 | 1766.6 | 1769.1 | 1786.7 | 1804.3 | 1821.9 | 1839.6 | 1900.0 |
| 27.5°  | 1791.7 | 1746.5 | 1749.0 | 1751.5 | 1751.5 | 1754.0 | 1781.7 | 1806.8 | 1834.5 | 1859.7 | 1935.2 |
| 30°    | 1809.4 | 1756.5 | 1751.5 | 1746.5 | 1741.4 | 1736.4 | 1774.1 | 1811.9 | 1849.6 | 1887.4 | 1945.3 |
| 32.5°  | 1869.8 | 1819.4 | 1806.8 | 1794.3 | 1781.7 | 1769.1 | 1814.4 | 1857.2 | 1902.5 | 1945.3 | 1993.1 |
| 35°    | 1935.2 | 1879.8 | 1874.8 | 1869.8 | 1862.2 | 1857.2 | 1897.4 | 1940.2 | 1980.5 | 2020.8 | 2063.5 |
| 37.5°  | 2033.3 | 1978.0 | 1972.9 | 1965.4 | 1960.4 | 1952.8 | 1998.1 | 2040.9 | 2086.2 | 2129.0 | 2166.7 |
| 40°    | 2179.3 | 2134.0 | 2131.5 | 2131.5 | 2129.0 | 2126.4 | 2161.7 | 2199.4 | 2234.7 | 2269.9 | 2295.0 |
| 42.5°  | 2373.1 | 2350.4 | 2358.0 | 2368.0 | 2375.6 | 2383.1 | 2410.8 | 2441.0 | 2468.7 | 2496.4 | 2488.8 |
| 45°    | 2652.4 | 2675.0 | 2677.6 | 2680.1 | 2682.6 | 2685.1 | 2692.7 | 2702.7 | 2710.3 | 2717.8 | 2687.6 |
| 47.5°  | 2974.5 | 3004.7 | 3019.8 | 3034.9 | 3047.5 | 3062.6 | 3052.5 | 3039.9 | 3029.9 | 3017.3 | 2941.8 |
| 50°    | 3357.0 | 3419.9 | 3417.4 | 3414.9 | 3409.9 | 3407.3 | 3387.2 | 3367.1 | 3344.4 | 3324.3 | 3213.6 |
| 52.5°  | 3659.0 | 3729.5 | 3742.0 | 3754.6 | 3767.2 | 3779.8 | 3742.0 | 3704.3 | 3664.0 | 3626.3 | 3487.9 |
| 55°    | 3983.6 | 4056.6 | 4059.1 | 4061.6 | 4061.6 | 4064.1 | 4011.3 | 3958.5 | 3903.1 | 3850.2 | 3706.8 |
| 57.5°  | 4225.2 | 4295.7 | 4288.1 | 4283.1 | 4275.5 | 4268.0 | 4205.1 | 4142.2 | 4079.2 | 4016.3 | 3872.9 |
| 60°    | 4315.8 | 4376.2 | 4361.1 | 4346.0 | 4328.4 | 4313.3 | 4265.5 | 4217.7 | 4167.3 | 4119.5 | 3981.1 |
| 62.5°  | 4273.0 | 4318.3 | 4295.7 | 4275.5 | 4252.9 | 4230.2 | 4169.8 | 4106.9 | 4046.5 | 3983.6 | 3883.0 |
| 65°    | 3991.2 | 4018.9 | 3988.7 | 3961.0 | 3933.3 | 3903.1 | 3852.8 | 3802.4 | 3749.6 | 3699.3 | 3631.3 |
| 67.5°  | 3515.6 | 3520.6 | 3518.1 | 3515.6 | 3513.0 | 3510.5 | 3437.5 | 3364.6 | 3289.1 | 3216.1 | 3211.1 |
| 70°    | 2863.8 | 2833.6 | 2838.6 | 2846.2 | 2851.2 | 2856.2 | 2800.9 | 2748.0 | 2692.7 | 2637.3 | 2662.5 |
| 72.5°  | 2209.5 | 2156.6 | 2169.2 | 2184.3 | 2196.9 | 2209.5 | 2164.2 | 2121.4 | 2076.1 | 2030.8 | 2066.0 |
| 75°    | 1640.8 | 1608.0 | 1620.6 | 1635.7 | 1648.3 | 1660.9 | 1643.3 | 1625.7 | 1605.5 | 1587.9 | 1620.6 |
| 77.5°  | 1250.7 | 1230.6 | 1233.1 | 1233.1 | 1235.6 | 1235.6 | 1238.1 | 1243.2 | 1245.7 | 1248.2 | 1283.4 |
| 80°    | 1019.2 | 1016.7 | 1014.2 | 1011.6 | 1006.6 | 1004.1 | 1029.2 | 1054.4 | 1079.6 | 1104.7 | 1122.4 |
| 82.5°  | 890.8  | 916.0  | 900.9  | 888.3  | 873.2  | 858.1  | 880.8  | 903.4  | 926.1  | 948.7  | 941.2  |
| 85°    | 724.8  | 755.0  | 727.3  | 699.6  | 669.4  | 641.7  | 661.8  | 679.5  | 699.6  | 717.2  | 707.1  |
| 87.5°  | 286.9  | 294.4  | 249.1  | 206.4  | 161.1  | 115.8  | 183.7  | 249.1  | 317.1  | 382.5  | 392.6  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P675990  
 CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305° | 307.5° | 310° | 312.5° | 315° | 317.5° | 320° | 322.5° | 325° | 327.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P675990

CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 330°   | 332.5° | 335°   | 337.5° | 340°   | 342.5° | 345°   | 347.5° | 350°   | 352.5° | 355°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 | 1811.9 |
| 2.5°   | 1955.3 | 1945.3 | 1937.7 | 1935.2 | 1930.2 | 1927.6 | 1922.6 | 1917.6 | 1910.0 | 1905.0 | 1897.4 |
| 5°     | 2020.8 | 2005.7 | 1988.0 | 1962.9 | 1940.2 | 1915.1 | 1889.9 | 1867.2 | 1844.6 | 1819.4 | 1796.8 |
| 7.5°   | 2023.3 | 1988.0 | 1952.8 | 1920.1 | 1884.9 | 1852.1 | 1816.9 | 1786.7 | 1754.0 | 1721.3 | 1691.1 |
| 10°    | 1995.6 | 1952.8 | 1910.0 | 1867.2 | 1827.0 | 1784.2 | 1741.4 | 1706.2 | 1668.4 | 1630.7 | 1595.5 |
| 12.5°  | 1972.9 | 1925.1 | 1877.3 | 1827.0 | 1779.2 | 1728.8 | 1678.5 | 1643.3 | 1608.0 | 1572.8 | 1537.6 |
| 15°    | 1945.3 | 1915.1 | 1887.4 | 1842.1 | 1796.8 | 1751.5 | 1706.2 | 1658.4 | 1613.1 | 1565.3 | 1517.5 |
| 17.5°  | 1922.6 | 1915.1 | 1907.5 | 1877.3 | 1847.1 | 1814.4 | 1784.2 | 1736.4 | 1688.6 | 1638.2 | 1590.4 |
| 20°    | 1910.0 | 1920.1 | 1930.2 | 1915.1 | 1900.0 | 1882.3 | 1867.2 | 1832.0 | 1796.8 | 1759.0 | 1723.8 |
| 22.5°  | 1925.1 | 1962.9 | 1998.1 | 2000.6 | 2005.7 | 2008.2 | 2010.7 | 1978.0 | 1945.3 | 1910.0 | 1877.3 |
| 25°    | 1960.4 | 2020.8 | 2081.1 | 2113.9 | 2146.6 | 2181.8 | 2214.5 | 2194.4 | 2174.3 | 2154.1 | 2134.0 |
| 27.5°  | 2008.2 | 2083.7 | 2159.2 | 2207.0 | 2252.3 | 2300.1 | 2347.9 | 2345.4 | 2342.9 | 2337.8 | 2335.3 |
| 30°    | 2000.6 | 2058.5 | 2116.4 | 2174.3 | 2232.1 | 2290.0 | 2347.9 | 2378.1 | 2405.8 | 2436.0 | 2466.2 |
| 32.5°  | 2043.4 | 2091.2 | 2141.5 | 2201.9 | 2262.3 | 2325.2 | 2385.6 | 2448.6 | 2509.0 | 2571.9 | 2634.8 |
| 35°    | 2108.8 | 2151.6 | 2196.9 | 2262.3 | 2330.3 | 2395.7 | 2463.7 | 2539.1 | 2617.2 | 2695.2 | 2770.7 |
| 37.5°  | 2207.0 | 2244.7 | 2285.0 | 2340.3 | 2398.2 | 2453.6 | 2511.5 | 2622.2 | 2732.9 | 2846.2 | 2956.9 |
| 40°    | 2320.2 | 2345.4 | 2370.5 | 2423.4 | 2476.2 | 2529.1 | 2581.9 | 2720.3 | 2858.7 | 2997.2 | 3135.6 |
| 42.5°  | 2483.8 | 2476.2 | 2468.7 | 2511.5 | 2556.8 | 2599.5 | 2644.8 | 2770.7 | 2896.5 | 3022.3 | 3148.1 |
| 45°    | 2657.4 | 2627.2 | 2597.0 | 2617.2 | 2639.8 | 2659.9 | 2682.6 | 2810.9 | 2939.3 | 3070.1 | 3198.5 |
| 47.5°  | 2866.3 | 2790.8 | 2715.3 | 2697.7 | 2680.1 | 2659.9 | 2642.3 | 2780.7 | 2919.1 | 3060.1 | 3198.5 |
| 50°    | 3102.8 | 2989.6 | 2878.9 | 2833.6 | 2785.8 | 2740.5 | 2692.7 | 2805.9 | 2921.7 | 3037.4 | 3150.7 |
| 52.5°  | 3349.5 | 3208.5 | 3070.1 | 2999.7 | 2929.2 | 2856.2 | 2785.8 | 2881.4 | 2979.5 | 3077.7 | 3173.3 |
| 55°    | 3560.8 | 3417.4 | 3271.5 | 3188.4 | 3105.4 | 3022.3 | 2939.3 | 3034.9 | 3130.5 | 3226.2 | 3321.8 |
| 57.5°  | 3729.5 | 3586.0 | 3442.6 | 3364.6 | 3284.0 | 3206.0 | 3125.5 | 3216.1 | 3309.2 | 3402.3 | 3492.9 |
| 60°    | 3845.2 | 3706.8 | 3568.4 | 3492.9 | 3417.4 | 3341.9 | 3266.4 | 3374.6 | 3482.8 | 3593.6 | 3701.8 |
| 62.5°  | 3784.8 | 3684.2 | 3583.5 | 3550.8 | 3518.1 | 3482.8 | 3450.1 | 3553.3 | 3654.0 | 3757.1 | 3860.3 |
| 65°    | 3563.4 | 3495.4 | 3427.5 | 3460.2 | 3495.4 | 3528.1 | 3563.4 | 3631.3 | 3699.3 | 3769.7 | 3837.7 |
| 67.5°  | 3203.5 | 3198.5 | 3190.9 | 3263.9 | 3336.9 | 3412.4 | 3485.4 | 3530.7 | 3573.4 | 3618.7 | 3664.0 |
| 70°    | 2687.6 | 2715.3 | 2740.5 | 2866.3 | 2992.1 | 3117.9 | 3243.8 | 3261.4 | 3279.0 | 3296.6 | 3314.2 |
| 72.5°  | 2103.8 | 2139.0 | 2176.8 | 2342.9 | 2506.4 | 2672.5 | 2838.6 | 2828.5 | 2818.5 | 2805.9 | 2795.8 |
| 75°    | 1655.9 | 1688.6 | 1723.8 | 1877.3 | 2030.8 | 2184.3 | 2337.8 | 2295.0 | 2254.8 | 2212.0 | 2169.2 |
| 77.5°  | 1321.2 | 1356.4 | 1394.1 | 1537.6 | 1681.0 | 1827.0 | 1970.4 | 1867.2 | 1764.1 | 1660.9 | 1557.7 |
| 80°    | 1137.5 | 1155.1 | 1170.2 | 1268.3 | 1363.9 | 1462.1 | 1560.2 | 1454.5 | 1346.3 | 1238.1 | 1132.4 |
| 82.5°  | 933.6  | 923.6  | 916.0  | 973.9  | 1031.8 | 1089.6 | 1147.5 | 1046.9 | 946.2  | 843.0  | 742.4  |
| 85°    | 697.1  | 687.0  | 676.9  | 707.1  | 737.3  | 770.0  | 800.2  | 684.5  | 568.7  | 450.5  | 334.7  |
| 87.5°  | 405.2  | 415.2  | 425.3  | 458.0  | 490.7  | 525.9  | 558.7  | 440.4  | 322.1  | 201.3  | 83.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P675990  
 CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 332.5° | 335° | 337.5° | 340° | 342.5° | 345° | 347.5° | 350° | 352.5° | 355° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |





REPORT NUMBER: P675990  
 CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360°   |
|--------|--------|--------|
| 0°     | 1811.9 | 1811.9 |
| 2.5°   | 1882.3 | 1869.8 |
| 5°     | 1779.2 | 1761.6 |
| 7.5°   | 1665.9 | 1643.3 |
| 10°    | 1562.7 | 1532.5 |
| 12.5°  | 1497.3 | 1459.6 |
| 15°    | 1472.2 | 1426.9 |
| 17.5°  | 1547.6 | 1504.9 |
| 20°    | 1663.4 | 1605.5 |
| 22.5°  | 1804.3 | 1733.9 |
| 25°    | 2048.4 | 1962.9 |
| 27.5°  | 2247.2 | 2159.2 |
| 30°    | 2370.5 | 2274.9 |
| 32.5°  | 2506.4 | 2380.6 |
| 35°    | 2647.4 | 2526.6 |
| 37.5°  | 2818.5 | 2682.6 |
| 40°    | 2994.6 | 2853.7 |
| 42.5°  | 3055.0 | 2964.4 |
| 45°    | 3112.9 | 3027.4 |
| 47.5°  | 3125.5 | 3055.0 |
| 50°    | 3138.1 | 3128.0 |
| 52.5°  | 3173.3 | 3170.8 |
| 55°    | 3324.3 | 3326.8 |
| 57.5°  | 3510.5 | 3525.6 |
| 60°    | 3681.6 | 3664.0 |
| 62.5°  | 3769.7 | 3679.1 |
| 65°    | 3709.3 | 3583.5 |
| 67.5°  | 3528.1 | 3392.2 |
| 70°    | 3130.5 | 2946.8 |
| 72.5°  | 2634.8 | 2473.7 |
| 75°    | 2030.8 | 1894.9 |
| 77.5°  | 1444.5 | 1331.2 |
| 80°    | 1016.7 | 903.4  |
| 82.5°  | 651.8  | 561.2  |
| 85°    | 294.4  | 256.7  |
| 87.5°  | 83.0   | 80.5   |
| 90°    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    |



REPORT NUMBER: P675990  
CATALOG NUMBER: CCW-SA-1E-740-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

(END OF REPORT)