

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1303876

Luminaire Tested: P3RT17R259050DE010 E3CBUS1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1303876  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-87)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3RT17R259050DE010 E3CBUS1MW  
Description: 3in Adjustable LED luminaire with, R25 optic, 5000K CCT AND, 90CRI , E3CBUS1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1931.0 lumens  
Efficiency: N/A  
Efficacy: 91.1 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.39  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1303876  
CATALOG NUMBER: P3RT17R259050DE010 E3CBUS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1303876  
 CATALOG NUMBER: P3RT17R259050DE010 E3CBUS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	96
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95	95	94
3	109	105	101	99	107	103	100	98	101	99	97	99	97	95	97	95	94	92	92	91
4	106	101	98	95	105	100	97	94	98	95	93	96	94	92	95	93	91	90	89	88
5	103	98	94	92	102	97	94	91	96	93	90	94	92	90	93	91	89	86	86	84
6	101	95	91	89	100	95	91	88	93	90	88	92	89	87	91	89	87	84	84	82
7	98	93	89	86	97	92	89	86	91	88	86	90	87	85	89	87	85	82	82	80
8	96	90	87	84	95	90	86	84	89	86	84	88	85	83	87	85	83	80	80	79
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	86	83	81	79	79	77
10	92	86	83	80	91	86	82	80	85	82	80	84	82	80	84	81	80	77	77	75

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2227607
5°	2063433
10°	1553745
15°	722070
20°	227216
25°	87876
30°	25498
35°	8165
40°	2634
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 0 cd/sqm



TEST NUMBER: P1303876

CATALOG NUMBER: P3RT17R259050DE010 E3CBUS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	819.0	42.4
10°-20°	902.7	46.7
20°-30°	185.4	9.6
30°-40°	22.5	1.2
40°-50°	1.4	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1907.0	98.8
0°-40°	1929.6	99.9
0°-60°	1931.0	100.0
0°-90°	1931.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1931.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10159	
5°	9374	819
15°	3181	903
25°	363	185
35°	30	23
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1303876  
CATALOG NUMBER: P3RT17R259050DE010 E3CBUS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10158.7
2.5°	9963.4
5°	9374.2
7.5°	8388.3
10°	6978.0
12.5°	5140.4
15°	3180.7
17.5°	1730.8
20°	973.7
22.5°	595.2
25°	363.2
27.5°	204.5
30°	100.7
32.5°	45.8
35°	30.5
37.5°	18.3
40°	9.2
42.5°	3.1
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)