

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P675993

Luminaire Tested: **CCW-SA-2B-740-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P675993
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2B-740-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @450mA w/
SLR distribution lens
Light Source: (32) 4000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5731.3 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2

Input Watts (W): 46
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 8.1 fc

Type IV - Short - N/A

REPORT NUMBER: P675993
CATALOG NUMBER: CCW-SA-2B-740-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1179.2	0.0	1179.2
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	4552.0	0.0	4552.0
	% Fixture	79.4	0.0	79.4
Total	Lumens	5731.3	0.0	5731.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.2	2.5
10°-20°	300.3	5.2
20°-30°	439.3	7.7
30°-40°	618.9	10.8
40°-50°	850.4	14.8
50°-60°	1159.2	20.2
60°-70°	1268.7	22.1
70°-80°	732.7	12.8
80°-90°	219.6	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5731.3	100.0
0°-180°	5731.3	100.0

Coefficient of Utilization



REPORT NUMBER: P675993


CATALOG NUMBER: CCW-SA-2B-740-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	588.6	10.3			
FM	(30°-60°)	2091.5	36.5			
FH	(60°-80°)	1685.3	29.4			G1/1800
FVH	(80°-90°)	186.6	3.3			G2/225
BL	(0°-30°)	293.2	5.1	B1/500		
BM	(30°-60°)	537.0	9.4	B1/1000		
BH	(60°-80°)	316.0	5.5	B1/500		G1/500
BVH	(80°-90°)	33.1	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short



REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2
2.5°	1888.7	1878.5	1870.9	1863.3	1853.1	1845.5	1835.3	1825.1	1812.4	1802.3	1789.5
5°	1779.4	1748.9	1718.4	1700.6	1680.2	1662.4	1642.1	1619.2	1596.4	1570.9	1548.1
7.5°	1659.9	1621.8	1583.6	1553.1	1520.1	1489.6	1456.5	1428.6	1400.6	1372.7	1344.7
10°	1548.1	1512.5	1476.9	1438.8	1398.1	1359.9	1319.3	1281.1	1243.0	1204.9	1166.8
12.5°	1474.3	1431.1	1390.5	1347.2	1306.6	1263.4	1220.1	1184.6	1149.0	1110.8	1075.2
15°	1441.3	1400.6	1362.5	1319.3	1276.1	1232.9	1189.6	1149.0	1110.8	1070.2	1029.5
17.5°	1520.1	1461.6	1403.2	1347.2	1291.3	1235.4	1179.5	1128.6	1077.8	1027.0	976.1
20°	1621.8	1548.1	1476.9	1408.2	1337.1	1268.4	1197.3	1126.1	1054.9	983.7	912.6
22.5°	1751.4	1667.5	1586.2	1497.2	1405.7	1316.7	1225.2	1136.3	1047.3	955.8	866.8
25°	1982.7	1883.6	1784.5	1657.4	1527.7	1400.6	1271.0	1154.1	1039.7	922.7	805.8
27.5°	2181.0	2046.3	1914.1	1761.6	1609.1	1456.5	1304.0	1169.3	1037.1	902.4	767.7
30°	2297.9	2165.8	2033.6	1848.0	1665.0	1479.4	1293.9	1143.9	996.4	846.5	696.5
32.5°	2404.7	2257.3	2109.8	1906.5	1700.6	1497.2	1291.3	1126.1	963.4	798.2	632.9
35°	2552.1	2389.4	2229.3	1992.9	1756.5	1520.1	1283.7	1113.4	940.5	770.2	597.4
37.5°	2709.7	2508.9	2310.6	2048.8	1787.0	1525.2	1263.4	1095.6	927.8	760.0	592.3
40°	2882.6	2638.6	2397.1	2107.3	1820.0	1530.3	1240.5	1072.7	904.9	734.6	566.9
42.5°	2994.4	2730.1	2465.7	2153.0	1842.9	1530.3	1217.6	1052.4	887.1	719.4	554.1
45°	3058.0	2801.2	2547.0	2209.0	1870.9	1532.8	1194.7	1032.0	869.4	704.1	541.4
47.5°	3085.9	2847.0	2608.1	2252.2	1898.8	1543.0	1187.1	1021.9	854.1	688.9	521.1
50°	3159.7	2948.7	2737.7	2356.4	1977.6	1596.4	1215.1	1037.1	861.7	683.8	505.9
52.5°	3202.9	3022.4	2841.9	2450.5	2059.0	1667.5	1276.1	1077.8	879.5	681.2	483.0
55°	3360.5	3187.6	3014.8	2597.9	2178.5	1761.6	1342.2	1123.5	904.9	683.8	465.2
57.5°	3561.3	3378.3	3197.8	2747.9	2297.9	1848.0	1398.1	1164.2	927.8	694.0	457.6
60°	3701.1	3523.2	3347.8	2869.9	2389.4	1911.6	1431.1	1187.1	943.1	696.5	452.5
62.5°	3716.3	3487.6	3261.3	2796.2	2331.0	1863.3	1398.1	1161.7	925.3	686.3	449.9
65°	3619.8	3352.8	3085.9	2641.1	2196.3	1751.4	1306.6	1090.5	874.4	655.8	439.8
67.5°	3426.6	3113.9	2801.2	2394.5	1987.8	1581.1	1174.4	988.8	805.8	620.2	434.7
70°	2976.6	2702.1	2430.1	2076.8	1726.0	1372.7	1019.3	866.8	716.8	564.3	411.8
72.5°	2498.7	2242.0	1987.8	1700.6	1415.9	1128.6	841.4	727.0	612.6	495.7	381.3
75°	1914.1	1720.9	1530.3	1316.7	1103.2	887.1	673.6	589.7	505.9	422.0	338.1
77.5°	1344.7	1240.5	1138.8	978.7	818.5	658.4	498.2	442.3	386.4	330.5	274.5
80°	912.6	854.1	798.2	683.8	569.4	452.5	338.1	302.5	264.4	228.8	190.6
82.5°	566.9	564.3	559.2	480.4	401.6	322.8	244.0	213.5	185.6	155.1	124.6
85°	259.3	302.5	343.2	300.0	256.7	213.5	170.3	150.0	129.6	106.8	86.4
87.5°	81.3	99.1	114.4	109.3	101.7	96.6	89.0	76.3	63.5	50.8	38.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993
 CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2
2.5°	1779.4	1771.7	1761.6	1751.4	1738.7	1728.5	1715.8	1703.1	1700.6	1695.5	1692.9
5°	1532.8	1517.6	1499.8	1484.5	1469.3	1451.5	1436.2	1418.4	1405.7	1390.5	1377.7
7.5°	1316.7	1291.3	1263.4	1235.4	1210.0	1184.6	1156.6	1131.2	1118.5	1105.8	1093.0
10°	1143.9	1118.5	1095.6	1070.2	1052.4	1037.1	1019.3	1001.5	986.3	971.0	955.8
12.5°	1057.5	1039.7	1021.9	1004.1	983.7	965.9	945.6	925.3	907.5	892.2	874.4
15°	1004.1	978.7	950.7	925.3	897.3	871.9	843.9	816.0	795.6	777.8	757.5
17.5°	940.5	902.4	866.8	828.7	798.2	767.7	734.6	704.1	681.2	655.8	632.9
20°	869.4	826.1	780.4	737.2	701.6	668.5	632.9	597.4	571.9	544.0	518.6
22.5°	808.3	752.4	694.0	635.5	597.4	559.2	518.6	480.4	457.6	432.1	409.3
25°	742.3	681.2	617.7	554.1	516.0	475.3	437.2	396.5	378.8	363.5	345.7
27.5°	706.7	645.7	582.1	521.1	485.5	447.4	411.8	373.7	361.0	345.7	333.0
30°	635.5	577.0	516.0	455.0	429.6	406.7	381.3	355.9	350.8	348.2	343.2
32.5°	571.9	510.9	449.9	388.9	366.0	343.2	320.3	297.4	294.9	289.8	287.2
35°	538.9	480.4	419.4	361.0	340.6	317.7	297.4	274.5	269.4	261.8	256.7
37.5°	531.3	470.3	406.7	345.7	325.4	305.0	282.2	261.8	256.7	251.7	246.6
40°	510.9	452.5	396.5	338.1	317.7	297.4	274.5	254.2	249.1	244.0	238.9
42.5°	495.7	439.8	381.3	322.8	305.0	287.2	266.9	249.1	244.0	238.9	231.3
45°	483.0	424.5	363.5	305.0	292.3	279.6	264.4	251.7	246.6	238.9	233.9
47.5°	462.6	406.7	348.2	289.8	277.1	266.9	254.2	241.5	236.4	231.3	226.2
50°	447.4	388.9	330.5	272.0	261.8	251.7	241.5	231.3	231.3	233.9	233.9
52.5°	427.0	371.1	315.2	259.3	249.1	238.9	228.8	218.6	221.2	223.7	226.2
55°	409.3	355.9	300.0	244.0	233.9	223.7	211.0	200.8	203.4	205.9	208.4
57.5°	401.6	345.7	289.8	233.9	223.7	211.0	200.8	188.1	188.1	188.1	188.1
60°	396.5	338.1	282.2	223.7	211.0	200.8	188.1	175.4	172.9	172.9	170.3
62.5°	394.0	335.5	279.6	221.2	205.9	193.2	177.9	162.7	160.1	157.6	155.1
65°	383.8	330.5	274.5	218.6	200.8	185.6	167.8	150.0	147.4	147.4	144.9
67.5°	381.3	325.4	272.0	216.1	198.3	177.9	160.1	139.8	137.3	134.7	132.2
70°	361.0	312.7	261.8	211.0	190.6	172.9	152.5	132.2	129.6	124.6	122.0
72.5°	335.5	292.3	246.6	200.8	180.5	160.1	139.8	119.5	116.9	114.4	109.3
75°	297.4	256.7	216.1	175.4	157.6	142.3	124.6	106.8	104.2	101.7	96.6
77.5°	244.0	211.0	180.5	147.4	134.7	122.0	109.3	96.6	94.1	91.5	86.4
80°	172.9	152.5	134.7	114.4	106.8	96.6	89.0	78.8	78.8	76.3	76.3
82.5°	114.4	104.2	94.1	83.9	78.8	73.7	68.6	63.5	63.5	61.0	61.0
85°	81.3	76.3	68.6	63.5	61.0	55.9	53.4	48.3	48.3	48.3	48.3
87.5°	38.1	38.1	35.6	35.6	33.0	33.0	30.5	28.0	28.0	28.0	28.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993
 CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2
2.5°	1687.9	1680.2	1672.6	1662.4	1654.8	1644.6	1631.9	1621.8	1609.1	1609.1	1606.5
5°	1362.5	1354.9	1347.2	1337.1	1329.4	1319.3	1311.7	1301.5	1291.3	1291.3	1288.8
7.5°	1080.3	1065.1	1049.8	1032.0	1016.8	1006.6	996.4	983.7	973.6	965.9	958.3
10°	940.5	925.3	907.5	892.2	874.4	861.7	849.0	833.8	821.1	810.9	800.7
12.5°	856.6	838.8	821.1	803.3	785.5	767.7	752.4	734.6	716.8	704.1	691.4
15°	737.2	719.4	701.6	683.8	666.0	645.7	625.3	602.4	582.1	571.9	564.3
17.5°	607.5	589.7	569.4	551.6	531.3	516.0	500.8	485.5	470.3	460.1	452.5
20°	490.6	470.3	449.9	429.6	409.3	399.1	388.9	378.8	368.6	361.0	355.9
22.5°	383.8	371.1	361.0	348.2	335.5	327.9	322.8	315.2	307.6	307.6	307.6
25°	327.9	320.3	315.2	307.6	300.0	297.4	294.9	289.8	287.2	284.7	284.7
27.5°	317.7	310.1	302.5	294.9	287.2	284.7	282.2	277.1	274.5	274.5	274.5
30°	338.1	335.5	333.0	330.5	327.9	322.8	315.2	310.1	302.5	297.4	292.3
32.5°	282.2	279.6	279.6	277.1	274.5	279.6	282.2	287.2	289.8	292.3	294.9
35°	249.1	244.0	238.9	233.9	228.8	226.2	223.7	221.2	218.6	218.6	216.1
37.5°	241.5	236.4	231.3	226.2	221.2	218.6	216.1	213.5	211.0	211.0	208.4
40°	233.9	228.8	226.2	221.2	216.1	213.5	211.0	205.9	203.4	200.8	200.8
42.5°	226.2	223.7	218.6	216.1	211.0	208.4	205.9	200.8	198.3	195.7	193.2
45°	226.2	221.2	216.1	211.0	205.9	203.4	198.3	195.7	190.6	190.6	188.1
47.5°	221.2	216.1	211.0	205.9	200.8	198.3	193.2	190.6	185.6	183.0	180.5
50°	233.9	226.2	216.1	208.4	198.3	195.7	190.6	188.1	183.0	180.5	177.9
52.5°	228.8	221.2	211.0	203.4	193.2	188.1	185.6	180.5	175.4	172.9	170.3
55°	211.0	203.4	198.3	190.6	183.0	177.9	172.9	167.8	162.7	160.1	160.1
57.5°	188.1	185.6	183.0	180.5	177.9	172.9	167.8	160.1	155.1	152.5	150.0
60°	167.8	170.3	172.9	175.4	177.9	170.3	162.7	155.1	147.4	144.9	142.3
62.5°	152.5	157.6	162.7	165.2	170.3	162.7	155.1	147.4	139.8	137.3	134.7
65°	142.3	144.9	144.9	147.4	147.4	142.3	139.8	134.7	129.6	127.1	127.1
67.5°	129.6	129.6	129.6	127.1	127.1	124.6	124.6	122.0	119.5	116.9	116.9
70°	116.9	116.9	116.9	114.4	114.4	111.8	111.8	109.3	106.8	106.8	104.2
72.5°	106.8	106.8	104.2	104.2	101.7	101.7	101.7	99.1	99.1	96.6	96.6
75°	94.1	94.1	91.5	91.5	89.0	89.0	89.0	86.4	86.4	86.4	83.9
77.5°	83.9	83.9	81.3	81.3	78.8	78.8	78.8	76.3	76.3	73.7	73.7
80°	73.7	73.7	71.2	71.2	68.6	68.6	66.1	66.1	63.5	63.5	61.0
82.5°	58.5	58.5	58.5	58.5	58.5	55.9	55.9	53.4	50.8	50.8	48.3
85°	48.3	48.3	48.3	45.8	45.8	45.8	43.2	43.2	40.7	38.1	38.1
87.5°	28.0	28.0	28.0	25.4	25.4	25.4	25.4	25.4	25.4	25.4	22.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993
 CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2
2.5°	1606.5	1604.0	1593.8	1583.6	1593.8	1604.0	1604.0	1604.0	1601.4	1601.4	1601.4
5°	1288.8	1286.2	1281.1	1276.1	1276.1	1273.5	1278.6	1283.7	1288.8	1293.9	1298.9
7.5°	948.2	940.5	932.9	925.3	930.4	932.9	940.5	945.6	953.2	958.3	971.0
10°	790.6	780.4	772.8	765.1	760.0	755.0	749.9	747.3	742.3	737.2	742.3
12.5°	676.2	663.5	650.7	635.5	632.9	630.4	625.3	620.2	615.2	610.1	607.5
15°	554.1	544.0	538.9	531.3	521.1	510.9	505.9	503.3	498.2	493.1	490.6
17.5°	442.3	432.1	424.5	416.9	414.3	409.3	409.3	409.3	409.3	409.3	409.3
20°	348.2	340.6	340.6	338.1	338.1	335.5	338.1	340.6	340.6	343.2	345.7
22.5°	305.0	305.0	302.5	300.0	302.5	302.5	305.0	307.6	310.1	312.7	315.2
25°	282.2	279.6	282.2	284.7	284.7	284.7	287.2	287.2	289.8	289.8	289.8
27.5°	272.0	272.0	274.5	274.5	277.1	277.1	277.1	274.5	274.5	272.0	272.0
30°	287.2	282.2	282.2	282.2	279.6	277.1	274.5	274.5	272.0	269.4	266.9
32.5°	297.4	300.0	297.4	292.3	289.8	284.7	282.2	277.1	274.5	269.4	264.4
35°	216.1	213.5	218.6	221.2	223.7	226.2	228.8	231.3	231.3	233.9	233.9
37.5°	208.4	205.9	205.9	203.4	203.4	203.4	203.4	203.4	200.8	200.8	203.4
40°	198.3	195.7	195.7	193.2	193.2	190.6	190.6	190.6	190.6	190.6	190.6
42.5°	190.6	188.1	188.1	188.1	188.1	185.6	185.6	183.0	183.0	180.5	180.5
45°	188.1	185.6	183.0	180.5	180.5	177.9	177.9	177.9	175.4	175.4	175.4
47.5°	177.9	175.4	175.4	172.9	172.9	170.3	170.3	170.3	167.8	167.8	167.8
50°	172.9	170.3	170.3	167.8	167.8	165.2	165.2	165.2	162.7	162.7	162.7
52.5°	165.2	162.7	162.7	162.7	160.1	157.6	157.6	157.6	155.1	155.1	155.1
55°	157.6	155.1	155.1	155.1	152.5	150.0	150.0	150.0	147.4	147.4	147.4
57.5°	147.4	144.9	144.9	142.3	142.3	142.3	142.3	142.3	139.8	139.8	139.8
60°	139.8	137.3	137.3	134.7	134.7	132.2	132.2	132.2	132.2	132.2	132.2
62.5°	132.2	129.6	127.1	124.6	127.1	127.1	127.1	127.1	124.6	124.6	124.6
65°	124.6	122.0	119.5	116.9	116.9	116.9	116.9	116.9	116.9	116.9	116.9
67.5°	114.4	111.8	109.3	106.8	109.3	109.3	109.3	109.3	109.3	109.3	109.3
70°	104.2	101.7	101.7	99.1	99.1	96.6	96.6	99.1	99.1	99.1	99.1
72.5°	94.1	91.5	91.5	89.0	89.0	89.0	89.0	89.0	89.0	89.0	89.0
75°	83.9	81.3	81.3	78.8	78.8	78.8	78.8	78.8	78.8	78.8	78.8
77.5°	71.2	68.6	68.6	68.6	68.6	68.6	68.6	71.2	71.2	71.2	71.2
80°	61.0	58.5	58.5	58.5	58.5	58.5	58.5	58.5	58.5	58.5	58.5
82.5°	48.3	45.8	45.8	45.8	45.8	45.8	45.8	45.8	45.8	45.8	45.8
85°	35.6	33.0	33.0	33.0	35.6	35.6	35.6	35.6	35.6	35.6	35.6
87.5°	22.9	20.3	20.3	20.3	22.9	22.9	22.9	22.9	20.3	20.3	20.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2
2.5°	1601.4	1601.4	1601.4	1598.9	1596.4	1593.8	1591.3	1598.9	1604.0	1611.6	1616.7
5°	1301.5	1306.6	1309.1	1316.7	1324.4	1332.0	1339.6	1344.7	1349.8	1352.3	1357.4
7.5°	981.2	993.9	1004.1	1014.2	1024.4	1032.0	1042.2	1049.8	1057.5	1065.1	1072.7
10°	744.8	749.9	752.4	762.6	770.2	780.4	788.0	795.6	803.3	808.3	816.0
12.5°	605.0	599.9	597.4	597.4	597.4	597.4	597.4	602.4	607.5	612.6	617.7
15°	488.1	485.5	483.0	480.4	477.9	472.8	470.3	475.3	480.4	485.5	490.6
17.5°	409.3	409.3	409.3	406.7	404.2	401.6	399.1	401.6	404.2	404.2	406.7
20°	350.8	353.3	355.9	358.4	358.4	361.0	361.0	363.5	366.0	366.0	368.6
22.5°	315.2	317.7	317.7	317.7	320.3	320.3	320.3	322.8	325.4	327.9	330.5
25°	287.2	287.2	284.7	284.7	287.2	287.2	287.2	287.2	289.8	289.8	289.8
27.5°	272.0	269.4	269.4	269.4	269.4	266.9	266.9	266.9	266.9	266.9	266.9
30°	264.4	261.8	259.3	256.7	256.7	254.2	251.7	251.7	251.7	251.7	251.7
32.5°	261.8	256.7	251.7	249.1	249.1	246.6	244.0	241.5	241.5	238.9	236.4
35°	233.9	231.3	231.3	228.8	226.2	223.7	221.2	221.2	221.2	218.6	218.6
37.5°	203.4	205.9	205.9	205.9	208.4	208.4	208.4	208.4	211.0	211.0	211.0
40°	190.6	190.6	190.6	193.2	195.7	195.7	198.3	198.3	200.8	200.8	200.8
42.5°	180.5	177.9	177.9	180.5	180.5	183.0	183.0	185.6	188.1	188.1	190.6
45°	175.4	172.9	172.9	172.9	172.9	170.3	170.3	172.9	175.4	177.9	180.5
47.5°	165.2	165.2	162.7	162.7	162.7	162.7	162.7	162.7	165.2	165.2	165.2
50°	160.1	160.1	157.6	157.6	157.6	157.6	157.6	157.6	157.6	157.6	157.6
52.5°	155.1	152.5	152.5	152.5	152.5	150.0	150.0	150.0	150.0	150.0	150.0
55°	147.4	144.9	144.9	144.9	144.9	144.9	144.9	144.9	147.4	147.4	147.4
57.5°	139.8	137.3	137.3	137.3	139.8	139.8	139.8	139.8	142.3	142.3	142.3
60°	132.2	132.2	132.2	132.2	132.2	132.2	132.2	134.7	134.7	137.3	137.3
62.5°	124.6	124.6	124.6	124.6	127.1	127.1	127.1	127.1	129.6	129.6	129.6
65°	116.9	116.9	116.9	116.9	119.5	119.5	119.5	119.5	119.5	119.5	119.5
67.5°	109.3	109.3	109.3	109.3	109.3	109.3	109.3	111.8	111.8	114.4	114.4
70°	99.1	96.6	96.6	99.1	99.1	101.7	101.7	104.2	104.2	106.8	106.8
72.5°	89.0	89.0	89.0	89.0	89.0	89.0	89.0	91.5	94.1	94.1	96.6
75°	78.8	78.8	78.8	78.8	81.3	81.3	81.3	83.9	83.9	86.4	86.4
77.5°	71.2	68.6	68.6	68.6	71.2	71.2	71.2	73.7	73.7	76.3	76.3
80°	58.5	58.5	58.5	58.5	61.0	61.0	61.0	61.0	63.5	63.5	63.5
82.5°	48.3	48.3	48.3	48.3	48.3	48.3	48.3	48.3	50.8	50.8	50.8
85°	35.6	35.6	35.6	35.6	38.1	38.1	38.1	38.1	38.1	38.1	38.1
87.5°	22.9	22.9	22.9	22.9	22.9	22.9	22.9	22.9	25.4	25.4	25.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993
 CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2
2.5°	1616.7	1616.7	1616.7	1616.7	1621.8	1624.3	1629.4	1631.9	1629.4	1626.9	1621.8
5°	1359.9	1362.5	1362.5	1365.0	1365.0	1365.0	1365.0	1365.0	1370.1	1375.2	1380.3
7.5°	1075.2	1077.8	1080.3	1082.9	1082.9	1082.9	1080.3	1080.3	1082.9	1082.9	1085.4
10°	823.6	833.8	841.4	849.0	843.9	836.3	831.2	823.6	823.6	823.6	821.1
12.5°	622.8	625.3	630.4	632.9	630.4	630.4	627.9	625.3	627.9	632.9	635.5
15°	493.1	493.1	495.7	495.7	498.2	500.8	500.8	503.3	508.4	510.9	516.0
17.5°	409.3	411.8	411.8	414.3	414.3	416.9	416.9	416.9	422.0	427.0	434.7
20°	368.6	368.6	368.6	368.6	368.6	366.0	366.0	363.5	366.0	371.1	373.7
22.5°	330.5	333.0	333.0	333.0	330.5	327.9	322.8	320.3	320.3	322.8	322.8
25°	289.8	287.2	287.2	284.7	284.7	287.2	287.2	287.2	289.8	289.8	292.3
27.5°	266.9	264.4	264.4	261.8	261.8	264.4	264.4	264.4	264.4	264.4	264.4
30°	249.1	249.1	246.6	244.0	246.6	246.6	249.1	249.1	251.7	251.7	254.2
32.5°	236.4	233.9	233.9	231.3	233.9	233.9	236.4	236.4	238.9	241.5	241.5
35°	218.6	218.6	218.6	218.6	218.6	218.6	216.1	216.1	216.1	216.1	216.1
37.5°	208.4	208.4	205.9	203.4	203.4	203.4	203.4	203.4	200.8	198.3	195.7
40°	200.8	198.3	198.3	195.7	193.2	193.2	190.6	188.1	188.1	185.6	185.6
42.5°	190.6	188.1	188.1	185.6	183.0	183.0	180.5	177.9	177.9	177.9	175.4
45°	177.9	177.9	175.4	172.9	172.9	172.9	170.3	170.3	170.3	170.3	167.8
47.5°	165.2	165.2	162.7	162.7	162.7	162.7	160.1	160.1	160.1	160.1	160.1
50°	157.6	157.6	157.6	157.6	157.6	157.6	155.1	155.1	155.1	155.1	155.1
52.5°	150.0	150.0	150.0	150.0	150.0	150.0	150.0	150.0	150.0	150.0	150.0
55°	147.4	147.4	147.4	147.4	147.4	147.4	144.9	144.9	144.9	147.4	147.4
57.5°	142.3	142.3	139.8	139.8	139.8	139.8	139.8	139.8	139.8	139.8	139.8
60°	137.3	137.3	137.3	137.3	137.3	137.3	137.3	137.3	137.3	137.3	137.3
62.5°	129.6	129.6	129.6	129.6	129.6	132.2	132.2	132.2	132.2	132.2	129.6
65°	119.5	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0	122.0
67.5°	114.4	114.4	114.4	114.4	114.4	114.4	114.4	114.4	114.4	114.4	114.4
70°	106.8	106.8	104.2	104.2	104.2	106.8	106.8	106.8	106.8	106.8	106.8
72.5°	96.6	96.6	96.6	96.6	96.6	96.6	96.6	96.6	96.6	99.1	99.1
75°	86.4	86.4	86.4	86.4	86.4	86.4	86.4	86.4	86.4	86.4	86.4
77.5°	76.3	76.3	73.7	73.7	73.7	76.3	76.3	76.3	76.3	78.8	78.8
80°	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.5	66.1	66.1
82.5°	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8	50.8	53.4	53.4
85°	38.1	40.7	40.7	40.7	40.7	40.7	40.7	40.7	40.7	43.2	43.2
87.5°	25.4	25.4	25.4	25.4	25.4	25.4	22.9	22.9	22.9	22.9	20.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993
 CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2
2.5°	1619.2	1621.8	1624.3	1624.3	1626.9	1629.4	1629.4	1639.6	1649.7	1654.8	1659.9
5°	1385.4	1382.8	1382.8	1380.3	1377.7	1385.4	1393.0	1408.2	1423.5	1426.0	1431.1
7.5°	1085.4	1088.0	1090.5	1090.5	1093.0	1085.4	1075.2	1077.8	1080.3	1093.0	1103.2
10°	821.1	823.6	826.1	826.1	828.7	826.1	821.1	828.7	836.3	846.5	859.2
12.5°	638.0	645.7	653.3	658.4	666.0	671.1	673.6	683.8	691.4	704.1	716.8
15°	521.1	526.2	531.3	536.4	541.4	546.5	551.6	561.8	571.9	587.2	602.4
17.5°	439.8	439.8	442.3	442.3	442.3	447.4	452.5	457.6	460.1	475.3	490.6
20°	376.2	373.7	371.1	368.6	366.0	371.1	373.7	376.2	378.8	388.9	396.5
22.5°	322.8	322.8	325.4	325.4	325.4	322.8	317.7	320.3	320.3	325.4	333.0
25°	292.3	292.3	292.3	289.8	289.8	292.3	294.9	294.9	292.3	294.9	297.4
27.5°	264.4	266.9	266.9	269.4	269.4	272.0	272.0	272.0	272.0	274.5	277.1
30°	254.2	254.2	256.7	256.7	256.7	259.3	261.8	261.8	261.8	264.4	269.4
32.5°	244.0	246.6	249.1	251.7	254.2	256.7	256.7	259.3	259.3	261.8	264.4
35°	216.1	213.5	213.5	211.0	208.4	208.4	208.4	208.4	205.9	208.4	208.4
37.5°	193.2	193.2	193.2	190.6	190.6	193.2	193.2	193.2	193.2	195.7	195.7
40°	183.0	183.0	183.0	183.0	183.0	183.0	183.0	185.6	185.6	188.1	190.6
42.5°	175.4	175.4	175.4	175.4	175.4	177.9	177.9	177.9	177.9	180.5	180.5
45°	167.8	167.8	167.8	167.8	167.8	167.8	167.8	170.3	170.3	172.9	175.4
47.5°	160.1	160.1	160.1	160.1	160.1	162.7	165.2	165.2	165.2	167.8	167.8
50°	155.1	155.1	155.1	155.1	155.1	157.6	157.6	160.1	160.1	162.7	165.2
52.5°	150.0	150.0	150.0	150.0	150.0	152.5	152.5	155.1	155.1	157.6	160.1
55°	147.4	147.4	147.4	144.9	144.9	147.4	147.4	150.0	150.0	152.5	152.5
57.5°	139.8	139.8	139.8	139.8	139.8	139.8	139.8	142.3	142.3	144.9	147.4
60°	137.3	137.3	134.7	134.7	132.2	134.7	134.7	137.3	137.3	139.8	139.8
62.5°	129.6	129.6	129.6	127.1	127.1	129.6	129.6	129.6	129.6	132.2	134.7
65°	122.0	122.0	122.0	119.5	119.5	122.0	122.0	122.0	122.0	124.6	127.1
67.5°	114.4	114.4	114.4	111.8	111.8	111.8	111.8	114.4	114.4	116.9	119.5
70°	106.8	106.8	106.8	104.2	104.2	104.2	101.7	104.2	106.8	109.3	109.3
72.5°	99.1	99.1	99.1	96.6	96.6	96.6	94.1	96.6	96.6	99.1	99.1
75°	86.4	86.4	86.4	86.4	86.4	86.4	83.9	83.9	83.9	86.4	86.4
77.5°	78.8	78.8	78.8	76.3	76.3	76.3	73.7	73.7	73.7	76.3	76.3
80°	66.1	66.1	66.1	63.5	63.5	63.5	61.0	61.0	61.0	63.5	63.5
82.5°	53.4	53.4	53.4	50.8	50.8	50.8	48.3	48.3	48.3	50.8	50.8
85°	43.2	43.2	43.2	43.2	43.2	43.2	40.7	40.7	40.7	43.2	45.8
87.5°	20.3	20.3	22.9	22.9	22.9	22.9	20.3	20.3	17.8	17.8	20.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2
2.5°	1665.0	1670.1	1682.8	1692.9	1705.7	1715.8	1723.4	1733.6	1741.2	1748.9	1754.0
5°	1433.7	1436.2	1448.9	1461.6	1471.8	1484.5	1502.3	1520.1	1537.9	1555.7	1568.4
7.5°	1115.9	1126.1	1141.3	1159.1	1174.4	1189.6	1207.4	1227.8	1245.6	1263.4	1281.1
10°	869.4	879.5	894.8	910.0	922.7	938.0	958.3	978.7	999.0	1019.3	1039.7
12.5°	729.5	742.3	760.0	777.8	793.1	810.9	836.3	859.2	884.6	907.5	932.9
15°	615.2	630.4	653.3	678.7	701.6	724.5	749.9	775.3	798.2	823.6	849.0
17.5°	505.9	521.1	541.4	564.3	584.7	605.0	635.5	663.5	694.0	721.9	749.9
20°	406.7	414.3	434.7	455.0	475.3	495.7	518.6	541.4	564.3	587.2	622.8
22.5°	338.1	343.2	353.3	361.0	371.1	378.8	401.6	424.5	444.8	467.7	500.8
25°	297.4	300.0	307.6	312.7	320.3	325.4	340.6	353.3	368.6	381.3	411.8
27.5°	277.1	279.6	282.2	284.7	287.2	289.8	300.0	310.1	317.7	327.9	355.9
30°	272.0	274.5	282.2	287.2	294.9	300.0	305.0	310.1	315.2	320.3	338.1
32.5°	266.9	269.4	269.4	266.9	266.9	264.4	269.4	272.0	277.1	279.6	294.9
35°	211.0	211.0	213.5	216.1	218.6	221.2	228.8	233.9	241.5	246.6	259.3
37.5°	198.3	198.3	200.8	205.9	208.4	211.0	216.1	221.2	226.2	231.3	244.0
40°	190.6	193.2	195.7	198.3	200.8	203.4	208.4	211.0	216.1	218.6	228.8
42.5°	183.0	183.0	185.6	190.6	193.2	195.7	200.8	203.4	208.4	211.0	221.2
45°	177.9	180.5	183.0	185.6	185.6	188.1	193.2	198.3	200.8	205.9	216.1
47.5°	170.3	170.3	175.4	177.9	183.0	185.6	190.6	193.2	198.3	200.8	211.0
50°	165.2	167.8	172.9	175.4	180.5	183.0	190.6	195.7	203.4	208.4	213.5
52.5°	160.1	162.7	167.8	170.3	175.4	177.9	188.1	198.3	205.9	216.1	216.1
55°	155.1	155.1	160.1	167.8	172.9	177.9	183.0	190.6	195.7	200.8	200.8
57.5°	147.4	150.0	155.1	162.7	167.8	172.9	177.9	183.0	185.6	190.6	188.1
60°	142.3	142.3	150.0	157.6	165.2	172.9	172.9	172.9	170.3	170.3	170.3
62.5°	134.7	137.3	147.4	160.1	170.3	180.5	172.9	165.2	157.6	150.0	152.5
65°	129.6	132.2	137.3	144.9	150.0	155.1	150.0	147.4	142.3	137.3	139.8
67.5°	119.5	122.0	124.6	124.6	127.1	127.1	127.1	127.1	127.1	127.1	129.6
70°	111.8	111.8	111.8	114.4	114.4	114.4	114.4	114.4	114.4	114.4	116.9
72.5°	101.7	101.7	101.7	101.7	101.7	101.7	101.7	101.7	101.7	101.7	104.2
75°	89.0	89.0	89.0	89.0	89.0	89.0	89.0	89.0	89.0	89.0	91.5
77.5°	78.8	78.8	78.8	78.8	78.8	78.8	78.8	78.8	76.3	76.3	78.8
80°	66.1	66.1	66.1	66.1	63.5	63.5	63.5	63.5	63.5	63.5	66.1
82.5°	53.4	53.4	53.4	53.4	50.8	50.8	50.8	50.8	48.3	48.3	50.8
85°	48.3	50.8	50.8	53.4	53.4	53.4	50.8	48.3	45.8	43.2	43.2
87.5°	20.3	20.3	20.3	20.3	17.8	17.8	17.8	17.8	17.8	17.8	17.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993
 CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2
2.5°	1761.6	1766.7	1771.7	1779.4	1789.5	1797.2	1804.8	1820.0	1837.8	1853.1	1868.3
5°	1581.1	1593.8	1606.5	1621.8	1637.0	1649.7	1665.0	1695.5	1726.0	1754.0	1784.5
7.5°	1296.4	1314.2	1329.4	1354.9	1377.7	1403.2	1426.0	1464.2	1499.8	1537.9	1573.5
10°	1060.0	1080.3	1100.7	1133.7	1169.3	1202.3	1235.4	1265.9	1298.9	1329.4	1359.9
12.5°	958.3	981.2	1006.6	1027.0	1049.8	1070.2	1090.5	1126.1	1161.7	1197.3	1232.9
15°	874.4	899.9	925.3	950.7	973.6	999.0	1021.9	1052.4	1085.4	1115.9	1146.4
17.5°	777.8	803.3	831.2	859.2	887.1	915.1	943.1	986.3	1029.5	1070.2	1113.4
20°	655.8	691.4	724.5	762.6	800.7	838.8	877.0	922.7	968.5	1011.7	1057.5
22.5°	533.8	566.9	599.9	645.7	691.4	734.6	780.4	841.4	899.9	960.9	1019.3
25°	444.8	475.3	505.9	556.7	605.0	655.8	704.1	777.8	849.0	922.7	993.9
27.5°	383.8	411.8	439.8	493.1	546.5	597.4	650.7	732.1	810.9	892.2	971.0
30°	355.9	373.7	391.5	442.3	493.1	541.4	592.3	671.1	749.9	828.7	907.5
32.5°	310.1	325.4	340.6	386.4	432.1	475.3	521.1	602.4	681.2	762.6	841.4
35°	274.5	287.2	300.0	343.2	383.8	427.0	467.7	549.1	630.4	711.7	793.1
37.5°	254.2	266.9	277.1	315.2	355.9	394.0	432.1	513.5	592.3	673.6	752.4
40°	238.9	246.6	256.7	294.9	330.5	368.6	404.2	477.9	554.1	627.9	701.6
42.5°	228.8	238.9	246.6	279.6	315.2	348.2	381.3	452.5	523.6	592.3	663.5
45°	226.2	236.4	246.6	274.5	302.5	327.9	355.9	424.5	493.1	561.8	630.4
47.5°	221.2	228.8	238.9	261.8	282.2	305.0	325.4	394.0	462.6	528.7	597.4
50°	218.6	221.2	226.2	246.6	266.9	287.2	307.6	376.2	444.8	513.5	582.1
52.5°	216.1	216.1	216.1	233.9	251.7	266.9	284.7	353.3	424.5	493.1	561.8
55°	200.8	198.3	198.3	216.1	231.3	249.1	264.4	333.0	401.6	467.7	536.4
57.5°	185.6	183.0	180.5	195.7	211.0	226.2	241.5	310.1	381.3	449.9	518.6
60°	170.3	167.8	167.8	183.0	195.7	211.0	223.7	294.9	363.5	434.7	503.3
62.5°	152.5	155.1	155.1	167.8	183.0	195.7	208.4	279.6	353.3	424.5	495.7
65°	139.8	142.3	142.3	157.6	172.9	188.1	203.4	272.0	343.2	411.8	480.4
67.5°	129.6	132.2	132.2	150.0	165.2	183.0	198.3	259.3	322.8	383.8	444.8
70°	119.5	119.5	122.0	139.8	157.6	175.4	193.2	246.6	300.0	350.8	404.2
72.5°	106.8	109.3	111.8	129.6	144.9	162.7	177.9	226.2	274.5	322.8	371.1
75°	94.1	96.6	99.1	114.4	129.6	144.9	160.1	205.9	249.1	294.9	338.1
77.5°	83.9	86.4	89.0	101.7	114.4	127.1	139.8	172.9	208.4	241.5	274.5
80°	68.6	68.6	71.2	81.3	91.5	99.1	109.3	132.2	155.1	175.4	198.3
82.5°	50.8	53.4	53.4	61.0	66.1	73.7	78.8	91.5	101.7	114.4	124.6
85°	43.2	40.7	40.7	45.8	48.3	53.4	55.9	63.5	68.6	76.3	81.3
87.5°	17.8	15.3	15.3	17.8	22.9	25.4	28.0	28.0	30.5	30.5	30.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993
 CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2
2.5°	1876.0	1881.1	1888.7	1893.8	1906.5	1916.6	1929.3	1939.5	1947.1	1959.9	1954.8
5°	1807.3	1830.2	1853.1	1876.0	1893.8	1911.6	1926.8	1944.6	1964.9	2003.1	2013.2
7.5°	1604.0	1634.5	1662.4	1692.9	1728.5	1764.1	1799.7	1835.3	1868.3	1916.6	1947.1
10°	1403.2	1446.4	1487.0	1530.3	1563.3	1596.4	1626.9	1659.9	1705.7	1754.0	1809.9
12.5°	1276.1	1319.3	1362.5	1405.7	1454.0	1499.8	1548.1	1593.8	1637.0	1675.2	1738.7
15°	1192.2	1240.5	1286.2	1332.0	1390.5	1446.4	1504.8	1560.8	1624.3	1675.2	1718.4
17.5°	1171.8	1230.3	1286.2	1344.7	1405.7	1466.7	1527.7	1588.7	1652.3	1728.5	1784.5
20°	1136.3	1215.1	1293.9	1372.7	1451.5	1527.7	1606.5	1682.8	1766.7	1858.2	1883.6
22.5°	1115.9	1210.0	1306.6	1400.6	1507.4	1616.7	1723.4	1830.2	1919.2	1987.8	2064.1
25°	1113.4	1230.3	1349.8	1466.7	1601.4	1733.6	1868.3	2000.5	2114.9	2183.5	2244.6
27.5°	1110.8	1253.2	1393.0	1532.8	1698.0	1860.7	2025.9	2188.6	2295.4	2394.5	2445.4
30°	1080.3	1250.6	1423.5	1593.8	1779.4	1964.9	2150.5	2336.1	2445.4	2514.0	2539.4
32.5°	1042.2	1243.0	1443.8	1644.6	1855.6	2066.6	2275.1	2486.0	2572.5	2630.9	2610.6
35°	1011.7	1232.9	1451.5	1670.1	1893.8	2120.0	2343.7	2567.4	2691.9	2773.3	2740.2
37.5°	983.7	1215.1	1446.4	1677.7	1939.5	2201.3	2463.2	2725.0	2844.5	2930.9	2892.8
40°	950.7	1197.3	1446.4	1692.9	1992.9	2290.3	2590.3	2887.7	3042.7	3116.4	3058.0
42.5°	922.7	1179.5	1438.8	1695.5	2015.8	2336.1	2656.3	2976.6	3149.5	3253.7	3180.0
45°	887.1	1143.9	1398.1	1654.8	2008.1	2361.5	2712.3	3065.6	3266.4	3347.8	3246.1
47.5°	849.0	1103.2	1354.9	1606.5	1982.7	2358.9	2735.2	3111.4	3296.9	3393.5	3299.5
50°	836.3	1090.5	1342.2	1596.4	2003.1	2412.3	2819.0	3225.7	3360.5	3439.3	3314.7
52.5°	833.8	1103.2	1375.2	1644.6	2053.9	2460.6	2869.9	3276.6	3385.9	3469.8	3357.9
55°	826.1	1118.5	1408.2	1698.0	2125.1	2554.7	2981.7	3408.8	3518.1	3579.1	3495.2
57.5°	833.8	1149.0	1461.6	1776.8	2216.6	2656.3	3096.1	3535.9	3668.1	3711.3	3693.5
60°	838.8	1174.4	1507.4	1842.9	2272.5	2702.1	3131.7	3561.3	3698.6	3805.3	3825.7
62.5°	826.1	1156.6	1484.5	1815.0	2203.9	2592.8	2981.7	3370.6	3596.9	3754.5	3846.0
65°	788.0	1093.0	1400.6	1705.7	2064.1	2425.0	2783.4	3141.9	3380.8	3614.7	3688.4
67.5°	704.1	963.4	1222.7	1482.0	1794.6	2107.3	2417.4	2730.1	3030.0	3256.3	3357.9
70°	610.1	813.4	1019.3	1222.7	1507.4	1792.1	2076.8	2361.5	2625.8	2875.0	2971.6
72.5°	531.3	688.9	849.0	1006.6	1210.0	1410.8	1614.1	1815.0	2127.6	2376.7	2470.8
75°	452.5	566.9	678.7	793.1	932.9	1072.7	1210.0	1349.8	1570.9	1794.6	1888.7
77.5°	348.2	424.5	498.2	571.9	668.5	762.6	859.2	953.2	1108.3	1276.1	1324.4
80°	241.5	284.7	325.4	368.6	444.8	521.1	597.4	673.6	775.3	869.4	943.1
82.5°	150.0	177.9	203.4	228.8	289.8	350.8	409.3	470.3	510.9	516.0	589.7
85°	96.6	114.4	129.6	144.9	180.5	218.6	254.2	289.8	259.3	241.5	287.2
87.5°	38.1	48.3	55.9	63.5	61.0	58.5	55.9	53.4	45.8	40.7	50.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993
 CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2
2.5°	1959.9	1967.5	1975.1	1980.2	1987.8	1990.4	1992.9	1992.9	1995.4	1998.0	2003.1
5°	2053.9	2069.2	2084.4	2097.1	2112.4	2125.1	2135.2	2148.0	2158.1	2158.1	2155.6
7.5°	1975.1	2013.2	2051.4	2089.5	2127.6	2155.6	2181.0	2209.0	2234.4	2239.5	2244.6
10°	1870.9	1911.6	1949.7	1990.4	2028.5	2071.7	2112.4	2153.0	2196.3	2203.9	2214.0
12.5°	1774.3	1822.6	1870.9	1916.6	1964.9	1995.4	2025.9	2053.9	2084.4	2104.7	2125.1
15°	1771.7	1812.4	1853.1	1891.2	1931.9	1949.7	1967.5	1982.7	2000.5	2000.5	2003.1
17.5°	1830.2	1855.6	1881.1	1903.9	1929.3	1931.9	1937.0	1939.5	1942.1	1934.4	1926.8
20°	1944.6	1954.8	1964.9	1975.1	1985.3	1967.5	1952.2	1934.4	1916.6	1896.3	1878.5
22.5°	2112.4	2089.5	2066.6	2043.7	2020.9	1990.4	1957.3	1926.8	1893.8	1868.3	1842.9
25°	2270.0	2242.0	2214.0	2186.1	2158.1	2092.0	2025.9	1957.3	1891.2	1863.3	1835.3
27.5°	2481.0	2437.7	2394.5	2351.3	2308.1	2219.1	2130.2	2041.2	1952.2	1903.9	1858.2
30°	2531.8	2483.5	2435.2	2384.4	2336.1	2249.6	2165.8	2079.3	1992.9	1937.0	1883.6
32.5°	2605.5	2549.6	2493.7	2437.7	2381.8	2297.9	2214.0	2127.6	2043.7	1992.9	1939.5
35°	2727.5	2664.0	2600.4	2534.3	2470.8	2384.4	2300.5	2214.0	2127.6	2069.2	2013.2
37.5°	2831.7	2758.0	2684.3	2610.6	2536.9	2460.6	2381.8	2305.6	2226.8	2168.3	2112.4
40°	2948.7	2867.3	2786.0	2707.2	2625.8	2554.7	2483.5	2409.8	2338.6	2292.8	2247.1
42.5°	3050.4	2951.2	2854.6	2758.0	2658.9	2610.6	2564.8	2516.5	2468.2	2445.4	2419.9
45°	3121.5	3030.0	2936.0	2844.5	2752.9	2717.4	2681.8	2646.2	2610.6	2633.5	2656.3
47.5°	3152.0	3078.3	3007.1	2936.0	2862.2	2875.0	2887.7	2897.8	2910.5	2941.0	2974.1
50°	3180.0	3139.3	3096.1	3055.4	3012.2	3060.5	3106.3	3154.6	3202.9	3266.4	3330.0
52.5°	3235.9	3213.0	3192.7	3169.8	3146.9	3230.8	3314.7	3398.6	3482.5	3553.7	3624.8
55°	3403.7	3385.9	3368.1	3347.8	3330.0	3449.4	3566.4	3685.8	3805.3	3879.0	3952.8
57.5°	3635.0	3624.8	3612.1	3602.0	3589.2	3706.2	3820.6	3935.0	4051.9	4123.1	4196.8
60°	3810.4	3812.9	3812.9	3815.5	3815.5	3904.5	3993.4	4084.9	4173.9	4234.9	4298.5
62.5°	3904.5	3899.4	3894.3	3889.2	3884.1	3957.8	4031.6	4105.3	4179.0	4224.7	4270.5
65°	3802.8	3830.7	3858.7	3886.7	3914.6	3924.8	3932.4	3942.6	3950.2	3978.2	4006.1
67.5°	3462.2	3518.1	3571.5	3627.4	3680.8	3642.6	3607.0	3568.9	3530.8	3538.4	3543.5
70°	3083.4	3146.9	3213.0	3276.6	3340.1	3251.2	3162.2	3070.7	2981.7	2951.2	2920.7
72.5°	2600.4	2656.3	2714.8	2770.7	2826.7	2717.4	2610.6	2501.3	2392.0	2338.6	2285.2
75°	1987.8	2053.9	2122.5	2188.6	2254.7	2132.7	2008.1	1886.1	1761.6	1726.0	1692.9
77.5°	1448.9	1527.7	1606.5	1685.3	1764.1	1654.8	1545.5	1433.7	1324.4	1304.0	1283.7
80°	1054.9	1115.9	1174.4	1235.4	1293.9	1230.3	1166.8	1103.2	1039.7	1037.1	1034.6
82.5°	711.7	765.1	816.0	869.4	920.2	894.8	871.9	846.5	821.1	846.5	874.4
85°	366.0	439.8	516.0	589.7	663.5	655.8	650.7	643.1	635.5	668.5	699.0
87.5°	73.7	137.3	200.8	261.8	325.4	310.1	294.9	277.1	261.8	272.0	279.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993
 CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2
2.5°	2005.6	2008.1	2008.1	2008.1	2008.1	2008.1	2003.1	2000.5	1995.4	1990.4	1982.7
5°	2155.6	2153.0	2142.9	2132.7	2120.0	2109.8	2102.2	2092.0	2084.4	2074.2	2059.0
7.5°	2249.6	2254.7	2236.9	2221.7	2203.9	2186.1	2168.3	2150.5	2132.7	2114.9	2079.3
10°	2221.7	2229.3	2219.1	2209.0	2196.3	2186.1	2165.8	2142.9	2122.5	2099.7	2056.4
12.5°	2142.9	2163.2	2158.1	2153.0	2148.0	2142.9	2130.2	2114.9	2102.2	2087.0	2038.7
15°	2003.1	2003.1	2005.6	2008.1	2008.1	2010.7	2013.2	2015.8	2018.3	2020.9	1992.9
17.5°	1919.2	1911.6	1911.6	1911.6	1911.6	1911.6	1921.7	1934.4	1944.6	1954.8	1947.1
20°	1858.2	1840.4	1837.8	1837.8	1835.3	1832.8	1850.5	1870.9	1888.7	1906.5	1916.6
22.5°	1817.5	1792.1	1789.5	1787.0	1784.5	1781.9	1804.8	1827.7	1850.5	1873.4	1909.0
25°	1807.3	1779.4	1781.9	1784.5	1784.5	1787.0	1804.8	1822.6	1840.4	1858.2	1919.2
27.5°	1809.9	1764.1	1766.7	1769.2	1769.2	1771.7	1799.7	1825.1	1853.1	1878.5	1954.8
30°	1827.7	1774.3	1769.2	1764.1	1759.0	1754.0	1792.1	1830.2	1868.3	1906.5	1964.9
32.5°	1888.7	1837.8	1825.1	1812.4	1799.7	1787.0	1832.8	1876.0	1921.7	1964.9	2013.2
35°	1954.8	1898.8	1893.8	1888.7	1881.1	1876.0	1916.6	1959.9	2000.5	2041.2	2084.4
37.5°	2053.9	1998.0	1992.9	1985.3	1980.2	1972.6	2018.3	2061.5	2107.3	2150.5	2188.6
40°	2201.3	2155.6	2153.0	2153.0	2150.5	2148.0	2183.5	2221.7	2257.3	2292.8	2318.3
42.5°	2397.1	2374.2	2381.8	2392.0	2399.6	2407.2	2435.2	2465.7	2493.7	2521.6	2514.0
45°	2679.2	2702.1	2704.6	2707.2	2709.7	2712.3	2719.9	2730.1	2737.7	2745.3	2714.8
47.5°	3004.6	3035.1	3050.4	3065.6	3078.3	3093.6	3083.4	3070.7	3060.5	3047.8	2971.6
50°	3391.0	3454.5	3452.0	3449.4	3444.4	3441.8	3421.5	3401.1	3378.3	3357.9	3246.1
52.5°	3696.0	3767.2	3779.9	3792.6	3805.3	3818.0	3779.9	3741.8	3701.1	3663.0	3523.2
55°	4023.9	4097.6	4100.2	4102.7	4102.7	4105.3	4051.9	3998.5	3942.6	3889.2	3744.3
57.5°	4268.0	4339.1	4331.5	4326.4	4318.8	4311.2	4247.6	4184.1	4120.5	4057.0	3912.1
60°	4359.5	4420.5	4405.2	4390.0	4372.2	4356.9	4308.6	4260.3	4209.5	4161.2	4021.4
62.5°	4316.3	4362.0	4339.1	4318.8	4295.9	4273.0	4212.0	4148.5	4087.5	4023.9	3922.2
65°	4031.6	4059.5	4029.0	4001.0	3973.1	3942.6	3891.7	3840.9	3787.5	3736.7	3668.1
67.5°	3551.1	3556.2	3553.7	3551.1	3548.6	3546.0	3472.3	3398.6	3322.3	3248.6	3243.5
70°	2892.8	2862.2	2867.3	2875.0	2880.0	2885.1	2829.2	2775.8	2719.9	2664.0	2689.4
72.5°	2231.8	2178.5	2191.2	2206.4	2219.1	2231.8	2186.1	2142.9	2097.1	2051.4	2087.0
75°	1657.4	1624.3	1637.0	1652.3	1665.0	1677.7	1659.9	1642.1	1621.8	1604.0	1637.0
77.5°	1263.4	1243.0	1245.6	1245.6	1248.1	1248.1	1250.6	1255.7	1258.3	1260.8	1296.4
80°	1029.5	1027.0	1024.4	1021.9	1016.8	1014.2	1039.7	1065.1	1090.5	1115.9	1133.7
82.5°	899.9	925.3	910.0	897.3	882.1	866.8	889.7	912.6	935.4	958.3	950.7
85°	732.1	762.6	734.6	706.7	676.2	648.2	668.5	686.3	706.7	724.5	714.3
87.5°	289.8	297.4	251.7	208.4	162.7	116.9	185.6	251.7	320.3	386.4	396.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993
 CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2	1830.2
2.5°	1975.1	1964.9	1957.3	1954.8	1949.7	1947.1	1942.1	1937.0	1929.3	1924.3	1916.6
5°	2041.2	2025.9	2008.1	1982.7	1959.9	1934.4	1909.0	1886.1	1863.3	1837.8	1815.0
7.5°	2043.7	2008.1	1972.6	1939.5	1903.9	1870.9	1835.3	1804.8	1771.7	1738.7	1708.2
10°	2015.8	1972.6	1929.3	1886.1	1845.5	1802.3	1759.0	1723.4	1685.3	1647.2	1611.6
12.5°	1992.9	1944.6	1896.3	1845.5	1797.2	1746.3	1695.5	1659.9	1624.3	1588.7	1553.1
15°	1964.9	1934.4	1906.5	1860.7	1815.0	1769.2	1723.4	1675.2	1629.4	1581.1	1532.8
17.5°	1942.1	1934.4	1926.8	1896.3	1865.8	1832.8	1802.3	1754.0	1705.7	1654.8	1606.5
20°	1929.3	1939.5	1949.7	1934.4	1919.2	1901.4	1886.1	1850.5	1815.0	1776.8	1741.2
22.5°	1944.6	1982.7	2018.3	2020.9	2025.9	2028.5	2031.0	1998.0	1964.9	1929.3	1896.3
25°	1980.2	2041.2	2102.2	2135.2	2168.3	2203.9	2236.9	2216.6	2196.3	2175.9	2155.6
27.5°	2028.5	2104.7	2181.0	2229.3	2275.1	2323.4	2371.7	2369.1	2366.6	2361.5	2358.9
30°	2020.9	2079.3	2137.8	2196.3	2254.7	2313.2	2371.7	2402.2	2430.1	2460.6	2491.1
32.5°	2064.1	2112.4	2163.2	2224.2	2285.2	2348.8	2409.8	2473.3	2534.3	2597.9	2661.4
35°	2130.2	2173.4	2219.1	2285.2	2353.9	2419.9	2488.6	2564.8	2643.6	2722.4	2798.7
37.5°	2229.3	2267.4	2308.1	2364.0	2422.5	2478.4	2536.9	2648.7	2760.6	2875.0	2986.8
40°	2343.7	2369.1	2394.5	2447.9	2501.3	2554.7	2608.1	2747.9	2887.7	3027.5	3167.3
42.5°	2508.9	2501.3	2493.7	2536.9	2582.6	2625.8	2671.6	2798.7	2925.8	3052.9	3180.0
45°	2684.3	2653.8	2623.3	2643.6	2666.5	2686.9	2709.7	2839.4	2969.0	3101.2	3230.8
47.5°	2895.3	2819.0	2742.8	2725.0	2707.2	2686.9	2669.1	2808.9	2948.7	3091.0	3230.8
50°	3134.2	3019.9	2908.0	2862.2	2814.0	2768.2	2719.9	2834.3	2951.2	3068.1	3182.5
52.5°	3383.4	3241.0	3101.2	3030.0	2958.8	2885.1	2814.0	2910.5	3009.7	3108.8	3205.4
55°	3596.9	3452.0	3304.5	3220.7	3136.8	3052.9	2969.0	3065.6	3162.2	3258.8	3355.4
57.5°	3767.2	3622.3	3477.4	3398.6	3317.3	3238.5	3157.1	3248.6	3342.7	3436.7	3528.2
60°	3884.1	3744.3	3604.5	3528.2	3452.0	3375.7	3299.5	3408.8	3518.1	3629.9	3739.2
62.5°	3823.1	3721.4	3619.8	3586.7	3553.7	3518.1	3485.0	3589.2	3690.9	3795.1	3899.4
65°	3599.4	3530.8	3462.2	3495.2	3530.8	3563.8	3599.4	3668.1	3736.7	3807.9	3876.5
67.5°	3235.9	3230.8	3223.2	3296.9	3370.6	3446.9	3520.6	3566.4	3609.6	3655.3	3701.1
70°	2714.8	2742.8	2768.2	2895.3	3022.4	3149.5	3276.6	3294.4	3312.2	3330.0	3347.8
72.5°	2125.1	2160.7	2198.8	2366.6	2531.8	2699.6	2867.3	2857.2	2847.0	2834.3	2824.1
75°	1672.6	1705.7	1741.2	1896.3	2051.4	2206.4	2361.5	2318.3	2277.6	2234.4	2191.2
77.5°	1334.5	1370.1	1408.2	1553.1	1698.0	1845.5	1990.4	1886.1	1781.9	1677.7	1573.5
80°	1149.0	1166.8	1182.0	1281.1	1377.7	1476.9	1576.0	1469.3	1359.9	1250.6	1143.9
82.5°	943.1	932.9	925.3	983.7	1042.2	1100.7	1159.1	1057.5	955.8	851.6	749.9
85°	704.1	694.0	683.8	714.3	744.8	777.8	808.3	691.4	574.5	455.0	338.1
87.5°	409.3	419.4	429.6	462.6	495.7	531.3	564.3	444.8	325.4	203.4	83.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993
 CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P675993
 CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	1830.2	1830.2
2.5°	1901.4	1888.7
5°	1797.2	1779.4
7.5°	1682.8	1659.9
10°	1578.6	1548.1
12.5°	1512.5	1474.3
15°	1487.0	1441.3
17.5°	1563.3	1520.1
20°	1680.2	1621.8
22.5°	1822.6	1751.4
25°	2069.2	1982.7
27.5°	2270.0	2181.0
30°	2394.5	2297.9
32.5°	2531.8	2404.7
35°	2674.1	2552.1
37.5°	2847.0	2709.7
40°	3024.9	2882.6
42.5°	3085.9	2994.4
45°	3144.4	3058.0
47.5°	3157.1	3085.9
50°	3169.8	3159.7
52.5°	3205.4	3202.9
55°	3357.9	3360.5
57.5°	3546.0	3561.3
60°	3718.9	3701.1
62.5°	3807.9	3716.3
65°	3746.9	3619.8
67.5°	3563.8	3426.6
70°	3162.2	2976.6
72.5°	2661.4	2498.7
75°	2051.4	1914.1
77.5°	1459.1	1344.7
80°	1027.0	912.6
82.5°	658.4	566.9
85°	297.4	259.3
87.5°	83.9	81.3
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P675993

CATALOG NUMBER: CCW-SA-2B-740-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)