

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: INVUE

Report Number: P676002

Luminaire Tested: **CCW-SA-1F-750-U-SLR**

Issue Date: 04/25/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P676002  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 04/25/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: INVUE  
Catalog Number: CCW-SA-1F-750-U-SLR  
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @1200mA w/  
SLR distribution lens  
Light Source: (16) 5000K CCT, 70 CRI LEDs  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6364.6 lumens  
Efficiency: N/A  
Efficacy: 95.0 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B1 - U0 - G2


Input Watts (W): 67  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 9 fc

Type IV - Short - N/A

REPORT NUMBER: P676002  
CATALOG NUMBER: CCW-SA-1F-750-U-SLR

## Luminous Intensity Polar Plot



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 1309.6   | 0.0    | 1309.6 |
|                    | % Fixture | 20.6     | 0.0    | 20.6   |
| <b>Street Side</b> | Lumens    | 5055.0   | 0.0    | 5055.0 |
|                    | % Fixture | 79.4     | 0.0    | 79.4   |
| <b>Total</b>       | Lumens    | 6364.6   | 0.0    | 6364.6 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 157.9  | 2.5       |
| 10°-20°   | 333.4  | 5.2       |
| 20°-30°   | 487.8  | 7.7       |
| 30°-40°   | 687.3  | 10.8      |
| 40°-50°   | 944.4  | 14.8      |
| 50°-60°   | 1287.3 | 20.2      |
| 60°-70°   | 1408.9 | 22.1      |
| 70°-80°   | 813.6  | 12.8      |
| 80°-90°   | 243.9  | 3.8       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 6364.6 | 100.0     |
| 0°-180°   | 6364.6 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P676002


CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 653.7  | 10.3      |                         |      |         |
| FM   | (30°-60°)   | 2322.6 | 36.5      |                         |      |         |
| FH   | (60°-80°)   | 1871.6 | 29.4      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 207.2  | 3.3       |                         |      | G2/225  |
| BL   | (0°-30°)    | 325.6  | 5.1       | B1/500                  |      |         |
| BM   | (30°-60°)   | 596.3  | 9.4       | B1/1000                 |      |         |
| BH   | (60°-80°)   | 351.0  | 5.5       | B1/500                  |      | G1/500  |
| BVH  | (80°-90°)   | 36.7   | 0.6       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B1-U0-G2**

Type IV Short



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5°  | 25°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 |
| 2.5°   | 2097.4 | 2086.1 | 2077.6 | 2069.2 | 2057.9 | 2049.4 | 2038.1 | 2026.8 | 2012.7 | 2001.4 | 1987.3 |
| 5°     | 1976.0 | 1942.1 | 1908.3 | 1888.5 | 1865.9 | 1846.2 | 1823.6 | 1798.2 | 1772.8 | 1744.5 | 1719.1 |
| 7.5°   | 1843.3 | 1801.0 | 1758.6 | 1724.8 | 1688.1 | 1654.2 | 1617.5 | 1586.4 | 1555.4 | 1524.3 | 1493.3 |
| 10°    | 1719.1 | 1679.6 | 1640.1 | 1597.7 | 1552.6 | 1510.2 | 1465.1 | 1422.7 | 1380.4 | 1338.0 | 1295.7 |
| 12.5°  | 1637.3 | 1589.3 | 1544.1 | 1496.1 | 1451.0 | 1403.0 | 1355.0 | 1315.5 | 1275.9 | 1233.6 | 1194.1 |
| 15°    | 1600.6 | 1555.4 | 1513.1 | 1465.1 | 1417.1 | 1369.1 | 1321.1 | 1275.9 | 1233.6 | 1188.4 | 1143.3 |
| 17.5°  | 1688.1 | 1623.1 | 1558.2 | 1496.1 | 1434.0 | 1371.9 | 1309.8 | 1253.4 | 1196.9 | 1140.4 | 1084.0 |
| 20°    | 1801.0 | 1719.1 | 1640.1 | 1563.9 | 1484.8 | 1408.6 | 1329.6 | 1250.5 | 1171.5 | 1092.4 | 1013.4 |
| 22.5°  | 1945.0 | 1851.8 | 1761.5 | 1662.7 | 1561.0 | 1462.2 | 1360.6 | 1261.8 | 1163.0 | 1061.4 | 962.6  |
| 25°    | 2201.8 | 2091.7 | 1981.6 | 1840.5 | 1696.5 | 1555.4 | 1411.4 | 1281.6 | 1154.6 | 1024.7 | 894.8  |
| 27.5°  | 2422.0 | 2272.4 | 2125.6 | 1956.2 | 1786.9 | 1617.5 | 1448.1 | 1298.5 | 1151.7 | 1002.1 | 852.5  |
| 30°    | 2551.9 | 2405.1 | 2258.3 | 2052.2 | 1849.0 | 1642.9 | 1436.8 | 1270.3 | 1106.6 | 940.0  | 773.5  |
| 32.5°  | 2670.4 | 2506.7 | 2343.0 | 2117.1 | 1888.5 | 1662.7 | 1434.0 | 1250.5 | 1069.9 | 886.4  | 702.9  |
| 35°    | 2834.2 | 2653.5 | 2475.6 | 2213.1 | 1950.6 | 1688.1 | 1425.5 | 1236.4 | 1044.5 | 855.3  | 663.4  |
| 37.5°  | 3009.2 | 2786.2 | 2566.0 | 2275.2 | 1984.5 | 1693.7 | 1403.0 | 1216.7 | 1030.3 | 844.0  | 657.7  |
| 40°    | 3201.1 | 2930.1 | 2662.0 | 2340.2 | 2021.2 | 1699.4 | 1377.6 | 1191.2 | 1004.9 | 815.8  | 629.5  |
| 42.5°  | 3325.3 | 3031.8 | 2738.2 | 2391.0 | 2046.6 | 1699.4 | 1352.2 | 1168.7 | 985.2  | 798.9  | 615.4  |
| 45°    | 3395.9 | 3110.8 | 2828.5 | 2453.1 | 2077.6 | 1702.2 | 1326.7 | 1146.1 | 965.4  | 781.9  | 601.3  |
| 47.5°  | 3427.0 | 3161.6 | 2896.3 | 2501.1 | 2108.7 | 1713.5 | 1318.3 | 1134.8 | 948.5  | 765.0  | 578.7  |
| 50°    | 3508.8 | 3274.5 | 3040.2 | 2616.8 | 2196.2 | 1772.8 | 1349.3 | 1151.7 | 956.9  | 759.3  | 561.7  |
| 52.5°  | 3556.8 | 3356.4 | 3156.0 | 2721.2 | 2286.5 | 1851.8 | 1417.1 | 1196.9 | 976.7  | 756.5  | 536.3  |
| 55°    | 3731.8 | 3539.9 | 3347.9 | 2885.0 | 2419.2 | 1956.2 | 1490.5 | 1247.7 | 1004.9 | 759.3  | 516.6  |
| 57.5°  | 3954.8 | 3751.6 | 3551.2 | 3051.5 | 2551.9 | 2052.2 | 1552.6 | 1292.9 | 1030.3 | 770.6  | 508.1  |
| 60°    | 4110.1 | 3912.5 | 3717.7 | 3187.0 | 2653.5 | 2122.8 | 1589.3 | 1318.3 | 1047.3 | 773.5  | 502.5  |
| 62.5°  | 4127.0 | 3873.0 | 3621.7 | 3105.1 | 2588.6 | 2069.2 | 1552.6 | 1290.0 | 1027.5 | 762.2  | 499.6  |
| 65°    | 4019.8 | 3723.4 | 3427.0 | 2933.0 | 2439.0 | 1945.0 | 1451.0 | 1211.0 | 971.1  | 728.3  | 488.4  |
| 67.5°  | 3805.2 | 3458.0 | 3110.8 | 2659.1 | 2207.5 | 1755.8 | 1304.2 | 1098.1 | 894.8  | 688.8  | 482.7  |
| 70°    | 3305.6 | 3000.7 | 2698.7 | 2306.3 | 1916.7 | 1524.3 | 1132.0 | 962.6  | 796.0  | 626.7  | 457.3  |
| 72.5°  | 2774.9 | 2489.8 | 2207.5 | 1888.5 | 1572.3 | 1253.4 | 934.4  | 807.3  | 680.3  | 550.5  | 423.4  |
| 75°    | 2125.6 | 1911.1 | 1699.4 | 1462.2 | 1225.1 | 985.2  | 748.1  | 654.9  | 561.7  | 468.6  | 375.4  |
| 77.5°  | 1493.3 | 1377.6 | 1264.6 | 1086.8 | 909.0  | 731.1  | 553.3  | 491.2  | 429.1  | 367.0  | 304.9  |
| 80°    | 1013.4 | 948.5  | 886.4  | 759.3  | 632.3  | 502.5  | 375.4  | 335.9  | 293.6  | 254.1  | 211.7  |
| 82.5°  | 629.5  | 626.7  | 621.0  | 533.5  | 446.0  | 358.5  | 271.0  | 237.1  | 206.1  | 172.2  | 138.3  |
| 85°    | 287.9  | 335.9  | 381.1  | 333.1  | 285.1  | 237.1  | 189.1  | 166.5  | 144.0  | 118.6  | 96.0   |
| 87.5°  | 90.3   | 110.1  | 127.0  | 121.4  | 112.9  | 107.3  | 98.8   | 84.7   | 70.6   | 56.5   | 42.3   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 25° |
|--------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |

REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 27.5°  | 30°    | 32.5°  | 35°    | 37.5°  | 40°    | 42.5°  | 45°    | 47.5°  | 50°    | 52.5°  |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 |
| 2.5°   | 1976.0 | 1967.5 | 1956.2 | 1945.0 | 1930.8 | 1919.5 | 1905.4 | 1891.3 | 1888.5 | 1882.8 | 1880.0 |
| 5°     | 1702.2 | 1685.2 | 1665.5 | 1648.6 | 1631.6 | 1611.9 | 1594.9 | 1575.2 | 1561.0 | 1544.1 | 1530.0 |
| 7.5°   | 1462.2 | 1434.0 | 1403.0 | 1371.9 | 1343.7 | 1315.5 | 1284.4 | 1256.2 | 1242.1 | 1227.9 | 1213.8 |
| 10°    | 1270.3 | 1242.1 | 1216.7 | 1188.4 | 1168.7 | 1151.7 | 1132.0 | 1112.2 | 1095.3 | 1078.3 | 1061.4 |
| 12.5°  | 1174.3 | 1154.6 | 1134.8 | 1115.0 | 1092.4 | 1072.7 | 1050.1 | 1027.5 | 1007.8 | 990.8  | 971.1  |
| 15°    | 1115.0 | 1086.8 | 1055.8 | 1027.5 | 996.5  | 968.2  | 937.2  | 906.1  | 883.6  | 863.8  | 841.2  |
| 17.5°  | 1044.5 | 1002.1 | 962.6  | 920.3  | 886.4  | 852.5  | 815.8  | 781.9  | 756.5  | 728.3  | 702.9  |
| 20°    | 965.4  | 917.4  | 866.6  | 818.6  | 779.1  | 742.4  | 702.9  | 663.4  | 635.1  | 604.1  | 575.9  |
| 22.5°  | 897.7  | 835.6  | 770.6  | 705.7  | 663.4  | 621.0  | 575.9  | 533.5  | 508.1  | 479.9  | 454.5  |
| 25°    | 824.3  | 756.5  | 686.0  | 615.4  | 573.0  | 527.9  | 485.5  | 440.4  | 420.6  | 403.7  | 383.9  |
| 27.5°  | 784.8  | 717.0  | 646.4  | 578.7  | 539.2  | 496.8  | 457.3  | 415.0  | 400.8  | 383.9  | 369.8  |
| 30°    | 705.7  | 640.8  | 573.0  | 505.3  | 477.1  | 451.7  | 423.4  | 395.2  | 389.6  | 386.7  | 381.1  |
| 32.5°  | 635.1  | 567.4  | 499.6  | 431.9  | 406.5  | 381.1  | 355.7  | 330.3  | 327.5  | 321.8  | 319.0  |
| 35°    | 598.4  | 533.5  | 465.8  | 400.8  | 378.3  | 352.9  | 330.3  | 304.9  | 299.2  | 290.8  | 285.1  |
| 37.5°  | 590.0  | 522.2  | 451.7  | 383.9  | 361.3  | 338.7  | 313.3  | 290.8  | 285.1  | 279.5  | 273.8  |
| 40°    | 567.4  | 502.5  | 440.4  | 375.4  | 352.9  | 330.3  | 304.9  | 282.3  | 276.6  | 271.0  | 265.3  |
| 42.5°  | 550.5  | 488.4  | 423.4  | 358.5  | 338.7  | 319.0  | 296.4  | 276.6  | 271.0  | 265.3  | 256.9  |
| 45°    | 536.3  | 471.4  | 403.7  | 338.7  | 324.6  | 310.5  | 293.6  | 279.5  | 273.8  | 265.3  | 259.7  |
| 47.5°  | 513.8  | 451.7  | 386.7  | 321.8  | 307.7  | 296.4  | 282.3  | 268.2  | 262.5  | 256.9  | 251.2  |
| 50°    | 496.8  | 431.9  | 367.0  | 302.0  | 290.8  | 279.5  | 268.2  | 256.9  | 256.9  | 259.7  | 259.7  |
| 52.5°  | 474.2  | 412.1  | 350.0  | 287.9  | 276.6  | 265.3  | 254.1  | 242.8  | 245.6  | 248.4  | 251.2  |
| 55°    | 454.5  | 395.2  | 333.1  | 271.0  | 259.7  | 248.4  | 234.3  | 223.0  | 225.8  | 228.7  | 231.5  |
| 57.5°  | 446.0  | 383.9  | 321.8  | 259.7  | 248.4  | 234.3  | 223.0  | 208.9  | 208.9  | 208.9  | 208.9  |
| 60°    | 440.4  | 375.4  | 313.3  | 248.4  | 234.3  | 223.0  | 208.9  | 194.8  | 192.0  | 192.0  | 189.1  |
| 62.5°  | 437.5  | 372.6  | 310.5  | 245.6  | 228.7  | 214.5  | 197.6  | 180.7  | 177.8  | 175.0  | 172.2  |
| 65°    | 426.3  | 367.0  | 304.9  | 242.8  | 223.0  | 206.1  | 186.3  | 166.5  | 163.7  | 163.7  | 160.9  |
| 67.5°  | 423.4  | 361.3  | 302.0  | 239.9  | 220.2  | 197.6  | 177.8  | 155.3  | 152.4  | 149.6  | 146.8  |
| 70°    | 400.8  | 347.2  | 290.8  | 234.3  | 211.7  | 192.0  | 169.4  | 146.8  | 144.0  | 138.3  | 135.5  |
| 72.5°  | 372.6  | 324.6  | 273.8  | 223.0  | 200.4  | 177.8  | 155.3  | 132.7  | 129.9  | 127.0  | 121.4  |
| 75°    | 330.3  | 285.1  | 239.9  | 194.8  | 175.0  | 158.1  | 138.3  | 118.6  | 115.7  | 112.9  | 107.3  |
| 77.5°  | 271.0  | 234.3  | 200.4  | 163.7  | 149.6  | 135.5  | 121.4  | 107.3  | 104.4  | 101.6  | 96.0   |
| 80°    | 192.0  | 169.4  | 149.6  | 127.0  | 118.6  | 107.3  | 98.8   | 87.5   | 87.5   | 84.7   | 84.7   |
| 82.5°  | 127.0  | 115.7  | 104.4  | 93.2   | 87.5   | 81.9   | 76.2   | 70.6   | 70.6   | 67.7   | 67.7   |
| 85°    | 90.3   | 84.7   | 76.2   | 70.6   | 67.7   | 62.1   | 59.3   | 53.6   | 53.6   | 53.6   | 53.6   |
| 87.5°  | 42.3   | 42.3   | 39.5   | 39.5   | 36.7   | 36.7   | 33.9   | 31.1   | 31.1   | 31.1   | 31.1   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 27.5° | 30° | 32.5° | 35° | 37.5° | 40° | 42.5° | 45° | 47.5° | 50° | 52.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   |

REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 55°    | 57.5°  | 60°    | 62.5°  | 65°    | 67.5°  | 70°    | 72.5°  | 75°    | 77.5°  | 80°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 |
| 2.5°   | 1874.4 | 1865.9 | 1857.4 | 1846.2 | 1837.7 | 1826.4 | 1812.3 | 1801.0 | 1786.9 | 1786.9 | 1784.0 |
| 5°     | 1513.1 | 1504.6 | 1496.1 | 1484.8 | 1476.4 | 1465.1 | 1456.6 | 1445.3 | 1434.0 | 1434.0 | 1431.2 |
| 7.5°   | 1199.7 | 1182.8 | 1165.8 | 1146.1 | 1129.1 | 1117.9 | 1106.6 | 1092.4 | 1081.2 | 1072.7 | 1064.2 |
| 10°    | 1044.5 | 1027.5 | 1007.8 | 990.8  | 971.1  | 956.9  | 942.8  | 925.9  | 911.8  | 900.5  | 889.2  |
| 12.5°  | 951.3  | 931.5  | 911.8  | 892.0  | 872.3  | 852.5  | 835.6  | 815.8  | 796.0  | 781.9  | 767.8  |
| 15°    | 818.6  | 798.9  | 779.1  | 759.3  | 739.6  | 717.0  | 694.4  | 669.0  | 646.4  | 635.1  | 626.7  |
| 17.5°  | 674.7  | 654.9  | 632.3  | 612.6  | 590.0  | 573.0  | 556.1  | 539.2  | 522.2  | 510.9  | 502.5  |
| 20°    | 544.8  | 522.2  | 499.6  | 477.1  | 454.5  | 443.2  | 431.9  | 420.6  | 409.3  | 400.8  | 395.2  |
| 22.5°  | 426.3  | 412.1  | 400.8  | 386.7  | 372.6  | 364.1  | 358.5  | 350.0  | 341.6  | 341.6  | 341.6  |
| 25°    | 364.1  | 355.7  | 350.0  | 341.6  | 333.1  | 330.3  | 327.5  | 321.8  | 319.0  | 316.2  | 316.2  |
| 27.5°  | 352.9  | 344.4  | 335.9  | 327.5  | 319.0  | 316.2  | 313.3  | 307.7  | 304.9  | 304.9  | 304.9  |
| 30°    | 375.4  | 372.6  | 369.8  | 367.0  | 364.1  | 358.5  | 350.0  | 344.4  | 335.9  | 330.3  | 324.6  |
| 32.5°  | 313.3  | 310.5  | 310.5  | 307.7  | 304.9  | 310.5  | 313.3  | 319.0  | 321.8  | 324.6  | 327.5  |
| 35°    | 276.6  | 271.0  | 265.3  | 259.7  | 254.1  | 251.2  | 248.4  | 245.6  | 242.8  | 242.8  | 239.9  |
| 37.5°  | 268.2  | 262.5  | 256.9  | 251.2  | 245.6  | 242.8  | 239.9  | 237.1  | 234.3  | 234.3  | 231.5  |
| 40°    | 259.7  | 254.1  | 251.2  | 245.6  | 239.9  | 237.1  | 234.3  | 228.7  | 225.8  | 223.0  | 223.0  |
| 42.5°  | 251.2  | 248.4  | 242.8  | 239.9  | 234.3  | 231.5  | 228.7  | 223.0  | 220.2  | 217.4  | 214.5  |
| 45°    | 251.2  | 245.6  | 239.9  | 234.3  | 228.7  | 225.8  | 220.2  | 217.4  | 211.7  | 211.7  | 208.9  |
| 47.5°  | 245.6  | 239.9  | 234.3  | 228.7  | 223.0  | 220.2  | 214.5  | 211.7  | 206.1  | 203.2  | 200.4  |
| 50°    | 259.7  | 251.2  | 239.9  | 231.5  | 220.2  | 217.4  | 211.7  | 208.9  | 203.2  | 200.4  | 197.6  |
| 52.5°  | 254.1  | 245.6  | 234.3  | 225.8  | 214.5  | 208.9  | 206.1  | 200.4  | 194.8  | 192.0  | 189.1  |
| 55°    | 234.3  | 225.8  | 220.2  | 211.7  | 203.2  | 197.6  | 192.0  | 186.3  | 180.7  | 177.8  | 177.8  |
| 57.5°  | 208.9  | 206.1  | 203.2  | 200.4  | 197.6  | 192.0  | 186.3  | 177.8  | 172.2  | 169.4  | 166.5  |
| 60°    | 186.3  | 189.1  | 192.0  | 194.8  | 197.6  | 189.1  | 180.7  | 172.2  | 163.7  | 160.9  | 158.1  |
| 62.5°  | 169.4  | 175.0  | 180.7  | 183.5  | 189.1  | 180.7  | 172.2  | 163.7  | 155.3  | 152.4  | 149.6  |
| 65°    | 158.1  | 160.9  | 160.9  | 163.7  | 163.7  | 158.1  | 155.3  | 149.6  | 144.0  | 141.1  | 141.1  |
| 67.5°  | 144.0  | 144.0  | 144.0  | 141.1  | 141.1  | 138.3  | 138.3  | 135.5  | 132.7  | 129.9  | 129.9  |
| 70°    | 129.9  | 129.9  | 129.9  | 127.0  | 127.0  | 124.2  | 124.2  | 121.4  | 118.6  | 118.6  | 115.7  |
| 72.5°  | 118.6  | 118.6  | 115.7  | 115.7  | 112.9  | 112.9  | 112.9  | 110.1  | 110.1  | 107.3  | 107.3  |
| 75°    | 104.4  | 104.4  | 101.6  | 101.6  | 98.8   | 98.8   | 98.8   | 96.0   | 96.0   | 96.0   | 93.2   |
| 77.5°  | 93.2   | 93.2   | 90.3   | 90.3   | 87.5   | 87.5   | 87.5   | 84.7   | 84.7   | 81.9   | 81.9   |
| 80°    | 81.9   | 81.9   | 79.0   | 79.0   | 76.2   | 76.2   | 73.4   | 73.4   | 70.6   | 70.6   | 67.7   |
| 82.5°  | 64.9   | 64.9   | 64.9   | 64.9   | 64.9   | 62.1   | 62.1   | 59.3   | 56.5   | 56.5   | 53.6   |
| 85°    | 53.6   | 53.6   | 53.6   | 50.8   | 50.8   | 50.8   | 48.0   | 48.0   | 45.2   | 42.3   | 42.3   |
| 87.5°  | 31.1   | 31.1   | 31.1   | 28.2   | 28.2   | 28.2   | 28.2   | 28.2   | 28.2   | 28.2   | 25.4   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 55° | 57.5° | 60° | 62.5° | 65° | 67.5° | 70° | 72.5° | 75° | 77.5° | 80° |
|--------|-----|-------|-----|-------|-----|-------|-----|-------|-----|-------|-----|
| 112.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 115°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 117.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 120°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 122.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 125°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 127.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 130°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 132.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 135°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 137.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 140°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 142.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 145°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 147.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 150°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 152.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 155°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 157.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 160°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 162.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 165°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 167.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 170°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 172.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 175°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 177.5° | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |
| 180°   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 82.5°  | 85°    | 87.5°  | 90°    | 92.5°  | 95°    | 97.5°  | 100°   | 102.5° | 105°   | 107.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 |
| 2.5°   | 1784.0 | 1781.2 | 1769.9 | 1758.6 | 1769.9 | 1781.2 | 1781.2 | 1781.2 | 1778.4 | 1778.4 | 1778.4 |
| 5°     | 1431.2 | 1428.4 | 1422.7 | 1417.1 | 1417.1 | 1414.3 | 1419.9 | 1425.5 | 1431.2 | 1436.8 | 1442.5 |
| 7.5°   | 1052.9 | 1044.5 | 1036.0 | 1027.5 | 1033.2 | 1036.0 | 1044.5 | 1050.1 | 1058.6 | 1064.2 | 1078.3 |
| 10°    | 877.9  | 866.6  | 858.1  | 849.7  | 844.0  | 838.4  | 832.7  | 829.9  | 824.3  | 818.6  | 824.3  |
| 12.5°  | 750.9  | 736.8  | 722.7  | 705.7  | 702.9  | 700.1  | 694.4  | 688.8  | 683.1  | 677.5  | 674.7  |
| 15°    | 615.4  | 604.1  | 598.4  | 590.0  | 578.7  | 567.4  | 561.7  | 558.9  | 553.3  | 547.6  | 544.8  |
| 17.5°  | 491.2  | 479.9  | 471.4  | 462.9  | 460.1  | 454.5  | 454.5  | 454.5  | 454.5  | 454.5  | 454.5  |
| 20°    | 386.7  | 378.3  | 378.3  | 375.4  | 375.4  | 372.6  | 375.4  | 378.3  | 378.3  | 381.1  | 383.9  |
| 22.5°  | 338.7  | 338.7  | 335.9  | 333.1  | 335.9  | 335.9  | 338.7  | 341.6  | 344.4  | 347.2  | 350.0  |
| 25°    | 313.3  | 310.5  | 313.3  | 316.2  | 316.2  | 316.2  | 319.0  | 319.0  | 321.8  | 321.8  | 321.8  |
| 27.5°  | 302.0  | 302.0  | 304.9  | 304.9  | 307.7  | 307.7  | 307.7  | 304.9  | 304.9  | 302.0  | 302.0  |
| 30°    | 319.0  | 313.3  | 313.3  | 313.3  | 310.5  | 307.7  | 304.9  | 304.9  | 302.0  | 299.2  | 296.4  |
| 32.5°  | 330.3  | 333.1  | 330.3  | 324.6  | 321.8  | 316.2  | 313.3  | 307.7  | 304.9  | 299.2  | 293.6  |
| 35°    | 239.9  | 237.1  | 242.8  | 245.6  | 248.4  | 251.2  | 254.1  | 256.9  | 256.9  | 259.7  | 259.7  |
| 37.5°  | 231.5  | 228.7  | 228.7  | 225.8  | 225.8  | 225.8  | 225.8  | 225.8  | 223.0  | 223.0  | 225.8  |
| 40°    | 220.2  | 217.4  | 217.4  | 214.5  | 214.5  | 211.7  | 211.7  | 211.7  | 211.7  | 211.7  | 211.7  |
| 42.5°  | 211.7  | 208.9  | 208.9  | 208.9  | 208.9  | 206.1  | 206.1  | 203.2  | 203.2  | 200.4  | 200.4  |
| 45°    | 208.9  | 206.1  | 203.2  | 200.4  | 200.4  | 197.6  | 197.6  | 197.6  | 194.8  | 194.8  | 194.8  |
| 47.5°  | 197.6  | 194.8  | 194.8  | 192.0  | 192.0  | 189.1  | 189.1  | 189.1  | 186.3  | 186.3  | 186.3  |
| 50°    | 192.0  | 189.1  | 189.1  | 186.3  | 186.3  | 183.5  | 183.5  | 183.5  | 180.7  | 180.7  | 180.7  |
| 52.5°  | 183.5  | 180.7  | 180.7  | 180.7  | 177.8  | 175.0  | 175.0  | 175.0  | 172.2  | 172.2  | 172.2  |
| 55°    | 175.0  | 172.2  | 172.2  | 172.2  | 169.4  | 166.5  | 166.5  | 166.5  | 163.7  | 163.7  | 163.7  |
| 57.5°  | 163.7  | 160.9  | 160.9  | 158.1  | 158.1  | 158.1  | 158.1  | 158.1  | 155.3  | 155.3  | 155.3  |
| 60°    | 155.3  | 152.4  | 152.4  | 149.6  | 149.6  | 146.8  | 146.8  | 146.8  | 146.8  | 146.8  | 146.8  |
| 62.5°  | 146.8  | 144.0  | 141.1  | 138.3  | 141.1  | 141.1  | 141.1  | 141.1  | 138.3  | 138.3  | 138.3  |
| 65°    | 138.3  | 135.5  | 132.7  | 129.9  | 129.9  | 129.9  | 129.9  | 129.9  | 129.9  | 129.9  | 129.9  |
| 67.5°  | 127.0  | 124.2  | 121.4  | 118.6  | 121.4  | 121.4  | 121.4  | 121.4  | 121.4  | 121.4  | 121.4  |
| 70°    | 115.7  | 112.9  | 112.9  | 110.1  | 110.1  | 107.3  | 107.3  | 110.1  | 110.1  | 110.1  | 110.1  |
| 72.5°  | 104.4  | 101.6  | 101.6  | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   |
| 75°    | 93.2   | 90.3   | 90.3   | 87.5   | 87.5   | 87.5   | 87.5   | 87.5   | 87.5   | 87.5   | 87.5   |
| 77.5°  | 79.0   | 76.2   | 76.2   | 76.2   | 76.2   | 76.2   | 76.2   | 79.0   | 79.0   | 79.0   | 79.0   |
| 80°    | 67.7   | 64.9   | 64.9   | 64.9   | 64.9   | 64.9   | 64.9   | 64.9   | 64.9   | 64.9   | 64.9   |
| 82.5°  | 53.6   | 50.8   | 50.8   | 50.8   | 50.8   | 50.8   | 50.8   | 50.8   | 50.8   | 50.8   | 50.8   |
| 85°    | 39.5   | 36.7   | 36.7   | 36.7   | 39.5   | 39.5   | 39.5   | 39.5   | 39.5   | 39.5   | 39.5   |
| 87.5°  | 25.4   | 22.6   | 22.6   | 22.6   | 25.4   | 25.4   | 25.4   | 25.4   | 22.6   | 22.6   | 22.6   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 82.5° | 85° | 87.5° | 90° | 92.5° | 95° | 97.5° | 100° | 102.5° | 105° | 107.5° |
|--------|-------|-----|-------|-----|-------|-----|-------|------|--------|------|--------|
| 112.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 110°   | 112.5° | 115°   | 117.5° | 120°   | 122.5° | 125°   | 127.5° | 130°   | 132.5° | 135°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 |
| 2.5°   | 1778.4 | 1778.4 | 1778.4 | 1775.6 | 1772.8 | 1769.9 | 1767.1 | 1775.6 | 1781.2 | 1789.7 | 1795.3 |
| 5°     | 1445.3 | 1451.0 | 1453.8 | 1462.2 | 1470.7 | 1479.2 | 1487.6 | 1493.3 | 1498.9 | 1501.8 | 1507.4 |
| 7.5°   | 1089.6 | 1103.7 | 1115.0 | 1126.3 | 1137.6 | 1146.1 | 1157.4 | 1165.8 | 1174.3 | 1182.8 | 1191.2 |
| 10°    | 827.1  | 832.7  | 835.6  | 846.9  | 855.3  | 866.6  | 875.1  | 883.6  | 892.0  | 897.7  | 906.1  |
| 12.5°  | 671.8  | 666.2  | 663.4  | 663.4  | 663.4  | 663.4  | 663.4  | 669.0  | 674.7  | 680.3  | 686.0  |
| 15°    | 542.0  | 539.2  | 536.3  | 533.5  | 530.7  | 525.1  | 522.2  | 527.9  | 533.5  | 539.2  | 544.8  |
| 17.5°  | 454.5  | 454.5  | 454.5  | 451.7  | 448.8  | 446.0  | 443.2  | 446.0  | 448.8  | 448.8  | 451.7  |
| 20°    | 389.6  | 392.4  | 395.2  | 398.0  | 398.0  | 400.8  | 400.8  | 403.7  | 406.5  | 406.5  | 409.3  |
| 22.5°  | 350.0  | 352.9  | 352.9  | 352.9  | 355.7  | 355.7  | 355.7  | 358.5  | 361.3  | 364.1  | 367.0  |
| 25°    | 319.0  | 319.0  | 316.2  | 316.2  | 319.0  | 319.0  | 319.0  | 319.0  | 321.8  | 321.8  | 321.8  |
| 27.5°  | 302.0  | 299.2  | 299.2  | 299.2  | 299.2  | 296.4  | 296.4  | 296.4  | 296.4  | 296.4  | 296.4  |
| 30°    | 293.6  | 290.8  | 287.9  | 285.1  | 285.1  | 282.3  | 279.5  | 279.5  | 279.5  | 279.5  | 279.5  |
| 32.5°  | 290.8  | 285.1  | 279.5  | 276.6  | 276.6  | 273.8  | 271.0  | 268.2  | 268.2  | 265.3  | 262.5  |
| 35°    | 259.7  | 256.9  | 256.9  | 254.1  | 251.2  | 248.4  | 245.6  | 245.6  | 245.6  | 242.8  | 242.8  |
| 37.5°  | 225.8  | 228.7  | 228.7  | 228.7  | 231.5  | 231.5  | 231.5  | 231.5  | 234.3  | 234.3  | 234.3  |
| 40°    | 211.7  | 211.7  | 211.7  | 214.5  | 217.4  | 217.4  | 220.2  | 220.2  | 223.0  | 223.0  | 223.0  |
| 42.5°  | 200.4  | 197.6  | 197.6  | 200.4  | 200.4  | 203.2  | 203.2  | 206.1  | 208.9  | 208.9  | 211.7  |
| 45°    | 194.8  | 192.0  | 192.0  | 192.0  | 192.0  | 189.1  | 189.1  | 192.0  | 194.8  | 197.6  | 200.4  |
| 47.5°  | 183.5  | 183.5  | 180.7  | 180.7  | 180.7  | 180.7  | 180.7  | 180.7  | 183.5  | 183.5  | 183.5  |
| 50°    | 177.8  | 177.8  | 175.0  | 175.0  | 175.0  | 175.0  | 175.0  | 175.0  | 175.0  | 175.0  | 175.0  |
| 52.5°  | 172.2  | 169.4  | 169.4  | 169.4  | 169.4  | 166.5  | 166.5  | 166.5  | 166.5  | 166.5  | 166.5  |
| 55°    | 163.7  | 160.9  | 160.9  | 160.9  | 160.9  | 160.9  | 160.9  | 160.9  | 163.7  | 163.7  | 163.7  |
| 57.5°  | 155.3  | 152.4  | 152.4  | 152.4  | 155.3  | 155.3  | 155.3  | 155.3  | 158.1  | 158.1  | 158.1  |
| 60°    | 146.8  | 146.8  | 146.8  | 146.8  | 146.8  | 146.8  | 146.8  | 149.6  | 149.6  | 152.4  | 152.4  |
| 62.5°  | 138.3  | 138.3  | 138.3  | 138.3  | 141.1  | 141.1  | 141.1  | 141.1  | 144.0  | 144.0  | 144.0  |
| 65°    | 129.9  | 129.9  | 129.9  | 129.9  | 132.7  | 132.7  | 132.7  | 132.7  | 132.7  | 132.7  | 132.7  |
| 67.5°  | 121.4  | 121.4  | 121.4  | 121.4  | 121.4  | 121.4  | 121.4  | 124.2  | 124.2  | 127.0  | 127.0  |
| 70°    | 110.1  | 107.3  | 107.3  | 110.1  | 110.1  | 112.9  | 112.9  | 115.7  | 115.7  | 118.6  | 118.6  |
| 72.5°  | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 101.6  | 104.4  | 104.4  | 107.3  |
| 75°    | 87.5   | 87.5   | 87.5   | 87.5   | 90.3   | 90.3   | 90.3   | 93.2   | 93.2   | 96.0   | 96.0   |
| 77.5°  | 79.0   | 76.2   | 76.2   | 76.2   | 79.0   | 79.0   | 79.0   | 81.9   | 81.9   | 84.7   | 84.7   |
| 80°    | 64.9   | 64.9   | 64.9   | 64.9   | 67.7   | 67.7   | 67.7   | 67.7   | 70.6   | 70.6   | 70.6   |
| 82.5°  | 53.6   | 53.6   | 53.6   | 53.6   | 53.6   | 53.6   | 53.6   | 53.6   | 56.5   | 56.5   | 56.5   |
| 85°    | 39.5   | 39.5   | 39.5   | 39.5   | 42.3   | 42.3   | 42.3   | 42.3   | 42.3   | 42.3   | 42.3   |
| 87.5°  | 25.4   | 25.4   | 25.4   | 25.4   | 25.4   | 25.4   | 25.4   | 25.4   | 28.2   | 28.2   | 28.2   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° | 135° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140°   | 142.5° | 145°   | 147.5° | 150°   | 152.5° | 155°   | 157.5° | 160°   | 162.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 |
| 2.5°   | 1795.3 | 1795.3 | 1795.3 | 1795.3 | 1801.0 | 1803.8 | 1809.5 | 1812.3 | 1809.5 | 1806.6 | 1801.0 |
| 5°     | 1510.2 | 1513.1 | 1513.1 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1515.9 | 1521.5 | 1527.2 | 1532.8 |
| 7.5°   | 1194.1 | 1196.9 | 1199.7 | 1202.5 | 1202.5 | 1202.5 | 1199.7 | 1199.7 | 1202.5 | 1202.5 | 1205.4 |
| 10°    | 914.6  | 925.9  | 934.4  | 942.8  | 937.2  | 928.7  | 923.1  | 914.6  | 914.6  | 914.6  | 911.8  |
| 12.5°  | 691.6  | 694.4  | 700.1  | 702.9  | 700.1  | 700.1  | 697.2  | 694.4  | 697.2  | 702.9  | 705.7  |
| 15°    | 547.6  | 547.6  | 550.5  | 550.5  | 553.3  | 556.1  | 556.1  | 558.9  | 564.6  | 567.4  | 573.0  |
| 17.5°  | 454.5  | 457.3  | 457.3  | 460.1  | 460.1  | 462.9  | 462.9  | 462.9  | 468.6  | 474.2  | 482.7  |
| 20°    | 409.3  | 409.3  | 409.3  | 409.3  | 409.3  | 406.5  | 406.5  | 403.7  | 406.5  | 412.1  | 415.0  |
| 22.5°  | 367.0  | 369.8  | 369.8  | 369.8  | 367.0  | 364.1  | 358.5  | 355.7  | 355.7  | 358.5  | 358.5  |
| 25°    | 321.8  | 319.0  | 319.0  | 316.2  | 316.2  | 319.0  | 319.0  | 319.0  | 321.8  | 321.8  | 324.6  |
| 27.5°  | 296.4  | 293.6  | 293.6  | 290.8  | 290.8  | 293.6  | 293.6  | 293.6  | 293.6  | 293.6  | 293.6  |
| 30°    | 276.6  | 276.6  | 273.8  | 271.0  | 273.8  | 273.8  | 276.6  | 276.6  | 279.5  | 279.5  | 282.3  |
| 32.5°  | 262.5  | 259.7  | 259.7  | 256.9  | 259.7  | 259.7  | 262.5  | 262.5  | 265.3  | 268.2  | 268.2  |
| 35°    | 242.8  | 242.8  | 242.8  | 242.8  | 242.8  | 242.8  | 239.9  | 239.9  | 239.9  | 239.9  | 239.9  |
| 37.5°  | 231.5  | 231.5  | 228.7  | 225.8  | 225.8  | 225.8  | 225.8  | 225.8  | 223.0  | 220.2  | 217.4  |
| 40°    | 223.0  | 220.2  | 220.2  | 217.4  | 214.5  | 214.5  | 211.7  | 208.9  | 208.9  | 206.1  | 206.1  |
| 42.5°  | 211.7  | 208.9  | 208.9  | 206.1  | 203.2  | 203.2  | 200.4  | 197.6  | 197.6  | 197.6  | 194.8  |
| 45°    | 197.6  | 197.6  | 194.8  | 192.0  | 192.0  | 192.0  | 189.1  | 189.1  | 189.1  | 189.1  | 186.3  |
| 47.5°  | 183.5  | 183.5  | 180.7  | 180.7  | 180.7  | 180.7  | 177.8  | 177.8  | 177.8  | 177.8  | 177.8  |
| 50°    | 175.0  | 175.0  | 175.0  | 175.0  | 175.0  | 175.0  | 172.2  | 172.2  | 172.2  | 172.2  | 172.2  |
| 52.5°  | 166.5  | 166.5  | 166.5  | 166.5  | 166.5  | 166.5  | 166.5  | 166.5  | 166.5  | 166.5  | 166.5  |
| 55°    | 163.7  | 163.7  | 163.7  | 163.7  | 163.7  | 163.7  | 160.9  | 160.9  | 160.9  | 163.7  | 163.7  |
| 57.5°  | 158.1  | 158.1  | 155.3  | 155.3  | 155.3  | 155.3  | 155.3  | 155.3  | 155.3  | 155.3  | 155.3  |
| 60°    | 152.4  | 152.4  | 152.4  | 152.4  | 152.4  | 152.4  | 152.4  | 152.4  | 152.4  | 152.4  | 152.4  |
| 62.5°  | 144.0  | 144.0  | 144.0  | 144.0  | 144.0  | 146.8  | 146.8  | 146.8  | 146.8  | 146.8  | 144.0  |
| 65°    | 132.7  | 135.5  | 135.5  | 135.5  | 135.5  | 135.5  | 135.5  | 135.5  | 135.5  | 135.5  | 135.5  |
| 67.5°  | 127.0  | 127.0  | 127.0  | 127.0  | 127.0  | 127.0  | 127.0  | 127.0  | 127.0  | 127.0  | 127.0  |
| 70°    | 118.6  | 118.6  | 115.7  | 115.7  | 115.7  | 118.6  | 118.6  | 118.6  | 118.6  | 118.6  | 118.6  |
| 72.5°  | 107.3  | 107.3  | 107.3  | 107.3  | 107.3  | 107.3  | 107.3  | 107.3  | 107.3  | 110.1  | 110.1  |
| 75°    | 96.0   | 96.0   | 96.0   | 96.0   | 96.0   | 96.0   | 96.0   | 96.0   | 96.0   | 96.0   | 96.0   |
| 77.5°  | 84.7   | 84.7   | 81.9   | 81.9   | 81.9   | 84.7   | 84.7   | 84.7   | 84.7   | 87.5   | 87.5   |
| 80°    | 70.6   | 70.6   | 70.6   | 70.6   | 70.6   | 70.6   | 70.6   | 70.6   | 70.6   | 73.4   | 73.4   |
| 82.5°  | 56.5   | 56.5   | 56.5   | 56.5   | 56.5   | 56.5   | 56.5   | 56.5   | 56.5   | 59.3   | 59.3   |
| 85°    | 42.3   | 45.2   | 45.2   | 45.2   | 45.2   | 45.2   | 45.2   | 45.2   | 45.2   | 48.0   | 48.0   |
| 87.5°  | 28.2   | 28.2   | 28.2   | 28.2   | 28.2   | 28.2   | 25.4   | 25.4   | 25.4   | 25.4   | 22.6   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° | 162.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 165°   | 167.5° | 170°   | 172.5° | 175°   | 177.5° | 180°   | 182.5° | 185°   | 187.5° | 190°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 |
| 2.5°   | 1798.2 | 1801.0 | 1803.8 | 1803.8 | 1806.6 | 1809.5 | 1809.5 | 1820.7 | 1832.0 | 1837.7 | 1843.3 |
| 5°     | 1538.5 | 1535.6 | 1535.6 | 1532.8 | 1530.0 | 1538.5 | 1546.9 | 1563.9 | 1580.8 | 1583.6 | 1589.3 |
| 7.5°   | 1205.4 | 1208.2 | 1211.0 | 1211.0 | 1213.8 | 1205.4 | 1194.1 | 1196.9 | 1199.7 | 1213.8 | 1225.1 |
| 10°    | 911.8  | 914.6  | 917.4  | 917.4  | 920.3  | 917.4  | 911.8  | 920.3  | 928.7  | 940.0  | 954.1  |
| 12.5°  | 708.5  | 717.0  | 725.5  | 731.1  | 739.6  | 745.2  | 748.1  | 759.3  | 767.8  | 781.9  | 796.0  |
| 15°    | 578.7  | 584.3  | 590.0  | 595.6  | 601.3  | 606.9  | 612.6  | 623.9  | 635.1  | 652.1  | 669.0  |
| 17.5°  | 488.4  | 488.4  | 491.2  | 491.2  | 491.2  | 496.8  | 502.5  | 508.1  | 510.9  | 527.9  | 544.8  |
| 20°    | 417.8  | 415.0  | 412.1  | 409.3  | 406.5  | 412.1  | 415.0  | 417.8  | 420.6  | 431.9  | 440.4  |
| 22.5°  | 358.5  | 358.5  | 361.3  | 361.3  | 361.3  | 358.5  | 352.9  | 355.7  | 355.7  | 361.3  | 369.8  |
| 25°    | 324.6  | 324.6  | 324.6  | 321.8  | 321.8  | 324.6  | 327.5  | 327.5  | 324.6  | 327.5  | 330.3  |
| 27.5°  | 293.6  | 296.4  | 296.4  | 299.2  | 299.2  | 302.0  | 302.0  | 302.0  | 302.0  | 304.9  | 307.7  |
| 30°    | 282.3  | 282.3  | 285.1  | 285.1  | 285.1  | 287.9  | 290.8  | 290.8  | 290.8  | 293.6  | 299.2  |
| 32.5°  | 271.0  | 273.8  | 276.6  | 279.5  | 282.3  | 285.1  | 285.1  | 287.9  | 287.9  | 290.8  | 293.6  |
| 35°    | 239.9  | 237.1  | 237.1  | 234.3  | 231.5  | 231.5  | 231.5  | 231.5  | 228.7  | 231.5  | 231.5  |
| 37.5°  | 214.5  | 214.5  | 214.5  | 211.7  | 211.7  | 214.5  | 214.5  | 214.5  | 214.5  | 217.4  | 217.4  |
| 40°    | 203.2  | 203.2  | 203.2  | 203.2  | 203.2  | 203.2  | 203.2  | 206.1  | 206.1  | 208.9  | 211.7  |
| 42.5°  | 194.8  | 194.8  | 194.8  | 194.8  | 194.8  | 197.6  | 197.6  | 197.6  | 197.6  | 200.4  | 200.4  |
| 45°    | 186.3  | 186.3  | 186.3  | 186.3  | 186.3  | 186.3  | 186.3  | 189.1  | 189.1  | 192.0  | 194.8  |
| 47.5°  | 177.8  | 177.8  | 177.8  | 177.8  | 177.8  | 180.7  | 183.5  | 183.5  | 183.5  | 186.3  | 186.3  |
| 50°    | 172.2  | 172.2  | 172.2  | 172.2  | 172.2  | 175.0  | 175.0  | 177.8  | 177.8  | 180.7  | 183.5  |
| 52.5°  | 166.5  | 166.5  | 166.5  | 166.5  | 166.5  | 169.4  | 169.4  | 172.2  | 172.2  | 175.0  | 177.8  |
| 55°    | 163.7  | 163.7  | 163.7  | 160.9  | 160.9  | 163.7  | 163.7  | 166.5  | 166.5  | 169.4  | 169.4  |
| 57.5°  | 155.3  | 155.3  | 155.3  | 155.3  | 155.3  | 155.3  | 155.3  | 158.1  | 158.1  | 160.9  | 163.7  |
| 60°    | 152.4  | 152.4  | 149.6  | 149.6  | 146.8  | 149.6  | 149.6  | 152.4  | 152.4  | 155.3  | 155.3  |
| 62.5°  | 144.0  | 144.0  | 144.0  | 141.1  | 141.1  | 144.0  | 144.0  | 144.0  | 144.0  | 146.8  | 149.6  |
| 65°    | 135.5  | 135.5  | 135.5  | 132.7  | 132.7  | 135.5  | 135.5  | 135.5  | 135.5  | 138.3  | 141.1  |
| 67.5°  | 127.0  | 127.0  | 127.0  | 124.2  | 124.2  | 124.2  | 124.2  | 127.0  | 127.0  | 129.9  | 132.7  |
| 70°    | 118.6  | 118.6  | 118.6  | 115.7  | 115.7  | 115.7  | 112.9  | 115.7  | 118.6  | 121.4  | 121.4  |
| 72.5°  | 110.1  | 110.1  | 110.1  | 107.3  | 107.3  | 107.3  | 104.4  | 107.3  | 107.3  | 110.1  | 110.1  |
| 75°    | 96.0   | 96.0   | 96.0   | 96.0   | 96.0   | 96.0   | 93.2   | 93.2   | 93.2   | 96.0   | 96.0   |
| 77.5°  | 87.5   | 87.5   | 87.5   | 84.7   | 84.7   | 84.7   | 81.9   | 81.9   | 81.9   | 84.7   | 84.7   |
| 80°    | 73.4   | 73.4   | 73.4   | 70.6   | 70.6   | 70.6   | 67.7   | 67.7   | 67.7   | 70.6   | 70.6   |
| 82.5°  | 59.3   | 59.3   | 59.3   | 56.5   | 56.5   | 56.5   | 53.6   | 53.6   | 53.6   | 56.5   | 56.5   |
| 85°    | 48.0   | 48.0   | 48.0   | 48.0   | 48.0   | 48.0   | 45.2   | 45.2   | 45.2   | 48.0   | 50.8   |
| 87.5°  | 22.6   | 22.6   | 25.4   | 25.4   | 25.4   | 25.4   | 22.6   | 22.6   | 19.8   | 19.8   | 22.6   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° | 190° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195°   | 197.5° | 200°   | 202.5° | 205°   | 207.5° | 210°   | 212.5° | 215°   | 217.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 |
| 2.5°   | 1849.0 | 1854.6 | 1868.7 | 1880.0 | 1894.1 | 1905.4 | 1913.9 | 1925.2 | 1933.7 | 1942.1 | 1947.8 |
| 5°     | 1592.1 | 1594.9 | 1609.0 | 1623.1 | 1634.4 | 1648.6 | 1668.3 | 1688.1 | 1707.8 | 1727.6 | 1741.7 |
| 7.5°   | 1239.2 | 1250.5 | 1267.5 | 1287.2 | 1304.2 | 1321.1 | 1340.9 | 1363.4 | 1383.2 | 1403.0 | 1422.7 |
| 10°    | 965.4  | 976.7  | 993.6  | 1010.6 | 1024.7 | 1041.6 | 1064.2 | 1086.8 | 1109.4 | 1132.0 | 1154.6 |
| 12.5°  | 810.2  | 824.3  | 844.0  | 863.8  | 880.7  | 900.5  | 928.7  | 954.1  | 982.4  | 1007.8 | 1036.0 |
| 15°    | 683.1  | 700.1  | 725.5  | 753.7  | 779.1  | 804.5  | 832.7  | 861.0  | 886.4  | 914.6  | 942.8  |
| 17.5°  | 561.7  | 578.7  | 601.3  | 626.7  | 649.3  | 671.8  | 705.7  | 736.8  | 770.6  | 801.7  | 832.7  |
| 20°    | 451.7  | 460.1  | 482.7  | 505.3  | 527.9  | 550.5  | 575.9  | 601.3  | 626.7  | 652.1  | 691.6  |
| 22.5°  | 375.4  | 381.1  | 392.4  | 400.8  | 412.1  | 420.6  | 446.0  | 471.4  | 494.0  | 519.4  | 556.1  |
| 25°    | 330.3  | 333.1  | 341.6  | 347.2  | 355.7  | 361.3  | 378.3  | 392.4  | 409.3  | 423.4  | 457.3  |
| 27.5°  | 307.7  | 310.5  | 313.3  | 316.2  | 319.0  | 321.8  | 333.1  | 344.4  | 352.9  | 364.1  | 395.2  |
| 30°    | 302.0  | 304.9  | 313.3  | 319.0  | 327.5  | 333.1  | 338.7  | 344.4  | 350.0  | 355.7  | 375.4  |
| 32.5°  | 296.4  | 299.2  | 299.2  | 296.4  | 296.4  | 293.6  | 299.2  | 302.0  | 307.7  | 310.5  | 327.5  |
| 35°    | 234.3  | 234.3  | 237.1  | 239.9  | 242.8  | 245.6  | 254.1  | 259.7  | 268.2  | 273.8  | 287.9  |
| 37.5°  | 220.2  | 220.2  | 223.0  | 228.7  | 231.5  | 234.3  | 239.9  | 245.6  | 251.2  | 256.9  | 271.0  |
| 40°    | 211.7  | 214.5  | 217.4  | 220.2  | 223.0  | 225.8  | 231.5  | 234.3  | 239.9  | 242.8  | 254.1  |
| 42.5°  | 203.2  | 203.2  | 206.1  | 211.7  | 214.5  | 217.4  | 223.0  | 225.8  | 231.5  | 234.3  | 245.6  |
| 45°    | 197.6  | 200.4  | 203.2  | 206.1  | 206.1  | 208.9  | 214.5  | 220.2  | 223.0  | 228.7  | 239.9  |
| 47.5°  | 189.1  | 189.1  | 194.8  | 197.6  | 203.2  | 206.1  | 211.7  | 214.5  | 220.2  | 223.0  | 234.3  |
| 50°    | 183.5  | 186.3  | 192.0  | 194.8  | 200.4  | 203.2  | 211.7  | 217.4  | 225.8  | 231.5  | 237.1  |
| 52.5°  | 177.8  | 180.7  | 186.3  | 189.1  | 194.8  | 197.6  | 208.9  | 220.2  | 228.7  | 239.9  | 239.9  |
| 55°    | 172.2  | 172.2  | 177.8  | 186.3  | 192.0  | 197.6  | 203.2  | 211.7  | 217.4  | 223.0  | 223.0  |
| 57.5°  | 163.7  | 166.5  | 172.2  | 180.7  | 186.3  | 192.0  | 197.6  | 203.2  | 206.1  | 211.7  | 208.9  |
| 60°    | 158.1  | 158.1  | 166.5  | 175.0  | 183.5  | 192.0  | 192.0  | 192.0  | 189.1  | 189.1  | 189.1  |
| 62.5°  | 149.6  | 152.4  | 163.7  | 177.8  | 189.1  | 200.4  | 192.0  | 183.5  | 175.0  | 166.5  | 169.4  |
| 65°    | 144.0  | 146.8  | 152.4  | 160.9  | 166.5  | 172.2  | 166.5  | 163.7  | 158.1  | 152.4  | 155.3  |
| 67.5°  | 132.7  | 135.5  | 138.3  | 138.3  | 141.1  | 141.1  | 141.1  | 141.1  | 141.1  | 141.1  | 144.0  |
| 70°    | 124.2  | 124.2  | 124.2  | 127.0  | 127.0  | 127.0  | 127.0  | 127.0  | 127.0  | 127.0  | 129.9  |
| 72.5°  | 112.9  | 112.9  | 112.9  | 112.9  | 112.9  | 112.9  | 112.9  | 112.9  | 112.9  | 112.9  | 115.7  |
| 75°    | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 98.8   | 101.6  |
| 77.5°  | 87.5   | 87.5   | 87.5   | 87.5   | 87.5   | 87.5   | 87.5   | 87.5   | 84.7   | 84.7   | 87.5   |
| 80°    | 73.4   | 73.4   | 73.4   | 73.4   | 70.6   | 70.6   | 70.6   | 70.6   | 70.6   | 70.6   | 73.4   |
| 82.5°  | 59.3   | 59.3   | 59.3   | 59.3   | 56.5   | 56.5   | 56.5   | 56.5   | 53.6   | 53.6   | 56.5   |
| 85°    | 53.6   | 56.5   | 56.5   | 59.3   | 59.3   | 59.3   | 56.5   | 53.6   | 50.8   | 48.0   | 48.0   |
| 87.5°  | 22.6   | 22.6   | 22.6   | 22.6   | 19.8   | 19.8   | 19.8   | 19.8   | 19.8   | 19.8   | 19.8   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° | 217.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 220°   | 222.5° | 225°   | 227.5° | 230°   | 232.5° | 235°   | 237.5° | 240°   | 242.5° | 245°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 |
| 2.5°   | 1956.2 | 1961.9 | 1967.5 | 1976.0 | 1987.3 | 1995.8 | 2004.2 | 2021.2 | 2040.9 | 2057.9 | 2074.8 |
| 5°     | 1755.8 | 1769.9 | 1784.0 | 1801.0 | 1817.9 | 1832.0 | 1849.0 | 1882.8 | 1916.7 | 1947.8 | 1981.6 |
| 7.5°   | 1439.7 | 1459.4 | 1476.4 | 1504.6 | 1530.0 | 1558.2 | 1583.6 | 1626.0 | 1665.5 | 1707.8 | 1747.4 |
| 10°    | 1177.1 | 1199.7 | 1222.3 | 1259.0 | 1298.5 | 1335.2 | 1371.9 | 1405.8 | 1442.5 | 1476.4 | 1510.2 |
| 12.5°  | 1064.2 | 1089.6 | 1117.9 | 1140.4 | 1165.8 | 1188.4 | 1211.0 | 1250.5 | 1290.0 | 1329.6 | 1369.1 |
| 15°    | 971.1  | 999.3  | 1027.5 | 1055.8 | 1081.2 | 1109.4 | 1134.8 | 1168.7 | 1205.4 | 1239.2 | 1273.1 |
| 17.5°  | 863.8  | 892.0  | 923.1  | 954.1  | 985.2  | 1016.2 | 1047.3 | 1095.3 | 1143.3 | 1188.4 | 1236.4 |
| 20°    | 728.3  | 767.8  | 804.5  | 846.9  | 889.2  | 931.5  | 973.9  | 1024.7 | 1075.5 | 1123.5 | 1174.3 |
| 22.5°  | 592.8  | 629.5  | 666.2  | 717.0  | 767.8  | 815.8  | 866.6  | 934.4  | 999.3  | 1067.0 | 1132.0 |
| 25°    | 494.0  | 527.9  | 561.7  | 618.2  | 671.8  | 728.3  | 781.9  | 863.8  | 942.8  | 1024.7 | 1103.7 |
| 27.5°  | 426.3  | 457.3  | 488.4  | 547.6  | 606.9  | 663.4  | 722.7  | 813.0  | 900.5  | 990.8  | 1078.3 |
| 30°    | 395.2  | 415.0  | 434.7  | 491.2  | 547.6  | 601.3  | 657.7  | 745.2  | 832.7  | 920.3  | 1007.8 |
| 32.5°  | 344.4  | 361.3  | 378.3  | 429.1  | 479.9  | 527.9  | 578.7  | 669.0  | 756.5  | 846.9  | 934.4  |
| 35°    | 304.9  | 319.0  | 333.1  | 381.1  | 426.3  | 474.2  | 519.4  | 609.7  | 700.1  | 790.4  | 880.7  |
| 37.5°  | 282.3  | 296.4  | 307.7  | 350.0  | 395.2  | 437.5  | 479.9  | 570.2  | 657.7  | 748.1  | 835.6  |
| 40°    | 265.3  | 273.8  | 285.1  | 327.5  | 367.0  | 409.3  | 448.8  | 530.7  | 615.4  | 697.2  | 779.1  |
| 42.5°  | 254.1  | 265.3  | 273.8  | 310.5  | 350.0  | 386.7  | 423.4  | 502.5  | 581.5  | 657.7  | 736.8  |
| 45°    | 251.2  | 262.5  | 273.8  | 304.9  | 335.9  | 364.1  | 395.2  | 471.4  | 547.6  | 623.9  | 700.1  |
| 47.5°  | 245.6  | 254.1  | 265.3  | 290.8  | 313.3  | 338.7  | 361.3  | 437.5  | 513.8  | 587.2  | 663.4  |
| 50°    | 242.8  | 245.6  | 251.2  | 273.8  | 296.4  | 319.0  | 341.6  | 417.8  | 494.0  | 570.2  | 646.4  |
| 52.5°  | 239.9  | 239.9  | 239.9  | 259.7  | 279.5  | 296.4  | 316.2  | 392.4  | 471.4  | 547.6  | 623.9  |
| 55°    | 223.0  | 220.2  | 220.2  | 239.9  | 256.9  | 276.6  | 293.6  | 369.8  | 446.0  | 519.4  | 595.6  |
| 57.5°  | 206.1  | 203.2  | 200.4  | 217.4  | 234.3  | 251.2  | 268.2  | 344.4  | 423.4  | 499.6  | 575.9  |
| 60°    | 189.1  | 186.3  | 186.3  | 203.2  | 217.4  | 234.3  | 248.4  | 327.5  | 403.7  | 482.7  | 558.9  |
| 62.5°  | 169.4  | 172.2  | 172.2  | 186.3  | 203.2  | 217.4  | 231.5  | 310.5  | 392.4  | 471.4  | 550.5  |
| 65°    | 155.3  | 158.1  | 158.1  | 175.0  | 192.0  | 208.9  | 225.8  | 302.0  | 381.1  | 457.3  | 533.5  |
| 67.5°  | 144.0  | 146.8  | 146.8  | 166.5  | 183.5  | 203.2  | 220.2  | 287.9  | 358.5  | 426.3  | 494.0  |
| 70°    | 132.7  | 132.7  | 135.5  | 155.3  | 175.0  | 194.8  | 214.5  | 273.8  | 333.1  | 389.6  | 448.8  |
| 72.5°  | 118.6  | 121.4  | 124.2  | 144.0  | 160.9  | 180.7  | 197.6  | 251.2  | 304.9  | 358.5  | 412.1  |
| 75°    | 104.4  | 107.3  | 110.1  | 127.0  | 144.0  | 160.9  | 177.8  | 228.7  | 276.6  | 327.5  | 375.4  |
| 77.5°  | 93.2   | 96.0   | 98.8   | 112.9  | 127.0  | 141.1  | 155.3  | 192.0  | 231.5  | 268.2  | 304.9  |
| 80°    | 76.2   | 76.2   | 79.0   | 90.3   | 101.6  | 110.1  | 121.4  | 146.8  | 172.2  | 194.8  | 220.2  |
| 82.5°  | 56.5   | 59.3   | 59.3   | 67.7   | 73.4   | 81.9   | 87.5   | 101.6  | 112.9  | 127.0  | 138.3  |
| 85°    | 48.0   | 45.2   | 45.2   | 50.8   | 53.6   | 59.3   | 62.1   | 70.6   | 76.2   | 84.7   | 90.3   |
| 87.5°  | 19.8   | 16.9   | 16.9   | 19.8   | 25.4   | 28.2   | 31.1   | 31.1   | 33.9   | 33.9   | 33.9   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° | 245° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°   | 252.5° | 255°   | 257.5° | 260°   | 262.5° | 265°   | 267.5° | 270°   | 272.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 |
| 2.5°   | 2083.3 | 2088.9 | 2097.4 | 2103.0 | 2117.1 | 2128.4 | 2142.6 | 2153.8 | 2162.3 | 2176.4 | 2170.8 |
| 5°     | 2007.1 | 2032.5 | 2057.9 | 2083.3 | 2103.0 | 2122.8 | 2139.7 | 2159.5 | 2182.1 | 2224.4 | 2235.7 |
| 7.5°   | 1781.2 | 1815.1 | 1846.2 | 1880.0 | 1919.5 | 1959.1 | 1998.6 | 2038.1 | 2074.8 | 2128.4 | 2162.3 |
| 10°    | 1558.2 | 1606.2 | 1651.4 | 1699.4 | 1736.1 | 1772.8 | 1806.6 | 1843.3 | 1894.1 | 1947.8 | 2009.9 |
| 12.5°  | 1417.1 | 1465.1 | 1513.1 | 1561.0 | 1614.7 | 1665.5 | 1719.1 | 1769.9 | 1817.9 | 1860.3 | 1930.8 |
| 15°    | 1323.9 | 1377.6 | 1428.4 | 1479.2 | 1544.1 | 1606.2 | 1671.1 | 1733.2 | 1803.8 | 1860.3 | 1908.3 |
| 17.5°  | 1301.3 | 1366.3 | 1428.4 | 1493.3 | 1561.0 | 1628.8 | 1696.5 | 1764.3 | 1834.9 | 1919.5 | 1981.6 |
| 20°    | 1261.8 | 1349.3 | 1436.8 | 1524.3 | 1611.9 | 1696.5 | 1784.0 | 1868.7 | 1961.9 | 2063.5 | 2091.7 |
| 22.5°  | 1239.2 | 1343.7 | 1451.0 | 1555.4 | 1674.0 | 1795.3 | 1913.9 | 2032.5 | 2131.3 | 2207.5 | 2292.2 |
| 25°    | 1236.4 | 1366.3 | 1498.9 | 1628.8 | 1778.4 | 1925.2 | 2074.8 | 2221.6 | 2348.6 | 2424.8 | 2492.6 |
| 27.5°  | 1233.6 | 1391.7 | 1546.9 | 1702.2 | 1885.7 | 2066.3 | 2249.8 | 2430.5 | 2549.0 | 2659.1 | 2715.6 |
| 30°    | 1199.7 | 1388.8 | 1580.8 | 1769.9 | 1976.0 | 2182.1 | 2388.1 | 2594.2 | 2715.6 | 2791.8 | 2820.0 |
| 32.5°  | 1157.4 | 1380.4 | 1603.4 | 1826.4 | 2060.7 | 2295.0 | 2526.5 | 2760.8 | 2856.7 | 2921.7 | 2899.1 |
| 35°    | 1123.5 | 1369.1 | 1611.9 | 1854.6 | 2103.0 | 2354.3 | 2602.7 | 2851.1 | 2989.4 | 3079.7 | 3043.0 |
| 37.5°  | 1092.4 | 1349.3 | 1606.2 | 1863.1 | 2153.8 | 2444.6 | 2735.4 | 3026.1 | 3158.8 | 3254.8 | 3212.4 |
| 40°    | 1055.8 | 1329.6 | 1606.2 | 1880.0 | 2213.1 | 2543.4 | 2876.5 | 3206.8 | 3379.0 | 3460.8 | 3395.9 |
| 42.5°  | 1024.7 | 1309.8 | 1597.7 | 1882.8 | 2238.5 | 2594.2 | 2949.9 | 3305.6 | 3497.5 | 3613.3 | 3531.4 |
| 45°    | 985.2  | 1270.3 | 1552.6 | 1837.7 | 2230.1 | 2622.4 | 3012.0 | 3404.4 | 3627.4 | 3717.7 | 3604.8 |
| 47.5°  | 942.8  | 1225.1 | 1504.6 | 1784.0 | 2201.8 | 2619.6 | 3037.4 | 3455.2 | 3661.3 | 3768.5 | 3664.1 |
| 50°    | 928.7  | 1211.0 | 1490.5 | 1772.8 | 2224.4 | 2678.9 | 3130.6 | 3582.2 | 3731.8 | 3819.3 | 3681.0 |
| 52.5°  | 925.9  | 1225.1 | 1527.2 | 1826.4 | 2280.9 | 2732.5 | 3187.0 | 3638.7 | 3760.1 | 3853.2 | 3729.0 |
| 55°    | 917.4  | 1242.1 | 1563.9 | 1885.7 | 2359.9 | 2837.0 | 3311.2 | 3785.5 | 3906.8 | 3974.6 | 3881.4 |
| 57.5°  | 925.9  | 1275.9 | 1623.1 | 1973.2 | 2461.5 | 2949.9 | 3438.2 | 3926.6 | 4073.4 | 4121.4 | 4101.6 |
| 60°    | 931.5  | 1304.2 | 1674.0 | 2046.6 | 2523.6 | 3000.7 | 3477.8 | 3954.8 | 4107.3 | 4225.8 | 4248.4 |
| 62.5°  | 917.4  | 1284.4 | 1648.6 | 2015.5 | 2447.4 | 2879.3 | 3311.2 | 3743.1 | 3994.3 | 4169.4 | 4271.0 |
| 65°    | 875.1  | 1213.8 | 1555.4 | 1894.1 | 2292.2 | 2693.0 | 3091.0 | 3489.1 | 3754.4 | 4014.1 | 4096.0 |
| 67.5°  | 781.9  | 1069.9 | 1357.8 | 1645.7 | 1992.9 | 2340.2 | 2684.5 | 3031.8 | 3364.9 | 3616.1 | 3729.0 |
| 70°    | 677.5  | 903.3  | 1132.0 | 1357.8 | 1674.0 | 1990.1 | 2306.3 | 2622.4 | 2916.0 | 3192.7 | 3299.9 |
| 72.5°  | 590.0  | 765.0  | 942.8  | 1117.9 | 1343.7 | 1566.7 | 1792.5 | 2015.5 | 2362.7 | 2639.4 | 2743.8 |
| 75°    | 502.5  | 629.5  | 753.7  | 880.7  | 1036.0 | 1191.2 | 1343.7 | 1498.9 | 1744.5 | 1992.9 | 2097.4 |
| 77.5°  | 386.7  | 471.4  | 553.3  | 635.1  | 742.4  | 846.9  | 954.1  | 1058.6 | 1230.8 | 1417.1 | 1470.7 |
| 80°    | 268.2  | 316.2  | 361.3  | 409.3  | 494.0  | 578.7  | 663.4  | 748.1  | 861.0  | 965.4  | 1047.3 |
| 82.5°  | 166.5  | 197.6  | 225.8  | 254.1  | 321.8  | 389.6  | 454.5  | 522.2  | 567.4  | 573.0  | 654.9  |
| 85°    | 107.3  | 127.0  | 144.0  | 160.9  | 200.4  | 242.8  | 282.3  | 321.8  | 287.9  | 268.2  | 319.0  |
| 87.5°  | 42.3   | 53.6   | 62.1   | 70.6   | 67.7   | 64.9   | 62.1   | 59.3   | 50.8   | 45.2   | 56.5   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P676002  
 CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° | 272.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 275°   | 277.5° | 280°   | 282.5° | 285°   | 287.5° | 290°   | 292.5° | 295°   | 297.5° | 300°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 |
| 2.5°   | 2176.4 | 2184.9 | 2193.4 | 2199.0 | 2207.5 | 2210.3 | 2213.1 | 2213.1 | 2215.9 | 2218.8 | 2224.4 |
| 5°     | 2280.9 | 2297.8 | 2314.7 | 2328.9 | 2345.8 | 2359.9 | 2371.2 | 2385.3 | 2396.6 | 2396.6 | 2393.8 |
| 7.5°   | 2193.4 | 2235.7 | 2278.0 | 2320.4 | 2362.7 | 2393.8 | 2422.0 | 2453.1 | 2481.3 | 2486.9 | 2492.6 |
| 10°    | 2077.6 | 2122.8 | 2165.1 | 2210.3 | 2252.6 | 2300.6 | 2345.8 | 2391.0 | 2439.0 | 2447.4 | 2458.7 |
| 12.5°  | 1970.4 | 2024.0 | 2077.6 | 2128.4 | 2182.1 | 2215.9 | 2249.8 | 2280.9 | 2314.7 | 2337.3 | 2359.9 |
| 15°    | 1967.5 | 2012.7 | 2057.9 | 2100.2 | 2145.4 | 2165.1 | 2184.9 | 2201.8 | 2221.6 | 2221.6 | 2224.4 |
| 17.5°  | 2032.5 | 2060.7 | 2088.9 | 2114.3 | 2142.6 | 2145.4 | 2151.0 | 2153.8 | 2156.7 | 2148.2 | 2139.7 |
| 20°    | 2159.5 | 2170.8 | 2182.1 | 2193.4 | 2204.7 | 2184.9 | 2168.0 | 2148.2 | 2128.4 | 2105.9 | 2086.1 |
| 22.5°  | 2345.8 | 2320.4 | 2295.0 | 2269.6 | 2244.2 | 2210.3 | 2173.6 | 2139.7 | 2103.0 | 2074.8 | 2046.6 |
| 25°    | 2520.8 | 2489.8 | 2458.7 | 2427.7 | 2396.6 | 2323.2 | 2249.8 | 2173.6 | 2100.2 | 2069.2 | 2038.1 |
| 27.5°  | 2755.1 | 2707.1 | 2659.1 | 2611.1 | 2563.2 | 2464.4 | 2365.6 | 2266.8 | 2168.0 | 2114.3 | 2063.5 |
| 30°    | 2811.6 | 2757.9 | 2704.3 | 2647.8 | 2594.2 | 2498.2 | 2405.1 | 2309.1 | 2213.1 | 2151.0 | 2091.7 |
| 32.5°  | 2893.4 | 2831.3 | 2769.2 | 2707.1 | 2645.0 | 2551.9 | 2458.7 | 2362.7 | 2269.6 | 2213.1 | 2153.8 |
| 35°    | 3028.9 | 2958.4 | 2887.8 | 2814.4 | 2743.8 | 2647.8 | 2554.7 | 2458.7 | 2362.7 | 2297.8 | 2235.7 |
| 37.5°  | 3144.7 | 3062.8 | 2980.9 | 2899.1 | 2817.2 | 2732.5 | 2645.0 | 2560.3 | 2472.8 | 2407.9 | 2345.8 |
| 40°    | 3274.5 | 3184.2 | 3093.9 | 3006.3 | 2916.0 | 2837.0 | 2757.9 | 2676.1 | 2597.0 | 2546.2 | 2495.4 |
| 42.5°  | 3387.4 | 3277.3 | 3170.1 | 3062.8 | 2952.7 | 2899.1 | 2848.3 | 2794.6 | 2741.0 | 2715.6 | 2687.4 |
| 45°    | 3466.5 | 3364.9 | 3260.4 | 3158.8 | 3057.2 | 3017.6 | 2978.1 | 2938.6 | 2899.1 | 2924.5 | 2949.9 |
| 47.5°  | 3500.3 | 3418.5 | 3339.4 | 3260.4 | 3178.5 | 3192.7 | 3206.8 | 3218.1 | 3232.2 | 3266.1 | 3302.7 |
| 50°    | 3531.4 | 3486.2 | 3438.2 | 3393.1 | 3345.1 | 3398.7 | 3449.5 | 3503.2 | 3556.8 | 3627.4 | 3697.9 |
| 52.5°  | 3593.5 | 3568.1 | 3545.5 | 3520.1 | 3494.7 | 3587.9 | 3681.0 | 3774.2 | 3867.3 | 3946.4 | 4025.4 |
| 55°    | 3779.8 | 3760.1 | 3740.3 | 3717.7 | 3697.9 | 3830.6 | 3960.5 | 4093.1 | 4225.8 | 4307.7 | 4389.5 |
| 57.5°  | 4036.7 | 4025.4 | 4011.3 | 4000.0 | 3985.9 | 4115.7 | 4242.8 | 4369.8 | 4499.6 | 4578.7 | 4660.5 |
| 60°    | 4231.5 | 4234.3 | 4234.3 | 4237.1 | 4237.1 | 4335.9 | 4434.7 | 4536.3 | 4635.1 | 4702.9 | 4773.5 |
| 62.5°  | 4335.9 | 4330.3 | 4324.6 | 4319.0 | 4313.3 | 4395.2 | 4477.1 | 4558.9 | 4640.8 | 4691.6 | 4742.4 |
| 65°    | 4223.0 | 4254.1 | 4285.1 | 4316.2 | 4347.2 | 4358.5 | 4367.0 | 4378.3 | 4386.7 | 4417.8 | 4448.8 |
| 67.5°  | 3844.7 | 3906.8 | 3966.1 | 4028.2 | 4087.5 | 4045.2 | 4005.6 | 3963.3 | 3921.0 | 3929.4 | 3935.1 |
| 70°    | 3424.1 | 3494.7 | 3568.1 | 3638.7 | 3709.2 | 3610.4 | 3511.6 | 3410.0 | 3311.2 | 3277.3 | 3243.5 |
| 72.5°  | 2887.8 | 2949.9 | 3014.8 | 3076.9 | 3139.0 | 3017.6 | 2899.1 | 2777.7 | 2656.3 | 2597.0 | 2537.8 |
| 75°    | 2207.5 | 2280.9 | 2357.1 | 2430.5 | 2503.9 | 2368.4 | 2230.1 | 2094.6 | 1956.2 | 1916.7 | 1880.0 |
| 77.5°  | 1609.0 | 1696.5 | 1784.0 | 1871.6 | 1959.1 | 1837.7 | 1716.3 | 1592.1 | 1470.7 | 1448.1 | 1425.5 |
| 80°    | 1171.5 | 1239.2 | 1304.2 | 1371.9 | 1436.8 | 1366.3 | 1295.7 | 1225.1 | 1154.6 | 1151.7 | 1148.9 |
| 82.5°  | 790.4  | 849.7  | 906.1  | 965.4  | 1021.9 | 993.6  | 968.2  | 940.0  | 911.8  | 940.0  | 971.1  |
| 85°    | 406.5  | 488.4  | 573.0  | 654.9  | 736.8  | 728.3  | 722.7  | 714.2  | 705.7  | 742.4  | 776.3  |
| 87.5°  | 81.9   | 152.4  | 223.0  | 290.8  | 361.3  | 344.4  | 327.5  | 307.7  | 290.8  | 302.0  | 310.5  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° | 300° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305°   | 307.5° | 310°   | 312.5° | 315°   | 317.5° | 320°   | 322.5° | 325°   | 327.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 |
| 2.5°   | 2227.2 | 2230.1 | 2230.1 | 2230.1 | 2230.1 | 2230.1 | 2224.4 | 2221.6 | 2215.9 | 2210.3 | 2201.8 |
| 5°     | 2393.8 | 2391.0 | 2379.7 | 2368.4 | 2354.3 | 2343.0 | 2334.5 | 2323.2 | 2314.7 | 2303.5 | 2286.5 |
| 7.5°   | 2498.2 | 2503.9 | 2484.1 | 2467.2 | 2447.4 | 2427.7 | 2407.9 | 2388.1 | 2368.4 | 2348.6 | 2309.1 |
| 10°    | 2467.2 | 2475.6 | 2464.4 | 2453.1 | 2439.0 | 2427.7 | 2405.1 | 2379.7 | 2357.1 | 2331.7 | 2283.7 |
| 12.5°  | 2379.7 | 2402.3 | 2396.6 | 2391.0 | 2385.3 | 2379.7 | 2365.6 | 2348.6 | 2334.5 | 2317.6 | 2263.9 |
| 15°    | 2224.4 | 2224.4 | 2227.2 | 2230.1 | 2230.1 | 2232.9 | 2235.7 | 2238.5 | 2241.4 | 2244.2 | 2213.1 |
| 17.5°  | 2131.3 | 2122.8 | 2122.8 | 2122.8 | 2122.8 | 2122.8 | 2134.1 | 2148.2 | 2159.5 | 2170.8 | 2162.3 |
| 20°    | 2063.5 | 2043.8 | 2040.9 | 2040.9 | 2038.1 | 2035.3 | 2055.0 | 2077.6 | 2097.4 | 2117.1 | 2128.4 |
| 22.5°  | 2018.3 | 1990.1 | 1987.3 | 1984.5 | 1981.6 | 1978.8 | 2004.2 | 2029.6 | 2055.0 | 2080.4 | 2120.0 |
| 25°    | 2007.1 | 1976.0 | 1978.8 | 1981.6 | 1981.6 | 1984.5 | 2004.2 | 2024.0 | 2043.8 | 2063.5 | 2131.3 |
| 27.5°  | 2009.9 | 1959.1 | 1961.9 | 1964.7 | 1964.7 | 1967.5 | 1998.6 | 2026.8 | 2057.9 | 2086.1 | 2170.8 |
| 30°    | 2029.6 | 1970.4 | 1964.7 | 1959.1 | 1953.4 | 1947.8 | 1990.1 | 2032.5 | 2074.8 | 2117.1 | 2182.1 |
| 32.5°  | 2097.4 | 2040.9 | 2026.8 | 2012.7 | 1998.6 | 1984.5 | 2035.3 | 2083.3 | 2134.1 | 2182.1 | 2235.7 |
| 35°    | 2170.8 | 2108.7 | 2103.0 | 2097.4 | 2088.9 | 2083.3 | 2128.4 | 2176.4 | 2221.6 | 2266.8 | 2314.7 |
| 37.5°  | 2280.9 | 2218.8 | 2213.1 | 2204.7 | 2199.0 | 2190.5 | 2241.4 | 2289.3 | 2340.2 | 2388.1 | 2430.5 |
| 40°    | 2444.6 | 2393.8 | 2391.0 | 2391.0 | 2388.1 | 2385.3 | 2424.8 | 2467.2 | 2506.7 | 2546.2 | 2574.4 |
| 42.5°  | 2662.0 | 2636.6 | 2645.0 | 2656.3 | 2664.8 | 2673.2 | 2704.3 | 2738.2 | 2769.2 | 2800.3 | 2791.8 |
| 45°    | 2975.3 | 3000.7 | 3003.5 | 3006.3 | 3009.2 | 3012.0 | 3020.5 | 3031.8 | 3040.2 | 3048.7 | 3014.8 |
| 47.5°  | 3336.6 | 3370.5 | 3387.4 | 3404.4 | 3418.5 | 3435.4 | 3424.1 | 3410.0 | 3398.7 | 3384.6 | 3299.9 |
| 50°    | 3765.7 | 3836.3 | 3833.4 | 3830.6 | 3825.0 | 3822.2 | 3799.6 | 3777.0 | 3751.6 | 3729.0 | 3604.8 |
| 52.5°  | 4104.4 | 4183.5 | 4197.6 | 4211.7 | 4225.8 | 4239.9 | 4197.6 | 4155.3 | 4110.1 | 4067.7 | 3912.5 |
| 55°    | 4468.6 | 4550.5 | 4553.3 | 4556.1 | 4556.1 | 4558.9 | 4499.6 | 4440.4 | 4378.3 | 4319.0 | 4158.1 |
| 57.5°  | 4739.6 | 4818.6 | 4810.2 | 4804.5 | 4796.0 | 4787.6 | 4717.0 | 4646.4 | 4575.9 | 4505.3 | 4344.4 |
| 60°    | 4841.2 | 4909.0 | 4892.0 | 4875.1 | 4855.3 | 4838.4 | 4784.7 | 4731.1 | 4674.7 | 4621.0 | 4465.8 |
| 62.5°  | 4793.2 | 4844.0 | 4818.6 | 4796.0 | 4770.6 | 4745.2 | 4677.5 | 4606.9 | 4539.2 | 4468.6 | 4355.7 |
| 65°    | 4477.1 | 4508.1 | 4474.2 | 4443.2 | 4412.1 | 4378.3 | 4321.8 | 4265.3 | 4206.1 | 4149.6 | 4073.4 |
| 67.5°  | 3943.5 | 3949.2 | 3946.4 | 3943.5 | 3940.7 | 3937.9 | 3856.0 | 3774.2 | 3689.5 | 3607.6 | 3602.0 |
| 70°    | 3212.4 | 3178.5 | 3184.2 | 3192.7 | 3198.3 | 3203.9 | 3141.8 | 3082.6 | 3020.5 | 2958.4 | 2986.6 |
| 72.5°  | 2478.5 | 2419.2 | 2433.3 | 2450.2 | 2464.4 | 2478.5 | 2427.7 | 2379.7 | 2328.9 | 2278.0 | 2317.6 |
| 75°    | 1840.5 | 1803.8 | 1817.9 | 1834.9 | 1849.0 | 1863.1 | 1843.3 | 1823.6 | 1801.0 | 1781.2 | 1817.9 |
| 77.5°  | 1403.0 | 1380.4 | 1383.2 | 1383.2 | 1386.0 | 1386.0 | 1388.8 | 1394.5 | 1397.3 | 1400.1 | 1439.7 |
| 80°    | 1143.3 | 1140.4 | 1137.6 | 1134.8 | 1129.1 | 1126.3 | 1154.6 | 1182.8 | 1211.0 | 1239.2 | 1259.0 |
| 82.5°  | 999.3  | 1027.5 | 1010.6 | 996.5  | 979.5  | 962.6  | 988.0  | 1013.4 | 1038.8 | 1064.2 | 1055.8 |
| 85°    | 813.0  | 846.9  | 815.8  | 784.8  | 750.9  | 719.8  | 742.4  | 762.2  | 784.8  | 804.5  | 793.2  |
| 87.5°  | 321.8  | 330.3  | 279.5  | 231.5  | 180.7  | 129.9  | 206.1  | 279.5  | 355.7  | 429.1  | 440.4  |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 302.5° | 305° | 307.5° | 310° | 312.5° | 315° | 317.5° | 320° | 322.5° | 325° | 327.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 330°   | 332.5° | 335°   | 337.5° | 340°   | 342.5° | 345°   | 347.5° | 350°   | 352.5° | 355°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 | 2032.5 |
| 2.5°   | 2193.4 | 2182.1 | 2173.6 | 2170.8 | 2165.1 | 2162.3 | 2156.7 | 2151.0 | 2142.6 | 2136.9 | 2128.4 |
| 5°     | 2266.8 | 2249.8 | 2230.1 | 2201.8 | 2176.4 | 2148.2 | 2120.0 | 2094.6 | 2069.2 | 2040.9 | 2015.5 |
| 7.5°   | 2269.6 | 2230.1 | 2190.5 | 2153.8 | 2114.3 | 2077.6 | 2038.1 | 2004.2 | 1967.5 | 1930.8 | 1897.0 |
| 10°    | 2238.5 | 2190.5 | 2142.6 | 2094.6 | 2049.4 | 2001.4 | 1953.4 | 1913.9 | 1871.6 | 1829.2 | 1789.7 |
| 12.5°  | 2213.1 | 2159.5 | 2105.9 | 2049.4 | 1995.8 | 1939.3 | 1882.8 | 1843.3 | 1803.8 | 1764.3 | 1724.8 |
| 15°    | 2182.1 | 2148.2 | 2117.1 | 2066.3 | 2015.5 | 1964.7 | 1913.9 | 1860.3 | 1809.5 | 1755.8 | 1702.2 |
| 17.5°  | 2156.7 | 2148.2 | 2139.7 | 2105.9 | 2072.0 | 2035.3 | 2001.4 | 1947.8 | 1894.1 | 1837.7 | 1784.0 |
| 20°    | 2142.6 | 2153.8 | 2165.1 | 2148.2 | 2131.3 | 2111.5 | 2094.6 | 2055.0 | 2015.5 | 1973.2 | 1933.7 |
| 22.5°  | 2159.5 | 2201.8 | 2241.4 | 2244.2 | 2249.8 | 2252.6 | 2255.5 | 2218.8 | 2182.1 | 2142.6 | 2105.9 |
| 25°    | 2199.0 | 2266.8 | 2334.5 | 2371.2 | 2407.9 | 2447.4 | 2484.1 | 2461.5 | 2439.0 | 2416.4 | 2393.8 |
| 27.5°  | 2252.6 | 2337.3 | 2422.0 | 2475.6 | 2526.5 | 2580.1 | 2633.7 | 2630.9 | 2628.1 | 2622.4 | 2619.6 |
| 30°    | 2244.2 | 2309.1 | 2374.0 | 2439.0 | 2503.9 | 2568.8 | 2633.7 | 2667.6 | 2698.7 | 2732.5 | 2766.4 |
| 32.5°  | 2292.2 | 2345.8 | 2402.3 | 2470.0 | 2537.8 | 2608.3 | 2676.1 | 2746.6 | 2814.4 | 2885.0 | 2955.5 |
| 35°    | 2365.6 | 2413.5 | 2464.4 | 2537.8 | 2614.0 | 2687.4 | 2763.6 | 2848.3 | 2935.8 | 3023.3 | 3108.0 |
| 37.5°  | 2475.6 | 2518.0 | 2563.2 | 2625.3 | 2690.2 | 2752.3 | 2817.2 | 2941.4 | 3065.6 | 3192.7 | 3316.9 |
| 40°    | 2602.7 | 2630.9 | 2659.1 | 2718.4 | 2777.7 | 2837.0 | 2896.3 | 3051.5 | 3206.8 | 3362.0 | 3517.3 |
| 42.5°  | 2786.2 | 2777.7 | 2769.2 | 2817.2 | 2868.0 | 2916.0 | 2966.8 | 3108.0 | 3249.1 | 3390.3 | 3531.4 |
| 45°    | 2980.9 | 2947.1 | 2913.2 | 2935.8 | 2961.2 | 2983.8 | 3009.2 | 3153.1 | 3297.1 | 3443.9 | 3587.9 |
| 47.5°  | 3215.2 | 3130.6 | 3045.9 | 3026.1 | 3006.3 | 2983.8 | 2964.0 | 3119.3 | 3274.5 | 3432.6 | 3587.9 |
| 50°    | 3480.6 | 3353.6 | 3229.4 | 3178.5 | 3124.9 | 3074.1 | 3020.5 | 3147.5 | 3277.3 | 3407.2 | 3534.2 |
| 52.5°  | 3757.2 | 3599.1 | 3443.9 | 3364.9 | 3285.8 | 3203.9 | 3124.9 | 3232.2 | 3342.3 | 3452.4 | 3559.6 |
| 55°    | 3994.3 | 3833.4 | 3669.7 | 3576.6 | 3483.4 | 3390.3 | 3297.1 | 3404.4 | 3511.6 | 3618.9 | 3726.2 |
| 57.5°  | 4183.5 | 4022.6 | 3861.7 | 3774.2 | 3683.8 | 3596.3 | 3506.0 | 3607.6 | 3712.1 | 3816.5 | 3918.1 |
| 60°    | 4313.3 | 4158.1 | 4002.8 | 3918.1 | 3833.4 | 3748.8 | 3664.1 | 3785.5 | 3906.8 | 4031.0 | 4152.4 |
| 62.5°  | 4245.6 | 4132.7 | 4019.8 | 3983.1 | 3946.4 | 3906.8 | 3870.1 | 3985.9 | 4098.8 | 4214.5 | 4330.3 |
| 65°    | 3997.2 | 3921.0 | 3844.7 | 3881.4 | 3921.0 | 3957.7 | 3997.2 | 4073.4 | 4149.6 | 4228.6 | 4304.9 |
| 67.5°  | 3593.5 | 3587.9 | 3579.4 | 3661.3 | 3743.1 | 3827.8 | 3909.7 | 3960.5 | 4008.5 | 4059.3 | 4110.1 |
| 70°    | 3014.8 | 3045.9 | 3074.1 | 3215.2 | 3356.4 | 3497.5 | 3638.7 | 3658.4 | 3678.2 | 3697.9 | 3717.7 |
| 72.5°  | 2359.9 | 2399.4 | 2441.8 | 2628.1 | 2811.6 | 2997.9 | 3184.2 | 3172.9 | 3161.6 | 3147.5 | 3136.2 |
| 75°    | 1857.4 | 1894.1 | 1933.7 | 2105.9 | 2278.0 | 2450.2 | 2622.4 | 2574.4 | 2529.3 | 2481.3 | 2433.3 |
| 77.5°  | 1482.0 | 1521.5 | 1563.9 | 1724.8 | 1885.7 | 2049.4 | 2210.3 | 2094.6 | 1978.8 | 1863.1 | 1747.4 |
| 80°    | 1275.9 | 1295.7 | 1312.6 | 1422.7 | 1530.0 | 1640.1 | 1750.2 | 1631.6 | 1510.2 | 1388.8 | 1270.3 |
| 82.5°  | 1047.3 | 1036.0 | 1027.5 | 1092.4 | 1157.4 | 1222.3 | 1287.2 | 1174.3 | 1061.4 | 945.7  | 832.7  |
| 85°    | 781.9  | 770.6  | 759.3  | 793.2  | 827.1  | 863.8  | 897.7  | 767.8  | 638.0  | 505.3  | 375.4  |
| 87.5°  | 454.5  | 465.8  | 477.1  | 513.8  | 550.5  | 590.0  | 626.7  | 494.0  | 361.3  | 225.8  | 93.2   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 330° | 332.5° | 335° | 337.5° | 340° | 342.5° | 345° | 347.5° | 350° | 352.5° | 355° |
|--------|------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P676002  
 CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360°   |
|--------|--------|--------|
| 0°     | 2032.5 | 2032.5 |
| 2.5°   | 2111.5 | 2097.4 |
| 5°     | 1995.8 | 1976.0 |
| 7.5°   | 1868.7 | 1843.3 |
| 10°    | 1753.0 | 1719.1 |
| 12.5°  | 1679.6 | 1637.3 |
| 15°    | 1651.4 | 1600.6 |
| 17.5°  | 1736.1 | 1688.1 |
| 20°    | 1865.9 | 1801.0 |
| 22.5°  | 2024.0 | 1945.0 |
| 25°    | 2297.8 | 2201.8 |
| 27.5°  | 2520.8 | 2422.0 |
| 30°    | 2659.1 | 2551.9 |
| 32.5°  | 2811.6 | 2670.4 |
| 35°    | 2969.6 | 2834.2 |
| 37.5°  | 3161.6 | 3009.2 |
| 40°    | 3359.2 | 3201.1 |
| 42.5°  | 3427.0 | 3325.3 |
| 45°    | 3491.9 | 3395.9 |
| 47.5°  | 3506.0 | 3427.0 |
| 50°    | 3520.1 | 3508.8 |
| 52.5°  | 3559.6 | 3556.8 |
| 55°    | 3729.0 | 3731.8 |
| 57.5°  | 3937.9 | 3954.8 |
| 60°    | 4129.8 | 4110.1 |
| 62.5°  | 4228.6 | 4127.0 |
| 65°    | 4160.9 | 4019.8 |
| 67.5°  | 3957.7 | 3805.2 |
| 70°    | 3511.6 | 3305.6 |
| 72.5°  | 2955.5 | 2774.9 |
| 75°    | 2278.0 | 2125.6 |
| 77.5°  | 1620.3 | 1493.3 |
| 80°    | 1140.4 | 1013.4 |
| 82.5°  | 731.1  | 629.5  |
| 85°    | 330.3  | 287.9  |
| 87.5°  | 93.2   | 90.3   |
| 90°    | 0.0    | 0.0    |
| 92.5°  | 0.0    | 0.0    |
| 95°    | 0.0    | 0.0    |
| 97.5°  | 0.0    | 0.0    |
| 100°   | 0.0    | 0.0    |
| 102.5° | 0.0    | 0.0    |
| 105°   | 0.0    | 0.0    |
| 107.5° | 0.0    | 0.0    |
| 110°   | 0.0    | 0.0    |

REPORT NUMBER: P676002

CATALOG NUMBER: CCW-SA-1F-750-U-SLR

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

(END OF REPORT)