

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: INVUE

Report Number: P676017

Luminaire Tested: **CCW-SA-2D-760-U-SLR**

Issue Date: 04/25/2023

Test Information

Test Method: LM-79-08
Report Number: P676017
Test Lab: INNOVATION CENTER(G1)
Issue Date: 04/25/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: INVUE
Catalog Number: CCW-SA-2D-760-U-SLR
Description: INVUE CLEAR CURVE Wall Pack MOUNT LIGHT SQUARE LUMINAIRE @800mA w/
SLR distribution lens
Light Source: (32) 5700K CCT, 70 CRI LEDs
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9467.3 lumens
Efficiency: N/A
Efficacy: 117.2 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B2 - U0 - G3

Input Watts (W): 80.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 13.4 fc

Type IV - Short - N/A

REPORT NUMBER: P676017
CATALOG NUMBER: CCW-SA-2D-760-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1948.0	0.0	1948.0
	% Fixture	20.6	0.0	20.6
Street Side	Lumens	7519.4	0.0	7519.4
	% Fixture	79.4	0.0	79.4
Total	Lumens	9467.3	0.0	9467.3
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.9	2.5
10°-20°	496.0	5.2
20°-30°	725.7	7.7
30°-40°	1022.3	10.8
40°-50°	1404.8	14.8
50°-60°	1914.8	20.2
60°-70°	2095.7	22.1
70°-80°	1210.3	12.8
80°-90°	362.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	9467.3	100.0
0°-180°	9467.3	100.0

Coefficient of Utilization



REPORT NUMBER: P676017


CATALOG NUMBER: CCW-SA-2D-760-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	972.3	10.3			
FM	(30°-60°)	3454.9	36.5			
FH	(60°-80°)	2784.0	29.4			G2/5000
FVH	(80°-90°)	308.2	3.3			G3/500
BL	(0°-30°)	484.3	5.1	B1/500		
BM	(30°-60°)	887.0	9.4	B1/1000		
BH	(60°-80°)	522.1	5.5	B2/1000		G2/1000
BVH	(80°-90°)	54.6	0.6			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Short



REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3
2.5°	3119.9	3103.1	3090.5	3077.9	3061.1	3048.5	3031.7	3014.9	2993.9	2977.1	2956.1
5°	2939.3	2888.9	2838.5	2809.1	2775.5	2746.1	2712.6	2674.8	2637.0	2595.0	2557.2
7.5°	2741.9	2679.0	2616.0	2565.6	2511.0	2460.6	2406.0	2359.8	2313.6	2267.5	2221.3
10°	2557.2	2498.4	2439.6	2376.6	2309.5	2246.5	2179.3	2116.3	2053.3	1990.3	1927.3
12.5°	2435.4	2364.0	2296.9	2225.5	2158.3	2086.9	2015.5	1956.7	1897.9	1835.0	1776.2
15°	2380.8	2313.6	2250.7	2179.3	2107.9	2036.5	1965.1	1897.9	1835.0	1767.8	1700.6
17.5°	2511.0	2414.4	2317.8	2225.5	2133.1	2040.7	1948.3	1864.4	1780.4	1696.4	1612.4
20°	2679.0	2557.2	2439.6	2326.2	2208.7	2095.3	1977.7	1860.2	1742.6	1625.0	1507.4
22.5°	2893.1	2754.5	2620.2	2473.2	2322.0	2175.1	2023.9	1877.0	1730.0	1578.8	1431.9
25°	3275.2	3111.5	2947.7	2737.7	2523.6	2313.6	2099.5	1906.3	1717.4	1524.2	1331.1
27.5°	3602.7	3380.2	3161.8	2909.9	2658.0	2406.0	2154.1	1931.5	1713.2	1490.6	1268.1
30°	3795.9	3577.5	3359.2	3052.7	2750.3	2443.8	2137.3	1889.6	1646.0	1398.3	1150.5
32.5°	3972.3	3728.7	3485.2	3149.3	2809.1	2473.2	2133.1	1860.2	1591.4	1318.5	1045.6
35°	4215.8	3947.1	3682.5	3292.0	2901.5	2511.0	2120.5	1839.2	1553.6	1272.3	986.8
37.5°	4476.1	4144.4	3816.9	3384.4	2951.9	2519.4	2086.9	1809.8	1532.6	1255.5	978.4
40°	4761.7	4358.6	3959.7	3481.0	3006.5	2527.8	2049.1	1772.0	1494.8	1213.5	936.4
42.5°	4946.4	4509.7	4073.0	3556.6	3044.3	2527.8	2011.3	1738.4	1465.5	1188.3	915.4
45°	5051.4	4627.3	4207.4	3648.9	3090.5	2532.0	1973.5	1704.8	1436.1	1163.1	894.4
47.5°	5097.6	4702.9	4308.2	3720.3	3136.7	2548.8	1960.9	1688.0	1410.9	1137.9	860.8
50°	5219.4	4870.8	4522.3	3892.5	3266.8	2637.0	2007.1	1713.2	1423.5	1129.5	835.6
52.5°	5290.7	4992.6	4694.5	4047.8	3401.2	2754.5	2107.9	1780.4	1452.9	1125.3	797.8
55°	5551.1	5265.5	4980.0	4291.4	3598.5	2909.9	2217.1	1856.0	1494.8	1129.5	768.4
57.5°	5882.8	5580.5	5282.3	4539.1	3795.9	3052.7	2309.5	1923.1	1532.6	1146.3	755.8
60°	6113.7	5819.8	5530.1	4740.7	3947.1	3157.6	2364.0	1960.9	1557.8	1150.5	747.4
62.5°	6138.9	5761.0	5387.3	4618.9	3850.5	3077.9	2309.5	1918.9	1528.4	1133.7	743.2
65°	5979.4	5538.5	5097.6	4362.8	3627.9	2893.1	2158.3	1801.4	1444.5	1083.3	726.4
67.5°	5660.3	5143.8	4627.3	3955.5	3283.6	2611.8	1939.9	1633.4	1331.1	1024.6	718.0
70°	4917.0	4463.5	4014.2	3430.6	2851.1	2267.5	1683.8	1431.9	1184.1	932.2	680.2
72.5°	4127.6	3703.5	3283.6	2809.1	2338.8	1864.4	1389.9	1200.9	1012.0	818.8	629.9
75°	3161.8	2842.7	2527.8	2175.1	1822.4	1465.5	1112.7	974.2	835.6	697.0	558.5
77.5°	2221.3	2049.1	1881.2	1616.6	1352.1	1087.5	823.0	730.6	638.2	545.9	453.5
80°	1507.4	1410.9	1318.5	1129.5	940.6	747.4	558.5	499.7	436.7	377.9	314.9
82.5°	936.4	932.2	923.8	793.6	663.4	533.3	403.1	352.7	306.5	256.1	205.8
85°	428.3	499.7	566.9	495.5	424.1	352.7	281.3	247.7	214.1	176.4	142.8
87.5°	134.4	163.8	189.0	180.6	168.0	159.6	147.0	126.0	105.0	84.0	63.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017
 CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3
2.5°	2939.3	2926.7	2909.9	2893.1	2872.1	2855.3	2834.3	2813.3	2809.1	2800.7	2796.5
5°	2532.0	2506.8	2477.4	2452.2	2427.0	2397.6	2372.4	2343.0	2322.0	2296.9	2275.9
7.5°	2175.1	2133.1	2086.9	2040.7	1998.7	1956.7	1910.5	1868.6	1847.6	1826.6	1805.6
10°	1889.6	1847.6	1809.8	1767.8	1738.4	1713.2	1683.8	1654.4	1629.2	1604.0	1578.8
12.5°	1746.8	1717.4	1688.0	1658.6	1625.0	1595.6	1562.0	1528.4	1499.0	1473.8	1444.5
15°	1658.6	1616.6	1570.4	1528.4	1482.2	1440.3	1394.1	1347.9	1314.3	1284.9	1251.3
17.5°	1553.6	1490.6	1431.9	1368.9	1318.5	1268.1	1213.5	1163.1	1125.3	1083.3	1045.6
20°	1436.1	1364.7	1289.1	1217.7	1158.9	1104.3	1045.6	986.8	944.8	898.6	856.6
22.5°	1335.3	1242.9	1146.3	1049.8	986.8	923.8	856.6	793.6	755.8	713.8	676.0
25°	1226.1	1125.3	1020.4	915.4	852.4	785.2	722.2	655.0	625.7	600.5	571.1
27.5°	1167.3	1066.5	961.6	860.8	802.0	739.0	680.2	617.3	596.3	571.1	550.1
30°	1049.8	953.2	852.4	751.6	709.6	671.8	629.9	587.9	579.5	575.3	566.9
32.5°	944.8	844.0	743.2	642.4	604.7	566.9	529.1	491.3	487.1	478.7	474.5
35°	890.2	793.6	692.8	596.3	562.7	524.9	491.3	453.5	445.1	432.5	424.1
37.5°	877.6	776.8	671.8	571.1	537.5	503.9	466.1	432.5	424.1	415.7	407.3
40°	844.0	747.4	655.0	558.5	524.9	491.3	453.5	419.9	411.5	403.1	394.7
42.5°	818.8	726.4	629.9	533.3	503.9	474.5	440.9	411.5	403.1	394.7	382.1
45°	797.8	701.2	600.5	503.9	482.9	461.9	436.7	415.7	407.3	394.7	386.3
47.5°	764.2	671.8	575.3	478.7	457.7	440.9	419.9	398.9	390.5	382.1	373.7
50°	739.0	642.4	545.9	449.3	432.5	415.7	398.9	382.1	382.1	386.3	386.3
52.5°	705.4	613.1	520.7	428.3	411.5	394.7	377.9	361.1	365.3	369.5	373.7
55°	676.0	587.9	495.5	403.1	386.3	369.5	348.5	331.7	335.9	340.1	344.3
57.5°	663.4	571.1	478.7	386.3	369.5	348.5	331.7	310.7	310.7	310.7	310.7
60°	655.0	558.5	466.1	369.5	348.5	331.7	310.7	289.7	285.5	285.5	281.3
62.5°	650.8	554.3	461.9	365.3	340.1	319.1	293.9	268.7	264.5	260.3	256.1
65°	634.0	545.9	453.5	361.1	331.7	306.5	277.1	247.7	243.5	243.5	239.3
67.5°	629.9	537.5	449.3	356.9	327.5	293.9	264.5	230.9	226.7	222.5	218.3
70°	596.3	516.5	432.5	348.5	314.9	285.5	251.9	218.3	214.1	205.8	201.6
72.5°	554.3	482.9	407.3	331.7	298.1	264.5	230.9	197.4	193.2	189.0	180.6
75°	491.3	424.1	356.9	289.7	260.3	235.1	205.8	176.4	172.2	168.0	159.6
77.5°	403.1	348.5	298.1	243.5	222.5	201.6	180.6	159.6	155.4	151.2	142.8
80°	285.5	251.9	222.5	189.0	176.4	159.6	147.0	130.2	130.2	126.0	126.0
82.5°	189.0	172.2	155.4	138.6	130.2	121.8	113.4	105.0	105.0	100.8	100.8
85°	134.4	126.0	113.4	105.0	100.8	92.4	88.2	79.8	79.8	79.8	79.8
87.5°	63.0	63.0	58.8	58.8	54.6	54.6	50.4	46.2	46.2	46.2	46.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017
 CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3
2.5°	2788.1	2775.5	2762.9	2746.1	2733.5	2716.8	2695.8	2679.0	2658.0	2658.0	2653.8
5°	2250.7	2238.1	2225.5	2208.7	2196.1	2179.3	2166.7	2149.9	2133.1	2133.1	2128.9
7.5°	1784.6	1759.4	1734.2	1704.8	1679.6	1662.8	1646.0	1625.0	1608.2	1595.6	1583.0
10°	1553.6	1528.4	1499.0	1473.8	1444.5	1423.5	1402.5	1377.3	1356.3	1339.5	1322.7
12.5°	1415.1	1385.7	1356.3	1326.9	1297.5	1268.1	1242.9	1213.5	1184.1	1163.1	1142.1
15°	1217.7	1188.3	1158.9	1129.5	1100.1	1066.5	1033.0	995.2	961.6	944.8	932.2
17.5°	1003.6	974.2	940.6	911.2	877.6	852.4	827.2	802.0	776.8	760.0	747.4
20°	810.4	776.8	743.2	709.6	676.0	659.2	642.4	625.7	608.9	596.3	587.9
22.5°	634.0	613.1	596.3	575.3	554.3	541.7	533.3	520.7	508.1	508.1	508.1
25°	541.7	529.1	520.7	508.1	495.5	491.3	487.1	478.7	474.5	470.3	470.3
27.5°	524.9	512.3	499.7	487.1	474.5	470.3	466.1	457.7	453.5	453.5	453.5
30°	558.5	554.3	550.1	545.9	541.7	533.3	520.7	512.3	499.7	491.3	482.9
32.5°	466.1	461.9	461.9	457.7	453.5	461.9	466.1	474.5	478.7	482.9	487.1
35°	411.5	403.1	394.7	386.3	377.9	373.7	369.5	365.3	361.1	361.1	356.9
37.5°	398.9	390.5	382.1	373.7	365.3	361.1	356.9	352.7	348.5	348.5	344.3
40°	386.3	377.9	373.7	365.3	356.9	352.7	348.5	340.1	335.9	331.7	331.7
42.5°	373.7	369.5	361.1	356.9	348.5	344.3	340.1	331.7	327.5	323.3	319.1
45°	373.7	365.3	356.9	348.5	340.1	335.9	327.5	323.3	314.9	314.9	310.7
47.5°	365.3	356.9	348.5	340.1	331.7	327.5	319.1	314.9	306.5	302.3	298.1
50°	386.3	373.7	356.9	344.3	327.5	323.3	314.9	310.7	302.3	298.1	293.9
52.5°	377.9	365.3	348.5	335.9	319.1	310.7	306.5	298.1	289.7	285.5	281.3
55°	348.5	335.9	327.5	314.9	302.3	293.9	285.5	277.1	268.7	264.5	264.5
57.5°	310.7	306.5	302.3	298.1	293.9	285.5	277.1	264.5	256.1	251.9	247.7
60°	277.1	281.3	285.5	289.7	293.9	281.3	268.7	256.1	243.5	239.3	235.1
62.5°	251.9	260.3	268.7	272.9	281.3	268.7	256.1	243.5	230.9	226.7	222.5
65°	235.1	239.3	239.3	243.5	243.5	235.1	230.9	222.5	214.1	210.0	210.0
67.5°	214.1	214.1	214.1	210.0	210.0	205.8	205.8	201.6	197.4	193.2	193.2
70°	193.2	193.2	193.2	189.0	189.0	184.8	184.8	180.6	176.4	176.4	172.2
72.5°	176.4	176.4	172.2	172.2	168.0	168.0	168.0	163.8	163.8	159.6	159.6
75°	155.4	155.4	151.2	151.2	147.0	147.0	147.0	142.8	142.8	142.8	138.6
77.5°	138.6	138.6	134.4	134.4	130.2	130.2	130.2	126.0	126.0	121.8	121.8
80°	121.8	121.8	117.6	117.6	113.4	113.4	109.2	109.2	105.0	105.0	100.8
82.5°	96.6	96.6	96.6	96.6	96.6	92.4	92.4	88.2	84.0	84.0	79.8
85°	79.8	79.8	79.8	75.6	75.6	75.6	71.4	71.4	67.2	63.0	63.0
87.5°	46.2	46.2	46.2	42.0	42.0	42.0	42.0	42.0	42.0	42.0	37.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017
 CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3
2.5°	2653.8	2649.6	2632.8	2616.0	2632.8	2649.6	2649.6	2649.6	2645.4	2645.4	2645.4
5°	2128.9	2124.7	2116.3	2107.9	2107.9	2103.7	2112.1	2120.5	2128.9	2137.3	2145.7
7.5°	1566.2	1553.6	1541.0	1528.4	1536.8	1541.0	1553.6	1562.0	1574.6	1583.0	1604.0
10°	1305.9	1289.1	1276.5	1263.9	1255.5	1247.1	1238.7	1234.5	1226.1	1217.7	1226.1
12.5°	1116.9	1095.9	1074.9	1049.8	1045.6	1041.4	1033.0	1024.6	1016.2	1007.8	1003.6
15°	915.4	898.6	890.2	877.6	860.8	844.0	835.6	831.4	823.0	814.6	810.4
17.5°	730.6	713.8	701.2	688.6	684.4	676.0	676.0	676.0	676.0	676.0	676.0
20°	575.3	562.7	562.7	558.5	558.5	554.3	558.5	562.7	562.7	566.9	571.1
22.5°	503.9	503.9	499.7	495.5	499.7	499.7	503.9	508.1	512.3	516.5	520.7
25°	466.1	461.9	466.1	470.3	470.3	470.3	474.5	474.5	478.7	478.7	478.7
27.5°	449.3	449.3	453.5	453.5	457.7	457.7	457.7	453.5	453.5	449.3	449.3
30°	474.5	466.1	466.1	466.1	461.9	457.7	453.5	453.5	449.3	445.1	440.9
32.5°	491.3	495.5	491.3	482.9	478.7	470.3	466.1	457.7	453.5	445.1	436.7
35°	356.9	352.7	361.1	365.3	369.5	373.7	377.9	382.1	382.1	386.3	386.3
37.5°	344.3	340.1	340.1	335.9	335.9	335.9	335.9	335.9	331.7	331.7	335.9
40°	327.5	323.3	323.3	319.1	319.1	314.9	314.9	314.9	314.9	314.9	314.9
42.5°	314.9	310.7	310.7	310.7	310.7	306.5	306.5	302.3	302.3	298.1	298.1
45°	310.7	306.5	302.3	298.1	298.1	293.9	293.9	293.9	289.7	289.7	289.7
47.5°	293.9	289.7	289.7	285.5	285.5	281.3	281.3	281.3	277.1	277.1	277.1
50°	285.5	281.3	281.3	277.1	277.1	272.9	272.9	272.9	268.7	268.7	268.7
52.5°	272.9	268.7	268.7	268.7	264.5	260.3	260.3	260.3	256.1	256.1	256.1
55°	260.3	256.1	256.1	256.1	251.9	247.7	247.7	247.7	243.5	243.5	243.5
57.5°	243.5	239.3	239.3	235.1	235.1	235.1	235.1	235.1	230.9	230.9	230.9
60°	230.9	226.7	226.7	222.5	222.5	218.3	218.3	218.3	218.3	218.3	218.3
62.5°	218.3	214.1	210.0	205.8	210.0	210.0	210.0	210.0	205.8	205.8	205.8
65°	205.8	201.6	197.4	193.2	193.2	193.2	193.2	193.2	193.2	193.2	193.2
67.5°	189.0	184.8	180.6	176.4	180.6	180.6	180.6	180.6	180.6	180.6	180.6
70°	172.2	168.0	168.0	163.8	163.8	159.6	159.6	163.8	163.8	163.8	163.8
72.5°	155.4	151.2	151.2	147.0	147.0	147.0	147.0	147.0	147.0	147.0	147.0
75°	138.6	134.4	134.4	130.2	130.2	130.2	130.2	130.2	130.2	130.2	130.2
77.5°	117.6	113.4	113.4	113.4	113.4	113.4	113.4	117.6	117.6	117.6	117.6
80°	100.8	96.6	96.6	96.6	96.6	96.6	96.6	96.6	96.6	96.6	96.6
82.5°	79.8	75.6	75.6	75.6	75.6	75.6	75.6	75.6	75.6	75.6	75.6
85°	58.8	54.6	54.6	54.6	58.8	58.8	58.8	58.8	58.8	58.8	58.8
87.5°	37.8	33.6	33.6	33.6	37.8	37.8	37.8	37.8	33.6	33.6	33.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3
2.5°	2645.4	2645.4	2645.4	2641.2	2637.0	2632.8	2628.6	2641.2	2649.6	2662.2	2670.6
5°	2149.9	2158.3	2162.5	2175.1	2187.7	2200.3	2212.9	2221.3	2229.7	2233.9	2242.3
7.5°	1620.8	1641.8	1658.6	1675.4	1692.2	1704.8	1721.6	1734.2	1746.8	1759.4	1772.0
10°	1230.3	1238.7	1242.9	1259.7	1272.3	1289.1	1301.7	1314.3	1326.9	1335.3	1347.9
12.5°	999.4	991.0	986.8	986.8	986.8	986.8	986.8	995.2	1003.6	1012.0	1020.4
15°	806.2	802.0	797.8	793.6	789.4	781.0	776.8	785.2	793.6	802.0	810.4
17.5°	676.0	676.0	676.0	671.8	667.6	663.4	659.2	663.4	667.6	667.6	671.8
20°	579.5	583.7	587.9	592.1	592.1	596.3	596.3	600.5	604.7	604.7	608.9
22.5°	520.7	524.9	524.9	524.9	529.1	529.1	529.1	533.3	537.5	541.7	545.9
25°	474.5	474.5	470.3	470.3	474.5	474.5	474.5	474.5	478.7	478.7	478.7
27.5°	449.3	445.1	445.1	445.1	445.1	440.9	440.9	440.9	440.9	440.9	440.9
30°	436.7	432.5	428.3	424.1	424.1	419.9	415.7	415.7	415.7	415.7	415.7
32.5°	432.5	424.1	415.7	411.5	411.5	407.3	403.1	398.9	398.9	394.7	390.5
35°	386.3	382.1	382.1	377.9	373.7	369.5	365.3	365.3	365.3	361.1	361.1
37.5°	335.9	340.1	340.1	340.1	344.3	344.3	344.3	344.3	348.5	348.5	348.5
40°	314.9	314.9	314.9	319.1	323.3	323.3	327.5	327.5	331.7	331.7	331.7
42.5°	298.1	293.9	293.9	298.1	298.1	302.3	302.3	306.5	310.7	310.7	314.9
45°	289.7	285.5	285.5	285.5	285.5	281.3	281.3	285.5	289.7	293.9	298.1
47.5°	272.9	272.9	268.7	268.7	268.7	268.7	268.7	268.7	272.9	272.9	272.9
50°	264.5	264.5	260.3	260.3	260.3	260.3	260.3	260.3	260.3	260.3	260.3
52.5°	256.1	251.9	251.9	251.9	251.9	247.7	247.7	247.7	247.7	247.7	247.7
55°	243.5	239.3	239.3	239.3	239.3	239.3	239.3	239.3	243.5	243.5	243.5
57.5°	230.9	226.7	226.7	226.7	230.9	230.9	230.9	230.9	235.1	235.1	235.1
60°	218.3	218.3	218.3	218.3	218.3	218.3	218.3	222.5	222.5	226.7	226.7
62.5°	205.8	205.8	205.8	205.8	210.0	210.0	210.0	210.0	214.1	214.1	214.1
65°	193.2	193.2	193.2	193.2	197.4	197.4	197.4	197.4	197.4	197.4	197.4
67.5°	180.6	180.6	180.6	180.6	180.6	180.6	180.6	184.8	184.8	189.0	189.0
70°	163.8	159.6	159.6	163.8	163.8	168.0	168.0	172.2	172.2	176.4	176.4
72.5°	147.0	147.0	147.0	147.0	147.0	147.0	147.0	151.2	155.4	155.4	159.6
75°	130.2	130.2	130.2	130.2	134.4	134.4	134.4	138.6	138.6	142.8	142.8
77.5°	117.6	113.4	113.4	113.4	117.6	117.6	117.6	121.8	121.8	126.0	126.0
80°	96.6	96.6	96.6	96.6	100.8	100.8	100.8	100.8	105.0	105.0	105.0
82.5°	79.8	79.8	79.8	79.8	79.8	79.8	79.8	79.8	84.0	84.0	84.0
85°	58.8	58.8	58.8	58.8	63.0	63.0	63.0	63.0	63.0	63.0	63.0
87.5°	37.8	37.8	37.8	37.8	37.8	37.8	37.8	37.8	42.0	42.0	42.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017
 CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3
2.5°	2670.6	2670.6	2670.6	2670.6	2679.0	2683.2	2691.6	2695.8	2691.6	2687.4	2679.0
5°	2246.5	2250.7	2250.7	2254.9	2254.9	2254.9	2254.9	2254.9	2263.3	2271.7	2280.1
7.5°	1776.2	1780.4	1784.6	1788.8	1788.8	1788.8	1784.6	1784.6	1788.8	1788.8	1793.0
10°	1360.5	1377.3	1389.9	1402.5	1394.1	1381.5	1373.1	1360.5	1360.5	1360.5	1356.3
12.5°	1028.8	1033.0	1041.4	1045.6	1041.4	1041.4	1037.2	1033.0	1037.2	1045.6	1049.8
15°	814.6	814.6	818.8	818.8	823.0	827.2	827.2	831.4	839.8	844.0	852.4
17.5°	676.0	680.2	680.2	684.4	684.4	688.6	688.6	688.6	697.0	705.4	718.0
20°	608.9	608.9	608.9	608.9	608.9	604.7	604.7	600.5	604.7	613.1	617.3
22.5°	545.9	550.1	550.1	550.1	545.9	541.7	533.3	529.1	529.1	533.3	533.3
25°	478.7	474.5	474.5	470.3	470.3	474.5	474.5	474.5	478.7	478.7	482.9
27.5°	440.9	436.7	436.7	432.5	432.5	436.7	436.7	436.7	436.7	436.7	436.7
30°	411.5	411.5	407.3	403.1	407.3	407.3	411.5	411.5	415.7	415.7	419.9
32.5°	390.5	386.3	386.3	382.1	386.3	386.3	390.5	390.5	394.7	398.9	398.9
35°	361.1	361.1	361.1	361.1	361.1	361.1	356.9	356.9	356.9	356.9	356.9
37.5°	344.3	344.3	340.1	335.9	335.9	335.9	335.9	335.9	331.7	327.5	323.3
40°	331.7	327.5	327.5	323.3	319.1	319.1	314.9	310.7	310.7	306.5	306.5
42.5°	314.9	310.7	310.7	306.5	302.3	302.3	298.1	293.9	293.9	293.9	289.7
45°	293.9	293.9	289.7	285.5	285.5	285.5	281.3	281.3	281.3	281.3	277.1
47.5°	272.9	272.9	268.7	268.7	268.7	268.7	264.5	264.5	264.5	264.5	264.5
50°	260.3	260.3	260.3	260.3	260.3	260.3	256.1	256.1	256.1	256.1	256.1
52.5°	247.7	247.7	247.7	247.7	247.7	247.7	247.7	247.7	247.7	247.7	247.7
55°	243.5	243.5	243.5	243.5	243.5	243.5	239.3	239.3	239.3	243.5	243.5
57.5°	235.1	235.1	230.9	230.9	230.9	230.9	230.9	230.9	230.9	230.9	230.9
60°	226.7	226.7	226.7	226.7	226.7	226.7	226.7	226.7	226.7	226.7	226.7
62.5°	214.1	214.1	214.1	214.1	214.1	218.3	218.3	218.3	218.3	218.3	214.1
65°	197.4	201.6	201.6	201.6	201.6	201.6	201.6	201.6	201.6	201.6	201.6
67.5°	189.0	189.0	189.0	189.0	189.0	189.0	189.0	189.0	189.0	189.0	189.0
70°	176.4	176.4	172.2	172.2	172.2	176.4	176.4	176.4	176.4	176.4	176.4
72.5°	159.6	159.6	159.6	159.6	159.6	159.6	159.6	159.6	159.6	163.8	163.8
75°	142.8	142.8	142.8	142.8	142.8	142.8	142.8	142.8	142.8	142.8	142.8
77.5°	126.0	126.0	121.8	121.8	121.8	126.0	126.0	126.0	126.0	130.2	130.2
80°	105.0	105.0	105.0	105.0	105.0	105.0	105.0	105.0	105.0	109.2	109.2
82.5°	84.0	84.0	84.0	84.0	84.0	84.0	84.0	84.0	84.0	88.2	88.2
85°	63.0	67.2	67.2	67.2	67.2	67.2	67.2	67.2	67.2	71.4	71.4
87.5°	42.0	42.0	42.0	42.0	42.0	42.0	37.8	37.8	37.8	37.8	33.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017
 CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3
2.5°	2674.8	2679.0	2683.2	2683.2	2687.4	2691.6	2691.6	2708.4	2725.2	2733.5	2741.9
5°	2288.5	2284.3	2284.3	2280.1	2275.9	2288.5	2301.1	2326.2	2351.4	2355.6	2364.0
7.5°	1793.0	1797.2	1801.4	1801.4	1805.6	1793.0	1776.2	1780.4	1784.6	1805.6	1822.4
10°	1356.3	1360.5	1364.7	1364.7	1368.9	1364.7	1356.3	1368.9	1381.5	1398.3	1419.3
12.5°	1053.9	1066.5	1079.1	1087.5	1100.1	1108.5	1112.7	1129.5	1142.1	1163.1	1184.1
15°	860.8	869.2	877.6	886.0	894.4	902.8	911.2	928.0	944.8	970.0	995.2
17.5°	726.4	726.4	730.6	730.6	730.6	739.0	747.4	755.8	760.0	785.2	810.4
20°	621.5	617.3	613.1	608.9	604.7	613.1	617.3	621.5	625.7	642.4	655.0
22.5°	533.3	533.3	537.5	537.5	537.5	533.3	524.9	529.1	529.1	537.5	550.1
25°	482.9	482.9	482.9	478.7	478.7	482.9	487.1	487.1	482.9	487.1	491.3
27.5°	436.7	440.9	440.9	445.1	445.1	449.3	449.3	449.3	449.3	453.5	457.7
30°	419.9	419.9	424.1	424.1	424.1	428.3	432.5	432.5	432.5	436.7	445.1
32.5°	403.1	407.3	411.5	415.7	419.9	424.1	424.1	428.3	428.3	432.5	436.7
35°	356.9	352.7	352.7	348.5	344.3	344.3	344.3	344.3	340.1	344.3	344.3
37.5°	319.1	319.1	319.1	314.9	314.9	319.1	319.1	319.1	319.1	323.3	323.3
40°	302.3	302.3	302.3	302.3	302.3	302.3	302.3	306.5	306.5	310.7	314.9
42.5°	289.7	289.7	289.7	289.7	289.7	293.9	293.9	293.9	293.9	298.1	298.1
45°	277.1	277.1	277.1	277.1	277.1	277.1	277.1	281.3	281.3	285.5	289.7
47.5°	264.5	264.5	264.5	264.5	264.5	268.7	272.9	272.9	272.9	277.1	277.1
50°	256.1	256.1	256.1	256.1	256.1	260.3	260.3	264.5	264.5	268.7	272.9
52.5°	247.7	247.7	247.7	247.7	247.7	251.9	251.9	256.1	256.1	260.3	264.5
55°	243.5	243.5	243.5	239.3	239.3	243.5	243.5	247.7	247.7	251.9	251.9
57.5°	230.9	230.9	230.9	230.9	230.9	230.9	230.9	235.1	235.1	239.3	243.5
60°	226.7	226.7	222.5	222.5	218.3	222.5	222.5	226.7	226.7	230.9	230.9
62.5°	214.1	214.1	214.1	210.0	210.0	214.1	214.1	214.1	214.1	218.3	222.5
65°	201.6	201.6	201.6	197.4	197.4	201.6	201.6	201.6	201.6	205.8	210.0
67.5°	189.0	189.0	189.0	184.8	184.8	184.8	184.8	189.0	189.0	193.2	197.4
70°	176.4	176.4	176.4	172.2	172.2	172.2	168.0	172.2	176.4	180.6	180.6
72.5°	163.8	163.8	163.8	159.6	159.6	159.6	155.4	159.6	159.6	163.8	163.8
75°	142.8	142.8	142.8	142.8	142.8	142.8	138.6	138.6	138.6	142.8	142.8
77.5°	130.2	130.2	130.2	126.0	126.0	126.0	121.8	121.8	121.8	126.0	126.0
80°	109.2	109.2	109.2	105.0	105.0	105.0	100.8	100.8	100.8	105.0	105.0
82.5°	88.2	88.2	88.2	84.0	84.0	84.0	79.8	79.8	79.8	84.0	84.0
85°	71.4	71.4	71.4	71.4	71.4	71.4	67.2	67.2	67.2	71.4	75.6
87.5°	33.6	33.6	37.8	37.8	37.8	37.8	33.6	33.6	29.4	29.4	33.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017
 CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3
2.5°	2750.3	2758.7	2779.7	2796.5	2817.5	2834.3	2846.9	2863.7	2876.3	2888.9	2897.3
5°	2368.2	2372.4	2393.4	2414.4	2431.2	2452.2	2481.6	2511.0	2540.4	2569.8	2590.8
7.5°	1843.4	1860.2	1885.4	1914.7	1939.9	1965.1	1994.5	2028.1	2057.5	2086.9	2116.3
10°	1436.1	1452.9	1478.0	1503.2	1524.2	1549.4	1583.0	1616.6	1650.2	1683.8	1717.4
12.5°	1205.1	1226.1	1255.5	1284.9	1310.1	1339.5	1381.5	1419.3	1461.3	1499.0	1541.0
15°	1016.2	1041.4	1079.1	1121.1	1158.9	1196.7	1238.7	1280.7	1318.5	1360.5	1402.5
17.5°	835.6	860.8	894.4	932.2	965.8	999.4	1049.8	1095.9	1146.3	1192.5	1238.7
20°	671.8	684.4	718.0	751.6	785.2	818.8	856.6	894.4	932.2	970.0	1028.8
22.5°	558.5	566.9	583.7	596.3	613.1	625.7	663.4	701.2	734.8	772.6	827.2
25°	491.3	495.5	508.1	516.5	529.1	537.5	562.7	583.7	608.9	629.9	680.2
27.5°	457.7	461.9	466.1	470.3	474.5	478.7	495.5	512.3	524.9	541.7	587.9
30°	449.3	453.5	466.1	474.5	487.1	495.5	503.9	512.3	520.7	529.1	558.5
32.5°	440.9	445.1	445.1	440.9	440.9	436.7	445.1	449.3	457.7	461.9	487.1
35°	348.5	348.5	352.7	356.9	361.1	365.3	377.9	386.3	398.9	407.3	428.3
37.5°	327.5	327.5	331.7	340.1	344.3	348.5	356.9	365.3	373.7	382.1	403.1
40°	314.9	319.1	323.3	327.5	331.7	335.9	344.3	348.5	356.9	361.1	377.9
42.5°	302.3	302.3	306.5	314.9	319.1	323.3	331.7	335.9	344.3	348.5	365.3
45°	293.9	298.1	302.3	306.5	306.5	310.7	319.1	327.5	331.7	340.1	356.9
47.5°	281.3	281.3	289.7	293.9	302.3	306.5	314.9	319.1	327.5	331.7	348.5
50°	272.9	277.1	285.5	289.7	298.1	302.3	314.9	323.3	335.9	344.3	352.7
52.5°	264.5	268.7	277.1	281.3	289.7	293.9	310.7	327.5	340.1	356.9	356.9
55°	256.1	256.1	264.5	277.1	285.5	293.9	302.3	314.9	323.3	331.7	331.7
57.5°	243.5	247.7	256.1	268.7	277.1	285.5	293.9	302.3	306.5	314.9	310.7
60°	235.1	235.1	247.7	260.3	272.9	285.5	285.5	285.5	281.3	281.3	281.3
62.5°	222.5	226.7	243.5	264.5	281.3	298.1	285.5	272.9	260.3	247.7	251.9
65°	214.1	218.3	226.7	239.3	247.7	256.1	247.7	243.5	235.1	226.7	230.9
67.5°	197.4	201.6	205.8	205.8	210.0	210.0	210.0	210.0	210.0	210.0	214.1
70°	184.8	184.8	184.8	189.0	189.0	189.0	189.0	189.0	189.0	189.0	193.2
72.5°	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0	168.0	172.2
75°	147.0	147.0	147.0	147.0	147.0	147.0	147.0	147.0	147.0	147.0	151.2
77.5°	130.2	130.2	130.2	130.2	130.2	130.2	130.2	130.2	126.0	126.0	130.2
80°	109.2	109.2	109.2	109.2	105.0	105.0	105.0	105.0	105.0	105.0	109.2
82.5°	88.2	88.2	88.2	88.2	84.0	84.0	84.0	84.0	79.8	79.8	84.0
85°	79.8	84.0	84.0	88.2	88.2	88.2	84.0	79.8	75.6	71.4	71.4
87.5°	33.6	33.6	33.6	33.6	29.4	29.4	29.4	29.4	29.4	29.4	29.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3
2.5°	2909.9	2918.3	2926.7	2939.3	2956.1	2968.7	2981.3	3006.5	3035.9	3061.1	3086.3
5°	2611.8	2632.8	2653.8	2679.0	2704.2	2725.2	2750.3	2800.7	2851.1	2897.3	2947.7
7.5°	2141.5	2170.9	2196.1	2238.1	2275.9	2317.8	2355.6	2418.6	2477.4	2540.4	2599.2
10°	1751.0	1784.6	1818.2	1872.8	1931.5	1986.1	2040.7	2091.1	2145.7	2196.1	2246.5
12.5°	1583.0	1620.8	1662.8	1696.4	1734.2	1767.8	1801.4	1860.2	1918.9	1977.7	2036.5
15°	1444.5	1486.4	1528.4	1570.4	1608.2	1650.2	1688.0	1738.4	1793.0	1843.4	1893.7
17.5°	1284.9	1326.9	1373.1	1419.3	1465.5	1511.6	1557.8	1629.2	1700.6	1767.8	1839.2
20°	1083.3	1142.1	1196.7	1259.7	1322.7	1385.7	1448.7	1524.2	1599.8	1671.2	1746.8
22.5°	881.8	936.4	991.0	1066.5	1142.1	1213.5	1289.1	1389.9	1486.4	1587.2	1683.8
25°	734.8	785.2	835.6	919.6	999.4	1083.3	1163.1	1284.9	1402.5	1524.2	1641.8
27.5°	634.0	680.2	726.4	814.6	902.8	986.8	1074.9	1209.3	1339.5	1473.8	1604.0
30°	587.9	617.3	646.6	730.6	814.6	894.4	978.4	1108.5	1238.7	1368.9	1499.0
32.5°	512.3	537.5	562.7	638.2	713.8	785.2	860.8	995.2	1125.3	1259.7	1389.9
35°	453.5	474.5	495.5	566.9	634.0	705.4	772.6	907.0	1041.4	1175.7	1310.1
37.5°	419.9	440.9	457.7	520.7	587.9	650.8	713.8	848.2	978.4	1112.7	1242.9
40°	394.7	407.3	424.1	487.1	545.9	608.9	667.6	789.4	915.4	1037.2	1158.9
42.5°	377.9	394.7	407.3	461.9	520.7	575.3	629.9	747.4	865.0	978.4	1095.9
45°	373.7	390.5	407.3	453.5	499.7	541.7	587.9	701.2	814.6	928.0	1041.4
47.5°	365.3	377.9	394.7	432.5	466.1	503.9	537.5	650.8	764.2	873.4	986.8
50°	361.1	365.3	373.7	407.3	440.9	474.5	508.1	621.5	734.8	848.2	961.6
52.5°	356.9	356.9	356.9	386.3	415.7	440.9	470.3	583.7	701.2	814.6	928.0
55°	331.7	327.5	327.5	356.9	382.1	411.5	436.7	550.1	663.4	772.6	886.0
57.5°	306.5	302.3	298.1	323.3	348.5	373.7	398.9	512.3	629.9	743.2	856.6
60°	281.3	277.1	277.1	302.3	323.3	348.5	369.5	487.1	600.5	718.0	831.4
62.5°	251.9	256.1	256.1	277.1	302.3	323.3	344.3	461.9	583.7	701.2	818.8
65°	230.9	235.1	235.1	260.3	285.5	310.7	335.9	449.3	566.9	680.2	793.6
67.5°	214.1	218.3	218.3	247.7	272.9	302.3	327.5	428.3	533.3	634.0	734.8
70°	197.4	197.4	201.6	230.9	260.3	289.7	319.1	407.3	495.5	579.5	667.6
72.5°	176.4	180.6	184.8	214.1	239.3	268.7	293.9	373.7	453.5	533.3	613.1
75°	155.4	159.6	163.8	189.0	214.1	239.3	264.5	340.1	411.5	487.1	558.5
77.5°	138.6	142.8	147.0	168.0	189.0	210.0	230.9	285.5	344.3	398.9	453.5
80°	113.4	113.4	117.6	134.4	151.2	163.8	180.6	218.3	256.1	289.7	327.5
82.5°	84.0	88.2	88.2	100.8	109.2	121.8	130.2	151.2	168.0	189.0	205.8
85°	71.4	67.2	67.2	75.6	79.8	88.2	92.4	105.0	113.4	126.0	134.4
87.5°	29.4	25.2	25.2	29.4	37.8	42.0	46.2	46.2	50.4	50.4	50.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3
2.5°	3098.9	3107.3	3119.9	3128.3	3149.3	3166.0	3187.0	3203.8	3216.4	3237.4	3229.0
5°	2985.5	3023.3	3061.1	3098.9	3128.3	3157.6	3182.8	3212.2	3245.8	3308.8	3325.6
7.5°	2649.6	2700.0	2746.1	2796.5	2855.3	2914.1	2972.9	3031.7	3086.3	3166.0	3216.4
10°	2317.8	2389.2	2456.4	2527.8	2582.4	2637.0	2687.4	2741.9	2817.5	2897.3	2989.7
12.5°	2107.9	2179.3	2250.7	2322.0	2401.8	2477.4	2557.2	2632.8	2704.2	2767.1	2872.1
15°	1969.3	2049.1	2124.7	2200.3	2296.9	2389.2	2485.8	2578.2	2683.2	2767.1	2838.5
17.5°	1935.7	2032.3	2124.7	2221.3	2322.0	2422.8	2523.6	2624.4	2729.4	2855.3	2947.7
20°	1877.0	2007.1	2137.3	2267.5	2397.6	2523.6	2653.8	2779.7	2918.3	3069.5	3111.5
22.5°	1843.4	1998.7	2158.3	2313.6	2490.0	2670.6	2846.9	3023.3	3170.2	3283.6	3409.6
25°	1839.2	2032.3	2229.7	2422.8	2645.4	2863.7	3086.3	3304.6	3493.6	3606.9	3707.7
27.5°	1835.0	2070.1	2301.1	2532.0	2804.9	3073.7	3346.6	3615.3	3791.7	3955.5	4039.4
30°	1784.6	2065.9	2351.4	2632.8	2939.3	3245.8	3552.4	3858.9	4039.4	4152.8	4194.8
32.5°	1721.6	2053.3	2385.0	2716.8	3065.3	3413.8	3758.1	4106.6	4249.4	4346.0	4312.4
35°	1671.2	2036.5	2397.6	2758.7	3128.3	3502.0	3871.5	4241.0	4446.7	4581.1	4526.5
37.5°	1625.0	2007.1	2389.2	2771.3	3203.8	3636.3	4068.8	4501.3	4698.7	4841.4	4778.5
40°	1570.4	1977.7	2389.2	2796.5	3292.0	3783.3	4278.8	4770.1	5026.2	5148.0	5051.4
42.5°	1524.2	1948.3	2376.6	2800.7	3329.8	3858.9	4388.0	4917.0	5202.6	5374.7	5253.0
45°	1465.5	1889.6	2309.5	2733.5	3317.2	3900.9	4480.3	5064.0	5395.7	5530.1	5362.1
47.5°	1402.5	1822.4	2238.1	2653.8	3275.2	3896.7	4518.1	5139.6	5446.1	5605.7	5450.3
50°	1381.5	1801.4	2217.1	2637.0	3308.8	3984.9	4656.7	5328.5	5551.1	5681.2	5475.5
52.5°	1377.3	1822.4	2271.7	2716.8	3392.8	4064.6	4740.7	5412.5	5593.1	5731.6	5546.9
55°	1364.7	1847.6	2326.2	2804.9	3510.4	4220.0	4925.4	5630.9	5811.4	5912.2	5773.6
57.5°	1377.3	1897.9	2414.4	2935.1	3661.5	4388.0	5114.4	5840.8	6059.2	6130.5	6101.1
60°	1385.7	1939.9	2490.0	3044.3	3753.9	4463.5	5173.2	5882.8	6109.5	6285.9	6319.5
62.5°	1364.7	1910.5	2452.2	2998.1	3640.5	4283.0	4925.4	5567.9	5941.6	6201.9	6353.1
65°	1301.7	1805.6	2313.6	2817.5	3409.6	4005.8	4597.9	5190.0	5584.7	5971.0	6092.8
67.5°	1163.1	1591.4	2019.7	2448.0	2964.5	3481.0	3993.3	4509.7	5005.2	5378.9	5546.9
70°	1007.8	1343.7	1683.8	2019.7	2490.0	2960.3	3430.6	3900.9	4337.6	4749.1	4908.6
72.5°	877.6	1137.9	1402.5	1662.8	1998.7	2330.4	2666.4	2998.1	3514.6	3926.1	4081.4
75°	747.4	936.4	1121.1	1310.1	1541.0	1772.0	1998.7	2229.7	2595.0	2964.5	3119.9
77.5°	575.3	701.2	823.0	944.8	1104.3	1259.7	1419.3	1574.6	1830.8	2107.9	2187.7
80°	398.9	470.3	537.5	608.9	734.8	860.8	986.8	1112.7	1280.7	1436.1	1557.8
82.5°	247.7	293.9	335.9	377.9	478.7	579.5	676.0	776.8	844.0	852.4	974.2
85°	159.6	189.0	214.1	239.3	298.1	361.1	419.9	478.7	428.3	398.9	474.5
87.5°	63.0	79.8	92.4	105.0	100.8	96.6	92.4	88.2	75.6	67.2	84.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017
 CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3
2.5°	3237.4	3250.0	3262.6	3271.0	3283.6	3287.8	3292.0	3292.0	3296.2	3300.4	3308.8
5°	3392.8	3418.0	3443.2	3464.2	3489.4	3510.4	3527.2	3548.2	3565.0	3565.0	3560.8
7.5°	3262.6	3325.6	3388.6	3451.6	3514.6	3560.8	3602.7	3648.9	3690.9	3699.3	3707.7
10°	3090.5	3157.6	3220.6	3287.8	3350.8	3422.2	3489.4	3556.6	3627.9	3640.5	3657.3
12.5°	2930.9	3010.7	3090.5	3166.0	3245.8	3296.2	3346.6	3392.8	3443.2	3476.8	3510.4
15°	2926.7	2993.9	3061.1	3124.1	3191.2	3220.6	3250.0	3275.2	3304.6	3304.6	3308.8
17.5°	3023.3	3065.3	3107.3	3145.1	3187.0	3191.2	3199.6	3203.8	3208.0	3195.4	3182.8
20°	3212.2	3229.0	3245.8	3262.6	3279.4	3250.0	3224.8	3195.4	3166.0	3132.5	3103.1
22.5°	3489.4	3451.6	3413.8	3376.0	3338.2	3287.8	3233.2	3182.8	3128.3	3086.3	3044.3
25°	3749.7	3703.5	3657.3	3611.1	3565.0	3455.8	3346.6	3233.2	3124.1	3077.9	3031.7
27.5°	4098.2	4026.8	3955.5	3884.1	3812.7	3665.7	3518.8	3371.8	3224.8	3145.1	3069.5
30°	4182.2	4102.4	4022.6	3938.7	3858.9	3716.1	3577.5	3434.8	3292.0	3199.6	3111.5
32.5°	4304.0	4211.6	4119.2	4026.8	3934.5	3795.9	3657.3	3514.6	3376.0	3292.0	3203.8
35°	4505.5	4400.6	4295.6	4186.4	4081.4	3938.7	3800.1	3657.3	3514.6	3418.0	3325.6
37.5°	4677.7	4555.9	4434.1	4312.4	4190.6	4064.6	3934.5	3808.5	3678.3	3581.7	3489.4
40°	4870.8	4736.5	4602.1	4471.9	4337.6	4220.0	4102.4	3980.7	3863.1	3787.5	3711.9
42.5°	5038.8	4875.0	4715.5	4555.9	4392.2	4312.4	4236.8	4157.0	4077.2	4039.4	3997.4
45°	5156.4	5005.2	4849.8	4698.7	4547.5	4488.7	4429.9	4371.2	4312.4	4350.2	4388.0
47.5°	5206.8	5085.0	4967.4	4849.8	4728.1	4749.1	4770.1	4786.9	4807.9	4858.2	4912.8
50°	5253.0	5185.8	5114.4	5047.2	4975.8	5055.6	5131.2	5211.0	5290.7	5395.7	5500.7
52.5°	5345.3	5307.5	5273.9	5236.2	5198.4	5336.9	5475.5	5614.1	5752.6	5870.2	5987.8
55°	5622.5	5593.1	5563.7	5530.1	5500.7	5698.0	5891.2	6088.6	6285.9	6407.7	6529.4
57.5°	6004.6	5987.8	5966.8	5950.0	5929.0	6122.1	6311.1	6500.1	6693.2	6810.8	6932.6
60°	6294.3	6298.5	6298.5	6302.7	6302.7	6449.7	6596.6	6747.8	6894.8	6995.5	7100.5
62.5°	6449.7	6441.3	6432.9	6424.5	6416.1	6537.8	6659.6	6781.4	6903.2	6978.7	7054.3
65°	6281.7	6327.9	6374.1	6420.3	6466.5	6483.3	6495.9	6512.7	6525.2	6571.4	6617.6
67.5°	5719.0	5811.4	5899.6	5992.0	6080.2	6017.2	5958.4	5895.4	5832.4	5845.0	5853.4
70°	5093.4	5198.4	5307.5	5412.5	5517.5	5370.5	5223.6	5072.4	4925.4	4875.0	4824.7
72.5°	4295.6	4388.0	4484.5	4576.9	4669.3	4488.7	4312.4	4131.8	3951.3	3863.1	3774.9
75°	3283.6	3392.8	3506.2	3615.3	3724.5	3523.0	3317.2	3115.7	2909.9	2851.1	2796.5
77.5°	2393.4	2523.6	2653.8	2783.9	2914.1	2733.5	2553.0	2368.2	2187.7	2154.1	2120.5
80°	1742.6	1843.4	1939.9	2040.7	2137.3	2032.3	1927.3	1822.4	1717.4	1713.2	1709.0
82.5°	1175.7	1263.9	1347.9	1436.1	1520.0	1478.0	1440.3	1398.3	1356.3	1398.3	1444.5
85°	604.7	726.4	852.4	974.2	1095.9	1083.3	1074.9	1062.3	1049.8	1104.3	1154.7
87.5°	121.8	226.7	331.7	432.5	537.5	512.3	487.1	457.7	432.5	449.3	461.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3
2.5°	3313.0	3317.2	3317.2	3317.2	3317.2	3317.2	3308.8	3304.6	3296.2	3287.8	3275.2
5°	3560.8	3556.6	3539.8	3523.0	3502.0	3485.2	3472.6	3455.8	3443.2	3426.4	3401.2
7.5°	3716.1	3724.5	3695.1	3669.9	3640.5	3611.1	3581.7	3552.4	3523.0	3493.6	3434.8
10°	3669.9	3682.5	3665.7	3648.9	3627.9	3611.1	3577.5	3539.8	3506.2	3468.4	3397.0
12.5°	3539.8	3573.3	3565.0	3556.6	3548.2	3539.8	3518.8	3493.6	3472.6	3447.4	3367.6
15°	3308.8	3308.8	3313.0	3317.2	3317.2	3321.4	3325.6	3329.8	3334.0	3338.2	3292.0
17.5°	3170.2	3157.6	3157.6	3157.6	3157.6	3157.6	3174.4	3195.4	3212.2	3229.0	3216.4
20°	3069.5	3040.1	3035.9	3035.9	3031.7	3027.5	3056.9	3090.5	3119.9	3149.3	3166.0
22.5°	3002.3	2960.3	2956.1	2951.9	2947.7	2943.5	2981.3	3019.1	3056.9	3094.7	3153.4
25°	2985.5	2939.3	2943.5	2947.7	2947.7	2951.9	2981.3	3010.7	3040.1	3069.5	3170.2
27.5°	2989.7	2914.1	2918.3	2922.5	2922.5	2926.7	2972.9	3014.9	3061.1	3103.1	3229.0
30°	3019.1	2930.9	2922.5	2914.1	2905.7	2897.3	2960.3	3023.3	3086.3	3149.3	3245.8
32.5°	3119.9	3035.9	3014.9	2993.9	2972.9	2951.9	3027.5	3098.9	3174.4	3245.8	3325.6
35°	3229.0	3136.7	3128.3	3119.9	3107.3	3098.9	3166.0	3237.4	3304.6	3371.8	3443.2
37.5°	3392.8	3300.4	3292.0	3279.4	3271.0	3258.4	3334.0	3405.4	3481.0	3552.4	3615.3
40°	3636.3	3560.8	3556.6	3556.6	3552.4	3548.2	3606.9	3669.9	3728.7	3787.5	3829.5
42.5°	3959.7	3921.9	3934.5	3951.3	3963.9	3976.5	4022.6	4073.0	4119.2	4165.4	4152.8
45°	4425.7	4463.5	4467.7	4471.9	4476.1	4480.3	4492.9	4509.7	4522.3	4534.9	4484.5
47.5°	4963.2	5013.6	5038.8	5064.0	5085.0	5110.2	5093.4	5072.4	5055.6	5034.6	4908.6
50°	5601.5	5706.4	5702.2	5698.0	5689.6	5685.4	5651.9	5618.3	5580.5	5546.9	5362.1
52.5°	6105.3	6222.9	6243.9	6264.9	6285.9	6306.9	6243.9	6180.9	6113.7	6050.8	5819.8
55°	6647.0	6768.8	6773.0	6777.2	6777.2	6781.4	6693.2	6605.0	6512.7	6424.5	6185.1
57.5°	7050.1	7167.7	7155.1	7146.7	7134.1	7121.5	7016.5	6911.6	6806.6	6701.6	6462.3
60°	7201.3	7302.1	7276.9	7251.7	7222.3	7197.1	7117.3	7037.5	6953.5	6873.8	6642.8
62.5°	7129.9	7205.5	7167.7	7134.1	7096.3	7058.5	6957.7	6852.8	6752.0	6647.0	6479.1
65°	6659.6	6705.8	6655.4	6609.2	6563.0	6512.7	6428.7	6344.7	6256.5	6172.5	6059.2
67.5°	5866.0	5874.4	5870.2	5866.0	5861.8	5857.6	5735.8	5614.1	5488.1	5366.3	5357.9
70°	4778.5	4728.1	4736.5	4749.1	4757.5	4765.9	4673.5	4585.3	4492.9	4400.6	4442.5
72.5°	3686.7	3598.5	3619.5	3644.7	3665.7	3686.7	3611.1	3539.8	3464.2	3388.6	3447.4
75°	2737.7	2683.2	2704.2	2729.4	2750.3	2771.3	2741.9	2712.6	2679.0	2649.6	2704.2
77.5°	2086.9	2053.3	2057.5	2057.5	2061.7	2061.7	2065.9	2074.3	2078.5	2082.7	2141.5
80°	1700.6	1696.4	1692.2	1688.0	1679.6	1675.4	1717.4	1759.4	1801.4	1843.4	1872.8
82.5°	1486.4	1528.4	1503.2	1482.2	1457.1	1431.9	1469.7	1507.4	1545.2	1583.0	1570.4
85°	1209.3	1259.7	1213.5	1167.3	1116.9	1070.7	1104.3	1133.7	1167.3	1196.7	1179.9
87.5°	478.7	491.3	415.7	344.3	268.7	193.2	306.5	415.7	529.1	638.2	655.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3	3023.3
2.5°	3262.6	3245.8	3233.2	3229.0	3220.6	3216.4	3208.0	3199.6	3187.0	3178.6	3166.0
5°	3371.8	3346.6	3317.2	3275.2	3237.4	3195.4	3153.4	3115.7	3077.9	3035.9	2998.1
7.5°	3376.0	3317.2	3258.4	3203.8	3145.1	3090.5	3031.7	2981.3	2926.7	2872.1	2821.7
10°	3329.8	3258.4	3187.0	3115.7	3048.5	2977.1	2905.7	2846.9	2783.9	2721.0	2662.2
12.5°	3292.0	3212.2	3132.5	3048.5	2968.7	2884.7	2800.7	2741.9	2683.2	2624.4	2565.6
15°	3245.8	3195.4	3149.3	3073.7	2998.1	2922.5	2846.9	2767.1	2691.6	2611.8	2532.0
17.5°	3208.0	3195.4	3182.8	3132.5	3082.1	3027.5	2977.1	2897.3	2817.5	2733.5	2653.8
20°	3187.0	3203.8	3220.6	3195.4	3170.2	3140.9	3115.7	3056.9	2998.1	2935.1	2876.3
22.5°	3212.2	3275.2	3334.0	3338.2	3346.6	3350.8	3355.0	3300.4	3245.8	3187.0	3132.5
25°	3271.0	3371.8	3472.6	3527.2	3581.7	3640.5	3695.1	3661.5	3627.9	3594.3	3560.8
27.5°	3350.8	3476.8	3602.7	3682.5	3758.1	3837.9	3917.7	3913.5	3909.3	3900.9	3896.7
30°	3338.2	3434.8	3531.4	3627.9	3724.5	3821.1	3917.7	3968.1	4014.2	4064.6	4115.0
32.5°	3409.6	3489.4	3573.3	3674.1	3774.9	3879.9	3980.7	4085.6	4186.4	4291.4	4396.4
35°	3518.8	3590.1	3665.7	3774.9	3888.3	3997.4	4110.8	4236.8	4367.0	4497.1	4623.1
37.5°	3682.5	3745.5	3812.7	3905.1	4001.6	4094.0	4190.6	4375.4	4560.1	4749.1	4933.8
40°	3871.5	3913.5	3955.5	4043.6	4131.8	4220.0	4308.2	4539.1	4770.1	5001.0	5232.0
42.5°	4144.4	4131.8	4119.2	4190.6	4266.2	4337.6	4413.2	4623.1	4833.1	5043.0	5253.0
45°	4434.1	4383.8	4333.4	4367.0	4404.8	4438.3	4476.1	4690.3	4904.4	5122.8	5336.9
47.5°	4782.7	4656.7	4530.7	4501.3	4471.9	4438.3	4409.0	4639.9	4870.8	5106.0	5336.9
50°	5177.4	4988.4	4803.7	4728.1	4648.3	4572.7	4492.9	4681.9	4875.0	5068.2	5257.1
52.5°	5588.9	5353.7	5122.8	5005.2	4887.6	4765.9	4648.3	4807.9	4971.6	5135.4	5294.9
55°	5941.6	5702.2	5458.7	5320.1	5181.6	5043.0	4904.4	5064.0	5223.6	5383.1	5542.7
57.5°	6222.9	5983.6	5744.2	5614.1	5479.7	5349.5	5215.2	5366.3	5521.7	5677.0	5828.2
60°	6416.1	6185.1	5954.2	5828.2	5702.2	5576.3	5450.3	5630.9	5811.4	5996.2	6176.7
62.5°	6315.3	6147.3	5979.4	5924.8	5870.2	5811.4	5756.8	5929.0	6096.9	6269.1	6441.3
65°	5945.8	5832.4	5719.0	5773.6	5832.4	5887.0	5945.8	6059.2	6172.5	6290.1	6403.5
67.5°	5345.3	5336.9	5324.3	5446.1	5567.9	5693.8	5815.6	5891.2	5962.6	6038.2	6113.7
70°	4484.5	4530.7	4572.7	4782.7	4992.6	5202.6	5412.5	5441.9	5471.3	5500.7	5530.1
72.5°	3510.4	3569.2	3632.1	3909.3	4182.2	4459.3	4736.5	4719.7	4702.9	4681.9	4665.1
75°	2762.9	2817.5	2876.3	3132.5	3388.6	3644.7	3900.9	3829.5	3762.3	3690.9	3619.5
77.5°	2204.5	2263.3	2326.2	2565.6	2804.9	3048.5	3287.8	3115.7	2943.5	2771.3	2599.2
80°	1897.9	1927.3	1952.5	2116.3	2275.9	2439.6	2603.4	2427.0	2246.5	2065.9	1889.6
82.5°	1557.8	1541.0	1528.4	1625.0	1721.6	1818.2	1914.7	1746.8	1578.8	1406.7	1238.7
85°	1163.1	1146.3	1129.5	1179.9	1230.3	1284.9	1335.3	1142.1	949.0	751.6	558.5
87.5°	676.0	692.8	709.6	764.2	818.8	877.6	932.2	734.8	537.5	335.9	138.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P676017
 CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	3023.3	3023.3
2.5°	3140.9	3119.9
5°	2968.7	2939.3
7.5°	2779.7	2741.9
10°	2607.6	2557.2
12.5°	2498.4	2435.4
15°	2456.4	2380.8
17.5°	2582.4	2511.0
20°	2775.5	2679.0
22.5°	3010.7	2893.1
25°	3418.0	3275.2
27.5°	3749.7	3602.7
30°	3955.5	3795.9
32.5°	4182.2	3972.3
35°	4417.3	4215.8
37.5°	4702.9	4476.1
40°	4996.8	4761.7
42.5°	5097.6	4946.4
45°	5194.2	5051.4
47.5°	5215.2	5097.6
50°	5236.2	5219.4
52.5°	5294.9	5290.7
55°	5546.9	5551.1
57.5°	5857.6	5882.8
60°	6143.1	6113.7
62.5°	6290.1	6138.9
65°	6189.3	5979.4
67.5°	5887.0	5660.3
70°	5223.6	4917.0
72.5°	4396.4	4127.6
75°	3388.6	3161.8
77.5°	2410.2	2221.3
80°	1696.4	1507.4
82.5°	1087.5	936.4
85°	491.3	428.3
87.5°	138.6	134.4
90°	0.0	0.0
92.5°	0.0	0.0
95°	0.0	0.0
97.5°	0.0	0.0
100°	0.0	0.0
102.5°	0.0	0.0
105°	0.0	0.0
107.5°	0.0	0.0
110°	0.0	0.0

REPORT NUMBER: P676017

CATALOG NUMBER: CCW-SA-2D-760-U-SLR

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	0.0	0.0
115°	0.0	0.0
117.5°	0.0	0.0
120°	0.0	0.0
122.5°	0.0	0.0
125°	0.0	0.0
127.5°	0.0	0.0
130°	0.0	0.0
132.5°	0.0	0.0
135°	0.0	0.0
137.5°	0.0	0.0
140°	0.0	0.0
142.5°	0.0	0.0
145°	0.0	0.0
147.5°	0.0	0.0
150°	0.0	0.0
152.5°	0.0	0.0
155°	0.0	0.0
157.5°	0.0	0.0
160°	0.0	0.0
162.5°	0.0	0.0
165°	0.0	0.0
167.5°	0.0	0.0
170°	0.0	0.0
172.5°	0.0	0.0
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)